

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331260-840

Luminaire Tested: **SA2XXDIP-C290D725U840-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331260-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXDIP-C290D725U840-4F0-1E-UDD-A4  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 725 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4177.1 lumens  
Efficiency: N/A  
Efficacy: 133.9 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 31.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331260-840  
CATALOG NUMBER: SA2XXDIP-C290D725U840-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P331260-840

CATALOG NUMBER: SA2XXDIP-C290D725U840-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39	32				
1	94	90	86	83	84	81	78	75	64	62	60	49	48	47	35	34	34	27				
2	86	79	73	68	77	71	66	62	57	53	50	43	41	39	31	30	29	23				
3	78	69	63	57	70	63	57	52	50	46	43	39	36	34	28	26	25	20				
4	72	62	54	48	64	56	49	44	45	40	37	35	32	29	25	23	22	17				
5	66	55	47	41	59	50	43	38	40	35	32	31	28	25	23	21	19	15				
6	61	49	42	36	55	45	38	33	36	31	28	28	25	22	21	19	17	14				
7	56	44	37	32	50	40	34	29	33	28	24	26	22	20	19	17	15	12				
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	18	15	14	11				
9	48	37	30	25	44	34	27	23	27	23	19	22	18	16	16	14	12	10				
10	45	34	27	22	41	31	25	21	25	21	17	20	17	14	15	13	11	9				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	9637	9637	9637	9637
5°	10804	9700	8596	9700
10°	12381	9621	7438	9621
15°	13697	9444	6572	9444
20°	13490	9256	5991	9256
25°	12162	9002	5624	9002
30°	10051	8600	5354	8600
35°	7324	8180	5164	8180
40°	5851	7685	5056	7685
45°	5112	7108	4914	7108
50°	4808	6551	4818	6551
55°	4428	5987	4687	5987
60°	4059	5383	4492	5383
65°	3698	4844	4294	4844
70°	3356	4319	4008	4319
75°	2982	3737	3550	3737
80°	2566	3087	2854	3087
85°	2297	2297	1704	2297



TEST NUMBER: P331260-840

CATALOG NUMBER: SA2XXDIP-C290D725U840-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	56.8	1.4
10°-20°	165.3	4.0
20°-30°	239.9	5.7
30°-40°	253.1	6.1
40°-50°	224.1	5.4
50°-60°	178.8	4.3
60°-70°	121.6	2.9
70°-80°	62.3	1.5
80°-90°	18.7	0.4
90°-100°	164.1	3.9
100°-110°	557.0	13.3
110°-120°	591.7	14.2
120°-130°	487.1	11.7
130°-140°	391.2	9.4
140°-150°	295.6	7.1
150°-160°	207.7	5.0
160°-170°	122.3	2.9
170°-180°	39.8	1.0
0°-30°	462.0	11.1
0°-40°	715.1	17.1
0°-60°	1118.0	26.8
0°-90°	1320.6	31.6
90°-120°	1312.8	31.4
90°-150°	2486.7	59.5
90°-180°	2856.0	68.4
0°-180°	4177.1	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	597	597	597	597	597	
5°	667	598	530	598	667	67
15°	819	565	393	565	819	226
25°	683	505	316	505	683	309
35°	372	415	262	415	372	242
45°	224	311	215	311	224	176
55°	157	213	166	213	157	141
65°	97	127	112	127	97	96
75°	48	60	57	60	48	51
85°	12	12	9	12	12	14
90°	26	1	26	1	26	15
95°	90	28	90	28	90	117
105°	890	96	890	96	890	861
115°	1171	170	1171	170	1171	1146
125°	950	237	950	237	950	858
135°	787	278	787	278	787	611
145°	628	317	628	317	628	399
155°	528	361	528	361	528	246
165°	463	393	463	393	463	132
175°	418	410	418	410	418	41
180°	410	410	410	410	410	



TEST NUMBER: P331260-840

CATALOG NUMBER: SA2XXDIP-C290D725U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9
2.5°	624.4	624.6	625.0	622.1	621.7	621.7	619.1	616.9	614.3	610.9	611.3
5°	666.6	669.1	670.0	667.3	663.2	662.8	658.8	652.5	646.4	641.7	638.2
7.5°	717.0	718.0	715.8	712.2	709.1	703.6	696.3	689.2	679.2	670.1	663.4
10°	755.2	756.6	752.7	747.4	743.1	736.6	726.1	715.3	702.3	689.6	679.5
12.5°	784.2	787.6	782.5	781.9	774.5	765.6	753.1	747.6	729.2	711.7	700.7
15°	819.4	819.2	819.7	815.3	809.8	808.4	795.2	780.6	754.8	744.4	726.5
17.5°	809.2	812.7	814.4	814.3	814.2	813.2	809.0	799.9	786.9	770.1	749.5
20°	785.1	789.6	790.3	795.6	798.6	802.4	804.1	801.5	793.6	779.5	761.6
22.5°	747.6	748.9	751.0	759.2	765.7	775.5	780.5	789.1	786.0	779.1	764.2
25°	682.7	680.4	688.4	692.6	707.5	723.1	734.4	746.7	757.7	764.4	760.0
27.5°	604.8	601.4	613.4	624.4	636.4	653.4	670.9	691.6	708.7	730.3	737.7
30°	539.1	541.2	552.6	564.3	582.7	606.5	626.3	648.9	673.6	697.6	714.4
32.5°	468.3	476.2	483.4	501.4	517.6	544.1	573.1	601.5	632.1	659.4	685.4
35°	371.6	380.8	390.9	403.9	426.7	453.0	481.3	519.6	561.4	598.7	629.4
37.5°	312.9	311.3	317.1	326.6	345.0	366.3	398.8	436.6	485.7	529.7	573.1
40°	277.6	276.7	280.7	289.5	303.5	319.1	347.6	380.8	426.5	480.2	531.8
42.5°	253.4	253.9	256.2	262.4	272.0	284.8	306.1	334.4	376.2	426.8	482.2
45°	223.9	225.5	228.0	231.1	236.5	247.1	259.0	279.2	312.3	354.5	409.0
47.5°	202.7	202.8	205.3	207.9	211.2	217.1	226.9	239.5	262.9	297.2	344.2
50°	191.4	189.8	191.6	193.6	197.0	201.2	207.6	219.5	235.1	262.9	302.2
52.5°	177.3	177.4	179.0	179.9	182.9	187.0	192.9	201.2	215.3	237.0	269.2
55°	157.3	158.5	159.5	160.8	163.6	166.5	171.2	176.6	187.6	203.9	227.8
57.5°	138.6	139.0	139.9	142.5	144.2	146.9	151.3	156.3	163.5	175.5	193.5
60°	125.7	125.7	127.5	128.7	131.0	133.7	137.1	142.0	148.5	158.2	172.8
62.5°	114.0	113.8	114.5	116.4	118.2	120.7	124.1	128.3	134.3	143.1	154.9
65°	96.8	96.3	97.8	98.2	100.0	102.5	105.3	109.7	114.5	120.9	131.5
67.5°	80.3	80.9	81.6	82.4	83.4	86.1	88.0	91.0	95.1	100.5	107.6
70°	71.1	71.1	71.1	71.8	73.2	74.5	76.3	78.9	82.8	87.4	93.8
72.5°	60.8	61.6	62.3	61.9	63.6	64.4	66.7	68.1	71.8	74.7	80.4
75°	47.8	47.8	47.8	48.9	49.6	50.2	51.6	53.0	54.8	58.5	61.5
77.5°	35.6	35.5	35.7	36.1	36.8	37.6	38.0	39.2	40.9	42.6	45.1
80°	27.6	28.0	28.2	28.7	28.7	29.1	29.4	31.0	32.1	33.2	34.8
82.5°	21.3	21.4	21.4	21.5	21.7	22.0	22.6	23.1	23.5	24.4	25.7
85°	12.4	12.1	12.1	12.6	12.4	12.4	12.8	13.3	13.3	13.5	14.2
87.5°	10.0	10.0	10.2	10.0	10.0	10.0	9.7	9.8	10.2	10.5	10.5
90°	26.1	26.1	26.1	26.1	26.1	25.2	23.7	25.2	26.1	26.9	26.1
92.5°	43.7	45.0	44.3	46.9	47.6	52.4	59.1	68.9	86.6	102.6	101.2
95°	90.0	89.2	91.6	97.9	108.2	125.5	158.6	206.8	270.7	309.4	274.0
97.5°	177.1	183.8	195.3	214.7	252.5	309.4	394.9	482.6	554.2	528.3	397.9
100°	282.6	296.8	319.7	353.7	419.2	514.7	622.9	720.7	737.3	623.6	429.4
102.5°	497.4	516.5	545.1	603.1	674.3	775.5	854.6	876.8	805.5	626.8	417.5
105°	889.7	900.7	934.6	983.6	1032.6	1058.6	1048.3	959.2	795.0	584.9	393.9
107.5°	1136.4	1151.1	1157.9	1160.6	1154.5	1116.2	1034.1	899.8	725.6	540.1	382.2
110°	1210.9	1211.7	1204.7	1189.6	1155.7	1091.0	990.0	848.6	682.1	518.7	379.7



TEST NUMBER: P331260-840

CATALOG NUMBER: SA2XXDIP-C290D725U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1209.7	1205.5	1192.0	1166.9	1119.7	1045.5	937.5	801.9	651.8	504.7	380.3
115°	1170.7	1163.6	1143.1	1106.7	1050.7	969.4	866.0	744.4	614.2	489.5	383.6
117.5°	1101.1	1095.1	1073.5	1035.1	978.0	901.7	807.9	701.1	590.5	482.0	389.3
120°	1056.2	1048.3	1025.4	988.4	933.1	861.2	777.6	679.6	577.8	477.6	393.1
122.5°	1009.5	1002.9	982.5	946.0	896.5	831.5	752.3	662.7	567.1	475.0	397.6
125°	949.7	943.3	923.6	893.6	847.8	788.6	719.1	637.8	551.8	470.5	404.1
127.5°	897.3	892.2	875.1	847.1	807.1	752.5	686.9	613.4	537.6	467.8	411.0
130°	867.6	861.2	845.5	818.6	779.9	727.8	665.5	597.5	528.2	466.6	416.1
132.5°	836.6	830.9	816.4	789.6	751.5	702.6	645.3	582.4	520.6	466.0	421.1
135°	787.1	783.9	769.7	743.7	709.6	665.5	613.4	561.3	510.0	464.9	427.1
137.5°	738.4	733.7	721.2	698.8	667.8	629.3	587.9	544.4	502.5	464.8	432.4
140°	705.0	700.2	688.3	667.8	642.6	607.8	571.6	533.6	498.2	464.1	434.9
142.5°	671.5	670.6	659.9	641.4	617.3	588.2	557.0	524.8	493.7	464.1	436.9
145°	628.3	626.0	618.1	604.7	585.7	562.9	538.4	512.3	487.9	462.6	438.9
147.5°	592.2	590.8	585.4	574.7	559.1	542.3	523.2	502.7	481.9	459.8	439.6
150°	570.8	570.0	565.2	555.7	543.9	529.7	513.1	495.7	476.8	457.9	438.9
152.5°	552.4	552.3	548.8	540.6	531.3	519.0	504.9	488.8	472.4	454.7	437.7
155°	528.2	529.7	526.5	521.0	512.3	503.6	491.8	479.2	464.1	449.2	435.8
157.5°	507.5	507.5	506.0	501.4	495.2	488.5	478.6	468.0	456.5	443.5	432.1
160°	494.1	494.1	493.4	489.5	483.9	478.4	469.7	461.0	450.8	439.7	430.2
162.5°	481.5	482.2	481.4	478.7	473.2	468.9	461.5	454.0	445.7	436.6	428.4
165°	463.4	464.1	464.1	461.0	457.9	454.7	449.2	443.6	437.4	430.2	424.7
167.5°	446.7	447.6	447.8	446.1	444.6	441.7	438.0	433.7	429.1	424.7	421.1
170°	436.6	438.1	438.9	436.6	435.8	434.1	431.0	428.7	424.7	421.5	419.2
172.5°	428.4	429.3	430.1	429.0	428.2	427.3	424.7	422.9	420.3	417.8	416.7
175°	417.6	419.2	420.0	419.2	419.2	418.4	417.6	416.8	414.4	413.6	412.8
177.5°	411.1	412.4	413.0	413.0	413.0	413.0	412.4	412.4	411.1	410.5	411.1
180°	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5



TEST NUMBER: P331260-840

CATALOG NUMBER: SA2XXDIP-C290D725U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9
2.5°	612.5	611.1	610.2	606.8	603.9	601.0	600.1	600.4	596.3	592.5	590.9
5°	636.4	631.8	627.4	621.3	613.9	605.8	601.8	598.5	590.5	581.8	576.7
7.5°	657.7	651.2	642.8	631.2	620.5	607.8	599.8	592.7	581.0	568.7	561.1
10°	670.8	661.9	651.1	636.8	623.8	608.3	597.6	586.8	573.1	558.4	549.2
12.5°	682.0	669.9	659.3	641.1	625.6	606.3	593.6	578.3	563.9	546.4	537.5
15°	708.6	686.4	666.2	645.5	626.5	599.7	585.4	565.0	546.0	524.4	514.1
17.5°	729.2	704.2	672.5	646.2	624.0	594.2	573.4	549.0	526.4	501.8	487.8
20°	740.9	712.3	678.1	646.9	620.4	586.3	563.6	538.7	512.3	484.5	469.4
22.5°	747.9	717.8	684.0	644.2	613.0	580.0	551.4	523.9	497.3	467.3	451.4
25°	750.1	722.7	686.8	641.9	603.8	566.4	532.0	505.3	473.0	445.0	421.9
27.5°	739.2	719.5	685.1	637.5	593.2	549.5	511.1	481.0	446.9	416.5	393.1
30°	725.8	714.4	680.9	633.2	584.7	537.8	495.5	461.3	427.4	396.7	372.7
32.5°	705.1	702.7	673.2	626.9	575.7	522.9	479.2	444.6	407.0	376.8	354.1
35°	664.4	675.4	656.8	613.0	558.9	501.7	454.4	415.0	376.0	347.1	325.8
37.5°	609.8	637.1	632.3	592.6	535.9	478.7	426.5	385.3	348.1	318.9	298.0
40°	572.1	607.0	612.1	576.9	519.9	460.9	405.6	364.6	328.3	301.6	280.5
42.5°	531.8	572.5	586.3	558.3	502.2	442.1	386.9	344.4	308.4	282.6	263.9
45°	464.1	518.0	543.0	526.9	472.8	411.3	354.5	311.3	278.7	254.4	239.9
47.5°	400.8	459.7	493.3	487.7	440.1	379.2	323.0	281.6	249.8	230.5	217.5
50°	356.1	416.6	457.2	459.1	416.6	356.3	299.8	260.8	231.7	213.6	203.0
52.5°	317.1	375.0	419.2	429.0	390.3	332.4	279.1	240.2	214.6	197.9	188.5
55°	266.3	315.2	364.3	382.2	351.2	296.2	246.8	212.7	188.5	177.1	168.8
57.5°	221.5	262.2	307.5	327.3	308.2	261.1	214.8	185.1	165.6	155.5	149.2
60°	197.7	229.8	270.2	293.9	277.3	235.4	195.0	166.7	150.7	141.8	135.8
62.5°	175.7	204.2	238.3	259.9	251.0	211.4	175.2	150.3	136.4	128.1	123.7
65°	145.0	167.4	193.9	213.8	207.8	177.8	148.1	126.8	115.8	109.2	105.7
67.5°	119.4	135.6	153.9	171.4	166.6	145.3	121.6	104.9	96.7	91.0	88.9
70°	103.2	115.6	131.9	145.9	142.0	124.6	105.7	91.5	84.4	79.6	77.6
72.5°	87.9	98.0	110.5	121.9	119.3	104.7	89.1	78.4	72.8	68.4	66.8
75°	66.3	74.1	81.7	89.3	88.6	77.4	68.2	59.9	55.5	52.1	51.4
77.5°	49.0	53.3	58.5	62.9	61.7	55.2	48.1	43.3	40.2	37.9	37.5
80°	37.4	39.9	43.6	46.8	45.2	42.4	36.7	33.2	31.0	28.7	27.8
82.5°	27.2	29.6	31.8	33.6	32.3	29.8	26.3	23.9	22.5	21.0	20.6
85°	14.2	15.6	16.6	17.0	16.6	14.9	13.3	12.4	11.2	10.5	10.3
87.5°	9.8	8.7	7.9	7.8	6.9	6.6	5.3	4.2	4.4	4.9	4.8
90°	21.3	15.8	11.8	9.5	7.9	6.4	3.1	0.8	3.1	6.4	7.9
92.5°	78.8	53.7	35.9	28.4	23.0	19.6	13.9	9.6	13.9	19.6	23.0
95°	182.4	113.7	77.4	58.4	45.7	38.7	30.8	27.7	30.8	38.7	45.7
97.5°	245.7	150.0	104.3	82.9	68.4	57.7	49.3	45.0	49.3	57.7	68.4
100°	258.9	162.6	120.8	98.7	82.9	70.3	63.1	60.8	63.1	70.3	82.9
102.5°	259.5	174.0	135.3	113.2	96.7	84.1	77.1	75.3	77.1	84.1	96.7
105°	263.7	193.4	156.3	134.2	116.8	105.0	99.5	96.3	99.5	105.0	116.8
107.5°	274.6	213.3	177.3	155.0	137.8	126.9	121.6	119.1	121.6	126.9	137.8
110°	283.4	226.5	191.9	169.0	152.4	142.1	137.3	134.2	137.3	142.1	152.4





TEST NUMBER: P331260-840

CATALOG NUMBER: SA2XXDIP-C290D725U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	292.9	239.2	205.7	182.2	166.2	156.6	151.3	148.0	151.3	156.6	166.2
115°	307.1	258.9	225.0	203.7	187.8	178.4	173.7	169.8	173.7	178.4	187.8
117.5°	322.2	277.1	245.7	223.6	208.4	200.1	195.3	192.2	195.3	200.1	208.4
120°	332.3	289.7	258.9	236.8	221.1	213.9	209.2	206.0	209.2	213.9	221.1
122.5°	341.2	301.7	272.9	250.0	234.3	226.5	221.9	219.3	221.9	226.5	234.3
125°	355.3	319.7	291.2	269.2	253.4	243.9	239.2	236.8	239.2	243.9	253.4
127.5°	368.3	336.5	308.8	286.1	270.9	260.5	253.9	250.7	253.9	260.5	270.9
130°	376.6	346.6	318.9	296.8	281.0	269.9	262.1	258.9	262.1	269.9	281.0
132.5°	384.8	355.4	329.0	306.9	290.5	278.8	270.3	266.5	270.3	278.8	290.5
135°	395.5	367.9	342.6	320.5	302.4	290.5	281.0	277.9	281.0	290.5	302.4
137.5°	403.7	378.0	353.0	332.5	314.5	301.8	292.4	288.6	292.4	301.8	314.5
140°	408.1	383.6	360.0	339.4	322.0	309.4	299.9	296.8	299.9	309.4	322.0
142.5°	411.9	388.1	365.1	345.8	329.0	316.4	307.6	305.0	307.6	316.4	329.0
145°	416.8	394.8	373.3	356.0	340.2	328.4	320.5	317.3	320.5	328.4	340.2
147.5°	419.5	400.1	380.0	364.6	351.4	340.5	333.0	330.6	333.0	340.5	351.4
150°	420.7	402.6	384.5	370.2	358.4	348.1	341.8	339.4	341.8	348.1	358.4
152.5°	421.4	405.2	388.9	375.9	364.7	355.7	349.4	348.3	349.4	355.7	364.7
155°	422.3	408.9	395.5	383.6	375.0	366.3	361.5	360.7	361.5	366.3	375.0
157.5°	422.3	411.6	400.2	390.3	383.3	375.8	371.9	371.2	371.9	375.8	383.3
160°	422.3	412.8	403.3	394.8	388.4	382.0	378.9	378.1	378.9	382.0	388.4
162.5°	421.7	413.5	405.3	398.5	392.8	387.8	384.6	385.1	384.6	387.8	392.8
165°	420.0	414.4	407.4	402.6	398.7	393.9	392.3	393.1	392.3	393.9	398.7
167.5°	418.9	414.2	409.1	406.1	403.2	400.2	398.8	399.8	398.8	400.2	403.2
170°	417.6	413.6	409.7	407.4	405.8	403.3	402.6	404.1	402.6	403.3	405.8
172.5°	415.7	413.0	410.3	408.6	407.7	405.3	405.8	406.7	405.8	405.3	407.7
175°	413.6	412.0	410.5	409.7	409.7	408.1	408.9	409.7	408.9	408.1	409.7
177.5°	412.4	411.1	410.5	410.5	410.5	409.2	409.9	411.1	409.9	409.2	410.5
180°	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5



TEST NUMBER: P331260-840

CATALOG NUMBER: SA2XXDIP-C290D725U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9
2.5°	589.1	587.9	584.1	582.1	578.8	575.6	573.6	574.5	575.2	574.9	574.3
5°	572.1	567.7	561.1	555.4	551.3	543.7	540.5	538.9	537.5	535.9	534.3
7.5°	552.0	545.1	535.6	527.5	519.8	510.3	504.9	501.8	498.5	494.8	491.6
10°	537.8	528.1	518.0	506.5	497.4	488.9	481.3	476.3	471.6	467.3	464.1
12.5°	522.7	511.6	499.1	483.4	473.3	461.1	460.0	451.1	443.9	441.2	437.5
15°	498.8	483.1	467.3	448.7	440.7	429.7	422.8	415.9	409.7	405.4	404.2
17.5°	471.5	451.3	435.6	422.2	409.1	397.8	391.4	386.0	380.8	375.1	374.3
20°	450.8	433.3	416.2	404.5	390.9	379.4	371.6	366.2	361.7	358.3	355.4
22.5°	431.1	412.0	396.3	383.5	370.2	360.9	354.8	349.4	345.8	342.0	339.2
25°	399.6	384.8	367.5	353.0	342.0	336.1	331.0	326.5	324.2	321.6	318.4
27.5°	372.0	355.5	339.4	328.2	318.5	313.3	309.6	306.5	304.4	302.9	301.0
30°	352.6	335.9	323.3	312.3	304.2	298.9	296.6	294.8	292.3	291.3	290.4
32.5°	333.9	318.8	308.0	298.4	290.8	287.3	285.3	283.6	281.7	280.7	278.8
35°	307.4	294.8	284.3	278.9	272.8	269.7	268.2	265.9	264.1	263.2	262.9
37.5°	282.5	271.6	264.6	257.8	255.2	253.4	251.2	249.6	249.0	248.9	248.6
40°	266.3	257.4	251.2	245.7	244.6	241.8	239.9	238.6	238.6	238.8	238.6
42.5°	251.7	243.6	238.1	233.4	232.1	230.5	228.5	228.5	228.8	229.6	228.8
45°	229.4	223.7	219.7	217.5	215.0	213.4	213.1	213.8	214.0	214.3	215.0
47.5°	208.9	205.1	201.6	199.0	197.9	197.7	197.4	198.6	199.8	200.2	201.2
50°	196.8	192.5	189.5	187.8	186.9	186.5	186.9	188.3	189.2	190.4	191.1
52.5°	183.3	180.2	178.1	176.8	176.5	176.8	176.8	178.4	179.9	180.4	180.7
55°	164.5	162.2	161.8	159.7	160.6	160.4	161.5	162.4	163.8	165.2	165.4
57.5°	145.7	143.9	142.7	142.9	143.2	144.2	145.1	146.7	148.1	149.7	149.8
60°	133.3	132.4	131.7	131.7	132.1	133.5	134.6	136.2	137.1	138.1	138.8
62.5°	121.9	121.0	120.3	120.7	121.9	122.7	124.0	124.9	125.8	126.7	127.0
65°	103.9	103.5	104.1	104.6	104.8	105.9	107.6	108.3	109.2	109.7	111.3
67.5°	87.4	87.5	87.4	88.0	89.4	89.6	91.1	92.7	92.9	93.8	94.8
70°	76.1	76.6	77.1	77.6	78.7	79.2	80.3	81.0	81.9	82.6	83.3
72.5°	65.8	65.9	66.4	66.3	67.4	68.3	69.3	70.0	70.9	71.8	72.4
75°	50.7	50.7	51.2	51.4	52.5	53.7	53.4	53.9	54.8	55.7	56.2
77.5°	37.1	36.6	37.1	37.3	37.7	38.6	38.8	39.4	40.5	40.2	40.7
80°	28.2	27.6	28.2	28.5	28.5	29.6	29.6	30.1	30.7	30.1	30.7
82.5°	20.1	19.8	20.3	20.4	20.7	20.8	21.1	21.2	21.9	21.6	21.9
85°	10.1	9.9	10.1	9.9	10.1	10.3	10.3	10.1	10.1	10.5	9.9
87.5°	5.0	5.4	6.0	7.0	7.8	7.8	7.4	7.3	7.0	6.9	7.1
90°	9.5	11.8	15.8	21.3	26.1	26.9	26.1	25.2	23.7	25.2	26.1
92.5°	28.4	35.9	53.7	78.8	101.2	102.6	86.6	68.9	59.1	52.4	47.6
95°	58.4	77.4	113.7	182.4	274.0	309.4	270.7	206.8	158.6	125.5	108.2
97.5°	82.9	104.3	150.0	245.7	397.9	528.3	554.2	482.6	394.9	309.4	252.5
100°	98.7	120.8	162.6	258.9	429.4	623.6	737.3	720.7	622.9	514.7	419.2
102.5°	113.2	135.3	174.0	259.5	417.5	626.8	805.5	876.8	854.6	775.5	674.3
105°	134.2	156.3	193.4	263.7	393.9	584.9	795.0	959.2	1048.3	1058.6	1032.6
107.5°	155.0	177.3	213.3	274.6	382.2	540.1	725.6	899.8	1034.1	1116.2	1154.5
110°	169.0	191.9	226.5	283.4	379.7	518.7	682.1	848.6	990.0	1091.0	1155.7



TEST NUMBER: P331260-840

CATALOG NUMBER: SA2XXDIP-C290D725U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	182.2	205.7	239.2	292.9	380.3	504.7	651.8	801.9	937.5	1045.5	1119.7
115°	203.7	225.0	258.9	307.1	383.6	489.5	614.2	744.4	866.0	969.4	1050.7
117.5°	223.6	245.7	277.1	322.2	389.3	482.0	590.5	701.1	807.9	901.7	978.0
120°	236.8	258.9	289.7	332.3	393.1	477.6	577.8	679.6	777.6	861.2	933.1
122.5°	250.0	272.9	301.7	341.2	397.6	475.0	567.1	662.7	752.3	831.5	896.5
125°	269.2	291.2	319.7	355.3	404.1	470.5	551.8	637.8	719.1	788.6	847.8
127.5°	286.1	308.8	336.5	368.3	411.0	467.8	537.6	613.4	686.9	752.5	807.1
130°	296.8	318.9	346.6	376.6	416.1	466.6	528.2	597.5	665.5	727.8	779.9
132.5°	306.9	329.0	355.4	384.8	421.1	466.0	520.6	582.4	645.3	702.6	751.5
135°	320.5	342.6	367.9	395.5	427.1	464.9	510.0	561.3	613.4	665.5	709.6
137.5°	332.5	353.0	378.0	403.7	432.4	464.8	502.5	544.4	587.9	629.3	667.8
140°	339.4	360.0	383.6	408.1	434.9	464.1	498.2	533.6	571.6	607.8	642.6
142.5°	345.8	365.1	388.1	411.9	436.9	464.1	493.7	524.8	557.0	588.2	617.3
145°	356.0	373.3	394.8	416.8	438.9	462.6	487.9	512.3	538.4	562.9	585.7
147.5°	364.6	380.0	400.1	419.5	439.6	459.8	481.9	502.7	523.2	542.3	559.1
150°	370.2	384.5	402.6	420.7	438.9	457.9	476.8	495.7	513.1	529.7	543.9
152.5°	375.9	388.9	405.2	421.4	437.7	454.7	472.4	488.8	504.9	519.0	531.3
155°	383.6	395.5	408.9	422.3	435.8	449.2	464.1	479.2	491.8	503.6	512.3
157.5°	390.3	400.2	411.6	422.3	432.1	443.5	456.5	468.0	478.6	488.5	495.2
160°	394.8	403.3	412.8	422.3	430.2	439.7	450.8	461.0	469.7	478.4	483.9
162.5°	398.5	405.3	413.5	421.7	428.4	436.6	445.7	454.0	461.5	468.9	473.2
165°	402.6	407.4	414.4	420.0	424.7	430.2	437.4	443.6	449.2	454.7	457.9
167.5°	406.1	409.1	414.2	418.9	421.1	424.7	429.1	433.7	438.0	441.7	444.6
170°	407.4	409.7	413.6	417.6	419.2	421.5	424.7	428.7	431.0	434.1	435.8
172.5°	408.6	410.3	413.0	415.7	416.7	417.8	420.3	422.9	424.7	427.3	428.2
175°	409.7	410.5	412.0	413.6	412.8	413.6	414.4	416.8	417.6	418.4	419.2
177.5°	410.5	410.5	411.1	412.4	411.1	410.5	411.1	412.4	412.4	413.0	413.0
180°	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5



TEST NUMBER: P331260-840

CATALOG NUMBER: SA2XXDIP-C290D725U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9
2.5°	572.5	572.1	572.1	570.5	572.1	572.1	572.5	574.3	574.9	575.2	574.5
5°	531.1	530.4	529.3	530.4	529.3	530.4	531.1	534.3	535.9	537.5	538.9
7.5°	490.1	487.4	487.0	484.2	487.0	487.4	490.1	491.6	494.8	498.5	501.8
10°	460.2	458.4	458.1	453.7	458.1	458.4	460.2	464.1	467.3	471.6	476.3
12.5°	437.5	433.0	433.9	431.4	433.9	433.0	437.5	437.5	441.2	443.9	451.1
15°	398.0	398.0	397.1	393.2	397.1	398.0	398.0	404.2	405.4	409.7	415.9
17.5°	369.7	369.2	367.1	368.2	367.1	369.2	369.7	374.3	375.1	380.8	386.0
20°	352.8	351.4	348.7	348.7	348.7	351.4	352.8	355.4	358.3	361.7	366.2
22.5°	336.9	336.8	333.9	334.8	333.9	336.8	336.9	339.2	342.0	345.8	349.4
25°	318.2	316.4	315.0	315.7	315.0	316.4	318.2	318.4	321.6	324.2	326.5
27.5°	300.4	299.4	299.3	297.5	299.3	299.4	300.4	301.0	302.9	304.4	306.5
30°	290.2	287.9	288.3	287.2	288.3	287.9	290.2	290.4	291.3	292.3	294.8
32.5°	278.4	277.6	277.2	276.2	277.2	277.6	278.4	278.8	280.7	281.7	283.6
35°	262.5	262.7	261.6	262.0	261.6	262.7	262.5	262.9	263.2	264.1	265.9
37.5°	248.4	249.1	248.6	248.7	248.6	249.1	248.4	248.6	248.9	249.0	249.6
40°	239.2	239.2	239.2	239.9	239.2	239.2	239.2	238.6	238.8	238.6	238.6
42.5°	230.5	230.0	229.7	229.6	229.7	230.0	230.5	228.8	229.6	228.8	228.5
45°	215.4	216.1	216.3	215.2	216.3	216.1	215.4	215.0	214.3	214.0	213.8
47.5°	201.8	201.9	201.8	202.8	201.8	201.9	201.8	201.2	200.2	199.8	198.6
50°	192.3	191.8	192.3	191.8	192.3	191.8	192.3	191.1	190.4	189.2	188.3
52.5°	182.2	182.3	182.0	181.9	182.0	182.3	182.2	180.7	180.4	179.9	178.4
55°	166.3	166.7	166.5	166.5	166.5	166.7	166.3	165.4	165.2	163.8	162.4
57.5°	150.0	150.4	150.7	149.7	150.7	150.4	150.0	149.8	149.7	148.1	146.7
60°	138.6	139.7	139.5	139.1	139.5	139.7	138.6	138.8	138.1	137.1	136.2
62.5°	128.1	128.6	128.5	128.4	128.5	128.6	128.1	127.0	126.7	125.8	124.9
65°	112.0	112.4	111.7	112.4	111.7	112.4	112.0	111.3	109.7	109.2	108.3
67.5°	94.5	94.7	95.2	95.5	95.2	94.7	94.5	94.8	93.8	92.9	92.7
70°	83.7	83.5	84.2	84.9	84.2	83.5	83.7	83.3	82.6	81.9	81.0
72.5°	72.3	72.8	72.6	73.1	72.6	72.8	72.3	72.4	71.8	70.9	70.0
75°	55.7	56.5	56.2	56.9	56.2	56.5	55.7	56.2	55.7	54.8	53.9
77.5°	40.3	40.4	40.3	40.7	40.3	40.4	40.3	40.7	40.2	40.5	39.4
80°	30.7	30.3	29.8	30.7	29.8	30.3	30.7	30.7	30.1	30.7	30.1
82.5°	21.4	21.6	21.2	21.2	21.2	21.6	21.4	21.9	21.6	21.9	21.2
85°	9.9	9.6	9.2	9.2	9.2	9.6	9.9	9.9	10.5	10.1	10.1
87.5°	7.1	6.9	6.9	6.7	6.9	6.9	7.1	7.1	6.9	7.0	7.3
90°	26.1	26.1	26.1	26.1	26.1	26.1	26.1	26.1	25.2	23.7	25.2
92.5°	46.9	44.3	45.0	43.7	45.0	44.3	46.9	47.6	52.4	59.1	68.9
95°	97.9	91.6	89.2	90.0	89.2	91.6	97.9	108.2	125.5	158.6	206.8
97.5°	214.7	195.3	183.8	177.1	183.8	195.3	214.7	252.5	309.4	394.9	482.6
100°	353.7	319.7	296.8	282.6	296.8	319.7	353.7	419.2	514.7	622.9	720.7
102.5°	603.1	545.1	516.5	497.4	516.5	545.1	603.1	674.3	775.5	854.6	876.8
105°	983.6	934.6	900.7	889.7	900.7	934.6	983.6	1032.6	1058.6	1048.3	959.2
107.5°	1160.6	1157.9	1151.1	1136.4	1151.1	1157.9	1160.6	1154.5	1116.2	1034.1	899.8
110°	1189.6	1204.7	1211.7	1210.9	1211.7	1204.7	1189.6	1155.7	1091.0	990.0	848.6



TEST NUMBER: P331260-840

CATALOG NUMBER: SA2XXDIP-C290D725U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1166.9	1192.0	1205.5	1209.7	1205.5	1192.0	1166.9	1119.7	1045.5	937.5	801.9
115°	1106.7	1143.1	1163.6	1170.7	1163.6	1143.1	1106.7	1050.7	969.4	866.0	744.4
117.5°	1035.1	1073.5	1095.1	1101.1	1095.1	1073.5	1035.1	978.0	901.7	807.9	701.1
120°	988.4	1025.4	1048.3	1056.2	1048.3	1025.4	988.4	933.1	861.2	777.6	679.6
122.5°	946.0	982.5	1002.9	1009.5	1002.9	982.5	946.0	896.5	831.5	752.3	662.7
125°	893.6	923.6	943.3	949.7	943.3	923.6	893.6	847.8	788.6	719.1	637.8
127.5°	847.1	875.1	892.2	897.3	892.2	875.1	847.1	807.1	752.5	686.9	613.4
130°	818.6	845.5	861.2	867.6	861.2	845.5	818.6	779.9	727.8	665.5	597.5
132.5°	789.6	816.4	830.9	836.6	830.9	816.4	789.6	751.5	702.6	645.3	582.4
135°	743.7	769.7	783.9	787.1	783.9	769.7	743.7	709.6	665.5	613.4	561.3
137.5°	698.8	721.2	733.7	738.4	733.7	721.2	698.8	667.8	629.3	587.9	544.4
140°	667.8	688.3	700.2	705.0	700.2	688.3	667.8	642.6	607.8	571.6	533.6
142.5°	641.4	659.9	670.6	671.5	670.6	659.9	641.4	617.3	588.2	557.0	524.8
145°	604.7	618.1	626.0	628.3	626.0	618.1	604.7	585.7	562.9	538.4	512.3
147.5°	574.7	585.4	590.8	592.2	590.8	585.4	574.7	559.1	542.3	523.2	502.7
150°	555.7	565.2	570.0	570.8	570.0	565.2	555.7	543.9	529.7	513.1	495.7
152.5°	540.6	548.8	552.3	552.4	552.3	548.8	540.6	531.3	519.0	504.9	488.8
155°	521.0	526.5	529.7	528.2	529.7	526.5	521.0	512.3	503.6	491.8	479.2
157.5°	501.4	506.0	507.5	507.5	507.5	506.0	501.4	495.2	488.5	478.6	468.0
160°	489.5	493.4	494.1	494.1	494.1	493.4	489.5	483.9	478.4	469.7	461.0
162.5°	478.7	481.4	482.2	481.5	482.2	481.4	478.7	473.2	468.9	461.5	454.0
165°	461.0	464.1	464.1	463.4	464.1	464.1	461.0	457.9	454.7	449.2	443.6
167.5°	446.1	447.8	447.6	446.7	447.6	447.8	446.1	444.6	441.7	438.0	433.7
170°	436.6	438.9	438.1	436.6	438.1	438.9	436.6	435.8	434.1	431.0	428.7
172.5°	429.0	430.1	429.3	428.4	429.3	430.1	429.0	428.2	427.3	424.7	422.9
175°	419.2	420.0	419.2	417.6	419.2	420.0	419.2	419.2	418.4	417.6	416.8
177.5°	413.0	413.0	412.4	411.1	412.4	413.0	413.0	413.0	413.0	412.4	412.4
180°	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5



TEST NUMBER: P331260-840

CATALOG NUMBER: SA2XXDIP-C290D725U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9
2.5°	573.6	575.6	578.8	582.1	584.1	587.9	589.1	590.9	592.5	596.3	600.4
5°	540.5	543.7	551.3	555.4	561.1	567.7	572.1	576.7	581.8	590.5	598.5
7.5°	504.9	510.3	519.8	527.5	535.6	545.1	552.0	561.1	568.7	581.0	592.7
10°	481.3	488.9	497.4	506.5	518.0	528.1	537.8	549.2	558.4	573.1	586.8
12.5°	460.0	461.1	473.3	483.4	499.1	511.6	522.7	537.5	546.4	563.9	578.3
15°	422.8	429.7	440.7	448.7	467.3	483.1	498.8	514.1	524.4	546.0	565.0
17.5°	391.4	397.8	409.1	422.2	435.6	451.3	471.5	487.8	501.8	526.4	549.0
20°	371.6	379.4	390.9	404.5	416.2	433.3	450.8	469.4	484.5	512.3	538.7
22.5°	354.8	360.9	370.2	383.5	396.3	412.0	431.1	451.4	467.3	497.3	523.9
25°	331.0	336.1	342.0	353.0	367.5	384.8	399.6	421.9	445.0	473.0	505.3
27.5°	309.6	313.3	318.5	328.2	339.4	355.5	372.0	393.1	416.5	446.9	481.0
30°	296.6	298.9	304.2	312.3	323.3	335.9	352.6	372.7	396.7	427.4	461.3
32.5°	285.3	287.3	290.8	298.4	308.0	318.8	333.9	354.1	376.8	407.0	444.6
35°	268.2	269.7	272.8	278.9	284.3	294.8	307.4	325.8	347.1	376.0	415.0
37.5°	251.2	253.4	255.2	257.8	264.6	271.6	282.5	298.0	318.9	348.1	385.3
40°	239.9	241.8	244.6	245.7	251.2	257.4	266.3	280.5	301.6	328.3	364.6
42.5°	228.5	230.5	232.1	233.4	238.1	243.6	251.7	263.9	282.6	308.4	344.4
45°	213.1	213.4	215.0	217.5	219.7	223.7	229.4	239.9	254.4	278.7	311.3
47.5°	197.4	197.7	197.9	199.0	201.6	205.1	208.9	217.5	230.5	249.8	281.6
50°	186.9	186.5	186.9	187.8	189.5	192.5	196.8	203.0	213.6	231.7	260.8
52.5°	176.8	176.8	176.5	176.8	178.1	180.2	183.3	188.5	197.9	214.6	240.2
55°	161.5	160.4	160.6	159.7	161.8	162.2	164.5	168.8	177.1	188.5	212.7
57.5°	145.1	144.2	143.2	142.9	142.7	143.9	145.7	149.2	155.5	165.6	185.1
60°	134.6	133.5	132.1	131.7	131.7	132.4	133.3	135.8	141.8	150.7	166.7
62.5°	124.0	122.7	121.9	120.7	120.3	121.0	121.9	123.7	128.1	136.4	150.3
65°	107.6	105.9	104.8	104.6	104.1	103.5	103.9	105.7	109.2	115.8	126.8
67.5°	91.1	89.6	89.4	88.0	87.4	87.5	87.4	88.9	91.0	96.7	104.9
70°	80.3	79.2	78.7	77.6	77.1	76.6	76.1	77.6	79.6	84.4	91.5
72.5°	69.3	68.3	67.4	66.3	66.4	65.9	65.8	66.8	68.4	72.8	78.4
75°	53.4	53.7	52.5	51.4	51.2	50.7	50.7	51.4	52.1	55.5	59.9
77.5°	38.8	38.6	37.7	37.3	37.1	36.6	37.1	37.5	37.9	40.2	43.3
80°	29.6	29.6	28.5	28.5	28.2	27.6	28.2	27.8	28.7	31.0	33.2
82.5°	21.1	20.8	20.7	20.4	20.3	19.8	20.1	20.6	21.0	22.5	23.9
85°	10.3	10.3	10.1	9.9	10.1	9.9	10.1	10.3	10.5	11.2	12.4
87.5°	7.4	7.8	7.8	7.0	6.0	5.4	5.0	4.8	4.9	4.4	4.2
90°	26.1	26.9	26.1	21.3	15.8	11.8	9.5	7.9	6.4	3.1	0.8
92.5°	86.6	102.6	101.2	78.8	53.7	35.9	28.4	23.0	19.6	13.9	9.6
95°	270.7	309.4	274.0	182.4	113.7	77.4	58.4	45.7	38.7	30.8	27.7
97.5°	554.2	528.3	397.9	245.7	150.0	104.3	82.9	68.4	57.7	49.3	45.0
100°	737.3	623.6	429.4	258.9	162.6	120.8	98.7	82.9	70.3	63.1	60.8
102.5°	805.5	626.8	417.5	259.5	174.0	135.3	113.2	96.7	84.1	77.1	75.3
105°	795.0	584.9	393.9	263.7	193.4	156.3	134.2	116.8	105.0	99.5	96.3
107.5°	725.6	540.1	382.2	274.6	213.3	177.3	155.0	137.8	126.9	121.6	119.1
110°	682.1	518.7	379.7	283.4	226.5	191.9	169.0	152.4	142.1	137.3	134.2



TEST NUMBER: P331260-840

CATALOG NUMBER: SA2XXDIP-C290D725U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	651.8	504.7	380.3	292.9	239.2	205.7	182.2	166.2	156.6	151.3	148.0
115°	614.2	489.5	383.6	307.1	258.9	225.0	203.7	187.8	178.4	173.7	169.8
117.5°	590.5	482.0	389.3	322.2	277.1	245.7	223.6	208.4	200.1	195.3	192.2
120°	577.8	477.6	393.1	332.3	289.7	258.9	236.8	221.1	213.9	209.2	206.0
122.5°	567.1	475.0	397.6	341.2	301.7	272.9	250.0	234.3	226.5	221.9	219.3
125°	551.8	470.5	404.1	355.3	319.7	291.2	269.2	253.4	243.9	239.2	236.8
127.5°	537.6	467.8	411.0	368.3	336.5	308.8	286.1	270.9	260.5	253.9	250.7
130°	528.2	466.6	416.1	376.6	346.6	318.9	296.8	281.0	269.9	262.1	258.9
132.5°	520.6	466.0	421.1	384.8	355.4	329.0	306.9	290.5	278.8	270.3	266.5
135°	510.0	464.9	427.1	395.5	367.9	342.6	320.5	302.4	290.5	281.0	277.9
137.5°	502.5	464.8	432.4	403.7	378.0	353.0	332.5	314.5	301.8	292.4	288.6
140°	498.2	464.1	434.9	408.1	383.6	360.0	339.4	322.0	309.4	299.9	296.8
142.5°	493.7	464.1	436.9	411.9	388.1	365.1	345.8	329.0	316.4	307.6	305.0
145°	487.9	462.6	438.9	416.8	394.8	373.3	356.0	340.2	328.4	320.5	317.3
147.5°	481.9	459.8	439.6	419.5	400.1	380.0	364.6	351.4	340.5	333.0	330.6
150°	476.8	457.9	438.9	420.7	402.6	384.5	370.2	358.4	348.1	341.8	339.4
152.5°	472.4	454.7	437.7	421.4	405.2	388.9	375.9	364.7	355.7	349.4	348.3
155°	464.1	449.2	435.8	422.3	408.9	395.5	383.6	375.0	366.3	361.5	360.7
157.5°	456.5	443.5	432.1	422.3	411.6	400.2	390.3	383.3	375.8	371.9	371.2
160°	450.8	439.7	430.2	422.3	412.8	403.3	394.8	388.4	382.0	378.9	378.1
162.5°	445.7	436.6	428.4	421.7	413.5	405.3	398.5	392.8	387.8	384.6	385.1
165°	437.4	430.2	424.7	420.0	414.4	407.4	402.6	398.7	393.9	392.3	393.1
167.5°	429.1	424.7	421.1	418.9	414.2	409.1	406.1	403.2	400.2	398.8	399.8
170°	424.7	421.5	419.2	417.6	413.6	409.7	407.4	405.8	403.3	402.6	404.1
172.5°	420.3	417.8	416.7	415.7	413.0	410.3	408.6	407.7	405.3	405.8	406.7
175°	414.4	413.6	412.8	413.6	412.0	410.5	409.7	409.7	408.1	408.9	409.7
177.5°	411.1	410.5	411.1	412.4	411.1	410.5	410.5	410.5	409.2	409.9	411.1
180°	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5



TEST NUMBER: P331260-840

CATALOG NUMBER: SA2XXDIP-C290D725U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9
2.5°	600.1	601.0	603.9	606.8	610.2	611.1	612.5	611.3	610.9	614.3	616.9
5°	601.8	605.8	613.9	621.3	627.4	631.8	636.4	638.2	641.7	646.4	652.5
7.5°	599.8	607.8	620.5	631.2	642.8	651.2	657.7	663.4	670.1	679.2	689.2
10°	597.6	608.3	623.8	636.8	651.1	661.9	670.8	679.5	689.6	702.3	715.3
12.5°	593.6	606.3	625.6	641.1	659.3	669.9	682.0	700.7	711.7	729.2	747.6
15°	585.4	599.7	626.5	645.5	666.2	686.4	708.6	726.5	744.4	754.8	780.6
17.5°	573.4	594.2	624.0	646.2	672.5	704.2	729.2	749.5	770.1	786.9	799.9
20°	563.6	586.3	620.4	646.9	678.1	712.3	740.9	761.6	779.5	793.6	801.5
22.5°	551.4	580.0	613.0	644.2	684.0	717.8	747.9	764.2	779.1	786.0	789.1
25°	532.0	566.4	603.8	641.9	686.8	722.7	750.1	760.0	764.4	757.7	746.7
27.5°	511.1	549.5	593.2	637.5	685.1	719.5	739.2	737.7	730.3	708.7	691.6
30°	495.5	537.8	584.7	633.2	680.9	714.4	725.8	714.4	697.6	673.6	648.9
32.5°	479.2	522.9	575.7	626.9	673.2	702.7	705.1	685.4	659.4	632.1	601.5
35°	454.4	501.7	558.9	613.0	656.8	675.4	664.4	629.4	598.7	561.4	519.6
37.5°	426.5	478.7	535.9	592.6	632.3	637.1	609.8	573.1	529.7	485.7	436.6
40°	405.6	460.9	519.9	576.9	612.1	607.0	572.1	531.8	480.2	426.5	380.8
42.5°	386.9	442.1	502.2	558.3	586.3	572.5	531.8	482.2	426.8	376.2	334.4
45°	354.5	411.3	472.8	526.9	543.0	518.0	464.1	409.0	354.5	312.3	279.2
47.5°	323.0	379.2	440.1	487.7	493.3	459.7	400.8	344.2	297.2	262.9	239.5
50°	299.8	356.3	416.6	459.1	457.2	416.6	356.1	302.2	262.9	235.1	219.5
52.5°	279.1	332.4	390.3	429.0	419.2	375.0	317.1	269.2	237.0	215.3	201.2
55°	246.8	296.2	351.2	382.2	364.3	315.2	266.3	227.8	203.9	187.6	176.6
57.5°	214.8	261.1	308.2	327.3	307.5	262.2	221.5	193.5	175.5	163.5	156.3
60°	195.0	235.4	277.3	293.9	270.2	229.8	197.7	172.8	158.2	148.5	142.0
62.5°	175.2	211.4	251.0	259.9	238.3	204.2	175.7	154.9	143.1	134.3	128.3
65°	148.1	177.8	207.8	213.8	193.9	167.4	145.0	131.5	120.9	114.5	109.7
67.5°	121.6	145.3	166.6	171.4	153.9	135.6	119.4	107.6	100.5	95.1	91.0
70°	105.7	124.6	142.0	145.9	131.9	115.6	103.2	93.8	87.4	82.8	78.9
72.5°	89.1	104.7	119.3	121.9	110.5	98.0	87.9	80.4	74.7	71.8	68.1
75°	68.2	77.4	88.6	89.3	81.7	74.1	66.3	61.5	58.5	54.8	53.0
77.5°	48.1	55.2	61.7	62.9	58.5	53.3	49.0	45.1	42.6	40.9	39.2
80°	36.7	42.4	45.2	46.8	43.6	39.9	37.4	34.8	33.2	32.1	31.0
82.5°	26.3	29.8	32.3	33.6	31.8	29.6	27.2	25.7	24.4	23.5	23.1
85°	13.3	14.9	16.6	17.0	16.6	15.6	14.2	14.2	13.5	13.3	13.3
87.5°	5.3	6.6	6.9	7.8	7.9	8.7	9.8	10.5	10.5	10.2	9.8
90°	3.1	6.4	7.9	9.5	11.8	15.8	21.3	26.1	26.9	26.1	25.2
92.5°	13.9	19.6	23.0	28.4	35.9	53.7	78.8	101.2	102.6	86.6	68.9
95°	30.8	38.7	45.7	58.4	77.4	113.7	182.4	274.0	309.4	270.7	206.8
97.5°	49.3	57.7	68.4	82.9	104.3	150.0	245.7	397.9	528.3	554.2	482.6
100°	63.1	70.3	82.9	98.7	120.8	162.6	258.9	429.4	623.6	737.3	720.7
102.5°	77.1	84.1	96.7	113.2	135.3	174.0	259.5	417.5	626.8	805.5	876.8
105°	99.5	105.0	116.8	134.2	156.3	193.4	263.7	393.9	584.9	795.0	959.2
107.5°	121.6	126.9	137.8	155.0	177.3	213.3	274.6	382.2	540.1	725.6	899.8
110°	137.3	142.1	152.4	169.0	191.9	226.5	283.4	379.7	518.7	682.1	848.6





TEST NUMBER: P331260-840

CATALOG NUMBER: SA2XXDIP-C290D725U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	151.3	156.6	166.2	182.2	205.7	239.2	292.9	380.3	504.7	651.8	801.9
115°	173.7	178.4	187.8	203.7	225.0	258.9	307.1	383.6	489.5	614.2	744.4
117.5°	195.3	200.1	208.4	223.6	245.7	277.1	322.2	389.3	482.0	590.5	701.1
120°	209.2	213.9	221.1	236.8	258.9	289.7	332.3	393.1	477.6	577.8	679.6
122.5°	221.9	226.5	234.3	250.0	272.9	301.7	341.2	397.6	475.0	567.1	662.7
125°	239.2	243.9	253.4	269.2	291.2	319.7	355.3	404.1	470.5	551.8	637.8
127.5°	253.9	260.5	270.9	286.1	308.8	336.5	368.3	411.0	467.8	537.6	613.4
130°	262.1	269.9	281.0	296.8	318.9	346.6	376.6	416.1	466.6	528.2	597.5
132.5°	270.3	278.8	290.5	306.9	329.0	355.4	384.8	421.1	466.0	520.6	582.4
135°	281.0	290.5	302.4	320.5	342.6	367.9	395.5	427.1	464.9	510.0	561.3
137.5°	292.4	301.8	314.5	332.5	353.0	378.0	403.7	432.4	464.8	502.5	544.4
140°	299.9	309.4	322.0	339.4	360.0	383.6	408.1	434.9	464.1	498.2	533.6
142.5°	307.6	316.4	329.0	345.8	365.1	388.1	411.9	436.9	464.1	493.7	524.8
145°	320.5	328.4	340.2	356.0	373.3	394.8	416.8	438.9	462.6	487.9	512.3
147.5°	333.0	340.5	351.4	364.6	380.0	400.1	419.5	439.6	459.8	481.9	502.7
150°	341.8	348.1	358.4	370.2	384.5	402.6	420.7	438.9	457.9	476.8	495.7
152.5°	349.4	355.7	364.7	375.9	388.9	405.2	421.4	437.7	454.7	472.4	488.8
155°	361.5	366.3	375.0	383.6	395.5	408.9	422.3	435.8	449.2	464.1	479.2
157.5°	371.9	375.8	383.3	390.3	400.2	411.6	422.3	432.1	443.5	456.5	468.0
160°	378.9	382.0	388.4	394.8	403.3	412.8	422.3	430.2	439.7	450.8	461.0
162.5°	384.6	387.8	392.8	398.5	405.3	413.5	421.7	428.4	436.6	445.7	454.0
165°	392.3	393.9	398.7	402.6	407.4	414.4	420.0	424.7	430.2	437.4	443.6
167.5°	398.8	400.2	403.2	406.1	409.1	414.2	418.9	421.1	424.7	429.1	433.7
170°	402.6	403.3	405.8	407.4	409.7	413.6	417.6	419.2	421.5	424.7	428.7
172.5°	405.8	405.3	407.7	408.6	410.3	413.0	415.7	416.7	417.8	420.3	422.9
175°	408.9	408.1	409.7	409.7	410.5	412.0	413.6	412.8	413.6	414.4	416.8
177.5°	409.9	409.2	410.5	410.5	410.5	411.1	412.4	411.1	410.5	411.1	412.4
180°	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5



TEST NUMBER: P331260-840

CATALOG NUMBER: SA2XXDIP-C290D725U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	596.9	596.9	596.9	596.9	596.9	596.9	596.9
2.5°	619.1	621.7	621.7	622.1	625.0	624.6	624.4
5°	658.8	662.8	663.2	667.3	670.0	669.1	666.6
7.5°	696.3	703.6	709.1	712.2	715.8	718.0	717.0
10°	726.1	736.6	743.1	747.4	752.7	756.6	755.2
12.5°	753.1	765.6	774.5	781.9	782.5	787.6	784.2
15°	795.2	808.4	809.8	815.3	819.7	819.2	819.4
17.5°	809.0	813.2	814.2	814.3	814.4	812.7	809.2
20°	804.1	802.4	798.6	795.6	790.3	789.6	785.1
22.5°	780.5	775.5	765.7	759.2	751.0	748.9	747.6
25°	734.4	723.1	707.5	692.6	688.4	680.4	682.7
27.5°	670.9	653.4	636.4	624.4	613.4	601.4	604.8
30°	626.3	606.5	582.7	564.3	552.6	541.2	539.1
32.5°	573.1	544.1	517.6	501.4	483.4	476.2	468.3
35°	481.3	453.0	426.7	403.9	390.9	380.8	371.6
37.5°	398.8	366.3	345.0	326.6	317.1	311.3	312.9
40°	347.6	319.1	303.5	289.5	280.7	276.7	277.6
42.5°	306.1	284.8	272.0	262.4	256.2	253.9	253.4
45°	259.0	247.1	236.5	231.1	228.0	225.5	223.9
47.5°	226.9	217.1	211.2	207.9	205.3	202.8	202.7
50°	207.6	201.2	197.0	193.6	191.6	189.8	191.4
52.5°	192.9	187.0	182.9	179.9	179.0	177.4	177.3
55°	171.2	166.5	163.6	160.8	159.5	158.5	157.3
57.5°	151.3	146.9	144.2	142.5	139.9	139.0	138.6
60°	137.1	133.7	131.0	128.7	127.5	125.7	125.7
62.5°	124.1	120.7	118.2	116.4	114.5	113.8	114.0
65°	105.3	102.5	100.0	98.2	97.8	96.3	96.8
67.5°	88.0	86.1	83.4	82.4	81.6	80.9	80.3
70°	76.3	74.5	73.2	71.8	71.1	71.1	71.1
72.5°	66.7	64.4	63.6	61.9	62.3	61.6	60.8
75°	51.6	50.2	49.6	48.9	47.8	47.8	47.8
77.5°	38.0	37.6	36.8	36.1	35.7	35.5	35.6
80°	29.4	29.1	28.7	28.7	28.2	28.0	27.6
82.5°	22.6	22.0	21.7	21.5	21.4	21.4	21.3
85°	12.8	12.4	12.4	12.6	12.1	12.1	12.4
87.5°	9.7	10.0	10.0	10.0	10.2	10.0	10.0
90°	23.7	25.2	26.1	26.1	26.1	26.1	26.1
92.5°	59.1	52.4	47.6	46.9	44.3	45.0	43.7
95°	158.6	125.5	108.2	97.9	91.6	89.2	90.0
97.5°	394.9	309.4	252.5	214.7	195.3	183.8	177.1
100°	622.9	514.7	419.2	353.7	319.7	296.8	282.6
102.5°	854.6	775.5	674.3	603.1	545.1	516.5	497.4
105°	1048.3	1058.6	1032.6	983.6	934.6	900.7	889.7
107.5°	1034.1	1116.2	1154.5	1160.6	1157.9	1151.1	1136.4
110°	990.0	1091.0	1155.7	1189.6	1204.7	1211.7	1210.9



TEST NUMBER: P331260-840

CATALOG NUMBER: SA2XXDIP-C290D725U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	937.5	1045.5	1119.7	1166.9	1192.0	1205.5	1209.7
115°	866.0	969.4	1050.7	1106.7	1143.1	1163.6	1170.7
117.5°	807.9	901.7	978.0	1035.1	1073.5	1095.1	1101.1
120°	777.6	861.2	933.1	988.4	1025.4	1048.3	1056.2
122.5°	752.3	831.5	896.5	946.0	982.5	1002.9	1009.5
125°	719.1	788.6	847.8	893.6	923.6	943.3	949.7
127.5°	686.9	752.5	807.1	847.1	875.1	892.2	897.3
130°	665.5	727.8	779.9	818.6	845.5	861.2	867.6
132.5°	645.3	702.6	751.5	789.6	816.4	830.9	836.6
135°	613.4	665.5	709.6	743.7	769.7	783.9	787.1
137.5°	587.9	629.3	667.8	698.8	721.2	733.7	738.4
140°	571.6	607.8	642.6	667.8	688.3	700.2	705.0
142.5°	557.0	588.2	617.3	641.4	659.9	670.6	671.5
145°	538.4	562.9	585.7	604.7	618.1	626.0	628.3
147.5°	523.2	542.3	559.1	574.7	585.4	590.8	592.2
150°	513.1	529.7	543.9	555.7	565.2	570.0	570.8
152.5°	504.9	519.0	531.3	540.6	548.8	552.3	552.4
155°	491.8	503.6	512.3	521.0	526.5	529.7	528.2
157.5°	478.6	488.5	495.2	501.4	506.0	507.5	507.5
160°	469.7	478.4	483.9	489.5	493.4	494.1	494.1
162.5°	461.5	468.9	473.2	478.7	481.4	482.2	481.5
165°	449.2	454.7	457.9	461.0	464.1	464.1	463.4
167.5°	438.0	441.7	444.6	446.1	447.8	447.6	446.7
170°	431.0	434.1	435.8	436.6	438.9	438.1	436.6
172.5°	424.7	427.3	428.2	429.0	430.1	429.3	428.4
175°	417.6	418.4	419.2	419.2	420.0	419.2	417.6
177.5°	412.4	413.0	413.0	413.0	413.0	412.4	411.1
180°	410.5	410.5	410.5	410.5	410.5	410.5	410.5

(END OF REPORT)