

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331269-840

Luminaire Tested: **SA2XXDIP-C290D925U840-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331269-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXDIP-C290D925U840-4F0-1E-UDD-A4  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 925 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4968.6 lumens  
Efficiency: N/A  
Efficacy: 133.2 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 37.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331269-840  
CATALOG NUMBER: SA2XXDIP-C290D925U840-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P331269-840

CATALOG NUMBER: SA2XXDIP-C290D925U840-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	102	102	102	102	91	91	91	91	70	70	70	52	52	52	35	35	35	27				
1	93	89	85	82	83	79	76	74	62	60	58	46	45	43	31	30	30	23				
2	85	78	72	67	75	70	65	61	54	51	48	40	38	37	27	26	25	20				
3	77	68	62	56	69	61	56	51	48	44	41	36	33	31	25	23	22	17				
4	71	61	53	47	63	54	48	43	43	38	35	32	29	27	22	20	19	15				
5	65	54	46	41	58	49	42	37	38	34	30	29	26	23	20	18	17	13				
6	60	48	41	35	53	44	37	32	35	30	26	26	23	20	18	16	15	11				
7	55	44	36	31	49	39	33	28	31	27	23	24	21	18	17	15	13	10				
8	51	39	32	27	46	36	29	25	28	24	20	22	19	16	15	13	12	9				
9	48	36	29	24	42	33	26	22	26	21	18	20	17	14	14	12	11	8				
10	44	33	26	21	40	30	24	20	24	19	16	18	15	13	13	11	10	8				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	9637	9637	9637	9637
5°	10804	9700	8596	9700
10°	12381	9621	7438	9621
15°	13697	9444	6572	9444
20°	13490	9256	5991	9256
25°	12162	9002	5624	9002
30°	10051	8600	5354	8600
35°	7324	8180	5164	8180
40°	5851	7685	5056	7685
45°	5112	7108	4914	7108
50°	4808	6551	4818	6551
55°	4428	5987	4687	5987
60°	4059	5383	4492	5383
65°	3698	4844	4294	4844
70°	3356	4319	4008	4319
75°	2982	3737	3550	3737
80°	2566	3087	2854	3087
85°	2297	2297	1704	2297



TEST NUMBER: P331269-840

CATALOG NUMBER: SA2XXDIP-C290D925U840-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	56.8	1.1
10°-20°	165.3	3.3
20°-30°	239.9	4.8
30°-40°	253.1	5.1
40°-50°	224.1	4.5
50°-60°	178.8	3.6
60°-70°	121.6	2.4
70°-80°	62.3	1.3
80°-90°	19.7	0.4
90°-100°	209.6	4.2
100°-110°	711.1	14.3
110°-120°	755.5	15.2
120°-130°	621.9	12.5
130°-140°	499.4	10.1
140°-150°	377.4	7.6
150°-160°	265.2	5.3
160°-170°	156.1	3.1
170°-180°	50.8	1.0
0°-30°	462.0	9.3
0°-40°	715.1	14.4
0°-60°	1118.0	22.5
0°-90°	1321.6	26.6
90°-120°	1676.1	33.7
90°-150°	3174.8	63.9
90°-180°	3647.0	73.4
0°-180°	4968.6	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	597	597	597	597	597	
5°	667	598	530	598	667	67
15°	819	565	393	565	819	226
25°	683	505	316	505	683	309
35°	372	415	262	415	372	242
45°	224	311	215	311	224	176
55°	157	213	166	213	157	141
65°	97	127	112	127	97	96
75°	48	60	57	60	48	51
85°	12	12	9	12	12	14
90°	33	1	33	1	33	18
95°	115	35	115	35	115	149
105°	1136	123	1136	123	1136	1099
115°	1495	217	1495	217	1495	1464
125°	1212	302	1212	302	1212	1096
135°	1005	355	1005	355	1005	781
145°	802	405	802	405	802	510
155°	674	461	674	461	674	315
165°	592	502	592	502	592	169
175°	533	523	533	523	533	52
180°	524	524	524	524	524	



TEST NUMBER: P331269-840

CATALOG NUMBER: SA2XXDIP-C290D925U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9
2.5°	624.4	624.6	625.0	622.1	621.7	621.7	619.1	616.9	614.3	610.9	611.3
5°	666.6	669.1	670.0	667.3	663.2	662.8	658.8	652.5	646.4	641.7	638.2
7.5°	717.0	718.0	715.8	712.2	709.1	703.6	696.3	689.2	679.2	670.1	663.4
10°	755.2	756.6	752.7	747.4	743.1	736.6	726.1	715.3	702.3	689.6	679.5
12.5°	784.2	787.6	782.5	781.9	774.5	765.6	753.1	747.6	729.2	711.7	700.7
15°	819.4	819.2	819.7	815.3	809.8	808.4	795.2	780.6	754.8	744.4	726.5
17.5°	809.2	812.7	814.4	814.3	814.2	813.2	809.0	799.9	786.9	770.1	749.5
20°	785.1	789.6	790.3	795.6	798.6	802.4	804.1	801.5	793.6	779.5	761.6
22.5°	747.6	748.9	751.0	759.2	765.7	775.5	780.5	789.1	786.0	779.1	764.2
25°	682.7	680.4	688.4	692.6	707.5	723.1	734.4	746.7	757.7	764.4	760.0
27.5°	604.8	601.4	613.4	624.4	636.4	653.4	670.9	691.6	708.7	730.3	737.7
30°	539.1	541.2	552.6	564.3	582.7	606.5	626.3	648.9	673.6	697.6	714.4
32.5°	468.3	476.2	483.4	501.4	517.6	544.1	573.1	601.5	632.1	659.4	685.4
35°	371.6	380.8	390.9	403.9	426.7	453.0	481.3	519.6	561.4	598.7	629.4
37.5°	312.9	311.3	317.1	326.6	345.0	366.3	398.8	436.6	485.7	529.7	573.1
40°	277.6	276.7	280.7	289.5	303.5	319.1	347.6	380.8	426.5	480.2	531.8
42.5°	253.4	253.9	256.2	262.4	272.0	284.8	306.1	334.4	376.2	426.8	482.2
45°	223.9	225.5	228.0	231.1	236.5	247.1	259.0	279.2	312.3	354.5	409.0
47.5°	202.7	202.8	205.3	207.9	211.2	217.1	226.9	239.5	262.9	297.2	344.2
50°	191.4	189.8	191.6	193.6	197.0	201.2	207.6	219.5	235.1	262.9	302.2
52.5°	177.3	177.4	179.0	179.9	182.9	187.0	192.9	201.2	215.3	237.0	269.2
55°	157.3	158.5	159.5	160.8	163.6	166.5	171.2	176.6	187.6	203.9	227.8
57.5°	138.6	139.0	139.9	142.5	144.2	146.9	151.3	156.3	163.5	175.5	193.5
60°	125.7	125.7	127.5	128.7	131.0	133.7	137.1	142.0	148.5	158.2	172.8
62.5°	114.0	113.8	114.5	116.4	118.2	120.7	124.1	128.3	134.3	143.1	154.9
65°	96.8	96.3	97.8	98.2	100.0	102.5	105.3	109.7	114.5	120.9	131.5
67.5°	80.3	80.9	81.6	82.4	83.4	86.1	88.0	91.0	95.1	100.5	107.6
70°	71.1	71.1	71.1	71.8	73.2	74.5	76.3	78.9	82.8	87.4	93.8
72.5°	60.8	61.6	62.3	61.9	63.6	64.4	66.7	68.1	71.8	74.7	80.4
75°	47.8	47.8	47.8	48.9	49.6	50.2	51.6	53.0	54.8	58.5	61.5
77.5°	35.6	35.5	35.7	36.1	36.8	37.6	38.0	39.2	40.9	42.6	45.1
80°	27.6	28.0	28.2	28.7	28.7	29.1	29.4	31.0	32.1	33.2	34.8
82.5°	21.3	21.4	21.4	21.5	21.7	22.0	22.6	23.1	23.5	24.4	25.7
85°	12.4	12.1	12.1	12.6	12.4	12.4	12.8	13.3	13.3	13.5	14.2
87.5°	11.4	11.4	11.6	11.4	11.4	11.4	11.0	11.2	11.6	12.0	12.0
90°	33.2	33.2	33.2	33.2	33.2	32.2	30.2	32.2	33.2	34.2	33.2
92.5°	55.8	57.5	56.7	59.9	60.7	67.0	75.4	87.9	110.7	131.0	129.2
95°	114.9	113.9	116.9	125.0	138.0	160.3	202.6	264.1	345.7	395.1	349.7
97.5°	226.2	234.6	249.3	274.2	322.3	395.1	504.1	616.2	707.5	674.5	508.0
100°	360.8	379.0	408.2	451.5	535.2	657.1	795.2	920.2	941.4	796.2	548.3
102.5°	635.0	659.5	696.0	770.0	860.9	990.2	1091.2	1119.3	1028.4	800.2	533.0
105°	1135.9	1149.9	1193.4	1255.8	1318.3	1351.6	1338.5	1224.6	1014.9	746.8	502.9
107.5°	1451.0	1469.7	1478.3	1481.8	1473.9	1425.1	1320.3	1148.8	926.5	689.6	488.0
110°	1546.1	1547.1	1538.0	1518.8	1475.5	1392.9	1263.8	1083.5	870.8	662.2	484.8



TEST NUMBER: P331269-840

CATALOG NUMBER: SA2XXDIP-C290D925U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1544.5	1539.0	1521.9	1489.9	1429.6	1334.8	1197.0	1023.8	832.1	644.4	485.5
115°	1494.7	1485.6	1459.4	1413.0	1341.5	1237.7	1105.6	950.4	784.2	624.9	489.8
117.5°	1405.7	1398.2	1370.5	1321.5	1248.6	1151.1	1031.5	895.1	753.9	615.4	497.1
120°	1348.6	1338.5	1309.2	1261.8	1191.3	1099.5	992.8	867.8	737.8	609.8	501.9
122.5°	1288.9	1280.4	1254.4	1207.8	1144.6	1061.7	960.5	846.0	724.1	606.5	507.6
125°	1212.4	1204.4	1179.2	1140.9	1082.5	1006.8	918.2	814.4	704.5	600.7	516.0
127.5°	1145.6	1139.1	1117.3	1081.5	1030.5	960.7	877.1	783.2	686.4	597.2	524.7
130°	1107.6	1099.5	1079.4	1045.2	995.8	929.3	849.6	763.0	674.3	595.6	531.2
132.5°	1068.1	1060.9	1042.4	1008.0	959.5	897.0	823.8	743.6	664.6	594.8	537.6
135°	1004.8	1000.8	982.7	949.4	906.1	849.6	783.2	716.6	651.1	593.6	545.2
137.5°	942.8	936.8	920.8	892.2	852.6	803.4	750.6	695.0	641.6	593.4	552.1
140°	900.0	894.0	878.9	852.6	820.4	776.1	729.7	681.4	636.0	592.6	555.3
142.5°	857.3	856.1	842.6	818.8	788.2	751.0	711.1	670.0	630.4	592.6	557.7
145°	802.2	799.2	789.2	772.0	747.8	718.6	687.4	654.1	622.9	590.6	560.4
147.5°	756.1	754.3	747.4	733.8	713.8	692.4	668.0	641.8	615.2	587.0	561.2
150°	728.7	727.7	721.6	709.5	694.4	676.3	655.1	633.0	608.7	584.6	560.4
152.5°	705.3	705.1	700.6	690.1	678.3	662.6	644.6	624.1	603.1	580.6	558.8
155°	674.3	676.3	672.3	665.2	654.1	643.0	627.9	611.8	592.6	573.5	556.3
157.5°	647.8	647.8	646.0	640.2	632.4	623.7	611.0	597.4	582.8	566.2	551.7
160°	631.0	631.0	630.0	624.9	617.8	610.8	599.7	588.5	575.5	561.4	549.3
162.5°	614.8	615.6	614.6	611.2	604.1	598.6	589.2	579.8	569.1	557.3	546.8
165°	591.6	592.6	592.6	588.5	584.6	580.6	573.5	566.4	558.4	549.3	542.2
167.5°	570.3	571.5	571.7	569.5	567.6	564.0	559.2	553.7	547.9	542.2	537.6
170°	557.3	559.4	560.4	557.3	556.3	554.3	550.3	547.2	542.2	538.2	535.2
172.5°	546.8	548.1	549.1	547.6	546.6	545.4	542.2	540.0	536.6	533.4	532.0
175°	533.2	535.2	536.2	535.2	535.2	534.2	533.2	532.2	529.2	528.2	527.1
177.5°	524.9	526.5	527.4	527.4	527.4	527.4	526.5	526.5	524.9	524.1	524.9
180°	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1



TEST NUMBER: P331269-840

CATALOG NUMBER: SA2XXDIP-C290D925U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9
2.5°	612.5	611.1	610.2	606.8	603.9	601.0	600.1	600.4	596.3	592.5	590.9
5°	636.4	631.8	627.4	621.3	613.9	605.8	601.8	598.5	590.5	581.8	576.7
7.5°	657.7	651.2	642.8	631.2	620.5	607.8	599.8	592.7	581.0	568.7	561.1
10°	670.8	661.9	651.1	636.8	623.8	608.3	597.6	586.8	573.1	558.4	549.2
12.5°	682.0	669.9	659.3	641.1	625.6	606.3	593.6	578.3	563.9	546.4	537.5
15°	708.6	686.4	666.2	645.5	626.5	599.7	585.4	565.0	546.0	524.4	514.1
17.5°	729.2	704.2	672.5	646.2	624.0	594.2	573.4	549.0	526.4	501.8	487.8
20°	740.9	712.3	678.1	646.9	620.4	586.3	563.6	538.7	512.3	484.5	469.4
22.5°	747.9	717.8	684.0	644.2	613.0	580.0	551.4	523.9	497.3	467.3	451.4
25°	750.1	722.7	686.8	641.9	603.8	566.4	532.0	505.3	473.0	445.0	421.9
27.5°	739.2	719.5	685.1	637.5	593.2	549.5	511.1	481.0	446.9	416.5	393.1
30°	725.8	714.4	680.9	633.2	584.7	537.8	495.5	461.3	427.4	396.7	372.7
32.5°	705.1	702.7	673.2	626.9	575.7	522.9	479.2	444.6	407.0	376.8	354.1
35°	664.4	675.4	656.8	613.0	558.9	501.7	454.4	415.0	376.0	347.1	325.8
37.5°	609.8	637.1	632.3	592.6	535.9	478.7	426.5	385.3	348.1	318.9	298.0
40°	572.1	607.0	612.1	576.9	519.9	460.9	405.6	364.6	328.3	301.6	280.5
42.5°	531.8	572.5	586.3	558.3	502.2	442.1	386.9	344.4	308.4	282.6	263.9
45°	464.1	518.0	543.0	526.9	472.8	411.3	354.5	311.3	278.7	254.4	239.9
47.5°	400.8	459.7	493.3	487.7	440.1	379.2	323.0	281.6	249.8	230.5	217.5
50°	356.1	416.6	457.2	459.1	416.6	356.3	299.8	260.8	231.7	213.6	203.0
52.5°	317.1	375.0	419.2	429.0	390.3	332.4	279.1	240.2	214.6	197.9	188.5
55°	266.3	315.2	364.3	382.2	351.2	296.2	246.8	212.7	188.5	177.1	168.8
57.5°	221.5	262.2	307.5	327.3	308.2	261.1	214.8	185.1	165.6	155.5	149.2
60°	197.7	229.8	270.2	293.9	277.3	235.4	195.0	166.7	150.7	141.8	135.8
62.5°	175.7	204.2	238.3	259.9	251.0	211.4	175.2	150.3	136.4	128.1	123.7
65°	145.0	167.4	193.9	213.8	207.8	177.8	148.1	126.8	115.8	109.2	105.7
67.5°	119.4	135.6	153.9	171.4	166.6	145.3	121.6	104.9	96.7	91.0	88.9
70°	103.2	115.6	131.9	145.9	142.0	124.6	105.7	91.5	84.4	79.6	77.6
72.5°	87.9	98.0	110.5	121.9	119.3	104.7	89.1	78.4	72.8	68.4	66.8
75°	66.3	74.1	81.7	89.3	88.6	77.4	68.2	59.9	55.5	52.1	51.4
77.5°	49.0	53.3	58.5	62.9	61.7	55.2	48.1	43.3	40.2	37.9	37.5
80°	37.4	39.9	43.6	46.8	45.2	42.4	36.7	33.2	31.0	28.7	27.8
82.5°	27.2	29.6	31.8	33.6	32.3	29.8	26.3	23.9	22.5	21.0	20.6
85°	14.2	15.6	16.6	17.0	16.6	14.9	13.3	12.4	11.2	10.5	10.3
87.5°	10.9	9.5	8.5	8.3	7.4	7.0	5.4	4.2	4.6	5.3	5.4
90°	27.2	20.2	15.1	12.1	10.1	8.1	4.0	1.0	4.0	8.1	10.1
92.5°	100.6	68.6	45.7	36.3	29.4	25.0	17.8	12.3	17.8	25.0	29.4
95°	232.8	145.1	98.8	74.6	58.5	49.4	39.3	35.2	39.3	49.4	58.5
97.5°	313.7	191.5	133.2	105.8	87.3	73.6	62.9	57.5	62.9	73.6	87.3
100°	330.6	207.6	154.2	126.0	105.8	89.7	80.6	77.6	80.6	89.7	105.8
102.5°	331.4	222.2	172.8	144.5	123.6	107.4	98.4	96.1	98.4	107.4	123.6
105°	336.6	246.9	199.5	171.4	149.2	134.0	127.0	123.0	127.0	134.0	149.2
107.5°	350.5	272.4	226.4	197.9	176.0	162.1	155.2	152.0	155.2	162.1	176.0
110°	361.8	289.2	244.9	215.7	194.5	181.4	175.4	171.4	175.4	181.4	194.5





TEST NUMBER: P331269-840

CATALOG NUMBER: SA2XXDIP-C290D925U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	374.0	305.4	262.7	232.6	212.3	200.0	193.1	189.0	193.1	200.0	212.3
115°	392.0	330.6	287.2	260.0	239.8	227.8	221.8	216.7	221.8	227.8	239.8
117.5°	411.4	353.8	313.7	285.4	266.1	255.4	249.3	245.3	249.3	255.4	266.1
120°	424.3	369.9	330.6	302.4	282.2	273.2	267.1	263.1	267.1	273.2	282.2
122.5°	435.6	385.2	348.3	319.3	299.1	289.2	283.2	280.0	283.2	289.2	299.1
125°	453.5	408.2	371.9	343.7	323.6	311.4	305.4	302.4	305.4	311.4	323.6
127.5°	470.3	429.6	394.3	365.3	345.9	332.5	324.2	320.1	324.2	332.5	345.9
130°	480.8	442.4	407.2	379.0	358.8	344.7	334.6	330.6	334.6	344.7	358.8
132.5°	491.2	453.7	420.1	391.8	370.9	356.0	345.1	340.2	345.1	356.0	370.9
135°	504.9	469.7	437.4	409.2	386.0	370.9	358.8	354.8	358.8	370.9	386.0
137.5°	515.4	482.6	450.7	424.5	401.5	385.4	373.3	368.5	373.3	385.4	401.5
140°	521.1	489.8	459.6	433.4	411.2	395.1	383.0	379.0	383.0	395.1	411.2
142.5°	525.9	495.4	466.1	441.4	420.1	403.9	392.6	389.4	392.6	403.9	420.1
145°	532.2	503.9	476.8	454.5	434.4	419.3	409.2	405.2	409.2	419.3	434.4
147.5°	535.6	510.8	485.2	465.4	448.7	434.7	425.2	422.1	425.2	434.7	448.7
150°	537.1	514.0	490.8	472.7	457.6	444.4	436.4	433.4	436.4	444.4	457.6
152.5°	538.0	517.3	496.4	480.0	465.6	454.1	446.1	444.6	446.1	454.1	465.6
155°	539.2	522.1	504.9	489.8	478.8	467.7	461.6	460.6	461.6	467.7	478.8
157.5°	539.2	525.5	511.0	498.3	489.4	479.8	474.9	473.9	474.9	479.8	489.4
160°	539.2	527.1	515.0	503.9	495.8	487.8	483.8	482.8	483.8	487.8	495.8
162.5°	538.4	528.0	517.5	508.8	501.5	495.0	491.0	491.6	491.0	495.0	501.5
165°	536.2	529.2	520.1	514.0	509.0	502.9	500.9	501.9	500.9	502.9	509.0
167.5°	534.8	529.0	522.3	518.5	514.8	511.0	509.2	510.4	509.2	511.0	514.8
170°	533.2	528.2	523.1	520.1	518.1	515.0	514.0	516.0	514.0	515.0	518.1
172.5°	530.8	527.4	523.9	521.7	520.5	517.5	518.1	519.3	518.1	517.5	520.5
175°	528.2	526.1	524.1	523.1	523.1	521.1	522.1	523.1	522.1	521.1	523.1
177.5°	526.5	524.9	524.1	524.1	524.1	522.5	523.3	524.9	523.3	522.5	524.1
180°	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1



TEST NUMBER: P331269-840

CATALOG NUMBER: SA2XXDIP-C290D925U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9
2.5°	589.1	587.9	584.1	582.1	578.8	575.6	573.6	574.5	575.2	574.9	574.3
5°	572.1	567.7	561.1	555.4	551.3	543.7	540.5	538.9	537.5	535.9	534.3
7.5°	552.0	545.1	535.6	527.5	519.8	510.3	504.9	501.8	498.5	494.8	491.6
10°	537.8	528.1	518.0	506.5	497.4	488.9	481.3	476.3	471.6	467.3	464.1
12.5°	522.7	511.6	499.1	483.4	473.3	461.1	460.0	451.1	443.9	441.2	437.5
15°	498.8	483.1	467.3	448.7	440.7	429.7	422.8	415.9	409.7	405.4	404.2
17.5°	471.5	451.3	435.6	422.2	409.1	397.8	391.4	386.0	380.8	375.1	374.3
20°	450.8	433.3	416.2	404.5	390.9	379.4	371.6	366.2	361.7	358.3	355.4
22.5°	431.1	412.0	396.3	383.5	370.2	360.9	354.8	349.4	345.8	342.0	339.2
25°	399.6	384.8	367.5	353.0	342.0	336.1	331.0	326.5	324.2	321.6	318.4
27.5°	372.0	355.5	339.4	328.2	318.5	313.3	309.6	306.5	304.4	302.9	301.0
30°	352.6	335.9	323.3	312.3	304.2	298.9	296.6	294.8	292.3	291.3	290.4
32.5°	333.9	318.8	308.0	298.4	290.8	287.3	285.3	283.6	281.7	280.7	278.8
35°	307.4	294.8	284.3	278.9	272.8	269.7	268.2	265.9	264.1	263.2	262.9
37.5°	282.5	271.6	264.6	257.8	255.2	253.4	251.2	249.6	249.0	248.9	248.6
40°	266.3	257.4	251.2	245.7	244.6	241.8	239.9	238.6	238.6	238.8	238.6
42.5°	251.7	243.6	238.1	233.4	232.1	230.5	228.5	228.5	228.8	229.6	228.8
45°	229.4	223.7	219.7	217.5	215.0	213.4	213.1	213.8	214.0	214.3	215.0
47.5°	208.9	205.1	201.6	199.0	197.9	197.7	197.4	198.6	199.8	200.2	201.2
50°	196.8	192.5	189.5	187.8	186.9	186.5	186.9	188.3	189.2	190.4	191.1
52.5°	183.3	180.2	178.1	176.8	176.5	176.8	176.8	178.4	179.9	180.4	180.7
55°	164.5	162.2	161.8	159.7	160.6	160.4	161.5	162.4	163.8	165.2	165.4
57.5°	145.7	143.9	142.7	142.9	143.2	144.2	145.1	146.7	148.1	149.7	149.8
60°	133.3	132.4	131.7	131.7	132.1	133.5	134.6	136.2	137.1	138.1	138.8
62.5°	121.9	121.0	120.3	120.7	121.9	122.7	124.0	124.9	125.8	126.7	127.0
65°	103.9	103.5	104.1	104.6	104.8	105.9	107.6	108.3	109.2	109.7	111.3
67.5°	87.4	87.5	87.4	88.0	89.4	89.6	91.1	92.7	92.9	93.8	94.8
70°	76.1	76.6	77.1	77.6	78.7	79.2	80.3	81.0	81.9	82.6	83.3
72.5°	65.8	65.9	66.4	66.3	67.4	68.3	69.3	70.0	70.9	71.8	72.4
75°	50.7	50.7	51.2	51.4	52.5	53.7	53.4	53.9	54.8	55.7	56.2
77.5°	37.1	36.6	37.1	37.3	37.7	38.6	38.8	39.4	40.5	40.2	40.7
80°	28.2	27.6	28.2	28.5	28.5	29.6	29.6	30.1	30.7	30.1	30.7
82.5°	20.1	19.8	20.3	20.4	20.7	20.8	21.1	21.2	21.9	21.6	21.9
85°	10.1	9.9	10.1	9.9	10.1	10.3	10.3	10.1	10.1	10.5	9.9
87.5°	5.6	6.0	6.8	8.2	9.2	9.2	8.9	8.7	8.3	8.3	8.5
90°	12.1	15.1	20.2	27.2	33.2	34.2	33.2	32.2	30.2	32.2	33.2
92.5°	36.3	45.7	68.6	100.6	129.2	131.0	110.7	87.9	75.4	67.0	60.7
95°	74.6	98.8	145.1	232.8	349.7	395.1	345.7	264.1	202.6	160.3	138.0
97.5°	105.8	133.2	191.5	313.7	508.0	674.5	707.5	616.2	504.1	395.1	322.3
100°	126.0	154.2	207.6	330.6	548.3	796.2	941.4	920.2	795.2	657.1	535.2
102.5°	144.5	172.8	222.2	331.4	533.0	800.2	1028.4	1119.3	1091.2	990.2	860.9
105°	171.4	199.5	246.9	336.6	502.9	746.8	1014.9	1224.6	1338.5	1351.6	1318.3
107.5°	197.9	226.4	272.4	350.5	488.0	689.6	926.5	1148.8	1320.3	1425.1	1473.9
110°	215.7	244.9	289.2	361.8	484.8	662.2	870.8	1083.5	1263.8	1392.9	1475.5



TEST NUMBER: P331269-840

CATALOG NUMBER: SA2XXDIP-C290D925U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	232.6	262.7	305.4	374.0	485.5	644.4	832.1	1023.8	1197.0	1334.8	1429.6
115°	260.0	287.2	330.6	392.0	489.8	624.9	784.2	950.4	1105.6	1237.7	1341.5
117.5°	285.4	313.7	353.8	411.4	497.1	615.4	753.9	895.1	1031.5	1151.1	1248.6
120°	302.4	330.6	369.9	424.3	501.9	609.8	737.8	867.8	992.8	1099.5	1191.3
122.5°	319.3	348.3	385.2	435.6	507.6	606.5	724.1	846.0	960.5	1061.7	1144.6
125°	343.7	371.9	408.2	453.5	516.0	600.7	704.5	814.4	918.2	1006.8	1082.5
127.5°	365.3	394.3	429.6	470.3	524.7	597.2	686.4	783.2	877.1	960.7	1030.5
130°	379.0	407.2	442.4	480.8	531.2	595.6	674.3	763.0	849.6	929.3	995.8
132.5°	391.8	420.1	453.7	491.2	537.6	594.8	664.6	743.6	823.8	897.0	959.5
135°	409.2	437.4	469.7	504.9	545.2	593.6	651.1	716.6	783.2	849.6	906.1
137.5°	424.5	450.7	482.6	515.4	552.1	593.4	641.6	695.0	750.6	803.4	852.6
140°	433.4	459.6	489.8	521.1	555.3	592.6	636.0	681.4	729.7	776.1	820.4
142.5°	441.4	466.1	495.4	525.9	557.7	592.6	630.4	670.0	711.1	751.0	788.2
145°	454.5	476.8	503.9	532.2	560.4	590.6	622.9	654.1	687.4	718.6	747.8
147.5°	465.4	485.2	510.8	535.6	561.2	587.0	615.2	641.8	668.0	692.4	713.8
150°	472.7	490.8	514.0	537.1	560.4	584.6	608.7	633.0	655.1	676.3	694.4
152.5°	480.0	496.4	517.3	538.0	558.8	580.6	603.1	624.1	644.6	662.6	678.3
155°	489.8	504.9	522.1	539.2	556.3	573.5	592.6	611.8	627.9	643.0	654.1
157.5°	498.3	511.0	525.5	539.2	551.7	566.2	582.8	597.4	611.0	623.7	632.4
160°	503.9	515.0	527.1	539.2	549.3	561.4	575.5	588.5	599.7	610.8	617.8
162.5°	508.8	517.5	528.0	538.4	546.8	557.3	569.1	579.8	589.2	598.6	604.1
165°	514.0	520.1	529.2	536.2	542.2	549.3	558.4	566.4	573.5	580.6	584.6
167.5°	518.5	522.3	529.0	534.8	537.6	542.2	547.9	553.7	559.2	564.0	567.6
170°	520.1	523.1	528.2	533.2	535.2	538.2	542.2	547.2	550.3	554.3	556.3
172.5°	521.7	523.9	527.4	530.8	532.0	533.4	536.6	540.0	542.2	545.4	546.6
175°	523.1	524.1	526.1	528.2	527.1	528.2	529.2	532.2	533.2	534.2	535.2
177.5°	524.1	524.1	524.9	526.5	524.9	524.1	524.9	526.5	526.5	527.4	527.4
180°	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1



TEST NUMBER: P331269-840

CATALOG NUMBER: SA2XXDIP-C290D925U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9
2.5°	572.5	572.1	572.1	570.5	572.1	572.1	572.5	574.3	574.9	575.2	574.5
5°	531.1	530.4	529.3	530.4	529.3	530.4	531.1	534.3	535.9	537.5	538.9
7.5°	490.1	487.4	487.0	484.2	487.0	487.4	490.1	491.6	494.8	498.5	501.8
10°	460.2	458.4	458.1	453.7	458.1	458.4	460.2	464.1	467.3	471.6	476.3
12.5°	437.5	433.0	433.9	431.4	433.9	433.0	437.5	437.5	441.2	443.9	451.1
15°	398.0	398.0	397.1	393.2	397.1	398.0	398.0	404.2	405.4	409.7	415.9
17.5°	369.7	369.2	367.1	368.2	367.1	369.2	369.7	374.3	375.1	380.8	386.0
20°	352.8	351.4	348.7	348.7	348.7	351.4	352.8	355.4	358.3	361.7	366.2
22.5°	336.9	336.8	333.9	334.8	333.9	336.8	336.9	339.2	342.0	345.8	349.4
25°	318.2	316.4	315.0	315.7	315.0	316.4	318.2	318.4	321.6	324.2	326.5
27.5°	300.4	299.4	299.3	297.5	299.3	299.4	300.4	301.0	302.9	304.4	306.5
30°	290.2	287.9	288.3	287.2	288.3	287.9	290.2	290.4	291.3	292.3	294.8
32.5°	278.4	277.6	277.2	276.2	277.2	277.6	278.4	278.8	280.7	281.7	283.6
35°	262.5	262.7	261.6	262.0	261.6	262.7	262.5	262.9	263.2	264.1	265.9
37.5°	248.4	249.1	248.6	248.7	248.6	249.1	248.4	248.6	248.9	249.0	249.6
40°	239.2	239.2	239.2	239.9	239.2	239.2	239.2	238.6	238.8	238.6	238.6
42.5°	230.5	230.0	229.7	229.6	229.7	230.0	230.5	228.8	229.6	228.8	228.5
45°	215.4	216.1	216.3	215.2	216.3	216.1	215.4	215.0	214.3	214.0	213.8
47.5°	201.8	201.9	201.8	202.8	201.8	201.9	201.8	201.2	200.2	199.8	198.6
50°	192.3	191.8	192.3	191.8	192.3	191.8	192.3	191.1	190.4	189.2	188.3
52.5°	182.2	182.3	182.0	181.9	182.0	182.3	182.2	180.7	180.4	179.9	178.4
55°	166.3	166.7	166.5	166.5	166.5	166.7	166.3	165.4	165.2	163.8	162.4
57.5°	150.0	150.4	150.7	149.7	150.7	150.4	150.0	149.8	149.7	148.1	146.7
60°	138.6	139.7	139.5	139.1	139.5	139.7	138.6	138.8	138.1	137.1	136.2
62.5°	128.1	128.6	128.5	128.4	128.5	128.6	128.1	127.0	126.7	125.8	124.9
65°	112.0	112.4	111.7	112.4	111.7	112.4	112.0	111.3	109.7	109.2	108.3
67.5°	94.5	94.7	95.2	95.5	95.2	94.7	94.5	94.8	93.8	92.9	92.7
70°	83.7	83.5	84.2	84.9	84.2	83.5	83.7	83.3	82.6	81.9	81.0
72.5°	72.3	72.8	72.6	73.1	72.6	72.8	72.3	72.4	71.8	70.9	70.0
75°	55.7	56.5	56.2	56.9	56.2	56.5	55.7	56.2	55.7	54.8	53.9
77.5°	40.3	40.4	40.3	40.7	40.3	40.4	40.3	40.7	40.2	40.5	39.4
80°	30.7	30.3	29.8	30.7	29.8	30.3	30.7	30.7	30.1	30.7	30.1
82.5°	21.4	21.6	21.2	21.2	21.2	21.6	21.4	21.9	21.6	21.9	21.2
85°	9.9	9.6	9.2	9.2	9.2	9.6	9.9	9.9	10.5	10.1	10.1
87.5°	8.5	8.3	8.3	8.1	8.3	8.3	8.5	8.5	8.3	8.3	8.7
90°	33.2	33.2	33.2	33.2	33.2	33.2	33.2	33.2	32.2	30.2	32.2
92.5°	59.9	56.7	57.5	55.8	57.5	56.7	59.9	60.7	67.0	75.4	87.9
95°	125.0	116.9	113.9	114.9	113.9	116.9	125.0	138.0	160.3	202.6	264.1
97.5°	274.2	249.3	234.6	226.2	234.6	249.3	274.2	322.3	395.1	504.1	616.2
100°	451.5	408.2	379.0	360.8	379.0	408.2	451.5	535.2	657.1	795.2	920.2
102.5°	770.0	696.0	659.5	635.0	659.5	696.0	770.0	860.9	990.2	1091.2	1119.3
105°	1255.8	1193.4	1149.9	1135.9	1149.9	1193.4	1255.8	1318.3	1351.6	1338.5	1224.6
107.5°	1481.8	1478.3	1469.7	1451.0	1469.7	1478.3	1481.8	1473.9	1425.1	1320.3	1148.8
110°	1518.8	1538.0	1547.1	1546.1	1547.1	1538.0	1518.8	1475.5	1392.9	1263.8	1083.5



TEST NUMBER: P331269-840  
 CATALOG NUMBER: SA2XXDIP-C290D925U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1489.9	1521.9	1539.0	1544.5	1539.0	1521.9	1489.9	1429.6	1334.8	1197.0	1023.8
115°	1413.0	1459.4	1485.6	1494.7	1485.6	1459.4	1413.0	1341.5	1237.7	1105.6	950.4
117.5°	1321.5	1370.5	1398.2	1405.7	1398.2	1370.5	1321.5	1248.6	1151.1	1031.5	895.1
120°	1261.8	1309.2	1338.5	1348.6	1338.5	1309.2	1261.8	1191.3	1099.5	992.8	867.8
122.5°	1207.8	1254.4	1280.4	1288.9	1280.4	1254.4	1207.8	1144.6	1061.7	960.5	846.0
125°	1140.9	1179.2	1204.4	1212.4	1204.4	1179.2	1140.9	1082.5	1006.8	918.2	814.4
127.5°	1081.5	1117.3	1139.1	1145.6	1139.1	1117.3	1081.5	1030.5	960.7	877.1	783.2
130°	1045.2	1079.4	1099.5	1107.6	1099.5	1079.4	1045.2	995.8	929.3	849.6	763.0
132.5°	1008.0	1042.4	1060.9	1068.1	1060.9	1042.4	1008.0	959.5	897.0	823.8	743.6
135°	949.4	982.7	1000.8	1004.8	1000.8	982.7	949.4	906.1	849.6	783.2	716.6
137.5°	892.2	920.8	936.8	942.8	936.8	920.8	892.2	852.6	803.4	750.6	695.0
140°	852.6	878.9	894.0	900.0	894.0	878.9	852.6	820.4	776.1	729.7	681.4
142.5°	818.8	842.6	856.1	857.3	856.1	842.6	818.8	788.2	751.0	711.1	670.0
145°	772.0	789.2	799.2	802.2	799.2	789.2	772.0	747.8	718.6	687.4	654.1
147.5°	733.8	747.4	754.3	756.1	754.3	747.4	733.8	713.8	692.4	668.0	641.8
150°	709.5	721.6	727.7	728.7	727.7	721.6	709.5	694.4	676.3	655.1	633.0
152.5°	690.1	700.6	705.1	705.3	705.1	700.6	690.1	678.3	662.6	644.6	624.1
155°	665.2	672.3	676.3	674.3	676.3	672.3	665.2	654.1	643.0	627.9	611.8
157.5°	640.2	646.0	647.8	647.8	647.8	646.0	640.2	632.4	623.7	611.0	597.4
160°	624.9	630.0	631.0	631.0	631.0	630.0	624.9	617.8	610.8	599.7	588.5
162.5°	611.2	614.6	615.6	614.8	615.6	614.6	611.2	604.1	598.6	589.2	579.8
165°	588.5	592.6	592.6	591.6	592.6	592.6	588.5	584.6	580.6	573.5	566.4
167.5°	569.5	571.7	571.5	570.3	571.5	571.7	569.5	567.6	564.0	559.2	553.7
170°	557.3	560.4	559.4	557.3	559.4	560.4	557.3	556.3	554.3	550.3	547.2
172.5°	547.6	549.1	548.1	546.8	548.1	549.1	547.6	546.6	545.4	542.2	540.0
175°	535.2	536.2	535.2	533.2	535.2	536.2	535.2	535.2	534.2	533.2	532.2
177.5°	527.4	527.4	526.5	524.9	526.5	527.4	527.4	527.4	527.4	526.5	526.5
180°	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1



TEST NUMBER: P331269-840

CATALOG NUMBER: SA2XXDIP-C290D925U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9
2.5°	573.6	575.6	578.8	582.1	584.1	587.9	589.1	590.9	592.5	596.3	600.4
5°	540.5	543.7	551.3	555.4	561.1	567.7	572.1	576.7	581.8	590.5	598.5
7.5°	504.9	510.3	519.8	527.5	535.6	545.1	552.0	561.1	568.7	581.0	592.7
10°	481.3	488.9	497.4	506.5	518.0	528.1	537.8	549.2	558.4	573.1	586.8
12.5°	460.0	461.1	473.3	483.4	499.1	511.6	522.7	537.5	546.4	563.9	578.3
15°	422.8	429.7	440.7	448.7	467.3	483.1	498.8	514.1	524.4	546.0	565.0
17.5°	391.4	397.8	409.1	422.2	435.6	451.3	471.5	487.8	501.8	526.4	549.0
20°	371.6	379.4	390.9	404.5	416.2	433.3	450.8	469.4	484.5	512.3	538.7
22.5°	354.8	360.9	370.2	383.5	396.3	412.0	431.1	451.4	467.3	497.3	523.9
25°	331.0	336.1	342.0	353.0	367.5	384.8	399.6	421.9	445.0	473.0	505.3
27.5°	309.6	313.3	318.5	328.2	339.4	355.5	372.0	393.1	416.5	446.9	481.0
30°	296.6	298.9	304.2	312.3	323.3	335.9	352.6	372.7	396.7	427.4	461.3
32.5°	285.3	287.3	290.8	298.4	308.0	318.8	333.9	354.1	376.8	407.0	444.6
35°	268.2	269.7	272.8	278.9	284.3	294.8	307.4	325.8	347.1	376.0	415.0
37.5°	251.2	253.4	255.2	257.8	264.6	271.6	282.5	298.0	318.9	348.1	385.3
40°	239.9	241.8	244.6	245.7	251.2	257.4	266.3	280.5	301.6	328.3	364.6
42.5°	228.5	230.5	232.1	233.4	238.1	243.6	251.7	263.9	282.6	308.4	344.4
45°	213.1	213.4	215.0	217.5	219.7	223.7	229.4	239.9	254.4	278.7	311.3
47.5°	197.4	197.7	197.9	199.0	201.6	205.1	208.9	217.5	230.5	249.8	281.6
50°	186.9	186.5	186.9	187.8	189.5	192.5	196.8	203.0	213.6	231.7	260.8
52.5°	176.8	176.8	176.5	176.8	178.1	180.2	183.3	188.5	197.9	214.6	240.2
55°	161.5	160.4	160.6	159.7	161.8	162.2	164.5	168.8	177.1	188.5	212.7
57.5°	145.1	144.2	143.2	142.9	142.7	143.9	145.7	149.2	155.5	165.6	185.1
60°	134.6	133.5	132.1	131.7	131.7	132.4	133.3	135.8	141.8	150.7	166.7
62.5°	124.0	122.7	121.9	120.7	120.3	121.0	121.9	123.7	128.1	136.4	150.3
65°	107.6	105.9	104.8	104.6	104.1	103.5	103.9	105.7	109.2	115.8	126.8
67.5°	91.1	89.6	89.4	88.0	87.4	87.5	87.4	88.9	91.0	96.7	104.9
70°	80.3	79.2	78.7	77.6	77.1	76.6	76.1	77.6	79.6	84.4	91.5
72.5°	69.3	68.3	67.4	66.3	66.4	65.9	65.8	66.8	68.4	72.8	78.4
75°	53.4	53.7	52.5	51.4	51.2	50.7	50.7	51.4	52.1	55.5	59.9
77.5°	38.8	38.6	37.7	37.3	37.1	36.6	37.1	37.5	37.9	40.2	43.3
80°	29.6	29.6	28.5	28.5	28.2	27.6	28.2	27.8	28.7	31.0	33.2
82.5°	21.1	20.8	20.7	20.4	20.3	19.8	20.1	20.6	21.0	22.5	23.9
85°	10.3	10.3	10.1	9.9	10.1	9.9	10.1	10.3	10.5	11.2	12.4
87.5°	8.9	9.2	9.2	8.2	6.8	6.0	5.6	5.4	5.3	4.6	4.2
90°	33.2	34.2	33.2	27.2	20.2	15.1	12.1	10.1	8.1	4.0	1.0
92.5°	110.7	131.0	129.2	100.6	68.6	45.7	36.3	29.4	25.0	17.8	12.3
95°	345.7	395.1	349.7	232.8	145.1	98.8	74.6	58.5	49.4	39.3	35.2
97.5°	707.5	674.5	508.0	313.7	191.5	133.2	105.8	87.3	73.6	62.9	57.5
100°	941.4	796.2	548.3	330.6	207.6	154.2	126.0	105.8	89.7	80.6	77.6
102.5°	1028.4	800.2	533.0	331.4	222.2	172.8	144.5	123.6	107.4	98.4	96.1
105°	1014.9	746.8	502.9	336.6	246.9	199.5	171.4	149.2	134.0	127.0	123.0
107.5°	926.5	689.6	488.0	350.5	272.4	226.4	197.9	176.0	162.1	155.2	152.0
110°	870.8	662.2	484.8	361.8	289.2	244.9	215.7	194.5	181.4	175.4	171.4



TEST NUMBER: P331269-840

CATALOG NUMBER: SA2XXDIP-C290D925U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	832.1	644.4	485.5	374.0	305.4	262.7	232.6	212.3	200.0	193.1	189.0
115°	784.2	624.9	489.8	392.0	330.6	287.2	260.0	239.8	227.8	221.8	216.7
117.5°	753.9	615.4	497.1	411.4	353.8	313.7	285.4	266.1	255.4	249.3	245.3
120°	737.8	609.8	501.9	424.3	369.9	330.6	302.4	282.2	273.2	267.1	263.1
122.5°	724.1	606.5	507.6	435.6	385.2	348.3	319.3	299.1	289.2	283.2	280.0
125°	704.5	600.7	516.0	453.5	408.2	371.9	343.7	323.6	311.4	305.4	302.4
127.5°	686.4	597.2	524.7	470.3	429.6	394.3	365.3	345.9	332.5	324.2	320.1
130°	674.3	595.6	531.2	480.8	442.4	407.2	379.0	358.8	344.7	334.6	330.6
132.5°	664.6	594.8	537.6	491.2	453.7	420.1	391.8	370.9	356.0	345.1	340.2
135°	651.1	593.6	545.2	504.9	469.7	437.4	409.2	386.0	370.9	358.8	354.8
137.5°	641.6	593.4	552.1	515.4	482.6	450.7	424.5	401.5	385.4	373.3	368.5
140°	636.0	592.6	555.3	521.1	489.8	459.6	433.4	411.2	395.1	383.0	379.0
142.5°	630.4	592.6	557.7	525.9	495.4	466.1	441.4	420.1	403.9	392.6	389.4
145°	622.9	590.6	560.4	532.2	503.9	476.8	454.5	434.4	419.3	409.2	405.2
147.5°	615.2	587.0	561.2	535.6	510.8	485.2	465.4	448.7	434.7	425.2	422.1
150°	608.7	584.6	560.4	537.1	514.0	490.8	472.7	457.6	444.4	436.4	433.4
152.5°	603.1	580.6	558.8	538.0	517.3	496.4	480.0	465.6	454.1	446.1	444.6
155°	592.6	573.5	556.3	539.2	522.1	504.9	489.8	478.8	467.7	461.6	460.6
157.5°	582.8	566.2	551.7	539.2	525.5	511.0	498.3	489.4	479.8	474.9	473.9
160°	575.5	561.4	549.3	539.2	527.1	515.0	503.9	495.8	487.8	483.8	482.8
162.5°	569.1	557.3	546.8	538.4	528.0	517.5	508.8	501.5	495.0	491.0	491.6
165°	558.4	549.3	542.2	536.2	529.2	520.1	514.0	509.0	502.9	500.9	501.9
167.5°	547.9	542.2	537.6	534.8	529.0	522.3	518.5	514.8	511.0	509.2	510.4
170°	542.2	538.2	535.2	533.2	528.2	523.1	520.1	518.1	515.0	514.0	516.0
172.5°	536.6	533.4	532.0	530.8	527.4	523.9	521.7	520.5	517.5	518.1	519.3
175°	529.2	528.2	527.1	528.2	526.1	524.1	523.1	523.1	521.1	522.1	523.1
177.5°	524.9	524.1	524.9	526.5	524.9	524.1	524.1	524.1	522.5	523.3	524.9
180°	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1



TEST NUMBER: P331269-840

CATALOG NUMBER: SA2XXDIP-C290D925U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9
2.5°	600.1	601.0	603.9	606.8	610.2	611.1	612.5	611.3	610.9	614.3	616.9
5°	601.8	605.8	613.9	621.3	627.4	631.8	636.4	638.2	641.7	646.4	652.5
7.5°	599.8	607.8	620.5	631.2	642.8	651.2	657.7	663.4	670.1	679.2	689.2
10°	597.6	608.3	623.8	636.8	651.1	661.9	670.8	679.5	689.6	702.3	715.3
12.5°	593.6	606.3	625.6	641.1	659.3	669.9	682.0	700.7	711.7	729.2	747.6
15°	585.4	599.7	626.5	645.5	666.2	686.4	708.6	726.5	744.4	754.8	780.6
17.5°	573.4	594.2	624.0	646.2	672.5	704.2	729.2	749.5	770.1	786.9	799.9
20°	563.6	586.3	620.4	646.9	678.1	712.3	740.9	761.6	779.5	793.6	801.5
22.5°	551.4	580.0	613.0	644.2	684.0	717.8	747.9	764.2	779.1	786.0	789.1
25°	532.0	566.4	603.8	641.9	686.8	722.7	750.1	760.0	764.4	757.7	746.7
27.5°	511.1	549.5	593.2	637.5	685.1	719.5	739.2	737.7	730.3	708.7	691.6
30°	495.5	537.8	584.7	633.2	680.9	714.4	725.8	714.4	697.6	673.6	648.9
32.5°	479.2	522.9	575.7	626.9	673.2	702.7	705.1	685.4	659.4	632.1	601.5
35°	454.4	501.7	558.9	613.0	656.8	675.4	664.4	629.4	598.7	561.4	519.6
37.5°	426.5	478.7	535.9	592.6	632.3	637.1	609.8	573.1	529.7	485.7	436.6
40°	405.6	460.9	519.9	576.9	612.1	607.0	572.1	531.8	480.2	426.5	380.8
42.5°	386.9	442.1	502.2	558.3	586.3	572.5	531.8	482.2	426.8	376.2	334.4
45°	354.5	411.3	472.8	526.9	543.0	518.0	464.1	409.0	354.5	312.3	279.2
47.5°	323.0	379.2	440.1	487.7	493.3	459.7	400.8	344.2	297.2	262.9	239.5
50°	299.8	356.3	416.6	459.1	457.2	416.6	356.1	302.2	262.9	235.1	219.5
52.5°	279.1	332.4	390.3	429.0	419.2	375.0	317.1	269.2	237.0	215.3	201.2
55°	246.8	296.2	351.2	382.2	364.3	315.2	266.3	227.8	203.9	187.6	176.6
57.5°	214.8	261.1	308.2	327.3	307.5	262.2	221.5	193.5	175.5	163.5	156.3
60°	195.0	235.4	277.3	293.9	270.2	229.8	197.7	172.8	158.2	148.5	142.0
62.5°	175.2	211.4	251.0	259.9	238.3	204.2	175.7	154.9	143.1	134.3	128.3
65°	148.1	177.8	207.8	213.8	193.9	167.4	145.0	131.5	120.9	114.5	109.7
67.5°	121.6	145.3	166.6	171.4	153.9	135.6	119.4	107.6	100.5	95.1	91.0
70°	105.7	124.6	142.0	145.9	131.9	115.6	103.2	93.8	87.4	82.8	78.9
72.5°	89.1	104.7	119.3	121.9	110.5	98.0	87.9	80.4	74.7	71.8	68.1
75°	68.2	77.4	88.6	89.3	81.7	74.1	66.3	61.5	58.5	54.8	53.0
77.5°	48.1	55.2	61.7	62.9	58.5	53.3	49.0	45.1	42.6	40.9	39.2
80°	36.7	42.4	45.2	46.8	43.6	39.9	37.4	34.8	33.2	32.1	31.0
82.5°	26.3	29.8	32.3	33.6	31.8	29.6	27.2	25.7	24.4	23.5	23.1
85°	13.3	14.9	16.6	17.0	16.6	15.6	14.2	14.2	13.5	13.3	13.3
87.5°	5.4	7.0	7.4	8.3	8.5	9.5	10.9	12.0	12.0	11.6	11.2
90°	4.0	8.1	10.1	12.1	15.1	20.2	27.2	33.2	34.2	33.2	32.2
92.5°	17.8	25.0	29.4	36.3	45.7	68.6	100.6	129.2	131.0	110.7	87.9
95°	39.3	49.4	58.5	74.6	98.8	145.1	232.8	349.7	395.1	345.7	264.1
97.5°	62.9	73.6	87.3	105.8	133.2	191.5	313.7	508.0	674.5	707.5	616.2
100°	80.6	89.7	105.8	126.0	154.2	207.6	330.6	548.3	796.2	941.4	920.2
102.5°	98.4	107.4	123.6	144.5	172.8	222.2	331.4	533.0	800.2	1028.4	1119.3
105°	127.0	134.0	149.2	171.4	199.5	246.9	336.6	502.9	746.8	1014.9	1224.6
107.5°	155.2	162.1	176.0	197.9	226.4	272.4	350.5	488.0	689.6	926.5	1148.8
110°	175.4	181.4	194.5	215.7	244.9	289.2	361.8	484.8	662.2	870.8	1083.5





TEST NUMBER: P331269-840

CATALOG NUMBER: SA2XXDIP-C290D925U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	193.1	200.0	212.3	232.6	262.7	305.4	374.0	485.5	644.4	832.1	1023.8
115°	221.8	227.8	239.8	260.0	287.2	330.6	392.0	489.8	624.9	784.2	950.4
117.5°	249.3	255.4	266.1	285.4	313.7	353.8	411.4	497.1	615.4	753.9	895.1
120°	267.1	273.2	282.2	302.4	330.6	369.9	424.3	501.9	609.8	737.8	867.8
122.5°	283.2	289.2	299.1	319.3	348.3	385.2	435.6	507.6	606.5	724.1	846.0
125°	305.4	311.4	323.6	343.7	371.9	408.2	453.5	516.0	600.7	704.5	814.4
127.5°	324.2	332.5	345.9	365.3	394.3	429.6	470.3	524.7	597.2	686.4	783.2
130°	334.6	344.7	358.8	379.0	407.2	442.4	480.8	531.2	595.6	674.3	763.0
132.5°	345.1	356.0	370.9	391.8	420.1	453.7	491.2	537.6	594.8	664.6	743.6
135°	358.8	370.9	386.0	409.2	437.4	469.7	504.9	545.2	593.6	651.1	716.6
137.5°	373.3	385.4	401.5	424.5	450.7	482.6	515.4	552.1	593.4	641.6	695.0
140°	383.0	395.1	411.2	433.4	459.6	489.8	521.1	555.3	592.6	636.0	681.4
142.5°	392.6	403.9	420.1	441.4	466.1	495.4	525.9	557.7	592.6	630.4	670.0
145°	409.2	419.3	434.4	454.5	476.8	503.9	532.2	560.4	590.6	622.9	654.1
147.5°	425.2	434.7	448.7	465.4	485.2	510.8	535.6	561.2	587.0	615.2	641.8
150°	436.4	444.4	457.6	472.7	490.8	514.0	537.1	560.4	584.6	608.7	633.0
152.5°	446.1	454.1	465.6	480.0	496.4	517.3	538.0	558.8	580.6	603.1	624.1
155°	461.6	467.7	478.8	489.8	504.9	522.1	539.2	556.3	573.5	592.6	611.8
157.5°	474.9	479.8	489.4	498.3	511.0	525.5	539.2	551.7	566.2	582.8	597.4
160°	483.8	487.8	495.8	503.9	515.0	527.1	539.2	549.3	561.4	575.5	588.5
162.5°	491.0	495.0	501.5	508.8	517.5	528.0	538.4	546.8	557.3	569.1	579.8
165°	500.9	502.9	509.0	514.0	520.1	529.2	536.2	542.2	549.3	558.4	566.4
167.5°	509.2	511.0	514.8	518.5	522.3	529.0	534.8	537.6	542.2	547.9	553.7
170°	514.0	515.0	518.1	520.1	523.1	528.2	533.2	535.2	538.2	542.2	547.2
172.5°	518.1	517.5	520.5	521.7	523.9	527.4	530.8	532.0	533.4	536.6	540.0
175°	522.1	521.1	523.1	523.1	524.1	526.1	528.2	527.1	528.2	529.2	532.2
177.5°	523.3	522.5	524.1	524.1	524.1	524.9	526.5	524.9	524.1	524.9	526.5
180°	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1



TEST NUMBER: P331269-840

CATALOG NUMBER: SA2XXDIP-C290D925U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	596.9	596.9	596.9	596.9	596.9	596.9	596.9
2.5°	619.1	621.7	621.7	622.1	625.0	624.6	624.4
5°	658.8	662.8	663.2	667.3	670.0	669.1	666.6
7.5°	696.3	703.6	709.1	712.2	715.8	718.0	717.0
10°	726.1	736.6	743.1	747.4	752.7	756.6	755.2
12.5°	753.1	765.6	774.5	781.9	782.5	787.6	784.2
15°	795.2	808.4	809.8	815.3	819.7	819.2	819.4
17.5°	809.0	813.2	814.2	814.3	814.4	812.7	809.2
20°	804.1	802.4	798.6	795.6	790.3	789.6	785.1
22.5°	780.5	775.5	765.7	759.2	751.0	748.9	747.6
25°	734.4	723.1	707.5	692.6	688.4	680.4	682.7
27.5°	670.9	653.4	636.4	624.4	613.4	601.4	604.8
30°	626.3	606.5	582.7	564.3	552.6	541.2	539.1
32.5°	573.1	544.1	517.6	501.4	483.4	476.2	468.3
35°	481.3	453.0	426.7	403.9	390.9	380.8	371.6
37.5°	398.8	366.3	345.0	326.6	317.1	311.3	312.9
40°	347.6	319.1	303.5	289.5	280.7	276.7	277.6
42.5°	306.1	284.8	272.0	262.4	256.2	253.9	253.4
45°	259.0	247.1	236.5	231.1	228.0	225.5	223.9
47.5°	226.9	217.1	211.2	207.9	205.3	202.8	202.7
50°	207.6	201.2	197.0	193.6	191.6	189.8	191.4
52.5°	192.9	187.0	182.9	179.9	179.0	177.4	177.3
55°	171.2	166.5	163.6	160.8	159.5	158.5	157.3
57.5°	151.3	146.9	144.2	142.5	139.9	139.0	138.6
60°	137.1	133.7	131.0	128.7	127.5	125.7	125.7
62.5°	124.1	120.7	118.2	116.4	114.5	113.8	114.0
65°	105.3	102.5	100.0	98.2	97.8	96.3	96.8
67.5°	88.0	86.1	83.4	82.4	81.6	80.9	80.3
70°	76.3	74.5	73.2	71.8	71.1	71.1	71.1
72.5°	66.7	64.4	63.6	61.9	62.3	61.6	60.8
75°	51.6	50.2	49.6	48.9	47.8	47.8	47.8
77.5°	38.0	37.6	36.8	36.1	35.7	35.5	35.6
80°	29.4	29.1	28.7	28.7	28.2	28.0	27.6
82.5°	22.6	22.0	21.7	21.5	21.4	21.4	21.3
85°	12.8	12.4	12.4	12.6	12.1	12.1	12.4
87.5°	11.0	11.4	11.4	11.4	11.6	11.4	11.4
90°	30.2	32.2	33.2	33.2	33.2	33.2	33.2
92.5°	75.4	67.0	60.7	59.9	56.7	57.5	55.8
95°	202.6	160.3	138.0	125.0	116.9	113.9	114.9
97.5°	504.1	395.1	322.3	274.2	249.3	234.6	226.2
100°	795.2	657.1	535.2	451.5	408.2	379.0	360.8
102.5°	1091.2	990.2	860.9	770.0	696.0	659.5	635.0
105°	1338.5	1351.6	1318.3	1255.8	1193.4	1149.9	1135.9
107.5°	1320.3	1425.1	1473.9	1481.8	1478.3	1469.7	1451.0
110°	1263.8	1392.9	1475.5	1518.8	1538.0	1547.1	1546.1



TEST NUMBER: P331269-840

CATALOG NUMBER: SA2XXDIP-C290D925U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	1197.0	1334.8	1429.6	1489.9	1521.9	1539.0	1544.5
115°	1105.6	1237.7	1341.5	1413.0	1459.4	1485.6	1494.7
117.5°	1031.5	1151.1	1248.6	1321.5	1370.5	1398.2	1405.7
120°	992.8	1099.5	1191.3	1261.8	1309.2	1338.5	1348.6
122.5°	960.5	1061.7	1144.6	1207.8	1254.4	1280.4	1288.9
125°	918.2	1006.8	1082.5	1140.9	1179.2	1204.4	1212.4
127.5°	877.1	960.7	1030.5	1081.5	1117.3	1139.1	1145.6
130°	849.6	929.3	995.8	1045.2	1079.4	1099.5	1107.6
132.5°	823.8	897.0	959.5	1008.0	1042.4	1060.9	1068.1
135°	783.2	849.6	906.1	949.4	982.7	1000.8	1004.8
137.5°	750.6	803.4	852.6	892.2	920.8	936.8	942.8
140°	729.7	776.1	820.4	852.6	878.9	894.0	900.0
142.5°	711.1	751.0	788.2	818.8	842.6	856.1	857.3
145°	687.4	718.6	747.8	772.0	789.2	799.2	802.2
147.5°	668.0	692.4	713.8	733.8	747.4	754.3	756.1
150°	655.1	676.3	694.4	709.5	721.6	727.7	728.7
152.5°	644.6	662.6	678.3	690.1	700.6	705.1	705.3
155°	627.9	643.0	654.1	665.2	672.3	676.3	674.3
157.5°	611.0	623.7	632.4	640.2	646.0	647.8	647.8
160°	599.7	610.8	617.8	624.9	630.0	631.0	631.0
162.5°	589.2	598.6	604.1	611.2	614.6	615.6	614.8
165°	573.5	580.6	584.6	588.5	592.6	592.6	591.6
167.5°	559.2	564.0	567.6	569.5	571.7	571.5	570.3
170°	550.3	554.3	556.3	557.3	560.4	559.4	557.3
172.5°	542.2	545.4	546.6	547.6	549.1	548.1	546.8
175°	533.2	534.2	535.2	535.2	536.2	535.2	533.2
177.5°	526.5	527.4	527.4	527.4	527.4	526.5	524.9
180°	524.1	524.1	524.1	524.1	524.1	524.1	524.1

(END OF REPORT)