

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331623-840

Luminaire Tested: **SA2XXRDIP-C290D530U840-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331623-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C290D530U840-4F0-1E-UDD-A4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 530 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3227.6 lumens
Efficiency: N/A
Efficacy: 126.1 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 25.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331623-840
CATALOG NUMBER: SA2XXRDIP-C290D530U840-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331623-840

CATALOG NUMBER: SA2XXRDIP-C290D530U840-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	43	43	43	35
1	95	91	87	84	86	83	79	77	67	65	63	52	51	49	39	38	37	31
2	87	80	74	70	79	73	68	64	59	56	53	46	44	42	35	33	32	27
3	80	71	64	59	72	65	59	54	53	48	45	42	39	36	31	29	28	23
4	73	63	56	50	66	58	51	46	47	43	39	37	34	32	28	26	25	21
5	67	56	49	43	61	52	45	40	42	38	34	34	30	28	26	24	22	18
6	62	51	43	38	56	47	40	35	38	34	30	31	27	25	24	21	20	17
7	58	46	39	33	52	42	36	31	35	30	27	28	25	22	22	19	18	15
8	54	42	35	30	49	39	32	28	32	27	24	26	22	20	20	18	16	14
9	50	38	31	26	45	35	29	25	29	25	21	24	20	18	19	16	15	12
10	47	35	28	24	42	32	26	22	27	23	19	22	19	16	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10658	10658	10658	10658
5°	11904	10726	9511	10726
10°	13209	10650	8243	10650
15°	13857	10494	6496	10494
20°	12014	10263	5620	10263
25°	7878	9948	5018	9948
30°	5304	9562	4542	9562
35°	4295	9079	4096	9079
40°	3819	8553	3792	8553
45°	3457	7935	3382	7935
50°	3145	7322	3135	7322
55°	2956	6643	2919	6643
60°	2474	6022	2444	6022
65°	2086	5467	2365	5467
70°	1926	4881	2233	4881
75°	1803	4255	2059	4255
80°	1664	3505	1832	3505
85°	1538	2760	1612	2760



TEST NUMBER: P331623-840

CATALOG NUMBER: SA2XXRDIP-C290D530U840-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	62.6	1.9
10°-20°	174.4	5.4
20°-30°	224.7	7.0
30°-40°	213.5	6.6
40°-50°	182.9	5.7
50°-60°	139.3	4.3
60°-70°	88.1	2.7
70°-80°	44.0	1.4
80°-90°	14.2	0.4
90°-100°	119.7	3.7
100°-110°	406.3	12.6
110°-120°	431.7	13.4
120°-130°	355.4	11.0
130°-140°	285.4	8.8
140°-150°	215.7	6.7
150°-160°	151.6	4.7
160°-170°	89.2	2.8
170°-180°	29.0	0.9
0°-30°	461.7	14.3
0°-40°	675.2	20.9
0°-60°	997.5	30.9
0°-90°	1143.7	35.4
90°-120°	957.8	29.7
90°-150°	1814.1	56.2
90°-180°	2084.0	64.6
0°-180°	3227.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	660	660	660	660	660	
5°	734	662	587	662	734	72
15°	829	628	389	628	829	224
25°	442	558	282	558	442	210
35°	218	461	208	461	218	139
45°	151	348	148	348	151	117
55°	105	236	104	236	105	92
65°	55	143	62	143	55	56
75°	29	68	33	68	29	31
85°	8	15	9	15	8	9
90°	19	1	19	1	19	11
95°	66	20	66	20	66	85
105°	649	70	649	70	649	628
115°	854	124	854	124	854	836
125°	693	173	693	173	693	626
135°	574	203	574	203	574	446
145°	458	232	458	232	458	291
155°	385	263	385	263	385	180
165°	338	287	338	287	338	97
175°	305	299	305	299	305	30
180°	299	299	299	299	299	



TEST NUMBER: P331623-840
 CATALOG NUMBER: SA2XXRDIP-C290D530U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1
2.5°	687.0	687.5	688.1	686.8	686.8	685.7	683.3	681.5	676.3	675.6	675.6
5°	734.5	734.1	735.0	732.0	727.9	726.9	722.6	716.8	710.8	704.3	702.9
7.5°	781.7	781.0	779.2	778.7	775.6	768.6	761.6	754.2	744.3	734.6	729.7
10°	805.7	813.2	808.6	800.6	802.1	791.4	785.7	775.8	767.5	753.1	749.9
12.5°	829.1	832.1	830.6	826.1	824.0	816.6	808.8	800.2	785.0	772.0	760.7
15°	829.0	833.3	834.6	833.1	834.2	833.8	829.7	822.6	809.3	795.1	782.6
17.5°	767.8	770.8	778.4	783.5	789.9	803.4	810.2	812.7	810.8	802.6	794.0
20°	699.2	694.2	715.3	726.0	735.2	758.1	777.9	785.5	797.6	797.4	795.1
22.5°	601.9	603.1	623.1	635.9	662.7	685.7	708.1	736.6	760.1	775.7	784.8
25°	442.2	451.0	470.9	488.4	518.2	560.9	599.7	644.6	687.0	720.5	752.5
27.5°	332.1	332.9	348.6	364.8	382.4	417.4	466.3	519.9	580.4	630.4	687.7
30°	284.5	283.1	289.7	299.6	314.8	341.8	378.5	431.2	491.6	566.8	633.8
32.5°	250.6	250.7	255.8	263.1	275.6	293.9	319.0	361.9	418.9	492.9	571.4
35°	217.9	217.7	221.4	226.6	231.9	243.6	260.8	283.3	322.6	391.5	471.8
37.5°	194.4	195.4	197.2	200.6	206.3	212.9	223.2	238.3	266.2	307.1	374.6
40°	181.2	181.7	184.2	186.9	190.4	195.4	203.9	216.1	236.5	269.0	318.4
42.5°	169.2	169.6	171.4	173.9	176.6	181.7	188.7	199.2	215.8	241.2	281.9
45°	151.4	151.4	153.0	154.1	157.1	161.7	167.4	176.2	187.6	206.4	233.5
47.5°	134.8	134.8	135.9	137.8	139.8	143.3	149.0	156.1	164.4	178.9	202.1
50°	125.2	125.5	126.1	127.7	129.0	132.1	136.5	142.7	151.4	162.7	181.9
52.5°	117.5	117.4	118.3	119.0	119.8	122.0	125.3	130.8	138.6	148.3	164.3
55°	105.0	104.1	105.5	106.6	107.3	108.3	110.1	113.5	120.2	128.5	140.4
57.5°	89.5	89.1	90.1	91.1	93.3	95.7	97.4	99.5	102.9	108.9	120.7
60°	76.6	76.6	78.7	79.4	81.9	85.1	88.4	90.2	93.6	97.5	106.2
62.5°	65.2	65.4	66.3	67.1	68.5	72.4	77.0	81.0	84.2	88.0	93.7
65°	54.6	55.0	55.0	55.5	56.5	57.4	59.2	62.4	68.2	73.4	77.8
67.5°	46.4	46.5	46.7	47.1	47.3	48.3	49.1	50.5	51.8	56.8	62.2
70°	40.8	41.5	41.3	41.7	42.0	42.4	43.3	44.0	46.2	47.3	50.5
72.5°	35.6	36.2	36.2	36.5	37.1	37.2	37.9	38.6	39.9	40.8	42.6
75°	28.9	28.7	28.9	29.4	29.6	29.8	29.8	30.7	31.4	32.3	33.5
77.5°	22.3	22.5	22.5	22.5	22.6	23.0	22.9	23.3	24.0	24.5	25.0
80°	17.9	18.1	17.9	18.1	18.4	18.6	18.4	18.6	19.3	19.7	19.7
82.5°	13.8	13.9	14.0	14.0	14.1	14.1	14.5	14.5	15.0	14.9	15.1
85°	8.3	8.1	8.1	8.1	8.3	8.5	8.3	8.3	8.5	8.5	8.5
87.5°	6.8	7.0	7.0	7.0	7.0	6.8	6.6	7.0	7.0	7.2	7.0
90°	19.0	19.0	19.0	19.0	19.0	18.4	17.3	18.4	19.0	19.6	19.0
92.5°	31.9	32.8	32.4	34.2	34.6	38.3	43.1	50.2	63.2	74.8	73.8
95°	65.6	65.0	66.9	71.4	78.9	91.6	115.7	150.9	197.5	225.8	199.9
97.5°	129.3	134.1	142.5	156.6	184.2	225.8	288.1	352.1	404.2	385.4	290.2
100°	206.2	216.5	233.3	258.0	305.8	375.5	454.4	525.8	537.9	454.9	313.3
102.5°	362.8	376.9	397.7	440.0	491.9	565.8	623.5	639.6	587.6	457.3	304.6
105°	649.0	657.1	681.9	717.6	753.3	772.3	764.8	699.7	580.0	426.8	287.4
107.5°	829.1	839.8	844.8	846.7	842.2	814.4	754.5	656.4	529.4	394.0	278.8
110°	883.4	884.0	878.9	867.9	843.1	795.9	722.2	619.1	497.6	378.4	277.0



TEST NUMBER: P331623-840
 CATALOG NUMBER: SA2XXRDIP-C290D530U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	882.5	879.4	869.6	851.3	816.9	762.8	684.0	585.0	475.4	368.2	277.5
115°	854.0	848.9	833.9	807.4	766.6	707.2	631.8	543.1	448.1	357.1	279.9
117.5°	803.2	798.9	783.2	755.2	713.5	657.8	589.4	511.5	430.8	351.6	284.1
120°	770.5	764.8	748.1	721.0	680.8	628.3	567.2	495.8	421.6	348.4	286.8
122.5°	736.5	731.6	716.8	690.1	654.0	606.6	548.9	483.4	413.7	346.6	290.0
125°	692.9	688.2	673.8	652.0	618.5	575.3	524.6	465.3	402.5	343.3	294.9
127.5°	654.6	650.9	638.4	617.9	588.9	549.0	501.2	447.5	392.2	341.3	299.8
130°	632.9	628.3	616.8	597.2	569.0	531.0	485.5	436.0	385.3	340.3	303.5
132.5°	610.4	606.2	595.6	576.0	548.3	512.6	470.8	425.0	379.7	339.9	307.2
135°	574.2	571.9	561.5	542.5	517.8	485.5	447.5	409.5	372.0	339.2	311.5
137.5°	538.7	535.2	526.1	509.8	487.3	459.1	429.0	397.2	366.6	339.1	315.5
140°	514.3	510.8	502.2	487.3	468.8	443.4	417.0	389.3	363.5	338.6	317.3
142.5°	489.9	489.2	481.5	467.9	450.4	429.2	406.4	382.8	360.2	338.6	318.7
145°	458.4	456.7	450.9	441.1	427.4	410.6	392.7	373.8	355.9	337.5	320.2
147.5°	432.0	431.0	427.1	419.3	407.9	395.7	381.7	366.8	351.5	335.4	320.6
150°	416.4	415.8	412.3	405.5	396.8	386.5	374.4	361.6	347.9	334.1	320.2
152.5°	403.0	402.9	400.4	394.4	387.6	378.6	368.4	356.6	344.7	331.7	319.3
155°	385.3	386.5	384.2	380.1	373.8	367.4	358.8	349.6	338.6	327.7	317.9
157.5°	370.2	370.2	369.2	365.8	361.3	356.4	349.1	341.4	333.0	323.6	315.3
160°	360.5	360.5	359.9	357.1	353.0	349.0	342.6	336.3	328.8	320.8	313.9
162.5°	351.3	351.7	351.2	349.2	345.2	342.1	336.7	331.2	325.2	318.5	312.5
165°	338.1	338.6	338.6	336.3	334.1	331.7	327.7	323.7	319.0	313.9	309.8
167.5°	325.9	326.6	326.7	325.4	324.4	322.2	319.5	316.4	313.1	309.8	307.2
170°	318.5	319.6	320.2	318.5	317.9	316.8	314.5	312.8	309.8	307.5	305.8
172.5°	312.5	313.2	313.8	313.0	312.4	311.6	309.8	308.6	306.6	304.8	304.0
175°	304.7	305.8	306.4	305.8	305.8	305.3	304.7	304.1	302.4	301.7	301.2
177.5°	299.9	300.8	301.3	301.3	301.3	301.3	300.8	300.8	299.9	299.4	299.9
180°	299.4	299.4	299.4	299.4	299.4	299.4	299.4	299.4	299.4	299.4	299.4



TEST NUMBER: P331623-840

CATALOG NUMBER: SA2XXRDIP-C290D530U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1
2.5°	676.0	674.5	673.2	669.9	668.2	664.6	664.1	663.9	659.1	654.5	653.2
5°	699.2	695.5	690.0	683.6	676.9	670.0	665.5	661.8	652.6	643.9	638.8
7.5°	722.6	714.7	705.2	693.1	682.9	671.6	663.1	655.5	642.5	630.0	621.6
10°	740.0	727.2	714.6	697.8	684.7	671.9	659.9	649.6	635.0	618.4	606.7
12.5°	750.8	736.7	719.3	703.0	686.0	669.6	653.7	640.5	623.2	606.1	592.3
15°	765.5	750.3	729.2	705.8	684.1	662.7	644.4	627.8	605.4	584.9	567.9
17.5°	777.5	756.6	734.0	706.9	681.7	654.6	631.0	609.9	584.8	560.2	540.2
20°	781.3	760.6	734.5	707.4	677.6	645.7	620.3	597.3	570.5	543.6	520.7
22.5°	778.9	762.9	733.8	701.4	670.9	637.5	608.7	582.1	552.3	524.9	498.4
25°	762.8	757.2	729.7	694.4	659.5	620.8	587.4	558.4	524.4	495.0	466.2
27.5°	725.0	736.9	719.8	682.2	643.4	601.9	564.4	531.3	496.0	463.0	434.2
30°	688.6	715.9	708.6	673.7	630.4	589.6	547.5	512.9	475.3	441.3	412.9
32.5°	638.9	684.0	691.2	662.0	617.1	572.3	528.3	493.8	454.5	418.8	391.0
35°	559.7	627.1	658.1	639.5	594.6	546.1	500.8	460.6	421.1	385.9	358.3
37.5°	465.2	557.1	608.7	610.1	568.8	518.5	469.0	429.1	388.7	354.1	324.3
40°	403.9	503.5	570.8	585.6	550.8	496.4	446.4	405.8	366.4	332.3	298.2
42.5°	348.9	448.1	530.7	556.6	529.0	474.9	424.7	382.3	344.0	311.8	276.9
45°	282.2	368.9	459.9	506.2	490.9	440.9	387.9	347.5	311.5	283.8	250.2
47.5°	238.0	299.1	387.3	449.9	449.7	404.0	351.8	313.3	279.8	253.8	226.7
50°	212.9	266.1	340.6	411.7	417.7	379.4	329.8	291.5	260.3	233.1	211.3
52.5°	190.3	234.2	301.1	369.4	386.4	353.1	305.1	269.7	239.4	214.3	195.7
55°	160.8	194.8	245.7	309.4	335.2	311.7	269.0	236.0	211.5	190.4	174.3
57.5°	136.0	161.5	202.4	253.7	283.6	268.9	233.7	206.8	185.8	166.7	154.1
60°	120.5	141.3	175.9	218.8	251.9	241.6	211.5	186.5	168.6	152.1	140.2
62.5°	105.7	123.7	153.4	188.2	218.4	214.2	189.7	168.6	153.0	137.9	127.8
65°	85.1	98.2	121.4	148.7	173.0	175.0	157.3	143.1	129.2	117.2	108.3
67.5°	67.8	76.3	92.6	115.6	133.8	140.4	129.6	118.7	107.6	98.4	90.6
70°	57.2	64.0	75.9	94.5	111.3	118.2	111.9	103.4	93.8	86.2	79.6
72.5°	46.3	53.0	61.8	75.4	89.8	97.3	95.0	89.0	81.2	74.8	68.6
75°	34.8	37.0	42.9	52.1	63.3	69.8	71.3	68.2	61.9	57.2	53.4
77.5°	25.8	27.1	29.9	34.6	42.0	47.8	50.1	49.7	45.4	42.7	39.2
80°	20.6	21.3	22.7	24.7	30.3	36.1	37.7	37.7	34.6	33.5	30.1
82.5°	15.7	16.2	17.1	18.2	20.7	25.8	27.6	27.9	26.1	24.5	21.8
85°	9.0	8.7	9.2	9.9	10.3	11.7	14.4	14.9	14.4	12.6	11.9
87.5°	6.3	5.7	5.0	4.5	4.4	4.4	4.8	5.5	5.0	4.9	4.8
90°	15.6	11.5	8.7	6.9	5.8	4.6	2.3	0.6	2.3	4.6	5.8
92.5°	57.5	39.2	26.2	20.7	16.9	14.2	10.1	7.1	10.1	14.2	16.9
95°	133.0	82.9	56.5	42.6	33.4	28.2	22.4	20.2	22.4	28.2	33.4
97.5°	179.3	109.5	76.1	60.5	49.9	42.0	36.0	32.8	36.0	42.0	49.9
100°	188.9	118.7	88.2	72.0	60.5	51.3	46.0	44.3	46.0	51.3	60.5
102.5°	189.3	126.9	98.7	82.6	70.6	61.4	56.2	54.9	56.2	61.4	70.6
105°	192.4	141.1	114.0	97.9	85.2	76.5	72.6	70.3	72.6	76.5	85.2
107.5°	200.3	155.6	129.4	113.1	100.6	92.6	88.7	86.8	88.7	92.6	100.6
110°	206.7	165.3	140.0	123.2	111.2	103.7	100.2	97.9	100.2	103.7	111.2



TEST NUMBER: P331623-840

CATALOG NUMBER: SA2XXRDIP-C290D530U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	213.7	174.5	150.1	132.9	121.3	114.2	110.4	108.1	110.4	114.2	121.3
115°	224.0	188.9	164.1	148.6	137.0	130.2	126.7	123.8	126.7	130.2	137.0
117.5°	235.1	202.2	179.3	163.1	152.1	145.9	142.5	140.2	142.5	145.9	152.1
120°	242.5	211.4	188.9	172.8	161.3	156.0	152.6	150.3	152.6	156.0	161.3
122.5°	248.9	220.2	199.0	182.5	171.0	165.3	161.9	160.0	161.9	165.3	171.0
125°	259.1	233.3	212.5	196.4	184.9	177.9	174.5	172.8	174.5	177.9	184.9
127.5°	268.7	245.5	225.3	208.7	197.6	190.1	185.2	182.9	185.2	190.1	197.6
130°	274.7	252.9	232.7	216.5	205.0	196.9	191.2	188.9	191.2	196.9	205.0
132.5°	280.7	259.2	240.0	223.9	212.0	203.4	197.2	194.4	197.2	203.4	212.0
135°	288.5	268.4	249.9	233.8	220.6	212.0	205.0	202.7	205.0	212.0	220.6
137.5°	294.5	275.8	257.5	242.6	229.4	220.3	213.3	210.6	213.3	220.3	229.4
140°	297.7	279.9	262.7	247.6	235.0	225.8	218.8	216.5	218.8	225.8	235.0
142.5°	300.5	283.2	266.3	252.3	240.0	230.9	224.4	222.6	224.4	230.9	240.0
145°	304.1	287.9	272.4	259.7	248.2	239.5	233.8	231.6	233.8	239.5	248.2
147.5°	306.1	291.9	277.2	266.0	256.4	248.4	242.9	241.2	242.9	248.4	256.4
150°	307.0	293.7	280.4	270.1	261.5	254.0	249.3	247.6	249.3	254.0	261.5
152.5°	307.4	295.6	283.7	274.3	266.1	259.5	254.9	254.1	254.9	259.5	266.1
155°	308.1	298.3	288.5	279.9	273.6	267.2	263.8	263.2	263.8	267.2	273.6
157.5°	308.1	300.2	292.0	284.8	279.6	274.2	271.4	270.7	271.4	274.2	279.6
160°	308.1	301.2	294.3	287.9	283.4	278.7	276.4	275.9	276.4	278.7	283.4
162.5°	307.6	301.6	295.7	290.7	286.6	282.9	280.5	280.9	280.5	282.9	286.6
165°	306.4	302.4	297.2	293.7	290.8	287.4	286.2	286.8	286.2	287.4	290.8
167.5°	305.6	302.3	298.4	296.3	294.2	292.0	290.9	291.6	290.9	292.0	294.2
170°	304.7	301.7	298.9	297.2	296.0	294.3	293.7	294.9	293.7	294.3	296.0
172.5°	303.3	301.3	299.3	298.1	297.4	295.7	296.0	296.7	296.0	295.7	297.4
175°	301.7	300.6	299.4	298.9	298.9	297.7	298.3	298.9	298.3	297.7	298.9
177.5°	300.8	299.9	299.4	299.4	299.4	298.5	299.0	299.9	299.0	298.5	299.4
180°	299.4	299.4	299.4	299.4	299.4	299.4	299.4	299.4	299.4	299.4	299.4



TEST NUMBER: P331623-840

CATALOG NUMBER: SA2XXRDIP-C290D530U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1
2.5°	650.9	649.5	647.1	643.5	641.3	637.4	634.9	636.3	636.7	636.3	636.0
5°	633.4	628.5	621.9	615.4	609.5	603.1	599.4	597.8	594.6	592.8	591.8
7.5°	612.2	603.9	594.5	583.3	573.8	563.8	558.8	556.2	549.7	546.1	543.0
10°	596.4	583.3	573.9	559.3	550.3	537.2	528.3	528.6	519.6	514.5	510.9
12.5°	579.0	564.6	549.0	535.7	523.3	512.8	502.0	497.7	488.2	483.3	473.4
15°	550.1	533.3	516.8	499.0	486.4	470.0	454.4	435.4	420.0	406.7	403.0
17.5°	518.6	497.8	481.2	460.2	438.6	411.2	393.1	382.0	372.8	365.8	360.5
20°	496.9	475.7	458.1	426.5	397.3	378.7	365.5	356.9	347.3	339.7	335.6
22.5°	474.1	452.1	428.0	392.6	369.9	355.1	343.3	333.5	326.9	321.0	317.2
25°	441.8	417.7	378.0	353.8	335.4	319.7	311.5	305.6	298.7	290.6	287.0
27.5°	407.7	369.4	340.8	322.8	305.3	295.2	287.7	278.8	272.7	269.0	265.2
30°	382.1	343.9	321.6	301.8	289.5	278.2	269.5	264.5	258.5	252.4	249.8
32.5°	353.8	323.2	301.7	285.4	272.8	263.2	256.3	248.1	243.9	240.0	234.8
35°	318.4	295.2	275.7	262.5	250.4	242.7	234.7	229.8	222.1	218.8	216.8
37.5°	288.5	268.4	253.9	239.8	230.4	221.8	216.8	209.1	205.8	201.3	196.9
40°	271.6	251.9	237.9	226.4	215.8	209.4	203.3	197.0	192.0	190.0	184.7
42.5°	254.4	238.3	224.3	211.8	204.7	197.8	190.1	185.5	180.3	176.9	173.7
45°	230.6	216.3	204.4	194.1	186.2	179.2	174.1	166.5	163.6	156.9	154.1
47.5°	209.6	196.4	185.0	175.2	167.6	163.0	155.6	149.7	144.9	140.8	137.2
50°	194.8	183.7	172.7	164.0	157.1	150.5	142.9	140.0	132.6	130.5	128.5
52.5°	181.2	170.7	160.7	152.1	145.2	138.8	132.1	128.2	123.2	121.2	119.7
55°	162.2	152.1	142.5	134.9	128.1	121.4	117.2	112.4	110.1	108.5	106.6
57.5°	143.1	134.0	126.6	119.0	112.0	106.7	102.0	99.1	96.7	94.6	92.4
60°	131.0	122.3	115.6	108.5	101.4	97.0	93.4	89.9	87.2	83.9	83.0
62.5°	118.2	110.5	104.4	97.5	91.3	87.4	83.8	80.6	77.3	72.6	71.3
65°	100.5	94.5	88.1	82.3	76.9	72.9	67.9	64.2	62.8	62.4	62.2
67.5°	84.5	78.9	73.3	67.5	62.5	58.9	56.2	55.7	54.7	54.5	53.8
70°	73.8	68.6	63.1	57.6	52.7	52.1	51.2	50.2	49.1	48.7	48.2
72.5°	64.3	58.9	53.3	49.0	46.9	46.0	45.1	44.1	43.4	42.9	42.7
75°	49.3	44.2	40.6	39.0	37.9	37.2	35.7	35.1	34.6	33.9	33.7
77.5°	35.5	32.6	31.0	30.0	28.8	28.1	27.3	26.6	26.1	26.0	25.5
80°	27.1	25.7	24.5	23.1	22.7	21.8	21.6	20.9	21.1	20.4	20.4
82.5°	21.0	19.3	18.3	17.7	17.2	16.5	16.3	16.0	16.0	15.5	15.5
85°	10.8	10.3	9.9	9.4	9.4	8.7	9.0	8.7	8.7	8.3	8.1
87.5°	4.8	5.0	5.3	6.1	6.8	6.7	6.6	6.3	6.1	6.3	6.2
90°	6.9	8.7	11.5	15.6	19.0	19.6	19.0	18.4	17.3	18.4	19.0
92.5°	20.7	26.2	39.2	57.5	73.8	74.8	63.2	50.2	43.1	38.3	34.6
95°	42.6	56.5	82.9	133.0	199.9	225.8	197.5	150.9	115.7	91.6	78.9
97.5°	60.5	76.1	109.5	179.3	290.2	385.4	404.2	352.1	288.1	225.8	184.2
100°	72.0	88.2	118.7	188.9	313.3	454.9	537.9	525.8	454.4	375.5	305.8
102.5°	82.6	98.7	126.9	189.3	304.6	457.3	587.6	639.6	623.5	565.8	491.9
105°	97.9	114.0	141.1	192.4	287.4	426.8	580.0	699.7	764.8	772.3	753.3
107.5°	113.1	129.4	155.6	200.3	278.8	394.0	529.4	656.4	754.5	814.4	842.2
110°	123.2	140.0	165.3	206.7	277.0	378.4	497.6	619.1	722.2	795.9	843.1



TEST NUMBER: P331623-840

CATALOG NUMBER: SA2XXRDIP-C290D530U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	132.9	150.1	174.5	213.7	277.5	368.2	475.4	585.0	684.0	762.8	816.9
115°	148.6	164.1	188.9	224.0	279.9	357.1	448.1	543.1	631.8	707.2	766.6
117.5°	163.1	179.3	202.2	235.1	284.1	351.6	430.8	511.5	589.4	657.8	713.5
120°	172.8	188.9	211.4	242.5	286.8	348.4	421.6	495.8	567.2	628.3	680.8
122.5°	182.5	199.0	220.2	248.9	290.0	346.6	413.7	483.4	548.9	606.6	654.0
125°	196.4	212.5	233.3	259.1	294.9	343.3	402.5	465.3	524.6	575.3	618.5
127.5°	208.7	225.3	245.5	268.7	299.8	341.3	392.2	447.5	501.2	549.0	588.9
130°	216.5	232.7	252.9	274.7	303.5	340.3	385.3	436.0	485.5	531.0	569.0
132.5°	223.9	240.0	259.2	280.7	307.2	339.9	379.7	425.0	470.8	512.6	548.3
135°	233.8	249.9	268.4	288.5	311.5	339.2	372.0	409.5	447.5	485.5	517.8
137.5°	242.6	257.5	275.8	294.5	315.5	339.1	366.6	397.2	429.0	459.1	487.3
140°	247.6	262.7	279.9	297.7	317.3	338.6	363.5	389.3	417.0	443.4	468.8
142.5°	252.3	266.3	283.2	300.5	318.7	338.6	360.2	382.8	406.4	429.2	450.4
145°	259.7	272.4	287.9	304.1	320.2	337.5	355.9	373.8	392.7	410.6	427.4
147.5°	266.0	277.2	291.9	306.1	320.6	335.4	351.5	366.8	381.7	395.7	407.9
150°	270.1	280.4	293.7	307.0	320.2	334.1	347.9	361.6	374.4	386.5	396.8
152.5°	274.3	283.7	295.6	307.4	319.3	331.7	344.7	356.6	368.4	378.6	387.6
155°	279.9	288.5	298.3	308.1	317.9	327.7	338.6	349.6	358.8	367.4	373.8
157.5°	284.8	292.0	300.2	308.1	315.3	323.6	333.0	341.4	349.1	356.4	361.3
160°	287.9	294.3	301.2	308.1	313.9	320.8	328.8	336.3	342.6	349.0	353.0
162.5°	290.7	295.7	301.6	307.6	312.5	318.5	325.2	331.2	336.7	342.1	345.2
165°	293.7	297.2	302.4	306.4	309.8	313.9	319.0	323.7	327.7	331.7	334.1
167.5°	296.3	298.4	302.3	305.6	307.2	309.8	313.1	316.4	319.5	322.2	324.4
170°	297.2	298.9	301.7	304.7	305.8	307.5	309.8	312.8	314.5	316.8	317.9
172.5°	298.1	299.3	301.3	303.3	304.0	304.8	306.6	308.6	309.8	311.6	312.4
175°	298.9	299.4	300.6	301.7	301.2	301.7	302.4	304.1	304.7	305.3	305.8
177.5°	299.4	299.4	299.9	300.8	299.9	299.4	299.9	300.8	300.8	301.3	301.3
180°	299.4	299.4	299.4	299.4	299.4	299.4	299.4	299.4	299.4	299.4	299.4



TEST NUMBER: P331623-840

CATALOG NUMBER: SA2XXRDIP-C290D530U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1
2.5°	634.0	634.3	633.8	634.1	633.8	634.3	634.0	636.0	636.3	636.7	636.3
5°	590.7	587.9	587.4	586.8	587.4	587.9	590.7	591.8	592.8	594.6	597.8
7.5°	539.1	538.7	537.5	535.8	537.5	538.7	539.1	543.0	546.1	549.7	556.2
10°	505.8	504.6	504.4	502.8	504.4	504.6	505.8	510.9	514.5	519.6	528.6
12.5°	466.9	459.5	458.8	454.7	458.8	459.5	466.9	473.4	483.3	488.2	497.7
15°	397.6	396.2	391.5	388.6	391.5	396.2	397.6	403.0	406.7	420.0	435.4
17.5°	357.9	353.4	351.9	351.3	351.9	353.4	357.9	360.5	365.8	372.8	382.0
20°	332.3	328.3	327.6	327.1	327.6	328.3	332.3	335.6	339.7	347.3	356.9
22.5°	314.8	310.4	308.7	307.3	308.7	310.4	314.8	317.2	321.0	326.9	333.5
25°	284.7	283.1	282.2	281.7	282.2	283.1	284.7	287.0	290.6	298.7	305.6
27.5°	261.2	257.6	256.9	255.7	256.9	257.6	261.2	265.2	269.0	272.7	278.8
30°	247.7	246.6	245.0	243.6	245.0	246.6	247.7	249.8	252.4	258.5	264.5
32.5°	232.0	231.0	229.5	228.9	229.5	231.0	232.0	234.8	240.0	243.9	248.1
35°	214.5	211.3	209.8	207.8	209.8	211.3	214.5	216.8	218.8	222.1	229.8
37.5°	196.0	194.3	192.4	193.1	192.4	194.3	196.0	196.9	201.3	205.8	209.1
40°	181.7	180.6	180.1	179.9	180.1	180.6	181.7	184.7	190.0	192.0	197.0
42.5°	170.3	167.1	165.9	165.9	165.9	167.1	170.3	173.7	176.9	180.3	185.5
45°	153.0	150.1	147.9	148.1	147.9	150.1	153.0	154.1	156.9	163.6	166.5
47.5°	135.3	135.2	133.9	134.3	133.9	135.2	135.3	137.2	140.8	144.9	149.7
50°	126.8	125.5	124.5	124.8	124.5	125.5	126.8	128.5	130.5	132.6	140.0
52.5°	118.8	117.5	116.8	117.9	116.8	117.5	118.8	119.7	121.2	123.2	128.2
55°	105.5	104.1	103.9	103.7	103.9	104.1	105.5	106.6	108.5	110.1	112.4
57.5°	90.7	89.8	88.4	87.9	88.4	89.8	90.7	92.4	94.6	96.7	99.1
60°	80.1	78.3	75.9	75.7	75.9	78.3	80.1	83.0	83.9	87.2	89.9
62.5°	70.3	70.0	69.5	69.5	69.5	70.0	70.3	71.3	72.6	77.3	80.6
65°	61.7	61.5	61.7	61.9	61.7	61.5	61.7	62.2	62.4	62.8	64.2
67.5°	53.7	53.3	52.9	53.1	52.9	53.3	53.7	53.8	54.5	54.7	55.7
70°	47.7	47.5	47.3	47.3	47.3	47.5	47.7	48.2	48.7	49.1	50.2
72.5°	41.8	41.8	41.6	41.4	41.6	41.8	41.8	42.7	42.9	43.4	44.1
75°	33.5	33.0	33.0	33.0	33.0	33.0	33.5	33.7	33.9	34.6	35.1
77.5°	25.5	25.2	25.0	24.8	25.0	25.2	25.5	25.5	26.0	26.1	26.6
80°	20.2	20.0	19.7	19.7	19.7	20.0	20.2	20.4	20.4	21.1	20.9
82.5°	15.5	15.1	15.1	14.9	15.1	15.1	15.5	15.5	15.5	16.0	16.0
85°	8.3	8.5	8.3	8.7	8.3	8.5	8.3	8.1	8.3	8.7	8.7
87.5°	6.2	6.0	6.2	6.0	6.2	6.0	6.2	6.2	6.3	6.1	6.3
90°	19.0	19.0	19.0	19.0	19.0	19.0	19.0	19.0	18.4	17.3	18.4
92.5°	34.2	32.4	32.8	31.9	32.8	32.4	34.2	34.6	38.3	43.1	50.2
95°	71.4	66.9	65.0	65.6	65.0	66.9	71.4	78.9	91.6	115.7	150.9
97.5°	156.6	142.5	134.1	129.3	134.1	142.5	156.6	184.2	225.8	288.1	352.1
100°	258.0	233.3	216.5	206.2	216.5	233.3	258.0	305.8	375.5	454.4	525.8
102.5°	440.0	397.7	376.9	362.8	376.9	397.7	440.0	491.9	565.8	623.5	639.6
105°	717.6	681.9	657.1	649.0	657.1	681.9	717.6	753.3	772.3	764.8	699.7
107.5°	846.7	844.8	839.8	829.1	839.8	844.8	846.7	842.2	814.4	754.5	656.4
110°	867.9	878.9	884.0	883.4	884.0	878.9	867.9	843.1	795.9	722.2	619.1



TEST NUMBER: P331623-840

CATALOG NUMBER: SA2XXRDIP-C290D530U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	851.3	869.6	879.4	882.5	879.4	869.6	851.3	816.9	762.8	684.0	585.0
115°	807.4	833.9	848.9	854.0	848.9	833.9	807.4	766.6	707.2	631.8	543.1
117.5°	755.2	783.2	798.9	803.2	798.9	783.2	755.2	713.5	657.8	589.4	511.5
120°	721.0	748.1	764.8	770.5	764.8	748.1	721.0	680.8	628.3	567.2	495.8
122.5°	690.1	716.8	731.6	736.5	731.6	716.8	690.1	654.0	606.6	548.9	483.4
125°	652.0	673.8	688.2	692.9	688.2	673.8	652.0	618.5	575.3	524.6	465.3
127.5°	617.9	638.4	650.9	654.6	650.9	638.4	617.9	588.9	549.0	501.2	447.5
130°	597.2	616.8	628.3	632.9	628.3	616.8	597.2	569.0	531.0	485.5	436.0
132.5°	576.0	595.6	606.2	610.4	606.2	595.6	576.0	548.3	512.6	470.8	425.0
135°	542.5	561.5	571.9	574.2	571.9	561.5	542.5	517.8	485.5	447.5	409.5
137.5°	509.8	526.1	535.2	538.7	535.2	526.1	509.8	487.3	459.1	429.0	397.2
140°	487.3	502.2	510.8	514.3	510.8	502.2	487.3	468.8	443.4	417.0	389.3
142.5°	467.9	481.5	489.2	489.9	489.2	481.5	467.9	450.4	429.2	406.4	382.8
145°	441.1	450.9	456.7	458.4	456.7	450.9	441.1	427.4	410.6	392.7	373.8
147.5°	419.3	427.1	431.0	432.0	431.0	427.1	419.3	407.9	395.7	381.7	366.8
150°	405.5	412.3	415.8	416.4	415.8	412.3	405.5	396.8	386.5	374.4	361.6
152.5°	394.4	400.4	402.9	403.0	402.9	400.4	394.4	387.6	378.6	368.4	356.6
155°	380.1	384.2	386.5	385.3	386.5	384.2	380.1	373.8	367.4	358.8	349.6
157.5°	365.8	369.2	370.2	370.2	370.2	369.2	365.8	361.3	356.4	349.1	341.4
160°	357.1	359.9	360.5	360.5	360.5	359.9	357.1	353.0	349.0	342.6	336.3
162.5°	349.2	351.2	351.7	351.3	351.7	351.2	349.2	345.2	342.1	336.7	331.2
165°	336.3	338.6	338.6	338.1	338.6	338.6	336.3	334.1	331.7	327.7	323.7
167.5°	325.4	326.7	326.6	325.9	326.6	326.7	325.4	324.4	322.2	319.5	316.4
170°	318.5	320.2	319.6	318.5	319.6	320.2	318.5	317.9	316.8	314.5	312.8
172.5°	313.0	313.8	313.2	312.5	313.2	313.8	313.0	312.4	311.6	309.8	308.6
175°	305.8	306.4	305.8	304.7	305.8	306.4	305.8	305.8	305.3	304.7	304.1
177.5°	301.3	301.3	300.8	299.9	300.8	301.3	301.3	301.3	301.3	300.8	300.8
180°	299.4	299.4	299.4	299.4	299.4	299.4	299.4	299.4	299.4	299.4	299.4



TEST NUMBER: P331623-840

CATALOG NUMBER: SA2XXRDIP-C290D530U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1
2.5°	634.9	637.4	641.3	643.5	647.1	649.5	650.9	653.2	654.5	659.1	663.9
5°	599.4	603.1	609.5	615.4	621.9	628.5	633.4	638.8	643.9	652.6	661.8
7.5°	558.8	563.8	573.8	583.3	594.5	603.9	612.2	621.6	630.0	642.5	655.5
10°	528.3	537.2	550.3	559.3	573.9	583.3	596.4	606.7	618.4	635.0	649.6
12.5°	502.0	512.8	523.3	535.7	549.0	564.6	579.0	592.3	606.1	623.2	640.5
15°	454.4	470.0	486.4	499.0	516.8	533.3	550.1	567.9	584.9	605.4	627.8
17.5°	393.1	411.2	438.6	460.2	481.2	497.8	518.6	540.2	560.2	584.8	609.9
20°	365.5	378.7	397.3	426.5	458.1	475.7	496.9	520.7	543.6	570.5	597.3
22.5°	343.3	355.1	369.9	392.6	428.0	452.1	474.1	498.4	524.9	552.3	582.1
25°	311.5	319.7	335.4	353.8	378.0	417.7	441.8	466.2	495.0	524.4	558.4
27.5°	287.7	295.2	305.3	322.8	340.8	369.4	407.7	434.2	463.0	496.0	531.3
30°	269.5	278.2	289.5	301.8	321.6	343.9	382.1	412.9	441.3	475.3	512.9
32.5°	256.3	263.2	272.8	285.4	301.7	323.2	353.8	391.0	418.8	454.5	493.8
35°	234.7	242.7	250.4	262.5	275.7	295.2	318.4	358.3	385.9	421.1	460.6
37.5°	216.8	221.8	230.4	239.8	253.9	268.4	288.5	324.3	354.1	388.7	429.1
40°	203.3	209.4	215.8	226.4	237.9	251.9	271.6	298.2	332.3	366.4	405.8
42.5°	190.1	197.8	204.7	211.8	224.3	238.3	254.4	276.9	311.8	344.0	382.3
45°	174.1	179.2	186.2	194.1	204.4	216.3	230.6	250.2	283.8	311.5	347.5
47.5°	155.6	163.0	167.6	175.2	185.0	196.4	209.6	226.7	253.8	279.8	313.3
50°	142.9	150.5	157.1	164.0	172.7	183.7	194.8	211.3	233.1	260.3	291.5
52.5°	132.1	138.8	145.2	152.1	160.7	170.7	181.2	195.7	214.3	239.4	269.7
55°	117.2	121.4	128.1	134.9	142.5	152.1	162.2	174.3	190.4	211.5	236.0
57.5°	102.0	106.7	112.0	119.0	126.6	134.0	143.1	154.1	166.7	185.8	206.8
60°	93.4	97.0	101.4	108.5	115.6	122.3	131.0	140.2	152.1	168.6	186.5
62.5°	83.8	87.4	91.3	97.5	104.4	110.5	118.2	127.8	137.9	153.0	168.6
65°	67.9	72.9	76.9	82.3	88.1	94.5	100.5	108.3	117.2	129.2	143.1
67.5°	56.2	58.9	62.5	67.5	73.3	78.9	84.5	90.6	98.4	107.6	118.7
70°	51.2	52.1	52.7	57.6	63.1	68.6	73.8	79.6	86.2	93.8	103.4
72.5°	45.1	46.0	46.9	49.0	53.3	58.9	64.3	68.6	74.8	81.2	89.0
75°	35.7	37.2	37.9	39.0	40.6	44.2	49.3	53.4	57.2	61.9	68.2
77.5°	27.3	28.1	28.8	30.0	31.0	32.6	35.5	39.2	42.7	45.4	49.7
80°	21.6	21.8	22.7	23.1	24.5	25.7	27.1	30.1	33.5	34.6	37.7
82.5°	16.3	16.5	17.2	17.7	18.3	19.3	21.0	21.8	24.5	26.1	27.9
85°	9.0	8.7	9.4	9.4	9.9	10.3	10.8	11.9	12.6	14.4	14.9
87.5°	6.6	6.7	6.8	6.1	5.3	5.0	4.8	4.8	4.9	5.0	5.5
90°	19.0	19.6	19.0	15.6	11.5	8.7	6.9	5.8	4.6	2.3	0.6
92.5°	63.2	74.8	73.8	57.5	39.2	26.2	20.7	16.9	14.2	10.1	7.1
95°	197.5	225.8	199.9	133.0	82.9	56.5	42.6	33.4	28.2	22.4	20.2
97.5°	404.2	385.4	290.2	179.3	109.5	76.1	60.5	49.9	42.0	36.0	32.8
100°	537.9	454.9	313.3	188.9	118.7	88.2	72.0	60.5	51.3	46.0	44.3
102.5°	587.6	457.3	304.6	189.3	126.9	98.7	82.6	70.6	61.4	56.2	54.9
105°	580.0	426.8	287.4	192.4	141.1	114.0	97.9	85.2	76.5	72.6	70.3
107.5°	529.4	394.0	278.8	200.3	155.6	129.4	113.1	100.6	92.6	88.7	86.8
110°	497.6	378.4	277.0	206.7	165.3	140.0	123.2	111.2	103.7	100.2	97.9



TEST NUMBER: P331623-840

CATALOG NUMBER: SA2XXRDIP-C290D530U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	475.4	368.2	277.5	213.7	174.5	150.1	132.9	121.3	114.2	110.4	108.1
115°	448.1	357.1	279.9	224.0	188.9	164.1	148.6	137.0	130.2	126.7	123.8
117.5°	430.8	351.6	284.1	235.1	202.2	179.3	163.1	152.1	145.9	142.5	140.2
120°	421.6	348.4	286.8	242.5	211.4	188.9	172.8	161.3	156.0	152.6	150.3
122.5°	413.7	346.6	290.0	248.9	220.2	199.0	182.5	171.0	165.3	161.9	160.0
125°	402.5	343.3	294.9	259.1	233.3	212.5	196.4	184.9	177.9	174.5	172.8
127.5°	392.2	341.3	299.8	268.7	245.5	225.3	208.7	197.6	190.1	185.2	182.9
130°	385.3	340.3	303.5	274.7	252.9	232.7	216.5	205.0	196.9	191.2	188.9
132.5°	379.7	339.9	307.2	280.7	259.2	240.0	223.9	212.0	203.4	197.2	194.4
135°	372.0	339.2	311.5	288.5	268.4	249.9	233.8	220.6	212.0	205.0	202.7
137.5°	366.6	339.1	315.5	294.5	275.8	257.5	242.6	229.4	220.3	213.3	210.6
140°	363.5	338.6	317.3	297.7	279.9	262.7	247.6	235.0	225.8	218.8	216.5
142.5°	360.2	338.6	318.7	300.5	283.2	266.3	252.3	240.0	230.9	224.4	222.6
145°	355.9	337.5	320.2	304.1	287.9	272.4	259.7	248.2	239.5	233.8	231.6
147.5°	351.5	335.4	320.6	306.1	291.9	277.2	266.0	256.4	248.4	242.9	241.2
150°	347.9	334.1	320.2	307.0	293.7	280.4	270.1	261.5	254.0	249.3	247.6
152.5°	344.7	331.7	319.3	307.4	295.6	283.7	274.3	266.1	259.5	254.9	254.1
155°	338.6	327.7	317.9	308.1	298.3	288.5	279.9	273.6	267.2	263.8	263.2
157.5°	333.0	323.6	315.3	308.1	300.2	292.0	284.8	279.6	274.2	271.4	270.7
160°	328.8	320.8	313.9	308.1	301.2	294.3	287.9	283.4	278.7	276.4	275.9
162.5°	325.2	318.5	312.5	307.6	301.6	295.7	290.7	286.6	282.9	280.5	280.9
165°	319.0	313.9	309.8	306.4	302.4	297.2	293.7	290.8	287.4	286.2	286.8
167.5°	313.1	309.8	307.2	305.6	302.3	298.4	296.3	294.2	292.0	290.9	291.6
170°	309.8	307.5	305.8	304.7	301.7	298.9	297.2	296.0	294.3	293.7	294.9
172.5°	306.6	304.8	304.0	303.3	301.3	299.3	298.1	297.4	295.7	296.0	296.7
175°	302.4	301.7	301.2	301.7	300.6	299.4	298.9	298.9	297.7	298.3	298.9
177.5°	299.9	299.4	299.9	300.8	299.9	299.4	299.4	299.4	298.5	299.0	299.9
180°	299.4	299.4	299.4	299.4	299.4	299.4	299.4	299.4	299.4	299.4	299.4



TEST NUMBER: P331623-840

CATALOG NUMBER: SA2XXRDIP-C290D530U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1
2.5°	664.1	664.6	668.2	669.9	673.2	674.5	676.0	675.6	675.6	676.3	681.5
5°	665.5	670.0	676.9	683.6	690.0	695.5	699.2	702.9	704.3	710.8	716.8
7.5°	663.1	671.6	682.9	693.1	705.2	714.7	722.6	729.7	734.6	744.3	754.2
10°	659.9	671.9	684.7	697.8	714.6	727.2	740.0	749.9	753.1	767.5	775.8
12.5°	653.7	669.6	686.0	703.0	719.3	736.7	750.8	760.7	772.0	785.0	800.2
15°	644.4	662.7	684.1	705.8	729.2	750.3	765.5	782.6	795.1	809.3	822.6
17.5°	631.0	654.6	681.7	706.9	734.0	756.6	777.5	794.0	802.6	810.8	812.7
20°	620.3	645.7	677.6	707.4	734.5	760.6	781.3	795.1	797.4	797.6	785.5
22.5°	608.7	637.5	670.9	701.4	733.8	762.9	778.9	784.8	775.7	760.1	736.6
25°	587.4	620.8	659.5	694.4	729.7	757.2	762.8	752.5	720.5	687.0	644.6
27.5°	564.4	601.9	643.4	682.2	719.8	736.9	725.0	687.7	630.4	580.4	519.9
30°	547.5	589.6	630.4	673.7	708.6	715.9	688.6	633.8	566.8	491.6	431.2
32.5°	528.3	572.3	617.1	662.0	691.2	684.0	638.9	571.4	492.9	418.9	361.9
35°	500.8	546.1	594.6	639.5	658.1	627.1	559.7	471.8	391.5	322.6	283.3
37.5°	469.0	518.5	568.8	610.1	608.7	557.1	465.2	374.6	307.1	266.2	238.3
40°	446.4	496.4	550.8	585.6	570.8	503.5	403.9	318.4	269.0	236.5	216.1
42.5°	424.7	474.9	529.0	556.6	530.7	448.1	348.9	281.9	241.2	215.8	199.2
45°	387.9	440.9	490.9	506.2	459.9	368.9	282.2	233.5	206.4	187.6	176.2
47.5°	351.8	404.0	449.7	449.9	387.3	299.1	238.0	202.1	178.9	164.4	156.1
50°	329.8	379.4	417.7	411.7	340.6	266.1	212.9	181.9	162.7	151.4	142.7
52.5°	305.1	353.1	386.4	369.4	301.1	234.2	190.3	164.3	148.3	138.6	130.8
55°	269.0	311.7	335.2	309.4	245.7	194.8	160.8	140.4	128.5	120.2	113.5
57.5°	233.7	268.9	283.6	253.7	202.4	161.5	136.0	120.7	108.9	102.9	99.5
60°	211.5	241.6	251.9	218.8	175.9	141.3	120.5	106.2	97.5	93.6	90.2
62.5°	189.7	214.2	218.4	188.2	153.4	123.7	105.7	93.7	88.0	84.2	81.0
65°	157.3	175.0	173.0	148.7	121.4	98.2	85.1	77.8	73.4	68.2	62.4
67.5°	129.6	140.4	133.8	115.6	92.6	76.3	67.8	62.2	56.8	51.8	50.5
70°	111.9	118.2	111.3	94.5	75.9	64.0	57.2	50.5	47.3	46.2	44.0
72.5°	95.0	97.3	89.8	75.4	61.8	53.0	46.3	42.6	40.8	39.9	38.6
75°	71.3	69.8	63.3	52.1	42.9	37.0	34.8	33.5	32.3	31.4	30.7
77.5°	50.1	47.8	42.0	34.6	29.9	27.1	25.8	25.0	24.5	24.0	23.3
80°	37.7	36.1	30.3	24.7	22.7	21.3	20.6	19.7	19.7	19.3	18.6
82.5°	27.6	25.8	20.7	18.2	17.1	16.2	15.7	15.1	14.9	15.0	14.5
85°	14.4	11.7	10.3	9.9	9.2	8.7	9.0	8.5	8.5	8.5	8.3
87.5°	4.8	4.4	4.4	4.5	5.0	5.7	6.3	7.0	7.2	7.0	7.0
90°	2.3	4.6	5.8	6.9	8.7	11.5	15.6	19.0	19.6	19.0	18.4
92.5°	10.1	14.2	16.9	20.7	26.2	39.2	57.5	73.8	74.8	63.2	50.2
95°	22.4	28.2	33.4	42.6	56.5	82.9	133.0	199.9	225.8	197.5	150.9
97.5°	36.0	42.0	49.9	60.5	76.1	109.5	179.3	290.2	385.4	404.2	352.1
100°	46.0	51.3	60.5	72.0	88.2	118.7	188.9	313.3	454.9	537.9	525.8
102.5°	56.2	61.4	70.6	82.6	98.7	126.9	189.3	304.6	457.3	587.6	639.6
105°	72.6	76.5	85.2	97.9	114.0	141.1	192.4	287.4	426.8	580.0	699.7
107.5°	88.7	92.6	100.6	113.1	129.4	155.6	200.3	278.8	394.0	529.4	656.4
110°	100.2	103.7	111.2	123.2	140.0	165.3	206.7	277.0	378.4	497.6	619.1



TEST NUMBER: P331623-840

CATALOG NUMBER: SA2XXRDIP-C290D530U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	110.4	114.2	121.3	132.9	150.1	174.5	213.7	277.5	368.2	475.4	585.0
115°	126.7	130.2	137.0	148.6	164.1	188.9	224.0	279.9	357.1	448.1	543.1
117.5°	142.5	145.9	152.1	163.1	179.3	202.2	235.1	284.1	351.6	430.8	511.5
120°	152.6	156.0	161.3	172.8	188.9	211.4	242.5	286.8	348.4	421.6	495.8
122.5°	161.9	165.3	171.0	182.5	199.0	220.2	248.9	290.0	346.6	413.7	483.4
125°	174.5	177.9	184.9	196.4	212.5	233.3	259.1	294.9	343.3	402.5	465.3
127.5°	185.2	190.1	197.6	208.7	225.3	245.5	268.7	299.8	341.3	392.2	447.5
130°	191.2	196.9	205.0	216.5	232.7	252.9	274.7	303.5	340.3	385.3	436.0
132.5°	197.2	203.4	212.0	223.9	240.0	259.2	280.7	307.2	339.9	379.7	425.0
135°	205.0	212.0	220.6	233.8	249.9	268.4	288.5	311.5	339.2	372.0	409.5
137.5°	213.3	220.3	229.4	242.6	257.5	275.8	294.5	315.5	339.1	366.6	397.2
140°	218.8	225.8	235.0	247.6	262.7	279.9	297.7	317.3	338.6	363.5	389.3
142.5°	224.4	230.9	240.0	252.3	266.3	283.2	300.5	318.7	338.6	360.2	382.8
145°	233.8	239.5	248.2	259.7	272.4	287.9	304.1	320.2	337.5	355.9	373.8
147.5°	242.9	248.4	256.4	266.0	277.2	291.9	306.1	320.6	335.4	351.5	366.8
150°	249.3	254.0	261.5	270.1	280.4	293.7	307.0	320.2	334.1	347.9	361.6
152.5°	254.9	259.5	266.1	274.3	283.7	295.6	307.4	319.3	331.7	344.7	356.6
155°	263.8	267.2	273.6	279.9	288.5	298.3	308.1	317.9	327.7	338.6	349.6
157.5°	271.4	274.2	279.6	284.8	292.0	300.2	308.1	315.3	323.6	333.0	341.4
160°	276.4	278.7	283.4	287.9	294.3	301.2	308.1	313.9	320.8	328.8	336.3
162.5°	280.5	282.9	286.6	290.7	295.7	301.6	307.6	312.5	318.5	325.2	331.2
165°	286.2	287.4	290.8	293.7	297.2	302.4	306.4	309.8	313.9	319.0	323.7
167.5°	290.9	292.0	294.2	296.3	298.4	302.3	305.6	307.2	309.8	313.1	316.4
170°	293.7	294.3	296.0	297.2	298.9	301.7	304.7	305.8	307.5	309.8	312.8
172.5°	296.0	295.7	297.4	298.1	299.3	301.3	303.3	304.0	304.8	306.6	308.6
175°	298.3	297.7	298.9	298.9	299.4	300.6	301.7	301.2	301.7	302.4	304.1
177.5°	299.0	298.5	299.4	299.4	299.4	299.9	300.8	299.9	299.4	299.9	300.8
180°	299.4	299.4	299.4	299.4	299.4	299.4	299.4	299.4	299.4	299.4	299.4



TEST NUMBER: P331623-840
 CATALOG NUMBER: SA2XXRDIP-C290D530U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	660.1	660.1	660.1	660.1	660.1	660.1	660.1
2.5°	683.3	685.7	686.8	686.8	688.1	687.5	687.0
5°	722.6	726.9	727.9	732.0	735.0	734.1	734.5
7.5°	761.6	768.6	775.6	778.7	779.2	781.0	781.7
10°	785.7	791.4	802.1	800.6	808.6	813.2	805.7
12.5°	808.8	816.6	824.0	826.1	830.6	832.1	829.1
15°	829.7	833.8	834.2	833.1	834.6	833.3	829.0
17.5°	810.2	803.4	789.9	783.5	778.4	770.8	767.8
20°	777.9	758.1	735.2	726.0	715.3	694.2	699.2
22.5°	708.1	685.7	662.7	635.9	623.1	603.1	601.9
25°	599.7	560.9	518.2	488.4	470.9	451.0	442.2
27.5°	466.3	417.4	382.4	364.8	348.6	332.9	332.1
30°	378.5	341.8	314.8	299.6	289.7	283.1	284.5
32.5°	319.0	293.9	275.6	263.1	255.8	250.7	250.6
35°	260.8	243.6	231.9	226.6	221.4	217.7	217.9
37.5°	223.2	212.9	206.3	200.6	197.2	195.4	194.4
40°	203.9	195.4	190.4	186.9	184.2	181.7	181.2
42.5°	188.7	181.7	176.6	173.9	171.4	169.6	169.2
45°	167.4	161.7	157.1	154.1	153.0	151.4	151.4
47.5°	149.0	143.3	139.8	137.8	135.9	134.8	134.8
50°	136.5	132.1	129.0	127.7	126.1	125.5	125.2
52.5°	125.3	122.0	119.8	119.0	118.3	117.4	117.5
55°	110.1	108.3	107.3	106.6	105.5	104.1	105.0
57.5°	97.4	95.7	93.3	91.1	90.1	89.1	89.5
60°	88.4	85.1	81.9	79.4	78.7	76.6	76.6
62.5°	77.0	72.4	68.5	67.1	66.3	65.4	65.2
65°	59.2	57.4	56.5	55.5	55.0	55.0	54.6
67.5°	49.1	48.3	47.3	47.1	46.7	46.5	46.4
70°	43.3	42.4	42.0	41.7	41.3	41.5	40.8
72.5°	37.9	37.2	37.1	36.5	36.2	36.2	35.6
75°	29.8	29.8	29.6	29.4	28.9	28.7	28.9
77.5°	22.9	23.0	22.6	22.5	22.5	22.5	22.3
80°	18.4	18.6	18.4	18.1	17.9	18.1	17.9
82.5°	14.5	14.1	14.1	14.0	14.0	13.9	13.8
85°	8.3	8.5	8.3	8.1	8.1	8.1	8.3
87.5°	6.6	6.8	7.0	7.0	7.0	7.0	6.8
90°	17.3	18.4	19.0	19.0	19.0	19.0	19.0
92.5°	43.1	38.3	34.6	34.2	32.4	32.8	31.9
95°	115.7	91.6	78.9	71.4	66.9	65.0	65.6
97.5°	288.1	225.8	184.2	156.6	142.5	134.1	129.3
100°	454.4	375.5	305.8	258.0	233.3	216.5	206.2
102.5°	623.5	565.8	491.9	440.0	397.7	376.9	362.8
105°	764.8	772.3	753.3	717.6	681.9	657.1	649.0
107.5°	754.5	814.4	842.2	846.7	844.8	839.8	829.1
110°	722.2	795.9	843.1	867.9	878.9	884.0	883.4



TEST NUMBER: P331623-840

CATALOG NUMBER: SA2XXRDIP-C290D530U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	684.0	762.8	816.9	851.3	869.6	879.4	882.5
115°	631.8	707.2	766.6	807.4	833.9	848.9	854.0
117.5°	589.4	657.8	713.5	755.2	783.2	798.9	803.2
120°	567.2	628.3	680.8	721.0	748.1	764.8	770.5
122.5°	548.9	606.6	654.0	690.1	716.8	731.6	736.5
125°	524.6	575.3	618.5	652.0	673.8	688.2	692.9
127.5°	501.2	549.0	588.9	617.9	638.4	650.9	654.6
130°	485.5	531.0	569.0	597.2	616.8	628.3	632.9
132.5°	470.8	512.6	548.3	576.0	595.6	606.2	610.4
135°	447.5	485.5	517.8	542.5	561.5	571.9	574.2
137.5°	429.0	459.1	487.3	509.8	526.1	535.2	538.7
140°	417.0	443.4	468.8	487.3	502.2	510.8	514.3
142.5°	406.4	429.2	450.4	467.9	481.5	489.2	489.9
145°	392.7	410.6	427.4	441.1	450.9	456.7	458.4
147.5°	381.7	395.7	407.9	419.3	427.1	431.0	432.0
150°	374.4	386.5	396.8	405.5	412.3	415.8	416.4
152.5°	368.4	378.6	387.6	394.4	400.4	402.9	403.0
155°	358.8	367.4	373.8	380.1	384.2	386.5	385.3
157.5°	349.1	356.4	361.3	365.8	369.2	370.2	370.2
160°	342.6	349.0	353.0	357.1	359.9	360.5	360.5
162.5°	336.7	342.1	345.2	349.2	351.2	351.7	351.3
165°	327.7	331.7	334.1	336.3	338.6	338.6	338.1
167.5°	319.5	322.2	324.4	325.4	326.7	326.6	325.9
170°	314.5	316.8	317.9	318.5	320.2	319.6	318.5
172.5°	309.8	311.6	312.4	313.0	313.8	313.2	312.5
175°	304.7	305.3	305.8	305.8	306.4	305.8	304.7
177.5°	300.8	301.3	301.3	301.3	301.3	300.8	299.9
180°	299.4	299.4	299.4	299.4	299.4	299.4	299.4

(END OF REPORT)