

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331259-940

Luminaire Tested: **SA2XXDIP-C290D725U940-4F0-1E-UDD-A1**

Issue Date: 10/7/2019


Test Information

Test Method: LM-79-08
Report Number: P331259-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C290D725U940-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 725 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3475.6 lumens
Efficiency: N/A
Efficacy: 111.4 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331259-940

CATALOG NUMBER: SA2XXDIP-C290D725U940-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331259-940

CATALOG NUMBER: SA2XXDIP-C290D725U940-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	34				
1	94	90	87	83	85	82	79	76	65	63	61	50	49	48	37	36	35	29				
2	86	79	73	68	78	72	67	63	58	54	51	45	42	40	33	31	30	25				
3	79	70	63	57	71	63	57	53	51	47	43	40	37	35	29	27	26	21				
4	72	62	54	49	65	56	50	45	46	41	37	36	32	30	26	24	23	19				
5	66	55	48	42	60	50	44	39	41	36	32	32	29	26	24	22	20	16				
6	61	50	42	36	55	45	38	34	37	32	28	29	26	23	22	19	18	15				
7	56	45	37	32	51	41	34	29	33	28	25	26	23	20	20	18	16	13				
8	52	41	33	28	47	37	31	26	30	26	22	24	21	18	18	16	14	12				
9	49	37	30	25	44	34	28	23	28	23	20	22	19	16	17	15	13	11				
10	45	34	27	22	41	31	25	21	26	21	18	21	17	15	16	13	12	10				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8510	8510	8510	8510
5°	9540	8566	7590	8566
10°	10932	8496	6568	8496
15°	12094	8339	5804	8339
20°	11911	8172	5290	8172
25°	10739	7949	4965	7949
30°	8874	7594	4728	7594
35°	6467	7222	4559	7222
40°	5166	6785	4466	6785
45°	4514	6277	4338	6277
50°	4245	5785	4253	5785
55°	3910	5286	4138	5286
60°	3584	4753	3965	4753
65°	3266	4279	3790	4279
70°	2965	3814	3541	3814
75°	2633	3300	3132	3300
80°	2259	2724	2520	2724
85°	2038	2038	1501	2038



TEST NUMBER: P331259-940

CATALOG NUMBER: SA2XXDIP-C290D725U940-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.2	1.4
10°-20°	145.9	4.2
20°-30°	211.8	6.1
30°-40°	223.5	6.4
40°-50°	197.9	5.7
50°-60°	157.9	4.5
60°-70°	107.3	3.1
70°-80°	55.0	1.6
80°-90°	16.6	0.5
90°-100°	52.3	1.5
100°-110°	162.5	4.7
110°-120°	277.9	8.0
120°-130°	365.4	10.5
130°-140°	410.1	11.8
140°-150°	402.1	11.6
150°-160°	337.3	9.7
160°-170°	223.7	6.4
170°-180°	78.2	2.2
0°-30°	407.9	11.7
0°-40°	631.4	18.2
0°-60°	987.2	28.4
0°-90°	1166.1	33.6
90°-120°	492.7	14.2
90°-150°	1670.3	48.1
90°-180°	2309.0	66.4
0°-180°	3475.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	527	527	527	527	527	
5°	589	528	468	528	589	59
15°	724	499	347	499	724	200
25°	603	446	279	446	603	272
35°	328	366	231	366	328	213
45°	198	275	190	275	198	155
55°	139	188	147	188	139	125
65°	86	112	99	112	86	85
75°	42	53	50	53	42	45
85°	11	11	8	11	11	13
90°	24	1	24	1	24	11
95°	43	36	43	36	43	48
105°	155	150	155	150	155	163
115°	279	279	279	279	279	275
125°	407	406	407	406	407	363
135°	531	525	531	525	531	409
145°	644	637	644	637	644	402
155°	734	728	734	728	734	338
165°	793	792	793	792	793	224
175°	822	825	822	825	822	78
180°	826	826	826	826	826	



TEST NUMBER: P331259-940

CATALOG NUMBER: SA2XXDIP-C290D725U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	551.3	551.5	551.9	549.3	548.9	548.9	546.7	544.7	542.4	539.4	539.8
5°	588.6	590.8	591.7	589.2	585.6	585.2	581.8	576.1	570.8	566.6	563.6
7.5°	633.1	634.0	632.0	628.8	626.2	621.3	614.8	608.6	599.8	591.7	585.8
10°	666.8	668.1	664.6	660.0	656.1	650.4	641.1	631.6	620.1	608.9	600.0
12.5°	692.4	695.4	691.0	690.5	683.9	676.0	664.9	660.1	643.9	628.4	618.8
15°	723.5	723.4	723.8	719.9	715.1	713.8	702.1	689.3	666.5	657.3	641.5
17.5°	714.5	717.6	719.1	719.0	718.9	718.1	714.3	706.3	694.8	680.0	661.8
20°	693.2	697.2	697.9	702.5	705.2	708.6	710.0	707.8	700.7	688.3	672.5
22.5°	660.1	661.3	663.2	670.4	676.1	684.7	689.2	696.8	694.0	688.0	674.8
25°	602.8	600.8	607.9	611.5	624.7	638.5	648.5	659.3	669.1	674.9	671.1
27.5°	534.0	531.0	541.6	551.3	562.0	576.9	592.4	610.6	625.8	644.9	651.4
30°	476.0	477.9	487.9	498.3	514.5	535.6	553.0	573.0	594.8	616.0	630.8
32.5°	413.5	420.4	426.9	442.7	457.0	480.5	506.0	531.1	558.1	582.3	605.2
35°	328.1	336.3	345.2	356.7	376.7	400.0	425.0	458.8	495.7	528.7	555.8
37.5°	276.3	274.9	280.0	288.4	304.6	323.4	352.1	385.5	428.9	467.7	506.0
40°	245.1	244.3	247.9	255.7	268.0	281.8	306.9	336.3	376.6	424.0	469.6
42.5°	223.7	224.2	226.2	231.7	240.1	251.5	270.3	295.2	332.2	376.8	425.8
45°	197.7	199.1	201.3	204.0	208.8	218.2	228.7	246.6	275.7	313.0	361.1
47.5°	179.0	179.1	181.3	183.6	186.5	191.7	200.4	211.5	232.1	262.4	303.9
50°	169.0	167.6	169.2	170.9	174.0	177.6	183.3	193.9	207.6	232.1	266.8
52.5°	156.6	156.7	158.1	158.8	161.5	165.1	170.3	177.6	190.1	209.3	237.7
55°	138.9	140.0	140.8	142.0	144.5	147.0	151.1	156.0	165.7	180.0	201.2
57.5°	122.3	122.7	123.5	125.8	127.3	129.7	133.6	138.0	144.4	155.0	170.9
60°	111.0	111.0	112.6	113.6	115.7	118.1	121.1	125.4	131.1	139.7	152.6
62.5°	100.7	100.5	101.1	102.8	104.3	106.6	109.6	113.2	118.6	126.4	136.8
65°	85.5	85.1	86.3	86.7	88.3	90.5	93.0	96.8	101.1	106.7	116.1
67.5°	70.9	71.4	72.1	72.8	73.7	76.1	77.7	80.3	84.0	88.7	95.0
70°	62.8	62.8	62.8	63.4	64.6	65.8	67.4	69.6	73.1	77.1	82.8
72.5°	53.7	54.4	55.0	54.7	56.2	56.9	58.9	60.1	63.4	66.0	71.0
75°	42.2	42.2	42.2	43.2	43.8	44.3	45.6	46.8	48.4	51.6	54.3
77.5°	31.5	31.4	31.6	31.8	32.5	33.2	33.5	34.6	36.1	37.6	39.9
80°	24.3	24.7	24.9	25.3	25.3	25.7	25.9	27.4	28.4	29.3	30.8
82.5°	18.8	18.9	18.9	19.0	19.2	19.4	20.0	20.4	20.8	21.6	22.6
85°	11.0	10.7	10.7	11.1	11.0	11.0	11.3	11.8	11.8	11.9	12.6
87.5°	8.9	8.9	9.1	8.8	8.8	9.0	9.1	9.0	9.2	9.5	8.9
90°	23.7	23.5	23.4	23.3	23.1	23.2	23.5	23.8	24.1	24.4	21.0
92.5°	22.6	22.6	22.6	22.5	22.5	22.4	22.4	22.3	22.2	22.2	21.4
95°	43.2	43.5	43.9	44.1	44.5	44.6	44.6	44.6	44.6	44.6	44.3
97.5°	74.8	74.9	74.9	75.0	75.0	75.0	75.0	75.0	75.0	75.0	74.4
100°	95.5	95.7	95.8	95.9	96.1	96.2	96.2	96.2	96.2	96.2	95.7
102.5°	118.9	119.0	119.2	119.4	119.5	119.6	119.4	119.3	119.1	119.0	118.4
105°	154.7	154.7	154.7	154.7	154.7	154.6	154.3	154.0	153.6	153.4	153.0
107.5°	188.5	189.2	189.9	190.6	191.4	191.6	191.5	191.4	191.3	191.1	191.1
110°	214.6	215.2	215.6	216.1	216.5	216.8	216.8	216.8	216.8	216.8	216.8



TEST NUMBER: P331259-940

CATALOG NUMBER: SA2XXDIP-C290D725U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	239.8	240.1	240.4	240.8	241.1	241.5	241.8	242.2	242.6	243.0	243.1
115°	278.8	279.3	279.7	280.2	280.6	281.0	281.2	281.2	281.4	281.6	281.9
117.5°	316.0	316.5	316.9	317.4	317.9	318.3	318.7	319.1	319.4	319.8	320.7
120°	342.2	342.7	343.1	343.6	344.1	344.3	344.3	344.3	344.3	344.3	345.5
122.5°	367.9	368.2	368.5	368.9	369.3	369.6	370.0	370.3	370.7	371.0	371.9
125°	407.1	407.2	407.3	407.5	407.7	408.0	408.4	408.9	409.4	409.8	410.3
127.5°	442.7	443.3	443.7	444.3	444.7	445.2	445.8	446.4	446.9	447.5	448.0
130°	468.4	469.0	469.7	470.2	470.8	471.4	471.6	472.0	472.3	472.6	472.9
132.5°	492.9	493.4	493.9	494.4	494.9	495.5	496.1	496.9	497.6	498.2	498.1
135°	531.1	531.5	532.1	532.5	533.0	533.2	533.4	533.6	533.8	533.9	533.6
137.5°	565.7	566.3	566.9	567.6	568.2	568.6	568.6	568.8	568.9	569.0	568.6
140°	589.7	590.3	590.9	591.6	592.1	592.5	592.5	592.5	592.5	592.5	591.7
142.5°	611.4	612.1	612.6	613.2	613.9	614.1	614.0	613.9	613.8	613.7	613.1
145°	644.0	644.6	645.2	645.9	646.5	646.8	646.6	646.4	646.3	646.1	645.2
147.5°	673.2	673.8	674.3	674.9	675.6	675.6	675.3	674.9	674.6	674.3	673.7
150°	692.1	692.6	693.0	693.5	694.0	694.0	693.5	693.0	692.6	692.1	691.5
152.5°	710.0	710.5	711.1	711.8	712.3	712.3	711.8	711.1	710.5	710.0	709.2
155°	734.0	734.4	734.9	735.3	735.8	735.7	734.9	734.1	733.3	732.5	732.1
157.5°	754.6	755.3	756.1	756.8	757.5	757.4	756.3	755.3	754.2	753.1	752.9
160°	767.4	768.0	768.7	769.3	769.9	769.7	768.8	767.9	767.0	766.0	765.9
162.5°	778.6	779.3	780.1	780.8	781.5	781.4	780.3	779.3	778.2	777.1	777.0
165°	793.2	794.0	794.7	795.5	796.3	796.1	795.0	794.0	792.9	791.8	791.8
167.5°	805.2	806.0	806.8	807.6	808.4	808.2	807.2	806.1	805.0	803.9	804.0
170°	811.3	812.3	813.2	814.1	815.0	814.9	813.9	812.8	811.7	810.6	810.7
172.5°	816.4	817.3	818.1	819.1	820.0	819.9	818.9	817.8	816.7	815.6	815.8
175°	821.8	822.7	823.6	824.6	825.5	825.4	824.3	823.2	822.2	821.1	821.4
177.5°	824.3	825.0	825.7	826.5	827.2	827.2	826.5	825.7	825.0	824.3	824.5
180°	825.9	825.9	825.9	825.9	825.9	825.9	825.9	825.9	825.9	825.9	825.9



TEST NUMBER: P331259-940

CATALOG NUMBER: SA2XXDIP-C290D725U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	540.8	539.6	538.8	535.8	533.2	530.7	529.9	530.1	526.6	523.2	521.7
5°	562.0	557.9	554.0	548.6	542.1	534.9	531.4	528.5	521.4	513.7	509.3
7.5°	580.8	575.0	567.6	557.3	547.9	536.7	529.6	523.3	513.0	502.1	495.4
10°	592.3	584.4	574.9	562.3	550.8	537.2	527.7	518.2	506.0	493.0	484.9
12.5°	602.2	591.6	582.2	566.1	552.4	535.4	524.1	510.7	497.9	482.5	474.6
15°	625.7	606.1	588.3	570.0	553.2	529.5	516.9	498.9	482.1	463.1	454.0
17.5°	643.9	621.8	593.8	570.6	551.0	524.7	506.3	484.7	464.8	443.1	430.7
20°	654.2	628.9	598.8	571.2	547.8	517.7	497.7	475.6	452.4	427.8	414.5
22.5°	660.4	633.8	604.0	568.8	541.3	512.1	486.9	462.6	439.1	412.6	398.6
25°	662.4	638.1	606.5	566.8	533.2	500.2	469.8	446.2	417.7	393.0	372.6
27.5°	652.7	635.3	604.9	562.9	523.8	485.2	451.3	424.7	394.6	367.7	347.1
30°	640.9	630.8	601.2	559.1	516.3	474.8	437.6	407.3	377.4	350.3	329.1
32.5°	622.6	620.5	594.4	553.6	508.4	461.7	423.1	392.6	359.4	332.7	312.6
35°	586.7	596.4	580.0	541.3	493.5	443.0	401.3	366.4	332.0	306.5	287.7
37.5°	538.4	562.6	558.3	523.3	473.2	422.7	376.6	340.2	307.4	281.6	263.1
40°	505.2	536.0	540.5	509.4	459.1	407.0	358.1	321.9	289.9	266.4	247.7
42.5°	469.6	505.5	517.7	492.9	443.4	390.4	341.6	304.1	272.3	249.5	233.0
45°	409.8	457.4	479.5	465.3	417.5	363.2	313.0	274.9	246.1	224.6	211.9
47.5°	353.9	405.9	435.6	430.6	388.6	334.8	285.2	248.6	220.6	203.5	192.1
50°	314.4	367.8	403.7	405.4	367.8	314.6	264.7	230.3	204.6	188.6	179.2
52.5°	280.0	331.1	370.1	378.8	344.6	293.6	246.5	212.1	189.5	174.8	166.5
55°	235.1	278.3	321.6	337.5	310.1	261.5	217.9	187.8	166.5	156.4	149.1
57.5°	195.6	231.5	271.5	289.0	272.2	230.5	189.7	163.5	146.2	137.3	131.7
60°	174.6	203.0	238.6	259.5	244.9	207.9	172.2	147.2	133.0	125.2	119.9
62.5°	155.2	180.3	210.4	229.5	221.6	186.6	154.7	132.7	120.5	113.1	109.2
65°	128.0	147.8	171.2	188.8	183.5	157.0	130.8	112.0	102.3	96.4	93.4
67.5°	105.4	119.8	135.9	151.3	147.1	128.3	107.4	92.6	85.4	80.3	78.5
70°	91.1	102.1	116.5	128.9	125.4	110.0	93.4	80.8	74.5	70.3	68.5
72.5°	77.6	86.5	97.6	107.6	105.3	92.5	78.6	69.2	64.3	60.4	58.9
75°	58.6	65.5	72.1	78.8	78.2	68.3	60.2	52.9	49.0	46.0	45.4
77.5°	43.2	47.1	51.6	55.6	54.5	48.8	42.4	38.3	35.5	33.4	33.1
80°	33.0	35.2	38.5	41.3	39.9	37.5	32.4	29.3	27.4	25.3	24.5
82.5°	24.0	26.1	28.1	29.7	28.5	26.3	23.2	21.1	19.9	18.5	18.2
85°	12.6	13.7	14.6	15.0	14.6	13.2	11.8	11.0	9.9	9.3	9.1
87.5°	8.4	7.7	7.0	6.8	6.0	5.6	4.5	3.7	3.9	4.1	4.2
90°	17.6	14.2	10.8	8.1	6.2	4.5	2.6	0.7	2.6	4.5	6.2
92.5°	20.5	19.7	18.9	17.8	16.5	15.2	13.7	12.4	13.7	15.2	16.5
95°	44.0	43.7	43.3	42.4	40.9	39.3	37.8	36.2	37.8	39.3	40.9
97.5°	73.8	73.2	72.7	71.7	70.3	68.9	67.6	66.3	67.6	68.9	70.3
100°	95.2	94.8	94.3	93.5	92.2	91.0	89.8	88.5	89.8	91.0	92.2
102.5°	117.9	117.3	116.7	115.9	114.9	114.0	112.9	111.9	112.9	114.0	114.9
105°	152.8	152.4	152.1	151.7	151.2	150.8	150.3	149.9	150.3	150.8	151.2
107.5°	191.1	191.1	191.1	190.7	190.1	189.4	188.8	188.1	188.8	189.4	190.1
110°	216.8	216.8	216.8	216.3	215.3	214.5	213.5	212.6	213.5	214.5	215.3



TEST NUMBER: P331259-940

CATALOG NUMBER: SA2XXDIP-C290D725U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	243.3	243.3	243.4	243.1	242.1	241.2	240.3	239.3	240.3	241.2	242.1
115°	282.2	282.5	282.9	282.5	281.6	280.6	279.7	278.8	279.7	280.6	281.6
117.5°	321.6	322.4	323.2	323.1	321.8	320.6	319.3	318.1	319.3	320.6	321.8
120°	346.8	348.0	349.3	349.3	348.0	346.8	345.5	344.3	345.5	346.8	348.0
122.5°	372.8	373.7	374.5	374.3	372.7	371.3	369.8	368.3	369.8	371.3	372.7
125°	410.7	411.3	411.7	411.3	409.8	408.4	407.1	405.6	407.1	408.4	409.8
127.5°	448.6	449.2	449.7	449.1	447.4	445.6	443.8	442.0	443.8	445.6	447.4
130°	473.1	473.5	473.8	473.0	470.9	469.0	466.9	464.9	466.9	469.0	470.9
132.5°	498.1	498.0	497.9	497.1	495.4	493.8	492.2	490.5	492.2	493.8	495.4
135°	533.2	533.0	532.6	531.6	529.9	528.2	526.6	524.9	526.6	528.2	529.9
137.5°	568.2	567.8	567.4	566.5	565.2	563.7	562.3	561.0	562.3	563.7	565.2
140°	590.9	590.1	589.3	588.3	586.8	585.5	584.1	582.7	584.1	585.5	586.8
142.5°	612.6	612.1	611.5	610.6	609.2	607.8	606.4	605.0	606.4	607.8	609.2
145°	644.3	643.4	642.4	641.4	640.3	639.3	638.1	637.0	638.1	639.3	640.3
147.5°	673.1	672.4	671.8	670.8	669.5	668.2	666.9	665.7	666.9	668.2	669.5
150°	690.9	690.3	689.6	688.8	688.0	687.0	686.1	685.2	686.1	687.0	688.0
152.5°	708.5	707.8	706.9	706.1	705.3	704.3	703.4	702.4	703.4	704.3	705.3
155°	731.6	731.1	730.7	730.2	729.8	729.3	728.8	728.3	728.8	729.3	729.8
157.5°	752.6	752.3	752.1	751.8	751.4	751.2	750.8	750.6	750.8	751.2	751.4
160°	765.7	765.5	765.4	765.2	764.8	764.6	764.2	763.9	764.2	764.6	764.8
162.5°	776.9	776.7	776.5	776.4	776.3	776.3	776.2	776.1	776.2	776.3	776.3
165°	791.8	791.8	791.8	791.8	792.0	792.2	792.4	792.5	792.4	792.2	792.0
167.5°	804.0	804.1	804.1	804.3	804.8	805.2	805.7	806.1	805.7	805.2	804.8
170°	810.9	811.1	811.2	811.5	812.0	812.4	813.0	813.4	813.0	812.4	812.0
172.5°	815.9	816.1	816.3	816.5	817.0	817.5	818.0	818.4	818.0	817.5	817.0
175°	821.7	822.0	822.3	822.7	823.1	823.6	824.1	824.6	824.1	823.6	823.1
177.5°	824.7	825.0	825.3	825.5	825.9	826.3	826.7	827.1	826.7	826.3	825.9
180°	825.9	825.9	825.9	825.9	825.9	825.9	825.9	825.9	825.9	825.9	825.9



TEST NUMBER: P331259-940

CATALOG NUMBER: SA2XXDIP-C290D725U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	520.1	519.2	515.8	514.0	511.0	508.3	506.5	507.3	507.9	507.7	507.1
5°	505.2	501.3	495.4	490.4	486.8	480.1	477.2	475.8	474.6	473.2	471.8
7.5°	487.4	481.3	473.0	465.7	459.0	450.6	445.9	443.1	440.1	436.9	434.1
10°	474.8	466.3	457.4	447.3	439.2	431.7	425.0	420.5	416.4	412.6	409.8
12.5°	461.5	451.7	440.7	426.9	417.9	407.2	406.2	398.3	392.0	389.6	386.3
15°	440.4	426.6	412.6	396.2	389.1	379.4	373.4	367.2	361.8	357.9	357.0
17.5°	416.3	398.5	384.6	372.8	361.2	351.2	345.6	340.8	336.3	331.2	330.5
20°	398.1	382.6	367.5	357.1	345.2	335.0	328.1	323.3	319.4	316.4	313.8
22.5°	380.7	363.8	349.9	338.7	326.9	318.7	313.3	308.5	305.3	302.0	299.5
25°	352.8	339.7	324.5	311.7	302.0	296.8	292.3	288.3	286.2	284.0	281.2
27.5°	328.5	313.9	299.7	289.8	281.2	276.6	273.4	270.6	268.8	267.4	265.8
30°	311.4	296.6	285.4	275.7	268.6	263.9	261.9	260.3	258.1	257.3	256.5
32.5°	294.8	281.5	272.0	263.5	256.8	253.7	251.9	250.4	248.7	247.9	246.2
35°	271.4	260.3	251.0	246.3	240.9	238.2	236.8	234.8	233.2	232.4	232.1
37.5°	249.4	239.8	233.6	227.7	225.3	223.7	221.8	220.4	219.9	219.8	219.5
40°	235.1	227.3	221.8	217.0	216.0	213.5	211.9	210.7	210.7	210.9	210.7
42.5°	222.2	215.1	210.3	206.1	204.9	203.5	201.8	201.8	202.1	202.8	202.1
45°	202.6	197.5	194.0	192.1	189.8	188.4	188.2	188.8	189.0	189.2	189.8
47.5°	184.5	181.1	178.0	175.8	174.8	174.6	174.3	175.4	176.4	176.7	177.6
50°	173.8	170.0	167.3	165.9	165.1	164.7	165.1	166.3	167.1	168.1	168.7
52.5°	161.8	159.1	157.3	156.1	155.9	156.1	156.1	157.6	158.8	159.3	159.5
55°	145.3	143.2	142.9	141.0	141.8	141.6	142.6	143.4	144.6	145.9	146.1
57.5°	128.7	127.1	126.0	126.2	126.4	127.3	128.1	129.6	130.8	132.2	132.2
60°	117.7	116.9	116.3	116.3	116.6	117.9	118.9	120.3	121.1	122.0	122.5
62.5°	107.6	106.8	106.2	106.6	107.6	108.3	109.5	110.3	111.1	111.9	112.2
65°	91.8	91.4	91.9	92.4	92.6	93.5	95.0	95.6	96.4	96.8	98.3
67.5°	77.1	77.2	77.1	77.7	78.9	79.1	80.4	81.9	82.0	82.8	83.7
70°	67.2	67.7	68.0	68.5	69.5	69.9	70.9	71.5	72.3	72.9	73.6
72.5°	58.1	58.2	58.7	58.6	59.5	60.3	61.2	61.8	62.6	63.4	63.9
75°	44.8	44.8	45.2	45.4	46.4	47.4	47.2	47.6	48.4	49.2	49.7
77.5°	32.7	32.3	32.7	32.9	33.3	34.1	34.2	34.8	35.8	35.5	35.9
80°	24.9	24.3	24.9	25.1	25.1	26.1	26.1	26.6	27.1	26.6	27.1
82.5°	17.7	17.5	17.9	18.0	18.3	18.4	18.6	18.7	19.4	19.1	19.4
85°	8.9	8.7	8.9	8.7	8.9	9.1	9.1	8.9	8.9	9.3	8.7
87.5°	4.4	4.7	5.3	6.0	6.5	7.0	6.8	6.7	6.6	6.2	6.2
90°	8.1	10.8	14.2	17.6	21.0	24.4	24.1	23.8	23.5	23.2	23.1
92.5°	17.8	18.9	19.7	20.5	21.4	22.2	22.2	22.3	22.4	22.4	22.5
95°	42.4	43.3	43.7	44.0	44.3	44.6	44.6	44.6	44.6	44.6	44.5
97.5°	71.7	72.7	73.2	73.8	74.4	75.0	75.0	75.0	75.0	75.0	75.0
100°	93.5	94.3	94.8	95.2	95.7	96.2	96.2	96.2	96.2	96.2	96.1
102.5°	115.9	116.7	117.3	117.9	118.4	119.0	119.1	119.3	119.4	119.6	119.5
105°	151.7	152.1	152.4	152.8	153.0	153.4	153.6	154.0	154.3	154.6	154.7
107.5°	190.7	191.1	191.1	191.1	191.1	191.1	191.3	191.4	191.5	191.6	191.4
110°	216.3	216.8	216.8	216.8	216.8	216.8	216.8	216.8	216.8	216.8	216.5



TEST NUMBER: P331259-940

CATALOG NUMBER: SA2XXDIP-C290D725U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	243.1	243.4	243.3	243.3	243.1	243.0	242.6	242.2	241.8	241.5	241.1
115°	282.5	282.9	282.5	282.2	281.9	281.6	281.4	281.2	281.2	281.0	280.6
117.5°	323.1	323.2	322.4	321.6	320.7	319.8	319.4	319.1	318.7	318.3	317.9
120°	349.3	349.3	348.0	346.8	345.5	344.3	344.3	344.3	344.3	344.3	344.1
122.5°	374.3	374.5	373.7	372.8	371.9	371.0	370.7	370.3	370.0	369.6	369.3
125°	411.3	411.7	411.3	410.7	410.3	409.8	409.4	408.9	408.4	408.0	407.7
127.5°	449.1	449.7	449.2	448.6	448.0	447.5	446.9	446.4	445.8	445.2	444.7
130°	473.0	473.8	473.5	473.1	472.9	472.6	472.3	472.0	471.6	471.4	470.8
132.5°	497.1	497.9	498.0	498.1	498.1	498.2	497.6	496.9	496.1	495.5	494.9
135°	531.6	532.6	533.0	533.2	533.6	533.9	533.8	533.6	533.4	533.2	533.0
137.5°	566.5	567.4	567.8	568.2	568.6	569.0	568.9	568.8	568.6	568.6	568.2
140°	588.3	589.3	590.1	590.9	591.7	592.5	592.5	592.5	592.5	592.5	592.1
142.5°	610.6	611.5	612.1	612.6	613.1	613.7	613.8	613.9	614.0	614.1	613.9
145°	641.4	642.4	643.4	644.3	645.2	646.1	646.3	646.4	646.6	646.8	646.5
147.5°	670.8	671.8	672.4	673.1	673.7	674.3	674.6	674.9	675.3	675.6	675.6
150°	688.8	689.6	690.3	690.9	691.5	692.1	692.6	693.0	693.5	694.0	694.0
152.5°	706.1	706.9	707.8	708.5	709.2	710.0	710.5	711.1	711.8	712.3	712.3
155°	730.2	730.7	731.1	731.6	732.1	732.5	733.3	734.1	734.9	735.7	735.8
157.5°	751.8	752.1	752.3	752.6	752.9	753.1	754.2	755.3	756.3	757.4	757.5
160°	765.2	765.4	765.5	765.7	765.9	766.0	767.0	767.9	768.8	769.7	769.9
162.5°	776.4	776.5	776.7	776.9	777.0	777.1	778.2	779.3	780.3	781.4	781.5
165°	791.8	791.8	791.8	791.8	791.8	791.8	792.9	794.0	795.0	796.1	796.3
167.5°	804.3	804.1	804.1	804.0	804.0	803.9	805.0	806.1	807.2	808.2	808.4
170°	811.5	811.2	811.1	810.9	810.7	810.6	811.7	812.8	813.9	814.9	815.0
172.5°	816.5	816.3	816.1	815.9	815.8	815.6	816.7	817.8	818.9	819.9	820.0
175°	822.7	822.3	822.0	821.7	821.4	821.1	822.2	823.2	824.3	825.4	825.5
177.5°	825.5	825.3	825.0	824.7	824.5	824.3	825.0	825.7	826.5	827.2	827.2
180°	825.9	825.9	825.9	825.9	825.9	825.9	825.9	825.9	825.9	825.9	825.9



TEST NUMBER: P331259-940

CATALOG NUMBER: SA2XXDIP-C290D725U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	505.5	505.2	505.2	503.7	505.2	505.2	505.5	507.1	507.7	507.9	507.3
5°	469.0	468.3	467.3	468.3	467.3	468.3	469.0	471.8	473.2	474.6	475.8
7.5°	432.7	430.3	430.0	427.6	430.0	430.3	432.7	434.1	436.9	440.1	443.1
10°	406.4	404.7	404.5	400.6	404.5	404.7	406.4	409.8	412.6	416.4	420.5
12.5°	386.3	382.4	383.2	380.9	383.2	382.4	386.3	386.3	389.6	392.0	398.3
15°	351.4	351.4	350.6	347.2	350.6	351.4	351.4	357.0	357.9	361.8	367.2
17.5°	326.5	326.0	324.1	325.1	324.1	326.0	326.5	330.5	331.2	336.3	340.8
20°	311.6	310.3	307.9	307.9	307.9	310.3	311.6	313.8	316.4	319.4	323.3
22.5°	297.5	297.4	294.8	295.6	294.8	297.4	297.5	299.5	302.0	305.3	308.5
25°	281.0	279.4	278.1	278.7	278.1	279.4	281.0	281.2	284.0	286.2	288.3
27.5°	265.3	264.4	264.3	262.7	264.3	264.4	265.3	265.8	267.4	268.8	270.6
30°	256.3	254.2	254.6	253.6	254.6	254.2	256.3	256.5	257.3	258.1	260.3
32.5°	245.8	245.1	244.8	243.9	244.8	245.1	245.8	246.2	247.9	248.7	250.4
35°	231.8	231.9	231.0	231.3	231.0	231.9	231.8	232.1	232.4	233.2	234.8
37.5°	219.4	220.0	219.5	219.6	219.5	220.0	219.4	219.5	219.8	219.9	220.4
40°	211.2	211.2	211.2	211.9	211.2	211.2	211.2	210.7	210.9	210.7	210.7
42.5°	203.5	203.1	202.9	202.8	202.9	203.1	203.5	202.1	202.8	202.1	201.8
45°	190.2	190.8	191.0	190.0	191.0	190.8	190.2	189.8	189.2	189.0	188.8
47.5°	178.2	178.3	178.2	179.1	178.2	178.3	178.2	177.6	176.7	176.4	175.4
50°	169.8	169.3	169.8	169.3	169.8	169.3	169.8	168.7	168.1	167.1	166.3
52.5°	160.9	161.0	160.7	160.6	160.7	161.0	160.9	159.5	159.3	158.8	157.6
55°	146.9	147.2	147.0	147.0	147.0	147.2	146.9	146.1	145.9	144.6	143.4
57.5°	132.4	132.8	133.0	132.2	133.0	132.8	132.4	132.2	132.2	130.8	129.6
60°	122.3	123.3	123.1	122.8	123.1	123.3	122.3	122.5	122.0	121.1	120.3
62.5°	113.1	113.5	113.4	113.3	113.4	113.5	113.1	112.2	111.9	111.1	110.3
65°	98.9	99.2	98.6	99.2	98.6	99.2	98.9	98.3	96.8	96.4	95.6
67.5°	83.5	83.6	84.1	84.4	84.1	83.6	83.5	83.7	82.8	82.0	81.9
70°	73.9	73.7	74.4	75.0	74.4	73.7	73.9	73.6	72.9	72.3	71.5
72.5°	63.8	64.3	64.1	64.6	64.1	64.3	63.8	63.9	63.4	62.6	61.8
75°	49.2	49.8	49.7	50.2	49.7	49.8	49.2	49.7	49.2	48.4	47.6
77.5°	35.6	35.7	35.6	35.9	35.6	35.7	35.6	35.9	35.5	35.8	34.8
80°	27.1	26.8	26.3	27.1	26.3	26.8	27.1	27.1	26.6	27.1	26.6
82.5°	18.9	19.1	18.7	18.7	18.7	19.1	18.9	19.4	19.1	19.4	18.7
85°	8.7	8.5	8.1	8.1	8.1	8.5	8.7	8.7	9.3	8.9	8.9
87.5°	6.2	6.2	6.2	6.1	6.2	6.2	6.2	6.2	6.2	6.6	6.7
90°	23.3	23.4	23.5	23.7	23.5	23.4	23.3	23.1	23.2	23.5	23.8
92.5°	22.5	22.6	22.6	22.6	22.6	22.6	22.5	22.5	22.4	22.4	22.3
95°	44.1	43.9	43.5	43.2	43.5	43.9	44.1	44.5	44.6	44.6	44.6
97.5°	75.0	74.9	74.9	74.8	74.9	74.9	75.0	75.0	75.0	75.0	75.0
100°	95.9	95.8	95.7	95.5	95.7	95.8	95.9	96.1	96.2	96.2	96.2
102.5°	119.4	119.2	119.0	118.9	119.0	119.2	119.4	119.5	119.6	119.4	119.3
105°	154.7	154.7	154.7	154.7	154.7	154.7	154.7	154.7	154.6	154.3	154.0
107.5°	190.6	189.9	189.2	188.5	189.2	189.9	190.6	191.4	191.6	191.5	191.4
110°	216.1	215.6	215.2	214.6	215.2	215.6	216.1	216.5	216.8	216.8	216.8



TEST NUMBER: P331259-940

CATALOG NUMBER: SA2XXDIP-C290D725U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	240.8	240.4	240.1	239.8	240.1	240.4	240.8	241.1	241.5	241.8	242.2
115°	280.2	279.7	279.3	278.8	279.3	279.7	280.2	280.6	281.0	281.2	281.2
117.5°	317.4	316.9	316.5	316.0	316.5	316.9	317.4	317.9	318.3	318.7	319.1
120°	343.6	343.1	342.7	342.2	342.7	343.1	343.6	344.1	344.3	344.3	344.3
122.5°	368.9	368.5	368.2	367.9	368.2	368.5	368.9	369.3	369.6	370.0	370.3
125°	407.5	407.3	407.2	407.1	407.2	407.3	407.5	407.7	408.0	408.4	408.9
127.5°	444.3	443.7	443.3	442.7	443.3	443.7	444.3	444.7	445.2	445.8	446.4
130°	470.2	469.7	469.0	468.4	469.0	469.7	470.2	470.8	471.4	471.6	472.0
132.5°	494.4	493.9	493.4	492.9	493.4	493.9	494.4	494.9	495.5	496.1	496.9
135°	532.5	532.1	531.5	531.1	531.5	532.1	532.5	533.0	533.2	533.4	533.6
137.5°	567.6	566.9	566.3	565.7	566.3	566.9	567.6	568.2	568.6	568.6	568.8
140°	591.6	590.9	590.3	589.7	590.3	590.9	591.6	592.1	592.5	592.5	592.5
142.5°	613.2	612.6	612.1	611.4	612.1	612.6	613.2	613.9	614.1	614.0	613.9
145°	645.9	645.2	644.6	644.0	644.6	645.2	645.9	646.5	646.8	646.6	646.4
147.5°	674.9	674.3	673.8	673.2	673.8	674.3	674.9	675.6	675.6	675.3	674.9
150°	693.5	693.0	692.6	692.1	692.6	693.0	693.5	694.0	694.0	693.5	693.0
152.5°	711.8	711.1	710.5	710.0	710.5	711.1	711.8	712.3	712.3	711.8	711.1
155°	735.3	734.9	734.4	734.0	734.4	734.9	735.3	735.8	735.7	734.9	734.1
157.5°	756.8	756.1	755.3	754.6	755.3	756.1	756.8	757.5	757.4	756.3	755.3
160°	769.3	768.7	768.0	767.4	768.0	768.7	769.3	769.9	769.7	768.8	767.9
162.5°	780.8	780.1	779.3	778.6	779.3	780.1	780.8	781.5	781.4	780.3	779.3
165°	795.5	794.7	794.0	793.2	794.0	794.7	795.5	796.3	796.1	795.0	794.0
167.5°	807.6	806.8	806.0	805.2	806.0	806.8	807.6	808.4	808.2	807.2	806.1
170°	814.1	813.2	812.3	811.3	812.3	813.2	814.1	815.0	814.9	813.9	812.8
172.5°	819.1	818.1	817.3	816.4	817.3	818.1	819.1	820.0	819.9	818.9	817.8
175°	824.6	823.6	822.7	821.8	822.7	823.6	824.6	825.5	825.4	824.3	823.2
177.5°	826.5	825.7	825.0	824.3	825.0	825.7	826.5	827.2	827.2	826.5	825.7
180°	825.9	825.9	825.9	825.9	825.9	825.9	825.9	825.9	825.9	825.9	825.9



TEST NUMBER: P331259-940

CATALOG NUMBER: SA2XXDIP-C290D725U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	506.5	508.3	511.0	514.0	515.8	519.2	520.1	521.7	523.2	526.6	530.1
5°	477.2	480.1	486.8	490.4	495.4	501.3	505.2	509.3	513.7	521.4	528.5
7.5°	445.9	450.6	459.0	465.7	473.0	481.3	487.4	495.4	502.1	513.0	523.3
10°	425.0	431.7	439.2	447.3	457.4	466.3	474.8	484.9	493.0	506.0	518.2
12.5°	406.2	407.2	417.9	426.9	440.7	451.7	461.5	474.6	482.5	497.9	510.7
15°	373.4	379.4	389.1	396.2	412.6	426.6	440.4	454.0	463.1	482.1	498.9
17.5°	345.6	351.2	361.2	372.8	384.6	398.5	416.3	430.7	443.1	464.8	484.7
20°	328.1	335.0	345.2	357.1	367.5	382.6	398.1	414.5	427.8	452.4	475.6
22.5°	313.3	318.7	326.9	338.7	349.9	363.8	380.7	398.6	412.6	439.1	462.6
25°	292.3	296.8	302.0	311.7	324.5	339.7	352.8	372.6	393.0	417.7	446.2
27.5°	273.4	276.6	281.2	289.8	299.7	313.9	328.5	347.1	367.7	394.6	424.7
30°	261.9	263.9	268.6	275.7	285.4	296.6	311.4	329.1	350.3	377.4	407.3
32.5°	251.9	253.7	256.8	263.5	272.0	281.5	294.8	312.6	332.7	359.4	392.6
35°	236.8	238.2	240.9	246.3	251.0	260.3	271.4	287.7	306.5	332.0	366.4
37.5°	221.8	223.7	225.3	227.7	233.6	239.8	249.4	263.1	281.6	307.4	340.2
40°	211.9	213.5	216.0	217.0	221.8	227.3	235.1	247.7	266.4	289.9	321.9
42.5°	201.8	203.5	204.9	206.1	210.3	215.1	222.2	233.0	249.5	272.3	304.1
45°	188.2	188.4	189.8	192.1	194.0	197.5	202.6	211.9	224.6	246.1	274.9
47.5°	174.3	174.6	174.8	175.8	178.0	181.1	184.5	192.1	203.5	220.6	248.6
50°	165.1	164.7	165.1	165.9	167.3	170.0	173.8	179.2	188.6	204.6	230.3
52.5°	156.1	156.1	155.9	156.1	157.3	159.1	161.8	166.5	174.8	189.5	212.1
55°	142.6	141.6	141.8	141.0	142.9	143.2	145.3	149.1	156.4	166.5	187.8
57.5°	128.1	127.3	126.4	126.2	126.0	127.1	128.7	131.7	137.3	146.2	163.5
60°	118.9	117.9	116.6	116.3	116.3	116.9	117.7	119.9	125.2	133.0	147.2
62.5°	109.5	108.3	107.6	106.6	106.2	106.8	107.6	109.2	113.1	120.5	132.7
65°	95.0	93.5	92.6	92.4	91.9	91.4	91.8	93.4	96.4	102.3	112.0
67.5°	80.4	79.1	78.9	77.7	77.1	77.2	77.1	78.5	80.3	85.4	92.6
70°	70.9	69.9	69.5	68.5	68.0	67.7	67.2	68.5	70.3	74.5	80.8
72.5°	61.2	60.3	59.5	58.6	58.7	58.2	58.1	58.9	60.4	64.3	69.2
75°	47.2	47.4	46.4	45.4	45.2	44.8	44.8	45.4	46.0	49.0	52.9
77.5°	34.2	34.1	33.3	32.9	32.7	32.3	32.7	33.1	33.4	35.5	38.3
80°	26.1	26.1	25.1	25.1	24.9	24.3	24.9	24.5	25.3	27.4	29.3
82.5°	18.6	18.4	18.3	18.0	17.9	17.5	17.7	18.2	18.5	19.9	21.1
85°	9.1	9.1	8.9	8.7	8.9	8.7	8.9	9.1	9.3	9.9	11.0
87.5°	6.8	7.0	6.5	6.0	5.3	4.7	4.4	4.2	4.1	3.9	3.7
90°	24.1	24.4	21.0	17.6	14.2	10.8	8.1	6.2	4.5	2.6	0.7
92.5°	22.2	22.2	21.4	20.5	19.7	18.9	17.8	16.5	15.2	13.7	12.4
95°	44.6	44.6	44.3	44.0	43.7	43.3	42.4	40.9	39.3	37.8	36.2
97.5°	75.0	75.0	74.4	73.8	73.2	72.7	71.7	70.3	68.9	67.6	66.3
100°	96.2	96.2	95.7	95.2	94.8	94.3	93.5	92.2	91.0	89.8	88.5
102.5°	119.1	119.0	118.4	117.9	117.3	116.7	115.9	114.9	114.0	112.9	111.9
105°	153.6	153.4	153.0	152.8	152.4	152.1	151.7	151.2	150.8	150.3	149.9
107.5°	191.3	191.1	191.1	191.1	191.1	191.1	190.7	190.1	189.4	188.8	188.1
110°	216.8	216.8	216.8	216.8	216.8	216.8	216.3	215.3	214.5	213.5	212.6



TEST NUMBER: P331259-940

CATALOG NUMBER: SA2XXDIP-C290D725U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	242.6	243.0	243.1	243.3	243.3	243.4	243.1	242.1	241.2	240.3	239.3
115°	281.4	281.6	281.9	282.2	282.5	282.9	282.5	281.6	280.6	279.7	278.8
117.5°	319.4	319.8	320.7	321.6	322.4	323.2	323.1	321.8	320.6	319.3	318.1
120°	344.3	344.3	345.5	346.8	348.0	349.3	349.3	348.0	346.8	345.5	344.3
122.5°	370.7	371.0	371.9	372.8	373.7	374.5	374.3	372.7	371.3	369.8	368.3
125°	409.4	409.8	410.3	410.7	411.3	411.7	411.3	409.8	408.4	407.1	405.6
127.5°	446.9	447.5	448.0	448.6	449.2	449.7	449.1	447.4	445.6	443.8	442.0
130°	472.3	472.6	472.9	473.1	473.5	473.8	473.0	470.9	469.0	466.9	464.9
132.5°	497.6	498.2	498.1	498.1	498.0	497.9	497.1	495.4	493.8	492.2	490.5
135°	533.8	533.9	533.6	533.2	533.0	532.6	531.6	529.9	528.2	526.6	524.9
137.5°	568.9	569.0	568.6	568.2	567.8	567.4	566.5	565.2	563.7	562.3	561.0
140°	592.5	592.5	591.7	590.9	590.1	589.3	588.3	586.8	585.5	584.1	582.7
142.5°	613.8	613.7	613.1	612.6	612.1	611.5	610.6	609.2	607.8	606.4	605.0
145°	646.3	646.1	645.2	644.3	643.4	642.4	641.4	640.3	639.3	638.1	637.0
147.5°	674.6	674.3	673.7	673.1	672.4	671.8	670.8	669.5	668.2	666.9	665.7
150°	692.6	692.1	691.5	690.9	690.3	689.6	688.8	688.0	687.0	686.1	685.2
152.5°	710.5	710.0	709.2	708.5	707.8	706.9	706.1	705.3	704.3	703.4	702.4
155°	733.3	732.5	732.1	731.6	731.1	730.7	730.2	729.8	729.3	728.8	728.3
157.5°	754.2	753.1	752.9	752.6	752.3	752.1	751.8	751.4	751.2	750.8	750.6
160°	767.0	766.0	765.9	765.7	765.5	765.4	765.2	764.8	764.6	764.2	763.9
162.5°	778.2	777.1	777.0	776.9	776.7	776.5	776.4	776.3	776.3	776.2	776.1
165°	792.9	791.8	791.8	791.8	791.8	791.8	791.8	792.0	792.2	792.4	792.5
167.5°	805.0	803.9	804.0	804.0	804.1	804.1	804.3	804.8	805.2	805.7	806.1
170°	811.7	810.6	810.7	810.9	811.1	811.2	811.5	812.0	812.4	813.0	813.4
172.5°	816.7	815.6	815.8	815.9	816.1	816.3	816.5	817.0	817.5	818.0	818.4
175°	822.2	821.1	821.4	821.7	822.0	822.3	822.7	823.1	823.6	824.1	824.6
177.5°	825.0	824.3	824.5	824.7	825.0	825.3	825.5	825.9	826.3	826.7	827.1
180°	825.9	825.9	825.9	825.9	825.9	825.9	825.9	825.9	825.9	825.9	825.9



TEST NUMBER: P331259-940

CATALOG NUMBER: SA2XXDIP-C290D725U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	529.9	530.7	533.2	535.8	538.8	539.6	540.8	539.8	539.4	542.4	544.7
5°	531.4	534.9	542.1	548.6	554.0	557.9	562.0	563.6	566.6	570.8	576.1
7.5°	529.6	536.7	547.9	557.3	567.6	575.0	580.8	585.8	591.7	599.8	608.6
10°	527.7	537.2	550.8	562.3	574.9	584.4	592.3	600.0	608.9	620.1	631.6
12.5°	524.1	535.4	552.4	566.1	582.2	591.6	602.2	618.8	628.4	643.9	660.1
15°	516.9	529.5	553.2	570.0	588.3	606.1	625.7	641.5	657.3	666.5	689.3
17.5°	506.3	524.7	551.0	570.6	593.8	621.8	643.9	661.8	680.0	694.8	706.3
20°	497.7	517.7	547.8	571.2	598.8	628.9	654.2	672.5	688.3	700.7	707.8
22.5°	486.9	512.1	541.3	568.8	604.0	633.8	660.4	674.8	688.0	694.0	696.8
25°	469.8	500.2	533.2	566.8	606.5	638.1	662.4	671.1	674.9	669.1	659.3
27.5°	451.3	485.2	523.8	562.9	604.9	635.3	652.7	651.4	644.9	625.8	610.6
30°	437.6	474.8	516.3	559.1	601.2	630.8	640.9	630.8	616.0	594.8	573.0
32.5°	423.1	461.7	508.4	553.6	594.4	620.5	622.6	605.2	582.3	558.1	531.1
35°	401.3	443.0	493.5	541.3	580.0	596.4	586.7	555.8	528.7	495.7	458.8
37.5°	376.6	422.7	473.2	523.3	558.3	562.6	538.4	506.0	467.7	428.9	385.5
40°	358.1	407.0	459.1	509.4	540.5	536.0	505.2	469.6	424.0	376.6	336.3
42.5°	341.6	390.4	443.4	492.9	517.7	505.5	469.6	425.8	376.8	332.2	295.2
45°	313.0	363.2	417.5	465.3	479.5	457.4	409.8	361.1	313.0	275.7	246.6
47.5°	285.2	334.8	388.6	430.6	435.6	405.9	353.9	303.9	262.4	232.1	211.5
50°	264.7	314.6	367.8	405.4	403.7	367.8	314.4	266.8	232.1	207.6	193.9
52.5°	246.5	293.6	344.6	378.8	370.1	331.1	280.0	237.7	209.3	190.1	177.6
55°	217.9	261.5	310.1	337.5	321.6	278.3	235.1	201.2	180.0	165.7	156.0
57.5°	189.7	230.5	272.2	289.0	271.5	231.5	195.6	170.9	155.0	144.4	138.0
60°	172.2	207.9	244.9	259.5	238.6	203.0	174.6	152.6	139.7	131.1	125.4
62.5°	154.7	186.6	221.6	229.5	210.4	180.3	155.2	136.8	126.4	118.6	113.2
65°	130.8	157.0	183.5	188.8	171.2	147.8	128.0	116.1	106.7	101.1	96.8
67.5°	107.4	128.3	147.1	151.3	135.9	119.8	105.4	95.0	88.7	84.0	80.3
70°	93.4	110.0	125.4	128.9	116.5	102.1	91.1	82.8	77.1	73.1	69.6
72.5°	78.6	92.5	105.3	107.6	97.6	86.5	77.6	71.0	66.0	63.4	60.1
75°	60.2	68.3	78.2	78.8	72.1	65.5	58.6	54.3	51.6	48.4	46.8
77.5°	42.4	48.8	54.5	55.6	51.6	47.1	43.2	39.9	37.6	36.1	34.6
80°	32.4	37.5	39.9	41.3	38.5	35.2	33.0	30.8	29.3	28.4	27.4
82.5°	23.2	26.3	28.5	29.7	28.1	26.1	24.0	22.6	21.6	20.8	20.4
85°	11.8	13.2	14.6	15.0	14.6	13.7	12.6	12.6	11.9	11.8	11.8
87.5°	4.5	5.6	6.0	6.8	7.0	7.7	8.4	8.9	9.5	9.2	9.0
90°	2.6	4.5	6.2	8.1	10.8	14.2	17.6	21.0	24.4	24.1	23.8
92.5°	13.7	15.2	16.5	17.8	18.9	19.7	20.5	21.4	22.2	22.2	22.3
95°	37.8	39.3	40.9	42.4	43.3	43.7	44.0	44.3	44.6	44.6	44.6
97.5°	67.6	68.9	70.3	71.7	72.7	73.2	73.8	74.4	75.0	75.0	75.0
100°	89.8	91.0	92.2	93.5	94.3	94.8	95.2	95.7	96.2	96.2	96.2
102.5°	112.9	114.0	114.9	115.9	116.7	117.3	117.9	118.4	119.0	119.1	119.3
105°	150.3	150.8	151.2	151.7	152.1	152.4	152.8	153.0	153.4	153.6	154.0
107.5°	188.8	189.4	190.1	190.7	191.1	191.1	191.1	191.1	191.1	191.3	191.4
110°	213.5	214.5	215.3	216.3	216.8	216.8	216.8	216.8	216.8	216.8	216.8



TEST NUMBER: P331259-940

CATALOG NUMBER: SA2XXDIP-C290D725U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	240.3	241.2	242.1	243.1	243.4	243.3	243.3	243.1	243.0	242.6	242.2
115°	279.7	280.6	281.6	282.5	282.9	282.5	282.2	281.9	281.6	281.4	281.2
117.5°	319.3	320.6	321.8	323.1	323.2	322.4	321.6	320.7	319.8	319.4	319.1
120°	345.5	346.8	348.0	349.3	349.3	348.0	346.8	345.5	344.3	344.3	344.3
122.5°	369.8	371.3	372.7	374.3	374.5	373.7	372.8	371.9	371.0	370.7	370.3
125°	407.1	408.4	409.8	411.3	411.7	411.3	410.7	410.3	409.8	409.4	408.9
127.5°	443.8	445.6	447.4	449.1	449.7	449.2	448.6	448.0	447.5	446.9	446.4
130°	466.9	469.0	470.9	473.0	473.8	473.5	473.1	472.9	472.6	472.3	472.0
132.5°	492.2	493.8	495.4	497.1	497.9	498.0	498.1	498.1	498.2	497.6	496.9
135°	526.6	528.2	529.9	531.6	532.6	533.0	533.2	533.6	533.9	533.8	533.6
137.5°	562.3	563.7	565.2	566.5	567.4	567.8	568.2	568.6	569.0	568.9	568.8
140°	584.1	585.5	586.8	588.3	589.3	590.1	590.9	591.7	592.5	592.5	592.5
142.5°	606.4	607.8	609.2	610.6	611.5	612.1	612.6	613.1	613.7	613.8	613.9
145°	638.1	639.3	640.3	641.4	642.4	643.4	644.3	645.2	646.1	646.3	646.4
147.5°	666.9	668.2	669.5	670.8	671.8	672.4	673.1	673.7	674.3	674.6	674.9
150°	686.1	687.0	688.0	688.8	689.6	690.3	690.9	691.5	692.1	692.6	693.0
152.5°	703.4	704.3	705.3	706.1	706.9	707.8	708.5	709.2	710.0	710.5	711.1
155°	728.8	729.3	729.8	730.2	730.7	731.1	731.6	732.1	732.5	733.3	734.1
157.5°	750.8	751.2	751.4	751.8	752.1	752.3	752.6	752.9	753.1	754.2	755.3
160°	764.2	764.6	764.8	765.2	765.4	765.5	765.7	765.9	766.0	767.0	767.9
162.5°	776.2	776.3	776.3	776.4	776.5	776.7	776.9	777.0	777.1	778.2	779.3
165°	792.4	792.2	792.0	791.8	791.8	791.8	791.8	791.8	791.8	792.9	794.0
167.5°	805.7	805.2	804.8	804.3	804.1	804.1	804.0	804.0	803.9	805.0	806.1
170°	813.0	812.4	812.0	811.5	811.2	811.1	810.9	810.7	810.6	811.7	812.8
172.5°	818.0	817.5	817.0	816.5	816.3	816.1	815.9	815.8	815.6	816.7	817.8
175°	824.1	823.6	823.1	822.7	822.3	822.0	821.7	821.4	821.1	822.2	823.2
177.5°	826.7	826.3	825.9	825.5	825.3	825.0	824.7	824.5	824.3	825.0	825.7
180°	825.9	825.9	825.9	825.9	825.9	825.9	825.9	825.9	825.9	825.9	825.9



TEST NUMBER: P331259-940

CATALOG NUMBER: SA2XXDIP-C290D725U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	546.7	548.9	548.9	549.3	551.9	551.5	551.3
5°	581.8	585.2	585.6	589.2	591.7	590.8	588.6
7.5°	614.8	621.3	626.2	628.8	632.0	634.0	633.1
10°	641.1	650.4	656.1	660.0	664.6	668.1	666.8
12.5°	664.9	676.0	683.9	690.5	691.0	695.4	692.4
15°	702.1	713.8	715.1	719.9	723.8	723.4	723.5
17.5°	714.3	718.1	718.9	719.0	719.1	717.6	714.5
20°	710.0	708.6	705.2	702.5	697.9	697.2	693.2
22.5°	689.2	684.7	676.1	670.4	663.2	661.3	660.1
25°	648.5	638.5	624.7	611.5	607.9	600.8	602.8
27.5°	592.4	576.9	562.0	551.3	541.6	531.0	534.0
30°	553.0	535.6	514.5	498.3	487.9	477.9	476.0
32.5°	506.0	480.5	457.0	442.7	426.9	420.4	413.5
35°	425.0	400.0	376.7	356.7	345.2	336.3	328.1
37.5°	352.1	323.4	304.6	288.4	280.0	274.9	276.3
40°	306.9	281.8	268.0	255.7	247.9	244.3	245.1
42.5°	270.3	251.5	240.1	231.7	226.2	224.2	223.7
45°	228.7	218.2	208.8	204.0	201.3	199.1	197.7
47.5°	200.4	191.7	186.5	183.6	181.3	179.1	179.0
50°	183.3	177.6	174.0	170.9	169.2	167.6	169.0
52.5°	170.3	165.1	161.5	158.8	158.1	156.7	156.6
55°	151.1	147.0	144.5	142.0	140.8	140.0	138.9
57.5°	133.6	129.7	127.3	125.8	123.5	122.7	122.3
60°	121.1	118.1	115.7	113.6	112.6	111.0	111.0
62.5°	109.6	106.6	104.3	102.8	101.1	100.5	100.7
65°	93.0	90.5	88.3	86.7	86.3	85.1	85.5
67.5°	77.7	76.1	73.7	72.8	72.1	71.4	70.9
70°	67.4	65.8	64.6	63.4	62.8	62.8	62.8
72.5°	58.9	56.9	56.2	54.7	55.0	54.4	53.7
75°	45.6	44.3	43.8	43.2	42.2	42.2	42.2
77.5°	33.5	33.2	32.5	31.8	31.6	31.4	31.5
80°	25.9	25.7	25.3	25.3	24.9	24.7	24.3
82.5°	20.0	19.4	19.2	19.0	18.9	18.9	18.8
85°	11.3	11.0	11.0	11.1	10.7	10.7	11.0
87.5°	9.1	9.0	8.8	8.8	9.1	8.9	8.9
90°	23.5	23.2	23.1	23.3	23.4	23.5	23.7
92.5°	22.4	22.4	22.5	22.5	22.6	22.6	22.6
95°	44.6	44.6	44.5	44.1	43.9	43.5	43.2
97.5°	75.0	75.0	75.0	75.0	74.9	74.9	74.8
100°	96.2	96.2	96.1	95.9	95.8	95.7	95.5
102.5°	119.4	119.6	119.5	119.4	119.2	119.0	118.9
105°	154.3	154.6	154.7	154.7	154.7	154.7	154.7
107.5°	191.5	191.6	191.4	190.6	189.9	189.2	188.5
110°	216.8	216.8	216.5	216.1	215.6	215.2	214.6



TEST NUMBER: P331259-940

CATALOG NUMBER: SA2XXDIP-C290D725U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	241.8	241.5	241.1	240.8	240.4	240.1	239.8
115°	281.2	281.0	280.6	280.2	279.7	279.3	278.8
117.5°	318.7	318.3	317.9	317.4	316.9	316.5	316.0
120°	344.3	344.3	344.1	343.6	343.1	342.7	342.2
122.5°	370.0	369.6	369.3	368.9	368.5	368.2	367.9
125°	408.4	408.0	407.7	407.5	407.3	407.2	407.1
127.5°	445.8	445.2	444.7	444.3	443.7	443.3	442.7
130°	471.6	471.4	470.8	470.2	469.7	469.0	468.4
132.5°	496.1	495.5	494.9	494.4	493.9	493.4	492.9
135°	533.4	533.2	533.0	532.5	532.1	531.5	531.1
137.5°	568.6	568.6	568.2	567.6	566.9	566.3	565.7
140°	592.5	592.5	592.1	591.6	590.9	590.3	589.7
142.5°	614.0	614.1	613.9	613.2	612.6	612.1	611.4
145°	646.6	646.8	646.5	645.9	645.2	644.6	644.0
147.5°	675.3	675.6	675.6	674.9	674.3	673.8	673.2
150°	693.5	694.0	694.0	693.5	693.0	692.6	692.1
152.5°	711.8	712.3	712.3	711.8	711.1	710.5	710.0
155°	734.9	735.7	735.8	735.3	734.9	734.4	734.0
157.5°	756.3	757.4	757.5	756.8	756.1	755.3	754.6
160°	768.8	769.7	769.9	769.3	768.7	768.0	767.4
162.5°	780.3	781.4	781.5	780.8	780.1	779.3	778.6
165°	795.0	796.1	796.3	795.5	794.7	794.0	793.2
167.5°	807.2	808.2	808.4	807.6	806.8	806.0	805.2
170°	813.9	814.9	815.0	814.1	813.2	812.3	811.3
172.5°	818.9	819.9	820.0	819.1	818.1	817.3	816.4
175°	824.3	825.4	825.5	824.6	823.6	822.7	821.8
177.5°	826.5	827.2	827.2	826.5	825.7	825.0	824.3
180°	825.9	825.9	825.9	825.9	825.9	825.9	825.9

(END OF REPORT)