

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331260-940

Luminaire Tested: **SA2XXDIP-C290D725U940-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331260-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C290D725U940-4F0-1E-UDD-A4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 725 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3688.4 lumens
Efficiency: N/A
Efficacy: 118.2 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331260-940
CATALOG NUMBER: SA2XXDIP-C290D725U940-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331260-940

CATALOG NUMBER: SA2XXDIP-C290D725U940-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39	32				
1	94	90	86	83	84	81	78	75	64	62	60	49	48	47	35	34	34	27				
2	86	79	73	68	77	71	66	62	57	53	50	43	41	39	31	30	29	23				
3	78	69	63	57	70	63	57	52	50	46	43	39	36	34	28	26	25	20				
4	72	62	54	48	64	56	49	44	45	40	37	35	32	29	25	23	22	17				
5	66	55	47	41	59	50	43	38	40	35	32	31	28	25	23	21	19	15				
6	61	49	42	36	55	45	38	33	36	31	28	28	25	22	21	19	17	14				
7	56	44	37	32	50	40	34	29	33	28	24	26	22	20	19	17	15	12				
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	18	15	14	11				
9	48	37	30	25	44	34	27	23	27	23	19	22	18	16	16	14	12	10				
10	45	34	27	22	41	31	25	21	25	21	17	20	17	14	15	13	11	9				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8510	8510	8510	8510
5°	9540	8566	7590	8566
10°	10932	8496	6568	8496
15°	12094	8339	5804	8339
20°	11911	8172	5290	8172
25°	10739	7949	4965	7949
30°	8874	7594	4728	7594
35°	6467	7222	4559	7222
40°	5166	6785	4466	6785
45°	4514	6277	4338	6277
50°	4245	5785	4253	5785
55°	3910	5286	4138	5286
60°	3584	4753	3965	4753
65°	3266	4279	3790	4279
70°	2965	3814	3541	3814
75°	2633	3300	3132	3300
80°	2259	2724	2520	2724
85°	2038	2038	1501	2038



TEST NUMBER: P331260-940

CATALOG NUMBER: SA2XXDIP-C290D725U940-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.2	1.4
10°-20°	145.9	4.0
20°-30°	211.8	5.7
30°-40°	223.5	6.1
40°-50°	197.9	5.4
50°-60°	157.9	4.3
60°-70°	107.3	2.9
70°-80°	55.0	1.5
80°-90°	16.5	0.4
90°-100°	144.9	3.9
100°-110°	491.8	13.3
110°-120°	522.5	14.2
120°-130°	430.1	11.7
130°-140°	345.4	9.4
140°-150°	261.0	7.1
150°-160°	183.4	5.0
160°-170°	108.0	2.9
170°-180°	35.1	1.0
0°-30°	407.9	11.1
0°-40°	631.4	17.1
0°-60°	987.2	26.8
0°-90°	1166.1	31.6
90°-120°	1159.2	31.4
90°-150°	2195.7	59.5
90°-180°	2522.0	68.4
0°-180°	3688.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	527	527	527	527	527	
5°	589	528	468	528	589	59
15°	724	499	347	499	724	200
25°	603	446	279	446	603	272
35°	328	366	231	366	328	213
45°	198	275	190	275	198	155
55°	139	188	147	188	139	125
65°	86	112	99	112	86	85
75°	42	53	50	53	42	45
85°	11	11	8	11	11	13
90°	23	1	23	1	23	13
95°	80	24	80	24	80	103
105°	786	85	786	85	786	760
115°	1034	150	1034	150	1034	1012
125°	839	209	839	209	839	758
135°	695	245	695	245	695	540
145°	555	280	555	280	555	352
155°	466	318	466	318	466	218
165°	409	347	409	347	409	117
175°	369	362	369	362	369	36
180°	362	362	362	362	362	



TEST NUMBER: P331260-940

CATALOG NUMBER: SA2XXDIP-C290D725U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	551.3	551.5	551.9	549.3	548.9	548.9	546.7	544.7	542.4	539.4	539.8
5°	588.6	590.8	591.7	589.2	585.6	585.2	581.8	576.1	570.8	566.6	563.6
7.5°	633.1	634.0	632.0	628.8	626.2	621.3	614.8	608.6	599.8	591.7	585.8
10°	666.8	668.1	664.6	660.0	656.1	650.4	641.1	631.6	620.1	608.9	600.0
12.5°	692.4	695.4	691.0	690.5	683.9	676.0	664.9	660.1	643.9	628.4	618.8
15°	723.5	723.4	723.8	719.9	715.1	713.8	702.1	689.3	666.5	657.3	641.5
17.5°	714.5	717.6	719.1	719.0	718.9	718.1	714.3	706.3	694.8	680.0	661.8
20°	693.2	697.2	697.9	702.5	705.2	708.6	710.0	707.8	700.7	688.3	672.5
22.5°	660.1	661.3	663.2	670.4	676.1	684.7	689.2	696.8	694.0	688.0	674.8
25°	602.8	600.8	607.9	611.5	624.7	638.5	648.5	659.3	669.1	674.9	671.1
27.5°	534.0	531.0	541.6	551.3	562.0	576.9	592.4	610.6	625.8	644.9	651.4
30°	476.0	477.9	487.9	498.3	514.5	535.6	553.0	573.0	594.8	616.0	630.8
32.5°	413.5	420.4	426.9	442.7	457.0	480.5	506.0	531.1	558.1	582.3	605.2
35°	328.1	336.3	345.2	356.7	376.7	400.0	425.0	458.8	495.7	528.7	555.8
37.5°	276.3	274.9	280.0	288.4	304.6	323.4	352.1	385.5	428.9	467.7	506.0
40°	245.1	244.3	247.9	255.7	268.0	281.8	306.9	336.3	376.6	424.0	469.6
42.5°	223.7	224.2	226.2	231.7	240.1	251.5	270.3	295.2	332.2	376.8	425.8
45°	197.7	199.1	201.3	204.0	208.8	218.2	228.7	246.6	275.7	313.0	361.1
47.5°	179.0	179.1	181.3	183.6	186.5	191.7	200.4	211.5	232.1	262.4	303.9
50°	169.0	167.6	169.2	170.9	174.0	177.6	183.3	193.9	207.6	232.1	266.8
52.5°	156.6	156.7	158.1	158.8	161.5	165.1	170.3	177.6	190.1	209.3	237.7
55°	138.9	140.0	140.8	142.0	144.5	147.0	151.1	156.0	165.7	180.0	201.2
57.5°	122.3	122.7	123.5	125.8	127.3	129.7	133.6	138.0	144.4	155.0	170.9
60°	111.0	111.0	112.6	113.6	115.7	118.1	121.1	125.4	131.1	139.7	152.6
62.5°	100.7	100.5	101.1	102.8	104.3	106.6	109.6	113.2	118.6	126.4	136.8
65°	85.5	85.1	86.3	86.7	88.3	90.5	93.0	96.8	101.1	106.7	116.1
67.5°	70.9	71.4	72.1	72.8	73.7	76.1	77.7	80.3	84.0	88.7	95.0
70°	62.8	62.8	62.8	63.4	64.6	65.8	67.4	69.6	73.1	77.1	82.8
72.5°	53.7	54.4	55.0	54.7	56.2	56.9	58.9	60.1	63.4	66.0	71.0
75°	42.2	42.2	42.2	43.2	43.8	44.3	45.6	46.8	48.4	51.6	54.3
77.5°	31.5	31.4	31.6	31.8	32.5	33.2	33.5	34.6	36.1	37.6	39.9
80°	24.3	24.7	24.9	25.3	25.3	25.7	25.9	27.4	28.4	29.3	30.8
82.5°	18.8	18.9	18.9	19.0	19.2	19.4	20.0	20.4	20.8	21.6	22.6
85°	11.0	10.7	10.7	11.1	11.0	11.0	11.3	11.8	11.8	11.9	12.6
87.5°	8.8	8.8	9.0	8.8	8.8	8.8	8.6	8.6	9.0	9.3	9.3
90°	23.0	23.0	23.0	23.0	23.0	22.3	21.0	22.3	23.0	23.7	23.0
92.5°	38.6	39.8	39.1	41.4	42.0	46.3	52.2	60.8	76.5	90.6	89.3
95°	79.5	78.7	80.9	86.4	95.5	110.8	140.1	182.6	239.1	273.2	241.9
97.5°	156.4	162.3	172.5	189.6	222.9	273.2	348.7	426.1	489.4	466.5	351.3
100°	249.5	262.1	282.3	312.3	370.1	454.5	550.0	636.4	651.0	550.6	379.2
102.5°	439.2	456.1	481.3	532.5	595.4	684.7	754.7	774.2	711.2	553.5	368.6
105°	785.6	795.3	825.3	868.5	911.8	934.8	925.7	846.9	702.0	516.5	347.9
107.5°	1003.4	1016.5	1022.4	1024.8	1019.4	985.6	913.1	794.5	640.7	476.9	337.5
110°	1069.3	1070.0	1063.7	1050.4	1020.5	963.3	874.1	749.3	602.3	458.0	335.3



TEST NUMBER: P331260-940

CATALOG NUMBER: SA2XXDIP-C290D725U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1068.2	1064.4	1052.6	1030.4	988.7	923.2	827.8	708.1	575.5	445.7	335.8
115°	1033.8	1027.4	1009.3	977.2	927.7	856.0	764.6	657.3	542.3	432.2	338.8
117.5°	972.2	967.0	947.9	914.0	863.5	796.2	713.4	619.1	521.4	425.6	343.8
120°	932.6	925.7	905.4	872.7	823.9	760.5	686.6	600.1	510.2	421.7	347.1
122.5°	891.4	885.6	867.5	835.4	791.6	734.2	664.3	585.1	500.8	419.5	351.1
125°	838.6	832.9	815.6	789.1	748.6	696.3	635.0	563.2	487.2	415.4	356.9
127.5°	792.3	787.8	772.8	748.0	712.7	664.4	606.5	541.6	474.7	413.0	362.9
130°	766.1	760.5	746.5	722.8	688.7	642.7	587.6	527.6	466.4	412.0	367.4
132.5°	738.7	733.7	720.9	697.2	663.6	620.4	569.8	514.2	459.7	411.4	371.8
135°	695.0	692.1	679.7	656.7	626.6	587.6	541.6	495.6	450.3	410.5	377.1
137.5°	652.0	647.8	636.9	617.1	589.7	555.7	519.2	480.7	443.7	410.5	381.8
140°	622.5	618.3	607.8	589.7	567.4	536.7	504.7	471.2	439.9	409.8	384.1
142.5°	592.9	592.1	582.7	566.3	545.1	519.4	491.9	463.4	436.0	409.8	385.8
145°	554.8	552.8	545.8	534.0	517.2	497.0	475.4	452.4	430.8	408.5	387.5
147.5°	522.9	521.7	516.9	507.5	493.7	478.8	462.0	443.9	425.5	406.0	388.2
150°	504.0	503.3	499.1	490.7	480.3	467.7	453.1	437.7	421.0	404.3	387.5
152.5°	487.8	487.7	484.6	477.3	469.1	458.3	445.9	431.6	417.1	401.5	386.5
155°	466.4	467.7	464.9	460.0	452.4	444.7	434.3	423.1	409.8	396.6	384.8
157.5°	448.1	448.1	446.8	442.7	437.3	431.3	422.6	413.2	403.1	391.6	381.6
160°	436.3	436.3	435.7	432.2	427.3	422.4	414.7	407.1	398.1	388.3	379.9
162.5°	425.2	425.8	425.1	422.7	417.9	414.0	407.5	400.9	393.5	385.5	378.3
165°	409.2	409.8	409.8	407.1	404.3	401.5	396.6	391.7	386.2	379.9	375.1
167.5°	394.4	395.2	395.4	393.9	392.6	390.0	386.7	383.0	378.9	375.1	371.8
170°	385.5	386.8	387.5	385.5	384.8	383.3	380.6	378.5	375.1	372.2	370.1
172.5°	378.3	379.1	379.8	378.8	378.1	377.3	375.1	373.4	371.1	368.9	367.9
175°	368.7	370.1	370.9	370.1	370.1	369.4	368.7	368.0	366.0	365.2	364.5
177.5°	363.0	364.2	364.7	364.7	364.7	364.7	364.2	364.2	363.0	362.5	363.0
180°	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5



TEST NUMBER: P331260-940

CATALOG NUMBER: SA2XXDIP-C290D725U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	540.8	539.6	538.8	535.8	533.2	530.7	529.9	530.1	526.6	523.2	521.7
5°	562.0	557.9	554.0	548.6	542.1	534.9	531.4	528.5	521.4	513.7	509.3
7.5°	580.8	575.0	567.6	557.3	547.9	536.7	529.6	523.3	513.0	502.1	495.4
10°	592.3	584.4	574.9	562.3	550.8	537.2	527.7	518.2	506.0	493.0	484.9
12.5°	602.2	591.6	582.2	566.1	552.4	535.4	524.1	510.7	497.9	482.5	474.6
15°	625.7	606.1	588.3	570.0	553.2	529.5	516.9	498.9	482.1	463.1	454.0
17.5°	643.9	621.8	593.8	570.6	551.0	524.7	506.3	484.7	464.8	443.1	430.7
20°	654.2	628.9	598.8	571.2	547.8	517.7	497.7	475.6	452.4	427.8	414.5
22.5°	660.4	633.8	604.0	568.8	541.3	512.1	486.9	462.6	439.1	412.6	398.6
25°	662.4	638.1	606.5	566.8	533.2	500.2	469.8	446.2	417.7	393.0	372.6
27.5°	652.7	635.3	604.9	562.9	523.8	485.2	451.3	424.7	394.6	367.7	347.1
30°	640.9	630.8	601.2	559.1	516.3	474.8	437.6	407.3	377.4	350.3	329.1
32.5°	622.6	620.5	594.4	553.6	508.4	461.7	423.1	392.6	359.4	332.7	312.6
35°	586.7	596.4	580.0	541.3	493.5	443.0	401.3	366.4	332.0	306.5	287.7
37.5°	538.4	562.6	558.3	523.3	473.2	422.7	376.6	340.2	307.4	281.6	263.1
40°	505.2	536.0	540.5	509.4	459.1	407.0	358.1	321.9	289.9	266.4	247.7
42.5°	469.6	505.5	517.7	492.9	443.4	390.4	341.6	304.1	272.3	249.5	233.0
45°	409.8	457.4	479.5	465.3	417.5	363.2	313.0	274.9	246.1	224.6	211.9
47.5°	353.9	405.9	435.6	430.6	388.6	334.8	285.2	248.6	220.6	203.5	192.1
50°	314.4	367.8	403.7	405.4	367.8	314.6	264.7	230.3	204.6	188.6	179.2
52.5°	280.0	331.1	370.1	378.8	344.6	293.6	246.5	212.1	189.5	174.8	166.5
55°	235.1	278.3	321.6	337.5	310.1	261.5	217.9	187.8	166.5	156.4	149.1
57.5°	195.6	231.5	271.5	289.0	272.2	230.5	189.7	163.5	146.2	137.3	131.7
60°	174.6	203.0	238.6	259.5	244.9	207.9	172.2	147.2	133.0	125.2	119.9
62.5°	155.2	180.3	210.4	229.5	221.6	186.6	154.7	132.7	120.5	113.1	109.2
65°	128.0	147.8	171.2	188.8	183.5	157.0	130.8	112.0	102.3	96.4	93.4
67.5°	105.4	119.8	135.9	151.3	147.1	128.3	107.4	92.6	85.4	80.3	78.5
70°	91.1	102.1	116.5	128.9	125.4	110.0	93.4	80.8	74.5	70.3	68.5
72.5°	77.6	86.5	97.6	107.6	105.3	92.5	78.6	69.2	64.3	60.4	58.9
75°	58.6	65.5	72.1	78.8	78.2	68.3	60.2	52.9	49.0	46.0	45.4
77.5°	43.2	47.1	51.6	55.6	54.5	48.8	42.4	38.3	35.5	33.4	33.1
80°	33.0	35.2	38.5	41.3	39.9	37.5	32.4	29.3	27.4	25.3	24.5
82.5°	24.0	26.1	28.1	29.7	28.5	26.3	23.2	21.1	19.9	18.5	18.2
85°	12.6	13.7	14.6	15.0	14.6	13.2	11.8	11.0	9.9	9.3	9.1
87.5°	8.6	7.7	7.0	6.9	6.1	5.8	4.6	3.7	3.9	4.4	4.3
90°	18.8	13.9	10.4	8.4	7.0	5.6	2.8	0.7	2.8	5.6	7.0
92.5°	69.6	47.4	31.7	25.1	20.3	17.3	12.3	8.5	12.3	17.3	20.3
95°	161.0	100.4	68.3	51.5	40.4	34.2	27.2	24.4	27.2	34.2	40.4
97.5°	217.0	132.4	92.1	73.2	60.4	50.9	43.5	39.8	43.5	50.9	60.4
100°	228.6	143.6	106.6	87.1	73.2	62.1	55.7	53.7	55.7	62.1	73.2
102.5°	229.2	153.6	119.5	100.0	85.4	74.3	68.0	66.5	68.0	74.3	85.4
105°	232.8	170.8	138.0	118.5	103.2	92.7	87.8	85.1	87.8	92.7	103.2
107.5°	242.5	188.3	156.6	136.9	121.7	112.1	107.4	105.1	107.4	112.1	121.7
110°	250.2	200.0	169.4	149.2	134.6	125.5	121.3	118.5	121.3	125.5	134.6



TEST NUMBER: P331260-940

CATALOG NUMBER: SA2XXDIP-C290D725U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	258.6	211.2	181.6	160.9	146.8	138.3	133.6	130.7	133.6	138.3	146.8
115°	271.2	228.6	198.7	179.9	165.9	157.6	153.4	149.9	153.4	157.6	165.9
117.5°	284.5	244.7	217.0	197.4	184.0	176.6	172.5	169.7	172.5	176.6	184.0
120°	293.5	255.8	228.6	209.1	195.2	188.9	184.8	181.9	184.8	188.9	195.2
122.5°	301.3	266.4	240.9	220.8	206.9	200.0	195.9	193.7	195.9	200.0	206.9
125°	313.7	282.3	257.2	237.7	223.7	215.3	211.2	209.1	211.2	215.3	223.7
127.5°	325.2	297.1	272.7	252.6	239.2	230.1	224.2	221.4	224.2	230.1	239.2
130°	332.5	306.0	281.6	262.1	248.2	238.4	231.4	228.6	231.4	238.4	248.2
132.5°	339.7	313.8	290.5	271.0	256.5	246.2	238.7	235.3	238.7	246.2	256.5
135°	349.2	324.9	302.6	283.0	267.0	256.5	248.2	245.4	248.2	256.5	267.0
137.5°	356.5	333.8	311.7	293.6	277.7	266.5	258.2	254.9	258.2	266.5	277.7
140°	360.3	338.8	317.9	299.7	284.4	273.2	264.8	262.1	264.8	273.2	284.4
142.5°	363.7	342.7	322.4	305.3	290.5	279.4	271.6	269.3	271.6	279.4	290.5
145°	368.0	348.6	329.7	314.3	300.4	290.0	283.0	280.2	283.0	290.0	300.4
147.5°	370.4	353.3	335.6	321.9	310.3	300.7	294.0	291.9	294.0	300.7	310.3
150°	371.5	355.5	339.5	326.9	316.5	307.4	301.8	299.7	301.8	307.4	316.5
152.5°	372.1	357.8	343.4	331.9	322.0	314.1	308.5	307.6	308.5	314.1	322.0
155°	372.9	361.1	349.2	338.8	331.1	323.4	319.2	318.5	319.2	323.4	331.1
157.5°	372.9	363.5	353.4	344.6	338.5	331.8	328.4	327.8	328.4	331.8	338.5
160°	372.9	364.5	356.1	348.6	343.0	337.3	334.6	333.9	334.6	337.3	343.0
162.5°	372.4	365.2	357.8	351.9	346.9	342.4	339.6	340.0	339.6	342.4	346.9
165°	370.9	366.0	359.7	355.5	352.0	347.9	346.4	347.1	346.4	347.9	352.0
167.5°	369.9	365.8	361.2	358.6	356.1	353.4	352.1	353.0	352.1	353.4	356.1
170°	368.7	365.2	361.8	359.7	358.3	356.1	355.5	356.9	355.5	356.1	358.3
172.5°	367.0	364.7	362.3	360.8	360.0	357.8	358.3	359.1	358.3	357.8	360.0
175°	365.2	363.8	362.5	361.8	361.8	360.3	361.1	361.8	361.1	360.3	361.8
177.5°	364.2	363.0	362.5	362.5	362.5	361.3	361.9	363.0	361.9	361.3	362.5
180°	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5



TEST NUMBER: P331260-940

CATALOG NUMBER: SA2XXDIP-C290D725U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	520.1	519.2	515.8	514.0	511.0	508.3	506.5	507.3	507.9	507.7	507.1
5°	505.2	501.3	495.4	490.4	486.8	480.1	477.2	475.8	474.6	473.2	471.8
7.5°	487.4	481.3	473.0	465.7	459.0	450.6	445.9	443.1	440.1	436.9	434.1
10°	474.8	466.3	457.4	447.3	439.2	431.7	425.0	420.5	416.4	412.6	409.8
12.5°	461.5	451.7	440.7	426.9	417.9	407.2	406.2	398.3	392.0	389.6	386.3
15°	440.4	426.6	412.6	396.2	389.1	379.4	373.4	367.2	361.8	357.9	357.0
17.5°	416.3	398.5	384.6	372.8	361.2	351.2	345.6	340.8	336.3	331.2	330.5
20°	398.1	382.6	367.5	357.1	345.2	335.0	328.1	323.3	319.4	316.4	313.8
22.5°	380.7	363.8	349.9	338.7	326.9	318.7	313.3	308.5	305.3	302.0	299.5
25°	352.8	339.7	324.5	311.7	302.0	296.8	292.3	288.3	286.2	284.0	281.2
27.5°	328.5	313.9	299.7	289.8	281.2	276.6	273.4	270.6	268.8	267.4	265.8
30°	311.4	296.6	285.4	275.7	268.6	263.9	261.9	260.3	258.1	257.3	256.5
32.5°	294.8	281.5	272.0	263.5	256.8	253.7	251.9	250.4	248.7	247.9	246.2
35°	271.4	260.3	251.0	246.3	240.9	238.2	236.8	234.8	233.2	232.4	232.1
37.5°	249.4	239.8	233.6	227.7	225.3	223.7	221.8	220.4	219.9	219.8	219.5
40°	235.1	227.3	221.8	217.0	216.0	213.5	211.9	210.7	210.7	210.9	210.7
42.5°	222.2	215.1	210.3	206.1	204.9	203.5	201.8	201.8	202.1	202.8	202.1
45°	202.6	197.5	194.0	192.1	189.8	188.4	188.2	188.8	189.0	189.2	189.8
47.5°	184.5	181.1	178.0	175.8	174.8	174.6	174.3	175.4	176.4	176.7	177.6
50°	173.8	170.0	167.3	165.9	165.1	164.7	165.1	166.3	167.1	168.1	168.7
52.5°	161.8	159.1	157.3	156.1	155.9	156.1	156.1	157.6	158.8	159.3	159.5
55°	145.3	143.2	142.9	141.0	141.8	141.6	142.6	143.4	144.6	145.9	146.1
57.5°	128.7	127.1	126.0	126.2	126.4	127.3	128.1	129.6	130.8	132.2	132.2
60°	117.7	116.9	116.3	116.3	116.6	117.9	118.9	120.3	121.1	122.0	122.5
62.5°	107.6	106.8	106.2	106.6	107.6	108.3	109.5	110.3	111.1	111.9	112.2
65°	91.8	91.4	91.9	92.4	92.6	93.5	95.0	95.6	96.4	96.8	98.3
67.5°	77.1	77.2	77.1	77.7	78.9	79.1	80.4	81.9	82.0	82.8	83.7
70°	67.2	67.7	68.0	68.5	69.5	69.9	70.9	71.5	72.3	72.9	73.6
72.5°	58.1	58.2	58.7	58.6	59.5	60.3	61.2	61.8	62.6	63.4	63.9
75°	44.8	44.8	45.2	45.4	46.4	47.4	47.2	47.6	48.4	49.2	49.7
77.5°	32.7	32.3	32.7	32.9	33.3	34.1	34.2	34.8	35.8	35.5	35.9
80°	24.9	24.3	24.9	25.1	25.1	26.1	26.1	26.6	27.1	26.6	27.1
82.5°	17.7	17.5	17.9	18.0	18.3	18.4	18.6	18.7	19.4	19.1	19.4
85°	8.9	8.7	8.9	8.7	8.9	9.1	9.1	8.9	8.9	9.3	8.7
87.5°	4.5	4.7	5.3	6.2	6.9	6.9	6.5	6.4	6.2	6.1	6.2
90°	8.4	10.4	13.9	18.8	23.0	23.7	23.0	22.3	21.0	22.3	23.0
92.5°	25.1	31.7	47.4	69.6	89.3	90.6	76.5	60.8	52.2	46.3	42.0
95°	51.5	68.3	100.4	161.0	241.9	273.2	239.1	182.6	140.1	110.8	95.5
97.5°	73.2	92.1	132.4	217.0	351.3	466.5	489.4	426.1	348.7	273.2	222.9
100°	87.1	106.6	143.6	228.6	379.2	550.6	651.0	636.4	550.0	454.5	370.1
102.5°	100.0	119.5	153.6	229.2	368.6	553.5	711.2	774.2	754.7	684.7	595.4
105°	118.5	138.0	170.8	232.8	347.9	516.5	702.0	846.9	925.7	934.8	911.8
107.5°	136.9	156.6	188.3	242.5	337.5	476.9	640.7	794.5	913.1	985.6	1019.4
110°	149.2	169.4	200.0	250.2	335.3	458.0	602.3	749.3	874.1	963.3	1020.5



TEST NUMBER: P331260-940

CATALOG NUMBER: SA2XXDIP-C290D725U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	160.9	181.6	211.2	258.6	335.8	445.7	575.5	708.1	827.8	923.2	988.7
115°	179.9	198.7	228.6	271.2	338.8	432.2	542.3	657.3	764.6	856.0	927.7
117.5°	197.4	217.0	244.7	284.5	343.8	425.6	521.4	619.1	713.4	796.2	863.5
120°	209.1	228.6	255.8	293.5	347.1	421.7	510.2	600.1	686.6	760.5	823.9
122.5°	220.8	240.9	266.4	301.3	351.1	419.5	500.8	585.1	664.3	734.2	791.6
125°	237.7	257.2	282.3	313.7	356.9	415.4	487.2	563.2	635.0	696.3	748.6
127.5°	252.6	272.7	297.1	325.2	362.9	413.0	474.7	541.6	606.5	664.4	712.7
130°	262.1	281.6	306.0	332.5	367.4	412.0	466.4	527.6	587.6	642.7	688.7
132.5°	271.0	290.5	313.8	339.7	371.8	411.4	459.7	514.2	569.8	620.4	663.6
135°	283.0	302.6	324.9	349.2	377.1	410.5	450.3	495.6	541.6	587.6	626.6
137.5°	293.6	311.7	333.8	356.5	381.8	410.5	443.7	480.7	519.2	555.7	589.7
140°	299.7	317.9	338.8	360.3	384.1	409.8	439.9	471.2	504.7	536.7	567.4
142.5°	305.3	322.4	342.7	363.7	385.8	409.8	436.0	463.4	491.9	519.4	545.1
145°	314.3	329.7	348.6	368.0	387.5	408.5	430.8	452.4	475.4	497.0	517.2
147.5°	321.9	335.6	353.3	370.4	388.2	406.0	425.5	443.9	462.0	478.8	493.7
150°	326.9	339.5	355.5	371.5	387.5	404.3	421.0	437.7	453.1	467.7	480.3
152.5°	331.9	343.4	357.8	372.1	386.5	401.5	417.1	431.6	445.9	458.3	469.1
155°	338.8	349.2	361.1	372.9	384.8	396.6	409.8	423.1	434.3	444.7	452.4
157.5°	344.6	353.4	363.5	372.9	381.6	391.6	403.1	413.2	422.6	431.3	437.3
160°	348.6	356.1	364.5	372.9	379.9	388.3	398.1	407.1	414.7	422.4	427.3
162.5°	351.9	357.8	365.2	372.4	378.3	385.5	393.5	400.9	407.5	414.0	417.9
165°	355.5	359.7	366.0	370.9	375.1	379.9	386.2	391.7	396.6	401.5	404.3
167.5°	358.6	361.2	365.8	369.9	371.8	375.1	378.9	383.0	386.7	390.0	392.6
170°	359.7	361.8	365.2	368.7	370.1	372.2	375.1	378.5	380.6	383.3	384.8
172.5°	360.8	362.3	364.7	367.0	367.9	368.9	371.1	373.4	375.1	377.3	378.1
175°	361.8	362.5	363.8	365.2	364.5	365.2	366.0	368.0	368.7	369.4	370.1
177.5°	362.5	362.5	363.0	364.2	363.0	362.5	363.0	364.2	364.2	364.7	364.7
180°	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5



TEST NUMBER: P331260-940

CATALOG NUMBER: SA2XXDIP-C290D725U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	505.5	505.2	505.2	503.7	505.2	505.2	505.5	507.1	507.7	507.9	507.3
5°	469.0	468.3	467.3	468.3	467.3	468.3	469.0	471.8	473.2	474.6	475.8
7.5°	432.7	430.3	430.0	427.6	430.0	430.3	432.7	434.1	436.9	440.1	443.1
10°	406.4	404.7	404.5	400.6	404.5	404.7	406.4	409.8	412.6	416.4	420.5
12.5°	386.3	382.4	383.2	380.9	383.2	382.4	386.3	386.3	389.6	392.0	398.3
15°	351.4	351.4	350.6	347.2	350.6	351.4	351.4	357.0	357.9	361.8	367.2
17.5°	326.5	326.0	324.1	325.1	324.1	326.0	326.5	330.5	331.2	336.3	340.8
20°	311.6	310.3	307.9	307.9	307.9	310.3	311.6	313.8	316.4	319.4	323.3
22.5°	297.5	297.4	294.8	295.6	294.8	297.4	297.5	299.5	302.0	305.3	308.5
25°	281.0	279.4	278.1	278.7	278.1	279.4	281.0	281.2	284.0	286.2	288.3
27.5°	265.3	264.4	264.3	262.7	264.3	264.4	265.3	265.8	267.4	268.8	270.6
30°	256.3	254.2	254.6	253.6	254.6	254.2	256.3	256.5	257.3	258.1	260.3
32.5°	245.8	245.1	244.8	243.9	244.8	245.1	245.8	246.2	247.9	248.7	250.4
35°	231.8	231.9	231.0	231.3	231.0	231.9	231.8	232.1	232.4	233.2	234.8
37.5°	219.4	220.0	219.5	219.6	219.5	220.0	219.4	219.5	219.8	219.9	220.4
40°	211.2	211.2	211.2	211.9	211.2	211.2	211.2	210.7	210.9	210.7	210.7
42.5°	203.5	203.1	202.9	202.8	202.9	203.1	203.5	202.1	202.8	202.1	201.8
45°	190.2	190.8	191.0	190.0	191.0	190.8	190.2	189.8	189.2	189.0	188.8
47.5°	178.2	178.3	178.2	179.1	178.2	178.3	178.2	177.6	176.7	176.4	175.4
50°	169.8	169.3	169.8	169.3	169.8	169.3	169.8	168.7	168.1	167.1	166.3
52.5°	160.9	161.0	160.7	160.6	160.7	161.0	160.9	159.5	159.3	158.8	157.6
55°	146.9	147.2	147.0	147.0	147.0	147.2	146.9	146.1	145.9	144.6	143.4
57.5°	132.4	132.8	133.0	132.2	133.0	132.8	132.4	132.2	132.2	130.8	129.6
60°	122.3	123.3	123.1	122.8	123.1	123.3	122.3	122.5	122.0	121.1	120.3
62.5°	113.1	113.5	113.4	113.3	113.4	113.5	113.1	112.2	111.9	111.1	110.3
65°	98.9	99.2	98.6	99.2	98.6	99.2	98.9	98.3	96.8	96.4	95.6
67.5°	83.5	83.6	84.1	84.4	84.1	83.6	83.5	83.7	82.8	82.0	81.9
70°	73.9	73.7	74.4	75.0	74.4	73.7	73.9	73.6	72.9	72.3	71.5
72.5°	63.8	64.3	64.1	64.6	64.1	64.3	63.8	63.9	63.4	62.6	61.8
75°	49.2	49.8	49.7	50.2	49.7	49.8	49.2	49.7	49.2	48.4	47.6
77.5°	35.6	35.7	35.6	35.9	35.6	35.7	35.6	35.9	35.5	35.8	34.8
80°	27.1	26.8	26.3	27.1	26.3	26.8	27.1	27.1	26.6	27.1	26.6
82.5°	18.9	19.1	18.7	18.7	18.7	19.1	18.9	19.4	19.1	19.4	18.7
85°	8.7	8.5	8.1	8.1	8.1	8.5	8.7	8.7	9.3	8.9	8.9
87.5°	6.2	6.1	6.1	5.9	6.1	6.1	6.2	6.2	6.1	6.2	6.4
90°	23.0	23.0	23.0	23.0	23.0	23.0	23.0	23.0	22.3	21.0	22.3
92.5°	41.4	39.1	39.8	38.6	39.8	39.1	41.4	42.0	46.3	52.2	60.8
95°	86.4	80.9	78.7	79.5	78.7	80.9	86.4	95.5	110.8	140.1	182.6
97.5°	189.6	172.5	162.3	156.4	162.3	172.5	189.6	222.9	273.2	348.7	426.1
100°	312.3	282.3	262.1	249.5	262.1	282.3	312.3	370.1	454.5	550.0	636.4
102.5°	532.5	481.3	456.1	439.2	456.1	481.3	532.5	595.4	684.7	754.7	774.2
105°	868.5	825.3	795.3	785.6	795.3	825.3	868.5	911.8	934.8	925.7	846.9
107.5°	1024.8	1022.4	1016.5	1003.4	1016.5	1022.4	1024.8	1019.4	985.6	913.1	794.5
110°	1050.4	1063.7	1070.0	1069.3	1070.0	1063.7	1050.4	1020.5	963.3	874.1	749.3



TEST NUMBER: P331260-940

CATALOG NUMBER: SA2XXDIP-C290D725U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1030.4	1052.6	1064.4	1068.2	1064.4	1052.6	1030.4	988.7	923.2	827.8	708.1
115°	977.2	1009.3	1027.4	1033.8	1027.4	1009.3	977.2	927.7	856.0	764.6	657.3
117.5°	914.0	947.9	967.0	972.2	967.0	947.9	914.0	863.5	796.2	713.4	619.1
120°	872.7	905.4	925.7	932.6	925.7	905.4	872.7	823.9	760.5	686.6	600.1
122.5°	835.4	867.5	885.6	891.4	885.6	867.5	835.4	791.6	734.2	664.3	585.1
125°	789.1	815.6	832.9	838.6	832.9	815.6	789.1	748.6	696.3	635.0	563.2
127.5°	748.0	772.8	787.8	792.3	787.8	772.8	748.0	712.7	664.4	606.5	541.6
130°	722.8	746.5	760.5	766.1	760.5	746.5	722.8	688.7	642.7	587.6	527.6
132.5°	697.2	720.9	733.7	738.7	733.7	720.9	697.2	663.6	620.4	569.8	514.2
135°	656.7	679.7	692.1	695.0	692.1	679.7	656.7	626.6	587.6	541.6	495.6
137.5°	617.1	636.9	647.8	652.0	647.8	636.9	617.1	589.7	555.7	519.2	480.7
140°	589.7	607.8	618.3	622.5	618.3	607.8	589.7	567.4	536.7	504.7	471.2
142.5°	566.3	582.7	592.1	592.9	592.1	582.7	566.3	545.1	519.4	491.9	463.4
145°	534.0	545.8	552.8	554.8	552.8	545.8	534.0	517.2	497.0	475.4	452.4
147.5°	507.5	516.9	521.7	522.9	521.7	516.9	507.5	493.7	478.8	462.0	443.9
150°	490.7	499.1	503.3	504.0	503.3	499.1	490.7	480.3	467.7	453.1	437.7
152.5°	477.3	484.6	487.7	487.8	487.7	484.6	477.3	469.1	458.3	445.9	431.6
155°	460.0	464.9	467.7	466.4	467.7	464.9	460.0	452.4	444.7	434.3	423.1
157.5°	442.7	446.8	448.1	448.1	448.1	446.8	442.7	437.3	431.3	422.6	413.2
160°	432.2	435.7	436.3	436.3	436.3	435.7	432.2	427.3	422.4	414.7	407.1
162.5°	422.7	425.1	425.8	425.2	425.8	425.1	422.7	417.9	414.0	407.5	400.9
165°	407.1	409.8	409.8	409.2	409.8	409.8	407.1	404.3	401.5	396.6	391.7
167.5°	393.9	395.4	395.2	394.4	395.2	395.4	393.9	392.6	390.0	386.7	383.0
170°	385.5	387.5	386.8	385.5	386.8	387.5	385.5	384.8	383.3	380.6	378.5
172.5°	378.8	379.8	379.1	378.3	379.1	379.8	378.8	378.1	377.3	375.1	373.4
175°	370.1	370.9	370.1	368.7	370.1	370.9	370.1	370.1	369.4	368.7	368.0
177.5°	364.7	364.7	364.2	363.0	364.2	364.7	364.7	364.7	364.7	364.2	364.2
180°	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5



TEST NUMBER: P331260-940
 CATALOG NUMBER: SA2XXDIP-C290D725U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	506.5	508.3	511.0	514.0	515.8	519.2	520.1	521.7	523.2	526.6	530.1
5°	477.2	480.1	486.8	490.4	495.4	501.3	505.2	509.3	513.7	521.4	528.5
7.5°	445.9	450.6	459.0	465.7	473.0	481.3	487.4	495.4	502.1	513.0	523.3
10°	425.0	431.7	439.2	447.3	457.4	466.3	474.8	484.9	493.0	506.0	518.2
12.5°	406.2	407.2	417.9	426.9	440.7	451.7	461.5	474.6	482.5	497.9	510.7
15°	373.4	379.4	389.1	396.2	412.6	426.6	440.4	454.0	463.1	482.1	498.9
17.5°	345.6	351.2	361.2	372.8	384.6	398.5	416.3	430.7	443.1	464.8	484.7
20°	328.1	335.0	345.2	357.1	367.5	382.6	398.1	414.5	427.8	452.4	475.6
22.5°	313.3	318.7	326.9	338.7	349.9	363.8	380.7	398.6	412.6	439.1	462.6
25°	292.3	296.8	302.0	311.7	324.5	339.7	352.8	372.6	393.0	417.7	446.2
27.5°	273.4	276.6	281.2	289.8	299.7	313.9	328.5	347.1	367.7	394.6	424.7
30°	261.9	263.9	268.6	275.7	285.4	296.6	311.4	329.1	350.3	377.4	407.3
32.5°	251.9	253.7	256.8	263.5	272.0	281.5	294.8	312.6	332.7	359.4	392.6
35°	236.8	238.2	240.9	246.3	251.0	260.3	271.4	287.7	306.5	332.0	366.4
37.5°	221.8	223.7	225.3	227.7	233.6	239.8	249.4	263.1	281.6	307.4	340.2
40°	211.9	213.5	216.0	217.0	221.8	227.3	235.1	247.7	266.4	289.9	321.9
42.5°	201.8	203.5	204.9	206.1	210.3	215.1	222.2	233.0	249.5	272.3	304.1
45°	188.2	188.4	189.8	192.1	194.0	197.5	202.6	211.9	224.6	246.1	274.9
47.5°	174.3	174.6	174.8	175.8	178.0	181.1	184.5	192.1	203.5	220.6	248.6
50°	165.1	164.7	165.1	165.9	167.3	170.0	173.8	179.2	188.6	204.6	230.3
52.5°	156.1	156.1	155.9	156.1	157.3	159.1	161.8	166.5	174.8	189.5	212.1
55°	142.6	141.6	141.8	141.0	142.9	143.2	145.3	149.1	156.4	166.5	187.8
57.5°	128.1	127.3	126.4	126.2	126.0	127.1	128.7	131.7	137.3	146.2	163.5
60°	118.9	117.9	116.6	116.3	116.3	116.9	117.7	119.9	125.2	133.0	147.2
62.5°	109.5	108.3	107.6	106.6	106.2	106.8	107.6	109.2	113.1	120.5	132.7
65°	95.0	93.5	92.6	92.4	91.9	91.4	91.8	93.4	96.4	102.3	112.0
67.5°	80.4	79.1	78.9	77.7	77.1	77.2	77.1	78.5	80.3	85.4	92.6
70°	70.9	69.9	69.5	68.5	68.0	67.7	67.2	68.5	70.3	74.5	80.8
72.5°	61.2	60.3	59.5	58.6	58.7	58.2	58.1	58.9	60.4	64.3	69.2
75°	47.2	47.4	46.4	45.4	45.2	44.8	44.8	45.4	46.0	49.0	52.9
77.5°	34.2	34.1	33.3	32.9	32.7	32.3	32.7	33.1	33.4	35.5	38.3
80°	26.1	26.1	25.1	25.1	24.9	24.3	24.9	24.5	25.3	27.4	29.3
82.5°	18.6	18.4	18.3	18.0	17.9	17.5	17.7	18.2	18.5	19.9	21.1
85°	9.1	9.1	8.9	8.7	8.9	8.7	8.9	9.1	9.3	9.9	11.0
87.5°	6.5	6.9	6.9	6.2	5.3	4.7	4.5	4.3	4.4	3.9	3.7
90°	23.0	23.7	23.0	18.8	13.9	10.4	8.4	7.0	5.6	2.8	0.7
92.5°	76.5	90.6	89.3	69.6	47.4	31.7	25.1	20.3	17.3	12.3	8.5
95°	239.1	273.2	241.9	161.0	100.4	68.3	51.5	40.4	34.2	27.2	24.4
97.5°	489.4	466.5	351.3	217.0	132.4	92.1	73.2	60.4	50.9	43.5	39.8
100°	651.0	550.6	379.2	228.6	143.6	106.6	87.1	73.2	62.1	55.7	53.7
102.5°	711.2	553.5	368.6	229.2	153.6	119.5	100.0	85.4	74.3	68.0	66.5
105°	702.0	516.5	347.9	232.8	170.8	138.0	118.5	103.2	92.7	87.8	85.1
107.5°	640.7	476.9	337.5	242.5	188.3	156.6	136.9	121.7	112.1	107.4	105.1
110°	602.3	458.0	335.3	250.2	200.0	169.4	149.2	134.6	125.5	121.3	118.5



TEST NUMBER: P331260-940

CATALOG NUMBER: SA2XXDIP-C290D725U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	575.5	445.7	335.8	258.6	211.2	181.6	160.9	146.8	138.3	133.6	130.7
115°	542.3	432.2	338.8	271.2	228.6	198.7	179.9	165.9	157.6	153.4	149.9
117.5°	521.4	425.6	343.8	284.5	244.7	217.0	197.4	184.0	176.6	172.5	169.7
120°	510.2	421.7	347.1	293.5	255.8	228.6	209.1	195.2	188.9	184.8	181.9
122.5°	500.8	419.5	351.1	301.3	266.4	240.9	220.8	206.9	200.0	195.9	193.7
125°	487.2	415.4	356.9	313.7	282.3	257.2	237.7	223.7	215.3	211.2	209.1
127.5°	474.7	413.0	362.9	325.2	297.1	272.7	252.6	239.2	230.1	224.2	221.4
130°	466.4	412.0	367.4	332.5	306.0	281.6	262.1	248.2	238.4	231.4	228.6
132.5°	459.7	411.4	371.8	339.7	313.8	290.5	271.0	256.5	246.2	238.7	235.3
135°	450.3	410.5	377.1	349.2	324.9	302.6	283.0	267.0	256.5	248.2	245.4
137.5°	443.7	410.5	381.8	356.5	333.8	311.7	293.6	277.7	266.5	258.2	254.9
140°	439.9	409.8	384.1	360.3	338.8	317.9	299.7	284.4	273.2	264.8	262.1
142.5°	436.0	409.8	385.8	363.7	342.7	322.4	305.3	290.5	279.4	271.6	269.3
145°	430.8	408.5	387.5	368.0	348.6	329.7	314.3	300.4	290.0	283.0	280.2
147.5°	425.5	406.0	388.2	370.4	353.3	335.6	321.9	310.3	300.7	294.0	291.9
150°	421.0	404.3	387.5	371.5	355.5	339.5	326.9	316.5	307.4	301.8	299.7
152.5°	417.1	401.5	386.5	372.1	357.8	343.4	331.9	322.0	314.1	308.5	307.6
155°	409.8	396.6	384.8	372.9	361.1	349.2	338.8	331.1	323.4	319.2	318.5
157.5°	403.1	391.6	381.6	372.9	363.5	353.4	344.6	338.5	331.8	328.4	327.8
160°	398.1	388.3	379.9	372.9	364.5	356.1	348.6	343.0	337.3	334.6	333.9
162.5°	393.5	385.5	378.3	372.4	365.2	357.8	351.9	346.9	342.4	339.6	340.0
165°	386.2	379.9	375.1	370.9	366.0	359.7	355.5	352.0	347.9	346.4	347.1
167.5°	378.9	375.1	371.8	369.9	365.8	361.2	358.6	356.1	353.4	352.1	353.0
170°	375.1	372.2	370.1	368.7	365.2	361.8	359.7	358.3	356.1	355.5	356.9
172.5°	371.1	368.9	367.9	367.0	364.7	362.3	360.8	360.0	357.8	358.3	359.1
175°	366.0	365.2	364.5	365.2	363.8	362.5	361.8	361.8	360.3	361.1	361.8
177.5°	363.0	362.5	363.0	364.2	363.0	362.5	362.5	362.5	361.3	361.9	363.0
180°	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5



TEST NUMBER: P331260-940

CATALOG NUMBER: SA2XXDIP-C290D725U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	529.9	530.7	533.2	535.8	538.8	539.6	540.8	539.8	539.4	542.4	544.7
5°	531.4	534.9	542.1	548.6	554.0	557.9	562.0	563.6	566.6	570.8	576.1
7.5°	529.6	536.7	547.9	557.3	567.6	575.0	580.8	585.8	591.7	599.8	608.6
10°	527.7	537.2	550.8	562.3	574.9	584.4	592.3	600.0	608.9	620.1	631.6
12.5°	524.1	535.4	552.4	566.1	582.2	591.6	602.2	618.8	628.4	643.9	660.1
15°	516.9	529.5	553.2	570.0	588.3	606.1	625.7	641.5	657.3	666.5	689.3
17.5°	506.3	524.7	551.0	570.6	593.8	621.8	643.9	661.8	680.0	694.8	706.3
20°	497.7	517.7	547.8	571.2	598.8	628.9	654.2	672.5	688.3	700.7	707.8
22.5°	486.9	512.1	541.3	568.8	604.0	633.8	660.4	674.8	688.0	694.0	696.8
25°	469.8	500.2	533.2	566.8	606.5	638.1	662.4	671.1	674.9	669.1	659.3
27.5°	451.3	485.2	523.8	562.9	604.9	635.3	652.7	651.4	644.9	625.8	610.6
30°	437.6	474.8	516.3	559.1	601.2	630.8	640.9	630.8	616.0	594.8	573.0
32.5°	423.1	461.7	508.4	553.6	594.4	620.5	622.6	605.2	582.3	558.1	531.1
35°	401.3	443.0	493.5	541.3	580.0	596.4	586.7	555.8	528.7	495.7	458.8
37.5°	376.6	422.7	473.2	523.3	558.3	562.6	538.4	506.0	467.7	428.9	385.5
40°	358.1	407.0	459.1	509.4	540.5	536.0	505.2	469.6	424.0	376.6	336.3
42.5°	341.6	390.4	443.4	492.9	517.7	505.5	469.6	425.8	376.8	332.2	295.2
45°	313.0	363.2	417.5	465.3	479.5	457.4	409.8	361.1	313.0	275.7	246.6
47.5°	285.2	334.8	388.6	430.6	435.6	405.9	353.9	303.9	262.4	232.1	211.5
50°	264.7	314.6	367.8	405.4	403.7	367.8	314.4	266.8	232.1	207.6	193.9
52.5°	246.5	293.6	344.6	378.8	370.1	331.1	280.0	237.7	209.3	190.1	177.6
55°	217.9	261.5	310.1	337.5	321.6	278.3	235.1	201.2	180.0	165.7	156.0
57.5°	189.7	230.5	272.2	289.0	271.5	231.5	195.6	170.9	155.0	144.4	138.0
60°	172.2	207.9	244.9	259.5	238.6	203.0	174.6	152.6	139.7	131.1	125.4
62.5°	154.7	186.6	221.6	229.5	210.4	180.3	155.2	136.8	126.4	118.6	113.2
65°	130.8	157.0	183.5	188.8	171.2	147.8	128.0	116.1	106.7	101.1	96.8
67.5°	107.4	128.3	147.1	151.3	135.9	119.8	105.4	95.0	88.7	84.0	80.3
70°	93.4	110.0	125.4	128.9	116.5	102.1	91.1	82.8	77.1	73.1	69.6
72.5°	78.6	92.5	105.3	107.6	97.6	86.5	77.6	71.0	66.0	63.4	60.1
75°	60.2	68.3	78.2	78.8	72.1	65.5	58.6	54.3	51.6	48.4	46.8
77.5°	42.4	48.8	54.5	55.6	51.6	47.1	43.2	39.9	37.6	36.1	34.6
80°	32.4	37.5	39.9	41.3	38.5	35.2	33.0	30.8	29.3	28.4	27.4
82.5°	23.2	26.3	28.5	29.7	28.1	26.1	24.0	22.6	21.6	20.8	20.4
85°	11.8	13.2	14.6	15.0	14.6	13.7	12.6	12.6	11.9	11.8	11.8
87.5°	4.6	5.8	6.1	6.9	7.0	7.7	8.6	9.3	9.3	9.0	8.6
90°	2.8	5.6	7.0	8.4	10.4	13.9	18.8	23.0	23.7	23.0	22.3
92.5°	12.3	17.3	20.3	25.1	31.7	47.4	69.6	89.3	90.6	76.5	60.8
95°	27.2	34.2	40.4	51.5	68.3	100.4	161.0	241.9	273.2	239.1	182.6
97.5°	43.5	50.9	60.4	73.2	92.1	132.4	217.0	351.3	466.5	489.4	426.1
100°	55.7	62.1	73.2	87.1	106.6	143.6	228.6	379.2	550.6	651.0	636.4
102.5°	68.0	74.3	85.4	100.0	119.5	153.6	229.2	368.6	553.5	711.2	774.2
105°	87.8	92.7	103.2	118.5	138.0	170.8	232.8	347.9	516.5	702.0	846.9
107.5°	107.4	112.1	121.7	136.9	156.6	188.3	242.5	337.5	476.9	640.7	794.5
110°	121.3	125.5	134.6	149.2	169.4	200.0	250.2	335.3	458.0	602.3	749.3



TEST NUMBER: P331260-940

CATALOG NUMBER: SA2XXDIP-C290D725U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	133.6	138.3	146.8	160.9	181.6	211.2	258.6	335.8	445.7	575.5	708.1
115°	153.4	157.6	165.9	179.9	198.7	228.6	271.2	338.8	432.2	542.3	657.3
117.5°	172.5	176.6	184.0	197.4	217.0	244.7	284.5	343.8	425.6	521.4	619.1
120°	184.8	188.9	195.2	209.1	228.6	255.8	293.5	347.1	421.7	510.2	600.1
122.5°	195.9	200.0	206.9	220.8	240.9	266.4	301.3	351.1	419.5	500.8	585.1
125°	211.2	215.3	223.7	237.7	257.2	282.3	313.7	356.9	415.4	487.2	563.2
127.5°	224.2	230.1	239.2	252.6	272.7	297.1	325.2	362.9	413.0	474.7	541.6
130°	231.4	238.4	248.2	262.1	281.6	306.0	332.5	367.4	412.0	466.4	527.6
132.5°	238.7	246.2	256.5	271.0	290.5	313.8	339.7	371.8	411.4	459.7	514.2
135°	248.2	256.5	267.0	283.0	302.6	324.9	349.2	377.1	410.5	450.3	495.6
137.5°	258.2	266.5	277.7	293.6	311.7	333.8	356.5	381.8	410.5	443.7	480.7
140°	264.8	273.2	284.4	299.7	317.9	338.8	360.3	384.1	409.8	439.9	471.2
142.5°	271.6	279.4	290.5	305.3	322.4	342.7	363.7	385.8	409.8	436.0	463.4
145°	283.0	290.0	300.4	314.3	329.7	348.6	368.0	387.5	408.5	430.8	452.4
147.5°	294.0	300.7	310.3	321.9	335.6	353.3	370.4	388.2	406.0	425.5	443.9
150°	301.8	307.4	316.5	326.9	339.5	355.5	371.5	387.5	404.3	421.0	437.7
152.5°	308.5	314.1	322.0	331.9	343.4	357.8	372.1	386.5	401.5	417.1	431.6
155°	319.2	323.4	331.1	338.8	349.2	361.1	372.9	384.8	396.6	409.8	423.1
157.5°	328.4	331.8	338.5	344.6	353.4	363.5	372.9	381.6	391.6	403.1	413.2
160°	334.6	337.3	343.0	348.6	356.1	364.5	372.9	379.9	388.3	398.1	407.1
162.5°	339.6	342.4	346.9	351.9	357.8	365.2	372.4	378.3	385.5	393.5	400.9
165°	346.4	347.9	352.0	355.5	359.7	366.0	370.9	375.1	379.9	386.2	391.7
167.5°	352.1	353.4	356.1	358.6	361.2	365.8	369.9	371.8	375.1	378.9	383.0
170°	355.5	356.1	358.3	359.7	361.8	365.2	368.7	370.1	372.2	375.1	378.5
172.5°	358.3	357.8	360.0	360.8	362.3	364.7	367.0	367.9	368.9	371.1	373.4
175°	361.1	360.3	361.8	361.8	362.5	363.8	365.2	364.5	365.2	366.0	368.0
177.5°	361.9	361.3	362.5	362.5	362.5	363.0	364.2	363.0	362.5	363.0	364.2
180°	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5



TEST NUMBER: P331260-940

CATALOG NUMBER: SA2XXDIP-C290D725U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	546.7	548.9	548.9	549.3	551.9	551.5	551.3
5°	581.8	585.2	585.6	589.2	591.7	590.8	588.6
7.5°	614.8	621.3	626.2	628.8	632.0	634.0	633.1
10°	641.1	650.4	656.1	660.0	664.6	668.1	666.8
12.5°	664.9	676.0	683.9	690.5	691.0	695.4	692.4
15°	702.1	713.8	715.1	719.9	723.8	723.4	723.5
17.5°	714.3	718.1	718.9	719.0	719.1	717.6	714.5
20°	710.0	708.6	705.2	702.5	697.9	697.2	693.2
22.5°	689.2	684.7	676.1	670.4	663.2	661.3	660.1
25°	648.5	638.5	624.7	611.5	607.9	600.8	602.8
27.5°	592.4	576.9	562.0	551.3	541.6	531.0	534.0
30°	553.0	535.6	514.5	498.3	487.9	477.9	476.0
32.5°	506.0	480.5	457.0	442.7	426.9	420.4	413.5
35°	425.0	400.0	376.7	356.7	345.2	336.3	328.1
37.5°	352.1	323.4	304.6	288.4	280.0	274.9	276.3
40°	306.9	281.8	268.0	255.7	247.9	244.3	245.1
42.5°	270.3	251.5	240.1	231.7	226.2	224.2	223.7
45°	228.7	218.2	208.8	204.0	201.3	199.1	197.7
47.5°	200.4	191.7	186.5	183.6	181.3	179.1	179.0
50°	183.3	177.6	174.0	170.9	169.2	167.6	169.0
52.5°	170.3	165.1	161.5	158.8	158.1	156.7	156.6
55°	151.1	147.0	144.5	142.0	140.8	140.0	138.9
57.5°	133.6	129.7	127.3	125.8	123.5	122.7	122.3
60°	121.1	118.1	115.7	113.6	112.6	111.0	111.0
62.5°	109.6	106.6	104.3	102.8	101.1	100.5	100.7
65°	93.0	90.5	88.3	86.7	86.3	85.1	85.5
67.5°	77.7	76.1	73.7	72.8	72.1	71.4	70.9
70°	67.4	65.8	64.6	63.4	62.8	62.8	62.8
72.5°	58.9	56.9	56.2	54.7	55.0	54.4	53.7
75°	45.6	44.3	43.8	43.2	42.2	42.2	42.2
77.5°	33.5	33.2	32.5	31.8	31.6	31.4	31.5
80°	25.9	25.7	25.3	25.3	24.9	24.7	24.3
82.5°	20.0	19.4	19.2	19.0	18.9	18.9	18.8
85°	11.3	11.0	11.0	11.1	10.7	10.7	11.0
87.5°	8.6	8.8	8.8	8.8	9.0	8.8	8.8
90°	21.0	22.3	23.0	23.0	23.0	23.0	23.0
92.5°	52.2	46.3	42.0	41.4	39.1	39.8	38.6
95°	140.1	110.8	95.5	86.4	80.9	78.7	79.5
97.5°	348.7	273.2	222.9	189.6	172.5	162.3	156.4
100°	550.0	454.5	370.1	312.3	282.3	262.1	249.5
102.5°	754.7	684.7	595.4	532.5	481.3	456.1	439.2
105°	925.7	934.8	911.8	868.5	825.3	795.3	785.6
107.5°	913.1	985.6	1019.4	1024.8	1022.4	1016.5	1003.4
110°	874.1	963.3	1020.5	1050.4	1063.7	1070.0	1069.3



TEST NUMBER: P331260-940

CATALOG NUMBER: SA2XXDIP-C290D725U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	827.8	923.2	988.7	1030.4	1052.6	1064.4	1068.2
115°	764.6	856.0	927.7	977.2	1009.3	1027.4	1033.8
117.5°	713.4	796.2	863.5	914.0	947.9	967.0	972.2
120°	686.6	760.5	823.9	872.7	905.4	925.7	932.6
122.5°	664.3	734.2	791.6	835.4	867.5	885.6	891.4
125°	635.0	696.3	748.6	789.1	815.6	832.9	838.6
127.5°	606.5	664.4	712.7	748.0	772.8	787.8	792.3
130°	587.6	642.7	688.7	722.8	746.5	760.5	766.1
132.5°	569.8	620.4	663.6	697.2	720.9	733.7	738.7
135°	541.6	587.6	626.6	656.7	679.7	692.1	695.0
137.5°	519.2	555.7	589.7	617.1	636.9	647.8	652.0
140°	504.7	536.7	567.4	589.7	607.8	618.3	622.5
142.5°	491.9	519.4	545.1	566.3	582.7	592.1	592.9
145°	475.4	497.0	517.2	534.0	545.8	552.8	554.8
147.5°	462.0	478.8	493.7	507.5	516.9	521.7	522.9
150°	453.1	467.7	480.3	490.7	499.1	503.3	504.0
152.5°	445.9	458.3	469.1	477.3	484.6	487.7	487.8
155°	434.3	444.7	452.4	460.0	464.9	467.7	466.4
157.5°	422.6	431.3	437.3	442.7	446.8	448.1	448.1
160°	414.7	422.4	427.3	432.2	435.7	436.3	436.3
162.5°	407.5	414.0	417.9	422.7	425.1	425.8	425.2
165°	396.6	401.5	404.3	407.1	409.8	409.8	409.2
167.5°	386.7	390.0	392.6	393.9	395.4	395.2	394.4
170°	380.6	383.3	384.8	385.5	387.5	386.8	385.5
172.5°	375.1	377.3	378.1	378.8	379.8	379.1	378.3
175°	368.7	369.4	370.1	370.1	370.9	370.1	368.7
177.5°	364.2	364.7	364.7	364.7	364.7	364.2	363.0
180°	362.5	362.5	362.5	362.5	362.5	362.5	362.5

(END OF REPORT)