

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331635-940

Luminaire Tested: **SA2XXRDIP-C290D925U940-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331635-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C290D925U940-4F0-1E-UDD-A4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 925 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4231.9 lumens
Efficiency: N/A
Efficacy: 113.5 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 37.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331635-940
CATALOG NUMBER: SA2XXRDIP-C290D925U940-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331635-940

CATALOG NUMBER: SA2XXRDIP-C290D925U940-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	32	32	32	24				24
1	92	88	85	81	82	79	76	73	61	59	57	44	43	42	29	28	28	21				21
2	84	77	72	67	75	69	64	60	54	50	48	39	37	36	26	25	24	18				18
3	77	68	62	56	68	61	55	51	48	44	41	35	33	30	23	22	21	16				16
4	71	61	53	48	63	54	48	43	42	38	35	31	29	26	21	20	18	14				14
5	65	54	47	41	58	49	42	37	38	34	30	28	25	23	19	18	16	12				12
6	60	49	41	36	53	44	37	32	34	30	26	26	23	20	18	16	14	11				11
7	55	44	36	31	49	39	33	29	31	27	23	23	20	18	16	14	13	10				10
8	51	40	33	28	46	36	30	25	28	24	21	21	18	16	15	13	12	9				9
9	48	36	29	24	42	33	27	22	26	22	19	20	17	15	14	12	11	8				8
10	44	33	26	22	40	30	24	20	24	20	17	18	15	13	13	11	10	8				8

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9411	9411	9411	9411
5°	10511	9470	8399	9470
10°	11663	9404	7279	9404
15°	12236	9267	5735	9267
20°	10608	9062	4962	9062
25°	6957	8783	4431	8783
30°	4683	8444	4010	8444
35°	3792	8016	3617	8016
40°	3372	7552	3347	7552
45°	3053	7005	2987	7005
50°	2778	6465	2768	6465
55°	2609	5866	2578	5866
60°	2186	5318	2160	5318
65°	1841	4829	2090	4829
70°	1699	4310	1969	4310
75°	1591	3755	1822	3755
80°	1469	3096	1618	3096
85°	1352	2445	1426	2445



TEST NUMBER: P331635-940

CATALOG NUMBER: SA2XXRDIP-C290D925U940-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.3	1.3
10°-20°	154.0	3.6
20°-30°	198.4	4.7
30°-40°	188.6	4.5
40°-50°	161.5	3.8
50°-60°	123.0	2.9
60°-70°	77.8	1.8
70°-80°	38.8	0.9
80°-90°	14.3	0.3
90°-100°	185.0	4.4
100°-110°	627.9	14.8
110°-120°	667.1	15.8
120°-130°	549.1	13.0
130°-140°	441.0	10.4
140°-150°	333.2	7.9
150°-160°	234.2	5.5
160°-170°	137.9	3.3
170°-180°	44.9	1.1
0°-30°	407.7	9.6
0°-40°	596.2	14.1
0°-60°	880.8	20.8
0°-90°	1011.6	23.9
90°-120°	1480.0	35.0
90°-150°	2803.4	66.2
90°-180°	3220.0	76.1
0°-180°	4231.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	583	583	583	583	583	
5°	648	584	518	584	648	64
15°	732	554	343	554	732	197
25°	390	493	249	493	390	185
35°	192	407	184	407	192	123
45°	134	307	131	307	134	103
55°	93	208	92	208	93	81
65°	48	126	55	126	48	49
75°	26	60	29	60	26	27
85°	7	13	8	13	7	9
90°	29	1	29	1	29	16
95°	102	31	102	31	102	132
105°	1003	109	1003	109	1003	970
115°	1320	191	1320	191	1320	1292
125°	1071	267	1071	267	1071	967
135°	887	313	887	313	887	689
145°	708	358	708	358	708	450
155°	595	407	595	407	595	278
165°	522	443	522	443	522	149
175°	471	462	471	462	471	46
180°	463	463	463	463	463	



TEST NUMBER: P331635-940

CATALOG NUMBER: SA2XXRDIP-C290D925U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9
2.5°	606.6	607.1	607.6	606.5	606.5	605.5	603.3	601.7	597.2	596.6	596.6
5°	648.5	648.2	649.0	646.3	642.7	641.9	638.0	632.9	627.7	621.9	620.6
7.5°	690.3	689.6	688.0	687.6	684.8	678.7	672.5	665.9	657.2	648.6	644.4
10°	711.4	718.1	714.0	706.9	708.3	698.8	693.8	685.0	677.7	664.9	662.2
12.5°	732.1	734.8	733.4	729.4	727.6	721.0	714.2	706.6	693.1	681.7	671.7
15°	732.0	735.8	736.9	735.7	736.6	736.3	732.6	726.4	714.6	702.0	691.1
17.5°	678.0	680.6	687.3	691.8	697.5	709.4	715.4	717.6	716.0	708.7	701.1
20°	617.4	613.0	631.6	641.1	649.2	669.4	686.9	693.6	704.3	704.1	702.0
22.5°	531.5	532.5	550.2	561.5	585.1	605.5	625.3	650.4	671.2	684.9	692.9
25°	390.5	398.2	415.8	431.2	457.5	495.3	529.5	569.2	606.6	636.2	664.4
27.5°	293.3	293.9	307.8	322.1	337.7	368.5	411.7	459.1	512.5	556.6	607.3
30°	251.2	249.9	255.8	264.6	277.9	301.8	334.2	380.8	434.1	500.5	559.6
32.5°	221.3	221.4	225.9	232.3	243.3	259.5	281.7	319.6	369.9	435.2	504.5
35°	192.4	192.3	195.5	200.1	204.7	215.1	230.3	250.1	284.8	345.7	416.6
37.5°	171.7	172.5	174.2	177.1	182.2	188.0	197.1	210.4	235.1	271.2	330.7
40°	160.0	160.4	162.6	165.1	168.1	172.5	180.0	190.8	208.8	237.6	281.2
42.5°	149.4	149.7	151.3	153.6	156.0	160.4	166.7	175.9	190.6	212.9	248.9
45°	133.7	133.7	135.1	136.1	138.8	142.8	147.8	155.6	165.7	182.3	206.2
47.5°	119.0	119.0	120.0	121.7	123.4	126.5	131.5	137.9	145.2	158.0	178.4
50°	110.6	110.8	111.4	112.8	113.9	116.6	120.6	126.0	133.7	143.7	160.6
52.5°	103.8	103.7	104.4	105.0	105.8	107.7	110.7	115.5	122.3	131.0	145.1
55°	92.7	91.9	93.2	94.2	94.8	95.6	97.2	100.2	106.1	113.4	123.9
57.5°	79.0	78.6	79.5	80.4	82.4	84.5	86.0	87.8	90.9	96.1	106.6
60°	67.7	67.7	69.5	70.1	72.3	75.2	78.0	79.6	82.7	86.1	93.8
62.5°	57.6	57.8	58.6	59.2	60.5	63.9	67.9	71.5	74.4	77.7	82.8
65°	48.2	48.6	48.6	49.0	49.8	50.6	52.3	55.1	60.2	64.8	68.7
67.5°	40.9	41.0	41.2	41.6	41.7	42.6	43.3	44.6	45.7	50.1	54.9
70°	36.0	36.6	36.5	36.8	37.1	37.5	38.3	38.9	40.8	41.7	44.6
72.5°	31.5	31.9	31.9	32.2	32.7	32.8	33.4	34.1	35.2	36.0	37.6
75°	25.5	25.3	25.5	25.9	26.1	26.3	26.3	27.1	27.7	28.5	29.6
77.5°	19.7	19.9	19.9	19.9	20.0	20.3	20.2	20.6	21.2	21.7	22.1
80°	15.8	16.0	15.8	16.0	16.2	16.4	16.2	16.4	17.0	17.4	17.4
82.5°	12.2	12.3	12.4	12.4	12.5	12.5	12.8	12.8	13.3	13.2	13.4
85°	7.3	7.1	7.1	7.1	7.3	7.5	7.3	7.3	7.5	7.5	7.5
87.5°	8.5	8.6	8.6	8.6	8.6	8.5	8.1	8.6	8.6	9.0	8.6
90°	29.3	29.3	29.3	29.3	29.3	28.4	26.7	28.4	29.3	30.2	29.3
92.5°	49.3	50.7	50.0	52.9	53.6	59.1	66.6	77.6	97.7	115.7	114.0
95°	101.5	100.6	103.3	110.4	121.9	141.5	178.9	233.2	305.2	348.8	308.8
97.5°	199.7	207.1	220.2	242.1	284.6	348.8	445.1	544.1	624.7	595.6	448.5
100°	318.6	334.7	360.4	398.7	472.6	580.2	702.1	812.5	831.3	703.0	484.1
102.5°	560.7	582.4	614.6	679.9	760.2	874.3	963.5	988.4	908.1	706.6	470.6
105°	1003.0	1015.4	1053.7	1108.8	1164.0	1193.5	1181.9	1081.3	896.2	659.4	444.1
107.5°	1281.2	1297.7	1305.4	1308.4	1301.5	1258.4	1165.8	1014.4	818.1	608.9	430.9
110°	1365.2	1366.1	1358.1	1341.1	1302.9	1229.9	1116.0	956.7	768.9	584.7	428.1



TEST NUMBER: P331635-940

CATALOG NUMBER: SA2XXRDIP-C290D925U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1363.8	1359.0	1343.8	1315.5	1262.3	1178.7	1056.9	904.0	734.8	569.0	428.7
115°	1319.8	1311.8	1288.6	1247.7	1184.5	1092.9	976.2	839.2	692.4	551.8	432.5
117.5°	1241.3	1234.6	1210.1	1166.9	1102.5	1016.5	910.8	790.4	665.7	543.4	438.9
120°	1190.8	1181.9	1156.0	1114.2	1052.0	970.9	876.6	766.2	651.5	538.4	443.2
122.5°	1138.1	1130.6	1107.6	1066.5	1010.7	937.5	848.1	747.0	639.4	535.6	448.2
125°	1070.6	1063.5	1041.3	1007.5	955.8	889.0	810.7	719.1	622.1	530.4	455.7
127.5°	1011.6	1005.8	986.6	954.9	909.9	848.3	774.5	691.5	606.1	527.4	463.3
130°	978.0	970.9	953.1	922.9	879.3	820.6	750.2	673.7	595.4	525.9	469.0
132.5°	943.2	936.7	920.4	890.1	847.2	792.0	727.5	656.6	586.8	525.2	474.7
135°	887.3	883.7	867.7	838.3	800.0	750.2	691.5	632.8	574.9	524.1	481.4
137.5°	832.5	827.2	813.1	787.8	752.9	709.4	662.8	613.7	566.5	524.0	487.5
140°	794.7	789.4	776.1	752.9	724.4	685.3	644.4	601.6	561.6	523.3	490.4
142.5°	757.0	755.9	744.0	723.0	696.0	663.2	627.9	591.7	556.6	523.3	492.5
145°	708.4	705.7	696.9	681.7	660.3	634.5	607.0	577.6	550.0	521.5	494.8
147.5°	667.6	666.0	660.0	647.9	630.3	611.4	589.9	566.7	543.2	518.4	495.5
150°	643.5	642.6	637.2	626.5	613.1	597.2	578.5	558.9	537.5	516.2	494.8
152.5°	622.8	622.6	618.7	609.4	599.0	585.1	569.2	551.1	532.5	512.6	493.4
155°	595.4	597.2	593.6	587.4	577.6	567.8	554.5	540.2	523.3	506.4	491.2
157.5°	572.0	572.0	570.4	565.3	558.4	550.7	539.5	527.5	514.6	500.0	487.1
160°	557.1	557.1	556.2	551.8	545.5	539.3	529.5	519.7	508.2	495.7	485.0
162.5°	542.9	543.6	542.7	539.7	533.4	528.6	520.2	511.9	502.5	492.1	482.9
165°	522.4	523.3	523.3	519.7	516.2	512.6	506.4	500.2	493.0	485.0	478.8
167.5°	503.5	504.6	504.8	502.8	501.2	498.0	493.7	488.9	483.8	478.8	474.7
170°	492.1	493.9	494.8	492.1	491.2	489.5	485.9	483.2	478.8	475.2	472.6
172.5°	482.9	483.9	484.8	483.6	482.7	481.6	478.8	476.8	473.9	471.0	469.8
175°	470.8	472.6	473.5	472.6	472.6	471.7	470.8	469.9	467.3	466.4	465.5
177.5°	463.5	464.9	465.7	465.7	465.7	465.7	464.9	464.9	463.5	462.8	463.5
180°	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8



TEST NUMBER: P331635-940

CATALOG NUMBER: SA2XXRDIP-C290D925U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9
2.5°	596.9	595.6	594.4	591.6	590.0	586.8	586.4	586.2	582.0	577.9	576.8
5°	617.4	614.1	609.3	603.6	597.7	591.7	587.6	584.3	576.2	568.6	564.1
7.5°	638.0	631.1	622.7	612.0	603.0	593.0	585.5	578.8	567.3	556.2	548.8
10°	653.4	642.1	631.0	616.2	604.6	593.3	582.7	573.6	560.7	546.1	535.7
12.5°	663.0	650.5	635.2	620.7	605.7	591.3	577.2	565.5	550.3	535.2	523.0
15°	675.9	662.5	643.9	623.2	604.0	585.1	569.0	554.4	534.6	516.5	501.5
17.5°	686.5	668.1	648.1	624.2	601.9	578.0	557.1	538.5	516.4	494.6	477.0
20°	689.9	671.6	648.5	624.6	598.3	570.2	547.7	527.4	503.7	480.0	459.8
22.5°	687.8	673.6	647.9	619.3	592.4	562.9	537.5	514.0	487.7	463.5	440.1
25°	673.5	668.6	644.4	613.1	582.4	548.1	518.7	493.0	463.1	437.1	411.6
27.5°	640.2	650.7	635.6	602.4	568.1	531.5	498.4	469.1	438.0	408.8	383.4
30°	608.1	632.1	625.7	594.9	556.6	520.6	483.5	452.9	419.7	389.7	364.6
32.5°	564.2	604.0	610.3	584.5	544.9	505.3	466.5	436.0	401.4	369.8	345.3
35°	494.2	553.8	581.1	564.7	525.0	482.2	442.2	406.7	371.8	340.7	316.4
37.5°	410.8	492.0	537.5	538.7	502.2	457.8	414.1	378.9	343.2	312.6	286.3
40°	356.7	444.6	504.0	517.1	486.3	438.4	394.1	358.3	323.5	293.5	263.3
42.5°	308.1	395.7	468.6	491.5	467.1	419.4	375.1	337.6	303.7	275.4	244.5
45°	249.1	325.7	406.1	447.0	433.5	389.3	342.5	306.8	275.1	250.6	221.0
47.5°	210.2	264.1	342.0	397.3	397.1	356.8	310.7	276.6	247.1	224.1	200.2
50°	188.0	235.0	300.8	363.6	368.8	335.0	291.2	257.4	229.9	205.8	186.5
52.5°	168.0	206.8	265.9	326.2	341.2	311.8	269.4	238.2	211.4	189.2	172.8
55°	142.0	172.0	217.0	273.2	296.0	275.3	237.6	208.4	186.7	168.1	153.9
57.5°	120.1	142.6	178.7	224.0	250.4	237.5	206.3	182.6	164.1	147.2	136.1
60°	106.4	124.8	155.3	193.2	222.4	213.3	186.7	164.7	148.9	134.3	123.8
62.5°	93.4	109.2	135.5	166.2	192.9	189.1	167.5	148.9	135.1	121.8	112.9
65°	75.2	86.7	107.2	131.3	152.8	154.5	138.9	126.4	114.0	103.5	95.6
67.5°	59.8	67.4	81.8	102.1	118.2	123.9	114.4	104.8	95.0	86.9	80.0
70°	50.5	56.5	67.1	83.5	98.3	104.3	98.8	91.3	82.8	76.2	70.3
72.5°	40.8	46.8	54.6	66.6	79.3	85.9	83.9	78.6	71.7	66.1	60.5
75°	30.8	32.6	37.9	46.0	55.9	61.6	63.0	60.2	54.7	50.5	47.2
77.5°	22.7	23.9	26.4	30.6	37.1	42.2	44.2	43.9	40.1	37.7	34.6
80°	18.2	18.8	20.1	21.8	26.8	31.8	33.3	33.3	30.6	29.6	26.6
82.5°	13.8	14.3	15.1	16.1	18.3	22.7	24.3	24.6	23.0	21.7	19.3
85°	7.9	7.7	8.1	8.7	9.1	10.3	12.8	13.2	12.8	11.1	10.5
87.5°	7.6	6.5	5.6	4.9	4.7	4.5	4.6	4.9	4.7	5.0	5.0
90°	24.0	17.8	13.4	10.7	8.9	7.1	3.6	0.9	3.6	7.1	8.9
92.5°	88.8	60.5	40.4	32.0	25.9	22.1	15.7	10.9	15.7	22.1	25.9
95°	205.5	128.1	87.2	65.9	51.6	43.6	34.7	31.1	34.7	43.6	51.6
97.5°	277.0	169.1	117.6	93.5	77.0	65.0	55.6	50.7	55.6	65.0	77.0
100°	291.9	183.3	136.2	111.3	93.5	79.2	71.2	68.5	71.2	79.2	93.5
102.5°	292.7	196.2	152.6	127.6	109.1	94.9	86.9	84.9	86.9	94.9	109.1
105°	297.2	218.0	176.2	151.3	131.7	118.3	112.2	108.6	112.2	118.3	131.7
107.5°	309.5	240.5	199.9	174.8	155.4	143.1	137.1	134.2	137.1	143.1	155.4
110°	319.5	255.4	216.2	190.5	171.7	160.2	154.9	151.3	154.9	160.2	171.7



TEST NUMBER: P331635-940

CATALOG NUMBER: SA2XXRDIP-C290D925U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	330.2	269.7	231.9	205.4	187.4	176.6	170.5	166.9	170.5	176.6	187.4
115°	346.2	291.9	253.6	229.6	211.8	201.2	195.8	191.4	195.8	201.2	211.8
117.5°	363.3	312.4	277.0	252.0	235.0	225.5	220.2	216.6	220.2	225.5	235.0
120°	374.7	326.6	291.9	267.0	249.1	241.2	235.9	232.3	235.9	241.2	249.1
122.5°	384.6	340.1	307.6	282.0	264.1	255.4	250.0	247.3	250.0	255.4	264.1
125°	400.5	360.4	328.4	303.4	285.7	275.0	269.7	267.0	269.7	275.0	285.7
127.5°	415.3	379.3	348.1	322.5	305.4	293.6	286.2	282.7	286.2	293.6	305.4
130°	424.5	390.7	359.5	334.7	316.8	304.3	295.4	291.9	295.4	304.3	316.8
132.5°	433.7	400.6	371.0	346.0	327.5	314.3	304.7	300.4	304.7	314.3	327.5
135°	445.9	414.7	386.2	361.3	340.8	327.5	316.8	313.3	316.8	327.5	340.8
137.5°	455.1	426.1	398.0	374.9	354.5	340.3	329.7	325.4	329.7	340.3	354.5
140°	460.1	432.5	405.8	382.7	363.1	348.8	338.2	334.7	338.2	348.8	363.1
142.5°	464.4	437.5	411.5	389.8	371.0	356.7	346.7	343.8	346.7	356.7	371.0
145°	469.9	445.0	421.0	401.4	383.6	370.2	361.3	357.8	361.3	370.2	383.6
147.5°	473.0	451.0	428.5	411.0	396.2	383.9	375.4	372.7	375.4	383.9	396.2
150°	474.3	453.9	433.4	417.4	404.0	392.4	385.3	382.7	385.3	392.4	404.0
152.5°	475.0	456.7	438.4	423.8	411.2	401.0	393.9	392.6	393.9	401.0	411.2
155°	476.1	461.0	445.9	432.5	422.8	413.0	407.6	406.7	407.6	413.0	422.8
157.5°	476.1	464.0	451.2	440.0	432.1	423.7	419.4	418.5	419.4	423.7	432.1
160°	476.1	465.5	454.8	445.0	437.8	430.7	427.2	426.3	427.2	430.7	437.8
162.5°	475.4	466.2	456.9	449.2	442.8	437.1	433.5	434.1	433.5	437.1	442.8
165°	473.5	467.3	459.2	453.9	449.4	444.1	442.3	443.2	442.3	444.1	449.4
167.5°	472.3	467.1	461.2	457.8	454.6	451.2	449.6	450.7	449.6	451.2	454.6
170°	470.8	466.4	461.9	459.2	457.4	454.8	453.9	455.7	453.9	454.8	457.4
172.5°	468.7	465.7	462.6	460.7	459.6	456.9	457.4	458.5	457.4	456.9	459.6
175°	466.4	464.6	462.8	461.9	461.9	460.1	461.0	461.9	461.0	460.1	461.9
177.5°	464.9	463.5	462.8	462.8	462.8	461.4	462.1	463.5	462.1	461.4	462.8
180°	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8



TEST NUMBER: P331635-940

CATALOG NUMBER: SA2XXRDIP-C290D925U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9
2.5°	574.7	573.5	571.4	568.2	566.2	562.8	560.6	561.9	562.2	561.9	561.6
5°	559.3	555.0	549.1	543.4	538.1	532.5	529.2	527.9	525.0	523.4	522.5
7.5°	540.6	533.2	525.0	515.1	506.7	497.8	493.4	491.2	485.4	482.2	479.5
10°	526.6	515.1	506.8	493.8	485.9	474.4	466.5	466.7	458.8	454.3	451.1
12.5°	511.2	498.6	484.7	473.1	462.1	452.8	443.3	439.4	431.1	426.8	418.0
15°	485.7	470.9	456.4	440.6	429.4	415.0	401.3	384.4	370.9	359.1	355.9
17.5°	457.9	439.5	424.9	406.4	387.3	363.1	347.1	337.3	329.2	323.0	318.3
20°	438.7	420.1	404.5	376.6	350.8	334.4	322.7	315.1	306.7	300.0	296.3
22.5°	418.7	399.2	377.9	346.7	326.6	313.5	303.1	294.4	288.6	283.5	280.1
25°	390.1	368.8	333.8	312.4	296.1	282.3	275.1	269.8	263.8	256.6	253.4
27.5°	360.0	326.2	301.0	285.0	269.6	260.6	254.0	246.2	240.8	237.6	234.2
30°	337.4	303.6	284.0	266.5	255.7	245.7	238.0	233.5	228.3	222.8	220.6
32.5°	312.4	285.3	266.4	252.0	240.9	232.4	226.3	219.1	215.3	212.0	207.3
35°	281.2	260.6	243.4	231.8	221.1	214.3	207.2	203.0	196.1	193.2	191.5
37.5°	254.8	237.0	224.2	211.8	203.4	195.8	191.5	184.7	181.7	177.7	173.9
40°	239.8	222.4	210.1	199.9	190.6	184.9	179.5	174.0	169.5	167.7	163.1
42.5°	224.6	210.4	198.0	187.0	180.7	174.7	167.8	163.8	159.2	156.2	153.4
45°	203.6	191.0	180.5	171.4	164.4	158.2	153.7	147.0	144.5	138.6	136.1
47.5°	185.1	173.4	163.4	154.7	148.0	143.9	137.4	132.2	128.0	124.3	121.2
50°	172.0	162.2	152.5	144.8	138.8	132.9	126.2	123.6	117.1	115.2	113.4
52.5°	160.0	150.7	141.9	134.3	128.2	122.5	116.6	113.2	108.8	107.0	105.7
55°	143.2	134.3	125.8	119.1	113.1	107.2	103.5	99.2	97.2	95.8	94.2
57.5°	126.4	118.3	111.8	105.0	98.9	94.3	90.1	87.5	85.4	83.6	81.6
60°	115.7	108.0	102.1	95.8	89.5	85.7	82.5	79.4	77.0	74.1	73.3
62.5°	104.3	97.6	92.2	86.1	80.6	77.1	74.0	71.2	68.2	64.1	63.0
65°	88.7	83.5	77.8	72.7	67.9	64.4	59.9	56.7	55.5	55.1	54.9
67.5°	74.6	69.6	64.7	59.6	55.2	52.0	49.7	49.2	48.3	48.2	47.5
70°	65.2	60.5	55.7	50.8	46.5	46.0	45.2	44.3	43.3	43.0	42.5
72.5°	56.8	52.0	47.1	43.2	41.4	40.7	39.9	39.0	38.3	37.9	37.7
75°	43.5	39.1	35.8	34.4	33.4	32.8	31.6	31.0	30.6	30.0	29.8
77.5°	31.4	28.8	27.4	26.5	25.4	24.8	24.1	23.5	23.0	22.9	22.6
80°	23.9	22.6	21.7	20.4	20.1	19.3	19.1	18.5	18.6	18.0	18.0
82.5°	18.5	17.0	16.1	15.6	15.2	14.5	14.4	14.1	14.1	13.6	13.6
85°	9.5	9.1	8.7	8.3	8.3	7.7	7.9	7.7	7.7	7.3	7.1
87.5°	5.2	5.6	6.2	7.4	8.5	8.5	8.3	7.9	7.6	7.9	7.9
90°	10.7	13.4	17.8	24.0	29.3	30.2	29.3	28.4	26.7	28.4	29.3
92.5°	32.0	40.4	60.5	88.8	114.0	115.7	97.7	77.6	66.6	59.1	53.6
95°	65.9	87.2	128.1	205.5	308.8	348.8	305.2	233.2	178.9	141.5	121.9
97.5°	93.5	117.6	169.1	277.0	448.5	595.6	624.7	544.1	445.1	348.8	284.6
100°	111.3	136.2	183.3	291.9	484.1	703.0	831.3	812.5	702.1	580.2	472.6
102.5°	127.6	152.6	196.2	292.7	470.6	706.6	908.1	988.4	963.5	874.3	760.2
105°	151.3	176.2	218.0	297.2	444.1	659.4	896.2	1081.3	1181.9	1193.5	1164.0
107.5°	174.8	199.9	240.5	309.5	430.9	608.9	818.1	1014.4	1165.8	1258.4	1301.5
110°	190.5	216.2	255.4	319.5	428.1	584.7	768.9	956.7	1116.0	1229.9	1302.9



TEST NUMBER: P331635-940

CATALOG NUMBER: SA2XXRDIP-C290D925U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	205.4	231.9	269.7	330.2	428.7	569.0	734.8	904.0	1056.9	1178.7	1262.3
115°	229.6	253.6	291.9	346.2	432.5	551.8	692.4	839.2	976.2	1092.9	1184.5
117.5°	252.0	277.0	312.4	363.3	438.9	543.4	665.7	790.4	910.8	1016.5	1102.5
120°	267.0	291.9	326.6	374.7	443.2	538.4	651.5	766.2	876.6	970.9	1052.0
122.5°	282.0	307.6	340.1	384.6	448.2	535.6	639.4	747.0	848.1	937.5	1010.7
125°	303.4	328.4	360.4	400.5	455.7	530.4	622.1	719.1	810.7	889.0	955.8
127.5°	322.5	348.1	379.3	415.3	463.3	527.4	606.1	691.5	774.5	848.3	909.9
130°	334.7	359.5	390.7	424.5	469.0	525.9	595.4	673.7	750.2	820.6	879.3
132.5°	346.0	371.0	400.6	433.7	474.7	525.2	586.8	656.6	727.5	792.0	847.2
135°	361.3	386.2	414.7	445.9	481.4	524.1	574.9	632.8	691.5	750.2	800.0
137.5°	374.9	398.0	426.1	455.1	487.5	524.0	566.5	613.7	662.8	709.4	752.9
140°	382.7	405.8	432.5	460.1	490.4	523.3	561.6	601.6	644.4	685.3	724.4
142.5°	389.8	411.5	437.5	464.4	492.5	523.3	556.6	591.7	627.9	663.2	696.0
145°	401.4	421.0	445.0	469.9	494.8	521.5	550.0	577.6	607.0	634.5	660.3
147.5°	411.0	428.5	451.0	473.0	495.5	518.4	543.2	566.7	589.9	611.4	630.3
150°	417.4	433.4	453.9	474.3	494.8	516.2	537.5	558.9	578.5	597.2	613.1
152.5°	423.8	438.4	456.7	475.0	493.4	512.6	532.5	551.1	569.2	585.1	599.0
155°	432.5	445.9	461.0	476.1	491.2	506.4	523.3	540.2	554.5	567.8	577.6
157.5°	440.0	451.2	464.0	476.1	487.1	500.0	514.6	527.5	539.5	550.7	558.4
160°	445.0	454.8	465.5	476.1	485.0	495.7	508.2	519.7	529.5	539.3	545.5
162.5°	449.2	456.9	466.2	475.4	482.9	492.1	502.5	511.9	520.2	528.6	533.4
165°	453.9	459.2	467.3	473.5	478.8	485.0	493.0	500.2	506.4	512.6	516.2
167.5°	457.8	461.2	467.1	472.3	474.7	478.8	483.8	488.9	493.7	498.0	501.2
170°	459.2	461.9	466.4	470.8	472.6	475.2	478.8	483.2	485.9	489.5	491.2
172.5°	460.7	462.6	465.7	468.7	469.8	471.0	473.9	476.8	478.8	481.6	482.7
175°	461.9	462.8	464.6	466.4	465.5	466.4	467.3	469.9	470.8	471.7	472.6
177.5°	462.8	462.8	463.5	464.9	463.5	462.8	463.5	464.9	464.9	465.7	465.7
180°	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8



TEST NUMBER: P331635-940

CATALOG NUMBER: SA2XXRDIP-C290D925U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9
2.5°	559.8	560.1	559.6	559.9	559.6	560.1	559.8	561.6	561.9	562.2	561.9
5°	521.6	519.2	518.7	518.2	518.7	519.2	521.6	522.5	523.4	525.0	527.9
7.5°	476.0	475.6	474.6	473.1	474.6	475.6	476.0	479.5	482.2	485.4	491.2
10°	446.7	445.6	445.4	444.0	445.4	445.6	446.7	451.1	454.3	458.8	466.7
12.5°	412.2	405.7	405.1	401.5	405.1	405.7	412.2	418.0	426.8	431.1	439.4
15°	351.1	349.8	345.7	343.1	345.7	349.8	351.1	355.9	359.1	370.9	384.4
17.5°	316.0	312.0	310.8	310.2	310.8	312.0	316.0	318.3	323.0	329.2	337.3
20°	293.5	289.9	289.3	288.8	289.3	289.9	293.5	296.3	300.0	306.7	315.1
22.5°	277.9	274.1	272.6	271.3	272.6	274.1	277.9	280.1	283.5	288.6	294.4
25°	251.4	249.9	249.1	248.7	249.1	249.9	251.4	253.4	256.6	263.8	269.8
27.5°	230.6	227.5	226.9	225.8	226.9	227.5	230.6	234.2	237.6	240.8	246.2
30°	218.7	217.8	216.3	215.1	216.3	217.8	218.7	220.6	222.8	228.3	233.5
32.5°	204.8	203.9	202.7	202.2	202.7	203.9	204.8	207.3	212.0	215.3	219.1
35°	189.4	186.5	185.3	183.5	185.3	186.5	189.4	191.5	193.2	196.1	203.0
37.5°	173.1	171.6	169.9	170.5	169.9	171.6	173.1	173.9	177.7	181.7	184.7
40°	160.4	159.4	159.0	158.8	159.0	159.4	160.4	163.1	167.7	169.5	174.0
42.5°	150.3	147.6	146.5	146.5	146.5	147.6	150.3	153.4	156.2	159.2	163.8
45°	135.1	132.5	130.6	130.8	130.6	132.5	135.1	136.1	138.6	144.5	147.0
47.5°	119.5	119.4	118.2	118.6	118.2	119.4	119.5	121.2	124.3	128.0	132.2
50°	112.0	110.8	109.9	110.2	109.9	110.8	112.0	113.4	115.2	117.1	123.6
52.5°	104.9	103.8	103.2	104.1	103.2	103.8	104.9	105.7	107.0	108.8	113.2
55°	93.2	91.9	91.8	91.6	91.8	91.9	93.2	94.2	95.8	97.2	99.2
57.5°	80.1	79.3	78.0	77.6	78.0	79.3	80.1	81.6	83.6	85.4	87.5
60°	70.7	69.1	67.1	66.9	67.1	69.1	70.7	73.3	74.1	77.0	79.4
62.5°	62.1	61.8	61.3	61.3	61.3	61.8	62.1	63.0	64.1	68.2	71.2
65°	54.5	54.3	54.5	54.7	54.5	54.3	54.5	54.9	55.1	55.5	56.7
67.5°	47.4	47.1	46.7	46.9	46.7	47.1	47.4	47.5	48.2	48.3	49.2
70°	42.1	41.9	41.7	41.7	41.7	41.9	42.1	42.5	43.0	43.3	44.3
72.5°	36.9	36.9	36.7	36.6	36.7	36.9	36.9	37.7	37.9	38.3	39.0
75°	29.6	29.2	29.2	29.2	29.2	29.2	29.6	29.8	30.0	30.6	31.0
77.5°	22.6	22.3	22.1	21.9	22.1	22.3	22.6	22.6	22.9	23.0	23.5
80°	17.8	17.7	17.4	17.4	17.4	17.7	17.8	18.0	18.0	18.6	18.5
82.5°	13.6	13.4	13.4	13.2	13.4	13.4	13.6	13.6	13.6	14.1	14.1
85°	7.3	7.5	7.3	7.7	7.3	7.5	7.3	7.1	7.3	7.7	7.7
87.5°	7.9	7.8	7.9	7.8	7.9	7.8	7.9	7.9	7.9	7.6	7.9
90°	29.3	29.3	29.3	29.3	29.3	29.3	29.3	29.3	28.4	26.7	28.4
92.5°	52.9	50.0	50.7	49.3	50.7	50.0	52.9	53.6	59.1	66.6	77.6
95°	110.4	103.3	100.6	101.5	100.6	103.3	110.4	121.9	141.5	178.9	233.2
97.5°	242.1	220.2	207.1	199.7	207.1	220.2	242.1	284.6	348.8	445.1	544.1
100°	398.7	360.4	334.7	318.6	334.7	360.4	398.7	472.6	580.2	702.1	812.5
102.5°	679.9	614.6	582.4	560.7	582.4	614.6	679.9	760.2	874.3	963.5	988.4
105°	1108.8	1053.7	1015.4	1003.0	1015.4	1053.7	1108.8	1164.0	1193.5	1181.9	1081.3
107.5°	1308.4	1305.4	1297.7	1281.2	1297.7	1305.4	1308.4	1301.5	1258.4	1165.8	1014.4
110°	1341.1	1358.1	1366.1	1365.2	1366.1	1358.1	1341.1	1302.9	1229.9	1116.0	956.7



TEST NUMBER: P331635-940

CATALOG NUMBER: SA2XXRDIP-C290D925U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1315.5	1343.8	1359.0	1363.8	1359.0	1343.8	1315.5	1262.3	1178.7	1056.9	904.0
115°	1247.7	1288.6	1311.8	1319.8	1311.8	1288.6	1247.7	1184.5	1092.9	976.2	839.2
117.5°	1166.9	1210.1	1234.6	1241.3	1234.6	1210.1	1166.9	1102.5	1016.5	910.8	790.4
120°	1114.2	1156.0	1181.9	1190.8	1181.9	1156.0	1114.2	1052.0	970.9	876.6	766.2
122.5°	1066.5	1107.6	1130.6	1138.1	1130.6	1107.6	1066.5	1010.7	937.5	848.1	747.0
125°	1007.5	1041.3	1063.5	1070.6	1063.5	1041.3	1007.5	955.8	889.0	810.7	719.1
127.5°	954.9	986.6	1005.8	1011.6	1005.8	986.6	954.9	909.9	848.3	774.5	691.5
130°	922.9	953.1	970.9	978.0	970.9	953.1	922.9	879.3	820.6	750.2	673.7
132.5°	890.1	920.4	936.7	943.2	936.7	920.4	890.1	847.2	792.0	727.5	656.6
135°	838.3	867.7	883.7	887.3	883.7	867.7	838.3	800.0	750.2	691.5	632.8
137.5°	787.8	813.1	827.2	832.5	827.2	813.1	787.8	752.9	709.4	662.8	613.7
140°	752.9	776.1	789.4	794.7	789.4	776.1	752.9	724.4	685.3	644.4	601.6
142.5°	723.0	744.0	755.9	757.0	755.9	744.0	723.0	696.0	663.2	627.9	591.7
145°	681.7	696.9	705.7	708.4	705.7	696.9	681.7	660.3	634.5	607.0	577.6
147.5°	647.9	660.0	666.0	667.6	666.0	660.0	647.9	630.3	611.4	589.9	566.7
150°	626.5	637.2	642.6	643.5	642.6	637.2	626.5	613.1	597.2	578.5	558.9
152.5°	609.4	618.7	622.6	622.8	622.6	618.7	609.4	599.0	585.1	569.2	551.1
155°	587.4	593.6	597.2	595.4	597.2	593.6	587.4	577.6	567.8	554.5	540.2
157.5°	565.3	570.4	572.0	572.0	572.0	570.4	565.3	558.4	550.7	539.5	527.5
160°	551.8	556.2	557.1	557.1	557.1	556.2	551.8	545.5	539.3	529.5	519.7
162.5°	539.7	542.7	543.6	542.9	543.6	542.7	539.7	533.4	528.6	520.2	511.9
165°	519.7	523.3	523.3	522.4	523.3	523.3	519.7	516.2	512.6	506.4	500.2
167.5°	502.8	504.8	504.6	503.5	504.6	504.8	502.8	501.2	498.0	493.7	488.9
170°	492.1	494.8	493.9	492.1	493.9	494.8	492.1	491.2	489.5	485.9	483.2
172.5°	483.6	484.8	483.9	482.9	483.9	484.8	483.6	482.7	481.6	478.8	476.8
175°	472.6	473.5	472.6	470.8	472.6	473.5	472.6	472.6	471.7	470.8	469.9
177.5°	465.7	465.7	464.9	463.5	464.9	465.7	465.7	465.7	465.7	464.9	464.9
180°	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8



TEST NUMBER: P331635-940
 CATALOG NUMBER: SA2XXRDIP-C290D925U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9
2.5°	560.6	562.8	566.2	568.2	571.4	573.5	574.7	576.8	577.9	582.0	586.2
5°	529.2	532.5	538.1	543.4	549.1	555.0	559.3	564.1	568.6	576.2	584.3
7.5°	493.4	497.8	506.7	515.1	525.0	533.2	540.6	548.8	556.2	567.3	578.8
10°	466.5	474.4	485.9	493.8	506.8	515.1	526.6	535.7	546.1	560.7	573.6
12.5°	443.3	452.8	462.1	473.1	484.7	498.6	511.2	523.0	535.2	550.3	565.5
15°	401.3	415.0	429.4	440.6	456.4	470.9	485.7	501.5	516.5	534.6	554.4
17.5°	347.1	363.1	387.3	406.4	424.9	439.5	457.9	477.0	494.6	516.4	538.5
20°	322.7	334.4	350.8	376.6	404.5	420.1	438.7	459.8	480.0	503.7	527.4
22.5°	303.1	313.5	326.6	346.7	377.9	399.2	418.7	440.1	463.5	487.7	514.0
25°	275.1	282.3	296.1	312.4	333.8	368.8	390.1	411.6	437.1	463.1	493.0
27.5°	254.0	260.6	269.6	285.0	301.0	326.2	360.0	383.4	408.8	438.0	469.1
30°	238.0	245.7	255.7	266.5	284.0	303.6	337.4	364.6	389.7	419.7	452.9
32.5°	226.3	232.4	240.9	252.0	266.4	285.3	312.4	345.3	369.8	401.4	436.0
35°	207.2	214.3	221.1	231.8	243.4	260.6	281.2	316.4	340.7	371.8	406.7
37.5°	191.5	195.8	203.4	211.8	224.2	237.0	254.8	286.3	312.6	343.2	378.9
40°	179.5	184.9	190.6	199.9	210.1	222.4	239.8	263.3	293.5	323.5	358.3
42.5°	167.8	174.7	180.7	187.0	198.0	210.4	224.6	244.5	275.4	303.7	337.6
45°	153.7	158.2	164.4	171.4	180.5	191.0	203.6	221.0	250.6	275.1	306.8
47.5°	137.4	143.9	148.0	154.7	163.4	173.4	185.1	200.2	224.1	247.1	276.6
50°	126.2	132.9	138.8	144.8	152.5	162.2	172.0	186.5	205.8	229.9	257.4
52.5°	116.6	122.5	128.2	134.3	141.9	150.7	160.0	172.8	189.2	211.4	238.2
55°	103.5	107.2	113.1	119.1	125.8	134.3	143.2	153.9	168.1	186.7	208.4
57.5°	90.1	94.3	98.9	105.0	111.8	118.3	126.4	136.1	147.2	164.1	182.6
60°	82.5	85.7	89.5	95.8	102.1	108.0	115.7	123.8	134.3	148.9	164.7
62.5°	74.0	77.1	80.6	86.1	92.2	97.6	104.3	112.9	121.8	135.1	148.9
65°	59.9	64.4	67.9	72.7	77.8	83.5	88.7	95.6	103.5	114.0	126.4
67.5°	49.7	52.0	55.2	59.6	64.7	69.6	74.6	80.0	86.9	95.0	104.8
70°	45.2	46.0	46.5	50.8	55.7	60.5	65.2	70.3	76.2	82.8	91.3
72.5°	39.9	40.7	41.4	43.2	47.1	52.0	56.8	60.5	66.1	71.7	78.6
75°	31.6	32.8	33.4	34.4	35.8	39.1	43.5	47.2	50.5	54.7	60.2
77.5°	24.1	24.8	25.4	26.5	27.4	28.8	31.4	34.6	37.7	40.1	43.9
80°	19.1	19.3	20.1	20.4	21.7	22.6	23.9	26.6	29.6	30.6	33.3
82.5°	14.4	14.5	15.2	15.6	16.1	17.0	18.5	19.3	21.7	23.0	24.6
85°	7.9	7.7	8.3	8.3	8.7	9.1	9.5	10.5	11.1	12.8	13.2
87.5°	8.3	8.5	8.5	7.4	6.2	5.6	5.2	5.0	5.0	4.7	4.9
90°	29.3	30.2	29.3	24.0	17.8	13.4	10.7	8.9	7.1	3.6	0.9
92.5°	97.7	115.7	114.0	88.8	60.5	40.4	32.0	25.9	22.1	15.7	10.9
95°	305.2	348.8	308.8	205.5	128.1	87.2	65.9	51.6	43.6	34.7	31.1
97.5°	624.7	595.6	448.5	277.0	169.1	117.6	93.5	77.0	65.0	55.6	50.7
100°	831.3	703.0	484.1	291.9	183.3	136.2	111.3	93.5	79.2	71.2	68.5
102.5°	908.1	706.6	470.6	292.7	196.2	152.6	127.6	109.1	94.9	86.9	84.9
105°	896.2	659.4	444.1	297.2	218.0	176.2	151.3	131.7	118.3	112.2	108.6
107.5°	818.1	608.9	430.9	309.5	240.5	199.9	174.8	155.4	143.1	137.1	134.2
110°	768.9	584.7	428.1	319.5	255.4	216.2	190.5	171.7	160.2	154.9	151.3



TEST NUMBER: P331635-940

CATALOG NUMBER: SA2XXRDIP-C290D925U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	734.8	569.0	428.7	330.2	269.7	231.9	205.4	187.4	176.6	170.5	166.9
115°	692.4	551.8	432.5	346.2	291.9	253.6	229.6	211.8	201.2	195.8	191.4
117.5°	665.7	543.4	438.9	363.3	312.4	277.0	252.0	235.0	225.5	220.2	216.6
120°	651.5	538.4	443.2	374.7	326.6	291.9	267.0	249.1	241.2	235.9	232.3
122.5°	639.4	535.6	448.2	384.6	340.1	307.6	282.0	264.1	255.4	250.0	247.3
125°	622.1	530.4	455.7	400.5	360.4	328.4	303.4	285.7	275.0	269.7	267.0
127.5°	606.1	527.4	463.3	415.3	379.3	348.1	322.5	305.4	293.6	286.2	282.7
130°	595.4	525.9	469.0	424.5	390.7	359.5	334.7	316.8	304.3	295.4	291.9
132.5°	586.8	525.2	474.7	433.7	400.6	371.0	346.0	327.5	314.3	304.7	300.4
135°	574.9	524.1	481.4	445.9	414.7	386.2	361.3	340.8	327.5	316.8	313.3
137.5°	566.5	524.0	487.5	455.1	426.1	398.0	374.9	354.5	340.3	329.7	325.4
140°	561.6	523.3	490.4	460.1	432.5	405.8	382.7	363.1	348.8	338.2	334.7
142.5°	556.6	523.3	492.5	464.4	437.5	411.5	389.8	371.0	356.7	346.7	343.8
145°	550.0	521.5	494.8	469.9	445.0	421.0	401.4	383.6	370.2	361.3	357.8
147.5°	543.2	518.4	495.5	473.0	451.0	428.5	411.0	396.2	383.9	375.4	372.7
150°	537.5	516.2	494.8	474.3	453.9	433.4	417.4	404.0	392.4	385.3	382.7
152.5°	532.5	512.6	493.4	475.0	456.7	438.4	423.8	411.2	401.0	393.9	392.6
155°	523.3	506.4	491.2	476.1	461.0	445.9	432.5	422.8	413.0	407.6	406.7
157.5°	514.6	500.0	487.1	476.1	464.0	451.2	440.0	432.1	423.7	419.4	418.5
160°	508.2	495.7	485.0	476.1	465.5	454.8	445.0	437.8	430.7	427.2	426.3
162.5°	502.5	492.1	482.9	475.4	466.2	456.9	449.2	442.8	437.1	433.5	434.1
165°	493.0	485.0	478.8	473.5	467.3	459.2	453.9	449.4	444.1	442.3	443.2
167.5°	483.8	478.8	474.7	472.3	467.1	461.2	457.8	454.6	451.2	449.6	450.7
170°	478.8	475.2	472.6	470.8	466.4	461.9	459.2	457.4	454.8	453.9	455.7
172.5°	473.9	471.0	469.8	468.7	465.7	462.6	460.7	459.6	456.9	457.4	458.5
175°	467.3	466.4	465.5	466.4	464.6	462.8	461.9	461.9	460.1	461.0	461.9
177.5°	463.5	462.8	463.5	464.9	463.5	462.8	462.8	462.8	461.4	462.1	463.5
180°	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8



TEST NUMBER: P331635-940

CATALOG NUMBER: SA2XXRDIP-C290D925U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9
2.5°	586.4	586.8	590.0	591.6	594.4	595.6	596.9	596.6	596.6	597.2	601.7
5°	587.6	591.7	597.7	603.6	609.3	614.1	617.4	620.6	621.9	627.7	632.9
7.5°	585.5	593.0	603.0	612.0	622.7	631.1	638.0	644.4	648.6	657.2	665.9
10°	582.7	593.3	604.6	616.2	631.0	642.1	653.4	662.2	664.9	677.7	685.0
12.5°	577.2	591.3	605.7	620.7	635.2	650.5	663.0	671.7	681.7	693.1	706.6
15°	569.0	585.1	604.0	623.2	643.9	662.5	675.9	691.1	702.0	714.6	726.4
17.5°	557.1	578.0	601.9	624.2	648.1	668.1	686.5	701.1	708.7	716.0	717.6
20°	547.7	570.2	598.3	624.6	648.5	671.6	689.9	702.0	704.1	704.3	693.6
22.5°	537.5	562.9	592.4	619.3	647.9	673.6	687.8	692.9	684.9	671.2	650.4
25°	518.7	548.1	582.4	613.1	644.4	668.6	673.5	664.4	636.2	606.6	569.2
27.5°	498.4	531.5	568.1	602.4	635.6	650.7	640.2	607.3	556.6	512.5	459.1
30°	483.5	520.6	556.6	594.9	625.7	632.1	608.1	559.6	500.5	434.1	380.8
32.5°	466.5	505.3	544.9	584.5	610.3	604.0	564.2	504.5	435.2	369.9	319.6
35°	442.2	482.2	525.0	564.7	581.1	553.8	494.2	416.6	345.7	284.8	250.1
37.5°	414.1	457.8	502.2	538.7	537.5	492.0	410.8	330.7	271.2	235.1	210.4
40°	394.1	438.4	486.3	517.1	504.0	444.6	356.7	281.2	237.6	208.8	190.8
42.5°	375.1	419.4	467.1	491.5	468.6	395.7	308.1	248.9	212.9	190.6	175.9
45°	342.5	389.3	433.5	447.0	406.1	325.7	249.1	206.2	182.3	165.7	155.6
47.5°	310.7	356.8	397.1	397.3	342.0	264.1	210.2	178.4	158.0	145.2	137.9
50°	291.2	335.0	368.8	363.6	300.8	235.0	188.0	160.6	143.7	133.7	126.0
52.5°	269.4	311.8	341.2	326.2	265.9	206.8	168.0	145.1	131.0	122.3	115.5
55°	237.6	275.3	296.0	273.2	217.0	172.0	142.0	123.9	113.4	106.1	100.2
57.5°	206.3	237.5	250.4	224.0	178.7	142.6	120.1	106.6	96.1	90.9	87.8
60°	186.7	213.3	222.4	193.2	155.3	124.8	106.4	93.8	86.1	82.7	79.6
62.5°	167.5	189.1	192.9	166.2	135.5	109.2	93.4	82.8	77.7	74.4	71.5
65°	138.9	154.5	152.8	131.3	107.2	86.7	75.2	68.7	64.8	60.2	55.1
67.5°	114.4	123.9	118.2	102.1	81.8	67.4	59.8	54.9	50.1	45.7	44.6
70°	98.8	104.3	98.3	83.5	67.1	56.5	50.5	44.6	41.7	40.8	38.9
72.5°	83.9	85.9	79.3	66.6	54.6	46.8	40.8	37.6	36.0	35.2	34.1
75°	63.0	61.6	55.9	46.0	37.9	32.6	30.8	29.6	28.5	27.7	27.1
77.5°	44.2	42.2	37.1	30.6	26.4	23.9	22.7	22.1	21.7	21.2	20.6
80°	33.3	31.8	26.8	21.8	20.1	18.8	18.2	17.4	17.4	17.0	16.4
82.5°	24.3	22.7	18.3	16.1	15.1	14.3	13.8	13.4	13.2	13.3	12.8
85°	12.8	10.3	9.1	8.7	8.1	7.7	7.9	7.5	7.5	7.5	7.3
87.5°	4.6	4.5	4.7	4.9	5.6	6.5	7.6	8.6	9.0	8.6	8.6
90°	3.6	7.1	8.9	10.7	13.4	17.8	24.0	29.3	30.2	29.3	28.4
92.5°	15.7	22.1	25.9	32.0	40.4	60.5	88.8	114.0	115.7	97.7	77.6
95°	34.7	43.6	51.6	65.9	87.2	128.1	205.5	308.8	348.8	305.2	233.2
97.5°	55.6	65.0	77.0	93.5	117.6	169.1	277.0	448.5	595.6	624.7	544.1
100°	71.2	79.2	93.5	111.3	136.2	183.3	291.9	484.1	703.0	831.3	812.5
102.5°	86.9	94.9	109.1	127.6	152.6	196.2	292.7	470.6	706.6	908.1	988.4
105°	112.2	118.3	131.7	151.3	176.2	218.0	297.2	444.1	659.4	896.2	1081.3
107.5°	137.1	143.1	155.4	174.8	199.9	240.5	309.5	430.9	608.9	818.1	1014.4
110°	154.9	160.2	171.7	190.5	216.2	255.4	319.5	428.1	584.7	768.9	956.7



TEST NUMBER: P331635-940

CATALOG NUMBER: SA2XXRDIP-C290D925U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	170.5	176.6	187.4	205.4	231.9	269.7	330.2	428.7	569.0	734.8	904.0
115°	195.8	201.2	211.8	229.6	253.6	291.9	346.2	432.5	551.8	692.4	839.2
117.5°	220.2	225.5	235.0	252.0	277.0	312.4	363.3	438.9	543.4	665.7	790.4
120°	235.9	241.2	249.1	267.0	291.9	326.6	374.7	443.2	538.4	651.5	766.2
122.5°	250.0	255.4	264.1	282.0	307.6	340.1	384.6	448.2	535.6	639.4	747.0
125°	269.7	275.0	285.7	303.4	328.4	360.4	400.5	455.7	530.4	622.1	719.1
127.5°	286.2	293.6	305.4	322.5	348.1	379.3	415.3	463.3	527.4	606.1	691.5
130°	295.4	304.3	316.8	334.7	359.5	390.7	424.5	469.0	525.9	595.4	673.7
132.5°	304.7	314.3	327.5	346.0	371.0	400.6	433.7	474.7	525.2	586.8	656.6
135°	316.8	327.5	340.8	361.3	386.2	414.7	445.9	481.4	524.1	574.9	632.8
137.5°	329.7	340.3	354.5	374.9	398.0	426.1	455.1	487.5	524.0	566.5	613.7
140°	338.2	348.8	363.1	382.7	405.8	432.5	460.1	490.4	523.3	561.6	601.6
142.5°	346.7	356.7	371.0	389.8	411.5	437.5	464.4	492.5	523.3	556.6	591.7
145°	361.3	370.2	383.6	401.4	421.0	445.0	469.9	494.8	521.5	550.0	577.6
147.5°	375.4	383.9	396.2	411.0	428.5	451.0	473.0	495.5	518.4	543.2	566.7
150°	385.3	392.4	404.0	417.4	433.4	453.9	474.3	494.8	516.2	537.5	558.9
152.5°	393.9	401.0	411.2	423.8	438.4	456.7	475.0	493.4	512.6	532.5	551.1
155°	407.6	413.0	422.8	432.5	445.9	461.0	476.1	491.2	506.4	523.3	540.2
157.5°	419.4	423.7	432.1	440.0	451.2	464.0	476.1	487.1	500.0	514.6	527.5
160°	427.2	430.7	437.8	445.0	454.8	465.5	476.1	485.0	495.7	508.2	519.7
162.5°	433.5	437.1	442.8	449.2	456.9	466.2	475.4	482.9	492.1	502.5	511.9
165°	442.3	444.1	449.4	453.9	459.2	467.3	473.5	478.8	485.0	493.0	500.2
167.5°	449.6	451.2	454.6	457.8	461.2	467.1	472.3	474.7	478.8	483.8	488.9
170°	453.9	454.8	457.4	459.2	461.9	466.4	470.8	472.6	475.2	478.8	483.2
172.5°	457.4	456.9	459.6	460.7	462.6	465.7	468.7	469.8	471.0	473.9	476.8
175°	461.0	460.1	461.9	461.9	462.8	464.6	466.4	465.5	466.4	467.3	469.9
177.5°	462.1	461.4	462.8	462.8	462.8	463.5	464.9	463.5	462.8	463.5	464.9
180°	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8



TEST NUMBER: P331635-940

CATALOG NUMBER: SA2XXRDIP-C290D925U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	582.9	582.9	582.9	582.9	582.9	582.9	582.9
2.5°	603.3	605.5	606.5	606.5	607.6	607.1	606.6
5°	638.0	641.9	642.7	646.3	649.0	648.2	648.5
7.5°	672.5	678.7	684.8	687.6	688.0	689.6	690.3
10°	693.8	698.8	708.3	706.9	714.0	718.1	711.4
12.5°	714.2	721.0	727.6	729.4	733.4	734.8	732.1
15°	732.6	736.3	736.6	735.7	736.9	735.8	732.0
17.5°	715.4	709.4	697.5	691.8	687.3	680.6	678.0
20°	686.9	669.4	649.2	641.1	631.6	613.0	617.4
22.5°	625.3	605.5	585.1	561.5	550.2	532.5	531.5
25°	529.5	495.3	457.5	431.2	415.8	398.2	390.5
27.5°	411.7	368.5	337.7	322.1	307.8	293.9	293.3
30°	334.2	301.8	277.9	264.6	255.8	249.9	251.2
32.5°	281.7	259.5	243.3	232.3	225.9	221.4	221.3
35°	230.3	215.1	204.7	200.1	195.5	192.3	192.4
37.5°	197.1	188.0	182.2	177.1	174.2	172.5	171.7
40°	180.0	172.5	168.1	165.1	162.6	160.4	160.0
42.5°	166.7	160.4	156.0	153.6	151.3	149.7	149.4
45°	147.8	142.8	138.8	136.1	135.1	133.7	133.7
47.5°	131.5	126.5	123.4	121.7	120.0	119.0	119.0
50°	120.6	116.6	113.9	112.8	111.4	110.8	110.6
52.5°	110.7	107.7	105.8	105.0	104.4	103.7	103.8
55°	97.2	95.6	94.8	94.2	93.2	91.9	92.7
57.5°	86.0	84.5	82.4	80.4	79.5	78.6	79.0
60°	78.0	75.2	72.3	70.1	69.5	67.7	67.7
62.5°	67.9	63.9	60.5	59.2	58.6	57.8	57.6
65°	52.3	50.6	49.8	49.0	48.6	48.6	48.2
67.5°	43.3	42.6	41.7	41.6	41.2	41.0	40.9
70°	38.3	37.5	37.1	36.8	36.5	36.6	36.0
72.5°	33.4	32.8	32.7	32.2	31.9	31.9	31.5
75°	26.3	26.3	26.1	25.9	25.5	25.3	25.5
77.5°	20.2	20.3	20.0	19.9	19.9	19.9	19.7
80°	16.2	16.4	16.2	16.0	15.8	16.0	15.8
82.5°	12.8	12.5	12.5	12.4	12.4	12.3	12.2
85°	7.3	7.5	7.3	7.1	7.1	7.1	7.3
87.5°	8.1	8.5	8.6	8.6	8.6	8.6	8.5
90°	26.7	28.4	29.3	29.3	29.3	29.3	29.3
92.5°	66.6	59.1	53.6	52.9	50.0	50.7	49.3
95°	178.9	141.5	121.9	110.4	103.3	100.6	101.5
97.5°	445.1	348.8	284.6	242.1	220.2	207.1	199.7
100°	702.1	580.2	472.6	398.7	360.4	334.7	318.6
102.5°	963.5	874.3	760.2	679.9	614.6	582.4	560.7
105°	1181.9	1193.5	1164.0	1108.8	1053.7	1015.4	1003.0
107.5°	1165.8	1258.4	1301.5	1308.4	1305.4	1297.7	1281.2
110°	1116.0	1229.9	1302.9	1341.1	1358.1	1366.1	1365.2



TEST NUMBER: P331635-940

CATALOG NUMBER: SA2XXRDIP-C290D925U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1056.9	1178.7	1262.3	1315.5	1343.8	1359.0	1363.8
115°	976.2	1092.9	1184.5	1247.7	1288.6	1311.8	1319.8
117.5°	910.8	1016.5	1102.5	1166.9	1210.1	1234.6	1241.3
120°	876.6	970.9	1052.0	1114.2	1156.0	1181.9	1190.8
122.5°	848.1	937.5	1010.7	1066.5	1107.6	1130.6	1138.1
125°	810.7	889.0	955.8	1007.5	1041.3	1063.5	1070.6
127.5°	774.5	848.3	909.9	954.9	986.6	1005.8	1011.6
130°	750.2	820.6	879.3	922.9	953.1	970.9	978.0
132.5°	727.5	792.0	847.2	890.1	920.4	936.7	943.2
135°	691.5	750.2	800.0	838.3	867.7	883.7	887.3
137.5°	662.8	709.4	752.9	787.8	813.1	827.2	832.5
140°	644.4	685.3	724.4	752.9	776.1	789.4	794.7
142.5°	627.9	663.2	696.0	723.0	744.0	755.9	757.0
145°	607.0	634.5	660.3	681.7	696.9	705.7	708.4
147.5°	589.9	611.4	630.3	647.9	660.0	666.0	667.6
150°	578.5	597.2	613.1	626.5	637.2	642.6	643.5
152.5°	569.2	585.1	599.0	609.4	618.7	622.6	622.8
155°	554.5	567.8	577.6	587.4	593.6	597.2	595.4
157.5°	539.5	550.7	558.4	565.3	570.4	572.0	572.0
160°	529.5	539.3	545.5	551.8	556.2	557.1	557.1
162.5°	520.2	528.6	533.4	539.7	542.7	543.6	542.9
165°	506.4	512.6	516.2	519.7	523.3	523.3	522.4
167.5°	493.7	498.0	501.2	502.8	504.8	504.6	503.5
170°	485.9	489.5	491.2	492.1	494.8	493.9	492.1
172.5°	478.8	481.6	482.7	483.6	484.8	483.9	482.9
175°	470.8	471.7	472.6	472.6	473.5	472.6	470.8
177.5°	464.9	465.7	465.7	465.7	465.7	464.9	463.5
180°	462.8	462.8	462.8	462.8	462.8	462.8	462.8

(END OF REPORT)