

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331653-940

Luminaire Tested: **SA2XXRDIP-C485D530U940-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331653-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C485D530U940-4F0-1E-UDD-A4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 530 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3498.8 lumens
Efficiency: N/A
Efficacy: 106.7 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 32.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331653-940
CATALOG NUMBER: SA2XXRDIP-C485D530U940-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331653-940

CATALOG NUMBER: SA2XXRDIP-C485D530U940-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	47
1	98	94	90	87	90	87	83	81	73	71	69	60	59	57	49	48	47	41
2	90	83	77	72	82	77	72	67	65	61	58	54	51	49	44	42	41	36
3	82	74	67	61	76	68	62	57	58	53	50	48	45	43	39	37	35	31
4	76	66	58	53	70	61	54	49	52	47	43	44	40	37	36	33	31	28
5	70	59	51	46	64	55	48	43	47	42	38	40	36	33	33	30	28	25
6	65	53	46	40	60	50	43	38	43	37	33	36	32	29	30	27	25	22
7	60	48	41	35	55	45	38	34	39	34	30	33	29	26	28	25	23	20
8	56	44	37	32	52	41	35	30	36	31	27	31	27	24	26	23	21	18
9	52	41	33	29	48	38	32	27	33	28	24	28	24	22	24	21	19	17
10	49	37	30	26	45	35	29	25	31	26	22	26	22	20	22	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15474	15474	15474	15474
5°	17280	15571	13807	15571
10°	19174	15462	11968	15462
15°	20117	15234	9429	15234
20°	17438	14899	8158	14899
25°	11437	14439	7285	14439
30°	7700	13882	6594	13882
35°	6236	13180	5947	13180
40°	5545	12416	5503	12416
45°	5019	11520	4912	11520
50°	4567	10630	4549	10630
55°	4293	9647	4236	9647
60°	3591	8741	3549	8741
65°	3030	7939	3435	7939
70°	2799	7091	3238	7091
75°	2620	6170	2994	6170
80°	2408	5077	2659	5077
85°	2205	4020	2353	4020



TEST NUMBER: P331653-940

CATALOG NUMBER: SA2XXRDIP-C485D530U940-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.8	2.6
10°-20°	253.1	7.2
20°-30°	326.2	9.3
30°-40°	310.0	8.9
40°-50°	265.6	7.6
50°-60°	202.2	5.8
60°-70°	127.8	3.7
70°-80°	63.8	1.8
80°-90°	19.0	0.5
90°-100°	105.7	3.0
100°-110°	358.8	10.3
110°-120°	381.2	10.9
120°-130°	313.8	9.0
130°-140°	252.0	7.2
140°-150°	190.4	5.4
150°-160°	133.8	3.8
160°-170°	78.8	2.3
170°-180°	25.6	0.7
0°-30°	670.2	19.2
0°-40°	980.2	28.0
0°-60°	1448.0	41.4
0°-90°	1658.6	47.4
90°-120°	845.7	24.2
90°-150°	1601.9	45.8
90°-180°	1840.0	52.6
0°-180°	3498.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	958	958	958	958	958	
5°	1066	961	852	961	1066	105
15°	1204	911	564	911	1204	325
25°	642	810	409	810	642	305
35°	316	669	302	669	316	202
45°	220	504	215	504	220	170
55°	152	343	150	343	152	134
65°	79	208	90	208	79	81
75°	42	99	48	99	42	45
85°	12	22	13	22	12	13
90°	17	0	17	0	17	10
95°	58	18	58	18	58	75
105°	573	62	573	62	573	555
115°	754	109	754	109	754	738
125°	612	153	612	153	612	553
135°	507	179	507	179	507	394
145°	405	204	405	204	405	257
155°	340	232	340	232	340	159
165°	298	253	298	253	298	85
175°	269	264	269	264	269	26
180°	264	264	264	264	264	



TEST NUMBER: P331653-940

CATALOG NUMBER: SA2XXRDIP-C485D530U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4
2.5°	997.3	998.1	998.9	997.0	997.0	995.4	991.9	989.3	981.8	980.7	980.7
5°	1066.2	1065.6	1066.9	1062.6	1056.6	1055.3	1048.9	1040.6	1032.0	1022.3	1020.3
7.5°	1134.9	1133.9	1131.2	1130.4	1125.9	1115.8	1105.6	1094.8	1080.4	1066.3	1059.3
10°	1169.5	1180.4	1173.8	1162.2	1164.5	1148.9	1140.5	1126.2	1114.2	1093.2	1088.6
12.5°	1203.5	1207.9	1205.8	1199.2	1196.2	1185.4	1174.1	1161.6	1139.5	1120.7	1104.3
15°	1203.5	1209.8	1211.5	1209.4	1211.1	1210.4	1204.4	1194.1	1174.8	1154.1	1136.2
17.5°	1114.6	1119.0	1129.9	1137.3	1146.7	1166.4	1176.1	1179.9	1177.0	1165.2	1152.5
20°	1014.9	1007.6	1038.3	1053.9	1067.3	1100.5	1129.2	1140.1	1157.8	1157.5	1154.1
22.5°	873.8	875.5	904.6	923.1	962.1	995.3	1028.0	1069.3	1103.5	1126.1	1139.2
25°	642.0	654.7	683.7	708.9	752.2	814.2	870.5	935.8	997.3	1046.0	1092.3
27.5°	482.1	483.1	506.0	529.5	555.2	605.9	676.8	754.7	842.6	915.0	998.4
30°	413.0	410.9	420.6	434.9	456.9	496.1	549.5	626.1	713.6	822.9	920.1
32.5°	363.9	364.0	371.3	381.9	400.1	426.6	463.2	525.3	608.1	715.5	829.5
35°	316.4	316.0	321.4	329.0	336.6	353.7	378.6	411.3	468.2	568.5	685.0
37.5°	282.2	283.7	286.3	291.1	299.5	309.0	324.0	345.9	386.5	445.8	543.7
40°	263.1	263.8	267.4	271.4	276.4	283.7	296.0	313.7	343.3	390.6	462.2
42.5°	245.5	246.1	248.8	252.4	256.4	263.8	273.9	289.2	313.3	350.1	409.2
45°	219.8	219.8	222.1	223.7	228.1	234.8	243.1	255.7	272.4	299.7	339.0
47.5°	195.6	195.7	197.2	200.1	202.9	208.0	216.2	226.6	238.7	259.8	293.4
50°	181.8	182.2	183.2	185.5	187.2	191.8	198.1	207.1	219.8	236.1	264.0
52.5°	170.6	170.4	171.7	172.7	173.8	177.2	181.9	189.8	201.2	215.3	238.5
55°	152.5	151.1	153.2	154.8	155.9	157.2	159.8	164.9	174.5	186.5	203.8
57.5°	129.8	129.3	130.7	132.2	135.4	139.0	141.2	144.5	149.5	158.0	175.2
60°	111.2	111.2	114.2	115.2	118.9	123.5	128.2	130.9	135.9	141.5	154.2
62.5°	94.7	95.0	96.4	97.4	99.4	105.1	111.7	117.5	122.3	127.7	136.1
65°	79.3	79.9	79.9	80.6	81.9	83.3	85.9	90.6	98.9	106.6	112.9
67.5°	67.2	67.5	67.7	68.3	68.7	70.1	71.2	73.3	75.2	82.5	90.3
70°	59.3	60.3	59.9	60.6	60.9	61.6	63.0	63.9	67.0	68.6	73.3
72.5°	51.8	52.5	52.5	52.9	53.8	53.9	54.9	55.9	57.9	59.3	61.8
75°	42.0	41.6	42.0	42.6	43.0	43.2	43.2	44.6	45.7	47.0	48.6
77.5°	32.4	32.7	32.6	32.7	32.7	33.3	33.3	33.9	34.9	35.6	36.4
80°	25.9	26.3	25.9	26.3	26.7	26.9	26.7	26.9	28.0	28.6	28.6
82.5°	20.2	20.2	20.4	20.4	20.5	20.6	21.0	21.1	21.8	21.7	21.9
85°	11.9	11.7	11.7	11.7	11.9	12.3	11.9	11.9	12.3	12.3	12.3
87.5°	7.6	7.8	7.8	7.8	7.8	7.8	7.6	8.0	7.8	8.3	7.8
90°	16.8	16.8	16.8	16.8	16.8	16.2	15.2	16.2	16.8	17.3	16.8
92.5°	28.2	29.0	28.6	30.2	30.6	33.8	38.1	44.3	55.8	66.1	65.2
95°	58.0	57.4	59.0	63.0	69.6	80.9	102.2	133.2	174.4	199.4	176.5
97.5°	114.1	118.4	125.8	138.3	162.6	199.4	254.4	310.9	357.0	340.3	256.3
100°	182.1	191.2	206.0	227.8	270.0	331.5	401.3	464.3	474.9	401.7	276.6
102.5°	320.4	332.8	351.2	388.5	434.4	499.6	550.5	564.8	518.9	403.8	268.9
105°	573.1	580.2	602.1	633.6	665.1	682.0	675.3	617.9	512.1	376.8	253.8
107.5°	732.1	741.5	745.9	747.6	743.7	719.1	666.2	579.6	467.4	347.9	246.2
110°	780.1	780.6	776.1	766.3	744.5	702.8	637.7	546.7	439.3	334.1	244.6



TEST NUMBER: P331653-940

CATALOG NUMBER: SA2XXRDIP-C485D530U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	779.3	776.5	767.9	751.7	721.3	673.5	604.0	516.6	419.8	325.1	245.0
115°	754.1	749.6	736.4	712.9	676.9	624.5	557.9	479.6	395.7	315.3	247.2
117.5°	709.3	705.4	691.5	666.8	630.0	580.9	520.4	451.7	380.4	310.5	250.8
120°	680.4	675.3	660.6	636.7	601.1	554.8	500.9	437.8	372.3	307.6	253.2
122.5°	650.3	646.0	632.9	609.4	577.5	535.7	484.6	426.9	365.3	306.0	256.1
125°	611.8	607.7	594.9	575.7	546.2	508.0	463.2	410.9	355.4	303.1	260.4
127.5°	578.0	574.7	563.7	545.6	520.0	484.7	442.6	395.1	346.3	301.4	264.7
130°	558.8	554.8	544.7	527.4	502.4	468.9	428.7	385.0	340.2	300.5	268.0
132.5°	539.0	535.3	525.9	508.6	484.1	452.6	415.7	375.2	335.3	300.1	271.3
135°	507.0	505.0	495.8	479.0	457.2	428.7	395.1	361.6	328.5	299.5	275.1
137.5°	475.6	472.6	464.6	450.1	430.3	405.4	378.8	350.7	323.7	299.4	278.6
140°	454.1	451.0	443.4	430.3	413.9	391.6	368.2	343.8	320.9	299.0	280.2
142.5°	432.6	431.9	425.2	413.1	397.7	379.0	358.8	338.0	318.1	299.0	281.4
145°	404.7	403.2	398.1	389.5	377.4	362.6	346.8	330.0	314.2	298.0	282.8
147.5°	381.5	380.6	377.1	370.2	360.2	349.4	337.1	323.9	310.4	296.1	283.1
150°	367.7	367.1	364.1	358.0	350.4	341.3	330.6	319.3	307.2	295.0	282.8
152.5°	355.9	355.8	353.6	348.2	342.2	334.3	325.3	314.9	304.3	292.9	282.0
155°	340.2	341.3	339.2	335.6	330.0	324.4	316.8	308.7	299.0	289.4	280.7
157.5°	326.9	326.9	326.0	323.0	319.1	314.7	308.3	301.5	294.0	285.7	278.4
160°	318.3	318.3	317.8	315.3	311.7	308.2	302.6	296.9	290.3	283.3	277.1
162.5°	310.2	310.6	310.1	308.4	304.8	302.1	297.3	292.5	287.1	281.2	275.9
165°	298.5	299.0	299.0	296.9	295.0	292.9	289.4	285.8	281.7	277.1	273.6
167.5°	287.8	288.4	288.5	287.3	286.4	284.5	282.1	279.4	276.4	273.6	271.3
170°	281.2	282.2	282.8	281.2	280.7	279.7	277.7	276.2	273.6	271.5	270.0
172.5°	275.9	276.5	277.1	276.3	275.8	275.2	273.6	272.5	270.7	269.1	268.4
175°	269.0	270.0	270.5	270.0	270.0	269.6	269.0	268.5	267.0	266.4	266.0
177.5°	264.8	265.6	266.1	266.1	266.1	266.1	265.6	265.6	264.8	264.4	264.8
180°	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4



TEST NUMBER: P331653-940

CATALOG NUMBER: SA2XXRDIP-C485D530U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4
2.5°	981.2	979.2	977.3	972.5	970.1	964.7	963.9	963.7	956.8	950.1	948.2
5°	1014.9	1009.7	1001.7	992.3	982.7	972.7	966.0	960.7	947.4	934.7	927.4
7.5°	1048.9	1037.5	1023.7	1006.0	991.3	974.8	962.6	951.5	932.6	914.5	902.3
10°	1074.2	1055.6	1037.3	1013.0	994.0	975.4	958.1	943.1	921.8	897.8	880.7
12.5°	1089.9	1069.4	1044.2	1020.5	995.9	972.1	949.0	929.7	904.7	879.9	859.7
15°	1111.3	1089.2	1058.6	1024.7	993.0	962.1	935.4	911.4	878.8	849.2	824.5
17.5°	1128.6	1098.3	1065.4	1026.2	989.5	950.2	915.9	885.2	848.9	813.2	784.2
20°	1134.2	1104.2	1066.2	1027.0	983.6	937.4	900.4	867.1	828.1	789.2	755.9
22.5°	1130.7	1107.4	1065.1	1018.2	973.8	925.4	883.7	845.0	801.8	762.1	723.4
25°	1107.2	1099.2	1059.3	1008.0	957.3	901.1	852.8	810.5	761.3	718.6	676.6
27.5°	1052.4	1069.7	1044.9	990.2	934.0	873.6	819.4	771.2	720.1	672.1	630.3
30°	999.7	1039.3	1028.6	978.0	915.1	855.8	794.9	744.6	690.0	640.7	599.4
32.5°	927.5	992.9	1003.4	961.0	895.9	830.7	766.9	716.8	659.9	607.9	567.7
35°	812.5	910.4	955.4	928.4	863.1	792.9	726.9	668.7	611.4	560.1	520.1
37.5°	675.4	808.7	883.7	885.6	825.6	752.6	680.8	622.9	564.3	514.0	470.7
40°	586.4	730.9	828.5	850.2	799.5	720.6	648.0	589.1	531.8	482.5	432.9
42.5°	506.5	650.5	770.4	808.1	767.9	689.5	616.6	555.0	499.3	452.6	402.0
45°	409.6	535.5	667.6	734.9	712.7	640.0	563.1	504.5	452.2	411.9	363.3
47.5°	345.5	434.3	562.1	653.2	652.7	586.5	510.9	454.7	406.2	368.5	329.0
50°	309.0	386.3	494.5	597.7	606.4	550.8	478.8	423.2	378.0	338.3	306.7
52.5°	276.3	339.9	437.2	536.2	560.8	512.6	442.9	391.6	347.6	311.1	284.0
55°	233.4	282.7	356.7	449.2	486.5	452.5	390.6	342.7	307.0	276.4	253.1
57.5°	197.4	234.4	293.7	368.3	411.7	390.3	339.3	300.3	269.8	242.1	223.7
60°	174.9	205.1	255.4	317.7	365.6	350.6	307.0	270.7	244.8	220.8	203.5
62.5°	153.6	179.6	222.7	273.2	317.2	310.9	275.4	244.9	222.1	200.3	185.7
65°	123.5	142.5	176.1	215.8	251.1	254.0	228.5	207.8	187.4	170.1	157.2
67.5°	98.4	110.8	134.5	167.8	194.3	203.8	188.1	172.3	156.1	142.8	131.5
70°	82.9	92.9	110.2	137.2	161.5	171.5	162.5	150.2	136.2	125.2	115.6
72.5°	67.2	77.0	89.7	109.5	130.4	141.2	138.0	129.1	117.8	108.7	99.6
75°	50.6	53.6	62.2	75.6	91.9	101.2	103.5	98.9	89.9	82.9	77.6
77.5°	37.5	39.2	43.3	50.4	61.0	69.3	72.8	72.2	66.0	62.0	57.0
80°	30.0	30.9	33.0	35.9	44.0	52.3	54.6	54.6	50.3	48.6	43.6
82.5°	22.7	23.5	24.7	26.4	30.1	37.4	39.9	40.5	37.7	35.6	31.7
85°	13.0	12.7	13.3	14.4	15.0	16.9	21.0	21.7	21.0	18.3	17.3
87.5°	7.3	6.9	6.3	5.7	5.8	5.9	6.8	7.8	7.0	6.7	6.3
90°	13.7	10.2	7.7	6.1	5.1	4.1	2.1	0.5	2.1	4.1	5.1
92.5°	50.7	34.6	23.1	18.3	14.9	12.6	8.9	6.2	8.9	12.6	14.9
95°	117.4	73.2	49.8	37.6	29.5	24.9	19.8	17.8	19.8	24.9	29.5
97.5°	158.3	96.7	67.2	53.4	44.1	37.1	31.7	29.0	31.7	37.1	44.1
100°	166.8	104.8	77.8	63.6	53.4	45.3	40.7	39.1	40.7	45.3	53.4
102.5°	167.2	112.1	87.1	72.9	62.3	54.2	49.7	48.5	49.7	54.2	62.3
105°	169.9	124.6	100.7	86.4	75.3	67.6	64.1	62.1	64.1	67.6	75.3
107.5°	176.8	137.4	114.2	99.9	88.8	81.8	78.3	76.7	78.3	81.8	88.8
110°	182.5	146.0	123.6	108.8	98.2	91.6	88.5	86.4	88.5	91.6	98.2



TEST NUMBER: P331653-940

CATALOG NUMBER: SA2XXRDIP-C485D530U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	188.7	154.1	132.5	117.3	107.1	100.9	97.5	95.4	97.5	100.9	107.1
115°	197.8	166.8	144.9	131.2	121.0	114.9	111.9	109.3	111.9	114.9	121.0
117.5°	207.6	178.5	158.3	144.0	134.3	128.9	125.8	123.8	125.8	128.9	134.3
120°	214.1	186.6	166.8	152.6	142.4	137.8	134.7	132.7	134.7	137.8	142.4
122.5°	219.8	194.4	175.8	161.1	151.0	146.0	142.9	141.2	142.9	146.0	151.0
125°	228.8	206.0	187.6	173.4	163.3	157.1	154.1	152.6	154.1	157.1	163.3
127.5°	237.3	216.8	198.9	184.3	174.5	167.8	163.5	161.5	163.5	167.8	174.5
130°	242.5	223.3	205.5	191.2	181.0	173.9	168.8	166.8	168.8	173.9	181.0
132.5°	247.9	228.9	212.0	197.7	187.2	179.6	174.2	171.7	174.2	179.6	187.2
135°	254.8	237.0	220.7	206.4	194.7	187.2	181.0	179.0	181.0	187.2	194.7
137.5°	260.0	243.5	227.4	214.2	202.6	194.5	188.3	185.9	188.3	194.5	202.6
140°	262.9	247.2	231.9	218.6	207.5	199.4	193.2	191.2	193.2	199.4	207.5
142.5°	265.4	250.0	235.1	222.7	212.0	203.8	198.1	196.5	198.1	203.8	212.0
145°	268.5	254.2	240.5	229.3	219.2	211.5	206.4	204.5	206.4	211.5	219.2
147.5°	270.3	257.7	244.8	234.9	226.4	219.4	214.5	212.9	214.5	219.4	226.4
150°	271.1	259.3	247.6	238.5	230.9	224.3	220.2	218.6	220.2	224.3	230.9
152.5°	271.4	261.0	250.5	242.2	235.0	229.2	225.1	224.4	225.1	229.2	235.0
155°	272.1	263.4	254.8	247.2	241.6	235.9	232.9	232.4	232.9	235.9	241.6
157.5°	272.1	265.1	257.8	251.5	246.9	242.1	239.6	239.1	239.6	242.1	246.9
160°	272.1	266.0	259.8	254.2	250.2	246.1	244.1	243.6	244.1	246.1	250.2
162.5°	271.6	266.4	261.1	256.7	253.1	249.8	247.7	248.1	247.7	249.8	253.1
165°	270.5	267.0	262.4	259.3	256.8	253.8	252.7	253.2	252.7	253.8	256.8
167.5°	269.8	266.9	263.5	261.6	259.8	257.8	256.9	257.5	256.9	257.8	259.8
170°	269.0	266.4	263.9	262.4	261.4	259.8	259.3	260.4	259.3	259.8	261.4
172.5°	267.8	266.1	264.3	263.2	262.6	261.1	261.4	262.0	261.4	261.1	262.6
175°	266.4	265.5	264.4	263.9	263.9	262.9	263.4	263.9	263.4	262.9	263.9
177.5°	265.6	264.8	264.4	264.4	264.4	263.6	264.0	264.8	264.0	263.6	264.4
180°	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4



TEST NUMBER: P331653-940

CATALOG NUMBER: SA2XXRDIP-C485D530U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4
2.5°	944.8	942.9	939.4	934.2	930.9	925.3	921.6	923.7	924.3	923.7	923.2
5°	919.4	912.4	902.8	893.4	884.8	875.5	870.1	867.8	863.1	860.5	859.2
7.5°	888.7	876.6	863.0	846.8	832.9	818.5	811.1	807.4	797.9	792.7	788.2
10°	865.8	846.8	833.1	811.8	798.9	779.9	766.9	767.2	754.2	746.9	741.5
12.5°	840.5	819.7	796.9	777.8	759.7	744.5	728.8	722.5	708.6	701.6	687.2
15°	798.5	774.2	750.3	724.2	706.0	682.3	659.7	632.0	609.8	590.4	585.1
17.5°	752.7	722.6	698.6	668.1	636.7	596.9	570.7	554.6	541.2	531.0	523.4
20°	721.3	690.6	665.0	619.0	576.8	549.7	530.5	518.2	504.2	493.2	487.1
22.5°	688.2	656.3	621.3	570.0	537.1	515.4	498.2	484.0	474.6	466.0	460.6
25°	641.3	606.4	548.8	513.4	486.9	464.2	452.2	443.5	433.5	421.9	416.6
27.5°	591.8	536.2	494.8	468.6	443.2	428.5	417.7	404.7	395.8	390.6	385.0
30°	554.7	499.2	466.9	438.2	420.3	403.9	391.3	384.0	375.3	366.3	362.7
32.5°	513.4	469.0	438.1	414.3	396.0	382.1	372.1	360.3	354.0	348.5	340.8
35°	462.2	428.6	400.3	380.9	363.6	352.3	340.6	333.7	322.4	317.7	314.7
37.5°	418.7	389.6	368.5	348.1	334.4	321.9	314.8	303.6	298.7	292.2	285.9
40°	394.2	365.6	345.4	328.7	313.3	304.0	295.1	286.1	278.7	275.7	268.0
42.5°	369.3	345.9	325.6	307.4	297.1	287.2	275.9	269.3	261.6	256.8	252.1
45°	334.7	314.1	296.7	281.7	270.4	260.1	252.7	241.7	237.5	227.7	223.7
47.5°	304.3	285.1	268.6	254.3	243.3	236.6	225.9	217.2	210.4	204.4	199.3
50°	282.7	266.7	250.7	238.1	228.1	218.5	207.5	203.1	192.4	189.5	186.5
52.5°	263.0	247.8	233.2	220.8	210.8	201.4	191.7	186.1	178.9	175.8	173.7
55°	235.4	220.8	206.8	195.8	185.8	176.1	170.1	163.2	159.8	157.5	154.8
57.5°	207.7	194.6	183.8	172.7	162.6	155.0	148.0	143.8	140.4	137.3	134.1
60°	190.1	177.5	167.8	157.5	147.2	140.9	135.5	130.5	126.5	121.9	120.6
62.5°	171.5	160.4	151.6	141.5	132.5	126.7	121.7	117.0	112.2	105.4	103.5
65°	145.9	137.2	127.9	119.6	111.6	105.9	98.5	93.3	91.2	90.6	90.2
67.5°	122.7	114.5	106.5	98.0	90.7	85.4	81.7	80.9	79.5	79.1	78.2
70°	107.2	99.6	91.6	83.6	76.6	75.6	74.3	72.9	71.2	70.6	69.9
72.5°	93.4	85.4	77.5	71.1	68.0	66.8	65.5	64.1	63.0	62.3	62.0
75°	71.6	64.3	58.9	56.6	54.9	53.9	52.0	50.9	50.3	49.3	49.0
77.5°	51.5	47.4	44.9	43.5	41.7	40.7	39.6	38.5	37.8	37.6	37.1
80°	39.3	37.3	35.7	33.6	33.0	31.7	31.3	30.3	30.7	29.6	29.6
82.5°	30.5	28.0	26.6	25.7	25.0	23.9	23.5	23.1	23.2	22.5	22.5
85°	15.7	15.0	14.4	13.6	13.6	12.7	13.0	12.7	12.7	11.9	11.7
87.5°	6.2	6.3	6.3	7.0	7.6	7.5	7.3	7.0	6.8	7.0	6.8
90°	6.1	7.7	10.2	13.7	16.8	17.3	16.8	16.2	15.2	16.2	16.8
92.5°	18.3	23.1	34.6	50.7	65.2	66.1	55.8	44.3	38.1	33.8	30.6
95°	37.6	49.8	73.2	117.4	176.5	199.4	174.4	133.2	102.2	80.9	69.6
97.5°	53.4	67.2	96.7	158.3	256.3	340.3	357.0	310.9	254.4	199.4	162.6
100°	63.6	77.8	104.8	166.8	276.6	401.7	474.9	464.3	401.3	331.5	270.0
102.5°	72.9	87.1	112.1	167.2	268.9	403.8	518.9	564.8	550.5	499.6	434.4
105°	86.4	100.7	124.6	169.9	253.8	376.8	512.1	617.9	675.3	682.0	665.1
107.5°	99.9	114.2	137.4	176.8	246.2	347.9	467.4	579.6	666.2	719.1	743.7
110°	108.8	123.6	146.0	182.5	244.6	334.1	439.3	546.7	637.7	702.8	744.5



TEST NUMBER: P331653-940

CATALOG NUMBER: SA2XXRDIP-C485D530U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	117.3	132.5	154.1	188.7	245.0	325.1	419.8	516.6	604.0	673.5	721.3
115°	131.2	144.9	166.8	197.8	247.2	315.3	395.7	479.6	557.9	624.5	676.9
117.5°	144.0	158.3	178.5	207.6	250.8	310.5	380.4	451.7	520.4	580.9	630.0
120°	152.6	166.8	186.6	214.1	253.2	307.6	372.3	437.8	500.9	554.8	601.1
122.5°	161.1	175.8	194.4	219.8	256.1	306.0	365.3	426.9	484.6	535.7	577.5
125°	173.4	187.6	206.0	228.8	260.4	303.1	355.4	410.9	463.2	508.0	546.2
127.5°	184.3	198.9	216.8	237.3	264.7	301.4	346.3	395.1	442.6	484.7	520.0
130°	191.2	205.5	223.3	242.5	268.0	300.5	340.2	385.0	428.7	468.9	502.4
132.5°	197.7	212.0	228.9	247.9	271.3	300.1	335.3	375.2	415.7	452.6	484.1
135°	206.4	220.7	237.0	254.8	275.1	299.5	328.5	361.6	395.1	428.7	457.2
137.5°	214.2	227.4	243.5	260.0	278.6	299.4	323.7	350.7	378.8	405.4	430.3
140°	218.6	231.9	247.2	262.9	280.2	299.0	320.9	343.8	368.2	391.6	413.9
142.5°	222.7	235.1	250.0	265.4	281.4	299.0	318.1	338.0	358.8	379.0	397.7
145°	229.3	240.5	254.2	268.5	282.8	298.0	314.2	330.0	346.8	362.6	377.4
147.5°	234.9	244.8	257.7	270.3	283.1	296.1	310.4	323.9	337.1	349.4	360.2
150°	238.5	247.6	259.3	271.1	282.8	295.0	307.2	319.3	330.6	341.3	350.4
152.5°	242.2	250.5	261.0	271.4	282.0	292.9	304.3	314.9	325.3	334.3	342.2
155°	247.2	254.8	263.4	272.1	280.7	289.4	299.0	308.7	316.8	324.4	330.0
157.5°	251.5	257.8	265.1	272.1	278.4	285.7	294.0	301.5	308.3	314.7	319.1
160°	254.2	259.8	266.0	272.1	277.1	283.3	290.3	296.9	302.6	308.2	311.7
162.5°	256.7	261.1	266.4	271.6	275.9	281.2	287.1	292.5	297.3	302.1	304.8
165°	259.3	262.4	267.0	270.5	273.6	277.1	281.7	285.8	289.4	292.9	295.0
167.5°	261.6	263.5	266.9	269.8	271.3	273.6	276.4	279.4	282.1	284.5	286.4
170°	262.4	263.9	266.4	269.0	270.0	271.5	273.6	276.2	277.7	279.7	280.7
172.5°	263.2	264.3	266.1	267.8	268.4	269.1	270.7	272.5	273.6	275.2	275.8
175°	263.9	264.4	265.5	266.4	266.0	266.4	267.0	268.5	269.0	269.6	270.0
177.5°	264.4	264.4	264.8	265.6	264.8	264.4	264.8	265.6	265.6	266.1	266.1
180°	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4



TEST NUMBER: P331653-940

CATALOG NUMBER: SA2XXRDIP-C485D530U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4
2.5°	920.2	920.8	920.0	920.5	920.0	920.8	920.2	923.2	923.7	924.3	923.7
5°	857.5	853.5	852.8	851.9	852.8	853.5	857.5	859.2	860.5	863.1	867.8
7.5°	782.5	781.9	780.2	777.8	780.2	781.9	782.5	788.2	792.7	797.9	807.4
10°	734.2	732.6	732.3	730.0	732.3	732.6	734.2	741.5	746.9	754.2	767.2
12.5°	677.8	667.1	665.9	660.1	665.9	667.1	677.8	687.2	701.6	708.6	722.5
15°	577.1	575.1	568.5	564.1	568.5	575.1	577.1	585.1	590.4	609.8	632.0
17.5°	519.5	513.0	511.0	510.1	511.0	513.0	519.5	523.4	531.0	541.2	554.6
20°	482.5	476.5	475.5	474.8	475.5	476.5	482.5	487.1	493.2	504.2	518.2
22.5°	456.9	450.7	448.1	446.1	448.1	450.7	456.9	460.6	466.0	474.6	484.0
25°	413.2	410.9	409.6	408.9	409.6	410.9	413.2	416.6	421.9	433.5	443.5
27.5°	379.1	374.0	372.9	371.2	372.9	374.0	379.1	385.0	390.6	395.8	404.7
30°	359.6	357.9	355.6	353.7	355.6	357.9	359.6	362.7	366.3	375.3	384.0
32.5°	336.7	335.4	333.2	332.3	333.2	335.4	336.7	340.8	348.5	354.0	360.3
35°	311.4	306.7	304.7	301.7	304.7	306.7	311.4	314.7	317.7	322.4	333.7
37.5°	284.5	282.0	279.3	280.3	279.3	282.0	284.5	285.9	292.2	298.7	303.6
40°	263.8	262.1	261.4	261.1	261.4	262.1	263.8	268.0	275.7	278.7	286.1
42.5°	247.2	242.6	240.9	240.9	240.9	242.6	247.2	252.1	256.8	261.6	269.3
45°	222.1	217.8	214.8	215.1	214.8	217.8	222.1	223.7	227.7	237.5	241.7
47.5°	196.4	196.3	194.4	195.0	194.4	196.3	196.4	199.3	204.4	210.4	217.2
50°	184.1	182.2	180.8	181.1	180.8	182.2	184.1	186.5	189.5	192.4	203.1
52.5°	172.5	170.7	169.6	171.0	169.6	170.7	172.5	173.7	175.8	178.9	186.1
55°	153.2	151.1	150.9	150.5	150.9	151.1	153.2	154.8	157.5	159.8	163.2
57.5°	131.7	130.4	128.3	127.5	128.3	130.4	131.7	134.1	137.3	140.4	143.8
60°	116.2	113.5	110.2	109.9	110.2	113.5	116.2	120.6	121.9	126.5	130.5
62.5°	102.1	101.6	100.9	100.9	100.9	101.6	102.1	103.5	105.4	112.2	117.0
65°	89.6	89.3	89.6	89.9	89.6	89.3	89.6	90.2	90.6	91.2	93.3
67.5°	78.0	77.5	76.9	77.1	76.9	77.5	78.0	78.2	79.1	79.5	80.9
70°	69.3	68.9	68.6	68.6	68.6	68.9	69.3	69.9	70.6	71.2	72.9
72.5°	60.7	60.6	60.4	60.1	60.4	60.6	60.7	62.0	62.3	63.0	64.1
75°	48.6	48.0	48.0	48.0	48.0	48.0	48.6	49.0	49.3	50.3	50.9
77.5°	37.0	36.7	36.4	36.1	36.4	36.7	37.0	37.1	37.6	37.8	38.5
80°	29.3	29.0	28.6	28.6	28.6	29.0	29.3	29.6	29.6	30.7	30.3
82.5°	22.4	22.0	21.9	21.7	21.9	22.0	22.4	22.5	22.5	23.2	23.1
85°	11.9	12.3	11.9	12.7	11.9	12.3	11.9	11.7	11.9	12.7	12.7
87.5°	6.8	6.5	6.8	6.5	6.8	6.5	6.8	6.8	7.0	6.8	7.0
90°	16.8	16.8	16.8	16.8	16.8	16.8	16.8	16.8	16.2	15.2	16.2
92.5°	30.2	28.6	29.0	28.2	29.0	28.6	30.2	30.6	33.8	38.1	44.3
95°	63.0	59.0	57.4	58.0	57.4	59.0	63.0	69.6	80.9	102.2	133.2
97.5°	138.3	125.8	118.4	114.1	118.4	125.8	138.3	162.6	199.4	254.4	310.9
100°	227.8	206.0	191.2	182.1	191.2	206.0	227.8	270.0	331.5	401.3	464.3
102.5°	388.5	351.2	332.8	320.4	332.8	351.2	388.5	434.4	499.6	550.5	564.8
105°	633.6	602.1	580.2	573.1	580.2	602.1	633.6	665.1	682.0	675.3	617.9
107.5°	747.6	745.9	741.5	732.1	741.5	745.9	747.6	743.7	719.1	666.2	579.6
110°	766.3	776.1	780.6	780.1	780.6	776.1	766.3	744.5	702.8	637.7	546.7



TEST NUMBER: P331653-940

CATALOG NUMBER: SA2XXRDIP-C485D530U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	751.7	767.9	776.5	779.3	776.5	767.9	751.7	721.3	673.5	604.0	516.6
115°	712.9	736.4	749.6	754.1	749.6	736.4	712.9	676.9	624.5	557.9	479.6
117.5°	666.8	691.5	705.4	709.3	705.4	691.5	666.8	630.0	580.9	520.4	451.7
120°	636.7	660.6	675.3	680.4	675.3	660.6	636.7	601.1	554.8	500.9	437.8
122.5°	609.4	632.9	646.0	650.3	646.0	632.9	609.4	577.5	535.7	484.6	426.9
125°	575.7	594.9	607.7	611.8	607.7	594.9	575.7	546.2	508.0	463.2	410.9
127.5°	545.6	563.7	574.7	578.0	574.7	563.7	545.6	520.0	484.7	442.6	395.1
130°	527.4	544.7	554.8	558.8	554.8	544.7	527.4	502.4	468.9	428.7	385.0
132.5°	508.6	525.9	535.3	539.0	535.3	525.9	508.6	484.1	452.6	415.7	375.2
135°	479.0	495.8	505.0	507.0	505.0	495.8	479.0	457.2	428.7	395.1	361.6
137.5°	450.1	464.6	472.6	475.6	472.6	464.6	450.1	430.3	405.4	378.8	350.7
140°	430.3	443.4	451.0	454.1	451.0	443.4	430.3	413.9	391.6	368.2	343.8
142.5°	413.1	425.2	431.9	432.6	431.9	425.2	413.1	397.7	379.0	358.8	338.0
145°	389.5	398.1	403.2	404.7	403.2	398.1	389.5	377.4	362.6	346.8	330.0
147.5°	370.2	377.1	380.6	381.5	380.6	377.1	370.2	360.2	349.4	337.1	323.9
150°	358.0	364.1	367.1	367.7	367.1	364.1	358.0	350.4	341.3	330.6	319.3
152.5°	348.2	353.6	355.8	355.9	355.8	353.6	348.2	342.2	334.3	325.3	314.9
155°	335.6	339.2	341.3	340.2	341.3	339.2	335.6	330.0	324.4	316.8	308.7
157.5°	323.0	326.0	326.9	326.9	326.9	326.0	323.0	319.1	314.7	308.3	301.5
160°	315.3	317.8	318.3	318.3	318.3	317.8	315.3	311.7	308.2	302.6	296.9
162.5°	308.4	310.1	310.6	310.2	310.6	310.1	308.4	304.8	302.1	297.3	292.5
165°	296.9	299.0	299.0	298.5	299.0	299.0	296.9	295.0	292.9	289.4	285.8
167.5°	287.3	288.5	288.4	287.8	288.4	288.5	287.3	286.4	284.5	282.1	279.4
170°	281.2	282.8	282.2	281.2	282.2	282.8	281.2	280.7	279.7	277.7	276.2
172.5°	276.3	277.1	276.5	275.9	276.5	277.1	276.3	275.8	275.2	273.6	272.5
175°	270.0	270.5	270.0	269.0	270.0	270.5	270.0	270.0	269.6	269.0	268.5
177.5°	266.1	266.1	265.6	264.8	265.6	266.1	266.1	266.1	266.1	265.6	265.6
180°	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4



TEST NUMBER: P331653-940

CATALOG NUMBER: SA2XXRDIP-C485D530U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4
2.5°	921.6	925.3	930.9	934.2	939.4	942.9	944.8	948.2	950.1	956.8	963.7
5°	870.1	875.5	884.8	893.4	902.8	912.4	919.4	927.4	934.7	947.4	960.7
7.5°	811.1	818.5	832.9	846.8	863.0	876.6	888.7	902.3	914.5	932.6	951.5
10°	766.9	779.9	798.9	811.8	833.1	846.8	865.8	880.7	897.8	921.8	943.1
12.5°	728.8	744.5	759.7	777.8	796.9	819.7	840.5	859.7	879.9	904.7	929.7
15°	659.7	682.3	706.0	724.2	750.3	774.2	798.5	824.5	849.2	878.8	911.4
17.5°	570.7	596.9	636.7	668.1	698.6	722.6	752.7	784.2	813.2	848.9	885.2
20°	530.5	549.7	576.8	619.0	665.0	690.6	721.3	755.9	789.2	828.1	867.1
22.5°	498.2	515.4	537.1	570.0	621.3	656.3	688.2	723.4	762.1	801.8	845.0
25°	452.2	464.2	486.9	513.4	548.8	606.4	641.3	676.6	718.6	761.3	810.5
27.5°	417.7	428.5	443.2	468.6	494.8	536.2	591.8	630.3	672.1	720.1	771.2
30°	391.3	403.9	420.3	438.2	466.9	499.2	554.7	599.4	640.7	690.0	744.6
32.5°	372.1	382.1	396.0	414.3	438.1	469.0	513.4	567.7	607.9	659.9	716.8
35°	340.6	352.3	363.6	380.9	400.3	428.6	462.2	520.1	560.1	611.4	668.7
37.5°	314.8	321.9	334.4	348.1	368.5	389.6	418.7	470.7	514.0	564.3	622.9
40°	295.1	304.0	313.3	328.7	345.4	365.6	394.2	432.9	482.5	531.8	589.1
42.5°	275.9	287.2	297.1	307.4	325.6	345.9	369.3	402.0	452.6	499.3	555.0
45°	252.7	260.1	270.4	281.7	296.7	314.1	334.7	363.3	411.9	452.2	504.5
47.5°	225.9	236.6	243.3	254.3	268.6	285.1	304.3	329.0	368.5	406.2	454.7
50°	207.5	218.5	228.1	238.1	250.7	266.7	282.7	306.7	338.3	378.0	423.2
52.5°	191.7	201.4	210.8	220.8	233.2	247.8	263.0	284.0	311.1	347.6	391.6
55°	170.1	176.1	185.8	195.8	206.8	220.8	235.4	253.1	276.4	307.0	342.7
57.5°	148.0	155.0	162.6	172.7	183.8	194.6	207.7	223.7	242.1	269.8	300.3
60°	135.5	140.9	147.2	157.5	167.8	177.5	190.1	203.5	220.8	244.8	270.7
62.5°	121.7	126.7	132.5	141.5	151.6	160.4	171.5	185.7	200.3	222.1	244.9
65°	98.5	105.9	111.6	119.6	127.9	137.2	145.9	157.2	170.1	187.4	207.8
67.5°	81.7	85.4	90.7	98.0	106.5	114.5	122.7	131.5	142.8	156.1	172.3
70°	74.3	75.6	76.6	83.6	91.6	99.6	107.2	115.6	125.2	136.2	150.2
72.5°	65.5	66.8	68.0	71.1	77.5	85.4	93.4	99.6	108.7	117.8	129.1
75°	52.0	53.9	54.9	56.6	58.9	64.3	71.6	77.6	82.9	89.9	98.9
77.5°	39.6	40.7	41.7	43.5	44.9	47.4	51.5	57.0	62.0	66.0	72.2
80°	31.3	31.7	33.0	33.6	35.7	37.3	39.3	43.6	48.6	50.3	54.6
82.5°	23.5	23.9	25.0	25.7	26.6	28.0	30.5	31.7	35.6	37.7	40.5
85°	13.0	12.7	13.6	13.6	14.4	15.0	15.7	17.3	18.3	21.0	21.7
87.5°	7.3	7.5	7.6	7.0	6.3	6.3	6.2	6.3	6.7	7.0	7.8
90°	16.8	17.3	16.8	13.7	10.2	7.7	6.1	5.1	4.1	2.1	0.5
92.5°	55.8	66.1	65.2	50.7	34.6	23.1	18.3	14.9	12.6	8.9	6.2
95°	174.4	199.4	176.5	117.4	73.2	49.8	37.6	29.5	24.9	19.8	17.8
97.5°	357.0	340.3	256.3	158.3	96.7	67.2	53.4	44.1	37.1	31.7	29.0
100°	474.9	401.7	276.6	166.8	104.8	77.8	63.6	53.4	45.3	40.7	39.1
102.5°	518.9	403.8	268.9	167.2	112.1	87.1	72.9	62.3	54.2	49.7	48.5
105°	512.1	376.8	253.8	169.9	124.6	100.7	86.4	75.3	67.6	64.1	62.1
107.5°	467.4	347.9	246.2	176.8	137.4	114.2	99.9	88.8	81.8	78.3	76.7
110°	439.3	334.1	244.6	182.5	146.0	123.6	108.8	98.2	91.6	88.5	86.4



TEST NUMBER: P331653-940

CATALOG NUMBER: SA2XXRDIP-C485D530U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	419.8	325.1	245.0	188.7	154.1	132.5	117.3	107.1	100.9	97.5	95.4
115°	395.7	315.3	247.2	197.8	166.8	144.9	131.2	121.0	114.9	111.9	109.3
117.5°	380.4	310.5	250.8	207.6	178.5	158.3	144.0	134.3	128.9	125.8	123.8
120°	372.3	307.6	253.2	214.1	186.6	166.8	152.6	142.4	137.8	134.7	132.7
122.5°	365.3	306.0	256.1	219.8	194.4	175.8	161.1	151.0	146.0	142.9	141.2
125°	355.4	303.1	260.4	228.8	206.0	187.6	173.4	163.3	157.1	154.1	152.6
127.5°	346.3	301.4	264.7	237.3	216.8	198.9	184.3	174.5	167.8	163.5	161.5
130°	340.2	300.5	268.0	242.5	223.3	205.5	191.2	181.0	173.9	168.8	166.8
132.5°	335.3	300.1	271.3	247.9	228.9	212.0	197.7	187.2	179.6	174.2	171.7
135°	328.5	299.5	275.1	254.8	237.0	220.7	206.4	194.7	187.2	181.0	179.0
137.5°	323.7	299.4	278.6	260.0	243.5	227.4	214.2	202.6	194.5	188.3	185.9
140°	320.9	299.0	280.2	262.9	247.2	231.9	218.6	207.5	199.4	193.2	191.2
142.5°	318.1	299.0	281.4	265.4	250.0	235.1	222.7	212.0	203.8	198.1	196.5
145°	314.2	298.0	282.8	268.5	254.2	240.5	229.3	219.2	211.5	206.4	204.5
147.5°	310.4	296.1	283.1	270.3	257.7	244.8	234.9	226.4	219.4	214.5	212.9
150°	307.2	295.0	282.8	271.1	259.3	247.6	238.5	230.9	224.3	220.2	218.6
152.5°	304.3	292.9	282.0	271.4	261.0	250.5	242.2	235.0	229.2	225.1	224.4
155°	299.0	289.4	280.7	272.1	263.4	254.8	247.2	241.6	235.9	232.9	232.4
157.5°	294.0	285.7	278.4	272.1	265.1	257.8	251.5	246.9	242.1	239.6	239.1
160°	290.3	283.3	277.1	272.1	266.0	259.8	254.2	250.2	246.1	244.1	243.6
162.5°	287.1	281.2	275.9	271.6	266.4	261.1	256.7	253.1	249.8	247.7	248.1
165°	281.7	277.1	273.6	270.5	267.0	262.4	259.3	256.8	253.8	252.7	253.2
167.5°	276.4	273.6	271.3	269.8	266.9	263.5	261.6	259.8	257.8	256.9	257.5
170°	273.6	271.5	270.0	269.0	266.4	263.9	262.4	261.4	259.8	259.3	260.4
172.5°	270.7	269.1	268.4	267.8	266.1	264.3	263.2	262.6	261.1	261.4	262.0
175°	267.0	266.4	266.0	266.4	265.5	264.4	263.9	263.9	262.9	263.4	263.9
177.5°	264.8	264.4	264.8	265.6	264.8	264.4	264.4	264.4	263.6	264.0	264.8
180°	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4



TEST NUMBER: P331653-940

CATALOG NUMBER: SA2XXRDIP-C485D530U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4
2.5°	963.9	964.7	970.1	972.5	977.3	979.2	981.2	980.7	980.7	981.8	989.3
5°	966.0	972.7	982.7	992.3	1001.7	1009.7	1014.9	1020.3	1022.3	1032.0	1040.6
7.5°	962.6	974.8	991.3	1006.0	1023.7	1037.5	1048.9	1059.3	1066.3	1080.4	1094.8
10°	958.1	975.4	994.0	1013.0	1037.3	1055.6	1074.2	1088.6	1093.2	1114.2	1126.2
12.5°	949.0	972.1	995.9	1020.5	1044.2	1069.4	1089.9	1104.3	1120.7	1139.5	1161.6
15°	935.4	962.1	993.0	1024.7	1058.6	1089.2	1111.3	1136.2	1154.1	1174.8	1194.1
17.5°	915.9	950.2	989.5	1026.2	1065.4	1098.3	1128.6	1152.5	1165.2	1177.0	1179.9
20°	900.4	937.4	983.6	1027.0	1066.2	1104.2	1134.2	1154.1	1157.5	1157.8	1140.1
22.5°	883.7	925.4	973.8	1018.2	1065.1	1107.4	1130.7	1139.2	1126.1	1103.5	1069.3
25°	852.8	901.1	957.3	1008.0	1059.3	1099.2	1107.2	1092.3	1046.0	997.3	935.8
27.5°	819.4	873.6	934.0	990.2	1044.9	1069.7	1052.4	998.4	915.0	842.6	754.7
30°	794.9	855.8	915.1	978.0	1028.6	1039.3	999.7	920.1	822.9	713.6	626.1
32.5°	766.9	830.7	895.9	961.0	1003.4	992.9	927.5	829.5	715.5	608.1	525.3
35°	726.9	792.9	863.1	928.4	955.4	910.4	812.5	685.0	568.5	468.2	411.3
37.5°	680.8	752.6	825.6	885.6	883.7	808.7	675.4	543.7	445.8	386.5	345.9
40°	648.0	720.6	799.5	850.2	828.5	730.9	586.4	462.2	390.6	343.3	313.7
42.5°	616.6	689.5	767.9	808.1	770.4	650.5	506.5	409.2	350.1	313.3	289.2
45°	563.1	640.0	712.7	734.9	667.6	535.5	409.6	339.0	299.7	272.4	255.7
47.5°	510.9	586.5	652.7	653.2	562.1	434.3	345.5	293.4	259.8	238.7	226.6
50°	478.8	550.8	606.4	597.7	494.5	386.3	309.0	264.0	236.1	219.8	207.1
52.5°	442.9	512.6	560.8	536.2	437.2	339.9	276.3	238.5	215.3	201.2	189.8
55°	390.6	452.5	486.5	449.2	356.7	282.7	233.4	203.8	186.5	174.5	164.9
57.5°	339.3	390.3	411.7	368.3	293.7	234.4	197.4	175.2	158.0	149.5	144.5
60°	307.0	350.6	365.6	317.7	255.4	205.1	174.9	154.2	141.5	135.9	130.9
62.5°	275.4	310.9	317.2	273.2	222.7	179.6	153.6	136.1	127.7	122.3	117.5
65°	228.5	254.0	251.1	215.8	176.1	142.5	123.5	112.9	106.6	98.9	90.6
67.5°	188.1	203.8	194.3	167.8	134.5	110.8	98.4	90.3	82.5	75.2	73.3
70°	162.5	171.5	161.5	137.2	110.2	92.9	82.9	73.3	68.6	67.0	63.9
72.5°	138.0	141.2	130.4	109.5	89.7	77.0	67.2	61.8	59.3	57.9	55.9
75°	103.5	101.2	91.9	75.6	62.2	53.6	50.6	48.6	47.0	45.7	44.6
77.5°	72.8	69.3	61.0	50.4	43.3	39.2	37.5	36.4	35.6	34.9	33.9
80°	54.6	52.3	44.0	35.9	33.0	30.9	30.0	28.6	28.6	28.0	26.9
82.5°	39.9	37.4	30.1	26.4	24.7	23.5	22.7	21.9	21.7	21.8	21.1
85°	21.0	16.9	15.0	14.4	13.3	12.7	13.0	12.3	12.3	12.3	11.9
87.5°	6.8	5.9	5.8	5.7	6.3	6.9	7.3	7.8	8.3	7.8	8.0
90°	2.1	4.1	5.1	6.1	7.7	10.2	13.7	16.8	17.3	16.8	16.2
92.5°	8.9	12.6	14.9	18.3	23.1	34.6	50.7	65.2	66.1	55.8	44.3
95°	19.8	24.9	29.5	37.6	49.8	73.2	117.4	176.5	199.4	174.4	133.2
97.5°	31.7	37.1	44.1	53.4	67.2	96.7	158.3	256.3	340.3	357.0	310.9
100°	40.7	45.3	53.4	63.6	77.8	104.8	166.8	276.6	401.7	474.9	464.3
102.5°	49.7	54.2	62.3	72.9	87.1	112.1	167.2	268.9	403.8	518.9	564.8
105°	64.1	67.6	75.3	86.4	100.7	124.6	169.9	253.8	376.8	512.1	617.9
107.5°	78.3	81.8	88.8	99.9	114.2	137.4	176.8	246.2	347.9	467.4	579.6
110°	88.5	91.6	98.2	108.8	123.6	146.0	182.5	244.6	334.1	439.3	546.7



TEST NUMBER: P331653-940

CATALOG NUMBER: SA2XXRDIP-C485D530U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	97.5	100.9	107.1	117.3	132.5	154.1	188.7	245.0	325.1	419.8	516.6
115°	111.9	114.9	121.0	131.2	144.9	166.8	197.8	247.2	315.3	395.7	479.6
117.5°	125.8	128.9	134.3	144.0	158.3	178.5	207.6	250.8	310.5	380.4	451.7
120°	134.7	137.8	142.4	152.6	166.8	186.6	214.1	253.2	307.6	372.3	437.8
122.5°	142.9	146.0	151.0	161.1	175.8	194.4	219.8	256.1	306.0	365.3	426.9
125°	154.1	157.1	163.3	173.4	187.6	206.0	228.8	260.4	303.1	355.4	410.9
127.5°	163.5	167.8	174.5	184.3	198.9	216.8	237.3	264.7	301.4	346.3	395.1
130°	168.8	173.9	181.0	191.2	205.5	223.3	242.5	268.0	300.5	340.2	385.0
132.5°	174.2	179.6	187.2	197.7	212.0	228.9	247.9	271.3	300.1	335.3	375.2
135°	181.0	187.2	194.7	206.4	220.7	237.0	254.8	275.1	299.5	328.5	361.6
137.5°	188.3	194.5	202.6	214.2	227.4	243.5	260.0	278.6	299.4	323.7	350.7
140°	193.2	199.4	207.5	218.6	231.9	247.2	262.9	280.2	299.0	320.9	343.8
142.5°	198.1	203.8	212.0	222.7	235.1	250.0	265.4	281.4	299.0	318.1	338.0
145°	206.4	211.5	219.2	229.3	240.5	254.2	268.5	282.8	298.0	314.2	330.0
147.5°	214.5	219.4	226.4	234.9	244.8	257.7	270.3	283.1	296.1	310.4	323.9
150°	220.2	224.3	230.9	238.5	247.6	259.3	271.1	282.8	295.0	307.2	319.3
152.5°	225.1	229.2	235.0	242.2	250.5	261.0	271.4	282.0	292.9	304.3	314.9
155°	232.9	235.9	241.6	247.2	254.8	263.4	272.1	280.7	289.4	299.0	308.7
157.5°	239.6	242.1	246.9	251.5	257.8	265.1	272.1	278.4	285.7	294.0	301.5
160°	244.1	246.1	250.2	254.2	259.8	266.0	272.1	277.1	283.3	290.3	296.9
162.5°	247.7	249.8	253.1	256.7	261.1	266.4	271.6	275.9	281.2	287.1	292.5
165°	252.7	253.8	256.8	259.3	262.4	267.0	270.5	273.6	277.1	281.7	285.8
167.5°	256.9	257.8	259.8	261.6	263.5	266.9	269.8	271.3	273.6	276.4	279.4
170°	259.3	259.8	261.4	262.4	263.9	266.4	269.0	270.0	271.5	273.6	276.2
172.5°	261.4	261.1	262.6	263.2	264.3	266.1	267.8	268.4	269.1	270.7	272.5
175°	263.4	262.9	263.9	263.9	264.4	265.5	266.4	266.0	266.4	267.0	268.5
177.5°	264.0	263.6	264.4	264.4	264.4	264.8	265.6	264.8	264.4	264.8	265.6
180°	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4



TEST NUMBER: P331653-940

CATALOG NUMBER: SA2XXRDIP-C485D530U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	958.4	958.4	958.4	958.4	958.4	958.4	958.4
2.5°	991.9	995.4	997.0	997.0	998.9	998.1	997.3
5°	1048.9	1055.3	1056.6	1062.6	1066.9	1065.6	1066.2
7.5°	1105.6	1115.8	1125.9	1130.4	1131.2	1133.9	1134.9
10°	1140.5	1148.9	1164.5	1162.2	1173.8	1180.4	1169.5
12.5°	1174.1	1185.4	1196.2	1199.2	1205.8	1207.9	1203.5
15°	1204.4	1210.4	1211.1	1209.4	1211.5	1209.8	1203.5
17.5°	1176.1	1166.4	1146.7	1137.3	1129.9	1119.0	1114.6
20°	1129.2	1100.5	1067.3	1053.9	1038.3	1007.6	1014.9
22.5°	1028.0	995.3	962.1	923.1	904.6	875.5	873.8
25°	870.5	814.2	752.2	708.9	683.7	654.7	642.0
27.5°	676.8	605.9	555.2	529.5	506.0	483.1	482.1
30°	549.5	496.1	456.9	434.9	420.6	410.9	413.0
32.5°	463.2	426.6	400.1	381.9	371.3	364.0	363.9
35°	378.6	353.7	336.6	329.0	321.4	316.0	316.4
37.5°	324.0	309.0	299.5	291.1	286.3	283.7	282.2
40°	296.0	283.7	276.4	271.4	267.4	263.8	263.1
42.5°	273.9	263.8	256.4	252.4	248.8	246.1	245.5
45°	243.1	234.8	228.1	223.7	222.1	219.8	219.8
47.5°	216.2	208.0	202.9	200.1	197.2	195.7	195.6
50°	198.1	191.8	187.2	185.5	183.2	182.2	181.8
52.5°	181.9	177.2	173.8	172.7	171.7	170.4	170.6
55°	159.8	157.2	155.9	154.8	153.2	151.1	152.5
57.5°	141.2	139.0	135.4	132.2	130.7	129.3	129.8
60°	128.2	123.5	118.9	115.2	114.2	111.2	111.2
62.5°	111.7	105.1	99.4	97.4	96.4	95.0	94.7
65°	85.9	83.3	81.9	80.6	79.9	79.9	79.3
67.5°	71.2	70.1	68.7	68.3	67.7	67.5	67.2
70°	63.0	61.6	60.9	60.6	59.9	60.3	59.3
72.5°	54.9	53.9	53.8	52.9	52.5	52.5	51.8
75°	43.2	43.2	43.0	42.6	42.0	41.6	42.0
77.5°	33.3	33.3	32.7	32.7	32.6	32.7	32.4
80°	26.7	26.9	26.7	26.3	25.9	26.3	25.9
82.5°	21.0	20.6	20.5	20.4	20.4	20.2	20.2
85°	11.9	12.3	11.9	11.7	11.7	11.7	11.9
87.5°	7.6	7.8	7.8	7.8	7.8	7.8	7.6
90°	15.2	16.2	16.8	16.8	16.8	16.8	16.8
92.5°	38.1	33.8	30.6	30.2	28.6	29.0	28.2
95°	102.2	80.9	69.6	63.0	59.0	57.4	58.0
97.5°	254.4	199.4	162.6	138.3	125.8	118.4	114.1
100°	401.3	331.5	270.0	227.8	206.0	191.2	182.1
102.5°	550.5	499.6	434.4	388.5	351.2	332.8	320.4
105°	675.3	682.0	665.1	633.6	602.1	580.2	573.1
107.5°	666.2	719.1	743.7	747.6	745.9	741.5	732.1
110°	637.7	702.8	744.5	766.3	776.1	780.6	780.1



TEST NUMBER: P331653-940

CATALOG NUMBER: SA2XXRDIP-C485D530U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	604.0	673.5	721.3	751.7	767.9	776.5	779.3
115°	557.9	624.5	676.9	712.9	736.4	749.6	754.1
117.5°	520.4	580.9	630.0	666.8	691.5	705.4	709.3
120°	500.9	554.8	601.1	636.7	660.6	675.3	680.4
122.5°	484.6	535.7	577.5	609.4	632.9	646.0	650.3
125°	463.2	508.0	546.2	575.7	594.9	607.7	611.8
127.5°	442.6	484.7	520.0	545.6	563.7	574.7	578.0
130°	428.7	468.9	502.4	527.4	544.7	554.8	558.8
132.5°	415.7	452.6	484.1	508.6	525.9	535.3	539.0
135°	395.1	428.7	457.2	479.0	495.8	505.0	507.0
137.5°	378.8	405.4	430.3	450.1	464.6	472.6	475.6
140°	368.2	391.6	413.9	430.3	443.4	451.0	454.1
142.5°	358.8	379.0	397.7	413.1	425.2	431.9	432.6
145°	346.8	362.6	377.4	389.5	398.1	403.2	404.7
147.5°	337.1	349.4	360.2	370.2	377.1	380.6	381.5
150°	330.6	341.3	350.4	358.0	364.1	367.1	367.7
152.5°	325.3	334.3	342.2	348.2	353.6	355.8	355.9
155°	316.8	324.4	330.0	335.6	339.2	341.3	340.2
157.5°	308.3	314.7	319.1	323.0	326.0	326.9	326.9
160°	302.6	308.2	311.7	315.3	317.8	318.3	318.3
162.5°	297.3	302.1	304.8	308.4	310.1	310.6	310.2
165°	289.4	292.9	295.0	296.9	299.0	299.0	298.5
167.5°	282.1	284.5	286.4	287.3	288.5	288.4	287.8
170°	277.7	279.7	280.7	281.2	282.8	282.2	281.2
172.5°	273.6	275.2	275.8	276.3	277.1	276.5	275.9
175°	269.0	269.6	270.0	270.0	270.5	270.0	269.0
177.5°	265.6	266.1	266.1	266.1	266.1	265.6	264.8
180°	264.4	264.4	264.4	264.4	264.4	264.4	264.4

(END OF REPORT)