

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331659-940

Luminaire Tested: **SA2XXRDIP-C485D725U940-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331659-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C485D725U940-4F0-1E-UDD-A4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 725 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4181.8 lumens
Efficiency: N/A
Efficacy: 108.9 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331659-940

CATALOG NUMBER: SA2XXRDIP-C485D725U940-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331659-940

CATALOG NUMBER: SA2XXRDIP-C485D725U940-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	95	95	95	95	78	78	78	61	61	61	47	47	47	40				
1	96	92	88	85	87	84	81	78	69	67	65	55	54	52	42	41	41	35				
2	88	81	75	71	80	74	69	65	61	58	55	49	47	45	38	36	35	30				
3	81	72	65	60	73	66	60	55	54	50	47	44	41	39	34	32	31	26				
4	74	64	57	51	67	59	52	47	49	44	40	40	36	34	31	29	27	23				
5	68	57	50	44	62	53	46	41	44	39	35	36	32	30	28	26	24	21				
6	63	52	44	39	57	48	41	36	40	35	31	33	29	26	26	23	22	19				
7	58	47	39	34	53	43	37	32	36	31	28	30	26	24	24	21	19	17				
8	54	43	35	30	50	39	33	28	33	28	25	28	24	21	22	20	18	15				
9	51	39	32	27	46	36	30	26	31	26	22	25	22	19	21	18	16	14				
10	47	36	29	25	43	33	27	23	28	24	20	24	20	18	19	17	15	13				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15474	15474	15474	15474
5°	17280	15571	13807	15571
10°	19174	15462	11968	15462
15°	20117	15234	9429	15234
20°	17438	14899	8158	14899
25°	11437	14439	7285	14439
30°	7700	13882	6594	13882
35°	6236	13180	5947	13180
40°	5545	12416	5503	12416
45°	5019	11520	4912	11520
50°	4567	10630	4549	10630
55°	4293	9647	4236	9647
60°	3591	8741	3549	8741
65°	3030	7939	3435	7939
70°	2799	7091	3238	7091
75°	2620	6170	2994	6170
80°	2408	5077	2659	5077
85°	2205	4020	2353	4020



TEST NUMBER: P331659-940

CATALOG NUMBER: SA2XXRDIP-C485D725U940-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.8	2.2
10°-20°	253.1	6.1
20°-30°	326.2	7.8
30°-40°	310.0	7.4
40°-50°	265.6	6.4
50°-60°	202.2	4.8
60°-70°	127.8	3.1
70°-80°	63.8	1.5
80°-90°	19.9	0.5
90°-100°	144.9	3.5
100°-110°	491.8	11.8
110°-120°	522.5	12.5
120°-130°	430.1	10.3
130°-140°	345.4	8.3
140°-150°	261.0	6.2
150°-160°	183.4	4.4
160°-170°	108.0	2.6
170°-180°	35.1	0.8
0°-30°	670.2	16.0
0°-40°	980.2	23.4
0°-60°	1448.0	34.6
0°-90°	1659.5	39.7
90°-120°	1159.2	27.7
90°-150°	2195.7	52.5
90°-180°	2522.0	60.3
0°-180°	4181.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	958	958	958	958	958	
5°	1066	961	852	961	1066	105
15°	1204	911	564	911	1204	325
25°	642	810	409	810	642	305
35°	316	669	302	669	316	202
45°	220	504	215	504	220	170
55°	152	343	150	343	152	134
65°	79	208	90	208	79	81
75°	42	99	48	99	42	45
85°	12	22	13	22	12	13
90°	23	1	23	1	23	13
95°	80	24	80	24	80	103
105°	786	85	786	85	786	760
115°	1034	150	1034	150	1034	1012
125°	839	209	839	209	839	758
135°	695	245	695	245	695	540
145°	555	280	555	280	555	352
155°	466	318	466	318	466	218
165°	409	347	409	347	409	117
175°	369	362	369	362	369	36
180°	362	362	362	362	362	



TEST NUMBER: P331659-940

CATALOG NUMBER: SA2XXRDIP-C485D725U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4
2.5°	997.3	998.1	998.9	997.0	997.0	995.4	991.9	989.3	981.8	980.7	980.7
5°	1066.2	1065.6	1066.9	1062.6	1056.6	1055.3	1048.9	1040.6	1032.0	1022.3	1020.3
7.5°	1134.9	1133.9	1131.2	1130.4	1125.9	1115.8	1105.6	1094.8	1080.4	1066.3	1059.3
10°	1169.5	1180.4	1173.8	1162.2	1164.5	1148.9	1140.5	1126.2	1114.2	1093.2	1088.6
12.5°	1203.5	1207.9	1205.8	1199.2	1196.2	1185.4	1174.1	1161.6	1139.5	1120.7	1104.3
15°	1203.5	1209.8	1211.5	1209.4	1211.1	1210.4	1204.4	1194.1	1174.8	1154.1	1136.2
17.5°	1114.6	1119.0	1129.9	1137.3	1146.7	1166.4	1176.1	1179.9	1177.0	1165.2	1152.5
20°	1014.9	1007.6	1038.3	1053.9	1067.3	1100.5	1129.2	1140.1	1157.8	1157.5	1154.1
22.5°	873.8	875.5	904.6	923.1	962.1	995.3	1028.0	1069.3	1103.5	1126.1	1139.2
25°	642.0	654.7	683.7	708.9	752.2	814.2	870.5	935.8	997.3	1046.0	1092.3
27.5°	482.1	483.1	506.0	529.5	555.2	605.9	676.8	754.7	842.6	915.0	998.4
30°	413.0	410.9	420.6	434.9	456.9	496.1	549.5	626.1	713.6	822.9	920.1
32.5°	363.9	364.0	371.3	381.9	400.1	426.6	463.2	525.3	608.1	715.5	829.5
35°	316.4	316.0	321.4	329.0	336.6	353.7	378.6	411.3	468.2	568.5	685.0
37.5°	282.2	283.7	286.3	291.1	299.5	309.0	324.0	345.9	386.5	445.8	543.7
40°	263.1	263.8	267.4	271.4	276.4	283.7	296.0	313.7	343.3	390.6	462.2
42.5°	245.5	246.1	248.8	252.4	256.4	263.8	273.9	289.2	313.3	350.1	409.2
45°	219.8	219.8	222.1	223.7	228.1	234.8	243.1	255.7	272.4	299.7	339.0
47.5°	195.6	195.7	197.2	200.1	202.9	208.0	216.2	226.6	238.7	259.8	293.4
50°	181.8	182.2	183.2	185.5	187.2	191.8	198.1	207.1	219.8	236.1	264.0
52.5°	170.6	170.4	171.7	172.7	173.8	177.2	181.9	189.8	201.2	215.3	238.5
55°	152.5	151.1	153.2	154.8	155.9	157.2	159.8	164.9	174.5	186.5	203.8
57.5°	129.8	129.3	130.7	132.2	135.4	139.0	141.2	144.5	149.5	158.0	175.2
60°	111.2	111.2	114.2	115.2	118.9	123.5	128.2	130.9	135.9	141.5	154.2
62.5°	94.7	95.0	96.4	97.4	99.4	105.1	111.7	117.5	122.3	127.7	136.1
65°	79.3	79.9	79.9	80.6	81.9	83.3	85.9	90.6	98.9	106.6	112.9
67.5°	67.2	67.5	67.7	68.3	68.7	70.1	71.2	73.3	75.2	82.5	90.3
70°	59.3	60.3	59.9	60.6	60.9	61.6	63.0	63.9	67.0	68.6	73.3
72.5°	51.8	52.5	52.5	52.9	53.8	53.9	54.9	55.9	57.9	59.3	61.8
75°	42.0	41.6	42.0	42.6	43.0	43.2	43.2	44.6	45.7	47.0	48.6
77.5°	32.4	32.7	32.6	32.7	32.7	33.3	33.3	33.9	34.9	35.6	36.4
80°	25.9	26.3	25.9	26.3	26.7	26.9	26.7	26.9	28.0	28.6	28.6
82.5°	20.2	20.2	20.4	20.4	20.5	20.6	21.0	21.1	21.8	21.7	21.9
85°	11.9	11.7	11.7	11.7	11.9	12.3	11.9	11.9	12.3	12.3	12.3
87.5°	8.8	9.1	9.1	9.1	9.1	9.0	8.7	9.3	9.1	9.5	9.1
90°	23.0	23.0	23.0	23.0	23.0	22.3	21.0	22.3	23.0	23.7	23.0
92.5°	38.6	39.8	39.1	41.4	42.0	46.3	52.2	60.8	76.5	90.6	89.3
95°	79.5	78.7	80.9	86.4	95.5	110.8	140.1	182.6	239.1	273.2	241.9
97.5°	156.4	162.3	172.5	189.6	222.9	273.2	348.7	426.1	489.4	466.5	351.3
100°	249.5	262.1	282.3	312.3	370.1	454.5	550.0	636.4	651.0	550.6	379.2
102.5°	439.2	456.1	481.3	532.5	595.4	684.7	754.7	774.2	711.2	553.5	368.6
105°	785.6	795.3	825.3	868.5	911.8	934.8	925.7	846.9	702.0	516.5	347.9
107.5°	1003.4	1016.5	1022.4	1024.8	1019.4	985.6	913.1	794.5	640.7	476.9	337.5
110°	1069.3	1070.0	1063.7	1050.4	1020.5	963.3	874.1	749.3	602.3	458.0	335.3



TEST NUMBER: P331659-940

CATALOG NUMBER: SA2XXRDIP-C485D725U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1068.2	1064.4	1052.6	1030.4	988.7	923.2	827.8	708.1	575.5	445.7	335.8
115°	1033.8	1027.4	1009.3	977.2	927.7	856.0	764.6	657.3	542.3	432.2	338.8
117.5°	972.2	967.0	947.9	914.0	863.5	796.2	713.4	619.1	521.4	425.6	343.8
120°	932.6	925.7	905.4	872.7	823.9	760.5	686.6	600.1	510.2	421.7	347.1
122.5°	891.4	885.6	867.5	835.4	791.6	734.2	664.3	585.1	500.8	419.5	351.1
125°	838.6	832.9	815.6	789.1	748.6	696.3	635.0	563.2	487.2	415.4	356.9
127.5°	792.3	787.8	772.8	748.0	712.7	664.4	606.5	541.6	474.7	413.0	362.9
130°	766.1	760.5	746.5	722.8	688.7	642.7	587.6	527.6	466.4	412.0	367.4
132.5°	738.7	733.7	720.9	697.2	663.6	620.4	569.8	514.2	459.7	411.4	371.8
135°	695.0	692.1	679.7	656.7	626.6	587.6	541.6	495.6	450.3	410.5	377.1
137.5°	652.0	647.8	636.9	617.1	589.7	555.7	519.2	480.7	443.7	410.5	381.8
140°	622.5	618.3	607.8	589.7	567.4	536.7	504.7	471.2	439.9	409.8	384.1
142.5°	592.9	592.1	582.7	566.3	545.1	519.4	491.9	463.4	436.0	409.8	385.8
145°	554.8	552.8	545.8	534.0	517.2	497.0	475.4	452.4	430.8	408.5	387.5
147.5°	522.9	521.7	516.9	507.5	493.7	478.8	462.0	443.9	425.5	406.0	388.2
150°	504.0	503.3	499.1	490.7	480.3	467.7	453.1	437.7	421.0	404.3	387.5
152.5°	487.8	487.7	484.6	477.3	469.1	458.3	445.9	431.6	417.1	401.5	386.5
155°	466.4	467.7	464.9	460.0	452.4	444.7	434.3	423.1	409.8	396.6	384.8
157.5°	448.1	448.1	446.8	442.7	437.3	431.3	422.6	413.2	403.1	391.6	381.6
160°	436.3	436.3	435.7	432.2	427.3	422.4	414.7	407.1	398.1	388.3	379.9
162.5°	425.2	425.8	425.1	422.7	417.9	414.0	407.5	400.9	393.5	385.5	378.3
165°	409.2	409.8	409.8	407.1	404.3	401.5	396.6	391.7	386.2	379.9	375.1
167.5°	394.4	395.2	395.4	393.9	392.6	390.0	386.7	383.0	378.9	375.1	371.8
170°	385.5	386.8	387.5	385.5	384.8	383.3	380.6	378.5	375.1	372.2	370.1
172.5°	378.3	379.1	379.8	378.8	378.1	377.3	375.1	373.4	371.1	368.9	367.9
175°	368.7	370.1	370.9	370.1	370.1	369.4	368.7	368.0	366.0	365.2	364.5
177.5°	363.0	364.2	364.7	364.7	364.7	364.7	364.2	364.2	363.0	362.5	363.0
180°	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5



TEST NUMBER: P331659-940

CATALOG NUMBER: SA2XXRDIP-C485D725U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4
2.5°	981.2	979.2	977.3	972.5	970.1	964.7	963.9	963.7	956.8	950.1	948.2
5°	1014.9	1009.7	1001.7	992.3	982.7	972.7	966.0	960.7	947.4	934.7	927.4
7.5°	1048.9	1037.5	1023.7	1006.0	991.3	974.8	962.6	951.5	932.6	914.5	902.3
10°	1074.2	1055.6	1037.3	1013.0	994.0	975.4	958.1	943.1	921.8	897.8	880.7
12.5°	1089.9	1069.4	1044.2	1020.5	995.9	972.1	949.0	929.7	904.7	879.9	859.7
15°	1111.3	1089.2	1058.6	1024.7	993.0	962.1	935.4	911.4	878.8	849.2	824.5
17.5°	1128.6	1098.3	1065.4	1026.2	989.5	950.2	915.9	885.2	848.9	813.2	784.2
20°	1134.2	1104.2	1066.2	1027.0	983.6	937.4	900.4	867.1	828.1	789.2	755.9
22.5°	1130.7	1107.4	1065.1	1018.2	973.8	925.4	883.7	845.0	801.8	762.1	723.4
25°	1107.2	1099.2	1059.3	1008.0	957.3	901.1	852.8	810.5	761.3	718.6	676.6
27.5°	1052.4	1069.7	1044.9	990.2	934.0	873.6	819.4	771.2	720.1	672.1	630.3
30°	999.7	1039.3	1028.6	978.0	915.1	855.8	794.9	744.6	690.0	640.7	599.4
32.5°	927.5	992.9	1003.4	961.0	895.9	830.7	766.9	716.8	659.9	607.9	567.7
35°	812.5	910.4	955.4	928.4	863.1	792.9	726.9	668.7	611.4	560.1	520.1
37.5°	675.4	808.7	883.7	885.6	825.6	752.6	680.8	622.9	564.3	514.0	470.7
40°	586.4	730.9	828.5	850.2	799.5	720.6	648.0	589.1	531.8	482.5	432.9
42.5°	506.5	650.5	770.4	808.1	767.9	689.5	616.6	555.0	499.3	452.6	402.0
45°	409.6	535.5	667.6	734.9	712.7	640.0	563.1	504.5	452.2	411.9	363.3
47.5°	345.5	434.3	562.1	653.2	652.7	586.5	510.9	454.7	406.2	368.5	329.0
50°	309.0	386.3	494.5	597.7	606.4	550.8	478.8	423.2	378.0	338.3	306.7
52.5°	276.3	339.9	437.2	536.2	560.8	512.6	442.9	391.6	347.6	311.1	284.0
55°	233.4	282.7	356.7	449.2	486.5	452.5	390.6	342.7	307.0	276.4	253.1
57.5°	197.4	234.4	293.7	368.3	411.7	390.3	339.3	300.3	269.8	242.1	223.7
60°	174.9	205.1	255.4	317.7	365.6	350.6	307.0	270.7	244.8	220.8	203.5
62.5°	153.6	179.6	222.7	273.2	317.2	310.9	275.4	244.9	222.1	200.3	185.7
65°	123.5	142.5	176.1	215.8	251.1	254.0	228.5	207.8	187.4	170.1	157.2
67.5°	98.4	110.8	134.5	167.8	194.3	203.8	188.1	172.3	156.1	142.8	131.5
70°	82.9	92.9	110.2	137.2	161.5	171.5	162.5	150.2	136.2	125.2	115.6
72.5°	67.2	77.0	89.7	109.5	130.4	141.2	138.0	129.1	117.8	108.7	99.6
75°	50.6	53.6	62.2	75.6	91.9	101.2	103.5	98.9	89.9	82.9	77.6
77.5°	37.5	39.2	43.3	50.4	61.0	69.3	72.8	72.2	66.0	62.0	57.0
80°	30.0	30.9	33.0	35.9	44.0	52.3	54.6	54.6	50.3	48.6	43.6
82.5°	22.7	23.5	24.7	26.4	30.1	37.4	39.9	40.5	37.7	35.6	31.7
85°	13.0	12.7	13.3	14.4	15.0	16.9	21.0	21.7	21.0	18.3	17.3
87.5°	8.3	7.6	6.9	6.2	6.2	6.2	7.0	7.8	7.2	7.0	6.7
90°	18.8	13.9	10.4	8.4	7.0	5.6	2.8	0.7	2.8	5.6	7.0
92.5°	69.6	47.4	31.7	25.1	20.3	17.3	12.3	8.5	12.3	17.3	20.3
95°	161.0	100.4	68.3	51.5	40.4	34.2	27.2	24.4	27.2	34.2	40.4
97.5°	217.0	132.4	92.1	73.2	60.4	50.9	43.5	39.8	43.5	50.9	60.4
100°	228.6	143.6	106.6	87.1	73.2	62.1	55.7	53.7	55.7	62.1	73.2
102.5°	229.2	153.6	119.5	100.0	85.4	74.3	68.0	66.5	68.0	74.3	85.4
105°	232.8	170.8	138.0	118.5	103.2	92.7	87.8	85.1	87.8	92.7	103.2
107.5°	242.5	188.3	156.6	136.9	121.7	112.1	107.4	105.1	107.4	112.1	121.7
110°	250.2	200.0	169.4	149.2	134.6	125.5	121.3	118.5	121.3	125.5	134.6



TEST NUMBER: P331659-940

CATALOG NUMBER: SA2XXRDIP-C485D725U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	258.6	211.2	181.6	160.9	146.8	138.3	133.6	130.7	133.6	138.3	146.8
115°	271.2	228.6	198.7	179.9	165.9	157.6	153.4	149.9	153.4	157.6	165.9
117.5°	284.5	244.7	217.0	197.4	184.0	176.6	172.5	169.7	172.5	176.6	184.0
120°	293.5	255.8	228.6	209.1	195.2	188.9	184.8	181.9	184.8	188.9	195.2
122.5°	301.3	266.4	240.9	220.8	206.9	200.0	195.9	193.7	195.9	200.0	206.9
125°	313.7	282.3	257.2	237.7	223.7	215.3	211.2	209.1	211.2	215.3	223.7
127.5°	325.2	297.1	272.7	252.6	239.2	230.1	224.2	221.4	224.2	230.1	239.2
130°	332.5	306.0	281.6	262.1	248.2	238.4	231.4	228.6	231.4	238.4	248.2
132.5°	339.7	313.8	290.5	271.0	256.5	246.2	238.7	235.3	238.7	246.2	256.5
135°	349.2	324.9	302.6	283.0	267.0	256.5	248.2	245.4	248.2	256.5	267.0
137.5°	356.5	333.8	311.7	293.6	277.7	266.5	258.2	254.9	258.2	266.5	277.7
140°	360.3	338.8	317.9	299.7	284.4	273.2	264.8	262.1	264.8	273.2	284.4
142.5°	363.7	342.7	322.4	305.3	290.5	279.4	271.6	269.3	271.6	279.4	290.5
145°	368.0	348.6	329.7	314.3	300.4	290.0	283.0	280.2	283.0	290.0	300.4
147.5°	370.4	353.3	335.6	321.9	310.3	300.7	294.0	291.9	294.0	300.7	310.3
150°	371.5	355.5	339.5	326.9	316.5	307.4	301.8	299.7	301.8	307.4	316.5
152.5°	372.1	357.8	343.4	331.9	322.0	314.1	308.5	307.6	308.5	314.1	322.0
155°	372.9	361.1	349.2	338.8	331.1	323.4	319.2	318.5	319.2	323.4	331.1
157.5°	372.9	363.5	353.4	344.6	338.5	331.8	328.4	327.8	328.4	331.8	338.5
160°	372.9	364.5	356.1	348.6	343.0	337.3	334.6	333.9	334.6	337.3	343.0
162.5°	372.4	365.2	357.8	351.9	346.9	342.4	339.6	340.0	339.6	342.4	346.9
165°	370.9	366.0	359.7	355.5	352.0	347.9	346.4	347.1	346.4	347.9	352.0
167.5°	369.9	365.8	361.2	358.6	356.1	353.4	352.1	353.0	352.1	353.4	356.1
170°	368.7	365.2	361.8	359.7	358.3	356.1	355.5	356.9	355.5	356.1	358.3
172.5°	367.0	364.7	362.3	360.8	360.0	357.8	358.3	359.1	358.3	357.8	360.0
175°	365.2	363.8	362.5	361.8	361.8	360.3	361.1	361.8	361.1	360.3	361.8
177.5°	364.2	363.0	362.5	362.5	362.5	361.3	361.9	363.0	361.9	361.3	362.5
180°	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5



TEST NUMBER: P331659-940

CATALOG NUMBER: SA2XXRDIP-C485D725U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4
2.5°	944.8	942.9	939.4	934.2	930.9	925.3	921.6	923.7	924.3	923.7	923.2
5°	919.4	912.4	902.8	893.4	884.8	875.5	870.1	867.8	863.1	860.5	859.2
7.5°	888.7	876.6	863.0	846.8	832.9	818.5	811.1	807.4	797.9	792.7	788.2
10°	865.8	846.8	833.1	811.8	798.9	779.9	766.9	767.2	754.2	746.9	741.5
12.5°	840.5	819.7	796.9	777.8	759.7	744.5	728.8	722.5	708.6	701.6	687.2
15°	798.5	774.2	750.3	724.2	706.0	682.3	659.7	632.0	609.8	590.4	585.1
17.5°	752.7	722.6	698.6	668.1	636.7	596.9	570.7	554.6	541.2	531.0	523.4
20°	721.3	690.6	665.0	619.0	576.8	549.7	530.5	518.2	504.2	493.2	487.1
22.5°	688.2	656.3	621.3	570.0	537.1	515.4	498.2	484.0	474.6	466.0	460.6
25°	641.3	606.4	548.8	513.4	486.9	464.2	452.2	443.5	433.5	421.9	416.6
27.5°	591.8	536.2	494.8	468.6	443.2	428.5	417.7	404.7	395.8	390.6	385.0
30°	554.7	499.2	466.9	438.2	420.3	403.9	391.3	384.0	375.3	366.3	362.7
32.5°	513.4	469.0	438.1	414.3	396.0	382.1	372.1	360.3	354.0	348.5	340.8
35°	462.2	428.6	400.3	380.9	363.6	352.3	340.6	333.7	322.4	317.7	314.7
37.5°	418.7	389.6	368.5	348.1	334.4	321.9	314.8	303.6	298.7	292.2	285.9
40°	394.2	365.6	345.4	328.7	313.3	304.0	295.1	286.1	278.7	275.7	268.0
42.5°	369.3	345.9	325.6	307.4	297.1	287.2	275.9	269.3	261.6	256.8	252.1
45°	334.7	314.1	296.7	281.7	270.4	260.1	252.7	241.7	237.5	227.7	223.7
47.5°	304.3	285.1	268.6	254.3	243.3	236.6	225.9	217.2	210.4	204.4	199.3
50°	282.7	266.7	250.7	238.1	228.1	218.5	207.5	203.1	192.4	189.5	186.5
52.5°	263.0	247.8	233.2	220.8	210.8	201.4	191.7	186.1	178.9	175.8	173.7
55°	235.4	220.8	206.8	195.8	185.8	176.1	170.1	163.2	159.8	157.5	154.8
57.5°	207.7	194.6	183.8	172.7	162.6	155.0	148.0	143.8	140.4	137.3	134.1
60°	190.1	177.5	167.8	157.5	147.2	140.9	135.5	130.5	126.5	121.9	120.6
62.5°	171.5	160.4	151.6	141.5	132.5	126.7	121.7	117.0	112.2	105.4	103.5
65°	145.9	137.2	127.9	119.6	111.6	105.9	98.5	93.3	91.2	90.6	90.2
67.5°	122.7	114.5	106.5	98.0	90.7	85.4	81.7	80.9	79.5	79.1	78.2
70°	107.2	99.6	91.6	83.6	76.6	75.6	74.3	72.9	71.2	70.6	69.9
72.5°	93.4	85.4	77.5	71.1	68.0	66.8	65.5	64.1	63.0	62.3	62.0
75°	71.6	64.3	58.9	56.6	54.9	53.9	52.0	50.9	50.3	49.3	49.0
77.5°	51.5	47.4	44.9	43.5	41.7	40.7	39.6	38.5	37.8	37.6	37.1
80°	39.3	37.3	35.7	33.6	33.0	31.7	31.3	30.3	30.7	29.6	29.6
82.5°	30.5	28.0	26.6	25.7	25.0	23.9	23.5	23.1	23.2	22.5	22.5
85°	15.7	15.0	14.4	13.6	13.6	12.7	13.0	12.7	12.7	11.9	11.7
87.5°	6.8	6.9	7.0	8.0	8.8	8.7	8.6	8.2	7.9	8.2	8.0
90°	8.4	10.4	13.9	18.8	23.0	23.7	23.0	22.3	21.0	22.3	23.0
92.5°	25.1	31.7	47.4	69.6	89.3	90.6	76.5	60.8	52.2	46.3	42.0
95°	51.5	68.3	100.4	161.0	241.9	273.2	239.1	182.6	140.1	110.8	95.5
97.5°	73.2	92.1	132.4	217.0	351.3	466.5	489.4	426.1	348.7	273.2	222.9
100°	87.1	106.6	143.6	228.6	379.2	550.6	651.0	636.4	550.0	454.5	370.1
102.5°	100.0	119.5	153.6	229.2	368.6	553.5	711.2	774.2	754.7	684.7	595.4
105°	118.5	138.0	170.8	232.8	347.9	516.5	702.0	846.9	925.7	934.8	911.8
107.5°	136.9	156.6	188.3	242.5	337.5	476.9	640.7	794.5	913.1	985.6	1019.4
110°	149.2	169.4	200.0	250.2	335.3	458.0	602.3	749.3	874.1	963.3	1020.5



TEST NUMBER: P331659-940

CATALOG NUMBER: SA2XXRDIP-C485D725U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	160.9	181.6	211.2	258.6	335.8	445.7	575.5	708.1	827.8	923.2	988.7
115°	179.9	198.7	228.6	271.2	338.8	432.2	542.3	657.3	764.6	856.0	927.7
117.5°	197.4	217.0	244.7	284.5	343.8	425.6	521.4	619.1	713.4	796.2	863.5
120°	209.1	228.6	255.8	293.5	347.1	421.7	510.2	600.1	686.6	760.5	823.9
122.5°	220.8	240.9	266.4	301.3	351.1	419.5	500.8	585.1	664.3	734.2	791.6
125°	237.7	257.2	282.3	313.7	356.9	415.4	487.2	563.2	635.0	696.3	748.6
127.5°	252.6	272.7	297.1	325.2	362.9	413.0	474.7	541.6	606.5	664.4	712.7
130°	262.1	281.6	306.0	332.5	367.4	412.0	466.4	527.6	587.6	642.7	688.7
132.5°	271.0	290.5	313.8	339.7	371.8	411.4	459.7	514.2	569.8	620.4	663.6
135°	283.0	302.6	324.9	349.2	377.1	410.5	450.3	495.6	541.6	587.6	626.6
137.5°	293.6	311.7	333.8	356.5	381.8	410.5	443.7	480.7	519.2	555.7	589.7
140°	299.7	317.9	338.8	360.3	384.1	409.8	439.9	471.2	504.7	536.7	567.4
142.5°	305.3	322.4	342.7	363.7	385.8	409.8	436.0	463.4	491.9	519.4	545.1
145°	314.3	329.7	348.6	368.0	387.5	408.5	430.8	452.4	475.4	497.0	517.2
147.5°	321.9	335.6	353.3	370.4	388.2	406.0	425.5	443.9	462.0	478.8	493.7
150°	326.9	339.5	355.5	371.5	387.5	404.3	421.0	437.7	453.1	467.7	480.3
152.5°	331.9	343.4	357.8	372.1	386.5	401.5	417.1	431.6	445.9	458.3	469.1
155°	338.8	349.2	361.1	372.9	384.8	396.6	409.8	423.1	434.3	444.7	452.4
157.5°	344.6	353.4	363.5	372.9	381.6	391.6	403.1	413.2	422.6	431.3	437.3
160°	348.6	356.1	364.5	372.9	379.9	388.3	398.1	407.1	414.7	422.4	427.3
162.5°	351.9	357.8	365.2	372.4	378.3	385.5	393.5	400.9	407.5	414.0	417.9
165°	355.5	359.7	366.0	370.9	375.1	379.9	386.2	391.7	396.6	401.5	404.3
167.5°	358.6	361.2	365.8	369.9	371.8	375.1	378.9	383.0	386.7	390.0	392.6
170°	359.7	361.8	365.2	368.7	370.1	372.2	375.1	378.5	380.6	383.3	384.8
172.5°	360.8	362.3	364.7	367.0	367.9	368.9	371.1	373.4	375.1	377.3	378.1
175°	361.8	362.5	363.8	365.2	364.5	365.2	366.0	368.0	368.7	369.4	370.1
177.5°	362.5	362.5	363.0	364.2	363.0	362.5	363.0	364.2	364.2	364.7	364.7
180°	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5



TEST NUMBER: P331659-940
 CATALOG NUMBER: SA2XXRDIP-C485D725U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4
2.5°	920.2	920.8	920.0	920.5	920.0	920.8	920.2	923.2	923.7	924.3	923.7
5°	857.5	853.5	852.8	851.9	852.8	853.5	857.5	859.2	860.5	863.1	867.8
7.5°	782.5	781.9	780.2	777.8	780.2	781.9	782.5	788.2	792.7	797.9	807.4
10°	734.2	732.6	732.3	730.0	732.3	732.6	734.2	741.5	746.9	754.2	767.2
12.5°	677.8	667.1	665.9	660.1	665.9	667.1	677.8	687.2	701.6	708.6	722.5
15°	577.1	575.1	568.5	564.1	568.5	575.1	577.1	585.1	590.4	609.8	632.0
17.5°	519.5	513.0	511.0	510.1	511.0	513.0	519.5	523.4	531.0	541.2	554.6
20°	482.5	476.5	475.5	474.8	475.5	476.5	482.5	487.1	493.2	504.2	518.2
22.5°	456.9	450.7	448.1	446.1	448.1	450.7	456.9	460.6	466.0	474.6	484.0
25°	413.2	410.9	409.6	408.9	409.6	410.9	413.2	416.6	421.9	433.5	443.5
27.5°	379.1	374.0	372.9	371.2	372.9	374.0	379.1	385.0	390.6	395.8	404.7
30°	359.6	357.9	355.6	353.7	355.6	357.9	359.6	362.7	366.3	375.3	384.0
32.5°	336.7	335.4	333.2	332.3	333.2	335.4	336.7	340.8	348.5	354.0	360.3
35°	311.4	306.7	304.7	301.7	304.7	306.7	311.4	314.7	317.7	322.4	333.7
37.5°	284.5	282.0	279.3	280.3	279.3	282.0	284.5	285.9	292.2	298.7	303.6
40°	263.8	262.1	261.4	261.1	261.4	262.1	263.8	268.0	275.7	278.7	286.1
42.5°	247.2	242.6	240.9	240.9	240.9	242.6	247.2	252.1	256.8	261.6	269.3
45°	222.1	217.8	214.8	215.1	214.8	217.8	222.1	223.7	227.7	237.5	241.7
47.5°	196.4	196.3	194.4	195.0	194.4	196.3	196.4	199.3	204.4	210.4	217.2
50°	184.1	182.2	180.8	181.1	180.8	182.2	184.1	186.5	189.5	192.4	203.1
52.5°	172.5	170.7	169.6	171.0	169.6	170.7	172.5	173.7	175.8	178.9	186.1
55°	153.2	151.1	150.9	150.5	150.9	151.1	153.2	154.8	157.5	159.8	163.2
57.5°	131.7	130.4	128.3	127.5	128.3	130.4	131.7	134.1	137.3	140.4	143.8
60°	116.2	113.5	110.2	109.9	110.2	113.5	116.2	120.6	121.9	126.5	130.5
62.5°	102.1	101.6	100.9	100.9	100.9	101.6	102.1	103.5	105.4	112.2	117.0
65°	89.6	89.3	89.6	89.9	89.6	89.3	89.6	90.2	90.6	91.2	93.3
67.5°	78.0	77.5	76.9	77.1	76.9	77.5	78.0	78.2	79.1	79.5	80.9
70°	69.3	68.9	68.6	68.6	68.6	68.9	69.3	69.9	70.6	71.2	72.9
72.5°	60.7	60.6	60.4	60.1	60.4	60.6	60.7	62.0	62.3	63.0	64.1
75°	48.6	48.0	48.0	48.0	48.0	48.0	48.6	49.0	49.3	50.3	50.9
77.5°	37.0	36.7	36.4	36.1	36.4	36.7	37.0	37.1	37.6	37.8	38.5
80°	29.3	29.0	28.6	28.6	28.6	29.0	29.3	29.6	29.6	30.7	30.3
82.5°	22.4	22.0	21.9	21.7	21.9	22.0	22.4	22.5	22.5	23.2	23.1
85°	11.9	12.3	11.9	12.7	11.9	12.3	11.9	11.7	11.9	12.7	12.7
87.5°	8.0	7.8	8.0	7.8	8.0	7.8	8.0	8.0	8.2	7.9	8.2
90°	23.0	23.0	23.0	23.0	23.0	23.0	23.0	23.0	22.3	21.0	22.3
92.5°	41.4	39.1	39.8	38.6	39.8	39.1	41.4	42.0	46.3	52.2	60.8
95°	86.4	80.9	78.7	79.5	78.7	80.9	86.4	95.5	110.8	140.1	182.6
97.5°	189.6	172.5	162.3	156.4	162.3	172.5	189.6	222.9	273.2	348.7	426.1
100°	312.3	282.3	262.1	249.5	262.1	282.3	312.3	370.1	454.5	550.0	636.4
102.5°	532.5	481.3	456.1	439.2	456.1	481.3	532.5	595.4	684.7	754.7	774.2
105°	868.5	825.3	795.3	785.6	795.3	825.3	868.5	911.8	934.8	925.7	846.9
107.5°	1024.8	1022.4	1016.5	1003.4	1016.5	1022.4	1024.8	1019.4	985.6	913.1	794.5
110°	1050.4	1063.7	1070.0	1069.3	1070.0	1063.7	1050.4	1020.5	963.3	874.1	749.3



TEST NUMBER: P331659-940

CATALOG NUMBER: SA2XXRDIP-C485D725U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1030.4	1052.6	1064.4	1068.2	1064.4	1052.6	1030.4	988.7	923.2	827.8	708.1
115°	977.2	1009.3	1027.4	1033.8	1027.4	1009.3	977.2	927.7	856.0	764.6	657.3
117.5°	914.0	947.9	967.0	972.2	967.0	947.9	914.0	863.5	796.2	713.4	619.1
120°	872.7	905.4	925.7	932.6	925.7	905.4	872.7	823.9	760.5	686.6	600.1
122.5°	835.4	867.5	885.6	891.4	885.6	867.5	835.4	791.6	734.2	664.3	585.1
125°	789.1	815.6	832.9	838.6	832.9	815.6	789.1	748.6	696.3	635.0	563.2
127.5°	748.0	772.8	787.8	792.3	787.8	772.8	748.0	712.7	664.4	606.5	541.6
130°	722.8	746.5	760.5	766.1	760.5	746.5	722.8	688.7	642.7	587.6	527.6
132.5°	697.2	720.9	733.7	738.7	733.7	720.9	697.2	663.6	620.4	569.8	514.2
135°	656.7	679.7	692.1	695.0	692.1	679.7	656.7	626.6	587.6	541.6	495.6
137.5°	617.1	636.9	647.8	652.0	647.8	636.9	617.1	589.7	555.7	519.2	480.7
140°	589.7	607.8	618.3	622.5	618.3	607.8	589.7	567.4	536.7	504.7	471.2
142.5°	566.3	582.7	592.1	592.9	592.1	582.7	566.3	545.1	519.4	491.9	463.4
145°	534.0	545.8	552.8	554.8	552.8	545.8	534.0	517.2	497.0	475.4	452.4
147.5°	507.5	516.9	521.7	522.9	521.7	516.9	507.5	493.7	478.8	462.0	443.9
150°	490.7	499.1	503.3	504.0	503.3	499.1	490.7	480.3	467.7	453.1	437.7
152.5°	477.3	484.6	487.7	487.8	487.7	484.6	477.3	469.1	458.3	445.9	431.6
155°	460.0	464.9	467.7	466.4	467.7	464.9	460.0	452.4	444.7	434.3	423.1
157.5°	442.7	446.8	448.1	448.1	448.1	446.8	442.7	437.3	431.3	422.6	413.2
160°	432.2	435.7	436.3	436.3	436.3	435.7	432.2	427.3	422.4	414.7	407.1
162.5°	422.7	425.1	425.8	425.2	425.8	425.1	422.7	417.9	414.0	407.5	400.9
165°	407.1	409.8	409.8	409.2	409.8	409.8	407.1	404.3	401.5	396.6	391.7
167.5°	393.9	395.4	395.2	394.4	395.2	395.4	393.9	392.6	390.0	386.7	383.0
170°	385.5	387.5	386.8	385.5	386.8	387.5	385.5	384.8	383.3	380.6	378.5
172.5°	378.8	379.8	379.1	378.3	379.1	379.8	378.8	378.1	377.3	375.1	373.4
175°	370.1	370.9	370.1	368.7	370.1	370.9	370.1	370.1	369.4	368.7	368.0
177.5°	364.7	364.7	364.2	363.0	364.2	364.7	364.7	364.7	364.7	364.2	364.2
180°	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5



TEST NUMBER: P331659-940

CATALOG NUMBER: SA2XXRDIP-C485D725U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4
2.5°	921.6	925.3	930.9	934.2	939.4	942.9	944.8	948.2	950.1	956.8	963.7
5°	870.1	875.5	884.8	893.4	902.8	912.4	919.4	927.4	934.7	947.4	960.7
7.5°	811.1	818.5	832.9	846.8	863.0	876.6	888.7	902.3	914.5	932.6	951.5
10°	766.9	779.9	798.9	811.8	833.1	846.8	865.8	880.7	897.8	921.8	943.1
12.5°	728.8	744.5	759.7	777.8	796.9	819.7	840.5	859.7	879.9	904.7	929.7
15°	659.7	682.3	706.0	724.2	750.3	774.2	798.5	824.5	849.2	878.8	911.4
17.5°	570.7	596.9	636.7	668.1	698.6	722.6	752.7	784.2	813.2	848.9	885.2
20°	530.5	549.7	576.8	619.0	665.0	690.6	721.3	755.9	789.2	828.1	867.1
22.5°	498.2	515.4	537.1	570.0	621.3	656.3	688.2	723.4	762.1	801.8	845.0
25°	452.2	464.2	486.9	513.4	548.8	606.4	641.3	676.6	718.6	761.3	810.5
27.5°	417.7	428.5	443.2	468.6	494.8	536.2	591.8	630.3	672.1	720.1	771.2
30°	391.3	403.9	420.3	438.2	466.9	499.2	554.7	599.4	640.7	690.0	744.6
32.5°	372.1	382.1	396.0	414.3	438.1	469.0	513.4	567.7	607.9	659.9	716.8
35°	340.6	352.3	363.6	380.9	400.3	428.6	462.2	520.1	560.1	611.4	668.7
37.5°	314.8	321.9	334.4	348.1	368.5	389.6	418.7	470.7	514.0	564.3	622.9
40°	295.1	304.0	313.3	328.7	345.4	365.6	394.2	432.9	482.5	531.8	589.1
42.5°	275.9	287.2	297.1	307.4	325.6	345.9	369.3	402.0	452.6	499.3	555.0
45°	252.7	260.1	270.4	281.7	296.7	314.1	334.7	363.3	411.9	452.2	504.5
47.5°	225.9	236.6	243.3	254.3	268.6	285.1	304.3	329.0	368.5	406.2	454.7
50°	207.5	218.5	228.1	238.1	250.7	266.7	282.7	306.7	338.3	378.0	423.2
52.5°	191.7	201.4	210.8	220.8	233.2	247.8	263.0	284.0	311.1	347.6	391.6
55°	170.1	176.1	185.8	195.8	206.8	220.8	235.4	253.1	276.4	307.0	342.7
57.5°	148.0	155.0	162.6	172.7	183.8	194.6	207.7	223.7	242.1	269.8	300.3
60°	135.5	140.9	147.2	157.5	167.8	177.5	190.1	203.5	220.8	244.8	270.7
62.5°	121.7	126.7	132.5	141.5	151.6	160.4	171.5	185.7	200.3	222.1	244.9
65°	98.5	105.9	111.6	119.6	127.9	137.2	145.9	157.2	170.1	187.4	207.8
67.5°	81.7	85.4	90.7	98.0	106.5	114.5	122.7	131.5	142.8	156.1	172.3
70°	74.3	75.6	76.6	83.6	91.6	99.6	107.2	115.6	125.2	136.2	150.2
72.5°	65.5	66.8	68.0	71.1	77.5	85.4	93.4	99.6	108.7	117.8	129.1
75°	52.0	53.9	54.9	56.6	58.9	64.3	71.6	77.6	82.9	89.9	98.9
77.5°	39.6	40.7	41.7	43.5	44.9	47.4	51.5	57.0	62.0	66.0	72.2
80°	31.3	31.7	33.0	33.6	35.7	37.3	39.3	43.6	48.6	50.3	54.6
82.5°	23.5	23.9	25.0	25.7	26.6	28.0	30.5	31.7	35.6	37.7	40.5
85°	13.0	12.7	13.6	13.6	14.4	15.0	15.7	17.3	18.3	21.0	21.7
87.5°	8.6	8.7	8.8	8.0	7.0	6.9	6.8	6.7	7.0	7.2	7.8
90°	23.0	23.7	23.0	18.8	13.9	10.4	8.4	7.0	5.6	2.8	0.7
92.5°	76.5	90.6	89.3	69.6	47.4	31.7	25.1	20.3	17.3	12.3	8.5
95°	239.1	273.2	241.9	161.0	100.4	68.3	51.5	40.4	34.2	27.2	24.4
97.5°	489.4	466.5	351.3	217.0	132.4	92.1	73.2	60.4	50.9	43.5	39.8
100°	651.0	550.6	379.2	228.6	143.6	106.6	87.1	73.2	62.1	55.7	53.7
102.5°	711.2	553.5	368.6	229.2	153.6	119.5	100.0	85.4	74.3	68.0	66.5
105°	702.0	516.5	347.9	232.8	170.8	138.0	118.5	103.2	92.7	87.8	85.1
107.5°	640.7	476.9	337.5	242.5	188.3	156.6	136.9	121.7	112.1	107.4	105.1
110°	602.3	458.0	335.3	250.2	200.0	169.4	149.2	134.6	125.5	121.3	118.5



TEST NUMBER: P331659-940

CATALOG NUMBER: SA2XXRDIP-C485D725U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	575.5	445.7	335.8	258.6	211.2	181.6	160.9	146.8	138.3	133.6	130.7
115°	542.3	432.2	338.8	271.2	228.6	198.7	179.9	165.9	157.6	153.4	149.9
117.5°	521.4	425.6	343.8	284.5	244.7	217.0	197.4	184.0	176.6	172.5	169.7
120°	510.2	421.7	347.1	293.5	255.8	228.6	209.1	195.2	188.9	184.8	181.9
122.5°	500.8	419.5	351.1	301.3	266.4	240.9	220.8	206.9	200.0	195.9	193.7
125°	487.2	415.4	356.9	313.7	282.3	257.2	237.7	223.7	215.3	211.2	209.1
127.5°	474.7	413.0	362.9	325.2	297.1	272.7	252.6	239.2	230.1	224.2	221.4
130°	466.4	412.0	367.4	332.5	306.0	281.6	262.1	248.2	238.4	231.4	228.6
132.5°	459.7	411.4	371.8	339.7	313.8	290.5	271.0	256.5	246.2	238.7	235.3
135°	450.3	410.5	377.1	349.2	324.9	302.6	283.0	267.0	256.5	248.2	245.4
137.5°	443.7	410.5	381.8	356.5	333.8	311.7	293.6	277.7	266.5	258.2	254.9
140°	439.9	409.8	384.1	360.3	338.8	317.9	299.7	284.4	273.2	264.8	262.1
142.5°	436.0	409.8	385.8	363.7	342.7	322.4	305.3	290.5	279.4	271.6	269.3
145°	430.8	408.5	387.5	368.0	348.6	329.7	314.3	300.4	290.0	283.0	280.2
147.5°	425.5	406.0	388.2	370.4	353.3	335.6	321.9	310.3	300.7	294.0	291.9
150°	421.0	404.3	387.5	371.5	355.5	339.5	326.9	316.5	307.4	301.8	299.7
152.5°	417.1	401.5	386.5	372.1	357.8	343.4	331.9	322.0	314.1	308.5	307.6
155°	409.8	396.6	384.8	372.9	361.1	349.2	338.8	331.1	323.4	319.2	318.5
157.5°	403.1	391.6	381.6	372.9	363.5	353.4	344.6	338.5	331.8	328.4	327.8
160°	398.1	388.3	379.9	372.9	364.5	356.1	348.6	343.0	337.3	334.6	333.9
162.5°	393.5	385.5	378.3	372.4	365.2	357.8	351.9	346.9	342.4	339.6	340.0
165°	386.2	379.9	375.1	370.9	366.0	359.7	355.5	352.0	347.9	346.4	347.1
167.5°	378.9	375.1	371.8	369.9	365.8	361.2	358.6	356.1	353.4	352.1	353.0
170°	375.1	372.2	370.1	368.7	365.2	361.8	359.7	358.3	356.1	355.5	356.9
172.5°	371.1	368.9	367.9	367.0	364.7	362.3	360.8	360.0	357.8	358.3	359.1
175°	366.0	365.2	364.5	365.2	363.8	362.5	361.8	361.8	360.3	361.1	361.8
177.5°	363.0	362.5	363.0	364.2	363.0	362.5	362.5	362.5	361.3	361.9	363.0
180°	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5



TEST NUMBER: P331659-940

CATALOG NUMBER: SA2XXRDIP-C485D725U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4
2.5°	963.9	964.7	970.1	972.5	977.3	979.2	981.2	980.7	980.7	981.8	989.3
5°	966.0	972.7	982.7	992.3	1001.7	1009.7	1014.9	1020.3	1022.3	1032.0	1040.6
7.5°	962.6	974.8	991.3	1006.0	1023.7	1037.5	1048.9	1059.3	1066.3	1080.4	1094.8
10°	958.1	975.4	994.0	1013.0	1037.3	1055.6	1074.2	1088.6	1093.2	1114.2	1126.2
12.5°	949.0	972.1	995.9	1020.5	1044.2	1069.4	1089.9	1104.3	1120.7	1139.5	1161.6
15°	935.4	962.1	993.0	1024.7	1058.6	1089.2	1111.3	1136.2	1154.1	1174.8	1194.1
17.5°	915.9	950.2	989.5	1026.2	1065.4	1098.3	1128.6	1152.5	1165.2	1177.0	1179.9
20°	900.4	937.4	983.6	1027.0	1066.2	1104.2	1134.2	1154.1	1157.5	1157.8	1140.1
22.5°	883.7	925.4	973.8	1018.2	1065.1	1107.4	1130.7	1139.2	1126.1	1103.5	1069.3
25°	852.8	901.1	957.3	1008.0	1059.3	1099.2	1107.2	1092.3	1046.0	997.3	935.8
27.5°	819.4	873.6	934.0	990.2	1044.9	1069.7	1052.4	998.4	915.0	842.6	754.7
30°	794.9	855.8	915.1	978.0	1028.6	1039.3	999.7	920.1	822.9	713.6	626.1
32.5°	766.9	830.7	895.9	961.0	1003.4	992.9	927.5	829.5	715.5	608.1	525.3
35°	726.9	792.9	863.1	928.4	955.4	910.4	812.5	685.0	568.5	468.2	411.3
37.5°	680.8	752.6	825.6	885.6	883.7	808.7	675.4	543.7	445.8	386.5	345.9
40°	648.0	720.6	799.5	850.2	828.5	730.9	586.4	462.2	390.6	343.3	313.7
42.5°	616.6	689.5	767.9	808.1	770.4	650.5	506.5	409.2	350.1	313.3	289.2
45°	563.1	640.0	712.7	734.9	667.6	535.5	409.6	339.0	299.7	272.4	255.7
47.5°	510.9	586.5	652.7	653.2	562.1	434.3	345.5	293.4	259.8	238.7	226.6
50°	478.8	550.8	606.4	597.7	494.5	386.3	309.0	264.0	236.1	219.8	207.1
52.5°	442.9	512.6	560.8	536.2	437.2	339.9	276.3	238.5	215.3	201.2	189.8
55°	390.6	452.5	486.5	449.2	356.7	282.7	233.4	203.8	186.5	174.5	164.9
57.5°	339.3	390.3	411.7	368.3	293.7	234.4	197.4	175.2	158.0	149.5	144.5
60°	307.0	350.6	365.6	317.7	255.4	205.1	174.9	154.2	141.5	135.9	130.9
62.5°	275.4	310.9	317.2	273.2	222.7	179.6	153.6	136.1	127.7	122.3	117.5
65°	228.5	254.0	251.1	215.8	176.1	142.5	123.5	112.9	106.6	98.9	90.6
67.5°	188.1	203.8	194.3	167.8	134.5	110.8	98.4	90.3	82.5	75.2	73.3
70°	162.5	171.5	161.5	137.2	110.2	92.9	82.9	73.3	68.6	67.0	63.9
72.5°	138.0	141.2	130.4	109.5	89.7	77.0	67.2	61.8	59.3	57.9	55.9
75°	103.5	101.2	91.9	75.6	62.2	53.6	50.6	48.6	47.0	45.7	44.6
77.5°	72.8	69.3	61.0	50.4	43.3	39.2	37.5	36.4	35.6	34.9	33.9
80°	54.6	52.3	44.0	35.9	33.0	30.9	30.0	28.6	28.6	28.0	26.9
82.5°	39.9	37.4	30.1	26.4	24.7	23.5	22.7	21.9	21.7	21.8	21.1
85°	21.0	16.9	15.0	14.4	13.3	12.7	13.0	12.3	12.3	12.3	11.9
87.5°	7.0	6.2	6.2	6.2	6.9	7.6	8.3	9.1	9.5	9.1	9.3
90°	2.8	5.6	7.0	8.4	10.4	13.9	18.8	23.0	23.7	23.0	22.3
92.5°	12.3	17.3	20.3	25.1	31.7	47.4	69.6	89.3	90.6	76.5	60.8
95°	27.2	34.2	40.4	51.5	68.3	100.4	161.0	241.9	273.2	239.1	182.6
97.5°	43.5	50.9	60.4	73.2	92.1	132.4	217.0	351.3	466.5	489.4	426.1
100°	55.7	62.1	73.2	87.1	106.6	143.6	228.6	379.2	550.6	651.0	636.4
102.5°	68.0	74.3	85.4	100.0	119.5	153.6	229.2	368.6	553.5	711.2	774.2
105°	87.8	92.7	103.2	118.5	138.0	170.8	232.8	347.9	516.5	702.0	846.9
107.5°	107.4	112.1	121.7	136.9	156.6	188.3	242.5	337.5	476.9	640.7	794.5
110°	121.3	125.5	134.6	149.2	169.4	200.0	250.2	335.3	458.0	602.3	749.3



TEST NUMBER: P331659-940

CATALOG NUMBER: SA2XXRDIP-C485D725U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	133.6	138.3	146.8	160.9	181.6	211.2	258.6	335.8	445.7	575.5	708.1
115°	153.4	157.6	165.9	179.9	198.7	228.6	271.2	338.8	432.2	542.3	657.3
117.5°	172.5	176.6	184.0	197.4	217.0	244.7	284.5	343.8	425.6	521.4	619.1
120°	184.8	188.9	195.2	209.1	228.6	255.8	293.5	347.1	421.7	510.2	600.1
122.5°	195.9	200.0	206.9	220.8	240.9	266.4	301.3	351.1	419.5	500.8	585.1
125°	211.2	215.3	223.7	237.7	257.2	282.3	313.7	356.9	415.4	487.2	563.2
127.5°	224.2	230.1	239.2	252.6	272.7	297.1	325.2	362.9	413.0	474.7	541.6
130°	231.4	238.4	248.2	262.1	281.6	306.0	332.5	367.4	412.0	466.4	527.6
132.5°	238.7	246.2	256.5	271.0	290.5	313.8	339.7	371.8	411.4	459.7	514.2
135°	248.2	256.5	267.0	283.0	302.6	324.9	349.2	377.1	410.5	450.3	495.6
137.5°	258.2	266.5	277.7	293.6	311.7	333.8	356.5	381.8	410.5	443.7	480.7
140°	264.8	273.2	284.4	299.7	317.9	338.8	360.3	384.1	409.8	439.9	471.2
142.5°	271.6	279.4	290.5	305.3	322.4	342.7	363.7	385.8	409.8	436.0	463.4
145°	283.0	290.0	300.4	314.3	329.7	348.6	368.0	387.5	408.5	430.8	452.4
147.5°	294.0	300.7	310.3	321.9	335.6	353.3	370.4	388.2	406.0	425.5	443.9
150°	301.8	307.4	316.5	326.9	339.5	355.5	371.5	387.5	404.3	421.0	437.7
152.5°	308.5	314.1	322.0	331.9	343.4	357.8	372.1	386.5	401.5	417.1	431.6
155°	319.2	323.4	331.1	338.8	349.2	361.1	372.9	384.8	396.6	409.8	423.1
157.5°	328.4	331.8	338.5	344.6	353.4	363.5	372.9	381.6	391.6	403.1	413.2
160°	334.6	337.3	343.0	348.6	356.1	364.5	372.9	379.9	388.3	398.1	407.1
162.5°	339.6	342.4	346.9	351.9	357.8	365.2	372.4	378.3	385.5	393.5	400.9
165°	346.4	347.9	352.0	355.5	359.7	366.0	370.9	375.1	379.9	386.2	391.7
167.5°	352.1	353.4	356.1	358.6	361.2	365.8	369.9	371.8	375.1	378.9	383.0
170°	355.5	356.1	358.3	359.7	361.8	365.2	368.7	370.1	372.2	375.1	378.5
172.5°	358.3	357.8	360.0	360.8	362.3	364.7	367.0	367.9	368.9	371.1	373.4
175°	361.1	360.3	361.8	361.8	362.5	363.8	365.2	364.5	365.2	366.0	368.0
177.5°	361.9	361.3	362.5	362.5	362.5	363.0	364.2	363.0	362.5	363.0	364.2
180°	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5



TEST NUMBER: P331659-940

CATALOG NUMBER: SA2XXRDIP-C485D725U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	958.4	958.4	958.4	958.4	958.4	958.4	958.4
2.5°	991.9	995.4	997.0	997.0	998.9	998.1	997.3
5°	1048.9	1055.3	1056.6	1062.6	1066.9	1065.6	1066.2
7.5°	1105.6	1115.8	1125.9	1130.4	1131.2	1133.9	1134.9
10°	1140.5	1148.9	1164.5	1162.2	1173.8	1180.4	1169.5
12.5°	1174.1	1185.4	1196.2	1199.2	1205.8	1207.9	1203.5
15°	1204.4	1210.4	1211.1	1209.4	1211.5	1209.8	1203.5
17.5°	1176.1	1166.4	1146.7	1137.3	1129.9	1119.0	1114.6
20°	1129.2	1100.5	1067.3	1053.9	1038.3	1007.6	1014.9
22.5°	1028.0	995.3	962.1	923.1	904.6	875.5	873.8
25°	870.5	814.2	752.2	708.9	683.7	654.7	642.0
27.5°	676.8	605.9	555.2	529.5	506.0	483.1	482.1
30°	549.5	496.1	456.9	434.9	420.6	410.9	413.0
32.5°	463.2	426.6	400.1	381.9	371.3	364.0	363.9
35°	378.6	353.7	336.6	329.0	321.4	316.0	316.4
37.5°	324.0	309.0	299.5	291.1	286.3	283.7	282.2
40°	296.0	283.7	276.4	271.4	267.4	263.8	263.1
42.5°	273.9	263.8	256.4	252.4	248.8	246.1	245.5
45°	243.1	234.8	228.1	223.7	222.1	219.8	219.8
47.5°	216.2	208.0	202.9	200.1	197.2	195.7	195.6
50°	198.1	191.8	187.2	185.5	183.2	182.2	181.8
52.5°	181.9	177.2	173.8	172.7	171.7	170.4	170.6
55°	159.8	157.2	155.9	154.8	153.2	151.1	152.5
57.5°	141.2	139.0	135.4	132.2	130.7	129.3	129.8
60°	128.2	123.5	118.9	115.2	114.2	111.2	111.2
62.5°	111.7	105.1	99.4	97.4	96.4	95.0	94.7
65°	85.9	83.3	81.9	80.6	79.9	79.9	79.3
67.5°	71.2	70.1	68.7	68.3	67.7	67.5	67.2
70°	63.0	61.6	60.9	60.6	59.9	60.3	59.3
72.5°	54.9	53.9	53.8	52.9	52.5	52.5	51.8
75°	43.2	43.2	43.0	42.6	42.0	41.6	42.0
77.5°	33.3	33.3	32.7	32.7	32.6	32.7	32.4
80°	26.7	26.9	26.7	26.3	25.9	26.3	25.9
82.5°	21.0	20.6	20.5	20.4	20.4	20.2	20.2
85°	11.9	12.3	11.9	11.7	11.7	11.7	11.9
87.5°	8.7	9.0	9.1	9.1	9.1	9.1	8.8
90°	21.0	22.3	23.0	23.0	23.0	23.0	23.0
92.5°	52.2	46.3	42.0	41.4	39.1	39.8	38.6
95°	140.1	110.8	95.5	86.4	80.9	78.7	79.5
97.5°	348.7	273.2	222.9	189.6	172.5	162.3	156.4
100°	550.0	454.5	370.1	312.3	282.3	262.1	249.5
102.5°	754.7	684.7	595.4	532.5	481.3	456.1	439.2
105°	925.7	934.8	911.8	868.5	825.3	795.3	785.6
107.5°	913.1	985.6	1019.4	1024.8	1022.4	1016.5	1003.4
110°	874.1	963.3	1020.5	1050.4	1063.7	1070.0	1069.3



TEST NUMBER: P331659-940
 CATALOG NUMBER: SA2XXRDIP-C485D725U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	827.8	923.2	988.7	1030.4	1052.6	1064.4	1068.2
115°	764.6	856.0	927.7	977.2	1009.3	1027.4	1033.8
117.5°	713.4	796.2	863.5	914.0	947.9	967.0	972.2
120°	686.6	760.5	823.9	872.7	905.4	925.7	932.6
122.5°	664.3	734.2	791.6	835.4	867.5	885.6	891.4
125°	635.0	696.3	748.6	789.1	815.6	832.9	838.6
127.5°	606.5	664.4	712.7	748.0	772.8	787.8	792.3
130°	587.6	642.7	688.7	722.8	746.5	760.5	766.1
132.5°	569.8	620.4	663.6	697.2	720.9	733.7	738.7
135°	541.6	587.6	626.6	656.7	679.7	692.1	695.0
137.5°	519.2	555.7	589.7	617.1	636.9	647.8	652.0
140°	504.7	536.7	567.4	589.7	607.8	618.3	622.5
142.5°	491.9	519.4	545.1	566.3	582.7	592.1	592.9
145°	475.4	497.0	517.2	534.0	545.8	552.8	554.8
147.5°	462.0	478.8	493.7	507.5	516.9	521.7	522.9
150°	453.1	467.7	480.3	490.7	499.1	503.3	504.0
152.5°	445.9	458.3	469.1	477.3	484.6	487.7	487.8
155°	434.3	444.7	452.4	460.0	464.9	467.7	466.4
157.5°	422.6	431.3	437.3	442.7	446.8	448.1	448.1
160°	414.7	422.4	427.3	432.2	435.7	436.3	436.3
162.5°	407.5	414.0	417.9	422.7	425.1	425.8	425.2
165°	396.6	401.5	404.3	407.1	409.8	409.8	409.2
167.5°	386.7	390.0	392.6	393.9	395.4	395.2	394.4
170°	380.6	383.3	384.8	385.5	387.5	386.8	385.5
172.5°	375.1	377.3	378.1	378.8	379.8	379.1	378.3
175°	368.7	369.4	370.1	370.1	370.9	370.1	368.7
177.5°	364.2	364.7	364.7	364.7	364.7	364.2	363.0
180°	362.5	362.5	362.5	362.5	362.5	362.5	362.5

(END OF REPORT)