

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332518-927

Luminaire Tested: **SA4XXDIP-C350D1035U927-4F0-1E-UDD-A1**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332518-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXDIP-C350D1035U927-4F0-1E-UDD-A1  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 350 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1035 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4088.3 lumens  
Efficiency: N/A  
Efficacy: 109.6 lumens/watt  
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 37.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332518-927

CATALOG NUMBER: SA4XXDIP-C350D1035U927-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P332518-927

CATALOG NUMBER: SA4XXDIP-C350D1035U927-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	38	38	38	31				
1	94	89	86	82	84	80	77	74	64	62	60	48	47	46	34	33	33	26				
2	85	78	72	67	76	70	65	61	56	52	50	42	40	38	30	29	28	22				
3	78	69	62	56	70	62	56	51	49	45	42	38	35	33	27	25	24	19				
4	71	61	53	48	64	55	48	43	44	39	36	34	30	28	24	22	20	16				
5	65	54	46	41	58	49	42	37	39	34	31	30	27	24	22	20	18	14				
6	60	48	41	35	54	44	37	32	35	30	27	27	24	21	20	17	16	13				
7	55	44	36	31	50	40	33	28	32	27	23	25	21	19	18	16	14	11				
8	51	40	32	27	46	36	29	25	29	24	21	23	19	17	16	14	13	10				
9	48	36	29	24	43	33	26	22	27	22	18	21	17	15	15	13	11	9				
10	45	33	26	21	40	30	24	20	24	20	17	19	16	13	14	12	10	8				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	3654	3654	3654	3654
5°	4302	3663	3233	3663
10°	5151	3647	2911	3647
15°	6095	3611	2674	3611
20°	6787	3572	2461	3572
25°	6897	3517	2314	3517
30°	5868	3464	2269	3464
35°	4512	3377	2269	3377
40°	3517	3276	2312	3276
45°	2932	3123	2351	3123
50°	2581	2936	2430	2936
55°	2365	2712	2528	2712
60°	2215	2512	2645	2512
65°	2063	2288	2743	2288
70°	1886	2065	2804	2065
75°	1684	1818	2773	1818
80°	1409	1492	2687	1492
85°	1074	1074	2566	1074



TEST NUMBER: P332518-927

CATALOG NUMBER: SA4XXDIP-C350D1035U927-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	44.1	1.1
10°-20°	135.9	3.3
20°-30°	215.5	5.3
30°-40°	239.8	5.9
40°-50°	218.3	5.3
50°-60°	178.4	4.4
60°-70°	127.4	3.1
70°-80°	70.1	1.7
80°-90°	22.2	0.5
90°-100°	67.4	1.6
100°-110°	199.8	4.9
110°-120°	339.1	8.3
120°-130°	447.1	10.9
130°-140°	502.1	12.3
140°-150°	493.4	12.1
150°-160°	415.0	10.2
160°-170°	276.1	6.8
170°-180°	96.7	2.4
0°-30°	395.5	9.7
0°-40°	635.3	15.5
0°-60°	1032.1	25.2
0°-90°	1251.8	30.6
90°-120°	606.3	14.8
90°-150°	2048.8	50.1
90°-180°	2837.0	69.4
0°-180°	4088.3	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	453	453	453	453	453	
5°	531	452	399	452	531	54
15°	729	432	320	432	729	206
25°	774	395	260	395	774	341
35°	458	343	230	343	458	291
45°	257	274	206	274	257	202
55°	168	193	180	193	168	152
65°	108	120	144	120	108	107
75°	54	58	89	58	54	57
85°	11	12	28	12	11	14
90°	24	2	24	2	24	12
95°	62	48	62	48	62	65
105°	193	184	193	184	193	203
115°	342	345	342	345	342	338
125°	498	502	498	502	498	444
135°	648	648	648	648	648	501
145°	788	787	788	787	788	493
155°	901	901	901	901	901	415
165°	979	981	979	981	979	276
175°	1016	1021	1016	1021	1016	96
180°	1022	1022	1022	1022	1022	



TEST NUMBER: P332518-927

CATALOG NUMBER: SA4XXDIP-C350D1035U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6
2.5°	481.6	481.6	480.1	479.7	478.7	477.4	477.1	474.6	469.8	467.5	467.0
5°	530.9	534.7	529.8	528.9	528.3	522.1	519.0	515.2	506.6	501.5	497.6
7.5°	589.8	590.2	588.0	586.4	581.5	576.2	568.1	559.4	549.1	538.5	530.4
10°	628.4	629.9	627.5	627.2	617.6	611.6	599.6	589.5	577.8	564.9	553.1
12.5°	669.2	667.2	665.9	657.9	656.1	645.2	631.2	620.8	602.9	588.0	572.3
15°	729.3	725.2	722.5	711.5	706.1	690.9	676.0	664.6	641.2	618.9	602.0
17.5°	764.5	768.7	762.6	758.0	744.0	733.3	718.2	694.2	675.9	648.2	626.9
20°	790.0	790.4	787.0	782.4	771.3	757.8	741.3	715.1	693.2	665.6	636.3
22.5°	796.9	797.0	795.6	791.2	782.8	771.9	755.3	733.3	706.8	676.8	647.5
25°	774.3	773.6	775.2	780.1	777.0	773.6	764.0	747.7	722.9	691.3	659.7
27.5°	690.1	695.4	704.9	716.8	728.4	737.2	739.7	736.3	721.0	695.0	661.9
30°	629.5	636.0	643.1	655.1	678.3	691.7	706.2	717.3	711.1	690.3	659.6
32.5°	563.0	564.6	575.1	588.7	610.1	635.6	658.9	681.4	688.8	677.9	652.2
35°	457.8	460.5	471.9	485.4	511.4	542.8	577.7	608.8	634.5	644.8	631.6
37.5°	373.6	381.1	389.2	403.7	426.7	454.9	491.1	531.4	569.7	595.3	599.7
40°	333.7	338.4	344.2	355.3	374.8	402.5	433.6	479.7	520.5	557.2	569.2
42.5°	302.2	305.0	308.6	318.5	333.4	361.0	389.4	430.0	470.8	514.8	534.9
45°	256.8	259.7	265.7	271.5	282.7	301.8	328.3	361.6	402.7	445.0	482.2
47.5°	224.1	225.9	229.4	235.7	245.3	257.9	279.3	307.2	345.2	386.4	426.0
50°	205.5	207.0	209.8	215.4	222.8	234.0	251.6	277.7	307.4	348.9	387.7
52.5°	190.8	191.4	193.5	197.3	203.1	212.5	227.0	248.6	276.3	313.2	351.9
55°	168.0	168.7	170.6	173.4	178.5	184.5	195.5	211.7	235.8	267.9	301.5
57.5°	149.2	149.8	151.3	152.4	156.6	161.4	170.0	181.5	199.8	227.0	257.0
60°	137.2	136.9	138.7	139.7	142.5	146.6	153.2	164.2	180.1	202.1	229.7
62.5°	125.6	125.0	126.6	127.9	129.4	132.9	138.3	146.9	159.9	179.7	203.6
65°	108.0	107.3	108.2	109.7	111.1	113.0	117.0	124.7	135.0	149.2	167.4
67.5°	90.4	91.2	91.3	92.1	92.9	95.5	98.2	103.6	110.9	122.3	137.7
70°	79.9	80.1	80.8	80.8	81.4	83.7	85.9	89.0	96.2	106.7	119.2
72.5°	69.4	70.2	69.9	70.4	70.9	72.4	74.0	77.1	83.1	90.9	101.6
75°	54.0	54.6	54.6	54.7	55.3	55.8	57.2	59.4	63.8	69.6	76.8
77.5°	39.4	39.5	39.7	40.4	40.4	41.3	42.2	44.0	46.2	50.1	54.7
80°	30.3	30.7	30.6	31.0	31.0	31.7	32.1	34.3	35.3	37.9	41.4
82.5°	22.3	22.7	22.6	23.1	23.4	23.6	24.1	25.0	26.0	28.3	29.7
85°	11.2	11.6	11.2	11.6	12.2	12.4	12.9	13.2	13.9	14.4	15.8
87.5°	8.1	8.4	8.3	8.4	8.6	8.6	8.6	8.2	8.6	8.6	8.9
90°	23.7	23.4	23.1	22.7	22.3	21.6	20.6	19.5	18.5	17.4	16.0
92.5°	35.1	34.9	34.7	34.5	34.3	33.8	33.2	32.6	31.9	31.3	30.3
95°	62.5	62.5	62.5	62.5	62.5	62.2	61.7	61.2	60.6	60.1	58.9
97.5°	97.9	97.9	97.9	97.9	97.9	97.6	97.0	96.3	95.7	95.1	93.6
100°	122.6	122.6	122.6	122.6	122.6	122.4	122.0	121.7	121.4	121.0	119.4
102.5°	150.4	150.3	150.1	150.0	149.8	149.5	149.0	148.5	148.1	147.6	146.1
105°	192.9	192.4	191.9	191.3	190.8	190.3	189.8	189.3	188.7	188.2	187.5
107.5°	234.3	234.4	234.4	234.5	234.5	234.2	233.8	233.3	232.8	232.3	232.2
110°	264.1	263.6	263.0	262.5	262.0	261.9	262.2	262.6	262.9	263.3	263.5



TEST NUMBER: P332518-927

CATALOG NUMBER: SA4XXDIP-C350D1035U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	294.5	294.4	294.2	294.1	294.1	294.1	294.1	294.1	294.2	294.3	294.6
115°	341.6	341.7	341.9	342.1	342.3	342.5	342.6	342.8	343.0	343.2	343.5
117.5°	386.5	386.8	387.2	387.5	387.9	388.4	389.0	389.6	390.1	390.8	391.0
120°	420.6	420.3	419.9	419.6	419.2	419.5	420.4	421.3	422.2	423.0	423.6
122.5°	449.1	449.7	450.4	451.0	451.6	452.3	452.9	453.4	454.1	454.6	454.9
125°	498.1	498.5	498.8	499.2	499.6	499.9	500.3	500.6	501.0	501.3	501.5
127.5°	543.5	543.8	544.1	544.4	544.6	544.9	545.3	545.7	546.1	546.4	546.7
130°	573.2	573.9	574.6	575.4	576.1	576.6	576.9	577.3	577.7	578.0	578.0
132.5°	604.9	605.1	605.5	605.7	606.0	606.3	606.7	607.0	607.4	607.8	607.8
135°	648.4	648.9	649.4	650.0	650.5	650.9	651.3	651.6	652.0	652.4	652.4
137.5°	694.1	694.0	693.9	693.8	693.6	693.9	694.3	694.7	695.2	695.7	695.4
140°	721.9	722.1	722.2	722.5	722.6	722.8	722.9	723.2	723.3	723.5	723.5
142.5°	749.7	749.8	749.8	749.9	749.9	750.0	750.0	750.0	750.0	750.0	750.2
145°	787.5	788.1	788.6	789.1	789.6	790.0	790.2	790.4	790.5	790.7	790.5
147.5°	825.9	826.0	826.2	826.3	826.5	826.6	826.8	827.0	827.1	827.3	827.4
150°	849.2	849.4	849.5	849.8	849.9	850.0	850.0	850.0	850.0	850.0	850.0
152.5°	870.7	871.2	871.6	872.1	872.6	872.6	872.1	871.7	871.3	870.8	870.8
155°	900.6	901.3	902.1	902.7	903.4	903.4	902.7	902.1	901.3	900.6	900.8
157.5°	927.3	928.0	928.5	929.2	929.7	929.8	929.2	928.7	928.2	927.6	927.7
160°	942.5	943.4	944.3	945.2	946.0	946.2	945.7	945.2	944.6	944.1	944.3
162.5°	958.3	959.3	960.1	961.0	961.9	961.8	960.8	959.9	958.9	958.0	958.2
165°	978.9	979.6	980.3	981.0	981.7	981.5	980.5	979.5	978.3	977.3	977.6
167.5°	993.6	994.7	995.8	996.9	998.0	998.0	997.0	995.9	994.8	993.8	993.7
170°	1001.8	1003.1	1004.2	1005.5	1006.7	1006.9	1005.8	1004.7	1003.7	1002.6	1002.4
172.5°	1008.8	1010.0	1011.2	1012.5	1013.7	1013.8	1012.5	1011.3	1010.1	1008.9	1008.9
175°	1016.1	1017.3	1018.5	1019.8	1021.0	1021.0	1019.8	1018.5	1017.3	1016.1	1016.2
177.5°	1019.9	1021.0	1022.1	1023.3	1024.4	1024.5	1023.4	1022.5	1021.4	1020.5	1020.5
180°	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4



TEST NUMBER: P332518-927

CATALOG NUMBER: SA4XXDIP-C350D1035U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6
2.5°	467.1	465.0	463.5	462.3	459.1	457.1	455.6	453.5	451.1	448.5	445.4
5°	493.6	487.3	482.6	475.5	468.7	463.1	457.2	452.0	445.7	438.7	433.6
7.5°	521.5	512.0	499.9	489.3	477.4	467.1	458.0	448.5	438.7	429.1	420.4
10°	539.2	527.0	513.5	497.6	482.6	469.3	456.9	444.9	433.2	421.7	411.7
12.5°	558.3	543.0	523.1	504.5	487.7	469.8	455.0	440.2	426.2	414.0	402.4
15°	583.8	561.9	538.8	513.9	491.8	471.0	450.5	432.0	416.2	400.1	388.8
17.5°	599.5	572.4	546.1	520.0	493.2	466.9	444.9	423.5	403.8	387.8	373.6
20°	609.9	582.9	550.1	524.0	492.2	465.2	439.7	415.8	395.2	378.2	363.5
22.5°	618.9	587.7	554.8	520.5	488.9	460.2	432.3	408.4	387.3	369.3	355.3
25°	623.8	588.0	552.3	518.2	482.2	448.3	422.9	394.8	372.3	353.4	338.4
27.5°	624.3	586.0	545.7	507.8	470.6	439.0	407.1	381.9	358.6	338.6	324.2
30°	622.7	582.7	539.4	498.4	461.1	426.7	398.9	371.6	347.8	327.9	312.9
32.5°	617.3	575.8	531.3	487.8	449.2	415.6	387.0	360.9	337.7	318.1	302.4
35°	602.2	561.1	513.7	468.5	429.0	395.1	369.2	342.7	319.5	301.0	285.7
37.5°	578.5	541.4	493.1	446.4	407.5	373.4	347.8	323.9	302.9	284.1	268.5
40°	557.8	525.1	476.7	431.2	389.2	356.8	332.8	310.9	290.0	272.2	257.4
42.5°	533.9	505.5	460.9	412.6	372.1	339.5	316.2	296.4	276.9	260.4	245.6
45°	491.4	472.6	430.6	386.0	343.8	313.1	290.8	273.5	257.1	240.9	228.5
47.5°	442.5	433.2	397.8	355.5	315.4	285.1	265.8	249.9	235.4	221.7	210.8
50°	409.6	405.1	374.6	333.7	295.5	267.0	247.5	233.8	221.4	209.5	199.1
52.5°	377.2	377.1	349.5	312.1	276.7	249.3	229.9	217.1	206.4	196.7	187.4
55°	327.7	333.0	311.4	278.1	246.4	221.6	204.1	192.7	185.2	177.2	170.2
57.5°	282.3	291.0	273.1	243.8	217.3	194.6	179.4	170.8	162.8	157.9	152.8
60°	252.5	260.8	246.9	222.2	197.3	177.8	163.3	155.6	148.7	145.3	141.7
62.5°	226.2	233.5	223.2	200.3	178.6	159.9	147.7	140.3	135.6	132.0	129.6
65°	188.5	194.6	185.8	169.1	150.5	135.5	125.6	119.8	115.3	113.8	111.1
67.5°	152.3	158.0	153.2	139.0	124.1	112.7	105.0	99.4	96.7	95.5	93.6
70°	130.9	136.5	131.4	119.1	107.6	98.1	90.7	87.5	84.8	84.2	81.6
72.5°	112.7	116.5	111.5	101.8	92.1	84.0	78.3	74.9	73.5	72.5	71.1
75°	84.5	87.9	84.5	77.1	70.1	64.5	59.7	58.3	56.6	56.1	55.1
77.5°	59.8	62.7	60.2	55.5	50.3	45.9	43.3	41.7	41.3	40.3	40.8
80°	45.7	47.6	45.2	42.0	37.9	34.9	33.0	32.1	31.0	30.6	31.3
82.5°	32.9	33.7	32.4	30.3	27.3	25.3	24.0	22.9	22.7	22.7	22.7
85°	17.0	16.9	16.7	14.8	13.9	12.6	11.8	11.6	11.4	11.8	12.2
87.5°	8.6	8.5	8.1	7.1	6.3	5.5	4.9	4.4	4.9	5.5	6.0
90°	14.6	13.2	11.8	10.1	8.2	6.3	4.3	2.4	4.3	6.3	8.2
92.5°	29.3	28.4	27.4	25.7	23.5	21.3	19.2	17.0	19.2	21.3	23.5
95°	57.7	56.4	55.1	53.8	52.2	50.6	49.0	47.5	49.0	50.6	52.2
97.5°	92.1	90.7	89.3	87.9	86.7	85.4	84.1	82.9	84.1	85.4	86.7
100°	117.8	116.2	114.6	113.5	112.8	112.1	111.4	110.7	111.4	112.1	112.8
102.5°	144.7	143.2	141.8	140.9	140.6	140.4	140.1	139.8	140.1	140.4	140.6
105°	186.8	186.1	185.4	185.0	184.7	184.6	184.4	184.3	184.4	184.6	184.7
107.5°	232.1	232.0	231.9	231.7	231.6	231.3	231.1	230.9	231.1	231.3	231.6
110°	263.6	263.8	264.0	264.0	263.6	263.2	262.8	262.5	262.8	263.2	263.6





TEST NUMBER: P332518-927

CATALOG NUMBER: SA4XXDIP-C350D1035U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	294.9	295.2	295.6	295.7	295.6	295.6	295.5	295.4	295.5	295.6	295.6
115°	343.9	344.2	344.6	344.8	344.8	344.8	344.8	344.8	344.8	344.8	344.8
117.5°	391.3	391.5	391.7	391.8	391.7	391.5	391.4	391.3	391.4	391.5	391.7
120°	424.1	424.6	425.2	425.1	424.4	423.7	422.9	422.2	422.9	423.7	424.4
122.5°	455.1	455.4	455.7	455.6	455.3	455.0	454.8	454.5	454.8	455.0	455.3
125°	501.7	501.8	502.0	502.1	502.1	502.1	502.1	502.1	502.1	502.1	502.1
127.5°	546.9	547.2	547.5	547.4	546.8	546.3	545.8	545.3	545.8	546.3	546.8
130°	578.0	578.0	578.0	577.7	577.2	576.7	576.2	575.6	576.2	576.7	577.2
132.5°	608.0	608.2	608.3	608.2	607.8	607.4	607.0	606.7	607.0	607.4	607.8
135°	652.4	652.4	652.4	651.8	650.8	649.7	648.6	647.6	648.6	649.7	650.8
137.5°	695.1	694.8	694.5	694.2	693.6	693.2	692.7	692.2	692.7	693.2	693.6
140°	723.5	723.5	723.5	723.3	722.9	722.6	722.2	721.9	722.2	722.6	722.9
142.5°	750.4	750.5	750.6	750.5	750.2	749.8	749.5	749.1	749.5	749.8	750.2
145°	790.4	790.2	790.0	789.6	788.9	788.1	787.4	786.7	787.4	788.1	788.9
147.5°	827.5	827.7	827.8	827.4	826.6	825.8	824.9	824.1	824.9	825.8	826.6
150°	850.0	850.0	850.0	849.7	849.0	848.3	847.6	846.8	847.6	848.3	849.0
152.5°	870.6	870.4	870.3	870.1	869.7	869.2	868.8	868.4	868.8	869.2	869.7
155°	900.9	901.1	901.3	901.4	901.4	901.4	901.4	901.4	901.4	901.4	901.4
157.5°	927.7	927.7	927.8	928.0	928.3	928.6	928.9	929.2	928.9	928.6	928.3
160°	944.4	944.6	944.8	945.0	945.2	945.3	945.5	945.7	945.5	945.3	945.2
162.5°	958.4	958.5	958.7	959.0	959.5	960.0	960.4	960.8	960.4	960.0	959.5
165°	978.0	978.3	978.7	979.1	979.7	980.2	980.7	981.3	980.7	980.2	979.7
167.5°	993.7	993.6	993.6	994.0	994.7	995.5	996.2	997.0	996.2	995.5	994.7
170°	1002.3	1002.1	1001.9	1002.3	1003.1	1004.0	1004.9	1005.8	1004.9	1004.0	1003.1
172.5°	1008.8	1008.8	1008.8	1009.2	1009.9	1010.7	1011.4	1012.1	1011.4	1010.7	1009.9
175°	1016.4	1016.6	1016.8	1017.3	1018.2	1019.1	1019.9	1020.8	1019.9	1019.1	1018.2
177.5°	1020.5	1020.5	1020.5	1020.8	1021.5	1022.2	1022.9	1023.7	1022.9	1022.2	1021.5
180°	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4



TEST NUMBER: P332518-927

CATALOG NUMBER: SA4XXDIP-C350D1035U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6
2.5°	443.9	442.5	440.6	437.9	435.6	433.2	432.6	431.7	433.6	432.1	431.6
5°	429.4	425.4	420.3	414.5	411.1	406.3	405.4	403.5	401.6	401.4	399.5
7.5°	413.9	408.1	401.5	395.6	390.1	384.8	381.3	380.6	377.8	376.1	374.3
10°	404.0	396.9	389.2	383.6	377.2	371.6	367.7	365.4	363.5	361.5	359.6
12.5°	392.4	384.8	378.4	372.3	364.8	360.5	354.0	350.1	349.7	349.7	344.9
15°	378.7	371.2	361.5	352.8	348.7	340.5	336.9	332.4	329.6	326.8	324.6
17.5°	363.1	353.8	346.2	336.3	328.4	321.9	317.2	314.5	310.2	306.3	303.4
20°	353.4	343.5	335.4	324.9	316.3	308.2	304.3	300.6	297.4	294.0	290.8
22.5°	343.5	333.1	323.3	313.1	305.1	296.5	292.7	287.6	284.6	282.7	279.6
25°	327.9	316.6	305.4	295.6	287.4	279.9	274.9	270.9	267.5	266.0	264.0
27.5°	310.9	299.8	288.9	277.8	268.5	263.0	259.0	256.0	254.1	252.1	251.1
30°	300.2	288.5	276.9	266.6	258.0	252.5	248.8	246.8	245.3	244.3	243.4
32.5°	289.2	277.7	265.5	256.1	248.3	243.5	240.7	238.6	237.9	237.6	237.2
35°	271.6	260.1	248.8	240.3	233.1	231.2	228.7	227.6	227.2	228.5	229.1
37.5°	254.7	243.9	233.5	225.4	220.5	217.9	217.0	217.1	218.4	219.5	220.9
40°	243.8	233.2	223.5	216.3	211.8	210.2	209.8	210.7	212.2	213.6	215.1
42.5°	233.1	222.8	213.9	207.2	204.1	202.5	202.7	203.7	205.8	207.4	209.6
45°	216.6	207.9	199.3	193.8	191.2	191.6	191.6	193.3	195.4	197.8	200.3
47.5°	201.0	192.3	185.2	180.6	179.3	179.0	180.0	182.2	185.1	188.1	191.5
50°	190.5	182.2	176.0	171.9	170.4	171.0	172.5	174.5	178.1	181.9	185.4
52.5°	179.8	172.3	166.6	162.8	161.7	162.7	164.2	167.5	170.6	174.7	179.0
55°	163.3	156.9	152.4	149.6	149.2	149.8	151.5	155.0	159.5	164.6	168.7
57.5°	146.9	141.5	137.4	135.5	135.6	136.2	138.9	143.1	148.0	153.4	158.7
60°	135.7	130.9	127.5	126.0	126.2	127.3	130.7	134.6	140.6	145.8	151.5
62.5°	125.2	121.0	117.7	116.4	116.1	118.6	121.8	125.9	131.9	137.8	143.9
65°	108.4	105.0	102.3	101.6	102.2	104.1	108.2	113.6	118.7	124.8	131.3
67.5°	91.9	89.1	87.3	87.6	88.3	91.1	94.5	99.2	105.0	111.4	117.6
70°	81.4	78.7	77.2	77.4	78.6	81.9	84.9	89.6	95.8	102.3	107.6
72.5°	70.6	68.8	67.5	68.3	69.4	71.7	75.5	80.2	85.6	91.7	97.3
75°	54.2	54.2	53.5	54.0	55.7	57.9	60.8	65.6	71.1	76.0	80.4
77.5°	40.2	39.8	40.2	41.0	41.9	44.6	47.8	51.3	55.4	60.3	64.0
80°	30.7	31.0	31.8	33.0	33.4	35.4	38.8	42.0	45.2	49.3	52.8
82.5°	23.1	23.3	23.8	25.2	25.6	27.8	29.9	33.1	36.0	38.8	41.7
85°	12.6	12.6	13.5	14.1	15.0	16.5	17.8	19.7	22.3	24.2	27.0
87.5°	6.8	7.1	8.0	8.6	9.3	10.4	10.9	12.8	13.5	14.5	16.0
90°	10.1	11.8	13.2	14.6	16.0	17.4	18.5	19.5	20.6	21.6	22.3
92.5°	25.7	27.4	28.4	29.3	30.3	31.3	31.9	32.6	33.2	33.8	34.3
95°	53.8	55.1	56.4	57.7	58.9	60.1	60.6	61.2	61.7	62.2	62.5
97.5°	87.9	89.3	90.7	92.1	93.6	95.1	95.7	96.3	97.0	97.6	97.9
100°	113.5	114.6	116.2	117.8	119.4	121.0	121.4	121.7	122.0	122.4	122.6
102.5°	140.9	141.8	143.2	144.7	146.1	147.6	148.1	148.5	149.0	149.5	149.8
105°	185.0	185.4	186.1	186.8	187.5	188.2	188.7	189.3	189.8	190.3	190.8
107.5°	231.7	231.9	232.0	232.1	232.2	232.3	232.8	233.3	233.8	234.2	234.5
110°	264.0	264.0	263.8	263.6	263.5	263.3	262.9	262.6	262.2	261.9	262.0



TEST NUMBER: P332518-927

CATALOG NUMBER: SA4XXDIP-C350D1035U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	295.7	295.6	295.2	294.9	294.6	294.3	294.2	294.1	294.1	294.1	294.1
115°	344.8	344.6	344.2	343.9	343.5	343.2	343.0	342.8	342.6	342.5	342.3
117.5°	391.8	391.7	391.5	391.3	391.0	390.8	390.1	389.6	389.0	388.4	387.9
120°	425.1	425.2	424.6	424.1	423.6	423.0	422.2	421.3	420.4	419.5	419.2
122.5°	455.6	455.7	455.4	455.1	454.9	454.6	454.1	453.4	452.9	452.3	451.6
125°	502.1	502.0	501.8	501.7	501.5	501.3	501.0	500.6	500.3	499.9	499.6
127.5°	547.4	547.5	547.2	546.9	546.7	546.4	546.1	545.7	545.3	544.9	544.6
130°	577.7	578.0	578.0	578.0	578.0	578.0	577.7	577.3	576.9	576.6	576.1
132.5°	608.2	608.3	608.2	608.0	607.8	607.8	607.4	607.0	606.7	606.3	606.0
135°	651.8	652.4	652.4	652.4	652.4	652.4	652.0	651.6	651.3	650.9	650.5
137.5°	694.2	694.5	694.8	695.1	695.4	695.7	695.2	694.7	694.3	693.9	693.6
140°	723.3	723.5	723.5	723.5	723.5	723.5	723.3	723.2	722.9	722.8	722.6
142.5°	750.5	750.6	750.5	750.4	750.2	750.0	750.0	750.0	750.0	750.0	749.9
145°	789.6	790.0	790.2	790.4	790.5	790.7	790.5	790.4	790.2	790.0	789.6
147.5°	827.4	827.8	827.7	827.5	827.4	827.3	827.1	827.0	826.8	826.6	826.5
150°	849.7	850.0	850.0	850.0	850.0	850.0	850.0	850.0	850.0	850.0	849.9
152.5°	870.1	870.3	870.4	870.6	870.8	870.8	871.3	871.7	872.1	872.6	872.6
155°	901.4	901.3	901.1	900.9	900.8	900.6	901.3	902.1	902.7	903.4	903.4
157.5°	928.0	927.8	927.7	927.7	927.7	927.6	928.2	928.7	929.2	929.8	929.7
160°	945.0	944.8	944.6	944.4	944.3	944.1	944.6	945.2	945.7	946.2	946.0
162.5°	959.0	958.7	958.5	958.4	958.2	958.0	958.9	959.9	960.8	961.8	961.9
165°	979.1	978.7	978.3	978.0	977.6	977.3	978.3	979.5	980.5	981.5	981.7
167.5°	994.0	993.6	993.6	993.7	993.7	993.8	994.8	995.9	997.0	998.0	998.0
170°	1002.3	1001.9	1002.1	1002.3	1002.4	1002.6	1003.7	1004.7	1005.8	1006.9	1006.7
172.5°	1009.2	1008.8	1008.8	1008.8	1008.9	1008.9	1010.1	1011.3	1012.5	1013.8	1013.7
175°	1017.3	1016.8	1016.6	1016.4	1016.2	1016.1	1017.3	1018.5	1019.8	1021.0	1021.0
177.5°	1020.8	1020.5	1020.5	1020.5	1020.5	1020.5	1021.4	1022.5	1023.4	1024.5	1024.4
180°	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4



TEST NUMBER: P332518-927

CATALOG NUMBER: SA4XXDIP-C350D1035U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6
2.5°	431.3	431.0	429.9	429.8	429.9	431.0	431.3	431.6	432.1	433.6	431.7
5°	398.4	397.4	396.9	398.9	396.9	397.4	398.4	399.5	401.4	401.6	403.5
7.5°	373.6	372.9	371.2	370.7	371.2	372.9	373.6	374.3	376.1	377.8	380.6
10°	357.7	357.0	355.5	355.1	355.5	357.0	357.7	359.6	361.5	363.5	365.4
12.5°	342.4	341.0	340.6	341.0	340.6	341.0	342.4	344.9	349.7	349.7	350.1
15°	322.1	321.3	319.2	319.9	319.2	321.3	322.1	324.6	326.8	329.6	332.4
17.5°	302.1	301.2	298.7	300.9	298.7	301.2	302.1	303.4	306.3	310.2	314.5
20°	289.5	288.0	286.7	286.5	286.7	288.0	289.5	290.8	294.0	297.4	300.6
22.5°	277.5	276.2	276.0	274.8	276.0	276.2	277.5	279.6	282.7	284.6	287.6
25°	262.4	261.2	260.8	259.8	260.8	261.2	262.4	264.0	266.0	267.5	270.9
27.5°	251.0	250.3	249.6	249.9	249.6	250.3	251.0	251.1	252.1	254.1	256.0
30°	243.9	243.8	243.4	243.4	243.4	243.8	243.9	243.4	244.3	245.3	246.8
32.5°	238.1	238.1	238.3	238.3	238.3	238.1	238.1	237.2	237.6	237.9	238.6
35°	229.9	230.4	230.8	230.2	230.8	230.4	229.9	229.1	228.5	227.2	227.6
37.5°	222.4	223.0	223.6	224.2	223.6	223.0	222.4	220.9	219.5	218.4	217.1
40°	216.7	218.0	218.4	219.4	218.4	218.0	216.7	215.1	213.6	212.2	210.7
42.5°	211.4	212.8	213.7	214.0	213.7	212.8	211.4	209.6	207.4	205.8	203.7
45°	203.0	204.5	205.9	205.9	205.9	204.5	203.0	200.3	197.8	195.4	193.3
47.5°	194.5	196.6	198.0	198.3	198.0	196.6	194.5	191.5	188.1	185.1	182.2
50°	188.6	191.2	192.6	193.5	192.6	191.2	188.6	185.4	181.9	178.1	174.5
52.5°	182.9	185.5	187.3	187.7	187.3	185.5	182.9	179.0	174.7	170.6	167.5
55°	173.0	176.8	178.9	179.6	178.9	176.8	173.0	168.7	164.6	159.5	155.0
57.5°	163.7	167.2	169.6	170.2	169.6	167.2	163.7	158.7	153.4	148.0	143.1
60°	156.5	160.3	163.3	163.8	163.3	160.3	156.5	151.5	145.8	140.6	134.6
62.5°	149.2	153.1	155.8	157.2	155.8	153.1	149.2	143.9	137.8	131.9	125.9
65°	136.5	140.5	143.1	143.6	143.1	140.5	136.5	131.3	124.8	118.7	113.6
67.5°	122.6	126.6	128.3	129.4	128.3	126.6	122.6	117.6	111.4	105.0	99.2
70°	112.9	116.1	118.0	118.8	118.0	116.1	112.9	107.6	102.3	95.8	89.6
72.5°	101.8	105.1	107.3	107.5	107.3	105.1	101.8	97.3	91.7	85.6	80.2
75°	84.8	87.8	88.9	88.9	88.9	87.8	84.8	80.4	76.0	71.1	65.6
77.5°	67.1	68.6	70.0	70.3	70.0	68.6	67.1	64.0	60.3	55.4	51.3
80°	55.7	56.6	57.8	57.8	57.8	56.6	55.7	52.8	49.3	45.2	42.0
82.5°	44.0	44.8	45.9	45.7	45.9	44.8	44.0	41.7	38.8	36.0	33.1
85°	26.6	28.3	28.1	27.7	28.1	28.3	26.6	27.0	24.2	22.3	19.7
87.5°	16.6	16.7	17.3	17.7	17.3	16.7	16.6	16.0	14.5	13.5	12.8
90°	22.7	23.1	23.4	23.7	23.4	23.1	22.7	22.3	21.6	20.6	19.5
92.5°	34.5	34.7	34.9	35.1	34.9	34.7	34.5	34.3	33.8	33.2	32.6
95°	62.5	62.5	62.5	62.5	62.5	62.5	62.5	62.5	62.2	61.7	61.2
97.5°	97.9	97.9	97.9	97.9	97.9	97.9	97.9	97.9	97.6	97.0	96.3
100°	122.6	122.6	122.6	122.6	122.6	122.6	122.6	122.6	122.4	122.0	121.7
102.5°	150.0	150.1	150.3	150.4	150.3	150.1	150.0	149.8	149.5	149.0	148.5
105°	191.3	191.9	192.4	192.9	192.4	191.9	191.3	190.8	190.3	189.8	189.3
107.5°	234.5	234.4	234.4	234.3	234.4	234.4	234.5	234.5	234.2	233.8	233.3
110°	262.5	263.0	263.6	264.1	263.6	263.0	262.5	262.0	261.9	262.2	262.6



TEST NUMBER: P332518-927

CATALOG NUMBER: SA4XXDIP-C350D1035U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	294.1	294.2	294.4	294.5	294.4	294.2	294.1	294.1	294.1	294.1	294.1
115°	342.1	341.9	341.7	341.6	341.7	341.9	342.1	342.3	342.5	342.6	342.8
117.5°	387.5	387.2	386.8	386.5	386.8	387.2	387.5	387.9	388.4	389.0	389.6
120°	419.6	419.9	420.3	420.6	420.3	419.9	419.6	419.2	419.5	420.4	421.3
122.5°	451.0	450.4	449.7	449.1	449.7	450.4	451.0	451.6	452.3	452.9	453.4
125°	499.2	498.8	498.5	498.1	498.5	498.8	499.2	499.6	499.9	500.3	500.6
127.5°	544.4	544.1	543.8	543.5	543.8	544.1	544.4	544.6	544.9	545.3	545.7
130°	575.4	574.6	573.9	573.2	573.9	574.6	575.4	576.1	576.6	576.9	577.3
132.5°	605.7	605.5	605.1	604.9	605.1	605.5	605.7	606.0	606.3	606.7	607.0
135°	650.0	649.4	648.9	648.4	648.9	649.4	650.0	650.5	650.9	651.3	651.6
137.5°	693.8	693.9	694.0	694.1	694.0	693.9	693.8	693.6	693.9	694.3	694.7
140°	722.5	722.2	722.1	721.9	722.1	722.2	722.5	722.6	722.8	722.9	723.2
142.5°	749.9	749.8	749.8	749.7	749.8	749.8	749.9	749.9	750.0	750.0	750.0
145°	789.1	788.6	788.1	787.5	788.1	788.6	789.1	789.6	790.0	790.2	790.4
147.5°	826.3	826.2	826.0	825.9	826.0	826.2	826.3	826.5	826.6	826.8	827.0
150°	849.8	849.5	849.4	849.2	849.4	849.5	849.8	849.9	850.0	850.0	850.0
152.5°	872.1	871.6	871.2	870.7	871.2	871.6	872.1	872.6	872.6	872.1	871.7
155°	902.7	902.1	901.3	900.6	901.3	902.1	902.7	903.4	903.4	902.7	902.1
157.5°	929.2	928.5	928.0	927.3	928.0	928.5	929.2	929.7	929.8	929.2	928.7
160°	945.2	944.3	943.4	942.5	943.4	944.3	945.2	946.0	946.2	945.7	945.2
162.5°	961.0	960.1	959.3	958.3	959.3	960.1	961.0	961.9	961.8	960.8	959.9
165°	981.0	980.3	979.6	978.9	979.6	980.3	981.0	981.7	981.5	980.5	979.5
167.5°	996.9	995.8	994.7	993.6	994.7	995.8	996.9	998.0	998.0	997.0	995.9
170°	1005.5	1004.2	1003.1	1001.8	1003.1	1004.2	1005.5	1006.7	1006.9	1005.8	1004.7
172.5°	1012.5	1011.2	1010.0	1008.8	1010.0	1011.2	1012.5	1013.7	1013.8	1012.5	1011.3
175°	1019.8	1018.5	1017.3	1016.1	1017.3	1018.5	1019.8	1021.0	1021.0	1019.8	1018.5
177.5°	1023.3	1022.1	1021.0	1019.9	1021.0	1022.1	1023.3	1024.4	1024.5	1023.4	1022.5
180°	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4



TEST NUMBER: P332518-927

CATALOG NUMBER: SA4XXDIP-C350D1035U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6
2.5°	432.6	433.2	435.6	437.9	440.6	442.5	443.9	445.4	448.5	451.1	453.5
5°	405.4	406.3	411.1	414.5	420.3	425.4	429.4	433.6	438.7	445.7	452.0
7.5°	381.3	384.8	390.1	395.6	401.5	408.1	413.9	420.4	429.1	438.7	448.5
10°	367.7	371.6	377.2	383.6	389.2	396.9	404.0	411.7	421.7	433.2	444.9
12.5°	354.0	360.5	364.8	372.3	378.4	384.8	392.4	402.4	414.0	426.2	440.2
15°	336.9	340.5	348.7	352.8	361.5	371.2	378.7	388.8	400.1	416.2	432.0
17.5°	317.2	321.9	328.4	336.3	346.2	353.8	363.1	373.6	387.8	403.8	423.5
20°	304.3	308.2	316.3	324.9	335.4	343.5	353.4	363.5	378.2	395.2	415.8
22.5°	292.7	296.5	305.1	313.1	323.3	333.1	343.5	355.3	369.3	387.3	408.4
25°	274.9	279.9	287.4	295.6	305.4	316.6	327.9	338.4	353.4	372.3	394.8
27.5°	259.0	263.0	268.5	277.8	288.9	299.8	310.9	324.2	338.6	358.6	381.9
30°	248.8	252.5	258.0	266.6	276.9	288.5	300.2	312.9	327.9	347.8	371.6
32.5°	240.7	243.5	248.3	256.1	265.5	277.7	289.2	302.4	318.1	337.7	360.9
35°	228.7	231.2	233.1	240.3	248.8	260.1	271.6	285.7	301.0	319.5	342.7
37.5°	217.0	217.9	220.5	225.4	233.5	243.9	254.7	268.5	284.1	302.9	323.9
40°	209.8	210.2	211.8	216.3	223.5	233.2	243.8	257.4	272.2	290.0	310.9
42.5°	202.7	202.5	204.1	207.2	213.9	222.8	233.1	245.6	260.4	276.9	296.4
45°	191.6	191.6	191.2	193.8	199.3	207.9	216.6	228.5	240.9	257.1	273.5
47.5°	180.0	179.0	179.3	180.6	185.2	192.3	201.0	210.8	221.7	235.4	249.9
50°	172.5	171.0	170.4	171.9	176.0	182.2	190.5	199.1	209.5	221.4	233.8
52.5°	164.2	162.7	161.7	162.8	166.6	172.3	179.8	187.4	196.7	206.4	217.1
55°	151.5	149.8	149.2	149.6	152.4	156.9	163.3	170.2	177.2	185.2	192.7
57.5°	138.9	136.2	135.6	135.5	137.4	141.5	146.9	152.8	157.9	162.8	170.8
60°	130.7	127.3	126.2	126.0	127.5	130.9	135.7	141.7	145.3	148.7	155.6
62.5°	121.8	118.6	116.1	116.4	117.7	121.0	125.2	129.6	132.0	135.6	140.3
65°	108.2	104.1	102.2	101.6	102.3	105.0	108.4	111.1	113.8	115.3	119.8
67.5°	94.5	91.1	88.3	87.6	87.3	89.1	91.9	93.6	95.5	96.7	99.4
70°	84.9	81.9	78.6	77.4	77.2	78.7	81.4	81.6	84.2	84.8	87.5
72.5°	75.5	71.7	69.4	68.3	67.5	68.8	70.6	71.1	72.5	73.5	74.9
75°	60.8	57.9	55.7	54.0	53.5	54.2	54.2	55.1	56.1	56.6	58.3
77.5°	47.8	44.6	41.9	41.0	40.2	39.8	40.2	40.8	40.3	41.3	41.7
80°	38.8	35.4	33.4	33.0	31.8	31.0	30.7	31.3	30.6	31.0	32.1
82.5°	29.9	27.8	25.6	25.2	23.8	23.3	23.1	22.7	22.7	22.7	22.9
85°	17.8	16.5	15.0	14.1	13.5	12.6	12.6	12.2	11.8	11.4	11.6
87.5°	10.9	10.4	9.3	8.6	8.0	7.1	6.8	6.0	5.5	4.9	4.4
90°	18.5	17.4	16.0	14.6	13.2	11.8	10.1	8.2	6.3	4.3	2.4
92.5°	31.9	31.3	30.3	29.3	28.4	27.4	25.7	23.5	21.3	19.2	17.0
95°	60.6	60.1	58.9	57.7	56.4	55.1	53.8	52.2	50.6	49.0	47.5
97.5°	95.7	95.1	93.6	92.1	90.7	89.3	87.9	86.7	85.4	84.1	82.9
100°	121.4	121.0	119.4	117.8	116.2	114.6	113.5	112.8	112.1	111.4	110.7
102.5°	148.1	147.6	146.1	144.7	143.2	141.8	140.9	140.6	140.4	140.1	139.8
105°	188.7	188.2	187.5	186.8	186.1	185.4	185.0	184.7	184.6	184.4	184.3
107.5°	232.8	232.3	232.2	232.1	232.0	231.9	231.7	231.6	231.3	231.1	230.9
110°	262.9	263.3	263.5	263.6	263.8	264.0	264.0	263.6	263.2	262.8	262.5



TEST NUMBER: P332518-927

CATALOG NUMBER: SA4XXDIP-C350D1035U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	294.2	294.3	294.6	294.9	295.2	295.6	295.7	295.6	295.6	295.5	295.4
115°	343.0	343.2	343.5	343.9	344.2	344.6	344.8	344.8	344.8	344.8	344.8
117.5°	390.1	390.8	391.0	391.3	391.5	391.7	391.8	391.7	391.5	391.4	391.3
120°	422.2	423.0	423.6	424.1	424.6	425.2	425.1	424.4	423.7	422.9	422.2
122.5°	454.1	454.6	454.9	455.1	455.4	455.7	455.6	455.3	455.0	454.8	454.5
125°	501.0	501.3	501.5	501.7	501.8	502.0	502.1	502.1	502.1	502.1	502.1
127.5°	546.1	546.4	546.7	546.9	547.2	547.5	547.4	546.8	546.3	545.8	545.3
130°	577.7	578.0	578.0	578.0	578.0	578.0	577.7	577.2	576.7	576.2	575.6
132.5°	607.4	607.8	607.8	608.0	608.2	608.3	608.2	607.8	607.4	607.0	606.7
135°	652.0	652.4	652.4	652.4	652.4	652.4	651.8	650.8	649.7	648.6	647.6
137.5°	695.2	695.7	695.4	695.1	694.8	694.5	694.2	693.6	693.2	692.7	692.2
140°	723.3	723.5	723.5	723.5	723.5	723.5	723.3	722.9	722.6	722.2	721.9
142.5°	750.0	750.0	750.2	750.4	750.5	750.6	750.5	750.2	749.8	749.5	749.1
145°	790.5	790.7	790.5	790.4	790.2	790.0	789.6	788.9	788.1	787.4	786.7
147.5°	827.1	827.3	827.4	827.5	827.7	827.8	827.4	826.6	825.8	824.9	824.1
150°	850.0	850.0	850.0	850.0	850.0	850.0	849.7	849.0	848.3	847.6	846.8
152.5°	871.3	870.8	870.8	870.6	870.4	870.3	870.1	869.7	869.2	868.8	868.4
155°	901.3	900.6	900.8	900.9	901.1	901.3	901.4	901.4	901.4	901.4	901.4
157.5°	928.2	927.6	927.7	927.7	927.7	927.8	928.0	928.3	928.6	928.9	929.2
160°	944.6	944.1	944.3	944.4	944.6	944.8	945.0	945.2	945.3	945.5	945.7
162.5°	958.9	958.0	958.2	958.4	958.5	958.7	959.0	959.5	960.0	960.4	960.8
165°	978.3	977.3	977.6	978.0	978.3	978.7	979.1	979.7	980.2	980.7	981.3
167.5°	994.8	993.8	993.7	993.7	993.6	993.6	994.0	994.7	995.5	996.2	997.0
170°	1003.7	1002.6	1002.4	1002.3	1002.1	1001.9	1002.3	1003.1	1004.0	1004.9	1005.8
172.5°	1010.1	1008.9	1008.9	1008.8	1008.8	1008.8	1009.2	1009.9	1010.7	1011.4	1012.1
175°	1017.3	1016.1	1016.2	1016.4	1016.6	1016.8	1017.3	1018.2	1019.1	1019.9	1020.8
177.5°	1021.4	1020.5	1020.5	1020.5	1020.5	1020.5	1020.8	1021.5	1022.2	1022.9	1023.7
180°	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4



TEST NUMBER: P332518-927

CATALOG NUMBER: SA4XXDIP-C350D1035U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6
2.5°	455.6	457.1	459.1	462.3	463.5	465.0	467.1	467.0	467.5	469.8	474.6
5°	457.2	463.1	468.7	475.5	482.6	487.3	493.6	497.6	501.5	506.6	515.2
7.5°	458.0	467.1	477.4	489.3	499.9	512.0	521.5	530.4	538.5	549.1	559.4
10°	456.9	469.3	482.6	497.6	513.5	527.0	539.2	553.1	564.9	577.8	589.5
12.5°	455.0	469.8	487.7	504.5	523.1	543.0	558.3	572.3	588.0	602.9	620.8
15°	450.5	471.0	491.8	513.9	538.8	561.9	583.8	602.0	618.9	641.2	664.6
17.5°	444.9	466.9	493.2	520.0	546.1	572.4	599.5	626.9	648.2	675.9	694.2
20°	439.7	465.2	492.2	524.0	550.1	582.9	609.9	636.3	665.6	693.2	715.1
22.5°	432.3	460.2	488.9	520.5	554.8	587.7	618.9	647.5	676.8	706.8	733.3
25°	422.9	448.3	482.2	518.2	552.3	588.0	623.8	659.7	691.3	722.9	747.7
27.5°	407.1	439.0	470.6	507.8	545.7	586.0	624.3	661.9	695.0	721.0	736.3
30°	398.9	426.7	461.1	498.4	539.4	582.7	622.7	659.6	690.3	711.1	717.3
32.5°	387.0	415.6	449.2	487.8	531.3	575.8	617.3	652.2	677.9	688.8	681.4
35°	369.2	395.1	429.0	468.5	513.7	561.1	602.2	631.6	644.8	634.5	608.8
37.5°	347.8	373.4	407.5	446.4	493.1	541.4	578.5	599.7	595.3	569.7	531.4
40°	332.8	356.8	389.2	431.2	476.7	525.1	557.8	569.2	557.2	520.5	479.7
42.5°	316.2	339.5	372.1	412.6	460.9	505.5	533.9	534.9	514.8	470.8	430.0
45°	290.8	313.1	343.8	386.0	430.6	472.6	491.4	482.2	445.0	402.7	361.6
47.5°	265.8	285.1	315.4	355.5	397.8	433.2	442.5	426.0	386.4	345.2	307.2
50°	247.5	267.0	295.5	333.7	374.6	405.1	409.6	387.7	348.9	307.4	277.7
52.5°	229.9	249.3	276.7	312.1	349.5	377.1	377.2	351.9	313.2	276.3	248.6
55°	204.1	221.6	246.4	278.1	311.4	333.0	327.7	301.5	267.9	235.8	211.7
57.5°	179.4	194.6	217.3	243.8	273.1	291.0	282.3	257.0	227.0	199.8	181.5
60°	163.3	177.8	197.3	222.2	246.9	260.8	252.5	229.7	202.1	180.1	164.2
62.5°	147.7	159.9	178.6	200.3	223.2	233.5	226.2	203.6	179.7	159.9	146.9
65°	125.6	135.5	150.5	169.1	185.8	194.6	188.5	167.4	149.2	135.0	124.7
67.5°	105.0	112.7	124.1	139.0	153.2	158.0	152.3	137.7	122.3	110.9	103.6
70°	90.7	98.1	107.6	119.1	131.4	136.5	130.9	119.2	106.7	96.2	89.0
72.5°	78.3	84.0	92.1	101.8	111.5	116.5	112.7	101.6	90.9	83.1	77.1
75°	59.7	64.5	70.1	77.1	84.5	87.9	84.5	76.8	69.6	63.8	59.4
77.5°	43.3	45.9	50.3	55.5	60.2	62.7	59.8	54.7	50.1	46.2	44.0
80°	33.0	34.9	37.9	42.0	45.2	47.6	45.7	41.4	37.9	35.3	34.3
82.5°	24.0	25.3	27.3	30.3	32.4	33.7	32.9	29.7	28.3	26.0	25.0
85°	11.8	12.6	13.9	14.8	16.7	16.9	17.0	15.8	14.4	13.9	13.2
87.5°	4.9	5.5	6.3	7.1	8.1	8.5	8.6	8.9	8.6	8.6	8.2
90°	4.3	6.3	8.2	10.1	11.8	13.2	14.6	16.0	17.4	18.5	19.5
92.5°	19.2	21.3	23.5	25.7	27.4	28.4	29.3	30.3	31.3	31.9	32.6
95°	49.0	50.6	52.2	53.8	55.1	56.4	57.7	58.9	60.1	60.6	61.2
97.5°	84.1	85.4	86.7	87.9	89.3	90.7	92.1	93.6	95.1	95.7	96.3
100°	111.4	112.1	112.8	113.5	114.6	116.2	117.8	119.4	121.0	121.4	121.7
102.5°	140.1	140.4	140.6	140.9	141.8	143.2	144.7	146.1	147.6	148.1	148.5
105°	184.4	184.6	184.7	185.0	185.4	186.1	186.8	187.5	188.2	188.7	189.3
107.5°	231.1	231.3	231.6	231.7	231.9	232.0	232.1	232.2	232.3	232.8	233.3
110°	262.8	263.2	263.6	264.0	264.0	263.8	263.6	263.5	263.3	262.9	262.6





TEST NUMBER: P332518-927

CATALOG NUMBER: SA4XXDIP-C350D1035U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	295.5	295.6	295.6	295.7	295.6	295.2	294.9	294.6	294.3	294.2	294.1
115°	344.8	344.8	344.8	344.8	344.6	344.2	343.9	343.5	343.2	343.0	342.8
117.5°	391.4	391.5	391.7	391.8	391.7	391.5	391.3	391.0	390.8	390.1	389.6
120°	422.9	423.7	424.4	425.1	425.2	424.6	424.1	423.6	423.0	422.2	421.3
122.5°	454.8	455.0	455.3	455.6	455.7	455.4	455.1	454.9	454.6	454.1	453.4
125°	502.1	502.1	502.1	502.1	502.0	501.8	501.7	501.5	501.3	501.0	500.6
127.5°	545.8	546.3	546.8	547.4	547.5	547.2	546.9	546.7	546.4	546.1	545.7
130°	576.2	576.7	577.2	577.7	578.0	578.0	578.0	578.0	578.0	577.7	577.3
132.5°	607.0	607.4	607.8	608.2	608.3	608.2	608.0	607.8	607.8	607.4	607.0
135°	648.6	649.7	650.8	651.8	652.4	652.4	652.4	652.4	652.4	652.0	651.6
137.5°	692.7	693.2	693.6	694.2	694.5	694.8	695.1	695.4	695.7	695.2	694.7
140°	722.2	722.6	722.9	723.3	723.5	723.5	723.5	723.5	723.5	723.3	723.2
142.5°	749.5	749.8	750.2	750.5	750.6	750.5	750.4	750.2	750.0	750.0	750.0
145°	787.4	788.1	788.9	789.6	790.0	790.2	790.4	790.5	790.7	790.5	790.4
147.5°	824.9	825.8	826.6	827.4	827.8	827.7	827.5	827.4	827.3	827.1	827.0
150°	847.6	848.3	849.0	849.7	850.0	850.0	850.0	850.0	850.0	850.0	850.0
152.5°	868.8	869.2	869.7	870.1	870.3	870.4	870.6	870.8	870.8	871.3	871.7
155°	901.4	901.4	901.4	901.4	901.3	901.1	900.9	900.8	900.6	901.3	902.1
157.5°	928.9	928.6	928.3	928.0	927.8	927.7	927.7	927.7	927.6	928.2	928.7
160°	945.5	945.3	945.2	945.0	944.8	944.6	944.4	944.3	944.1	944.6	945.2
162.5°	960.4	960.0	959.5	959.0	958.7	958.5	958.4	958.2	958.0	958.9	959.9
165°	980.7	980.2	979.7	979.1	978.7	978.3	978.0	977.6	977.3	978.3	979.5
167.5°	996.2	995.5	994.7	994.0	993.6	993.6	993.7	993.7	993.8	994.8	995.9
170°	1004.9	1004.0	1003.1	1002.3	1001.9	1002.1	1002.3	1002.4	1002.6	1003.7	1004.7
172.5°	1011.4	1010.7	1009.9	1009.2	1008.8	1008.8	1008.8	1008.9	1008.9	1010.1	1011.3
175°	1019.9	1019.1	1018.2	1017.3	1016.8	1016.6	1016.4	1016.2	1016.1	1017.3	1018.5
177.5°	1022.9	1022.2	1021.5	1020.8	1020.5	1020.5	1020.5	1020.5	1020.5	1021.4	1022.5
180°	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4



TEST NUMBER: P332518-927

CATALOG NUMBER: SA4XXDIP-C350D1035U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	452.6	452.6	452.6	452.6	452.6	452.6	452.6
2.5°	477.1	477.4	478.7	479.7	480.1	481.6	481.6
5°	519.0	522.1	528.3	528.9	529.8	534.7	530.9
7.5°	568.1	576.2	581.5	586.4	588.0	590.2	589.8
10°	599.6	611.6	617.6	627.2	627.5	629.9	628.4
12.5°	631.2	645.2	656.1	657.9	665.9	667.2	669.2
15°	676.0	690.9	706.1	711.5	722.5	725.2	729.3
17.5°	718.2	733.3	744.0	758.0	762.6	768.7	764.5
20°	741.3	757.8	771.3	782.4	787.0	790.4	790.0
22.5°	755.3	771.9	782.8	791.2	795.6	797.0	796.9
25°	764.0	773.6	777.0	780.1	775.2	773.6	774.3
27.5°	739.7	737.2	728.4	716.8	704.9	695.4	690.1
30°	706.2	691.7	678.3	655.1	643.1	636.0	629.5
32.5°	658.9	635.6	610.1	588.7	575.1	564.6	563.0
35°	577.7	542.8	511.4	485.4	471.9	460.5	457.8
37.5°	491.1	454.9	426.7	403.7	389.2	381.1	373.6
40°	433.6	402.5	374.8	355.3	344.2	338.4	333.7
42.5°	389.4	361.0	333.4	318.5	308.6	305.0	302.2
45°	328.3	301.8	282.7	271.5	265.7	259.7	256.8
47.5°	279.3	257.9	245.3	235.7	229.4	225.9	224.1
50°	251.6	234.0	222.8	215.4	209.8	207.0	205.5
52.5°	227.0	212.5	203.1	197.3	193.5	191.4	190.8
55°	195.5	184.5	178.5	173.4	170.6	168.7	168.0
57.5°	170.0	161.4	156.6	152.4	151.3	149.8	149.2
60°	153.2	146.6	142.5	139.7	138.7	136.9	137.2
62.5°	138.3	132.9	129.4	127.9	126.6	125.0	125.6
65°	117.0	113.0	111.1	109.7	108.2	107.3	108.0
67.5°	98.2	95.5	92.9	92.1	91.3	91.2	90.4
70°	85.9	83.7	81.4	80.8	80.8	80.1	79.9
72.5°	74.0	72.4	70.9	70.4	69.9	70.2	69.4
75°	57.2	55.8	55.3	54.7	54.6	54.6	54.0
77.5°	42.2	41.3	40.4	40.4	39.7	39.5	39.4
80°	32.1	31.7	31.0	31.0	30.6	30.7	30.3
82.5°	24.1	23.6	23.4	23.1	22.6	22.7	22.3
85°	12.9	12.4	12.2	11.6	11.2	11.6	11.2
87.5°	8.6	8.6	8.6	8.4	8.3	8.4	8.1
90°	20.6	21.6	22.3	22.7	23.1	23.4	23.7
92.5°	33.2	33.8	34.3	34.5	34.7	34.9	35.1
95°	61.7	62.2	62.5	62.5	62.5	62.5	62.5
97.5°	97.0	97.6	97.9	97.9	97.9	97.9	97.9
100°	122.0	122.4	122.6	122.6	122.6	122.6	122.6
102.5°	149.0	149.5	149.8	150.0	150.1	150.3	150.4
105°	189.8	190.3	190.8	191.3	191.9	192.4	192.9
107.5°	233.8	234.2	234.5	234.5	234.4	234.4	234.3
110°	262.2	261.9	262.0	262.5	263.0	263.6	264.1



TEST NUMBER: P332518-927

CATALOG NUMBER: SA4XXDIP-C350D1035U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	294.1	294.1	294.1	294.1	294.2	294.4	294.5
115°	342.6	342.5	342.3	342.1	341.9	341.7	341.6
117.5°	389.0	388.4	387.9	387.5	387.2	386.8	386.5
120°	420.4	419.5	419.2	419.6	419.9	420.3	420.6
122.5°	452.9	452.3	451.6	451.0	450.4	449.7	449.1
125°	500.3	499.9	499.6	499.2	498.8	498.5	498.1
127.5°	545.3	544.9	544.6	544.4	544.1	543.8	543.5
130°	576.9	576.6	576.1	575.4	574.6	573.9	573.2
132.5°	606.7	606.3	606.0	605.7	605.5	605.1	604.9
135°	651.3	650.9	650.5	650.0	649.4	648.9	648.4
137.5°	694.3	693.9	693.6	693.8	693.9	694.0	694.1
140°	722.9	722.8	722.6	722.5	722.2	722.1	721.9
142.5°	750.0	750.0	749.9	749.9	749.8	749.8	749.7
145°	790.2	790.0	789.6	789.1	788.6	788.1	787.5
147.5°	826.8	826.6	826.5	826.3	826.2	826.0	825.9
150°	850.0	850.0	849.9	849.8	849.5	849.4	849.2
152.5°	872.1	872.6	872.6	872.1	871.6	871.2	870.7
155°	902.7	903.4	903.4	902.7	902.1	901.3	900.6
157.5°	929.2	929.8	929.7	929.2	928.5	928.0	927.3
160°	945.7	946.2	946.0	945.2	944.3	943.4	942.5
162.5°	960.8	961.8	961.9	961.0	960.1	959.3	958.3
165°	980.5	981.5	981.7	981.0	980.3	979.6	978.9
167.5°	997.0	998.0	998.0	996.9	995.8	994.7	993.6
170°	1005.8	1006.9	1006.7	1005.5	1004.2	1003.1	1001.8
172.5°	1012.5	1013.8	1013.7	1012.5	1011.2	1010.0	1008.8
175°	1019.8	1021.0	1021.0	1019.8	1018.5	1017.3	1016.1
177.5°	1023.4	1024.5	1024.4	1023.3	1022.1	1021.0	1019.9
180°	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4

(END OF REPORT)