

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332519-927

Luminaire Tested: **SA4XXDIP-C350D1035U927-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332519-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C350D1035U927-4F0-1E-UDD-A4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4178.5 lumens
Efficiency: N/A
Efficacy: 112.0 lumens/watt
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 37.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332519-927
CATALOG NUMBER: SA4XXDIP-C350D1035U927-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332519-927

CATALOG NUMBER: SA4XXDIP-C350D1035U927-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	38	38	38	30				30
1	93	89	86	82	84	80	77	74	63	61	59	48	46	45	33	33	32	25				25
2	85	78	72	67	76	70	65	61	56	52	49	42	40	38	30	28	27	22				22
3	78	69	62	56	69	62	56	51	49	45	42	37	35	32	26	25	23	18				18
4	71	61	53	47	64	55	48	43	44	39	35	33	30	28	24	22	20	16				16
5	65	54	46	41	58	49	42	37	39	34	30	30	27	24	21	19	18	14				14
6	60	48	41	35	54	44	37	32	35	30	27	27	24	21	19	17	15	12				12
7	55	44	36	31	50	39	33	28	32	27	23	24	21	18	18	15	14	11				11
8	51	39	32	27	46	36	29	25	29	24	21	22	19	16	16	14	12	10				10
9	48	36	29	24	43	33	26	22	26	22	18	20	17	15	15	13	11	9				9
10	44	33	26	21	40	30	24	20	24	20	16	19	16	13	14	12	10	8				8

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	3654	3654	3654	3654
5°	4302	3663	3233	3663
10°	5151	3647	2911	3647
15°	6095	3611	2674	3611
20°	6787	3572	2461	3572
25°	6897	3517	2314	3517
30°	5868	3464	2269	3464
35°	4512	3377	2269	3377
40°	3517	3276	2312	3276
45°	2932	3123	2351	3123
50°	2581	2936	2430	2936
55°	2365	2712	2528	2712
60°	2215	2512	2645	2512
65°	2063	2288	2743	2288
70°	1886	2065	2804	2065
75°	1684	1818	2773	1818
80°	1409	1492	2687	1492
85°	1037	1074	2566	1074



TEST NUMBER: P332519-927

CATALOG NUMBER: SA4XXDIP-C350D1035U927-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.1	1.1
10°-20°	135.9	3.3
20°-30°	215.5	5.2
30°-40°	239.8	5.7
40°-50°	218.3	5.2
50°-60°	178.4	4.3
60°-70°	127.4	3.0
70°-80°	70.1	1.7
80°-90°	21.4	0.5
90°-100°	290.8	7.0
100°-110°	605.1	14.5
110°-120°	542.0	13.0
120°-130°	455.9	10.9
130°-140°	380.1	9.1
140°-150°	290.4	7.0
150°-160°	204.1	4.9
160°-170°	120.1	2.9
170°-180°	39.1	0.9
0°-30°	395.5	9.5
0°-40°	635.3	15.2
0°-60°	1032.1	24.7
0°-90°	1250.9	29.9
90°-120°	1437.9	34.4
90°-150°	2564.4	61.4
90°-180°	2928.0	70.1
0°-180°	4178.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	453	453	453	453	453	
5°	531	452	399	452	531	54
15°	729	432	320	432	729	206
25°	774	395	260	395	774	341
35°	458	343	230	343	458	291
45°	257	274	206	274	257	202
55°	168	193	180	193	168	152
65°	108	120	144	120	108	107
75°	54	58	89	58	54	57
85°	11	12	28	12	11	14
90°	17	1	17	1	17	14
95°	193	26	193	26	193	299
105°	1113	92	1113	92	1113	1100
115°	1068	163	1068	163	1068	1061
125°	852	227	852	227	852	775
135°	762	270	762	270	762	588
145°	622	311	622	311	622	395
155°	521	354	521	354	521	243
165°	455	385	455	385	455	130
175°	410	402	410	402	410	40
180°	402	402	402	402	402	



TEST NUMBER: P332519-927

CATALOG NUMBER: SA4XXDIP-C350D1035U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6
2.5°	481.6	481.6	480.1	479.7	478.7	477.4	477.1	474.6	469.8	467.5	467.0
5°	530.9	534.7	529.8	528.9	528.3	522.1	519.0	515.2	506.6	501.5	497.6
7.5°	589.8	590.2	588.0	586.4	581.5	576.2	568.1	559.4	549.1	538.5	530.4
10°	628.4	629.9	627.5	627.2	617.6	611.6	599.6	589.5	577.8	564.9	553.1
12.5°	669.2	667.2	665.9	657.9	656.1	645.2	631.2	620.8	602.9	588.0	572.3
15°	729.3	725.2	722.5	711.5	706.1	690.9	676.0	664.6	641.2	618.9	602.0
17.5°	764.5	768.7	762.6	758.0	744.0	733.3	718.2	694.2	675.9	648.2	626.9
20°	790.0	790.4	787.0	782.4	771.3	757.8	741.3	715.1	693.2	665.6	636.3
22.5°	796.9	797.0	795.6	791.2	782.8	771.9	755.3	733.3	706.8	676.8	647.5
25°	774.3	773.6	775.2	780.1	777.0	773.6	764.0	747.7	722.9	691.3	659.7
27.5°	690.1	695.4	704.9	716.8	728.4	737.2	739.7	736.3	721.0	695.0	661.9
30°	629.5	636.0	643.1	655.1	678.3	691.7	706.2	717.3	711.1	690.3	659.6
32.5°	563.0	564.6	575.1	588.7	610.1	635.6	658.9	681.4	688.8	677.9	652.2
35°	457.8	460.5	471.9	485.4	511.4	542.8	577.7	608.8	634.5	644.8	631.6
37.5°	373.6	381.1	389.2	403.7	426.7	454.9	491.1	531.4	569.7	595.3	599.7
40°	333.7	338.4	344.2	355.3	374.8	402.5	433.6	479.7	520.5	557.2	569.2
42.5°	302.2	305.0	308.6	318.5	333.4	361.0	389.4	430.0	470.8	514.8	534.9
45°	256.8	259.7	265.7	271.5	282.7	301.8	328.3	361.6	402.7	445.0	482.2
47.5°	224.1	225.9	229.4	235.7	245.3	257.9	279.3	307.2	345.2	386.4	426.0
50°	205.5	207.0	209.8	215.4	222.8	234.0	251.6	277.7	307.4	348.9	387.7
52.5°	190.8	191.4	193.5	197.3	203.1	212.5	227.0	248.6	276.3	313.2	351.9
55°	168.0	168.7	170.6	173.4	178.5	184.5	195.5	211.7	235.8	267.9	301.5
57.5°	149.2	149.8	151.3	152.4	156.6	161.4	170.0	181.5	199.8	227.0	257.0
60°	137.2	136.9	138.7	139.7	142.5	146.6	153.2	164.2	180.1	202.1	229.7
62.5°	125.6	125.0	126.6	127.9	129.4	132.9	138.3	146.9	159.9	179.7	203.6
65°	108.0	107.3	108.2	109.7	111.1	113.0	117.0	124.7	135.0	149.2	167.4
67.5°	90.4	91.2	91.3	92.1	92.9	95.5	98.2	103.6	110.9	122.3	137.7
70°	79.9	80.1	80.8	80.8	81.4	83.7	85.9	89.0	96.2	106.7	119.2
72.5°	69.4	70.2	69.9	70.4	70.9	72.4	74.0	77.1	83.1	90.9	101.6
75°	54.0	54.6	54.6	54.7	55.3	55.8	57.2	59.4	63.8	69.6	76.8
77.5°	39.4	39.5	39.7	40.4	40.4	41.3	42.2	44.0	46.2	50.1	54.7
80°	30.3	30.7	30.6	31.0	31.0	31.7	32.1	34.3	35.3	37.9	41.4
82.5°	22.3	22.7	22.6	23.1	23.4	23.6	24.1	25.0	26.0	28.3	29.7
85°	11.2	11.6	11.2	11.6	12.2	12.4	12.9	13.2	13.9	14.4	15.8
87.5°	6.7	7.1	7.2	7.2	7.4	7.5	7.5	7.2	7.6	7.9	8.2
90°	16.6	16.6	17.4	16.6	15.8	15.8	15.1	14.3	13.5	14.3	12.7
92.5°	60.9	60.9	63.6	67.9	77.2	93.0	116.9	155.3	209.0	250.9	219.5
95°	193.0	203.3	217.5	242.0	280.7	357.4	463.4	586.0	662.7	644.5	486.4
97.5°	515.8	532.3	556.0	603.6	660.4	742.9	820.2	865.9	832.6	678.8	455.2
100°	725.2	731.5	755.3	803.5	872.3	930.8	969.6	953.8	838.3	635.8	412.8
102.5°	907.4	912.5	937.5	972.4	1014.6	1039.0	1027.8	949.4	790.8	582.1	384.4
105°	1112.7	1117.5	1128.5	1134.9	1133.3	1100.8	1022.5	885.7	704.6	518.8	359.8
107.5°	1189.0	1186.9	1179.0	1160.9	1121.9	1051.4	941.1	795.4	635.0	483.4	355.4
110°	1190.3	1183.1	1168.9	1135.7	1079.5	992.5	877.8	741.0	600.2	471.3	356.6



TEST NUMBER: P332519-927

CATALOG NUMBER: SA4XXDIP-C350D1035U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1152.9	1141.4	1121.4	1081.2	1017.5	930.5	822.1	701.2	580.7	465.6	360.4
115°	1068.4	1062.1	1036.8	989.4	926.9	851.0	758.4	661.2	562.3	462.6	367.7
117.5°	982.9	977.9	952.4	912.5	859.2	794.8	722.1	641.5	554.1	461.8	375.5
120°	934.8	926.1	905.5	870.7	825.6	769.5	706.2	632.6	549.6	461.8	381.2
122.5°	896.8	888.1	870.7	841.0	802.9	753.7	696.1	625.1	544.5	461.2	386.9
125°	852.5	847.8	832.7	809.8	778.2	734.7	680.1	612.1	536.2	460.3	395.5
127.5°	826.6	821.8	809.2	788.8	757.0	715.7	661.3	596.3	525.0	458.5	402.2
130°	811.4	806.7	794.0	774.2	741.8	699.9	646.1	583.7	518.0	457.9	407.3
132.5°	794.3	789.6	777.5	755.3	723.5	681.5	629.1	570.4	511.7	457.2	411.7
135°	762.4	757.6	745.0	722.9	691.2	651.6	603.4	552.0	502.2	456.3	418.4
137.5°	722.9	717.2	706.7	684.8	655.3	619.6	578.9	535.4	493.9	456.1	422.3
140°	694.3	688.0	677.0	659.6	631.8	598.7	563.1	525.9	489.6	455.5	425.5
142.5°	664.0	659.6	649.7	633.6	609.1	580.4	549.8	517.1	485.8	455.5	428.0
145°	622.4	618.5	610.5	597.1	577.3	555.2	531.5	504.5	479.3	453.9	429.4
147.5°	585.5	584.2	578.1	566.6	552.0	534.6	515.6	494.2	473.4	451.1	430.2
150°	564.7	563.9	559.1	548.8	536.2	522.0	506.1	488.0	469.0	449.2	430.2
152.5°	545.7	544.9	542.0	533.7	522.9	511.2	496.6	481.0	463.9	446.0	429.0
155°	521.2	521.2	518.8	512.5	504.5	495.0	483.2	470.6	456.3	441.3	427.1
157.5°	499.6	499.6	498.2	493.5	487.5	479.9	469.9	459.3	448.5	436.4	425.0
160°	486.4	486.4	485.6	480.9	476.1	469.8	461.1	452.3	442.9	432.6	423.1
162.5°	473.7	474.4	473.6	468.8	465.3	459.6	452.8	445.4	437.8	428.8	421.2
165°	454.7	455.5	456.3	453.1	450.0	446.0	440.5	435.8	429.4	423.1	417.6
167.5°	439.7	440.4	440.5	438.5	436.9	434.5	430.1	426.4	421.8	417.4	413.8
170°	430.2	430.2	431.0	430.2	428.6	426.3	423.1	420.7	416.8	413.6	411.2
172.5°	420.7	422.0	422.8	422.0	421.0	419.3	417.4	415.7	412.3	409.8	408.7
175°	409.6	411.2	412.8	411.2	411.2	411.2	409.6	408.8	407.3	405.7	405.7
177.5°	403.1	404.4	405.7	405.0	405.7	405.0	405.0	404.4	403.8	403.1	403.1
180°	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5



TEST NUMBER: P332519-927

CATALOG NUMBER: SA4XXDIP-C350D1035U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6
2.5°	467.1	465.0	463.5	462.3	459.1	457.1	455.6	453.5	451.1	448.5	445.4
5°	493.6	487.3	482.6	475.5	468.7	463.1	457.2	452.0	445.7	438.7	433.6
7.5°	521.5	512.0	499.9	489.3	477.4	467.1	458.0	448.5	438.7	429.1	420.4
10°	539.2	527.0	513.5	497.6	482.6	469.3	456.9	444.9	433.2	421.7	411.7
12.5°	558.3	543.0	523.1	504.5	487.7	469.8	455.0	440.2	426.2	414.0	402.4
15°	583.8	561.9	538.8	513.9	491.8	471.0	450.5	432.0	416.2	400.1	388.8
17.5°	599.5	572.4	546.1	520.0	493.2	466.9	444.9	423.5	403.8	387.8	373.6
20°	609.9	582.9	550.1	524.0	492.2	465.2	439.7	415.8	395.2	378.2	363.5
22.5°	618.9	587.7	554.8	520.5	488.9	460.2	432.3	408.4	387.3	369.3	355.3
25°	623.8	588.0	552.3	518.2	482.2	448.3	422.9	394.8	372.3	353.4	338.4
27.5°	624.3	586.0	545.7	507.8	470.6	439.0	407.1	381.9	358.6	338.6	324.2
30°	622.7	582.7	539.4	498.4	461.1	426.7	398.9	371.6	347.8	327.9	312.9
32.5°	617.3	575.8	531.3	487.8	449.2	415.6	387.0	360.9	337.7	318.1	302.4
35°	602.2	561.1	513.7	468.5	429.0	395.1	369.2	342.7	319.5	301.0	285.7
37.5°	578.5	541.4	493.1	446.4	407.5	373.4	347.8	323.9	302.9	284.1	268.5
40°	557.8	525.1	476.7	431.2	389.2	356.8	332.8	310.9	290.0	272.2	257.4
42.5°	533.9	505.5	460.9	412.6	372.1	339.5	316.2	296.4	276.9	260.4	245.6
45°	491.4	472.6	430.6	386.0	343.8	313.1	290.8	273.5	257.1	240.9	228.5
47.5°	442.5	433.2	397.8	355.5	315.4	285.1	265.8	249.9	235.4	221.7	210.8
50°	409.6	405.1	374.6	333.7	295.5	267.0	247.5	233.8	221.4	209.5	199.1
52.5°	377.2	377.1	349.5	312.1	276.7	249.3	229.9	217.1	206.4	196.7	187.4
55°	327.7	333.0	311.4	278.1	246.4	221.6	204.1	192.7	185.2	177.2	170.2
57.5°	282.3	291.0	273.1	243.8	217.3	194.6	179.4	170.8	162.8	157.9	152.8
60°	252.5	260.8	246.9	222.2	197.3	177.8	163.3	155.6	148.7	145.3	141.7
62.5°	226.2	233.5	223.2	200.3	178.6	159.9	147.7	140.3	135.6	132.0	129.6
65°	188.5	194.6	185.8	169.1	150.5	135.5	125.6	119.8	115.3	113.8	111.1
67.5°	152.3	158.0	153.2	139.0	124.1	112.7	105.0	99.4	96.7	95.5	93.6
70°	130.9	136.5	131.4	119.1	107.6	98.1	90.7	87.5	84.8	84.2	81.6
72.5°	112.7	116.5	111.5	101.8	92.1	84.0	78.3	74.9	73.5	72.5	71.1
75°	84.5	87.9	84.5	77.1	70.1	64.5	59.7	58.3	56.6	56.1	55.1
77.5°	59.8	62.7	60.2	55.5	50.3	45.9	43.3	41.7	41.3	40.3	40.8
80°	45.7	47.6	45.2	42.0	37.9	34.9	33.0	32.1	31.0	30.6	31.3
82.5°	32.9	33.7	32.4	30.3	27.3	25.3	24.0	22.9	22.7	22.7	22.7
85°	17.0	16.9	16.7	14.8	13.9	12.6	11.8	11.6	11.4	11.8	12.2
87.5°	7.9	8.1	7.0	6.3	5.8	5.1	4.5	4.0	4.5	5.1	5.5
90°	11.1	11.1	6.3	6.3	5.5	4.8	2.4	0.8	2.4	4.8	5.5
92.5°	159.8	98.4	58.2	41.7	30.2	20.6	13.2	9.0	13.2	20.6	30.2
95°	297.4	167.6	98.9	65.7	46.7	36.4	28.4	26.1	28.4	36.4	46.7
97.5°	267.3	160.3	107.3	79.4	63.1	53.6	46.8	46.8	46.8	53.6	63.1
100°	251.5	162.2	115.5	90.2	75.1	65.7	60.1	60.1	60.1	65.7	75.1
102.5°	247.1	168.4	126.2	102.2	87.8	78.9	74.0	72.7	74.0	78.9	87.8
105°	249.1	183.5	145.5	122.6	108.4	98.9	94.9	92.5	94.9	98.9	108.4
107.5°	260.8	201.1	166.2	143.6	130.0	119.9	116.0	114.4	116.0	119.9	130.0
110°	269.7	214.3	179.5	158.2	143.9	134.4	130.5	128.9	130.5	134.4	143.9



TEST NUMBER: P332519-927

CATALOG NUMBER: SA4XXDIP-C350D1035U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	279.2	227.0	193.5	172.1	157.9	149.0	144.4	142.8	144.4	149.0	157.9
115°	294.2	246.8	215.1	193.8	178.7	170.8	165.2	163.0	165.2	170.8	178.7
117.5°	309.5	265.9	235.8	213.7	199.6	190.9	186.0	183.8	186.0	190.9	199.6
120°	320.3	279.2	249.1	227.0	213.5	204.9	199.3	197.7	199.3	204.9	213.5
122.5°	330.4	291.8	261.7	240.3	225.5	217.5	211.9	210.4	211.9	217.5	225.5
125°	345.6	309.2	280.7	258.6	243.6	234.9	230.1	227.0	230.1	234.9	243.6
127.5°	358.7	325.3	297.9	275.5	259.8	249.9	244.2	241.7	244.2	249.9	259.8
130°	366.9	336.1	309.2	286.3	271.2	259.4	253.1	249.9	253.1	259.4	271.2
132.5°	375.2	345.0	318.1	296.4	280.1	268.9	260.6	258.1	260.6	268.9	280.1
135°	386.0	357.4	331.4	310.8	294.2	280.7	272.8	269.7	272.8	280.7	294.2
137.5°	393.6	366.9	342.6	323.0	305.7	292.9	284.2	281.2	284.2	292.9	305.7
140°	398.5	373.3	349.6	330.6	313.9	300.6	291.8	289.5	291.8	300.6	313.9
142.5°	402.3	379.0	355.8	337.5	321.5	308.7	300.7	298.3	300.7	308.7	321.5
145°	406.5	385.2	364.6	347.2	332.2	321.1	313.1	310.8	313.1	321.1	332.2
147.5°	410.1	391.5	372.2	356.5	344.0	332.6	325.7	324.9	325.7	332.6	344.0
150°	412.0	394.7	377.2	362.2	350.4	340.9	334.5	333.7	334.5	340.9	350.4
152.5°	413.3	397.2	381.7	367.9	357.3	348.5	342.1	342.0	342.1	348.5	357.3
155°	414.4	400.9	387.5	375.7	366.9	359.0	354.3	353.5	354.3	359.0	366.9
157.5°	414.4	403.6	392.3	382.9	375.3	369.2	364.7	364.7	364.7	369.2	375.3
160°	414.4	404.9	395.5	386.7	380.4	374.9	371.7	371.7	371.7	374.9	380.4
162.5°	414.4	406.2	397.4	390.5	384.8	379.9	377.4	378.0	377.4	379.9	384.8
165°	412.8	406.5	399.3	394.7	390.7	386.7	385.2	385.2	385.2	386.7	390.7
167.5°	410.9	406.3	401.1	397.5	395.3	392.3	391.5	392.3	391.5	392.3	395.3
170°	409.6	405.7	401.7	399.3	397.8	395.5	394.7	395.5	394.7	395.5	397.8
172.5°	408.4	405.0	402.3	400.6	399.7	397.9	397.8	398.5	397.8	397.9	399.7
175°	406.5	404.1	402.5	402.5	401.7	400.9	400.9	401.7	400.9	400.9	401.7
177.5°	404.4	403.1	402.5	402.5	402.5	401.9	402.5	403.1	402.5	401.9	402.5
180°	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5



TEST NUMBER: P332519-927

CATALOG NUMBER: SA4XXDIP-C350D1035U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6
2.5°	443.9	442.5	440.6	437.9	435.6	433.2	432.6	431.7	433.6	432.1	431.6
5°	429.4	425.4	420.3	414.5	411.1	406.3	405.4	403.5	401.6	401.4	399.5
7.5°	413.9	408.1	401.5	395.6	390.1	384.8	381.3	380.6	377.8	376.1	374.3
10°	404.0	396.9	389.2	383.6	377.2	371.6	367.7	365.4	363.5	361.5	359.6
12.5°	392.4	384.8	378.4	372.3	364.8	360.5	354.0	350.1	349.7	349.7	344.9
15°	378.7	371.2	361.5	352.8	348.7	340.5	336.9	332.4	329.6	326.8	324.6
17.5°	363.1	353.8	346.2	336.3	328.4	321.9	317.2	314.5	310.2	306.3	303.4
20°	353.4	343.5	335.4	324.9	316.3	308.2	304.3	300.6	297.4	294.0	290.8
22.5°	343.5	333.1	323.3	313.1	305.1	296.5	292.7	287.6	284.6	282.7	279.6
25°	327.9	316.6	305.4	295.6	287.4	279.9	274.9	270.9	267.5	266.0	264.0
27.5°	310.9	299.8	288.9	277.8	268.5	263.0	259.0	256.0	254.1	252.1	251.1
30°	300.2	288.5	276.9	266.6	258.0	252.5	248.8	246.8	245.3	244.3	243.4
32.5°	289.2	277.7	265.5	256.1	248.3	243.5	240.7	238.6	237.9	237.6	237.2
35°	271.6	260.1	248.8	240.3	233.1	231.2	228.7	227.6	227.2	228.5	229.1
37.5°	254.7	243.9	233.5	225.4	220.5	217.9	217.0	217.1	218.4	219.5	220.9
40°	243.8	233.2	223.5	216.3	211.8	210.2	209.8	210.7	212.2	213.6	215.1
42.5°	233.1	222.8	213.9	207.2	204.1	202.5	202.7	203.7	205.8	207.4	209.6
45°	216.6	207.9	199.3	193.8	191.2	191.6	191.6	193.3	195.4	197.8	200.3
47.5°	201.0	192.3	185.2	180.6	179.3	179.0	180.0	182.2	185.1	188.1	191.5
50°	190.5	182.2	176.0	171.9	170.4	171.0	172.5	174.5	178.1	181.9	185.4
52.5°	179.8	172.3	166.6	162.8	161.7	162.7	164.2	167.5	170.6	174.7	179.0
55°	163.3	156.9	152.4	149.6	149.2	149.8	151.5	155.0	159.5	164.6	168.7
57.5°	146.9	141.5	137.4	135.5	135.6	136.2	138.9	143.1	148.0	153.4	158.7
60°	135.7	130.9	127.5	126.0	126.2	127.3	130.7	134.6	140.6	145.8	151.5
62.5°	125.2	121.0	117.7	116.4	116.1	118.6	121.8	125.9	131.9	137.8	143.9
65°	108.4	105.0	102.3	101.6	102.2	104.1	108.2	113.6	118.7	124.8	131.3
67.5°	91.9	89.1	87.3	87.6	88.3	91.1	94.5	99.2	105.0	111.4	117.6
70°	81.4	78.7	77.2	77.4	78.6	81.9	84.9	89.6	95.8	102.3	107.6
72.5°	70.6	68.8	67.5	68.3	69.4	71.7	75.5	80.2	85.6	91.7	97.3
75°	54.2	54.2	53.5	54.0	55.7	57.9	60.8	65.6	71.1	76.0	80.4
77.5°	40.2	39.8	40.2	41.0	41.9	44.6	47.8	51.3	55.4	60.3	64.0
80°	30.7	31.0	31.8	33.0	33.4	35.4	38.8	42.0	45.2	49.3	52.8
82.5°	23.1	23.3	23.8	25.2	25.6	27.8	29.9	33.1	36.0	38.8	41.7
85°	12.6	12.6	13.5	14.1	15.0	16.5	17.8	19.7	22.3	24.2	27.0
87.5°	6.1	6.1	7.6	7.9	8.7	9.7	9.9	11.7	12.4	13.4	14.7
90°	6.3	6.3	11.1	11.1	12.7	14.3	13.5	14.3	15.1	15.8	15.8
92.5°	41.7	58.2	98.4	159.8	219.5	250.9	209.0	155.3	116.9	93.0	77.2
95°	65.7	98.9	167.6	297.4	486.4	644.5	662.7	586.0	463.4	357.4	280.7
97.5°	79.4	107.3	160.3	267.3	455.2	678.8	832.6	865.9	820.2	742.9	660.4
100°	90.2	115.5	162.2	251.5	412.8	635.8	838.3	953.8	969.6	930.8	872.3
102.5°	102.2	126.2	168.4	247.1	384.4	582.1	790.8	949.4	1027.8	1039.0	1014.6
105°	122.6	145.5	183.5	249.1	359.8	518.8	704.6	885.7	1022.5	1100.8	1133.3
107.5°	143.6	166.2	201.1	260.8	355.4	483.4	635.0	795.4	941.1	1051.4	1121.9
110°	158.2	179.5	214.3	269.7	356.6	471.3	600.2	741.0	877.8	992.5	1079.5



TEST NUMBER: P332519-927

CATALOG NUMBER: SA4XXDIP-C350D1035U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	172.1	193.5	227.0	279.2	360.4	465.6	580.7	701.2	822.1	930.5	1017.5
115°	193.8	215.1	246.8	294.2	367.7	462.6	562.3	661.2	758.4	851.0	926.9
117.5°	213.7	235.8	265.9	309.5	375.5	461.8	554.1	641.5	722.1	794.8	859.2
120°	227.0	249.1	279.2	320.3	381.2	461.8	549.6	632.6	706.2	769.5	825.6
122.5°	240.3	261.7	291.8	330.4	386.9	461.2	544.5	625.1	696.1	753.7	802.9
125°	258.6	280.7	309.2	345.6	395.5	460.3	536.2	612.1	680.1	734.7	778.2
127.5°	275.5	297.9	325.3	358.7	402.2	458.5	525.0	596.3	661.3	715.7	757.0
130°	286.3	309.2	336.1	366.9	407.3	457.9	518.0	583.7	646.1	699.9	741.8
132.5°	296.4	318.1	345.0	375.2	411.7	457.2	511.7	570.4	629.1	681.5	723.5
135°	310.8	331.4	357.4	386.0	418.4	456.3	502.2	552.0	603.4	651.6	691.2
137.5°	323.0	342.6	366.9	393.6	422.3	456.1	493.9	535.4	578.9	619.6	655.3
140°	330.6	349.6	373.3	398.5	425.5	455.5	489.6	525.9	563.1	598.7	631.8
142.5°	337.5	355.8	379.0	402.3	428.0	455.5	485.8	517.1	549.8	580.4	609.1
145°	347.2	364.6	385.2	406.5	429.4	453.9	479.3	504.5	531.5	555.2	577.3
147.5°	356.5	372.2	391.5	410.1	430.2	451.1	473.4	494.2	515.6	534.6	552.0
150°	362.2	377.2	394.7	412.0	430.2	449.2	469.0	488.0	506.1	522.0	536.2
152.5°	367.9	381.7	397.2	413.3	429.0	446.0	463.9	481.0	496.6	511.2	522.9
155°	375.7	387.5	400.9	414.4	427.1	441.3	456.3	470.6	483.2	495.0	504.5
157.5°	382.9	392.3	403.6	414.4	425.0	436.4	448.5	459.3	469.9	479.9	487.5
160°	386.7	395.5	404.9	414.4	423.1	432.6	442.9	452.3	461.1	469.8	476.1
162.5°	390.5	397.4	406.2	414.4	421.2	428.8	437.8	445.4	452.8	459.6	465.3
165°	394.7	399.3	406.5	412.8	417.6	423.1	429.4	435.8	440.5	446.0	450.0
167.5°	397.5	401.1	406.3	410.9	413.8	417.4	421.8	426.4	430.1	434.5	436.9
170°	399.3	401.7	405.7	409.6	411.2	413.6	416.8	420.7	423.1	426.3	428.6
172.5°	400.6	402.3	405.0	408.4	408.7	409.8	412.3	415.7	417.4	419.3	421.0
175°	402.5	402.5	404.1	406.5	405.7	405.7	407.3	408.8	409.6	411.2	411.2
177.5°	402.5	402.5	403.1	404.4	403.1	403.1	403.8	404.4	405.0	405.0	405.7
180°	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5



TEST NUMBER: P332519-927

CATALOG NUMBER: SA4XXDIP-C350D1035U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6
2.5°	431.3	431.0	429.9	429.8	429.9	431.0	431.3	431.6	432.1	433.6	431.7
5°	398.4	397.4	396.9	398.9	396.9	397.4	398.4	399.5	401.4	401.6	403.5
7.5°	373.6	372.9	371.2	370.7	371.2	372.9	373.6	374.3	376.1	377.8	380.6
10°	357.7	357.0	355.5	355.1	355.5	357.0	357.7	359.6	361.5	363.5	365.4
12.5°	342.4	341.0	340.6	341.0	340.6	341.0	342.4	344.9	349.7	349.7	350.1
15°	322.1	321.3	319.2	319.9	319.2	321.3	322.1	324.6	326.8	329.6	332.4
17.5°	302.1	301.2	298.7	300.9	298.7	301.2	302.1	303.4	306.3	310.2	314.5
20°	289.5	288.0	286.7	286.5	286.7	288.0	289.5	290.8	294.0	297.4	300.6
22.5°	277.5	276.2	276.0	274.8	276.0	276.2	277.5	279.6	282.7	284.6	287.6
25°	262.4	261.2	260.8	259.8	260.8	261.2	262.4	264.0	266.0	267.5	270.9
27.5°	251.0	250.3	249.6	249.9	249.6	250.3	251.0	251.1	252.1	254.1	256.0
30°	243.9	243.8	243.4	243.4	243.4	243.8	243.9	243.4	244.3	245.3	246.8
32.5°	238.1	238.1	238.3	238.3	238.3	238.1	238.1	237.2	237.6	237.9	238.6
35°	229.9	230.4	230.8	230.2	230.8	230.4	229.9	229.1	228.5	227.2	227.6
37.5°	222.4	223.0	223.6	224.2	223.6	223.0	222.4	220.9	219.5	218.4	217.1
40°	216.7	218.0	218.4	219.4	218.4	218.0	216.7	215.1	213.6	212.2	210.7
42.5°	211.4	212.8	213.7	214.0	213.7	212.8	211.4	209.6	207.4	205.8	203.7
45°	203.0	204.5	205.9	205.9	205.9	204.5	203.0	200.3	197.8	195.4	193.3
47.5°	194.5	196.6	198.0	198.3	198.0	196.6	194.5	191.5	188.1	185.1	182.2
50°	188.6	191.2	192.6	193.5	192.6	191.2	188.6	185.4	181.9	178.1	174.5
52.5°	182.9	185.5	187.3	187.7	187.3	185.5	182.9	179.0	174.7	170.6	167.5
55°	173.0	176.8	178.9	179.6	178.9	176.8	173.0	168.7	164.6	159.5	155.0
57.5°	163.7	167.2	169.6	170.2	169.6	167.2	163.7	158.7	153.4	148.0	143.1
60°	156.5	160.3	163.3	163.8	163.3	160.3	156.5	151.5	145.8	140.6	134.6
62.5°	149.2	153.1	155.8	157.2	155.8	153.1	149.2	143.9	137.8	131.9	125.9
65°	136.5	140.5	143.1	143.6	143.1	140.5	136.5	131.3	124.8	118.7	113.6
67.5°	122.6	126.6	128.3	129.4	128.3	126.6	122.6	117.6	111.4	105.0	99.2
70°	112.9	116.1	118.0	118.8	118.0	116.1	112.9	107.6	102.3	95.8	89.6
72.5°	101.8	105.1	107.3	107.5	107.3	105.1	101.8	97.3	91.7	85.6	80.2
75°	84.8	87.8	88.9	88.9	88.9	87.8	84.8	80.4	76.0	71.1	65.6
77.5°	67.1	68.6	70.0	70.3	70.0	68.6	67.1	64.0	60.3	55.4	51.3
80°	55.7	56.6	57.8	57.8	57.8	56.6	55.7	52.8	49.3	45.2	42.0
82.5°	44.0	44.8	45.9	45.7	45.9	44.8	44.0	41.7	38.8	36.0	33.1
85°	26.6	28.3	28.1	27.7	28.1	28.3	26.6	27.0	24.2	22.3	19.7
87.5°	15.3	15.6	15.9	16.2	15.9	15.6	15.3	14.7	13.4	12.4	11.7
90°	16.6	17.4	16.6	16.6	16.6	17.4	16.6	15.8	15.8	15.1	14.3
92.5°	67.9	63.6	60.9	60.9	60.9	63.6	67.9	77.2	93.0	116.9	155.3
95°	242.0	217.5	203.3	193.0	203.3	217.5	242.0	280.7	357.4	463.4	586.0
97.5°	603.6	556.0	532.3	515.8	532.3	556.0	603.6	660.4	742.9	820.2	865.9
100°	803.5	755.3	731.5	725.2	731.5	755.3	803.5	872.3	930.8	969.6	953.8
102.5°	972.4	937.5	912.5	907.4	912.5	937.5	972.4	1014.6	1039.0	1027.8	949.4
105°	1134.9	1128.5	1117.5	1112.7	1117.5	1128.5	1134.9	1133.3	1100.8	1022.5	885.7
107.5°	1160.9	1179.0	1186.9	1189.0	1186.9	1179.0	1160.9	1121.9	1051.4	941.1	795.4
110°	1135.7	1168.9	1183.1	1190.3	1183.1	1168.9	1135.7	1079.5	992.5	877.8	741.0



TEST NUMBER: P332519-927

CATALOG NUMBER: SA4XXDIP-C350D1035U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1081.2	1121.4	1141.4	1152.9	1141.4	1121.4	1081.2	1017.5	930.5	822.1	701.2
115°	989.4	1036.8	1062.1	1068.4	1062.1	1036.8	989.4	926.9	851.0	758.4	661.2
117.5°	912.5	952.4	977.9	982.9	977.9	952.4	912.5	859.2	794.8	722.1	641.5
120°	870.7	905.5	926.1	934.8	926.1	905.5	870.7	825.6	769.5	706.2	632.6
122.5°	841.0	870.7	888.1	896.8	888.1	870.7	841.0	802.9	753.7	696.1	625.1
125°	809.8	832.7	847.8	852.5	847.8	832.7	809.8	778.2	734.7	680.1	612.1
127.5°	788.8	809.2	821.8	826.6	821.8	809.2	788.8	757.0	715.7	661.3	596.3
130°	774.2	794.0	806.7	811.4	806.7	794.0	774.2	741.8	699.9	646.1	583.7
132.5°	755.3	777.5	789.6	794.3	789.6	777.5	755.3	723.5	681.5	629.1	570.4
135°	722.9	745.0	757.6	762.4	757.6	745.0	722.9	691.2	651.6	603.4	552.0
137.5°	684.8	706.7	717.2	722.9	717.2	706.7	684.8	655.3	619.6	578.9	535.4
140°	659.6	677.0	688.0	694.3	688.0	677.0	659.6	631.8	598.7	563.1	525.9
142.5°	633.6	649.7	659.6	664.0	659.6	649.7	633.6	609.1	580.4	549.8	517.1
145°	597.1	610.5	618.5	622.4	618.5	610.5	597.1	577.3	555.2	531.5	504.5
147.5°	566.6	578.1	584.2	585.5	584.2	578.1	566.6	552.0	534.6	515.6	494.2
150°	548.8	559.1	563.9	564.7	563.9	559.1	548.8	536.2	522.0	506.1	488.0
152.5°	533.7	542.0	544.9	545.7	544.9	542.0	533.7	522.9	511.2	496.6	481.0
155°	512.5	518.8	521.2	521.2	521.2	518.8	512.5	504.5	495.0	483.2	470.6
157.5°	493.5	498.2	499.6	499.6	499.6	498.2	493.5	487.5	479.9	469.9	459.3
160°	480.9	485.6	486.4	486.4	486.4	485.6	480.9	476.1	469.8	461.1	452.3
162.5°	468.8	473.6	474.4	473.7	474.4	473.6	468.8	465.3	459.6	452.8	445.4
165°	453.1	456.3	455.5	454.7	455.5	456.3	453.1	450.0	446.0	440.5	435.8
167.5°	438.5	440.5	440.4	439.7	440.4	440.5	438.5	436.9	434.5	430.1	426.4
170°	430.2	431.0	430.2	430.2	430.2	431.0	430.2	428.6	426.3	423.1	420.7
172.5°	422.0	422.8	422.0	420.7	422.0	422.8	422.0	421.0	419.3	417.4	415.7
175°	411.2	412.8	411.2	409.6	411.2	412.8	411.2	411.2	411.2	409.6	408.8
177.5°	405.0	405.7	404.4	403.1	404.4	405.7	405.0	405.7	405.0	405.0	404.4
180°	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5



TEST NUMBER: P332519-927

CATALOG NUMBER: SA4XXDIP-C350D1035U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6
2.5°	432.6	433.2	435.6	437.9	440.6	442.5	443.9	445.4	448.5	451.1	453.5
5°	405.4	406.3	411.1	414.5	420.3	425.4	429.4	433.6	438.7	445.7	452.0
7.5°	381.3	384.8	390.1	395.6	401.5	408.1	413.9	420.4	429.1	438.7	448.5
10°	367.7	371.6	377.2	383.6	389.2	396.9	404.0	411.7	421.7	433.2	444.9
12.5°	354.0	360.5	364.8	372.3	378.4	384.8	392.4	402.4	414.0	426.2	440.2
15°	336.9	340.5	348.7	352.8	361.5	371.2	378.7	388.8	400.1	416.2	432.0
17.5°	317.2	321.9	328.4	336.3	346.2	353.8	363.1	373.6	387.8	403.8	423.5
20°	304.3	308.2	316.3	324.9	335.4	343.5	353.4	363.5	378.2	395.2	415.8
22.5°	292.7	296.5	305.1	313.1	323.3	333.1	343.5	355.3	369.3	387.3	408.4
25°	274.9	279.9	287.4	295.6	305.4	316.6	327.9	338.4	353.4	372.3	394.8
27.5°	259.0	263.0	268.5	277.8	288.9	299.8	310.9	324.2	338.6	358.6	381.9
30°	248.8	252.5	258.0	266.6	276.9	288.5	300.2	312.9	327.9	347.8	371.6
32.5°	240.7	243.5	248.3	256.1	265.5	277.7	289.2	302.4	318.1	337.7	360.9
35°	228.7	231.2	233.1	240.3	248.8	260.1	271.6	285.7	301.0	319.5	342.7
37.5°	217.0	217.9	220.5	225.4	233.5	243.9	254.7	268.5	284.1	302.9	323.9
40°	209.8	210.2	211.8	216.3	223.5	233.2	243.8	257.4	272.2	290.0	310.9
42.5°	202.7	202.5	204.1	207.2	213.9	222.8	233.1	245.6	260.4	276.9	296.4
45°	191.6	191.6	191.2	193.8	199.3	207.9	216.6	228.5	240.9	257.1	273.5
47.5°	180.0	179.0	179.3	180.6	185.2	192.3	201.0	210.8	221.7	235.4	249.9
50°	172.5	171.0	170.4	171.9	176.0	182.2	190.5	199.1	209.5	221.4	233.8
52.5°	164.2	162.7	161.7	162.8	166.6	172.3	179.8	187.4	196.7	206.4	217.1
55°	151.5	149.8	149.2	149.6	152.4	156.9	163.3	170.2	177.2	185.2	192.7
57.5°	138.9	136.2	135.6	135.5	137.4	141.5	146.9	152.8	157.9	162.8	170.8
60°	130.7	127.3	126.2	126.0	127.5	130.9	135.7	141.7	145.3	148.7	155.6
62.5°	121.8	118.6	116.1	116.4	117.7	121.0	125.2	129.6	132.0	135.6	140.3
65°	108.2	104.1	102.2	101.6	102.3	105.0	108.4	111.1	113.8	115.3	119.8
67.5°	94.5	91.1	88.3	87.6	87.3	89.1	91.9	93.6	95.5	96.7	99.4
70°	84.9	81.9	78.6	77.4	77.2	78.7	81.4	81.6	84.2	84.8	87.5
72.5°	75.5	71.7	69.4	68.3	67.5	68.8	70.6	71.1	72.5	73.5	74.9
75°	60.8	57.9	55.7	54.0	53.5	54.2	54.2	55.1	56.1	56.6	58.3
77.5°	47.8	44.6	41.9	41.0	40.2	39.8	40.2	40.8	40.3	41.3	41.7
80°	38.8	35.4	33.4	33.0	31.8	31.0	30.7	31.3	30.6	31.0	32.1
82.5°	29.9	27.8	25.6	25.2	23.8	23.3	23.1	22.7	22.7	22.7	22.9
85°	17.8	16.5	15.0	14.1	13.5	12.6	12.6	12.2	11.8	11.4	11.6
87.5°	9.9	9.7	8.7	7.9	7.6	6.1	6.1	5.5	5.1	4.5	4.0
90°	13.5	14.3	12.7	11.1	11.1	6.3	6.3	5.5	4.8	2.4	0.8
92.5°	209.0	250.9	219.5	159.8	98.4	58.2	41.7	30.2	20.6	13.2	9.0
95°	662.7	644.5	486.4	297.4	167.6	98.9	65.7	46.7	36.4	28.4	26.1
97.5°	832.6	678.8	455.2	267.3	160.3	107.3	79.4	63.1	53.6	46.8	46.8
100°	838.3	635.8	412.8	251.5	162.2	115.5	90.2	75.1	65.7	60.1	60.1
102.5°	790.8	582.1	384.4	247.1	168.4	126.2	102.2	87.8	78.9	74.0	72.7
105°	704.6	518.8	359.8	249.1	183.5	145.5	122.6	108.4	98.9	94.9	92.5
107.5°	635.0	483.4	355.4	260.8	201.1	166.2	143.6	130.0	119.9	116.0	114.4
110°	600.2	471.3	356.6	269.7	214.3	179.5	158.2	143.9	134.4	130.5	128.9



TEST NUMBER: P332519-927

CATALOG NUMBER: SA4XXDIP-C350D1035U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	580.7	465.6	360.4	279.2	227.0	193.5	172.1	157.9	149.0	144.4	142.8
115°	562.3	462.6	367.7	294.2	246.8	215.1	193.8	178.7	170.8	165.2	163.0
117.5°	554.1	461.8	375.5	309.5	265.9	235.8	213.7	199.6	190.9	186.0	183.8
120°	549.6	461.8	381.2	320.3	279.2	249.1	227.0	213.5	204.9	199.3	197.7
122.5°	544.5	461.2	386.9	330.4	291.8	261.7	240.3	225.5	217.5	211.9	210.4
125°	536.2	460.3	395.5	345.6	309.2	280.7	258.6	243.6	234.9	230.1	227.0
127.5°	525.0	458.5	402.2	358.7	325.3	297.9	275.5	259.8	249.9	244.2	241.7
130°	518.0	457.9	407.3	366.9	336.1	309.2	286.3	271.2	259.4	253.1	249.9
132.5°	511.7	457.2	411.7	375.2	345.0	318.1	296.4	280.1	268.9	260.6	258.1
135°	502.2	456.3	418.4	386.0	357.4	331.4	310.8	294.2	280.7	272.8	269.7
137.5°	493.9	456.1	422.3	393.6	366.9	342.6	323.0	305.7	292.9	284.2	281.2
140°	489.6	455.5	425.5	398.5	373.3	349.6	330.6	313.9	300.6	291.8	289.5
142.5°	485.8	455.5	428.0	402.3	379.0	355.8	337.5	321.5	308.7	300.7	298.3
145°	479.3	453.9	429.4	406.5	385.2	364.6	347.2	332.2	321.1	313.1	310.8
147.5°	473.4	451.1	430.2	410.1	391.5	372.2	356.5	344.0	332.6	325.7	324.9
150°	469.0	449.2	430.2	412.0	394.7	377.2	362.2	350.4	340.9	334.5	333.7
152.5°	463.9	446.0	429.0	413.3	397.2	381.7	367.9	357.3	348.5	342.1	342.0
155°	456.3	441.3	427.1	414.4	400.9	387.5	375.7	366.9	359.0	354.3	353.5
157.5°	448.5	436.4	425.0	414.4	403.6	392.3	382.9	375.3	369.2	364.7	364.7
160°	442.9	432.6	423.1	414.4	404.9	395.5	386.7	380.4	374.9	371.7	371.7
162.5°	437.8	428.8	421.2	414.4	406.2	397.4	390.5	384.8	379.9	377.4	378.0
165°	429.4	423.1	417.6	412.8	406.5	399.3	394.7	390.7	386.7	385.2	385.2
167.5°	421.8	417.4	413.8	410.9	406.3	401.1	397.5	395.3	392.3	391.5	392.3
170°	416.8	413.6	411.2	409.6	405.7	401.7	399.3	397.8	395.5	394.7	395.5
172.5°	412.3	409.8	408.7	408.4	405.0	402.3	400.6	399.7	397.9	397.8	398.5
175°	407.3	405.7	405.7	406.5	404.1	402.5	402.5	401.7	400.9	400.9	401.7
177.5°	403.8	403.1	403.1	404.4	403.1	402.5	402.5	402.5	401.9	402.5	403.1
180°	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5



TEST NUMBER: P332519-927

CATALOG NUMBER: SA4XXDIP-C350D1035U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6
2.5°	455.6	457.1	459.1	462.3	463.5	465.0	467.1	467.0	467.5	469.8	474.6
5°	457.2	463.1	468.7	475.5	482.6	487.3	493.6	497.6	501.5	506.6	515.2
7.5°	458.0	467.1	477.4	489.3	499.9	512.0	521.5	530.4	538.5	549.1	559.4
10°	456.9	469.3	482.6	497.6	513.5	527.0	539.2	553.1	564.9	577.8	589.5
12.5°	455.0	469.8	487.7	504.5	523.1	543.0	558.3	572.3	588.0	602.9	620.8
15°	450.5	471.0	491.8	513.9	538.8	561.9	583.8	602.0	618.9	641.2	664.6
17.5°	444.9	466.9	493.2	520.0	546.1	572.4	599.5	626.9	648.2	675.9	694.2
20°	439.7	465.2	492.2	524.0	550.1	582.9	609.9	636.3	665.6	693.2	715.1
22.5°	432.3	460.2	488.9	520.5	554.8	587.7	618.9	647.5	676.8	706.8	733.3
25°	422.9	448.3	482.2	518.2	552.3	588.0	623.8	659.7	691.3	722.9	747.7
27.5°	407.1	439.0	470.6	507.8	545.7	586.0	624.3	661.9	695.0	721.0	736.3
30°	398.9	426.7	461.1	498.4	539.4	582.7	622.7	659.6	690.3	711.1	717.3
32.5°	387.0	415.6	449.2	487.8	531.3	575.8	617.3	652.2	677.9	688.8	681.4
35°	369.2	395.1	429.0	468.5	513.7	561.1	602.2	631.6	644.8	634.5	608.8
37.5°	347.8	373.4	407.5	446.4	493.1	541.4	578.5	599.7	595.3	569.7	531.4
40°	332.8	356.8	389.2	431.2	476.7	525.1	557.8	569.2	557.2	520.5	479.7
42.5°	316.2	339.5	372.1	412.6	460.9	505.5	533.9	534.9	514.8	470.8	430.0
45°	290.8	313.1	343.8	386.0	430.6	472.6	491.4	482.2	445.0	402.7	361.6
47.5°	265.8	285.1	315.4	355.5	397.8	433.2	442.5	426.0	386.4	345.2	307.2
50°	247.5	267.0	295.5	333.7	374.6	405.1	409.6	387.7	348.9	307.4	277.7
52.5°	229.9	249.3	276.7	312.1	349.5	377.1	377.2	351.9	313.2	276.3	248.6
55°	204.1	221.6	246.4	278.1	311.4	333.0	327.7	301.5	267.9	235.8	211.7
57.5°	179.4	194.6	217.3	243.8	273.1	291.0	282.3	257.0	227.0	199.8	181.5
60°	163.3	177.8	197.3	222.2	246.9	260.8	252.5	229.7	202.1	180.1	164.2
62.5°	147.7	159.9	178.6	200.3	223.2	233.5	226.2	203.6	179.7	159.9	146.9
65°	125.6	135.5	150.5	169.1	185.8	194.6	188.5	167.4	149.2	135.0	124.7
67.5°	105.0	112.7	124.1	139.0	153.2	158.0	152.3	137.7	122.3	110.9	103.6
70°	90.7	98.1	107.6	119.1	131.4	136.5	130.9	119.2	106.7	96.2	89.0
72.5°	78.3	84.0	92.1	101.8	111.5	116.5	112.7	101.6	90.9	83.1	77.1
75°	59.7	64.5	70.1	77.1	84.5	87.9	84.5	76.8	69.6	63.8	59.4
77.5°	43.3	45.9	50.3	55.5	60.2	62.7	59.8	54.7	50.1	46.2	44.0
80°	33.0	34.9	37.9	42.0	45.2	47.6	45.7	41.4	37.9	35.3	34.3
82.5°	24.0	25.3	27.3	30.3	32.4	33.7	32.9	29.7	28.3	26.0	25.0
85°	11.8	12.6	13.9	14.8	16.7	16.9	17.0	15.8	14.4	13.9	13.2
87.5°	4.5	5.1	5.8	6.3	7.0	8.1	7.9	8.2	7.9	7.6	7.2
90°	2.4	4.8	5.5	6.3	6.3	11.1	11.1	12.7	14.3	13.5	14.3
92.5°	13.2	20.6	30.2	41.7	58.2	98.4	159.8	219.5	250.9	209.0	155.3
95°	28.4	36.4	46.7	65.7	98.9	167.6	297.4	486.4	644.5	662.7	586.0
97.5°	46.8	53.6	63.1	79.4	107.3	160.3	267.3	455.2	678.8	832.6	865.9
100°	60.1	65.7	75.1	90.2	115.5	162.2	251.5	412.8	635.8	838.3	953.8
102.5°	74.0	78.9	87.8	102.2	126.2	168.4	247.1	384.4	582.1	790.8	949.4
105°	94.9	98.9	108.4	122.6	145.5	183.5	249.1	359.8	518.8	704.6	885.7
107.5°	116.0	119.9	130.0	143.6	166.2	201.1	260.8	355.4	483.4	635.0	795.4
110°	130.5	134.4	143.9	158.2	179.5	214.3	269.7	356.6	471.3	600.2	741.0



TEST NUMBER: P332519-927

CATALOG NUMBER: SA4XXDIP-C350D1035U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	144.4	149.0	157.9	172.1	193.5	227.0	279.2	360.4	465.6	580.7	701.2
115°	165.2	170.8	178.7	193.8	215.1	246.8	294.2	367.7	462.6	562.3	661.2
117.5°	186.0	190.9	199.6	213.7	235.8	265.9	309.5	375.5	461.8	554.1	641.5
120°	199.3	204.9	213.5	227.0	249.1	279.2	320.3	381.2	461.8	549.6	632.6
122.5°	211.9	217.5	225.5	240.3	261.7	291.8	330.4	386.9	461.2	544.5	625.1
125°	230.1	234.9	243.6	258.6	280.7	309.2	345.6	395.5	460.3	536.2	612.1
127.5°	244.2	249.9	259.8	275.5	297.9	325.3	358.7	402.2	458.5	525.0	596.3
130°	253.1	259.4	271.2	286.3	309.2	336.1	366.9	407.3	457.9	518.0	583.7
132.5°	260.6	268.9	280.1	296.4	318.1	345.0	375.2	411.7	457.2	511.7	570.4
135°	272.8	280.7	294.2	310.8	331.4	357.4	386.0	418.4	456.3	502.2	552.0
137.5°	284.2	292.9	305.7	323.0	342.6	366.9	393.6	422.3	456.1	493.9	535.4
140°	291.8	300.6	313.9	330.6	349.6	373.3	398.5	425.5	455.5	489.6	525.9
142.5°	300.7	308.7	321.5	337.5	355.8	379.0	402.3	428.0	455.5	485.8	517.1
145°	313.1	321.1	332.2	347.2	364.6	385.2	406.5	429.4	453.9	479.3	504.5
147.5°	325.7	332.6	344.0	356.5	372.2	391.5	410.1	430.2	451.1	473.4	494.2
150°	334.5	340.9	350.4	362.2	377.2	394.7	412.0	430.2	449.2	469.0	488.0
152.5°	342.1	348.5	357.3	367.9	381.7	397.2	413.3	429.0	446.0	463.9	481.0
155°	354.3	359.0	366.9	375.7	387.5	400.9	414.4	427.1	441.3	456.3	470.6
157.5°	364.7	369.2	375.3	382.9	392.3	403.6	414.4	425.0	436.4	448.5	459.3
160°	371.7	374.9	380.4	386.7	395.5	404.9	414.4	423.1	432.6	442.9	452.3
162.5°	377.4	379.9	384.8	390.5	397.4	406.2	414.4	421.2	428.8	437.8	445.4
165°	385.2	386.7	390.7	394.7	399.3	406.5	412.8	417.6	423.1	429.4	435.8
167.5°	391.5	392.3	395.3	397.5	401.1	406.3	410.9	413.8	417.4	421.8	426.4
170°	394.7	395.5	397.8	399.3	401.7	405.7	409.6	411.2	413.6	416.8	420.7
172.5°	397.8	397.9	399.7	400.6	402.3	405.0	408.4	408.7	409.8	412.3	415.7
175°	400.9	400.9	401.7	402.5	402.5	404.1	406.5	405.7	405.7	407.3	408.8
177.5°	402.5	401.9	402.5	402.5	402.5	403.1	404.4	403.1	403.1	403.8	404.4
180°	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5



TEST NUMBER: P332519-927

CATALOG NUMBER: SA4XXDIP-C350D1035U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	452.6	452.6	452.6	452.6	452.6	452.6	452.6
2.5°	477.1	477.4	478.7	479.7	480.1	481.6	481.6
5°	519.0	522.1	528.3	528.9	529.8	534.7	530.9
7.5°	568.1	576.2	581.5	586.4	588.0	590.2	589.8
10°	599.6	611.6	617.6	627.2	627.5	629.9	628.4
12.5°	631.2	645.2	656.1	657.9	665.9	667.2	669.2
15°	676.0	690.9	706.1	711.5	722.5	725.2	729.3
17.5°	718.2	733.3	744.0	758.0	762.6	768.7	764.5
20°	741.3	757.8	771.3	782.4	787.0	790.4	790.0
22.5°	755.3	771.9	782.8	791.2	795.6	797.0	796.9
25°	764.0	773.6	777.0	780.1	775.2	773.6	774.3
27.5°	739.7	737.2	728.4	716.8	704.9	695.4	690.1
30°	706.2	691.7	678.3	655.1	643.1	636.0	629.5
32.5°	658.9	635.6	610.1	588.7	575.1	564.6	563.0
35°	577.7	542.8	511.4	485.4	471.9	460.5	457.8
37.5°	491.1	454.9	426.7	403.7	389.2	381.1	373.6
40°	433.6	402.5	374.8	355.3	344.2	338.4	333.7
42.5°	389.4	361.0	333.4	318.5	308.6	305.0	302.2
45°	328.3	301.8	282.7	271.5	265.7	259.7	256.8
47.5°	279.3	257.9	245.3	235.7	229.4	225.9	224.1
50°	251.6	234.0	222.8	215.4	209.8	207.0	205.5
52.5°	227.0	212.5	203.1	197.3	193.5	191.4	190.8
55°	195.5	184.5	178.5	173.4	170.6	168.7	168.0
57.5°	170.0	161.4	156.6	152.4	151.3	149.8	149.2
60°	153.2	146.6	142.5	139.7	138.7	136.9	137.2
62.5°	138.3	132.9	129.4	127.9	126.6	125.0	125.6
65°	117.0	113.0	111.1	109.7	108.2	107.3	108.0
67.5°	98.2	95.5	92.9	92.1	91.3	91.2	90.4
70°	85.9	83.7	81.4	80.8	80.8	80.1	79.9
72.5°	74.0	72.4	70.9	70.4	69.9	70.2	69.4
75°	57.2	55.8	55.3	54.7	54.6	54.6	54.0
77.5°	42.2	41.3	40.4	40.4	39.7	39.5	39.4
80°	32.1	31.7	31.0	31.0	30.6	30.7	30.3
82.5°	24.1	23.6	23.4	23.1	22.6	22.7	22.3
85°	12.9	12.4	12.2	11.6	11.2	11.6	11.2
87.5°	7.5	7.5	7.4	7.2	7.2	7.1	6.7
90°	15.1	15.8	15.8	16.6	17.4	16.6	16.6
92.5°	116.9	93.0	77.2	67.9	63.6	60.9	60.9
95°	463.4	357.4	280.7	242.0	217.5	203.3	193.0
97.5°	820.2	742.9	660.4	603.6	556.0	532.3	515.8
100°	969.6	930.8	872.3	803.5	755.3	731.5	725.2
102.5°	1027.8	1039.0	1014.6	972.4	937.5	912.5	907.4
105°	1022.5	1100.8	1133.3	1134.9	1128.5	1117.5	1112.7
107.5°	941.1	1051.4	1121.9	1160.9	1179.0	1186.9	1189.0
110°	877.8	992.5	1079.5	1135.7	1168.9	1183.1	1190.3



TEST NUMBER: P332519-927

CATALOG NUMBER: SA4XXDIP-C350D1035U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	822.1	930.5	1017.5	1081.2	1121.4	1141.4	1152.9
115°	758.4	851.0	926.9	989.4	1036.8	1062.1	1068.4
117.5°	722.1	794.8	859.2	912.5	952.4	977.9	982.9
120°	706.2	769.5	825.6	870.7	905.5	926.1	934.8
122.5°	696.1	753.7	802.9	841.0	870.7	888.1	896.8
125°	680.1	734.7	778.2	809.8	832.7	847.8	852.5
127.5°	661.3	715.7	757.0	788.8	809.2	821.8	826.6
130°	646.1	699.9	741.8	774.2	794.0	806.7	811.4
132.5°	629.1	681.5	723.5	755.3	777.5	789.6	794.3
135°	603.4	651.6	691.2	722.9	745.0	757.6	762.4
137.5°	578.9	619.6	655.3	684.8	706.7	717.2	722.9
140°	563.1	598.7	631.8	659.6	677.0	688.0	694.3
142.5°	549.8	580.4	609.1	633.6	649.7	659.6	664.0
145°	531.5	555.2	577.3	597.1	610.5	618.5	622.4
147.5°	515.6	534.6	552.0	566.6	578.1	584.2	585.5
150°	506.1	522.0	536.2	548.8	559.1	563.9	564.7
152.5°	496.6	511.2	522.9	533.7	542.0	544.9	545.7
155°	483.2	495.0	504.5	512.5	518.8	521.2	521.2
157.5°	469.9	479.9	487.5	493.5	498.2	499.6	499.6
160°	461.1	469.8	476.1	480.9	485.6	486.4	486.4
162.5°	452.8	459.6	465.3	468.8	473.6	474.4	473.7
165°	440.5	446.0	450.0	453.1	456.3	455.5	454.7
167.5°	430.1	434.5	436.9	438.5	440.5	440.4	439.7
170°	423.1	426.3	428.6	430.2	431.0	430.2	430.2
172.5°	417.4	419.3	421.0	422.0	422.8	422.0	420.7
175°	409.6	411.2	411.2	411.2	412.8	411.2	409.6
177.5°	405.0	405.0	405.7	405.0	405.7	404.4	403.1
180°	402.5	402.5	402.5	402.5	402.5	402.5	402.5

(END OF REPORT)