

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332582-927

Luminaire Tested: **SA4XXDIP-C795D365U927-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332582-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C795D365U927-4F0-1E-UDD-A4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3843.3 lumens
Efficiency: N/A
Efficacy: 109.8 lumens/watt
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 35
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332582-927
CATALOG NUMBER: SA4XXDIP-C795D365U927-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332582-927

CATALOG NUMBER: SA4XXDIP-C795D365U927-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	113	113	113	113	107	107	107	107	96	96	96	86	86	86	77	77	77	73				
1	103	99	95	91	98	94	91	87	85	82	80	77	75	73	69	67	66	62				
2	94	87	81	75	89	83	77	72	75	70	67	68	64	61	61	58	56	53				
3	86	77	69	63	82	73	66	61	66	61	57	60	56	52	54	51	48	45				
4	79	68	60	54	75	65	58	52	59	53	49	54	49	45	49	45	42	39				
5	73	61	53	47	69	58	51	45	53	47	42	49	43	39	44	40	37	34				
6	67	55	47	41	64	53	45	40	48	42	37	44	39	35	40	36	32	30				
7	62	50	42	36	59	48	40	35	44	38	33	40	35	31	37	32	29	27				
8	58	45	38	32	55	44	36	31	40	34	29	37	32	28	34	29	26	24				
9	54	42	34	29	52	40	33	28	37	31	27	34	29	25	31	27	24	22				
10	51	38	31	26	48	37	30	25	34	28	24	32	26	23	29	25	21	20				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8211	8211	8211	8211
5°	9669	8232	7266	8232
10°	11576	8196	6542	8196
15°	13697	8113	6007	8113
20°	15253	8028	5530	8028
25°	15499	7904	5201	7904
30°	13189	7784	5097	7784
35°	10139	7591	5099	7591
40°	7904	7361	5195	7361
45°	6590	7018	5281	7018
50°	5800	6599	5461	6599
55°	5313	6096	5681	6096
60°	4979	5646	5945	5646
65°	4634	5142	6164	5142
70°	4237	4645	6305	4645
75°	3787	4086	6229	4086
80°	3175	3347	6034	3347
85°	2343	2418	5771	2418



TEST NUMBER: P332582-927

CATALOG NUMBER: SA4XXDIP-C795D365U927-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.1	2.6
10°-20°	305.4	7.9
20°-30°	484.3	12.6
30°-40°	539.0	14.0
40°-50°	490.6	12.8
50°-60°	400.9	10.4
60°-70°	286.2	7.4
70°-80°	157.6	4.1
80°-90°	43.8	1.1
90°-100°	102.9	2.7
100°-110°	214.2	5.6
110°-120°	191.9	5.0
120°-130°	161.4	4.2
130°-140°	134.6	3.5
140°-150°	102.8	2.7
150°-160°	72.3	1.9
160°-170°	42.5	1.1
170°-180°	13.8	0.4
0°-30°	888.8	23.1
0°-40°	1427.7	37.1
0°-60°	2319.2	60.3
0°-90°	2806.9	73.0
90°-120°	509.0	13.2
90°-150°	907.8	23.6
90°-180°	1036.0	27.0
0°-180°	3843.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1017	1017	1017	1017	1017	
5°	1193	1016	897	1016	1193	121
15°	1639	971	719	971	1639	463
25°	1740	887	584	887	1740	767
35°	1029	770	517	770	1029	653
45°	577	615	463	615	577	455
55°	378	433	404	433	378	341
65°	243	269	323	269	243	240
75°	121	131	200	131	121	129
85°	25	26	62	26	25	31
90°	6	0	6	0	6	6
95°	68	9	68	9	68	106
105°	394	33	394	33	394	389
115°	378	58	378	58	378	375
125°	302	80	302	80	302	274
135°	270	96	270	96	270	208
145°	220	110	220	110	220	140
155°	184	125	184	125	184	86
165°	161	136	161	136	161	46
175°	145	142	145	142	145	14
180°	142	142	142	142	142	



TEST NUMBER: P332582-927

CATALOG NUMBER: SA4XXDIP-C795D365U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1017.1	1017.1	1017.1	1017.1	1017.1	1017.1	1017.1	1017.1	1017.1	1017.1	1017.1
2.5°	1082.4	1082.1	1078.7	1078.1	1075.7	1072.7	1072.0	1066.6	1055.8	1050.8	1049.4
5°	1193.2	1201.6	1190.6	1188.5	1187.2	1173.4	1166.2	1157.8	1138.4	1127.0	1118.2
7.5°	1325.3	1326.3	1321.5	1317.6	1306.9	1294.7	1276.6	1257.2	1234.1	1210.1	1192.0
10°	1412.2	1415.6	1410.2	1409.3	1387.8	1374.4	1347.3	1324.6	1298.5	1269.4	1242.9
12.5°	1504.0	1499.2	1496.4	1478.4	1474.4	1449.9	1418.5	1395.0	1354.8	1321.4	1286.0
15°	1638.9	1629.7	1623.7	1598.9	1586.7	1552.5	1519.2	1493.6	1440.9	1390.8	1352.8
17.5°	1718.1	1727.4	1713.7	1703.5	1671.9	1648.0	1614.0	1560.0	1518.9	1456.6	1408.7
20°	1775.4	1776.2	1768.7	1758.2	1733.3	1703.0	1665.9	1606.9	1557.6	1495.6	1430.0
22.5°	1790.9	1791.1	1787.9	1778.1	1759.2	1734.6	1697.3	1648.0	1588.2	1520.9	1455.2
25°	1740.0	1738.4	1742.2	1753.1	1745.9	1738.4	1716.8	1680.2	1624.6	1553.4	1482.6
27.5°	1550.9	1562.6	1584.0	1610.9	1636.9	1656.7	1662.2	1654.7	1620.3	1561.7	1487.6
30°	1414.8	1429.1	1445.1	1472.0	1524.3	1554.3	1587.1	1611.9	1598.1	1551.3	1482.2
32.5°	1265.1	1268.7	1292.4	1323.1	1371.0	1428.5	1480.6	1531.1	1547.8	1523.3	1465.7
35°	1028.8	1034.7	1060.4	1090.8	1149.4	1219.7	1298.1	1368.0	1425.7	1448.9	1419.4
37.5°	839.6	856.5	874.6	907.3	958.9	1022.2	1103.6	1194.1	1280.1	1337.8	1347.5
40°	750.0	760.5	773.6	798.4	842.2	904.6	974.5	1078.2	1169.6	1252.1	1279.1
42.5°	679.1	685.3	693.3	715.8	749.2	811.2	875.0	966.2	1058.0	1156.7	1201.9
45°	577.2	583.5	597.0	610.1	635.3	678.3	737.7	812.7	905.0	1000.2	1083.6
47.5°	503.6	507.6	515.6	529.6	551.0	579.4	627.7	690.4	775.9	868.3	957.2
50°	461.8	465.1	471.4	484.1	500.5	525.8	565.4	624.0	690.9	784.1	871.2
52.5°	428.7	430.1	434.7	443.3	456.4	477.6	510.1	558.6	620.8	703.9	790.8
55°	377.5	379.2	383.4	389.8	401.1	414.5	439.4	475.6	530.0	602.1	677.5
57.5°	335.3	336.5	340.1	342.5	351.9	362.8	382.0	407.8	449.0	510.1	577.4
60°	308.4	307.5	311.8	313.9	320.2	329.5	344.2	369.1	404.9	454.2	516.1
62.5°	282.1	280.9	284.5	287.2	290.9	298.8	310.9	330.3	359.4	403.9	457.5
65°	242.6	241.0	243.1	246.4	249.9	254.1	262.9	280.2	303.3	335.3	376.2
67.5°	203.0	204.9	205.2	206.8	208.8	214.5	220.6	232.8	249.1	274.8	309.4
70°	179.5	179.9	181.6	181.6	182.8	187.9	193.0	200.1	216.1	239.7	267.9
72.5°	155.9	157.6	157.0	158.4	159.2	162.6	166.4	173.2	186.8	204.3	228.1
75°	121.4	122.6	122.6	123.0	124.3	125.6	128.5	133.6	143.2	156.3	172.8
77.5°	88.5	88.6	89.2	90.8	90.8	92.8	95.0	99.0	103.8	112.7	122.8
80°	68.3	69.1	68.7	69.6	69.6	71.2	72.0	77.1	79.2	85.1	93.1
82.5°	50.1	50.9	50.8	52.0	52.7	53.0	54.2	56.2	58.3	63.5	66.8
85°	25.3	26.1	25.3	26.1	27.4	27.8	29.1	29.5	31.2	32.5	35.4
87.5°	8.6	9.6	9.7	9.9	10.5	10.9	11.2	10.8	12.0	12.4	13.7
90°	5.9	5.9	6.2	5.9	5.6	5.6	5.3	5.1	4.8	5.1	4.5
92.5°	21.5	21.5	22.5	24.0	27.3	33.0	41.4	55.0	74.0	88.8	77.7
95°	68.3	71.9	77.0	85.6	99.4	126.5	164.1	207.5	234.6	228.1	172.2
97.5°	182.6	188.5	196.9	213.7	233.8	263.0	290.4	306.5	294.8	240.3	161.1
100°	256.7	259.0	267.4	284.5	308.8	329.5	343.3	337.6	296.8	225.1	146.2
102.5°	321.2	323.1	331.9	344.3	359.2	367.8	363.8	336.1	280.0	206.0	136.1
105°	394.0	395.6	399.5	401.8	401.2	389.8	362.0	313.5	249.5	183.6	127.4
107.5°	420.9	420.2	417.4	411.0	397.2	372.2	333.2	281.6	224.8	171.1	125.8
110°	421.4	418.8	413.8	402.0	382.1	351.4	310.8	262.4	212.5	166.8	126.3



TEST NUMBER: P332582-927

CATALOG NUMBER: SA4XXDIP-C795D365U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	408.1	404.1	397.0	382.8	360.2	329.4	291.0	248.2	205.6	164.9	127.6
115°	378.3	376.0	367.0	350.2	328.1	301.3	268.5	234.1	199.1	163.8	130.2
117.5°	347.9	346.2	337.2	323.1	304.2	281.4	255.6	227.1	196.1	163.5	132.9
120°	331.0	327.9	320.6	308.2	292.3	272.4	250.0	223.9	194.6	163.5	135.0
122.5°	317.5	314.4	308.2	297.7	284.2	266.8	246.4	221.3	192.8	163.3	137.0
125°	301.8	300.2	294.9	286.7	275.5	260.1	240.7	216.7	189.8	163.0	140.0
127.5°	292.6	291.0	286.5	279.2	268.0	253.4	234.1	211.1	185.8	162.3	142.4
130°	287.2	285.6	281.1	274.1	262.6	247.8	228.8	206.6	183.4	162.1	144.2
132.5°	281.2	279.6	275.3	267.4	256.1	241.3	222.7	201.9	181.2	161.9	145.8
135°	269.9	268.2	263.7	255.9	244.7	230.7	213.7	195.4	177.8	161.5	148.1
137.5°	255.9	253.9	250.2	242.5	232.0	219.4	204.9	189.6	174.9	161.5	149.5
140°	245.8	243.6	239.6	233.5	223.7	211.9	199.3	186.2	173.3	161.3	150.6
142.5°	235.0	233.5	230.0	224.3	215.6	205.4	194.6	183.1	172.0	161.3	151.5
145°	220.3	219.0	216.1	211.4	204.4	196.5	188.1	178.6	169.7	160.7	152.0
147.5°	207.3	206.8	204.7	200.6	195.4	189.3	182.5	175.0	167.6	159.7	152.3
150°	199.9	199.6	198.0	194.3	189.8	184.8	179.2	172.8	166.0	159.0	152.3
152.5°	193.2	192.9	191.9	188.9	185.1	181.0	175.9	170.3	164.2	157.9	151.9
155°	184.5	184.5	183.6	181.4	178.6	175.2	171.0	166.6	161.5	156.2	151.2
157.5°	176.9	176.9	176.4	174.7	172.6	169.9	166.4	162.6	158.8	154.5	150.4
160°	172.2	172.2	171.9	170.2	168.6	166.3	163.2	160.2	156.8	153.1	149.8
162.5°	167.7	167.9	167.6	166.0	164.8	162.7	160.3	157.7	155.0	151.8	149.1
165°	161.0	161.3	161.5	160.4	159.3	157.9	156.0	154.2	152.0	149.8	147.8
167.5°	155.7	155.9	156.0	155.2	154.6	153.8	152.3	151.0	149.3	147.7	146.5
170°	152.3	152.3	152.6	152.3	151.8	150.9	149.8	148.9	147.6	146.4	145.6
172.5°	148.9	149.4	149.6	149.4	149.1	148.5	147.7	147.2	146.0	145.0	144.7
175°	145.0	145.6	146.2	145.6	145.6	145.6	145.0	144.7	144.2	143.6	143.6
177.5°	142.8	143.1	143.6	143.4	143.6	143.4	143.4	143.1	143.0	142.8	142.8
180°	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5



TEST NUMBER: P332582-927

CATALOG NUMBER: SA4XXDIP-C795D365U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1017.1	1017.1	1017.1	1017.1	1017.1	1017.1	1017.1	1017.1	1017.1	1017.1	1017.1
2.5°	1049.7	1045.0	1041.6	1038.9	1031.6	1027.1	1023.8	1019.1	1013.7	1008.0	1000.8
5°	1109.3	1095.0	1084.5	1068.4	1053.3	1040.6	1027.6	1015.8	1001.5	985.9	974.5
7.5°	1172.0	1150.6	1123.3	1099.6	1073.0	1049.8	1029.1	1007.9	985.8	964.4	944.8
10°	1211.7	1184.3	1154.0	1118.2	1084.5	1054.6	1026.7	999.8	973.7	947.5	925.2
12.5°	1254.5	1220.4	1175.5	1133.7	1095.9	1055.9	1022.4	989.4	957.8	930.3	904.3
15°	1311.9	1262.7	1210.9	1154.8	1105.1	1058.4	1012.4	970.7	935.3	899.0	873.8
17.5°	1347.3	1286.3	1227.0	1168.5	1108.3	1049.3	999.8	951.6	907.4	871.3	839.5
20°	1370.6	1309.9	1236.1	1177.6	1106.0	1045.3	988.0	934.5	888.1	849.8	816.9
22.5°	1390.8	1320.6	1246.9	1169.8	1098.5	1034.2	971.5	917.6	870.3	829.9	798.4
25°	1401.7	1321.2	1241.2	1164.5	1083.6	1007.3	950.5	887.3	836.7	794.2	760.5
27.5°	1402.9	1316.8	1226.3	1141.1	1057.6	986.6	914.7	858.3	805.8	760.8	728.4
30°	1399.2	1309.5	1212.1	1119.8	1036.0	958.9	896.6	835.0	781.6	736.9	703.1
32.5°	1387.3	1294.0	1193.9	1096.2	1009.4	934.0	869.6	811.1	759.0	714.9	679.6
35°	1353.3	1261.0	1154.4	1052.9	963.9	887.7	829.6	770.2	718.0	676.2	642.1
37.5°	1299.9	1216.5	1108.1	1003.1	915.8	839.2	781.6	727.9	680.7	638.3	603.4
40°	1253.4	1180.1	1071.4	969.0	874.6	801.8	747.8	698.5	651.8	611.7	578.5
42.5°	1199.8	1135.9	1035.7	927.2	836.2	763.0	710.4	666.1	622.1	585.1	551.8
45°	1104.2	1062.2	967.7	867.5	772.7	703.6	653.5	614.7	577.7	541.4	513.6
47.5°	994.3	973.5	894.1	798.8	708.8	640.7	597.2	561.4	528.9	498.3	473.7
50°	920.6	910.5	841.8	750.0	664.0	599.9	556.1	525.4	497.6	470.6	447.4
52.5°	847.8	847.4	785.5	701.4	621.9	560.2	516.7	488.0	463.9	442.0	421.1
55°	736.5	748.2	699.8	624.8	553.6	498.0	458.8	433.1	416.3	398.2	382.5
57.5°	634.2	653.8	613.9	547.8	488.4	437.1	403.1	383.7	365.8	354.8	343.5
60°	567.5	586.1	554.8	499.2	443.2	399.4	366.9	349.7	334.1	326.5	318.5
62.5°	508.2	524.7	501.6	450.0	401.4	359.3	331.9	315.3	304.8	296.5	291.2
65°	423.4	437.3	417.6	380.0	338.3	304.6	282.3	269.2	259.1	255.7	249.9
67.5°	342.3	354.9	344.2	312.4	278.9	253.3	235.9	223.4	217.4	214.4	210.2
70°	294.1	306.7	295.3	267.5	241.9	220.4	203.9	196.8	190.4	189.2	183.2
72.5°	253.3	261.9	250.5	228.8	206.8	188.7	175.9	168.4	165.2	162.9	159.7
75°	190.0	197.6	190.0	173.2	157.6	145.0	134.0	131.0	127.2	126.0	123.9
77.5°	134.5	141.1	135.2	124.7	113.0	103.3	97.4	93.6	92.8	90.5	91.6
80°	102.8	107.0	101.6	94.3	85.1	78.3	74.1	72.0	69.6	68.7	70.3
82.5°	73.8	75.7	72.9	68.0	61.2	56.8	53.9	51.5	51.0	51.2	51.2
85°	38.3	37.9	37.5	33.3	31.2	28.2	26.5	26.1	25.7	26.5	27.4
87.5°	13.6	13.9	13.2	11.9	10.9	9.7	9.3	8.8	9.3	9.7	10.1
90°	3.9	3.9	2.2	2.2	2.0	1.7	0.9	0.3	0.9	1.7	2.0
92.5°	56.6	34.9	20.6	14.8	10.7	7.3	4.7	3.2	4.7	7.3	10.7
95°	105.3	59.3	35.0	23.2	16.6	12.9	10.1	9.3	10.1	12.9	16.6
97.5°	94.7	56.7	37.9	28.1	22.3	19.0	16.6	16.6	16.6	19.0	22.3
100°	89.0	57.4	40.9	31.9	26.6	23.2	21.3	21.3	21.3	23.2	26.6
102.5°	87.5	59.7	44.7	36.2	31.1	28.0	26.2	25.7	26.2	28.0	31.1
105°	88.2	65.0	51.5	43.4	38.3	35.0	33.6	32.8	33.6	35.0	38.3
107.5°	92.4	71.1	58.9	50.9	46.0	42.5	41.0	40.5	41.0	42.5	46.0
110°	95.5	75.9	63.5	56.0	50.9	47.6	46.2	45.6	46.2	47.6	50.9



TEST NUMBER: P332582-927

CATALOG NUMBER: SA4XXDIP-C795D365U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	98.9	80.3	68.4	60.9	55.8	52.8	51.1	50.5	51.1	52.8	55.8
115°	104.2	87.4	76.1	68.6	63.3	60.4	58.5	57.7	58.5	60.4	63.3
117.5°	109.6	94.1	83.5	75.7	70.7	67.6	65.8	65.0	65.8	67.6	70.7
120°	113.4	98.9	88.2	80.3	75.6	72.5	70.6	70.0	70.6	72.5	75.6
122.5°	117.0	103.3	92.7	85.1	79.9	77.0	75.0	74.5	75.0	77.0	79.9
125°	122.3	109.5	99.4	91.6	86.3	83.2	81.4	80.3	81.4	83.2	86.3
127.5°	127.0	115.2	105.4	97.5	92.0	88.5	86.4	85.6	86.4	88.5	92.0
130°	129.9	119.0	109.5	101.3	96.0	91.8	89.6	88.5	89.6	91.8	96.0
132.5°	132.8	122.2	112.6	105.0	99.2	95.2	92.3	91.4	92.3	95.2	99.2
135°	136.7	126.5	117.3	110.0	104.2	99.4	96.6	95.5	96.6	99.4	104.2
137.5°	139.3	129.9	121.3	114.3	108.2	103.7	100.6	99.6	100.6	103.7	108.2
140°	141.1	132.1	123.7	117.0	111.1	106.4	103.3	102.5	103.3	106.4	111.1
142.5°	142.4	134.2	126.0	119.5	113.8	109.3	106.5	105.6	106.5	109.3	113.8
145°	143.9	136.3	129.0	122.9	117.6	113.7	110.9	110.0	110.9	113.7	117.6
147.5°	145.2	138.6	131.7	126.2	121.8	117.8	115.3	115.0	115.3	117.8	121.8
150°	145.8	139.7	133.6	128.3	124.1	120.6	118.4	118.1	118.4	120.6	124.1
152.5°	146.3	140.6	135.1	130.2	126.5	123.3	121.1	121.0	121.1	123.3	126.5
155°	146.7	142.0	137.2	133.0	129.9	127.1	125.4	125.2	125.4	127.1	129.9
157.5°	146.7	142.9	138.9	135.5	132.8	130.7	129.1	129.1	129.1	130.7	132.8
160°	146.7	143.4	140.0	136.9	134.7	132.7	131.6	131.6	131.6	132.7	134.7
162.5°	146.7	143.8	140.7	138.2	136.3	134.5	133.6	133.8	133.6	134.5	136.3
165°	146.2	143.9	141.4	139.7	138.3	136.9	136.3	136.3	136.3	136.9	138.3
167.5°	145.4	143.9	142.0	140.7	139.9	138.9	138.6	138.9	138.6	138.9	139.9
170°	145.0	143.6	142.2	141.4	140.9	140.0	139.7	140.0	139.7	140.0	140.9
172.5°	144.6	143.4	142.4	141.8	141.5	140.9	140.9	141.1	140.9	140.9	141.5
175°	143.9	143.1	142.5	142.5	142.2	142.0	142.0	142.2	142.0	142.0	142.2
177.5°	143.1	142.8	142.5	142.5	142.5	142.3	142.5	142.8	142.5	142.3	142.5
180°	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5



TEST NUMBER: P332582-927

CATALOG NUMBER: SA4XXDIP-C795D365U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1017.1	1017.1	1017.1	1017.1	1017.1	1017.1	1017.1	1017.1	1017.1	1017.1	1017.1
2.5°	997.5	994.5	990.1	984.0	979.0	973.6	972.2	970.2	974.2	970.9	969.9
5°	964.8	955.9	944.6	931.5	923.9	913.0	910.9	906.7	902.5	902.1	897.8
7.5°	930.2	917.2	902.3	889.0	876.6	864.7	856.9	855.2	849.0	845.3	841.1
10°	907.9	891.9	874.6	862.0	847.7	835.0	826.2	821.2	816.9	812.3	808.1
12.5°	881.6	864.6	850.4	836.7	819.7	810.1	795.5	786.8	785.9	786.0	775.1
15°	851.0	834.2	812.3	792.9	783.6	765.1	757.1	746.9	740.7	734.4	729.3
17.5°	816.1	795.1	778.0	755.7	738.1	723.3	712.8	706.7	697.2	688.2	681.8
20°	794.2	771.8	753.8	730.2	710.7	692.6	683.8	675.3	668.2	660.6	653.5
22.5°	771.9	748.6	726.4	703.5	685.5	666.4	657.8	646.3	639.5	635.3	628.2
25°	736.9	711.6	686.3	664.4	645.9	629.0	617.7	608.8	601.2	597.9	593.2
27.5°	698.8	673.7	649.3	624.4	603.3	591.1	582.0	575.4	570.9	566.5	564.4
30°	674.5	648.4	622.3	599.1	579.7	567.5	559.0	554.4	551.0	549.0	546.8
32.5°	649.9	624.2	596.7	575.5	558.2	547.3	540.9	536.2	534.6	533.8	533.1
35°	610.5	584.4	559.0	540.1	523.7	519.5	514.0	511.5	510.6	513.6	514.8
37.5°	572.3	548.0	524.8	506.4	495.7	489.5	487.6	487.7	490.8	493.4	496.4
40°	547.7	524.1	502.2	486.2	476.1	472.3	471.4	473.6	476.9	479.9	483.2
42.5°	523.8	500.5	480.6	465.6	458.6	455.1	455.6	457.7	462.4	466.0	471.1
45°	486.6	467.2	447.8	435.6	429.8	430.6	430.6	434.4	439.0	444.5	450.0
47.5°	451.6	432.1	416.1	405.9	402.8	402.1	404.5	409.4	416.1	422.9	430.5
50°	428.0	409.5	395.6	386.3	382.9	384.2	387.6	392.2	400.2	408.7	416.7
52.5°	404.1	387.3	374.4	365.8	363.5	365.7	369.1	376.4	383.4	392.5	402.2
55°	366.9	352.6	342.5	336.2	335.3	336.6	340.4	348.4	358.5	369.9	379.2
57.5°	329.9	318.0	308.7	304.4	304.8	305.9	312.2	321.7	332.5	344.6	356.6
60°	305.1	294.1	286.5	283.1	283.5	286.1	293.7	302.5	316.0	327.8	340.4
62.5°	281.5	271.8	264.6	261.6	260.9	266.5	273.8	283.0	296.4	309.6	323.2
65°	243.5	235.9	230.0	228.4	229.7	233.9	243.1	255.3	266.7	280.6	294.9
67.5°	206.4	200.2	196.1	196.9	198.4	204.7	212.5	222.9	235.8	250.3	264.4
70°	182.8	177.0	173.6	174.0	176.5	184.1	190.8	201.4	215.3	230.0	241.9
72.5°	158.6	154.7	151.7	153.4	156.0	161.2	169.6	180.1	192.3	206.1	218.6
75°	121.8	121.8	120.1	121.4	125.2	130.2	136.5	147.4	159.7	170.6	180.8
77.5°	90.3	89.4	90.5	92.1	94.2	100.2	107.4	115.3	124.5	135.4	143.8
80°	69.1	69.6	71.6	74.1	75.0	79.6	87.2	94.3	101.6	110.8	118.8
82.5°	51.9	52.4	53.4	56.6	57.4	62.4	67.3	74.5	81.0	87.2	93.9
85°	28.2	28.2	30.3	31.6	33.7	37.1	40.0	44.2	50.1	54.3	60.7
87.5°	11.2	11.2	12.9	13.6	14.7	16.5	17.1	20.9	22.3	24.0	27.1
90°	2.2	2.2	3.9	3.9	4.5	5.1	4.8	5.1	5.3	5.6	5.6
92.5°	14.8	20.6	34.9	56.6	77.7	88.8	74.0	55.0	41.4	33.0	27.3
95°	23.2	35.0	59.3	105.3	172.2	228.1	234.6	207.5	164.1	126.5	99.4
97.5°	28.1	37.9	56.7	94.7	161.1	240.3	294.8	306.5	290.4	263.0	233.8
100°	31.9	40.9	57.4	89.0	146.2	225.1	296.8	337.6	343.3	329.5	308.8
102.5°	36.2	44.7	59.7	87.5	136.1	206.0	280.0	336.1	363.8	367.8	359.2
105°	43.4	51.5	65.0	88.2	127.4	183.6	249.5	313.5	362.0	389.8	401.2
107.5°	50.9	58.9	71.1	92.4	125.8	171.1	224.8	281.6	333.2	372.2	397.2
110°	56.0	63.5	75.9	95.5	126.3	166.8	212.5	262.4	310.8	351.4	382.1



TEST NUMBER: P332582-927

CATALOG NUMBER: SA4XXDIP-C795D365U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	60.9	68.4	80.3	98.9	127.6	164.9	205.6	248.2	291.0	329.4	360.2
115°	68.6	76.1	87.4	104.2	130.2	163.8	199.1	234.1	268.5	301.3	328.1
117.5°	75.7	83.5	94.1	109.6	132.9	163.5	196.1	227.1	255.6	281.4	304.2
120°	80.3	88.2	98.9	113.4	135.0	163.5	194.6	223.9	250.0	272.4	292.3
122.5°	85.1	92.7	103.3	117.0	137.0	163.3	192.8	221.3	246.4	266.8	284.2
125°	91.6	99.4	109.5	122.3	140.0	163.0	189.8	216.7	240.7	260.1	275.5
127.5°	97.5	105.4	115.2	127.0	142.4	162.3	185.8	211.1	234.1	253.4	268.0
130°	101.3	109.5	119.0	129.9	144.2	162.1	183.4	206.6	228.8	247.8	262.6
132.5°	105.0	112.6	122.2	132.8	145.8	161.9	181.2	201.9	222.7	241.3	256.1
135°	110.0	117.3	126.5	136.7	148.1	161.5	177.8	195.4	213.7	230.7	244.7
137.5°	114.3	121.3	129.9	139.3	149.5	161.5	174.9	189.6	204.9	219.4	232.0
140°	117.0	123.7	132.1	141.1	150.6	161.3	173.3	186.2	199.3	211.9	223.7
142.5°	119.5	126.0	134.2	142.4	151.5	161.3	172.0	183.1	194.6	205.4	215.6
145°	122.9	129.0	136.3	143.9	152.0	160.7	169.7	178.6	188.1	196.5	204.4
147.5°	126.2	131.7	138.6	145.2	152.3	159.7	167.6	175.0	182.5	189.3	195.4
150°	128.3	133.6	139.7	145.8	152.3	159.0	166.0	172.8	179.2	184.8	189.8
152.5°	130.2	135.1	140.6	146.3	151.9	157.9	164.2	170.3	175.9	181.0	185.1
155°	133.0	137.2	142.0	146.7	151.2	156.2	161.5	166.6	171.0	175.2	178.6
157.5°	135.5	138.9	142.9	146.7	150.4	154.5	158.8	162.6	166.4	169.9	172.6
160°	136.9	140.0	143.4	146.7	149.8	153.1	156.8	160.2	163.2	166.3	168.6
162.5°	138.2	140.7	143.8	146.7	149.1	151.8	155.0	157.7	160.3	162.7	164.8
165°	139.7	141.4	143.9	146.2	147.8	149.8	152.0	154.2	156.0	157.9	159.3
167.5°	140.7	142.0	143.9	145.4	146.5	147.7	149.3	151.0	152.3	153.8	154.6
170°	141.4	142.2	143.6	145.0	145.6	146.4	147.6	148.9	149.8	150.9	151.8
172.5°	141.8	142.4	143.4	144.6	144.7	145.0	146.0	147.2	147.7	148.5	149.1
175°	142.5	142.5	143.1	143.9	143.6	143.6	144.2	144.7	145.0	145.6	145.6
177.5°	142.5	142.5	142.8	143.1	142.8	142.8	143.0	143.1	143.4	143.4	143.6
180°	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5



TEST NUMBER: P332582-927

CATALOG NUMBER: SA4XXDIP-C795D365U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1017.1	1017.1	1017.1	1017.1	1017.1	1017.1	1017.1	1017.1	1017.1	1017.1	1017.1
2.5°	969.2	968.5	966.1	965.8	966.1	968.5	969.2	969.9	970.9	974.2	970.2
5°	895.3	893.2	891.9	896.6	891.9	893.2	895.3	897.8	902.1	902.5	906.7
7.5°	839.6	837.9	834.2	833.1	834.2	837.9	839.6	841.1	845.3	849.0	855.2
10°	803.8	802.2	798.8	798.0	798.8	802.2	803.8	808.1	812.3	816.9	821.2
12.5°	769.4	766.1	765.4	766.3	765.4	766.1	769.4	775.1	786.0	785.9	786.8
15°	723.8	722.2	717.5	718.7	717.5	722.2	723.8	729.3	734.4	740.7	746.9
17.5°	678.8	676.8	671.1	676.1	671.1	676.8	678.8	681.8	688.2	697.2	706.7
20°	650.5	647.1	644.2	643.7	644.2	647.1	650.5	653.5	660.6	668.2	675.3
22.5°	623.5	620.5	620.3	617.5	620.3	620.5	623.5	628.2	635.3	639.5	646.3
25°	589.9	586.9	586.1	583.9	586.1	586.9	589.9	593.2	597.9	601.2	608.8
27.5°	564.0	562.5	561.0	561.7	561.0	562.5	564.0	564.4	566.5	570.9	575.4
30°	548.1	547.7	546.8	546.8	546.8	547.7	548.1	546.8	549.0	551.0	554.4
32.5°	535.0	534.9	535.4	535.4	535.4	534.9	535.0	533.1	533.8	534.6	536.2
35°	516.5	517.8	518.6	517.4	518.6	517.8	516.5	514.8	513.6	510.6	511.5
37.5°	499.9	501.1	502.3	503.7	502.3	501.1	499.9	496.4	493.4	490.8	487.7
40°	487.0	490.0	490.8	493.0	490.8	490.0	487.0	483.2	479.9	476.9	473.6
42.5°	474.9	478.2	480.4	480.8	480.4	478.2	474.9	471.1	466.0	462.4	457.7
45°	456.3	459.6	462.6	462.6	462.6	459.6	456.3	450.0	444.5	439.0	434.4
47.5°	437.0	441.9	444.8	445.6	444.8	441.9	437.0	430.5	422.9	416.1	409.4
50°	423.8	429.8	432.7	434.8	432.7	429.8	423.8	416.7	408.7	400.2	392.2
52.5°	411.1	416.9	420.9	422.0	420.9	416.9	411.1	402.2	392.5	383.4	376.4
55°	388.9	397.3	402.0	403.6	402.0	397.3	388.9	379.2	369.9	358.5	348.4
57.5°	368.0	375.7	381.1	382.4	381.1	375.7	368.0	356.6	344.6	332.5	321.7
60°	351.8	360.2	366.9	368.2	366.9	360.2	351.8	340.4	327.8	316.0	302.5
62.5°	335.3	344.0	350.1	353.4	350.1	344.0	335.3	323.2	309.6	296.4	283.0
65°	306.7	315.5	321.5	322.7	321.5	315.5	306.7	294.9	280.6	266.7	255.3
67.5°	275.5	284.4	288.3	290.7	288.3	284.4	275.5	264.4	250.3	235.8	222.9
70°	253.7	260.8	265.0	267.1	265.0	260.8	253.7	241.9	230.0	215.3	201.4
72.5°	228.7	236.1	241.1	241.5	241.1	236.1	228.7	218.6	206.1	192.3	180.1
75°	190.4	197.2	199.7	199.7	199.7	197.2	190.4	180.8	170.6	159.7	147.4
77.5°	150.8	154.2	157.4	158.0	157.4	154.2	150.8	143.8	135.4	124.5	115.3
80°	125.2	127.2	129.8	129.8	129.8	127.2	125.2	118.8	110.8	101.6	94.3
82.5°	98.9	100.6	103.1	102.8	103.1	100.6	98.9	93.9	87.2	81.0	74.5
85°	59.8	63.6	63.2	62.3	63.2	63.6	59.8	60.7	54.3	50.1	44.2
87.5°	28.1	28.5	29.5	30.2	29.5	28.5	28.1	27.1	24.0	22.3	20.9
90°	5.9	6.2	5.9	5.9	5.9	6.2	5.9	5.6	5.6	5.3	5.1
92.5°	24.0	22.5	21.5	21.5	21.5	22.5	24.0	27.3	33.0	41.4	55.0
95°	85.6	77.0	71.9	68.3	71.9	77.0	85.6	99.4	126.5	164.1	207.5
97.5°	213.7	196.9	188.5	182.6	188.5	196.9	213.7	233.8	263.0	290.4	306.5
100°	284.5	267.4	259.0	256.7	259.0	267.4	284.5	308.8	329.5	343.3	337.6
102.5°	344.3	331.9	323.1	321.2	323.1	331.9	344.3	359.2	367.8	363.8	336.1
105°	401.8	399.5	395.6	394.0	395.6	399.5	401.8	401.2	389.8	362.0	313.5
107.5°	411.0	417.4	420.2	420.9	420.2	417.4	411.0	397.2	372.2	333.2	281.6
110°	402.0	413.8	418.8	421.4	418.8	413.8	402.0	382.1	351.4	310.8	262.4



TEST NUMBER: P332582-927

CATALOG NUMBER: SA4XXDIP-C795D365U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	382.8	397.0	404.1	408.1	404.1	397.0	382.8	360.2	329.4	291.0	248.2
115°	350.2	367.0	376.0	378.3	376.0	367.0	350.2	328.1	301.3	268.5	234.1
117.5°	323.1	337.2	346.2	347.9	346.2	337.2	323.1	304.2	281.4	255.6	227.1
120°	308.2	320.6	327.9	331.0	327.9	320.6	308.2	292.3	272.4	250.0	223.9
122.5°	297.7	308.2	314.4	317.5	314.4	308.2	297.7	284.2	266.8	246.4	221.3
125°	286.7	294.9	300.2	301.8	300.2	294.9	286.7	275.5	260.1	240.7	216.7
127.5°	279.2	286.5	291.0	292.6	291.0	286.5	279.2	268.0	253.4	234.1	211.1
130°	274.1	281.1	285.6	287.2	285.6	281.1	274.1	262.6	247.8	228.8	206.6
132.5°	267.4	275.3	279.6	281.2	279.6	275.3	267.4	256.1	241.3	222.7	201.9
135°	255.9	263.7	268.2	269.9	268.2	263.7	255.9	244.7	230.7	213.7	195.4
137.5°	242.5	250.2	253.9	255.9	253.9	250.2	242.5	232.0	219.4	204.9	189.6
140°	233.5	239.6	243.6	245.8	243.6	239.6	233.5	223.7	211.9	199.3	186.2
142.5°	224.3	230.0	233.5	235.0	233.5	230.0	224.3	215.6	205.4	194.6	183.1
145°	211.4	216.1	219.0	220.3	219.0	216.1	211.4	204.4	196.5	188.1	178.6
147.5°	200.6	204.7	206.8	207.3	206.8	204.7	200.6	195.4	189.3	182.5	175.0
150°	194.3	198.0	199.6	199.9	199.6	198.0	194.3	189.8	184.8	179.2	172.8
152.5°	188.9	191.9	192.9	193.2	192.9	191.9	188.9	185.1	181.0	175.9	170.3
155°	181.4	183.6	184.5	184.5	184.5	183.6	181.4	178.6	175.2	171.0	166.6
157.5°	174.7	176.4	176.9	176.9	176.9	176.4	174.7	172.6	169.9	166.4	162.6
160°	170.2	171.9	172.2	172.2	172.2	171.9	170.2	168.6	166.3	163.2	160.2
162.5°	166.0	167.6	167.9	167.7	167.9	167.6	166.0	164.8	162.7	160.3	157.7
165°	160.4	161.5	161.3	161.0	161.3	161.5	160.4	159.3	157.9	156.0	154.2
167.5°	155.2	156.0	155.9	155.7	155.9	156.0	155.2	154.6	153.8	152.3	151.0
170°	152.3	152.6	152.3	152.3	152.3	152.6	152.3	151.8	150.9	149.8	148.9
172.5°	149.4	149.6	149.4	148.9	149.4	149.6	149.4	149.1	148.5	147.7	147.2
175°	145.6	146.2	145.6	145.0	145.6	146.2	145.6	145.6	145.6	145.0	144.7
177.5°	143.4	143.6	143.1	142.8	143.1	143.6	143.4	143.6	143.4	143.4	143.1
180°	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5



TEST NUMBER: P332582-927

CATALOG NUMBER: SA4XXDIP-C795D365U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1017.1	1017.1	1017.1	1017.1	1017.1	1017.1	1017.1	1017.1	1017.1	1017.1	1017.1
2.5°	972.2	973.6	979.0	984.0	990.1	994.5	997.5	1000.8	1008.0	1013.7	1019.1
5°	910.9	913.0	923.9	931.5	944.6	955.9	964.8	974.5	985.9	1001.5	1015.8
7.5°	856.9	864.7	876.6	889.0	902.3	917.2	930.2	944.8	964.4	985.8	1007.9
10°	826.2	835.0	847.7	862.0	874.6	891.9	907.9	925.2	947.5	973.7	999.8
12.5°	795.5	810.1	819.7	836.7	850.4	864.6	881.6	904.3	930.3	957.8	989.4
15°	757.1	765.1	783.6	792.9	812.3	834.2	851.0	873.8	899.0	935.3	970.7
17.5°	712.8	723.3	738.1	755.7	778.0	795.1	816.1	839.5	871.3	907.4	951.6
20°	683.8	692.6	710.7	730.2	753.8	771.8	794.2	816.9	849.8	888.1	934.5
22.5°	657.8	666.4	685.5	703.5	726.4	748.6	771.9	798.4	829.9	870.3	917.6
25°	617.7	629.0	645.9	664.4	686.3	711.6	736.9	760.5	794.2	836.7	887.3
27.5°	582.0	591.1	603.3	624.4	649.3	673.7	698.8	728.4	760.8	805.8	858.3
30°	559.0	567.5	579.7	599.1	622.3	648.4	674.5	703.1	736.9	781.6	835.0
32.5°	540.9	547.3	558.2	575.5	596.7	624.2	649.9	679.6	714.9	759.0	811.1
35°	514.0	519.5	523.7	540.1	559.0	584.4	610.5	642.1	676.2	718.0	770.2
37.5°	487.6	489.5	495.7	506.4	524.8	548.0	572.3	603.4	638.3	680.7	727.9
40°	471.4	472.3	476.1	486.2	502.2	524.1	547.7	578.5	611.7	651.8	698.5
42.5°	455.6	455.1	458.6	465.6	480.6	500.5	523.8	551.8	585.1	622.1	666.1
45°	430.6	430.6	429.8	435.6	447.8	467.2	486.6	513.6	541.4	577.7	614.7
47.5°	404.5	402.1	402.8	405.9	416.1	432.1	451.6	473.7	498.3	528.9	561.4
50°	387.6	384.2	382.9	386.3	395.6	409.5	428.0	447.4	470.6	497.6	525.4
52.5°	369.1	365.7	363.5	365.8	374.4	387.3	404.1	421.1	442.0	463.9	488.0
55°	340.4	336.6	335.3	336.2	342.5	352.6	366.9	382.5	398.2	416.3	433.1
57.5°	312.2	305.9	304.8	304.4	308.7	318.0	329.9	343.5	354.8	365.8	383.7
60°	293.7	286.1	283.5	283.1	286.5	294.1	305.1	318.5	326.5	334.1	349.7
62.5°	273.8	266.5	260.9	261.6	264.6	271.8	281.5	291.2	296.5	304.8	315.3
65°	243.1	233.9	229.7	228.4	230.0	235.9	243.5	249.9	255.7	259.1	269.2
67.5°	212.5	204.7	198.4	196.9	196.1	200.2	206.4	210.2	214.4	217.4	223.4
70°	190.8	184.1	176.5	174.0	173.6	177.0	182.8	183.2	189.2	190.4	196.8
72.5°	169.6	161.2	156.0	153.4	151.7	154.7	158.6	159.7	162.9	165.2	168.4
75°	136.5	130.2	125.2	121.4	120.1	121.8	121.8	123.9	126.0	127.2	131.0
77.5°	107.4	100.2	94.2	92.1	90.5	89.4	90.3	91.6	90.5	92.8	93.6
80°	87.2	79.6	75.0	74.1	71.6	69.6	69.1	70.3	68.7	69.6	72.0
82.5°	67.3	62.4	57.4	56.6	53.4	52.4	51.9	51.2	51.2	51.0	51.5
85°	40.0	37.1	33.7	31.6	30.3	28.2	28.2	27.4	26.5	25.7	26.1
87.5°	17.1	16.5	14.7	13.6	12.9	11.2	11.2	10.1	9.7	9.3	8.8
90°	4.8	5.1	4.5	3.9	3.9	2.2	2.2	2.0	1.7	0.9	0.3
92.5°	74.0	88.8	77.7	56.6	34.9	20.6	14.8	10.7	7.3	4.7	3.2
95°	234.6	228.1	172.2	105.3	59.3	35.0	23.2	16.6	12.9	10.1	9.3
97.5°	294.8	240.3	161.1	94.7	56.7	37.9	28.1	22.3	19.0	16.6	16.6
100°	296.8	225.1	146.2	89.0	57.4	40.9	31.9	26.6	23.2	21.3	21.3
102.5°	280.0	206.0	136.1	87.5	59.7	44.7	36.2	31.1	28.0	26.2	25.7
105°	249.5	183.6	127.4	88.2	65.0	51.5	43.4	38.3	35.0	33.6	32.8
107.5°	224.8	171.1	125.8	92.4	71.1	58.9	50.9	46.0	42.5	41.0	40.5
110°	212.5	166.8	126.3	95.5	75.9	63.5	56.0	50.9	47.6	46.2	45.6



TEST NUMBER: P332582-927

CATALOG NUMBER: SA4XXDIP-C795D365U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	205.6	164.9	127.6	98.9	80.3	68.4	60.9	55.8	52.8	51.1	50.5
115°	199.1	163.8	130.2	104.2	87.4	76.1	68.6	63.3	60.4	58.5	57.7
117.5°	196.1	163.5	132.9	109.6	94.1	83.5	75.7	70.7	67.6	65.8	65.0
120°	194.6	163.5	135.0	113.4	98.9	88.2	80.3	75.6	72.5	70.6	70.0
122.5°	192.8	163.3	137.0	117.0	103.3	92.7	85.1	79.9	77.0	75.0	74.5
125°	189.8	163.0	140.0	122.3	109.5	99.4	91.6	86.3	83.2	81.4	80.3
127.5°	185.8	162.3	142.4	127.0	115.2	105.4	97.5	92.0	88.5	86.4	85.6
130°	183.4	162.1	144.2	129.9	119.0	109.5	101.3	96.0	91.8	89.6	88.5
132.5°	181.2	161.9	145.8	132.8	122.2	112.6	105.0	99.2	95.2	92.3	91.4
135°	177.8	161.5	148.1	136.7	126.5	117.3	110.0	104.2	99.4	96.6	95.5
137.5°	174.9	161.5	149.5	139.3	129.9	121.3	114.3	108.2	103.7	100.6	99.6
140°	173.3	161.3	150.6	141.1	132.1	123.7	117.0	111.1	106.4	103.3	102.5
142.5°	172.0	161.3	151.5	142.4	134.2	126.0	119.5	113.8	109.3	106.5	105.6
145°	169.7	160.7	152.0	143.9	136.3	129.0	122.9	117.6	113.7	110.9	110.0
147.5°	167.6	159.7	152.3	145.2	138.6	131.7	126.2	121.8	117.8	115.3	115.0
150°	166.0	159.0	152.3	145.8	139.7	133.6	128.3	124.1	120.6	118.4	118.1
152.5°	164.2	157.9	151.9	146.3	140.6	135.1	130.2	126.5	123.3	121.1	121.0
155°	161.5	156.2	151.2	146.7	142.0	137.2	133.0	129.9	127.1	125.4	125.2
157.5°	158.8	154.5	150.4	146.7	142.9	138.9	135.5	132.8	130.7	129.1	129.1
160°	156.8	153.1	149.8	146.7	143.4	140.0	136.9	134.7	132.7	131.6	131.6
162.5°	155.0	151.8	149.1	146.7	143.8	140.7	138.2	136.3	134.5	133.6	133.8
165°	152.0	149.8	147.8	146.2	143.9	141.4	139.7	138.3	136.9	136.3	136.3
167.5°	149.3	147.7	146.5	145.4	143.9	142.0	140.7	139.9	138.9	138.6	138.9
170°	147.6	146.4	145.6	145.0	143.6	142.2	141.4	140.9	140.0	139.7	140.0
172.5°	146.0	145.0	144.7	144.6	143.4	142.4	141.8	141.5	140.9	140.9	141.1
175°	144.2	143.6	143.6	143.9	143.1	142.5	142.5	142.2	142.0	142.0	142.2
177.5°	143.0	142.8	142.8	143.1	142.8	142.5	142.5	142.5	142.3	142.5	142.8
180°	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5



TEST NUMBER: P332582-927

CATALOG NUMBER: SA4XXDIP-C795D365U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1017.1	1017.1	1017.1	1017.1	1017.1	1017.1	1017.1	1017.1	1017.1	1017.1	1017.1
2.5°	1023.8	1027.1	1031.6	1038.9	1041.6	1045.0	1049.7	1049.4	1050.8	1055.8	1066.6
5°	1027.6	1040.6	1053.3	1068.4	1084.5	1095.0	1109.3	1118.2	1127.0	1138.4	1157.8
7.5°	1029.1	1049.8	1073.0	1099.6	1123.3	1150.6	1172.0	1192.0	1210.1	1234.1	1257.2
10°	1026.7	1054.6	1084.5	1118.2	1154.0	1184.3	1211.7	1242.9	1269.4	1298.5	1324.6
12.5°	1022.4	1055.9	1095.9	1133.7	1175.5	1220.4	1254.5	1286.0	1321.4	1354.8	1395.0
15°	1012.4	1058.4	1105.1	1154.8	1210.9	1262.7	1311.9	1352.8	1390.8	1440.9	1493.6
17.5°	999.8	1049.3	1108.3	1168.5	1227.0	1286.3	1347.3	1408.7	1456.6	1518.9	1560.0
20°	988.0	1045.3	1106.0	1177.6	1236.1	1309.9	1370.6	1430.0	1495.6	1557.6	1606.9
22.5°	971.5	1034.2	1098.5	1169.8	1246.9	1320.6	1390.8	1455.2	1520.9	1588.2	1648.0
25°	950.5	1007.3	1083.6	1164.5	1241.2	1321.2	1401.7	1482.6	1553.4	1624.6	1680.2
27.5°	914.7	986.6	1057.6	1141.1	1226.3	1316.8	1402.9	1487.6	1561.7	1620.3	1654.7
30°	896.6	958.9	1036.0	1119.8	1212.1	1309.5	1399.2	1482.2	1551.3	1598.1	1611.9
32.5°	869.6	934.0	1009.4	1096.2	1193.9	1294.0	1387.3	1465.7	1523.3	1547.8	1531.1
35°	829.6	887.7	963.9	1052.9	1154.4	1261.0	1353.3	1419.4	1448.9	1425.7	1368.0
37.5°	781.6	839.2	915.8	1003.1	1108.1	1216.5	1299.9	1347.5	1337.8	1280.1	1194.1
40°	747.8	801.8	874.6	969.0	1071.4	1180.1	1253.4	1279.1	1252.1	1169.6	1078.2
42.5°	710.4	763.0	836.2	927.2	1035.7	1135.9	1199.8	1201.9	1156.7	1058.0	966.2
45°	653.5	703.6	772.7	867.5	967.7	1062.2	1104.2	1083.6	1000.2	905.0	812.7
47.5°	597.2	640.7	708.8	798.8	894.1	973.5	994.3	957.2	868.3	775.9	690.4
50°	556.1	599.9	664.0	750.0	841.8	910.5	920.6	871.2	784.1	690.9	624.0
52.5°	516.7	560.2	621.9	701.4	785.5	847.4	847.8	790.8	703.9	620.8	558.6
55°	458.8	498.0	553.6	624.8	699.8	748.2	736.5	677.5	602.1	530.0	475.6
57.5°	403.1	437.1	488.4	547.8	613.9	653.8	634.2	577.4	510.1	449.0	407.8
60°	366.9	399.4	443.2	499.2	554.8	586.1	567.5	516.1	454.2	404.9	369.1
62.5°	331.9	359.3	401.4	450.0	501.6	524.7	508.2	457.5	403.9	359.4	330.3
65°	282.3	304.6	338.3	380.0	417.6	437.3	423.4	376.2	335.3	303.3	280.2
67.5°	235.9	253.3	278.9	312.4	344.2	354.9	342.3	309.4	274.8	249.1	232.8
70°	203.9	220.4	241.9	267.5	295.3	306.7	294.1	267.9	239.7	216.1	200.1
72.5°	175.9	188.7	206.8	228.8	250.5	261.9	253.3	228.1	204.3	186.8	173.2
75°	134.0	145.0	157.6	173.2	190.0	197.6	190.0	172.8	156.3	143.2	133.6
77.5°	97.4	103.3	113.0	124.7	135.2	141.1	134.5	122.8	112.7	103.8	99.0
80°	74.1	78.3	85.1	94.3	101.6	107.0	102.8	93.1	85.1	79.2	77.1
82.5°	53.9	56.8	61.2	68.0	72.9	75.7	73.8	66.8	63.5	58.3	56.2
85°	26.5	28.2	31.2	33.3	37.5	37.9	38.3	35.4	32.5	31.2	29.5
87.5°	9.3	9.7	10.9	11.9	13.2	13.9	13.6	13.7	12.4	12.0	10.8
90°	0.9	1.7	2.0	2.2	2.2	3.9	3.9	4.5	5.1	4.8	5.1
92.5°	4.7	7.3	10.7	14.8	20.6	34.9	56.6	77.7	88.8	74.0	55.0
95°	10.1	12.9	16.6	23.2	35.0	59.3	105.3	172.2	228.1	234.6	207.5
97.5°	16.6	19.0	22.3	28.1	37.9	56.7	94.7	161.1	240.3	294.8	306.5
100°	21.3	23.2	26.6	31.9	40.9	57.4	89.0	146.2	225.1	296.8	337.6
102.5°	26.2	28.0	31.1	36.2	44.7	59.7	87.5	136.1	206.0	280.0	336.1
105°	33.6	35.0	38.3	43.4	51.5	65.0	88.2	127.4	183.6	249.5	313.5
107.5°	41.0	42.5	46.0	50.9	58.9	71.1	92.4	125.8	171.1	224.8	281.6
110°	46.2	47.6	50.9	56.0	63.5	75.9	95.5	126.3	166.8	212.5	262.4



TEST NUMBER: P332582-927

CATALOG NUMBER: SA4XXDIP-C795D365U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	51.1	52.8	55.8	60.9	68.4	80.3	98.9	127.6	164.9	205.6	248.2
115°	58.5	60.4	63.3	68.6	76.1	87.4	104.2	130.2	163.8	199.1	234.1
117.5°	65.8	67.6	70.7	75.7	83.5	94.1	109.6	132.9	163.5	196.1	227.1
120°	70.6	72.5	75.6	80.3	88.2	98.9	113.4	135.0	163.5	194.6	223.9
122.5°	75.0	77.0	79.9	85.1	92.7	103.3	117.0	137.0	163.3	192.8	221.3
125°	81.4	83.2	86.3	91.6	99.4	109.5	122.3	140.0	163.0	189.8	216.7
127.5°	86.4	88.5	92.0	97.5	105.4	115.2	127.0	142.4	162.3	185.8	211.1
130°	89.6	91.8	96.0	101.3	109.5	119.0	129.9	144.2	162.1	183.4	206.6
132.5°	92.3	95.2	99.2	105.0	112.6	122.2	132.8	145.8	161.9	181.2	201.9
135°	96.6	99.4	104.2	110.0	117.3	126.5	136.7	148.1	161.5	177.8	195.4
137.5°	100.6	103.7	108.2	114.3	121.3	129.9	139.3	149.5	161.5	174.9	189.6
140°	103.3	106.4	111.1	117.0	123.7	132.1	141.1	150.6	161.3	173.3	186.2
142.5°	106.5	109.3	113.8	119.5	126.0	134.2	142.4	151.5	161.3	172.0	183.1
145°	110.9	113.7	117.6	122.9	129.0	136.3	143.9	152.0	160.7	169.7	178.6
147.5°	115.3	117.8	121.8	126.2	131.7	138.6	145.2	152.3	159.7	167.6	175.0
150°	118.4	120.6	124.1	128.3	133.6	139.7	145.8	152.3	159.0	166.0	172.8
152.5°	121.1	123.3	126.5	130.2	135.1	140.6	146.3	151.9	157.9	164.2	170.3
155°	125.4	127.1	129.9	133.0	137.2	142.0	146.7	151.2	156.2	161.5	166.6
157.5°	129.1	130.7	132.8	135.5	138.9	142.9	146.7	150.4	154.5	158.8	162.6
160°	131.6	132.7	134.7	136.9	140.0	143.4	146.7	149.8	153.1	156.8	160.2
162.5°	133.6	134.5	136.3	138.2	140.7	143.8	146.7	149.1	151.8	155.0	157.7
165°	136.3	136.9	138.3	139.7	141.4	143.9	146.2	147.8	149.8	152.0	154.2
167.5°	138.6	138.9	139.9	140.7	142.0	143.9	145.4	146.5	147.7	149.3	151.0
170°	139.7	140.0	140.9	141.4	142.2	143.6	145.0	145.6	146.4	147.6	148.9
172.5°	140.9	140.9	141.5	141.8	142.4	143.4	144.6	144.7	145.0	146.0	147.2
175°	142.0	142.0	142.2	142.5	142.5	143.1	143.9	143.6	143.6	144.2	144.7
177.5°	142.5	142.3	142.5	142.5	142.5	142.8	143.1	142.8	142.8	143.0	143.1
180°	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5



TEST NUMBER: P332582-927

CATALOG NUMBER: SA4XXDIP-C795D365U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1017.1	1017.1	1017.1	1017.1	1017.1	1017.1	1017.1
2.5°	1072.0	1072.7	1075.7	1078.1	1078.7	1082.1	1082.4
5°	1166.2	1173.4	1187.2	1188.5	1190.6	1201.6	1193.2
7.5°	1276.6	1294.7	1306.9	1317.6	1321.5	1326.3	1325.3
10°	1347.3	1374.4	1387.8	1409.3	1410.2	1415.6	1412.2
12.5°	1418.5	1449.9	1474.4	1478.4	1496.4	1499.2	1504.0
15°	1519.2	1552.5	1586.7	1598.9	1623.7	1629.7	1638.9
17.5°	1614.0	1648.0	1671.9	1703.5	1713.7	1727.4	1718.1
20°	1665.9	1703.0	1733.3	1758.2	1768.7	1776.2	1775.4
22.5°	1697.3	1734.6	1759.2	1778.1	1787.9	1791.1	1790.9
25°	1716.8	1738.4	1745.9	1753.1	1742.2	1738.4	1740.0
27.5°	1662.2	1656.7	1636.9	1610.9	1584.0	1562.6	1550.9
30°	1587.1	1554.3	1524.3	1472.0	1445.1	1429.1	1414.8
32.5°	1480.6	1428.5	1371.0	1323.1	1292.4	1268.7	1265.1
35°	1298.1	1219.7	1149.4	1090.8	1060.4	1034.7	1028.8
37.5°	1103.6	1022.2	958.9	907.3	874.6	856.5	839.6
40°	974.5	904.6	842.2	798.4	773.6	760.5	750.0
42.5°	875.0	811.2	749.2	715.8	693.3	685.3	679.1
45°	737.7	678.3	635.3	610.1	597.0	583.5	577.2
47.5°	627.7	579.4	551.0	529.6	515.6	507.6	503.6
50°	565.4	525.8	500.5	484.1	471.4	465.1	461.8
52.5°	510.1	477.6	456.4	443.3	434.7	430.1	428.7
55°	439.4	414.5	401.1	389.8	383.4	379.2	377.5
57.5°	382.0	362.8	351.9	342.5	340.1	336.5	335.3
60°	344.2	329.5	320.2	313.9	311.8	307.5	308.4
62.5°	310.9	298.8	290.9	287.2	284.5	280.9	282.1
65°	262.9	254.1	249.9	246.4	243.1	241.0	242.6
67.5°	220.6	214.5	208.8	206.8	205.2	204.9	203.0
70°	193.0	187.9	182.8	181.6	181.6	179.9	179.5
72.5°	166.4	162.6	159.2	158.4	157.0	157.6	155.9
75°	128.5	125.6	124.3	123.0	122.6	122.6	121.4
77.5°	95.0	92.8	90.8	90.8	89.2	88.6	88.5
80°	72.0	71.2	69.6	69.6	68.7	69.1	68.3
82.5°	54.2	53.0	52.7	52.0	50.8	50.9	50.1
85°	29.1	27.8	27.4	26.1	25.3	26.1	25.3
87.5°	11.2	10.9	10.5	9.9	9.7	9.6	8.6
90°	5.3	5.6	5.6	5.9	6.2	5.9	5.9
92.5°	41.4	33.0	27.3	24.0	22.5	21.5	21.5
95°	164.1	126.5	99.4	85.6	77.0	71.9	68.3
97.5°	290.4	263.0	233.8	213.7	196.9	188.5	182.6
100°	343.3	329.5	308.8	284.5	267.4	259.0	256.7
102.5°	363.8	367.8	359.2	344.3	331.9	323.1	321.2
105°	362.0	389.8	401.2	401.8	399.5	395.6	394.0
107.5°	333.2	372.2	397.2	411.0	417.4	420.2	420.9
110°	310.8	351.4	382.1	402.0	413.8	418.8	421.4



TEST NUMBER: P332582-927

CATALOG NUMBER: SA4XXDIP-C795D365U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	291.0	329.4	360.2	382.8	397.0	404.1	408.1
115°	268.5	301.3	328.1	350.2	367.0	376.0	378.3
117.5°	255.6	281.4	304.2	323.1	337.2	346.2	347.9
120°	250.0	272.4	292.3	308.2	320.6	327.9	331.0
122.5°	246.4	266.8	284.2	297.7	308.2	314.4	317.5
125°	240.7	260.1	275.5	286.7	294.9	300.2	301.8
127.5°	234.1	253.4	268.0	279.2	286.5	291.0	292.6
130°	228.8	247.8	262.6	274.1	281.1	285.6	287.2
132.5°	222.7	241.3	256.1	267.4	275.3	279.6	281.2
135°	213.7	230.7	244.7	255.9	263.7	268.2	269.9
137.5°	204.9	219.4	232.0	242.5	250.2	253.9	255.9
140°	199.3	211.9	223.7	233.5	239.6	243.6	245.8
142.5°	194.6	205.4	215.6	224.3	230.0	233.5	235.0
145°	188.1	196.5	204.4	211.4	216.1	219.0	220.3
147.5°	182.5	189.3	195.4	200.6	204.7	206.8	207.3
150°	179.2	184.8	189.8	194.3	198.0	199.6	199.9
152.5°	175.9	181.0	185.1	188.9	191.9	192.9	193.2
155°	171.0	175.2	178.6	181.4	183.6	184.5	184.5
157.5°	166.4	169.9	172.6	174.7	176.4	176.9	176.9
160°	163.2	166.3	168.6	170.2	171.9	172.2	172.2
162.5°	160.3	162.7	164.8	166.0	167.6	167.9	167.7
165°	156.0	157.9	159.3	160.4	161.5	161.3	161.0
167.5°	152.3	153.8	154.6	155.2	156.0	155.9	155.7
170°	149.8	150.9	151.8	152.3	152.6	152.3	152.3
172.5°	147.7	148.5	149.1	149.4	149.6	149.4	148.9
175°	145.0	145.6	145.6	145.6	146.2	145.6	145.0
177.5°	143.4	143.4	143.6	143.4	143.6	143.1	142.8
180°	142.5	142.5	142.5	142.5	142.5	142.5	142.5

(END OF REPORT)