

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332867-927

Luminaire Tested: **SA4XXRDIP-C350D365U927-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332867-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C350D365U927-4F0-1E-UDD-A4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2213.5 lumens
Efficiency: N/A
Efficacy: 109.0 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 20.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332867-927
CATALOG NUMBER: SA4XXRDIP-C350D365U927-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332867-927

CATALOG NUMBER: SA4XXRDIP-C350D365U927-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	53				53
1	99	95	91	88	92	88	85	82	75	73	71	64	62	61	53	52	51	46				46
2	91	83	77	72	84	78	72	68	67	63	60	57	54	51	47	45	44	39				39
3	83	74	67	61	77	69	62	57	59	54	51	50	47	44	42	40	38	34				34
4	76	66	58	52	70	61	54	49	53	48	43	45	41	38	38	35	33	29				29
5	70	59	51	45	65	55	48	42	47	42	38	41	37	33	34	31	29	26				26
6	65	53	45	39	60	49	42	37	43	37	33	37	33	29	31	28	26	23				23
7	60	48	40	34	55	45	38	33	39	33	29	34	29	26	29	25	23	20				20
8	56	43	36	31	51	41	34	29	36	30	26	31	27	23	26	23	21	18				18
9	52	40	32	27	48	37	31	26	33	27	24	28	24	21	24	21	19	17				17
10	48	36	29	25	45	34	28	23	30	25	21	26	22	19	23	19	17	15				15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	3756	3756	3756	3756
5°	4357	3767	3331	3767
10°	5155	3751	2972	3751
15°	5954	3717	2554	3717
20°	6630	3669	2310	3669
25°	6844	3622	2144	3622
30°	5991	3566	2045	3566
35°	4664	3481	1985	3481
40°	3497	3385	1952	3385
45°	2762	3230	1934	3230
50°	2331	3052	1879	3052
55°	2031	2856	1779	2856
60°	1828	2651	1574	2651
65°	1612	2432	1354	2432
70°	1452	2205	1220	2205
75°	1216	1953	1042	1953
80°	1027	1664	976	1664
85°	861	1306	861	1306



TEST NUMBER: P332867-927

CATALOG NUMBER: SA4XXRDIP-C350D365U927-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.1	2.0
10°-20°	136.0	6.1
20°-30°	212.7	9.6
30°-40°	236.5	10.7
40°-50°	209.8	9.5
50°-60°	163.5	7.4
60°-70°	107.0	4.8
70°-80°	52.6	2.4
80°-90°	13.8	0.6
90°-100°	102.9	4.7
100°-110°	214.2	9.7
110°-120°	191.9	8.7
120°-130°	161.4	7.3
130°-140°	134.6	6.1
140°-150°	102.8	4.6
150°-160°	72.3	3.3
160°-170°	42.5	1.9
170°-180°	13.8	0.6
0°-30°	393.8	17.8
0°-40°	630.3	28.5
0°-60°	1003.6	45.3
0°-90°	1177.0	53.2
90°-120°	509.0	23.0
90°-150°	907.8	41.0
90°-180°	1036.0	46.8
0°-180°	2213.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	465	465	465	465	465	
5°	538	465	411	465	538	54
15°	712	445	306	445	712	203
25°	768	407	241	407	768	341
35°	473	353	201	353	473	297
45°	242	283	169	283	242	192
55°	144	203	126	203	144	131
65°	84	127	71	127	84	85
75°	39	63	33	63	39	43
85°	9	14	9	14	9	11
90°	6	0	6	0	6	5
95°	68	9	68	9	68	106
105°	394	33	394	33	394	389
115°	378	58	378	58	378	375
125°	302	80	302	80	302	274
135°	270	96	270	96	270	208
145°	220	110	220	110	220	140
155°	184	125	184	125	184	86
165°	161	136	161	136	161	46
175°	145	142	145	142	145	14
180°	142	142	142	142	142	



TEST NUMBER: P332867-927

CATALOG NUMBER: SA4XXRDIP-C350D365U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3
2.5°	490.8	492.2	490.8	490.7	489.2	488.7	488.1	486.2	482.6	480.5	480.9
5°	537.7	542.4	539.8	539.4	535.3	531.2	528.5	522.5	516.1	511.8	508.3
7.5°	591.9	594.6	592.9	590.3	583.7	579.9	573.8	565.9	554.4	545.7	537.7
10°	628.8	631.1	630.3	625.4	620.6	610.6	605.0	594.0	579.5	568.1	557.4
12.5°	665.1	667.5	660.9	661.2	651.9	644.0	635.2	621.2	604.6	589.9	576.5
15°	712.4	709.4	709.4	705.7	695.4	684.5	675.3	660.7	639.7	622.1	603.5
17.5°	749.5	750.5	749.0	740.1	732.1	720.8	703.9	686.9	667.4	643.7	624.8
20°	771.7	771.7	770.0	764.0	753.5	741.5	723.3	704.7	680.0	656.2	634.9
22.5°	780.7	781.3	779.3	774.4	764.9	753.2	737.7	718.8	693.3	666.5	640.1
25°	768.3	771.9	772.2	771.0	768.1	761.0	747.7	728.4	705.5	676.4	647.9
27.5°	705.4	709.9	713.8	720.3	729.0	733.4	734.0	724.2	704.3	676.3	647.6
30°	642.7	646.4	658.6	674.5	686.9	698.2	708.0	710.6	699.3	674.2	644.0
32.5°	573.1	578.2	590.4	607.5	628.1	647.2	669.1	680.2	679.9	664.9	637.0
35°	473.2	477.0	488.2	506.2	530.9	559.3	594.0	620.9	639.3	638.0	620.9
37.5°	381.7	385.9	397.2	412.2	436.2	471.2	504.8	542.0	575.9	595.0	589.3
40°	331.8	332.0	343.1	358.5	381.0	411.5	448.1	489.3	527.2	558.2	564.1
42.5°	292.6	292.6	299.9	316.5	332.6	361.4	396.3	437.3	481.6	517.4	533.2
45°	241.9	243.5	249.5	259.4	272.2	296.6	324.6	362.6	412.3	454.6	481.1
47.5°	204.8	207.3	211.1	219.2	229.3	245.6	268.7	302.9	343.3	389.9	427.5
50°	185.6	186.0	190.8	195.4	204.1	217.1	237.3	265.9	303.0	347.8	389.6
52.5°	169.1	169.1	172.0	177.7	184.8	194.9	211.3	237.2	270.1	310.3	353.5
55°	144.3	145.3	147.6	152.0	157.5	164.6	177.5	197.0	222.9	257.2	296.4
57.5°	125.6	126.0	127.8	129.7	134.7	139.9	149.6	163.1	184.9	213.0	249.5
60°	113.2	113.4	114.0	116.8	120.7	125.6	132.2	143.6	162.0	187.7	216.6
62.5°	101.2	101.6	102.4	104.5	107.6	110.9	117.8	127.0	142.2	164.1	190.1
65°	84.4	84.5	85.9	86.6	89.0	92.1	97.1	103.3	113.8	132.2	151.9
67.5°	70.5	70.5	70.6	71.6	73.3	75.3	78.3	83.3	91.2	102.4	119.8
70°	61.5	61.5	61.9	62.4	63.4	65.0	66.8	70.5	76.3	85.5	98.8
72.5°	53.1	53.2	53.6	53.7	54.2	55.6	56.9	59.3	63.5	70.5	81.3
75°	39.0	39.5	40.5	41.3	42.2	42.0	43.3	44.8	46.1	50.2	56.4
77.5°	29.0	28.8	28.8	29.5	29.5	29.8	30.7	31.8	32.9	34.8	37.0
80°	22.1	22.1	22.7	22.9	22.7	22.9	23.8	24.4	24.7	25.5	27.6
82.5°	16.7	17.0	16.9	17.0	17.1	17.3	18.1	18.2	18.6	18.9	19.7
85°	9.3	9.6	9.7	9.3	9.3	9.3	9.7	9.9	10.3	10.1	10.5
87.5°	4.4	4.4	4.5	4.4	4.6	4.4	4.5	4.8	4.4	4.6	4.5
90°	5.9	5.9	6.2	5.9	5.6	5.6	5.3	5.1	4.8	5.1	4.5
92.5°	21.5	21.5	22.5	24.0	27.3	33.0	41.4	55.0	74.0	88.8	77.7
95°	68.3	71.9	77.0	85.6	99.4	126.5	164.1	207.5	234.6	228.1	172.2
97.5°	182.6	188.5	196.9	213.7	233.8	263.0	290.4	306.5	294.8	240.3	161.1
100°	256.7	259.0	267.4	284.5	308.8	329.5	343.3	337.6	296.8	225.1	146.2
102.5°	321.2	323.1	331.9	344.3	359.2	367.8	363.8	336.1	280.0	206.0	136.1
105°	394.0	395.6	399.5	401.8	401.2	389.8	362.0	313.5	249.5	183.6	127.4
107.5°	420.9	420.2	417.4	411.0	397.2	372.2	333.2	281.6	224.8	171.1	125.8
110°	421.4	418.8	413.8	402.0	382.1	351.4	310.8	262.4	212.5	166.8	126.3



TEST NUMBER: P332867-927

CATALOG NUMBER: SA4XXRDIP-C350D365U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	408.1	404.1	397.0	382.8	360.2	329.4	291.0	248.2	205.6	164.9	127.6
115°	378.3	376.0	367.0	350.2	328.1	301.3	268.5	234.1	199.1	163.8	130.2
117.5°	347.9	346.2	337.2	323.1	304.2	281.4	255.6	227.1	196.1	163.5	132.9
120°	331.0	327.9	320.6	308.2	292.3	272.4	250.0	223.9	194.6	163.5	135.0
122.5°	317.5	314.4	308.2	297.7	284.2	266.8	246.4	221.3	192.8	163.3	137.0
125°	301.8	300.2	294.9	286.7	275.5	260.1	240.7	216.7	189.8	163.0	140.0
127.5°	292.6	291.0	286.5	279.2	268.0	253.4	234.1	211.1	185.8	162.3	142.4
130°	287.2	285.6	281.1	274.1	262.6	247.8	228.8	206.6	183.4	162.1	144.2
132.5°	281.2	279.6	275.3	267.4	256.1	241.3	222.7	201.9	181.2	161.9	145.8
135°	269.9	268.2	263.7	255.9	244.7	230.7	213.7	195.4	177.8	161.5	148.1
137.5°	255.9	253.9	250.2	242.5	232.0	219.4	204.9	189.6	174.9	161.5	149.5
140°	245.8	243.6	239.6	233.5	223.7	211.9	199.3	186.2	173.3	161.3	150.6
142.5°	235.0	233.5	230.0	224.3	215.6	205.4	194.6	183.1	172.0	161.3	151.5
145°	220.3	219.0	216.1	211.4	204.4	196.5	188.1	178.6	169.7	160.7	152.0
147.5°	207.3	206.8	204.7	200.6	195.4	189.3	182.5	175.0	167.6	159.7	152.3
150°	199.9	199.6	198.0	194.3	189.8	184.8	179.2	172.8	166.0	159.0	152.3
152.5°	193.2	192.9	191.9	188.9	185.1	181.0	175.9	170.3	164.2	157.9	151.9
155°	184.5	184.5	183.6	181.4	178.6	175.2	171.0	166.6	161.5	156.2	151.2
157.5°	176.9	176.9	176.4	174.7	172.6	169.9	166.4	162.6	158.8	154.5	150.4
160°	172.2	172.2	171.9	170.2	168.6	166.3	163.2	160.2	156.8	153.1	149.8
162.5°	167.7	167.9	167.6	166.0	164.8	162.7	160.3	157.7	155.0	151.8	149.1
165°	161.0	161.3	161.5	160.4	159.3	157.9	156.0	154.2	152.0	149.8	147.8
167.5°	155.7	155.9	156.0	155.2	154.6	153.8	152.3	151.0	149.3	147.7	146.5
170°	152.3	152.3	152.6	152.3	151.8	150.9	149.8	148.9	147.6	146.4	145.6
172.5°	148.9	149.4	149.6	149.4	149.1	148.5	147.7	147.2	146.0	145.0	144.7
175°	145.0	145.6	146.2	145.6	145.6	145.6	145.0	144.7	144.2	143.6	143.6
177.5°	142.8	143.1	143.6	143.4	143.6	143.4	143.4	143.1	143.0	142.8	142.8
180°	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5



TEST NUMBER: P332867-927

CATALOG NUMBER: SA4XXRDIP-C350D365U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3
2.5°	479.4	477.4	476.3	473.9	471.0	469.5	468.2	466.2	463.7	461.0	459.1
5°	503.7	499.2	493.6	486.9	480.9	475.1	470.0	464.9	459.1	453.1	447.2
7.5°	528.7	519.9	510.3	499.2	488.5	478.7	469.7	461.1	451.4	442.6	434.7
10°	546.1	534.2	520.9	506.8	492.7	480.5	468.5	457.6	445.7	435.0	426.0
12.5°	560.2	546.1	530.1	512.6	495.7	480.9	467.1	453.0	439.3	427.8	415.7
15°	583.6	564.4	542.8	521.7	499.9	479.7	461.2	444.7	429.1	412.8	401.4
17.5°	599.8	576.8	550.6	525.4	499.5	475.8	454.4	434.7	416.8	400.1	386.5
20°	609.3	584.0	554.9	526.2	497.2	471.9	448.9	427.1	408.5	390.5	376.4
22.5°	614.7	586.7	554.9	524.9	494.8	467.4	442.1	419.5	399.3	381.2	365.7
25°	616.5	586.5	554.1	519.5	486.6	457.5	431.2	406.6	384.1	366.1	349.7
27.5°	614.0	578.7	545.5	510.1	476.0	445.4	417.9	392.1	369.6	350.2	333.3
30°	610.5	572.6	536.9	500.2	465.7	436.3	407.2	382.5	359.0	339.0	321.9
32.5°	602.6	565.1	526.7	489.1	454.2	423.8	396.2	371.4	348.4	327.9	309.7
35°	587.2	549.1	507.6	468.9	434.6	403.1	377.2	353.2	331.3	309.3	290.3
37.5°	566.8	528.0	486.6	444.3	409.9	380.2	356.5	333.9	312.5	292.5	271.3
40°	547.6	512.2	469.4	427.5	392.2	363.5	341.6	321.2	299.6	279.7	258.6
42.5°	524.4	494.2	451.0	408.8	374.1	346.4	326.0	306.0	286.4	267.1	245.0
45°	485.6	462.7	422.2	381.8	346.7	319.2	300.6	282.9	265.7	247.3	226.5
47.5°	441.1	425.6	390.7	349.2	316.8	292.2	274.0	259.6	245.0	226.6	208.4
50°	410.2	400.3	366.5	328.7	297.7	275.0	256.5	243.0	230.8	213.2	196.9
52.5°	377.2	371.9	343.4	307.2	277.3	255.1	239.2	227.1	214.8	200.1	184.9
55°	326.9	329.8	305.6	274.3	246.1	227.4	213.0	202.9	192.3	180.0	168.2
57.5°	275.6	285.9	269.7	242.2	215.8	198.4	187.6	179.1	170.2	160.0	149.9
60°	244.9	253.5	244.3	220.1	197.0	180.9	170.8	164.2	155.4	146.1	138.4
62.5°	214.8	224.1	218.6	199.1	177.7	163.8	154.9	148.8	142.2	134.0	126.0
65°	177.2	183.2	180.5	167.1	151.9	140.1	131.8	127.3	121.3	115.3	108.2
67.5°	135.7	147.3	145.8	138.6	125.5	116.2	110.8	106.9	101.4	97.0	92.1
70°	111.5	122.2	122.1	116.2	109.1	100.5	96.7	93.4	88.5	84.2	80.2
72.5°	91.3	101.1	102.6	98.1	93.2	86.7	83.1	80.8	76.0	73.1	69.9
75°	63.9	71.1	73.0	73.0	70.7	67.3	64.1	62.6	59.3	56.6	54.7
77.5°	41.9	46.4	49.4	50.0	50.4	49.2	46.6	45.6	42.9	42.1	40.2
80°	29.6	32.6	36.0	37.2	38.0	37.7	36.6	35.8	33.4	32.4	31.7
82.5°	20.4	22.1	24.9	27.4	27.1	28.1	27.1	26.5	24.6	24.3	23.6
85°	10.7	10.9	11.2	12.9	13.9	14.3	14.4	14.1	13.5	13.5	12.2
87.5°	4.4	4.2	4.2	4.2	4.3	4.8	5.1	5.1	4.8	4.5	4.1
90°	3.9	3.9	2.2	2.2	2.0	1.7	0.9	0.3	0.9	1.7	2.0
92.5°	56.6	34.9	20.6	14.8	10.7	7.3	4.7	3.2	4.7	7.3	10.7
95°	105.3	59.3	35.0	23.2	16.6	12.9	10.1	9.3	10.1	12.9	16.6
97.5°	94.7	56.7	37.9	28.1	22.3	19.0	16.6	16.6	16.6	19.0	22.3
100°	89.0	57.4	40.9	31.9	26.6	23.2	21.3	21.3	21.3	23.2	26.6
102.5°	87.5	59.7	44.7	36.2	31.1	28.0	26.2	25.7	26.2	28.0	31.1
105°	88.2	65.0	51.5	43.4	38.3	35.0	33.6	32.8	33.6	35.0	38.3
107.5°	92.4	71.1	58.9	50.9	46.0	42.5	41.0	40.5	41.0	42.5	46.0
110°	95.5	75.9	63.5	56.0	50.9	47.6	46.2	45.6	46.2	47.6	50.9



TEST NUMBER: P332867-927

CATALOG NUMBER: SA4XXRDIP-C350D365U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	98.9	80.3	68.4	60.9	55.8	52.8	51.1	50.5	51.1	52.8	55.8
115°	104.2	87.4	76.1	68.6	63.3	60.4	58.5	57.7	58.5	60.4	63.3
117.5°	109.6	94.1	83.5	75.7	70.7	67.6	65.8	65.0	65.8	67.6	70.7
120°	113.4	98.9	88.2	80.3	75.6	72.5	70.6	70.0	70.6	72.5	75.6
122.5°	117.0	103.3	92.7	85.1	79.9	77.0	75.0	74.5	75.0	77.0	79.9
125°	122.3	109.5	99.4	91.6	86.3	83.2	81.4	80.3	81.4	83.2	86.3
127.5°	127.0	115.2	105.4	97.5	92.0	88.5	86.4	85.6	86.4	88.5	92.0
130°	129.9	119.0	109.5	101.3	96.0	91.8	89.6	88.5	89.6	91.8	96.0
132.5°	132.8	122.2	112.6	105.0	99.2	95.2	92.3	91.4	92.3	95.2	99.2
135°	136.7	126.5	117.3	110.0	104.2	99.4	96.6	95.5	96.6	99.4	104.2
137.5°	139.3	129.9	121.3	114.3	108.2	103.7	100.6	99.6	100.6	103.7	108.2
140°	141.1	132.1	123.7	117.0	111.1	106.4	103.3	102.5	103.3	106.4	111.1
142.5°	142.4	134.2	126.0	119.5	113.8	109.3	106.5	105.6	106.5	109.3	113.8
145°	143.9	136.3	129.0	122.9	117.6	113.7	110.9	110.0	110.9	113.7	117.6
147.5°	145.2	138.6	131.7	126.2	121.8	117.8	115.3	115.0	115.3	117.8	121.8
150°	145.8	139.7	133.6	128.3	124.1	120.6	118.4	118.1	118.4	120.6	124.1
152.5°	146.3	140.6	135.1	130.2	126.5	123.3	121.1	121.0	121.1	123.3	126.5
155°	146.7	142.0	137.2	133.0	129.9	127.1	125.4	125.2	125.4	127.1	129.9
157.5°	146.7	142.9	138.9	135.5	132.8	130.7	129.1	129.1	129.1	130.7	132.8
160°	146.7	143.4	140.0	136.9	134.7	132.7	131.6	131.6	131.6	132.7	134.7
162.5°	146.7	143.8	140.7	138.2	136.3	134.5	133.6	133.8	133.6	134.5	136.3
165°	146.2	143.9	141.4	139.7	138.3	136.9	136.3	136.3	136.3	136.9	138.3
167.5°	145.4	143.9	142.0	140.7	139.9	138.9	138.6	138.9	138.6	138.9	139.9
170°	145.0	143.6	142.2	141.4	140.9	140.0	139.7	140.0	139.7	140.0	140.9
172.5°	144.6	143.4	142.4	141.8	141.5	140.9	140.9	141.1	140.9	140.9	141.5
175°	143.9	143.1	142.5	142.5	142.2	142.0	142.0	142.2	142.0	142.0	142.2
177.5°	143.1	142.8	142.5	142.5	142.5	142.3	142.5	142.8	142.5	142.3	142.5
180°	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5



TEST NUMBER: P332867-927

CATALOG NUMBER: SA4XXRDIP-C350D365U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3
2.5°	456.9	455.4	453.5	451.2	448.5	446.2	445.0	446.0	446.5	445.2	445.0
5°	443.0	438.3	434.6	429.0	424.5	420.7	418.1	416.9	417.3	414.3	413.6
7.5°	427.4	421.8	415.7	409.0	402.8	397.3	394.4	392.8	389.6	388.2	386.0
10°	417.3	409.9	403.9	395.9	388.8	382.3	379.1	376.4	373.3	371.8	368.6
12.5°	407.0	398.3	391.7	383.5	376.2	368.4	365.3	360.4	355.5	352.3	348.2
15°	392.4	381.9	373.8	364.1	355.5	346.5	338.4	329.4	326.1	318.9	314.8
17.5°	375.3	364.7	354.7	341.7	328.4	317.1	308.6	299.9	294.8	290.3	288.1
20°	364.1	354.3	340.5	325.3	310.5	298.1	291.1	285.5	279.9	276.7	274.5
22.5°	353.5	341.0	324.9	308.5	293.7	284.0	278.1	272.4	267.8	264.7	261.7
25°	335.6	319.2	302.2	283.4	273.4	264.9	258.6	253.8	251.0	247.1	245.6
27.5°	317.3	297.5	278.7	266.1	255.6	247.8	242.2	238.8	235.2	232.7	230.7
30°	303.2	283.1	266.3	254.2	243.5	237.2	232.7	228.5	225.7	223.6	222.2
32.5°	289.2	269.2	255.0	242.1	233.6	227.4	222.6	219.5	217.3	214.7	213.7
35°	269.0	251.2	238.8	227.2	218.6	213.0	209.2	206.0	204.1	203.4	202.9
37.5°	249.6	235.0	221.7	212.2	204.5	200.1	195.7	194.1	192.8	191.5	192.1
40°	237.3	223.6	211.8	201.8	195.5	190.7	188.1	186.2	185.1	185.1	185.1
42.5°	226.7	213.3	201.8	192.7	186.6	182.4	179.5	177.9	177.5	177.4	178.3
45°	210.2	197.8	186.2	178.6	173.4	169.3	167.6	166.3	166.3	167.1	167.2
47.5°	193.8	182.2	172.9	164.5	159.6	157.1	155.6	155.0	155.0	155.7	156.6
50°	183.7	172.3	163.1	155.6	151.1	148.7	147.3	146.9	147.3	147.3	148.7
52.5°	172.8	162.6	153.5	147.2	142.1	139.8	139.1	138.6	138.8	139.4	140.0
55°	156.8	147.6	138.9	132.9	129.2	127.7	126.0	126.2	125.8	126.2	126.2
57.5°	140.6	132.4	124.4	119.6	116.3	114.2	112.3	112.8	112.3	112.2	111.9
60°	130.3	121.3	114.9	110.6	106.9	105.0	103.3	103.7	103.1	102.7	102.0
62.5°	119.1	111.5	105.4	101.3	98.3	96.2	94.4	94.1	92.8	91.5	89.8
65°	102.7	96.6	91.1	87.2	84.4	82.7	81.4	80.2	77.4	74.5	73.0
67.5°	86.9	82.4	77.3	74.0	71.7	69.6	67.0	65.1	62.5	60.8	59.9
70°	76.7	72.4	68.0	64.9	62.4	60.4	57.6	56.2	54.3	53.6	52.7
72.5°	66.9	62.9	58.9	56.0	53.5	51.8	49.6	48.3	47.5	47.1	46.3
75°	52.1	49.0	45.9	43.3	41.3	40.1	39.2	38.3	37.9	36.2	35.3
77.5°	38.0	35.9	34.1	32.2	30.7	29.9	28.1	27.1	26.5	25.7	25.4
80°	29.6	28.1	26.2	25.1	23.1	22.3	21.5	21.4	21.2	21.0	20.8
82.5°	22.3	20.8	18.9	18.2	17.7	17.2	16.8	16.6	16.4	16.5	16.5
85°	11.2	10.5	10.5	10.3	10.1	9.9	9.7	9.7	9.6	9.7	9.6
87.5°	4.2	4.0	4.4	4.1	4.4	4.4	4.3	4.3	4.5	4.3	4.3
90°	2.2	2.2	3.9	3.9	4.5	5.1	4.8	5.1	5.3	5.6	5.6
92.5°	14.8	20.6	34.9	56.6	77.7	88.8	74.0	55.0	41.4	33.0	27.3
95°	23.2	35.0	59.3	105.3	172.2	228.1	234.6	207.5	164.1	126.5	99.4
97.5°	28.1	37.9	56.7	94.7	161.1	240.3	294.8	306.5	290.4	263.0	233.8
100°	31.9	40.9	57.4	89.0	146.2	225.1	296.8	337.6	343.3	329.5	308.8
102.5°	36.2	44.7	59.7	87.5	136.1	206.0	280.0	336.1	363.8	367.8	359.2
105°	43.4	51.5	65.0	88.2	127.4	183.6	249.5	313.5	362.0	389.8	401.2
107.5°	50.9	58.9	71.1	92.4	125.8	171.1	224.8	281.6	333.2	372.2	397.2
110°	56.0	63.5	75.9	95.5	126.3	166.8	212.5	262.4	310.8	351.4	382.1



TEST NUMBER: P332867-927

CATALOG NUMBER: SA4XXRDIP-C350D365U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	60.9	68.4	80.3	98.9	127.6	164.9	205.6	248.2	291.0	329.4	360.2
115°	68.6	76.1	87.4	104.2	130.2	163.8	199.1	234.1	268.5	301.3	328.1
117.5°	75.7	83.5	94.1	109.6	132.9	163.5	196.1	227.1	255.6	281.4	304.2
120°	80.3	88.2	98.9	113.4	135.0	163.5	194.6	223.9	250.0	272.4	292.3
122.5°	85.1	92.7	103.3	117.0	137.0	163.3	192.8	221.3	246.4	266.8	284.2
125°	91.6	99.4	109.5	122.3	140.0	163.0	189.8	216.7	240.7	260.1	275.5
127.5°	97.5	105.4	115.2	127.0	142.4	162.3	185.8	211.1	234.1	253.4	268.0
130°	101.3	109.5	119.0	129.9	144.2	162.1	183.4	206.6	228.8	247.8	262.6
132.5°	105.0	112.6	122.2	132.8	145.8	161.9	181.2	201.9	222.7	241.3	256.1
135°	110.0	117.3	126.5	136.7	148.1	161.5	177.8	195.4	213.7	230.7	244.7
137.5°	114.3	121.3	129.9	139.3	149.5	161.5	174.9	189.6	204.9	219.4	232.0
140°	117.0	123.7	132.1	141.1	150.6	161.3	173.3	186.2	199.3	211.9	223.7
142.5°	119.5	126.0	134.2	142.4	151.5	161.3	172.0	183.1	194.6	205.4	215.6
145°	122.9	129.0	136.3	143.9	152.0	160.7	169.7	178.6	188.1	196.5	204.4
147.5°	126.2	131.7	138.6	145.2	152.3	159.7	167.6	175.0	182.5	189.3	195.4
150°	128.3	133.6	139.7	145.8	152.3	159.0	166.0	172.8	179.2	184.8	189.8
152.5°	130.2	135.1	140.6	146.3	151.9	157.9	164.2	170.3	175.9	181.0	185.1
155°	133.0	137.2	142.0	146.7	151.2	156.2	161.5	166.6	171.0	175.2	178.6
157.5°	135.5	138.9	142.9	146.7	150.4	154.5	158.8	162.6	166.4	169.9	172.6
160°	136.9	140.0	143.4	146.7	149.8	153.1	156.8	160.2	163.2	166.3	168.6
162.5°	138.2	140.7	143.8	146.7	149.1	151.8	155.0	157.7	160.3	162.7	164.8
165°	139.7	141.4	143.9	146.2	147.8	149.8	152.0	154.2	156.0	157.9	159.3
167.5°	140.7	142.0	143.9	145.4	146.5	147.7	149.3	151.0	152.3	153.8	154.6
170°	141.4	142.2	143.6	145.0	145.6	146.4	147.6	148.9	149.8	150.9	151.8
172.5°	141.8	142.4	143.4	144.6	144.7	145.0	146.0	147.2	147.7	148.5	149.1
175°	142.5	142.5	143.1	143.9	143.6	143.6	144.2	144.7	145.0	145.6	145.6
177.5°	142.5	142.5	142.8	143.1	142.8	142.8	143.0	143.1	143.4	143.4	143.6
180°	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5



TEST NUMBER: P332867-927

CATALOG NUMBER: SA4XXRDIP-C350D365U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3
2.5°	444.2	444.5	443.5	443.1	443.5	444.5	444.2	445.0	445.2	446.5	446.0
5°	412.1	411.7	410.7	411.0	410.7	411.7	412.1	413.6	414.3	417.3	416.9
7.5°	384.6	383.2	383.6	382.1	383.6	383.2	384.6	386.0	388.2	389.6	392.8
10°	367.8	365.8	364.1	362.6	364.1	365.8	367.8	368.6	371.8	373.3	376.4
12.5°	344.9	343.1	340.9	341.3	340.9	343.1	344.9	348.2	352.3	355.5	360.4
15°	312.4	309.5	305.1	305.6	305.1	309.5	312.4	314.8	318.9	326.1	329.4
17.5°	284.8	284.8	282.7	283.3	282.7	284.8	284.8	288.1	290.3	294.8	299.9
20°	270.5	269.3	269.4	268.9	269.4	269.3	270.5	274.5	276.7	279.9	285.5
22.5°	260.6	259.0	257.7	256.6	257.7	259.0	260.6	261.7	264.7	267.8	272.4
25°	243.9	242.8	241.1	240.7	241.1	242.8	243.9	245.6	247.1	251.0	253.8
27.5°	229.2	229.0	228.3	227.4	228.3	229.0	229.2	230.7	232.7	235.2	238.8
30°	220.7	220.3	219.9	219.4	219.9	220.3	220.7	222.2	223.6	225.7	228.5
32.5°	213.0	212.8	212.4	212.5	212.4	212.8	213.0	213.7	214.7	217.3	219.5
35°	202.1	201.9	201.5	201.4	201.5	201.9	202.1	202.9	203.4	204.1	206.0
37.5°	191.9	192.4	192.2	192.1	192.2	192.4	191.9	192.1	191.5	192.8	194.1
40°	184.9	185.1	185.4	185.2	185.4	185.1	184.9	185.1	185.1	185.1	186.2
42.5°	179.0	179.0	179.6	179.0	179.6	179.0	179.0	178.3	177.4	177.5	177.9
45°	168.6	169.7	169.4	169.4	169.4	169.7	168.6	167.2	167.1	166.3	166.3
47.5°	157.1	158.1	158.4	158.3	158.4	158.1	157.1	156.6	155.7	155.0	155.0
50°	149.6	149.2	149.8	149.6	149.8	149.2	149.6	148.7	147.3	147.3	146.9
52.5°	140.5	140.5	140.5	140.3	140.5	140.5	140.5	140.0	139.4	138.8	138.6
55°	126.4	126.6	126.2	126.4	126.2	126.6	126.4	126.2	126.2	125.8	126.2
57.5°	111.1	110.2	110.5	110.1	110.5	110.2	111.1	111.9	112.2	112.3	112.8
60°	100.1	98.6	98.2	97.5	98.2	98.6	100.1	102.0	102.7	103.1	103.7
62.5°	87.9	86.7	85.5	86.1	85.5	86.7	87.9	89.8	91.5	92.8	94.1
65°	71.5	70.7	70.1	70.9	70.1	70.7	71.5	73.0	74.5	77.4	80.2
67.5°	59.1	58.7	58.7	58.4	58.7	58.7	59.1	59.9	60.8	62.5	65.1
70°	52.7	52.1	52.1	51.7	52.1	52.1	52.7	52.7	53.6	54.3	56.2
72.5°	46.1	45.6	45.7	45.5	45.7	45.6	46.1	46.3	47.1	47.5	48.3
75°	34.1	33.2	33.2	33.4	33.2	33.2	34.1	35.3	36.2	37.9	38.3
77.5°	25.4	25.3	25.5	25.2	25.5	25.3	25.4	25.4	25.7	26.5	27.1
80°	20.8	20.6	20.4	21.0	20.4	20.6	20.8	20.8	21.0	21.2	21.4
82.5°	16.2	16.2	16.1	16.8	16.1	16.2	16.2	16.5	16.5	16.4	16.6
85°	9.7	9.3	9.7	9.3	9.7	9.3	9.7	9.6	9.7	9.6	9.7
87.5°	4.6	4.5	4.4	4.4	4.4	4.5	4.6	4.3	4.3	4.5	4.3
90°	5.9	6.2	5.9	5.9	5.9	6.2	5.9	5.6	5.6	5.3	5.1
92.5°	24.0	22.5	21.5	21.5	21.5	22.5	24.0	27.3	33.0	41.4	55.0
95°	85.6	77.0	71.9	68.3	71.9	77.0	85.6	99.4	126.5	164.1	207.5
97.5°	213.7	196.9	188.5	182.6	188.5	196.9	213.7	233.8	263.0	290.4	306.5
100°	284.5	267.4	259.0	256.7	259.0	267.4	284.5	308.8	329.5	343.3	337.6
102.5°	344.3	331.9	323.1	321.2	323.1	331.9	344.3	359.2	367.8	363.8	336.1
105°	401.8	399.5	395.6	394.0	395.6	399.5	401.8	401.2	389.8	362.0	313.5
107.5°	411.0	417.4	420.2	420.9	420.2	417.4	411.0	397.2	372.2	333.2	281.6
110°	402.0	413.8	418.8	421.4	418.8	413.8	402.0	382.1	351.4	310.8	262.4



TEST NUMBER: P332867-927

CATALOG NUMBER: SA4XXRDIP-C350D365U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	382.8	397.0	404.1	408.1	404.1	397.0	382.8	360.2	329.4	291.0	248.2
115°	350.2	367.0	376.0	378.3	376.0	367.0	350.2	328.1	301.3	268.5	234.1
117.5°	323.1	337.2	346.2	347.9	346.2	337.2	323.1	304.2	281.4	255.6	227.1
120°	308.2	320.6	327.9	331.0	327.9	320.6	308.2	292.3	272.4	250.0	223.9
122.5°	297.7	308.2	314.4	317.5	314.4	308.2	297.7	284.2	266.8	246.4	221.3
125°	286.7	294.9	300.2	301.8	300.2	294.9	286.7	275.5	260.1	240.7	216.7
127.5°	279.2	286.5	291.0	292.6	291.0	286.5	279.2	268.0	253.4	234.1	211.1
130°	274.1	281.1	285.6	287.2	285.6	281.1	274.1	262.6	247.8	228.8	206.6
132.5°	267.4	275.3	279.6	281.2	279.6	275.3	267.4	256.1	241.3	222.7	201.9
135°	255.9	263.7	268.2	269.9	268.2	263.7	255.9	244.7	230.7	213.7	195.4
137.5°	242.5	250.2	253.9	255.9	253.9	250.2	242.5	232.0	219.4	204.9	189.6
140°	233.5	239.6	243.6	245.8	243.6	239.6	233.5	223.7	211.9	199.3	186.2
142.5°	224.3	230.0	233.5	235.0	233.5	230.0	224.3	215.6	205.4	194.6	183.1
145°	211.4	216.1	219.0	220.3	219.0	216.1	211.4	204.4	196.5	188.1	178.6
147.5°	200.6	204.7	206.8	207.3	206.8	204.7	200.6	195.4	189.3	182.5	175.0
150°	194.3	198.0	199.6	199.9	199.6	198.0	194.3	189.8	184.8	179.2	172.8
152.5°	188.9	191.9	192.9	193.2	192.9	191.9	188.9	185.1	181.0	175.9	170.3
155°	181.4	183.6	184.5	184.5	184.5	183.6	181.4	178.6	175.2	171.0	166.6
157.5°	174.7	176.4	176.9	176.9	176.9	176.4	174.7	172.6	169.9	166.4	162.6
160°	170.2	171.9	172.2	172.2	172.2	171.9	170.2	168.6	166.3	163.2	160.2
162.5°	166.0	167.6	167.9	167.7	167.9	167.6	166.0	164.8	162.7	160.3	157.7
165°	160.4	161.5	161.3	161.0	161.3	161.5	160.4	159.3	157.9	156.0	154.2
167.5°	155.2	156.0	155.9	155.7	155.9	156.0	155.2	154.6	153.8	152.3	151.0
170°	152.3	152.6	152.3	152.3	152.3	152.6	152.3	151.8	150.9	149.8	148.9
172.5°	149.4	149.6	149.4	148.9	149.4	149.6	149.4	149.1	148.5	147.7	147.2
175°	145.6	146.2	145.6	145.0	145.6	146.2	145.6	145.6	145.6	145.0	144.7
177.5°	143.4	143.6	143.1	142.8	143.1	143.6	143.4	143.6	143.4	143.4	143.1
180°	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5



TEST NUMBER: P332867-927

CATALOG NUMBER: SA4XXRDIP-C350D365U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3
2.5°	445.0	446.2	448.5	451.2	453.5	455.4	456.9	459.1	461.0	463.7	466.2
5°	418.1	420.7	424.5	429.0	434.6	438.3	443.0	447.2	453.1	459.1	464.9
7.5°	394.4	397.3	402.8	409.0	415.7	421.8	427.4	434.7	442.6	451.4	461.1
10°	379.1	382.3	388.8	395.9	403.9	409.9	417.3	426.0	435.0	445.7	457.6
12.5°	365.3	368.4	376.2	383.5	391.7	398.3	407.0	415.7	427.8	439.3	453.0
15°	338.4	346.5	355.5	364.1	373.8	381.9	392.4	401.4	412.8	429.1	444.7
17.5°	308.6	317.1	328.4	341.7	354.7	364.7	375.3	386.5	400.1	416.8	434.7
20°	291.1	298.1	310.5	325.3	340.5	354.3	364.1	376.4	390.5	408.5	427.1
22.5°	278.1	284.0	293.7	308.5	324.9	341.0	353.5	365.7	381.2	399.3	419.5
25°	258.6	264.9	273.4	283.4	302.2	319.2	335.6	349.7	366.1	384.1	406.6
27.5°	242.2	247.8	255.6	266.1	278.7	297.5	317.3	333.3	350.2	369.6	392.1
30°	232.7	237.2	243.5	254.2	266.3	283.1	303.2	321.9	339.0	359.0	382.5
32.5°	222.6	227.4	233.6	242.1	255.0	269.2	289.2	309.7	327.9	348.4	371.4
35°	209.2	213.0	218.6	227.2	238.8	251.2	269.0	290.3	309.3	331.3	353.2
37.5°	195.7	200.1	204.5	212.2	221.7	235.0	249.6	271.3	292.5	312.5	333.9
40°	188.1	190.7	195.5	201.8	211.8	223.6	237.3	258.6	279.7	299.6	321.2
42.5°	179.5	182.4	186.6	192.7	201.8	213.3	226.7	245.0	267.1	286.4	306.0
45°	167.6	169.3	173.4	178.6	186.2	197.8	210.2	226.5	247.3	265.7	282.9
47.5°	155.6	157.1	159.6	164.5	172.9	182.2	193.8	208.4	226.6	245.0	259.6
50°	147.3	148.7	151.1	155.6	163.1	172.3	183.7	196.9	213.2	230.8	243.0
52.5°	139.1	139.8	142.1	147.2	153.5	162.6	172.8	184.9	200.1	214.8	227.1
55°	126.0	127.7	129.2	132.9	138.9	147.6	156.8	168.2	180.0	192.3	202.9
57.5°	112.3	114.2	116.3	119.6	124.4	132.4	140.6	149.9	160.0	170.2	179.1
60°	103.3	105.0	106.9	110.6	114.9	121.3	130.3	138.4	146.1	155.4	164.2
62.5°	94.4	96.2	98.3	101.3	105.4	111.5	119.1	126.0	134.0	142.2	148.8
65°	81.4	82.7	84.4	87.2	91.1	96.6	102.7	108.2	115.3	121.3	127.3
67.5°	67.0	69.6	71.7	74.0	77.3	82.4	86.9	92.1	97.0	101.4	106.9
70°	57.6	60.4	62.4	64.9	68.0	72.4	76.7	80.2	84.2	88.5	93.4
72.5°	49.6	51.8	53.5	56.0	58.9	62.9	66.9	69.9	73.1	76.0	80.8
75°	39.2	40.1	41.3	43.3	45.9	49.0	52.1	54.7	56.6	59.3	62.6
77.5°	28.1	29.9	30.7	32.2	34.1	35.9	38.0	40.2	42.1	42.9	45.6
80°	21.5	22.3	23.1	25.1	26.2	28.1	29.6	31.7	32.4	33.4	35.8
82.5°	16.8	17.2	17.7	18.2	18.9	20.8	22.3	23.6	24.3	24.6	26.5
85°	9.7	9.9	10.1	10.3	10.5	10.5	11.2	12.2	13.5	13.5	14.1
87.5°	4.3	4.4	4.4	4.1	4.4	4.0	4.2	4.1	4.5	4.8	5.1
90°	4.8	5.1	4.5	3.9	3.9	2.2	2.2	2.0	1.7	0.9	0.3
92.5°	74.0	88.8	77.7	56.6	34.9	20.6	14.8	10.7	7.3	4.7	3.2
95°	234.6	228.1	172.2	105.3	59.3	35.0	23.2	16.6	12.9	10.1	9.3
97.5°	294.8	240.3	161.1	94.7	56.7	37.9	28.1	22.3	19.0	16.6	16.6
100°	296.8	225.1	146.2	89.0	57.4	40.9	31.9	26.6	23.2	21.3	21.3
102.5°	280.0	206.0	136.1	87.5	59.7	44.7	36.2	31.1	28.0	26.2	25.7
105°	249.5	183.6	127.4	88.2	65.0	51.5	43.4	38.3	35.0	33.6	32.8
107.5°	224.8	171.1	125.8	92.4	71.1	58.9	50.9	46.0	42.5	41.0	40.5
110°	212.5	166.8	126.3	95.5	75.9	63.5	56.0	50.9	47.6	46.2	45.6



TEST NUMBER: P332867-927

CATALOG NUMBER: SA4XXRDIP-C350D365U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	205.6	164.9	127.6	98.9	80.3	68.4	60.9	55.8	52.8	51.1	50.5
115°	199.1	163.8	130.2	104.2	87.4	76.1	68.6	63.3	60.4	58.5	57.7
117.5°	196.1	163.5	132.9	109.6	94.1	83.5	75.7	70.7	67.6	65.8	65.0
120°	194.6	163.5	135.0	113.4	98.9	88.2	80.3	75.6	72.5	70.6	70.0
122.5°	192.8	163.3	137.0	117.0	103.3	92.7	85.1	79.9	77.0	75.0	74.5
125°	189.8	163.0	140.0	122.3	109.5	99.4	91.6	86.3	83.2	81.4	80.3
127.5°	185.8	162.3	142.4	127.0	115.2	105.4	97.5	92.0	88.5	86.4	85.6
130°	183.4	162.1	144.2	129.9	119.0	109.5	101.3	96.0	91.8	89.6	88.5
132.5°	181.2	161.9	145.8	132.8	122.2	112.6	105.0	99.2	95.2	92.3	91.4
135°	177.8	161.5	148.1	136.7	126.5	117.3	110.0	104.2	99.4	96.6	95.5
137.5°	174.9	161.5	149.5	139.3	129.9	121.3	114.3	108.2	103.7	100.6	99.6
140°	173.3	161.3	150.6	141.1	132.1	123.7	117.0	111.1	106.4	103.3	102.5
142.5°	172.0	161.3	151.5	142.4	134.2	126.0	119.5	113.8	109.3	106.5	105.6
145°	169.7	160.7	152.0	143.9	136.3	129.0	122.9	117.6	113.7	110.9	110.0
147.5°	167.6	159.7	152.3	145.2	138.6	131.7	126.2	121.8	117.8	115.3	115.0
150°	166.0	159.0	152.3	145.8	139.7	133.6	128.3	124.1	120.6	118.4	118.1
152.5°	164.2	157.9	151.9	146.3	140.6	135.1	130.2	126.5	123.3	121.1	121.0
155°	161.5	156.2	151.2	146.7	142.0	137.2	133.0	129.9	127.1	125.4	125.2
157.5°	158.8	154.5	150.4	146.7	142.9	138.9	135.5	132.8	130.7	129.1	129.1
160°	156.8	153.1	149.8	146.7	143.4	140.0	136.9	134.7	132.7	131.6	131.6
162.5°	155.0	151.8	149.1	146.7	143.8	140.7	138.2	136.3	134.5	133.6	133.8
165°	152.0	149.8	147.8	146.2	143.9	141.4	139.7	138.3	136.9	136.3	136.3
167.5°	149.3	147.7	146.5	145.4	143.9	142.0	140.7	139.9	138.9	138.6	138.9
170°	147.6	146.4	145.6	145.0	143.6	142.2	141.4	140.9	140.0	139.7	140.0
172.5°	146.0	145.0	144.7	144.6	143.4	142.4	141.8	141.5	140.9	140.9	141.1
175°	144.2	143.6	143.6	143.9	143.1	142.5	142.5	142.2	142.0	142.0	142.2
177.5°	143.0	142.8	142.8	143.1	142.8	142.5	142.5	142.5	142.3	142.5	142.8
180°	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5



TEST NUMBER: P332867-927

CATALOG NUMBER: SA4XXRDIP-C350D365U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3
2.5°	468.2	469.5	471.0	473.9	476.3	477.4	479.4	480.9	480.5	482.6	486.2
5°	470.0	475.1	480.9	486.9	493.6	499.2	503.7	508.3	511.8	516.1	522.5
7.5°	469.7	478.7	488.5	499.2	510.3	519.9	528.7	537.7	545.7	554.4	565.9
10°	468.5	480.5	492.7	506.8	520.9	534.2	546.1	557.4	568.1	579.5	594.0
12.5°	467.1	480.9	495.7	512.6	530.1	546.1	560.2	576.5	589.9	604.6	621.2
15°	461.2	479.7	499.9	521.7	542.8	564.4	583.6	603.5	622.1	639.7	660.7
17.5°	454.4	475.8	499.5	525.4	550.6	576.8	599.8	624.8	643.7	667.4	686.9
20°	448.9	471.9	497.2	526.2	554.9	584.0	609.3	634.9	656.2	680.0	704.7
22.5°	442.1	467.4	494.8	524.9	554.9	586.7	614.7	640.1	666.5	693.3	718.8
25°	431.2	457.5	486.6	519.5	554.1	586.5	616.5	647.9	676.4	705.5	728.4
27.5°	417.9	445.4	476.0	510.1	545.5	578.7	614.0	647.6	676.3	704.3	724.2
30°	407.2	436.3	465.7	500.2	536.9	572.6	610.5	644.0	674.2	699.3	710.6
32.5°	396.2	423.8	454.2	489.1	526.7	565.1	602.6	637.0	664.9	679.9	680.2
35°	377.2	403.1	434.6	468.9	507.6	549.1	587.2	620.9	638.0	639.3	620.9
37.5°	356.5	380.2	409.9	444.3	486.6	528.0	566.8	589.3	595.0	575.9	542.0
40°	341.6	363.5	392.2	427.5	469.4	512.2	547.6	564.1	558.2	527.2	489.3
42.5°	326.0	346.4	374.1	408.8	451.0	494.2	524.4	533.2	517.4	481.6	437.3
45°	300.6	319.2	346.7	381.8	422.2	462.7	485.6	481.1	454.6	412.3	362.6
47.5°	274.0	292.2	316.8	349.2	390.7	425.6	441.1	427.5	389.9	343.3	302.9
50°	256.5	275.0	297.7	328.7	366.5	400.3	410.2	389.6	347.8	303.0	265.9
52.5°	239.2	255.1	277.3	307.2	343.4	371.9	377.2	353.5	310.3	270.1	237.2
55°	213.0	227.4	246.1	274.3	305.6	329.8	326.9	296.4	257.2	222.9	197.0
57.5°	187.6	198.4	215.8	242.2	269.7	285.9	275.6	249.5	213.0	184.9	163.1
60°	170.8	180.9	197.0	220.1	244.3	253.5	244.9	216.6	187.7	162.0	143.6
62.5°	154.9	163.8	177.7	199.1	218.6	224.1	214.8	190.1	164.1	142.2	127.0
65°	131.8	140.1	151.9	167.1	180.5	183.2	177.2	151.9	132.2	113.8	103.3
67.5°	110.8	116.2	125.5	138.6	145.8	147.3	135.7	119.8	102.4	91.2	83.3
70°	96.7	100.5	109.1	116.2	122.1	122.2	111.5	98.8	85.5	76.3	70.5
72.5°	83.1	86.7	93.2	98.1	102.6	101.1	91.3	81.3	70.5	63.5	59.3
75°	64.1	67.3	70.7	73.0	73.0	71.1	63.9	56.4	50.2	46.1	44.8
77.5°	46.6	49.2	50.4	50.0	49.4	46.4	41.9	37.0	34.8	32.9	31.8
80°	36.6	37.7	38.0	37.2	36.0	32.6	29.6	27.6	25.5	24.7	24.4
82.5°	27.1	28.1	27.1	27.4	24.9	22.1	20.4	19.7	18.9	18.6	18.2
85°	14.4	14.3	13.9	12.9	11.2	10.9	10.7	10.5	10.1	10.3	9.9
87.5°	5.1	4.8	4.3	4.2	4.2	4.2	4.4	4.5	4.6	4.4	4.8
90°	0.9	1.7	2.0	2.2	2.2	3.9	3.9	4.5	5.1	4.8	5.1
92.5°	4.7	7.3	10.7	14.8	20.6	34.9	56.6	77.7	88.8	74.0	55.0
95°	10.1	12.9	16.6	23.2	35.0	59.3	105.3	172.2	228.1	234.6	207.5
97.5°	16.6	19.0	22.3	28.1	37.9	56.7	94.7	161.1	240.3	294.8	306.5
100°	21.3	23.2	26.6	31.9	40.9	57.4	89.0	146.2	225.1	296.8	337.6
102.5°	26.2	28.0	31.1	36.2	44.7	59.7	87.5	136.1	206.0	280.0	336.1
105°	33.6	35.0	38.3	43.4	51.5	65.0	88.2	127.4	183.6	249.5	313.5
107.5°	41.0	42.5	46.0	50.9	58.9	71.1	92.4	125.8	171.1	224.8	281.6
110°	46.2	47.6	50.9	56.0	63.5	75.9	95.5	126.3	166.8	212.5	262.4



TEST NUMBER: P332867-927

CATALOG NUMBER: SA4XXRDIP-C350D365U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	51.1	52.8	55.8	60.9	68.4	80.3	98.9	127.6	164.9	205.6	248.2
115°	58.5	60.4	63.3	68.6	76.1	87.4	104.2	130.2	163.8	199.1	234.1
117.5°	65.8	67.6	70.7	75.7	83.5	94.1	109.6	132.9	163.5	196.1	227.1
120°	70.6	72.5	75.6	80.3	88.2	98.9	113.4	135.0	163.5	194.6	223.9
122.5°	75.0	77.0	79.9	85.1	92.7	103.3	117.0	137.0	163.3	192.8	221.3
125°	81.4	83.2	86.3	91.6	99.4	109.5	122.3	140.0	163.0	189.8	216.7
127.5°	86.4	88.5	92.0	97.5	105.4	115.2	127.0	142.4	162.3	185.8	211.1
130°	89.6	91.8	96.0	101.3	109.5	119.0	129.9	144.2	162.1	183.4	206.6
132.5°	92.3	95.2	99.2	105.0	112.6	122.2	132.8	145.8	161.9	181.2	201.9
135°	96.6	99.4	104.2	110.0	117.3	126.5	136.7	148.1	161.5	177.8	195.4
137.5°	100.6	103.7	108.2	114.3	121.3	129.9	139.3	149.5	161.5	174.9	189.6
140°	103.3	106.4	111.1	117.0	123.7	132.1	141.1	150.6	161.3	173.3	186.2
142.5°	106.5	109.3	113.8	119.5	126.0	134.2	142.4	151.5	161.3	172.0	183.1
145°	110.9	113.7	117.6	122.9	129.0	136.3	143.9	152.0	160.7	169.7	178.6
147.5°	115.3	117.8	121.8	126.2	131.7	138.6	145.2	152.3	159.7	167.6	175.0
150°	118.4	120.6	124.1	128.3	133.6	139.7	145.8	152.3	159.0	166.0	172.8
152.5°	121.1	123.3	126.5	130.2	135.1	140.6	146.3	151.9	157.9	164.2	170.3
155°	125.4	127.1	129.9	133.0	137.2	142.0	146.7	151.2	156.2	161.5	166.6
157.5°	129.1	130.7	132.8	135.5	138.9	142.9	146.7	150.4	154.5	158.8	162.6
160°	131.6	132.7	134.7	136.9	140.0	143.4	146.7	149.8	153.1	156.8	160.2
162.5°	133.6	134.5	136.3	138.2	140.7	143.8	146.7	149.1	151.8	155.0	157.7
165°	136.3	136.9	138.3	139.7	141.4	143.9	146.2	147.8	149.8	152.0	154.2
167.5°	138.6	138.9	139.9	140.7	142.0	143.9	145.4	146.5	147.7	149.3	151.0
170°	139.7	140.0	140.9	141.4	142.2	143.6	145.0	145.6	146.4	147.6	148.9
172.5°	140.9	140.9	141.5	141.8	142.4	143.4	144.6	144.7	145.0	146.0	147.2
175°	142.0	142.0	142.2	142.5	142.5	143.1	143.9	143.6	143.6	144.2	144.7
177.5°	142.5	142.3	142.5	142.5	142.5	142.8	143.1	142.8	142.8	143.0	143.1
180°	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5



TEST NUMBER: P332867-927

CATALOG NUMBER: SA4XXRDIP-C350D365U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	465.3	465.3	465.3	465.3	465.3	465.3	465.3
2.5°	488.1	488.7	489.2	490.7	490.8	492.2	490.8
5°	528.5	531.2	535.3	539.4	539.8	542.4	537.7
7.5°	573.8	579.9	583.7	590.3	592.9	594.6	591.9
10°	605.0	610.6	620.6	625.4	630.3	631.1	628.8
12.5°	635.2	644.0	651.9	661.2	660.9	667.5	665.1
15°	675.3	684.5	695.4	705.7	709.4	709.4	712.4
17.5°	703.9	720.8	732.1	740.1	749.0	750.5	749.5
20°	723.3	741.5	753.5	764.0	770.0	771.7	771.7
22.5°	737.7	753.2	764.9	774.4	779.3	781.3	780.7
25°	747.7	761.0	768.1	771.0	772.2	771.9	768.3
27.5°	734.0	733.4	729.0	720.3	713.8	709.9	705.4
30°	708.0	698.2	686.9	674.5	658.6	646.4	642.7
32.5°	669.1	647.2	628.1	607.5	590.4	578.2	573.1
35°	594.0	559.3	530.9	506.2	488.2	477.0	473.2
37.5°	504.8	471.2	436.2	412.2	397.2	385.9	381.7
40°	448.1	411.5	381.0	358.5	343.1	332.0	331.8
42.5°	396.3	361.4	332.6	316.5	299.9	292.6	292.6
45°	324.6	296.6	272.2	259.4	249.5	243.5	241.9
47.5°	268.7	245.6	229.3	219.2	211.1	207.3	204.8
50°	237.3	217.1	204.1	195.4	190.8	186.0	185.6
52.5°	211.3	194.9	184.8	177.7	172.0	169.1	169.1
55°	177.5	164.6	157.5	152.0	147.6	145.3	144.3
57.5°	149.6	139.9	134.7	129.7	127.8	126.0	125.6
60°	132.2	125.6	120.7	116.8	114.0	113.4	113.2
62.5°	117.8	110.9	107.6	104.5	102.4	101.6	101.2
65°	97.1	92.1	89.0	86.6	85.9	84.5	84.4
67.5°	78.3	75.3	73.3	71.6	70.6	70.5	70.5
70°	66.8	65.0	63.4	62.4	61.9	61.5	61.5
72.5°	56.9	55.6	54.2	53.7	53.6	53.2	53.1
75°	43.3	42.0	42.2	41.3	40.5	39.5	39.0
77.5°	30.7	29.8	29.5	29.5	28.8	28.8	29.0
80°	23.8	22.9	22.7	22.9	22.7	22.1	22.1
82.5°	18.1	17.3	17.1	17.0	16.9	17.0	16.7
85°	9.7	9.3	9.3	9.3	9.7	9.6	9.3
87.5°	4.5	4.4	4.6	4.4	4.5	4.4	4.4
90°	5.3	5.6	5.6	5.9	6.2	5.9	5.9
92.5°	41.4	33.0	27.3	24.0	22.5	21.5	21.5
95°	164.1	126.5	99.4	85.6	77.0	71.9	68.3
97.5°	290.4	263.0	233.8	213.7	196.9	188.5	182.6
100°	343.3	329.5	308.8	284.5	267.4	259.0	256.7
102.5°	363.8	367.8	359.2	344.3	331.9	323.1	321.2
105°	362.0	389.8	401.2	401.8	399.5	395.6	394.0
107.5°	333.2	372.2	397.2	411.0	417.4	420.2	420.9
110°	310.8	351.4	382.1	402.0	413.8	418.8	421.4



TEST NUMBER: P332867-927

CATALOG NUMBER: SA4XXRDIP-C350D365U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	291.0	329.4	360.2	382.8	397.0	404.1	408.1
115°	268.5	301.3	328.1	350.2	367.0	376.0	378.3
117.5°	255.6	281.4	304.2	323.1	337.2	346.2	347.9
120°	250.0	272.4	292.3	308.2	320.6	327.9	331.0
122.5°	246.4	266.8	284.2	297.7	308.2	314.4	317.5
125°	240.7	260.1	275.5	286.7	294.9	300.2	301.8
127.5°	234.1	253.4	268.0	279.2	286.5	291.0	292.6
130°	228.8	247.8	262.6	274.1	281.1	285.6	287.2
132.5°	222.7	241.3	256.1	267.4	275.3	279.6	281.2
135°	213.7	230.7	244.7	255.9	263.7	268.2	269.9
137.5°	204.9	219.4	232.0	242.5	250.2	253.9	255.9
140°	199.3	211.9	223.7	233.5	239.6	243.6	245.8
142.5°	194.6	205.4	215.6	224.3	230.0	233.5	235.0
145°	188.1	196.5	204.4	211.4	216.1	219.0	220.3
147.5°	182.5	189.3	195.4	200.6	204.7	206.8	207.3
150°	179.2	184.8	189.8	194.3	198.0	199.6	199.9
152.5°	175.9	181.0	185.1	188.9	191.9	192.9	193.2
155°	171.0	175.2	178.6	181.4	183.6	184.5	184.5
157.5°	166.4	169.9	172.6	174.7	176.4	176.9	176.9
160°	163.2	166.3	168.6	170.2	171.9	172.2	172.2
162.5°	160.3	162.7	164.8	166.0	167.6	167.9	167.7
165°	156.0	157.9	159.3	160.4	161.5	161.3	161.0
167.5°	152.3	153.8	154.6	155.2	156.0	155.9	155.7
170°	149.8	150.9	151.8	152.3	152.6	152.3	152.3
172.5°	147.7	148.5	149.1	149.4	149.6	149.4	148.9
175°	145.0	145.6	145.6	145.6	146.2	145.6	145.0
177.5°	143.4	143.4	143.6	143.4	143.6	143.1	142.8
180°	142.5	142.5	142.5	142.5	142.5	142.5	142.5

(END OF REPORT)