

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332873-927

Luminaire Tested: **SA4XXRDIP-C350D590U927-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332873-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C350D590U927-4F0-1E-UDD-A4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2850.4 lumens
Efficiency: N/A
Efficacy: 111.3 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 25.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332873-927
CATALOG NUMBER: SA4XXRDIP-C350D590U927-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332873-927

CATALOG NUMBER: SA4XXRDIP-C350D590U927-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	48	48	48	41				41
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	43	42	41				36	
2	88	81	75	70	80	74	69	65	61	58	55	49	47	45	38	37	35				30	
3	80	71	64	59	73	65	59	54	54	50	46	44	41	38	34	32	31				26	
4	74	63	56	50	67	58	52	46	48	43	40	39	36	33	31	29	27				23	
5	68	56	49	43	62	52	45	40	43	38	34	35	32	29	28	25	23				20	
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	25	23	21				18	
7	58	46	38	33	53	42	35	31	36	30	27	29	25	22	23	21	18				16	
8	54	42	34	29	49	38	32	27	32	27	24	27	23	20	21	19	17				14	
9	50	38	31	26	45	35	29	24	30	25	21	25	21	18	20	17	15				13	
10	47	35	28	23	43	32	26	22	27	22	19	23	19	16	18	16	14				12	

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	3756	3756	3756	3756
5°	4357	3767	3331	3767
10°	5155	3751	2972	3751
15°	5954	3717	2554	3717
20°	6630	3669	2310	3669
25°	6844	3622	2144	3622
30°	5991	3566	2045	3566
35°	4664	3481	1985	3481
40°	3497	3385	1952	3385
45°	2762	3230	1934	3230
50°	2331	3052	1879	3052
55°	2031	2856	1779	2856
60°	1828	2651	1574	2651
65°	1612	2432	1354	2432
70°	1452	2205	1220	2205
75°	1216	1953	1042	1953
80°	1027	1664	976	1664
85°	861	1306	861	1306



TEST NUMBER: P332873-927

CATALOG NUMBER: SA4XXRDIP-C350D590U927-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.1	1.6
10°-20°	136.0	4.8
20°-30°	212.7	7.5
30°-40°	236.5	8.3
40°-50°	209.8	7.4
50°-60°	163.5	5.7
60°-70°	107.0	3.8
70°-80°	52.6	1.8
80°-90°	14.3	0.5
90°-100°	166.1	5.8
100°-110°	345.8	12.1
110°-120°	309.7	10.9
120°-130°	260.5	9.1
130°-140°	217.2	7.6
140°-150°	166.0	5.8
150°-160°	116.6	4.1
160°-170°	68.6	2.4
170°-180°	22.3	0.8
0°-30°	393.8	13.8
0°-40°	630.3	22.1
0°-60°	1003.6	35.2
0°-90°	1177.5	41.3
90°-120°	821.6	28.8
90°-150°	1465.3	51.4
90°-180°	1673.0	58.7
0°-180°	2850.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	465	465	465	465	465	
5°	538	465	411	465	538	54
15°	712	445	306	445	712	203
25°	768	407	241	407	768	341
35°	473	353	201	353	473	297
45°	242	283	169	283	242	192
55°	144	203	126	203	144	131
65°	84	127	71	127	84	85
75°	39	63	33	63	39	43
85°	9	14	9	14	9	11
90°	10	0	10	0	10	8
95°	110	15	110	15	110	171
105°	636	53	636	53	636	629
115°	610	93	610	93	610	606
125°	487	130	487	130	487	443
135°	436	154	436	154	436	336
145°	356	178	356	178	356	225
155°	298	202	298	202	298	139
165°	260	220	260	220	260	74
175°	234	230	234	230	234	23
180°	230	230	230	230	230	



TEST NUMBER: P332873-927

CATALOG NUMBER: SA4XXRDIP-C350D590U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3
2.5°	490.8	492.2	490.8	490.7	489.2	488.7	488.1	486.2	482.6	480.5	480.9
5°	537.7	542.4	539.8	539.4	535.3	531.2	528.5	522.5	516.1	511.8	508.3
7.5°	591.9	594.6	592.9	590.3	583.7	579.9	573.8	565.9	554.4	545.7	537.7
10°	628.8	631.1	630.3	625.4	620.6	610.6	605.0	594.0	579.5	568.1	557.4
12.5°	665.1	667.5	660.9	661.2	651.9	644.0	635.2	621.2	604.6	589.9	576.5
15°	712.4	709.4	709.4	705.7	695.4	684.5	675.3	660.7	639.7	622.1	603.5
17.5°	749.5	750.5	749.0	740.1	732.1	720.8	703.9	686.9	667.4	643.7	624.8
20°	771.7	771.7	770.0	764.0	753.5	741.5	723.3	704.7	680.0	656.2	634.9
22.5°	780.7	781.3	779.3	774.4	764.9	753.2	737.7	718.8	693.3	666.5	640.1
25°	768.3	771.9	772.2	771.0	768.1	761.0	747.7	728.4	705.5	676.4	647.9
27.5°	705.4	709.9	713.8	720.3	729.0	733.4	734.0	724.2	704.3	676.3	647.6
30°	642.7	646.4	658.6	674.5	686.9	698.2	708.0	710.6	699.3	674.2	644.0
32.5°	573.1	578.2	590.4	607.5	628.1	647.2	669.1	680.2	679.9	664.9	637.0
35°	473.2	477.0	488.2	506.2	530.9	559.3	594.0	620.9	639.3	638.0	620.9
37.5°	381.7	385.9	397.2	412.2	436.2	471.2	504.8	542.0	575.9	595.0	589.3
40°	331.8	332.0	343.1	358.5	381.0	411.5	448.1	489.3	527.2	558.2	564.1
42.5°	292.6	292.6	299.9	316.5	332.6	361.4	396.3	437.3	481.6	517.4	533.2
45°	241.9	243.5	249.5	259.4	272.2	296.6	324.6	362.6	412.3	454.6	481.1
47.5°	204.8	207.3	211.1	219.2	229.3	245.6	268.7	302.9	343.3	389.9	427.5
50°	185.6	186.0	190.8	195.4	204.1	217.1	237.3	265.9	303.0	347.8	389.6
52.5°	169.1	169.1	172.0	177.7	184.8	194.9	211.3	237.2	270.1	310.3	353.5
55°	144.3	145.3	147.6	152.0	157.5	164.6	177.5	197.0	222.9	257.2	296.4
57.5°	125.6	126.0	127.8	129.7	134.7	139.9	149.6	163.1	184.9	213.0	249.5
60°	113.2	113.4	114.0	116.8	120.7	125.6	132.2	143.6	162.0	187.7	216.6
62.5°	101.2	101.6	102.4	104.5	107.6	110.9	117.8	127.0	142.2	164.1	190.1
65°	84.4	84.5	85.9	86.6	89.0	92.1	97.1	103.3	113.8	132.2	151.9
67.5°	70.5	70.5	70.6	71.6	73.3	75.3	78.3	83.3	91.2	102.4	119.8
70°	61.5	61.5	61.9	62.4	63.4	65.0	66.8	70.5	76.3	85.5	98.8
72.5°	53.1	53.2	53.6	53.7	54.2	55.6	56.9	59.3	63.5	70.5	81.3
75°	39.0	39.5	40.5	41.3	42.2	42.0	43.3	44.8	46.1	50.2	56.4
77.5°	29.0	28.8	28.8	29.5	29.5	29.8	30.7	31.8	32.9	34.8	37.0
80°	22.1	22.1	22.7	22.9	22.7	22.9	23.8	24.4	24.7	25.5	27.6
82.5°	16.7	17.0	16.9	17.0	17.1	17.3	18.1	18.2	18.6	18.9	19.7
85°	9.3	9.6	9.7	9.3	9.3	9.3	9.7	9.9	10.3	10.1	10.5
87.5°	5.2	5.1	5.3	5.2	5.2	5.1	5.1	5.4	5.0	5.2	5.1
90°	9.5	9.5	9.9	9.5	9.0	9.0	8.6	8.2	7.7	8.2	7.2
92.5°	34.8	34.8	36.4	38.7	44.1	53.2	66.8	88.7	119.4	143.3	125.5
95°	110.3	116.1	124.3	138.3	160.4	204.2	264.8	334.9	378.7	368.3	277.9
97.5°	294.7	304.1	317.7	344.9	377.3	424.5	468.7	494.7	475.8	387.9	260.2
100°	414.4	418.0	431.6	459.1	498.4	531.9	554.1	545.0	479.0	363.3	235.9
102.5°	518.5	521.4	535.7	555.6	579.8	593.7	587.3	542.5	451.9	332.6	219.6
105°	635.8	638.5	644.8	648.5	647.6	629.1	584.3	506.1	402.7	296.4	205.7
107.5°	679.4	678.2	673.7	663.4	641.0	600.8	537.7	454.6	362.9	276.2	203.1
110°	680.1	676.0	667.9	649.0	616.9	567.1	501.6	423.4	343.0	269.3	203.8



TEST NUMBER: P332873-927

CATALOG NUMBER: SA4XXRDIP-C350D590U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	658.8	652.2	640.8	617.8	581.4	531.7	469.8	400.7	331.8	266.1	206.0
115°	610.5	606.9	592.5	565.3	529.7	486.2	433.4	377.8	321.3	264.4	210.2
117.5°	561.7	558.8	544.2	521.4	490.9	454.2	412.6	366.5	316.6	263.9	214.5
120°	534.2	529.2	517.5	497.6	471.7	439.7	403.5	361.6	314.1	263.9	217.9
122.5°	512.5	507.5	497.6	480.5	458.8	430.6	397.8	357.2	311.2	263.6	221.1
125°	487.1	484.4	475.9	462.7	444.7	419.8	388.6	349.7	306.4	263.0	225.9
127.5°	472.3	469.6	462.4	450.8	432.5	409.0	377.9	340.7	300.0	262.0	229.8
130°	463.7	461.0	453.7	442.4	423.9	399.9	369.2	333.5	296.0	261.7	232.7
132.5°	453.9	451.1	444.3	431.6	413.4	389.4	359.4	325.9	292.4	261.3	235.3
135°	435.6	432.9	425.7	413.0	395.0	372.3	344.8	315.4	286.9	260.7	239.1
137.5°	413.0	409.8	403.9	391.3	374.5	354.0	330.8	305.9	282.3	260.6	241.3
140°	396.8	393.2	386.8	376.9	361.1	342.1	321.8	300.5	279.7	260.3	243.1
142.5°	379.4	376.9	371.3	362.0	348.1	331.6	314.2	295.5	277.6	260.3	244.5
145°	355.6	353.4	348.9	341.2	329.9	317.3	303.6	288.3	273.9	259.4	245.4
147.5°	334.6	333.7	330.3	323.8	315.4	305.5	294.6	282.4	270.5	257.8	245.8
150°	322.7	322.2	319.5	313.6	306.4	298.3	289.2	278.8	268.0	256.7	245.8
152.5°	311.8	311.3	309.7	304.9	298.8	292.1	283.8	274.8	265.1	254.8	245.1
155°	297.8	297.8	296.4	292.9	288.3	282.9	276.1	268.9	260.7	252.2	244.0
157.5°	285.5	285.5	284.7	282.0	278.5	274.2	268.5	262.4	256.4	249.4	242.9
160°	277.9	277.9	277.5	274.7	272.0	268.4	263.5	258.5	253.1	247.2	241.8
162.5°	270.7	271.1	270.6	267.9	265.9	262.6	258.7	254.5	250.2	245.0	240.7
165°	259.8	260.3	260.7	259.0	257.1	254.8	251.7	249.0	245.4	241.8	238.6
167.5°	251.3	251.6	251.7	250.6	249.6	248.3	245.7	243.7	241.1	238.5	236.5
170°	245.8	245.8	246.3	245.8	244.9	243.6	241.8	240.4	238.1	236.3	235.0
172.5°	240.4	241.1	241.6	241.1	240.6	239.6	238.5	237.5	235.6	234.2	233.5
175°	234.1	235.0	235.9	235.0	235.0	235.0	234.1	233.6	232.7	231.8	231.8
177.5°	230.4	231.1	231.8	231.5	231.8	231.5	231.5	231.1	230.8	230.4	230.4
180°	230.0	230.0	230.0	230.0	230.0	230.0	230.0	230.0	230.0	230.0	230.0



TEST NUMBER: P332873-927

CATALOG NUMBER: SA4XXRDIP-C350D590U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3
2.5°	479.4	477.4	476.3	473.9	471.0	469.5	468.2	466.2	463.7	461.0	459.1
5°	503.7	499.2	493.6	486.9	480.9	475.1	470.0	464.9	459.1	453.1	447.2
7.5°	528.7	519.9	510.3	499.2	488.5	478.7	469.7	461.1	451.4	442.6	434.7
10°	546.1	534.2	520.9	506.8	492.7	480.5	468.5	457.6	445.7	435.0	426.0
12.5°	560.2	546.1	530.1	512.6	495.7	480.9	467.1	453.0	439.3	427.8	415.7
15°	583.6	564.4	542.8	521.7	499.9	479.7	461.2	444.7	429.1	412.8	401.4
17.5°	599.8	576.8	550.6	525.4	499.5	475.8	454.4	434.7	416.8	400.1	386.5
20°	609.3	584.0	554.9	526.2	497.2	471.9	448.9	427.1	408.5	390.5	376.4
22.5°	614.7	586.7	554.9	524.9	494.8	467.4	442.1	419.5	399.3	381.2	365.7
25°	616.5	586.5	554.1	519.5	486.6	457.5	431.2	406.6	384.1	366.1	349.7
27.5°	614.0	578.7	545.5	510.1	476.0	445.4	417.9	392.1	369.6	350.2	333.3
30°	610.5	572.6	536.9	500.2	465.7	436.3	407.2	382.5	359.0	339.0	321.9
32.5°	602.6	565.1	526.7	489.1	454.2	423.8	396.2	371.4	348.4	327.9	309.7
35°	587.2	549.1	507.6	468.9	434.6	403.1	377.2	353.2	331.3	309.3	290.3
37.5°	566.8	528.0	486.6	444.3	409.9	380.2	356.5	333.9	312.5	292.5	271.3
40°	547.6	512.2	469.4	427.5	392.2	363.5	341.6	321.2	299.6	279.7	258.6
42.5°	524.4	494.2	451.0	408.8	374.1	346.4	326.0	306.0	286.4	267.1	245.0
45°	485.6	462.7	422.2	381.8	346.7	319.2	300.6	282.9	265.7	247.3	226.5
47.5°	441.1	425.6	390.7	349.2	316.8	292.2	274.0	259.6	245.0	226.6	208.4
50°	410.2	400.3	366.5	328.7	297.7	275.0	256.5	243.0	230.8	213.2	196.9
52.5°	377.2	371.9	343.4	307.2	277.3	255.1	239.2	227.1	214.8	200.1	184.9
55°	326.9	329.8	305.6	274.3	246.1	227.4	213.0	202.9	192.3	180.0	168.2
57.5°	275.6	285.9	269.7	242.2	215.8	198.4	187.6	179.1	170.2	160.0	149.9
60°	244.9	253.5	244.3	220.1	197.0	180.9	170.8	164.2	155.4	146.1	138.4
62.5°	214.8	224.1	218.6	199.1	177.7	163.8	154.9	148.8	142.2	134.0	126.0
65°	177.2	183.2	180.5	167.1	151.9	140.1	131.8	127.3	121.3	115.3	108.2
67.5°	135.7	147.3	145.8	138.6	125.5	116.2	110.8	106.9	101.4	97.0	92.1
70°	111.5	122.2	122.1	116.2	109.1	100.5	96.7	93.4	88.5	84.2	80.2
72.5°	91.3	101.1	102.6	98.1	93.2	86.7	83.1	80.8	76.0	73.1	69.9
75°	63.9	71.1	73.0	73.0	70.7	67.3	64.1	62.6	59.3	56.6	54.7
77.5°	41.9	46.4	49.4	50.0	50.4	49.2	46.6	45.6	42.9	42.1	40.2
80°	29.6	32.6	36.0	37.2	38.0	37.7	36.6	35.8	33.4	32.4	31.7
82.5°	20.4	22.1	24.9	27.4	27.1	28.1	27.1	26.5	24.6	24.3	23.6
85°	10.7	10.9	11.2	12.9	13.9	14.3	14.4	14.1	13.5	13.5	12.2
87.5°	4.8	4.8	4.4	4.4	4.5	5.1	5.2	5.2	4.9	4.8	4.4
90°	6.3	6.3	3.6	3.6	3.2	2.7	1.3	0.5	1.3	2.7	3.2
92.5°	91.3	56.2	33.3	23.8	17.3	11.7	7.5	5.1	7.5	11.7	17.3
95°	169.9	95.8	56.5	37.5	26.7	20.8	16.2	14.9	16.2	20.8	26.7
97.5°	152.7	91.6	61.3	45.4	36.0	30.7	26.8	26.8	26.8	30.7	36.0
100°	143.7	92.6	66.0	51.5	42.9	37.5	34.4	34.4	34.4	37.5	42.9
102.5°	141.2	96.3	72.1	58.4	50.1	45.1	42.3	41.6	42.3	45.1	50.1
105°	142.4	104.8	83.2	70.0	61.9	56.5	54.3	52.8	54.3	56.5	61.9
107.5°	149.0	114.9	95.0	82.1	74.3	68.5	66.2	65.4	66.2	68.5	74.3
110°	154.1	122.5	102.6	90.4	82.2	76.8	74.5	73.7	74.5	76.8	82.2



TEST NUMBER: P332873-927

CATALOG NUMBER: SA4XXRDIP-C350D590U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	159.5	129.7	110.5	98.3	90.2	85.2	82.5	81.6	82.5	85.2	90.2
115°	168.1	141.0	122.9	110.7	102.1	97.6	94.4	93.1	94.4	97.6	102.1
117.5°	176.9	151.9	134.8	122.1	114.1	109.1	106.3	105.0	106.3	109.1	114.1
120°	183.0	159.5	142.4	129.7	122.0	117.0	113.9	113.0	113.9	117.0	122.0
122.5°	188.8	166.8	149.6	137.3	128.9	124.3	121.1	120.2	121.1	124.3	128.9
125°	197.5	176.7	160.4	147.7	139.2	134.2	131.5	129.7	131.5	134.2	139.2
127.5°	205.0	185.9	170.2	157.4	148.5	142.8	139.6	138.1	139.6	142.8	148.5
130°	209.7	192.0	176.7	163.6	155.0	148.2	144.6	142.8	144.6	148.2	155.0
132.5°	214.4	197.1	181.7	169.4	160.1	153.7	148.9	147.5	148.9	153.7	160.1
135°	220.5	204.2	189.3	177.6	168.1	160.4	155.9	154.1	155.9	160.4	168.1
137.5°	224.9	209.7	195.7	184.6	174.7	167.4	162.4	160.7	162.4	167.4	174.7
140°	227.8	213.3	199.7	188.9	179.4	171.7	166.8	165.4	166.8	171.7	179.4
142.5°	229.9	216.6	203.4	192.9	183.7	176.4	171.8	170.5	171.8	176.4	183.7
145°	232.3	220.1	208.3	198.4	189.8	183.5	179.0	177.6	179.0	183.5	189.8
147.5°	234.3	223.7	212.7	203.7	196.5	190.0	186.1	185.6	186.1	190.0	196.5
150°	235.4	225.5	215.6	207.0	200.2	194.8	191.2	190.7	191.2	194.8	200.2
152.5°	236.1	227.0	218.1	210.2	204.1	199.1	195.5	195.4	195.5	199.1	204.1
155°	236.8	229.1	221.4	214.7	209.7	205.2	202.5	202.0	202.5	205.2	209.7
157.5°	236.8	230.7	224.1	218.8	214.4	211.0	208.4	208.4	208.4	211.0	214.4
160°	236.8	231.4	225.9	220.9	217.4	214.2	212.4	212.4	212.4	214.2	217.4
162.5°	236.8	232.1	227.0	223.2	219.9	217.1	215.6	216.0	215.6	217.1	219.9
165°	235.9	232.3	228.2	225.5	223.2	220.9	220.1	220.1	220.1	220.9	223.2
167.5°	234.8	232.2	229.2	227.1	225.9	224.1	223.7	224.1	223.7	224.1	225.9
170°	234.1	231.8	229.6	228.2	227.3	225.9	225.5	225.9	225.5	225.9	227.3
172.5°	233.4	231.5	229.9	228.9	228.4	227.4	227.3	227.8	227.3	227.4	228.4
175°	232.3	230.9	230.0	230.0	229.6	229.1	229.1	229.6	229.1	229.1	229.6
177.5°	231.1	230.4	230.0	230.0	230.0	229.7	230.0	230.4	230.0	229.7	230.0
180°	230.0	230.0	230.0	230.0	230.0	230.0	230.0	230.0	230.0	230.0	230.0



TEST NUMBER: P332873-927

CATALOG NUMBER: SA4XXRDIP-C350D590U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3
2.5°	456.9	455.4	453.5	451.2	448.5	446.2	445.0	446.0	446.5	445.2	445.0
5°	443.0	438.3	434.6	429.0	424.5	420.7	418.1	416.9	417.3	414.3	413.6
7.5°	427.4	421.8	415.7	409.0	402.8	397.3	394.4	392.8	389.6	388.2	386.0
10°	417.3	409.9	403.9	395.9	388.8	382.3	379.1	376.4	373.3	371.8	368.6
12.5°	407.0	398.3	391.7	383.5	376.2	368.4	365.3	360.4	355.5	352.3	348.2
15°	392.4	381.9	373.8	364.1	355.5	346.5	338.4	329.4	326.1	318.9	314.8
17.5°	375.3	364.7	354.7	341.7	328.4	317.1	308.6	299.9	294.8	290.3	288.1
20°	364.1	354.3	340.5	325.3	310.5	298.1	291.1	285.5	279.9	276.7	274.5
22.5°	353.5	341.0	324.9	308.5	293.7	284.0	278.1	272.4	267.8	264.7	261.7
25°	335.6	319.2	302.2	283.4	273.4	264.9	258.6	253.8	251.0	247.1	245.6
27.5°	317.3	297.5	278.7	266.1	255.6	247.8	242.2	238.8	235.2	232.7	230.7
30°	303.2	283.1	266.3	254.2	243.5	237.2	232.7	228.5	225.7	223.6	222.2
32.5°	289.2	269.2	255.0	242.1	233.6	227.4	222.6	219.5	217.3	214.7	213.7
35°	269.0	251.2	238.8	227.2	218.6	213.0	209.2	206.0	204.1	203.4	202.9
37.5°	249.6	235.0	221.7	212.2	204.5	200.1	195.7	194.1	192.8	191.5	192.1
40°	237.3	223.6	211.8	201.8	195.5	190.7	188.1	186.2	185.1	185.1	185.1
42.5°	226.7	213.3	201.8	192.7	186.6	182.4	179.5	177.9	177.5	177.4	178.3
45°	210.2	197.8	186.2	178.6	173.4	169.3	167.6	166.3	166.3	167.1	167.2
47.5°	193.8	182.2	172.9	164.5	159.6	157.1	155.6	155.0	155.0	155.7	156.6
50°	183.7	172.3	163.1	155.6	151.1	148.7	147.3	146.9	147.3	147.3	148.7
52.5°	172.8	162.6	153.5	147.2	142.1	139.8	139.1	138.6	138.8	139.4	140.0
55°	156.8	147.6	138.9	132.9	129.2	127.7	126.0	126.2	125.8	126.2	126.2
57.5°	140.6	132.4	124.4	119.6	116.3	114.2	112.3	112.8	112.3	112.2	111.9
60°	130.3	121.3	114.9	110.6	106.9	105.0	103.3	103.7	103.1	102.7	102.0
62.5°	119.1	111.5	105.4	101.3	98.3	96.2	94.4	94.1	92.8	91.5	89.8
65°	102.7	96.6	91.1	87.2	84.4	82.7	81.4	80.2	77.4	74.5	73.0
67.5°	86.9	82.4	77.3	74.0	71.7	69.6	67.0	65.1	62.5	60.8	59.9
70°	76.7	72.4	68.0	64.9	62.4	60.4	57.6	56.2	54.3	53.6	52.7
72.5°	66.9	62.9	58.9	56.0	53.5	51.8	49.6	48.3	47.5	47.1	46.3
75°	52.1	49.0	45.9	43.3	41.3	40.1	39.2	38.3	37.9	36.2	35.3
77.5°	38.0	35.9	34.1	32.2	30.7	29.9	28.1	27.1	26.5	25.7	25.4
80°	29.6	28.1	26.2	25.1	23.1	22.3	21.5	21.4	21.2	21.0	20.8
82.5°	22.3	20.8	18.9	18.2	17.7	17.2	16.8	16.6	16.4	16.5	16.5
85°	11.2	10.5	10.5	10.3	10.1	9.9	9.7	9.7	9.6	9.7	9.6
87.5°	4.4	4.4	4.8	4.6	4.9	5.1	4.8	4.9	5.1	5.0	5.0
90°	3.6	3.6	6.3	6.3	7.2	8.2	7.7	8.2	8.6	9.0	9.0
92.5°	23.8	33.3	56.2	91.3	125.5	143.3	119.4	88.7	66.8	53.2	44.1
95°	37.5	56.5	95.8	169.9	277.9	368.3	378.7	334.9	264.8	204.2	160.4
97.5°	45.4	61.3	91.6	152.7	260.2	387.9	475.8	494.7	468.7	424.5	377.3
100°	51.5	66.0	92.6	143.7	235.9	363.3	479.0	545.0	554.1	531.9	498.4
102.5°	58.4	72.1	96.3	141.2	219.6	332.6	451.9	542.5	587.3	593.7	579.8
105°	70.0	83.2	104.8	142.4	205.7	296.4	402.7	506.1	584.3	629.1	647.6
107.5°	82.1	95.0	114.9	149.0	203.1	276.2	362.9	454.6	537.7	600.8	641.0
110°	90.4	102.6	122.5	154.1	203.8	269.3	343.0	423.4	501.6	567.1	616.9



TEST NUMBER: P332873-927

CATALOG NUMBER: SA4XXRDIP-C350D590U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	98.3	110.5	129.7	159.5	206.0	266.1	331.8	400.7	469.8	531.7	581.4
115°	110.7	122.9	141.0	168.1	210.2	264.4	321.3	377.8	433.4	486.2	529.7
117.5°	122.1	134.8	151.9	176.9	214.5	263.9	316.6	366.5	412.6	454.2	490.9
120°	129.7	142.4	159.5	183.0	217.9	263.9	314.1	361.6	403.5	439.7	471.7
122.5°	137.3	149.6	166.8	188.8	221.1	263.6	311.2	357.2	397.8	430.6	458.8
125°	147.7	160.4	176.7	197.5	225.9	263.0	306.4	349.7	388.6	419.8	444.7
127.5°	157.4	170.2	185.9	205.0	229.8	262.0	300.0	340.7	377.9	409.0	432.5
130°	163.6	176.7	192.0	209.7	232.7	261.7	296.0	333.5	369.2	399.9	423.9
132.5°	169.4	181.7	197.1	214.4	235.3	261.3	292.4	325.9	359.4	389.4	413.4
135°	177.6	189.3	204.2	220.5	239.1	260.7	286.9	315.4	344.8	372.3	395.0
137.5°	184.6	195.7	209.7	224.9	241.3	260.6	282.3	305.9	330.8	354.0	374.5
140°	188.9	199.7	213.3	227.8	243.1	260.3	279.7	300.5	321.8	342.1	361.1
142.5°	192.9	203.4	216.6	229.9	244.5	260.3	277.6	295.5	314.2	331.6	348.1
145°	198.4	208.3	220.1	232.3	245.4	259.4	273.9	288.3	303.6	317.3	329.9
147.5°	203.7	212.7	223.7	234.3	245.8	257.8	270.5	282.4	294.6	305.5	315.4
150°	207.0	215.6	225.5	235.4	245.8	256.7	268.0	278.8	289.2	298.3	306.4
152.5°	210.2	218.1	227.0	236.1	245.1	254.8	265.1	274.8	283.8	292.1	298.8
155°	214.7	221.4	229.1	236.8	244.0	252.2	260.7	268.9	276.1	282.9	288.3
157.5°	218.8	224.1	230.7	236.8	242.9	249.4	256.4	262.4	268.5	274.2	278.5
160°	220.9	225.9	231.4	236.8	241.8	247.2	253.1	258.5	263.5	268.4	272.0
162.5°	223.2	227.0	232.1	236.8	240.7	245.0	250.2	254.5	258.7	262.6	265.9
165°	225.5	228.2	232.3	235.9	238.6	241.8	245.4	249.0	251.7	254.8	257.1
167.5°	227.1	229.2	232.2	234.8	236.5	238.5	241.1	243.7	245.7	248.3	249.6
170°	228.2	229.6	231.8	234.1	235.0	236.3	238.1	240.4	241.8	243.6	244.9
172.5°	228.9	229.9	231.5	233.4	233.5	234.2	235.6	237.5	238.5	239.6	240.6
175°	230.0	230.0	230.9	232.3	231.8	231.8	232.7	233.6	234.1	235.0	235.0
177.5°	230.0	230.0	230.4	231.1	230.4	230.4	230.8	231.1	231.5	231.5	231.8
180°	230.0	230.0	230.0	230.0	230.0	230.0	230.0	230.0	230.0	230.0	230.0



TEST NUMBER: P332873-927

CATALOG NUMBER: SA4XXRDIP-C350D590U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3
2.5°	444.2	444.5	443.5	443.1	443.5	444.5	444.2	445.0	445.2	446.5	446.0
5°	412.1	411.7	410.7	411.0	410.7	411.7	412.1	413.6	414.3	417.3	416.9
7.5°	384.6	383.2	383.6	382.1	383.6	383.2	384.6	386.0	388.2	389.6	392.8
10°	367.8	365.8	364.1	362.6	364.1	365.8	367.8	368.6	371.8	373.3	376.4
12.5°	344.9	343.1	340.9	341.3	340.9	343.1	344.9	348.2	352.3	355.5	360.4
15°	312.4	309.5	305.1	305.6	305.1	309.5	312.4	314.8	318.9	326.1	329.4
17.5°	284.8	284.8	282.7	283.3	282.7	284.8	284.8	288.1	290.3	294.8	299.9
20°	270.5	269.3	269.4	268.9	269.4	269.3	270.5	274.5	276.7	279.9	285.5
22.5°	260.6	259.0	257.7	256.6	257.7	259.0	260.6	261.7	264.7	267.8	272.4
25°	243.9	242.8	241.1	240.7	241.1	242.8	243.9	245.6	247.1	251.0	253.8
27.5°	229.2	229.0	228.3	227.4	228.3	229.0	229.2	230.7	232.7	235.2	238.8
30°	220.7	220.3	219.9	219.4	219.9	220.3	220.7	222.2	223.6	225.7	228.5
32.5°	213.0	212.8	212.4	212.5	212.4	212.8	213.0	213.7	214.7	217.3	219.5
35°	202.1	201.9	201.5	201.4	201.5	201.9	202.1	202.9	203.4	204.1	206.0
37.5°	191.9	192.4	192.2	192.1	192.2	192.4	191.9	192.1	191.5	192.8	194.1
40°	184.9	185.1	185.4	185.2	185.4	185.1	184.9	185.1	185.1	185.1	186.2
42.5°	179.0	179.0	179.6	179.0	179.6	179.0	179.0	178.3	177.4	177.5	177.9
45°	168.6	169.7	169.4	169.4	169.4	169.7	168.6	167.2	167.1	166.3	166.3
47.5°	157.1	158.1	158.4	158.3	158.4	158.1	157.1	156.6	155.7	155.0	155.0
50°	149.6	149.2	149.8	149.6	149.8	149.2	149.6	148.7	147.3	147.3	146.9
52.5°	140.5	140.5	140.5	140.3	140.5	140.5	140.5	140.0	139.4	138.8	138.6
55°	126.4	126.6	126.2	126.4	126.2	126.6	126.4	126.2	126.2	125.8	126.2
57.5°	111.1	110.2	110.5	110.1	110.5	110.2	111.1	111.9	112.2	112.3	112.8
60°	100.1	98.6	98.2	97.5	98.2	98.6	100.1	102.0	102.7	103.1	103.7
62.5°	87.9	86.7	85.5	86.1	85.5	86.7	87.9	89.8	91.5	92.8	94.1
65°	71.5	70.7	70.1	70.9	70.1	70.7	71.5	73.0	74.5	77.4	80.2
67.5°	59.1	58.7	58.7	58.4	58.7	58.7	59.1	59.9	60.8	62.5	65.1
70°	52.7	52.1	52.1	51.7	52.1	52.1	52.7	52.7	53.6	54.3	56.2
72.5°	46.1	45.6	45.7	45.5	45.7	45.6	46.1	46.3	47.1	47.5	48.3
75°	34.1	33.2	33.2	33.4	33.2	33.2	34.1	35.3	36.2	37.9	38.3
77.5°	25.4	25.3	25.5	25.2	25.5	25.3	25.4	25.4	25.7	26.5	27.1
80°	20.8	20.6	20.4	21.0	20.4	20.6	20.8	20.8	21.0	21.2	21.4
82.5°	16.2	16.2	16.1	16.8	16.1	16.2	16.2	16.5	16.5	16.4	16.6
85°	9.7	9.3	9.7	9.3	9.7	9.3	9.7	9.6	9.7	9.6	9.7
87.5°	5.4	5.3	5.1	5.2	5.1	5.3	5.4	5.0	5.0	5.1	4.9
90°	9.5	9.9	9.5	9.5	9.5	9.9	9.5	9.0	9.0	8.6	8.2
92.5°	38.7	36.4	34.8	34.8	34.8	36.4	38.7	44.1	53.2	66.8	88.7
95°	138.3	124.3	116.1	110.3	116.1	124.3	138.3	160.4	204.2	264.8	334.9
97.5°	344.9	317.7	304.1	294.7	304.1	317.7	344.9	377.3	424.5	468.7	494.7
100°	459.1	431.6	418.0	414.4	418.0	431.6	459.1	498.4	531.9	554.1	545.0
102.5°	555.6	535.7	521.4	518.5	521.4	535.7	555.6	579.8	593.7	587.3	542.5
105°	648.5	644.8	638.5	635.8	638.5	644.8	648.5	647.6	629.1	584.3	506.1
107.5°	663.4	673.7	678.2	679.4	678.2	673.7	663.4	641.0	600.8	537.7	454.6
110°	649.0	667.9	676.0	680.1	676.0	667.9	649.0	616.9	567.1	501.6	423.4



TEST NUMBER: P332873-927

CATALOG NUMBER: SA4XXRDIP-C350D590U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	617.8	640.8	652.2	658.8	652.2	640.8	617.8	581.4	531.7	469.8	400.7
115°	565.3	592.5	606.9	610.5	606.9	592.5	565.3	529.7	486.2	433.4	377.8
117.5°	521.4	544.2	558.8	561.7	558.8	544.2	521.4	490.9	454.2	412.6	366.5
120°	497.6	517.5	529.2	534.2	529.2	517.5	497.6	471.7	439.7	403.5	361.6
122.5°	480.5	497.6	507.5	512.5	507.5	497.6	480.5	458.8	430.6	397.8	357.2
125°	462.7	475.9	484.4	487.1	484.4	475.9	462.7	444.7	419.8	388.6	349.7
127.5°	450.8	462.4	469.6	472.3	469.6	462.4	450.8	432.5	409.0	377.9	340.7
130°	442.4	453.7	461.0	463.7	461.0	453.7	442.4	423.9	399.9	369.2	333.5
132.5°	431.6	444.3	451.1	453.9	451.1	444.3	431.6	413.4	389.4	359.4	325.9
135°	413.0	425.7	432.9	435.6	432.9	425.7	413.0	395.0	372.3	344.8	315.4
137.5°	391.3	403.9	409.8	413.0	409.8	403.9	391.3	374.5	354.0	330.8	305.9
140°	376.9	386.8	393.2	396.8	393.2	386.8	376.9	361.1	342.1	321.8	300.5
142.5°	362.0	371.3	376.9	379.4	376.9	371.3	362.0	348.1	331.6	314.2	295.5
145°	341.2	348.9	353.4	355.6	353.4	348.9	341.2	329.9	317.3	303.6	288.3
147.5°	323.8	330.3	333.7	334.6	333.7	330.3	323.8	315.4	305.5	294.6	282.4
150°	313.6	319.5	322.2	322.7	322.2	319.5	313.6	306.4	298.3	289.2	278.8
152.5°	304.9	309.7	311.3	311.8	311.3	309.7	304.9	298.8	292.1	283.8	274.8
155°	292.9	296.4	297.8	297.8	297.8	296.4	292.9	288.3	282.9	276.1	268.9
157.5°	282.0	284.7	285.5	285.5	285.5	284.7	282.0	278.5	274.2	268.5	262.4
160°	274.7	277.5	277.9	277.9	277.9	277.5	274.7	272.0	268.4	263.5	258.5
162.5°	267.9	270.6	271.1	270.7	271.1	270.6	267.9	265.9	262.6	258.7	254.5
165°	259.0	260.7	260.3	259.8	260.3	260.7	259.0	257.1	254.8	251.7	249.0
167.5°	250.6	251.7	251.6	251.3	251.6	251.7	250.6	249.6	248.3	245.7	243.7
170°	245.8	246.3	245.8	245.8	245.8	246.3	245.8	244.9	243.6	241.8	240.4
172.5°	241.1	241.6	241.1	240.4	241.1	241.6	241.1	240.6	239.6	238.5	237.5
175°	235.0	235.9	235.0	234.1	235.0	235.9	235.0	235.0	235.0	234.1	233.6
177.5°	231.5	231.8	231.1	230.4	231.1	231.8	231.5	231.8	231.5	231.5	231.1
180°	230.0	230.0	230.0	230.0	230.0	230.0	230.0	230.0	230.0	230.0	230.0



TEST NUMBER: P332873-927

CATALOG NUMBER: SA4XXRDIP-C350D590U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3
2.5°	445.0	446.2	448.5	451.2	453.5	455.4	456.9	459.1	461.0	463.7	466.2
5°	418.1	420.7	424.5	429.0	434.6	438.3	443.0	447.2	453.1	459.1	464.9
7.5°	394.4	397.3	402.8	409.0	415.7	421.8	427.4	434.7	442.6	451.4	461.1
10°	379.1	382.3	388.8	395.9	403.9	409.9	417.3	426.0	435.0	445.7	457.6
12.5°	365.3	368.4	376.2	383.5	391.7	398.3	407.0	415.7	427.8	439.3	453.0
15°	338.4	346.5	355.5	364.1	373.8	381.9	392.4	401.4	412.8	429.1	444.7
17.5°	308.6	317.1	328.4	341.7	354.7	364.7	375.3	386.5	400.1	416.8	434.7
20°	291.1	298.1	310.5	325.3	340.5	354.3	364.1	376.4	390.5	408.5	427.1
22.5°	278.1	284.0	293.7	308.5	324.9	341.0	353.5	365.7	381.2	399.3	419.5
25°	258.6	264.9	273.4	283.4	302.2	319.2	335.6	349.7	366.1	384.1	406.6
27.5°	242.2	247.8	255.6	266.1	278.7	297.5	317.3	333.3	350.2	369.6	392.1
30°	232.7	237.2	243.5	254.2	266.3	283.1	303.2	321.9	339.0	359.0	382.5
32.5°	222.6	227.4	233.6	242.1	255.0	269.2	289.2	309.7	327.9	348.4	371.4
35°	209.2	213.0	218.6	227.2	238.8	251.2	269.0	290.3	309.3	331.3	353.2
37.5°	195.7	200.1	204.5	212.2	221.7	235.0	249.6	271.3	292.5	312.5	333.9
40°	188.1	190.7	195.5	201.8	211.8	223.6	237.3	258.6	279.7	299.6	321.2
42.5°	179.5	182.4	186.6	192.7	201.8	213.3	226.7	245.0	267.1	286.4	306.0
45°	167.6	169.3	173.4	178.6	186.2	197.8	210.2	226.5	247.3	265.7	282.9
47.5°	155.6	157.1	159.6	164.5	172.9	182.2	193.8	208.4	226.6	245.0	259.6
50°	147.3	148.7	151.1	155.6	163.1	172.3	183.7	196.9	213.2	230.8	243.0
52.5°	139.1	139.8	142.1	147.2	153.5	162.6	172.8	184.9	200.1	214.8	227.1
55°	126.0	127.7	129.2	132.9	138.9	147.6	156.8	168.2	180.0	192.3	202.9
57.5°	112.3	114.2	116.3	119.6	124.4	132.4	140.6	149.9	160.0	170.2	179.1
60°	103.3	105.0	106.9	110.6	114.9	121.3	130.3	138.4	146.1	155.4	164.2
62.5°	94.4	96.2	98.3	101.3	105.4	111.5	119.1	126.0	134.0	142.2	148.8
65°	81.4	82.7	84.4	87.2	91.1	96.6	102.7	108.2	115.3	121.3	127.3
67.5°	67.0	69.6	71.7	74.0	77.3	82.4	86.9	92.1	97.0	101.4	106.9
70°	57.6	60.4	62.4	64.9	68.0	72.4	76.7	80.2	84.2	88.5	93.4
72.5°	49.6	51.8	53.5	56.0	58.9	62.9	66.9	69.9	73.1	76.0	80.8
75°	39.2	40.1	41.3	43.3	45.9	49.0	52.1	54.7	56.6	59.3	62.6
77.5°	28.1	29.9	30.7	32.2	34.1	35.9	38.0	40.2	42.1	42.9	45.6
80°	21.5	22.3	23.1	25.1	26.2	28.1	29.6	31.7	32.4	33.4	35.8
82.5°	16.8	17.2	17.7	18.2	18.9	20.8	22.3	23.6	24.3	24.6	26.5
85°	9.7	9.9	10.1	10.3	10.5	10.5	11.2	12.2	13.5	13.5	14.1
87.5°	4.8	5.1	4.9	4.6	4.8	4.4	4.4	4.4	4.8	4.9	5.2
90°	7.7	8.2	7.2	6.3	6.3	3.6	3.6	3.2	2.7	1.3	0.5
92.5°	119.4	143.3	125.5	91.3	56.2	33.3	23.8	17.3	11.7	7.5	5.1
95°	378.7	368.3	277.9	169.9	95.8	56.5	37.5	26.7	20.8	16.2	14.9
97.5°	475.8	387.9	260.2	152.7	91.6	61.3	45.4	36.0	30.7	26.8	26.8
100°	479.0	363.3	235.9	143.7	92.6	66.0	51.5	42.9	37.5	34.4	34.4
102.5°	451.9	332.6	219.6	141.2	96.3	72.1	58.4	50.1	45.1	42.3	41.6
105°	402.7	296.4	205.7	142.4	104.8	83.2	70.0	61.9	56.5	54.3	52.8
107.5°	362.9	276.2	203.1	149.0	114.9	95.0	82.1	74.3	68.5	66.2	65.4
110°	343.0	269.3	203.8	154.1	122.5	102.6	90.4	82.2	76.8	74.5	73.7



TEST NUMBER: P332873-927

CATALOG NUMBER: SA4XXRDIP-C350D590U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	331.8	266.1	206.0	159.5	129.7	110.5	98.3	90.2	85.2	82.5	81.6
115°	321.3	264.4	210.2	168.1	141.0	122.9	110.7	102.1	97.6	94.4	93.1
117.5°	316.6	263.9	214.5	176.9	151.9	134.8	122.1	114.1	109.1	106.3	105.0
120°	314.1	263.9	217.9	183.0	159.5	142.4	129.7	122.0	117.0	113.9	113.0
122.5°	311.2	263.6	221.1	188.8	166.8	149.6	137.3	128.9	124.3	121.1	120.2
125°	306.4	263.0	225.9	197.5	176.7	160.4	147.7	139.2	134.2	131.5	129.7
127.5°	300.0	262.0	229.8	205.0	185.9	170.2	157.4	148.5	142.8	139.6	138.1
130°	296.0	261.7	232.7	209.7	192.0	176.7	163.6	155.0	148.2	144.6	142.8
132.5°	292.4	261.3	235.3	214.4	197.1	181.7	169.4	160.1	153.7	148.9	147.5
135°	286.9	260.7	239.1	220.5	204.2	189.3	177.6	168.1	160.4	155.9	154.1
137.5°	282.3	260.6	241.3	224.9	209.7	195.7	184.6	174.7	167.4	162.4	160.7
140°	279.7	260.3	243.1	227.8	213.3	199.7	188.9	179.4	171.7	166.8	165.4
142.5°	277.6	260.3	244.5	229.9	216.6	203.4	192.9	183.7	176.4	171.8	170.5
145°	273.9	259.4	245.4	232.3	220.1	208.3	198.4	189.8	183.5	179.0	177.6
147.5°	270.5	257.8	245.8	234.3	223.7	212.7	203.7	196.5	190.0	186.1	185.6
150°	268.0	256.7	245.8	235.4	225.5	215.6	207.0	200.2	194.8	191.2	190.7
152.5°	265.1	254.8	245.1	236.1	227.0	218.1	210.2	204.1	199.1	195.5	195.4
155°	260.7	252.2	244.0	236.8	229.1	221.4	214.7	209.7	205.2	202.5	202.0
157.5°	256.4	249.4	242.9	236.8	230.7	224.1	218.8	214.4	211.0	208.4	208.4
160°	253.1	247.2	241.8	236.8	231.4	225.9	220.9	217.4	214.2	212.4	212.4
162.5°	250.2	245.0	240.7	236.8	232.1	227.0	223.2	219.9	217.1	215.6	216.0
165°	245.4	241.8	238.6	235.9	232.3	228.2	225.5	223.2	220.9	220.1	220.1
167.5°	241.1	238.5	236.5	234.8	232.2	229.2	227.1	225.9	224.1	223.7	224.1
170°	238.1	236.3	235.0	234.1	231.8	229.6	228.2	227.3	225.9	225.5	225.9
172.5°	235.6	234.2	233.5	233.4	231.5	229.9	228.9	228.4	227.4	227.3	227.8
175°	232.7	231.8	231.8	232.3	230.9	230.0	230.0	229.6	229.1	229.1	229.6
177.5°	230.8	230.4	230.4	231.1	230.4	230.0	230.0	230.0	229.7	230.0	230.4
180°	230.0	230.0	230.0	230.0	230.0	230.0	230.0	230.0	230.0	230.0	230.0



TEST NUMBER: P332873-927

CATALOG NUMBER: SA4XXRDIP-C350D590U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3
2.5°	468.2	469.5	471.0	473.9	476.3	477.4	479.4	480.9	480.5	482.6	486.2
5°	470.0	475.1	480.9	486.9	493.6	499.2	503.7	508.3	511.8	516.1	522.5
7.5°	469.7	478.7	488.5	499.2	510.3	519.9	528.7	537.7	545.7	554.4	565.9
10°	468.5	480.5	492.7	506.8	520.9	534.2	546.1	557.4	568.1	579.5	594.0
12.5°	467.1	480.9	495.7	512.6	530.1	546.1	560.2	576.5	589.9	604.6	621.2
15°	461.2	479.7	499.9	521.7	542.8	564.4	583.6	603.5	622.1	639.7	660.7
17.5°	454.4	475.8	499.5	525.4	550.6	576.8	599.8	624.8	643.7	667.4	686.9
20°	448.9	471.9	497.2	526.2	554.9	584.0	609.3	634.9	656.2	680.0	704.7
22.5°	442.1	467.4	494.8	524.9	554.9	586.7	614.7	640.1	666.5	693.3	718.8
25°	431.2	457.5	486.6	519.5	554.1	586.5	616.5	647.9	676.4	705.5	728.4
27.5°	417.9	445.4	476.0	510.1	545.5	578.7	614.0	647.6	676.3	704.3	724.2
30°	407.2	436.3	465.7	500.2	536.9	572.6	610.5	644.0	674.2	699.3	710.6
32.5°	396.2	423.8	454.2	489.1	526.7	565.1	602.6	637.0	664.9	679.9	680.2
35°	377.2	403.1	434.6	468.9	507.6	549.1	587.2	620.9	638.0	639.3	620.9
37.5°	356.5	380.2	409.9	444.3	486.6	528.0	566.8	589.3	595.0	575.9	542.0
40°	341.6	363.5	392.2	427.5	469.4	512.2	547.6	564.1	558.2	527.2	489.3
42.5°	326.0	346.4	374.1	408.8	451.0	494.2	524.4	533.2	517.4	481.6	437.3
45°	300.6	319.2	346.7	381.8	422.2	462.7	485.6	481.1	454.6	412.3	362.6
47.5°	274.0	292.2	316.8	349.2	390.7	425.6	441.1	427.5	389.9	343.3	302.9
50°	256.5	275.0	297.7	328.7	366.5	400.3	410.2	389.6	347.8	303.0	265.9
52.5°	239.2	255.1	277.3	307.2	343.4	371.9	377.2	353.5	310.3	270.1	237.2
55°	213.0	227.4	246.1	274.3	305.6	329.8	326.9	296.4	257.2	222.9	197.0
57.5°	187.6	198.4	215.8	242.2	269.7	285.9	275.6	249.5	213.0	184.9	163.1
60°	170.8	180.9	197.0	220.1	244.3	253.5	244.9	216.6	187.7	162.0	143.6
62.5°	154.9	163.8	177.7	199.1	218.6	224.1	214.8	190.1	164.1	142.2	127.0
65°	131.8	140.1	151.9	167.1	180.5	183.2	177.2	151.9	132.2	113.8	103.3
67.5°	110.8	116.2	125.5	138.6	145.8	147.3	135.7	119.8	102.4	91.2	83.3
70°	96.7	100.5	109.1	116.2	122.1	122.2	111.5	98.8	85.5	76.3	70.5
72.5°	83.1	86.7	93.2	98.1	102.6	101.1	91.3	81.3	70.5	63.5	59.3
75°	64.1	67.3	70.7	73.0	73.0	71.1	63.9	56.4	50.2	46.1	44.8
77.5°	46.6	49.2	50.4	50.0	49.4	46.4	41.9	37.0	34.8	32.9	31.8
80°	36.6	37.7	38.0	37.2	36.0	32.6	29.6	27.6	25.5	24.7	24.4
82.5°	27.1	28.1	27.1	27.4	24.9	22.1	20.4	19.7	18.9	18.6	18.2
85°	14.4	14.3	13.9	12.9	11.2	10.9	10.7	10.5	10.1	10.3	9.9
87.5°	5.2	5.1	4.5	4.4	4.4	4.8	4.8	5.1	5.2	5.0	5.4
90°	1.3	2.7	3.2	3.6	3.6	6.3	6.3	7.2	8.2	7.7	8.2
92.5°	7.5	11.7	17.3	23.8	33.3	56.2	91.3	125.5	143.3	119.4	88.7
95°	16.2	20.8	26.7	37.5	56.5	95.8	169.9	277.9	368.3	378.7	334.9
97.5°	26.8	30.7	36.0	45.4	61.3	91.6	152.7	260.2	387.9	475.8	494.7
100°	34.4	37.5	42.9	51.5	66.0	92.6	143.7	235.9	363.3	479.0	545.0
102.5°	42.3	45.1	50.1	58.4	72.1	96.3	141.2	219.6	332.6	451.9	542.5
105°	54.3	56.5	61.9	70.0	83.2	104.8	142.4	205.7	296.4	402.7	506.1
107.5°	66.2	68.5	74.3	82.1	95.0	114.9	149.0	203.1	276.2	362.9	454.6
110°	74.5	76.8	82.2	90.4	102.6	122.5	154.1	203.8	269.3	343.0	423.4



TEST NUMBER: P332873-927

CATALOG NUMBER: SA4XXRDIP-C350D590U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	82.5	85.2	90.2	98.3	110.5	129.7	159.5	206.0	266.1	331.8	400.7
115°	94.4	97.6	102.1	110.7	122.9	141.0	168.1	210.2	264.4	321.3	377.8
117.5°	106.3	109.1	114.1	122.1	134.8	151.9	176.9	214.5	263.9	316.6	366.5
120°	113.9	117.0	122.0	129.7	142.4	159.5	183.0	217.9	263.9	314.1	361.6
122.5°	121.1	124.3	128.9	137.3	149.6	166.8	188.8	221.1	263.6	311.2	357.2
125°	131.5	134.2	139.2	147.7	160.4	176.7	197.5	225.9	263.0	306.4	349.7
127.5°	139.6	142.8	148.5	157.4	170.2	185.9	205.0	229.8	262.0	300.0	340.7
130°	144.6	148.2	155.0	163.6	176.7	192.0	209.7	232.7	261.7	296.0	333.5
132.5°	148.9	153.7	160.1	169.4	181.7	197.1	214.4	235.3	261.3	292.4	325.9
135°	155.9	160.4	168.1	177.6	189.3	204.2	220.5	239.1	260.7	286.9	315.4
137.5°	162.4	167.4	174.7	184.6	195.7	209.7	224.9	241.3	260.6	282.3	305.9
140°	166.8	171.7	179.4	188.9	199.7	213.3	227.8	243.1	260.3	279.7	300.5
142.5°	171.8	176.4	183.7	192.9	203.4	216.6	229.9	244.5	260.3	277.6	295.5
145°	179.0	183.5	189.8	198.4	208.3	220.1	232.3	245.4	259.4	273.9	288.3
147.5°	186.1	190.0	196.5	203.7	212.7	223.7	234.3	245.8	257.8	270.5	282.4
150°	191.2	194.8	200.2	207.0	215.6	225.5	235.4	245.8	256.7	268.0	278.8
152.5°	195.5	199.1	204.1	210.2	218.1	227.0	236.1	245.1	254.8	265.1	274.8
155°	202.5	205.2	209.7	214.7	221.4	229.1	236.8	244.0	252.2	260.7	268.9
157.5°	208.4	211.0	214.4	218.8	224.1	230.7	236.8	242.9	249.4	256.4	262.4
160°	212.4	214.2	217.4	220.9	225.9	231.4	236.8	241.8	247.2	253.1	258.5
162.5°	215.6	217.1	219.9	223.2	227.0	232.1	236.8	240.7	245.0	250.2	254.5
165°	220.1	220.9	223.2	225.5	228.2	232.3	235.9	238.6	241.8	245.4	249.0
167.5°	223.7	224.1	225.9	227.1	229.2	232.2	234.8	236.5	238.5	241.1	243.7
170°	225.5	225.9	227.3	228.2	229.6	231.8	234.1	235.0	236.3	238.1	240.4
172.5°	227.3	227.4	228.4	228.9	229.9	231.5	233.4	233.5	234.2	235.6	237.5
175°	229.1	229.1	229.6	230.0	230.0	230.9	232.3	231.8	231.8	232.7	233.6
177.5°	230.0	229.7	230.0	230.0	230.0	230.4	231.1	230.4	230.4	230.8	231.1
180°	230.0	230.0	230.0	230.0	230.0	230.0	230.0	230.0	230.0	230.0	230.0



TEST NUMBER: P332873-927

CATALOG NUMBER: SA4XXRDIP-C350D590U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	465.3	465.3	465.3	465.3	465.3	465.3	465.3
2.5°	488.1	488.7	489.2	490.7	490.8	492.2	490.8
5°	528.5	531.2	535.3	539.4	539.8	542.4	537.7
7.5°	573.8	579.9	583.7	590.3	592.9	594.6	591.9
10°	605.0	610.6	620.6	625.4	630.3	631.1	628.8
12.5°	635.2	644.0	651.9	661.2	660.9	667.5	665.1
15°	675.3	684.5	695.4	705.7	709.4	709.4	712.4
17.5°	703.9	720.8	732.1	740.1	749.0	750.5	749.5
20°	723.3	741.5	753.5	764.0	770.0	771.7	771.7
22.5°	737.7	753.2	764.9	774.4	779.3	781.3	780.7
25°	747.7	761.0	768.1	771.0	772.2	771.9	768.3
27.5°	734.0	733.4	729.0	720.3	713.8	709.9	705.4
30°	708.0	698.2	686.9	674.5	658.6	646.4	642.7
32.5°	669.1	647.2	628.1	607.5	590.4	578.2	573.1
35°	594.0	559.3	530.9	506.2	488.2	477.0	473.2
37.5°	504.8	471.2	436.2	412.2	397.2	385.9	381.7
40°	448.1	411.5	381.0	358.5	343.1	332.0	331.8
42.5°	396.3	361.4	332.6	316.5	299.9	292.6	292.6
45°	324.6	296.6	272.2	259.4	249.5	243.5	241.9
47.5°	268.7	245.6	229.3	219.2	211.1	207.3	204.8
50°	237.3	217.1	204.1	195.4	190.8	186.0	185.6
52.5°	211.3	194.9	184.8	177.7	172.0	169.1	169.1
55°	177.5	164.6	157.5	152.0	147.6	145.3	144.3
57.5°	149.6	139.9	134.7	129.7	127.8	126.0	125.6
60°	132.2	125.6	120.7	116.8	114.0	113.4	113.2
62.5°	117.8	110.9	107.6	104.5	102.4	101.6	101.2
65°	97.1	92.1	89.0	86.6	85.9	84.5	84.4
67.5°	78.3	75.3	73.3	71.6	70.6	70.5	70.5
70°	66.8	65.0	63.4	62.4	61.9	61.5	61.5
72.5°	56.9	55.6	54.2	53.7	53.6	53.2	53.1
75°	43.3	42.0	42.2	41.3	40.5	39.5	39.0
77.5°	30.7	29.8	29.5	29.5	28.8	28.8	29.0
80°	23.8	22.9	22.7	22.9	22.7	22.1	22.1
82.5°	18.1	17.3	17.1	17.0	16.9	17.0	16.7
85°	9.7	9.3	9.3	9.3	9.7	9.6	9.3
87.5°	5.1	5.1	5.2	5.2	5.3	5.1	5.2
90°	8.6	9.0	9.0	9.5	9.9	9.5	9.5
92.5°	66.8	53.2	44.1	38.7	36.4	34.8	34.8
95°	264.8	204.2	160.4	138.3	124.3	116.1	110.3
97.5°	468.7	424.5	377.3	344.9	317.7	304.1	294.7
100°	554.1	531.9	498.4	459.1	431.6	418.0	414.4
102.5°	587.3	593.7	579.8	555.6	535.7	521.4	518.5
105°	584.3	629.1	647.6	648.5	644.8	638.5	635.8
107.5°	537.7	600.8	641.0	663.4	673.7	678.2	679.4
110°	501.6	567.1	616.9	649.0	667.9	676.0	680.1



TEST NUMBER: P332873-927

CATALOG NUMBER: SA4XXRDIP-C350D590U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	469.8	531.7	581.4	617.8	640.8	652.2	658.8
115°	433.4	486.2	529.7	565.3	592.5	606.9	610.5
117.5°	412.6	454.2	490.9	521.4	544.2	558.8	561.7
120°	403.5	439.7	471.7	497.6	517.5	529.2	534.2
122.5°	397.8	430.6	458.8	480.5	497.6	507.5	512.5
125°	388.6	419.8	444.7	462.7	475.9	484.4	487.1
127.5°	377.9	409.0	432.5	450.8	462.4	469.6	472.3
130°	369.2	399.9	423.9	442.4	453.7	461.0	463.7
132.5°	359.4	389.4	413.4	431.6	444.3	451.1	453.9
135°	344.8	372.3	395.0	413.0	425.7	432.9	435.6
137.5°	330.8	354.0	374.5	391.3	403.9	409.8	413.0
140°	321.8	342.1	361.1	376.9	386.8	393.2	396.8
142.5°	314.2	331.6	348.1	362.0	371.3	376.9	379.4
145°	303.6	317.3	329.9	341.2	348.9	353.4	355.6
147.5°	294.6	305.5	315.4	323.8	330.3	333.7	334.6
150°	289.2	298.3	306.4	313.6	319.5	322.2	322.7
152.5°	283.8	292.1	298.8	304.9	309.7	311.3	311.8
155°	276.1	282.9	288.3	292.9	296.4	297.8	297.8
157.5°	268.5	274.2	278.5	282.0	284.7	285.5	285.5
160°	263.5	268.4	272.0	274.7	277.5	277.9	277.9
162.5°	258.7	262.6	265.9	267.9	270.6	271.1	270.7
165°	251.7	254.8	257.1	259.0	260.7	260.3	259.8
167.5°	245.7	248.3	249.6	250.6	251.7	251.6	251.3
170°	241.8	243.6	244.9	245.8	246.3	245.8	245.8
172.5°	238.5	239.6	240.6	241.1	241.6	241.1	240.4
175°	234.1	235.0	235.0	235.0	235.9	235.0	234.1
177.5°	231.5	231.5	231.8	231.5	231.8	231.1	230.4
180°	230.0	230.0	230.0	230.0	230.0	230.0	230.0

(END OF REPORT)