

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332879-927

Luminaire Tested: **SA4XXRDIP-C350D810U927-4F0-1E-UDD-A4**

Issue Date: 10/7/2019


Test Information

Test Method: LM-79-08
Report Number: P332879-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C350D810U927-4F0-1E-UDD-A4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3471.0 lumens
Efficiency: N/A
Efficacy: 111.3 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332879-927
CATALOG NUMBER: SA4XXRDIP-C350D810U927-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332879-927

CATALOG NUMBER: SA4XXRDIP-C350D810U927-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	34				
1	95	90	87	83	85	82	79	76	66	63	62	51	49	48	37	36	36	29				
2	86	79	73	69	78	72	67	63	58	54	51	45	43	41	33	32	30	25				
3	79	70	63	57	71	63	57	53	51	47	44	40	37	35	29	28	26	21				
4	72	62	54	49	65	56	50	45	46	41	37	36	32	30	26	24	23	19				
5	66	55	47	42	60	50	44	39	41	36	32	32	29	26	24	22	20	16				
6	61	49	42	36	55	45	38	33	37	32	28	29	26	23	22	19	18	14				
7	56	45	37	32	51	41	34	29	33	28	25	26	23	20	20	18	16	13				
8	52	40	33	28	47	37	30	26	30	25	22	24	21	18	18	16	14	12				
9	49	37	30	25	44	34	27	23	28	23	20	22	19	16	17	15	13	11				
10	45	34	27	22	41	31	25	21	26	21	18	20	17	15	16	13	12	10				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	3756	3756	3756	3756
5°	4357	3767	3331	3767
10°	5155	3751	2972	3751
15°	5954	3717	2554	3717
20°	6630	3669	2310	3669
25°	6844	3622	2144	3622
30°	5991	3566	2045	3566
35°	4664	3481	1985	3481
40°	3497	3385	1952	3385
45°	2762	3230	1934	3230
50°	2331	3052	1879	3052
55°	2031	2856	1779	2856
60°	1828	2651	1574	2651
65°	1612	2432	1354	2432
70°	1452	2205	1220	2205
75°	1216	1953	1042	1953
80°	1027	1664	976	1664
85°	861	1306	861	1306



TEST NUMBER: P332879-927

CATALOG NUMBER: SA4XXRDIP-C350D810U927-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.1	1.3
10°-20°	136.0	3.9
20°-30°	212.7	6.1
30°-40°	236.5	6.8
40°-50°	209.8	6.0
50°-60°	163.5	4.7
60°-70°	107.0	3.1
70°-80°	52.6	1.5
80°-90°	14.7	0.4
90°-100°	227.7	6.6
100°-110°	474.0	13.7
110°-120°	424.5	12.2
120°-130°	357.1	10.3
130°-140°	297.7	8.6
140°-150°	227.5	6.6
150°-160°	159.9	4.6
160°-170°	94.0	2.7
170°-180°	30.6	0.9
0°-30°	393.8	11.3
0°-40°	630.3	18.2
0°-60°	1003.6	28.9
0°-90°	1178.0	33.9
90°-120°	1126.2	32.4
90°-150°	2008.5	57.9
90°-180°	2293.0	66.1
0°-180°	3471.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	465	465	465	465	465	
5°	538	465	411	465	538	54
15°	712	445	306	445	712	203
25°	768	407	241	407	768	341
35°	473	353	201	353	473	297
45°	242	283	169	283	242	192
55°	144	203	126	203	144	131
65°	84	127	71	127	84	85
75°	39	63	33	63	39	43
85°	9	14	9	14	9	11
90°	13	1	13	1	13	11
95°	151	20	151	20	151	235
105°	872	72	872	72	872	862
115°	837	128	837	128	837	831
125°	668	178	668	178	668	607
135°	597	211	597	211	597	461
145°	488	243	488	243	488	309
155°	408	277	408	277	408	190
165°	356	302	356	302	356	102
175°	321	315	321	315	321	31
180°	315	315	315	315	315	



TEST NUMBER: P332879-927

CATALOG NUMBER: SA4XXRDIP-C350D810U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3
2.5°	490.8	492.2	490.8	490.7	489.2	488.7	488.1	486.2	482.6	480.5	480.9
5°	537.7	542.4	539.8	539.4	535.3	531.2	528.5	522.5	516.1	511.8	508.3
7.5°	591.9	594.6	592.9	590.3	583.7	579.9	573.8	565.9	554.4	545.7	537.7
10°	628.8	631.1	630.3	625.4	620.6	610.6	605.0	594.0	579.5	568.1	557.4
12.5°	665.1	667.5	660.9	661.2	651.9	644.0	635.2	621.2	604.6	589.9	576.5
15°	712.4	709.4	709.4	705.7	695.4	684.5	675.3	660.7	639.7	622.1	603.5
17.5°	749.5	750.5	749.0	740.1	732.1	720.8	703.9	686.9	667.4	643.7	624.8
20°	771.7	771.7	770.0	764.0	753.5	741.5	723.3	704.7	680.0	656.2	634.9
22.5°	780.7	781.3	779.3	774.4	764.9	753.2	737.7	718.8	693.3	666.5	640.1
25°	768.3	771.9	772.2	771.0	768.1	761.0	747.7	728.4	705.5	676.4	647.9
27.5°	705.4	709.9	713.8	720.3	729.0	733.4	734.0	724.2	704.3	676.3	647.6
30°	642.7	646.4	658.6	674.5	686.9	698.2	708.0	710.6	699.3	674.2	644.0
32.5°	573.1	578.2	590.4	607.5	628.1	647.2	669.1	680.2	679.9	664.9	637.0
35°	473.2	477.0	488.2	506.2	530.9	559.3	594.0	620.9	639.3	638.0	620.9
37.5°	381.7	385.9	397.2	412.2	436.2	471.2	504.8	542.0	575.9	595.0	589.3
40°	331.8	332.0	343.1	358.5	381.0	411.5	448.1	489.3	527.2	558.2	564.1
42.5°	292.6	292.6	299.9	316.5	332.6	361.4	396.3	437.3	481.6	517.4	533.2
45°	241.9	243.5	249.5	259.4	272.2	296.6	324.6	362.6	412.3	454.6	481.1
47.5°	204.8	207.3	211.1	219.2	229.3	245.6	268.7	302.9	343.3	389.9	427.5
50°	185.6	186.0	190.8	195.4	204.1	217.1	237.3	265.9	303.0	347.8	389.6
52.5°	169.1	169.1	172.0	177.7	184.8	194.9	211.3	237.2	270.1	310.3	353.5
55°	144.3	145.3	147.6	152.0	157.5	164.6	177.5	197.0	222.9	257.2	296.4
57.5°	125.6	126.0	127.8	129.7	134.7	139.9	149.6	163.1	184.9	213.0	249.5
60°	113.2	113.4	114.0	116.8	120.7	125.6	132.2	143.6	162.0	187.7	216.6
62.5°	101.2	101.6	102.4	104.5	107.6	110.9	117.8	127.0	142.2	164.1	190.1
65°	84.4	84.5	85.9	86.6	89.0	92.1	97.1	103.3	113.8	132.2	151.9
67.5°	70.5	70.5	70.6	71.6	73.3	75.3	78.3	83.3	91.2	102.4	119.8
70°	61.5	61.5	61.9	62.4	63.4	65.0	66.8	70.5	76.3	85.5	98.8
72.5°	53.1	53.2	53.6	53.7	54.2	55.6	56.9	59.3	63.5	70.5	81.3
75°	39.0	39.5	40.5	41.3	42.2	42.0	43.3	44.8	46.1	50.2	56.4
77.5°	29.0	28.8	28.8	29.5	29.5	29.8	30.7	31.8	32.9	34.8	37.0
80°	22.1	22.1	22.7	22.9	22.7	22.9	23.8	24.4	24.7	25.5	27.6
82.5°	16.7	17.0	16.9	17.0	17.1	17.3	18.1	18.2	18.6	18.9	19.7
85°	9.3	9.6	9.7	9.3	9.3	9.3	9.7	9.9	10.3	10.1	10.5
87.5°	5.9	5.8	6.0	5.9	5.9	5.8	5.8	5.9	5.5	5.9	5.5
90°	13.0	13.0	13.6	13.0	12.4	12.4	11.8	11.2	10.5	11.2	9.9
92.5°	47.7	47.7	49.8	53.2	60.4	72.9	91.6	121.7	163.7	196.5	172.0
95°	151.1	159.2	170.3	189.6	219.9	280.0	363.0	459.0	519.1	504.9	381.0
97.5°	404.0	416.8	435.5	472.8	517.2	581.9	642.5	678.1	652.1	531.7	356.6
100°	568.0	573.0	591.5	629.3	683.3	729.0	759.4	747.0	656.6	498.0	323.4
102.5°	710.7	714.7	734.3	761.7	794.7	813.8	805.0	743.5	619.4	455.9	301.0
105°	871.6	875.3	883.9	888.9	887.6	862.2	800.9	693.8	551.9	406.3	281.9
107.5°	931.2	929.6	923.4	909.3	878.7	823.5	737.1	623.1	497.4	378.6	278.4
110°	932.2	926.7	915.5	889.5	845.5	777.4	687.5	580.4	470.2	369.2	279.3



TEST NUMBER: P332879-927

CATALOG NUMBER: SA4XXRDIP-C350D810U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	903.0	894.0	878.4	846.8	796.9	728.8	644.0	549.2	454.8	364.7	282.3
115°	836.9	831.9	812.1	774.9	726.0	666.5	594.1	517.8	440.4	362.3	288.0
117.5°	769.8	766.0	745.9	714.7	673.0	622.5	565.5	502.5	434.0	361.7	294.1
120°	732.1	725.3	709.2	682.0	646.7	602.7	553.2	495.5	430.5	361.7	298.6
122.5°	702.4	695.6	682.0	658.7	628.8	590.3	545.2	489.6	426.5	361.2	303.0
125°	667.7	664.0	652.3	634.3	609.5	575.4	532.7	479.4	419.9	360.5	309.7
127.5°	647.5	643.7	633.8	617.8	592.9	560.5	517.9	467.1	411.1	359.2	315.1
130°	635.6	631.8	621.9	606.4	581.0	548.2	506.0	457.2	405.8	358.6	319.0
132.5°	622.2	618.5	609.0	591.5	566.6	533.9	492.7	446.7	400.8	358.1	322.5
135°	597.1	593.4	583.5	566.2	541.4	510.4	472.6	432.4	393.3	357.4	327.6
137.5°	566.2	561.7	553.5	536.4	513.3	485.3	453.4	419.4	386.9	357.3	330.7
140°	543.8	538.9	530.2	516.6	495.0	468.9	441.0	411.9	383.4	356.8	333.3
142.5°	520.1	516.6	508.9	496.3	477.1	454.6	430.6	405.0	380.5	356.8	335.3
145°	487.5	484.4	478.2	467.7	452.2	434.8	416.3	395.2	375.3	355.5	336.4
147.5°	458.6	457.5	452.8	443.8	432.4	418.7	403.9	387.1	370.8	353.3	337.0
150°	442.3	441.6	437.9	429.9	419.9	408.8	396.4	382.1	367.3	351.8	337.0
152.5°	427.4	426.7	424.5	418.0	409.6	400.4	389.0	376.8	363.4	349.4	336.0
155°	408.2	408.2	406.3	401.4	395.2	387.8	378.5	368.5	357.4	345.6	334.5
157.5°	391.3	391.3	390.2	386.5	381.8	375.9	368.0	359.7	351.3	341.8	332.9
160°	381.0	381.0	380.3	376.6	372.9	368.0	361.2	354.3	346.9	338.8	331.4
162.5°	371.1	371.5	370.9	367.2	364.5	360.0	354.7	348.9	342.9	335.9	329.9
165°	356.2	356.8	357.4	354.9	352.4	349.4	345.0	341.3	336.4	331.4	327.1
167.5°	344.4	344.9	345.0	343.4	342.1	340.3	336.8	334.0	330.4	326.9	324.1
170°	337.0	337.0	337.5	337.0	335.7	333.9	331.4	329.5	326.5	323.9	322.1
172.5°	329.5	330.5	331.1	330.5	329.8	328.4	326.9	325.6	323.0	321.0	320.1
175°	320.8	322.1	323.4	322.1	322.1	322.1	320.8	320.3	319.0	317.7	317.7
177.5°	315.8	316.8	317.7	317.3	317.7	317.3	317.3	316.8	316.2	315.8	315.8
180°	315.3	315.3	315.3	315.3	315.3	315.3	315.3	315.3	315.3	315.3	315.3



TEST NUMBER: P332879-927

CATALOG NUMBER: SA4XXRDIP-C350D810U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3
2.5°	479.4	477.4	476.3	473.9	471.0	469.5	468.2	466.2	463.7	461.0	459.1
5°	503.7	499.2	493.6	486.9	480.9	475.1	470.0	464.9	459.1	453.1	447.2
7.5°	528.7	519.9	510.3	499.2	488.5	478.7	469.7	461.1	451.4	442.6	434.7
10°	546.1	534.2	520.9	506.8	492.7	480.5	468.5	457.6	445.7	435.0	426.0
12.5°	560.2	546.1	530.1	512.6	495.7	480.9	467.1	453.0	439.3	427.8	415.7
15°	583.6	564.4	542.8	521.7	499.9	479.7	461.2	444.7	429.1	412.8	401.4
17.5°	599.8	576.8	550.6	525.4	499.5	475.8	454.4	434.7	416.8	400.1	386.5
20°	609.3	584.0	554.9	526.2	497.2	471.9	448.9	427.1	408.5	390.5	376.4
22.5°	614.7	586.7	554.9	524.9	494.8	467.4	442.1	419.5	399.3	381.2	365.7
25°	616.5	586.5	554.1	519.5	486.6	457.5	431.2	406.6	384.1	366.1	349.7
27.5°	614.0	578.7	545.5	510.1	476.0	445.4	417.9	392.1	369.6	350.2	333.3
30°	610.5	572.6	536.9	500.2	465.7	436.3	407.2	382.5	359.0	339.0	321.9
32.5°	602.6	565.1	526.7	489.1	454.2	423.8	396.2	371.4	348.4	327.9	309.7
35°	587.2	549.1	507.6	468.9	434.6	403.1	377.2	353.2	331.3	309.3	290.3
37.5°	566.8	528.0	486.6	444.3	409.9	380.2	356.5	333.9	312.5	292.5	271.3
40°	547.6	512.2	469.4	427.5	392.2	363.5	341.6	321.2	299.6	279.7	258.6
42.5°	524.4	494.2	451.0	408.8	374.1	346.4	326.0	306.0	286.4	267.1	245.0
45°	485.6	462.7	422.2	381.8	346.7	319.2	300.6	282.9	265.7	247.3	226.5
47.5°	441.1	425.6	390.7	349.2	316.8	292.2	274.0	259.6	245.0	226.6	208.4
50°	410.2	400.3	366.5	328.7	297.7	275.0	256.5	243.0	230.8	213.2	196.9
52.5°	377.2	371.9	343.4	307.2	277.3	255.1	239.2	227.1	214.8	200.1	184.9
55°	326.9	329.8	305.6	274.3	246.1	227.4	213.0	202.9	192.3	180.0	168.2
57.5°	275.6	285.9	269.7	242.2	215.8	198.4	187.6	179.1	170.2	160.0	149.9
60°	244.9	253.5	244.3	220.1	197.0	180.9	170.8	164.2	155.4	146.1	138.4
62.5°	214.8	224.1	218.6	199.1	177.7	163.8	154.9	148.8	142.2	134.0	126.0
65°	177.2	183.2	180.5	167.1	151.9	140.1	131.8	127.3	121.3	115.3	108.2
67.5°	135.7	147.3	145.8	138.6	125.5	116.2	110.8	106.9	101.4	97.0	92.1
70°	111.5	122.2	122.1	116.2	109.1	100.5	96.7	93.4	88.5	84.2	80.2
72.5°	91.3	101.1	102.6	98.1	93.2	86.7	83.1	80.8	76.0	73.1	69.9
75°	63.9	71.1	73.0	73.0	70.7	67.3	64.1	62.6	59.3	56.6	54.7
77.5°	41.9	46.4	49.4	50.0	50.4	49.2	46.6	45.6	42.9	42.1	40.2
80°	29.6	32.6	36.0	37.2	38.0	37.7	36.6	35.8	33.4	32.4	31.7
82.5°	20.4	22.1	24.9	27.4	27.1	28.1	27.1	26.5	24.6	24.3	23.6
85°	10.7	10.9	11.2	12.9	13.9	14.3	14.4	14.1	13.5	13.5	12.2
87.5°	5.3	5.1	4.8	4.8	4.8	5.2	5.3	5.2	5.0	4.9	4.6
90°	8.6	8.6	5.0	5.0	4.4	3.7	1.8	0.6	1.8	3.7	4.4
92.5°	125.1	77.1	45.6	32.7	23.7	16.1	10.3	7.1	10.3	16.1	23.7
95°	232.9	131.3	77.4	51.4	36.5	28.5	22.3	20.4	22.3	28.5	36.5
97.5°	209.4	125.5	84.0	62.2	49.4	42.0	36.7	36.7	36.7	42.0	49.4
100°	197.0	127.0	90.5	70.6	58.9	51.4	47.1	47.1	47.1	51.4	58.9
102.5°	193.5	131.9	98.9	80.0	68.8	61.8	58.0	57.0	58.0	61.8	68.8
105°	195.1	143.7	114.0	96.0	84.8	77.4	74.3	72.5	74.3	77.4	84.8
107.5°	204.3	157.5	130.2	112.5	101.8	93.9	90.8	89.6	90.8	93.9	101.8
110°	211.2	167.9	140.6	123.9	112.7	105.3	102.2	101.0	102.2	105.3	112.7



TEST NUMBER: P332879-927

CATALOG NUMBER: SA4XXRDIP-C350D810U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	218.6	177.8	151.5	134.8	123.7	116.7	113.1	111.9	113.1	116.7	123.7
115°	230.4	193.3	168.5	151.8	140.0	133.8	129.4	127.6	129.4	133.8	140.0
117.5°	242.4	208.3	184.7	167.4	156.4	149.6	145.7	143.9	145.7	149.6	156.4
120°	250.9	218.6	195.1	177.8	167.2	160.4	156.1	154.9	156.1	160.4	167.2
122.5°	258.8	228.5	205.0	188.1	176.7	170.3	166.0	164.8	166.0	170.3	176.7
125°	270.7	242.2	219.9	202.6	190.8	183.9	180.2	177.8	180.2	183.9	190.8
127.5°	281.0	254.8	233.3	215.8	203.5	195.7	191.3	189.3	191.3	195.7	203.5
130°	287.4	263.2	242.2	224.3	212.5	203.2	198.2	195.7	198.2	203.2	212.5
132.5°	293.8	270.2	249.1	232.2	219.4	210.6	204.1	202.2	204.1	210.6	219.4
135°	302.3	280.0	259.5	243.4	230.4	219.9	213.7	211.2	213.7	219.9	230.4
137.5°	308.2	287.4	268.3	252.9	239.5	229.4	222.6	220.3	222.6	229.4	239.5
140°	312.2	292.4	273.8	258.9	245.9	235.4	228.5	226.7	228.5	235.4	245.9
142.5°	315.1	296.8	278.8	264.4	251.8	241.9	235.5	233.6	235.5	241.9	251.8
145°	318.4	301.7	285.6	272.0	260.2	251.5	245.3	243.4	245.3	251.5	260.2
147.5°	321.2	306.7	291.5	279.2	269.4	260.5	255.1	254.4	255.1	260.5	269.4
150°	322.7	309.1	295.5	283.7	274.4	267.0	262.1	261.4	262.1	267.0	274.4
152.5°	323.7	311.1	299.0	288.2	279.9	272.9	268.0	267.8	268.0	272.9	279.9
155°	324.6	314.0	303.5	294.2	287.4	281.2	277.5	276.9	277.5	281.2	287.4
157.5°	324.6	316.2	307.2	299.9	294.0	289.1	285.7	285.7	285.7	289.1	294.0
160°	324.6	317.1	309.7	302.9	297.9	293.6	291.1	291.1	291.1	293.6	297.9
162.5°	324.6	318.1	311.2	305.9	301.4	297.5	295.6	296.1	295.6	297.5	301.4
165°	323.4	318.4	312.8	309.1	306.0	302.9	301.7	301.7	301.7	302.9	306.0
167.5°	321.9	318.3	314.2	311.3	309.6	307.2	306.7	307.2	306.7	307.2	309.6
170°	320.8	317.7	314.7	312.8	311.6	309.7	309.1	309.7	309.1	309.7	311.6
172.5°	319.9	317.3	315.1	313.8	313.1	311.7	311.6	312.2	311.6	311.7	313.1
175°	318.4	316.6	315.3	315.3	314.7	314.0	314.0	314.7	314.0	314.0	314.7
177.5°	316.8	315.8	315.3	315.3	315.3	314.8	315.3	315.8	315.3	314.8	315.3
180°	315.3	315.3	315.3	315.3	315.3	315.3	315.3	315.3	315.3	315.3	315.3



TEST NUMBER: P332879-927

CATALOG NUMBER: SA4XXRDIP-C350D810U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3
2.5°	456.9	455.4	453.5	451.2	448.5	446.2	445.0	446.0	446.5	445.2	445.0
5°	443.0	438.3	434.6	429.0	424.5	420.7	418.1	416.9	417.3	414.3	413.6
7.5°	427.4	421.8	415.7	409.0	402.8	397.3	394.4	392.8	389.6	388.2	386.0
10°	417.3	409.9	403.9	395.9	388.8	382.3	379.1	376.4	373.3	371.8	368.6
12.5°	407.0	398.3	391.7	383.5	376.2	368.4	365.3	360.4	355.5	352.3	348.2
15°	392.4	381.9	373.8	364.1	355.5	346.5	338.4	329.4	326.1	318.9	314.8
17.5°	375.3	364.7	354.7	341.7	328.4	317.1	308.6	299.9	294.8	290.3	288.1
20°	364.1	354.3	340.5	325.3	310.5	298.1	291.1	285.5	279.9	276.7	274.5
22.5°	353.5	341.0	324.9	308.5	293.7	284.0	278.1	272.4	267.8	264.7	261.7
25°	335.6	319.2	302.2	283.4	273.4	264.9	258.6	253.8	251.0	247.1	245.6
27.5°	317.3	297.5	278.7	266.1	255.6	247.8	242.2	238.8	235.2	232.7	230.7
30°	303.2	283.1	266.3	254.2	243.5	237.2	232.7	228.5	225.7	223.6	222.2
32.5°	289.2	269.2	255.0	242.1	233.6	227.4	222.6	219.5	217.3	214.7	213.7
35°	269.0	251.2	238.8	227.2	218.6	213.0	209.2	206.0	204.1	203.4	202.9
37.5°	249.6	235.0	221.7	212.2	204.5	200.1	195.7	194.1	192.8	191.5	192.1
40°	237.3	223.6	211.8	201.8	195.5	190.7	188.1	186.2	185.1	185.1	185.1
42.5°	226.7	213.3	201.8	192.7	186.6	182.4	179.5	177.9	177.5	177.4	178.3
45°	210.2	197.8	186.2	178.6	173.4	169.3	167.6	166.3	166.3	167.1	167.2
47.5°	193.8	182.2	172.9	164.5	159.6	157.1	155.6	155.0	155.0	155.7	156.6
50°	183.7	172.3	163.1	155.6	151.1	148.7	147.3	146.9	147.3	147.3	148.7
52.5°	172.8	162.6	153.5	147.2	142.1	139.8	139.1	138.6	138.8	139.4	140.0
55°	156.8	147.6	138.9	132.9	129.2	127.7	126.0	126.2	125.8	126.2	126.2
57.5°	140.6	132.4	124.4	119.6	116.3	114.2	112.3	112.8	112.3	112.2	111.9
60°	130.3	121.3	114.9	110.6	106.9	105.0	103.3	103.7	103.1	102.7	102.0
62.5°	119.1	111.5	105.4	101.3	98.3	96.2	94.4	94.1	92.8	91.5	89.8
65°	102.7	96.6	91.1	87.2	84.4	82.7	81.4	80.2	77.4	74.5	73.0
67.5°	86.9	82.4	77.3	74.0	71.7	69.6	67.0	65.1	62.5	60.8	59.9
70°	76.7	72.4	68.0	64.9	62.4	60.4	57.6	56.2	54.3	53.6	52.7
72.5°	66.9	62.9	58.9	56.0	53.5	51.8	49.6	48.3	47.5	47.1	46.3
75°	52.1	49.0	45.9	43.3	41.3	40.1	39.2	38.3	37.9	36.2	35.3
77.5°	38.0	35.9	34.1	32.2	30.7	29.9	28.1	27.1	26.5	25.7	25.4
80°	29.6	28.1	26.2	25.1	23.1	22.3	21.5	21.4	21.2	21.0	20.8
82.5°	22.3	20.8	18.9	18.2	17.7	17.2	16.8	16.6	16.4	16.5	16.5
85°	11.2	10.5	10.5	10.3	10.1	9.9	9.7	9.7	9.6	9.7	9.6
87.5°	4.8	4.6	5.3	5.1	5.5	5.7	5.4	5.5	5.8	5.6	5.6
90°	5.0	5.0	8.6	8.6	9.9	11.2	10.5	11.2	11.8	12.4	12.4
92.5°	32.7	45.6	77.1	125.1	172.0	196.5	163.7	121.7	91.6	72.9	60.4
95°	51.4	77.4	131.3	232.9	381.0	504.9	519.1	459.0	363.0	280.0	219.9
97.5°	62.2	84.0	125.5	209.4	356.6	531.7	652.1	678.1	642.5	581.9	517.2
100°	70.6	90.5	127.0	197.0	323.4	498.0	656.6	747.0	759.4	729.0	683.3
102.5°	80.0	98.9	131.9	193.5	301.0	455.9	619.4	743.5	805.0	813.8	794.7
105°	96.0	114.0	143.7	195.1	281.9	406.3	551.9	693.8	800.9	862.2	887.6
107.5°	112.5	130.2	157.5	204.3	278.4	378.6	497.4	623.1	737.1	823.5	878.7
110°	123.9	140.6	167.9	211.2	279.3	369.2	470.2	580.4	687.5	777.4	845.5



TEST NUMBER: P332879-927

CATALOG NUMBER: SA4XXRDIP-C350D810U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	134.8	151.5	177.8	218.6	282.3	364.7	454.8	549.2	644.0	728.8	796.9
115°	151.8	168.5	193.3	230.4	288.0	362.3	440.4	517.8	594.1	666.5	726.0
117.5°	167.4	184.7	208.3	242.4	294.1	361.7	434.0	502.5	565.5	622.5	673.0
120°	177.8	195.1	218.6	250.9	298.6	361.7	430.5	495.5	553.2	602.7	646.7
122.5°	188.1	205.0	228.5	258.8	303.0	361.2	426.5	489.6	545.2	590.3	628.8
125°	202.6	219.9	242.2	270.7	309.7	360.5	419.9	479.4	532.7	575.4	609.5
127.5°	215.8	233.3	254.8	281.0	315.1	359.2	411.1	467.1	517.9	560.5	592.9
130°	224.3	242.2	263.2	287.4	319.0	358.6	405.8	457.2	506.0	548.2	581.0
132.5°	232.2	249.1	270.2	293.8	322.5	358.1	400.8	446.7	492.7	533.9	566.6
135°	243.4	259.5	280.0	302.3	327.6	357.4	393.3	432.4	472.6	510.4	541.4
137.5°	252.9	268.3	287.4	308.2	330.7	357.3	386.9	419.4	453.4	485.3	513.3
140°	258.9	273.8	292.4	312.2	333.3	356.8	383.4	411.9	441.0	468.9	495.0
142.5°	264.4	278.8	296.8	315.1	335.3	356.8	380.5	405.0	430.6	454.6	477.1
145°	272.0	285.6	301.7	318.4	336.4	355.5	375.3	395.2	416.3	434.8	452.2
147.5°	279.2	291.5	306.7	321.2	337.0	353.3	370.8	387.1	403.9	418.7	432.4
150°	283.7	295.5	309.1	322.7	337.0	351.8	367.3	382.1	396.4	408.8	419.9
152.5°	288.2	299.0	311.1	323.7	336.0	349.4	363.4	376.8	389.0	400.4	409.6
155°	294.2	303.5	314.0	324.6	334.5	345.6	357.4	368.5	378.5	387.8	395.2
157.5°	299.9	307.2	316.2	324.6	332.9	341.8	351.3	359.7	368.0	375.9	381.8
160°	302.9	309.7	317.1	324.6	331.4	338.8	346.9	354.3	361.2	368.0	372.9
162.5°	305.9	311.2	318.1	324.6	329.9	335.9	342.9	348.9	354.7	360.0	364.5
165°	309.1	312.8	318.4	323.4	327.1	331.4	336.4	341.3	345.0	349.4	352.4
167.5°	311.3	314.2	318.3	321.9	324.1	326.9	330.4	334.0	336.8	340.3	342.1
170°	312.8	314.7	317.7	320.8	322.1	323.9	326.5	329.5	331.4	333.9	335.7
172.5°	313.8	315.1	317.3	319.9	320.1	321.0	323.0	325.6	326.9	328.4	329.8
175°	315.3	315.3	316.6	318.4	317.7	317.7	319.0	320.3	320.8	322.1	322.1
177.5°	315.3	315.3	315.8	316.8	315.8	315.8	316.2	316.8	317.3	317.3	317.7
180°	315.3	315.3	315.3	315.3	315.3	315.3	315.3	315.3	315.3	315.3	315.3



TEST NUMBER: P332879-927

CATALOG NUMBER: SA4XXRDIP-C350D810U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3
2.5°	444.2	444.5	443.5	443.1	443.5	444.5	444.2	445.0	445.2	446.5	446.0
5°	412.1	411.7	410.7	411.0	410.7	411.7	412.1	413.6	414.3	417.3	416.9
7.5°	384.6	383.2	383.6	382.1	383.6	383.2	384.6	386.0	388.2	389.6	392.8
10°	367.8	365.8	364.1	362.6	364.1	365.8	367.8	368.6	371.8	373.3	376.4
12.5°	344.9	343.1	340.9	341.3	340.9	343.1	344.9	348.2	352.3	355.5	360.4
15°	312.4	309.5	305.1	305.6	305.1	309.5	312.4	314.8	318.9	326.1	329.4
17.5°	284.8	284.8	282.7	283.3	282.7	284.8	284.8	288.1	290.3	294.8	299.9
20°	270.5	269.3	269.4	268.9	269.4	269.3	270.5	274.5	276.7	279.9	285.5
22.5°	260.6	259.0	257.7	256.6	257.7	259.0	260.6	261.7	264.7	267.8	272.4
25°	243.9	242.8	241.1	240.7	241.1	242.8	243.9	245.6	247.1	251.0	253.8
27.5°	229.2	229.0	228.3	227.4	228.3	229.0	229.2	230.7	232.7	235.2	238.8
30°	220.7	220.3	219.9	219.4	219.9	220.3	220.7	222.2	223.6	225.7	228.5
32.5°	213.0	212.8	212.4	212.5	212.4	212.8	213.0	213.7	214.7	217.3	219.5
35°	202.1	201.9	201.5	201.4	201.5	201.9	202.1	202.9	203.4	204.1	206.0
37.5°	191.9	192.4	192.2	192.1	192.2	192.4	191.9	192.1	191.5	192.8	194.1
40°	184.9	185.1	185.4	185.2	185.4	185.1	184.9	185.1	185.1	185.1	186.2
42.5°	179.0	179.0	179.6	179.0	179.6	179.0	179.0	178.3	177.4	177.5	177.9
45°	168.6	169.7	169.4	169.4	169.4	169.7	168.6	167.2	167.1	166.3	166.3
47.5°	157.1	158.1	158.4	158.3	158.4	158.1	157.1	156.6	155.7	155.0	155.0
50°	149.6	149.2	149.8	149.6	149.8	149.2	149.6	148.7	147.3	147.3	146.9
52.5°	140.5	140.5	140.5	140.3	140.5	140.5	140.5	140.0	139.4	138.8	138.6
55°	126.4	126.6	126.2	126.4	126.2	126.6	126.4	126.2	126.2	125.8	126.2
57.5°	111.1	110.2	110.5	110.1	110.5	110.2	111.1	111.9	112.2	112.3	112.8
60°	100.1	98.6	98.2	97.5	98.2	98.6	100.1	102.0	102.7	103.1	103.7
62.5°	87.9	86.7	85.5	86.1	85.5	86.7	87.9	89.8	91.5	92.8	94.1
65°	71.5	70.7	70.1	70.9	70.1	70.7	71.5	73.0	74.5	77.4	80.2
67.5°	59.1	58.7	58.7	58.4	58.7	58.7	59.1	59.9	60.8	62.5	65.1
70°	52.7	52.1	52.1	51.7	52.1	52.1	52.7	52.7	53.6	54.3	56.2
72.5°	46.1	45.6	45.7	45.5	45.7	45.6	46.1	46.3	47.1	47.5	48.3
75°	34.1	33.2	33.2	33.4	33.2	33.2	34.1	35.3	36.2	37.9	38.3
77.5°	25.4	25.3	25.5	25.2	25.5	25.3	25.4	25.4	25.7	26.5	27.1
80°	20.8	20.6	20.4	21.0	20.4	20.6	20.8	20.8	21.0	21.2	21.4
82.5°	16.2	16.2	16.1	16.8	16.1	16.2	16.2	16.5	16.5	16.4	16.6
85°	9.7	9.3	9.7	9.3	9.7	9.3	9.7	9.6	9.7	9.6	9.7
87.5°	6.0	6.0	5.8	5.9	5.8	6.0	6.0	5.6	5.6	5.8	5.5
90°	13.0	13.6	13.0	13.0	13.0	13.6	13.0	12.4	12.4	11.8	11.2
92.5°	53.2	49.8	47.7	47.7	47.7	49.8	53.2	60.4	72.9	91.6	121.7
95°	189.6	170.3	159.2	151.1	159.2	170.3	189.6	219.9	280.0	363.0	459.0
97.5°	472.8	435.5	416.8	404.0	416.8	435.5	472.8	517.2	581.9	642.5	678.1
100°	629.3	591.5	573.0	568.0	573.0	591.5	629.3	683.3	729.0	759.4	747.0
102.5°	761.7	734.3	714.7	710.7	714.7	734.3	761.7	794.7	813.8	805.0	743.5
105°	888.9	883.9	875.3	871.6	875.3	883.9	888.9	887.6	862.2	800.9	693.8
107.5°	909.3	923.4	929.6	931.2	929.6	923.4	909.3	878.7	823.5	737.1	623.1
110°	889.5	915.5	926.7	932.2	926.7	915.5	889.5	845.5	777.4	687.5	580.4



TEST NUMBER: P332879-927

CATALOG NUMBER: SA4XXRDIP-C350D810U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	846.8	878.4	894.0	903.0	894.0	878.4	846.8	796.9	728.8	644.0	549.2
115°	774.9	812.1	831.9	836.9	831.9	812.1	774.9	726.0	666.5	594.1	517.8
117.5°	714.7	745.9	766.0	769.8	766.0	745.9	714.7	673.0	622.5	565.5	502.5
120°	682.0	709.2	725.3	732.1	725.3	709.2	682.0	646.7	602.7	553.2	495.5
122.5°	658.7	682.0	695.6	702.4	695.6	682.0	658.7	628.8	590.3	545.2	489.6
125°	634.3	652.3	664.0	667.7	664.0	652.3	634.3	609.5	575.4	532.7	479.4
127.5°	617.8	633.8	643.7	647.5	643.7	633.8	617.8	592.9	560.5	517.9	467.1
130°	606.4	621.9	631.8	635.6	631.8	621.9	606.4	581.0	548.2	506.0	457.2
132.5°	591.5	609.0	618.5	622.2	618.5	609.0	591.5	566.6	533.9	492.7	446.7
135°	566.2	583.5	593.4	597.1	593.4	583.5	566.2	541.4	510.4	472.6	432.4
137.5°	536.4	553.5	561.7	566.2	561.7	553.5	536.4	513.3	485.3	453.4	419.4
140°	516.6	530.2	538.9	543.8	538.9	530.2	516.6	495.0	468.9	441.0	411.9
142.5°	496.3	508.9	516.6	520.1	516.6	508.9	496.3	477.1	454.6	430.6	405.0
145°	467.7	478.2	484.4	487.5	484.4	478.2	467.7	452.2	434.8	416.3	395.2
147.5°	443.8	452.8	457.5	458.6	457.5	452.8	443.8	432.4	418.7	403.9	387.1
150°	429.9	437.9	441.6	442.3	441.6	437.9	429.9	419.9	408.8	396.4	382.1
152.5°	418.0	424.5	426.7	427.4	426.7	424.5	418.0	409.6	400.4	389.0	376.8
155°	401.4	406.3	408.2	408.2	408.2	406.3	401.4	395.2	387.8	378.5	368.5
157.5°	386.5	390.2	391.3	391.3	391.3	390.2	386.5	381.8	375.9	368.0	359.7
160°	376.6	380.3	381.0	381.0	381.0	380.3	376.6	372.9	368.0	361.2	354.3
162.5°	367.2	370.9	371.5	371.1	371.5	370.9	367.2	364.5	360.0	354.7	348.9
165°	354.9	357.4	356.8	356.2	356.8	357.4	354.9	352.4	349.4	345.0	341.3
167.5°	343.4	345.0	344.9	344.4	344.9	345.0	343.4	342.1	340.3	336.8	334.0
170°	337.0	337.5	337.0	337.0	337.0	337.5	337.0	335.7	333.9	331.4	329.5
172.5°	330.5	331.1	330.5	329.5	330.5	331.1	330.5	329.8	328.4	326.9	325.6
175°	322.1	323.4	322.1	320.8	322.1	323.4	322.1	322.1	322.1	320.8	320.3
177.5°	317.3	317.7	316.8	315.8	316.8	317.7	317.3	317.7	317.3	317.3	316.8
180°	315.3	315.3	315.3	315.3	315.3	315.3	315.3	315.3	315.3	315.3	315.3



TEST NUMBER: P332879-927

CATALOG NUMBER: SA4XXRDIP-C350D810U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3
2.5°	445.0	446.2	448.5	451.2	453.5	455.4	456.9	459.1	461.0	463.7	466.2
5°	418.1	420.7	424.5	429.0	434.6	438.3	443.0	447.2	453.1	459.1	464.9
7.5°	394.4	397.3	402.8	409.0	415.7	421.8	427.4	434.7	442.6	451.4	461.1
10°	379.1	382.3	388.8	395.9	403.9	409.9	417.3	426.0	435.0	445.7	457.6
12.5°	365.3	368.4	376.2	383.5	391.7	398.3	407.0	415.7	427.8	439.3	453.0
15°	338.4	346.5	355.5	364.1	373.8	381.9	392.4	401.4	412.8	429.1	444.7
17.5°	308.6	317.1	328.4	341.7	354.7	364.7	375.3	386.5	400.1	416.8	434.7
20°	291.1	298.1	310.5	325.3	340.5	354.3	364.1	376.4	390.5	408.5	427.1
22.5°	278.1	284.0	293.7	308.5	324.9	341.0	353.5	365.7	381.2	399.3	419.5
25°	258.6	264.9	273.4	283.4	302.2	319.2	335.6	349.7	366.1	384.1	406.6
27.5°	242.2	247.8	255.6	266.1	278.7	297.5	317.3	333.3	350.2	369.6	392.1
30°	232.7	237.2	243.5	254.2	266.3	283.1	303.2	321.9	339.0	359.0	382.5
32.5°	222.6	227.4	233.6	242.1	255.0	269.2	289.2	309.7	327.9	348.4	371.4
35°	209.2	213.0	218.6	227.2	238.8	251.2	269.0	290.3	309.3	331.3	353.2
37.5°	195.7	200.1	204.5	212.2	221.7	235.0	249.6	271.3	292.5	312.5	333.9
40°	188.1	190.7	195.5	201.8	211.8	223.6	237.3	258.6	279.7	299.6	321.2
42.5°	179.5	182.4	186.6	192.7	201.8	213.3	226.7	245.0	267.1	286.4	306.0
45°	167.6	169.3	173.4	178.6	186.2	197.8	210.2	226.5	247.3	265.7	282.9
47.5°	155.6	157.1	159.6	164.5	172.9	182.2	193.8	208.4	226.6	245.0	259.6
50°	147.3	148.7	151.1	155.6	163.1	172.3	183.7	196.9	213.2	230.8	243.0
52.5°	139.1	139.8	142.1	147.2	153.5	162.6	172.8	184.9	200.1	214.8	227.1
55°	126.0	127.7	129.2	132.9	138.9	147.6	156.8	168.2	180.0	192.3	202.9
57.5°	112.3	114.2	116.3	119.6	124.4	132.4	140.6	149.9	160.0	170.2	179.1
60°	103.3	105.0	106.9	110.6	114.9	121.3	130.3	138.4	146.1	155.4	164.2
62.5°	94.4	96.2	98.3	101.3	105.4	111.5	119.1	126.0	134.0	142.2	148.8
65°	81.4	82.7	84.4	87.2	91.1	96.6	102.7	108.2	115.3	121.3	127.3
67.5°	67.0	69.6	71.7	74.0	77.3	82.4	86.9	92.1	97.0	101.4	106.9
70°	57.6	60.4	62.4	64.9	68.0	72.4	76.7	80.2	84.2	88.5	93.4
72.5°	49.6	51.8	53.5	56.0	58.9	62.9	66.9	69.9	73.1	76.0	80.8
75°	39.2	40.1	41.3	43.3	45.9	49.0	52.1	54.7	56.6	59.3	62.6
77.5°	28.1	29.9	30.7	32.2	34.1	35.9	38.0	40.2	42.1	42.9	45.6
80°	21.5	22.3	23.1	25.1	26.2	28.1	29.6	31.7	32.4	33.4	35.8
82.5°	16.8	17.2	17.7	18.2	18.9	20.8	22.3	23.6	24.3	24.6	26.5
85°	9.7	9.9	10.1	10.3	10.5	10.5	11.2	12.2	13.5	13.5	14.1
87.5°	5.4	5.7	5.5	5.1	5.3	4.6	4.8	4.6	4.9	5.0	5.2
90°	10.5	11.2	9.9	8.6	8.6	5.0	5.0	4.4	3.7	1.8	0.6
92.5°	163.7	196.5	172.0	125.1	77.1	45.6	32.7	23.7	16.1	10.3	7.1
95°	519.1	504.9	381.0	232.9	131.3	77.4	51.4	36.5	28.5	22.3	20.4
97.5°	652.1	531.7	356.6	209.4	125.5	84.0	62.2	49.4	42.0	36.7	36.7
100°	656.6	498.0	323.4	197.0	127.0	90.5	70.6	58.9	51.4	47.1	47.1
102.5°	619.4	455.9	301.0	193.5	131.9	98.9	80.0	68.8	61.8	58.0	57.0
105°	551.9	406.3	281.9	195.1	143.7	114.0	96.0	84.8	77.4	74.3	72.5
107.5°	497.4	378.6	278.4	204.3	157.5	130.2	112.5	101.8	93.9	90.8	89.6
110°	470.2	369.2	279.3	211.2	167.9	140.6	123.9	112.7	105.3	102.2	101.0



TEST NUMBER: P332879-927

CATALOG NUMBER: SA4XXRDIP-C350D810U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	454.8	364.7	282.3	218.6	177.8	151.5	134.8	123.7	116.7	113.1	111.9
115°	440.4	362.3	288.0	230.4	193.3	168.5	151.8	140.0	133.8	129.4	127.6
117.5°	434.0	361.7	294.1	242.4	208.3	184.7	167.4	156.4	149.6	145.7	143.9
120°	430.5	361.7	298.6	250.9	218.6	195.1	177.8	167.2	160.4	156.1	154.9
122.5°	426.5	361.2	303.0	258.8	228.5	205.0	188.1	176.7	170.3	166.0	164.8
125°	419.9	360.5	309.7	270.7	242.2	219.9	202.6	190.8	183.9	180.2	177.8
127.5°	411.1	359.2	315.1	281.0	254.8	233.3	215.8	203.5	195.7	191.3	189.3
130°	405.8	358.6	319.0	287.4	263.2	242.2	224.3	212.5	203.2	198.2	195.7
132.5°	400.8	358.1	322.5	293.8	270.2	249.1	232.2	219.4	210.6	204.1	202.2
135°	393.3	357.4	327.6	302.3	280.0	259.5	243.4	230.4	219.9	213.7	211.2
137.5°	386.9	357.3	330.7	308.2	287.4	268.3	252.9	239.5	229.4	222.6	220.3
140°	383.4	356.8	333.3	312.2	292.4	273.8	258.9	245.9	235.4	228.5	226.7
142.5°	380.5	356.8	335.3	315.1	296.8	278.8	264.4	251.8	241.9	235.5	233.6
145°	375.3	355.5	336.4	318.4	301.7	285.6	272.0	260.2	251.5	245.3	243.4
147.5°	370.8	353.3	337.0	321.2	306.7	291.5	279.2	269.4	260.5	255.1	254.4
150°	367.3	351.8	337.0	322.7	309.1	295.5	283.7	274.4	267.0	262.1	261.4
152.5°	363.4	349.4	336.0	323.7	311.1	299.0	288.2	279.9	272.9	268.0	267.8
155°	357.4	345.6	334.5	324.6	314.0	303.5	294.2	287.4	281.2	277.5	276.9
157.5°	351.3	341.8	332.9	324.6	316.2	307.2	299.9	294.0	289.1	285.7	285.7
160°	346.9	338.8	331.4	324.6	317.1	309.7	302.9	297.9	293.6	291.1	291.1
162.5°	342.9	335.9	329.9	324.6	318.1	311.2	305.9	301.4	297.5	295.6	296.1
165°	336.4	331.4	327.1	323.4	318.4	312.8	309.1	306.0	302.9	301.7	301.7
167.5°	330.4	326.9	324.1	321.9	318.3	314.2	311.3	309.6	307.2	306.7	307.2
170°	326.5	323.9	322.1	320.8	317.7	314.7	312.8	311.6	309.7	309.1	309.7
172.5°	323.0	321.0	320.1	319.9	317.3	315.1	313.8	313.1	311.7	311.6	312.2
175°	319.0	317.7	317.7	318.4	316.6	315.3	315.3	314.7	314.0	314.0	314.7
177.5°	316.2	315.8	315.8	316.8	315.8	315.3	315.3	315.3	314.8	315.3	315.8
180°	315.3	315.3	315.3	315.3	315.3	315.3	315.3	315.3	315.3	315.3	315.3



TEST NUMBER: P332879-927

CATALOG NUMBER: SA4XXRDIP-C350D810U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3	465.3
2.5°	468.2	469.5	471.0	473.9	476.3	477.4	479.4	480.9	480.5	482.6	486.2
5°	470.0	475.1	480.9	486.9	493.6	499.2	503.7	508.3	511.8	516.1	522.5
7.5°	469.7	478.7	488.5	499.2	510.3	519.9	528.7	537.7	545.7	554.4	565.9
10°	468.5	480.5	492.7	506.8	520.9	534.2	546.1	557.4	568.1	579.5	594.0
12.5°	467.1	480.9	495.7	512.6	530.1	546.1	560.2	576.5	589.9	604.6	621.2
15°	461.2	479.7	499.9	521.7	542.8	564.4	583.6	603.5	622.1	639.7	660.7
17.5°	454.4	475.8	499.5	525.4	550.6	576.8	599.8	624.8	643.7	667.4	686.9
20°	448.9	471.9	497.2	526.2	554.9	584.0	609.3	634.9	656.2	680.0	704.7
22.5°	442.1	467.4	494.8	524.9	554.9	586.7	614.7	640.1	666.5	693.3	718.8
25°	431.2	457.5	486.6	519.5	554.1	586.5	616.5	647.9	676.4	705.5	728.4
27.5°	417.9	445.4	476.0	510.1	545.5	578.7	614.0	647.6	676.3	704.3	724.2
30°	407.2	436.3	465.7	500.2	536.9	572.6	610.5	644.0	674.2	699.3	710.6
32.5°	396.2	423.8	454.2	489.1	526.7	565.1	602.6	637.0	664.9	679.9	680.2
35°	377.2	403.1	434.6	468.9	507.6	549.1	587.2	620.9	638.0	639.3	620.9
37.5°	356.5	380.2	409.9	444.3	486.6	528.0	566.8	589.3	595.0	575.9	542.0
40°	341.6	363.5	392.2	427.5	469.4	512.2	547.6	564.1	558.2	527.2	489.3
42.5°	326.0	346.4	374.1	408.8	451.0	494.2	524.4	533.2	517.4	481.6	437.3
45°	300.6	319.2	346.7	381.8	422.2	462.7	485.6	481.1	454.6	412.3	362.6
47.5°	274.0	292.2	316.8	349.2	390.7	425.6	441.1	427.5	389.9	343.3	302.9
50°	256.5	275.0	297.7	328.7	366.5	400.3	410.2	389.6	347.8	303.0	265.9
52.5°	239.2	255.1	277.3	307.2	343.4	371.9	377.2	353.5	310.3	270.1	237.2
55°	213.0	227.4	246.1	274.3	305.6	329.8	326.9	296.4	257.2	222.9	197.0
57.5°	187.6	198.4	215.8	242.2	269.7	285.9	275.6	249.5	213.0	184.9	163.1
60°	170.8	180.9	197.0	220.1	244.3	253.5	244.9	216.6	187.7	162.0	143.6
62.5°	154.9	163.8	177.7	199.1	218.6	224.1	214.8	190.1	164.1	142.2	127.0
65°	131.8	140.1	151.9	167.1	180.5	183.2	177.2	151.9	132.2	113.8	103.3
67.5°	110.8	116.2	125.5	138.6	145.8	147.3	135.7	119.8	102.4	91.2	83.3
70°	96.7	100.5	109.1	116.2	122.1	122.2	111.5	98.8	85.5	76.3	70.5
72.5°	83.1	86.7	93.2	98.1	102.6	101.1	91.3	81.3	70.5	63.5	59.3
75°	64.1	67.3	70.7	73.0	73.0	71.1	63.9	56.4	50.2	46.1	44.8
77.5°	46.6	49.2	50.4	50.0	49.4	46.4	41.9	37.0	34.8	32.9	31.8
80°	36.6	37.7	38.0	37.2	36.0	32.6	29.6	27.6	25.5	24.7	24.4
82.5°	27.1	28.1	27.1	27.4	24.9	22.1	20.4	19.7	18.9	18.6	18.2
85°	14.4	14.3	13.9	12.9	11.2	10.9	10.7	10.5	10.1	10.3	9.9
87.5°	5.3	5.2	4.8	4.8	4.8	5.1	5.3	5.5	5.9	5.5	5.9
90°	1.8	3.7	4.4	5.0	5.0	8.6	8.6	9.9	11.2	10.5	11.2
92.5°	10.3	16.1	23.7	32.7	45.6	77.1	125.1	172.0	196.5	163.7	121.7
95°	22.3	28.5	36.5	51.4	77.4	131.3	232.9	381.0	504.9	519.1	459.0
97.5°	36.7	42.0	49.4	62.2	84.0	125.5	209.4	356.6	531.7	652.1	678.1
100°	47.1	51.4	58.9	70.6	90.5	127.0	197.0	323.4	498.0	656.6	747.0
102.5°	58.0	61.8	68.8	80.0	98.9	131.9	193.5	301.0	455.9	619.4	743.5
105°	74.3	77.4	84.8	96.0	114.0	143.7	195.1	281.9	406.3	551.9	693.8
107.5°	90.8	93.9	101.8	112.5	130.2	157.5	204.3	278.4	378.6	497.4	623.1
110°	102.2	105.3	112.7	123.9	140.6	167.9	211.2	279.3	369.2	470.2	580.4



TEST NUMBER: P332879-927

CATALOG NUMBER: SA4XXRDIP-C350D810U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	113.1	116.7	123.7	134.8	151.5	177.8	218.6	282.3	364.7	454.8	549.2
115°	129.4	133.8	140.0	151.8	168.5	193.3	230.4	288.0	362.3	440.4	517.8
117.5°	145.7	149.6	156.4	167.4	184.7	208.3	242.4	294.1	361.7	434.0	502.5
120°	156.1	160.4	167.2	177.8	195.1	218.6	250.9	298.6	361.7	430.5	495.5
122.5°	166.0	170.3	176.7	188.1	205.0	228.5	258.8	303.0	361.2	426.5	489.6
125°	180.2	183.9	190.8	202.6	219.9	242.2	270.7	309.7	360.5	419.9	479.4
127.5°	191.3	195.7	203.5	215.8	233.3	254.8	281.0	315.1	359.2	411.1	467.1
130°	198.2	203.2	212.5	224.3	242.2	263.2	287.4	319.0	358.6	405.8	457.2
132.5°	204.1	210.6	219.4	232.2	249.1	270.2	293.8	322.5	358.1	400.8	446.7
135°	213.7	219.9	230.4	243.4	259.5	280.0	302.3	327.6	357.4	393.3	432.4
137.5°	222.6	229.4	239.5	252.9	268.3	287.4	308.2	330.7	357.3	386.9	419.4
140°	228.5	235.4	245.9	258.9	273.8	292.4	312.2	333.3	356.8	383.4	411.9
142.5°	235.5	241.9	251.8	264.4	278.8	296.8	315.1	335.3	356.8	380.5	405.0
145°	245.3	251.5	260.2	272.0	285.6	301.7	318.4	336.4	355.5	375.3	395.2
147.5°	255.1	260.5	269.4	279.2	291.5	306.7	321.2	337.0	353.3	370.8	387.1
150°	262.1	267.0	274.4	283.7	295.5	309.1	322.7	337.0	351.8	367.3	382.1
152.5°	268.0	272.9	279.9	288.2	299.0	311.1	323.7	336.0	349.4	363.4	376.8
155°	277.5	281.2	287.4	294.2	303.5	314.0	324.6	334.5	345.6	357.4	368.5
157.5°	285.7	289.1	294.0	299.9	307.2	316.2	324.6	332.9	341.8	351.3	359.7
160°	291.1	293.6	297.9	302.9	309.7	317.1	324.6	331.4	338.8	346.9	354.3
162.5°	295.6	297.5	301.4	305.9	311.2	318.1	324.6	329.9	335.9	342.9	348.9
165°	301.7	302.9	306.0	309.1	312.8	318.4	323.4	327.1	331.4	336.4	341.3
167.5°	306.7	307.2	309.6	311.3	314.2	318.3	321.9	324.1	326.9	330.4	334.0
170°	309.1	309.7	311.6	312.8	314.7	317.7	320.8	322.1	323.9	326.5	329.5
172.5°	311.6	311.7	313.1	313.8	315.1	317.3	319.9	320.1	321.0	323.0	325.6
175°	314.0	314.0	314.7	315.3	315.3	316.6	318.4	317.7	317.7	319.0	320.3
177.5°	315.3	314.8	315.3	315.3	315.3	315.8	316.8	315.8	315.8	316.2	316.8
180°	315.3	315.3	315.3	315.3	315.3	315.3	315.3	315.3	315.3	315.3	315.3



TEST NUMBER: P332879-927

CATALOG NUMBER: SA4XXRDIP-C350D810U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	465.3	465.3	465.3	465.3	465.3	465.3	465.3
2.5°	488.1	488.7	489.2	490.7	490.8	492.2	490.8
5°	528.5	531.2	535.3	539.4	539.8	542.4	537.7
7.5°	573.8	579.9	583.7	590.3	592.9	594.6	591.9
10°	605.0	610.6	620.6	625.4	630.3	631.1	628.8
12.5°	635.2	644.0	651.9	661.2	660.9	667.5	665.1
15°	675.3	684.5	695.4	705.7	709.4	709.4	712.4
17.5°	703.9	720.8	732.1	740.1	749.0	750.5	749.5
20°	723.3	741.5	753.5	764.0	770.0	771.7	771.7
22.5°	737.7	753.2	764.9	774.4	779.3	781.3	780.7
25°	747.7	761.0	768.1	771.0	772.2	771.9	768.3
27.5°	734.0	733.4	729.0	720.3	713.8	709.9	705.4
30°	708.0	698.2	686.9	674.5	658.6	646.4	642.7
32.5°	669.1	647.2	628.1	607.5	590.4	578.2	573.1
35°	594.0	559.3	530.9	506.2	488.2	477.0	473.2
37.5°	504.8	471.2	436.2	412.2	397.2	385.9	381.7
40°	448.1	411.5	381.0	358.5	343.1	332.0	331.8
42.5°	396.3	361.4	332.6	316.5	299.9	292.6	292.6
45°	324.6	296.6	272.2	259.4	249.5	243.5	241.9
47.5°	268.7	245.6	229.3	219.2	211.1	207.3	204.8
50°	237.3	217.1	204.1	195.4	190.8	186.0	185.6
52.5°	211.3	194.9	184.8	177.7	172.0	169.1	169.1
55°	177.5	164.6	157.5	152.0	147.6	145.3	144.3
57.5°	149.6	139.9	134.7	129.7	127.8	126.0	125.6
60°	132.2	125.6	120.7	116.8	114.0	113.4	113.2
62.5°	117.8	110.9	107.6	104.5	102.4	101.6	101.2
65°	97.1	92.1	89.0	86.6	85.9	84.5	84.4
67.5°	78.3	75.3	73.3	71.6	70.6	70.5	70.5
70°	66.8	65.0	63.4	62.4	61.9	61.5	61.5
72.5°	56.9	55.6	54.2	53.7	53.6	53.2	53.1
75°	43.3	42.0	42.2	41.3	40.5	39.5	39.0
77.5°	30.7	29.8	29.5	29.5	28.8	28.8	29.0
80°	23.8	22.9	22.7	22.9	22.7	22.1	22.1
82.5°	18.1	17.3	17.1	17.0	16.9	17.0	16.7
85°	9.7	9.3	9.3	9.3	9.7	9.6	9.3
87.5°	5.8	5.8	5.9	5.9	6.0	5.8	5.9
90°	11.8	12.4	12.4	13.0	13.6	13.0	13.0
92.5°	91.6	72.9	60.4	53.2	49.8	47.7	47.7
95°	363.0	280.0	219.9	189.6	170.3	159.2	151.1
97.5°	642.5	581.9	517.2	472.8	435.5	416.8	404.0
100°	759.4	729.0	683.3	629.3	591.5	573.0	568.0
102.5°	805.0	813.8	794.7	761.7	734.3	714.7	710.7
105°	800.9	862.2	887.6	888.9	883.9	875.3	871.6
107.5°	737.1	823.5	878.7	909.3	923.4	929.6	931.2
110°	687.5	777.4	845.5	889.5	915.5	926.7	932.2



TEST NUMBER: P332879-927

CATALOG NUMBER: SA4XXRDIP-C350D810U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	644.0	728.8	796.9	846.8	878.4	894.0	903.0
115°	594.1	666.5	726.0	774.9	812.1	831.9	836.9
117.5°	565.5	622.5	673.0	714.7	745.9	766.0	769.8
120°	553.2	602.7	646.7	682.0	709.2	725.3	732.1
122.5°	545.2	590.3	628.8	658.7	682.0	695.6	702.4
125°	532.7	575.4	609.5	634.3	652.3	664.0	667.7
127.5°	517.9	560.5	592.9	617.8	633.8	643.7	647.5
130°	506.0	548.2	581.0	606.4	621.9	631.8	635.6
132.5°	492.7	533.9	566.6	591.5	609.0	618.5	622.2
135°	472.6	510.4	541.4	566.2	583.5	593.4	597.1
137.5°	453.4	485.3	513.3	536.4	553.5	561.7	566.2
140°	441.0	468.9	495.0	516.6	530.2	538.9	543.8
142.5°	430.6	454.6	477.1	496.3	508.9	516.6	520.1
145°	416.3	434.8	452.2	467.7	478.2	484.4	487.5
147.5°	403.9	418.7	432.4	443.8	452.8	457.5	458.6
150°	396.4	408.8	419.9	429.9	437.9	441.6	442.3
152.5°	389.0	400.4	409.6	418.0	424.5	426.7	427.4
155°	378.5	387.8	395.2	401.4	406.3	408.2	408.2
157.5°	368.0	375.9	381.8	386.5	390.2	391.3	391.3
160°	361.2	368.0	372.9	376.6	380.3	381.0	381.0
162.5°	354.7	360.0	364.5	367.2	370.9	371.5	371.1
165°	345.0	349.4	352.4	354.9	357.4	356.8	356.2
167.5°	336.8	340.3	342.1	343.4	345.0	344.9	344.4
170°	331.4	333.9	335.7	337.0	337.5	337.0	337.0
172.5°	326.9	328.4	329.8	330.5	331.1	330.5	329.5
175°	320.8	322.1	322.1	322.1	323.4	322.1	320.8
177.5°	317.3	317.3	317.7	317.3	317.7	316.8	315.8
180°	315.3	315.3	315.3	315.3	315.3	315.3	315.3

(END OF REPORT)