

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332921-927

Luminaire Tested: **SA4XXRDIP-C575D1205U927-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332921-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXRDIP-C575D1205U927-4F0-1E-UDD-A4  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 575 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5344.0 lumens  
Efficiency: N/A  
Efficacy: 108.2 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 49.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332921-927

CATALOG NUMBER: SA4XXRDIP-C575D1205U927-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P332921-927

CATALOG NUMBER: SA4XXRDIP-C575D1205U927-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	43	43	43	36
1	95	91	87	84	86	83	79	77	67	65	63	52	51	50	39	38	37	31
2	87	80	74	69	78	72	68	63	59	55	52	46	44	42	35	33	32	27
3	79	70	63	58	72	64	58	53	52	48	44	41	38	36	31	29	28	23
4	73	62	55	49	66	57	50	45	46	42	38	37	34	31	28	26	24	20
5	67	56	48	42	60	51	44	39	42	37	33	33	30	27	25	23	21	17
6	61	50	42	37	56	46	39	34	38	32	29	30	26	24	23	20	19	15
7	57	45	37	32	51	41	35	30	34	29	25	27	24	21	21	18	17	14
8	53	41	33	28	48	37	31	26	31	26	22	25	21	19	19	17	15	12
9	49	37	30	25	44	34	28	23	28	23	20	23	19	17	18	15	13	11
10	46	34	27	22	41	31	25	21	26	21	18	21	18	15	17	14	12	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	6176	6176	6176	6176
5°	7164	6195	5476	6195
10°	8475	6167	4887	6167
15°	9789	6110	4199	6110
20°	10899	6032	3797	6032
25°	11251	5955	3526	5955
30°	9849	5862	3361	5862
35°	7666	5723	3263	5723
40°	5750	5564	3209	5564
45°	4539	5310	3181	5310
50°	3832	5016	3090	5016
55°	3340	4694	2923	4694
60°	3006	4359	2588	4359
65°	2649	3998	2225	3998
70°	2386	3623	2009	3623
75°	1999	3213	1712	3213
80°	1692	2738	1604	2738
85°	1426	2140	1426	2140



TEST NUMBER: P332921-927

CATALOG NUMBER: SA4XXRDIP-C575D1205U927-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	74.1	1.4
10°-20°	223.6	4.2
20°-30°	349.7	6.5
30°-40°	388.8	7.3
40°-50°	344.9	6.5
50°-60°	268.8	5.0
60°-70°	176.0	3.3
70°-80°	86.5	1.6
80°-90°	23.9	0.4
90°-100°	338.4	6.3
100°-110°	704.3	13.2
110°-120°	630.9	11.8
120°-130°	530.7	9.9
130°-140°	442.5	8.3
140°-150°	338.0	6.3
150°-160°	237.6	4.4
160°-170°	139.8	2.6
170°-180°	45.5	0.9
0°-30°	647.4	12.1
0°-40°	1036.2	19.4
0°-60°	1649.9	30.9
0°-90°	1936.4	36.2
90°-120°	1673.6	31.3
90°-150°	2984.8	55.9
90°-180°	3408.0	63.8
0°-180°	5344.0	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	765	765	765	765	765	
5°	884	764	676	764	884	89
15°	1171	731	502	731	1171	333
25°	1263	668	396	668	1263	560
35°	778	581	331	581	778	488
45°	398	465	279	465	398	315
55°	237	334	208	334	237	216
65°	139	209	116	209	139	140
75°	64	103	55	103	64	71
85°	15	23	15	23	15	18
90°	19	1	19	1	19	16
95°	225	30	225	30	225	349
105°	1295	108	1295	108	1295	1280
115°	1244	190	1244	190	1244	1235
125°	992	264	992	264	992	902
135°	887	314	887	314	887	685
145°	724	362	724	362	724	459
155°	607	412	607	412	607	283
165°	529	448	529	448	529	152
175°	477	468	477	468	477	46
180°	469	469	469	469	469	



TEST NUMBER: P332921-927

CATALOG NUMBER: SA4XXRDIP-C575D1205U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0
2.5°	806.9	809.1	806.9	806.7	804.2	803.5	802.5	799.3	793.4	789.9	790.7
5°	884.0	891.7	887.4	886.8	880.0	873.2	868.9	859.0	848.5	841.5	835.6
7.5°	973.1	977.6	974.9	970.5	959.6	953.3	943.3	930.3	911.6	897.1	884.1
10°	1033.8	1037.4	1036.3	1028.3	1020.3	1003.9	994.7	976.4	952.7	933.9	916.3
12.5°	1093.4	1097.4	1086.6	1087.0	1071.7	1058.8	1044.2	1021.4	993.9	969.6	947.7
15°	1171.2	1166.3	1166.3	1160.2	1143.2	1125.3	1110.2	1086.2	1051.6	1022.7	992.2
17.5°	1232.2	1233.9	1231.4	1216.8	1203.5	1185.0	1157.3	1129.3	1097.2	1058.3	1027.1
20°	1268.7	1268.7	1265.9	1256.0	1238.7	1219.0	1189.1	1158.6	1117.9	1078.8	1043.6
22.5°	1283.4	1284.4	1281.2	1273.0	1257.5	1238.3	1212.8	1181.8	1139.9	1095.8	1052.3
25°	1263.1	1268.9	1269.6	1267.4	1262.8	1251.1	1229.2	1197.5	1159.8	1112.1	1065.2
27.5°	1159.7	1167.0	1173.5	1184.2	1198.3	1205.8	1206.7	1190.6	1157.8	1111.8	1064.7
30°	1056.6	1062.7	1082.8	1109.0	1129.3	1147.8	1163.9	1168.2	1149.7	1108.3	1058.8
32.5°	942.1	950.5	970.6	998.8	1032.7	1064.0	1100.0	1118.3	1117.8	1093.1	1047.2
35°	777.9	784.1	802.6	832.2	872.9	919.4	976.4	1020.8	1051.1	1048.8	1020.8
37.5°	627.4	634.4	653.1	677.6	717.1	774.7	829.9	891.0	946.9	978.3	968.8
40°	545.6	545.9	564.0	589.3	626.3	676.5	736.7	804.5	866.7	917.6	927.4
42.5°	480.9	481.0	493.1	520.3	546.9	594.2	651.6	718.9	791.8	850.5	876.6
45°	397.6	400.4	410.3	426.6	447.5	487.6	533.5	596.1	677.8	747.4	790.9
47.5°	336.7	340.8	347.1	360.4	377.1	403.8	441.7	498.0	564.4	641.0	702.9
50°	305.1	305.8	313.8	321.2	335.6	357.0	390.2	437.0	498.1	571.7	640.5
52.5°	278.1	277.9	282.7	292.1	303.9	320.4	347.3	390.0	444.1	510.1	581.1
55°	237.3	238.8	242.6	249.9	258.9	270.6	291.9	323.9	366.5	422.9	487.3
57.5°	206.4	207.2	210.1	213.3	221.4	230.0	245.9	268.2	304.0	350.2	410.3
60°	186.2	186.5	187.4	192.0	198.5	206.5	217.3	236.1	266.3	308.6	356.0
62.5°	166.4	167.0	168.4	171.8	176.8	182.4	193.6	208.7	233.8	269.8	312.6
65°	138.7	139.0	141.2	142.4	146.4	151.3	159.6	169.8	187.1	217.3	249.7
67.5°	115.9	115.9	116.0	117.7	120.5	123.7	128.7	136.9	149.9	168.4	196.9
70°	101.1	101.1	101.7	102.7	104.2	106.9	109.7	115.9	125.5	140.5	162.4
72.5°	87.3	87.5	88.2	88.3	89.1	91.4	93.5	97.4	104.5	115.9	133.6
75°	64.1	65.0	66.5	67.8	69.3	69.1	71.2	73.7	75.8	82.6	92.8
77.5°	47.7	47.2	47.4	48.5	48.6	49.0	50.5	52.4	54.0	57.2	60.8
80°	36.4	36.4	37.3	37.6	37.3	37.6	39.1	40.1	40.7	41.9	45.3
82.5°	27.5	28.0	27.6	28.0	28.2	28.5	29.8	29.9	30.6	31.1	32.5
85°	15.4	15.7	16.0	15.4	15.4	15.4	16.0	16.3	17.0	16.6	17.3
87.5°	9.3	9.0	9.5	9.3	9.3	9.1	9.2	9.5	8.8	9.3	8.9
90°	19.3	19.3	20.3	19.3	18.4	18.4	17.5	16.6	15.7	16.6	14.7
92.5°	70.9	70.9	74.0	79.0	89.8	108.3	136.0	180.8	243.2	292.0	255.6
95°	224.6	236.5	253.2	281.7	326.8	416.1	539.4	682.1	771.4	750.2	566.1
97.5°	600.4	619.5	647.1	702.5	768.7	864.7	954.7	1007.8	969.2	790.2	529.8
100°	844.1	851.5	879.1	935.3	1015.3	1083.5	1128.5	1110.2	975.7	740.1	480.5
102.5°	1056.2	1062.1	1091.2	1131.9	1181.0	1209.3	1196.3	1105.0	920.5	677.5	447.3
105°	1295.1	1300.7	1313.6	1321.0	1319.1	1281.4	1190.3	1030.9	820.1	603.9	418.8
107.5°	1383.9	1381.5	1372.3	1351.3	1305.8	1223.8	1095.4	925.8	739.2	562.6	413.7
110°	1385.4	1377.1	1360.5	1321.8	1256.5	1155.2	1021.8	862.5	698.7	548.7	415.2



TEST NUMBER: P332921-927

CATALOG NUMBER: SA4XXRDIP-C575D1205U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1342.0	1328.5	1305.3	1258.5	1184.3	1083.1	957.0	816.1	675.8	542.0	419.5
115°	1243.6	1236.3	1206.8	1151.6	1078.9	990.5	882.8	769.5	654.5	538.5	428.0
117.5°	1144.0	1138.3	1108.5	1062.1	1000.1	925.1	840.4	746.7	644.9	537.6	437.0
120°	1088.1	1077.9	1054.0	1013.5	961.0	895.6	822.0	736.4	639.8	537.6	443.7
122.5°	1043.9	1033.7	1013.5	978.9	934.5	877.3	810.2	727.5	633.9	536.9	450.4
125°	992.3	986.8	969.3	942.6	905.8	855.2	791.6	712.5	624.1	535.8	460.3
127.5°	962.1	956.6	941.9	918.1	881.1	833.1	769.8	694.0	611.0	533.7	468.2
130°	944.4	938.9	924.2	901.2	863.5	814.7	752.1	679.4	602.9	533.0	474.0
132.5°	924.6	919.0	905.1	879.1	842.1	793.3	732.2	663.8	595.6	532.3	479.2
135°	887.4	881.9	867.1	841.4	804.5	758.5	702.3	642.5	584.6	531.2	487.0
137.5°	841.4	834.7	822.6	797.2	762.7	721.1	673.8	623.2	575.0	530.9	491.5
140°	808.2	800.8	788.0	767.7	735.5	696.8	655.4	612.1	569.8	530.2	495.3
142.5°	772.9	767.7	756.3	737.5	709.0	675.5	639.9	601.8	565.4	530.2	498.2
145°	724.5	719.9	710.7	695.0	672.0	646.2	618.6	587.3	557.9	528.4	499.9
147.5°	681.5	679.9	672.9	659.5	642.5	622.3	600.2	575.4	551.0	525.1	500.7
150°	657.3	656.3	650.8	638.8	624.1	607.5	589.1	568.0	545.9	522.8	500.7
152.5°	635.2	634.2	630.9	621.2	608.6	595.0	578.1	559.8	540.0	519.2	499.3
155°	606.7	606.7	603.9	596.5	587.3	576.2	562.4	547.7	531.2	513.7	497.1
157.5°	581.6	581.6	580.0	574.4	567.4	558.6	547.0	534.6	522.1	507.9	494.7
160°	566.1	566.1	565.2	559.7	554.1	546.8	536.6	526.6	515.5	503.5	492.5
162.5°	551.4	552.2	551.2	545.7	541.6	535.0	527.1	518.4	509.6	499.1	490.3
165°	529.3	530.2	531.2	527.4	523.8	519.2	512.7	507.2	499.9	492.5	486.0
167.5°	511.8	512.5	512.7	510.3	508.5	505.7	500.6	496.4	491.0	485.8	481.6
170°	500.7	500.7	501.7	500.7	498.9	496.1	492.5	489.7	485.1	481.4	478.6
172.5°	489.7	491.2	492.1	491.2	490.0	488.1	485.8	483.8	480.0	477.0	475.7
175°	476.8	478.6	480.5	478.6	478.6	478.6	476.8	475.9	474.0	472.2	472.2
177.5°	469.3	470.7	472.2	471.5	472.2	471.5	471.5	470.7	470.0	469.3	469.3
180°	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6



TEST NUMBER: P332921-927

CATALOG NUMBER: SA4XXRDIP-C575D1205U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0
2.5°	788.2	784.7	783.0	779.0	774.4	771.9	769.7	766.5	762.3	757.9	754.6
5°	828.2	820.8	811.5	800.4	790.6	781.0	772.7	764.4	754.9	745.0	735.1
7.5°	869.3	854.7	839.0	820.8	803.1	787.0	772.2	758.0	742.0	727.6	714.5
10°	897.9	878.1	856.3	833.1	810.0	790.0	770.2	752.3	732.6	715.1	700.3
12.5°	921.1	897.9	871.6	842.7	814.9	790.7	768.0	744.7	722.3	703.2	683.5
15°	959.5	927.7	892.3	857.8	821.7	788.8	758.2	731.1	705.5	678.7	659.9
17.5°	986.0	948.2	905.2	863.7	821.1	782.2	747.0	714.7	685.2	657.8	635.4
20°	1001.7	960.1	912.4	865.1	817.4	775.8	737.9	702.1	671.6	642.1	618.9
22.5°	1010.6	964.6	912.4	862.9	813.5	768.4	726.8	689.6	656.3	626.8	601.2
25°	1013.4	964.1	910.8	854.1	799.9	752.1	708.9	668.5	631.5	602.0	574.8
27.5°	1009.5	951.4	896.8	838.6	782.7	732.3	687.0	644.5	607.5	575.8	548.0
30°	1003.5	941.4	882.7	822.4	765.6	717.2	669.5	628.8	590.3	557.3	529.3
32.5°	990.8	929.0	866.0	804.1	746.6	696.8	651.5	610.5	572.7	539.0	509.2
35°	965.4	902.8	834.3	770.9	714.5	662.7	620.1	580.7	544.6	508.6	477.1
37.5°	931.8	868.0	799.9	730.4	673.9	625.0	586.0	549.0	513.7	480.9	446.0
40°	900.3	842.1	771.8	702.7	644.8	597.6	561.6	528.0	492.6	459.9	425.0
42.5°	862.1	812.5	741.5	672.2	615.0	569.5	535.9	503.1	470.9	439.2	402.8
45°	798.3	760.7	694.1	627.6	569.9	524.9	494.1	465.1	436.7	406.5	372.3
47.5°	725.2	699.7	642.3	574.1	520.8	480.3	450.5	426.8	402.8	372.6	342.6
50°	674.4	658.1	602.6	540.3	489.5	452.2	421.7	399.4	379.5	350.5	323.6
52.5°	620.1	611.5	564.6	505.0	455.9	419.4	393.3	373.4	353.1	329.0	303.9
55°	537.6	542.2	502.4	450.9	404.7	373.9	350.1	333.5	316.2	295.9	276.5
57.5°	453.0	470.0	443.3	398.1	354.7	326.3	308.4	294.4	280.0	263.0	246.4
60°	402.5	416.7	401.6	361.9	323.9	297.5	280.8	270.0	255.5	240.1	227.4
62.5°	353.2	368.4	359.4	327.3	292.2	269.3	254.7	244.6	233.9	220.4	207.2
65°	291.3	301.1	296.8	274.6	249.7	230.2	216.7	209.3	199.4	189.6	177.8
67.5°	223.1	242.2	239.6	227.8	206.3	191.1	182.2	175.7	166.7	159.4	151.4
70°	183.4	201.0	200.7	191.1	179.4	165.2	159.1	153.5	145.4	138.4	131.9
72.5°	150.1	166.2	168.6	161.3	153.3	142.5	136.6	132.8	125.0	120.2	114.9
75°	105.1	116.8	119.9	119.9	116.2	110.7	105.4	103.0	97.4	93.1	90.0
77.5°	68.9	76.3	81.1	82.2	82.8	81.0	76.6	74.9	70.7	69.1	66.1
80°	48.7	53.6	59.2	61.0	62.6	61.9	60.1	58.9	54.9	53.3	52.1
82.5°	33.7	36.4	41.0	45.0	44.6	46.2	44.6	43.6	40.6	40.0	38.7
85°	17.6	17.9	18.5	21.2	22.8	23.4	23.8	23.1	22.2	22.2	20.0
87.5°	8.5	8.2	7.6	7.6	7.7	8.5	8.7	8.6	8.2	8.0	7.4
90°	12.9	12.9	7.4	7.4	6.4	5.5	2.8	1.0	2.8	5.5	6.4
92.5°	185.9	114.5	67.7	48.6	35.2	23.9	15.3	10.5	15.3	23.9	35.2
95°	346.1	195.1	115.1	76.4	54.3	42.4	33.1	30.3	33.1	42.4	54.3
97.5°	311.2	186.5	124.8	92.4	73.4	62.4	54.5	54.5	54.5	62.4	73.4
100°	292.7	188.7	134.4	105.0	87.5	76.4	69.9	69.9	69.9	76.4	87.5
102.5°	287.6	196.1	146.9	118.9	102.2	91.9	86.2	84.7	86.2	91.9	102.2
105°	289.9	213.6	169.4	142.7	126.1	115.1	110.4	107.7	110.4	115.1	126.1
107.5°	303.6	234.0	193.5	167.2	151.3	139.6	134.9	133.1	134.9	139.6	151.3
110°	313.9	249.5	209.0	184.1	167.5	156.5	151.9	150.0	151.9	156.5	167.5





TEST NUMBER: P332921-927

CATALOG NUMBER: SA4XXRDIP-C575D1205U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	325.0	264.2	225.1	200.3	183.7	173.4	168.1	166.3	168.1	173.4	183.7
115°	342.5	287.2	250.4	225.5	208.0	198.8	192.4	189.6	192.4	198.8	208.0
117.5°	360.3	309.5	274.5	248.7	232.3	222.2	216.5	213.9	216.5	222.2	232.3
120°	372.8	325.0	289.9	264.2	248.5	238.4	232.0	230.1	232.0	238.4	248.5
122.5°	384.6	339.7	304.7	279.6	262.5	253.2	246.7	244.9	246.7	253.2	262.5
125°	402.3	359.9	326.8	301.0	283.5	273.4	267.8	264.2	267.8	273.4	283.5
127.5°	417.6	378.7	346.7	320.7	302.5	290.9	284.2	281.3	284.2	290.9	302.5
130°	427.1	391.3	359.9	333.2	315.8	301.9	294.5	290.9	294.5	301.9	315.8
132.5°	436.7	401.6	370.3	345.0	326.1	313.0	303.4	300.5	303.4	313.0	326.1
135°	449.2	416.1	385.7	361.8	342.5	326.8	317.6	313.9	317.6	326.8	342.5
137.5°	458.0	427.1	398.8	376.0	355.8	341.0	330.8	327.3	330.8	341.0	355.8
140°	463.9	434.5	406.9	384.8	365.4	349.8	339.7	336.9	339.7	349.8	365.4
142.5°	468.3	441.1	414.2	392.8	374.3	359.3	350.0	347.2	350.0	359.3	374.3
145°	473.2	448.3	424.4	404.1	386.6	373.8	364.6	361.8	364.6	373.8	386.6
147.5°	477.4	455.7	433.2	414.9	400.4	387.1	379.1	378.1	379.1	387.1	400.4
150°	479.6	459.3	439.1	421.6	407.8	396.7	389.4	388.5	389.4	396.7	407.8
152.5°	481.1	462.3	444.3	428.3	415.9	405.6	398.2	398.0	398.2	405.6	415.9
155°	482.4	466.7	451.1	437.3	427.1	417.9	412.4	411.5	412.4	417.9	427.1
157.5°	482.4	469.8	456.6	445.7	436.9	429.7	424.5	424.5	424.5	429.7	436.9
160°	482.4	471.3	460.3	450.1	442.8	436.3	432.6	432.6	432.6	436.3	442.8
162.5°	482.4	472.8	462.5	454.6	447.9	442.2	439.3	440.0	439.3	442.2	447.9
165°	480.5	473.2	464.9	459.3	454.7	450.1	448.3	448.3	448.3	450.1	454.7
167.5°	478.3	472.9	466.9	462.6	460.1	456.6	455.7	456.6	455.7	456.6	460.1
170°	476.8	472.2	467.6	464.9	463.0	460.3	459.3	460.3	459.3	460.3	463.0
172.5°	475.4	471.5	468.3	466.4	465.2	463.2	463.0	463.9	463.0	463.2	465.2
175°	473.2	470.4	468.6	468.6	467.6	466.7	466.7	467.6	466.7	466.7	467.6
177.5°	470.7	469.3	468.6	468.6	468.6	467.8	468.6	469.3	468.6	467.8	468.6
180°	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6



TEST NUMBER: P332921-927

CATALOG NUMBER: SA4XXRDIP-C575D1205U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0
2.5°	751.2	748.8	745.5	741.8	737.4	733.5	731.7	733.2	734.0	732.0	731.7
5°	728.3	720.6	714.5	705.2	697.8	691.7	687.3	685.5	686.1	681.2	679.9
7.5°	702.6	693.5	683.4	672.4	662.2	653.2	648.4	645.8	640.6	638.3	634.5
10°	686.1	673.8	663.9	650.9	639.3	628.4	623.2	618.9	613.7	611.2	605.9
12.5°	669.1	654.8	644.0	630.5	618.5	605.5	600.6	592.6	584.3	579.2	572.4
15°	645.1	627.9	614.6	598.6	584.4	569.6	556.3	541.5	536.0	524.3	517.5
17.5°	617.0	599.5	583.1	561.7	539.8	521.4	507.2	493.1	484.6	477.1	473.6
20°	598.6	582.6	559.8	534.8	510.4	490.0	478.6	469.4	460.2	455.0	451.2
22.5°	581.1	560.6	534.1	507.2	482.8	466.9	457.2	447.7	440.2	435.2	430.3
25°	551.8	524.9	496.9	466.0	449.4	435.5	425.0	417.3	412.7	406.2	403.8
27.5°	521.6	489.1	458.1	437.4	420.1	407.4	398.3	392.5	386.7	382.5	379.3
30°	498.4	465.4	437.7	418.0	400.4	389.9	382.5	375.7	371.1	367.7	365.3
32.5°	475.5	442.5	419.1	398.0	384.1	373.9	366.0	360.9	357.3	352.9	351.4
35°	442.3	413.0	392.7	373.6	359.4	350.1	344.0	338.7	335.6	334.5	333.5
37.5°	410.4	386.4	364.6	348.9	336.3	329.0	321.7	319.2	317.0	314.8	315.8
40°	390.2	367.7	348.3	331.7	321.5	313.5	309.1	306.1	304.2	304.2	304.2
42.5°	372.7	350.7	331.8	316.9	306.7	299.9	295.1	292.5	291.9	291.6	293.1
45°	345.5	325.2	306.1	293.7	285.1	278.3	275.5	273.4	273.4	274.6	275.0
47.5°	318.6	299.5	284.2	270.4	262.4	258.3	255.8	254.7	254.8	256.0	257.5
50°	302.1	283.3	268.2	255.8	248.4	244.4	242.2	241.6	242.2	242.2	244.4
52.5°	284.1	267.2	252.4	242.0	233.6	229.9	228.7	227.8	228.2	229.2	230.1
55°	257.7	242.6	228.4	218.6	212.4	209.9	207.2	207.5	206.8	207.5	207.5
57.5°	231.2	217.7	204.5	196.6	191.2	187.7	184.7	185.4	184.6	184.4	183.9
60°	214.2	199.4	188.9	181.9	175.7	172.6	169.8	170.5	169.5	168.9	167.7
62.5°	195.7	183.4	173.4	166.6	161.6	158.0	155.3	154.6	152.5	150.4	147.7
65°	168.9	158.8	149.8	143.3	138.7	135.9	133.8	131.9	127.3	122.4	119.9
67.5°	142.8	135.5	127.1	121.7	118.0	114.3	110.2	107.0	102.7	100.0	98.5
70°	126.0	119.0	111.9	106.6	102.7	99.3	94.6	92.4	89.4	88.2	86.6
72.5°	110.0	103.5	96.8	92.1	87.9	85.2	81.6	79.4	78.0	77.6	76.0
75°	85.7	80.5	75.5	71.2	67.8	66.0	64.4	62.9	62.3	59.5	57.9
77.5°	62.5	59.0	56.0	52.9	50.5	49.3	46.3	44.5	43.5	42.1	41.8
80°	48.7	46.3	43.2	41.3	37.9	36.7	35.4	35.2	34.9	34.5	34.2
82.5°	36.6	34.1	31.1	29.9	29.1	28.3	27.6	27.3	26.9	27.1	27.1
85°	18.5	17.3	17.3	17.0	16.6	16.3	16.0	16.0	15.7	16.0	15.7
87.5°	7.6	7.4	8.5	8.0	8.6	9.0	8.6	8.7	9.2	8.9	8.9
90°	7.4	7.4	12.9	12.9	14.7	16.6	15.7	16.6	17.5	18.4	18.4
92.5°	48.6	67.7	114.5	185.9	255.6	292.0	243.2	180.8	136.0	108.3	89.8
95°	76.4	115.1	195.1	346.1	566.1	750.2	771.4	682.1	539.4	416.1	326.8
97.5°	92.4	124.8	186.5	311.2	529.8	790.2	969.2	1007.8	954.7	864.7	768.7
100°	105.0	134.4	188.7	292.7	480.5	740.1	975.7	1110.2	1128.5	1083.5	1015.3
102.5°	118.9	146.9	196.1	287.6	447.3	677.5	920.5	1105.0	1196.3	1209.3	1181.0
105°	142.7	169.4	213.6	289.9	418.8	603.9	820.1	1030.9	1190.3	1281.4	1319.1
107.5°	167.2	193.5	234.0	303.6	413.7	562.6	739.2	925.8	1095.4	1223.8	1305.8
110°	184.1	209.0	249.5	313.9	415.2	548.7	698.7	862.5	1021.8	1155.2	1256.5



TEST NUMBER: P332921-927

CATALOG NUMBER: SA4XXRDIP-C575D1205U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	200.3	225.1	264.2	325.0	419.5	542.0	675.8	816.1	957.0	1083.1	1184.3
115°	225.5	250.4	287.2	342.5	428.0	538.5	654.5	769.5	882.8	990.5	1078.9
117.5°	248.7	274.5	309.5	360.3	437.0	537.6	644.9	746.7	840.4	925.1	1000.1
120°	264.2	289.9	325.0	372.8	443.7	537.6	639.8	736.4	822.0	895.6	961.0
122.5°	279.6	304.7	339.7	384.6	450.4	536.9	633.9	727.5	810.2	877.3	934.5
125°	301.0	326.8	359.9	402.3	460.3	535.8	624.1	712.5	791.6	855.2	905.8
127.5°	320.7	346.7	378.7	417.6	468.2	533.7	611.0	694.0	769.8	833.1	881.1
130°	333.2	359.9	391.3	427.1	474.0	533.0	602.9	679.4	752.1	814.7	863.5
132.5°	345.0	370.3	401.6	436.7	479.2	532.3	595.6	663.8	732.2	793.3	842.1
135°	361.8	385.7	416.1	449.2	487.0	531.2	584.6	642.5	702.3	758.5	804.5
137.5°	376.0	398.8	427.1	458.0	491.5	530.9	575.0	623.2	673.8	721.1	762.7
140°	384.8	406.9	434.5	463.9	495.3	530.2	569.8	612.1	655.4	696.8	735.5
142.5°	392.8	414.2	441.1	468.3	498.2	530.2	565.4	601.8	639.9	675.5	709.0
145°	404.1	424.4	448.3	473.2	499.9	528.4	557.9	587.3	618.6	646.2	672.0
147.5°	414.9	433.2	455.7	477.4	500.7	525.1	551.0	575.4	600.2	622.3	642.5
150°	421.6	439.1	459.3	479.6	500.7	522.8	545.9	568.0	589.1	607.5	624.1
152.5°	428.3	444.3	462.3	481.1	499.3	519.2	540.0	559.8	578.1	595.0	608.6
155°	437.3	451.1	466.7	482.4	497.1	513.7	531.2	547.7	562.4	576.2	587.3
157.5°	445.7	456.6	469.8	482.4	494.7	507.9	522.1	534.6	547.0	558.6	567.4
160°	450.1	460.3	471.3	482.4	492.5	503.5	515.5	526.6	536.6	546.8	554.1
162.5°	454.6	462.5	472.8	482.4	490.3	499.1	509.6	518.4	527.1	535.0	541.6
165°	459.3	464.9	473.2	480.5	486.0	492.5	499.9	507.2	512.7	519.2	523.8
167.5°	462.6	466.9	472.9	478.3	481.6	485.8	491.0	496.4	500.6	505.7	508.5
170°	464.9	467.6	472.2	476.8	478.6	481.4	485.1	489.7	492.5	496.1	498.9
172.5°	466.4	468.3	471.5	475.4	475.7	477.0	480.0	483.8	485.8	488.1	490.0
175°	468.6	468.6	470.4	473.2	472.2	472.2	474.0	475.9	476.8	478.6	478.6
177.5°	468.6	468.6	469.3	470.7	469.3	469.3	470.0	470.7	471.5	471.5	472.2
180°	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6



TEST NUMBER: P332921-927

CATALOG NUMBER: SA4XXRDIP-C575D1205U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0
2.5°	730.2	730.7	729.0	728.5	729.0	730.7	730.2	731.7	732.0	734.0	733.2
5°	677.5	676.8	675.3	675.7	675.3	676.8	677.5	679.9	681.2	686.1	685.5
7.5°	632.3	629.9	630.7	628.1	630.7	629.9	632.3	634.5	638.3	640.6	645.8
10°	604.8	601.3	598.6	596.1	598.6	601.3	604.8	605.9	611.2	613.7	618.9
12.5°	567.0	564.1	560.3	561.1	560.3	564.1	567.0	572.4	579.2	584.3	592.6
15°	513.5	508.9	501.5	502.4	501.5	508.9	513.5	517.5	524.3	536.0	541.5
17.5°	468.2	468.3	464.9	465.6	464.9	468.3	468.2	473.6	477.1	484.6	493.1
20°	444.7	442.6	442.9	442.0	442.9	442.6	444.7	451.2	455.0	460.2	469.4
22.5°	428.5	425.9	423.7	421.8	423.7	425.9	428.5	430.3	435.2	440.2	447.7
25°	401.0	399.2	396.4	395.8	396.4	399.2	401.0	403.8	406.2	412.7	417.3
27.5°	376.8	376.4	375.3	373.9	375.3	376.4	376.8	379.3	382.5	386.7	392.5
30°	362.7	362.2	361.6	360.6	361.6	362.2	362.7	365.3	367.7	371.1	375.7
32.5°	350.2	349.8	349.2	349.3	349.2	349.8	350.2	351.4	352.9	357.3	360.9
35°	332.2	331.9	331.4	331.1	331.4	331.9	332.2	333.5	334.5	335.6	338.7
37.5°	315.5	316.3	315.9	315.8	315.9	316.3	315.5	315.8	314.8	317.0	319.2
40°	303.9	304.2	304.8	304.5	304.8	304.2	303.9	304.2	304.2	304.2	306.1
42.5°	294.3	294.4	295.2	294.1	295.2	294.4	294.3	293.1	291.6	291.9	292.5
45°	277.1	278.9	278.6	278.6	278.6	278.9	277.1	275.0	274.6	273.4	273.4
47.5°	258.3	259.9	260.3	260.2	260.3	259.9	258.3	257.5	256.0	254.8	254.7
50°	246.0	245.3	246.3	246.0	246.3	245.3	246.0	244.4	242.2	242.2	241.6
52.5°	230.9	231.1	231.0	230.7	231.0	231.1	230.9	230.1	229.2	228.2	227.8
55°	207.7	208.0	207.5	207.7	207.5	208.0	207.7	207.5	207.5	206.8	207.5
57.5°	182.6	181.1	181.7	181.0	181.7	181.1	182.6	183.9	184.4	184.6	185.4
60°	164.6	162.2	161.5	160.3	161.5	162.2	164.6	167.7	168.9	169.5	170.5
62.5°	144.3	142.7	140.5	141.6	140.5	142.7	144.3	147.7	150.4	152.5	154.6
65°	117.4	116.2	115.3	116.5	115.3	116.2	117.4	119.9	122.4	127.3	131.9
67.5°	97.2	96.6	96.6	95.9	96.6	96.6	97.2	98.5	100.0	102.7	107.0
70°	86.6	85.7	85.7	85.1	85.7	85.7	86.6	86.6	88.2	89.4	92.4
72.5°	75.7	74.9	75.1	74.7	75.1	74.9	75.7	76.0	77.6	78.0	79.4
75°	56.1	54.6	54.6	54.9	54.6	54.6	56.1	57.9	59.5	62.3	62.9
77.5°	41.8	41.5	42.0	41.4	42.0	41.5	41.8	41.8	42.1	43.5	44.5
80°	34.2	33.9	33.6	34.5	33.6	33.9	34.2	34.2	34.5	34.9	35.2
82.5°	26.5	26.5	26.5	27.6	26.5	26.5	26.5	27.1	27.1	26.9	27.3
85°	16.0	15.4	16.0	15.4	16.0	15.4	16.0	15.7	16.0	15.7	16.0
87.5°	9.5	9.5	9.0	9.3	9.0	9.5	9.5	8.9	8.9	9.2	8.7
90°	19.3	20.3	19.3	19.3	19.3	20.3	19.3	18.4	18.4	17.5	16.6
92.5°	79.0	74.0	70.9	70.9	70.9	74.0	79.0	89.8	108.3	136.0	180.8
95°	281.7	253.2	236.5	224.6	236.5	253.2	281.7	326.8	416.1	539.4	682.1
97.5°	702.5	647.1	619.5	600.4	619.5	647.1	702.5	768.7	864.7	954.7	1007.8
100°	935.3	879.1	851.5	844.1	851.5	879.1	935.3	1015.3	1083.5	1128.5	1110.2
102.5°	1131.9	1091.2	1062.1	1056.2	1062.1	1091.2	1131.9	1181.0	1209.3	1196.3	1105.0
105°	1321.0	1313.6	1300.7	1295.1	1300.7	1313.6	1321.0	1319.1	1281.4	1190.3	1030.9
107.5°	1351.3	1372.3	1381.5	1383.9	1381.5	1372.3	1351.3	1305.8	1223.8	1095.4	925.8
110°	1321.8	1360.5	1377.1	1385.4	1377.1	1360.5	1321.8	1256.5	1155.2	1021.8	862.5



TEST NUMBER: P332921-927

CATALOG NUMBER: SA4XXRDIP-C575D1205U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1258.5	1305.3	1328.5	1342.0	1328.5	1305.3	1258.5	1184.3	1083.1	957.0	816.1
115°	1151.6	1206.8	1236.3	1243.6	1236.3	1206.8	1151.6	1078.9	990.5	882.8	769.5
117.5°	1062.1	1108.5	1138.3	1144.0	1138.3	1108.5	1062.1	1000.1	925.1	840.4	746.7
120°	1013.5	1054.0	1077.9	1088.1	1077.9	1054.0	1013.5	961.0	895.6	822.0	736.4
122.5°	978.9	1013.5	1033.7	1043.9	1033.7	1013.5	978.9	934.5	877.3	810.2	727.5
125°	942.6	969.3	986.8	992.3	986.8	969.3	942.6	905.8	855.2	791.6	712.5
127.5°	918.1	941.9	956.6	962.1	956.6	941.9	918.1	881.1	833.1	769.8	694.0
130°	901.2	924.2	938.9	944.4	938.9	924.2	901.2	863.5	814.7	752.1	679.4
132.5°	879.1	905.1	919.0	924.6	919.0	905.1	879.1	842.1	793.3	732.2	663.8
135°	841.4	867.1	881.9	887.4	881.9	867.1	841.4	804.5	758.5	702.3	642.5
137.5°	797.2	822.6	834.7	841.4	834.7	822.6	797.2	762.7	721.1	673.8	623.2
140°	767.7	788.0	800.8	808.2	800.8	788.0	767.7	735.5	696.8	655.4	612.1
142.5°	737.5	756.3	767.7	772.9	767.7	756.3	737.5	709.0	675.5	639.9	601.8
145°	695.0	710.7	719.9	724.5	719.9	710.7	695.0	672.0	646.2	618.6	587.3
147.5°	659.5	672.9	679.9	681.5	679.9	672.9	659.5	642.5	622.3	600.2	575.4
150°	638.8	650.8	656.3	657.3	656.3	650.8	638.8	624.1	607.5	589.1	568.0
152.5°	621.2	630.9	634.2	635.2	634.2	630.9	621.2	608.6	595.0	578.1	559.8
155°	596.5	603.9	606.7	606.7	606.7	603.9	596.5	587.3	576.2	562.4	547.7
157.5°	574.4	580.0	581.6	581.6	581.6	580.0	574.4	567.4	558.6	547.0	534.6
160°	559.7	565.2	566.1	566.1	566.1	565.2	559.7	554.1	546.8	536.6	526.6
162.5°	545.7	551.2	552.2	551.4	552.2	551.2	545.7	541.6	535.0	527.1	518.4
165°	527.4	531.2	530.2	529.3	530.2	531.2	527.4	523.8	519.2	512.7	507.2
167.5°	510.3	512.7	512.5	511.8	512.5	512.7	510.3	508.5	505.7	500.6	496.4
170°	500.7	501.7	500.7	500.7	500.7	501.7	500.7	498.9	496.1	492.5	489.7
172.5°	491.2	492.1	491.2	489.7	491.2	492.1	491.2	490.0	488.1	485.8	483.8
175°	478.6	480.5	478.6	476.8	478.6	480.5	478.6	478.6	478.6	476.8	475.9
177.5°	471.5	472.2	470.7	469.3	470.7	472.2	471.5	472.2	471.5	471.5	470.7
180°	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6



TEST NUMBER: P332921-927

CATALOG NUMBER: SA4XXRDIP-C575D1205U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0
2.5°	731.7	733.5	737.4	741.8	745.5	748.8	751.2	754.6	757.9	762.3	766.5
5°	687.3	691.7	697.8	705.2	714.5	720.6	728.3	735.1	745.0	754.9	764.4
7.5°	648.4	653.2	662.2	672.4	683.4	693.5	702.6	714.5	727.6	742.0	758.0
10°	623.2	628.4	639.3	650.9	663.9	673.8	686.1	700.3	715.1	732.6	752.3
12.5°	600.6	605.5	618.5	630.5	644.0	654.8	669.1	683.5	703.2	722.3	744.7
15°	556.3	569.6	584.4	598.6	614.6	627.9	645.1	659.9	678.7	705.5	731.1
17.5°	507.2	521.4	539.8	561.7	583.1	599.5	617.0	635.4	657.8	685.2	714.7
20°	478.6	490.0	510.4	534.8	559.8	582.6	598.6	618.9	642.1	671.6	702.1
22.5°	457.2	466.9	482.8	507.2	534.1	560.6	581.1	601.2	626.8	656.3	689.6
25°	425.0	435.5	449.4	466.0	496.9	524.9	551.8	574.8	602.0	631.5	668.5
27.5°	398.3	407.4	420.1	437.4	458.1	489.1	521.6	548.0	575.8	607.5	644.5
30°	382.5	389.9	400.4	418.0	437.7	465.4	498.4	529.3	557.3	590.3	628.8
32.5°	366.0	373.9	384.1	398.0	419.1	442.5	475.5	509.2	539.0	572.7	610.5
35°	344.0	350.1	359.4	373.6	392.7	413.0	442.3	477.1	508.6	544.6	580.7
37.5°	321.7	329.0	336.3	348.9	364.6	386.4	410.4	446.0	480.9	513.7	549.0
40°	309.1	313.5	321.5	331.7	348.3	367.7	390.2	425.0	459.9	492.6	528.0
42.5°	295.1	299.9	306.7	316.9	331.8	350.7	372.7	402.8	439.2	470.9	503.1
45°	275.5	278.3	285.1	293.7	306.1	325.2	345.5	372.3	406.5	436.7	465.1
47.5°	255.8	258.3	262.4	270.4	284.2	299.5	318.6	342.6	372.6	402.8	426.8
50°	242.2	244.4	248.4	255.8	268.2	283.3	302.1	323.6	350.5	379.5	399.4
52.5°	228.7	229.9	233.6	242.0	252.4	267.2	284.1	303.9	329.0	353.1	373.4
55°	207.2	209.9	212.4	218.6	228.4	242.6	257.7	276.5	295.9	316.2	333.5
57.5°	184.7	187.7	191.2	196.6	204.5	217.7	231.2	246.4	263.0	280.0	294.4
60°	169.8	172.6	175.7	181.9	188.9	199.4	214.2	227.4	240.1	255.5	270.0
62.5°	155.3	158.0	161.6	166.6	173.4	183.4	195.7	207.2	220.4	233.9	244.6
65°	133.8	135.9	138.7	143.3	149.8	158.8	168.9	177.8	189.6	199.4	209.3
67.5°	110.2	114.3	118.0	121.7	127.1	135.5	142.8	151.4	159.4	166.7	175.7
70°	94.6	99.3	102.7	106.6	111.9	119.0	126.0	131.9	138.4	145.4	153.5
72.5°	81.6	85.2	87.9	92.1	96.8	103.5	110.0	114.9	120.2	125.0	132.8
75°	64.4	66.0	67.8	71.2	75.5	80.5	85.7	90.0	93.1	97.4	103.0
77.5°	46.3	49.3	50.5	52.9	56.0	59.0	62.5	66.1	69.1	70.7	74.9
80°	35.4	36.7	37.9	41.3	43.2	46.3	48.7	52.1	53.3	54.9	58.9
82.5°	27.6	28.3	29.1	29.9	31.1	34.1	36.6	38.7	40.0	40.6	43.6
85°	16.0	16.3	16.6	17.0	17.3	17.3	18.5	20.0	22.2	22.2	23.1
87.5°	8.6	9.0	8.6	8.0	8.5	7.4	7.6	7.4	8.0	8.2	8.6
90°	15.7	16.6	14.7	12.9	12.9	7.4	7.4	6.4	5.5	2.8	1.0
92.5°	243.2	292.0	255.6	185.9	114.5	67.7	48.6	35.2	23.9	15.3	10.5
95°	771.4	750.2	566.1	346.1	195.1	115.1	76.4	54.3	42.4	33.1	30.3
97.5°	969.2	790.2	529.8	311.2	186.5	124.8	92.4	73.4	62.4	54.5	54.5
100°	975.7	740.1	480.5	292.7	188.7	134.4	105.0	87.5	76.4	69.9	69.9
102.5°	920.5	677.5	447.3	287.6	196.1	146.9	118.9	102.2	91.9	86.2	84.7
105°	820.1	603.9	418.8	289.9	213.6	169.4	142.7	126.1	115.1	110.4	107.7
107.5°	739.2	562.6	413.7	303.6	234.0	193.5	167.2	151.3	139.6	134.9	133.1
110°	698.7	548.7	415.2	313.9	249.5	209.0	184.1	167.5	156.5	151.9	150.0



TEST NUMBER: P332921-927

CATALOG NUMBER: SA4XXRDIP-C575D1205U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	675.8	542.0	419.5	325.0	264.2	225.1	200.3	183.7	173.4	168.1	166.3
115°	654.5	538.5	428.0	342.5	287.2	250.4	225.5	208.0	198.8	192.4	189.6
117.5°	644.9	537.6	437.0	360.3	309.5	274.5	248.7	232.3	222.2	216.5	213.9
120°	639.8	537.6	443.7	372.8	325.0	289.9	264.2	248.5	238.4	232.0	230.1
122.5°	633.9	536.9	450.4	384.6	339.7	304.7	279.6	262.5	253.2	246.7	244.9
125°	624.1	535.8	460.3	402.3	359.9	326.8	301.0	283.5	273.4	267.8	264.2
127.5°	611.0	533.7	468.2	417.6	378.7	346.7	320.7	302.5	290.9	284.2	281.3
130°	602.9	533.0	474.0	427.1	391.3	359.9	333.2	315.8	301.9	294.5	290.9
132.5°	595.6	532.3	479.2	436.7	401.6	370.3	345.0	326.1	313.0	303.4	300.5
135°	584.6	531.2	487.0	449.2	416.1	385.7	361.8	342.5	326.8	317.6	313.9
137.5°	575.0	530.9	491.5	458.0	427.1	398.8	376.0	355.8	341.0	330.8	327.3
140°	569.8	530.2	495.3	463.9	434.5	406.9	384.8	365.4	349.8	339.7	336.9
142.5°	565.4	530.2	498.2	468.3	441.1	414.2	392.8	374.3	359.3	350.0	347.2
145°	557.9	528.4	499.9	473.2	448.3	424.4	404.1	386.6	373.8	364.6	361.8
147.5°	551.0	525.1	500.7	477.4	455.7	433.2	414.9	400.4	387.1	379.1	378.1
150°	545.9	522.8	500.7	479.6	459.3	439.1	421.6	407.8	396.7	389.4	388.5
152.5°	540.0	519.2	499.3	481.1	462.3	444.3	428.3	415.9	405.6	398.2	398.0
155°	531.2	513.7	497.1	482.4	466.7	451.1	437.3	427.1	417.9	412.4	411.5
157.5°	522.1	507.9	494.7	482.4	469.8	456.6	445.7	436.9	429.7	424.5	424.5
160°	515.5	503.5	492.5	482.4	471.3	460.3	450.1	442.8	436.3	432.6	432.6
162.5°	509.6	499.1	490.3	482.4	472.8	462.5	454.6	447.9	442.2	439.3	440.0
165°	499.9	492.5	486.0	480.5	473.2	464.9	459.3	454.7	450.1	448.3	448.3
167.5°	491.0	485.8	481.6	478.3	472.9	466.9	462.6	460.1	456.6	455.7	456.6
170°	485.1	481.4	478.6	476.8	472.2	467.6	464.9	463.0	460.3	459.3	460.3
172.5°	480.0	477.0	475.7	475.4	471.5	468.3	466.4	465.2	463.2	463.0	463.9
175°	474.0	472.2	472.2	473.2	470.4	468.6	468.6	467.6	466.7	466.7	467.6
177.5°	470.0	469.3	469.3	470.7	469.3	468.6	468.6	468.6	467.8	468.6	469.3
180°	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6





TEST NUMBER: P332921-927

CATALOG NUMBER: SA4XXRDIP-C575D1205U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0
2.5°	769.7	771.9	774.4	779.0	783.0	784.7	788.2	790.7	789.9	793.4	799.3
5°	772.7	781.0	790.6	800.4	811.5	820.8	828.2	835.6	841.5	848.5	859.0
7.5°	772.2	787.0	803.1	820.8	839.0	854.7	869.3	884.1	897.1	911.6	930.3
10°	770.2	790.0	810.0	833.1	856.3	878.1	897.9	916.3	933.9	952.7	976.4
12.5°	768.0	790.7	814.9	842.7	871.6	897.9	921.1	947.7	969.6	993.9	1021.4
15°	758.2	788.8	821.7	857.8	892.3	927.7	959.5	992.2	1022.7	1051.6	1086.2
17.5°	747.0	782.2	821.1	863.7	905.2	948.2	986.0	1027.1	1058.3	1097.2	1129.3
20°	737.9	775.8	817.4	865.1	912.4	960.1	1001.7	1043.6	1078.8	1117.9	1158.6
22.5°	726.8	768.4	813.5	862.9	912.4	964.6	1010.6	1052.3	1095.8	1139.9	1181.8
25°	708.9	752.1	799.9	854.1	910.8	964.1	1013.4	1065.2	1112.1	1159.8	1197.5
27.5°	687.0	732.3	782.7	838.6	896.8	951.4	1009.5	1064.7	1111.8	1157.8	1190.6
30°	669.5	717.2	765.6	822.4	882.7	941.4	1003.5	1058.8	1108.3	1149.7	1168.2
32.5°	651.5	696.8	746.6	804.1	866.0	929.0	990.8	1047.2	1093.1	1117.8	1118.3
35°	620.1	662.7	714.5	770.9	834.3	902.8	965.4	1020.8	1048.8	1051.1	1020.8
37.5°	586.0	625.0	673.9	730.4	799.9	868.0	931.8	968.8	978.3	946.9	891.0
40°	561.6	597.6	644.8	702.7	771.8	842.1	900.3	927.4	917.6	866.7	804.5
42.5°	535.9	569.5	615.0	672.2	741.5	812.5	862.1	876.6	850.5	791.8	718.9
45°	494.1	524.9	569.9	627.6	694.1	760.7	798.3	790.9	747.4	677.8	596.1
47.5°	450.5	480.3	520.8	574.1	642.3	699.7	725.2	702.9	641.0	564.4	498.0
50°	421.7	452.2	489.5	540.3	602.6	658.1	674.4	640.5	571.7	498.1	437.0
52.5°	393.3	419.4	455.9	505.0	564.6	611.5	620.1	581.1	510.1	444.1	390.0
55°	350.1	373.9	404.7	450.9	502.4	542.2	537.6	487.3	422.9	366.5	323.9
57.5°	308.4	326.3	354.7	398.1	443.3	470.0	453.0	410.3	350.2	304.0	268.2
60°	280.8	297.5	323.9	361.9	401.6	416.7	402.5	356.0	308.6	266.3	236.1
62.5°	254.7	269.3	292.2	327.3	359.4	368.4	353.2	312.6	269.8	233.8	208.7
65°	216.7	230.2	249.7	274.6	296.8	301.1	291.3	249.7	217.3	187.1	169.8
67.5°	182.2	191.1	206.3	227.8	239.6	242.2	223.1	196.9	168.4	149.9	136.9
70°	159.1	165.2	179.4	191.1	200.7	201.0	183.4	162.4	140.5	125.5	115.9
72.5°	136.6	142.5	153.3	161.3	168.6	166.2	150.1	133.6	115.9	104.5	97.4
75°	105.4	110.7	116.2	119.9	119.9	116.8	105.1	92.8	82.6	75.8	73.7
77.5°	76.6	81.0	82.8	82.2	81.1	76.3	68.9	60.8	57.2	54.0	52.4
80°	60.1	61.9	62.6	61.0	59.2	53.6	48.7	45.3	41.9	40.7	40.1
82.5°	44.6	46.2	44.6	45.0	41.0	36.4	33.7	32.5	31.1	30.6	29.9
85°	23.8	23.4	22.8	21.2	18.5	17.9	17.6	17.3	16.6	17.0	16.3
87.5°	8.7	8.5	7.7	7.6	7.6	8.2	8.5	8.9	9.3	8.8	9.5
90°	2.8	5.5	6.4	7.4	7.4	12.9	12.9	14.7	16.6	15.7	16.6
92.5°	15.3	23.9	35.2	48.6	67.7	114.5	185.9	255.6	292.0	243.2	180.8
95°	33.1	42.4	54.3	76.4	115.1	195.1	346.1	566.1	750.2	771.4	682.1
97.5°	54.5	62.4	73.4	92.4	124.8	186.5	311.2	529.8	790.2	969.2	1007.8
100°	69.9	76.4	87.5	105.0	134.4	188.7	292.7	480.5	740.1	975.7	1110.2
102.5°	86.2	91.9	102.2	118.9	146.9	196.1	287.6	447.3	677.5	920.5	1105.0
105°	110.4	115.1	126.1	142.7	169.4	213.6	289.9	418.8	603.9	820.1	1030.9
107.5°	134.9	139.6	151.3	167.2	193.5	234.0	303.6	413.7	562.6	739.2	925.8
110°	151.9	156.5	167.5	184.1	209.0	249.5	313.9	415.2	548.7	698.7	862.5





TEST NUMBER: P332921-927

CATALOG NUMBER: SA4XXRDIP-C575D1205U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	168.1	173.4	183.7	200.3	225.1	264.2	325.0	419.5	542.0	675.8	816.1
115°	192.4	198.8	208.0	225.5	250.4	287.2	342.5	428.0	538.5	654.5	769.5
117.5°	216.5	222.2	232.3	248.7	274.5	309.5	360.3	437.0	537.6	644.9	746.7
120°	232.0	238.4	248.5	264.2	289.9	325.0	372.8	443.7	537.6	639.8	736.4
122.5°	246.7	253.2	262.5	279.6	304.7	339.7	384.6	450.4	536.9	633.9	727.5
125°	267.8	273.4	283.5	301.0	326.8	359.9	402.3	460.3	535.8	624.1	712.5
127.5°	284.2	290.9	302.5	320.7	346.7	378.7	417.6	468.2	533.7	611.0	694.0
130°	294.5	301.9	315.8	333.2	359.9	391.3	427.1	474.0	533.0	602.9	679.4
132.5°	303.4	313.0	326.1	345.0	370.3	401.6	436.7	479.2	532.3	595.6	663.8
135°	317.6	326.8	342.5	361.8	385.7	416.1	449.2	487.0	531.2	584.6	642.5
137.5°	330.8	341.0	355.8	376.0	398.8	427.1	458.0	491.5	530.9	575.0	623.2
140°	339.7	349.8	365.4	384.8	406.9	434.5	463.9	495.3	530.2	569.8	612.1
142.5°	350.0	359.3	374.3	392.8	414.2	441.1	468.3	498.2	530.2	565.4	601.8
145°	364.6	373.8	386.6	404.1	424.4	448.3	473.2	499.9	528.4	557.9	587.3
147.5°	379.1	387.1	400.4	414.9	433.2	455.7	477.4	500.7	525.1	551.0	575.4
150°	389.4	396.7	407.8	421.6	439.1	459.3	479.6	500.7	522.8	545.9	568.0
152.5°	398.2	405.6	415.9	428.3	444.3	462.3	481.1	499.3	519.2	540.0	559.8
155°	412.4	417.9	427.1	437.3	451.1	466.7	482.4	497.1	513.7	531.2	547.7
157.5°	424.5	429.7	436.9	445.7	456.6	469.8	482.4	494.7	507.9	522.1	534.6
160°	432.6	436.3	442.8	450.1	460.3	471.3	482.4	492.5	503.5	515.5	526.6
162.5°	439.3	442.2	447.9	454.6	462.5	472.8	482.4	490.3	499.1	509.6	518.4
165°	448.3	450.1	454.7	459.3	464.9	473.2	480.5	486.0	492.5	499.9	507.2
167.5°	455.7	456.6	460.1	462.6	466.9	472.9	478.3	481.6	485.8	491.0	496.4
170°	459.3	460.3	463.0	464.9	467.6	472.2	476.8	478.6	481.4	485.1	489.7
172.5°	463.0	463.2	465.2	466.4	468.3	471.5	475.4	475.7	477.0	480.0	483.8
175°	466.7	466.7	467.6	468.6	468.6	470.4	473.2	472.2	472.2	474.0	475.9
177.5°	468.6	467.8	468.6	468.6	468.6	469.3	470.7	469.3	469.3	470.0	470.7
180°	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6



TEST NUMBER: P332921-927

CATALOG NUMBER: SA4XXRDIP-C575D1205U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	765.0	765.0	765.0	765.0	765.0	765.0	765.0
2.5°	802.5	803.5	804.2	806.7	806.9	809.1	806.9
5°	868.9	873.2	880.0	886.8	887.4	891.7	884.0
7.5°	943.3	953.3	959.6	970.5	974.9	977.6	973.1
10°	994.7	1003.9	1020.3	1028.3	1036.3	1037.4	1033.8
12.5°	1044.2	1058.8	1071.7	1087.0	1086.6	1097.4	1093.4
15°	1110.2	1125.3	1143.2	1160.2	1166.3	1166.3	1171.2
17.5°	1157.3	1185.0	1203.5	1216.8	1231.4	1233.9	1232.2
20°	1189.1	1219.0	1238.7	1256.0	1265.9	1268.7	1268.7
22.5°	1212.8	1238.3	1257.5	1273.0	1281.2	1284.4	1283.4
25°	1229.2	1251.1	1262.8	1267.4	1269.6	1268.9	1263.1
27.5°	1206.7	1205.8	1198.3	1184.2	1173.5	1167.0	1159.7
30°	1163.9	1147.8	1129.3	1109.0	1082.8	1062.7	1056.6
32.5°	1100.0	1064.0	1032.7	998.8	970.6	950.5	942.1
35°	976.4	919.4	872.9	832.2	802.6	784.1	777.9
37.5°	829.9	774.7	717.1	677.6	653.1	634.4	627.4
40°	736.7	676.5	626.3	589.3	564.0	545.9	545.6
42.5°	651.6	594.2	546.9	520.3	493.1	481.0	480.9
45°	533.5	487.6	447.5	426.6	410.3	400.4	397.6
47.5°	441.7	403.8	377.1	360.4	347.1	340.8	336.7
50°	390.2	357.0	335.6	321.2	313.8	305.8	305.1
52.5°	347.3	320.4	303.9	292.1	282.7	277.9	278.1
55°	291.9	270.6	258.9	249.9	242.6	238.8	237.3
57.5°	245.9	230.0	221.4	213.3	210.1	207.2	206.4
60°	217.3	206.5	198.5	192.0	187.4	186.5	186.2
62.5°	193.6	182.4	176.8	171.8	168.4	167.0	166.4
65°	159.6	151.3	146.4	142.4	141.2	139.0	138.7
67.5°	128.7	123.7	120.5	117.7	116.0	115.9	115.9
70°	109.7	106.9	104.2	102.7	101.7	101.1	101.1
72.5°	93.5	91.4	89.1	88.3	88.2	87.5	87.3
75°	71.2	69.1	69.3	67.8	66.5	65.0	64.1
77.5°	50.5	49.0	48.6	48.5	47.4	47.2	47.7
80°	39.1	37.6	37.3	37.6	37.3	36.4	36.4
82.5°	29.8	28.5	28.2	28.0	27.6	28.0	27.5
85°	16.0	15.4	15.4	15.4	16.0	15.7	15.4
87.5°	9.2	9.1	9.3	9.3	9.5	9.0	9.3
90°	17.5	18.4	18.4	19.3	20.3	19.3	19.3
92.5°	136.0	108.3	89.8	79.0	74.0	70.9	70.9
95°	539.4	416.1	326.8	281.7	253.2	236.5	224.6
97.5°	954.7	864.7	768.7	702.5	647.1	619.5	600.4
100°	1128.5	1083.5	1015.3	935.3	879.1	851.5	844.1
102.5°	1196.3	1209.3	1181.0	1131.9	1091.2	1062.1	1056.2
105°	1190.3	1281.4	1319.1	1321.0	1313.6	1300.7	1295.1
107.5°	1095.4	1223.8	1305.8	1351.3	1372.3	1381.5	1383.9
110°	1021.8	1155.2	1256.5	1321.8	1360.5	1377.1	1385.4



TEST NUMBER: P332921-927

CATALOG NUMBER: SA4XXRDIP-C575D1205U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	957.0	1083.1	1184.3	1258.5	1305.3	1328.5	1342.0
115°	882.8	990.5	1078.9	1151.6	1206.8	1236.3	1243.6
117.5°	840.4	925.1	1000.1	1062.1	1108.5	1138.3	1144.0
120°	822.0	895.6	961.0	1013.5	1054.0	1077.9	1088.1
122.5°	810.2	877.3	934.5	978.9	1013.5	1033.7	1043.9
125°	791.6	855.2	905.8	942.6	969.3	986.8	992.3
127.5°	769.8	833.1	881.1	918.1	941.9	956.6	962.1
130°	752.1	814.7	863.5	901.2	924.2	938.9	944.4
132.5°	732.2	793.3	842.1	879.1	905.1	919.0	924.6
135°	702.3	758.5	804.5	841.4	867.1	881.9	887.4
137.5°	673.8	721.1	762.7	797.2	822.6	834.7	841.4
140°	655.4	696.8	735.5	767.7	788.0	800.8	808.2
142.5°	639.9	675.5	709.0	737.5	756.3	767.7	772.9
145°	618.6	646.2	672.0	695.0	710.7	719.9	724.5
147.5°	600.2	622.3	642.5	659.5	672.9	679.9	681.5
150°	589.1	607.5	624.1	638.8	650.8	656.3	657.3
152.5°	578.1	595.0	608.6	621.2	630.9	634.2	635.2
155°	562.4	576.2	587.3	596.5	603.9	606.7	606.7
157.5°	547.0	558.6	567.4	574.4	580.0	581.6	581.6
160°	536.6	546.8	554.1	559.7	565.2	566.1	566.1
162.5°	527.1	535.0	541.6	545.7	551.2	552.2	551.4
165°	512.7	519.2	523.8	527.4	531.2	530.2	529.3
167.5°	500.6	505.7	508.5	510.3	512.7	512.5	511.8
170°	492.5	496.1	498.9	500.7	501.7	500.7	500.7
172.5°	485.8	488.1	490.0	491.2	492.1	491.2	489.7
175°	476.8	478.6	478.6	478.6	480.5	478.6	476.8
177.5°	471.5	471.5	472.2	471.5	472.2	470.7	469.3
180°	468.6	468.6	468.6	468.6	468.6	468.6	468.6

(END OF REPORT)