

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332897-927

Luminaire Tested: **SA4XXRDIP-C575D365U927-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332897-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXRDIP-C575D365U927-4F0-1E-UDD-A4  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 575 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2971.0 lumens  
Efficiency: N/A  
Efficacy: 108.0 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 27.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332897-927  
CATALOG NUMBER: SA4XXRDIP-C575D365U927-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P332897-927

CATALOG NUMBER: SA4XXRDIP-C575D365U927-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	92	92	92	80	80	80	70	70	70	65
1	102	98	94	90	96	92	89	86	81	79	77	72	70	68	63	62	60	56
2	93	86	80	75	87	81	76	71	72	68	65	64	61	58	56	54	52	48
3	85	76	69	63	80	72	66	60	64	59	55	57	53	50	50	47	45	41
4	78	68	60	54	74	64	57	52	57	52	47	51	47	43	45	42	39	36
5	72	61	53	47	68	58	50	45	52	46	41	46	41	38	41	37	34	31
6	67	55	47	41	63	52	45	39	47	41	36	42	37	33	37	33	30	28
7	62	50	42	36	58	47	40	35	43	37	32	38	33	30	34	30	27	25
8	58	45	37	32	54	43	36	31	39	33	29	35	30	27	31	28	25	22
9	54	41	34	29	51	40	33	28	36	30	26	32	28	24	29	25	22	20
10	50	38	31	26	47	36	30	25	33	27	24	30	25	22	27	23	20	18

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	6176	6176	6176	6176
5°	7164	6195	5476	6195
10°	8475	6167	4887	6167
15°	9789	6110	4199	6110
20°	10899	6032	3797	6032
25°	11251	5955	3526	5955
30°	9849	5862	3361	5862
35°	7666	5723	3263	5723
40°	5750	5564	3209	5564
45°	4539	5310	3181	5310
50°	3832	5016	3090	5016
55°	3340	4694	2923	4694
60°	3006	4359	2588	4359
65°	2649	3998	2225	3998
70°	2386	3623	2009	3623
75°	1999	3213	1712	3213
80°	1692	2738	1604	2738
85°	1426	2140	1426	2140



TEST NUMBER: P332897-927

CATALOG NUMBER: SA4XXRDIP-C575D365U927-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	74.1	2.5
10°-20°	223.6	7.5
20°-30°	349.7	11.8
30°-40°	388.8	13.1
40°-50°	344.9	11.6
50°-60°	268.8	9.0
60°-70°	176.0	5.9
70°-80°	86.5	2.9
80°-90°	22.1	0.7
90°-100°	102.9	3.5
100°-110°	214.2	7.2
110°-120°	191.9	6.5
120°-130°	161.4	5.4
130°-140°	134.6	4.5
140°-150°	102.8	3.5
150°-160°	72.3	2.4
160°-170°	42.5	1.4
170°-180°	13.8	0.5
0°-30°	647.4	21.8
0°-40°	1036.2	34.9
0°-60°	1649.9	55.5
0°-90°	1934.6	65.1
90°-120°	509.0	17.1
90°-150°	907.8	30.6
90°-180°	1036.0	34.9
0°-180°	2971.0	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	765	765	765	765	765	
5°	884	764	676	764	884	89
15°	1171	731	502	731	1171	333
25°	1263	668	396	668	1263	560
35°	778	581	331	581	778	488
45°	398	465	279	465	398	315
55°	237	334	208	334	237	216
65°	139	209	116	209	139	140
75°	64	103	55	103	64	71
85°	15	23	15	23	15	18
90°	6	0	6	0	6	5
95°	68	9	68	9	68	106
105°	394	33	394	33	394	389
115°	378	58	378	58	378	375
125°	302	80	302	80	302	274
135°	270	96	270	96	270	208
145°	220	110	220	110	220	140
155°	184	125	184	125	184	86
165°	161	136	161	136	161	46
175°	145	142	145	142	145	14
180°	142	142	142	142	142	



TEST NUMBER: P332897-927

CATALOG NUMBER: SA4XXRDIP-C575D365U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0
2.5°	806.9	809.1	806.9	806.7	804.2	803.5	802.5	799.3	793.4	789.9	790.7
5°	884.0	891.7	887.4	886.8	880.0	873.2	868.9	859.0	848.5	841.5	835.6
7.5°	973.1	977.6	974.9	970.5	959.6	953.3	943.3	930.3	911.6	897.1	884.1
10°	1033.8	1037.4	1036.3	1028.3	1020.3	1003.9	994.7	976.4	952.7	933.9	916.3
12.5°	1093.4	1097.4	1086.6	1087.0	1071.7	1058.8	1044.2	1021.4	993.9	969.6	947.7
15°	1171.2	1166.3	1166.3	1160.2	1143.2	1125.3	1110.2	1086.2	1051.6	1022.7	992.2
17.5°	1232.2	1233.9	1231.4	1216.8	1203.5	1185.0	1157.3	1129.3	1097.2	1058.3	1027.1
20°	1268.7	1268.7	1265.9	1256.0	1238.7	1219.0	1189.1	1158.6	1117.9	1078.8	1043.6
22.5°	1283.4	1284.4	1281.2	1273.0	1257.5	1238.3	1212.8	1181.8	1139.9	1095.8	1052.3
25°	1263.1	1268.9	1269.6	1267.4	1262.8	1251.1	1229.2	1197.5	1159.8	1112.1	1065.2
27.5°	1159.7	1167.0	1173.5	1184.2	1198.3	1205.8	1206.7	1190.6	1157.8	1111.8	1064.7
30°	1056.6	1062.7	1082.8	1109.0	1129.3	1147.8	1163.9	1168.2	1149.7	1108.3	1058.8
32.5°	942.1	950.5	970.6	998.8	1032.7	1064.0	1100.0	1118.3	1117.8	1093.1	1047.2
35°	777.9	784.1	802.6	832.2	872.9	919.4	976.4	1020.8	1051.1	1048.8	1020.8
37.5°	627.4	634.4	653.1	677.6	717.1	774.7	829.9	891.0	946.9	978.3	968.8
40°	545.6	545.9	564.0	589.3	626.3	676.5	736.7	804.5	866.7	917.6	927.4
42.5°	480.9	481.0	493.1	520.3	546.9	594.2	651.6	718.9	791.8	850.5	876.6
45°	397.6	400.4	410.3	426.6	447.5	487.6	533.5	596.1	677.8	747.4	790.9
47.5°	336.7	340.8	347.1	360.4	377.1	403.8	441.7	498.0	564.4	641.0	702.9
50°	305.1	305.8	313.8	321.2	335.6	357.0	390.2	437.0	498.1	571.7	640.5
52.5°	278.1	277.9	282.7	292.1	303.9	320.4	347.3	390.0	444.1	510.1	581.1
55°	237.3	238.8	242.6	249.9	258.9	270.6	291.9	323.9	366.5	422.9	487.3
57.5°	206.4	207.2	210.1	213.3	221.4	230.0	245.9	268.2	304.0	350.2	410.3
60°	186.2	186.5	187.4	192.0	198.5	206.5	217.3	236.1	266.3	308.6	356.0
62.5°	166.4	167.0	168.4	171.8	176.8	182.4	193.6	208.7	233.8	269.8	312.6
65°	138.7	139.0	141.2	142.4	146.4	151.3	159.6	169.8	187.1	217.3	249.7
67.5°	115.9	115.9	116.0	117.7	120.5	123.7	128.7	136.9	149.9	168.4	196.9
70°	101.1	101.1	101.7	102.7	104.2	106.9	109.7	115.9	125.5	140.5	162.4
72.5°	87.3	87.5	88.2	88.3	89.1	91.4	93.5	97.4	104.5	115.9	133.6
75°	64.1	65.0	66.5	67.8	69.3	69.1	71.2	73.7	75.8	82.6	92.8
77.5°	47.7	47.2	47.4	48.5	48.6	49.0	50.5	52.4	54.0	57.2	60.8
80°	36.4	36.4	37.3	37.6	37.3	37.6	39.1	40.1	40.7	41.9	45.3
82.5°	27.5	28.0	27.6	28.0	28.2	28.5	29.8	29.9	30.6	31.1	32.5
85°	15.4	15.7	16.0	15.4	15.4	15.4	16.0	16.3	17.0	16.6	17.3
87.5°	6.6	6.3	6.7	6.6	6.8	6.6	6.7	7.2	6.7	6.9	6.8
90°	5.9	5.9	6.2	5.9	5.6	5.6	5.3	5.1	4.8	5.1	4.5
92.5°	21.5	21.5	22.5	24.0	27.3	33.0	41.4	55.0	74.0	88.8	77.7
95°	68.3	71.9	77.0	85.6	99.4	126.5	164.1	207.5	234.6	228.1	172.2
97.5°	182.6	188.5	196.9	213.7	233.8	263.0	290.4	306.5	294.8	240.3	161.1
100°	256.7	259.0	267.4	284.5	308.8	329.5	343.3	337.6	296.8	225.1	146.2
102.5°	321.2	323.1	331.9	344.3	359.2	367.8	363.8	336.1	280.0	206.0	136.1
105°	394.0	395.6	399.5	401.8	401.2	389.8	362.0	313.5	249.5	183.6	127.4
107.5°	420.9	420.2	417.4	411.0	397.2	372.2	333.2	281.6	224.8	171.1	125.8
110°	421.4	418.8	413.8	402.0	382.1	351.4	310.8	262.4	212.5	166.8	126.3



TEST NUMBER: P332897-927

CATALOG NUMBER: SA4XXRDIP-C575D365U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	408.1	404.1	397.0	382.8	360.2	329.4	291.0	248.2	205.6	164.9	127.6
115°	378.3	376.0	367.0	350.2	328.1	301.3	268.5	234.1	199.1	163.8	130.2
117.5°	347.9	346.2	337.2	323.1	304.2	281.4	255.6	227.1	196.1	163.5	132.9
120°	331.0	327.9	320.6	308.2	292.3	272.4	250.0	223.9	194.6	163.5	135.0
122.5°	317.5	314.4	308.2	297.7	284.2	266.8	246.4	221.3	192.8	163.3	137.0
125°	301.8	300.2	294.9	286.7	275.5	260.1	240.7	216.7	189.8	163.0	140.0
127.5°	292.6	291.0	286.5	279.2	268.0	253.4	234.1	211.1	185.8	162.3	142.4
130°	287.2	285.6	281.1	274.1	262.6	247.8	228.8	206.6	183.4	162.1	144.2
132.5°	281.2	279.6	275.3	267.4	256.1	241.3	222.7	201.9	181.2	161.9	145.8
135°	269.9	268.2	263.7	255.9	244.7	230.7	213.7	195.4	177.8	161.5	148.1
137.5°	255.9	253.9	250.2	242.5	232.0	219.4	204.9	189.6	174.9	161.5	149.5
140°	245.8	243.6	239.6	233.5	223.7	211.9	199.3	186.2	173.3	161.3	150.6
142.5°	235.0	233.5	230.0	224.3	215.6	205.4	194.6	183.1	172.0	161.3	151.5
145°	220.3	219.0	216.1	211.4	204.4	196.5	188.1	178.6	169.7	160.7	152.0
147.5°	207.3	206.8	204.7	200.6	195.4	189.3	182.5	175.0	167.6	159.7	152.3
150°	199.9	199.6	198.0	194.3	189.8	184.8	179.2	172.8	166.0	159.0	152.3
152.5°	193.2	192.9	191.9	188.9	185.1	181.0	175.9	170.3	164.2	157.9	151.9
155°	184.5	184.5	183.6	181.4	178.6	175.2	171.0	166.6	161.5	156.2	151.2
157.5°	176.9	176.9	176.4	174.7	172.6	169.9	166.4	162.6	158.8	154.5	150.4
160°	172.2	172.2	171.9	170.2	168.6	166.3	163.2	160.2	156.8	153.1	149.8
162.5°	167.7	167.9	167.6	166.0	164.8	162.7	160.3	157.7	155.0	151.8	149.1
165°	161.0	161.3	161.5	160.4	159.3	157.9	156.0	154.2	152.0	149.8	147.8
167.5°	155.7	155.9	156.0	155.2	154.6	153.8	152.3	151.0	149.3	147.7	146.5
170°	152.3	152.3	152.6	152.3	151.8	150.9	149.8	148.9	147.6	146.4	145.6
172.5°	148.9	149.4	149.6	149.4	149.1	148.5	147.7	147.2	146.0	145.0	144.7
175°	145.0	145.6	146.2	145.6	145.6	145.6	145.0	144.7	144.2	143.6	143.6
177.5°	142.8	143.1	143.6	143.4	143.6	143.4	143.4	143.1	143.0	142.8	142.8
180°	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5



TEST NUMBER: P332897-927

CATALOG NUMBER: SA4XXRDIP-C575D365U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0
2.5°	788.2	784.7	783.0	779.0	774.4	771.9	769.7	766.5	762.3	757.9	754.6
5°	828.2	820.8	811.5	800.4	790.6	781.0	772.7	764.4	754.9	745.0	735.1
7.5°	869.3	854.7	839.0	820.8	803.1	787.0	772.2	758.0	742.0	727.6	714.5
10°	897.9	878.1	856.3	833.1	810.0	790.0	770.2	752.3	732.6	715.1	700.3
12.5°	921.1	897.9	871.6	842.7	814.9	790.7	768.0	744.7	722.3	703.2	683.5
15°	959.5	927.7	892.3	857.8	821.7	788.8	758.2	731.1	705.5	678.7	659.9
17.5°	986.0	948.2	905.2	863.7	821.1	782.2	747.0	714.7	685.2	657.8	635.4
20°	1001.7	960.1	912.4	865.1	817.4	775.8	737.9	702.1	671.6	642.1	618.9
22.5°	1010.6	964.6	912.4	862.9	813.5	768.4	726.8	689.6	656.3	626.8	601.2
25°	1013.4	964.1	910.8	854.1	799.9	752.1	708.9	668.5	631.5	602.0	574.8
27.5°	1009.5	951.4	896.8	838.6	782.7	732.3	687.0	644.5	607.5	575.8	548.0
30°	1003.5	941.4	882.7	822.4	765.6	717.2	669.5	628.8	590.3	557.3	529.3
32.5°	990.8	929.0	866.0	804.1	746.6	696.8	651.5	610.5	572.7	539.0	509.2
35°	965.4	902.8	834.3	770.9	714.5	662.7	620.1	580.7	544.6	508.6	477.1
37.5°	931.8	868.0	799.9	730.4	673.9	625.0	586.0	549.0	513.7	480.9	446.0
40°	900.3	842.1	771.8	702.7	644.8	597.6	561.6	528.0	492.6	459.9	425.0
42.5°	862.1	812.5	741.5	672.2	615.0	569.5	535.9	503.1	470.9	439.2	402.8
45°	798.3	760.7	694.1	627.6	569.9	524.9	494.1	465.1	436.7	406.5	372.3
47.5°	725.2	699.7	642.3	574.1	520.8	480.3	450.5	426.8	402.8	372.6	342.6
50°	674.4	658.1	602.6	540.3	489.5	452.2	421.7	399.4	379.5	350.5	323.6
52.5°	620.1	611.5	564.6	505.0	455.9	419.4	393.3	373.4	353.1	329.0	303.9
55°	537.6	542.2	502.4	450.9	404.7	373.9	350.1	333.5	316.2	295.9	276.5
57.5°	453.0	470.0	443.3	398.1	354.7	326.3	308.4	294.4	280.0	263.0	246.4
60°	402.5	416.7	401.6	361.9	323.9	297.5	280.8	270.0	255.5	240.1	227.4
62.5°	353.2	368.4	359.4	327.3	292.2	269.3	254.7	244.6	233.9	220.4	207.2
65°	291.3	301.1	296.8	274.6	249.7	230.2	216.7	209.3	199.4	189.6	177.8
67.5°	223.1	242.2	239.6	227.8	206.3	191.1	182.2	175.7	166.7	159.4	151.4
70°	183.4	201.0	200.7	191.1	179.4	165.2	159.1	153.5	145.4	138.4	131.9
72.5°	150.1	166.2	168.6	161.3	153.3	142.5	136.6	132.8	125.0	120.2	114.9
75°	105.1	116.8	119.9	119.9	116.2	110.7	105.4	103.0	97.4	93.1	90.0
77.5°	68.9	76.3	81.1	82.2	82.8	81.0	76.6	74.9	70.7	69.1	66.1
80°	48.7	53.6	59.2	61.0	62.6	61.9	60.1	58.9	54.9	53.3	52.1
82.5°	33.7	36.4	41.0	45.0	44.6	46.2	44.6	43.6	40.6	40.0	38.7
85°	17.6	17.9	18.5	21.2	22.8	23.4	23.8	23.1	22.2	22.2	20.0
87.5°	6.7	6.4	6.6	6.6	6.8	7.8	8.3	8.5	7.8	7.2	6.6
90°	3.9	3.9	2.2	2.2	2.0	1.7	0.9	0.3	0.9	1.7	2.0
92.5°	56.6	34.9	20.6	14.8	10.7	7.3	4.7	3.2	4.7	7.3	10.7
95°	105.3	59.3	35.0	23.2	16.6	12.9	10.1	9.3	10.1	12.9	16.6
97.5°	94.7	56.7	37.9	28.1	22.3	19.0	16.6	16.6	16.6	19.0	22.3
100°	89.0	57.4	40.9	31.9	26.6	23.2	21.3	21.3	21.3	23.2	26.6
102.5°	87.5	59.7	44.7	36.2	31.1	28.0	26.2	25.7	26.2	28.0	31.1
105°	88.2	65.0	51.5	43.4	38.3	35.0	33.6	32.8	33.6	35.0	38.3
107.5°	92.4	71.1	58.9	50.9	46.0	42.5	41.0	40.5	41.0	42.5	46.0
110°	95.5	75.9	63.5	56.0	50.9	47.6	46.2	45.6	46.2	47.6	50.9





TEST NUMBER: P332897-927

CATALOG NUMBER: SA4XXRDIP-C575D365U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	98.9	80.3	68.4	60.9	55.8	52.8	51.1	50.5	51.1	52.8	55.8
115°	104.2	87.4	76.1	68.6	63.3	60.4	58.5	57.7	58.5	60.4	63.3
117.5°	109.6	94.1	83.5	75.7	70.7	67.6	65.8	65.0	65.8	67.6	70.7
120°	113.4	98.9	88.2	80.3	75.6	72.5	70.6	70.0	70.6	72.5	75.6
122.5°	117.0	103.3	92.7	85.1	79.9	77.0	75.0	74.5	75.0	77.0	79.9
125°	122.3	109.5	99.4	91.6	86.3	83.2	81.4	80.3	81.4	83.2	86.3
127.5°	127.0	115.2	105.4	97.5	92.0	88.5	86.4	85.6	86.4	88.5	92.0
130°	129.9	119.0	109.5	101.3	96.0	91.8	89.6	88.5	89.6	91.8	96.0
132.5°	132.8	122.2	112.6	105.0	99.2	95.2	92.3	91.4	92.3	95.2	99.2
135°	136.7	126.5	117.3	110.0	104.2	99.4	96.6	95.5	96.6	99.4	104.2
137.5°	139.3	129.9	121.3	114.3	108.2	103.7	100.6	99.6	100.6	103.7	108.2
140°	141.1	132.1	123.7	117.0	111.1	106.4	103.3	102.5	103.3	106.4	111.1
142.5°	142.4	134.2	126.0	119.5	113.8	109.3	106.5	105.6	106.5	109.3	113.8
145°	143.9	136.3	129.0	122.9	117.6	113.7	110.9	110.0	110.9	113.7	117.6
147.5°	145.2	138.6	131.7	126.2	121.8	117.8	115.3	115.0	115.3	117.8	121.8
150°	145.8	139.7	133.6	128.3	124.1	120.6	118.4	118.1	118.4	120.6	124.1
152.5°	146.3	140.6	135.1	130.2	126.5	123.3	121.1	121.0	121.1	123.3	126.5
155°	146.7	142.0	137.2	133.0	129.9	127.1	125.4	125.2	125.4	127.1	129.9
157.5°	146.7	142.9	138.9	135.5	132.8	130.7	129.1	129.1	129.1	130.7	132.8
160°	146.7	143.4	140.0	136.9	134.7	132.7	131.6	131.6	131.6	132.7	134.7
162.5°	146.7	143.8	140.7	138.2	136.3	134.5	133.6	133.8	133.6	134.5	136.3
165°	146.2	143.9	141.4	139.7	138.3	136.9	136.3	136.3	136.3	136.9	138.3
167.5°	145.4	143.9	142.0	140.7	139.9	138.9	138.6	138.9	138.6	138.9	139.9
170°	145.0	143.6	142.2	141.4	140.9	140.0	139.7	140.0	139.7	140.0	140.9
172.5°	144.6	143.4	142.4	141.8	141.5	140.9	140.9	141.1	140.9	140.9	141.5
175°	143.9	143.1	142.5	142.5	142.2	142.0	142.0	142.2	142.0	142.0	142.2
177.5°	143.1	142.8	142.5	142.5	142.5	142.3	142.5	142.8	142.5	142.3	142.5
180°	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5



TEST NUMBER: P332897-927

CATALOG NUMBER: SA4XXRDIP-C575D365U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0
2.5°	751.2	748.8	745.5	741.8	737.4	733.5	731.7	733.2	734.0	732.0	731.7
5°	728.3	720.6	714.5	705.2	697.8	691.7	687.3	685.5	686.1	681.2	679.9
7.5°	702.6	693.5	683.4	672.4	662.2	653.2	648.4	645.8	640.6	638.3	634.5
10°	686.1	673.8	663.9	650.9	639.3	628.4	623.2	618.9	613.7	611.2	605.9
12.5°	669.1	654.8	644.0	630.5	618.5	605.5	600.6	592.6	584.3	579.2	572.4
15°	645.1	627.9	614.6	598.6	584.4	569.6	556.3	541.5	536.0	524.3	517.5
17.5°	617.0	599.5	583.1	561.7	539.8	521.4	507.2	493.1	484.6	477.1	473.6
20°	598.6	582.6	559.8	534.8	510.4	490.0	478.6	469.4	460.2	455.0	451.2
22.5°	581.1	560.6	534.1	507.2	482.8	466.9	457.2	447.7	440.2	435.2	430.3
25°	551.8	524.9	496.9	466.0	449.4	435.5	425.0	417.3	412.7	406.2	403.8
27.5°	521.6	489.1	458.1	437.4	420.1	407.4	398.3	392.5	386.7	382.5	379.3
30°	498.4	465.4	437.7	418.0	400.4	389.9	382.5	375.7	371.1	367.7	365.3
32.5°	475.5	442.5	419.1	398.0	384.1	373.9	366.0	360.9	357.3	352.9	351.4
35°	442.3	413.0	392.7	373.6	359.4	350.1	344.0	338.7	335.6	334.5	333.5
37.5°	410.4	386.4	364.6	348.9	336.3	329.0	321.7	319.2	317.0	314.8	315.8
40°	390.2	367.7	348.3	331.7	321.5	313.5	309.1	306.1	304.2	304.2	304.2
42.5°	372.7	350.7	331.8	316.9	306.7	299.9	295.1	292.5	291.9	291.6	293.1
45°	345.5	325.2	306.1	293.7	285.1	278.3	275.5	273.4	273.4	274.6	275.0
47.5°	318.6	299.5	284.2	270.4	262.4	258.3	255.8	254.7	254.8	256.0	257.5
50°	302.1	283.3	268.2	255.8	248.4	244.4	242.2	241.6	242.2	242.2	244.4
52.5°	284.1	267.2	252.4	242.0	233.6	229.9	228.7	227.8	228.2	229.2	230.1
55°	257.7	242.6	228.4	218.6	212.4	209.9	207.2	207.5	206.8	207.5	207.5
57.5°	231.2	217.7	204.5	196.6	191.2	187.7	184.7	185.4	184.6	184.4	183.9
60°	214.2	199.4	188.9	181.9	175.7	172.6	169.8	170.5	169.5	168.9	167.7
62.5°	195.7	183.4	173.4	166.6	161.6	158.0	155.3	154.6	152.5	150.4	147.7
65°	168.9	158.8	149.8	143.3	138.7	135.9	133.8	131.9	127.3	122.4	119.9
67.5°	142.8	135.5	127.1	121.7	118.0	114.3	110.2	107.0	102.7	100.0	98.5
70°	126.0	119.0	111.9	106.6	102.7	99.3	94.6	92.4	89.4	88.2	86.6
72.5°	110.0	103.5	96.8	92.1	87.9	85.2	81.6	79.4	78.0	77.6	76.0
75°	85.7	80.5	75.5	71.2	67.8	66.0	64.4	62.9	62.3	59.5	57.9
77.5°	62.5	59.0	56.0	52.9	50.5	49.3	46.3	44.5	43.5	42.1	41.8
80°	48.7	46.3	43.2	41.3	37.9	36.7	35.4	35.2	34.9	34.5	34.2
82.5°	36.6	34.1	31.1	29.9	29.1	28.3	27.6	27.3	26.9	27.1	27.1
85°	18.5	17.3	17.3	17.0	16.6	16.3	16.0	16.0	15.7	16.0	15.7
87.5°	6.6	6.3	6.7	6.2	6.6	6.7	6.3	6.4	6.7	6.3	6.3
90°	2.2	2.2	3.9	3.9	4.5	5.1	4.8	5.1	5.3	5.6	5.6
92.5°	14.8	20.6	34.9	56.6	77.7	88.8	74.0	55.0	41.4	33.0	27.3
95°	23.2	35.0	59.3	105.3	172.2	228.1	234.6	207.5	164.1	126.5	99.4
97.5°	28.1	37.9	56.7	94.7	161.1	240.3	294.8	306.5	290.4	263.0	233.8
100°	31.9	40.9	57.4	89.0	146.2	225.1	296.8	337.6	343.3	329.5	308.8
102.5°	36.2	44.7	59.7	87.5	136.1	206.0	280.0	336.1	363.8	367.8	359.2
105°	43.4	51.5	65.0	88.2	127.4	183.6	249.5	313.5	362.0	389.8	401.2
107.5°	50.9	58.9	71.1	92.4	125.8	171.1	224.8	281.6	333.2	372.2	397.2
110°	56.0	63.5	75.9	95.5	126.3	166.8	212.5	262.4	310.8	351.4	382.1



TEST NUMBER: P332897-927

CATALOG NUMBER: SA4XXRDIP-C575D365U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	60.9	68.4	80.3	98.9	127.6	164.9	205.6	248.2	291.0	329.4	360.2
115°	68.6	76.1	87.4	104.2	130.2	163.8	199.1	234.1	268.5	301.3	328.1
117.5°	75.7	83.5	94.1	109.6	132.9	163.5	196.1	227.1	255.6	281.4	304.2
120°	80.3	88.2	98.9	113.4	135.0	163.5	194.6	223.9	250.0	272.4	292.3
122.5°	85.1	92.7	103.3	117.0	137.0	163.3	192.8	221.3	246.4	266.8	284.2
125°	91.6	99.4	109.5	122.3	140.0	163.0	189.8	216.7	240.7	260.1	275.5
127.5°	97.5	105.4	115.2	127.0	142.4	162.3	185.8	211.1	234.1	253.4	268.0
130°	101.3	109.5	119.0	129.9	144.2	162.1	183.4	206.6	228.8	247.8	262.6
132.5°	105.0	112.6	122.2	132.8	145.8	161.9	181.2	201.9	222.7	241.3	256.1
135°	110.0	117.3	126.5	136.7	148.1	161.5	177.8	195.4	213.7	230.7	244.7
137.5°	114.3	121.3	129.9	139.3	149.5	161.5	174.9	189.6	204.9	219.4	232.0
140°	117.0	123.7	132.1	141.1	150.6	161.3	173.3	186.2	199.3	211.9	223.7
142.5°	119.5	126.0	134.2	142.4	151.5	161.3	172.0	183.1	194.6	205.4	215.6
145°	122.9	129.0	136.3	143.9	152.0	160.7	169.7	178.6	188.1	196.5	204.4
147.5°	126.2	131.7	138.6	145.2	152.3	159.7	167.6	175.0	182.5	189.3	195.4
150°	128.3	133.6	139.7	145.8	152.3	159.0	166.0	172.8	179.2	184.8	189.8
152.5°	130.2	135.1	140.6	146.3	151.9	157.9	164.2	170.3	175.9	181.0	185.1
155°	133.0	137.2	142.0	146.7	151.2	156.2	161.5	166.6	171.0	175.2	178.6
157.5°	135.5	138.9	142.9	146.7	150.4	154.5	158.8	162.6	166.4	169.9	172.6
160°	136.9	140.0	143.4	146.7	149.8	153.1	156.8	160.2	163.2	166.3	168.6
162.5°	138.2	140.7	143.8	146.7	149.1	151.8	155.0	157.7	160.3	162.7	164.8
165°	139.7	141.4	143.9	146.2	147.8	149.8	152.0	154.2	156.0	157.9	159.3
167.5°	140.7	142.0	143.9	145.4	146.5	147.7	149.3	151.0	152.3	153.8	154.6
170°	141.4	142.2	143.6	145.0	145.6	146.4	147.6	148.9	149.8	150.9	151.8
172.5°	141.8	142.4	143.4	144.6	144.7	145.0	146.0	147.2	147.7	148.5	149.1
175°	142.5	142.5	143.1	143.9	143.6	143.6	144.2	144.7	145.0	145.6	145.6
177.5°	142.5	142.5	142.8	143.1	142.8	142.8	143.0	143.1	143.4	143.4	143.6
180°	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5



TEST NUMBER: P332897-927

CATALOG NUMBER: SA4XXRDIP-C575D365U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0
2.5°	730.2	730.7	729.0	728.5	729.0	730.7	730.2	731.7	732.0	734.0	733.2
5°	677.5	676.8	675.3	675.7	675.3	676.8	677.5	679.9	681.2	686.1	685.5
7.5°	632.3	629.9	630.7	628.1	630.7	629.9	632.3	634.5	638.3	640.6	645.8
10°	604.8	601.3	598.6	596.1	598.6	601.3	604.8	605.9	611.2	613.7	618.9
12.5°	567.0	564.1	560.3	561.1	560.3	564.1	567.0	572.4	579.2	584.3	592.6
15°	513.5	508.9	501.5	502.4	501.5	508.9	513.5	517.5	524.3	536.0	541.5
17.5°	468.2	468.3	464.9	465.6	464.9	468.3	468.2	473.6	477.1	484.6	493.1
20°	444.7	442.6	442.9	442.0	442.9	442.6	444.7	451.2	455.0	460.2	469.4
22.5°	428.5	425.9	423.7	421.8	423.7	425.9	428.5	430.3	435.2	440.2	447.7
25°	401.0	399.2	396.4	395.8	396.4	399.2	401.0	403.8	406.2	412.7	417.3
27.5°	376.8	376.4	375.3	373.9	375.3	376.4	376.8	379.3	382.5	386.7	392.5
30°	362.7	362.2	361.6	360.6	361.6	362.2	362.7	365.3	367.7	371.1	375.7
32.5°	350.2	349.8	349.2	349.3	349.2	349.8	350.2	351.4	352.9	357.3	360.9
35°	332.2	331.9	331.4	331.1	331.4	331.9	332.2	333.5	334.5	335.6	338.7
37.5°	315.5	316.3	315.9	315.8	315.9	316.3	315.5	315.8	314.8	317.0	319.2
40°	303.9	304.2	304.8	304.5	304.8	304.2	303.9	304.2	304.2	304.2	306.1
42.5°	294.3	294.4	295.2	294.1	295.2	294.4	294.3	293.1	291.6	291.9	292.5
45°	277.1	278.9	278.6	278.6	278.6	278.9	277.1	275.0	274.6	273.4	273.4
47.5°	258.3	259.9	260.3	260.2	260.3	259.9	258.3	257.5	256.0	254.8	254.7
50°	246.0	245.3	246.3	246.0	246.3	245.3	246.0	244.4	242.2	242.2	241.6
52.5°	230.9	231.1	231.0	230.7	231.0	231.1	230.9	230.1	229.2	228.2	227.8
55°	207.7	208.0	207.5	207.7	207.5	208.0	207.7	207.5	207.5	206.8	207.5
57.5°	182.6	181.1	181.7	181.0	181.7	181.1	182.6	183.9	184.4	184.6	185.4
60°	164.6	162.2	161.5	160.3	161.5	162.2	164.6	167.7	168.9	169.5	170.5
62.5°	144.3	142.7	140.5	141.6	140.5	142.7	144.3	147.7	150.4	152.5	154.6
65°	117.4	116.2	115.3	116.5	115.3	116.2	117.4	119.9	122.4	127.3	131.9
67.5°	97.2	96.6	96.6	95.9	96.6	96.6	97.2	98.5	100.0	102.7	107.0
70°	86.6	85.7	85.7	85.1	85.7	85.7	86.6	86.6	88.2	89.4	92.4
72.5°	75.7	74.9	75.1	74.7	75.1	74.9	75.7	76.0	77.6	78.0	79.4
75°	56.1	54.6	54.6	54.9	54.6	54.6	56.1	57.9	59.5	62.3	62.9
77.5°	41.8	41.5	42.0	41.4	42.0	41.5	41.8	41.8	42.1	43.5	44.5
80°	34.2	33.9	33.6	34.5	33.6	33.9	34.2	34.2	34.5	34.9	35.2
82.5°	26.5	26.5	26.5	27.6	26.5	26.5	26.5	27.1	27.1	26.9	27.3
85°	16.0	15.4	16.0	15.4	16.0	15.4	16.0	15.7	16.0	15.7	16.0
87.5°	6.8	6.7	6.3	6.6	6.3	6.7	6.8	6.3	6.3	6.7	6.4
90°	5.9	6.2	5.9	5.9	5.9	6.2	5.9	5.6	5.6	5.3	5.1
92.5°	24.0	22.5	21.5	21.5	21.5	22.5	24.0	27.3	33.0	41.4	55.0
95°	85.6	77.0	71.9	68.3	71.9	77.0	85.6	99.4	126.5	164.1	207.5
97.5°	213.7	196.9	188.5	182.6	188.5	196.9	213.7	233.8	263.0	290.4	306.5
100°	284.5	267.4	259.0	256.7	259.0	267.4	284.5	308.8	329.5	343.3	337.6
102.5°	344.3	331.9	323.1	321.2	323.1	331.9	344.3	359.2	367.8	363.8	336.1
105°	401.8	399.5	395.6	394.0	395.6	399.5	401.8	401.2	389.8	362.0	313.5
107.5°	411.0	417.4	420.2	420.9	420.2	417.4	411.0	397.2	372.2	333.2	281.6
110°	402.0	413.8	418.8	421.4	418.8	413.8	402.0	382.1	351.4	310.8	262.4



TEST NUMBER: P332897-927

CATALOG NUMBER: SA4XXRDIP-C575D365U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	382.8	397.0	404.1	408.1	404.1	397.0	382.8	360.2	329.4	291.0	248.2
115°	350.2	367.0	376.0	378.3	376.0	367.0	350.2	328.1	301.3	268.5	234.1
117.5°	323.1	337.2	346.2	347.9	346.2	337.2	323.1	304.2	281.4	255.6	227.1
120°	308.2	320.6	327.9	331.0	327.9	320.6	308.2	292.3	272.4	250.0	223.9
122.5°	297.7	308.2	314.4	317.5	314.4	308.2	297.7	284.2	266.8	246.4	221.3
125°	286.7	294.9	300.2	301.8	300.2	294.9	286.7	275.5	260.1	240.7	216.7
127.5°	279.2	286.5	291.0	292.6	291.0	286.5	279.2	268.0	253.4	234.1	211.1
130°	274.1	281.1	285.6	287.2	285.6	281.1	274.1	262.6	247.8	228.8	206.6
132.5°	267.4	275.3	279.6	281.2	279.6	275.3	267.4	256.1	241.3	222.7	201.9
135°	255.9	263.7	268.2	269.9	268.2	263.7	255.9	244.7	230.7	213.7	195.4
137.5°	242.5	250.2	253.9	255.9	253.9	250.2	242.5	232.0	219.4	204.9	189.6
140°	233.5	239.6	243.6	245.8	243.6	239.6	233.5	223.7	211.9	199.3	186.2
142.5°	224.3	230.0	233.5	235.0	233.5	230.0	224.3	215.6	205.4	194.6	183.1
145°	211.4	216.1	219.0	220.3	219.0	216.1	211.4	204.4	196.5	188.1	178.6
147.5°	200.6	204.7	206.8	207.3	206.8	204.7	200.6	195.4	189.3	182.5	175.0
150°	194.3	198.0	199.6	199.9	199.6	198.0	194.3	189.8	184.8	179.2	172.8
152.5°	188.9	191.9	192.9	193.2	192.9	191.9	188.9	185.1	181.0	175.9	170.3
155°	181.4	183.6	184.5	184.5	184.5	183.6	181.4	178.6	175.2	171.0	166.6
157.5°	174.7	176.4	176.9	176.9	176.9	176.4	174.7	172.6	169.9	166.4	162.6
160°	170.2	171.9	172.2	172.2	172.2	171.9	170.2	168.6	166.3	163.2	160.2
162.5°	166.0	167.6	167.9	167.7	167.9	167.6	166.0	164.8	162.7	160.3	157.7
165°	160.4	161.5	161.3	161.0	161.3	161.5	160.4	159.3	157.9	156.0	154.2
167.5°	155.2	156.0	155.9	155.7	155.9	156.0	155.2	154.6	153.8	152.3	151.0
170°	152.3	152.6	152.3	152.3	152.3	152.6	152.3	151.8	150.9	149.8	148.9
172.5°	149.4	149.6	149.4	148.9	149.4	149.6	149.4	149.1	148.5	147.7	147.2
175°	145.6	146.2	145.6	145.0	145.6	146.2	145.6	145.6	145.6	145.0	144.7
177.5°	143.4	143.6	143.1	142.8	143.1	143.6	143.4	143.6	143.4	143.4	143.1
180°	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5



TEST NUMBER: P332897-927

CATALOG NUMBER: SA4XXRDIP-C575D365U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0
2.5°	731.7	733.5	737.4	741.8	745.5	748.8	751.2	754.6	757.9	762.3	766.5
5°	687.3	691.7	697.8	705.2	714.5	720.6	728.3	735.1	745.0	754.9	764.4
7.5°	648.4	653.2	662.2	672.4	683.4	693.5	702.6	714.5	727.6	742.0	758.0
10°	623.2	628.4	639.3	650.9	663.9	673.8	686.1	700.3	715.1	732.6	752.3
12.5°	600.6	605.5	618.5	630.5	644.0	654.8	669.1	683.5	703.2	722.3	744.7
15°	556.3	569.6	584.4	598.6	614.6	627.9	645.1	659.9	678.7	705.5	731.1
17.5°	507.2	521.4	539.8	561.7	583.1	599.5	617.0	635.4	657.8	685.2	714.7
20°	478.6	490.0	510.4	534.8	559.8	582.6	598.6	618.9	642.1	671.6	702.1
22.5°	457.2	466.9	482.8	507.2	534.1	560.6	581.1	601.2	626.8	656.3	689.6
25°	425.0	435.5	449.4	466.0	496.9	524.9	551.8	574.8	602.0	631.5	668.5
27.5°	398.3	407.4	420.1	437.4	458.1	489.1	521.6	548.0	575.8	607.5	644.5
30°	382.5	389.9	400.4	418.0	437.7	465.4	498.4	529.3	557.3	590.3	628.8
32.5°	366.0	373.9	384.1	398.0	419.1	442.5	475.5	509.2	539.0	572.7	610.5
35°	344.0	350.1	359.4	373.6	392.7	413.0	442.3	477.1	508.6	544.6	580.7
37.5°	321.7	329.0	336.3	348.9	364.6	386.4	410.4	446.0	480.9	513.7	549.0
40°	309.1	313.5	321.5	331.7	348.3	367.7	390.2	425.0	459.9	492.6	528.0
42.5°	295.1	299.9	306.7	316.9	331.8	350.7	372.7	402.8	439.2	470.9	503.1
45°	275.5	278.3	285.1	293.7	306.1	325.2	345.5	372.3	406.5	436.7	465.1
47.5°	255.8	258.3	262.4	270.4	284.2	299.5	318.6	342.6	372.6	402.8	426.8
50°	242.2	244.4	248.4	255.8	268.2	283.3	302.1	323.6	350.5	379.5	399.4
52.5°	228.7	229.9	233.6	242.0	252.4	267.2	284.1	303.9	329.0	353.1	373.4
55°	207.2	209.9	212.4	218.6	228.4	242.6	257.7	276.5	295.9	316.2	333.5
57.5°	184.7	187.7	191.2	196.6	204.5	217.7	231.2	246.4	263.0	280.0	294.4
60°	169.8	172.6	175.7	181.9	188.9	199.4	214.2	227.4	240.1	255.5	270.0
62.5°	155.3	158.0	161.6	166.6	173.4	183.4	195.7	207.2	220.4	233.9	244.6
65°	133.8	135.9	138.7	143.3	149.8	158.8	168.9	177.8	189.6	199.4	209.3
67.5°	110.2	114.3	118.0	121.7	127.1	135.5	142.8	151.4	159.4	166.7	175.7
70°	94.6	99.3	102.7	106.6	111.9	119.0	126.0	131.9	138.4	145.4	153.5
72.5°	81.6	85.2	87.9	92.1	96.8	103.5	110.0	114.9	120.2	125.0	132.8
75°	64.4	66.0	67.8	71.2	75.5	80.5	85.7	90.0	93.1	97.4	103.0
77.5°	46.3	49.3	50.5	52.9	56.0	59.0	62.5	66.1	69.1	70.7	74.9
80°	35.4	36.7	37.9	41.3	43.2	46.3	48.7	52.1	53.3	54.9	58.9
82.5°	27.6	28.3	29.1	29.9	31.1	34.1	36.6	38.7	40.0	40.6	43.6
85°	16.0	16.3	16.6	17.0	17.3	17.3	18.5	20.0	22.2	22.2	23.1
87.5°	6.3	6.7	6.6	6.2	6.7	6.3	6.6	6.6	7.2	7.8	8.5
90°	4.8	5.1	4.5	3.9	3.9	2.2	2.2	2.0	1.7	0.9	0.3
92.5°	74.0	88.8	77.7	56.6	34.9	20.6	14.8	10.7	7.3	4.7	3.2
95°	234.6	228.1	172.2	105.3	59.3	35.0	23.2	16.6	12.9	10.1	9.3
97.5°	294.8	240.3	161.1	94.7	56.7	37.9	28.1	22.3	19.0	16.6	16.6
100°	296.8	225.1	146.2	89.0	57.4	40.9	31.9	26.6	23.2	21.3	21.3
102.5°	280.0	206.0	136.1	87.5	59.7	44.7	36.2	31.1	28.0	26.2	25.7
105°	249.5	183.6	127.4	88.2	65.0	51.5	43.4	38.3	35.0	33.6	32.8
107.5°	224.8	171.1	125.8	92.4	71.1	58.9	50.9	46.0	42.5	41.0	40.5
110°	212.5	166.8	126.3	95.5	75.9	63.5	56.0	50.9	47.6	46.2	45.6



TEST NUMBER: P332897-927

CATALOG NUMBER: SA4XXRDIP-C575D365U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	205.6	164.9	127.6	98.9	80.3	68.4	60.9	55.8	52.8	51.1	50.5
115°	199.1	163.8	130.2	104.2	87.4	76.1	68.6	63.3	60.4	58.5	57.7
117.5°	196.1	163.5	132.9	109.6	94.1	83.5	75.7	70.7	67.6	65.8	65.0
120°	194.6	163.5	135.0	113.4	98.9	88.2	80.3	75.6	72.5	70.6	70.0
122.5°	192.8	163.3	137.0	117.0	103.3	92.7	85.1	79.9	77.0	75.0	74.5
125°	189.8	163.0	140.0	122.3	109.5	99.4	91.6	86.3	83.2	81.4	80.3
127.5°	185.8	162.3	142.4	127.0	115.2	105.4	97.5	92.0	88.5	86.4	85.6
130°	183.4	162.1	144.2	129.9	119.0	109.5	101.3	96.0	91.8	89.6	88.5
132.5°	181.2	161.9	145.8	132.8	122.2	112.6	105.0	99.2	95.2	92.3	91.4
135°	177.8	161.5	148.1	136.7	126.5	117.3	110.0	104.2	99.4	96.6	95.5
137.5°	174.9	161.5	149.5	139.3	129.9	121.3	114.3	108.2	103.7	100.6	99.6
140°	173.3	161.3	150.6	141.1	132.1	123.7	117.0	111.1	106.4	103.3	102.5
142.5°	172.0	161.3	151.5	142.4	134.2	126.0	119.5	113.8	109.3	106.5	105.6
145°	169.7	160.7	152.0	143.9	136.3	129.0	122.9	117.6	113.7	110.9	110.0
147.5°	167.6	159.7	152.3	145.2	138.6	131.7	126.2	121.8	117.8	115.3	115.0
150°	166.0	159.0	152.3	145.8	139.7	133.6	128.3	124.1	120.6	118.4	118.1
152.5°	164.2	157.9	151.9	146.3	140.6	135.1	130.2	126.5	123.3	121.1	121.0
155°	161.5	156.2	151.2	146.7	142.0	137.2	133.0	129.9	127.1	125.4	125.2
157.5°	158.8	154.5	150.4	146.7	142.9	138.9	135.5	132.8	130.7	129.1	129.1
160°	156.8	153.1	149.8	146.7	143.4	140.0	136.9	134.7	132.7	131.6	131.6
162.5°	155.0	151.8	149.1	146.7	143.8	140.7	138.2	136.3	134.5	133.6	133.8
165°	152.0	149.8	147.8	146.2	143.9	141.4	139.7	138.3	136.9	136.3	136.3
167.5°	149.3	147.7	146.5	145.4	143.9	142.0	140.7	139.9	138.9	138.6	138.9
170°	147.6	146.4	145.6	145.0	143.6	142.2	141.4	140.9	140.0	139.7	140.0
172.5°	146.0	145.0	144.7	144.6	143.4	142.4	141.8	141.5	140.9	140.9	141.1
175°	144.2	143.6	143.6	143.9	143.1	142.5	142.5	142.2	142.0	142.0	142.2
177.5°	143.0	142.8	142.8	143.1	142.8	142.5	142.5	142.5	142.3	142.5	142.8
180°	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5



TEST NUMBER: P332897-927

CATALOG NUMBER: SA4XXRDIP-C575D365U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0	765.0
2.5°	769.7	771.9	774.4	779.0	783.0	784.7	788.2	790.7	789.9	793.4	799.3
5°	772.7	781.0	790.6	800.4	811.5	820.8	828.2	835.6	841.5	848.5	859.0
7.5°	772.2	787.0	803.1	820.8	839.0	854.7	869.3	884.1	897.1	911.6	930.3
10°	770.2	790.0	810.0	833.1	856.3	878.1	897.9	916.3	933.9	952.7	976.4
12.5°	768.0	790.7	814.9	842.7	871.6	897.9	921.1	947.7	969.6	993.9	1021.4
15°	758.2	788.8	821.7	857.8	892.3	927.7	959.5	992.2	1022.7	1051.6	1086.2
17.5°	747.0	782.2	821.1	863.7	905.2	948.2	986.0	1027.1	1058.3	1097.2	1129.3
20°	737.9	775.8	817.4	865.1	912.4	960.1	1001.7	1043.6	1078.8	1117.9	1158.6
22.5°	726.8	768.4	813.5	862.9	912.4	964.6	1010.6	1052.3	1095.8	1139.9	1181.8
25°	708.9	752.1	799.9	854.1	910.8	964.1	1013.4	1065.2	1112.1	1159.8	1197.5
27.5°	687.0	732.3	782.7	838.6	896.8	951.4	1009.5	1064.7	1111.8	1157.8	1190.6
30°	669.5	717.2	765.6	822.4	882.7	941.4	1003.5	1058.8	1108.3	1149.7	1168.2
32.5°	651.5	696.8	746.6	804.1	866.0	929.0	990.8	1047.2	1093.1	1117.8	1118.3
35°	620.1	662.7	714.5	770.9	834.3	902.8	965.4	1020.8	1048.8	1051.1	1020.8
37.5°	586.0	625.0	673.9	730.4	799.9	868.0	931.8	968.8	978.3	946.9	891.0
40°	561.6	597.6	644.8	702.7	771.8	842.1	900.3	927.4	917.6	866.7	804.5
42.5°	535.9	569.5	615.0	672.2	741.5	812.5	862.1	876.6	850.5	791.8	718.9
45°	494.1	524.9	569.9	627.6	694.1	760.7	798.3	790.9	747.4	677.8	596.1
47.5°	450.5	480.3	520.8	574.1	642.3	699.7	725.2	702.9	641.0	564.4	498.0
50°	421.7	452.2	489.5	540.3	602.6	658.1	674.4	640.5	571.7	498.1	437.0
52.5°	393.3	419.4	455.9	505.0	564.6	611.5	620.1	581.1	510.1	444.1	390.0
55°	350.1	373.9	404.7	450.9	502.4	542.2	537.6	487.3	422.9	366.5	323.9
57.5°	308.4	326.3	354.7	398.1	443.3	470.0	453.0	410.3	350.2	304.0	268.2
60°	280.8	297.5	323.9	361.9	401.6	416.7	402.5	356.0	308.6	266.3	236.1
62.5°	254.7	269.3	292.2	327.3	359.4	368.4	353.2	312.6	269.8	233.8	208.7
65°	216.7	230.2	249.7	274.6	296.8	301.1	291.3	249.7	217.3	187.1	169.8
67.5°	182.2	191.1	206.3	227.8	239.6	242.2	223.1	196.9	168.4	149.9	136.9
70°	159.1	165.2	179.4	191.1	200.7	201.0	183.4	162.4	140.5	125.5	115.9
72.5°	136.6	142.5	153.3	161.3	168.6	166.2	150.1	133.6	115.9	104.5	97.4
75°	105.4	110.7	116.2	119.9	119.9	116.8	105.1	92.8	82.6	75.8	73.7
77.5°	76.6	81.0	82.8	82.2	81.1	76.3	68.9	60.8	57.2	54.0	52.4
80°	60.1	61.9	62.6	61.0	59.2	53.6	48.7	45.3	41.9	40.7	40.1
82.5°	44.6	46.2	44.6	45.0	41.0	36.4	33.7	32.5	31.1	30.6	29.9
85°	23.8	23.4	22.8	21.2	18.5	17.9	17.6	17.3	16.6	17.0	16.3
87.5°	8.3	7.8	6.8	6.6	6.6	6.4	6.7	6.8	6.9	6.7	7.2
90°	0.9	1.7	2.0	2.2	2.2	3.9	3.9	4.5	5.1	4.8	5.1
92.5°	4.7	7.3	10.7	14.8	20.6	34.9	56.6	77.7	88.8	74.0	55.0
95°	10.1	12.9	16.6	23.2	35.0	59.3	105.3	172.2	228.1	234.6	207.5
97.5°	16.6	19.0	22.3	28.1	37.9	56.7	94.7	161.1	240.3	294.8	306.5
100°	21.3	23.2	26.6	31.9	40.9	57.4	89.0	146.2	225.1	296.8	337.6
102.5°	26.2	28.0	31.1	36.2	44.7	59.7	87.5	136.1	206.0	280.0	336.1
105°	33.6	35.0	38.3	43.4	51.5	65.0	88.2	127.4	183.6	249.5	313.5
107.5°	41.0	42.5	46.0	50.9	58.9	71.1	92.4	125.8	171.1	224.8	281.6
110°	46.2	47.6	50.9	56.0	63.5	75.9	95.5	126.3	166.8	212.5	262.4





TEST NUMBER: P332897-927

CATALOG NUMBER: SA4XXRDIP-C575D365U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	51.1	52.8	55.8	60.9	68.4	80.3	98.9	127.6	164.9	205.6	248.2
115°	58.5	60.4	63.3	68.6	76.1	87.4	104.2	130.2	163.8	199.1	234.1
117.5°	65.8	67.6	70.7	75.7	83.5	94.1	109.6	132.9	163.5	196.1	227.1
120°	70.6	72.5	75.6	80.3	88.2	98.9	113.4	135.0	163.5	194.6	223.9
122.5°	75.0	77.0	79.9	85.1	92.7	103.3	117.0	137.0	163.3	192.8	221.3
125°	81.4	83.2	86.3	91.6	99.4	109.5	122.3	140.0	163.0	189.8	216.7
127.5°	86.4	88.5	92.0	97.5	105.4	115.2	127.0	142.4	162.3	185.8	211.1
130°	89.6	91.8	96.0	101.3	109.5	119.0	129.9	144.2	162.1	183.4	206.6
132.5°	92.3	95.2	99.2	105.0	112.6	122.2	132.8	145.8	161.9	181.2	201.9
135°	96.6	99.4	104.2	110.0	117.3	126.5	136.7	148.1	161.5	177.8	195.4
137.5°	100.6	103.7	108.2	114.3	121.3	129.9	139.3	149.5	161.5	174.9	189.6
140°	103.3	106.4	111.1	117.0	123.7	132.1	141.1	150.6	161.3	173.3	186.2
142.5°	106.5	109.3	113.8	119.5	126.0	134.2	142.4	151.5	161.3	172.0	183.1
145°	110.9	113.7	117.6	122.9	129.0	136.3	143.9	152.0	160.7	169.7	178.6
147.5°	115.3	117.8	121.8	126.2	131.7	138.6	145.2	152.3	159.7	167.6	175.0
150°	118.4	120.6	124.1	128.3	133.6	139.7	145.8	152.3	159.0	166.0	172.8
152.5°	121.1	123.3	126.5	130.2	135.1	140.6	146.3	151.9	157.9	164.2	170.3
155°	125.4	127.1	129.9	133.0	137.2	142.0	146.7	151.2	156.2	161.5	166.6
157.5°	129.1	130.7	132.8	135.5	138.9	142.9	146.7	150.4	154.5	158.8	162.6
160°	131.6	132.7	134.7	136.9	140.0	143.4	146.7	149.8	153.1	156.8	160.2
162.5°	133.6	134.5	136.3	138.2	140.7	143.8	146.7	149.1	151.8	155.0	157.7
165°	136.3	136.9	138.3	139.7	141.4	143.9	146.2	147.8	149.8	152.0	154.2
167.5°	138.6	138.9	139.9	140.7	142.0	143.9	145.4	146.5	147.7	149.3	151.0
170°	139.7	140.0	140.9	141.4	142.2	143.6	145.0	145.6	146.4	147.6	148.9
172.5°	140.9	140.9	141.5	141.8	142.4	143.4	144.6	144.7	145.0	146.0	147.2
175°	142.0	142.0	142.2	142.5	142.5	143.1	143.9	143.6	143.6	144.2	144.7
177.5°	142.5	142.3	142.5	142.5	142.5	142.8	143.1	142.8	142.8	143.0	143.1
180°	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5



TEST NUMBER: P332897-927

CATALOG NUMBER: SA4XXRDIP-C575D365U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	765.0	765.0	765.0	765.0	765.0	765.0	765.0
2.5°	802.5	803.5	804.2	806.7	806.9	809.1	806.9
5°	868.9	873.2	880.0	886.8	887.4	891.7	884.0
7.5°	943.3	953.3	959.6	970.5	974.9	977.6	973.1
10°	994.7	1003.9	1020.3	1028.3	1036.3	1037.4	1033.8
12.5°	1044.2	1058.8	1071.7	1087.0	1086.6	1097.4	1093.4
15°	1110.2	1125.3	1143.2	1160.2	1166.3	1166.3	1171.2
17.5°	1157.3	1185.0	1203.5	1216.8	1231.4	1233.9	1232.2
20°	1189.1	1219.0	1238.7	1256.0	1265.9	1268.7	1268.7
22.5°	1212.8	1238.3	1257.5	1273.0	1281.2	1284.4	1283.4
25°	1229.2	1251.1	1262.8	1267.4	1269.6	1268.9	1263.1
27.5°	1206.7	1205.8	1198.3	1184.2	1173.5	1167.0	1159.7
30°	1163.9	1147.8	1129.3	1109.0	1082.8	1062.7	1056.6
32.5°	1100.0	1064.0	1032.7	998.8	970.6	950.5	942.1
35°	976.4	919.4	872.9	832.2	802.6	784.1	777.9
37.5°	829.9	774.7	717.1	677.6	653.1	634.4	627.4
40°	736.7	676.5	626.3	589.3	564.0	545.9	545.6
42.5°	651.6	594.2	546.9	520.3	493.1	481.0	480.9
45°	533.5	487.6	447.5	426.6	410.3	400.4	397.6
47.5°	441.7	403.8	377.1	360.4	347.1	340.8	336.7
50°	390.2	357.0	335.6	321.2	313.8	305.8	305.1
52.5°	347.3	320.4	303.9	292.1	282.7	277.9	278.1
55°	291.9	270.6	258.9	249.9	242.6	238.8	237.3
57.5°	245.9	230.0	221.4	213.3	210.1	207.2	206.4
60°	217.3	206.5	198.5	192.0	187.4	186.5	186.2
62.5°	193.6	182.4	176.8	171.8	168.4	167.0	166.4
65°	159.6	151.3	146.4	142.4	141.2	139.0	138.7
67.5°	128.7	123.7	120.5	117.7	116.0	115.9	115.9
70°	109.7	106.9	104.2	102.7	101.7	101.1	101.1
72.5°	93.5	91.4	89.1	88.3	88.2	87.5	87.3
75°	71.2	69.1	69.3	67.8	66.5	65.0	64.1
77.5°	50.5	49.0	48.6	48.5	47.4	47.2	47.7
80°	39.1	37.6	37.3	37.6	37.3	36.4	36.4
82.5°	29.8	28.5	28.2	28.0	27.6	28.0	27.5
85°	16.0	15.4	15.4	15.4	16.0	15.7	15.4
87.5°	6.7	6.6	6.8	6.6	6.7	6.3	6.6
90°	5.3	5.6	5.6	5.9	6.2	5.9	5.9
92.5°	41.4	33.0	27.3	24.0	22.5	21.5	21.5
95°	164.1	126.5	99.4	85.6	77.0	71.9	68.3
97.5°	290.4	263.0	233.8	213.7	196.9	188.5	182.6
100°	343.3	329.5	308.8	284.5	267.4	259.0	256.7
102.5°	363.8	367.8	359.2	344.3	331.9	323.1	321.2
105°	362.0	389.8	401.2	401.8	399.5	395.6	394.0
107.5°	333.2	372.2	397.2	411.0	417.4	420.2	420.9
110°	310.8	351.4	382.1	402.0	413.8	418.8	421.4



TEST NUMBER: P332897-927

CATALOG NUMBER: SA4XXRDIP-C575D365U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	291.0	329.4	360.2	382.8	397.0	404.1	408.1
115°	268.5	301.3	328.1	350.2	367.0	376.0	378.3
117.5°	255.6	281.4	304.2	323.1	337.2	346.2	347.9
120°	250.0	272.4	292.3	308.2	320.6	327.9	331.0
122.5°	246.4	266.8	284.2	297.7	308.2	314.4	317.5
125°	240.7	260.1	275.5	286.7	294.9	300.2	301.8
127.5°	234.1	253.4	268.0	279.2	286.5	291.0	292.6
130°	228.8	247.8	262.6	274.1	281.1	285.6	287.2
132.5°	222.7	241.3	256.1	267.4	275.3	279.6	281.2
135°	213.7	230.7	244.7	255.9	263.7	268.2	269.9
137.5°	204.9	219.4	232.0	242.5	250.2	253.9	255.9
140°	199.3	211.9	223.7	233.5	239.6	243.6	245.8
142.5°	194.6	205.4	215.6	224.3	230.0	233.5	235.0
145°	188.1	196.5	204.4	211.4	216.1	219.0	220.3
147.5°	182.5	189.3	195.4	200.6	204.7	206.8	207.3
150°	179.2	184.8	189.8	194.3	198.0	199.6	199.9
152.5°	175.9	181.0	185.1	188.9	191.9	192.9	193.2
155°	171.0	175.2	178.6	181.4	183.6	184.5	184.5
157.5°	166.4	169.9	172.6	174.7	176.4	176.9	176.9
160°	163.2	166.3	168.6	170.2	171.9	172.2	172.2
162.5°	160.3	162.7	164.8	166.0	167.6	167.9	167.7
165°	156.0	157.9	159.3	160.4	161.5	161.3	161.0
167.5°	152.3	153.8	154.6	155.2	156.0	155.9	155.7
170°	149.8	150.9	151.8	152.3	152.6	152.3	152.3
172.5°	147.7	148.5	149.1	149.4	149.6	149.4	148.9
175°	145.0	145.6	145.6	145.6	146.2	145.6	145.0
177.5°	143.4	143.4	143.6	143.4	143.6	143.1	142.8
180°	142.5	142.5	142.5	142.5	142.5	142.5	142.5

(END OF REPORT)