

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332528-830

Luminaire Tested: **SA4XXDIP-C350D1205U830-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332528-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C350D1205U830-4F0-1E-UDD-A4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5543.2 lumens
Efficiency: N/A
Efficacy: 131.4 lumens/watt
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 42.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332528-830
CATALOG NUMBER: SA4XXDIP-C350D1205U830-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332528-830

CATALOG NUMBER: SA4XXDIP-C350D1205U830-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	70	70	70	52	52	52	35	35	35	27
1	93	89	85	82	83	79	76	73	62	60	58	46	44	43	31	30	30	23
2	84	77	72	67	75	69	64	60	54	51	48	40	38	36	27	26	25	19
3	77	68	61	56	69	61	55	50	48	44	40	36	33	31	24	23	21	16
4	70	60	53	47	63	54	48	43	43	38	34	32	29	26	22	20	19	14
5	65	54	46	40	57	48	42	37	38	33	30	28	25	23	20	18	16	12
6	59	48	40	35	53	43	36	32	34	29	26	26	22	20	18	16	14	11
7	55	43	36	30	49	39	32	28	31	26	23	23	20	18	16	14	13	10
8	51	39	32	27	45	35	29	24	28	23	20	21	18	16	15	13	11	9
9	47	35	28	23	42	32	26	22	26	21	18	20	16	14	14	12	10	8
10	44	32	26	21	39	29	23	19	24	19	16	18	15	13	13	11	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4347	4347	4347	4347
5°	5119	4358	3847	4358
10°	6129	4339	3463	4339
15°	7252	4296	3181	4296
20°	8076	4250	2928	4250
25°	8206	4185	2754	4185
30°	6982	4121	2699	4121
35°	5368	4018	2699	4018
40°	4185	3898	2751	3898
45°	3489	3716	2797	3716
50°	3071	3493	2891	3493
55°	2814	3227	3008	3227
60°	2635	2989	3147	2989
65°	2455	2722	3265	2722
70°	2242	2460	3338	2460
75°	2006	2165	3300	2165
80°	1678	1776	3194	1776
85°	1241	1288	3057	1288



TEST NUMBER: P332528-830

CATALOG NUMBER: SA4XXDIP-C350D1205U830-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.5	0.9
10°-20°	161.7	2.9
20°-30°	256.4	4.6
30°-40°	285.4	5.1
40°-50°	259.8	4.7
50°-60°	212.3	3.8
60°-70°	151.5	2.7
70°-80°	83.4	1.5
80°-90°	25.9	0.5
90°-100°	402.7	7.3
100°-110°	838.0	15.1
110°-120°	750.6	13.5
120°-130°	631.4	11.4
130°-140°	526.5	9.5
140°-150°	402.2	7.3
150°-160°	282.7	5.1
160°-170°	166.3	3.0
170°-180°	54.1	1.0
0°-30°	470.6	8.5
0°-40°	755.9	13.6
0°-60°	1227.9	22.2
0°-90°	1488.8	26.9
90°-120°	1991.3	35.9
90°-150°	3551.4	64.1
90°-180°	4054.0	73.1
0°-180°	5543.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	538	538	538	538	538	
5°	632	538	475	538	632	64
15°	868	514	381	514	868	245
25°	921	470	309	470	921	406
35°	545	408	274	408	545	346
45°	306	326	245	326	306	241
55°	200	229	214	229	200	181
65°	128	142	171	142	128	127
75°	64	69	106	69	64	68
85°	13	14	33	14	13	17
90°	23	1	23	1	23	19
95°	267	36	267	36	267	415
105°	1541	128	1541	128	1541	1524
115°	1480	226	1480	226	1480	1469
125°	1181	314	1181	314	1181	1073
135°	1056	373	1056	373	1056	815
145°	862	430	862	430	862	546
155°	722	490	722	490	722	337
165°	630	533	630	533	630	180
175°	567	556	567	556	567	55
180°	558	558	558	558	558	



TEST NUMBER: P332528-830

CATALOG NUMBER: SA4XXDIP-C350D1205U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	538.5	538.5	538.5	538.5	538.5	538.5	538.5	538.5	538.5	538.5	538.5
2.5°	573.1	573.0	571.2	570.8	569.6	568.0	567.6	564.7	559.0	556.3	555.6
5°	631.7	636.2	630.4	629.2	628.6	621.2	617.5	613.0	602.8	596.7	592.0
7.5°	701.7	702.2	699.6	697.7	691.9	685.5	675.9	665.6	653.4	640.7	631.1
10°	747.7	749.5	746.6	746.2	734.8	727.6	713.4	701.3	687.5	672.1	658.1
12.5°	796.3	793.8	792.3	782.8	780.6	767.6	751.0	738.7	717.3	699.6	680.9
15°	867.7	862.8	859.7	846.6	840.1	822.0	804.4	790.8	762.9	736.3	716.2
17.5°	909.6	914.5	907.4	901.9	885.2	872.5	854.5	826.0	804.2	771.2	745.8
20°	940.0	940.5	936.4	930.9	917.8	901.6	882.0	850.8	824.7	791.9	757.1
22.5°	948.2	948.3	946.6	941.4	931.4	918.4	898.6	872.5	840.9	805.3	770.4
25°	921.2	920.4	922.4	928.2	924.4	920.4	909.0	889.6	860.2	822.5	784.9
27.5°	821.1	827.4	838.7	852.9	866.7	877.1	880.1	876.1	857.9	826.9	787.6
30°	749.0	756.7	765.2	779.4	807.1	822.9	840.3	853.5	846.1	821.3	784.8
32.5°	669.9	671.8	684.3	700.5	725.9	756.3	783.9	810.7	819.5	806.5	776.0
35°	544.7	547.9	561.5	577.5	608.5	645.8	687.3	724.3	754.9	767.1	751.5
37.5°	444.5	453.5	463.1	480.3	507.7	541.2	584.3	632.3	677.8	708.3	713.5
40°	397.1	402.7	409.5	422.7	445.9	478.9	515.9	570.8	619.3	663.0	677.2
42.5°	359.6	362.9	367.1	379.0	396.6	429.5	463.4	511.6	560.2	612.5	636.4
45°	305.6	309.0	316.1	323.0	336.4	359.1	390.6	430.3	479.2	529.5	573.7
47.5°	266.6	268.7	273.0	280.4	291.8	306.8	332.3	365.5	410.8	459.8	506.8
50°	244.5	246.3	249.6	256.3	265.0	278.4	299.4	330.4	365.8	415.1	461.3
52.5°	227.0	227.7	230.2	234.7	241.7	252.9	270.1	295.8	328.8	372.7	418.7
55°	199.9	200.8	203.0	206.3	212.4	219.5	232.6	251.8	280.6	318.8	358.7
57.5°	177.6	178.2	180.0	181.3	186.3	192.1	202.3	215.9	237.7	270.1	305.8
60°	163.2	162.9	165.0	166.2	169.6	174.5	182.3	195.4	214.3	240.4	273.2
62.5°	149.4	148.7	150.6	152.1	154.0	158.2	164.6	174.8	190.3	213.9	242.2
65°	128.5	127.6	128.8	130.5	132.2	134.5	139.2	148.4	160.6	177.6	199.2
67.5°	107.5	108.5	108.7	109.5	110.6	113.6	116.8	123.3	132.0	145.5	163.8
70°	95.0	95.3	96.1	96.1	96.8	99.5	102.2	105.9	114.4	127.0	141.9
72.5°	82.6	83.5	83.1	83.8	84.4	86.1	88.0	91.7	98.9	108.2	120.8
75°	64.3	64.9	64.9	65.1	65.8	66.4	68.1	70.7	75.9	82.8	91.4
77.5°	46.8	46.9	47.2	48.1	48.1	49.1	50.2	52.4	55.0	59.7	65.0
80°	36.1	36.6	36.4	36.9	36.9	37.7	38.2	40.8	41.9	45.1	49.3
82.5°	26.5	27.0	26.9	27.5	27.9	28.1	28.7	29.8	30.9	33.6	35.3
85°	13.4	13.9	13.4	13.9	14.5	14.7	15.4	15.6	16.5	17.2	18.8
87.5°	8.5	9.0	9.2	9.2	9.3	9.5	9.5	9.1	9.6	10.0	10.3
90°	23.0	23.0	24.1	23.0	21.9	21.9	20.8	19.7	18.7	19.7	17.5
92.5°	84.4	84.4	88.0	94.0	106.9	128.8	161.8	215.1	289.4	347.4	304.1
95°	267.2	281.4	301.2	335.2	388.8	495.0	641.8	811.5	917.8	892.6	673.5
97.5°	714.4	737.1	770.0	835.8	914.5	1028.9	1136.0	1199.1	1153.1	940.2	630.4
100°	1004.4	1013.1	1045.9	1112.8	1208.1	1289.1	1342.7	1320.9	1160.9	880.5	571.7
102.5°	1256.7	1263.7	1298.3	1346.7	1405.1	1438.9	1423.3	1314.8	1095.2	806.1	532.3
105°	1541.0	1547.6	1562.9	1571.7	1569.4	1524.6	1416.2	1226.6	975.8	718.5	498.3
107.5°	1646.6	1643.7	1632.8	1607.8	1553.7	1456.0	1303.3	1101.5	879.5	669.4	492.2
110°	1648.3	1638.5	1618.7	1572.7	1495.0	1374.5	1215.7	1026.2	831.3	652.8	494.0



TEST NUMBER: P332528-830

CATALOG NUMBER: SA4XXDIP-C350D1205U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1596.7	1580.6	1553.0	1497.4	1409.1	1288.6	1138.6	971.0	804.1	644.9	499.2
115°	1479.7	1470.9	1435.9	1370.2	1283.6	1178.5	1050.4	915.6	778.7	640.7	509.3
117.5°	1361.1	1354.3	1318.9	1263.7	1189.9	1100.7	999.9	888.4	767.3	639.6	520.0
120°	1294.6	1282.5	1254.1	1205.9	1143.4	1065.6	978.1	876.2	761.2	639.6	527.9
122.5°	1242.0	1229.9	1205.9	1164.7	1111.9	1043.8	964.0	865.6	754.2	638.8	535.8
125°	1180.6	1174.1	1153.3	1121.5	1077.7	1017.5	941.9	847.7	742.5	637.4	547.6
127.5°	1144.7	1138.2	1120.7	1092.4	1048.4	991.2	915.9	825.8	727.0	635.0	557.0
130°	1123.7	1117.1	1099.6	1072.2	1027.4	969.3	894.8	808.3	717.4	634.1	564.0
132.5°	1100.0	1093.4	1076.9	1045.9	1001.9	943.9	871.2	789.9	708.6	633.3	570.1
135°	1055.8	1049.2	1031.7	1001.1	957.2	902.5	835.7	764.5	695.5	632.0	579.4
137.5°	1001.1	993.2	978.7	948.5	907.5	858.0	801.7	741.5	684.1	631.7	584.8
140°	961.6	952.8	937.5	913.4	875.1	829.1	779.8	728.3	678.0	630.8	589.3
142.5°	919.5	913.4	899.8	877.5	843.6	803.7	761.4	716.0	672.7	630.8	592.8
145°	862.0	856.5	845.6	826.9	799.6	768.8	736.0	698.8	663.7	628.7	594.7
147.5°	810.9	809.0	800.6	784.7	764.5	740.4	714.1	684.6	655.6	624.7	595.8
150°	782.0	780.9	774.3	760.1	742.5	722.8	701.0	675.8	649.5	622.1	595.8
152.5°	755.7	754.6	750.6	739.0	724.2	707.9	687.8	666.1	642.4	617.7	594.1
155°	721.8	721.8	718.5	709.7	698.8	685.6	669.2	651.7	632.0	611.1	591.4
157.5°	692.0	692.0	690.0	683.4	675.1	664.6	650.8	636.1	621.2	604.4	588.6
160°	673.5	673.5	672.5	665.9	659.3	650.5	638.5	626.5	613.3	599.1	586.0
162.5°	656.0	657.0	655.8	649.2	644.4	636.6	627.2	616.8	606.3	593.8	583.3
165°	629.8	630.8	632.0	627.5	623.2	617.7	610.0	603.5	594.7	586.0	578.2
167.5°	609.0	609.8	610.0	607.2	605.0	601.7	595.6	590.6	584.2	578.1	573.1
170°	595.8	595.8	596.9	595.8	593.6	590.3	586.0	582.7	577.2	572.8	569.5
172.5°	582.7	584.4	585.5	584.4	583.1	580.7	578.1	575.6	571.1	567.5	566.0
175°	567.3	569.5	571.7	569.5	569.5	569.5	567.3	566.3	564.0	561.8	561.8
177.5°	558.4	560.1	561.8	561.0	561.8	561.0	561.0	560.1	559.2	558.4	558.4
180°	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5



TEST NUMBER: P332528-830

CATALOG NUMBER: SA4XXDIP-C350D1205U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	538.5	538.5	538.5	538.5	538.5	538.5	538.5	538.5	538.5	538.5	538.5
2.5°	555.8	553.3	551.5	550.1	546.2	543.8	542.1	539.6	536.7	533.7	529.9
5°	587.3	579.8	574.2	565.7	557.7	551.0	544.0	537.8	530.3	522.0	515.9
7.5°	620.5	609.2	594.7	582.2	568.1	555.8	544.9	533.7	522.0	510.6	500.2
10°	641.6	627.1	611.0	592.0	574.2	558.4	543.7	529.3	515.5	501.7	489.8
12.5°	664.2	646.1	622.4	600.2	580.2	559.0	541.3	523.8	507.1	492.6	478.8
15°	694.7	668.5	641.1	611.4	585.1	560.3	536.0	514.0	495.2	476.0	462.6
17.5°	713.3	681.0	649.7	618.7	586.8	555.5	529.3	503.9	480.4	461.4	444.5
20°	725.7	693.5	654.5	623.5	585.6	553.5	523.1	494.7	470.2	450.0	432.5
22.5°	736.3	699.3	660.2	619.3	581.6	547.5	514.3	485.9	460.8	439.4	422.7
25°	742.2	699.6	657.1	616.5	573.7	533.4	503.2	469.8	443.0	420.5	402.7
27.5°	742.8	697.2	649.2	604.2	560.0	522.4	484.4	454.4	426.7	402.8	385.7
30°	740.8	693.3	641.8	593.0	548.6	507.7	474.7	442.1	413.8	390.1	372.3
32.5°	734.5	685.1	632.2	580.4	534.4	494.5	460.4	429.4	401.8	378.5	359.8
35°	716.5	667.6	611.2	557.4	510.4	470.0	439.2	407.7	380.1	358.1	340.0
37.5°	688.2	644.1	586.7	531.1	484.8	444.3	413.8	385.4	360.4	338.0	319.5
40°	663.6	624.8	567.2	513.0	463.1	424.5	396.0	369.9	345.1	323.9	306.2
42.5°	635.3	601.4	548.4	491.0	442.7	404.0	376.2	352.7	329.4	309.8	292.2
45°	584.7	562.3	512.4	459.3	409.1	372.5	346.0	325.5	305.9	286.6	271.9
47.5°	526.5	515.4	473.3	422.9	375.3	339.2	316.2	297.3	280.0	263.8	250.8
50°	487.4	482.0	445.7	397.1	351.6	317.6	294.5	278.1	263.4	249.2	236.9
52.5°	448.8	448.7	415.8	371.4	329.2	296.6	273.5	258.4	245.6	234.0	223.0
55°	389.9	396.2	370.5	330.8	293.1	263.6	242.9	229.3	220.4	210.8	202.6
57.5°	335.8	346.2	325.0	290.0	258.5	231.5	213.4	203.2	193.7	187.8	181.8
60°	300.5	310.3	293.8	264.4	234.7	211.5	194.3	185.1	176.9	172.9	168.6
62.5°	269.1	277.8	265.6	238.3	212.5	190.2	175.7	166.9	161.4	157.0	154.2
65°	224.2	231.6	221.0	201.2	179.1	161.3	149.5	142.5	137.2	135.4	132.2
67.5°	181.3	187.9	182.3	165.4	147.7	134.1	124.9	118.3	115.1	113.6	111.3
70°	155.7	162.4	156.4	141.7	128.0	116.7	107.9	104.2	100.9	100.2	97.1
72.5°	134.1	138.6	132.6	121.1	109.5	99.9	93.1	89.2	87.5	86.2	84.5
75°	100.6	104.6	100.6	91.7	83.4	76.7	71.0	69.4	67.4	66.7	65.6
77.5°	71.2	74.6	71.6	66.1	59.9	54.7	51.6	49.6	49.1	48.0	48.5
80°	54.4	56.6	53.7	50.0	45.1	41.5	39.3	38.2	36.9	36.4	37.2
82.5°	39.1	40.1	38.5	36.0	32.4	30.1	28.6	27.2	27.0	27.1	27.1
85°	20.3	20.1	19.9	17.6	16.5	15.0	14.0	13.9	13.6	14.0	14.5
87.5°	9.8	10.0	8.6	7.8	7.1	6.3	5.5	4.9	5.5	6.3	6.7
90°	15.4	15.4	8.8	8.8	7.6	6.6	3.3	1.1	3.3	6.6	7.6
92.5°	221.2	136.3	80.6	57.9	41.8	28.5	18.2	12.4	18.2	28.5	41.8
95°	411.8	232.1	137.0	90.9	64.7	50.4	39.4	36.1	39.4	50.4	64.7
97.5°	370.2	221.9	148.5	110.0	87.4	74.3	64.8	64.8	64.8	74.3	87.4
100°	348.3	224.5	159.9	124.9	104.1	90.9	83.2	83.2	83.2	90.9	104.1
102.5°	342.1	233.3	174.8	141.5	121.6	109.3	102.5	100.8	102.5	109.3	121.6
105°	345.0	254.1	201.5	169.8	150.1	137.0	131.4	128.2	131.4	137.0	150.1
107.5°	361.2	278.4	230.3	198.9	180.0	166.1	160.5	158.3	160.5	166.1	180.0
110°	373.4	296.8	248.6	219.0	199.3	186.2	180.7	178.5	180.7	186.2	199.3



TEST NUMBER: P332528-830
 CATALOG NUMBER: SA4XXDIP-C350D1205U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	386.6	314.3	267.9	238.4	218.6	206.3	200.0	197.8	200.0	206.3	218.6
115°	407.5	341.7	297.9	268.3	247.5	236.6	228.9	225.6	228.9	236.6	247.5
117.5°	428.7	368.3	326.6	296.0	276.4	264.4	257.6	254.5	257.6	264.4	276.4
120°	443.6	386.6	345.0	314.3	295.7	283.7	276.0	273.8	276.0	283.7	295.7
122.5°	457.6	404.2	362.5	332.7	312.4	301.2	293.5	291.3	293.5	301.2	312.4
125°	478.6	428.2	388.8	358.2	337.3	325.3	318.7	314.3	318.7	325.3	337.3
127.5°	496.8	450.5	412.5	381.5	359.9	346.1	338.2	334.7	338.2	346.1	359.9
130°	508.2	465.5	428.2	396.4	375.7	359.2	350.4	346.1	350.4	359.2	375.7
132.5°	519.6	477.8	440.5	410.5	388.0	372.4	361.0	357.5	361.0	372.4	388.0
135°	534.5	495.0	458.9	430.5	407.5	388.8	377.9	373.4	377.9	388.8	407.5
137.5°	545.0	508.2	474.5	447.3	423.4	405.7	393.6	389.5	393.6	405.7	423.4
140°	552.0	517.0	484.1	457.8	434.8	416.2	404.2	400.9	404.2	416.2	434.8
142.5°	557.2	524.8	492.9	467.4	445.4	427.5	416.4	413.1	416.4	427.5	445.4
145°	563.0	533.4	504.9	480.8	460.0	444.7	433.8	430.5	433.8	444.7	460.0
147.5°	568.0	542.2	515.4	493.7	476.5	460.6	451.0	449.9	451.0	460.6	476.5
150°	570.6	546.5	522.5	501.6	485.2	472.0	463.3	462.2	463.3	472.0	485.2
152.5°	572.4	550.1	528.6	509.5	494.8	482.6	473.8	473.5	473.8	482.6	494.8
155°	573.9	555.3	536.7	520.3	508.2	497.2	490.7	489.6	490.7	497.2	508.2
157.5°	573.9	559.0	543.3	530.3	519.8	511.2	505.1	505.1	505.1	511.2	519.8
160°	573.9	560.7	547.6	535.6	526.8	519.2	514.7	514.7	514.7	519.2	526.8
162.5°	573.9	562.5	550.3	540.8	532.9	526.1	522.6	523.5	522.6	526.1	532.9
165°	571.7	563.0	553.1	546.5	541.0	535.6	533.4	533.4	533.4	535.6	541.0
167.5°	569.1	562.7	555.5	550.4	547.4	543.3	542.2	543.3	542.2	543.3	547.4
170°	567.3	561.8	556.4	553.1	550.9	547.6	546.5	547.6	546.5	547.6	550.9
172.5°	565.6	561.0	557.2	554.9	553.6	551.1	550.9	552.0	550.9	551.1	553.6
175°	563.0	559.7	557.5	557.5	556.4	555.3	555.3	556.4	555.3	555.3	556.4
177.5°	560.1	558.4	557.5	557.5	557.5	556.6	557.5	558.4	557.5	556.6	557.5
180°	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5



TEST NUMBER: P332528-830

CATALOG NUMBER: SA4XXDIP-C350D1205U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	538.5	538.5	538.5	538.5	538.5	538.5	538.5	538.5	538.5	538.5	538.5
2.5°	528.1	526.5	524.2	521.0	518.3	515.5	514.7	513.7	515.9	514.1	513.5
5°	510.9	506.1	500.1	493.2	489.2	483.4	482.3	480.0	477.8	477.6	475.3
7.5°	492.5	485.6	477.7	470.7	464.2	457.8	453.6	452.8	449.5	447.5	445.4
10°	480.7	472.2	463.1	456.4	448.8	442.1	437.4	434.8	432.5	430.1	427.8
12.5°	466.8	457.8	450.3	443.0	434.0	429.0	421.2	416.6	416.1	416.1	410.4
15°	450.6	441.7	430.1	419.8	414.9	405.1	400.9	395.5	392.2	388.8	386.2
17.5°	432.1	420.9	411.9	400.1	390.8	383.0	377.4	374.2	369.1	364.4	361.0
20°	420.5	408.7	399.1	386.5	376.4	366.7	362.0	357.6	353.8	349.8	346.0
22.5°	408.7	396.3	384.7	372.5	363.0	352.8	348.3	342.2	338.7	336.4	332.6
25°	390.1	376.7	363.4	351.8	342.0	333.0	327.1	322.3	318.3	316.5	314.1
27.5°	369.9	356.7	343.7	330.5	319.4	312.9	308.1	304.6	302.3	299.9	298.8
30°	357.1	343.3	329.5	317.2	307.0	300.5	296.1	293.6	291.8	290.7	289.5
32.5°	344.1	330.5	315.9	304.7	295.5	289.7	286.3	283.9	283.0	282.7	282.2
35°	323.2	309.4	296.1	286.0	277.3	275.0	272.1	270.8	270.3	271.9	272.6
37.5°	303.0	290.2	277.9	268.2	262.4	259.2	258.2	258.3	259.9	261.2	262.8
40°	290.0	277.5	265.9	257.4	252.0	250.1	249.6	250.7	252.5	254.1	255.9
42.5°	277.3	265.0	254.5	246.6	242.8	240.9	241.2	242.3	244.9	246.8	249.4
45°	257.7	247.4	237.1	230.6	227.5	228.0	228.0	230.0	232.4	235.4	238.3
47.5°	239.1	228.8	220.4	214.9	213.3	212.9	214.1	216.8	220.3	223.9	227.9
50°	226.7	216.8	209.4	204.5	202.7	203.4	205.2	207.6	211.9	216.4	220.6
52.5°	214.0	205.0	198.2	193.7	192.4	193.6	195.4	199.3	203.0	207.8	212.9
55°	194.3	186.7	181.3	178.0	177.6	178.2	180.2	184.5	189.8	195.9	200.8
57.5°	174.7	168.3	163.4	161.2	161.4	162.0	165.3	170.3	176.1	182.5	188.8
60°	161.5	155.7	151.7	149.9	150.1	151.5	155.5	160.1	167.3	173.5	180.2
62.5°	149.0	143.9	140.1	138.5	138.2	141.1	145.0	149.8	156.9	163.9	171.2
65°	128.9	124.9	121.8	120.9	121.6	123.9	128.8	135.2	141.2	148.5	156.2
67.5°	109.3	106.0	103.9	104.2	105.1	108.4	112.4	118.0	124.9	132.5	140.0
70°	96.8	93.7	91.9	92.1	93.5	97.5	101.0	106.6	114.0	121.8	128.0
72.5°	84.0	81.9	80.3	81.2	82.6	85.3	89.8	95.4	101.9	109.1	115.7
75°	64.5	64.5	63.6	64.3	66.3	68.9	72.3	78.0	84.5	90.4	95.7
77.5°	47.8	47.3	47.9	48.7	49.9	53.1	56.9	61.1	65.9	71.7	76.2
80°	36.6	36.9	37.9	39.3	39.7	42.1	46.2	50.0	53.7	58.6	62.9
82.5°	27.5	27.7	28.3	30.0	30.4	33.1	35.6	39.4	42.9	46.2	49.7
85°	15.0	15.0	16.0	16.8	17.8	19.6	21.2	23.5	26.6	28.7	32.1
87.5°	7.4	7.4	9.5	9.8	10.8	12.2	12.3	14.5	15.4	16.5	18.1
90°	8.8	8.8	15.4	15.4	17.5	19.7	18.7	19.7	20.8	21.9	21.9
92.5°	57.9	80.6	136.3	221.2	304.1	347.4	289.4	215.1	161.8	128.8	106.9
95°	90.9	137.0	232.1	411.8	673.5	892.6	917.8	811.5	641.8	495.0	388.8
97.5°	110.0	148.5	221.9	370.2	630.4	940.2	1153.1	1199.1	1136.0	1028.9	914.5
100°	124.9	159.9	224.5	348.3	571.7	880.5	1160.9	1320.9	1342.7	1289.1	1208.1
102.5°	141.5	174.8	233.3	342.1	532.3	806.1	1095.2	1314.8	1423.3	1438.9	1405.1
105°	169.8	201.5	254.1	345.0	498.3	718.5	975.8	1226.6	1416.2	1524.6	1569.4
107.5°	198.9	230.3	278.4	361.2	492.2	669.4	879.5	1101.5	1303.3	1456.0	1553.7
110°	219.0	248.6	296.8	373.4	494.0	652.8	831.3	1026.2	1215.7	1374.5	1495.0



TEST NUMBER: P332528-830

CATALOG NUMBER: SA4XXDIP-C350D1205U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	238.4	267.9	314.3	386.6	499.2	644.9	804.1	971.0	1138.6	1288.6	1409.1
115°	268.3	297.9	341.7	407.5	509.3	640.7	778.7	915.6	1050.4	1178.5	1283.6
117.5°	296.0	326.6	368.3	428.7	520.0	639.6	767.3	888.4	999.9	1100.7	1189.9
120°	314.3	345.0	386.6	443.6	527.9	639.6	761.2	876.2	978.1	1065.6	1143.4
122.5°	332.7	362.5	404.2	457.6	535.8	638.8	754.2	865.6	964.0	1043.8	1111.9
125°	358.2	388.8	428.2	478.6	547.6	637.4	742.5	847.7	941.9	1017.5	1077.7
127.5°	381.5	412.5	450.5	496.8	557.0	635.0	727.0	825.8	915.9	991.2	1048.4
130°	396.4	428.2	465.5	508.2	564.0	634.1	717.4	808.3	894.8	969.3	1027.4
132.5°	410.5	440.5	477.8	519.6	570.1	633.3	708.6	789.9	871.2	943.9	1001.9
135°	430.5	458.9	495.0	534.5	579.4	632.0	695.5	764.5	835.7	902.5	957.2
137.5°	447.3	474.5	508.2	545.0	584.8	631.7	684.1	741.5	801.7	858.0	907.5
140°	457.8	484.1	517.0	552.0	589.3	630.8	678.0	728.3	779.8	829.1	875.1
142.5°	467.4	492.9	524.8	557.2	592.8	630.8	672.7	716.0	761.4	803.7	843.6
145°	480.8	504.9	533.4	563.0	594.7	628.7	663.7	698.8	736.0	768.8	799.6
147.5°	493.7	515.4	542.2	568.0	595.8	624.7	655.6	684.6	714.1	740.4	764.5
150°	501.6	522.5	546.5	570.6	595.8	622.1	649.5	675.8	701.0	722.8	742.5
152.5°	509.5	528.6	550.1	572.4	594.1	617.7	642.4	666.1	687.8	707.9	724.2
155°	520.3	536.7	555.3	573.9	591.4	611.1	632.0	651.7	669.2	685.6	698.8
157.5°	530.3	543.3	559.0	573.9	588.6	604.4	621.2	636.1	650.8	664.6	675.1
160°	535.6	547.6	560.7	573.9	586.0	599.1	613.3	626.5	638.5	650.5	659.3
162.5°	540.8	550.3	562.5	573.9	583.3	593.8	606.3	616.8	627.2	636.6	644.4
165°	546.5	553.1	563.0	571.7	578.2	586.0	594.7	603.5	610.0	617.7	623.2
167.5°	550.4	555.5	562.7	569.1	573.1	578.1	584.2	590.6	595.6	601.7	605.0
170°	553.1	556.4	561.8	567.3	569.5	572.8	577.2	582.7	586.0	590.3	593.6
172.5°	554.9	557.2	561.0	565.6	566.0	567.5	571.1	575.6	578.1	580.7	583.1
175°	557.5	557.5	559.7	563.0	561.8	561.8	564.0	566.3	567.3	569.5	569.5
177.5°	557.5	557.5	558.4	560.1	558.4	558.4	559.2	560.1	561.0	561.0	561.8
180°	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5



TEST NUMBER: P332528-830

CATALOG NUMBER: SA4XXDIP-C350D1205U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	538.5	538.5	538.5	538.5	538.5	538.5	538.5	538.5	538.5	538.5	538.5
2.5°	513.1	512.8	511.5	511.3	511.5	512.8	513.1	513.5	514.1	515.9	513.7
5°	474.0	472.9	472.2	474.7	472.2	472.9	474.0	475.3	477.6	477.8	480.0
7.5°	444.5	443.7	441.7	441.0	441.7	443.7	444.5	445.4	447.5	449.5	452.8
10°	425.7	424.7	422.9	422.4	422.9	424.7	425.7	427.8	430.1	432.5	434.8
12.5°	407.4	405.7	405.3	405.8	405.3	405.7	407.4	410.4	416.1	416.1	416.6
15°	383.2	382.3	379.8	380.6	379.8	382.3	383.2	386.2	388.8	392.2	395.5
17.5°	359.4	358.4	355.3	358.0	355.3	358.4	359.4	361.0	364.4	369.1	374.2
20°	344.4	342.6	341.1	340.8	341.1	342.6	344.4	346.0	349.8	353.8	357.6
22.5°	330.2	328.6	328.4	327.0	328.4	328.6	330.2	332.6	336.4	338.7	342.2
25°	312.3	310.8	310.3	309.2	310.3	310.8	312.3	314.1	316.5	318.3	322.3
27.5°	298.6	297.8	297.0	297.4	297.0	297.8	298.6	298.8	299.9	302.3	304.6
30°	290.2	290.0	289.5	289.5	289.5	290.0	290.2	289.5	290.7	291.8	293.6
32.5°	283.2	283.2	283.5	283.5	283.5	283.2	283.2	282.2	282.7	283.0	283.9
35°	273.5	274.2	274.6	273.9	274.6	274.2	273.5	272.6	271.9	270.3	270.8
37.5°	264.7	265.3	266.0	266.7	266.0	265.3	264.7	262.8	261.2	259.9	258.3
40°	257.9	259.4	259.9	261.0	259.9	259.4	257.9	255.9	254.1	252.5	250.7
42.5°	251.5	253.2	254.3	254.6	254.3	253.2	251.5	249.4	246.8	244.9	242.3
45°	241.6	243.4	245.0	245.0	245.0	243.4	241.6	238.3	235.4	232.4	230.0
47.5°	231.4	233.9	235.5	235.9	235.5	233.9	231.4	227.9	223.9	220.3	216.8
50°	224.4	227.5	229.1	230.2	229.1	227.5	224.4	220.6	216.4	211.9	207.6
52.5°	217.6	220.7	222.8	223.4	222.8	220.7	217.6	212.9	207.8	203.0	199.3
55°	205.9	210.4	212.8	213.7	212.8	210.4	205.9	200.8	195.9	189.8	184.5
57.5°	194.8	199.0	201.8	202.5	201.8	199.0	194.8	188.8	182.5	176.1	170.3
60°	186.2	190.8	194.3	194.9	194.3	190.8	186.2	180.2	173.5	167.3	160.1
62.5°	177.5	182.2	185.4	187.1	185.4	182.2	177.5	171.2	163.9	156.9	149.8
65°	162.4	167.1	170.2	170.9	170.2	167.1	162.4	156.2	148.5	141.2	135.2
67.5°	145.9	150.6	152.6	153.9	152.6	150.6	145.9	140.0	132.5	124.9	118.0
70°	134.3	138.1	140.3	141.4	140.3	138.1	134.3	128.0	121.8	114.0	106.6
72.5°	121.1	125.1	127.6	127.9	127.6	125.1	121.1	115.7	109.1	101.9	95.4
75°	100.9	104.4	105.8	105.8	105.8	104.4	100.9	95.7	90.4	84.5	78.0
77.5°	79.8	81.6	83.3	83.7	83.3	81.6	79.8	76.2	71.7	65.9	61.1
80°	66.3	67.4	68.7	68.7	68.7	67.4	66.3	62.9	58.6	53.7	50.0
82.5°	52.3	53.3	54.6	54.4	54.6	53.3	52.3	49.7	46.2	42.9	39.4
85°	31.7	33.6	33.5	33.0	33.5	33.6	31.7	32.1	28.7	26.6	23.5
87.5°	18.9	19.2	19.6	20.0	19.6	19.2	18.9	18.1	16.5	15.4	14.5
90°	23.0	24.1	23.0	23.0	23.0	24.1	23.0	21.9	21.9	20.8	19.7
92.5°	94.0	88.0	84.4	84.4	84.4	88.0	94.0	106.9	128.8	161.8	215.1
95°	335.2	301.2	281.4	267.2	281.4	301.2	335.2	388.8	495.0	641.8	811.5
97.5°	835.8	770.0	737.1	714.4	737.1	770.0	835.8	914.5	1028.9	1136.0	1199.1
100°	1112.8	1045.9	1013.1	1004.4	1013.1	1045.9	1112.8	1208.1	1289.1	1342.7	1320.9
102.5°	1346.7	1298.3	1263.7	1256.7	1263.7	1298.3	1346.7	1405.1	1438.9	1423.3	1314.8
105°	1571.7	1562.9	1547.6	1541.0	1547.6	1562.9	1571.7	1569.4	1524.6	1416.2	1226.6
107.5°	1607.8	1632.8	1643.7	1646.6	1643.7	1632.8	1607.8	1553.7	1456.0	1303.3	1101.5
110°	1572.7	1618.7	1638.5	1648.3	1638.5	1618.7	1572.7	1495.0	1374.5	1215.7	1026.2



TEST NUMBER: P332528-830

CATALOG NUMBER: SA4XXDIP-C350D1205U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1497.4	1553.0	1580.6	1596.7	1580.6	1553.0	1497.4	1409.1	1288.6	1138.6	971.0
115°	1370.2	1435.9	1470.9	1479.7	1470.9	1435.9	1370.2	1283.6	1178.5	1050.4	915.6
117.5°	1263.7	1318.9	1354.3	1361.1	1354.3	1318.9	1263.7	1189.9	1100.7	999.9	888.4
120°	1205.9	1254.1	1282.5	1294.6	1282.5	1254.1	1205.9	1143.4	1065.6	978.1	876.2
122.5°	1164.7	1205.9	1229.9	1242.0	1229.9	1205.9	1164.7	1111.9	1043.8	964.0	865.6
125°	1121.5	1153.3	1174.1	1180.6	1174.1	1153.3	1121.5	1077.7	1017.5	941.9	847.7
127.5°	1092.4	1120.7	1138.2	1144.7	1138.2	1120.7	1092.4	1048.4	991.2	915.9	825.8
130°	1072.2	1099.6	1117.1	1123.7	1117.1	1099.6	1072.2	1027.4	969.3	894.8	808.3
132.5°	1045.9	1076.9	1093.4	1100.0	1093.4	1076.9	1045.9	1001.9	943.9	871.2	789.9
135°	1001.1	1031.7	1049.2	1055.8	1049.2	1031.7	1001.1	957.2	902.5	835.7	764.5
137.5°	948.5	978.7	993.2	1001.1	993.2	978.7	948.5	907.5	858.0	801.7	741.5
140°	913.4	937.5	952.8	961.6	952.8	937.5	913.4	875.1	829.1	779.8	728.3
142.5°	877.5	899.8	913.4	919.5	913.4	899.8	877.5	843.6	803.7	761.4	716.0
145°	826.9	845.6	856.5	862.0	856.5	845.6	826.9	799.6	768.8	736.0	698.8
147.5°	784.7	800.6	809.0	810.9	809.0	800.6	784.7	764.5	740.4	714.1	684.6
150°	760.1	774.3	780.9	782.0	780.9	774.3	760.1	742.5	722.8	701.0	675.8
152.5°	739.0	750.6	754.6	755.7	754.6	750.6	739.0	724.2	707.9	687.8	666.1
155°	709.7	718.5	721.8	721.8	721.8	718.5	709.7	698.8	685.6	669.2	651.7
157.5°	683.4	690.0	692.0	692.0	692.0	690.0	683.4	675.1	664.6	650.8	636.1
160°	665.9	672.5	673.5	673.5	673.5	672.5	665.9	659.3	650.5	638.5	626.5
162.5°	649.2	655.8	657.0	656.0	657.0	655.8	649.2	644.4	636.6	627.2	616.8
165°	627.5	632.0	630.8	629.8	630.8	632.0	627.5	623.2	617.7	610.0	603.5
167.5°	607.2	610.0	609.8	609.0	609.8	610.0	607.2	605.0	601.7	595.6	590.6
170°	595.8	596.9	595.8	595.8	595.8	596.9	595.8	593.6	590.3	586.0	582.7
172.5°	584.4	585.5	584.4	582.7	584.4	585.5	584.4	583.1	580.7	578.1	575.6
175°	569.5	571.7	569.5	567.3	569.5	571.7	569.5	569.5	569.5	567.3	566.3
177.5°	561.0	561.8	560.1	558.4	560.1	561.8	561.0	561.8	561.0	561.0	560.1
180°	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5



TEST NUMBER: P332528-830

CATALOG NUMBER: SA4XXDIP-C350D1205U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	538.5	538.5	538.5	538.5	538.5	538.5	538.5	538.5	538.5	538.5	538.5
2.5°	514.7	515.5	518.3	521.0	524.2	526.5	528.1	529.9	533.7	536.7	539.6
5°	482.3	483.4	489.2	493.2	500.1	506.1	510.9	515.9	522.0	530.3	537.8
7.5°	453.6	457.8	464.2	470.7	477.7	485.6	492.5	500.2	510.6	522.0	533.7
10°	437.4	442.1	448.8	456.4	463.1	472.2	480.7	489.8	501.7	515.5	529.3
12.5°	421.2	429.0	434.0	443.0	450.3	457.8	466.8	478.8	492.6	507.1	523.8
15°	400.9	405.1	414.9	419.8	430.1	441.7	450.6	462.6	476.0	495.2	514.0
17.5°	377.4	383.0	390.8	400.1	411.9	420.9	432.1	444.5	461.4	480.4	503.9
20°	362.0	366.7	376.4	386.5	399.1	408.7	420.5	432.5	450.0	470.2	494.7
22.5°	348.3	352.8	363.0	372.5	384.7	396.3	408.7	422.7	439.4	460.8	485.9
25°	327.1	333.0	342.0	351.8	363.4	376.7	390.1	402.7	420.5	443.0	469.8
27.5°	308.1	312.9	319.4	330.5	343.7	356.7	369.9	385.7	402.8	426.7	454.4
30°	296.1	300.5	307.0	317.2	329.5	343.3	357.1	372.3	390.1	413.8	442.1
32.5°	286.3	289.7	295.5	304.7	315.9	330.5	344.1	359.8	378.5	401.8	429.4
35°	272.1	275.0	277.3	286.0	296.1	309.4	323.2	340.0	358.1	380.1	407.7
37.5°	258.2	259.2	262.4	268.2	277.9	290.2	303.0	319.5	338.0	360.4	385.4
40°	249.6	250.1	252.0	257.4	265.9	277.5	290.0	306.2	323.9	345.1	369.9
42.5°	241.2	240.9	242.8	246.6	254.5	265.0	277.3	292.2	309.8	329.4	352.7
45°	228.0	228.0	227.5	230.6	237.1	247.4	257.7	271.9	286.6	305.9	325.5
47.5°	214.1	212.9	213.3	214.9	220.4	228.8	239.1	250.8	263.8	280.0	297.3
50°	205.2	203.4	202.7	204.5	209.4	216.8	226.7	236.9	249.2	263.4	278.1
52.5°	195.4	193.6	192.4	193.7	198.2	205.0	214.0	223.0	234.0	245.6	258.4
55°	180.2	178.2	177.6	178.0	181.3	186.7	194.3	202.6	210.8	220.4	229.3
57.5°	165.3	162.0	161.4	161.2	163.4	168.3	174.7	181.8	187.8	193.7	203.2
60°	155.5	151.5	150.1	149.9	151.7	155.7	161.5	168.6	172.9	176.9	185.1
62.5°	145.0	141.1	138.2	138.5	140.1	143.9	149.0	154.2	157.0	161.4	166.9
65°	128.8	123.9	121.6	120.9	121.8	124.9	128.9	132.2	135.4	137.2	142.5
67.5°	112.4	108.4	105.1	104.2	103.9	106.0	109.3	111.3	113.6	115.1	118.3
70°	101.0	97.5	93.5	92.1	91.9	93.7	96.8	97.1	100.2	100.9	104.2
72.5°	89.8	85.3	82.6	81.2	80.3	81.9	84.0	84.5	86.2	87.5	89.2
75°	72.3	68.9	66.3	64.3	63.6	64.5	64.5	65.6	66.7	67.4	69.4
77.5°	56.9	53.1	49.9	48.7	47.9	47.3	47.8	48.5	48.0	49.1	49.6
80°	46.2	42.1	39.7	39.3	37.9	36.9	36.6	37.2	36.4	36.9	38.2
82.5°	35.6	33.1	30.4	30.0	28.3	27.7	27.5	27.1	27.1	27.0	27.2
85°	21.2	19.6	17.8	16.8	16.0	15.0	15.0	14.5	14.0	13.6	13.9
87.5°	12.3	12.2	10.8	9.8	9.5	7.4	7.4	6.7	6.3	5.5	4.9
90°	18.7	19.7	17.5	15.4	15.4	8.8	8.8	7.6	6.6	3.3	1.1
92.5°	289.4	347.4	304.1	221.2	136.3	80.6	57.9	41.8	28.5	18.2	12.4
95°	917.8	892.6	673.5	411.8	232.1	137.0	90.9	64.7	50.4	39.4	36.1
97.5°	1153.1	940.2	630.4	370.2	221.9	148.5	110.0	87.4	74.3	64.8	64.8
100°	1160.9	880.5	571.7	348.3	224.5	159.9	124.9	104.1	90.9	83.2	83.2
102.5°	1095.2	806.1	532.3	342.1	233.3	174.8	141.5	121.6	109.3	102.5	100.8
105°	975.8	718.5	498.3	345.0	254.1	201.5	169.8	150.1	137.0	131.4	128.2
107.5°	879.5	669.4	492.2	361.2	278.4	230.3	198.9	180.0	166.1	160.5	158.3
110°	831.3	652.8	494.0	373.4	296.8	248.6	219.0	199.3	186.2	180.7	178.5



TEST NUMBER: P332528-830

CATALOG NUMBER: SA4XXDIP-C350D1205U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	804.1	644.9	499.2	386.6	314.3	267.9	238.4	218.6	206.3	200.0	197.8
115°	778.7	640.7	509.3	407.5	341.7	297.9	268.3	247.5	236.6	228.9	225.6
117.5°	767.3	639.6	520.0	428.7	368.3	326.6	296.0	276.4	264.4	257.6	254.5
120°	761.2	639.6	527.9	443.6	386.6	345.0	314.3	295.7	283.7	276.0	273.8
122.5°	754.2	638.8	535.8	457.6	404.2	362.5	332.7	312.4	301.2	293.5	291.3
125°	742.5	637.4	547.6	478.6	428.2	388.8	358.2	337.3	325.3	318.7	314.3
127.5°	727.0	635.0	557.0	496.8	450.5	412.5	381.5	359.9	346.1	338.2	334.7
130°	717.4	634.1	564.0	508.2	465.5	428.2	396.4	375.7	359.2	350.4	346.1
132.5°	708.6	633.3	570.1	519.6	477.8	440.5	410.5	388.0	372.4	361.0	357.5
135°	695.5	632.0	579.4	534.5	495.0	458.9	430.5	407.5	388.8	377.9	373.4
137.5°	684.1	631.7	584.8	545.0	508.2	474.5	447.3	423.4	405.7	393.6	389.5
140°	678.0	630.8	589.3	552.0	517.0	484.1	457.8	434.8	416.2	404.2	400.9
142.5°	672.7	630.8	592.8	557.2	524.8	492.9	467.4	445.4	427.5	416.4	413.1
145°	663.7	628.7	594.7	563.0	533.4	504.9	480.8	460.0	444.7	433.8	430.5
147.5°	655.6	624.7	595.8	568.0	542.2	515.4	493.7	476.5	460.6	451.0	449.9
150°	649.5	622.1	595.8	570.6	546.5	522.5	501.6	485.2	472.0	463.3	462.2
152.5°	642.4	617.7	594.1	572.4	550.1	528.6	509.5	494.8	482.6	473.8	473.5
155°	632.0	611.1	591.4	573.9	555.3	536.7	520.3	508.2	497.2	490.7	489.6
157.5°	621.2	604.4	588.6	573.9	559.0	543.3	530.3	519.8	511.2	505.1	505.1
160°	613.3	599.1	586.0	573.9	560.7	547.6	535.6	526.8	519.2	514.7	514.7
162.5°	606.3	593.8	583.3	573.9	562.5	550.3	540.8	532.9	526.1	522.6	523.5
165°	594.7	586.0	578.2	571.7	563.0	553.1	546.5	541.0	535.6	533.4	533.4
167.5°	584.2	578.1	573.1	569.1	562.7	555.5	550.4	547.4	543.3	542.2	543.3
170°	577.2	572.8	569.5	567.3	561.8	556.4	553.1	550.9	547.6	546.5	547.6
172.5°	571.1	567.5	566.0	565.6	561.0	557.2	554.9	553.6	551.1	550.9	552.0
175°	564.0	561.8	561.8	563.0	559.7	557.5	557.5	556.4	555.3	555.3	556.4
177.5°	559.2	558.4	558.4	560.1	558.4	557.5	557.5	557.5	556.6	557.5	558.4
180°	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5



TEST NUMBER: P332528-830

CATALOG NUMBER: SA4XXDIP-C350D1205U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	538.5	538.5	538.5	538.5	538.5	538.5	538.5	538.5	538.5	538.5	538.5
2.5°	542.1	543.8	546.2	550.1	551.5	553.3	555.8	555.6	556.3	559.0	564.7
5°	544.0	551.0	557.7	565.7	574.2	579.8	587.3	592.0	596.7	602.8	613.0
7.5°	544.9	555.8	568.1	582.2	594.7	609.2	620.5	631.1	640.7	653.4	665.6
10°	543.7	558.4	574.2	592.0	611.0	627.1	641.6	658.1	672.1	687.5	701.3
12.5°	541.3	559.0	580.2	600.2	622.4	646.1	664.2	680.9	699.6	717.3	738.7
15°	536.0	560.3	585.1	611.4	641.1	668.5	694.7	716.2	736.3	762.9	790.8
17.5°	529.3	555.5	586.8	618.7	649.7	681.0	713.3	745.8	771.2	804.2	826.0
20°	523.1	553.5	585.6	623.5	654.5	693.5	725.7	757.1	791.9	824.7	850.8
22.5°	514.3	547.5	581.6	619.3	660.2	699.3	736.3	770.4	805.3	840.9	872.5
25°	503.2	533.4	573.7	616.5	657.1	699.6	742.2	784.9	822.5	860.2	889.6
27.5°	484.4	522.4	560.0	604.2	649.2	697.2	742.8	787.6	826.9	857.9	876.1
30°	474.7	507.7	548.6	593.0	641.8	693.3	740.8	784.8	821.3	846.1	853.5
32.5°	460.4	494.5	534.4	580.4	632.2	685.1	734.5	776.0	806.5	819.5	810.7
35°	439.2	470.0	510.4	557.4	611.2	667.6	716.5	751.5	767.1	754.9	724.3
37.5°	413.8	444.3	484.8	531.1	586.7	644.1	688.2	713.5	708.3	677.8	632.3
40°	396.0	424.5	463.1	513.0	567.2	624.8	663.6	677.2	663.0	619.3	570.8
42.5°	376.2	404.0	442.7	491.0	548.4	601.4	635.3	636.4	612.5	560.2	511.6
45°	346.0	372.5	409.1	459.3	512.4	562.3	584.7	573.7	529.5	479.2	430.3
47.5°	316.2	339.2	375.3	422.9	473.3	515.4	526.5	506.8	459.8	410.8	365.5
50°	294.5	317.6	351.6	397.1	445.7	482.0	487.4	461.3	415.1	365.8	330.4
52.5°	273.5	296.6	329.2	371.4	415.8	448.7	448.8	418.7	372.7	328.8	295.8
55°	242.9	263.6	293.1	330.8	370.5	396.2	389.9	358.7	318.8	280.6	251.8
57.5°	213.4	231.5	258.5	290.0	325.0	346.2	335.8	305.8	270.1	237.7	215.9
60°	194.3	211.5	234.7	264.4	293.8	310.3	300.5	273.2	240.4	214.3	195.4
62.5°	175.7	190.2	212.5	238.3	265.6	277.8	269.1	242.2	213.9	190.3	174.8
65°	149.5	161.3	179.1	201.2	221.0	231.6	224.2	199.2	177.6	160.6	148.4
67.5°	124.9	134.1	147.7	165.4	182.3	187.9	181.3	163.8	145.5	132.0	123.3
70°	107.9	116.7	128.0	141.7	156.4	162.4	155.7	141.9	127.0	114.4	105.9
72.5°	93.1	99.9	109.5	121.1	132.6	138.6	134.1	120.8	108.2	98.9	91.7
75°	71.0	76.7	83.4	91.7	100.6	104.6	100.6	91.4	82.8	75.9	70.7
77.5°	51.6	54.7	59.9	66.1	71.6	74.6	71.2	65.0	59.7	55.0	52.4
80°	39.3	41.5	45.1	50.0	53.7	56.6	54.4	49.3	45.1	41.9	40.8
82.5°	28.6	30.1	32.4	36.0	38.5	40.1	39.1	35.3	33.6	30.9	29.8
85°	14.0	15.0	16.5	17.6	19.9	20.1	20.3	18.8	17.2	16.5	15.6
87.5°	5.5	6.3	7.1	7.8	8.6	10.0	9.8	10.3	10.0	9.6	9.1
90°	3.3	6.6	7.6	8.8	8.8	15.4	15.4	17.5	19.7	18.7	19.7
92.5°	18.2	28.5	41.8	57.9	80.6	136.3	221.2	304.1	347.4	289.4	215.1
95°	39.4	50.4	64.7	90.9	137.0	232.1	411.8	673.5	892.6	917.8	811.5
97.5°	64.8	74.3	87.4	110.0	148.5	221.9	370.2	630.4	940.2	1153.1	1199.1
100°	83.2	90.9	104.1	124.9	159.9	224.5	348.3	571.7	880.5	1160.9	1320.9
102.5°	102.5	109.3	121.6	141.5	174.8	233.3	342.1	532.3	806.1	1095.2	1314.8
105°	131.4	137.0	150.1	169.8	201.5	254.1	345.0	498.3	718.5	975.8	1226.6
107.5°	160.5	166.1	180.0	198.9	230.3	278.4	361.2	492.2	669.4	879.5	1101.5
110°	180.7	186.2	199.3	219.0	248.6	296.8	373.4	494.0	652.8	831.3	1026.2



TEST NUMBER: P332528-830

CATALOG NUMBER: SA4XXDIP-C350D1205U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	200.0	206.3	218.6	238.4	267.9	314.3	386.6	499.2	644.9	804.1	971.0
115°	228.9	236.6	247.5	268.3	297.9	341.7	407.5	509.3	640.7	778.7	915.6
117.5°	257.6	264.4	276.4	296.0	326.6	368.3	428.7	520.0	639.6	767.3	888.4
120°	276.0	283.7	295.7	314.3	345.0	386.6	443.6	527.9	639.6	761.2	876.2
122.5°	293.5	301.2	312.4	332.7	362.5	404.2	457.6	535.8	638.8	754.2	865.6
125°	318.7	325.3	337.3	358.2	388.8	428.2	478.6	547.6	637.4	742.5	847.7
127.5°	338.2	346.1	359.9	381.5	412.5	450.5	496.8	557.0	635.0	727.0	825.8
130°	350.4	359.2	375.7	396.4	428.2	465.5	508.2	564.0	634.1	717.4	808.3
132.5°	361.0	372.4	388.0	410.5	440.5	477.8	519.6	570.1	633.3	708.6	789.9
135°	377.9	388.8	407.5	430.5	458.9	495.0	534.5	579.4	632.0	695.5	764.5
137.5°	393.6	405.7	423.4	447.3	474.5	508.2	545.0	584.8	631.7	684.1	741.5
140°	404.2	416.2	434.8	457.8	484.1	517.0	552.0	589.3	630.8	678.0	728.3
142.5°	416.4	427.5	445.4	467.4	492.9	524.8	557.2	592.8	630.8	672.7	716.0
145°	433.8	444.7	460.0	480.8	504.9	533.4	563.0	594.7	628.7	663.7	698.8
147.5°	451.0	460.6	476.5	493.7	515.4	542.2	568.0	595.8	624.7	655.6	684.6
150°	463.3	472.0	485.2	501.6	522.5	546.5	570.6	595.8	622.1	649.5	675.8
152.5°	473.8	482.6	494.8	509.5	528.6	550.1	572.4	594.1	617.7	642.4	666.1
155°	490.7	497.2	508.2	520.3	536.7	555.3	573.9	591.4	611.1	632.0	651.7
157.5°	505.1	511.2	519.8	530.3	543.3	559.0	573.9	588.6	604.4	621.2	636.1
160°	514.7	519.2	526.8	535.6	547.6	560.7	573.9	586.0	599.1	613.3	626.5
162.5°	522.6	526.1	532.9	540.8	550.3	562.5	573.9	583.3	593.8	606.3	616.8
165°	533.4	535.6	541.0	546.5	553.1	563.0	571.7	578.2	586.0	594.7	603.5
167.5°	542.2	543.3	547.4	550.4	555.5	562.7	569.1	573.1	578.1	584.2	590.6
170°	546.5	547.6	550.9	553.1	556.4	561.8	567.3	569.5	572.8	577.2	582.7
172.5°	550.9	551.1	553.6	554.9	557.2	561.0	565.6	566.0	567.5	571.1	575.6
175°	555.3	555.3	556.4	557.5	557.5	559.7	563.0	561.8	561.8	564.0	566.3
177.5°	557.5	556.6	557.5	557.5	557.5	558.4	560.1	558.4	558.4	559.2	560.1
180°	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5	557.5



TEST NUMBER: P332528-830

CATALOG NUMBER: SA4XXDIP-C350D1205U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	538.5	538.5	538.5	538.5	538.5	538.5	538.5
2.5°	567.6	568.0	569.6	570.8	571.2	573.0	573.1
5°	617.5	621.2	628.6	629.2	630.4	636.2	631.7
7.5°	675.9	685.5	691.9	697.7	699.6	702.2	701.7
10°	713.4	727.6	734.8	746.2	746.6	749.5	747.7
12.5°	751.0	767.6	780.6	782.8	792.3	793.8	796.3
15°	804.4	822.0	840.1	846.6	859.7	862.8	867.7
17.5°	854.5	872.5	885.2	901.9	907.4	914.5	909.6
20°	882.0	901.6	917.8	930.9	936.4	940.5	940.0
22.5°	898.6	918.4	931.4	941.4	946.6	948.3	948.2
25°	909.0	920.4	924.4	928.2	922.4	920.4	921.2
27.5°	880.1	877.1	866.7	852.9	838.7	827.4	821.1
30°	840.3	822.9	807.1	779.4	765.2	756.7	749.0
32.5°	783.9	756.3	725.9	700.5	684.3	671.8	669.9
35°	687.3	645.8	608.5	577.5	561.5	547.9	544.7
37.5°	584.3	541.2	507.7	480.3	463.1	453.5	444.5
40°	515.9	478.9	445.9	422.7	409.5	402.7	397.1
42.5°	463.4	429.5	396.6	379.0	367.1	362.9	359.6
45°	390.6	359.1	336.4	323.0	316.1	309.0	305.6
47.5°	332.3	306.8	291.8	280.4	273.0	268.7	266.6
50°	299.4	278.4	265.0	256.3	249.6	246.3	244.5
52.5°	270.1	252.9	241.7	234.7	230.2	227.7	227.0
55°	232.6	219.5	212.4	206.3	203.0	200.8	199.9
57.5°	202.3	192.1	186.3	181.3	180.0	178.2	177.6
60°	182.3	174.5	169.6	166.2	165.0	162.9	163.2
62.5°	164.6	158.2	154.0	152.1	150.6	148.7	149.4
65°	139.2	134.5	132.2	130.5	128.8	127.6	128.5
67.5°	116.8	113.6	110.6	109.5	108.7	108.5	107.5
70°	102.2	99.5	96.8	96.1	96.1	95.3	95.0
72.5°	88.0	86.1	84.4	83.8	83.1	83.5	82.6
75°	68.1	66.4	65.8	65.1	64.9	64.9	64.3
77.5°	50.2	49.1	48.1	48.1	47.2	46.9	46.8
80°	38.2	37.7	36.9	36.9	36.4	36.6	36.1
82.5°	28.7	28.1	27.9	27.5	26.9	27.0	26.5
85°	15.4	14.7	14.5	13.9	13.4	13.9	13.4
87.5°	9.5	9.5	9.3	9.2	9.2	9.0	8.5
90°	20.8	21.9	21.9	23.0	24.1	23.0	23.0
92.5°	161.8	128.8	106.9	94.0	88.0	84.4	84.4
95°	641.8	495.0	388.8	335.2	301.2	281.4	267.2
97.5°	1136.0	1028.9	914.5	835.8	770.0	737.1	714.4
100°	1342.7	1289.1	1208.1	1112.8	1045.9	1013.1	1004.4
102.5°	1423.3	1438.9	1405.1	1346.7	1298.3	1263.7	1256.7
105°	1416.2	1524.6	1569.4	1571.7	1562.9	1547.6	1541.0
107.5°	1303.3	1456.0	1553.7	1607.8	1632.8	1643.7	1646.6
110°	1215.7	1374.5	1495.0	1572.7	1618.7	1638.5	1648.3



TEST NUMBER: P332528-830

CATALOG NUMBER: SA4XXDIP-C350D1205U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1138.6	1288.6	1409.1	1497.4	1553.0	1580.6	1596.7
115°	1050.4	1178.5	1283.6	1370.2	1435.9	1470.9	1479.7
117.5°	999.9	1100.7	1189.9	1263.7	1318.9	1354.3	1361.1
120°	978.1	1065.6	1143.4	1205.9	1254.1	1282.5	1294.6
122.5°	964.0	1043.8	1111.9	1164.7	1205.9	1229.9	1242.0
125°	941.9	1017.5	1077.7	1121.5	1153.3	1174.1	1180.6
127.5°	915.9	991.2	1048.4	1092.4	1120.7	1138.2	1144.7
130°	894.8	969.3	1027.4	1072.2	1099.6	1117.1	1123.7
132.5°	871.2	943.9	1001.9	1045.9	1076.9	1093.4	1100.0
135°	835.7	902.5	957.2	1001.1	1031.7	1049.2	1055.8
137.5°	801.7	858.0	907.5	948.5	978.7	993.2	1001.1
140°	779.8	829.1	875.1	913.4	937.5	952.8	961.6
142.5°	761.4	803.7	843.6	877.5	899.8	913.4	919.5
145°	736.0	768.8	799.6	826.9	845.6	856.5	862.0
147.5°	714.1	740.4	764.5	784.7	800.6	809.0	810.9
150°	701.0	722.8	742.5	760.1	774.3	780.9	782.0
152.5°	687.8	707.9	724.2	739.0	750.6	754.6	755.7
155°	669.2	685.6	698.8	709.7	718.5	721.8	721.8
157.5°	650.8	664.6	675.1	683.4	690.0	692.0	692.0
160°	638.5	650.5	659.3	665.9	672.5	673.5	673.5
162.5°	627.2	636.6	644.4	649.2	655.8	657.0	656.0
165°	610.0	617.7	623.2	627.5	632.0	630.8	629.8
167.5°	595.6	601.7	605.0	607.2	610.0	609.8	609.0
170°	586.0	590.3	593.6	595.8	596.9	595.8	595.8
172.5°	578.1	580.7	583.1	584.4	585.5	584.4	582.7
175°	567.3	569.5	569.5	569.5	571.7	569.5	567.3
177.5°	561.0	561.0	561.8	561.0	561.8	560.1	558.4
180°	557.5	557.5	557.5	557.5	557.5	557.5	557.5

(END OF REPORT)