

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332572-830

Luminaire Tested: **SA4XXDIP-C575D1205U830-4F0-1E-UDD-A1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332572-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C575D1205U830-4F0-1E-UDD-A1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1205 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6375.0 lumens
Efficiency: N/A
Efficacy: 129.0 lumens/watt
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 49.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332572-830
CATALOG NUMBER: SA4XXDIP-C575D1205U830-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P332572-830

CATALOG NUMBER: SA4XXDIP-C575D1205U830-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45	38
1	95	91	87	84	86	83	80	77	68	65	63	53	52	51	40	39	39	33
2	87	80	74	69	79	73	68	63	59	56	53	47	45	42	36	34	33	28
3	79	70	63	57	72	64	58	53	52	48	44	42	39	36	32	30	28	24
4	73	62	55	49	66	57	50	45	47	42	38	37	34	31	29	26	24	20
5	67	55	48	42	60	51	44	39	42	37	33	33	30	27	26	23	21	18
6	61	50	42	36	56	46	39	34	38	32	29	30	27	24	23	21	19	16
7	57	45	37	32	51	41	34	29	34	29	25	28	24	21	21	19	17	14
8	53	41	33	28	48	37	31	26	31	26	22	25	21	19	20	17	15	13
9	49	37	30	25	44	34	28	23	28	23	20	23	19	17	18	15	14	11
10	46	34	27	22	42	31	25	21	26	21	18	21	18	15	17	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	7146	7146	7146	7146
5°	8417	7165	6324	7165
10°	10077	7133	5694	7133
15°	11922	7061	5229	7061
20°	13277	6988	4814	6988
25°	13491	6879	4528	6879
30°	11479	6776	4437	6776
35°	8825	6606	4438	6606
40°	6880	6407	4521	6407
45°	5736	6109	4598	6109
50°	5048	5743	4752	5743
55°	4625	5306	4944	5306
60°	4334	4913	5176	4913
65°	4034	4476	5366	4476
70°	3687	4043	5488	4043
75°	3297	3556	5421	3556
80°	2762	2915	5249	2915
85°	2038	2103	5030	2103



TEST NUMBER: P332572-830

CATALOG NUMBER: SA4XXDIP-C575D1205U830-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.2	1.4
10°-20°	265.8	4.2
20°-30°	421.5	6.6
30°-40°	469.1	7.4
40°-50°	427.0	6.7
50°-60°	349.0	5.5
60°-70°	249.1	3.9
70°-80°	137.2	2.2
80°-90°	41.7	0.7
90°-100°	93.4	1.5
100°-110°	276.7	4.3
110°-120°	469.6	7.4
120°-130°	619.1	9.7
130°-140°	695.3	10.9
140°-150°	683.3	10.7
150°-160°	574.7	9.0
160°-170°	382.4	6.0
170°-180°	133.9	2.1
0°-30°	773.6	12.1
0°-40°	1242.8	19.5
0°-60°	2018.8	31.7
0°-90°	2446.7	38.4
90°-120°	839.6	13.2
90°-150°	2837.4	44.5
90°-180°	3928.0	61.6
0°-180°	6375.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	885	885	885	885	885	
5°	1039	884	780	884	1039	106
15°	1426	845	626	845	1426	403
25°	1515	772	508	772	1515	668
35°	896	670	450	670	896	568
45°	502	535	403	535	502	396
55°	329	377	351	377	329	297
65°	211	234	281	234	211	209
75°	106	114	174	114	106	112
85°	22	23	54	23	22	28
90°	33	3	33	3	33	17
95°	86	66	86	66	86	90
105°	267	255	267	255	267	282
115°	473	477	473	477	473	468
125°	690	695	690	695	690	615
135°	898	897	898	897	898	693
145°	1091	1090	1091	1090	1091	683
155°	1247	1248	1247	1248	1247	574
165°	1356	1359	1356	1359	1356	382
175°	1407	1414	1407	1414	1407	134
180°	1416	1416	1416	1416	1416	



TEST NUMBER: P332572-830

CATALOG NUMBER: SA4XXDIP-C575D1205U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2
2.5°	942.2	941.9	939.0	938.4	936.3	933.7	933.1	928.4	919.0	914.6	913.4
5°	1038.6	1045.9	1036.3	1034.5	1033.4	1021.3	1015.1	1007.8	990.9	981.0	973.3
7.5°	1153.6	1154.4	1150.3	1146.9	1137.6	1127.0	1111.2	1094.3	1074.2	1053.3	1037.6
10°	1229.3	1232.2	1227.5	1226.7	1208.0	1196.3	1172.8	1153.0	1130.2	1104.9	1081.9
12.5°	1309.1	1305.0	1302.5	1286.9	1283.4	1262.0	1234.7	1214.3	1179.2	1150.1	1119.4
15°	1426.5	1418.5	1413.3	1391.8	1381.1	1351.4	1322.4	1300.0	1254.2	1210.6	1177.5
17.5°	1495.5	1503.5	1491.7	1482.8	1455.3	1434.5	1404.9	1357.9	1322.0	1267.8	1226.2
20°	1545.4	1546.1	1539.5	1530.3	1508.7	1482.3	1450.0	1398.7	1355.8	1301.8	1244.6
22.5°	1558.9	1559.1	1556.2	1547.7	1531.3	1509.9	1477.3	1434.5	1382.5	1323.9	1266.7
25°	1514.6	1513.2	1516.5	1526.0	1519.8	1513.2	1494.4	1462.5	1414.1	1352.1	1290.5
27.5°	1350.0	1360.1	1378.8	1402.2	1424.8	1442.0	1446.9	1440.4	1410.3	1359.3	1294.9
30°	1231.4	1244.0	1257.8	1281.4	1326.8	1352.8	1381.5	1403.1	1391.0	1350.3	1290.2
32.5°	1101.2	1104.3	1124.9	1151.7	1193.4	1243.4	1288.7	1332.7	1347.3	1326.0	1275.7
35°	895.5	900.7	923.0	949.4	1000.4	1061.7	1129.9	1190.7	1241.0	1261.2	1235.5
37.5°	730.8	745.6	761.3	789.7	834.6	889.8	960.6	1039.3	1114.3	1164.4	1172.9
40°	652.8	661.9	673.4	694.9	733.1	787.4	848.2	938.5	1018.0	1090.0	1113.4
42.5°	591.2	596.5	603.5	623.0	652.1	706.1	761.7	841.0	921.0	1006.9	1046.2
45°	502.4	507.9	519.6	531.0	553.0	590.4	642.2	707.4	787.7	870.6	943.2
47.5°	438.3	441.9	448.8	461.0	479.7	504.4	546.4	600.9	675.3	755.8	833.2
50°	401.9	404.8	410.4	421.4	435.6	457.7	492.1	543.1	601.4	682.5	758.4
52.5°	373.2	374.4	378.4	385.9	397.3	415.8	444.0	486.2	540.5	612.7	688.2
55°	328.6	330.1	333.8	339.2	349.1	360.9	382.5	414.1	461.4	524.1	589.7
57.5°	291.9	292.9	296.1	298.1	306.3	315.8	332.4	355.0	390.9	444.0	502.7
60°	268.4	267.7	271.4	273.2	278.7	286.8	299.6	321.2	352.4	395.3	449.2
62.5°	245.5	244.5	247.6	250.1	253.2	260.0	270.6	287.5	312.8	351.7	398.2
65°	211.2	209.8	211.6	214.5	217.4	221.1	228.8	243.8	264.0	291.9	327.4
67.5°	176.7	178.3	178.6	180.0	181.7	186.7	192.0	202.6	216.9	239.2	269.3
70°	156.2	156.6	158.1	158.1	159.2	163.5	168.0	174.2	188.1	208.7	233.3
72.5°	135.7	137.2	136.7	137.8	138.6	141.6	144.8	150.7	162.6	177.9	198.6
75°	105.7	106.7	106.7	107.1	108.2	109.2	111.9	116.2	124.7	136.0	150.3
77.5°	77.0	77.2	77.7	79.0	79.0	80.8	82.7	86.1	90.4	98.1	106.9
80°	59.4	60.1	59.8	60.5	60.5	62.0	62.7	67.1	68.9	74.1	81.1
82.5°	43.5	44.3	44.2	45.2	45.8	46.1	47.1	48.9	50.7	55.3	58.2
85°	22.0	22.7	22.0	22.7	23.8	24.2	25.3	25.6	27.1	28.3	30.8
87.5°	13.0	13.8	13.7	13.9	14.4	14.5	14.5	13.9	14.8	14.8	15.6
90°	32.9	32.3	31.9	31.4	30.9	30.0	28.5	27.1	25.5	24.1	22.1
92.5°	48.6	48.4	48.1	47.8	47.4	46.8	46.0	45.1	44.2	43.4	42.0
95°	86.5	86.5	86.5	86.5	86.5	86.1	85.4	84.6	84.0	83.2	81.5
97.5°	135.5	135.5	135.5	135.5	135.5	135.2	134.2	133.4	132.5	131.6	129.6
100°	169.8	169.8	169.8	169.8	169.8	169.5	169.0	168.5	168.1	167.6	165.3
102.5°	208.3	208.1	207.9	207.7	207.5	207.1	206.4	205.7	205.0	204.3	202.4
105°	267.2	266.5	265.7	265.0	264.3	263.5	262.8	262.1	261.4	260.6	259.7
107.5°	324.6	324.6	324.7	324.7	324.8	324.4	323.8	323.1	322.4	321.7	321.6
110°	365.7	365.0	364.3	363.5	362.8	362.7	363.2	363.6	364.2	364.7	364.9



TEST NUMBER: P332572-830

CATALOG NUMBER: SA4XXDIP-C575D1205U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	407.8	407.6	407.5	407.4	407.2	407.2	407.3	407.4	407.5	407.6	408.0
115°	473.1	473.3	473.5	473.8	474.0	474.3	474.5	474.8	475.0	475.2	475.7
117.5°	535.3	535.7	536.2	536.7	537.2	537.8	538.7	539.5	540.4	541.2	541.5
120°	582.6	582.1	581.5	581.1	580.6	581.0	582.2	583.4	584.7	585.9	586.5
122.5°	622.0	622.8	623.8	624.6	625.5	626.3	627.2	628.0	628.9	629.6	630.0
125°	689.8	690.3	690.9	691.4	691.8	692.3	692.8	693.2	693.8	694.3	694.5
127.5°	752.7	753.1	753.5	753.9	754.3	754.7	755.3	755.7	756.2	756.7	757.1
130°	793.9	794.8	795.9	796.8	797.8	798.5	799.0	799.5	800.0	800.5	800.5
132.5°	837.7	838.1	838.5	838.9	839.2	839.7	840.2	840.7	841.1	841.7	841.9
135°	898.0	898.6	899.4	900.1	900.9	901.4	901.9	902.5	903.0	903.4	903.4
137.5°	961.2	961.1	960.9	960.8	960.6	960.9	961.5	962.1	962.8	963.4	963.0
140°	999.8	1000.0	1000.2	1000.5	1000.8	1001.0	1001.3	1001.5	1001.7	1001.9	1001.9
142.5°	1038.3	1038.4	1038.4	1038.5	1038.5	1038.6	1038.6	1038.7	1038.7	1038.8	1039.0
145°	1090.7	1091.4	1092.1	1092.9	1093.5	1094.1	1094.3	1094.6	1094.8	1095.0	1094.8
147.5°	1143.7	1143.9	1144.2	1144.4	1144.6	1144.8	1145.1	1145.3	1145.5	1145.7	1145.8
150°	1176.1	1176.3	1176.6	1176.8	1177.0	1177.1	1177.1	1177.1	1177.1	1177.1	1177.1
152.5°	1205.9	1206.5	1207.1	1207.8	1208.4	1208.4	1207.9	1207.2	1206.6	1206.1	1205.9
155°	1247.3	1248.2	1249.2	1250.2	1251.1	1251.1	1250.2	1249.2	1248.2	1247.3	1247.5
157.5°	1284.3	1285.1	1285.9	1286.8	1287.6	1287.6	1286.9	1286.2	1285.4	1284.7	1284.8
160°	1305.3	1306.6	1307.7	1308.9	1310.1	1310.4	1309.7	1308.9	1308.2	1307.5	1307.7
162.5°	1327.2	1328.4	1329.6	1330.9	1332.1	1332.0	1330.7	1329.4	1328.0	1326.7	1327.0
165°	1355.7	1356.6	1357.6	1358.6	1359.5	1359.3	1357.8	1356.4	1354.9	1353.5	1354.0
167.5°	1376.0	1377.5	1379.0	1380.5	1382.1	1382.1	1380.6	1379.1	1377.7	1376.2	1376.2
170°	1387.4	1389.1	1390.8	1392.5	1394.2	1394.4	1392.9	1391.5	1390.0	1388.6	1388.3
172.5°	1397.0	1398.7	1400.4	1402.1	1403.9	1403.9	1402.2	1400.6	1398.9	1397.3	1397.2
175°	1407.1	1408.8	1410.5	1412.2	1413.9	1413.9	1412.2	1410.5	1408.8	1407.1	1407.4
177.5°	1412.4	1413.9	1415.5	1417.0	1418.6	1418.7	1417.4	1416.0	1414.7	1413.2	1413.2
180°	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9



TEST NUMBER: P332572-830

CATALOG NUMBER: SA4XXDIP-C575D1205U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2
2.5°	913.7	909.6	906.7	904.4	897.9	894.1	891.2	887.0	882.3	877.3	871.2
5°	965.6	953.1	944.0	930.0	916.8	905.8	894.5	884.2	871.7	858.2	848.2
7.5°	1020.1	1001.5	977.8	957.2	934.0	913.8	895.8	877.3	858.1	839.4	822.4
10°	1054.7	1030.9	1004.5	973.3	944.0	917.9	893.7	870.2	847.5	824.7	805.3
12.5°	1091.9	1062.2	1023.2	986.7	953.9	919.1	889.9	861.1	833.7	809.8	787.1
15°	1142.0	1099.1	1054.0	1005.2	962.0	921.2	881.3	844.9	814.2	782.6	760.6
17.5°	1172.7	1119.6	1068.1	1017.1	964.7	913.3	870.2	828.4	789.8	758.5	730.8
20°	1193.0	1140.2	1076.0	1025.0	962.6	909.8	860.0	813.4	773.1	739.7	711.1
22.5°	1210.6	1149.5	1085.3	1018.2	956.2	900.1	845.6	798.7	757.5	722.4	694.9
25°	1220.1	1150.1	1080.3	1013.6	943.2	876.8	827.4	772.3	728.3	691.3	661.9
27.5°	1221.2	1146.2	1067.4	993.3	920.6	858.8	796.3	747.1	701.4	662.2	634.0
30°	1217.9	1139.8	1055.1	974.8	901.8	834.6	780.4	726.9	680.2	641.4	612.1
32.5°	1207.6	1126.2	1039.2	954.2	878.6	812.9	757.0	706.1	660.6	622.4	591.5
35°	1177.9	1097.6	1004.8	916.4	839.1	772.7	722.1	670.3	624.9	588.6	558.9
37.5°	1131.5	1058.9	964.6	873.1	797.1	730.5	680.2	633.6	592.6	555.6	525.2
40°	1091.0	1027.2	932.6	843.5	761.3	697.9	650.9	608.0	567.3	532.4	503.5
42.5°	1044.3	988.7	901.4	807.1	727.8	664.1	618.4	579.9	541.5	509.3	480.3
45°	961.2	924.5	842.4	755.1	672.6	612.5	568.8	535.1	502.8	471.3	447.0
47.5°	865.5	847.3	778.2	695.3	617.0	557.7	519.9	488.7	460.4	433.7	412.4
50°	801.3	792.5	732.7	652.8	578.0	522.3	484.1	457.3	433.1	409.6	389.5
52.5°	737.9	737.6	683.7	610.5	541.3	487.6	449.8	424.7	403.8	384.7	366.6
55°	641.0	651.3	609.2	543.8	481.9	433.5	399.4	377.0	362.3	346.6	333.0
57.5°	552.0	569.1	534.3	476.8	425.1	380.5	350.8	334.0	318.4	308.9	299.0
60°	494.0	510.1	483.0	434.6	385.8	347.6	319.4	304.3	290.8	284.2	277.2
62.5°	442.3	456.8	436.6	391.7	349.4	312.7	288.9	274.5	265.3	258.1	253.4
65°	368.5	380.7	363.4	330.8	294.5	265.1	245.7	234.3	225.6	222.6	217.4
67.5°	297.9	309.0	299.6	271.9	242.8	220.6	205.4	194.4	189.3	186.6	183.0
70°	256.0	267.0	257.0	232.9	210.5	191.8	177.5	171.3	165.8	164.7	159.6
72.5°	220.5	228.0	218.0	199.2	180.0	164.2	153.2	146.7	143.7	141.8	139.0
75°	165.4	172.0	165.4	150.7	137.1	126.1	116.6	114.0	110.7	109.6	107.8
77.5°	117.1	122.8	117.7	108.6	98.4	89.9	84.8	81.5	80.8	78.9	79.7
80°	89.4	93.1	88.4	82.2	74.1	68.2	64.6	62.7	60.5	59.8	61.3
82.5°	64.3	65.9	63.4	59.3	53.3	49.4	46.9	44.8	44.4	44.5	44.5
85°	33.4	33.0	32.6	28.9	27.1	24.6	23.1	22.7	22.3	23.1	23.8
87.5°	15.2	15.1	14.4	12.8	11.4	9.9	9.1	8.3	9.1	9.9	10.7
90°	20.2	18.3	16.3	13.9	11.3	8.7	5.9	3.3	5.9	8.7	11.3
92.5°	40.6	39.3	37.9	35.7	32.6	29.6	26.5	23.5	26.5	29.6	32.6
95°	79.8	78.1	76.4	74.5	72.3	70.1	67.9	65.7	67.9	70.1	72.3
97.5°	127.6	125.6	123.7	121.8	120.0	118.3	116.5	114.8	116.5	118.3	120.0
100°	163.2	161.0	158.8	157.2	156.2	155.2	154.3	153.4	154.3	155.2	156.2
102.5°	200.4	198.3	196.3	195.2	194.7	194.4	194.0	193.6	194.0	194.4	194.7
105°	258.6	257.7	256.7	256.1	255.9	255.6	255.4	255.1	255.4	255.6	255.9
107.5°	321.4	321.3	321.1	320.9	320.7	320.4	320.1	319.7	320.1	320.4	320.7
110°	365.1	365.4	365.6	365.5	365.0	364.5	364.0	363.5	364.0	364.5	365.0



TEST NUMBER: P332572-830

CATALOG NUMBER: SA4XXDIP-C575D1205U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	408.5	408.9	409.3	409.5	409.4	409.3	409.3	409.1	409.3	409.3	409.4
115°	476.3	476.7	477.2	477.4	477.4	477.4	477.4	477.4	477.4	477.4	477.4
117.5°	541.9	542.2	542.5	542.6	542.4	542.2	542.1	541.9	542.1	542.2	542.4
120°	587.3	588.1	588.8	588.6	587.7	586.7	585.7	584.8	585.7	586.7	587.7
122.5°	630.4	630.7	631.0	631.0	630.6	630.2	629.8	629.4	629.8	630.2	630.6
125°	694.7	695.0	695.2	695.3	695.3	695.3	695.3	695.3	695.3	695.3	695.3
127.5°	757.4	757.8	758.3	758.1	757.3	756.6	755.9	755.2	755.9	756.6	757.3
130°	800.5	800.5	800.5	800.1	799.4	798.6	798.0	797.2	798.0	798.6	799.4
132.5°	842.1	842.3	842.4	842.3	841.7	841.2	840.7	840.1	840.7	841.2	841.7
135°	903.4	903.4	903.4	902.7	901.3	899.8	898.3	896.8	898.3	899.8	901.3
137.5°	962.6	962.2	961.9	961.3	960.6	960.0	959.3	958.6	959.3	960.0	960.6
140°	1001.9	1001.9	1001.9	1001.7	1001.3	1000.8	1000.2	999.8	1000.2	1000.8	1001.3
142.5°	1039.2	1039.3	1039.5	1039.4	1038.9	1038.4	1037.9	1037.5	1037.9	1038.4	1038.9
145°	1094.6	1094.3	1094.1	1093.4	1092.5	1091.6	1090.5	1089.6	1090.5	1091.6	1092.5
147.5°	1146.0	1146.2	1146.4	1145.9	1144.7	1143.6	1142.5	1141.2	1142.5	1143.6	1144.7
150°	1177.1	1177.1	1177.1	1176.7	1175.7	1174.8	1173.7	1172.8	1173.7	1174.8	1175.7
152.5°	1205.7	1205.5	1205.3	1204.9	1204.3	1203.7	1203.2	1202.6	1203.2	1203.7	1204.3
155°	1247.7	1248.0	1248.2	1248.3	1248.3	1248.3	1248.3	1248.3	1248.3	1248.3	1248.3
157.5°	1284.8	1284.9	1284.9	1285.2	1285.6	1286.0	1286.5	1286.9	1286.5	1286.0	1285.6
160°	1308.0	1308.2	1308.4	1308.7	1308.9	1309.2	1309.5	1309.7	1309.5	1309.2	1308.9
162.5°	1327.3	1327.5	1327.8	1328.1	1328.8	1329.5	1330.0	1330.7	1330.0	1329.5	1328.8
165°	1354.4	1354.9	1355.4	1356.0	1356.8	1357.4	1358.2	1359.0	1358.2	1357.4	1356.8
167.5°	1376.1	1376.1	1376.0	1376.6	1377.5	1378.6	1379.6	1380.6	1379.6	1378.6	1377.5
170°	1388.0	1387.8	1387.5	1388.0	1389.2	1390.4	1391.7	1392.9	1391.7	1390.4	1389.2
172.5°	1397.2	1397.1	1397.0	1397.6	1398.5	1399.6	1400.6	1401.7	1400.6	1399.6	1398.5
175°	1407.6	1407.9	1408.1	1408.8	1410.0	1411.3	1412.5	1413.7	1412.5	1411.3	1410.0
177.5°	1413.2	1413.2	1413.2	1413.7	1414.8	1415.7	1416.6	1417.7	1416.6	1415.7	1414.8
180°	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9



TEST NUMBER: P332572-830

CATALOG NUMBER: SA4XXDIP-C575D1205U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2
2.5°	868.3	865.6	861.8	856.5	852.2	847.4	846.2	844.5	848.0	845.1	844.2
5°	839.8	832.1	822.2	810.9	804.3	794.7	792.9	789.2	785.5	785.1	781.5
7.5°	809.6	798.3	785.4	773.8	763.1	752.7	745.8	744.4	739.0	735.8	732.2
10°	790.3	776.4	761.3	750.4	737.8	726.9	719.2	714.7	711.1	707.0	703.4
12.5°	767.4	752.6	740.2	728.3	713.5	705.1	692.5	684.9	684.1	684.2	674.7
15°	740.7	726.1	707.0	690.2	682.1	666.0	659.0	650.2	644.7	639.2	634.8
17.5°	710.4	692.1	677.2	657.8	642.4	629.6	620.4	615.1	606.9	599.1	593.4
20°	691.3	671.8	656.1	635.6	618.7	602.9	595.2	587.9	581.6	575.0	568.8
22.5°	671.9	651.6	632.4	612.4	596.6	580.0	572.6	562.6	556.7	553.0	546.8
25°	641.4	619.4	597.4	578.3	562.2	547.5	537.6	529.9	523.3	520.4	516.3
27.5°	608.2	586.4	565.1	543.5	525.2	514.5	506.6	500.8	497.0	493.1	491.3
30°	587.1	564.4	541.7	521.5	504.6	494.0	486.6	482.6	479.7	477.9	476.0
32.5°	565.7	543.3	519.3	501.0	485.9	476.4	470.8	466.7	465.3	464.7	464.0
35°	531.4	508.7	486.6	470.1	455.8	452.1	447.4	445.2	444.5	447.0	448.2
37.5°	498.1	477.0	456.8	440.8	431.4	426.0	424.4	424.5	427.2	429.4	432.1
40°	476.7	456.2	437.2	423.2	414.4	411.1	410.4	412.2	415.1	417.7	420.7
42.5°	455.9	435.6	418.4	405.3	399.2	396.2	396.6	398.4	402.6	405.7	410.1
45°	423.6	406.7	389.8	379.2	374.1	374.8	374.8	378.1	382.1	386.9	391.6
47.5°	393.1	376.1	362.2	353.3	350.6	350.0	352.0	356.4	362.2	368.1	374.8
50°	372.6	356.5	344.3	336.3	333.4	334.4	337.4	341.4	348.4	355.7	362.7
52.5°	351.8	337.1	325.8	318.4	316.3	318.3	321.2	327.6	333.8	341.7	350.1
55°	319.4	307.0	298.1	292.7	291.9	293.0	296.3	303.3	312.1	322.0	330.1
57.5°	287.2	276.8	268.7	264.9	265.3	266.4	271.7	280.0	289.5	300.0	310.4
60°	265.5	256.0	249.4	246.5	246.9	249.0	255.6	263.3	275.0	285.3	296.3
62.5°	245.0	236.6	230.3	227.6	227.2	232.0	238.3	246.3	258.1	269.5	281.3
65°	212.0	205.4	200.2	198.8	199.8	203.5	211.6	222.3	232.1	244.2	256.7
67.5°	179.6	174.3	170.8	171.4	172.8	178.1	184.9	194.1	205.3	217.8	230.2
70°	159.2	154.0	151.1	151.5	153.6	160.2	166.2	175.3	187.4	200.2	210.5
72.5°	138.1	134.7	132.1	133.6	135.7	140.3	147.6	156.8	167.5	179.4	190.3
75°	105.9	105.9	104.5	105.7	109.0	113.3	118.9	128.4	139.0	148.5	157.3
77.5°	78.6	77.9	78.8	80.1	82.0	87.2	93.5	100.4	108.3	117.9	125.2
80°	60.1	60.5	62.3	64.6	65.3	69.3	75.9	82.2	88.4	96.4	103.4
82.5°	45.1	45.5	46.5	49.3	50.0	54.4	58.6	64.8	70.5	75.9	81.7
85°	24.6	24.6	26.4	27.5	29.3	32.2	34.9	38.5	43.6	47.3	52.8
87.5°	12.2	12.6	14.2	15.2	16.5	18.3	19.2	22.7	24.2	25.9	28.7
90°	13.9	16.3	18.3	20.2	22.1	24.1	25.5	27.1	28.5	30.0	30.9
92.5°	35.7	37.9	39.3	40.6	42.0	43.4	44.2	45.1	46.0	46.8	47.4
95°	74.5	76.4	78.1	79.8	81.5	83.2	84.0	84.6	85.4	86.1	86.5
97.5°	121.8	123.7	125.6	127.6	129.6	131.6	132.5	133.4	134.2	135.2	135.5
100°	157.2	158.8	161.0	163.2	165.3	167.6	168.1	168.5	169.0	169.5	169.8
102.5°	195.2	196.3	198.3	200.4	202.4	204.3	205.0	205.7	206.4	207.1	207.5
105°	256.1	256.7	257.7	258.6	259.7	260.6	261.4	262.1	262.8	263.5	264.3
107.5°	320.9	321.1	321.3	321.4	321.6	321.7	322.4	323.1	323.8	324.4	324.8
110°	365.5	365.6	365.4	365.1	364.9	364.7	364.2	363.6	363.2	362.7	362.8



TEST NUMBER: P332572-830

CATALOG NUMBER: SA4XXDIP-C575D1205U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	409.5	409.3	408.9	408.5	408.0	407.6	407.5	407.4	407.3	407.2	407.2
115°	477.4	477.2	476.7	476.3	475.7	475.2	475.0	474.8	474.5	474.3	474.0
117.5°	542.6	542.5	542.2	541.9	541.5	541.2	540.4	539.5	538.7	537.8	537.2
120°	588.6	588.8	588.1	587.3	586.5	585.9	584.7	583.4	582.2	581.0	580.6
122.5°	631.0	631.0	630.7	630.4	630.0	629.6	628.9	628.0	627.2	626.3	625.5
125°	695.3	695.2	695.0	694.7	694.5	694.3	693.8	693.2	692.8	692.3	691.8
127.5°	758.1	758.3	757.8	757.4	757.1	756.7	756.2	755.7	755.3	754.7	754.3
130°	800.1	800.5	800.5	800.5	800.5	800.5	800.0	799.5	799.0	798.5	797.8
132.5°	842.3	842.4	842.3	842.1	841.9	841.7	841.1	840.7	840.2	839.7	839.2
135°	902.7	903.4	903.4	903.4	903.4	903.4	903.0	902.5	901.9	901.4	900.9
137.5°	961.3	961.9	962.2	962.6	963.0	963.4	962.8	962.1	961.5	960.9	960.6
140°	1001.7	1001.9	1001.9	1001.9	1001.9	1001.9	1001.7	1001.5	1001.3	1001.0	1000.8
142.5°	1039.4	1039.5	1039.3	1039.2	1039.0	1038.8	1038.7	1038.7	1038.6	1038.6	1038.5
145°	1093.4	1094.1	1094.3	1094.6	1094.8	1095.0	1094.8	1094.6	1094.3	1094.1	1093.5
147.5°	1145.9	1146.4	1146.2	1146.0	1145.8	1145.7	1145.5	1145.3	1145.1	1144.8	1144.6
150°	1176.7	1177.1	1177.1	1177.1	1177.1	1177.1	1177.1	1177.1	1177.1	1177.1	1177.0
152.5°	1204.9	1205.3	1205.5	1205.7	1205.9	1206.1	1206.6	1207.2	1207.9	1208.4	1208.4
155°	1248.3	1248.2	1248.0	1247.7	1247.5	1247.3	1248.2	1249.2	1250.2	1251.1	1251.1
157.5°	1285.2	1284.9	1284.9	1284.8	1284.8	1284.7	1285.4	1286.2	1286.9	1287.6	1287.6
160°	1308.7	1308.4	1308.2	1308.0	1307.7	1307.5	1308.2	1308.9	1309.7	1310.4	1310.1
162.5°	1328.1	1327.8	1327.5	1327.3	1327.0	1326.7	1328.0	1329.4	1330.7	1332.0	1332.1
165°	1356.0	1355.4	1354.9	1354.4	1354.0	1353.5	1354.9	1356.4	1357.8	1359.3	1359.5
167.5°	1376.6	1376.0	1376.1	1376.1	1376.2	1376.2	1377.7	1379.1	1380.6	1382.1	1382.1
170°	1388.0	1387.5	1387.8	1388.0	1388.3	1388.6	1390.0	1391.5	1392.9	1394.4	1394.2
172.5°	1397.6	1397.0	1397.1	1397.2	1397.2	1397.3	1398.9	1400.6	1402.2	1403.9	1403.9
175°	1408.8	1408.1	1407.9	1407.6	1407.4	1407.1	1408.8	1410.5	1412.2	1413.9	1413.9
177.5°	1413.7	1413.2	1413.2	1413.2	1413.2	1413.2	1414.7	1416.0	1417.4	1418.7	1418.6
180°	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9



TEST NUMBER: P332572-830

CATALOG NUMBER: SA4XXDIP-C575D1205U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2
2.5°	843.6	843.0	840.9	840.7	840.9	843.0	843.6	844.2	845.1	848.0	844.5
5°	779.3	777.5	776.4	780.4	776.4	777.5	779.3	781.5	785.1	785.5	789.2
7.5°	730.8	729.3	726.1	725.1	726.1	729.3	730.8	732.2	735.8	739.0	744.4
10°	699.7	698.2	695.3	694.6	695.3	698.2	699.7	703.4	707.0	711.1	714.7
12.5°	669.8	666.8	666.3	667.0	666.3	666.8	669.8	674.7	684.2	684.1	684.9
15°	630.0	628.6	624.5	625.7	624.5	628.6	630.0	634.8	639.2	644.7	650.2
17.5°	590.9	589.1	584.2	588.5	584.2	589.1	590.9	593.4	599.1	606.9	615.1
20°	566.2	563.3	560.7	560.3	560.7	563.3	566.2	568.8	575.0	581.6	587.9
22.5°	542.7	540.1	539.9	537.4	539.9	540.1	542.7	546.8	553.0	556.7	562.6
25°	513.4	510.9	510.1	508.3	510.1	510.9	513.4	516.3	520.4	523.3	529.9
27.5°	490.9	489.7	488.3	488.9	488.3	489.7	490.9	491.3	493.1	497.0	500.8
30°	477.1	476.7	476.0	476.0	476.0	476.7	477.1	476.0	477.9	479.7	482.6
32.5°	465.7	465.6	466.0	466.0	466.0	465.6	465.7	464.0	464.7	465.3	466.7
35°	449.6	450.7	451.5	450.3	451.5	450.7	449.6	448.2	447.0	444.5	445.2
37.5°	435.1	436.2	437.2	438.5	437.2	436.2	435.1	432.1	429.4	427.2	424.5
40°	424.0	426.5	427.3	429.0	427.3	426.5	424.0	420.7	417.7	415.1	412.2
42.5°	413.4	416.2	418.1	418.5	418.1	416.2	413.4	410.1	405.7	402.6	398.4
45°	397.2	400.1	402.7	402.7	402.7	400.1	397.2	391.6	386.9	382.1	378.1
47.5°	380.4	384.7	387.2	387.9	387.2	384.7	380.4	374.8	368.1	362.2	356.4
50°	368.9	374.1	376.6	378.4	376.6	374.1	368.9	362.7	355.7	348.4	341.4
52.5°	357.8	362.9	366.4	367.3	366.4	362.9	357.8	350.1	341.7	333.8	327.6
55°	338.5	345.8	349.9	351.3	349.9	345.8	338.5	330.1	322.0	312.1	303.3
57.5°	320.3	327.1	331.8	332.8	331.8	327.1	320.3	310.4	300.0	289.5	280.0
60°	306.2	313.6	319.4	320.6	319.4	313.6	306.2	296.3	285.3	275.0	263.3
62.5°	291.8	299.4	304.7	307.6	304.7	299.4	291.8	281.3	269.5	258.1	246.3
65°	267.0	274.7	279.8	280.9	279.8	274.7	267.0	256.7	244.2	232.1	222.3
67.5°	239.9	247.5	250.9	253.1	250.9	247.5	239.9	230.2	217.8	205.3	194.1
70°	220.7	227.0	230.6	232.5	230.6	227.0	220.7	210.5	200.2	187.4	175.3
72.5°	199.1	205.6	209.8	210.2	209.8	205.6	199.1	190.3	179.4	167.5	156.8
75°	165.8	171.6	173.8	173.8	173.8	171.6	165.8	157.3	148.5	139.0	128.4
77.5°	131.2	134.2	137.0	137.6	137.0	134.2	131.2	125.2	117.9	108.3	100.4
80°	109.0	110.7	112.9	112.9	112.9	110.7	109.0	103.4	96.4	88.4	82.2
82.5°	86.1	87.6	89.7	89.4	89.7	87.6	86.1	81.7	75.9	70.5	64.8
85°	52.0	55.4	55.0	54.3	55.0	55.4	52.0	52.8	47.3	43.6	38.5
87.5°	29.8	30.2	31.1	31.8	31.1	30.2	29.8	28.7	25.9	24.2	22.7
90°	31.4	31.9	32.3	32.9	32.3	31.9	31.4	30.9	30.0	28.5	27.1
92.5°	47.8	48.1	48.4	48.6	48.4	48.1	47.8	47.4	46.8	46.0	45.1
95°	86.5	86.5	86.5	86.5	86.5	86.5	86.5	86.5	86.1	85.4	84.6
97.5°	135.5	135.5	135.5	135.5	135.5	135.5	135.5	135.5	135.2	134.2	133.4
100°	169.8	169.8	169.8	169.8	169.8	169.8	169.8	169.8	169.5	169.0	168.5
102.5°	207.7	207.9	208.1	208.3	208.1	207.9	207.7	207.5	207.1	206.4	205.7
105°	265.0	265.7	266.5	267.2	266.5	265.7	265.0	264.3	263.5	262.8	262.1
107.5°	324.7	324.7	324.6	324.6	324.6	324.7	324.7	324.8	324.4	323.8	323.1
110°	363.5	364.3	365.0	365.7	365.0	364.3	363.5	362.8	362.7	363.2	363.6



TEST NUMBER: P332572-830

CATALOG NUMBER: SA4XXDIP-C575D1205U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	407.4	407.5	407.6	407.8	407.6	407.5	407.4	407.2	407.2	407.3	407.4
115°	473.8	473.5	473.3	473.1	473.3	473.5	473.8	474.0	474.3	474.5	474.8
117.5°	536.7	536.2	535.7	535.3	535.7	536.2	536.7	537.2	537.8	538.7	539.5
120°	581.1	581.5	582.1	582.6	582.1	581.5	581.1	580.6	581.0	582.2	583.4
122.5°	624.6	623.8	622.8	622.0	622.8	623.8	624.6	625.5	626.3	627.2	628.0
125°	691.4	690.9	690.3	689.8	690.3	690.9	691.4	691.8	692.3	692.8	693.2
127.5°	753.9	753.5	753.1	752.7	753.1	753.5	753.9	754.3	754.7	755.3	755.7
130°	796.8	795.9	794.8	793.9	794.8	795.9	796.8	797.8	798.5	799.0	799.5
132.5°	838.9	838.5	838.1	837.7	838.1	838.5	838.9	839.2	839.7	840.2	840.7
135°	900.1	899.4	898.6	898.0	898.6	899.4	900.1	900.9	901.4	901.9	902.5
137.5°	960.8	960.9	961.1	961.2	961.1	960.9	960.8	960.6	960.9	961.5	962.1
140°	1000.5	1000.2	1000.0	999.8	1000.0	1000.2	1000.5	1000.8	1001.0	1001.3	1001.5
142.5°	1038.5	1038.4	1038.4	1038.3	1038.4	1038.4	1038.5	1038.5	1038.6	1038.6	1038.7
145°	1092.9	1092.1	1091.4	1090.7	1091.4	1092.1	1092.9	1093.5	1094.1	1094.3	1094.6
147.5°	1144.4	1144.2	1143.9	1143.7	1143.9	1144.2	1144.4	1144.6	1144.8	1145.1	1145.3
150°	1176.8	1176.6	1176.3	1176.1	1176.3	1176.6	1176.8	1177.0	1177.1	1177.1	1177.1
152.5°	1207.8	1207.1	1206.5	1205.9	1206.5	1207.1	1207.8	1208.4	1208.4	1207.9	1207.2
155°	1250.2	1249.2	1248.2	1247.3	1248.2	1249.2	1250.2	1251.1	1251.1	1250.2	1249.2
157.5°	1286.8	1285.9	1285.1	1284.3	1285.1	1285.9	1286.8	1287.6	1287.6	1286.9	1286.2
160°	1308.9	1307.7	1306.6	1305.3	1306.6	1307.7	1308.9	1310.1	1310.4	1309.7	1308.9
162.5°	1330.9	1329.6	1328.4	1327.2	1328.4	1329.6	1330.9	1332.1	1332.0	1330.7	1329.4
165°	1358.6	1357.6	1356.6	1355.7	1356.6	1357.6	1358.6	1359.5	1359.3	1357.8	1356.4
167.5°	1380.5	1379.0	1377.5	1376.0	1377.5	1379.0	1380.5	1382.1	1382.1	1380.6	1379.1
170°	1392.5	1390.8	1389.1	1387.4	1389.1	1390.8	1392.5	1394.2	1394.4	1392.9	1391.5
172.5°	1402.1	1400.4	1398.7	1397.0	1398.7	1400.4	1402.1	1403.9	1403.9	1402.2	1400.6
175°	1412.2	1410.5	1408.8	1407.1	1408.8	1410.5	1412.2	1413.9	1413.9	1412.2	1410.5
177.5°	1417.0	1415.5	1413.9	1412.4	1413.9	1415.5	1417.0	1418.6	1418.7	1417.4	1416.0
180°	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9



TEST NUMBER: P332572-830

CATALOG NUMBER: SA4XXDIP-C575D1205U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2
2.5°	846.2	847.4	852.2	856.5	861.8	865.6	868.3	871.2	877.3	882.3	887.0
5°	792.9	794.7	804.3	810.9	822.2	832.1	839.8	848.2	858.2	871.7	884.2
7.5°	745.8	752.7	763.1	773.8	785.4	798.3	809.6	822.4	839.4	858.1	877.3
10°	719.2	726.9	737.8	750.4	761.3	776.4	790.3	805.3	824.7	847.5	870.2
12.5°	692.5	705.1	713.5	728.3	740.2	752.6	767.4	787.1	809.8	833.7	861.1
15°	659.0	666.0	682.1	690.2	707.0	726.1	740.7	760.6	782.6	814.2	844.9
17.5°	620.4	629.6	642.4	657.8	677.2	692.1	710.4	730.8	758.5	789.8	828.4
20°	595.2	602.9	618.7	635.6	656.1	671.8	691.3	711.1	739.7	773.1	813.4
22.5°	572.6	580.0	596.6	612.4	632.4	651.6	671.9	694.9	722.4	757.5	798.7
25°	537.6	547.5	562.2	578.3	597.4	619.4	641.4	661.9	691.3	728.3	772.3
27.5°	506.6	514.5	525.2	543.5	565.1	586.4	608.2	634.0	662.2	701.4	747.1
30°	486.6	494.0	504.6	521.5	541.7	564.4	587.1	612.1	641.4	680.2	726.9
32.5°	470.8	476.4	485.9	501.0	519.3	543.3	565.7	591.5	622.4	660.6	706.1
35°	447.4	452.1	455.8	470.1	486.6	508.7	531.4	558.9	588.6	624.9	670.3
37.5°	424.4	426.0	431.4	440.8	456.8	477.0	498.1	525.2	555.6	592.6	633.6
40°	410.4	411.1	414.4	423.2	437.2	456.2	476.7	503.5	532.4	567.3	608.0
42.5°	396.6	396.2	399.2	405.3	418.4	435.6	455.9	480.3	509.3	541.5	579.9
45°	374.8	374.8	374.1	379.2	389.8	406.7	423.6	447.0	471.3	502.8	535.1
47.5°	352.0	350.0	350.6	353.3	362.2	376.1	393.1	412.4	433.7	460.4	488.7
50°	337.4	334.4	333.4	336.3	344.3	356.5	372.6	389.5	409.6	433.1	457.3
52.5°	321.2	318.3	316.3	318.4	325.8	337.1	351.8	366.6	384.7	403.8	424.7
55°	296.3	293.0	291.9	292.7	298.1	307.0	319.4	333.0	346.6	362.3	377.0
57.5°	271.7	266.4	265.3	264.9	268.7	276.8	287.2	299.0	308.9	318.4	334.0
60°	255.6	249.0	246.9	246.5	249.4	256.0	265.5	277.2	284.2	290.8	304.3
62.5°	238.3	232.0	227.2	227.6	230.3	236.6	245.0	253.4	258.1	265.3	274.5
65°	211.6	203.5	199.8	198.8	200.2	205.4	212.0	217.4	222.6	225.6	234.3
67.5°	184.9	178.1	172.8	171.4	170.8	174.3	179.6	183.0	186.6	189.3	194.4
70°	166.2	160.2	153.6	151.5	151.1	154.0	159.2	159.6	164.7	165.8	171.3
72.5°	147.6	140.3	135.7	133.6	132.1	134.7	138.1	139.0	141.8	143.7	146.7
75°	118.9	113.3	109.0	105.7	104.5	105.9	105.9	107.8	109.6	110.7	114.0
77.5°	93.5	87.2	82.0	80.1	78.8	77.9	78.6	79.7	78.9	80.8	81.5
80°	75.9	69.3	65.3	64.6	62.3	60.5	60.1	61.3	59.8	60.5	62.7
82.5°	58.6	54.4	50.0	49.3	46.5	45.5	45.1	44.5	44.5	44.4	44.8
85°	34.9	32.2	29.3	27.5	26.4	24.6	24.6	23.8	23.1	22.3	22.7
87.5°	19.2	18.3	16.5	15.2	14.2	12.6	12.2	10.7	9.9	9.1	8.3
90°	25.5	24.1	22.1	20.2	18.3	16.3	13.9	11.3	8.7	5.9	3.3
92.5°	44.2	43.4	42.0	40.6	39.3	37.9	35.7	32.6	29.6	26.5	23.5
95°	84.0	83.2	81.5	79.8	78.1	76.4	74.5	72.3	70.1	67.9	65.7
97.5°	132.5	131.6	129.6	127.6	125.6	123.7	121.8	120.0	118.3	116.5	114.8
100°	168.1	167.6	165.3	163.2	161.0	158.8	157.2	156.2	155.2	154.3	153.4
102.5°	205.0	204.3	202.4	200.4	198.3	196.3	195.2	194.7	194.4	194.0	193.6
105°	261.4	260.6	259.7	258.6	257.7	256.7	256.1	255.9	255.6	255.4	255.1
107.5°	322.4	321.7	321.6	321.4	321.3	321.1	320.9	320.7	320.4	320.1	319.7
110°	364.2	364.7	364.9	365.1	365.4	365.6	365.5	365.0	364.5	364.0	363.5



TEST NUMBER: P332572-830
 CATALOG NUMBER: SA4XXDIP-C575D1205U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	407.5	407.6	408.0	408.5	408.9	409.3	409.5	409.4	409.3	409.3	409.1
115°	475.0	475.2	475.7	476.3	476.7	477.2	477.4	477.4	477.4	477.4	477.4
117.5°	540.4	541.2	541.5	541.9	542.2	542.5	542.6	542.4	542.2	542.1	541.9
120°	584.7	585.9	586.5	587.3	588.1	588.8	588.6	587.7	586.7	585.7	584.8
122.5°	628.9	629.6	630.0	630.4	630.7	631.0	631.0	630.6	630.2	629.8	629.4
125°	693.8	694.3	694.5	694.7	695.0	695.2	695.3	695.3	695.3	695.3	695.3
127.5°	756.2	756.7	757.1	757.4	757.8	758.3	758.1	757.3	756.6	755.9	755.2
130°	800.0	800.5	800.5	800.5	800.5	800.5	800.1	799.4	798.6	798.0	797.2
132.5°	841.1	841.7	841.9	842.1	842.3	842.4	842.3	841.7	841.2	840.7	840.1
135°	903.0	903.4	903.4	903.4	903.4	903.4	902.7	901.3	899.8	898.3	896.8
137.5°	962.8	963.4	963.0	962.6	962.2	961.9	961.3	960.6	960.0	959.3	958.6
140°	1001.7	1001.9	1001.9	1001.9	1001.9	1001.9	1001.7	1001.3	1000.8	1000.2	999.8
142.5°	1038.7	1038.8	1039.0	1039.2	1039.3	1039.5	1039.4	1038.9	1038.4	1037.9	1037.5
145°	1094.8	1095.0	1094.8	1094.6	1094.3	1094.1	1093.4	1092.5	1091.6	1090.5	1089.6
147.5°	1145.5	1145.7	1145.8	1146.0	1146.2	1146.4	1145.9	1144.7	1143.6	1142.5	1141.2
150°	1177.1	1177.1	1177.1	1177.1	1177.1	1177.1	1176.7	1175.7	1174.8	1173.7	1172.8
152.5°	1206.6	1206.1	1205.9	1205.7	1205.5	1205.3	1204.9	1204.3	1203.7	1203.2	1202.6
155°	1248.2	1247.3	1247.5	1247.7	1248.0	1248.2	1248.3	1248.3	1248.3	1248.3	1248.3
157.5°	1285.4	1284.7	1284.8	1284.8	1284.9	1284.9	1285.2	1285.6	1286.0	1286.5	1286.9
160°	1308.2	1307.5	1307.7	1308.0	1308.2	1308.4	1308.7	1308.9	1309.2	1309.5	1309.7
162.5°	1328.0	1326.7	1327.0	1327.3	1327.5	1327.8	1328.1	1328.8	1329.5	1330.0	1330.7
165°	1354.9	1353.5	1354.0	1354.4	1354.9	1355.4	1356.0	1356.8	1357.4	1358.2	1359.0
167.5°	1377.7	1376.2	1376.2	1376.1	1376.1	1376.0	1376.6	1377.5	1378.6	1379.6	1380.6
170°	1390.0	1388.6	1388.3	1388.0	1387.8	1387.5	1388.0	1389.2	1390.4	1391.7	1392.9
172.5°	1398.9	1397.3	1397.2	1397.2	1397.1	1397.0	1397.6	1398.5	1399.6	1400.6	1401.7
175°	1408.8	1407.1	1407.4	1407.6	1407.9	1408.1	1408.8	1410.0	1411.3	1412.5	1413.7
177.5°	1414.7	1413.2	1413.2	1413.2	1413.2	1413.2	1413.7	1414.8	1415.7	1416.6	1417.7
180°	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9



TEST NUMBER: P332572-830

CATALOG NUMBER: SA4XXDIP-C575D1205U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2	885.2
2.5°	891.2	894.1	897.9	904.4	906.7	909.6	913.7	913.4	914.6	919.0	928.4
5°	894.5	905.8	916.8	930.0	944.0	953.1	965.6	973.3	981.0	990.9	1007.8
7.5°	895.8	913.8	934.0	957.2	977.8	1001.5	1020.1	1037.6	1053.3	1074.2	1094.3
10°	893.7	917.9	944.0	973.3	1004.5	1030.9	1054.7	1081.9	1104.9	1130.2	1153.0
12.5°	889.9	919.1	953.9	986.7	1023.2	1062.2	1091.9	1119.4	1150.1	1179.2	1214.3
15°	881.3	921.2	962.0	1005.2	1054.0	1099.1	1142.0	1177.5	1210.6	1254.2	1300.0
17.5°	870.2	913.3	964.7	1017.1	1068.1	1119.6	1172.7	1226.2	1267.8	1322.0	1357.9
20°	860.0	909.8	962.6	1025.0	1076.0	1140.2	1193.0	1244.6	1301.8	1355.8	1398.7
22.5°	845.6	900.1	956.2	1018.2	1085.3	1149.5	1210.6	1266.7	1323.9	1382.5	1434.5
25°	827.4	876.8	943.2	1013.6	1080.3	1150.1	1220.1	1290.5	1352.1	1414.1	1462.5
27.5°	796.3	858.8	920.6	993.3	1067.4	1146.2	1221.2	1294.9	1359.3	1410.3	1440.4
30°	780.4	834.6	901.8	974.8	1055.1	1139.8	1217.9	1290.2	1350.3	1391.0	1403.1
32.5°	757.0	812.9	878.6	954.2	1039.2	1126.2	1207.6	1275.7	1326.0	1347.3	1332.7
35°	722.1	772.7	839.1	916.4	1004.8	1097.6	1177.9	1235.5	1261.2	1241.0	1190.7
37.5°	680.2	730.5	797.1	873.1	964.6	1058.9	1131.5	1172.9	1164.4	1114.3	1039.3
40°	650.9	697.9	761.3	843.5	932.6	1027.2	1091.0	1113.4	1090.0	1018.0	938.5
42.5°	618.4	664.1	727.8	807.1	901.4	988.7	1044.3	1046.2	1006.9	921.0	841.0
45°	568.8	612.5	672.6	755.1	842.4	924.5	961.2	943.2	870.6	787.7	707.4
47.5°	519.9	557.7	617.0	695.3	778.2	847.3	865.5	833.2	755.8	675.3	600.9
50°	484.1	522.3	578.0	652.8	732.7	792.5	801.3	758.4	682.5	601.4	543.1
52.5°	449.8	487.6	541.3	610.5	683.7	737.6	737.9	688.2	612.7	540.5	486.2
55°	399.4	433.5	481.9	543.8	609.2	651.3	641.0	589.7	524.1	461.4	414.1
57.5°	350.8	380.5	425.1	476.8	534.3	569.1	552.0	502.7	444.0	390.9	355.0
60°	319.4	347.6	385.8	434.6	483.0	510.1	494.0	449.2	395.3	352.4	321.2
62.5°	288.9	312.7	349.4	391.7	436.6	456.8	442.3	398.2	351.7	312.8	287.5
65°	245.7	265.1	294.5	330.8	363.4	380.7	368.5	327.4	291.9	264.0	243.8
67.5°	205.4	220.6	242.8	271.9	299.6	309.0	297.9	269.3	239.2	216.9	202.6
70°	177.5	191.8	210.5	232.9	257.0	267.0	256.0	233.3	208.7	188.1	174.2
72.5°	153.2	164.2	180.0	199.2	218.0	228.0	220.5	198.6	177.9	162.6	150.7
75°	116.6	126.1	137.1	150.7	165.4	172.0	165.4	150.3	136.0	124.7	116.2
77.5°	84.8	89.9	98.4	108.6	117.7	122.8	117.1	106.9	98.1	90.4	86.1
80°	64.6	68.2	74.1	82.2	88.4	93.1	89.4	81.1	74.1	68.9	67.1
82.5°	46.9	49.4	53.3	59.3	63.4	65.9	64.3	58.2	55.3	50.7	48.9
85°	23.1	24.6	27.1	28.9	32.6	33.0	33.4	30.8	28.3	27.1	25.6
87.5°	9.1	9.9	11.4	12.8	14.4	15.1	15.2	15.6	14.8	14.8	13.9
90°	5.9	8.7	11.3	13.9	16.3	18.3	20.2	22.1	24.1	25.5	27.1
92.5°	26.5	29.6	32.6	35.7	37.9	39.3	40.6	42.0	43.4	44.2	45.1
95°	67.9	70.1	72.3	74.5	76.4	78.1	79.8	81.5	83.2	84.0	84.6
97.5°	116.5	118.3	120.0	121.8	123.7	125.6	127.6	129.6	131.6	132.5	133.4
100°	154.3	155.2	156.2	157.2	158.8	161.0	163.2	165.3	167.6	168.1	168.5
102.5°	194.0	194.4	194.7	195.2	196.3	198.3	200.4	202.4	204.3	205.0	205.7
105°	255.4	255.6	255.9	256.1	256.7	257.7	258.6	259.7	260.6	261.4	262.1
107.5°	320.1	320.4	320.7	320.9	321.1	321.3	321.4	321.6	321.7	322.4	323.1
110°	364.0	364.5	365.0	365.5	365.6	365.4	365.1	364.9	364.7	364.2	363.6



TEST NUMBER: P332572-830

CATALOG NUMBER: SA4XXDIP-C575D1205U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	409.3	409.3	409.4	409.5	409.3	408.9	408.5	408.0	407.6	407.5	407.4
115°	477.4	477.4	477.4	477.4	477.2	476.7	476.3	475.7	475.2	475.0	474.8
117.5°	542.1	542.2	542.4	542.6	542.5	542.2	541.9	541.5	541.2	540.4	539.5
120°	585.7	586.7	587.7	588.6	588.8	588.1	587.3	586.5	585.9	584.7	583.4
122.5°	629.8	630.2	630.6	631.0	631.0	630.7	630.4	630.0	629.6	628.9	628.0
125°	695.3	695.3	695.3	695.3	695.2	695.0	694.7	694.5	694.3	693.8	693.2
127.5°	755.9	756.6	757.3	758.1	758.3	757.8	757.4	757.1	756.7	756.2	755.7
130°	798.0	798.6	799.4	800.1	800.5	800.5	800.5	800.5	800.5	800.0	799.5
132.5°	840.7	841.2	841.7	842.3	842.4	842.3	842.1	841.9	841.7	841.1	840.7
135°	898.3	899.8	901.3	902.7	903.4	903.4	903.4	903.4	903.4	903.0	902.5
137.5°	959.3	960.0	960.6	961.3	961.9	962.2	962.6	963.0	963.4	962.8	962.1
140°	1000.2	1000.8	1001.3	1001.7	1001.9	1001.9	1001.9	1001.9	1001.9	1001.7	1001.5
142.5°	1037.9	1038.4	1038.9	1039.4	1039.5	1039.3	1039.2	1039.0	1038.8	1038.7	1038.7
145°	1090.5	1091.6	1092.5	1093.4	1094.1	1094.3	1094.6	1094.8	1095.0	1094.8	1094.6
147.5°	1142.5	1143.6	1144.7	1145.9	1146.4	1146.2	1146.0	1145.8	1145.7	1145.5	1145.3
150°	1173.7	1174.8	1175.7	1176.7	1177.1	1177.1	1177.1	1177.1	1177.1	1177.1	1177.1
152.5°	1203.2	1203.7	1204.3	1204.9	1205.3	1205.5	1205.7	1205.9	1206.1	1206.6	1207.2
155°	1248.3	1248.3	1248.3	1248.3	1248.2	1248.0	1247.7	1247.5	1247.3	1248.2	1249.2
157.5°	1286.5	1286.0	1285.6	1285.2	1284.9	1284.9	1284.8	1284.8	1284.7	1285.4	1286.2
160°	1309.5	1309.2	1308.9	1308.7	1308.4	1308.2	1308.0	1307.7	1307.5	1308.2	1308.9
162.5°	1330.0	1329.5	1328.8	1328.1	1327.8	1327.5	1327.3	1327.0	1326.7	1328.0	1329.4
165°	1358.2	1357.4	1356.8	1356.0	1355.4	1354.9	1354.4	1354.0	1353.5	1354.9	1356.4
167.5°	1379.6	1378.6	1377.5	1376.6	1376.0	1376.1	1376.1	1376.2	1376.2	1377.7	1379.1
170°	1391.7	1390.4	1389.2	1388.0	1387.5	1387.8	1388.0	1388.3	1388.6	1390.0	1391.5
172.5°	1400.6	1399.6	1398.5	1397.6	1397.0	1397.1	1397.2	1397.2	1397.3	1398.9	1400.6
175°	1412.5	1411.3	1410.0	1408.8	1408.1	1407.9	1407.6	1407.4	1407.1	1408.8	1410.5
177.5°	1416.6	1415.7	1414.8	1413.7	1413.2	1413.2	1413.2	1413.2	1413.2	1414.7	1416.0
180°	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9



TEST NUMBER: P332572-830

CATALOG NUMBER: SA4XXDIP-C575D1205U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	885.2	885.2	885.2	885.2	885.2	885.2	885.2
2.5°	933.1	933.7	936.3	938.4	939.0	941.9	942.2
5°	1015.1	1021.3	1033.4	1034.5	1036.3	1045.9	1038.6
7.5°	1111.2	1127.0	1137.6	1146.9	1150.3	1154.4	1153.6
10°	1172.8	1196.3	1208.0	1226.7	1227.5	1232.2	1229.3
12.5°	1234.7	1262.0	1283.4	1286.9	1302.5	1305.0	1309.1
15°	1322.4	1351.4	1381.1	1391.8	1413.3	1418.5	1426.5
17.5°	1404.9	1434.5	1455.3	1482.8	1491.7	1503.5	1495.5
20°	1450.0	1482.3	1508.7	1530.3	1539.5	1546.1	1545.4
22.5°	1477.3	1509.9	1531.3	1547.7	1556.2	1559.1	1558.9
25°	1494.4	1513.2	1519.8	1526.0	1516.5	1513.2	1514.6
27.5°	1446.9	1442.0	1424.8	1402.2	1378.8	1360.1	1350.0
30°	1381.5	1352.8	1326.8	1281.4	1257.8	1244.0	1231.4
32.5°	1288.7	1243.4	1193.4	1151.7	1124.9	1104.3	1101.2
35°	1129.9	1061.7	1000.4	949.4	923.0	900.7	895.5
37.5°	960.6	889.8	834.6	789.7	761.3	745.6	730.8
40°	848.2	787.4	733.1	694.9	673.4	661.9	652.8
42.5°	761.7	706.1	652.1	623.0	603.5	596.5	591.2
45°	642.2	590.4	553.0	531.0	519.6	507.9	502.4
47.5°	546.4	504.4	479.7	461.0	448.8	441.9	438.3
50°	492.1	457.7	435.6	421.4	410.4	404.8	401.9
52.5°	444.0	415.8	397.3	385.9	378.4	374.4	373.2
55°	382.5	360.9	349.1	339.2	333.8	330.1	328.6
57.5°	332.4	315.8	306.3	298.1	296.1	292.9	291.9
60°	299.6	286.8	278.7	273.2	271.4	267.7	268.4
62.5°	270.6	260.0	253.2	250.1	247.6	244.5	245.5
65°	228.8	221.1	217.4	214.5	211.6	209.8	211.2
67.5°	192.0	186.7	181.7	180.0	178.6	178.3	176.7
70°	168.0	163.5	159.2	158.1	158.1	156.6	156.2
72.5°	144.8	141.6	138.6	137.8	136.7	137.2	135.7
75°	111.9	109.2	108.2	107.1	106.7	106.7	105.7
77.5°	82.7	80.8	79.0	79.0	77.7	77.2	77.0
80°	62.7	62.0	60.5	60.5	59.8	60.1	59.4
82.5°	47.1	46.1	45.8	45.2	44.2	44.3	43.5
85°	25.3	24.2	23.8	22.7	22.0	22.7	22.0
87.5°	14.5	14.5	14.4	13.9	13.7	13.8	13.0
90°	28.5	30.0	30.9	31.4	31.9	32.3	32.9
92.5°	46.0	46.8	47.4	47.8	48.1	48.4	48.6
95°	85.4	86.1	86.5	86.5	86.5	86.5	86.5
97.5°	134.2	135.2	135.5	135.5	135.5	135.5	135.5
100°	169.0	169.5	169.8	169.8	169.8	169.8	169.8
102.5°	206.4	207.1	207.5	207.7	207.9	208.1	208.3
105°	262.8	263.5	264.3	265.0	265.7	266.5	267.2
107.5°	323.8	324.4	324.8	324.7	324.7	324.6	324.6
110°	363.2	362.7	362.8	363.5	364.3	365.0	365.7



TEST NUMBER: P332572-830

CATALOG NUMBER: SA4XXDIP-C575D1205U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	407.3	407.2	407.2	407.4	407.5	407.6	407.8
115°	474.5	474.3	474.0	473.8	473.5	473.3	473.1
117.5°	538.7	537.8	537.2	536.7	536.2	535.7	535.3
120°	582.2	581.0	580.6	581.1	581.5	582.1	582.6
122.5°	627.2	626.3	625.5	624.6	623.8	622.8	622.0
125°	692.8	692.3	691.8	691.4	690.9	690.3	689.8
127.5°	755.3	754.7	754.3	753.9	753.5	753.1	752.7
130°	799.0	798.5	797.8	796.8	795.9	794.8	793.9
132.5°	840.2	839.7	839.2	838.9	838.5	838.1	837.7
135°	901.9	901.4	900.9	900.1	899.4	898.6	898.0
137.5°	961.5	960.9	960.6	960.8	960.9	961.1	961.2
140°	1001.3	1001.0	1000.8	1000.5	1000.2	1000.0	999.8
142.5°	1038.6	1038.6	1038.5	1038.5	1038.4	1038.4	1038.3
145°	1094.3	1094.1	1093.5	1092.9	1092.1	1091.4	1090.7
147.5°	1145.1	1144.8	1144.6	1144.4	1144.2	1143.9	1143.7
150°	1177.1	1177.1	1177.0	1176.8	1176.6	1176.3	1176.1
152.5°	1207.9	1208.4	1208.4	1207.8	1207.1	1206.5	1205.9
155°	1250.2	1251.1	1251.1	1250.2	1249.2	1248.2	1247.3
157.5°	1286.9	1287.6	1287.6	1286.8	1285.9	1285.1	1284.3
160°	1309.7	1310.4	1310.1	1308.9	1307.7	1306.6	1305.3
162.5°	1330.7	1332.0	1332.1	1330.9	1329.6	1328.4	1327.2
165°	1357.8	1359.3	1359.5	1358.6	1357.6	1356.6	1355.7
167.5°	1380.6	1382.1	1382.1	1380.5	1379.0	1377.5	1376.0
170°	1392.9	1394.4	1394.2	1392.5	1390.8	1389.1	1387.4
172.5°	1402.2	1403.9	1403.9	1402.1	1400.4	1398.7	1397.0
175°	1412.2	1413.9	1413.9	1412.2	1410.5	1408.8	1407.1
177.5°	1417.4	1418.7	1418.6	1417.0	1415.5	1413.9	1412.4
180°	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9	1415.9

(END OF REPORT)