

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332975-930

Luminaire Tested: **SA4XXRDIP-C1020D1035U930-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332975-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C1020D1035U930-4F0-1E-UDD-A4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6551.4 lumens
Efficiency: N/A
Efficacy: 108.3 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 60.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332975-930
CATALOG NUMBER: SA4XXRDIP-C1020D1035U930-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332975-930

CATALOG NUMBER: SA4XXRDIP-C1020D1035U930-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60	54
1	99	95	91	88	92	88	85	82	76	73	71	64	63	61	54	53	52	47
2	91	84	78	73	84	78	73	68	67	63	60	57	54	52	48	46	44	40
3	83	74	67	61	77	69	63	58	60	55	51	51	47	44	43	40	38	34
4	76	66	58	52	70	61	55	49	53	48	44	46	42	38	39	36	33	30
5	70	59	51	45	65	55	48	43	48	42	38	41	37	34	35	32	29	26
6	65	53	45	39	60	50	42	37	43	38	33	37	33	30	32	28	26	23
7	60	48	40	35	56	45	38	33	39	34	30	34	30	26	29	26	23	21
8	56	44	36	31	52	41	34	29	36	30	26	31	27	24	27	23	21	19
9	52	40	32	27	48	37	31	26	33	28	24	29	24	21	25	21	19	17
10	49	37	29	25	45	34	28	24	30	25	21	27	22	19	23	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	11293	11293	11293	11293
5°	13100	11327	10011	11327
10°	15497	11278	8936	11278
15°	17901	11173	7678	11173
20°	19930	11030	6943	11030
25°	20574	10889	6446	10889
30°	18011	10718	6147	10718
35°	14020	10464	5966	10464
40°	10513	10175	5868	10175
45°	8301	9710	5817	9710
50°	7008	9173	5649	9173
55°	6108	8583	5346	8583
60°	5496	7971	4732	7971
65°	4844	7310	4069	7310
70°	4362	6626	3673	6626
75°	3656	5873	3132	5873
80°	3092	5002	2934	5002
85°	2612	3909	2612	3909



TEST NUMBER: P332975-930

CATALOG NUMBER: SA4XXRDIP-C1020D1035U930-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	135.5	2.1
10°-20°	408.9	6.2
20°-30°	639.5	9.8
30°-40°	710.9	10.9
40°-50°	630.7	9.6
50°-60°	491.5	7.5
60°-70°	321.8	4.9
70°-80°	158.2	2.4
80°-90°	41.3	0.6
90°-100°	299.2	4.6
100°-110°	622.8	9.5
110°-120°	557.8	8.5
120°-130°	469.2	7.2
130°-140°	391.2	6.0
140°-150°	298.9	4.6
150°-160°	210.1	3.2
160°-170°	123.6	1.9
170°-180°	40.2	0.6
0°-30°	1183.9	18.1
0°-40°	1894.8	28.9
0°-60°	3017.0	46.1
0°-90°	3538.4	54.0
90°-120°	1479.8	22.6
90°-150°	2639.2	40.3
90°-180°	3013.0	46.0
0°-180°	6551.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1399	1399	1399	1399	1399	
5°	1616	1398	1235	1398	1616	164
15°	2142	1337	919	1337	2142	609
25°	2310	1222	724	1222	2310	1025
35°	1423	1062	605	1062	1423	892
45°	727	850	510	850	727	576
55°	434	610	380	610	434	395
65°	254	383	213	383	254	255
75°	117	188	100	188	117	129
85°	28	42	28	42	28	32
90°	17	1	17	1	17	15
95°	199	27	199	27	199	308
105°	1145	95	1145	95	1145	1132
115°	1100	168	1100	168	1100	1092
125°	877	234	877	234	877	797
135°	785	278	785	278	785	606
145°	641	320	641	320	641	406
155°	536	364	536	364	536	250
165°	468	396	468	396	468	134
175°	422	413	422	413	422	41
180°	414	414	414	414	414	



TEST NUMBER: P332975-930

CATALOG NUMBER: SA4XXRDIP-C1020D1035U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9
2.5°	1475.5	1479.6	1475.5	1475.1	1470.6	1469.3	1467.5	1461.6	1450.7	1444.5	1445.8
5°	1616.5	1630.5	1622.7	1621.5	1609.2	1596.8	1588.9	1570.8	1551.7	1538.7	1528.0
7.5°	1779.5	1787.5	1782.7	1774.7	1754.7	1743.3	1725.0	1701.2	1666.9	1640.5	1616.6
10°	1890.4	1897.1	1894.9	1880.2	1865.6	1835.7	1818.8	1785.6	1742.1	1707.8	1675.6
12.5°	1999.5	2006.7	1986.9	1987.5	1959.8	1936.3	1909.4	1867.6	1817.5	1773.1	1732.9
15°	2141.8	2132.7	2132.7	2121.5	2090.4	2057.8	2030.2	1986.2	1923.0	1870.1	1814.3
17.5°	2253.2	2256.3	2251.7	2225.0	2200.7	2166.9	2116.3	2065.0	2006.4	1935.3	1878.2
20°	2319.9	2319.9	2314.8	2296.8	2265.2	2229.1	2174.5	2118.6	2044.3	1972.7	1908.5
22.5°	2346.9	2348.7	2342.8	2327.8	2299.5	2264.2	2217.7	2161.0	2084.4	2003.8	1924.2
25°	2309.7	2320.4	2321.6	2317.6	2309.2	2287.7	2247.7	2189.6	2120.9	2033.5	1947.8
27.5°	2120.6	2134.1	2145.9	2165.4	2191.4	2204.9	2206.7	2177.2	2117.2	2033.1	1946.9
30°	1932.1	1943.3	1980.0	2027.9	2065.1	2098.9	2128.3	2136.1	2102.3	2026.8	1936.0
32.5°	1722.9	1738.2	1774.8	1826.4	1888.3	1945.6	2011.4	2045.0	2044.1	1998.8	1914.8
35°	1422.6	1433.9	1467.7	1521.8	1596.2	1681.3	1785.6	1866.7	1921.9	1918.0	1866.7
37.5°	1147.3	1160.0	1194.2	1239.1	1311.2	1416.6	1517.5	1629.3	1731.5	1788.8	1771.6
40°	997.6	998.2	1031.4	1077.7	1145.3	1237.1	1347.0	1471.0	1584.9	1677.9	1695.9
42.5°	879.5	879.5	901.6	951.4	1000.1	1086.5	1191.5	1314.6	1447.8	1555.3	1603.0
45°	727.1	732.1	750.2	780.1	818.4	891.6	975.6	1090.1	1239.4	1366.8	1446.3
47.5°	615.7	623.1	634.6	659.0	689.5	738.3	807.8	910.6	1032.1	1172.2	1285.3
50°	558.0	559.1	573.7	587.3	613.8	652.6	713.5	799.2	910.8	1045.5	1171.2
52.5°	508.4	508.2	517.0	534.1	555.6	586.0	635.1	713.1	812.0	932.8	1062.5
55°	434.0	436.8	443.6	457.1	473.4	494.9	533.8	592.4	670.2	773.3	891.1
57.5°	377.4	378.9	384.2	389.9	404.9	420.4	449.6	490.3	556.0	640.4	750.2
60°	340.4	341.0	342.7	351.1	363.0	377.6	397.4	431.7	487.0	564.2	651.0
62.5°	304.4	305.3	307.9	314.1	323.3	333.5	354.1	381.7	427.5	493.4	571.6
65°	253.6	254.2	258.1	260.4	267.7	276.7	292.0	310.5	342.1	397.4	456.6
67.5°	211.9	211.9	212.1	215.2	220.3	226.2	235.4	250.2	274.0	307.9	360.1
70°	184.8	184.8	186.0	187.7	190.5	195.6	200.6	211.9	229.4	257.0	297.0
72.5°	159.6	160.0	161.2	161.5	163.0	167.1	170.9	178.1	191.1	211.9	244.3
75°	117.2	119.0	121.7	124.0	126.8	126.3	130.2	134.7	138.7	151.1	169.7
77.5°	87.2	86.3	86.7	88.6	88.9	89.5	92.3	95.8	98.7	104.6	111.3
80°	66.5	66.5	68.2	68.7	68.2	68.7	71.6	73.3	74.4	76.6	82.8
82.5°	50.3	51.2	50.6	51.2	51.5	52.1	54.5	54.8	55.9	56.8	59.4
85°	28.2	28.8	29.3	28.2	28.2	28.2	29.3	29.8	31.0	30.4	31.6
87.5°	13.4	12.9	13.5	13.4	13.6	13.2	13.5	14.2	13.1	13.8	13.5
90°	17.1	17.1	17.9	17.1	16.3	16.3	15.5	14.7	13.9	14.7	13.0
92.5°	62.7	62.7	65.5	69.9	79.4	95.7	120.3	159.9	215.1	258.2	225.9
95°	198.6	209.2	223.8	249.1	288.9	367.9	477.0	603.1	682.1	663.3	500.6
97.5°	530.8	547.8	572.2	621.2	679.6	764.6	844.2	891.1	856.9	698.6	468.5
100°	746.4	752.8	777.3	827.0	897.7	958.0	997.8	981.6	862.7	654.4	424.9
102.5°	933.9	939.1	964.8	1000.8	1044.2	1069.3	1057.8	977.1	813.9	599.1	395.6
105°	1145.2	1150.1	1161.5	1168.0	1166.4	1132.9	1052.4	911.6	725.2	533.9	370.3
107.5°	1223.7	1221.6	1213.4	1194.8	1154.6	1082.1	968.6	818.6	653.5	497.5	365.7
110°	1225.0	1217.6	1203.0	1168.8	1111.0	1021.5	903.4	762.6	617.8	485.1	367.0



TEST NUMBER: P332975-930

CATALOG NUMBER: SA4XXRDIP-C1020D1035U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1186.5	1174.7	1154.1	1112.8	1047.2	957.7	846.1	721.6	597.6	479.2	371.0
115°	1099.6	1093.1	1067.1	1018.2	953.9	875.8	780.6	680.4	578.7	476.1	378.5
117.5°	1011.5	1006.5	980.2	939.1	884.3	818.0	743.1	660.2	570.2	475.3	386.5
120°	962.1	953.1	932.0	896.1	849.7	792.0	726.8	651.1	565.7	475.3	392.3
122.5°	923.0	914.0	896.1	865.5	826.3	775.7	716.4	643.4	560.4	474.7	398.2
125°	877.4	872.5	857.0	833.5	800.9	756.1	699.9	630.0	551.9	473.7	407.0
127.5°	850.7	845.8	832.8	811.8	779.1	736.6	680.6	613.7	540.3	471.9	413.9
130°	835.1	830.2	817.2	796.8	763.4	720.3	665.0	600.7	533.1	471.2	419.1
132.5°	817.5	812.6	800.2	777.3	744.6	701.4	647.4	587.0	526.6	470.6	423.7
135°	784.6	779.8	766.7	744.0	711.3	670.7	621.0	568.1	516.8	469.6	430.6
137.5°	744.0	738.1	727.3	704.8	674.4	637.6	595.8	551.1	508.3	469.4	434.6
140°	714.6	708.1	696.8	678.8	650.3	616.1	579.5	541.3	503.9	468.8	437.9
142.5°	683.4	678.8	668.7	652.1	626.9	597.3	565.8	532.1	499.9	468.8	440.5
145°	640.6	636.5	628.4	614.5	594.2	571.4	547.0	519.3	493.3	467.2	442.0
147.5°	602.6	601.2	595.0	583.1	568.1	550.2	530.7	508.7	487.2	464.2	442.8
150°	581.1	580.3	575.4	564.8	551.9	537.2	520.9	502.2	482.7	462.3	442.8
152.5°	561.6	560.8	557.8	549.3	538.2	526.1	511.1	495.0	477.4	459.0	441.5
155°	536.4	536.4	533.9	527.4	519.3	509.5	497.3	484.3	469.6	454.2	439.5
157.5°	514.2	514.2	512.7	507.8	501.7	493.9	483.6	472.7	461.6	449.1	437.4
160°	500.6	500.6	499.8	494.9	490.0	483.5	474.5	465.5	455.8	445.2	435.5
162.5°	487.5	488.2	487.4	482.5	478.9	473.0	466.0	458.4	450.6	441.3	433.5
165°	468.0	468.8	469.6	466.4	463.1	459.0	453.4	448.5	442.0	435.5	429.7
167.5°	452.6	453.2	453.4	451.3	449.6	447.2	442.6	438.9	434.1	429.6	425.8
170°	442.8	442.8	443.6	442.8	441.2	438.7	435.5	433.0	428.9	425.7	423.2
172.5°	433.0	434.3	435.1	434.3	433.3	431.5	429.6	427.8	424.4	421.8	420.6
175°	421.6	423.2	424.9	423.2	423.2	423.2	421.6	420.8	419.1	417.5	417.5
177.5°	414.9	416.2	417.5	416.9	417.5	416.9	416.9	416.2	415.6	414.9	414.9
180°	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3



TEST NUMBER: P332975-930

CATALOG NUMBER: SA4XXRDIP-C1020D1035U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9
2.5°	1441.3	1435.0	1431.8	1424.6	1416.0	1411.5	1407.5	1401.6	1393.9	1385.8	1380.0
5°	1514.4	1500.9	1484.0	1463.7	1445.7	1428.2	1413.0	1397.7	1380.3	1362.3	1344.3
7.5°	1589.5	1562.9	1534.1	1500.9	1468.6	1439.2	1412.1	1386.2	1356.8	1330.6	1306.7
10°	1641.8	1605.7	1565.7	1523.5	1481.2	1444.5	1408.5	1375.8	1339.7	1307.6	1280.5
12.5°	1684.2	1641.8	1593.7	1541.1	1490.2	1445.9	1404.4	1361.8	1320.8	1286.0	1249.9
15°	1754.5	1696.5	1631.7	1568.6	1502.6	1442.3	1386.5	1336.9	1290.1	1241.1	1206.7
17.5°	1802.9	1734.1	1655.2	1579.4	1501.5	1430.4	1366.0	1306.9	1253.0	1202.9	1162.0
20°	1831.7	1755.7	1668.3	1582.1	1494.7	1418.6	1349.3	1283.9	1228.2	1174.0	1131.7
22.5°	1848.0	1763.8	1668.3	1578.0	1487.5	1405.1	1329.0	1260.9	1200.2	1146.1	1099.3
25°	1853.2	1763.0	1665.5	1561.8	1462.6	1375.2	1296.3	1222.5	1154.9	1100.7	1051.2
27.5°	1846.0	1739.8	1639.9	1533.5	1431.2	1339.0	1256.2	1178.7	1110.9	1052.9	1002.0
30°	1835.2	1721.3	1614.2	1503.7	1400.0	1311.6	1224.2	1149.8	1079.3	1019.0	967.8
32.5°	1811.7	1698.8	1583.6	1470.4	1365.3	1274.1	1191.2	1116.4	1047.3	985.7	931.2
35°	1765.3	1650.8	1525.8	1409.7	1306.4	1211.8	1134.0	1061.8	995.9	930.0	872.5
37.5°	1704.1	1587.1	1462.7	1335.5	1232.3	1142.9	1071.5	1003.8	939.5	879.2	815.5
40°	1646.3	1539.8	1411.3	1285.1	1179.1	1092.8	1027.0	965.5	900.7	840.9	777.2
42.5°	1576.5	1485.7	1355.8	1229.1	1124.5	1041.5	980.0	919.9	861.0	803.1	736.6
45°	1459.8	1391.0	1269.3	1147.5	1042.1	959.9	903.5	850.5	798.7	743.4	680.9
47.5°	1326.1	1279.5	1174.4	1049.8	952.3	878.2	823.8	780.5	736.6	681.4	626.6
50°	1233.2	1203.3	1101.9	988.1	895.0	826.8	771.0	730.4	693.8	640.8	591.8
52.5°	1134.0	1118.1	1032.4	923.6	833.7	766.9	719.2	682.7	645.6	601.6	555.7
55°	982.9	991.4	918.7	824.6	740.0	683.7	640.3	609.8	578.3	541.1	505.6
57.5°	828.5	859.4	810.6	728.0	648.7	596.6	563.9	538.3	511.8	481.0	450.7
60°	736.1	762.0	734.4	661.7	592.4	543.9	513.5	493.7	467.2	439.0	416.0
62.5°	645.9	673.6	657.3	598.6	534.2	492.5	465.7	447.3	427.5	403.0	379.0
65°	532.6	550.7	542.7	502.2	456.6	421.0	396.2	382.7	364.7	346.7	325.2
67.5°	408.0	442.8	438.1	416.6	377.2	349.4	333.2	321.2	304.8	291.4	276.9
70°	335.3	367.5	366.9	349.4	328.0	302.1	290.8	280.7	266.0	253.1	241.2
72.5°	274.5	303.9	308.3	294.9	280.2	260.7	249.8	242.8	228.6	219.7	210.1
75°	192.2	213.6	219.2	219.2	212.5	202.4	192.7	188.3	178.1	170.2	164.6
77.5°	126.0	139.6	148.4	150.3	151.4	148.0	140.1	137.0	129.1	126.4	121.0
80°	89.0	98.1	108.2	111.6	114.4	113.3	109.9	107.6	100.4	97.5	95.2
82.5°	61.6	66.5	74.8	82.3	81.5	84.5	81.5	79.7	74.2	73.1	70.9
85°	32.1	32.7	33.8	38.9	41.7	42.8	43.4	42.2	40.6	40.6	36.6
87.5°	13.1	12.6	12.6	12.6	12.9	14.5	15.3	15.5	14.4	13.6	12.4
90°	11.4	11.4	6.5	6.5	5.7	4.9	2.4	0.8	2.4	4.9	5.7
92.5°	164.4	101.3	59.9	43.0	31.1	21.2	13.5	9.3	13.5	21.2	31.1
95°	306.1	172.5	101.7	67.6	48.0	37.4	29.3	26.8	29.3	37.4	48.0
97.5°	275.1	164.9	110.4	81.7	65.0	55.2	48.2	48.2	48.2	55.2	65.0
100°	258.9	166.9	118.9	92.8	77.3	67.6	61.9	61.9	61.9	67.6	77.3
102.5°	254.3	173.3	129.9	105.2	90.3	81.2	76.1	74.8	76.1	81.2	90.3
105°	256.4	188.8	149.8	126.1	111.5	101.7	97.7	95.2	97.7	101.7	111.5
107.5°	268.4	206.9	171.0	147.8	133.8	123.4	119.4	117.7	119.4	123.4	133.8
110°	277.5	220.5	184.7	162.8	148.1	138.4	134.3	132.6	134.3	138.4	148.1



TEST NUMBER: P332975-930

CATALOG NUMBER: SA4XXRDIP-C1020D1035U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	287.3	233.6	199.1	177.1	162.5	153.4	148.6	147.0	148.6	153.4	162.5
115°	302.8	254.0	221.4	199.4	183.9	175.8	170.1	167.7	170.1	175.8	183.9
117.5°	318.5	273.6	242.7	219.9	205.5	196.5	191.4	189.1	191.4	196.5	205.5
120°	329.6	287.3	256.4	233.6	219.7	210.8	205.1	203.5	205.1	210.8	219.7
122.5°	340.1	300.4	269.4	247.3	232.1	223.8	218.1	216.5	218.1	223.8	232.1
125°	355.7	318.2	288.9	266.1	250.7	241.7	236.8	233.6	236.8	241.7	250.7
127.5°	369.2	334.8	306.6	283.6	267.4	257.2	251.4	248.7	251.4	257.2	267.4
130°	377.6	345.9	318.2	294.6	279.2	266.9	260.5	257.2	260.5	266.9	279.2
132.5°	386.1	355.1	327.3	305.1	288.3	276.7	268.2	265.6	268.2	276.7	288.3
135°	397.2	367.9	341.0	319.8	302.8	288.9	280.8	277.5	280.8	288.9	302.8
137.5°	405.0	377.6	352.6	332.4	314.6	301.5	292.5	289.4	292.5	301.5	314.6
140°	410.2	384.2	359.8	340.2	323.1	309.3	300.4	297.9	300.4	309.3	323.1
142.5°	414.1	390.0	366.2	347.4	330.9	317.7	309.5	307.0	309.5	317.7	330.9
145°	418.3	396.4	375.2	357.3	341.9	330.4	322.3	319.8	322.3	330.4	341.9
147.5°	422.1	402.9	383.0	366.9	354.1	342.3	335.2	334.4	335.2	342.3	354.1
150°	424.0	406.2	388.2	372.8	360.6	350.8	344.3	343.5	344.3	350.8	360.6
152.5°	425.3	408.8	392.8	378.6	367.7	358.7	352.1	352.0	352.1	358.7	367.7
155°	426.5	412.6	398.8	386.6	377.6	369.5	364.6	363.8	364.6	369.5	377.6
157.5°	426.5	415.4	403.7	394.1	386.3	379.9	375.4	375.4	375.4	379.9	386.3
160°	426.5	416.7	407.0	398.0	391.5	385.8	382.5	382.5	382.5	385.8	391.5
162.5°	426.5	418.0	409.0	401.9	396.1	391.0	388.4	389.1	388.4	391.0	396.1
165°	424.9	418.3	411.0	406.2	402.1	398.0	396.4	396.4	396.4	398.0	402.1
167.5°	422.9	418.2	412.8	409.1	406.8	403.7	402.9	403.7	402.9	403.7	406.8
170°	421.6	417.5	413.4	411.0	409.4	407.0	406.2	407.0	406.2	407.0	409.4
172.5°	420.3	416.9	414.1	412.3	411.3	409.5	409.4	410.2	409.4	409.5	411.3
175°	418.3	415.9	414.3	414.3	413.4	412.6	412.6	413.4	412.6	412.6	413.4
177.5°	416.2	414.9	414.3	414.3	414.3	413.6	414.3	414.9	414.3	413.6	414.3
180°	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3



TEST NUMBER: P332975-930

CATALOG NUMBER: SA4XXRDIP-C1020D1035U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9
2.5°	1373.6	1369.1	1363.3	1356.5	1348.4	1341.2	1338.1	1340.8	1342.1	1338.5	1338.1
5°	1331.9	1317.8	1306.4	1289.6	1276.0	1264.8	1256.9	1253.5	1254.6	1245.6	1243.3
7.5°	1284.8	1268.1	1249.7	1229.6	1210.9	1194.3	1185.6	1180.9	1171.3	1167.3	1160.4
10°	1254.6	1232.1	1214.1	1190.3	1169.0	1149.2	1139.6	1131.7	1122.2	1117.7	1108.1
12.5°	1223.5	1197.3	1177.5	1152.9	1131.1	1107.3	1098.1	1083.5	1068.5	1059.1	1046.8
15°	1179.7	1148.1	1123.9	1094.5	1068.6	1041.5	1017.3	990.3	980.2	958.7	946.3
17.5°	1128.4	1096.3	1066.3	1027.0	987.0	953.4	927.6	901.6	886.1	872.5	866.2
20°	1094.5	1065.3	1023.5	977.9	933.4	896.2	875.3	858.4	841.5	831.9	825.2
22.5°	1062.5	1025.1	976.6	927.4	882.9	853.8	836.1	818.7	804.9	795.8	786.8
25°	1008.9	959.9	908.6	852.2	821.7	796.4	777.2	763.1	754.7	742.8	738.3
27.5°	953.7	894.4	837.8	799.9	768.2	745.0	728.3	717.7	707.0	699.4	693.6
30°	911.3	851.1	800.4	764.3	732.1	713.0	699.4	687.1	678.6	672.4	667.9
32.5°	869.4	809.1	766.5	727.7	702.4	683.7	669.3	660.0	653.4	645.3	642.6
35°	808.8	755.2	718.0	683.1	657.2	640.3	629.0	619.4	613.8	611.6	609.8
37.5°	750.5	706.7	666.7	638.1	614.9	601.6	588.3	583.6	579.8	575.7	577.5
40°	713.5	672.4	636.9	606.4	587.8	573.2	565.3	559.7	556.3	556.3	556.3
42.5°	681.5	641.3	606.7	579.4	560.8	548.4	539.6	534.8	533.8	533.3	536.0
45°	631.9	594.6	559.7	537.1	521.4	508.9	503.9	499.9	499.9	502.2	502.7
47.5°	582.5	547.7	519.7	494.4	480.0	472.2	467.8	465.8	466.0	468.2	470.8
50°	552.4	518.0	490.3	467.8	454.3	446.9	443.0	441.9	443.0	443.0	446.9
52.5°	519.4	488.7	461.5	442.5	427.2	420.4	418.2	416.6	417.3	419.1	420.8
55°	471.2	443.6	417.7	399.6	388.3	383.8	378.8	379.3	378.2	379.3	379.3
57.5°	422.8	398.0	373.9	359.6	349.7	343.2	337.6	339.2	337.5	337.3	336.4
60°	391.8	364.7	345.5	332.6	321.2	315.6	310.5	311.7	310.0	308.8	306.6
62.5°	357.9	335.3	317.1	304.6	295.5	289.0	284.0	282.8	278.9	275.1	270.1
65°	308.8	290.2	273.9	262.1	253.6	248.6	244.6	241.2	232.8	223.7	219.2
67.5°	261.2	247.8	232.5	222.5	215.6	209.0	201.5	195.7	187.8	182.9	180.0
70°	230.5	217.5	204.6	195.0	187.7	181.5	173.0	169.1	163.5	161.2	158.4
72.5°	201.2	189.1	177.1	168.4	160.6	155.8	149.1	145.2	142.7	141.8	139.0
75°	156.7	147.1	138.1	130.2	124.0	120.6	117.8	115.0	113.8	108.8	106.0
77.5°	114.3	108.0	102.3	96.7	92.3	90.1	84.6	81.4	79.5	77.1	76.6
80°	89.0	84.5	78.9	75.5	69.3	67.1	64.8	64.2	63.7	63.1	62.5
82.5°	66.9	62.5	56.8	54.8	53.1	51.8	50.4	49.8	49.2	49.6	49.5
85°	33.8	31.6	31.6	31.0	30.4	29.8	29.3	29.3	28.8	29.3	28.8
87.5°	12.6	12.1	13.1	12.2	13.0	13.3	12.7	12.9	13.5	12.7	12.7
90°	6.5	6.5	11.4	11.4	13.0	14.7	13.9	14.7	15.5	16.3	16.3
92.5°	43.0	59.9	101.3	164.4	225.9	258.2	215.1	159.9	120.3	95.7	79.4
95°	67.6	101.7	172.5	306.1	500.6	663.3	682.1	603.1	477.0	367.9	288.9
97.5°	81.7	110.4	164.9	275.1	468.5	698.6	856.9	891.1	844.2	764.6	679.6
100°	92.8	118.9	166.9	258.9	424.9	654.4	862.7	981.6	997.8	958.0	897.7
102.5°	105.2	129.9	173.3	254.3	395.6	599.1	813.9	977.1	1057.8	1069.3	1044.2
105°	126.1	149.8	188.8	256.4	370.3	533.9	725.2	911.6	1052.4	1132.9	1166.4
107.5°	147.8	171.0	206.9	268.4	365.7	497.5	653.5	818.6	968.6	1082.1	1154.6
110°	162.8	184.7	220.5	277.5	367.0	485.1	617.8	762.6	903.4	1021.5	1111.0



TEST NUMBER: P332975-930

CATALOG NUMBER: SA4XXRDIP-C1020D1035U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	177.1	199.1	233.6	287.3	371.0	479.2	597.6	721.6	846.1	957.7	1047.2
115°	199.4	221.4	254.0	302.8	378.5	476.1	578.7	680.4	780.6	875.8	953.9
117.5°	219.9	242.7	273.6	318.5	386.5	475.3	570.2	660.2	743.1	818.0	884.3
120°	233.6	256.4	287.3	329.6	392.3	475.3	565.7	651.1	726.8	792.0	849.7
122.5°	247.3	269.4	300.4	340.1	398.2	474.7	560.4	643.4	716.4	775.7	826.3
125°	266.1	288.9	318.2	355.7	407.0	473.7	551.9	630.0	699.9	756.1	800.9
127.5°	283.6	306.6	334.8	369.2	413.9	471.9	540.3	613.7	680.6	736.6	779.1
130°	294.6	318.2	345.9	377.6	419.1	471.2	533.1	600.7	665.0	720.3	763.4
132.5°	305.1	327.3	355.1	386.1	423.7	470.6	526.6	587.0	647.4	701.4	744.6
135°	319.8	341.0	367.9	397.2	430.6	469.6	516.8	568.1	621.0	670.7	711.3
137.5°	332.4	352.6	377.6	405.0	434.6	469.4	508.3	551.1	595.8	637.6	674.4
140°	340.2	359.8	384.2	410.2	437.9	468.8	503.9	541.3	579.5	616.1	650.3
142.5°	347.4	366.2	390.0	414.1	440.5	468.8	499.9	532.1	565.8	597.3	626.9
145°	357.3	375.2	396.4	418.3	442.0	467.2	493.3	519.3	547.0	571.4	594.2
147.5°	366.9	383.0	402.9	422.1	442.8	464.2	487.2	508.7	530.7	550.2	568.1
150°	372.8	388.2	406.2	424.0	442.8	462.3	482.7	502.2	520.9	537.2	551.9
152.5°	378.6	392.8	408.8	425.3	441.5	459.0	477.4	495.0	511.1	526.1	538.2
155°	386.6	398.8	412.6	426.5	439.5	454.2	469.6	484.3	497.3	509.5	519.3
157.5°	394.1	403.7	415.4	426.5	437.4	449.1	461.6	472.7	483.6	493.9	501.7
160°	398.0	407.0	416.7	426.5	435.5	445.2	455.8	465.5	474.5	483.5	490.0
162.5°	401.9	409.0	418.0	426.5	433.5	441.3	450.6	458.4	466.0	473.0	478.9
165°	406.2	411.0	418.3	424.9	429.7	435.5	442.0	448.5	453.4	459.0	463.1
167.5°	409.1	412.8	418.2	422.9	425.8	429.6	434.1	438.9	442.6	447.2	449.6
170°	411.0	413.4	417.5	421.6	423.2	425.7	428.9	433.0	435.5	438.7	441.2
172.5°	412.3	414.1	416.9	420.3	420.6	421.8	424.4	427.8	429.6	431.5	433.3
175°	414.3	414.3	415.9	418.3	417.5	417.5	419.1	420.8	421.6	423.2	423.2
177.5°	414.3	414.3	414.9	416.2	414.9	414.9	415.6	416.2	416.9	416.9	417.5
180°	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3



TEST NUMBER: P332975-930

CATALOG NUMBER: SA4XXRDIP-C1020D1035U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9
2.5°	1335.3	1336.2	1333.1	1332.2	1333.1	1336.2	1335.3	1338.1	1338.5	1342.1	1340.8
5°	1238.8	1237.7	1234.9	1235.4	1234.9	1237.7	1238.8	1243.3	1245.6	1254.6	1253.5
7.5°	1156.3	1151.9	1153.2	1148.7	1153.2	1151.9	1156.3	1160.4	1167.3	1171.3	1180.9
10°	1105.8	1099.6	1094.5	1090.1	1094.5	1099.6	1105.8	1108.1	1117.7	1122.2	1131.7
12.5°	1036.8	1031.5	1024.7	1026.1	1024.7	1031.5	1036.8	1046.8	1059.1	1068.5	1083.5
15°	939.0	930.5	917.0	918.7	917.0	930.5	939.0	946.3	958.7	980.2	990.3
17.5°	856.1	856.2	850.0	851.5	850.0	856.2	856.1	866.2	872.5	886.1	901.6
20°	813.3	809.3	809.9	808.2	809.9	809.3	813.3	825.2	831.9	841.5	858.4
22.5°	783.6	778.7	774.8	771.3	774.8	778.7	783.6	786.8	795.8	804.9	818.7
25°	733.3	729.9	724.8	723.7	724.8	729.9	733.3	738.3	742.8	754.7	763.1
27.5°	689.1	688.4	686.4	683.8	686.4	688.4	689.1	693.6	699.4	707.0	717.7
30°	663.4	662.3	661.1	659.4	661.1	662.3	663.4	667.9	672.4	678.6	687.1
32.5°	640.4	639.7	638.5	638.7	638.5	639.7	640.4	642.6	645.3	653.4	660.0
35°	607.6	607.0	605.9	605.4	605.9	607.0	607.6	609.8	611.6	613.8	619.4
37.5°	576.9	578.4	577.7	577.6	577.7	578.4	576.9	577.5	575.7	579.8	583.6
40°	555.7	556.3	557.4	556.8	557.4	556.3	555.7	556.3	556.3	556.3	559.7
42.5°	538.2	538.3	539.8	537.9	539.8	538.3	538.2	536.0	533.3	533.8	534.8
45°	506.7	510.1	509.5	509.5	509.5	510.1	506.7	502.7	502.2	499.9	499.9
47.5°	472.3	475.2	476.1	475.9	476.1	475.2	472.3	470.8	468.2	466.0	465.8
50°	449.8	448.7	450.4	449.8	450.4	448.7	449.8	446.9	443.0	443.0	441.9
52.5°	422.2	422.5	422.4	421.8	422.4	422.5	422.2	420.8	419.1	417.3	416.6
55°	379.8	380.4	379.3	379.8	379.3	380.4	379.8	379.3	379.3	378.2	379.3
57.5°	333.9	331.2	332.3	330.9	332.3	331.2	333.9	336.4	337.3	337.5	339.2
60°	301.0	296.4	295.3	293.1	295.3	296.4	301.0	306.6	308.8	310.0	311.7
62.5°	264.0	260.8	257.0	258.8	257.0	260.8	264.0	270.1	275.1	278.9	282.8
65°	214.7	212.5	210.8	213.0	210.8	212.5	214.7	219.2	223.7	232.8	241.2
67.5°	177.7	176.5	176.5	175.4	176.5	176.5	177.7	180.0	182.9	187.8	195.7
70°	158.4	156.7	156.7	155.6	156.7	156.7	158.4	158.4	161.2	163.5	169.1
72.5°	138.5	136.8	137.3	136.6	137.3	136.8	138.5	139.0	141.8	142.7	145.2
75°	102.6	99.8	99.8	100.4	99.8	99.8	102.6	106.0	108.8	113.8	115.0
77.5°	76.6	76.0	76.8	75.7	76.8	76.0	76.6	76.6	77.1	79.5	81.4
80°	62.5	62.0	61.5	63.1	61.5	62.0	62.5	62.5	63.1	63.7	64.2
82.5°	48.6	48.5	48.3	50.5	48.3	48.5	48.6	49.5	49.6	49.2	49.8
85°	29.3	28.2	29.3	28.2	29.3	28.2	29.3	28.8	29.3	28.8	29.3
87.5°	13.8	13.5	12.9	13.4	12.9	13.5	13.8	12.7	12.7	13.5	12.9
90°	17.1	17.9	17.1	17.1	17.1	17.9	17.1	16.3	16.3	15.5	14.7
92.5°	69.9	65.5	62.7	62.7	62.7	65.5	69.9	79.4	95.7	120.3	159.9
95°	249.1	223.8	209.2	198.6	209.2	223.8	249.1	288.9	367.9	477.0	603.1
97.5°	621.2	572.2	547.8	530.8	547.8	572.2	621.2	679.6	764.6	844.2	891.1
100°	827.0	777.3	752.8	746.4	752.8	777.3	827.0	897.7	958.0	997.8	981.6
102.5°	1000.8	964.8	939.1	933.9	939.1	964.8	1000.8	1044.2	1069.3	1057.8	977.1
105°	1168.0	1161.5	1150.1	1145.2	1150.1	1161.5	1168.0	1166.4	1132.9	1052.4	911.6
107.5°	1194.8	1213.4	1221.6	1223.7	1221.6	1213.4	1194.8	1154.6	1082.1	968.6	818.6
110°	1168.8	1203.0	1217.6	1225.0	1217.6	1203.0	1168.8	1111.0	1021.5	903.4	762.6



TEST NUMBER: P332975-930

CATALOG NUMBER: SA4XXRDIP-C1020D1035U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1112.8	1154.1	1174.7	1186.5	1174.7	1154.1	1112.8	1047.2	957.7	846.1	721.6
115°	1018.2	1067.1	1093.1	1099.6	1093.1	1067.1	1018.2	953.9	875.8	780.6	680.4
117.5°	939.1	980.2	1006.5	1011.5	1006.5	980.2	939.1	884.3	818.0	743.1	660.2
120°	896.1	932.0	953.1	962.1	953.1	932.0	896.1	849.7	792.0	726.8	651.1
122.5°	865.5	896.1	914.0	923.0	914.0	896.1	865.5	826.3	775.7	716.4	643.4
125°	833.5	857.0	872.5	877.4	872.5	857.0	833.5	800.9	756.1	699.9	630.0
127.5°	811.8	832.8	845.8	850.7	845.8	832.8	811.8	779.1	736.6	680.6	613.7
130°	796.8	817.2	830.2	835.1	830.2	817.2	796.8	763.4	720.3	665.0	600.7
132.5°	777.3	800.2	812.6	817.5	812.6	800.2	777.3	744.6	701.4	647.4	587.0
135°	744.0	766.7	779.8	784.6	779.8	766.7	744.0	711.3	670.7	621.0	568.1
137.5°	704.8	727.3	738.1	744.0	738.1	727.3	704.8	674.4	637.6	595.8	551.1
140°	678.8	696.8	708.1	714.6	708.1	696.8	678.8	650.3	616.1	579.5	541.3
142.5°	652.1	668.7	678.8	683.4	678.8	668.7	652.1	626.9	597.3	565.8	532.1
145°	614.5	628.4	636.5	640.6	636.5	628.4	614.5	594.2	571.4	547.0	519.3
147.5°	583.1	595.0	601.2	602.6	601.2	595.0	583.1	568.1	550.2	530.7	508.7
150°	564.8	575.4	580.3	581.1	580.3	575.4	564.8	551.9	537.2	520.9	502.2
152.5°	549.3	557.8	560.8	561.6	560.8	557.8	549.3	538.2	526.1	511.1	495.0
155°	527.4	533.9	536.4	536.4	536.4	533.9	527.4	519.3	509.5	497.3	484.3
157.5°	507.8	512.7	514.2	514.2	514.2	512.7	507.8	501.7	493.9	483.6	472.7
160°	494.9	499.8	500.6	500.6	500.6	499.8	494.9	490.0	483.5	474.5	465.5
162.5°	482.5	487.4	488.2	487.5	488.2	487.4	482.5	478.9	473.0	466.0	458.4
165°	466.4	469.6	468.8	468.0	468.8	469.6	466.4	463.1	459.0	453.4	448.5
167.5°	451.3	453.4	453.2	452.6	453.2	453.4	451.3	449.6	447.2	442.6	438.9
170°	442.8	443.6	442.8	442.8	442.8	443.6	442.8	441.2	438.7	435.5	433.0
172.5°	434.3	435.1	434.3	433.0	434.3	435.1	434.3	433.3	431.5	429.6	427.8
175°	423.2	424.9	423.2	421.6	423.2	424.9	423.2	423.2	423.2	421.6	420.8
177.5°	416.9	417.5	416.2	414.9	416.2	417.5	416.9	417.5	416.9	416.9	416.2
180°	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3



TEST NUMBER: P332975-930

CATALOG NUMBER: SA4XXRDIP-C1020D1035U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9
2.5°	1338.1	1341.2	1348.4	1356.5	1363.3	1369.1	1373.6	1380.0	1385.8	1393.9	1401.6
5°	1256.9	1264.8	1276.0	1289.6	1306.4	1317.8	1331.9	1344.3	1362.3	1380.3	1397.7
7.5°	1185.6	1194.3	1210.9	1229.6	1249.7	1268.1	1284.8	1306.7	1330.6	1356.8	1386.2
10°	1139.6	1149.2	1169.0	1190.3	1214.1	1232.1	1254.6	1280.5	1307.6	1339.7	1375.8
12.5°	1098.1	1107.3	1131.1	1152.9	1177.5	1197.3	1223.5	1249.9	1286.0	1320.8	1361.8
15°	1017.3	1041.5	1068.6	1094.5	1123.9	1148.1	1179.7	1206.7	1241.1	1290.1	1336.9
17.5°	927.6	953.4	987.0	1027.0	1066.3	1096.3	1128.4	1162.0	1202.9	1253.0	1306.9
20°	875.3	896.2	933.4	977.9	1023.5	1065.3	1094.5	1131.7	1174.0	1228.2	1283.9
22.5°	836.1	853.8	882.9	927.4	976.6	1025.1	1062.5	1099.3	1146.1	1200.2	1260.9
25°	777.2	796.4	821.7	852.2	908.6	959.9	1008.9	1051.2	1100.7	1154.9	1222.5
27.5°	728.3	745.0	768.2	799.9	837.8	894.4	953.7	1002.0	1052.9	1110.9	1178.7
30°	699.4	713.0	732.1	764.3	800.4	851.1	911.3	967.8	1019.0	1079.3	1149.8
32.5°	669.3	683.7	702.4	727.7	766.5	809.1	869.4	931.2	985.7	1047.3	1116.4
35°	629.0	640.3	657.2	683.1	718.0	755.2	808.8	872.5	930.0	995.9	1061.8
37.5°	588.3	601.6	614.9	638.1	666.7	706.7	750.5	815.5	879.2	939.5	1003.8
40°	565.3	573.2	587.8	606.4	636.9	672.4	713.5	777.2	840.9	900.7	965.5
42.5°	539.6	548.4	560.8	579.4	606.7	641.3	681.5	736.6	803.1	861.0	919.9
45°	503.9	508.9	521.4	537.1	559.7	594.6	631.9	680.9	743.4	798.7	850.5
47.5°	467.8	472.2	480.0	494.4	519.7	547.7	582.5	626.6	681.4	736.6	780.5
50°	443.0	446.9	454.3	467.8	490.3	518.0	552.4	591.8	640.8	693.8	730.4
52.5°	418.2	420.4	427.2	442.5	461.5	488.7	519.4	555.7	601.6	645.6	682.7
55°	378.8	383.8	388.3	399.6	417.7	443.6	471.2	505.6	541.1	578.3	609.8
57.5°	337.6	343.2	349.7	359.6	373.9	398.0	422.8	450.7	481.0	511.8	538.3
60°	310.5	315.6	321.2	332.6	345.5	364.7	391.8	416.0	439.0	467.2	493.7
62.5°	284.0	289.0	295.5	304.6	317.1	335.3	357.9	379.0	403.0	427.5	447.3
65°	244.6	248.6	253.6	262.1	273.9	290.2	308.8	325.2	346.7	364.7	382.7
67.5°	201.5	209.0	215.6	222.5	232.5	247.8	261.2	276.9	291.4	304.8	321.2
70°	173.0	181.5	187.7	195.0	204.6	217.5	230.5	241.2	253.1	266.0	280.7
72.5°	149.1	155.8	160.6	168.4	177.1	189.1	201.2	210.1	219.7	228.6	242.8
75°	117.8	120.6	124.0	130.2	138.1	147.1	156.7	164.6	170.2	178.1	188.3
77.5°	84.6	90.1	92.3	96.7	102.3	108.0	114.3	121.0	126.4	129.1	137.0
80°	64.8	67.1	69.3	75.5	78.9	84.5	89.0	95.2	97.5	100.4	107.6
82.5°	50.4	51.8	53.1	54.8	56.8	62.5	66.9	70.9	73.1	74.2	79.7
85°	29.3	29.8	30.4	31.0	31.6	31.6	33.8	36.6	40.6	40.6	42.2
87.5°	12.7	13.3	13.0	12.2	13.1	12.1	12.6	12.4	13.6	14.4	15.5
90°	13.9	14.7	13.0	11.4	11.4	6.5	6.5	5.7	4.9	2.4	0.8
92.5°	215.1	258.2	225.9	164.4	101.3	59.9	43.0	31.1	21.2	13.5	9.3
95°	682.1	663.3	500.6	306.1	172.5	101.7	67.6	48.0	37.4	29.3	26.8
97.5°	856.9	698.6	468.5	275.1	164.9	110.4	81.7	65.0	55.2	48.2	48.2
100°	862.7	654.4	424.9	258.9	166.9	118.9	92.8	77.3	67.6	61.9	61.9
102.5°	813.9	599.1	395.6	254.3	173.3	129.9	105.2	90.3	81.2	76.1	74.8
105°	725.2	533.9	370.3	256.4	188.8	149.8	126.1	111.5	101.7	97.7	95.2
107.5°	653.5	497.5	365.7	268.4	206.9	171.0	147.8	133.8	123.4	119.4	117.7
110°	617.8	485.1	367.0	277.5	220.5	184.7	162.8	148.1	138.4	134.3	132.6



TEST NUMBER: P332975-930

CATALOG NUMBER: SA4XXRDIP-C1020D1035U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	597.6	479.2	371.0	287.3	233.6	199.1	177.1	162.5	153.4	148.6	147.0
115°	578.7	476.1	378.5	302.8	254.0	221.4	199.4	183.9	175.8	170.1	167.7
117.5°	570.2	475.3	386.5	318.5	273.6	242.7	219.9	205.5	196.5	191.4	189.1
120°	565.7	475.3	392.3	329.6	287.3	256.4	233.6	219.7	210.8	205.1	203.5
122.5°	560.4	474.7	398.2	340.1	300.4	269.4	247.3	232.1	223.8	218.1	216.5
125°	551.9	473.7	407.0	355.7	318.2	288.9	266.1	250.7	241.7	236.8	233.6
127.5°	540.3	471.9	413.9	369.2	334.8	306.6	283.6	267.4	257.2	251.4	248.7
130°	533.1	471.2	419.1	377.6	345.9	318.2	294.6	279.2	266.9	260.5	257.2
132.5°	526.6	470.6	423.7	386.1	355.1	327.3	305.1	288.3	276.7	268.2	265.6
135°	516.8	469.6	430.6	397.2	367.9	341.0	319.8	302.8	288.9	280.8	277.5
137.5°	508.3	469.4	434.6	405.0	377.6	352.6	332.4	314.6	301.5	292.5	289.4
140°	503.9	468.8	437.9	410.2	384.2	359.8	340.2	323.1	309.3	300.4	297.9
142.5°	499.9	468.8	440.5	414.1	390.0	366.2	347.4	330.9	317.7	309.5	307.0
145°	493.3	467.2	442.0	418.3	396.4	375.2	357.3	341.9	330.4	322.3	319.8
147.5°	487.2	464.2	442.8	422.1	402.9	383.0	366.9	354.1	342.3	335.2	334.4
150°	482.7	462.3	442.8	424.0	406.2	388.2	372.8	360.6	350.8	344.3	343.5
152.5°	477.4	459.0	441.5	425.3	408.8	392.8	378.6	367.7	358.7	352.1	352.0
155°	469.6	454.2	439.5	426.5	412.6	398.8	386.6	377.6	369.5	364.6	363.8
157.5°	461.6	449.1	437.4	426.5	415.4	403.7	394.1	386.3	379.9	375.4	375.4
160°	455.8	445.2	435.5	426.5	416.7	407.0	398.0	391.5	385.8	382.5	382.5
162.5°	450.6	441.3	433.5	426.5	418.0	409.0	401.9	396.1	391.0	388.4	389.1
165°	442.0	435.5	429.7	424.9	418.3	411.0	406.2	402.1	398.0	396.4	396.4
167.5°	434.1	429.6	425.8	422.9	418.2	412.8	409.1	406.8	403.7	402.9	403.7
170°	428.9	425.7	423.2	421.6	417.5	413.4	411.0	409.4	407.0	406.2	407.0
172.5°	424.4	421.8	420.6	420.3	416.9	414.1	412.3	411.3	409.5	409.4	410.2
175°	419.1	417.5	417.5	418.3	415.9	414.3	414.3	413.4	412.6	412.6	413.4
177.5°	415.6	414.9	414.9	416.2	414.9	414.3	414.3	414.3	413.6	414.3	414.9
180°	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3



TEST NUMBER: P332975-930

CATALOG NUMBER: SA4XXRDIP-C1020D1035U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9
2.5°	1407.5	1411.5	1416.0	1424.6	1431.8	1435.0	1441.3	1445.8	1444.5	1450.7	1461.6
5°	1413.0	1428.2	1445.7	1463.7	1484.0	1500.9	1514.4	1528.0	1538.7	1551.7	1570.8
7.5°	1412.1	1439.2	1468.6	1500.9	1534.1	1562.9	1589.5	1616.6	1640.5	1666.9	1701.2
10°	1408.5	1444.5	1481.2	1523.5	1565.7	1605.7	1641.8	1675.6	1707.8	1742.1	1785.6
12.5°	1404.4	1445.9	1490.2	1541.1	1593.7	1641.8	1684.2	1732.9	1773.1	1817.5	1867.6
15°	1386.5	1442.3	1502.6	1568.6	1631.7	1696.5	1754.5	1814.3	1870.1	1923.0	1986.2
17.5°	1366.0	1430.4	1501.5	1579.4	1655.2	1734.1	1802.9	1878.2	1935.3	2006.4	2065.0
20°	1349.3	1418.6	1494.7	1582.1	1668.3	1755.7	1831.7	1908.5	1972.7	2044.3	2118.6
22.5°	1329.0	1405.1	1487.5	1578.0	1668.3	1763.8	1848.0	1924.2	2003.8	2084.4	2161.0
25°	1296.3	1375.2	1462.6	1561.8	1665.5	1763.0	1853.2	1947.8	2033.5	2120.9	2189.6
27.5°	1256.2	1339.0	1431.2	1533.5	1639.9	1739.8	1846.0	1946.9	2033.1	2117.2	2177.2
30°	1224.2	1311.6	1400.0	1503.7	1614.2	1721.3	1835.2	1936.0	2026.8	2102.3	2136.1
32.5°	1191.2	1274.1	1365.3	1470.4	1583.6	1698.8	1811.7	1914.8	1998.8	2044.1	2045.0
35°	1134.0	1211.8	1306.4	1409.7	1525.8	1650.8	1765.3	1866.7	1918.0	1921.9	1866.7
37.5°	1071.5	1142.9	1232.3	1335.5	1462.7	1587.1	1704.1	1771.6	1788.8	1731.5	1629.3
40°	1027.0	1092.8	1179.1	1285.1	1411.3	1539.8	1646.3	1695.9	1677.9	1584.9	1471.0
42.5°	980.0	1041.5	1124.5	1229.1	1355.8	1485.7	1576.5	1603.0	1555.3	1447.8	1314.6
45°	903.5	959.9	1042.1	1147.5	1269.3	1391.0	1459.8	1446.3	1366.8	1239.4	1090.1
47.5°	823.8	878.2	952.3	1049.8	1174.4	1279.5	1326.1	1285.3	1172.2	1032.1	910.6
50°	771.0	826.8	895.0	988.1	1101.9	1203.3	1233.2	1171.2	1045.5	910.8	799.2
52.5°	719.2	766.9	833.7	923.6	1032.4	1118.1	1134.0	1062.5	932.8	812.0	713.1
55°	640.3	683.7	740.0	824.6	918.7	991.4	982.9	891.1	773.3	670.2	592.4
57.5°	563.9	596.6	648.7	728.0	810.6	859.4	828.5	750.2	640.4	556.0	490.3
60°	513.5	543.9	592.4	661.7	734.4	762.0	736.1	651.0	564.2	487.0	431.7
62.5°	465.7	492.5	534.2	598.6	657.3	673.6	645.9	571.6	493.4	427.5	381.7
65°	396.2	421.0	456.6	502.2	542.7	550.7	532.6	456.6	397.4	342.1	310.5
67.5°	333.2	349.4	377.2	416.6	438.1	442.8	408.0	360.1	307.9	274.0	250.2
70°	290.8	302.1	328.0	349.4	366.9	367.5	335.3	297.0	257.0	229.4	211.9
72.5°	249.8	260.7	280.2	294.9	308.3	303.9	274.5	244.3	211.9	191.1	178.1
75°	192.7	202.4	212.5	219.2	219.2	213.6	192.2	169.7	151.1	138.7	134.7
77.5°	140.1	148.0	151.4	150.3	148.4	139.6	126.0	111.3	104.6	98.7	95.8
80°	109.9	113.3	114.4	111.6	108.2	98.1	89.0	82.8	76.6	74.4	73.3
82.5°	81.5	84.5	81.5	82.3	74.8	66.5	61.6	59.4	56.8	55.9	54.8
85°	43.4	42.8	41.7	38.9	33.8	32.7	32.1	31.6	30.4	31.0	29.8
87.5°	15.3	14.5	12.9	12.6	12.6	12.6	13.1	13.5	13.8	13.1	14.2
90°	2.4	4.9	5.7	6.5	6.5	11.4	11.4	13.0	14.7	13.9	14.7
92.5°	13.5	21.2	31.1	43.0	59.9	101.3	164.4	225.9	258.2	215.1	159.9
95°	29.3	37.4	48.0	67.6	101.7	172.5	306.1	500.6	663.3	682.1	603.1
97.5°	48.2	55.2	65.0	81.7	110.4	164.9	275.1	468.5	698.6	856.9	891.1
100°	61.9	67.6	77.3	92.8	118.9	166.9	258.9	424.9	654.4	862.7	981.6
102.5°	76.1	81.2	90.3	105.2	129.9	173.3	254.3	395.6	599.1	813.9	977.1
105°	97.7	101.7	111.5	126.1	149.8	188.8	256.4	370.3	533.9	725.2	911.6
107.5°	119.4	123.4	133.8	147.8	171.0	206.9	268.4	365.7	497.5	653.5	818.6
110°	134.3	138.4	148.1	162.8	184.7	220.5	277.5	367.0	485.1	617.8	762.6



TEST NUMBER: P332975-930

CATALOG NUMBER: SA4XXRDIP-C1020D1035U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	148.6	153.4	162.5	177.1	199.1	233.6	287.3	371.0	479.2	597.6	721.6
115°	170.1	175.8	183.9	199.4	221.4	254.0	302.8	378.5	476.1	578.7	680.4
117.5°	191.4	196.5	205.5	219.9	242.7	273.6	318.5	386.5	475.3	570.2	660.2
120°	205.1	210.8	219.7	233.6	256.4	287.3	329.6	392.3	475.3	565.7	651.1
122.5°	218.1	223.8	232.1	247.3	269.4	300.4	340.1	398.2	474.7	560.4	643.4
125°	236.8	241.7	250.7	266.1	288.9	318.2	355.7	407.0	473.7	551.9	630.0
127.5°	251.4	257.2	267.4	283.6	306.6	334.8	369.2	413.9	471.9	540.3	613.7
130°	260.5	266.9	279.2	294.6	318.2	345.9	377.6	419.1	471.2	533.1	600.7
132.5°	268.2	276.7	288.3	305.1	327.3	355.1	386.1	423.7	470.6	526.6	587.0
135°	280.8	288.9	302.8	319.8	341.0	367.9	397.2	430.6	469.6	516.8	568.1
137.5°	292.5	301.5	314.6	332.4	352.6	377.6	405.0	434.6	469.4	508.3	551.1
140°	300.4	309.3	323.1	340.2	359.8	384.2	410.2	437.9	468.8	503.9	541.3
142.5°	309.5	317.7	330.9	347.4	366.2	390.0	414.1	440.5	468.8	499.9	532.1
145°	322.3	330.4	341.9	357.3	375.2	396.4	418.3	442.0	467.2	493.3	519.3
147.5°	335.2	342.3	354.1	366.9	383.0	402.9	422.1	442.8	464.2	487.2	508.7
150°	344.3	350.8	360.6	372.8	388.2	406.2	424.0	442.8	462.3	482.7	502.2
152.5°	352.1	358.7	367.7	378.6	392.8	408.8	425.3	441.5	459.0	477.4	495.0
155°	364.6	369.5	377.6	386.6	398.8	412.6	426.5	439.5	454.2	469.6	484.3
157.5°	375.4	379.9	386.3	394.1	403.7	415.4	426.5	437.4	449.1	461.6	472.7
160°	382.5	385.8	391.5	398.0	407.0	416.7	426.5	435.5	445.2	455.8	465.5
162.5°	388.4	391.0	396.1	401.9	409.0	418.0	426.5	433.5	441.3	450.6	458.4
165°	396.4	398.0	402.1	406.2	411.0	418.3	424.9	429.7	435.5	442.0	448.5
167.5°	402.9	403.7	406.8	409.1	412.8	418.2	422.9	425.8	429.6	434.1	438.9
170°	406.2	407.0	409.4	411.0	413.4	417.5	421.6	423.2	425.7	428.9	433.0
172.5°	409.4	409.5	411.3	412.3	414.1	416.9	420.3	420.6	421.8	424.4	427.8
175°	412.6	412.6	413.4	414.3	414.3	415.9	418.3	417.5	417.5	419.1	420.8
177.5°	414.3	413.6	414.3	414.3	414.3	414.9	416.2	414.9	414.9	415.6	416.2
180°	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3



TEST NUMBER: P332975-930

CATALOG NUMBER: SA4XXRDIP-C1020D1035U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9
2.5°	1467.5	1469.3	1470.6	1475.1	1475.5	1479.6	1475.5
5°	1588.9	1596.8	1609.2	1621.5	1622.7	1630.5	1616.5
7.5°	1725.0	1743.3	1754.7	1774.7	1782.7	1787.5	1779.5
10°	1818.8	1835.7	1865.6	1880.2	1894.9	1897.1	1890.4
12.5°	1909.4	1936.3	1959.8	1987.5	1986.9	2006.7	1999.5
15°	2030.2	2057.8	2090.4	2121.5	2132.7	2132.7	2141.8
17.5°	2116.3	2166.9	2200.7	2225.0	2251.7	2256.3	2253.2
20°	2174.5	2229.1	2265.2	2296.8	2314.8	2319.9	2319.9
22.5°	2217.7	2264.2	2299.5	2327.8	2342.8	2348.7	2346.9
25°	2247.7	2287.7	2309.2	2317.6	2321.6	2320.4	2309.7
27.5°	2206.7	2204.9	2191.4	2165.4	2145.9	2134.1	2120.6
30°	2128.3	2098.9	2065.1	2027.9	1980.0	1943.3	1932.1
32.5°	2011.4	1945.6	1888.3	1826.4	1774.8	1738.2	1722.9
35°	1785.6	1681.3	1596.2	1521.8	1467.7	1433.9	1422.6
37.5°	1517.5	1416.6	1311.2	1239.1	1194.2	1160.0	1147.3
40°	1347.0	1237.1	1145.3	1077.7	1031.4	998.2	997.6
42.5°	1191.5	1086.5	1000.1	951.4	901.6	879.5	879.5
45°	975.6	891.6	818.4	780.1	750.2	732.1	727.1
47.5°	807.8	738.3	689.5	659.0	634.6	623.1	615.7
50°	713.5	652.6	613.8	587.3	573.7	559.1	558.0
52.5°	635.1	586.0	555.6	534.1	517.0	508.2	508.4
55°	533.8	494.9	473.4	457.1	443.6	436.8	434.0
57.5°	449.6	420.4	404.9	389.9	384.2	378.9	377.4
60°	397.4	377.6	363.0	351.1	342.7	341.0	340.4
62.5°	354.1	333.5	323.3	314.1	307.9	305.3	304.4
65°	292.0	276.7	267.7	260.4	258.1	254.2	253.6
67.5°	235.4	226.2	220.3	215.2	212.1	211.9	211.9
70°	200.6	195.6	190.5	187.7	186.0	184.8	184.8
72.5°	170.9	167.1	163.0	161.5	161.2	160.0	159.6
75°	130.2	126.3	126.8	124.0	121.7	119.0	117.2
77.5°	92.3	89.5	88.9	88.6	86.7	86.3	87.2
80°	71.6	68.7	68.2	68.7	68.2	66.5	66.5
82.5°	54.5	52.1	51.5	51.2	50.6	51.2	50.3
85°	29.3	28.2	28.2	28.2	29.3	28.8	28.2
87.5°	13.5	13.2	13.6	13.4	13.5	12.9	13.4
90°	15.5	16.3	16.3	17.1	17.9	17.1	17.1
92.5°	120.3	95.7	79.4	69.9	65.5	62.7	62.7
95°	477.0	367.9	288.9	249.1	223.8	209.2	198.6
97.5°	844.2	764.6	679.6	621.2	572.2	547.8	530.8
100°	997.8	958.0	897.7	827.0	777.3	752.8	746.4
102.5°	1057.8	1069.3	1044.2	1000.8	964.8	939.1	933.9
105°	1052.4	1132.9	1166.4	1168.0	1161.5	1150.1	1145.2
107.5°	968.6	1082.1	1154.6	1194.8	1213.4	1221.6	1223.7
110°	903.4	1021.5	1111.0	1168.8	1203.0	1217.6	1225.0



TEST NUMBER: P332975-930

CATALOG NUMBER: SA4XXRDIP-C1020D1035U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	846.1	957.7	1047.2	1112.8	1154.1	1174.7	1186.5
115°	780.6	875.8	953.9	1018.2	1067.1	1093.1	1099.6
117.5°	743.1	818.0	884.3	939.1	980.2	1006.5	1011.5
120°	726.8	792.0	849.7	896.1	932.0	953.1	962.1
122.5°	716.4	775.7	826.3	865.5	896.1	914.0	923.0
125°	699.9	756.1	800.9	833.5	857.0	872.5	877.4
127.5°	680.6	736.6	779.1	811.8	832.8	845.8	850.7
130°	665.0	720.3	763.4	796.8	817.2	830.2	835.1
132.5°	647.4	701.4	744.6	777.3	800.2	812.6	817.5
135°	621.0	670.7	711.3	744.0	766.7	779.8	784.6
137.5°	595.8	637.6	674.4	704.8	727.3	738.1	744.0
140°	579.5	616.1	650.3	678.8	696.8	708.1	714.6
142.5°	565.8	597.3	626.9	652.1	668.7	678.8	683.4
145°	547.0	571.4	594.2	614.5	628.4	636.5	640.6
147.5°	530.7	550.2	568.1	583.1	595.0	601.2	602.6
150°	520.9	537.2	551.9	564.8	575.4	580.3	581.1
152.5°	511.1	526.1	538.2	549.3	557.8	560.8	561.6
155°	497.3	509.5	519.3	527.4	533.9	536.4	536.4
157.5°	483.6	493.9	501.7	507.8	512.7	514.2	514.2
160°	474.5	483.5	490.0	494.9	499.8	500.6	500.6
162.5°	466.0	473.0	478.9	482.5	487.4	488.2	487.5
165°	453.4	459.0	463.1	466.4	469.6	468.8	468.0
167.5°	442.6	447.2	449.6	451.3	453.4	453.2	452.6
170°	435.5	438.7	441.2	442.8	443.6	442.8	442.8
172.5°	429.6	431.5	433.3	434.3	435.1	434.3	433.0
175°	421.6	423.2	423.2	423.2	424.9	423.2	421.6
177.5°	416.9	416.9	417.5	416.9	417.5	416.2	414.9
180°	414.3	414.3	414.3	414.3	414.3	414.3	414.3

(END OF REPORT)