

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332528

Luminaire Tested: **SA4XXDIP-C350D1205U835-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332528
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C350D1205U835-4F0-1E-UDD-A4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5881.1 lumens
Efficiency: N/A
Efficacy: 139.4 lumens/watt
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 42.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332528
CATALOG NUMBER: SA4XXDIP-C350D1205U835-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332528

CATALOG NUMBER: SA4XXDIP-C350D1205U835-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	70	70	70	52	52	52	35	35	35	27
1	93	89	85	82	83	79	76	73	62	60	58	46	44	43	31	30	30	23
2	84	77	72	67	75	69	64	60	54	51	48	40	38	36	27	26	25	19
3	77	68	61	56	69	61	55	50	48	44	40	36	33	31	24	23	21	16
4	70	60	53	47	63	54	48	43	43	38	34	32	29	26	22	20	19	14
5	65	54	46	40	57	48	42	37	38	33	30	28	25	23	20	18	16	12
6	59	48	40	35	53	43	36	32	34	29	26	26	22	20	18	16	14	11
7	55	43	36	30	49	39	32	28	31	26	23	23	20	18	16	14	13	10
8	51	39	32	27	45	35	29	24	28	23	20	21	18	16	15	13	11	9
9	47	35	28	23	42	32	26	22	26	21	18	20	16	14	14	12	10	8
10	44	32	26	21	39	29	23	19	24	19	16	18	15	13	13	11	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4612	4612	4612	4612
5°	5431	4624	4081	4624
10°	6503	4604	3674	4604
15°	7694	4557	3375	4557
20°	8568	4509	3107	4509
25°	8706	4440	2922	4440
30°	7408	4373	2864	4373
35°	5695	4263	2864	4263
40°	4440	4135	2918	4135
45°	3701	3942	2967	3942
50°	3258	3706	3067	3706
55°	2985	3424	3191	3424
60°	2796	3171	3339	3171
65°	2604	2888	3463	2888
70°	2379	2608	3541	2608
75°	2127	2296	3500	2296
80°	1781	1883	3389	1883
85°	1315	1362	3242	1362



TEST NUMBER: P332528

CATALOG NUMBER: SA4XXDIP-C350D1205U835-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.7	0.9
10°-20°	171.6	2.9
20°-30°	272.0	4.6
30°-40°	302.8	5.1
40°-50°	275.6	4.7
50°-60°	225.2	3.8
60°-70°	160.8	2.7
70°-80°	88.5	1.5
80°-90°	27.4	0.5
90°-100°	427.2	7.3
100°-110°	889.1	15.1
110°-120°	796.4	13.5
120°-130°	669.9	11.4
130°-140°	558.5	9.5
140°-150°	426.7	7.3
150°-160°	299.9	5.1
160°-170°	176.4	3.0
170°-180°	57.4	1.0
0°-30°	499.3	8.5
0°-40°	802.0	13.6
0°-60°	1302.8	22.2
0°-90°	1579.5	26.9
90°-120°	2112.7	35.9
90°-150°	3767.8	64.1
90°-180°	4302.0	73.1
0°-180°	5881.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	571	571	571	571	571	
5°	670	571	504	571	670	68
15°	921	545	404	545	921	260
25°	977	498	328	498	977	431
35°	578	433	291	433	578	367
45°	324	345	260	345	324	255
55°	212	243	227	243	212	192
65°	136	151	181	151	136	135
75°	68	74	112	74	68	72
85°	14	15	35	15	14	18
90°	24	1	24	1	24	20
95°	284	38	284	38	284	440
105°	1635	136	1635	136	1635	1616
115°	1570	239	1570	239	1570	1558
125°	1253	334	1253	334	1253	1138
135°	1120	396	1120	396	1120	865
145°	914	457	914	457	914	580
155°	766	519	766	519	766	357
165°	668	566	668	566	668	191
175°	602	590	602	590	602	59
180°	592	592	592	592	592	



TEST NUMBER: P332528

CATALOG NUMBER: SA4XXDIP-C350D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3
2.5°	608.0	607.9	606.0	605.6	604.3	602.6	602.2	599.1	593.1	590.2	589.5
5°	670.2	675.0	668.8	667.6	666.9	659.1	655.1	650.4	639.5	633.1	628.1
7.5°	744.5	745.0	742.3	740.2	734.1	727.3	717.1	706.2	693.2	679.8	669.6
10°	793.3	795.2	792.1	791.7	779.6	772.0	756.9	744.1	729.4	713.1	698.2
12.5°	844.8	842.2	840.6	830.5	828.2	814.4	796.8	783.7	761.0	742.2	722.4
15°	920.6	915.4	912.1	898.2	891.3	872.1	853.4	839.0	809.4	781.2	759.9
17.5°	965.1	970.3	962.7	956.9	939.2	925.7	906.6	876.3	853.2	818.2	791.3
20°	997.3	997.8	993.5	987.6	973.7	956.6	935.8	902.7	875.0	840.2	803.2
22.5°	1006.0	1006.1	1004.3	998.8	988.2	974.4	953.4	925.7	892.2	854.4	817.4
25°	977.4	976.5	978.6	984.8	980.8	976.5	964.4	943.8	912.6	872.6	832.8
27.5°	871.2	877.8	889.8	904.9	919.5	930.6	933.7	929.5	910.2	877.3	835.6
30°	794.7	802.8	811.8	826.9	856.3	873.1	891.5	905.5	897.7	871.4	832.6
32.5°	710.7	712.7	726.0	743.2	770.1	802.4	831.7	860.1	869.5	855.7	823.3
35°	577.9	581.3	595.7	612.7	645.6	685.2	729.2	768.5	800.9	813.9	797.3
37.5°	471.6	481.1	491.3	509.6	538.6	574.2	619.9	670.8	719.1	751.5	757.0
40°	421.3	427.2	434.5	448.5	473.1	508.1	547.4	605.6	657.0	703.4	718.5
42.5°	381.5	385.0	389.5	402.1	420.8	455.7	491.6	542.8	594.3	649.8	675.2
45°	324.2	327.8	335.4	342.7	356.9	381.0	414.4	456.5	508.4	561.8	608.7
47.5°	282.9	285.1	289.6	297.5	309.6	325.5	352.6	387.8	435.8	487.8	537.7
50°	259.4	261.3	264.8	271.9	281.2	295.4	317.6	350.5	388.1	440.4	489.4
52.5°	240.8	241.6	244.2	249.0	256.4	268.3	286.6	313.8	348.8	395.4	444.2
55°	212.1	213.0	215.4	218.9	225.3	232.9	246.8	267.2	297.7	338.2	380.6
57.5°	188.4	189.1	191.0	192.4	197.7	203.8	214.6	229.1	252.2	286.6	324.4
60°	173.2	172.8	175.1	176.3	179.9	185.1	193.4	207.3	227.4	255.1	289.9
62.5°	158.5	157.8	159.8	161.4	163.4	167.8	174.6	185.5	201.9	226.9	257.0
65°	136.3	135.4	136.6	138.5	140.3	142.7	147.7	157.4	170.4	188.4	211.3
67.5°	114.1	115.1	115.3	116.2	117.3	120.5	123.9	130.8	140.0	154.4	173.8
70°	100.8	101.1	102.0	102.0	102.7	105.6	108.4	112.4	121.4	134.7	150.5
72.5°	87.6	88.6	88.2	88.9	89.5	91.4	93.4	97.3	104.9	114.8	128.2
75°	68.2	68.9	68.9	69.1	69.8	70.5	72.2	75.0	80.5	87.8	97.0
77.5°	49.7	49.8	50.1	51.0	51.0	52.1	53.3	55.6	58.3	63.3	69.0
80°	38.3	38.8	38.6	39.1	39.1	40.0	40.5	43.3	44.5	47.8	52.3
82.5°	28.1	28.6	28.5	29.2	29.6	29.8	30.4	31.6	32.8	35.7	37.5
85°	14.2	14.7	14.2	14.7	15.4	15.6	16.3	16.6	17.5	18.2	19.9
87.5°	9.0	9.6	9.8	9.8	9.9	10.1	10.1	9.7	10.2	10.6	10.9
90°	24.4	24.4	25.6	24.4	23.2	23.2	22.1	20.9	19.8	20.9	18.6
92.5°	89.5	89.5	93.4	99.7	113.4	136.7	171.7	228.2	307.0	368.6	322.6
95°	283.5	298.6	319.6	355.6	412.5	525.2	680.9	861.0	973.8	947.0	714.6
97.5°	757.9	782.0	816.9	886.8	970.3	1091.6	1205.2	1272.2	1223.4	997.5	668.8
100°	1065.6	1074.9	1109.7	1180.6	1281.7	1367.7	1424.6	1401.4	1231.7	934.2	606.6
102.5°	1333.3	1340.7	1377.4	1428.8	1490.8	1526.6	1510.1	1394.9	1162.0	855.2	564.7
105°	1634.9	1641.9	1658.2	1667.5	1665.1	1617.5	1502.5	1301.4	1035.3	762.3	528.7
107.5°	1747.0	1743.9	1732.3	1705.8	1648.4	1544.8	1382.8	1168.7	933.1	710.2	522.2
110°	1748.8	1738.4	1717.4	1668.6	1586.1	1458.3	1289.8	1088.8	882.0	692.6	524.1



TEST NUMBER: P332528

CATALOG NUMBER: SA4XXDIP-C350D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1694.0	1677.0	1647.7	1588.7	1495.0	1367.2	1208.0	1030.2	853.1	684.2	529.6
115°	1569.9	1560.6	1523.4	1453.7	1361.9	1250.3	1114.4	971.4	826.2	679.8	540.3
117.5°	1444.1	1436.9	1399.3	1340.7	1262.4	1167.8	1060.9	942.6	814.1	678.6	551.7
120°	1373.5	1360.7	1330.5	1279.4	1213.1	1130.6	1037.7	929.6	807.6	678.6	560.1
122.5°	1317.7	1304.9	1279.4	1235.7	1179.7	1107.4	1022.8	918.4	800.2	677.7	568.5
125°	1252.6	1245.7	1223.6	1189.9	1143.4	1079.5	999.3	899.4	787.8	676.3	581.0
127.5°	1214.5	1207.6	1189.0	1159.0	1112.3	1051.6	971.7	876.1	771.3	673.7	591.0
130°	1192.2	1185.2	1166.6	1137.6	1090.0	1028.4	949.4	857.6	761.1	672.8	598.4
132.5°	1167.1	1160.1	1142.5	1109.7	1063.0	1001.4	924.3	838.0	751.8	671.9	604.9
135°	1120.2	1113.2	1094.6	1062.1	1015.6	957.5	886.6	811.1	737.9	670.5	614.7
137.5°	1062.1	1053.7	1038.4	1006.3	962.8	910.3	850.6	786.7	725.8	670.2	620.5
140°	1020.2	1010.9	994.7	969.1	928.4	879.6	827.3	772.7	719.3	669.3	625.2
142.5°	975.6	969.1	954.7	931.0	895.0	852.7	807.8	759.7	713.7	669.3	628.9
145°	914.5	908.7	897.1	877.3	848.3	815.7	780.9	741.4	704.2	667.0	631.0
147.5°	860.3	858.3	849.4	832.5	811.1	785.5	757.6	726.3	695.6	662.8	632.1
150°	829.7	828.5	821.5	806.4	787.8	766.9	743.7	717.0	689.1	660.0	632.1
152.5°	801.8	800.6	796.4	784.1	768.3	751.1	729.7	706.7	681.6	655.4	630.3
155°	765.8	765.8	762.3	753.0	741.4	727.4	710.0	691.4	670.5	648.4	627.5
157.5°	734.2	734.2	732.1	725.1	716.3	705.1	690.5	674.9	659.1	641.2	624.5
160°	714.6	714.6	713.5	706.5	699.5	690.2	677.4	664.7	650.7	635.6	621.7
162.5°	696.0	697.0	695.8	688.8	683.7	675.4	665.4	654.4	643.3	630.0	618.9
165°	668.2	669.3	670.5	665.8	661.2	655.4	647.2	640.3	631.0	621.7	613.5
167.5°	646.1	647.0	647.2	644.2	641.9	638.4	631.9	626.6	619.8	613.3	608.0
170°	632.1	632.1	633.3	632.1	629.8	626.3	621.7	618.2	612.4	607.7	604.2
172.5°	618.2	620.0	621.2	620.0	618.6	616.1	613.3	610.7	605.9	602.1	600.5
175°	601.9	604.2	606.6	604.2	604.2	604.2	601.9	600.8	598.4	596.1	596.1
177.5°	592.4	594.2	596.1	595.2	596.1	595.2	595.2	594.2	593.3	592.4	592.4
180°	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5



TEST NUMBER: P332528

CATALOG NUMBER: SA4XXDIP-C350D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3
2.5°	589.7	587.0	585.1	583.6	579.5	577.0	575.1	572.5	569.4	566.2	562.2
5°	623.1	615.1	609.2	600.2	591.7	584.6	577.2	570.6	562.6	553.8	547.4
7.5°	658.3	646.3	631.0	617.7	602.7	589.7	578.1	566.2	553.8	541.7	530.7
10°	680.7	665.3	648.2	628.1	609.2	592.4	576.8	561.6	546.9	532.3	519.7
12.5°	704.7	685.5	660.3	636.8	615.6	593.1	574.3	555.7	538.0	522.6	508.0
15°	737.0	709.3	680.2	648.7	620.8	594.5	568.7	545.3	525.4	505.0	490.8
17.5°	756.8	722.5	689.3	656.4	622.6	589.4	561.6	534.6	509.7	489.5	471.6
20°	769.9	735.8	694.4	661.5	621.3	587.2	555.0	524.9	498.9	477.4	458.9
22.5°	781.2	741.9	700.4	657.1	617.1	580.9	545.7	515.5	488.9	466.2	448.5
25°	787.4	742.2	697.2	654.1	608.7	565.9	533.9	498.4	470.0	446.1	427.2
27.5°	788.1	739.7	688.8	641.0	594.1	554.2	513.9	482.1	452.7	427.4	409.2
30°	786.0	735.6	680.9	629.1	582.0	538.7	503.6	469.1	439.0	413.9	395.0
32.5°	779.3	726.9	670.7	615.8	567.0	524.6	488.5	455.6	426.3	401.6	381.7
35°	760.2	708.3	648.5	591.4	541.5	498.7	466.0	432.6	403.3	379.9	360.7
37.5°	730.2	683.4	622.5	563.5	514.4	471.4	439.0	408.9	382.4	358.6	339.0
40°	704.1	662.9	601.8	544.3	491.3	450.4	420.1	392.4	366.1	343.6	324.9
42.5°	674.0	638.1	581.8	520.9	469.7	428.6	399.1	374.2	349.5	328.7	310.0
45°	620.3	596.6	543.6	487.3	434.0	395.2	367.1	345.3	324.5	304.1	288.5
47.5°	558.6	546.8	502.2	448.7	398.2	359.9	335.5	315.4	297.1	279.9	266.1
50°	517.1	511.4	472.9	421.3	373.0	337.0	312.4	295.1	279.5	264.4	251.3
52.5°	476.2	476.0	441.2	394.0	349.3	314.7	290.2	274.1	260.6	248.3	236.6
55°	413.7	420.3	393.1	351.0	311.0	279.7	257.7	243.3	233.8	223.7	214.9
57.5°	356.3	367.3	344.8	307.7	274.3	245.6	226.4	215.6	205.5	199.3	192.9
60°	318.8	329.2	311.7	280.5	249.0	224.4	206.1	196.4	187.7	183.4	178.9
62.5°	285.5	294.7	281.8	252.8	225.5	201.8	186.4	177.1	171.2	166.6	163.6
65°	237.9	245.7	234.5	213.5	190.0	171.1	158.6	151.2	145.6	143.7	140.3
67.5°	192.3	199.4	193.4	175.5	156.7	142.3	132.5	125.5	122.1	120.5	118.1
70°	165.2	172.3	165.9	150.3	135.8	123.8	114.5	110.5	107.0	106.3	103.0
72.5°	142.3	147.1	140.7	128.5	116.2	106.0	98.8	94.6	92.8	91.5	89.7
75°	106.7	111.0	106.7	97.3	88.5	81.4	75.3	73.6	71.5	70.8	69.6
77.5°	75.5	79.2	76.0	70.1	63.5	58.0	54.7	52.6	52.1	50.9	51.5
80°	57.7	60.1	57.0	53.0	47.8	44.0	41.7	40.5	39.1	38.6	39.5
82.5°	41.5	42.5	40.9	38.2	34.4	31.9	30.3	28.9	28.6	28.7	28.7
85°	21.5	21.3	21.1	18.7	17.5	15.9	14.9	14.7	14.4	14.9	15.4
87.5°	10.4	10.6	9.1	8.3	7.5	6.7	5.8	5.2	5.8	6.7	7.1
90°	16.3	16.3	9.3	9.3	8.1	7.0	3.5	1.2	3.5	7.0	8.1
92.5°	234.7	144.6	85.5	61.4	44.4	30.2	19.3	13.2	19.3	30.2	44.4
95°	436.9	246.3	145.3	96.4	68.6	53.5	41.8	38.3	41.8	53.5	68.6
97.5°	392.8	235.4	157.6	116.7	92.7	78.8	68.8	68.8	68.8	78.8	92.7
100°	369.5	238.2	169.7	132.5	110.4	96.4	88.3	88.3	88.3	96.4	110.4
102.5°	363.0	247.5	185.5	150.1	129.0	116.0	108.8	106.9	108.8	116.0	129.0
105°	366.0	269.6	213.8	180.1	159.2	145.3	139.4	136.0	139.4	145.3	159.2
107.5°	383.2	295.4	244.3	211.0	191.0	176.2	170.3	168.0	170.3	176.2	191.0
110°	396.2	314.9	263.8	232.4	211.5	197.5	191.7	189.4	191.7	197.5	211.5



TEST NUMBER: P332528

CATALOG NUMBER: SA4XXDIP-C350D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	410.2	333.5	284.2	252.9	231.9	218.9	212.2	209.9	212.2	218.9	231.9
115°	432.3	362.5	316.1	284.7	262.6	251.0	242.9	239.4	242.9	251.0	262.6
117.5°	454.8	390.7	346.5	314.0	293.3	280.5	273.3	270.0	273.3	280.5	293.3
120°	470.6	410.2	366.0	333.5	313.7	301.0	292.8	290.5	292.8	301.0	313.7
122.5°	485.5	428.8	384.6	353.0	331.4	319.6	311.4	309.1	311.4	319.6	331.4
125°	507.8	454.3	412.5	380.0	357.9	345.1	338.1	333.5	338.1	345.1	357.9
127.5°	527.1	478.0	437.6	404.8	381.8	367.2	358.8	355.1	358.8	367.2	381.8
130°	539.2	493.9	454.3	420.6	398.6	381.1	371.8	367.2	371.8	381.1	398.6
132.5°	551.3	506.9	467.4	435.5	411.6	395.1	383.0	379.3	383.0	395.1	411.6
135°	567.1	525.2	486.9	456.7	432.3	412.5	400.9	396.2	400.9	412.5	432.3
137.5°	578.2	539.2	503.4	474.6	449.2	430.4	417.6	413.2	417.6	430.4	449.2
140°	585.6	548.5	513.6	485.7	461.3	441.6	428.8	425.3	428.8	441.6	461.3
142.5°	591.2	556.8	522.9	495.9	472.5	453.6	441.8	438.3	441.8	453.6	472.5
145°	597.3	565.9	535.7	510.1	488.0	471.8	460.2	456.7	460.2	471.8	488.0
147.5°	602.6	575.2	546.8	523.8	505.5	488.7	478.5	477.3	478.5	488.7	505.5
150°	605.4	579.8	554.3	532.2	514.8	500.8	491.5	490.4	491.5	500.8	514.8
152.5°	607.3	583.6	560.8	540.6	525.0	512.0	502.7	502.4	502.7	512.0	525.0
155°	608.9	589.1	569.4	552.0	539.2	527.5	520.6	519.4	520.6	527.5	539.2
157.5°	608.9	593.1	576.4	562.6	551.5	542.4	535.9	535.9	535.9	542.4	551.5
160°	608.9	594.9	581.0	568.2	558.9	550.8	546.1	546.1	546.1	550.8	558.9
162.5°	608.9	596.8	583.8	573.8	565.4	558.2	554.5	555.4	554.5	558.2	565.4
165°	606.6	597.3	586.8	579.8	574.0	568.2	565.9	565.9	565.9	568.2	574.0
167.5°	603.8	597.0	589.4	584.0	580.8	576.4	575.2	576.4	575.2	576.4	580.8
170°	601.9	596.1	590.3	586.8	584.5	581.0	579.8	581.0	579.8	581.0	584.5
172.5°	600.1	595.2	591.2	588.7	587.3	584.7	584.5	585.6	584.5	584.7	587.3
175°	597.3	593.8	591.5	591.5	590.3	589.1	589.1	590.3	589.1	589.1	590.3
177.5°	594.2	592.4	591.5	591.5	591.5	590.5	591.5	592.4	591.5	590.5	591.5
180°	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5



TEST NUMBER: P332528

CATALOG NUMBER: SA4XXDIP-C350D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3
2.5°	560.3	558.6	556.2	552.8	549.9	546.9	546.1	545.0	547.3	545.4	544.8
5°	542.0	537.0	530.6	523.3	519.0	512.9	511.7	509.3	506.9	506.7	504.3
7.5°	522.5	515.2	506.8	499.4	492.5	485.7	481.3	480.4	476.9	474.8	472.5
10°	510.0	501.0	491.3	484.2	476.2	469.1	464.1	461.3	458.9	456.3	453.9
12.5°	495.3	485.7	477.7	470.0	460.5	455.1	446.9	442.0	441.5	441.5	435.4
15°	478.1	468.6	456.3	445.4	440.2	429.8	425.3	419.6	416.1	412.5	409.7
17.5°	458.4	446.6	437.0	424.5	414.6	406.3	400.4	397.0	391.6	386.6	383.0
20°	446.1	433.6	423.4	410.1	399.3	389.1	384.1	379.4	375.4	371.1	367.1
22.5°	433.6	420.5	408.1	395.2	385.1	374.3	369.5	363.1	359.3	356.9	352.9
25°	413.9	399.7	385.5	373.2	362.8	353.3	347.0	342.0	337.7	335.8	333.2
27.5°	392.5	378.4	364.7	350.7	338.9	332.0	326.9	323.2	320.7	318.2	317.0
30°	378.9	364.2	349.6	336.5	325.7	318.8	314.1	311.5	309.6	308.4	307.2
32.5°	365.1	350.6	335.2	323.3	313.5	307.4	303.8	301.2	300.3	299.9	299.4
35°	342.9	328.3	314.1	303.4	294.2	291.8	288.7	287.3	286.8	288.5	289.2
37.5°	321.5	307.9	294.8	284.5	278.4	275.0	273.9	274.0	275.7	277.1	278.8
40°	307.7	294.4	282.1	273.1	267.4	265.3	264.8	266.0	267.9	269.6	271.5
42.5°	294.2	281.2	270.0	261.6	257.6	255.6	255.9	257.1	259.8	261.8	264.6
45°	273.4	262.5	251.6	244.7	241.4	241.9	241.9	244.0	246.6	249.7	252.8
47.5°	253.7	242.7	233.8	228.0	226.3	225.9	227.2	230.0	233.7	237.5	241.8
50°	240.5	230.0	222.2	217.0	215.1	215.8	217.7	220.3	224.8	229.6	234.1
52.5°	227.0	217.5	210.3	205.5	204.1	205.4	207.3	211.4	215.4	220.5	225.9
55°	206.1	198.1	192.4	188.9	188.4	189.1	191.2	195.7	201.4	207.8	213.0
57.5°	185.4	178.6	173.4	171.0	171.2	171.9	175.4	180.7	186.8	193.6	200.3
60°	171.3	165.2	160.9	159.0	159.3	160.7	165.0	169.9	177.5	184.1	191.2
62.5°	158.1	152.7	148.6	146.9	146.6	149.7	153.8	158.9	166.5	173.9	181.6
65°	136.8	132.5	129.2	128.3	129.0	131.4	136.6	143.4	149.8	157.6	165.7
67.5°	116.0	112.5	110.2	110.6	111.5	115.0	119.3	125.2	132.5	140.6	148.5
70°	102.7	99.4	97.5	97.7	99.2	103.4	107.2	113.1	120.9	129.2	135.8
72.5°	89.1	86.9	85.2	86.2	87.6	90.5	95.3	101.2	108.1	115.8	122.8
75°	68.4	68.4	67.5	68.2	70.3	73.1	76.7	82.8	89.7	95.9	101.5
77.5°	50.7	50.2	50.8	51.7	52.9	56.3	60.4	64.8	69.9	76.1	80.8
80°	38.8	39.1	40.2	41.7	42.1	44.7	49.0	53.0	57.0	62.2	66.7
82.5°	29.2	29.4	30.0	31.8	32.3	35.1	37.8	41.8	45.5	49.0	52.7
85°	15.9	15.9	17.0	17.8	18.9	20.8	22.5	24.9	28.2	30.5	34.1
87.5°	7.9	7.9	10.1	10.4	11.5	12.9	13.0	15.4	16.3	17.5	19.2
90°	9.3	9.3	16.3	16.3	18.6	20.9	19.8	20.9	22.1	23.2	23.2
92.5°	61.4	85.5	144.6	234.7	322.6	368.6	307.0	228.2	171.7	136.7	113.4
95°	96.4	145.3	246.3	436.9	714.6	947.0	973.8	861.0	680.9	525.2	412.5
97.5°	116.7	157.6	235.4	392.8	668.8	997.5	1223.4	1272.2	1205.2	1091.6	970.3
100°	132.5	169.7	238.2	369.5	606.6	934.2	1231.7	1401.4	1424.6	1367.7	1281.7
102.5°	150.1	185.5	247.5	363.0	564.7	855.2	1162.0	1394.9	1510.1	1526.6	1490.8
105°	180.1	213.8	269.6	366.0	528.7	762.3	1035.3	1301.4	1502.5	1617.5	1665.1
107.5°	211.0	244.3	295.4	383.2	522.2	710.2	933.1	1168.7	1382.8	1544.8	1648.4
110°	232.4	263.8	314.9	396.2	524.1	692.6	882.0	1088.8	1289.8	1458.3	1586.1



TEST NUMBER: P332528

CATALOG NUMBER: SA4XXDIP-C350D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	252.9	284.2	333.5	410.2	529.6	684.2	853.1	1030.2	1208.0	1367.2	1495.0
115°	284.7	316.1	362.5	432.3	540.3	679.8	826.2	971.4	1114.4	1250.3	1361.9
117.5°	314.0	346.5	390.7	454.8	551.7	678.6	814.1	942.6	1060.9	1167.8	1262.4
120°	333.5	366.0	410.2	470.6	560.1	678.6	807.6	929.6	1037.7	1130.6	1213.1
122.5°	353.0	384.6	428.8	485.5	568.5	677.7	800.2	918.4	1022.8	1107.4	1179.7
125°	380.0	412.5	454.3	507.8	581.0	676.3	787.8	899.4	999.3	1079.5	1143.4
127.5°	404.8	437.6	478.0	527.1	591.0	673.7	771.3	876.1	971.7	1051.6	1112.3
130°	420.6	454.3	493.9	539.2	598.4	672.8	761.1	857.6	949.4	1028.4	1090.0
132.5°	435.5	467.4	506.9	551.3	604.9	671.9	751.8	838.0	924.3	1001.4	1063.0
135°	456.7	486.9	525.2	567.1	614.7	670.5	737.9	811.1	886.6	957.5	1015.6
137.5°	474.6	503.4	539.2	578.2	620.5	670.2	725.8	786.7	850.6	910.3	962.8
140°	485.7	513.6	548.5	585.6	625.2	669.3	719.3	772.7	827.3	879.6	928.4
142.5°	495.9	522.9	556.8	591.2	628.9	669.3	713.7	759.7	807.8	852.7	895.0
145°	510.1	535.7	565.9	597.3	631.0	667.0	704.2	741.4	780.9	815.7	848.3
147.5°	523.8	546.8	575.2	602.6	632.1	662.8	695.6	726.3	757.6	785.5	811.1
150°	532.2	554.3	579.8	605.4	632.1	660.0	689.1	717.0	743.7	766.9	787.8
152.5°	540.6	560.8	583.6	607.3	630.3	655.4	681.6	706.7	729.7	751.1	768.3
155°	552.0	569.4	589.1	608.9	627.5	648.4	670.5	691.4	710.0	727.4	741.4
157.5°	562.6	576.4	593.1	608.9	624.5	641.2	659.1	674.9	690.5	705.1	716.3
160°	568.2	581.0	594.9	608.9	621.7	635.6	650.7	664.7	677.4	690.2	699.5
162.5°	573.8	583.8	596.8	608.9	618.9	630.0	643.3	654.4	665.4	675.4	683.7
165°	579.8	586.8	597.3	606.6	613.5	621.7	631.0	640.3	647.2	655.4	661.2
167.5°	584.0	589.4	597.0	603.8	608.0	613.3	619.8	626.6	631.9	638.4	641.9
170°	586.8	590.3	596.1	601.9	604.2	607.7	612.4	618.2	621.7	626.3	629.8
172.5°	588.7	591.2	595.2	600.1	600.5	602.1	605.9	610.7	613.3	616.1	618.6
175°	591.5	591.5	593.8	597.3	596.1	596.1	598.4	600.8	601.9	604.2	604.2
177.5°	591.5	591.5	592.4	594.2	592.4	592.4	593.3	594.2	595.2	595.2	596.1
180°	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5



TEST NUMBER: P332528

CATALOG NUMBER: SA4XXDIP-C350D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3
2.5°	544.4	544.1	542.7	542.5	542.7	544.1	544.4	544.8	545.4	547.3	545.0
5°	502.9	501.7	501.0	503.6	501.0	501.7	502.9	504.3	506.7	506.9	509.3
7.5°	471.6	470.7	468.6	467.9	468.6	470.7	471.6	472.5	474.8	476.9	480.4
10°	451.6	450.6	448.7	448.2	448.7	450.6	451.6	453.9	456.3	458.9	461.3
12.5°	432.2	430.4	430.0	430.5	430.0	430.4	432.2	435.4	441.5	441.5	442.0
15°	406.6	405.6	403.0	403.8	403.0	405.6	406.6	409.7	412.5	416.1	419.6
17.5°	381.3	380.2	377.0	379.8	377.0	380.2	381.3	383.0	386.6	391.6	397.0
20°	365.4	363.5	361.9	361.6	361.9	363.5	365.4	367.1	371.1	375.4	379.4
22.5°	350.3	348.6	348.4	346.9	348.4	348.6	350.3	352.9	356.9	359.3	363.1
25°	331.3	329.7	329.2	328.0	329.2	329.7	331.3	333.2	335.8	337.7	342.0
27.5°	316.8	316.0	315.1	315.5	315.1	316.0	316.8	317.0	318.2	320.7	323.2
30°	307.9	307.7	307.2	307.2	307.2	307.7	307.9	307.2	308.4	309.6	311.5
32.5°	300.5	300.5	300.8	300.8	300.8	300.5	300.5	299.4	299.9	300.3	301.2
35°	290.2	290.9	291.3	290.6	291.3	290.9	290.2	289.2	288.5	286.8	287.3
37.5°	280.8	281.5	282.2	283.0	282.2	281.5	280.8	278.8	277.1	275.7	274.0
40°	273.6	275.2	275.7	276.9	275.7	275.2	273.6	271.5	269.6	267.9	266.0
42.5°	266.8	268.6	269.8	270.1	269.8	268.6	266.8	264.6	261.8	259.8	257.1
45°	256.3	258.2	259.9	259.9	259.9	258.2	256.3	252.8	249.7	246.6	244.0
47.5°	245.5	248.2	249.9	250.3	249.9	248.2	245.5	241.8	237.5	233.7	230.0
50°	238.1	241.4	243.1	244.2	243.1	241.4	238.1	234.1	229.6	224.8	220.3
52.5°	230.9	234.2	236.4	237.0	236.4	234.2	230.9	225.9	220.5	215.4	211.4
55°	218.4	223.2	225.8	226.7	225.8	223.2	218.4	213.0	207.8	201.4	195.7
57.5°	206.7	211.1	214.1	214.8	214.1	211.1	206.7	200.3	193.6	186.8	180.7
60°	197.6	202.4	206.1	206.8	206.1	202.4	197.6	191.2	184.1	177.5	169.9
62.5°	188.3	193.3	196.7	198.5	196.7	193.3	188.3	181.6	173.9	166.5	158.9
65°	172.3	177.3	180.6	181.3	180.6	177.3	172.3	165.7	157.6	149.8	143.4
67.5°	154.8	159.8	161.9	163.3	161.9	159.8	154.8	148.5	140.6	132.5	125.2
70°	142.5	146.5	148.9	150.0	148.9	146.5	142.5	135.8	129.2	120.9	113.1
72.5°	128.5	132.7	135.4	135.7	135.4	132.7	128.5	122.8	115.8	108.1	101.2
75°	107.0	110.8	112.2	112.2	112.2	110.8	107.0	101.5	95.9	89.7	82.8
77.5°	84.7	86.6	88.4	88.8	88.4	86.6	84.7	80.8	76.1	69.9	64.8
80°	70.3	71.5	72.9	72.9	72.9	71.5	70.3	66.7	62.2	57.0	53.0
82.5°	55.5	56.5	57.9	57.7	57.9	56.5	55.5	52.7	49.0	45.5	41.8
85°	33.6	35.7	35.5	35.0	35.5	35.7	33.6	34.1	30.5	28.2	24.9
87.5°	20.0	20.4	20.8	21.2	20.8	20.4	20.0	19.2	17.5	16.3	15.4
90°	24.4	25.6	24.4	24.4	24.4	25.6	24.4	23.2	23.2	22.1	20.9
92.5°	99.7	93.4	89.5	89.5	89.5	93.4	99.7	113.4	136.7	171.7	228.2
95°	355.6	319.6	298.6	283.5	298.6	319.6	355.6	412.5	525.2	680.9	861.0
97.5°	886.8	816.9	782.0	757.9	782.0	816.9	886.8	970.3	1091.6	1205.2	1272.2
100°	1180.6	1109.7	1074.9	1065.6	1074.9	1109.7	1180.6	1281.7	1367.7	1424.6	1401.4
102.5°	1428.8	1377.4	1340.7	1333.3	1340.7	1377.4	1428.8	1490.8	1526.6	1510.1	1394.9
105°	1667.5	1658.2	1641.9	1634.9	1641.9	1658.2	1667.5	1665.1	1617.5	1502.5	1301.4
107.5°	1705.8	1732.3	1743.9	1747.0	1743.9	1732.3	1705.8	1648.4	1544.8	1382.8	1168.7
110°	1668.6	1717.4	1738.4	1748.8	1738.4	1717.4	1668.6	1586.1	1458.3	1289.8	1088.8



TEST NUMBER: P332528

CATALOG NUMBER: SA4XXDIP-C350D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1588.7	1647.7	1677.0	1694.0	1677.0	1647.7	1588.7	1495.0	1367.2	1208.0	1030.2
115°	1453.7	1523.4	1560.6	1569.9	1560.6	1523.4	1453.7	1361.9	1250.3	1114.4	971.4
117.5°	1340.7	1399.3	1436.9	1444.1	1436.9	1399.3	1340.7	1262.4	1167.8	1060.9	942.6
120°	1279.4	1330.5	1360.7	1373.5	1360.7	1330.5	1279.4	1213.1	1130.6	1037.7	929.6
122.5°	1235.7	1279.4	1304.9	1317.7	1304.9	1279.4	1235.7	1179.7	1107.4	1022.8	918.4
125°	1189.9	1223.6	1245.7	1252.6	1245.7	1223.6	1189.9	1143.4	1079.5	999.3	899.4
127.5°	1159.0	1189.0	1207.6	1214.5	1207.6	1189.0	1159.0	1112.3	1051.6	971.7	876.1
130°	1137.6	1166.6	1185.2	1192.2	1185.2	1166.6	1137.6	1090.0	1028.4	949.4	857.6
132.5°	1109.7	1142.5	1160.1	1167.1	1160.1	1142.5	1109.7	1063.0	1001.4	924.3	838.0
135°	1062.1	1094.6	1113.2	1120.2	1113.2	1094.6	1062.1	1015.6	957.5	886.6	811.1
137.5°	1006.3	1038.4	1053.7	1062.1	1053.7	1038.4	1006.3	962.8	910.3	850.6	786.7
140°	969.1	994.7	1010.9	1020.2	1010.9	994.7	969.1	928.4	879.6	827.3	772.7
142.5°	931.0	954.7	969.1	975.6	969.1	954.7	931.0	895.0	852.7	807.8	759.7
145°	877.3	897.1	908.7	914.5	908.7	897.1	877.3	848.3	815.7	780.9	741.4
147.5°	832.5	849.4	858.3	860.3	858.3	849.4	832.5	811.1	785.5	757.6	726.3
150°	806.4	821.5	828.5	829.7	828.5	821.5	806.4	787.8	766.9	743.7	717.0
152.5°	784.1	796.4	800.6	801.8	800.6	796.4	784.1	768.3	751.1	729.7	706.7
155°	753.0	762.3	765.8	765.8	765.8	762.3	753.0	741.4	727.4	710.0	691.4
157.5°	725.1	732.1	734.2	734.2	734.2	732.1	725.1	716.3	705.1	690.5	674.9
160°	706.5	713.5	714.6	714.6	714.6	713.5	706.5	699.5	690.2	677.4	664.7
162.5°	688.8	695.8	697.0	696.0	697.0	695.8	688.8	683.7	675.4	665.4	654.4
165°	665.8	670.5	669.3	668.2	669.3	670.5	665.8	661.2	655.4	647.2	640.3
167.5°	644.2	647.2	647.0	646.1	647.0	647.2	644.2	641.9	638.4	631.9	626.6
170°	632.1	633.3	632.1	632.1	632.1	633.3	632.1	629.8	626.3	621.7	618.2
172.5°	620.0	621.2	620.0	618.2	620.0	621.2	620.0	618.6	616.1	613.3	610.7
175°	604.2	606.6	604.2	601.9	604.2	606.6	604.2	604.2	604.2	601.9	600.8
177.5°	595.2	596.1	594.2	592.4	594.2	596.1	595.2	596.1	595.2	595.2	594.2
180°	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5



TEST NUMBER: P332528

CATALOG NUMBER: SA4XXDIP-C350D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3
2.5°	546.1	546.9	549.9	552.8	556.2	558.6	560.3	562.2	566.2	569.4	572.5
5°	511.7	512.9	519.0	523.3	530.6	537.0	542.0	547.4	553.8	562.6	570.6
7.5°	481.3	485.7	492.5	499.4	506.8	515.2	522.5	530.7	541.7	553.8	566.2
10°	464.1	469.1	476.2	484.2	491.3	501.0	510.0	519.7	532.3	546.9	561.6
12.5°	446.9	455.1	460.5	470.0	477.7	485.7	495.3	508.0	522.6	538.0	555.7
15°	425.3	429.8	440.2	445.4	456.3	468.6	478.1	490.8	505.0	525.4	545.3
17.5°	400.4	406.3	414.6	424.5	437.0	446.6	458.4	471.6	489.5	509.7	534.6
20°	384.1	389.1	399.3	410.1	423.4	433.6	446.1	458.9	477.4	498.9	524.9
22.5°	369.5	374.3	385.1	395.2	408.1	420.5	433.6	448.5	466.2	488.9	515.5
25°	347.0	353.3	362.8	373.2	385.5	399.7	413.9	427.2	446.1	470.0	498.4
27.5°	326.9	332.0	338.9	350.7	364.7	378.4	392.5	409.2	427.4	452.7	482.1
30°	314.1	318.8	325.7	336.5	349.6	364.2	378.9	395.0	413.9	439.0	469.1
32.5°	303.8	307.4	313.5	323.3	335.2	350.6	365.1	381.7	401.6	426.3	455.6
35°	288.7	291.8	294.2	303.4	314.1	328.3	342.9	360.7	379.9	403.3	432.6
37.5°	273.9	275.0	278.4	284.5	294.8	307.9	321.5	339.0	358.6	382.4	408.9
40°	264.8	265.3	267.4	273.1	282.1	294.4	307.7	324.9	343.6	366.1	392.4
42.5°	255.9	255.6	257.6	261.6	270.0	281.2	294.2	310.0	328.7	349.5	374.2
45°	241.9	241.9	241.4	244.7	251.6	262.5	273.4	288.5	304.1	324.5	345.3
47.5°	227.2	225.9	226.3	228.0	233.8	242.7	253.7	266.1	279.9	297.1	315.4
50°	217.7	215.8	215.1	217.0	222.2	230.0	240.5	251.3	264.4	279.5	295.1
52.5°	207.3	205.4	204.1	205.5	210.3	217.5	227.0	236.6	248.3	260.6	274.1
55°	191.2	189.1	188.4	188.9	192.4	198.1	206.1	214.9	223.7	233.8	243.3
57.5°	175.4	171.9	171.2	171.0	173.4	178.6	185.4	192.9	199.3	205.5	215.6
60°	165.0	160.7	159.3	159.0	160.9	165.2	171.3	178.9	183.4	187.7	196.4
62.5°	153.8	149.7	146.6	146.9	148.6	152.7	158.1	163.6	166.6	171.2	177.1
65°	136.6	131.4	129.0	128.3	129.2	132.5	136.8	140.3	143.7	145.6	151.2
67.5°	119.3	115.0	111.5	110.6	110.2	112.5	116.0	118.1	120.5	122.1	125.5
70°	107.2	103.4	99.2	97.7	97.5	99.4	102.7	103.0	106.3	107.0	110.5
72.5°	95.3	90.5	87.6	86.2	85.2	86.9	89.1	89.7	91.5	92.8	94.6
75°	76.7	73.1	70.3	68.2	67.5	68.4	68.4	69.6	70.8	71.5	73.6
77.5°	60.4	56.3	52.9	51.7	50.8	50.2	50.7	51.5	50.9	52.1	52.6
80°	49.0	44.7	42.1	41.7	40.2	39.1	38.8	39.5	38.6	39.1	40.5
82.5°	37.8	35.1	32.3	31.8	30.0	29.4	29.2	28.7	28.7	28.6	28.9
85°	22.5	20.8	18.9	17.8	17.0	15.9	15.9	15.4	14.9	14.4	14.7
87.5°	13.0	12.9	11.5	10.4	10.1	7.9	7.9	7.1	6.7	5.8	5.2
90°	19.8	20.9	18.6	16.3	16.3	9.3	9.3	8.1	7.0	3.5	1.2
92.5°	307.0	368.6	322.6	234.7	144.6	85.5	61.4	44.4	30.2	19.3	13.2
95°	973.8	947.0	714.6	436.9	246.3	145.3	96.4	68.6	53.5	41.8	38.3
97.5°	1223.4	997.5	668.8	392.8	235.4	157.6	116.7	92.7	78.8	68.8	68.8
100°	1231.7	934.2	606.6	369.5	238.2	169.7	132.5	110.4	96.4	88.3	88.3
102.5°	1162.0	855.2	564.7	363.0	247.5	185.5	150.1	129.0	116.0	108.8	106.9
105°	1035.3	762.3	528.7	366.0	269.6	213.8	180.1	159.2	145.3	139.4	136.0
107.5°	933.1	710.2	522.2	383.2	295.4	244.3	211.0	191.0	176.2	170.3	168.0
110°	882.0	692.6	524.1	396.2	314.9	263.8	232.4	211.5	197.5	191.7	189.4



TEST NUMBER: P332528

CATALOG NUMBER: SA4XXDIP-C350D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	853.1	684.2	529.6	410.2	333.5	284.2	252.9	231.9	218.9	212.2	209.9
115°	826.2	679.8	540.3	432.3	362.5	316.1	284.7	262.6	251.0	242.9	239.4
117.5°	814.1	678.6	551.7	454.8	390.7	346.5	314.0	293.3	280.5	273.3	270.0
120°	807.6	678.6	560.1	470.6	410.2	366.0	333.5	313.7	301.0	292.8	290.5
122.5°	800.2	677.7	568.5	485.5	428.8	384.6	353.0	331.4	319.6	311.4	309.1
125°	787.8	676.3	581.0	507.8	454.3	412.5	380.0	357.9	345.1	338.1	333.5
127.5°	771.3	673.7	591.0	527.1	478.0	437.6	404.8	381.8	367.2	358.8	355.1
130°	761.1	672.8	598.4	539.2	493.9	454.3	420.6	398.6	381.1	371.8	367.2
132.5°	751.8	671.9	604.9	551.3	506.9	467.4	435.5	411.6	395.1	383.0	379.3
135°	737.9	670.5	614.7	567.1	525.2	486.9	456.7	432.3	412.5	400.9	396.2
137.5°	725.8	670.2	620.5	578.2	539.2	503.4	474.6	449.2	430.4	417.6	413.2
140°	719.3	669.3	625.2	585.6	548.5	513.6	485.7	461.3	441.6	428.8	425.3
142.5°	713.7	669.3	628.9	591.2	556.8	522.9	495.9	472.5	453.6	441.8	438.3
145°	704.2	667.0	631.0	597.3	565.9	535.7	510.1	488.0	471.8	460.2	456.7
147.5°	695.6	662.8	632.1	602.6	575.2	546.8	523.8	505.5	488.7	478.5	477.3
150°	689.1	660.0	632.1	605.4	579.8	554.3	532.2	514.8	500.8	491.5	490.4
152.5°	681.6	655.4	630.3	607.3	583.6	560.8	540.6	525.0	512.0	502.7	502.4
155°	670.5	648.4	627.5	608.9	589.1	569.4	552.0	539.2	527.5	520.6	519.4
157.5°	659.1	641.2	624.5	608.9	593.1	576.4	562.6	551.5	542.4	535.9	535.9
160°	650.7	635.6	621.7	608.9	594.9	581.0	568.2	558.9	550.8	546.1	546.1
162.5°	643.3	630.0	618.9	608.9	596.8	583.8	573.8	565.4	558.2	554.5	555.4
165°	631.0	621.7	613.5	606.6	597.3	586.8	579.8	574.0	568.2	565.9	565.9
167.5°	619.8	613.3	608.0	603.8	597.0	589.4	584.0	580.8	576.4	575.2	576.4
170°	612.4	607.7	604.2	601.9	596.1	590.3	586.8	584.5	581.0	579.8	581.0
172.5°	605.9	602.1	600.5	600.1	595.2	591.2	588.7	587.3	584.7	584.5	585.6
175°	598.4	596.1	596.1	597.3	593.8	591.5	591.5	590.3	589.1	589.1	590.3
177.5°	593.3	592.4	592.4	594.2	592.4	591.5	591.5	591.5	590.5	591.5	592.4
180°	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5



TEST NUMBER: P332528

CATALOG NUMBER: SA4XXDIP-C350D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3
2.5°	575.1	577.0	579.5	583.6	585.1	587.0	589.7	589.5	590.2	593.1	599.1
5°	577.2	584.6	591.7	600.2	609.2	615.1	623.1	628.1	633.1	639.5	650.4
7.5°	578.1	589.7	602.7	617.7	631.0	646.3	658.3	669.6	679.8	693.2	706.2
10°	576.8	592.4	609.2	628.1	648.2	665.3	680.7	698.2	713.1	729.4	744.1
12.5°	574.3	593.1	615.6	636.8	660.3	685.5	704.7	722.4	742.2	761.0	783.7
15°	568.7	594.5	620.8	648.7	680.2	709.3	737.0	759.9	781.2	809.4	839.0
17.5°	561.6	589.4	622.6	656.4	689.3	722.5	756.8	791.3	818.2	853.2	876.3
20°	555.0	587.2	621.3	661.5	694.4	735.8	769.9	803.2	840.2	875.0	902.7
22.5°	545.7	580.9	617.1	657.1	700.4	741.9	781.2	817.4	854.4	892.2	925.7
25°	533.9	565.9	608.7	654.1	697.2	742.2	787.4	832.8	872.6	912.6	943.8
27.5°	513.9	554.2	594.1	641.0	688.8	739.7	788.1	835.6	877.3	910.2	929.5
30°	503.6	538.7	582.0	629.1	680.9	735.6	786.0	832.6	871.4	897.7	905.5
32.5°	488.5	524.6	567.0	615.8	670.7	726.9	779.3	823.3	855.7	869.5	860.1
35°	466.0	498.7	541.5	591.4	648.5	708.3	760.2	797.3	813.9	800.9	768.5
37.5°	439.0	471.4	514.4	563.5	622.5	683.4	730.2	757.0	751.5	719.1	670.8
40°	420.1	450.4	491.3	544.3	601.8	662.9	704.1	718.5	703.4	657.0	605.6
42.5°	399.1	428.6	469.7	520.9	581.8	638.1	674.0	675.2	649.8	594.3	542.8
45°	367.1	395.2	434.0	487.3	543.6	596.6	620.3	608.7	561.8	508.4	456.5
47.5°	335.5	359.9	398.2	448.7	502.2	546.8	558.6	537.7	487.8	435.8	387.8
50°	312.4	337.0	373.0	421.3	472.9	511.4	517.1	489.4	440.4	388.1	350.5
52.5°	290.2	314.7	349.3	394.0	441.2	476.0	476.2	444.2	395.4	348.8	313.8
55°	257.7	279.7	311.0	351.0	393.1	420.3	413.7	380.6	338.2	297.7	267.2
57.5°	226.4	245.6	274.3	307.7	344.8	367.3	356.3	324.4	286.6	252.2	229.1
60°	206.1	224.4	249.0	280.5	311.7	329.2	318.8	289.9	255.1	227.4	207.3
62.5°	186.4	201.8	225.5	252.8	281.8	294.7	285.5	257.0	226.9	201.9	185.5
65°	158.6	171.1	190.0	213.5	234.5	245.7	237.9	211.3	188.4	170.4	157.4
67.5°	132.5	142.3	156.7	175.5	193.4	199.4	192.3	173.8	154.4	140.0	130.8
70°	114.5	123.8	135.8	150.3	165.9	172.3	165.2	150.5	134.7	121.4	112.4
72.5°	98.8	106.0	116.2	128.5	140.7	147.1	142.3	128.2	114.8	104.9	97.3
75°	75.3	81.4	88.5	97.3	106.7	111.0	106.7	97.0	87.8	80.5	75.0
77.5°	54.7	58.0	63.5	70.1	76.0	79.2	75.5	69.0	63.3	58.3	55.6
80°	41.7	44.0	47.8	53.0	57.0	60.1	57.7	52.3	47.8	44.5	43.3
82.5°	30.3	31.9	34.4	38.2	40.9	42.5	41.5	37.5	35.7	32.8	31.6
85°	14.9	15.9	17.5	18.7	21.1	21.3	21.5	19.9	18.2	17.5	16.6
87.5°	5.8	6.7	7.5	8.3	9.1	10.6	10.4	10.9	10.6	10.2	9.7
90°	3.5	7.0	8.1	9.3	9.3	16.3	16.3	18.6	20.9	19.8	20.9
92.5°	19.3	30.2	44.4	61.4	85.5	144.6	234.7	322.6	368.6	307.0	228.2
95°	41.8	53.5	68.6	96.4	145.3	246.3	436.9	714.6	947.0	973.8	861.0
97.5°	68.8	78.8	92.7	116.7	157.6	235.4	392.8	668.8	997.5	1223.4	1272.2
100°	88.3	96.4	110.4	132.5	169.7	238.2	369.5	606.6	934.2	1231.7	1401.4
102.5°	108.8	116.0	129.0	150.1	185.5	247.5	363.0	564.7	855.2	1162.0	1394.9
105°	139.4	145.3	159.2	180.1	213.8	269.6	366.0	528.7	762.3	1035.3	1301.4
107.5°	170.3	176.2	191.0	211.0	244.3	295.4	383.2	522.2	710.2	933.1	1168.7
110°	191.7	197.5	211.5	232.4	263.8	314.9	396.2	524.1	692.6	882.0	1088.8



TEST NUMBER: P332528

CATALOG NUMBER: SA4XXDIP-C350D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	212.2	218.9	231.9	252.9	284.2	333.5	410.2	529.6	684.2	853.1	1030.2
115°	242.9	251.0	262.6	284.7	316.1	362.5	432.3	540.3	679.8	826.2	971.4
117.5°	273.3	280.5	293.3	314.0	346.5	390.7	454.8	551.7	678.6	814.1	942.6
120°	292.8	301.0	313.7	333.5	366.0	410.2	470.6	560.1	678.6	807.6	929.6
122.5°	311.4	319.6	331.4	353.0	384.6	428.8	485.5	568.5	677.7	800.2	918.4
125°	338.1	345.1	357.9	380.0	412.5	454.3	507.8	581.0	676.3	787.8	899.4
127.5°	358.8	367.2	381.8	404.8	437.6	478.0	527.1	591.0	673.7	771.3	876.1
130°	371.8	381.1	398.6	420.6	454.3	493.9	539.2	598.4	672.8	761.1	857.6
132.5°	383.0	395.1	411.6	435.5	467.4	506.9	551.3	604.9	671.9	751.8	838.0
135°	400.9	412.5	432.3	456.7	486.9	525.2	567.1	614.7	670.5	737.9	811.1
137.5°	417.6	430.4	449.2	474.6	503.4	539.2	578.2	620.5	670.2	725.8	786.7
140°	428.8	441.6	461.3	485.7	513.6	548.5	585.6	625.2	669.3	719.3	772.7
142.5°	441.8	453.6	472.5	495.9	522.9	556.8	591.2	628.9	669.3	713.7	759.7
145°	460.2	471.8	488.0	510.1	535.7	565.9	597.3	631.0	667.0	704.2	741.4
147.5°	478.5	488.7	505.5	523.8	546.8	575.2	602.6	632.1	662.8	695.6	726.3
150°	491.5	500.8	514.8	532.2	554.3	579.8	605.4	632.1	660.0	689.1	717.0
152.5°	502.7	512.0	525.0	540.6	560.8	583.6	607.3	630.3	655.4	681.6	706.7
155°	520.6	527.5	539.2	552.0	569.4	589.1	608.9	627.5	648.4	670.5	691.4
157.5°	535.9	542.4	551.5	562.6	576.4	593.1	608.9	624.5	641.2	659.1	674.9
160°	546.1	550.8	558.9	568.2	581.0	594.9	608.9	621.7	635.6	650.7	664.7
162.5°	554.5	558.2	565.4	573.8	583.8	596.8	608.9	618.9	630.0	643.3	654.4
165°	565.9	568.2	574.0	579.8	586.8	597.3	606.6	613.5	621.7	631.0	640.3
167.5°	575.2	576.4	580.8	584.0	589.4	597.0	603.8	608.0	613.3	619.8	626.6
170°	579.8	581.0	584.5	586.8	590.3	596.1	601.9	604.2	607.7	612.4	618.2
172.5°	584.5	584.7	587.3	588.7	591.2	595.2	600.1	600.5	602.1	605.9	610.7
175°	589.1	589.1	590.3	591.5	591.5	593.8	597.3	596.1	596.1	598.4	600.8
177.5°	591.5	590.5	591.5	591.5	591.5	592.4	594.2	592.4	592.4	593.3	594.2
180°	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5	591.5



TEST NUMBER: P332528

CATALOG NUMBER: SA4XXDIP-C350D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	571.3	571.3	571.3	571.3	571.3	571.3	571.3
2.5°	602.2	602.6	604.3	605.6	606.0	607.9	608.0
5°	655.1	659.1	666.9	667.6	668.8	675.0	670.2
7.5°	717.1	727.3	734.1	740.2	742.3	745.0	744.5
10°	756.9	772.0	779.6	791.7	792.1	795.2	793.3
12.5°	796.8	814.4	828.2	830.5	840.6	842.2	844.8
15°	853.4	872.1	891.3	898.2	912.1	915.4	920.6
17.5°	906.6	925.7	939.2	956.9	962.7	970.3	965.1
20°	935.8	956.6	973.7	987.6	993.5	997.8	997.3
22.5°	953.4	974.4	988.2	998.8	1004.3	1006.1	1006.0
25°	964.4	976.5	980.8	984.8	978.6	976.5	977.4
27.5°	933.7	930.6	919.5	904.9	889.8	877.8	871.2
30°	891.5	873.1	856.3	826.9	811.8	802.8	794.7
32.5°	831.7	802.4	770.1	743.2	726.0	712.7	710.7
35°	729.2	685.2	645.6	612.7	595.7	581.3	577.9
37.5°	619.9	574.2	538.6	509.6	491.3	481.1	471.6
40°	547.4	508.1	473.1	448.5	434.5	427.2	421.3
42.5°	491.6	455.7	420.8	402.1	389.5	385.0	381.5
45°	414.4	381.0	356.9	342.7	335.4	327.8	324.2
47.5°	352.6	325.5	309.6	297.5	289.6	285.1	282.9
50°	317.6	295.4	281.2	271.9	264.8	261.3	259.4
52.5°	286.6	268.3	256.4	249.0	244.2	241.6	240.8
55°	246.8	232.9	225.3	218.9	215.4	213.0	212.1
57.5°	214.6	203.8	197.7	192.4	191.0	189.1	188.4
60°	193.4	185.1	179.9	176.3	175.1	172.8	173.2
62.5°	174.6	167.8	163.4	161.4	159.8	157.8	158.5
65°	147.7	142.7	140.3	138.5	136.6	135.4	136.3
67.5°	123.9	120.5	117.3	116.2	115.3	115.1	114.1
70°	108.4	105.6	102.7	102.0	102.0	101.1	100.8
72.5°	93.4	91.4	89.5	88.9	88.2	88.6	87.6
75°	72.2	70.5	69.8	69.1	68.9	68.9	68.2
77.5°	53.3	52.1	51.0	51.0	50.1	49.8	49.7
80°	40.5	40.0	39.1	39.1	38.6	38.8	38.3
82.5°	30.4	29.8	29.6	29.2	28.5	28.6	28.1
85°	16.3	15.6	15.4	14.7	14.2	14.7	14.2
87.5°	10.1	10.1	9.9	9.8	9.8	9.6	9.0
90°	22.1	23.2	23.2	24.4	25.6	24.4	24.4
92.5°	171.7	136.7	113.4	99.7	93.4	89.5	89.5
95°	680.9	525.2	412.5	355.6	319.6	298.6	283.5
97.5°	1205.2	1091.6	970.3	886.8	816.9	782.0	757.9
100°	1424.6	1367.7	1281.7	1180.6	1109.7	1074.9	1065.6
102.5°	1510.1	1526.6	1490.8	1428.8	1377.4	1340.7	1333.3
105°	1502.5	1617.5	1665.1	1667.5	1658.2	1641.9	1634.9
107.5°	1382.8	1544.8	1648.4	1705.8	1732.3	1743.9	1747.0
110°	1289.8	1458.3	1586.1	1668.6	1717.4	1738.4	1748.8



TEST NUMBER: P332528

CATALOG NUMBER: SA4XXDIP-C350D1205U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1208.0	1367.2	1495.0	1588.7	1647.7	1677.0	1694.0
115°	1114.4	1250.3	1361.9	1453.7	1523.4	1560.6	1569.9
117.5°	1060.9	1167.8	1262.4	1340.7	1399.3	1436.9	1444.1
120°	1037.7	1130.6	1213.1	1279.4	1330.5	1360.7	1373.5
122.5°	1022.8	1107.4	1179.7	1235.7	1279.4	1304.9	1317.7
125°	999.3	1079.5	1143.4	1189.9	1223.6	1245.7	1252.6
127.5°	971.7	1051.6	1112.3	1159.0	1189.0	1207.6	1214.5
130°	949.4	1028.4	1090.0	1137.6	1166.6	1185.2	1192.2
132.5°	924.3	1001.4	1063.0	1109.7	1142.5	1160.1	1167.1
135°	886.6	957.5	1015.6	1062.1	1094.6	1113.2	1120.2
137.5°	850.6	910.3	962.8	1006.3	1038.4	1053.7	1062.1
140°	827.3	879.6	928.4	969.1	994.7	1010.9	1020.2
142.5°	807.8	852.7	895.0	931.0	954.7	969.1	975.6
145°	780.9	815.7	848.3	877.3	897.1	908.7	914.5
147.5°	757.6	785.5	811.1	832.5	849.4	858.3	860.3
150°	743.7	766.9	787.8	806.4	821.5	828.5	829.7
152.5°	729.7	751.1	768.3	784.1	796.4	800.6	801.8
155°	710.0	727.4	741.4	753.0	762.3	765.8	765.8
157.5°	690.5	705.1	716.3	725.1	732.1	734.2	734.2
160°	677.4	690.2	699.5	706.5	713.5	714.6	714.6
162.5°	665.4	675.4	683.7	688.8	695.8	697.0	696.0
165°	647.2	655.4	661.2	665.8	670.5	669.3	668.2
167.5°	631.9	638.4	641.9	644.2	647.2	647.0	646.1
170°	621.7	626.3	629.8	632.1	633.3	632.1	632.1
172.5°	613.3	616.1	618.6	620.0	621.2	620.0	618.2
175°	601.9	604.2	604.2	604.2	606.6	604.2	601.9
177.5°	595.2	595.2	596.1	595.2	596.1	594.2	592.4
180°	591.5	591.5	591.5	591.5	591.5	591.5	591.5

(END OF REPORT)