

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332867

Luminaire Tested: **SA4XXRDIP-C350D365U835-4F0-1E-UDD-A4**


Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332867  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXRDIP-C350D365U835-4F0-1E-UDD-A4  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 350 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2794.2 lumens  
Efficiency: N/A  
Efficacy: 137.6 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 20.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332867  
CATALOG NUMBER: SA4XXRDIP-C350D365U835-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P332867

CATALOG NUMBER: SA4XXRDIP-C350D365U835-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	53
1	99	95	91	88	92	88	85	82	75	73	71	64	62	61	53	52	51	46
2	91	83	77	72	84	78	72	68	67	63	60	57	54	51	47	45	44	39
3	83	74	67	61	77	69	62	57	59	54	51	50	47	44	42	40	38	34
4	76	66	58	52	70	61	54	49	53	48	43	45	41	38	38	35	33	29
5	70	59	51	45	65	55	48	42	47	42	38	41	37	33	34	31	29	26
6	65	53	45	39	60	49	42	37	43	37	33	37	33	29	31	28	26	23
7	60	48	40	34	55	45	38	33	39	33	29	34	29	26	29	25	23	20
8	56	43	36	31	51	41	34	29	36	30	26	31	27	23	26	23	21	18
9	52	40	32	27	48	37	31	26	33	27	24	28	24	21	24	21	19	17
10	48	36	29	25	45	34	28	23	30	25	21	26	22	19	23	19	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	4742	4742	4742	4742
5°	5501	4756	4204	4756
10°	6507	4736	3752	4736
15°	7516	4692	3224	4692
20°	8369	4631	2916	4631
25°	8639	4572	2707	4572
30°	7563	4501	2581	4501
35°	5887	4394	2505	4394
40°	4415	4272	2464	4272
45°	3486	4077	2442	4077
50°	2943	3852	2372	3852
55°	2564	3605	2245	3605
60°	2307	3347	1988	3347
65°	2034	3070	1710	3070
70°	1832	2783	1541	2783
75°	1535	2464	1313	2464
80°	1297	2101	1232	2101
85°	1093	1649	1093	1649



TEST NUMBER: P332867

CATALOG NUMBER: SA4XXRDIP-C350D365U835-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	56.9	2.0
10°-20°	171.7	6.1
20°-30°	268.5	9.6
30°-40°	298.5	10.7
40°-50°	264.9	9.5
50°-60°	206.4	7.4
60°-70°	135.1	4.8
70°-80°	66.4	2.4
80°-90°	17.4	0.6
90°-100°	129.9	4.7
100°-110°	270.4	9.7
110°-120°	242.2	8.7
120°-130°	203.7	7.3
130°-140°	169.9	6.1
140°-150°	129.8	4.6
150°-160°	91.2	3.3
160°-170°	53.7	1.9
170°-180°	17.5	0.6
0°-30°	497.1	17.8
0°-40°	795.6	28.5
0°-60°	1266.9	45.3
0°-90°	1485.8	53.2
90°-120°	642.6	23.0
90°-150°	1146.0	41.0
90°-180°	1308.0	46.8
0°-180°	2794.2	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	587	587	587	587	587	
5°	679	587	519	587	679	69
15°	899	561	386	561	899	256
25°	970	513	304	513	970	430
35°	597	446	254	446	597	374
45°	305	357	214	357	305	242
55°	182	256	160	256	182	166
65°	106	161	90	161	106	107
75°	49	79	42	79	49	54
85°	12	18	12	18	12	14
90°	7	0	7	0	7	7
95°	86	12	86	12	86	134
105°	497	41	497	41	497	492
115°	478	73	478	73	478	474
125°	381	101	381	101	381	346
135°	341	120	341	120	341	263
145°	278	139	278	139	278	176
155°	233	158	233	158	233	109
165°	203	172	203	172	203	58
175°	183	180	183	180	183	18
180°	180	180	180	180	180	



TEST NUMBER: P332867

CATALOG NUMBER: SA4XXRDIP-C350D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4
2.5°	619.6	621.3	619.6	619.4	617.5	616.9	616.2	613.7	609.2	606.5	607.1
5°	678.8	684.7	681.4	680.9	675.7	670.5	667.2	659.6	651.5	646.1	641.6
7.5°	747.2	750.6	748.5	745.2	736.8	732.0	724.3	714.4	699.9	688.9	678.8
10°	793.8	796.6	795.7	789.5	783.4	770.8	763.7	749.8	731.5	717.1	703.6
12.5°	839.6	842.6	834.3	834.6	822.9	813.0	801.8	784.2	763.2	744.6	727.7
15°	899.3	895.5	895.5	890.8	877.8	864.1	852.5	834.0	807.5	785.3	761.8
17.5°	946.1	947.4	945.5	934.3	924.1	909.9	888.6	867.1	842.5	812.6	788.7
20°	974.1	974.1	972.0	964.4	951.2	936.0	913.1	889.6	858.4	828.3	801.4
22.5°	985.5	986.2	983.7	977.5	965.6	950.8	931.2	907.4	875.2	841.4	808.0
25°	969.9	974.4	974.8	973.2	969.6	960.6	943.8	919.5	890.6	853.9	817.9
27.5°	890.4	896.1	901.1	909.3	920.2	925.8	926.6	914.2	889.0	853.7	817.5
30°	811.3	816.0	831.4	851.5	867.1	881.3	893.7	897.0	882.8	851.1	813.0
32.5°	723.4	729.9	745.3	766.9	792.9	817.0	844.6	858.7	858.3	839.3	804.1
35°	597.3	602.1	616.3	639.0	670.2	706.0	749.8	783.8	807.0	805.4	783.8
37.5°	481.8	487.1	501.4	520.3	550.6	594.8	637.2	684.2	727.0	751.1	743.9
40°	418.9	419.1	433.1	452.5	480.9	519.5	565.6	617.7	665.5	704.6	712.1
42.5°	369.3	369.3	378.6	399.5	419.9	456.2	500.3	552.0	608.0	653.1	673.1
45°	305.3	307.4	315.0	327.5	343.6	374.4	409.7	457.7	520.4	573.9	607.3
47.5°	258.5	261.7	266.5	276.7	289.5	310.0	339.2	382.4	433.4	492.2	539.7
50°	234.3	234.8	240.9	246.6	257.7	274.1	299.6	335.6	382.5	439.0	491.8
52.5°	213.5	213.4	217.1	224.3	233.3	246.0	266.7	299.4	341.0	391.7	446.2
55°	182.2	183.4	186.3	191.9	198.8	207.8	224.1	248.7	281.4	324.7	374.2
57.5°	158.5	159.1	161.3	163.7	170.0	176.6	188.8	205.9	233.4	268.9	315.0
60°	142.9	143.2	143.9	147.4	152.4	158.6	166.9	181.3	204.5	236.9	273.4
62.5°	127.8	128.2	129.3	131.9	135.8	140.0	148.7	160.3	179.5	207.2	240.0
65°	106.5	106.7	108.4	109.3	112.4	116.2	122.6	130.4	143.7	166.9	191.7
67.5°	89.0	89.0	89.1	90.4	92.5	95.0	98.8	105.1	115.1	129.3	151.2
70°	77.6	77.6	78.1	78.8	80.0	82.1	84.3	89.0	96.3	107.9	124.7
72.5°	67.0	67.2	67.7	67.8	68.4	70.2	71.8	74.8	80.2	89.0	102.6
75°	49.2	49.9	51.1	52.1	53.3	53.0	54.7	56.6	58.2	63.4	71.2
77.5°	36.6	36.3	36.4	37.2	37.3	37.6	38.8	40.2	41.5	43.9	46.7
80°	27.9	27.9	28.6	28.9	28.6	28.9	30.1	30.8	31.2	32.2	34.8
82.5°	21.1	21.5	21.3	21.5	21.6	21.9	22.9	23.0	23.5	23.9	24.9
85°	11.8	12.1	12.3	11.8	11.8	11.8	12.3	12.5	13.0	12.8	13.3
87.5°	5.6	5.5	5.7	5.6	5.8	5.6	5.7	6.0	5.6	5.8	5.7
90°	7.4	7.4	7.8	7.4	7.1	7.1	6.7	6.4	6.0	6.4	5.7
92.5°	27.2	27.2	28.4	30.3	34.5	41.6	52.2	69.4	93.4	112.1	98.1
95°	86.2	90.8	97.2	108.1	125.5	159.7	207.1	261.9	296.2	288.0	217.4
97.5°	230.5	237.9	248.5	269.7	295.1	332.0	366.6	386.9	372.1	303.4	203.4
100°	324.1	326.9	337.5	359.1	389.8	416.0	433.3	426.2	374.6	284.2	184.5
102.5°	405.5	407.8	419.0	434.6	453.4	464.3	459.3	424.3	353.4	260.1	171.8
105°	497.3	499.4	504.3	507.2	506.5	492.0	457.0	395.8	314.9	231.8	160.8
107.5°	531.3	530.4	526.9	518.8	501.4	469.8	420.6	355.5	283.8	216.0	158.8
110°	531.9	528.7	522.4	507.5	482.4	443.6	392.3	331.2	268.3	210.6	159.4



TEST NUMBER: P332867

CATALOG NUMBER: SA4XXRDIP-C350D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	515.2	510.1	501.2	483.2	454.7	415.8	367.4	313.3	259.5	208.1	161.1
115°	477.5	474.7	463.3	442.1	414.2	380.3	338.9	295.5	251.3	206.8	164.3
117.5°	439.2	437.0	425.6	407.8	384.0	355.2	322.7	286.7	247.6	206.4	167.8
120°	417.8	413.9	404.7	389.1	369.0	343.9	315.6	282.7	245.6	206.4	170.4
122.5°	400.8	396.9	389.1	375.8	358.8	336.8	311.1	279.3	243.4	206.1	172.9
125°	381.0	378.9	372.2	361.9	347.8	328.3	303.9	273.6	239.6	205.7	176.7
127.5°	369.4	367.3	361.6	352.5	338.3	319.9	295.5	266.5	234.6	204.9	179.8
130°	362.6	360.5	354.8	346.0	331.5	312.8	288.8	260.8	231.5	204.6	182.0
132.5°	355.0	352.9	347.5	337.5	323.3	304.6	281.1	254.9	228.7	204.4	184.0
135°	340.7	338.6	332.9	323.0	308.9	291.2	269.7	246.7	224.4	203.9	187.0
137.5°	323.0	320.5	315.8	306.1	292.8	276.9	258.7	239.3	220.8	203.9	188.7
140°	310.3	307.5	302.5	294.8	282.4	267.5	251.6	235.0	218.8	203.6	190.1
142.5°	296.7	294.8	290.4	283.2	272.2	259.3	245.7	231.1	217.1	203.6	191.3
145°	278.1	276.4	272.8	266.8	258.0	248.1	237.5	225.5	214.2	202.9	191.9
147.5°	261.7	261.0	258.4	253.2	246.7	238.9	230.4	220.9	211.6	201.6	192.3
150°	252.3	252.0	249.9	245.3	239.6	233.3	226.2	218.1	209.6	200.7	192.3
152.5°	243.9	243.5	242.2	238.5	233.7	228.5	222.0	215.0	207.3	199.3	191.7
155°	232.9	232.9	231.8	229.0	225.5	221.2	215.9	210.3	203.9	197.2	190.9
157.5°	223.3	223.3	222.7	220.5	217.9	214.5	210.0	205.3	200.5	195.0	189.9
160°	217.4	217.4	217.0	214.9	212.8	209.9	206.0	202.2	197.9	193.3	189.1
162.5°	211.7	212.0	211.6	209.5	208.0	205.4	202.4	199.1	195.7	191.6	188.2
165°	203.2	203.6	203.9	202.5	201.1	199.3	196.9	194.7	191.9	189.1	186.6
167.5°	196.5	196.8	196.9	195.9	195.2	194.2	192.2	190.6	188.5	186.5	184.9
170°	192.3	192.3	192.6	192.3	191.6	190.5	189.1	188.0	186.3	184.8	183.8
172.5°	188.0	188.6	188.9	188.6	188.2	187.4	186.5	185.8	184.3	183.1	182.7
175°	183.1	183.8	184.5	183.8	183.8	183.8	183.1	182.7	182.0	181.3	181.3
177.5°	180.2	180.7	181.3	181.0	181.3	181.0	181.0	180.7	180.5	180.2	180.2
180°	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9



TEST NUMBER: P332867

CATALOG NUMBER: SA4XXRDIP-C350D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4
2.5°	605.2	602.6	601.2	598.2	594.6	592.7	591.0	588.5	585.3	581.9	579.5
5°	635.9	630.2	623.1	614.6	607.1	599.7	593.3	586.9	579.6	572.0	564.5
7.5°	667.4	656.3	644.2	630.2	616.7	604.3	592.9	582.1	569.8	558.7	548.7
10°	689.4	674.3	657.5	639.7	622.0	606.6	591.4	577.7	562.6	549.1	537.7
12.5°	707.2	689.4	669.2	647.1	625.7	607.1	589.7	571.8	554.6	540.0	524.8
15°	736.7	712.4	685.2	658.6	631.0	605.6	582.2	561.4	541.7	521.1	506.7
17.5°	757.1	728.1	695.0	663.2	630.5	600.6	573.6	548.8	526.1	505.1	487.9
20°	769.2	737.2	700.5	664.3	627.6	595.7	566.6	539.1	515.7	493.0	475.2
22.5°	776.0	740.6	700.5	662.6	624.6	590.0	558.1	529.5	504.0	481.2	461.6
25°	778.2	740.3	699.4	655.8	614.2	577.5	544.3	513.3	484.9	462.2	441.4
27.5°	775.1	730.5	688.6	643.9	600.9	562.3	527.5	494.9	466.5	442.1	420.7
30°	770.6	722.8	677.8	631.4	587.9	550.7	514.0	482.8	453.2	427.9	406.4
32.5°	760.7	713.3	664.9	617.4	573.3	535.0	500.2	468.8	439.8	413.9	391.0
35°	741.2	693.2	640.7	591.9	548.6	508.8	476.2	445.9	418.2	390.5	366.4
37.5°	715.5	666.5	614.2	560.8	517.4	479.9	450.0	421.5	394.5	369.2	342.5
40°	691.3	646.6	592.6	539.6	495.1	458.9	431.2	405.4	378.2	353.1	326.4
42.5°	662.0	623.9	569.3	516.1	472.2	437.3	411.5	386.3	361.5	337.2	309.3
45°	613.0	584.1	533.0	481.9	437.6	403.0	379.4	357.1	335.4	312.2	285.9
47.5°	556.8	537.3	493.2	440.8	399.9	368.8	345.9	327.7	309.3	286.1	263.1
50°	517.8	505.3	462.7	414.9	375.8	347.2	323.8	306.7	291.3	269.1	248.5
52.5°	476.2	469.5	433.5	387.8	350.1	322.0	302.0	286.7	271.1	252.6	233.4
55°	412.7	416.3	385.8	346.2	310.7	287.1	268.9	256.1	242.8	227.2	212.3
57.5°	347.9	360.9	340.4	305.7	272.4	250.5	236.8	226.1	214.9	202.0	189.2
60°	309.1	320.0	308.4	277.8	248.7	228.4	215.6	207.3	196.2	184.4	174.7
62.5°	271.2	282.9	276.0	251.3	224.3	206.8	195.5	187.8	179.5	169.2	159.1
65°	223.7	231.2	227.9	210.9	191.7	176.8	166.4	160.7	153.1	145.6	136.6
67.5°	171.3	185.9	184.0	174.9	158.4	146.7	139.9	134.9	128.0	122.4	116.3
70°	140.8	154.3	154.1	146.7	137.7	126.9	122.1	117.9	111.7	106.3	101.3
72.5°	115.3	127.6	129.5	123.8	117.7	109.4	104.9	102.0	96.0	92.3	88.2
75°	80.7	89.7	92.1	92.1	89.2	85.0	80.9	79.0	74.8	71.5	69.1
77.5°	52.9	58.6	62.3	63.1	63.6	62.1	58.8	57.5	54.2	53.1	50.8
80°	37.4	41.2	45.4	46.9	48.0	47.6	46.2	45.2	42.1	40.9	40.0
82.5°	25.8	27.9	31.4	34.6	34.2	35.5	34.2	33.5	31.1	30.7	29.8
85°	13.5	13.7	14.2	16.3	17.5	18.0	18.2	17.8	17.0	17.0	15.4
87.5°	5.5	5.3	5.3	5.3	5.4	6.1	6.5	6.5	6.1	5.7	5.2
90°	4.9	4.9	2.8	2.8	2.5	2.1	1.1	0.4	1.1	2.1	2.5
92.5°	71.4	44.0	26.0	18.7	13.5	9.2	5.9	4.0	5.9	9.2	13.5
95°	132.9	74.9	44.2	29.3	20.9	16.3	12.7	11.7	12.7	16.3	20.9
97.5°	119.5	71.6	47.9	35.5	28.2	24.0	20.9	20.9	20.9	24.0	28.2
100°	112.4	72.5	51.6	40.3	33.6	29.3	26.9	26.9	26.9	29.3	33.6
102.5°	110.4	75.3	56.4	45.7	39.2	35.3	33.1	32.5	33.1	35.3	39.2
105°	111.3	82.0	65.0	54.8	48.4	44.2	42.4	41.4	42.4	44.2	48.4
107.5°	116.6	89.8	74.3	64.2	58.1	53.6	51.8	51.1	51.8	53.6	58.1
110°	120.5	95.8	80.2	70.7	64.3	60.1	58.3	57.6	58.3	60.1	64.3





TEST NUMBER: P332867

CATALOG NUMBER: SA4XXRDIP-C350D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	124.8	101.4	86.4	76.9	70.5	66.6	64.5	63.8	64.5	66.6	70.5
115°	131.5	110.3	96.1	86.6	79.9	76.3	73.9	72.8	73.9	76.3	79.9
117.5°	138.3	118.8	105.4	95.5	89.2	85.3	83.1	82.1	83.1	85.3	89.2
120°	143.1	124.8	111.3	101.4	95.4	91.5	89.1	88.4	89.1	91.5	95.4
122.5°	147.7	130.4	117.0	107.4	100.8	97.2	94.7	94.0	94.7	97.2	100.8
125°	154.4	138.2	125.5	115.6	108.9	105.0	102.8	101.4	102.8	105.0	108.9
127.5°	160.3	145.4	133.1	123.1	116.1	111.7	109.1	108.0	109.1	111.7	116.1
130°	164.0	150.2	138.2	127.9	121.2	115.9	113.1	111.7	113.1	115.9	121.2
132.5°	167.7	154.2	142.1	132.5	125.2	120.2	116.5	115.4	116.5	120.2	125.2
135°	172.5	159.7	148.1	138.9	131.5	125.5	121.9	120.5	121.9	125.5	131.5
137.5°	175.9	164.0	153.1	144.3	136.6	130.9	127.0	125.7	127.0	130.9	136.6
140°	178.1	166.8	156.2	147.7	140.3	134.3	130.4	129.4	130.4	134.3	140.3
142.5°	179.8	169.4	159.0	150.8	143.7	138.0	134.4	133.3	134.4	138.0	143.7
145°	181.7	172.1	162.9	155.2	148.4	143.5	140.0	138.9	140.0	143.5	148.4
147.5°	183.3	174.9	166.3	159.3	153.7	148.7	145.5	145.2	145.5	148.7	153.7
150°	184.1	176.4	168.6	161.9	156.6	152.3	149.5	149.1	149.5	152.3	156.6
152.5°	184.7	177.5	170.6	164.4	159.7	155.7	152.9	152.8	152.9	155.7	159.7
155°	185.2	179.2	173.2	167.9	164.0	160.5	158.3	158.0	158.3	160.5	164.0
157.5°	185.2	180.4	175.3	171.1	167.7	165.0	163.0	163.0	163.0	165.0	167.7
160°	185.2	181.0	176.7	172.8	170.0	167.5	166.1	166.1	166.1	167.5	170.0
162.5°	185.2	181.5	177.6	174.5	172.0	169.8	168.7	168.9	168.7	169.8	172.0
165°	184.5	181.7	178.5	176.4	174.6	172.8	172.1	172.1	172.1	172.8	174.6
167.5°	183.6	181.6	179.3	177.6	176.6	175.3	174.9	175.3	174.9	175.3	176.6
170°	183.1	181.3	179.5	178.5	177.8	176.7	176.4	176.7	176.4	176.7	177.8
172.5°	182.5	181.0	179.8	179.0	178.6	177.8	177.8	178.1	177.8	177.8	178.6
175°	181.7	180.6	179.9	179.9	179.5	179.2	179.2	179.5	179.2	179.2	179.5
177.5°	180.7	180.2	179.9	179.9	179.9	179.6	179.9	180.2	179.9	179.6	179.9
180°	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9



TEST NUMBER: P332867

CATALOG NUMBER: SA4XXRDIP-C350D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4
2.5°	576.8	574.9	572.5	569.6	566.2	563.2	561.8	563.0	563.6	562.0	561.8
5°	559.2	553.3	548.6	541.5	535.8	531.1	527.8	526.3	526.8	523.0	522.1
7.5°	539.5	532.5	524.7	516.3	508.5	501.5	497.9	495.9	491.8	490.1	487.2
10°	526.8	517.4	509.8	499.8	490.8	482.6	478.5	475.2	471.2	469.3	465.3
12.5°	513.8	502.8	494.4	484.1	474.9	465.0	461.1	455.0	448.7	444.7	439.5
15°	495.3	482.1	471.9	459.6	448.7	437.4	427.2	415.8	411.6	402.6	397.4
17.5°	473.8	460.4	447.8	431.3	414.5	400.3	389.5	378.6	372.1	366.4	363.7
20°	459.6	447.3	429.8	410.6	391.9	376.3	367.5	360.4	353.3	349.3	346.5
22.5°	446.2	430.4	410.1	389.4	370.7	358.5	351.1	343.8	338.0	334.2	330.4
25°	423.6	403.0	381.5	357.8	345.1	334.4	326.4	320.4	316.9	311.9	310.0
27.5°	400.5	375.5	351.8	335.9	322.6	312.8	305.8	301.4	296.9	293.7	291.2
30°	382.7	357.4	336.1	320.9	307.4	299.4	293.7	288.5	284.9	282.3	280.5
32.5°	365.1	339.8	321.9	305.6	294.9	287.1	281.0	277.1	274.3	271.0	269.8
35°	339.6	317.1	301.5	286.8	276.0	268.9	264.1	260.1	257.7	256.8	256.1
37.5°	315.1	296.7	279.9	267.9	258.2	252.6	247.0	245.0	243.4	241.7	242.5
40°	299.6	282.3	267.4	254.7	246.8	240.7	237.4	235.0	233.6	233.6	233.6
42.5°	286.2	269.3	254.7	243.3	235.5	230.3	226.6	224.6	224.1	223.9	225.1
45°	265.3	249.7	235.0	225.5	218.9	213.7	211.6	209.9	209.9	210.9	211.1
47.5°	244.6	230.0	218.2	207.6	201.5	198.3	196.4	195.6	195.7	196.6	197.7
50°	231.9	217.5	205.9	196.4	190.8	187.7	186.0	185.5	186.0	186.0	187.7
52.5°	218.1	205.2	193.8	185.8	179.4	176.5	175.6	174.9	175.2	176.0	176.7
55°	197.9	186.3	175.4	167.8	163.1	161.2	159.0	159.3	158.8	159.3	159.3
57.5°	177.5	167.1	157.0	151.0	146.8	144.1	141.8	142.4	141.7	141.6	141.2
60°	164.5	153.1	145.1	139.6	134.9	132.5	130.4	130.9	130.2	129.7	128.7
62.5°	150.3	140.8	133.1	127.9	124.1	121.4	119.2	118.8	117.1	115.5	113.4
65°	129.7	121.9	115.0	110.1	106.5	104.4	102.7	101.3	97.7	94.0	92.1
67.5°	109.7	104.0	97.6	93.4	90.5	87.8	84.6	82.2	78.9	76.8	75.6
70°	96.8	91.4	85.9	81.9	78.8	76.2	72.7	71.0	68.6	67.7	66.5
72.5°	84.5	79.4	74.4	70.7	67.5	65.4	62.6	61.0	59.9	59.5	58.4
75°	65.8	61.8	58.0	54.7	52.1	50.6	49.5	48.3	47.8	45.7	44.5
77.5°	48.0	45.3	43.0	40.6	38.8	37.8	35.5	34.2	33.4	32.4	32.1
80°	37.4	35.5	33.1	31.7	29.1	28.2	27.2	27.0	26.7	26.5	26.3
82.5°	28.1	26.2	23.9	23.0	22.3	21.7	21.2	20.9	20.7	20.8	20.8
85°	14.2	13.3	13.3	13.0	12.8	12.5	12.3	12.3	12.1	12.3	12.1
87.5°	5.3	5.1	5.5	5.2	5.5	5.6	5.4	5.4	5.7	5.4	5.4
90°	2.8	2.8	4.9	4.9	5.7	6.4	6.0	6.4	6.7	7.1	7.1
92.5°	18.7	26.0	44.0	71.4	98.1	112.1	93.4	69.4	52.2	41.6	34.5
95°	29.3	44.2	74.9	132.9	217.4	288.0	296.2	261.9	207.1	159.7	125.5
97.5°	35.5	47.9	71.6	119.5	203.4	303.4	372.1	386.9	366.6	332.0	295.1
100°	40.3	51.6	72.5	112.4	184.5	284.2	374.6	426.2	433.3	416.0	389.8
102.5°	45.7	56.4	75.3	110.4	171.8	260.1	353.4	424.3	459.3	464.3	453.4
105°	54.8	65.0	82.0	111.3	160.8	231.8	314.9	395.8	457.0	492.0	506.5
107.5°	64.2	74.3	89.8	116.6	158.8	216.0	283.8	355.5	420.6	469.8	501.4
110°	70.7	80.2	95.8	120.5	159.4	210.6	268.3	331.2	392.3	443.6	482.4



TEST NUMBER: P332867

CATALOG NUMBER: SA4XXRDIP-C350D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	76.9	86.4	101.4	124.8	161.1	208.1	259.5	313.3	367.4	415.8	454.7
115°	86.6	96.1	110.3	131.5	164.3	206.8	251.3	295.5	338.9	380.3	414.2
117.5°	95.5	105.4	118.8	138.3	167.8	206.4	247.6	286.7	322.7	355.2	384.0
120°	101.4	111.3	124.8	143.1	170.4	206.4	245.6	282.7	315.6	343.9	369.0
122.5°	107.4	117.0	130.4	147.7	172.9	206.1	243.4	279.3	311.1	336.8	358.8
125°	115.6	125.5	138.2	154.4	176.7	205.7	239.6	273.6	303.9	328.3	347.8
127.5°	123.1	133.1	145.4	160.3	179.8	204.9	234.6	266.5	295.5	319.9	338.3
130°	127.9	138.2	150.2	164.0	182.0	204.6	231.5	260.8	288.8	312.8	331.5
132.5°	132.5	142.1	154.2	167.7	184.0	204.4	228.7	254.9	281.1	304.6	323.3
135°	138.9	148.1	159.7	172.5	187.0	203.9	224.4	246.7	269.7	291.2	308.9
137.5°	144.3	153.1	164.0	175.9	188.7	203.9	220.8	239.3	258.7	276.9	292.8
140°	147.7	156.2	166.8	178.1	190.1	203.6	218.8	235.0	251.6	267.5	282.4
142.5°	150.8	159.0	169.4	179.8	191.3	203.6	217.1	231.1	245.7	259.3	272.2
145°	155.2	162.9	172.1	181.7	191.9	202.9	214.2	225.5	237.5	248.1	258.0
147.5°	159.3	166.3	174.9	183.3	192.3	201.6	211.6	220.9	230.4	238.9	246.7
150°	161.9	168.6	176.4	184.1	192.3	200.7	209.6	218.1	226.2	233.3	239.6
152.5°	164.4	170.6	177.5	184.7	191.7	199.3	207.3	215.0	222.0	228.5	233.7
155°	167.9	173.2	179.2	185.2	190.9	197.2	203.9	210.3	215.9	221.2	225.5
157.5°	171.1	175.3	180.4	185.2	189.9	195.0	200.5	205.3	210.0	214.5	217.9
160°	172.8	176.7	181.0	185.2	189.1	193.3	197.9	202.2	206.0	209.9	212.8
162.5°	174.5	177.6	181.5	185.2	188.2	191.6	195.7	199.1	202.4	205.4	208.0
165°	176.4	178.5	181.7	184.5	186.6	189.1	191.9	194.7	196.9	199.3	201.1
167.5°	177.6	179.3	181.6	183.6	184.9	186.5	188.5	190.6	192.2	194.2	195.2
170°	178.5	179.5	181.3	183.1	183.8	184.8	186.3	188.0	189.1	190.5	191.6
172.5°	179.0	179.8	181.0	182.5	182.7	183.1	184.3	185.8	186.5	187.4	188.2
175°	179.9	179.9	180.6	181.7	181.3	181.3	182.0	182.7	183.1	183.8	183.8
177.5°	179.9	179.9	180.2	180.7	180.2	180.2	180.5	180.7	181.0	181.0	181.3
180°	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9



TEST NUMBER: P332867

CATALOG NUMBER: SA4XXRDIP-C350D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4
2.5°	560.7	561.1	559.8	559.4	559.8	561.1	560.7	561.8	562.0	563.6	563.0
5°	520.2	519.7	518.5	518.8	518.5	519.7	520.2	522.1	523.0	526.8	526.3
7.5°	485.5	483.7	484.2	482.3	484.2	483.7	485.5	487.2	490.1	491.8	495.9
10°	464.3	461.7	459.6	457.7	459.6	461.7	464.3	465.3	469.3	471.2	475.2
12.5°	435.4	433.1	430.3	430.8	430.3	433.1	435.4	439.5	444.7	448.7	455.0
15°	394.3	390.7	385.1	385.8	385.1	390.7	394.3	397.4	402.6	411.6	415.8
17.5°	359.5	359.5	356.9	357.6	356.9	359.5	359.5	363.7	366.4	372.1	378.6
20°	341.5	339.9	340.1	339.4	340.1	339.9	341.5	346.5	349.3	353.3	360.4
22.5°	329.0	327.0	325.3	323.9	325.3	327.0	329.0	330.4	334.2	338.0	343.8
25°	307.9	306.5	304.4	303.9	304.4	306.5	307.9	310.0	311.9	316.9	320.4
27.5°	289.3	289.1	288.2	287.1	288.2	289.1	289.3	291.2	293.7	296.9	301.4
30°	278.6	278.1	277.6	276.9	277.6	278.1	278.6	280.5	282.3	284.9	288.5
32.5°	268.9	268.6	268.1	268.2	268.1	268.6	268.9	269.8	271.0	274.3	277.1
35°	255.1	254.9	254.4	254.2	254.4	254.9	255.1	256.1	256.8	257.7	260.1
37.5°	242.3	242.9	242.6	242.5	242.6	242.9	242.3	242.5	241.7	243.4	245.0
40°	233.4	233.6	234.1	233.8	234.1	233.6	233.4	233.6	233.6	233.6	235.0
42.5°	226.0	226.0	226.7	225.9	226.7	226.0	226.0	225.1	223.9	224.1	224.6
45°	212.8	214.2	213.9	213.9	213.9	214.2	212.8	211.1	210.9	209.9	209.9
47.5°	198.3	199.6	199.9	199.8	199.9	199.6	198.3	197.7	196.6	195.7	195.6
50°	188.9	188.4	189.1	188.9	189.1	188.4	188.9	187.7	186.0	186.0	185.5
52.5°	177.3	177.4	177.4	177.1	177.4	177.4	177.3	176.7	176.0	175.2	174.9
55°	159.5	159.8	159.3	159.5	159.3	159.8	159.5	159.3	159.3	158.8	159.3
57.5°	140.2	139.1	139.5	139.0	139.5	139.1	140.2	141.2	141.6	141.7	142.4
60°	126.4	124.5	124.0	123.1	124.0	124.5	126.4	128.7	129.7	130.2	130.9
62.5°	110.9	109.5	107.9	108.7	107.9	109.5	110.9	113.4	115.5	117.1	118.8
65°	90.2	89.2	88.5	89.5	88.5	89.2	90.2	92.1	94.0	97.7	101.3
67.5°	74.6	74.1	74.1	73.7	74.1	74.1	74.6	75.6	76.8	78.9	82.2
70°	66.5	65.8	65.8	65.3	65.8	65.8	66.5	66.5	67.7	68.6	71.0
72.5°	58.2	57.5	57.7	57.4	57.7	57.5	58.2	58.4	59.5	59.9	61.0
75°	43.1	41.9	41.9	42.1	41.9	41.9	43.1	44.5	45.7	47.8	48.3
77.5°	32.1	31.9	32.2	31.8	32.2	31.9	32.1	32.1	32.4	33.4	34.2
80°	26.3	26.0	25.8	26.5	25.8	26.0	26.3	26.3	26.5	26.7	27.0
82.5°	20.4	20.4	20.3	21.2	20.3	20.4	20.4	20.8	20.8	20.7	20.9
85°	12.3	11.8	12.3	11.8	12.3	11.8	12.3	12.1	12.3	12.1	12.3
87.5°	5.8	5.7	5.5	5.6	5.5	5.7	5.8	5.4	5.4	5.7	5.4
90°	7.4	7.8	7.4	7.4	7.4	7.8	7.4	7.1	7.1	6.7	6.4
92.5°	30.3	28.4	27.2	27.2	27.2	28.4	30.3	34.5	41.6	52.2	69.4
95°	108.1	97.2	90.8	86.2	90.8	97.2	108.1	125.5	159.7	207.1	261.9
97.5°	269.7	248.5	237.9	230.5	237.9	248.5	269.7	295.1	332.0	366.6	386.9
100°	359.1	337.5	326.9	324.1	326.9	337.5	359.1	389.8	416.0	433.3	426.2
102.5°	434.6	419.0	407.8	405.5	407.8	419.0	434.6	453.4	464.3	459.3	424.3
105°	507.2	504.3	499.4	497.3	499.4	504.3	507.2	506.5	492.0	457.0	395.8
107.5°	518.8	526.9	530.4	531.3	530.4	526.9	518.8	501.4	469.8	420.6	355.5
110°	507.5	522.4	528.7	531.9	528.7	522.4	507.5	482.4	443.6	392.3	331.2



TEST NUMBER: P332867

CATALOG NUMBER: SA4XXRDIP-C350D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	483.2	501.2	510.1	515.2	510.1	501.2	483.2	454.7	415.8	367.4	313.3
115°	442.1	463.3	474.7	477.5	474.7	463.3	442.1	414.2	380.3	338.9	295.5
117.5°	407.8	425.6	437.0	439.2	437.0	425.6	407.8	384.0	355.2	322.7	286.7
120°	389.1	404.7	413.9	417.8	413.9	404.7	389.1	369.0	343.9	315.6	282.7
122.5°	375.8	389.1	396.9	400.8	396.9	389.1	375.8	358.8	336.8	311.1	279.3
125°	361.9	372.2	378.9	381.0	378.9	372.2	361.9	347.8	328.3	303.9	273.6
127.5°	352.5	361.6	367.3	369.4	367.3	361.6	352.5	338.3	319.9	295.5	266.5
130°	346.0	354.8	360.5	362.6	360.5	354.8	346.0	331.5	312.8	288.8	260.8
132.5°	337.5	347.5	352.9	355.0	352.9	347.5	337.5	323.3	304.6	281.1	254.9
135°	323.0	332.9	338.6	340.7	338.6	332.9	323.0	308.9	291.2	269.7	246.7
137.5°	306.1	315.8	320.5	323.0	320.5	315.8	306.1	292.8	276.9	258.7	239.3
140°	294.8	302.5	307.5	310.3	307.5	302.5	294.8	282.4	267.5	251.6	235.0
142.5°	283.2	290.4	294.8	296.7	294.8	290.4	283.2	272.2	259.3	245.7	231.1
145°	266.8	272.8	276.4	278.1	276.4	272.8	266.8	258.0	248.1	237.5	225.5
147.5°	253.2	258.4	261.0	261.7	261.0	258.4	253.2	246.7	238.9	230.4	220.9
150°	245.3	249.9	252.0	252.3	252.0	249.9	245.3	239.6	233.3	226.2	218.1
152.5°	238.5	242.2	243.5	243.9	243.5	242.2	238.5	233.7	228.5	222.0	215.0
155°	229.0	231.8	232.9	232.9	232.9	231.8	229.0	225.5	221.2	215.9	210.3
157.5°	220.5	222.7	223.3	223.3	223.3	222.7	220.5	217.9	214.5	210.0	205.3
160°	214.9	217.0	217.4	217.4	217.4	217.0	214.9	212.8	209.9	206.0	202.2
162.5°	209.5	211.6	212.0	211.7	212.0	211.6	209.5	208.0	205.4	202.4	199.1
165°	202.5	203.9	203.6	203.2	203.6	203.9	202.5	201.1	199.3	196.9	194.7
167.5°	195.9	196.9	196.8	196.5	196.8	196.9	195.9	195.2	194.2	192.2	190.6
170°	192.3	192.6	192.3	192.3	192.3	192.6	192.3	191.6	190.5	189.1	188.0
172.5°	188.6	188.9	188.6	188.0	188.6	188.9	188.6	188.2	187.4	186.5	185.8
175°	183.8	184.5	183.8	183.1	183.8	184.5	183.8	183.8	183.8	183.1	182.7
177.5°	181.0	181.3	180.7	180.2	180.7	181.3	181.0	181.3	181.0	181.0	180.7
180°	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9



TEST NUMBER: P332867

CATALOG NUMBER: SA4XXRDIP-C350D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4
2.5°	561.8	563.2	566.2	569.6	572.5	574.9	576.8	579.5	581.9	585.3	588.5
5°	527.8	531.1	535.8	541.5	548.6	553.3	559.2	564.5	572.0	579.6	586.9
7.5°	497.9	501.5	508.5	516.3	524.7	532.5	539.5	548.7	558.7	569.8	582.1
10°	478.5	482.6	490.8	499.8	509.8	517.4	526.8	537.7	549.1	562.6	577.7
12.5°	461.1	465.0	474.9	484.1	494.4	502.8	513.8	524.8	540.0	554.6	571.8
15°	427.2	437.4	448.7	459.6	471.9	482.1	495.3	506.7	521.1	541.7	561.4
17.5°	389.5	400.3	414.5	431.3	447.8	460.4	473.8	487.9	505.1	526.1	548.8
20°	367.5	376.3	391.9	410.6	429.8	447.3	459.6	475.2	493.0	515.7	539.1
22.5°	351.1	358.5	370.7	389.4	410.1	430.4	446.2	461.6	481.2	504.0	529.5
25°	326.4	334.4	345.1	357.8	381.5	403.0	423.6	441.4	462.2	484.9	513.3
27.5°	305.8	312.8	322.6	335.9	351.8	375.5	400.5	420.7	442.1	466.5	494.9
30°	293.7	299.4	307.4	320.9	336.1	357.4	382.7	406.4	427.9	453.2	482.8
32.5°	281.0	287.1	294.9	305.6	321.9	339.8	365.1	391.0	413.9	439.8	468.8
35°	264.1	268.9	276.0	286.8	301.5	317.1	339.6	366.4	390.5	418.2	445.9
37.5°	247.0	252.6	258.2	267.9	279.9	296.7	315.1	342.5	369.2	394.5	421.5
40°	237.4	240.7	246.8	254.7	267.4	282.3	299.6	326.4	353.1	378.2	405.4
42.5°	226.6	230.3	235.5	243.3	254.7	269.3	286.2	309.3	337.2	361.5	386.3
45°	211.6	213.7	218.9	225.5	235.0	249.7	265.3	285.9	312.2	335.4	357.1
47.5°	196.4	198.3	201.5	207.6	218.2	230.0	244.6	263.1	286.1	309.3	327.7
50°	186.0	187.7	190.8	196.4	205.9	217.5	231.9	248.5	269.1	291.3	306.7
52.5°	175.6	176.5	179.4	185.8	193.8	205.2	218.1	233.4	252.6	271.1	286.7
55°	159.0	161.2	163.1	167.8	175.4	186.3	197.9	212.3	227.2	242.8	256.1
57.5°	141.8	144.1	146.8	151.0	157.0	167.1	177.5	189.2	202.0	214.9	226.1
60°	130.4	132.5	134.9	139.6	145.1	153.1	164.5	174.7	184.4	196.2	207.3
62.5°	119.2	121.4	124.1	127.9	133.1	140.8	150.3	159.1	169.2	179.5	187.8
65°	102.7	104.4	106.5	110.1	115.0	121.9	129.7	136.6	145.6	153.1	160.7
67.5°	84.6	87.8	90.5	93.4	97.6	104.0	109.7	116.3	122.4	128.0	134.9
70°	72.7	76.2	78.8	81.9	85.9	91.4	96.8	101.3	106.3	111.7	117.9
72.5°	62.6	65.4	67.5	70.7	74.4	79.4	84.5	88.2	92.3	96.0	102.0
75°	49.5	50.6	52.1	54.7	58.0	61.8	65.8	69.1	71.5	74.8	79.0
77.5°	35.5	37.8	38.8	40.6	43.0	45.3	48.0	50.8	53.1	54.2	57.5
80°	27.2	28.2	29.1	31.7	33.1	35.5	37.4	40.0	40.9	42.1	45.2
82.5°	21.2	21.7	22.3	23.0	23.9	26.2	28.1	29.8	30.7	31.1	33.5
85°	12.3	12.5	12.8	13.0	13.3	13.3	14.2	15.4	17.0	17.0	17.8
87.5°	5.4	5.6	5.5	5.2	5.5	5.1	5.3	5.2	5.7	6.1	6.5
90°	6.0	6.4	5.7	4.9	4.9	2.8	2.8	2.5	2.1	1.1	0.4
92.5°	93.4	112.1	98.1	71.4	44.0	26.0	18.7	13.5	9.2	5.9	4.0
95°	296.2	288.0	217.4	132.9	74.9	44.2	29.3	20.9	16.3	12.7	11.7
97.5°	372.1	303.4	203.4	119.5	71.6	47.9	35.5	28.2	24.0	20.9	20.9
100°	374.6	284.2	184.5	112.4	72.5	51.6	40.3	33.6	29.3	26.9	26.9
102.5°	353.4	260.1	171.8	110.4	75.3	56.4	45.7	39.2	35.3	33.1	32.5
105°	314.9	231.8	160.8	111.3	82.0	65.0	54.8	48.4	44.2	42.4	41.4
107.5°	283.8	216.0	158.8	116.6	89.8	74.3	64.2	58.1	53.6	51.8	51.1
110°	268.3	210.6	159.4	120.5	95.8	80.2	70.7	64.3	60.1	58.3	57.6



TEST NUMBER: P332867

CATALOG NUMBER: SA4XXRDIP-C350D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	259.5	208.1	161.1	124.8	101.4	86.4	76.9	70.5	66.6	64.5	63.8
115°	251.3	206.8	164.3	131.5	110.3	96.1	86.6	79.9	76.3	73.9	72.8
117.5°	247.6	206.4	167.8	138.3	118.8	105.4	95.5	89.2	85.3	83.1	82.1
120°	245.6	206.4	170.4	143.1	124.8	111.3	101.4	95.4	91.5	89.1	88.4
122.5°	243.4	206.1	172.9	147.7	130.4	117.0	107.4	100.8	97.2	94.7	94.0
125°	239.6	205.7	176.7	154.4	138.2	125.5	115.6	108.9	105.0	102.8	101.4
127.5°	234.6	204.9	179.8	160.3	145.4	133.1	123.1	116.1	111.7	109.1	108.0
130°	231.5	204.6	182.0	164.0	150.2	138.2	127.9	121.2	115.9	113.1	111.7
132.5°	228.7	204.4	184.0	167.7	154.2	142.1	132.5	125.2	120.2	116.5	115.4
135°	224.4	203.9	187.0	172.5	159.7	148.1	138.9	131.5	125.5	121.9	120.5
137.5°	220.8	203.9	188.7	175.9	164.0	153.1	144.3	136.6	130.9	127.0	125.7
140°	218.8	203.6	190.1	178.1	166.8	156.2	147.7	140.3	134.3	130.4	129.4
142.5°	217.1	203.6	191.3	179.8	169.4	159.0	150.8	143.7	138.0	134.4	133.3
145°	214.2	202.9	191.9	181.7	172.1	162.9	155.2	148.4	143.5	140.0	138.9
147.5°	211.6	201.6	192.3	183.3	174.9	166.3	159.3	153.7	148.7	145.5	145.2
150°	209.6	200.7	192.3	184.1	176.4	168.6	161.9	156.6	152.3	149.5	149.1
152.5°	207.3	199.3	191.7	184.7	177.5	170.6	164.4	159.7	155.7	152.9	152.8
155°	203.9	197.2	190.9	185.2	179.2	173.2	167.9	164.0	160.5	158.3	158.0
157.5°	200.5	195.0	189.9	185.2	180.4	175.3	171.1	167.7	165.0	163.0	163.0
160°	197.9	193.3	189.1	185.2	181.0	176.7	172.8	170.0	167.5	166.1	166.1
162.5°	195.7	191.6	188.2	185.2	181.5	177.6	174.5	172.0	169.8	168.7	168.9
165°	191.9	189.1	186.6	184.5	181.7	178.5	176.4	174.6	172.8	172.1	172.1
167.5°	188.5	186.5	184.9	183.6	181.6	179.3	177.6	176.6	175.3	174.9	175.3
170°	186.3	184.8	183.8	183.1	181.3	179.5	178.5	177.8	176.7	176.4	176.7
172.5°	184.3	183.1	182.7	182.5	181.0	179.8	179.0	178.6	177.8	177.8	178.1
175°	182.0	181.3	181.3	181.7	180.6	179.9	179.9	179.5	179.2	179.2	179.5
177.5°	180.5	180.2	180.2	180.7	180.2	179.9	179.9	179.9	179.6	179.9	180.2
180°	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9



TEST NUMBER: P332867

CATALOG NUMBER: SA4XXRDIP-C350D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4	587.4
2.5°	591.0	592.7	594.6	598.2	601.2	602.6	605.2	607.1	606.5	609.2	613.7
5°	593.3	599.7	607.1	614.6	623.1	630.2	635.9	641.6	646.1	651.5	659.6
7.5°	592.9	604.3	616.7	630.2	644.2	656.3	667.4	678.8	688.9	699.9	714.4
10°	591.4	606.6	622.0	639.7	657.5	674.3	689.4	703.6	717.1	731.5	749.8
12.5°	589.7	607.1	625.7	647.1	669.2	689.4	707.2	727.7	744.6	763.2	784.2
15°	582.2	605.6	631.0	658.6	685.2	712.4	736.7	761.8	785.3	807.5	834.0
17.5°	573.6	600.6	630.5	663.2	695.0	728.1	757.1	788.7	812.6	842.5	867.1
20°	566.6	595.7	627.6	664.3	700.5	737.2	769.2	801.4	828.3	858.4	889.6
22.5°	558.1	590.0	624.6	662.6	700.5	740.6	776.0	808.0	841.4	875.2	907.4
25°	544.3	577.5	614.2	655.8	699.4	740.3	778.2	817.9	853.9	890.6	919.5
27.5°	527.5	562.3	600.9	643.9	688.6	730.5	775.1	817.5	853.7	889.0	914.2
30°	514.0	550.7	587.9	631.4	677.8	722.8	770.6	813.0	851.1	882.8	897.0
32.5°	500.2	535.0	573.3	617.4	664.9	713.3	760.7	804.1	839.3	858.3	858.7
35°	476.2	508.8	548.6	591.9	640.7	693.2	741.2	783.8	805.4	807.0	783.8
37.5°	450.0	479.9	517.4	560.8	614.2	666.5	715.5	743.9	751.1	727.0	684.2
40°	431.2	458.9	495.1	539.6	592.6	646.6	691.3	712.1	704.6	665.5	617.7
42.5°	411.5	437.3	472.2	516.1	569.3	623.9	662.0	673.1	653.1	608.0	552.0
45°	379.4	403.0	437.6	481.9	533.0	584.1	613.0	607.3	573.9	520.4	457.7
47.5°	345.9	368.8	399.9	440.8	493.2	537.3	556.8	539.7	492.2	433.4	382.4
50°	323.8	347.2	375.8	414.9	462.7	505.3	517.8	491.8	439.0	382.5	335.6
52.5°	302.0	322.0	350.1	387.8	433.5	469.5	476.2	446.2	391.7	341.0	299.4
55°	268.9	287.1	310.7	346.2	385.8	416.3	412.7	374.2	324.7	281.4	248.7
57.5°	236.8	250.5	272.4	305.7	340.4	360.9	347.9	315.0	268.9	233.4	205.9
60°	215.6	228.4	248.7	277.8	308.4	320.0	309.1	273.4	236.9	204.5	181.3
62.5°	195.5	206.8	224.3	251.3	276.0	282.9	271.2	240.0	207.2	179.5	160.3
65°	166.4	176.8	191.7	210.9	227.9	231.2	223.7	191.7	166.9	143.7	130.4
67.5°	139.9	146.7	158.4	174.9	184.0	185.9	171.3	151.2	129.3	115.1	105.1
70°	122.1	126.9	137.7	146.7	154.1	154.3	140.8	124.7	107.9	96.3	89.0
72.5°	104.9	109.4	117.7	123.8	129.5	127.6	115.3	102.6	89.0	80.2	74.8
75°	80.9	85.0	89.2	92.1	92.1	89.7	80.7	71.2	63.4	58.2	56.6
77.5°	58.8	62.1	63.6	63.1	62.3	58.6	52.9	46.7	43.9	41.5	40.2
80°	46.2	47.6	48.0	46.9	45.4	41.2	37.4	34.8	32.2	31.2	30.8
82.5°	34.2	35.5	34.2	34.6	31.4	27.9	25.8	24.9	23.9	23.5	23.0
85°	18.2	18.0	17.5	16.3	14.2	13.7	13.5	13.3	12.8	13.0	12.5
87.5°	6.5	6.1	5.4	5.3	5.3	5.3	5.5	5.7	5.8	5.6	6.0
90°	1.1	2.1	2.5	2.8	2.8	4.9	4.9	5.7	6.4	6.0	6.4
92.5°	5.9	9.2	13.5	18.7	26.0	44.0	71.4	98.1	112.1	93.4	69.4
95°	12.7	16.3	20.9	29.3	44.2	74.9	132.9	217.4	288.0	296.2	261.9
97.5°	20.9	24.0	28.2	35.5	47.9	71.6	119.5	203.4	303.4	372.1	386.9
100°	26.9	29.3	33.6	40.3	51.6	72.5	112.4	184.5	284.2	374.6	426.2
102.5°	33.1	35.3	39.2	45.7	56.4	75.3	110.4	171.8	260.1	353.4	424.3
105°	42.4	44.2	48.4	54.8	65.0	82.0	111.3	160.8	231.8	314.9	395.8
107.5°	51.8	53.6	58.1	64.2	74.3	89.8	116.6	158.8	216.0	283.8	355.5
110°	58.3	60.1	64.3	70.7	80.2	95.8	120.5	159.4	210.6	268.3	331.2





TEST NUMBER: P332867

CATALOG NUMBER: SA4XXRDIP-C350D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	64.5	66.6	70.5	76.9	86.4	101.4	124.8	161.1	208.1	259.5	313.3
115°	73.9	76.3	79.9	86.6	96.1	110.3	131.5	164.3	206.8	251.3	295.5
117.5°	83.1	85.3	89.2	95.5	105.4	118.8	138.3	167.8	206.4	247.6	286.7
120°	89.1	91.5	95.4	101.4	111.3	124.8	143.1	170.4	206.4	245.6	282.7
122.5°	94.7	97.2	100.8	107.4	117.0	130.4	147.7	172.9	206.1	243.4	279.3
125°	102.8	105.0	108.9	115.6	125.5	138.2	154.4	176.7	205.7	239.6	273.6
127.5°	109.1	111.7	116.1	123.1	133.1	145.4	160.3	179.8	204.9	234.6	266.5
130°	113.1	115.9	121.2	127.9	138.2	150.2	164.0	182.0	204.6	231.5	260.8
132.5°	116.5	120.2	125.2	132.5	142.1	154.2	167.7	184.0	204.4	228.7	254.9
135°	121.9	125.5	131.5	138.9	148.1	159.7	172.5	187.0	203.9	224.4	246.7
137.5°	127.0	130.9	136.6	144.3	153.1	164.0	175.9	188.7	203.9	220.8	239.3
140°	130.4	134.3	140.3	147.7	156.2	166.8	178.1	190.1	203.6	218.8	235.0
142.5°	134.4	138.0	143.7	150.8	159.0	169.4	179.8	191.3	203.6	217.1	231.1
145°	140.0	143.5	148.4	155.2	162.9	172.1	181.7	191.9	202.9	214.2	225.5
147.5°	145.5	148.7	153.7	159.3	166.3	174.9	183.3	192.3	201.6	211.6	220.9
150°	149.5	152.3	156.6	161.9	168.6	176.4	184.1	192.3	200.7	209.6	218.1
152.5°	152.9	155.7	159.7	164.4	170.6	177.5	184.7	191.7	199.3	207.3	215.0
155°	158.3	160.5	164.0	167.9	173.2	179.2	185.2	190.9	197.2	203.9	210.3
157.5°	163.0	165.0	167.7	171.1	175.3	180.4	185.2	189.9	195.0	200.5	205.3
160°	166.1	167.5	170.0	172.8	176.7	181.0	185.2	189.1	193.3	197.9	202.2
162.5°	168.7	169.8	172.0	174.5	177.6	181.5	185.2	188.2	191.6	195.7	199.1
165°	172.1	172.8	174.6	176.4	178.5	181.7	184.5	186.6	189.1	191.9	194.7
167.5°	174.9	175.3	176.6	177.6	179.3	181.6	183.6	184.9	186.5	188.5	190.6
170°	176.4	176.7	177.8	178.5	179.5	181.3	183.1	183.8	184.8	186.3	188.0
172.5°	177.8	177.8	178.6	179.0	179.8	181.0	182.5	182.7	183.1	184.3	185.8
175°	179.2	179.2	179.5	179.9	179.9	180.6	181.7	181.3	181.3	182.0	182.7
177.5°	179.9	179.6	179.9	179.9	179.9	180.2	180.7	180.2	180.2	180.5	180.7
180°	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9



TEST NUMBER: P332867

CATALOG NUMBER: SA4XXRDIP-C350D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	587.4	587.4	587.4	587.4	587.4	587.4	587.4
2.5°	616.2	616.9	617.5	619.4	619.6	621.3	619.6
5°	667.2	670.5	675.7	680.9	681.4	684.7	678.8
7.5°	724.3	732.0	736.8	745.2	748.5	750.6	747.2
10°	763.7	770.8	783.4	789.5	795.7	796.6	793.8
12.5°	801.8	813.0	822.9	834.6	834.3	842.6	839.6
15°	852.5	864.1	877.8	890.8	895.5	895.5	899.3
17.5°	888.6	909.9	924.1	934.3	945.5	947.4	946.1
20°	913.1	936.0	951.2	964.4	972.0	974.1	974.1
22.5°	931.2	950.8	965.6	977.5	983.7	986.2	985.5
25°	943.8	960.6	969.6	973.2	974.8	974.4	969.9
27.5°	926.6	925.8	920.2	909.3	901.1	896.1	890.4
30°	893.7	881.3	867.1	851.5	831.4	816.0	811.3
32.5°	844.6	817.0	792.9	766.9	745.3	729.9	723.4
35°	749.8	706.0	670.2	639.0	616.3	602.1	597.3
37.5°	637.2	594.8	550.6	520.3	501.4	487.1	481.8
40°	565.6	519.5	480.9	452.5	433.1	419.1	418.9
42.5°	500.3	456.2	419.9	399.5	378.6	369.3	369.3
45°	409.7	374.4	343.6	327.5	315.0	307.4	305.3
47.5°	339.2	310.0	289.5	276.7	266.5	261.7	258.5
50°	299.6	274.1	257.7	246.6	240.9	234.8	234.3
52.5°	266.7	246.0	233.3	224.3	217.1	213.4	213.5
55°	224.1	207.8	198.8	191.9	186.3	183.4	182.2
57.5°	188.8	176.6	170.0	163.7	161.3	159.1	158.5
60°	166.9	158.6	152.4	147.4	143.9	143.2	142.9
62.5°	148.7	140.0	135.8	131.9	129.3	128.2	127.8
65°	122.6	116.2	112.4	109.3	108.4	106.7	106.5
67.5°	98.8	95.0	92.5	90.4	89.1	89.0	89.0
70°	84.3	82.1	80.0	78.8	78.1	77.6	77.6
72.5°	71.8	70.2	68.4	67.8	67.7	67.2	67.0
75°	54.7	53.0	53.3	52.1	51.1	49.9	49.2
77.5°	38.8	37.6	37.3	37.2	36.4	36.3	36.6
80°	30.1	28.9	28.6	28.9	28.6	27.9	27.9
82.5°	22.9	21.9	21.6	21.5	21.3	21.5	21.1
85°	12.3	11.8	11.8	11.8	12.3	12.1	11.8
87.5°	5.7	5.6	5.8	5.6	5.7	5.5	5.6
90°	6.7	7.1	7.1	7.4	7.8	7.4	7.4
92.5°	52.2	41.6	34.5	30.3	28.4	27.2	27.2
95°	207.1	159.7	125.5	108.1	97.2	90.8	86.2
97.5°	366.6	332.0	295.1	269.7	248.5	237.9	230.5
100°	433.3	416.0	389.8	359.1	337.5	326.9	324.1
102.5°	459.3	464.3	453.4	434.6	419.0	407.8	405.5
105°	457.0	492.0	506.5	507.2	504.3	499.4	497.3
107.5°	420.6	469.8	501.4	518.8	526.9	530.4	531.3
110°	392.3	443.6	482.4	507.5	522.4	528.7	531.9



TEST NUMBER: P332867

CATALOG NUMBER: SA4XXRDIP-C350D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	367.4	415.8	454.7	483.2	501.2	510.1	515.2
115°	338.9	380.3	414.2	442.1	463.3	474.7	477.5
117.5°	322.7	355.2	384.0	407.8	425.6	437.0	439.2
120°	315.6	343.9	369.0	389.1	404.7	413.9	417.8
122.5°	311.1	336.8	358.8	375.8	389.1	396.9	400.8
125°	303.9	328.3	347.8	361.9	372.2	378.9	381.0
127.5°	295.5	319.9	338.3	352.5	361.6	367.3	369.4
130°	288.8	312.8	331.5	346.0	354.8	360.5	362.6
132.5°	281.1	304.6	323.3	337.5	347.5	352.9	355.0
135°	269.7	291.2	308.9	323.0	332.9	338.6	340.7
137.5°	258.7	276.9	292.8	306.1	315.8	320.5	323.0
140°	251.6	267.5	282.4	294.8	302.5	307.5	310.3
142.5°	245.7	259.3	272.2	283.2	290.4	294.8	296.7
145°	237.5	248.1	258.0	266.8	272.8	276.4	278.1
147.5°	230.4	238.9	246.7	253.2	258.4	261.0	261.7
150°	226.2	233.3	239.6	245.3	249.9	252.0	252.3
152.5°	222.0	228.5	233.7	238.5	242.2	243.5	243.9
155°	215.9	221.2	225.5	229.0	231.8	232.9	232.9
157.5°	210.0	214.5	217.9	220.5	222.7	223.3	223.3
160°	206.0	209.9	212.8	214.9	217.0	217.4	217.4
162.5°	202.4	205.4	208.0	209.5	211.6	212.0	211.7
165°	196.9	199.3	201.1	202.5	203.9	203.6	203.2
167.5°	192.2	194.2	195.2	195.9	196.9	196.8	196.5
170°	189.1	190.5	191.6	192.3	192.6	192.3	192.3
172.5°	186.5	187.4	188.2	188.6	188.9	188.6	188.0
175°	183.1	183.8	183.8	183.8	184.5	183.8	183.1
177.5°	181.0	181.0	181.3	181.0	181.3	180.7	180.2
180°	179.9	179.9	179.9	179.9	179.9	179.9	179.9

(END OF REPORT)