

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332903

Luminaire Tested: **SA4XXRDIP-C575D590U835-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332903  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXRDIP-C575D590U835-4F0-1E-UDD-A4  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 575 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4554.4 lumens  
Efficiency: N/A  
Efficacy: 138.9 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 32.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332903  
CATALOG NUMBER: SA4XXRDIP-C575D590U835-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P332903

CATALOG NUMBER: SA4XXRDIP-C575D590U835-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	54
1	99	95	91	88	92	88	85	82	76	73	71	64	62	61	53	52	51	46
2	91	83	78	73	84	78	73	68	67	63	60	57	54	52	48	46	44	39
3	83	74	67	61	77	69	63	58	59	55	51	51	47	44	43	40	38	34
4	76	66	58	52	70	61	54	49	53	48	44	45	41	38	38	35	33	30
5	70	59	51	45	65	55	48	43	48	42	38	41	37	33	35	32	29	26
6	65	53	45	39	60	49	42	37	43	37	33	37	33	29	32	28	26	23
7	60	48	40	34	55	45	38	33	39	34	29	34	29	26	29	26	23	20
8	56	43	36	31	52	41	34	29	36	30	26	31	27	23	27	23	21	18
9	52	40	32	27	48	37	31	26	33	27	24	29	24	21	25	21	19	17
10	48	37	29	25	45	34	28	24	30	25	21	26	22	19	23	20	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	7796	7796	7796	7796
5°	9043	7819	6912	7819
10°	10698	7785	6169	7785
15°	12357	7713	5300	7713
20°	13759	7614	4793	7614
25°	14203	7517	4450	7517
30°	12433	7399	4243	7399
35°	9678	7224	4119	7224
40°	7258	7024	4051	7024
45°	5730	6703	4015	6703
50°	4838	6332	3900	6332
55°	4217	5925	3690	5925
60°	3794	5503	3266	5503
65°	3345	5047	2810	5047
70°	3012	4574	2535	4574
75°	2523	4055	2162	4055
80°	2134	3454	2027	3454
85°	1806	2705	1806	2705



TEST NUMBER: P332903

CATALOG NUMBER: SA4XXRDIP-C575D590U835-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	93.6	2.1
10°-20°	282.2	6.2
20°-30°	441.5	9.7
30°-40°	490.8	10.8
40°-50°	435.4	9.6
50°-60°	339.3	7.4
60°-70°	222.1	4.9
70°-80°	109.2	2.4
80°-90°	28.6	0.6
90°-100°	209.7	4.6
100°-110°	436.5	9.6
110°-120°	391.0	8.6
120°-130°	328.9	7.2
130°-140°	274.2	6.0
140°-150°	209.5	4.6
150°-160°	147.2	3.2
160°-170°	86.6	1.9
170°-180°	28.2	0.6
0°-30°	817.3	17.9
0°-40°	1308.0	28.7
0°-60°	2082.7	45.7
0°-90°	2442.7	53.6
90°-120°	1037.2	22.8
90°-150°	1849.7	40.6
90°-180°	2112.0	46.4
0°-180°	4554.4	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	966	966	966	966	966	
5°	1116	965	853	965	1116	113
15°	1478	923	634	923	1478	420
25°	1594	844	500	844	1594	707
35°	982	733	418	733	982	616
45°	502	587	352	587	502	397
55°	300	421	262	421	300	273
65°	175	264	147	264	175	176
75°	81	130	69	130	81	89
85°	20	29	20	29	20	22
90°	12	1	12	1	12	11
95°	139	19	139	19	139	216
105°	803	67	803	67	803	794
115°	771	118	771	118	771	765
125°	615	164	615	164	615	559
135°	550	194	550	194	550	424
145°	449	224	449	224	449	285
155°	376	255	376	255	376	175
165°	328	278	328	278	328	94
175°	296	290	296	290	296	29
180°	290	290	290	290	290	



TEST NUMBER: P332903

CATALOG NUMBER: SA4XXRDIP-C575D590U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7
2.5°	1018.6	1021.4	1018.6	1018.3	1015.2	1014.3	1013.0	1009.0	1001.5	997.1	998.1
5°	1115.9	1125.6	1120.2	1119.4	1110.8	1102.3	1096.8	1084.4	1071.1	1062.2	1054.8
7.5°	1228.4	1234.0	1230.6	1225.1	1211.3	1203.4	1190.8	1174.4	1150.7	1132.5	1116.0
10°	1305.0	1309.6	1308.1	1298.0	1287.9	1267.2	1255.6	1232.6	1202.6	1178.9	1156.7
12.5°	1380.3	1385.3	1371.6	1372.1	1352.9	1336.6	1318.1	1289.3	1254.6	1224.0	1196.3
15°	1478.5	1472.3	1472.3	1464.5	1443.1	1420.5	1401.5	1371.1	1327.5	1291.0	1252.5
17.5°	1555.4	1557.6	1554.4	1536.0	1519.2	1495.9	1460.9	1425.5	1385.0	1335.9	1296.6
20°	1601.5	1601.5	1598.0	1585.5	1563.7	1538.8	1501.1	1462.6	1411.2	1361.8	1317.4
22.5°	1620.1	1621.4	1617.3	1607.0	1587.4	1563.1	1531.0	1491.8	1438.9	1383.3	1328.3
25°	1594.5	1601.8	1602.6	1599.9	1594.1	1579.3	1551.7	1511.6	1464.1	1403.8	1344.7
27.5°	1463.9	1473.2	1481.4	1494.8	1512.7	1522.1	1523.3	1502.9	1461.5	1403.5	1344.0
30°	1333.8	1341.5	1366.8	1399.9	1425.6	1448.9	1469.2	1474.6	1451.3	1399.1	1336.5
32.5°	1189.3	1199.9	1225.2	1260.8	1303.6	1343.1	1388.6	1411.7	1411.1	1379.8	1321.9
35°	982.0	989.8	1013.2	1050.5	1101.9	1160.6	1232.6	1288.6	1326.8	1324.0	1288.6
37.5°	792.0	800.8	824.4	855.4	905.2	977.9	1047.6	1124.8	1195.3	1234.9	1223.0
40°	688.7	689.1	712.0	743.9	790.6	854.0	929.9	1015.5	1094.1	1158.3	1170.7
42.5°	607.1	607.2	622.4	656.8	690.4	750.1	822.5	907.5	999.5	1073.6	1106.6
45°	501.9	505.4	517.9	538.5	564.9	615.5	673.5	752.5	855.6	943.5	998.4
47.5°	425.0	430.2	438.1	454.9	476.0	509.7	557.6	628.6	712.5	809.2	887.3
50°	385.2	386.0	396.1	405.4	423.7	450.6	492.6	551.7	628.8	721.7	808.5
52.5°	351.0	350.8	356.9	368.7	383.6	404.5	438.4	492.3	560.6	643.9	733.5
55°	299.6	301.5	306.2	315.5	326.8	341.6	368.5	408.9	462.6	533.8	615.1
57.5°	260.5	261.5	265.2	269.2	279.5	290.3	310.4	338.5	383.8	442.1	517.9
60°	235.0	235.4	236.6	242.4	250.6	260.7	274.3	298.0	336.2	389.5	449.4
62.5°	210.1	210.8	212.6	216.9	223.2	230.2	244.4	263.5	295.1	340.6	394.6
65°	175.1	175.5	178.2	179.8	184.8	191.0	201.5	214.4	236.2	274.3	315.2
67.5°	146.3	146.3	146.4	148.6	152.1	156.2	162.5	172.8	189.2	212.6	248.6
70°	127.6	127.6	128.4	129.6	131.5	135.0	138.5	146.3	158.4	177.4	205.0
72.5°	110.2	110.5	111.3	111.5	112.5	115.4	118.0	122.9	131.9	146.3	168.6
75°	80.9	82.1	84.0	85.6	87.5	87.2	89.9	93.0	95.7	104.3	117.1
77.5°	60.2	59.6	59.8	61.2	61.4	61.8	63.7	66.1	68.2	72.2	76.8
80°	45.9	45.9	47.1	47.5	47.1	47.5	49.4	50.6	51.4	52.9	57.2
82.5°	34.7	35.3	34.9	35.3	35.6	36.0	37.6	37.8	38.6	39.2	41.0
85°	19.5	19.8	20.2	19.5	19.5	19.5	20.2	20.6	21.4	21.0	21.8
87.5°	9.2	8.9	9.4	9.2	9.4	9.1	9.3	9.8	9.1	9.5	9.3
90°	12.0	12.0	12.5	12.0	11.4	11.4	10.8	10.3	9.7	10.3	9.1
92.5°	43.9	43.9	45.9	48.9	55.7	67.1	84.3	112.0	150.7	180.9	158.4
95°	139.2	146.6	156.9	174.6	202.5	257.8	334.3	422.7	478.0	464.9	350.8
97.5°	372.0	383.9	401.0	435.4	476.3	535.9	591.7	624.5	600.6	489.7	328.4
100°	523.1	527.7	544.8	579.6	629.2	671.4	699.4	688.0	604.7	458.6	297.8
102.5°	654.5	658.2	676.2	701.4	731.9	749.5	741.4	684.8	570.4	419.9	277.2
105°	802.6	806.0	814.0	818.6	817.5	794.1	737.6	638.9	508.3	374.2	259.6
107.5°	857.6	856.1	850.4	837.4	809.2	758.4	678.8	573.8	458.1	348.7	256.4
110°	858.5	853.4	843.1	819.2	778.7	715.9	633.2	534.5	433.0	340.0	257.3



TEST NUMBER: P332903

CATALOG NUMBER: SA4XXRDIP-C575D590U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	831.6	823.3	808.9	779.9	733.9	671.2	593.0	505.8	418.8	335.9	260.0
115°	770.7	766.1	747.9	713.6	668.6	613.8	547.1	476.9	405.6	333.7	265.3
117.5°	709.0	705.4	686.9	658.2	619.7	573.3	520.8	462.7	399.7	333.1	270.8
120°	674.3	668.0	653.2	628.1	595.5	555.0	509.4	456.4	396.5	333.1	275.0
122.5°	646.9	640.6	628.1	606.6	579.1	543.6	502.1	450.9	392.8	332.7	279.1
125°	614.9	611.5	600.7	584.1	561.3	529.9	490.6	441.5	386.8	332.0	285.2
127.5°	596.2	592.8	583.7	569.0	546.0	516.3	477.0	430.1	378.7	330.7	290.1
130°	585.3	581.9	572.7	558.5	535.1	504.8	466.1	421.0	373.6	330.3	293.8
132.5°	573.0	569.5	560.9	544.8	521.8	491.6	453.7	411.4	369.1	329.8	297.0
135°	549.9	546.5	537.4	521.4	498.6	470.0	435.3	398.2	362.2	329.1	301.8
137.5°	521.4	517.3	509.8	494.0	472.7	446.9	417.6	386.2	356.3	329.0	304.6
140°	500.9	496.3	488.3	475.8	455.8	431.8	406.2	379.3	353.1	328.6	306.9
142.5°	478.9	475.8	468.7	457.0	439.4	418.6	396.6	373.0	350.4	328.6	308.7
145°	448.9	446.1	440.4	430.7	416.4	400.5	383.3	363.9	345.7	327.4	309.8
147.5°	422.4	421.3	417.0	408.7	398.2	385.6	371.9	356.5	341.5	325.4	310.3
150°	407.3	406.7	403.3	395.9	386.8	376.5	365.1	352.0	338.3	324.0	310.3
152.5°	393.6	393.0	391.0	384.9	377.2	368.7	358.2	346.9	334.6	321.7	309.4
155°	375.9	375.9	374.2	369.7	363.9	357.1	348.5	339.4	329.1	318.3	308.0
157.5°	360.4	360.4	359.4	356.0	351.6	346.1	339.0	331.3	323.6	314.8	306.6
160°	350.8	350.8	350.3	346.8	343.4	338.8	332.6	326.3	319.5	312.0	305.2
162.5°	341.7	342.2	341.6	338.2	335.7	331.5	326.6	321.3	315.8	309.3	303.8
165°	328.0	328.6	329.1	326.9	324.6	321.7	317.7	314.3	309.8	305.2	301.2
167.5°	317.2	317.6	317.7	316.3	315.1	313.4	310.2	307.6	304.3	301.1	298.5
170°	310.3	310.3	310.9	310.3	309.2	307.5	305.2	303.5	300.6	298.3	296.6
172.5°	303.5	304.4	305.0	304.4	303.7	302.5	301.1	299.8	297.4	295.6	294.8
175°	295.5	296.6	297.8	296.6	296.6	296.6	295.5	294.9	293.8	292.6	292.6
177.5°	290.8	291.7	292.6	292.2	292.6	292.2	292.2	291.7	291.3	290.8	290.8
180°	290.4	290.4	290.4	290.4	290.4	290.4	290.4	290.4	290.4	290.4	290.4



TEST NUMBER: P332903

CATALOG NUMBER: SA4XXRDIP-C575D590U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7
2.5°	995.0	990.6	988.4	983.4	977.5	974.4	971.6	967.6	962.3	956.7	952.6
5°	1045.5	1036.1	1024.4	1010.4	998.0	985.9	975.4	964.9	952.9	940.4	928.0
7.5°	1097.3	1078.9	1059.1	1036.1	1013.8	993.5	974.8	956.9	936.7	918.5	902.0
10°	1133.4	1108.5	1080.9	1051.7	1022.5	997.2	972.3	949.7	924.8	902.7	884.0
12.5°	1162.7	1133.4	1100.2	1063.8	1028.7	998.1	969.5	940.1	911.8	887.7	862.8
15°	1211.2	1171.1	1126.4	1082.8	1037.3	995.7	957.1	922.9	890.6	856.8	833.0
17.5°	1244.6	1197.0	1142.7	1090.3	1036.5	987.4	943.0	902.2	864.9	830.4	802.1
20°	1264.5	1212.0	1151.7	1092.1	1031.8	979.3	931.5	886.3	847.8	810.5	781.3
22.5°	1275.7	1217.6	1151.7	1089.3	1026.9	970.0	917.5	870.5	828.5	791.2	758.9
25°	1279.3	1217.0	1149.7	1078.1	1009.7	949.4	894.9	843.9	797.2	759.9	725.6
27.5°	1274.3	1201.0	1132.1	1058.6	988.0	924.4	867.2	813.6	766.9	726.8	691.7
30°	1266.8	1188.3	1114.3	1038.1	966.5	905.4	845.1	793.7	745.1	703.5	668.1
32.5°	1250.7	1172.7	1093.2	1015.0	942.5	879.6	822.4	770.7	723.0	680.4	642.8
35°	1218.6	1139.6	1053.2	973.1	901.9	836.5	782.8	733.0	687.5	642.0	602.3
37.5°	1176.3	1095.7	1009.7	922.0	850.7	789.0	739.7	693.0	648.5	607.0	563.0
40°	1136.5	1063.0	974.3	887.1	814.0	754.4	708.9	666.5	621.8	580.5	536.5
42.5°	1088.3	1025.6	936.0	848.5	776.3	718.9	676.5	635.1	594.4	554.4	508.5
45°	1007.7	960.3	876.2	792.2	719.4	662.6	623.7	587.1	551.3	513.2	470.0
47.5°	915.4	883.3	810.8	724.7	657.4	606.3	568.7	538.8	508.5	470.4	432.5
50°	851.3	830.7	760.7	682.1	617.9	570.8	532.3	504.2	479.0	442.4	408.5
52.5°	782.8	771.9	712.7	637.5	575.5	529.4	496.5	471.3	445.7	415.3	383.6
55°	678.6	684.4	634.2	569.2	510.9	472.0	442.0	421.0	399.2	373.5	349.0
57.5°	571.9	593.3	559.6	502.5	447.8	411.9	389.3	371.6	353.4	332.0	311.1
60°	508.1	526.0	507.0	456.8	408.9	375.5	354.5	340.8	322.5	303.1	287.1
62.5°	445.9	465.0	453.7	413.2	368.8	340.0	321.5	308.8	295.2	278.2	261.6
65°	367.7	380.1	374.7	346.7	315.2	290.6	273.5	264.2	251.7	239.3	224.5
67.5°	281.6	305.7	302.5	287.6	260.4	241.2	230.0	221.8	210.4	201.2	191.1
70°	231.5	253.7	253.3	241.2	226.4	208.5	200.8	193.8	183.6	174.7	166.5
72.5°	189.5	209.8	212.8	203.6	193.5	179.9	172.4	167.6	157.8	151.7	145.0
75°	132.7	147.5	151.4	151.4	146.7	139.7	133.1	130.0	122.9	117.5	113.6
77.5°	87.0	96.3	102.4	103.8	104.5	102.2	96.7	94.5	89.2	87.2	83.5
80°	61.5	67.7	74.7	77.0	79.0	78.2	75.9	74.3	69.3	67.3	65.8
82.5°	42.5	45.9	51.7	56.8	56.3	58.3	56.3	55.0	51.2	50.5	48.9
85°	22.2	22.6	23.3	26.8	28.8	29.6	30.0	29.2	28.0	28.0	25.3
87.5°	9.1	8.8	8.7	8.7	8.9	10.0	10.6	10.7	10.0	9.4	8.6
90°	8.0	8.0	4.6	4.6	4.0	3.4	1.7	0.6	1.7	3.4	4.0
92.5°	115.2	71.0	42.0	30.1	21.8	14.8	9.5	6.5	9.5	14.8	21.8
95°	214.5	120.9	71.3	47.3	33.7	26.2	20.5	18.8	20.5	26.2	33.7
97.5°	192.8	115.6	77.4	57.3	45.5	38.7	33.8	33.8	33.8	38.7	45.5
100°	181.4	116.9	83.3	65.0	54.2	47.3	43.4	43.4	43.4	47.3	54.2
102.5°	178.2	121.5	91.0	73.7	63.3	56.9	53.4	52.5	53.4	56.9	63.3
105°	179.7	132.3	105.0	88.4	78.2	71.3	68.5	66.7	68.5	71.3	78.2
107.5°	188.1	145.0	119.9	103.6	93.8	86.5	83.6	82.5	83.6	86.5	93.8
110°	194.5	154.6	129.5	114.1	103.8	97.0	94.1	93.0	94.1	97.0	103.8





TEST NUMBER: P332903

CATALOG NUMBER: SA4XXRDIP-C575D590U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	201.4	163.7	139.5	124.1	113.9	107.5	104.2	103.0	104.2	107.5	113.9
115°	212.2	178.0	155.2	139.8	128.9	123.2	119.2	117.5	119.2	123.2	128.9
117.5°	223.3	191.8	170.1	154.1	144.0	137.7	134.2	132.6	134.2	137.7	144.0
120°	231.0	201.4	179.7	163.7	154.0	147.7	143.8	142.6	143.8	147.7	154.0
122.5°	238.3	210.5	188.8	173.3	162.7	156.9	152.9	151.7	152.9	156.9	162.7
125°	249.3	223.0	202.5	186.5	175.7	169.4	166.0	163.7	166.0	169.4	175.7
127.5°	258.8	234.7	214.8	198.7	187.4	180.3	176.2	174.3	176.2	180.3	187.4
130°	264.7	242.4	223.0	206.5	195.7	187.1	182.5	180.3	182.5	187.1	195.7
132.5°	270.6	248.8	229.4	213.8	202.1	194.0	188.0	186.2	188.0	194.0	202.1
135°	278.4	257.8	239.0	224.2	212.2	202.5	196.8	194.5	196.8	202.5	212.2
137.5°	283.9	264.7	247.1	233.0	220.5	211.3	205.0	202.9	205.0	211.3	220.5
140°	287.5	269.3	252.1	238.4	226.5	216.8	210.5	208.8	210.5	216.8	226.5
142.5°	290.2	273.4	256.7	243.5	231.9	222.7	216.9	215.2	216.9	222.7	231.9
145°	293.2	277.8	263.0	250.4	239.6	231.6	225.9	224.2	225.9	231.6	239.6
147.5°	295.8	282.4	268.5	257.2	248.1	239.9	234.9	234.3	234.9	239.9	248.1
150°	297.2	284.7	272.1	261.3	252.7	245.9	241.3	240.7	241.3	245.9	252.7
152.5°	298.1	286.5	275.3	265.4	257.7	251.3	246.8	246.7	246.8	251.3	257.7
155°	298.9	289.2	279.5	271.0	264.7	259.0	255.6	255.0	255.6	259.0	264.7
157.5°	298.9	291.2	282.9	276.2	270.7	266.3	263.1	263.1	263.1	266.3	270.7
160°	298.9	292.1	285.2	278.9	274.4	270.4	268.1	268.1	268.1	270.4	274.4
162.5°	298.9	293.0	286.6	281.7	277.6	274.0	272.2	272.7	272.2	274.0	277.6
165°	297.8	293.2	288.1	284.7	281.8	278.9	277.8	277.8	277.8	278.9	281.8
167.5°	296.4	293.1	289.3	286.7	285.1	282.9	282.4	282.9	282.4	282.9	285.1
170°	295.5	292.6	289.8	288.1	286.9	285.2	284.7	285.2	284.7	285.2	286.9
172.5°	294.6	292.2	290.2	289.0	288.3	287.0	286.9	287.5	286.9	287.0	288.3
175°	293.2	291.5	290.4	290.4	289.8	289.2	289.2	289.8	289.2	289.2	289.8
177.5°	291.7	290.8	290.4	290.4	290.4	289.9	290.4	290.8	290.4	289.9	290.4
180°	290.4	290.4	290.4	290.4	290.4	290.4	290.4	290.4	290.4	290.4	290.4



TEST NUMBER: P332903

CATALOG NUMBER: SA4XXRDIP-C575D590U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7
2.5°	948.3	945.2	941.1	936.4	930.8	925.9	923.7	925.5	926.5	924.0	923.7
5°	919.4	909.7	901.9	890.2	880.9	873.1	867.6	865.3	866.1	859.9	858.3
7.5°	886.9	875.4	862.7	848.8	835.9	824.5	818.5	815.2	808.6	805.8	801.0
10°	866.1	850.5	838.1	821.7	807.0	793.3	786.7	781.3	774.7	771.5	764.9
12.5°	844.6	826.6	812.9	795.9	780.8	764.4	758.1	748.0	737.6	731.1	722.6
15°	814.3	792.6	775.8	755.6	737.7	719.0	702.3	683.6	676.6	661.8	653.3
17.5°	778.9	756.8	736.1	709.0	681.4	658.2	640.3	622.5	611.7	602.3	597.9
20°	755.6	735.4	706.6	675.1	644.3	618.6	604.2	592.6	580.9	574.3	569.6
22.5°	733.5	707.7	674.2	640.2	609.5	589.4	577.2	565.2	555.7	549.4	543.2
25°	696.5	662.6	627.2	588.3	567.3	549.8	536.5	526.8	521.0	512.8	509.7
27.5°	658.4	617.4	578.3	552.2	530.3	514.3	502.8	495.5	488.1	482.8	478.8
30°	629.1	587.5	552.5	527.6	505.4	492.2	482.8	474.3	468.5	464.2	461.1
32.5°	600.2	558.6	529.1	502.4	484.9	472.0	462.0	455.6	451.0	445.5	443.6
35°	558.3	521.4	495.7	471.6	453.7	442.0	434.2	427.6	423.7	422.2	421.0
37.5°	518.1	487.8	460.2	440.4	424.5	415.3	406.1	402.9	400.2	397.4	398.7
40°	492.6	464.2	439.7	418.7	405.8	395.7	390.2	386.4	384.0	384.0	384.0
42.5°	470.5	442.7	418.8	400.0	387.1	378.6	372.5	369.2	368.5	368.1	370.0
45°	436.2	410.5	386.4	370.8	359.9	351.3	347.8	345.1	345.1	346.7	347.1
47.5°	402.2	378.1	358.7	341.3	331.3	326.0	322.9	321.5	321.7	323.2	325.0
50°	381.3	357.6	338.5	322.9	313.6	308.5	305.8	305.0	305.8	305.8	308.5
52.5°	358.6	337.3	318.6	305.5	294.9	290.2	288.7	287.6	288.1	289.3	290.5
55°	325.3	306.2	288.3	275.9	268.1	265.0	261.5	261.9	261.1	261.9	261.9
57.5°	291.9	274.8	258.1	248.2	241.4	236.9	233.1	234.1	233.0	232.8	232.2
60°	270.4	251.7	238.5	229.6	221.8	217.9	214.4	215.2	214.0	213.2	211.7
62.5°	247.1	231.5	218.9	210.3	204.0	199.5	196.0	195.2	192.5	189.9	186.4
65°	213.2	200.4	189.1	180.9	175.1	171.6	168.9	166.5	160.7	154.5	151.4
67.5°	180.3	171.0	160.5	153.6	148.9	144.3	139.1	135.1	129.6	126.2	124.3
70°	159.1	150.2	141.2	134.6	129.6	125.3	119.4	116.7	112.8	111.3	109.3
72.5°	138.9	130.6	122.2	116.3	110.9	107.5	103.0	100.2	98.5	97.9	95.9
75°	108.2	101.6	95.3	89.9	85.6	83.3	81.3	79.4	78.6	75.1	73.1
77.5°	78.9	74.5	70.7	66.8	63.7	62.2	58.4	56.2	54.9	53.2	52.8
80°	61.5	58.4	54.5	52.1	47.9	46.3	44.7	44.4	44.0	43.6	43.2
82.5°	46.2	43.1	39.2	37.8	36.7	35.7	34.8	34.4	34.0	34.2	34.2
85°	23.3	21.8	21.8	21.4	21.0	20.6	20.2	20.2	19.8	20.2	19.8
87.5°	8.7	8.4	9.1	8.4	9.0	9.2	8.8	8.9	9.3	8.8	8.8
90°	4.6	4.6	8.0	8.0	9.1	10.3	9.7	10.3	10.8	11.4	11.4
92.5°	30.1	42.0	71.0	115.2	158.4	180.9	150.7	112.0	84.3	67.1	55.7
95°	47.3	71.3	120.9	214.5	350.8	464.9	478.0	422.7	334.3	257.8	202.5
97.5°	57.3	77.4	115.6	192.8	328.4	489.7	600.6	624.5	591.7	535.9	476.3
100°	65.0	83.3	116.9	181.4	297.8	458.6	604.7	688.0	699.4	671.4	629.2
102.5°	73.7	91.0	121.5	178.2	277.2	419.9	570.4	684.8	741.4	749.5	731.9
105°	88.4	105.0	132.3	179.7	259.6	374.2	508.3	638.9	737.6	794.1	817.5
107.5°	103.6	119.9	145.0	188.1	256.4	348.7	458.1	573.8	678.8	758.4	809.2
110°	114.1	129.5	154.6	194.5	257.3	340.0	433.0	534.5	633.2	715.9	778.7



TEST NUMBER: P332903

CATALOG NUMBER: SA4XXRDIP-C575D590U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	124.1	139.5	163.7	201.4	260.0	335.9	418.8	505.8	593.0	671.2	733.9
115°	139.8	155.2	178.0	212.2	265.3	333.7	405.6	476.9	547.1	613.8	668.6
117.5°	154.1	170.1	191.8	223.3	270.8	333.1	399.7	462.7	520.8	573.3	619.7
120°	163.7	179.7	201.4	231.0	275.0	333.1	396.5	456.4	509.4	555.0	595.5
122.5°	173.3	188.8	210.5	238.3	279.1	332.7	392.8	450.9	502.1	543.6	579.1
125°	186.5	202.5	223.0	249.3	285.2	332.0	386.8	441.5	490.6	529.9	561.3
127.5°	198.7	214.8	234.7	258.8	290.1	330.7	378.7	430.1	477.0	516.3	546.0
130°	206.5	223.0	242.4	264.7	293.8	330.3	373.6	421.0	466.1	504.8	535.1
132.5°	213.8	229.4	248.8	270.6	297.0	329.8	369.1	411.4	453.7	491.6	521.8
135°	224.2	239.0	257.8	278.4	301.8	329.1	362.2	398.2	435.3	470.0	498.6
137.5°	233.0	247.1	264.7	283.9	304.6	329.0	356.3	386.2	417.6	446.9	472.7
140°	238.4	252.1	269.3	287.5	306.9	328.6	353.1	379.3	406.2	431.8	455.8
142.5°	243.5	256.7	273.4	290.2	308.7	328.6	350.4	373.0	396.6	418.6	439.4
145°	250.4	263.0	277.8	293.2	309.8	327.4	345.7	363.9	383.3	400.5	416.4
147.5°	257.2	268.5	282.4	295.8	310.3	325.4	341.5	356.5	371.9	385.6	398.2
150°	261.3	272.1	284.7	297.2	310.3	324.0	338.3	352.0	365.1	376.5	386.8
152.5°	265.4	275.3	286.5	298.1	309.4	321.7	334.6	346.9	358.2	368.7	377.2
155°	271.0	279.5	289.2	298.9	308.0	318.3	329.1	339.4	348.5	357.1	363.9
157.5°	276.2	282.9	291.2	298.9	306.6	314.8	323.6	331.3	339.0	346.1	351.6
160°	278.9	285.2	292.1	298.9	305.2	312.0	319.5	326.3	332.6	338.8	343.4
162.5°	281.7	286.6	293.0	298.9	303.8	309.3	315.8	321.3	326.6	331.5	335.7
165°	284.7	288.1	293.2	297.8	301.2	305.2	309.8	314.3	317.7	321.7	324.6
167.5°	286.7	289.3	293.1	296.4	298.5	301.1	304.3	307.6	310.2	313.4	315.1
170°	288.1	289.8	292.6	295.5	296.6	298.3	300.6	303.5	305.2	307.5	309.2
172.5°	289.0	290.2	292.2	294.6	294.8	295.6	297.4	299.8	301.1	302.5	303.7
175°	290.4	290.4	291.5	293.2	292.6	292.6	293.8	294.9	295.5	296.6	296.6
177.5°	290.4	290.4	290.8	291.7	290.8	290.8	291.3	291.7	292.2	292.2	292.6
180°	290.4	290.4	290.4	290.4	290.4	290.4	290.4	290.4	290.4	290.4	290.4



TEST NUMBER: P332903

CATALOG NUMBER: SA4XXRDIP-C575D590U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7
2.5°	921.8	922.4	920.3	919.6	920.3	922.4	921.8	923.7	924.0	926.5	925.5
5°	855.2	854.4	852.5	852.9	852.5	854.4	855.2	858.3	859.9	866.1	865.3
7.5°	798.2	795.2	796.1	792.9	796.1	795.2	798.2	801.0	805.8	808.6	815.2
10°	763.4	759.1	755.6	752.5	755.6	759.1	763.4	764.9	771.5	774.7	781.3
12.5°	715.8	712.1	707.3	708.3	707.3	712.1	715.8	722.6	731.1	737.6	748.0
15°	648.2	642.4	633.0	634.2	633.0	642.4	648.2	653.3	661.8	676.6	683.6
17.5°	591.0	591.1	586.8	587.8	586.8	591.1	591.0	597.9	602.3	611.7	622.5
20°	561.4	558.7	559.1	557.9	559.1	558.7	561.4	569.6	574.3	580.9	592.6
22.5°	540.9	537.6	534.8	532.4	534.8	537.6	540.9	543.2	549.4	555.7	565.2
25°	506.2	503.9	500.4	499.6	500.4	503.9	506.2	509.7	512.8	521.0	526.8
27.5°	475.7	475.2	473.8	472.0	473.8	475.2	475.7	478.8	482.8	488.1	495.5
30°	457.9	457.2	456.4	455.2	456.4	457.2	457.9	461.1	464.2	468.5	474.3
32.5°	442.1	441.6	440.8	440.9	440.8	441.6	442.1	443.6	445.5	451.0	455.6
35°	419.4	419.0	418.3	417.9	418.3	419.0	419.4	421.0	422.2	423.7	427.6
37.5°	398.3	399.3	398.8	398.7	398.8	399.3	398.3	398.7	397.4	400.2	402.9
40°	383.6	384.0	384.8	384.4	384.8	384.0	383.6	384.0	384.0	384.0	386.4
42.5°	371.5	371.6	372.7	371.3	372.7	371.6	371.5	370.0	368.1	368.5	369.2
45°	349.8	352.1	351.7	351.7	351.7	352.1	349.8	347.1	346.7	345.1	345.1
47.5°	326.0	328.1	328.6	328.5	328.6	328.1	326.0	325.0	323.2	321.7	321.5
50°	310.5	309.7	310.9	310.5	310.9	309.7	310.5	308.5	305.8	305.8	305.0
52.5°	291.5	291.7	291.6	291.2	291.6	291.7	291.5	290.5	289.3	288.1	287.6
55°	262.2	262.6	261.9	262.2	261.9	262.6	262.2	261.9	261.9	261.1	261.9
57.5°	230.5	228.6	229.4	228.5	229.4	228.6	230.5	232.2	232.8	233.0	234.1
60°	207.8	204.7	203.9	202.3	203.9	204.7	207.8	211.7	213.2	214.0	215.2
62.5°	182.2	180.1	177.4	178.7	177.4	180.1	182.2	186.4	189.9	192.5	195.2
65°	148.2	146.7	145.5	147.1	145.5	146.7	148.2	151.4	154.5	160.7	166.5
67.5°	122.7	121.9	121.9	121.1	121.9	121.9	122.7	124.3	126.2	129.6	135.1
70°	109.3	108.2	108.2	107.4	108.2	108.2	109.3	109.3	111.3	112.8	116.7
72.5°	95.6	94.5	94.8	94.3	94.8	94.5	95.6	95.9	97.9	98.5	100.2
75°	70.8	68.9	68.9	69.3	68.9	68.9	70.8	73.1	75.1	78.6	79.4
77.5°	52.8	52.4	53.0	52.3	53.0	52.4	52.8	52.8	53.2	54.9	56.2
80°	43.2	42.8	42.4	43.6	42.4	42.8	43.2	43.2	43.6	44.0	44.4
82.5°	33.5	33.5	33.4	34.9	33.4	33.5	33.5	34.2	34.2	34.0	34.4
85°	20.2	19.5	20.2	19.5	20.2	19.5	20.2	19.8	20.2	19.8	20.2
87.5°	9.6	9.4	8.9	9.2	8.9	9.4	9.6	8.8	8.8	9.3	8.9
90°	12.0	12.5	12.0	12.0	12.0	12.5	12.0	11.4	11.4	10.8	10.3
92.5°	48.9	45.9	43.9	43.9	43.9	45.9	48.9	55.7	67.1	84.3	112.0
95°	174.6	156.9	146.6	139.2	146.6	156.9	174.6	202.5	257.8	334.3	422.7
97.5°	435.4	401.0	383.9	372.0	383.9	401.0	435.4	476.3	535.9	591.7	624.5
100°	579.6	544.8	527.7	523.1	527.7	544.8	579.6	629.2	671.4	699.4	688.0
102.5°	701.4	676.2	658.2	654.5	658.2	676.2	701.4	731.9	749.5	741.4	684.8
105°	818.6	814.0	806.0	802.6	806.0	814.0	818.6	817.5	794.1	737.6	638.9
107.5°	837.4	850.4	856.1	857.6	856.1	850.4	837.4	809.2	758.4	678.8	573.8
110°	819.2	843.1	853.4	858.5	853.4	843.1	819.2	778.7	715.9	633.2	534.5



TEST NUMBER: P332903

CATALOG NUMBER: SA4XXRDIP-C575D590U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	779.9	808.9	823.3	831.6	823.3	808.9	779.9	733.9	671.2	593.0	505.8
115°	713.6	747.9	766.1	770.7	766.1	747.9	713.6	668.6	613.8	547.1	476.9
117.5°	658.2	686.9	705.4	709.0	705.4	686.9	658.2	619.7	573.3	520.8	462.7
120°	628.1	653.2	668.0	674.3	668.0	653.2	628.1	595.5	555.0	509.4	456.4
122.5°	606.6	628.1	640.6	646.9	640.6	628.1	606.6	579.1	543.6	502.1	450.9
125°	584.1	600.7	611.5	614.9	611.5	600.7	584.1	561.3	529.9	490.6	441.5
127.5°	569.0	583.7	592.8	596.2	592.8	583.7	569.0	546.0	516.3	477.0	430.1
130°	558.5	572.7	581.9	585.3	581.9	572.7	558.5	535.1	504.8	466.1	421.0
132.5°	544.8	560.9	569.5	573.0	569.5	560.9	544.8	521.8	491.6	453.7	411.4
135°	521.4	537.4	546.5	549.9	546.5	537.4	521.4	498.6	470.0	435.3	398.2
137.5°	494.0	509.8	517.3	521.4	517.3	509.8	494.0	472.7	446.9	417.6	386.2
140°	475.8	488.3	496.3	500.9	496.3	488.3	475.8	455.8	431.8	406.2	379.3
142.5°	457.0	468.7	475.8	478.9	475.8	468.7	457.0	439.4	418.6	396.6	373.0
145°	430.7	440.4	446.1	448.9	446.1	440.4	430.7	416.4	400.5	383.3	363.9
147.5°	408.7	417.0	421.3	422.4	421.3	417.0	408.7	398.2	385.6	371.9	356.5
150°	395.9	403.3	406.7	407.3	406.7	403.3	395.9	386.8	376.5	365.1	352.0
152.5°	384.9	391.0	393.0	393.6	393.0	391.0	384.9	377.2	368.7	358.2	346.9
155°	369.7	374.2	375.9	375.9	375.9	374.2	369.7	363.9	357.1	348.5	339.4
157.5°	356.0	359.4	360.4	360.4	360.4	359.4	356.0	351.6	346.1	339.0	331.3
160°	346.8	350.3	350.8	350.8	350.8	350.3	346.8	343.4	338.8	332.6	326.3
162.5°	338.2	341.6	342.2	341.7	342.2	341.6	338.2	335.7	331.5	326.6	321.3
165°	326.9	329.1	328.6	328.0	328.6	329.1	326.9	324.6	321.7	317.7	314.3
167.5°	316.3	317.7	317.6	317.2	317.6	317.7	316.3	315.1	313.4	310.2	307.6
170°	310.3	310.9	310.3	310.3	310.3	310.9	310.3	309.2	307.5	305.2	303.5
172.5°	304.4	305.0	304.4	303.5	304.4	305.0	304.4	303.7	302.5	301.1	299.8
175°	296.6	297.8	296.6	295.5	296.6	297.8	296.6	296.6	296.6	295.5	294.9
177.5°	292.2	292.6	291.7	290.8	291.7	292.6	292.2	292.6	292.2	292.2	291.7
180°	290.4	290.4	290.4	290.4	290.4	290.4	290.4	290.4	290.4	290.4	290.4



TEST NUMBER: P332903

CATALOG NUMBER: SA4XXRDIP-C575D590U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7
2.5°	923.7	925.9	930.8	936.4	941.1	945.2	948.3	952.6	956.7	962.3	967.6
5°	867.6	873.1	880.9	890.2	901.9	909.7	919.4	928.0	940.4	952.9	964.9
7.5°	818.5	824.5	835.9	848.8	862.7	875.4	886.9	902.0	918.5	936.7	956.9
10°	786.7	793.3	807.0	821.7	838.1	850.5	866.1	884.0	902.7	924.8	949.7
12.5°	758.1	764.4	780.8	795.9	812.9	826.6	844.6	862.8	887.7	911.8	940.1
15°	702.3	719.0	737.7	755.6	775.8	792.6	814.3	833.0	856.8	890.6	922.9
17.5°	640.3	658.2	681.4	709.0	736.1	756.8	778.9	802.1	830.4	864.9	902.2
20°	604.2	618.6	644.3	675.1	706.6	735.4	755.6	781.3	810.5	847.8	886.3
22.5°	577.2	589.4	609.5	640.2	674.2	707.7	733.5	758.9	791.2	828.5	870.5
25°	536.5	549.8	567.3	588.3	627.2	662.6	696.5	725.6	759.9	797.2	843.9
27.5°	502.8	514.3	530.3	552.2	578.3	617.4	658.4	691.7	726.8	766.9	813.6
30°	482.8	492.2	505.4	527.6	552.5	587.5	629.1	668.1	703.5	745.1	793.7
32.5°	462.0	472.0	484.9	502.4	529.1	558.6	600.2	642.8	680.4	723.0	770.7
35°	434.2	442.0	453.7	471.6	495.7	521.4	558.3	602.3	642.0	687.5	733.0
37.5°	406.1	415.3	424.5	440.4	460.2	487.8	518.1	563.0	607.0	648.5	693.0
40°	390.2	395.7	405.8	418.7	439.7	464.2	492.6	536.5	580.5	621.8	666.5
42.5°	372.5	378.6	387.1	400.0	418.8	442.7	470.5	508.5	554.4	594.4	635.1
45°	347.8	351.3	359.9	370.8	386.4	410.5	436.2	470.0	513.2	551.3	587.1
47.5°	322.9	326.0	331.3	341.3	358.7	378.1	402.2	432.5	470.4	508.5	538.8
50°	305.8	308.5	313.6	322.9	338.5	357.6	381.3	408.5	442.4	479.0	504.2
52.5°	288.7	290.2	294.9	305.5	318.6	337.3	358.6	383.6	415.3	445.7	471.3
55°	261.5	265.0	268.1	275.9	288.3	306.2	325.3	349.0	373.5	399.2	421.0
57.5°	233.1	236.9	241.4	248.2	258.1	274.8	291.9	311.1	332.0	353.4	371.6
60°	214.4	217.9	221.8	229.6	238.5	251.7	270.4	287.1	303.1	322.5	340.8
62.5°	196.0	199.5	204.0	210.3	218.9	231.5	247.1	261.6	278.2	295.2	308.8
65°	168.9	171.6	175.1	180.9	189.1	200.4	213.2	224.5	239.3	251.7	264.2
67.5°	139.1	144.3	148.9	153.6	160.5	171.0	180.3	191.1	201.2	210.4	221.8
70°	119.4	125.3	129.6	134.6	141.2	150.2	159.1	166.5	174.7	183.6	193.8
72.5°	103.0	107.5	110.9	116.3	122.2	130.6	138.9	145.0	151.7	157.8	167.6
75°	81.3	83.3	85.6	89.9	95.3	101.6	108.2	113.6	117.5	122.9	130.0
77.5°	58.4	62.2	63.7	66.8	70.7	74.5	78.9	83.5	87.2	89.2	94.5
80°	44.7	46.3	47.9	52.1	54.5	58.4	61.5	65.8	67.3	69.3	74.3
82.5°	34.8	35.7	36.7	37.8	39.2	43.1	46.2	48.9	50.5	51.2	55.0
85°	20.2	20.6	21.0	21.4	21.8	21.8	23.3	25.3	28.0	28.0	29.2
87.5°	8.8	9.2	9.0	8.4	9.1	8.4	8.7	8.6	9.4	10.0	10.7
90°	9.7	10.3	9.1	8.0	8.0	4.6	4.6	4.0	3.4	1.7	0.6
92.5°	150.7	180.9	158.4	115.2	71.0	42.0	30.1	21.8	14.8	9.5	6.5
95°	478.0	464.9	350.8	214.5	120.9	71.3	47.3	33.7	26.2	20.5	18.8
97.5°	600.6	489.7	328.4	192.8	115.6	77.4	57.3	45.5	38.7	33.8	33.8
100°	604.7	458.6	297.8	181.4	116.9	83.3	65.0	54.2	47.3	43.4	43.4
102.5°	570.4	419.9	277.2	178.2	121.5	91.0	73.7	63.3	56.9	53.4	52.5
105°	508.3	374.2	259.6	179.7	132.3	105.0	88.4	78.2	71.3	68.5	66.7
107.5°	458.1	348.7	256.4	188.1	145.0	119.9	103.6	93.8	86.5	83.6	82.5
110°	433.0	340.0	257.3	194.5	154.6	129.5	114.1	103.8	97.0	94.1	93.0



TEST NUMBER: P332903

CATALOG NUMBER: SA4XXRDIP-C575D590U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	418.8	335.9	260.0	201.4	163.7	139.5	124.1	113.9	107.5	104.2	103.0
115°	405.6	333.7	265.3	212.2	178.0	155.2	139.8	128.9	123.2	119.2	117.5
117.5°	399.7	333.1	270.8	223.3	191.8	170.1	154.1	144.0	137.7	134.2	132.6
120°	396.5	333.1	275.0	231.0	201.4	179.7	163.7	154.0	147.7	143.8	142.6
122.5°	392.8	332.7	279.1	238.3	210.5	188.8	173.3	162.7	156.9	152.9	151.7
125°	386.8	332.0	285.2	249.3	223.0	202.5	186.5	175.7	169.4	166.0	163.7
127.5°	378.7	330.7	290.1	258.8	234.7	214.8	198.7	187.4	180.3	176.2	174.3
130°	373.6	330.3	293.8	264.7	242.4	223.0	206.5	195.7	187.1	182.5	180.3
132.5°	369.1	329.8	297.0	270.6	248.8	229.4	213.8	202.1	194.0	188.0	186.2
135°	362.2	329.1	301.8	278.4	257.8	239.0	224.2	212.2	202.5	196.8	194.5
137.5°	356.3	329.0	304.6	283.9	264.7	247.1	233.0	220.5	211.3	205.0	202.9
140°	353.1	328.6	306.9	287.5	269.3	252.1	238.4	226.5	216.8	210.5	208.8
142.5°	350.4	328.6	308.7	290.2	273.4	256.7	243.5	231.9	222.7	216.9	215.2
145°	345.7	327.4	309.8	293.2	277.8	263.0	250.4	239.6	231.6	225.9	224.2
147.5°	341.5	325.4	310.3	295.8	282.4	268.5	257.2	248.1	239.9	234.9	234.3
150°	338.3	324.0	310.3	297.2	284.7	272.1	261.3	252.7	245.9	241.3	240.7
152.5°	334.6	321.7	309.4	298.1	286.5	275.3	265.4	257.7	251.3	246.8	246.7
155°	329.1	318.3	308.0	298.9	289.2	279.5	271.0	264.7	259.0	255.6	255.0
157.5°	323.6	314.8	306.6	298.9	291.2	282.9	276.2	270.7	266.3	263.1	263.1
160°	319.5	312.0	305.2	298.9	292.1	285.2	278.9	274.4	270.4	268.1	268.1
162.5°	315.8	309.3	303.8	298.9	293.0	286.6	281.7	277.6	274.0	272.2	272.7
165°	309.8	305.2	301.2	297.8	293.2	288.1	284.7	281.8	278.9	277.8	277.8
167.5°	304.3	301.1	298.5	296.4	293.1	289.3	286.7	285.1	282.9	282.4	282.9
170°	300.6	298.3	296.6	295.5	292.6	289.8	288.1	286.9	285.2	284.7	285.2
172.5°	297.4	295.6	294.8	294.6	292.2	290.2	289.0	288.3	287.0	286.9	287.5
175°	293.8	292.6	292.6	293.2	291.5	290.4	290.4	289.8	289.2	289.2	289.8
177.5°	291.3	290.8	290.8	291.7	290.8	290.4	290.4	290.4	289.9	290.4	290.8
180°	290.4	290.4	290.4	290.4	290.4	290.4	290.4	290.4	290.4	290.4	290.4



TEST NUMBER: P332903

CATALOG NUMBER: SA4XXRDIP-C575D590U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7
2.5°	971.6	974.4	977.5	983.4	988.4	990.6	995.0	998.1	997.1	1001.5	1009.0
5°	975.4	985.9	998.0	1010.4	1024.4	1036.1	1045.5	1054.8	1062.2	1071.1	1084.4
7.5°	974.8	993.5	1013.8	1036.1	1059.1	1078.9	1097.3	1116.0	1132.5	1150.7	1174.4
10°	972.3	997.2	1022.5	1051.7	1080.9	1108.5	1133.4	1156.7	1178.9	1202.6	1232.6
12.5°	969.5	998.1	1028.7	1063.8	1100.2	1133.4	1162.7	1196.3	1224.0	1254.6	1289.3
15°	957.1	995.7	1037.3	1082.8	1126.4	1171.1	1211.2	1252.5	1291.0	1327.5	1371.1
17.5°	943.0	987.4	1036.5	1090.3	1142.7	1197.0	1244.6	1296.6	1335.9	1385.0	1425.5
20°	931.5	979.3	1031.8	1092.1	1151.7	1212.0	1264.5	1317.4	1361.8	1411.2	1462.6
22.5°	917.5	970.0	1026.9	1089.3	1151.7	1217.6	1275.7	1328.3	1383.3	1438.9	1491.8
25°	894.9	949.4	1009.7	1078.1	1149.7	1217.0	1279.3	1344.7	1403.8	1464.1	1511.6
27.5°	867.2	924.4	988.0	1058.6	1132.1	1201.0	1274.3	1344.0	1403.5	1461.5	1502.9
30°	845.1	905.4	966.5	1038.1	1114.3	1188.3	1266.8	1336.5	1399.1	1451.3	1474.6
32.5°	822.4	879.6	942.5	1015.0	1093.2	1172.7	1250.7	1321.9	1379.8	1411.1	1411.7
35°	782.8	836.5	901.9	973.1	1053.2	1139.6	1218.6	1288.6	1324.0	1326.8	1288.6
37.5°	739.7	789.0	850.7	922.0	1009.7	1095.7	1176.3	1223.0	1234.9	1195.3	1124.8
40°	708.9	754.4	814.0	887.1	974.3	1063.0	1136.5	1170.7	1158.3	1094.1	1015.5
42.5°	676.5	718.9	776.3	848.5	936.0	1025.6	1088.3	1106.6	1073.6	999.5	907.5
45°	623.7	662.6	719.4	792.2	876.2	960.3	1007.7	998.4	943.5	855.6	752.5
47.5°	568.7	606.3	657.4	724.7	810.8	883.3	915.4	887.3	809.2	712.5	628.6
50°	532.3	570.8	617.9	682.1	760.7	830.7	851.3	808.5	721.7	628.8	551.7
52.5°	496.5	529.4	575.5	637.5	712.7	771.9	782.8	733.5	643.9	560.6	492.3
55°	442.0	472.0	510.9	569.2	634.2	684.4	678.6	615.1	533.8	462.6	408.9
57.5°	389.3	411.9	447.8	502.5	559.6	593.3	571.9	517.9	442.1	383.8	338.5
60°	354.5	375.5	408.9	456.8	507.0	526.0	508.1	449.4	389.5	336.2	298.0
62.5°	321.5	340.0	368.8	413.2	453.7	465.0	445.9	394.6	340.6	295.1	263.5
65°	273.5	290.6	315.2	346.7	374.7	380.1	367.7	315.2	274.3	236.2	214.4
67.5°	230.0	241.2	260.4	287.6	302.5	305.7	281.6	248.6	212.6	189.2	172.8
70°	200.8	208.5	226.4	241.2	253.3	253.7	231.5	205.0	177.4	158.4	146.3
72.5°	172.4	179.9	193.5	203.6	212.8	209.8	189.5	168.6	146.3	131.9	122.9
75°	133.1	139.7	146.7	151.4	151.4	147.5	132.7	117.1	104.3	95.7	93.0
77.5°	96.7	102.2	104.5	103.8	102.4	96.3	87.0	76.8	72.2	68.2	66.1
80°	75.9	78.2	79.0	77.0	74.7	67.7	61.5	57.2	52.9	51.4	50.6
82.5°	56.3	58.3	56.3	56.8	51.7	45.9	42.5	41.0	39.2	38.6	37.8
85°	30.0	29.6	28.8	26.8	23.3	22.6	22.2	21.8	21.0	21.4	20.6
87.5°	10.6	10.0	8.9	8.7	8.7	8.8	9.1	9.3	9.5	9.1	9.8
90°	1.7	3.4	4.0	4.6	4.6	8.0	8.0	9.1	10.3	9.7	10.3
92.5°	9.5	14.8	21.8	30.1	42.0	71.0	115.2	158.4	180.9	150.7	112.0
95°	20.5	26.2	33.7	47.3	71.3	120.9	214.5	350.8	464.9	478.0	422.7
97.5°	33.8	38.7	45.5	57.3	77.4	115.6	192.8	328.4	489.7	600.6	624.5
100°	43.4	47.3	54.2	65.0	83.3	116.9	181.4	297.8	458.6	604.7	688.0
102.5°	53.4	56.9	63.3	73.7	91.0	121.5	178.2	277.2	419.9	570.4	684.8
105°	68.5	71.3	78.2	88.4	105.0	132.3	179.7	259.6	374.2	508.3	638.9
107.5°	83.6	86.5	93.8	103.6	119.9	145.0	188.1	256.4	348.7	458.1	573.8
110°	94.1	97.0	103.8	114.1	129.5	154.6	194.5	257.3	340.0	433.0	534.5





TEST NUMBER: P332903

CATALOG NUMBER: SA4XXRDIP-C575D590U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	104.2	107.5	113.9	124.1	139.5	163.7	201.4	260.0	335.9	418.8	505.8
115°	119.2	123.2	128.9	139.8	155.2	178.0	212.2	265.3	333.7	405.6	476.9
117.5°	134.2	137.7	144.0	154.1	170.1	191.8	223.3	270.8	333.1	399.7	462.7
120°	143.8	147.7	154.0	163.7	179.7	201.4	231.0	275.0	333.1	396.5	456.4
122.5°	152.9	156.9	162.7	173.3	188.8	210.5	238.3	279.1	332.7	392.8	450.9
125°	166.0	169.4	175.7	186.5	202.5	223.0	249.3	285.2	332.0	386.8	441.5
127.5°	176.2	180.3	187.4	198.7	214.8	234.7	258.8	290.1	330.7	378.7	430.1
130°	182.5	187.1	195.7	206.5	223.0	242.4	264.7	293.8	330.3	373.6	421.0
132.5°	188.0	194.0	202.1	213.8	229.4	248.8	270.6	297.0	329.8	369.1	411.4
135°	196.8	202.5	212.2	224.2	239.0	257.8	278.4	301.8	329.1	362.2	398.2
137.5°	205.0	211.3	220.5	233.0	247.1	264.7	283.9	304.6	329.0	356.3	386.2
140°	210.5	216.8	226.5	238.4	252.1	269.3	287.5	306.9	328.6	353.1	379.3
142.5°	216.9	222.7	231.9	243.5	256.7	273.4	290.2	308.7	328.6	350.4	373.0
145°	225.9	231.6	239.6	250.4	263.0	277.8	293.2	309.8	327.4	345.7	363.9
147.5°	234.9	239.9	248.1	257.2	268.5	282.4	295.8	310.3	325.4	341.5	356.5
150°	241.3	245.9	252.7	261.3	272.1	284.7	297.2	310.3	324.0	338.3	352.0
152.5°	246.8	251.3	257.7	265.4	275.3	286.5	298.1	309.4	321.7	334.6	346.9
155°	255.6	259.0	264.7	271.0	279.5	289.2	298.9	308.0	318.3	329.1	339.4
157.5°	263.1	266.3	270.7	276.2	282.9	291.2	298.9	306.6	314.8	323.6	331.3
160°	268.1	270.4	274.4	278.9	285.2	292.1	298.9	305.2	312.0	319.5	326.3
162.5°	272.2	274.0	277.6	281.7	286.6	293.0	298.9	303.8	309.3	315.8	321.3
165°	277.8	278.9	281.8	284.7	288.1	293.2	297.8	301.2	305.2	309.8	314.3
167.5°	282.4	282.9	285.1	286.7	289.3	293.1	296.4	298.5	301.1	304.3	307.6
170°	284.7	285.2	286.9	288.1	289.8	292.6	295.5	296.6	298.3	300.6	303.5
172.5°	286.9	287.0	288.3	289.0	290.2	292.2	294.6	294.8	295.6	297.4	299.8
175°	289.2	289.2	289.8	290.4	290.4	291.5	293.2	292.6	292.6	293.8	294.9
177.5°	290.4	289.9	290.4	290.4	290.4	290.8	291.7	290.8	290.8	291.3	291.7
180°	290.4	290.4	290.4	290.4	290.4	290.4	290.4	290.4	290.4	290.4	290.4



TEST NUMBER: P332903

CATALOG NUMBER: SA4XXRDIP-C575D590U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	965.7	965.7	965.7	965.7	965.7	965.7	965.7
2.5°	1013.0	1014.3	1015.2	1018.3	1018.6	1021.4	1018.6
5°	1096.8	1102.3	1110.8	1119.4	1120.2	1125.6	1115.9
7.5°	1190.8	1203.4	1211.3	1225.1	1230.6	1234.0	1228.4
10°	1255.6	1267.2	1287.9	1298.0	1308.1	1309.6	1305.0
12.5°	1318.1	1336.6	1352.9	1372.1	1371.6	1385.3	1380.3
15°	1401.5	1420.5	1443.1	1464.5	1472.3	1472.3	1478.5
17.5°	1460.9	1495.9	1519.2	1536.0	1554.4	1557.6	1555.4
20°	1501.1	1538.8	1563.7	1585.5	1598.0	1601.5	1601.5
22.5°	1531.0	1563.1	1587.4	1607.0	1617.3	1621.4	1620.1
25°	1551.7	1579.3	1594.1	1599.9	1602.6	1601.8	1594.5
27.5°	1523.3	1522.1	1512.7	1494.8	1481.4	1473.2	1463.9
30°	1469.2	1448.9	1425.6	1399.9	1366.8	1341.5	1333.8
32.5°	1388.6	1343.1	1303.6	1260.8	1225.2	1199.9	1189.3
35°	1232.6	1160.6	1101.9	1050.5	1013.2	989.8	982.0
37.5°	1047.6	977.9	905.2	855.4	824.4	800.8	792.0
40°	929.9	854.0	790.6	743.9	712.0	689.1	688.7
42.5°	822.5	750.1	690.4	656.8	622.4	607.2	607.1
45°	673.5	615.5	564.9	538.5	517.9	505.4	501.9
47.5°	557.6	509.7	476.0	454.9	438.1	430.2	425.0
50°	492.6	450.6	423.7	405.4	396.1	386.0	385.2
52.5°	438.4	404.5	383.6	368.7	356.9	350.8	351.0
55°	368.5	341.6	326.8	315.5	306.2	301.5	299.6
57.5°	310.4	290.3	279.5	269.2	265.2	261.5	260.5
60°	274.3	260.7	250.6	242.4	236.6	235.4	235.0
62.5°	244.4	230.2	223.2	216.9	212.6	210.8	210.1
65°	201.5	191.0	184.8	179.8	178.2	175.5	175.1
67.5°	162.5	156.2	152.1	148.6	146.4	146.3	146.3
70°	138.5	135.0	131.5	129.6	128.4	127.6	127.6
72.5°	118.0	115.4	112.5	111.5	111.3	110.5	110.2
75°	89.9	87.2	87.5	85.6	84.0	82.1	80.9
77.5°	63.7	61.8	61.4	61.2	59.8	59.6	60.2
80°	49.4	47.5	47.1	47.5	47.1	45.9	45.9
82.5°	37.6	36.0	35.6	35.3	34.9	35.3	34.7
85°	20.2	19.5	19.5	19.5	20.2	19.8	19.5
87.5°	9.3	9.1	9.4	9.2	9.4	8.9	9.2
90°	10.8	11.4	11.4	12.0	12.5	12.0	12.0
92.5°	84.3	67.1	55.7	48.9	45.9	43.9	43.9
95°	334.3	257.8	202.5	174.6	156.9	146.6	139.2
97.5°	591.7	535.9	476.3	435.4	401.0	383.9	372.0
100°	699.4	671.4	629.2	579.6	544.8	527.7	523.1
102.5°	741.4	749.5	731.9	701.4	676.2	658.2	654.5
105°	737.6	794.1	817.5	818.6	814.0	806.0	802.6
107.5°	678.8	758.4	809.2	837.4	850.4	856.1	857.6
110°	633.2	715.9	778.7	819.2	843.1	853.4	858.5



TEST NUMBER: P332903

CATALOG NUMBER: SA4XXRDIP-C575D590U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	593.0	671.2	733.9	779.9	808.9	823.3	831.6
115°	547.1	613.8	668.6	713.6	747.9	766.1	770.7
117.5°	520.8	573.3	619.7	658.2	686.9	705.4	709.0
120°	509.4	555.0	595.5	628.1	653.2	668.0	674.3
122.5°	502.1	543.6	579.1	606.6	628.1	640.6	646.9
125°	490.6	529.9	561.3	584.1	600.7	611.5	614.9
127.5°	477.0	516.3	546.0	569.0	583.7	592.8	596.2
130°	466.1	504.8	535.1	558.5	572.7	581.9	585.3
132.5°	453.7	491.6	521.8	544.8	560.9	569.5	573.0
135°	435.3	470.0	498.6	521.4	537.4	546.5	549.9
137.5°	417.6	446.9	472.7	494.0	509.8	517.3	521.4
140°	406.2	431.8	455.8	475.8	488.3	496.3	500.9
142.5°	396.6	418.6	439.4	457.0	468.7	475.8	478.9
145°	383.3	400.5	416.4	430.7	440.4	446.1	448.9
147.5°	371.9	385.6	398.2	408.7	417.0	421.3	422.4
150°	365.1	376.5	386.8	395.9	403.3	406.7	407.3
152.5°	358.2	368.7	377.2	384.9	391.0	393.0	393.6
155°	348.5	357.1	363.9	369.7	374.2	375.9	375.9
157.5°	339.0	346.1	351.6	356.0	359.4	360.4	360.4
160°	332.6	338.8	343.4	346.8	350.3	350.8	350.8
162.5°	326.6	331.5	335.7	338.2	341.6	342.2	341.7
165°	317.7	321.7	324.6	326.9	329.1	328.6	328.0
167.5°	310.2	313.4	315.1	316.3	317.7	317.6	317.2
170°	305.2	307.5	309.2	310.3	310.9	310.3	310.3
172.5°	301.1	302.5	303.7	304.4	305.0	304.4	303.5
175°	295.5	296.6	296.6	296.6	297.8	296.6	295.5
177.5°	292.2	292.2	292.6	292.2	292.6	291.7	290.8
180°	290.4	290.4	290.4	290.4	290.4	290.4	290.4

(END OF REPORT)