

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332528-935

Luminaire Tested: **SA4XXDIP-C350D1205U935-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332528-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C350D1205U935-4F0-1E-UDD-A4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5063.7 lumens
Efficiency: N/A
Efficacy: 120.0 lumens/watt
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 42.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332528-935
CATALOG NUMBER: SA4XXDIP-C350D1205U935-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332528-935

CATALOG NUMBER: SA4XXDIP-C350D1205U935-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	70	70	70	52	52	52	35	35	35	27
1	93	89	85	82	83	79	76	73	62	60	58	46	44	43	31	30	30	23
2	84	77	72	67	75	69	64	60	54	51	48	40	38	36	27	26	25	19
3	77	68	61	56	69	61	55	50	48	44	40	36	33	31	24	23	21	16
4	70	60	53	47	63	54	48	43	43	38	34	32	29	26	22	20	19	14
5	65	54	46	40	57	48	42	37	38	33	30	28	25	23	20	18	16	12
6	59	48	40	35	53	43	36	32	34	29	26	26	22	20	18	16	14	11
7	55	43	36	30	49	39	32	28	31	26	23	23	20	18	16	14	13	10
8	51	39	32	27	45	35	29	24	28	23	20	21	18	16	15	13	11	9
9	47	35	28	23	42	32	26	22	26	21	18	20	16	14	14	12	10	8
10	44	32	26	21	39	29	23	19	24	19	16	18	15	13	13	11	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	3971	3971	3971	3971
5°	4676	3981	3514	3981
10°	5599	3963	3163	3963
15°	6624	3924	2906	3924
20°	7377	3882	2674	3882
25°	7496	3822	2515	3822
30°	6378	3765	2466	3765
35°	4904	3671	2466	3671
40°	3822	3561	2512	3561
45°	3186	3394	2555	3394
50°	2804	3191	2641	3191
55°	2570	2949	2747	2949
60°	2407	2730	2876	2730
65°	2243	2487	2982	2487
70°	2049	2245	3050	2245
75°	1831	1978	3013	1978
80°	1534	1623	2920	1623
85°	1130	1176	2788	1176



TEST NUMBER: P332528-935

CATALOG NUMBER: SA4XXDIP-C350D1205U935-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.9	0.9
10°-20°	147.7	2.9
20°-30°	234.2	4.6
30°-40°	260.7	5.1
40°-50°	237.3	4.7
50°-60°	193.9	3.8
60°-70°	138.4	2.7
70°-80°	76.2	1.5
80°-90°	23.6	0.5
90°-100°	367.8	7.3
100°-110°	765.5	15.1
110°-120°	685.7	13.5
120°-130°	576.8	11.4
130°-140°	480.9	9.5
140°-150°	367.4	7.3
150°-160°	258.2	5.1
160°-170°	151.9	3.0
170°-180°	49.4	1.0
0°-30°	429.9	8.5
0°-40°	690.5	13.6
0°-60°	1121.7	22.2
0°-90°	1360.0	26.9
90°-120°	1819.0	35.9
90°-150°	3244.1	64.1
90°-180°	3704.0	73.1
0°-180°	5063.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	492	492	492	492	492	
5°	577	491	434	491	577	59
15°	793	470	348	470	793	224
25°	842	429	282	429	842	371
35°	498	372	250	372	498	316
45°	279	297	224	297	279	220
55°	183	210	195	210	183	165
65°	117	130	156	130	117	116
75°	59	63	97	63	59	62
85°	12	13	30	13	12	15
90°	21	1	21	1	21	17
95°	244	33	244	33	244	379
105°	1408	117	1408	117	1408	1392
115°	1352	206	1352	206	1352	1342
125°	1078	287	1078	287	1078	980
135°	964	341	964	341	964	744
145°	787	393	787	393	787	499
155°	659	447	659	447	659	308
165°	575	487	575	487	575	165
175°	518	508	518	508	518	50
180°	509	509	509	509	509	



TEST NUMBER: P332528-935

CATALOG NUMBER: SA4XXDIP-C350D1205U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9
2.5°	523.5	523.4	521.8	521.4	520.3	518.8	518.5	515.8	510.7	508.2	507.6
5°	577.0	581.2	575.8	574.8	574.2	567.5	564.0	560.0	550.6	545.1	540.8
7.5°	641.0	641.4	639.1	637.3	632.1	626.2	617.4	608.0	596.8	585.3	576.5
10°	683.0	684.7	682.0	681.7	671.2	664.7	651.7	640.7	628.0	614.0	601.2
12.5°	727.4	725.1	723.8	715.1	713.1	701.2	686.0	674.8	655.2	639.0	622.0
15°	792.6	788.2	785.3	773.4	767.4	750.9	734.8	722.4	696.9	672.6	654.3
17.5°	831.0	835.4	828.9	823.9	808.7	797.0	780.6	754.5	734.6	704.5	681.3
20°	858.7	859.1	855.4	850.3	838.4	823.6	805.7	777.2	753.4	723.4	691.6
22.5°	866.2	866.3	864.7	860.0	850.8	839.0	820.9	797.0	768.2	735.6	703.8
25°	841.5	840.8	842.6	847.9	844.5	840.8	830.3	812.6	785.7	751.3	717.0
27.5°	750.1	755.8	766.1	779.1	791.7	801.2	803.9	800.3	783.7	755.4	719.5
30°	684.2	691.2	699.0	712.0	737.3	751.7	767.6	779.6	772.9	750.3	716.9
32.5°	611.9	613.6	625.1	639.9	663.1	690.9	716.1	740.5	748.6	736.8	708.9
35°	497.6	500.5	512.9	527.5	555.9	590.0	627.8	661.7	689.6	700.8	686.5
37.5°	406.0	414.2	423.0	438.8	463.7	494.4	533.7	577.6	619.1	647.0	651.8
40°	362.7	367.8	374.1	386.2	407.3	437.5	471.3	521.4	565.7	605.6	618.6
42.5°	328.5	331.5	335.4	346.2	362.3	392.4	423.3	467.4	511.7	559.5	581.3
45°	279.1	282.2	288.8	295.1	307.3	328.0	356.8	393.0	437.7	483.7	524.1
47.5°	243.6	245.5	249.3	256.1	266.6	280.3	303.6	333.9	375.2	420.0	463.0
50°	223.3	225.0	228.0	234.1	242.1	254.3	273.5	301.8	334.2	379.2	421.4
52.5°	207.3	208.0	210.3	214.4	220.8	231.0	246.8	270.2	300.3	340.4	382.5
55°	182.6	183.4	185.5	188.5	194.0	200.5	212.5	230.1	256.3	291.2	327.7
57.5°	162.2	162.8	164.5	165.7	170.2	175.5	184.8	197.3	217.1	246.8	279.3
60°	149.1	148.8	150.8	151.8	154.9	159.4	166.5	178.5	195.8	219.6	249.6
62.5°	136.5	135.9	137.6	139.0	140.7	144.5	150.3	159.7	173.8	195.4	221.3
65°	117.4	116.6	117.6	119.2	120.8	122.9	127.2	135.5	146.7	162.2	181.9
67.5°	98.2	99.1	99.3	100.0	101.0	103.8	106.7	112.6	120.5	132.9	149.6
70°	86.8	87.0	87.8	87.8	88.4	90.9	93.3	96.8	104.5	116.0	129.6
72.5°	75.4	76.3	75.9	76.5	77.1	78.7	80.4	83.8	90.3	98.8	110.4
75°	58.7	59.3	59.3	59.5	60.1	60.7	62.2	64.6	69.3	75.6	83.5
77.5°	42.8	42.9	43.1	43.9	43.9	44.9	45.9	47.9	50.2	54.5	59.4
80°	33.0	33.4	33.2	33.7	33.7	34.4	34.9	37.3	38.3	41.2	45.0
82.5°	24.2	24.6	24.5	25.1	25.5	25.7	26.2	27.2	28.2	30.7	32.3
85°	12.2	12.7	12.2	12.7	13.3	13.4	14.0	14.3	15.1	15.7	17.1
87.5°	7.7	8.3	8.4	8.4	8.5	8.7	8.7	8.4	8.8	9.1	9.4
90°	21.0	21.0	22.0	21.0	20.0	20.0	19.0	18.0	17.0	18.0	16.0
92.5°	77.1	77.1	80.4	85.8	97.6	117.7	147.8	196.5	264.3	317.4	277.8
95°	244.1	257.1	275.2	306.2	355.2	452.2	586.3	741.3	838.4	815.4	615.3
97.5°	652.6	673.3	703.4	763.5	835.4	939.9	1037.7	1095.4	1053.3	858.8	575.8
100°	917.5	925.5	955.5	1016.5	1103.5	1177.6	1226.6	1206.6	1060.5	804.3	522.3
102.5°	1148.0	1154.3	1185.9	1230.2	1283.6	1314.4	1300.2	1201.0	1000.5	736.3	486.2
105°	1407.6	1413.7	1427.7	1435.7	1433.7	1392.7	1293.7	1120.5	891.4	656.3	455.2
107.5°	1504.2	1501.5	1491.5	1468.7	1419.3	1330.1	1190.6	1006.3	803.4	611.5	449.6
110°	1505.7	1496.8	1478.7	1436.7	1365.6	1255.6	1110.5	937.5	759.4	596.3	451.3



TEST NUMBER: P332528-935

CATALOG NUMBER: SA4XXDIP-C350D1205U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1458.5	1443.9	1418.7	1367.9	1287.2	1177.2	1040.1	887.0	734.5	589.1	456.0
115°	1351.7	1343.7	1311.6	1251.6	1172.6	1076.5	959.5	836.4	711.4	585.3	465.2
117.5°	1243.4	1237.2	1204.8	1154.3	1086.9	1005.5	913.4	811.6	700.9	584.3	475.0
120°	1182.6	1171.6	1145.6	1101.6	1044.5	973.4	893.5	800.4	695.3	584.3	482.2
122.5°	1134.5	1123.5	1101.6	1063.9	1015.7	953.5	880.6	790.7	689.0	583.5	489.5
125°	1078.5	1072.5	1053.5	1024.5	984.5	929.4	860.4	774.4	678.3	582.3	500.2
127.5°	1045.7	1039.7	1023.7	997.9	957.7	905.4	836.6	754.3	664.1	580.1	508.9
130°	1026.5	1020.5	1004.4	979.5	938.5	885.5	817.4	738.4	655.3	579.3	515.2
132.5°	1004.9	998.8	983.7	955.5	915.2	862.2	795.8	721.5	647.3	578.5	520.8
135°	964.5	958.5	942.5	914.5	874.4	824.4	763.4	698.4	635.3	577.3	529.3
137.5°	914.5	907.2	894.1	866.4	829.0	783.8	732.4	677.3	624.9	577.0	534.3
140°	878.4	870.4	856.4	834.4	799.4	757.3	712.3	665.3	619.3	576.3	538.3
142.5°	840.0	834.4	822.0	801.6	770.6	734.2	695.5	654.1	614.5	576.3	541.5
145°	787.4	782.4	772.4	755.4	730.4	702.3	672.4	638.3	606.3	574.3	543.3
147.5°	740.7	739.0	731.3	716.8	698.4	676.3	652.3	625.3	598.9	570.7	544.2
150°	714.4	713.3	707.3	694.3	678.3	660.3	640.3	617.3	593.3	568.3	544.2
152.5°	690.3	689.3	685.7	675.1	661.5	646.7	628.3	608.5	586.9	564.3	542.7
155°	659.4	659.4	656.3	648.3	638.3	626.3	611.3	595.3	577.3	558.3	540.3
157.5°	632.1	632.1	630.3	624.3	616.7	607.1	594.5	581.1	567.5	552.1	537.7
160°	615.3	615.3	614.3	608.3	602.3	594.3	583.2	572.3	560.3	547.3	535.3
162.5°	599.3	600.1	599.1	593.1	588.7	581.5	572.9	563.4	553.9	542.4	532.9
165°	575.3	576.3	577.3	573.3	569.3	564.3	557.2	551.3	543.3	535.3	528.2
167.5°	556.3	557.1	557.2	554.7	552.7	549.7	544.1	539.5	533.6	528.1	523.5
170°	544.2	544.2	545.3	544.2	542.3	539.2	535.3	532.3	527.3	523.2	520.2
172.5°	532.3	533.8	534.9	533.8	532.6	530.5	528.1	525.8	521.7	518.4	517.0
175°	518.2	520.2	522.3	520.2	520.2	520.2	518.2	517.3	515.2	513.2	513.2
177.5°	510.1	511.6	513.2	512.5	513.2	512.5	512.5	511.6	510.8	510.1	510.1
180°	509.3	509.3	509.3	509.3	509.3	509.3	509.3	509.3	509.3	509.3	509.3



TEST NUMBER: P332528-935

CATALOG NUMBER: SA4XXDIP-C350D1205U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9
2.5°	507.7	505.4	503.8	502.5	498.9	496.8	495.2	492.9	490.3	487.5	484.1
5°	536.5	529.6	524.5	516.8	509.5	503.3	497.0	491.3	484.4	476.8	471.3
7.5°	566.8	556.5	543.3	531.8	518.9	507.7	497.7	487.5	476.8	466.4	456.9
10°	586.1	572.8	558.1	540.8	524.5	510.1	496.6	483.5	470.9	458.3	447.5
12.5°	606.7	590.2	568.5	548.3	530.0	510.7	494.5	478.5	463.2	450.0	437.4
15°	634.6	610.7	585.7	558.5	534.5	511.9	489.7	469.5	452.4	434.8	422.6
17.5°	651.6	622.1	593.5	565.2	536.1	507.5	483.5	460.3	438.9	421.5	406.0
20°	662.9	633.5	597.9	569.6	534.9	505.6	477.9	451.9	429.6	411.0	395.1
22.5°	672.6	638.8	603.0	565.8	531.3	500.2	469.8	443.8	420.9	401.4	386.2
25°	678.0	639.0	600.3	563.2	524.1	487.2	459.7	429.1	404.7	384.1	367.8
27.5°	678.6	636.9	593.1	551.9	511.5	477.2	442.5	415.1	389.8	368.0	352.3
30°	676.7	633.4	586.3	541.7	501.1	463.8	433.6	403.9	378.0	356.4	340.1
32.5°	671.0	625.9	577.5	530.2	488.2	451.7	420.6	392.3	367.0	345.8	328.6
35°	654.5	609.8	558.4	509.2	466.2	429.4	401.2	372.5	347.2	327.1	310.6
37.5°	628.7	588.4	536.0	485.2	442.9	405.9	378.0	352.1	329.2	308.8	291.9
40°	606.2	570.8	518.1	468.6	423.0	387.8	361.7	337.9	315.2	295.8	279.7
42.5°	580.3	549.4	500.9	448.5	404.4	369.0	343.6	322.2	300.9	283.0	266.9
45°	534.1	513.7	468.0	419.6	373.7	340.3	316.1	297.3	279.4	261.8	248.4
47.5°	481.0	470.8	432.4	386.3	342.9	309.9	288.9	271.6	255.8	241.0	229.1
50°	445.2	440.3	407.2	362.7	321.2	290.2	269.0	254.1	240.6	227.6	216.4
52.5°	410.0	409.8	379.9	339.2	300.7	271.0	249.9	236.0	224.4	213.8	203.7
55°	356.2	361.9	338.5	302.2	267.8	240.8	221.9	209.5	201.3	192.6	185.0
57.5°	306.8	316.2	296.9	264.9	236.2	211.5	194.9	185.6	176.9	171.6	166.1
60°	274.5	283.4	268.4	241.5	214.4	193.2	177.5	169.1	161.6	157.9	154.0
62.5°	245.8	253.7	242.6	217.7	194.2	173.7	160.5	152.5	147.4	143.4	140.9
65°	204.8	211.5	201.9	183.8	163.6	147.3	136.6	130.2	125.4	123.7	120.8
67.5°	165.6	171.7	166.5	151.1	134.9	122.5	114.1	108.1	105.1	103.8	101.7
70°	142.2	148.4	142.8	129.4	116.9	106.6	98.6	95.1	92.1	91.5	88.7
72.5°	122.5	126.7	121.1	110.6	100.0	91.3	85.1	81.5	79.9	78.8	77.2
75°	91.9	95.6	91.9	83.8	76.2	70.1	64.8	63.4	61.6	61.0	59.9
77.5°	65.0	68.2	65.4	60.4	54.7	49.9	47.1	45.3	44.9	43.8	44.3
80°	49.7	51.7	49.1	45.6	41.2	37.9	35.9	34.9	33.7	33.2	34.0
82.5°	35.7	36.6	35.2	32.9	29.6	27.5	26.1	24.9	24.6	24.7	24.7
85°	18.5	18.3	18.2	16.1	15.1	13.7	12.8	12.7	12.4	12.8	13.3
87.5°	9.0	9.1	7.8	7.1	6.5	5.8	5.0	4.5	5.0	5.8	6.1
90°	14.0	14.0	8.0	8.0	7.0	6.0	3.0	1.0	3.0	6.0	7.0
92.5°	202.1	124.5	73.6	52.9	38.2	26.0	16.6	11.4	16.6	26.0	38.2
95°	376.2	212.1	125.1	83.0	59.1	46.1	36.0	33.0	36.0	46.1	59.1
97.5°	338.2	202.7	135.7	100.5	79.8	67.8	59.2	59.2	59.2	67.8	79.8
100°	318.1	205.1	146.1	114.1	95.1	83.0	76.0	76.0	76.0	83.0	95.1
102.5°	312.5	213.1	159.7	129.2	111.1	99.9	93.7	92.0	93.7	99.9	111.1
105°	315.1	232.1	184.1	155.1	137.1	125.1	120.0	117.1	120.0	125.1	137.1
107.5°	329.9	254.3	210.3	181.7	164.5	151.7	146.6	144.6	146.6	151.7	164.5
110°	341.1	271.1	227.1	200.1	182.1	170.0	165.1	163.1	165.1	170.0	182.1



TEST NUMBER: P332528-935

CATALOG NUMBER: SA4XXDIP-C350D1205U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	353.2	287.1	244.7	217.7	199.7	188.5	182.7	180.7	182.7	188.5	199.7
115°	372.2	312.1	272.2	245.1	226.1	216.1	209.1	206.1	209.1	216.1	226.1
117.5°	391.6	336.4	298.3	270.4	252.5	241.5	235.3	232.5	235.3	241.5	252.5
120°	405.2	353.2	315.1	287.1	270.1	259.2	252.1	250.1	252.1	259.2	270.1
122.5°	418.0	369.2	331.1	303.9	285.3	275.2	268.1	266.1	268.1	275.2	285.3
125°	437.2	391.2	355.2	327.2	308.2	297.1	291.1	287.1	291.1	297.1	308.2
127.5°	453.8	411.6	376.8	348.5	328.7	316.2	308.9	305.7	308.9	316.2	328.7
130°	464.3	425.2	391.2	362.1	343.2	328.1	320.1	316.2	320.1	328.1	343.2
132.5°	474.7	436.4	402.4	375.0	354.4	340.2	329.8	326.6	329.8	340.2	354.4
135°	488.3	452.2	419.2	393.2	372.2	355.2	345.2	341.1	345.2	355.2	372.2
137.5°	497.8	464.3	433.4	408.6	386.8	370.6	359.6	355.8	359.6	370.6	386.8
140°	504.2	472.3	442.2	418.2	397.2	380.2	369.2	366.2	369.2	380.2	397.2
142.5°	509.0	479.4	450.2	427.0	406.8	390.5	380.4	377.4	380.4	390.5	406.8
145°	514.3	487.2	461.2	439.2	420.2	406.2	396.2	393.2	396.2	406.2	420.2
147.5°	518.8	495.2	470.8	451.0	435.2	420.8	412.0	411.0	412.0	420.8	435.2
150°	521.2	499.2	477.3	458.2	443.2	431.2	423.2	422.2	423.2	431.2	443.2
152.5°	522.9	502.5	482.8	465.5	452.0	440.8	432.8	432.6	432.8	440.8	452.0
155°	524.3	507.2	490.3	475.3	464.3	454.2	448.2	447.2	448.2	454.2	464.3
157.5°	524.3	510.7	496.3	484.4	474.8	467.0	461.4	461.4	461.4	467.0	474.8
160°	524.3	512.2	500.2	489.2	481.2	474.2	470.2	470.2	470.2	474.2	481.2
162.5°	524.3	513.8	502.7	494.0	486.8	480.6	477.4	478.2	477.4	480.6	486.8
165°	522.3	514.3	505.2	499.2	494.2	489.2	487.2	487.2	487.2	489.2	494.2
167.5°	519.9	514.0	507.5	502.8	500.1	496.3	495.2	496.3	495.2	496.3	500.1
170°	518.2	513.2	508.2	505.2	503.3	500.2	499.2	500.2	499.2	500.2	503.3
172.5°	516.7	512.5	509.0	506.9	505.7	503.4	503.3	504.2	503.3	503.4	505.7
175°	514.3	511.3	509.3	509.3	508.2	507.2	507.2	508.2	507.2	507.2	508.2
177.5°	511.6	510.1	509.3	509.3	509.3	508.4	509.3	510.1	509.3	508.4	509.3
180°	509.3	509.3	509.3	509.3	509.3	509.3	509.3	509.3	509.3	509.3	509.3



TEST NUMBER: P332528-935

CATALOG NUMBER: SA4XXDIP-C350D1205U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9
2.5°	482.4	481.0	478.9	476.0	473.5	470.9	470.2	469.2	471.2	469.6	469.1
5°	466.7	462.4	456.8	450.6	446.9	441.6	440.6	438.5	436.4	436.3	434.2
7.5°	449.9	443.6	436.4	430.0	424.0	418.2	414.4	413.6	410.6	408.8	406.8
10°	439.1	431.4	423.0	416.9	410.0	403.9	399.6	397.2	395.1	392.9	390.8
12.5°	426.5	418.2	411.3	404.7	396.5	391.8	384.8	380.6	380.1	380.1	374.9
15°	411.6	403.5	392.9	383.5	379.0	370.1	366.2	361.3	358.3	355.2	352.8
17.5°	394.7	384.5	376.3	365.5	357.0	349.8	344.7	341.8	337.2	332.9	329.8
20°	384.1	373.3	364.5	353.1	343.8	335.0	330.7	326.7	323.2	319.5	316.1
22.5°	373.3	362.1	351.4	340.3	331.6	322.3	318.1	312.6	309.4	307.3	303.8
25°	356.4	344.1	331.9	321.3	312.4	304.2	298.8	294.5	290.8	289.1	286.9
27.5°	337.9	325.8	314.0	302.0	291.8	285.9	281.5	278.3	276.1	274.0	272.9
30°	326.2	313.6	301.0	289.7	280.4	274.5	270.4	268.2	266.6	265.5	264.5
32.5°	314.4	301.9	288.6	278.4	269.9	264.7	261.6	259.3	258.6	258.2	257.8
35°	295.2	282.7	270.4	261.2	253.3	251.2	248.6	247.4	246.9	248.4	249.0
37.5°	276.8	265.1	253.8	245.0	239.7	236.8	235.8	235.9	237.4	238.6	240.0
40°	264.9	253.5	242.9	235.1	230.2	228.4	228.0	229.0	230.7	232.1	233.8
42.5°	253.3	242.1	232.5	225.2	221.8	220.1	220.3	221.4	223.7	225.4	227.8
45°	235.4	226.0	216.6	210.7	207.8	208.3	208.3	210.1	212.3	215.0	217.7
47.5°	218.4	209.0	201.3	196.3	194.8	194.5	195.6	198.0	201.2	204.5	208.2
50°	207.1	198.0	191.3	186.8	185.2	185.8	187.4	189.7	193.6	197.7	201.6
52.5°	195.4	187.3	181.1	176.9	175.7	176.8	178.5	182.0	185.5	189.9	194.5
55°	177.5	170.6	165.7	162.6	162.2	162.8	164.6	168.5	173.4	178.9	183.4
57.5°	159.6	153.8	149.3	147.2	147.4	148.0	151.0	155.6	160.8	166.7	172.5
60°	147.5	142.2	138.5	136.9	137.2	138.4	142.1	146.3	152.8	158.5	164.6
62.5°	136.1	131.5	127.9	126.5	126.2	128.9	132.4	136.8	143.4	149.7	156.4
65°	117.8	114.1	111.2	110.5	111.1	113.1	117.6	123.5	129.0	135.7	142.7
67.5°	99.9	96.9	94.9	95.2	96.0	99.0	102.7	107.8	114.1	121.1	127.9
70°	88.4	85.6	83.9	84.1	85.4	89.0	92.3	97.4	104.1	111.2	116.9
72.5°	76.7	74.8	73.4	74.2	75.4	77.9	82.1	87.1	93.1	99.7	105.7
75°	58.9	58.9	58.1	58.7	60.5	62.9	66.0	71.3	77.2	82.6	87.4
77.5°	43.7	43.2	43.7	44.5	45.5	48.5	52.0	55.8	60.2	65.5	69.6
80°	33.4	33.7	34.6	35.9	36.2	38.5	42.2	45.6	49.1	53.6	57.4
82.5°	25.1	25.3	25.8	27.4	27.8	30.2	32.5	36.0	39.2	42.2	45.4
85°	13.7	13.7	14.6	15.3	16.3	17.9	19.4	21.4	24.3	26.3	29.4
87.5°	6.8	6.8	8.7	9.0	9.9	11.1	11.2	13.3	14.0	15.1	16.5
90°	8.0	8.0	14.0	14.0	16.0	18.0	17.0	18.0	19.0	20.0	20.0
92.5°	52.9	73.6	124.5	202.1	277.8	317.4	264.3	196.5	147.8	117.7	97.6
95°	83.0	125.1	212.1	376.2	615.3	815.4	838.4	741.3	586.3	452.2	355.2
97.5°	100.5	135.7	202.7	338.2	575.8	858.8	1053.3	1095.4	1037.7	939.9	835.4
100°	114.1	146.1	205.1	318.1	522.3	804.3	1060.5	1206.6	1226.6	1177.6	1103.5
102.5°	129.2	159.7	213.1	312.5	486.2	736.3	1000.5	1201.0	1300.2	1314.4	1283.6
105°	155.1	184.1	232.1	315.1	455.2	656.3	891.4	1120.5	1293.7	1392.7	1433.7
107.5°	181.7	210.3	254.3	329.9	449.6	611.5	803.4	1006.3	1190.6	1330.1	1419.3
110°	200.1	227.1	271.1	341.1	451.3	596.3	759.4	937.5	1110.5	1255.6	1365.6



TEST NUMBER: P332528-935

CATALOG NUMBER: SA4XXDIP-C350D1205U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	217.7	244.7	287.1	353.2	456.0	589.1	734.5	887.0	1040.1	1177.2	1287.2
115°	245.1	272.2	312.1	372.2	465.2	585.3	711.4	836.4	959.5	1076.5	1172.6
117.5°	270.4	298.3	336.4	391.6	475.0	584.3	700.9	811.6	913.4	1005.5	1086.9
120°	287.1	315.1	353.2	405.2	482.2	584.3	695.3	800.4	893.5	973.4	1044.5
122.5°	303.9	331.1	369.2	418.0	489.5	583.5	689.0	790.7	880.6	953.5	1015.7
125°	327.2	355.2	391.2	437.2	500.2	582.3	678.3	774.4	860.4	929.4	984.5
127.5°	348.5	376.8	411.6	453.8	508.9	580.1	664.1	754.3	836.6	905.4	957.7
130°	362.1	391.2	425.2	464.3	515.2	579.3	655.3	738.4	817.4	885.5	938.5
132.5°	375.0	402.4	436.4	474.7	520.8	578.5	647.3	721.5	795.8	862.2	915.2
135°	393.2	419.2	452.2	488.3	529.3	577.3	635.3	698.4	763.4	824.4	874.4
137.5°	408.6	433.4	464.3	497.8	534.3	577.0	624.9	677.3	732.4	783.8	829.0
140°	418.2	442.2	472.3	504.2	538.3	576.3	619.3	665.3	712.3	757.3	799.4
142.5°	427.0	450.2	479.4	509.0	541.5	576.3	614.5	654.1	695.5	734.2	770.6
145°	439.2	461.2	487.2	514.3	543.3	574.3	606.3	638.3	672.4	702.3	730.4
147.5°	451.0	470.8	495.2	518.8	544.2	570.7	598.9	625.3	652.3	676.3	698.4
150°	458.2	477.3	499.2	521.2	544.2	568.3	593.3	617.3	640.3	660.3	678.3
152.5°	465.5	482.8	502.5	522.9	542.7	564.3	586.9	608.5	628.3	646.7	661.5
155°	475.3	490.3	507.2	524.3	540.3	558.3	577.3	595.3	611.3	626.3	638.3
157.5°	484.4	496.3	510.7	524.3	537.7	552.1	567.5	581.1	594.5	607.1	616.7
160°	489.2	500.2	512.2	524.3	535.3	547.3	560.3	572.3	583.2	594.3	602.3
162.5°	494.0	502.7	513.8	524.3	532.9	542.4	553.9	563.4	572.9	581.5	588.7
165°	499.2	505.2	514.3	522.3	528.2	535.3	543.3	551.3	557.2	564.3	569.3
167.5°	502.8	507.5	514.0	519.9	523.5	528.1	533.6	539.5	544.1	549.7	552.7
170°	505.2	508.2	513.2	518.2	520.2	523.2	527.3	532.3	535.3	539.2	542.3
172.5°	506.9	509.0	512.5	516.7	517.0	518.4	521.7	525.8	528.1	530.5	532.6
175°	509.3	509.3	511.3	514.3	513.2	513.2	515.2	517.3	518.2	520.2	520.2
177.5°	509.3	509.3	510.1	511.6	510.1	510.1	510.8	511.6	512.5	512.5	513.2
180°	509.3	509.3	509.3	509.3	509.3	509.3	509.3	509.3	509.3	509.3	509.3



TEST NUMBER: P332528-935

CATALOG NUMBER: SA4XXDIP-C350D1205U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9
2.5°	468.7	468.5	467.3	467.1	467.3	468.5	468.7	469.1	469.6	471.2	469.2
5°	433.0	432.0	431.4	433.6	431.4	432.0	433.0	434.2	436.3	436.4	438.5
7.5°	406.0	405.3	403.5	402.9	403.5	405.3	406.0	406.8	408.8	410.6	413.6
10°	388.8	388.0	386.3	385.9	386.3	388.0	388.8	390.8	392.9	395.1	397.2
12.5°	372.1	370.6	370.2	370.7	370.2	370.6	372.1	374.9	380.1	380.1	380.6
15°	350.1	349.2	347.0	347.7	347.0	349.2	350.1	352.8	355.2	358.3	361.3
17.5°	328.3	327.4	324.6	327.0	324.6	327.4	328.3	329.8	332.9	337.2	341.8
20°	314.6	313.0	311.6	311.3	311.6	313.0	314.6	316.1	319.5	323.2	326.7
22.5°	301.6	300.1	300.0	298.7	300.0	300.1	301.6	303.8	307.3	309.4	312.6
25°	285.2	283.9	283.4	282.4	283.4	283.9	285.2	286.9	289.1	290.8	294.5
27.5°	272.8	272.1	271.3	271.6	271.3	272.1	272.8	272.9	274.0	276.1	278.3
30°	265.1	264.9	264.5	264.5	264.5	264.9	265.1	264.5	265.5	266.6	268.2
32.5°	258.7	258.7	259.0	259.0	259.0	258.7	258.7	257.8	258.2	258.6	259.3
35°	249.9	250.5	250.8	250.2	250.8	250.5	249.9	249.0	248.4	246.9	247.4
37.5°	241.8	242.4	243.0	243.7	243.0	242.4	241.8	240.0	238.6	237.4	235.9
40°	235.6	236.9	237.4	238.4	237.4	236.9	235.6	233.8	232.1	230.7	229.0
42.5°	229.7	231.3	232.3	232.6	232.3	231.3	229.7	227.8	225.4	223.7	221.4
45°	220.7	222.3	223.8	223.8	223.8	222.3	220.7	217.7	215.0	212.3	210.1
47.5°	211.4	213.7	215.2	215.5	215.2	213.7	211.4	208.2	204.5	201.2	198.0
50°	205.0	207.8	209.3	210.3	209.3	207.8	205.0	201.6	197.7	193.6	189.7
52.5°	198.8	201.6	203.5	204.1	203.5	201.6	198.8	194.5	189.9	185.5	182.0
55°	188.0	192.2	194.4	195.2	194.4	192.2	188.0	183.4	178.9	173.4	168.5
57.5°	178.0	181.8	184.3	184.9	184.3	181.8	178.0	172.5	166.7	160.8	155.6
60°	170.1	174.3	177.5	178.1	177.5	174.3	170.1	164.6	158.5	152.8	146.3
62.5°	162.1	166.4	169.4	170.9	169.4	166.4	162.1	156.4	149.7	143.4	136.8
65°	148.4	152.7	155.5	156.1	155.5	152.7	148.4	142.7	135.7	129.0	123.5
67.5°	133.3	137.6	139.4	140.6	139.4	137.6	133.3	127.9	121.1	114.1	107.8
70°	122.7	126.1	128.2	129.2	128.2	126.1	122.7	116.9	111.2	104.1	97.4
72.5°	110.6	114.3	116.6	116.8	116.6	114.3	110.6	105.7	99.7	93.1	87.1
75°	92.1	95.4	96.6	96.6	96.6	95.4	92.1	87.4	82.6	77.2	71.3
77.5°	72.9	74.6	76.1	76.5	76.1	74.6	72.9	69.6	65.5	60.2	55.8
80°	60.5	61.6	62.8	62.8	62.8	61.6	60.5	57.4	53.6	49.1	45.6
82.5°	47.8	48.6	49.9	49.7	49.9	48.6	47.8	45.4	42.2	39.2	36.0
85°	28.9	30.7	30.6	30.1	30.6	30.7	28.9	29.4	26.3	24.3	21.4
87.5°	17.2	17.6	17.9	18.3	17.9	17.6	17.2	16.5	15.1	14.0	13.3
90°	21.0	22.0	21.0	21.0	21.0	22.0	21.0	20.0	20.0	19.0	18.0
92.5°	85.8	80.4	77.1	77.1	77.1	80.4	85.8	97.6	117.7	147.8	196.5
95°	306.2	275.2	257.1	244.1	257.1	275.2	306.2	355.2	452.2	586.3	741.3
97.5°	763.5	703.4	673.3	652.6	673.3	703.4	763.5	835.4	939.9	1037.7	1095.4
100°	1016.5	955.5	925.5	917.5	925.5	955.5	1016.5	1103.5	1177.6	1226.6	1206.6
102.5°	1230.2	1185.9	1154.3	1148.0	1154.3	1185.9	1230.2	1283.6	1314.4	1300.2	1201.0
105°	1435.7	1427.7	1413.7	1407.6	1413.7	1427.7	1435.7	1433.7	1392.7	1293.7	1120.5
107.5°	1468.7	1491.5	1501.5	1504.2	1501.5	1491.5	1468.7	1419.3	1330.1	1190.6	1006.3
110°	1436.7	1478.7	1496.8	1505.7	1496.8	1478.7	1436.7	1365.6	1255.6	1110.5	937.5



TEST NUMBER: P332528-935

CATALOG NUMBER: SA4XXDIP-C350D1205U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1367.9	1418.7	1443.9	1458.5	1443.9	1418.7	1367.9	1287.2	1177.2	1040.1	887.0
115°	1251.6	1311.6	1343.7	1351.7	1343.7	1311.6	1251.6	1172.6	1076.5	959.5	836.4
117.5°	1154.3	1204.8	1237.2	1243.4	1237.2	1204.8	1154.3	1086.9	1005.5	913.4	811.6
120°	1101.6	1145.6	1171.6	1182.6	1171.6	1145.6	1101.6	1044.5	973.4	893.5	800.4
122.5°	1063.9	1101.6	1123.5	1134.5	1123.5	1101.6	1063.9	1015.7	953.5	880.6	790.7
125°	1024.5	1053.5	1072.5	1078.5	1072.5	1053.5	1024.5	984.5	929.4	860.4	774.4
127.5°	997.9	1023.7	1039.7	1045.7	1039.7	1023.7	997.9	957.7	905.4	836.6	754.3
130°	979.5	1004.4	1020.5	1026.5	1020.5	1004.4	979.5	938.5	885.5	817.4	738.4
132.5°	955.5	983.7	998.8	1004.9	998.8	983.7	955.5	915.2	862.2	795.8	721.5
135°	914.5	942.5	958.5	964.5	958.5	942.5	914.5	874.4	824.4	763.4	698.4
137.5°	866.4	894.1	907.2	914.5	907.2	894.1	866.4	829.0	783.8	732.4	677.3
140°	834.4	856.4	870.4	878.4	870.4	856.4	834.4	799.4	757.3	712.3	665.3
142.5°	801.6	822.0	834.4	840.0	834.4	822.0	801.6	770.6	734.2	695.5	654.1
145°	755.4	772.4	782.4	787.4	782.4	772.4	755.4	730.4	702.3	672.4	638.3
147.5°	716.8	731.3	739.0	740.7	739.0	731.3	716.8	698.4	676.3	652.3	625.3
150°	694.3	707.3	713.3	714.4	713.3	707.3	694.3	678.3	660.3	640.3	617.3
152.5°	675.1	685.7	689.3	690.3	689.3	685.7	675.1	661.5	646.7	628.3	608.5
155°	648.3	656.3	659.4	659.4	659.4	656.3	648.3	638.3	626.3	611.3	595.3
157.5°	624.3	630.3	632.1	632.1	632.1	630.3	624.3	616.7	607.1	594.5	581.1
160°	608.3	614.3	615.3	615.3	615.3	614.3	608.3	602.3	594.3	583.2	572.3
162.5°	593.1	599.1	600.1	599.3	600.1	599.1	593.1	588.7	581.5	572.9	563.4
165°	573.3	577.3	576.3	575.3	576.3	577.3	573.3	569.3	564.3	557.2	551.3
167.5°	554.7	557.2	557.1	556.3	557.1	557.2	554.7	552.7	549.7	544.1	539.5
170°	544.2	545.3	544.2	544.2	544.2	545.3	544.2	542.3	539.2	535.3	532.3
172.5°	533.8	534.9	533.8	532.3	533.8	534.9	533.8	532.6	530.5	528.1	525.8
175°	520.2	522.3	520.2	518.2	520.2	522.3	520.2	520.2	520.2	518.2	517.3
177.5°	512.5	513.2	511.6	510.1	511.6	513.2	512.5	513.2	512.5	512.5	511.6
180°	509.3	509.3	509.3	509.3	509.3	509.3	509.3	509.3	509.3	509.3	509.3



TEST NUMBER: P332528-935

CATALOG NUMBER: SA4XXDIP-C350D1205U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9
2.5°	470.2	470.9	473.5	476.0	478.9	481.0	482.4	484.1	487.5	490.3	492.9
5°	440.6	441.6	446.9	450.6	456.8	462.4	466.7	471.3	476.8	484.4	491.3
7.5°	414.4	418.2	424.0	430.0	436.4	443.6	449.9	456.9	466.4	476.8	487.5
10°	399.6	403.9	410.0	416.9	423.0	431.4	439.1	447.5	458.3	470.9	483.5
12.5°	384.8	391.8	396.5	404.7	411.3	418.2	426.5	437.4	450.0	463.2	478.5
15°	366.2	370.1	379.0	383.5	392.9	403.5	411.6	422.6	434.8	452.4	469.5
17.5°	344.7	349.8	357.0	365.5	376.3	384.5	394.7	406.0	421.5	438.9	460.3
20°	330.7	335.0	343.8	353.1	364.5	373.3	384.1	395.1	411.0	429.6	451.9
22.5°	318.1	322.3	331.6	340.3	351.4	362.1	373.3	386.2	401.4	420.9	443.8
25°	298.8	304.2	312.4	321.3	331.9	344.1	356.4	367.8	384.1	404.7	429.1
27.5°	281.5	285.9	291.8	302.0	314.0	325.8	337.9	352.3	368.0	389.8	415.1
30°	270.4	274.5	280.4	289.7	301.0	313.6	326.2	340.1	356.4	378.0	403.9
32.5°	261.6	264.7	269.9	278.4	288.6	301.9	314.4	328.6	345.8	367.0	392.3
35°	248.6	251.2	253.3	261.2	270.4	282.7	295.2	310.6	327.1	347.2	372.5
37.5°	235.8	236.8	239.7	245.0	253.8	265.1	276.8	291.9	308.8	329.2	352.1
40°	228.0	228.4	230.2	235.1	242.9	253.5	264.9	279.7	295.8	315.2	337.9
42.5°	220.3	220.1	221.8	225.2	232.5	242.1	253.3	266.9	283.0	300.9	322.2
45°	208.3	208.3	207.8	210.7	216.6	226.0	235.4	248.4	261.8	279.4	297.3
47.5°	195.6	194.5	194.8	196.3	201.3	209.0	218.4	229.1	241.0	255.8	271.6
50°	187.4	185.8	185.2	186.8	191.3	198.0	207.1	216.4	227.6	240.6	254.1
52.5°	178.5	176.8	175.7	176.9	181.1	187.3	195.4	203.7	213.8	224.4	236.0
55°	164.6	162.8	162.2	162.6	165.7	170.6	177.5	185.0	192.6	201.3	209.5
57.5°	151.0	148.0	147.4	147.2	149.3	153.8	159.6	166.1	171.6	176.9	185.6
60°	142.1	138.4	137.2	136.9	138.5	142.2	147.5	154.0	157.9	161.6	169.1
62.5°	132.4	128.9	126.2	126.5	127.9	131.5	136.1	140.9	143.4	147.4	152.5
65°	117.6	113.1	111.1	110.5	111.2	114.1	117.8	120.8	123.7	125.4	130.2
67.5°	102.7	99.0	96.0	95.2	94.9	96.9	99.9	101.7	103.8	105.1	108.1
70°	92.3	89.0	85.4	84.1	83.9	85.6	88.4	88.7	91.5	92.1	95.1
72.5°	82.1	77.9	75.4	74.2	73.4	74.8	76.7	77.2	78.8	79.9	81.5
75°	66.0	62.9	60.5	58.7	58.1	58.9	58.9	59.9	61.0	61.6	63.4
77.5°	52.0	48.5	45.5	44.5	43.7	43.2	43.7	44.3	43.8	44.9	45.3
80°	42.2	38.5	36.2	35.9	34.6	33.7	33.4	34.0	33.2	33.7	34.9
82.5°	32.5	30.2	27.8	27.4	25.8	25.3	25.1	24.7	24.7	24.6	24.9
85°	19.4	17.9	16.3	15.3	14.6	13.7	13.7	13.3	12.8	12.4	12.7
87.5°	11.2	11.1	9.9	9.0	8.7	6.8	6.8	6.1	5.8	5.0	4.5
90°	17.0	18.0	16.0	14.0	14.0	8.0	8.0	7.0	6.0	3.0	1.0
92.5°	264.3	317.4	277.8	202.1	124.5	73.6	52.9	38.2	26.0	16.6	11.4
95°	838.4	815.4	615.3	376.2	212.1	125.1	83.0	59.1	46.1	36.0	33.0
97.5°	1053.3	858.8	575.8	338.2	202.7	135.7	100.5	79.8	67.8	59.2	59.2
100°	1060.5	804.3	522.3	318.1	205.1	146.1	114.1	95.1	83.0	76.0	76.0
102.5°	1000.5	736.3	486.2	312.5	213.1	159.7	129.2	111.1	99.9	93.7	92.0
105°	891.4	656.3	455.2	315.1	232.1	184.1	155.1	137.1	125.1	120.0	117.1
107.5°	803.4	611.5	449.6	329.9	254.3	210.3	181.7	164.5	151.7	146.6	144.6
110°	759.4	596.3	451.3	341.1	271.1	227.1	200.1	182.1	170.0	165.1	163.1



TEST NUMBER: P332528-935

CATALOG NUMBER: SA4XXDIP-C350D1205U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	734.5	589.1	456.0	353.2	287.1	244.7	217.7	199.7	188.5	182.7	180.7
115°	711.4	585.3	465.2	372.2	312.1	272.2	245.1	226.1	216.1	209.1	206.1
117.5°	700.9	584.3	475.0	391.6	336.4	298.3	270.4	252.5	241.5	235.3	232.5
120°	695.3	584.3	482.2	405.2	353.2	315.1	287.1	270.1	259.2	252.1	250.1
122.5°	689.0	583.5	489.5	418.0	369.2	331.1	303.9	285.3	275.2	268.1	266.1
125°	678.3	582.3	500.2	437.2	391.2	355.2	327.2	308.2	297.1	291.1	287.1
127.5°	664.1	580.1	508.9	453.8	411.6	376.8	348.5	328.7	316.2	308.9	305.7
130°	655.3	579.3	515.2	464.3	425.2	391.2	362.1	343.2	328.1	320.1	316.2
132.5°	647.3	578.5	520.8	474.7	436.4	402.4	375.0	354.4	340.2	329.8	326.6
135°	635.3	577.3	529.3	488.3	452.2	419.2	393.2	372.2	355.2	345.2	341.1
137.5°	624.9	577.0	534.3	497.8	464.3	433.4	408.6	386.8	370.6	359.6	355.8
140°	619.3	576.3	538.3	504.2	472.3	442.2	418.2	397.2	380.2	369.2	366.2
142.5°	614.5	576.3	541.5	509.0	479.4	450.2	427.0	406.8	390.5	380.4	377.4
145°	606.3	574.3	543.3	514.3	487.2	461.2	439.2	420.2	406.2	396.2	393.2
147.5°	598.9	570.7	544.2	518.8	495.2	470.8	451.0	435.2	420.8	412.0	411.0
150°	593.3	568.3	544.2	521.2	499.2	477.3	458.2	443.2	431.2	423.2	422.2
152.5°	586.9	564.3	542.7	522.9	502.5	482.8	465.5	452.0	440.8	432.8	432.6
155°	577.3	558.3	540.3	524.3	507.2	490.3	475.3	464.3	454.2	448.2	447.2
157.5°	567.5	552.1	537.7	524.3	510.7	496.3	484.4	474.8	467.0	461.4	461.4
160°	560.3	547.3	535.3	524.3	512.2	500.2	489.2	481.2	474.2	470.2	470.2
162.5°	553.9	542.4	532.9	524.3	513.8	502.7	494.0	486.8	480.6	477.4	478.2
165°	543.3	535.3	528.2	522.3	514.3	505.2	499.2	494.2	489.2	487.2	487.2
167.5°	533.6	528.1	523.5	519.9	514.0	507.5	502.8	500.1	496.3	495.2	496.3
170°	527.3	523.2	520.2	518.2	513.2	508.2	505.2	503.3	500.2	499.2	500.2
172.5°	521.7	518.4	517.0	516.7	512.5	509.0	506.9	505.7	503.4	503.3	504.2
175°	515.2	513.2	513.2	514.3	511.3	509.3	509.3	508.2	507.2	507.2	508.2
177.5°	510.8	510.1	510.1	511.6	510.1	509.3	509.3	509.3	508.4	509.3	510.1
180°	509.3	509.3	509.3	509.3	509.3	509.3	509.3	509.3	509.3	509.3	509.3



TEST NUMBER: P332528-935

CATALOG NUMBER: SA4XXDIP-C350D1205U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9
2.5°	495.2	496.8	498.9	502.5	503.8	505.4	507.7	507.6	508.2	510.7	515.8
5°	497.0	503.3	509.5	516.8	524.5	529.6	536.5	540.8	545.1	550.6	560.0
7.5°	497.7	507.7	518.9	531.8	543.3	556.5	566.8	576.5	585.3	596.8	608.0
10°	496.6	510.1	524.5	540.8	558.1	572.8	586.1	601.2	614.0	628.0	640.7
12.5°	494.5	510.7	530.0	548.3	568.5	590.2	606.7	622.0	639.0	655.2	674.8
15°	489.7	511.9	534.5	558.5	585.7	610.7	634.6	654.3	672.6	696.9	722.4
17.5°	483.5	507.5	536.1	565.2	593.5	622.1	651.6	681.3	704.5	734.6	754.5
20°	477.9	505.6	534.9	569.6	597.9	633.5	662.9	691.6	723.4	753.4	777.2
22.5°	469.8	500.2	531.3	565.8	603.0	638.8	672.6	703.8	735.6	768.2	797.0
25°	459.7	487.2	524.1	563.2	600.3	639.0	678.0	717.0	751.3	785.7	812.6
27.5°	442.5	477.2	511.5	551.9	593.1	636.9	678.6	719.5	755.4	783.7	800.3
30°	433.6	463.8	501.1	541.7	586.3	633.4	676.7	716.9	750.3	772.9	779.6
32.5°	420.6	451.7	488.2	530.2	577.5	625.9	671.0	708.9	736.8	748.6	740.5
35°	401.2	429.4	466.2	509.2	558.4	609.8	654.5	686.5	700.8	689.6	661.7
37.5°	378.0	405.9	442.9	485.2	536.0	588.4	628.7	651.8	647.0	619.1	577.6
40°	361.7	387.8	423.0	468.6	518.1	570.8	606.2	618.6	605.6	565.7	521.4
42.5°	343.6	369.0	404.4	448.5	500.9	549.4	580.3	581.3	559.5	511.7	467.4
45°	316.1	340.3	373.7	419.6	468.0	513.7	534.1	524.1	483.7	437.7	393.0
47.5°	288.9	309.9	342.9	386.3	432.4	470.8	481.0	463.0	420.0	375.2	333.9
50°	269.0	290.2	321.2	362.7	407.2	440.3	445.2	421.4	379.2	334.2	301.8
52.5°	249.9	271.0	300.7	339.2	379.9	409.8	410.0	382.5	340.4	300.3	270.2
55°	221.9	240.8	267.8	302.2	338.5	361.9	356.2	327.7	291.2	256.3	230.1
57.5°	194.9	211.5	236.2	264.9	296.9	316.2	306.8	279.3	246.8	217.1	197.3
60°	177.5	193.2	214.4	241.5	268.4	283.4	274.5	249.6	219.6	195.8	178.5
62.5°	160.5	173.7	194.2	217.7	242.6	253.7	245.8	221.3	195.4	173.8	159.7
65°	136.6	147.3	163.6	183.8	201.9	211.5	204.8	181.9	162.2	146.7	135.5
67.5°	114.1	122.5	134.9	151.1	166.5	171.7	165.6	149.6	132.9	120.5	112.6
70°	98.6	106.6	116.9	129.4	142.8	148.4	142.2	129.6	116.0	104.5	96.8
72.5°	85.1	91.3	100.0	110.6	121.1	126.7	122.5	110.4	98.8	90.3	83.8
75°	64.8	70.1	76.2	83.8	91.9	95.6	91.9	83.5	75.6	69.3	64.6
77.5°	47.1	49.9	54.7	60.4	65.4	68.2	65.0	59.4	54.5	50.2	47.9
80°	35.9	37.9	41.2	45.6	49.1	51.7	49.7	45.0	41.2	38.3	37.3
82.5°	26.1	27.5	29.6	32.9	35.2	36.6	35.7	32.3	30.7	28.2	27.2
85°	12.8	13.7	15.1	16.1	18.2	18.3	18.5	17.1	15.7	15.1	14.3
87.5°	5.0	5.8	6.5	7.1	7.8	9.1	9.0	9.4	9.1	8.8	8.4
90°	3.0	6.0	7.0	8.0	8.0	14.0	14.0	16.0	18.0	17.0	18.0
92.5°	16.6	26.0	38.2	52.9	73.6	124.5	202.1	277.8	317.4	264.3	196.5
95°	36.0	46.1	59.1	83.0	125.1	212.1	376.2	615.3	815.4	838.4	741.3
97.5°	59.2	67.8	79.8	100.5	135.7	202.7	338.2	575.8	858.8	1053.3	1095.4
100°	76.0	83.0	95.1	114.1	146.1	205.1	318.1	522.3	804.3	1060.5	1206.6
102.5°	93.7	99.9	111.1	129.2	159.7	213.1	312.5	486.2	736.3	1000.5	1201.0
105°	120.0	125.1	137.1	155.1	184.1	232.1	315.1	455.2	656.3	891.4	1120.5
107.5°	146.6	151.7	164.5	181.7	210.3	254.3	329.9	449.6	611.5	803.4	1006.3
110°	165.1	170.0	182.1	200.1	227.1	271.1	341.1	451.3	596.3	759.4	937.5



TEST NUMBER: P332528-935

CATALOG NUMBER: SA4XXDIP-C350D1205U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	182.7	188.5	199.7	217.7	244.7	287.1	353.2	456.0	589.1	734.5	887.0
115°	209.1	216.1	226.1	245.1	272.2	312.1	372.2	465.2	585.3	711.4	836.4
117.5°	235.3	241.5	252.5	270.4	298.3	336.4	391.6	475.0	584.3	700.9	811.6
120°	252.1	259.2	270.1	287.1	315.1	353.2	405.2	482.2	584.3	695.3	800.4
122.5°	268.1	275.2	285.3	303.9	331.1	369.2	418.0	489.5	583.5	689.0	790.7
125°	291.1	297.1	308.2	327.2	355.2	391.2	437.2	500.2	582.3	678.3	774.4
127.5°	308.9	316.2	328.7	348.5	376.8	411.6	453.8	508.9	580.1	664.1	754.3
130°	320.1	328.1	343.2	362.1	391.2	425.2	464.3	515.2	579.3	655.3	738.4
132.5°	329.8	340.2	354.4	375.0	402.4	436.4	474.7	520.8	578.5	647.3	721.5
135°	345.2	355.2	372.2	393.2	419.2	452.2	488.3	529.3	577.3	635.3	698.4
137.5°	359.6	370.6	386.8	408.6	433.4	464.3	497.8	534.3	577.0	624.9	677.3
140°	369.2	380.2	397.2	418.2	442.2	472.3	504.2	538.3	576.3	619.3	665.3
142.5°	380.4	390.5	406.8	427.0	450.2	479.4	509.0	541.5	576.3	614.5	654.1
145°	396.2	406.2	420.2	439.2	461.2	487.2	514.3	543.3	574.3	606.3	638.3
147.5°	412.0	420.8	435.2	451.0	470.8	495.2	518.8	544.2	570.7	598.9	625.3
150°	423.2	431.2	443.2	458.2	477.3	499.2	521.2	544.2	568.3	593.3	617.3
152.5°	432.8	440.8	452.0	465.5	482.8	502.5	522.9	542.7	564.3	586.9	608.5
155°	448.2	454.2	464.3	475.3	490.3	507.2	524.3	540.3	558.3	577.3	595.3
157.5°	461.4	467.0	474.8	484.4	496.3	510.7	524.3	537.7	552.1	567.5	581.1
160°	470.2	474.2	481.2	489.2	500.2	512.2	524.3	535.3	547.3	560.3	572.3
162.5°	477.4	480.6	486.8	494.0	502.7	513.8	524.3	532.9	542.4	553.9	563.4
165°	487.2	489.2	494.2	499.2	505.2	514.3	522.3	528.2	535.3	543.3	551.3
167.5°	495.2	496.3	500.1	502.8	507.5	514.0	519.9	523.5	528.1	533.6	539.5
170°	499.2	500.2	503.3	505.2	508.2	513.2	518.2	520.2	523.2	527.3	532.3
172.5°	503.3	503.4	505.7	506.9	509.0	512.5	516.7	517.0	518.4	521.7	525.8
175°	507.2	507.2	508.2	509.3	509.3	511.3	514.3	513.2	513.2	515.2	517.3
177.5°	509.3	508.4	509.3	509.3	509.3	510.1	511.6	510.1	510.1	510.8	511.6
180°	509.3	509.3	509.3	509.3	509.3	509.3	509.3	509.3	509.3	509.3	509.3



TEST NUMBER: P332528-935

CATALOG NUMBER: SA4XXDIP-C350D1205U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	491.9	491.9	491.9	491.9	491.9	491.9	491.9
2.5°	518.5	518.8	520.3	521.4	521.8	523.4	523.5
5°	564.0	567.5	574.2	574.8	575.8	581.2	577.0
7.5°	617.4	626.2	632.1	637.3	639.1	641.4	641.0
10°	651.7	664.7	671.2	681.7	682.0	684.7	683.0
12.5°	686.0	701.2	713.1	715.1	723.8	725.1	727.4
15°	734.8	750.9	767.4	773.4	785.3	788.2	792.6
17.5°	780.6	797.0	808.7	823.9	828.9	835.4	831.0
20°	805.7	823.6	838.4	850.3	855.4	859.1	858.7
22.5°	820.9	839.0	850.8	860.0	864.7	866.3	866.2
25°	830.3	840.8	844.5	847.9	842.6	840.8	841.5
27.5°	803.9	801.2	791.7	779.1	766.1	755.8	750.1
30°	767.6	751.7	737.3	712.0	699.0	691.2	684.2
32.5°	716.1	690.9	663.1	639.9	625.1	613.6	611.9
35°	627.8	590.0	555.9	527.5	512.9	500.5	497.6
37.5°	533.7	494.4	463.7	438.8	423.0	414.2	406.0
40°	471.3	437.5	407.3	386.2	374.1	367.8	362.7
42.5°	423.3	392.4	362.3	346.2	335.4	331.5	328.5
45°	356.8	328.0	307.3	295.1	288.8	282.2	279.1
47.5°	303.6	280.3	266.6	256.1	249.3	245.5	243.6
50°	273.5	254.3	242.1	234.1	228.0	225.0	223.3
52.5°	246.8	231.0	220.8	214.4	210.3	208.0	207.3
55°	212.5	200.5	194.0	188.5	185.5	183.4	182.6
57.5°	184.8	175.5	170.2	165.7	164.5	162.8	162.2
60°	166.5	159.4	154.9	151.8	150.8	148.8	149.1
62.5°	150.3	144.5	140.7	139.0	137.6	135.9	136.5
65°	127.2	122.9	120.8	119.2	117.6	116.6	117.4
67.5°	106.7	103.8	101.0	100.0	99.3	99.1	98.2
70°	93.3	90.9	88.4	87.8	87.8	87.0	86.8
72.5°	80.4	78.7	77.1	76.5	75.9	76.3	75.4
75°	62.2	60.7	60.1	59.5	59.3	59.3	58.7
77.5°	45.9	44.9	43.9	43.9	43.1	42.9	42.8
80°	34.9	34.4	33.7	33.7	33.2	33.4	33.0
82.5°	26.2	25.7	25.5	25.1	24.5	24.6	24.2
85°	14.0	13.4	13.3	12.7	12.2	12.7	12.2
87.5°	8.7	8.7	8.5	8.4	8.4	8.3	7.7
90°	19.0	20.0	20.0	21.0	22.0	21.0	21.0
92.5°	147.8	117.7	97.6	85.8	80.4	77.1	77.1
95°	586.3	452.2	355.2	306.2	275.2	257.1	244.1
97.5°	1037.7	939.9	835.4	763.5	703.4	673.3	652.6
100°	1226.6	1177.6	1103.5	1016.5	955.5	925.5	917.5
102.5°	1300.2	1314.4	1283.6	1230.2	1185.9	1154.3	1148.0
105°	1293.7	1392.7	1433.7	1435.7	1427.7	1413.7	1407.6
107.5°	1190.6	1330.1	1419.3	1468.7	1491.5	1501.5	1504.2
110°	1110.5	1255.6	1365.6	1436.7	1478.7	1496.8	1505.7



TEST NUMBER: P332528-935

CATALOG NUMBER: SA4XXDIP-C350D1205U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1040.1	1177.2	1287.2	1367.9	1418.7	1443.9	1458.5
115°	959.5	1076.5	1172.6	1251.6	1311.6	1343.7	1351.7
117.5°	913.4	1005.5	1086.9	1154.3	1204.8	1237.2	1243.4
120°	893.5	973.4	1044.5	1101.6	1145.6	1171.6	1182.6
122.5°	880.6	953.5	1015.7	1063.9	1101.6	1123.5	1134.5
125°	860.4	929.4	984.5	1024.5	1053.5	1072.5	1078.5
127.5°	836.6	905.4	957.7	997.9	1023.7	1039.7	1045.7
130°	817.4	885.5	938.5	979.5	1004.4	1020.5	1026.5
132.5°	795.8	862.2	915.2	955.5	983.7	998.8	1004.9
135°	763.4	824.4	874.4	914.5	942.5	958.5	964.5
137.5°	732.4	783.8	829.0	866.4	894.1	907.2	914.5
140°	712.3	757.3	799.4	834.4	856.4	870.4	878.4
142.5°	695.5	734.2	770.6	801.6	822.0	834.4	840.0
145°	672.4	702.3	730.4	755.4	772.4	782.4	787.4
147.5°	652.3	676.3	698.4	716.8	731.3	739.0	740.7
150°	640.3	660.3	678.3	694.3	707.3	713.3	714.4
152.5°	628.3	646.7	661.5	675.1	685.7	689.3	690.3
155°	611.3	626.3	638.3	648.3	656.3	659.4	659.4
157.5°	594.5	607.1	616.7	624.3	630.3	632.1	632.1
160°	583.2	594.3	602.3	608.3	614.3	615.3	615.3
162.5°	572.9	581.5	588.7	593.1	599.1	600.1	599.3
165°	557.2	564.3	569.3	573.3	577.3	576.3	575.3
167.5°	544.1	549.7	552.7	554.7	557.2	557.1	556.3
170°	535.3	539.2	542.3	544.2	545.3	544.2	544.2
172.5°	528.1	530.5	532.6	533.8	534.9	533.8	532.3
175°	518.2	520.2	520.2	520.2	522.3	520.2	518.2
177.5°	512.5	512.5	513.2	512.5	513.2	511.6	510.1
180°	509.3	509.3	509.3	509.3	509.3	509.3	509.3

(END OF REPORT)