

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332501-935

Luminaire Tested: **SA4XXDIP-C350D590U935-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332501-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C350D590U935-4F0-1E-UDD-A4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3176.8 lumens
Efficiency: N/A
Efficacy: 124.1 lumens/watt
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 25.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332501-935
CATALOG NUMBER: SA4XXDIP-C350D590U935-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332501-935

CATALOG NUMBER: SA4XXDIP-C350D590U935-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	49	49	49	43
1	96	92	88	85	88	84	81	78	70	67	65	56	55	53	44	43	42	36
2	88	81	75	70	80	74	69	64	61	58	54	50	47	45	39	37	36	31
3	80	71	64	58	73	65	59	54	54	50	46	44	41	38	35	33	31	26
4	73	63	55	49	67	58	51	46	48	43	39	39	36	33	31	29	27	23
5	67	56	48	42	61	52	45	40	43	38	34	35	32	29	28	25	23	20
6	62	50	42	37	57	46	39	34	39	34	30	32	28	25	26	23	21	18
7	57	45	38	32	52	42	35	30	35	30	26	29	25	22	23	20	18	16
8	53	41	34	28	49	38	31	27	32	27	23	27	23	20	21	19	16	14
9	50	38	30	25	45	35	28	24	30	24	21	25	21	18	20	17	15	13
10	46	34	27	23	42	32	26	21	27	22	19	23	19	16	18	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	3971	3971	3971	3971
5°	4676	3981	3514	3981
10°	5599	3963	3163	3963
15°	6624	3924	2906	3924
20°	7377	3882	2674	3882
25°	7496	3822	2515	3822
30°	6378	3765	2466	3765
35°	4904	3671	2466	3671
40°	3822	3561	2512	3561
45°	3186	3394	2555	3394
50°	2804	3191	2641	3191
55°	2570	2949	2747	2949
60°	2407	2730	2876	2730
65°	2243	2487	2982	2487
70°	2049	2245	3050	2245
75°	1831	1978	3013	1978
80°	1534	1623	2920	1623
85°	1130	1176	2788	1176



TEST NUMBER: P332501-935

CATALOG NUMBER: SA4XXDIP-C350D590U935-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.9	1.5
10°-20°	147.7	4.6
20°-30°	234.2	7.4
30°-40°	260.7	8.2
40°-50°	237.3	7.5
50°-60°	193.9	6.1
60°-70°	138.4	4.4
70°-80°	76.2	2.4
80°-90°	22.2	0.7
90°-100°	180.6	5.7
100°-110°	375.8	11.8
110°-120°	336.6	10.6
120°-130°	283.1	8.9
130°-140°	236.1	7.4
140°-150°	180.4	5.7
150°-160°	126.8	4.0
160°-170°	74.6	2.3
170°-180°	24.3	0.8
0°-30°	429.9	13.5
0°-40°	690.5	21.7
0°-60°	1121.7	35.3
0°-90°	1358.6	42.8
90°-120°	893.0	28.1
90°-150°	1592.6	50.1
90°-180°	1818.0	57.2
0°-180°	3176.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	492	492	492	492	492	
5°	577	491	434	491	577	59
15°	793	470	348	470	793	224
25°	842	429	282	429	842	371
35°	498	372	250	372	498	316
45°	279	297	224	297	279	220
55°	183	210	195	210	183	165
65°	117	130	156	130	117	116
75°	59	63	97	63	59	62
85°	12	13	30	13	12	15
90°	10	0	10	0	10	9
95°	120	16	120	16	120	186
105°	691	57	691	57	691	683
115°	664	101	664	101	664	659
125°	529	141	529	141	529	481
135°	474	168	474	168	474	365
145°	386	193	386	193	386	245
155°	324	220	324	220	324	151
165°	282	239	282	239	282	81
175°	254	250	254	250	254	25
180°	250	250	250	250	250	



TEST NUMBER: P332501-935

CATALOG NUMBER: SA4XXDIP-C350D590U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9
2.5°	523.5	523.4	521.8	521.4	520.3	518.8	518.5	515.8	510.7	508.2	507.6
5°	577.0	581.2	575.8	574.8	574.2	567.5	564.0	560.0	550.6	545.1	540.8
7.5°	641.0	641.4	639.1	637.3	632.1	626.2	617.4	608.0	596.8	585.3	576.5
10°	683.0	684.7	682.0	681.7	671.2	664.7	651.7	640.7	628.0	614.0	601.2
12.5°	727.4	725.1	723.8	715.1	713.1	701.2	686.0	674.8	655.2	639.0	622.0
15°	792.6	788.2	785.3	773.4	767.4	750.9	734.8	722.4	696.9	672.6	654.3
17.5°	831.0	835.4	828.9	823.9	808.7	797.0	780.6	754.5	734.6	704.5	681.3
20°	858.7	859.1	855.4	850.3	838.4	823.6	805.7	777.2	753.4	723.4	691.6
22.5°	866.2	866.3	864.7	860.0	850.8	839.0	820.9	797.0	768.2	735.6	703.8
25°	841.5	840.8	842.6	847.9	844.5	840.8	830.3	812.6	785.7	751.3	717.0
27.5°	750.1	755.8	766.1	779.1	791.7	801.2	803.9	800.3	783.7	755.4	719.5
30°	684.2	691.2	699.0	712.0	737.3	751.7	767.6	779.6	772.9	750.3	716.9
32.5°	611.9	613.6	625.1	639.9	663.1	690.9	716.1	740.5	748.6	736.8	708.9
35°	497.6	500.5	512.9	527.5	555.9	590.0	627.8	661.7	689.6	700.8	686.5
37.5°	406.0	414.2	423.0	438.8	463.7	494.4	533.7	577.6	619.1	647.0	651.8
40°	362.7	367.8	374.1	386.2	407.3	437.5	471.3	521.4	565.7	605.6	618.6
42.5°	328.5	331.5	335.4	346.2	362.3	392.4	423.3	467.4	511.7	559.5	581.3
45°	279.1	282.2	288.8	295.1	307.3	328.0	356.8	393.0	437.7	483.7	524.1
47.5°	243.6	245.5	249.3	256.1	266.6	280.3	303.6	333.9	375.2	420.0	463.0
50°	223.3	225.0	228.0	234.1	242.1	254.3	273.5	301.8	334.2	379.2	421.4
52.5°	207.3	208.0	210.3	214.4	220.8	231.0	246.8	270.2	300.3	340.4	382.5
55°	182.6	183.4	185.5	188.5	194.0	200.5	212.5	230.1	256.3	291.2	327.7
57.5°	162.2	162.8	164.5	165.7	170.2	175.5	184.8	197.3	217.1	246.8	279.3
60°	149.1	148.8	150.8	151.8	154.9	159.4	166.5	178.5	195.8	219.6	249.6
62.5°	136.5	135.9	137.6	139.0	140.7	144.5	150.3	159.7	173.8	195.4	221.3
65°	117.4	116.6	117.6	119.2	120.8	122.9	127.2	135.5	146.7	162.2	181.9
67.5°	98.2	99.1	99.3	100.0	101.0	103.8	106.7	112.6	120.5	132.9	149.6
70°	86.8	87.0	87.8	87.8	88.4	90.9	93.3	96.8	104.5	116.0	129.6
72.5°	75.4	76.3	75.9	76.5	77.1	78.7	80.4	83.8	90.3	98.8	110.4
75°	58.7	59.3	59.3	59.5	60.1	60.7	62.2	64.6	69.3	75.6	83.5
77.5°	42.8	42.9	43.1	43.9	43.9	44.9	45.9	47.9	50.2	54.5	59.4
80°	33.0	33.4	33.2	33.7	33.7	34.4	34.9	37.3	38.3	41.2	45.0
82.5°	24.2	24.6	24.5	25.1	25.5	25.7	26.2	27.2	28.2	30.7	32.3
85°	12.2	12.7	12.2	12.7	13.3	13.4	14.0	14.3	15.1	15.7	17.1
87.5°	5.7	6.1	6.2	6.3	6.5	6.7	6.7	6.5	7.1	7.3	7.7
90°	10.3	10.3	10.8	10.3	9.8	9.8	9.3	8.9	8.4	8.9	7.8
92.5°	37.8	37.8	39.5	42.1	48.0	57.8	72.6	96.4	129.8	155.8	136.4
95°	119.9	126.2	135.1	150.3	174.4	222.0	287.8	363.9	411.6	400.3	302.0
97.5°	320.3	330.5	345.3	374.9	410.1	461.4	509.5	537.7	517.1	421.6	282.8
100°	450.4	454.3	469.1	499.0	541.7	578.1	602.2	592.4	520.6	394.9	256.4
102.5°	563.5	566.7	582.2	603.9	630.2	645.3	638.3	589.6	491.1	361.5	238.7
105°	691.0	694.0	700.9	704.8	703.9	683.7	635.1	550.1	437.6	322.2	223.5
107.5°	738.4	737.1	732.2	721.0	696.7	653.0	584.4	494.0	394.4	300.2	220.8
110°	739.2	734.8	725.9	705.3	670.5	616.4	545.2	460.2	372.8	292.7	221.5



TEST NUMBER: P332501-935

CATALOG NUMBER: SA4XXDIP-C350D590U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	716.0	708.9	696.5	671.5	631.9	577.9	510.6	435.5	360.6	289.2	223.9
115°	663.6	659.6	643.9	614.4	575.7	528.5	471.1	410.6	349.2	287.3	228.4
117.5°	610.4	607.3	591.4	566.7	533.6	493.6	448.4	398.4	344.1	286.8	233.2
120°	580.6	575.1	562.4	540.8	512.7	477.9	438.6	393.0	341.4	286.8	236.8
122.5°	557.0	551.6	540.8	522.3	498.6	468.0	432.3	388.2	338.2	286.5	240.3
125°	529.4	526.5	517.2	502.9	483.3	456.2	422.4	380.1	333.0	285.9	245.6
127.5°	513.3	510.4	502.6	489.9	470.1	444.5	410.7	370.3	326.1	284.7	249.8
130°	503.9	501.0	493.1	480.9	460.7	434.6	401.3	362.5	321.7	284.4	253.0
132.5°	493.4	490.3	482.9	469.1	449.3	423.3	390.6	354.2	317.8	284.0	255.7
135°	473.5	470.5	462.7	448.9	429.3	404.7	374.8	342.9	311.9	283.4	259.8
137.5°	448.9	445.4	438.9	425.3	407.0	384.8	359.6	332.5	306.8	283.3	262.3
140°	431.3	427.3	420.4	409.7	392.4	371.8	349.7	326.6	304.0	282.9	264.2
142.5°	412.3	409.7	403.6	393.5	378.3	360.4	341.5	321.2	301.7	282.9	265.8
145°	386.5	384.1	379.2	370.8	358.5	344.8	330.0	313.3	297.6	281.9	266.7
147.5°	363.7	362.7	359.0	351.9	342.9	332.0	320.2	306.9	294.0	280.2	267.2
150°	350.7	350.2	347.2	340.9	333.0	324.2	314.4	303.1	291.3	279.0	267.2
152.5°	338.9	338.4	336.7	331.4	324.8	317.5	308.4	298.7	288.1	277.0	266.4
155°	323.6	323.6	322.2	318.3	313.3	307.5	300.1	292.2	283.4	274.1	265.2
157.5°	310.3	310.3	309.4	306.5	302.7	298.0	291.9	285.2	278.6	271.0	264.0
160°	302.0	302.0	301.6	298.6	295.7	291.7	286.4	280.9	275.1	268.6	262.8
162.5°	294.2	294.6	294.1	291.2	289.0	285.4	281.2	276.6	271.9	266.3	261.6
165°	282.4	282.9	283.4	281.5	279.5	277.0	273.5	270.6	266.7	262.8	259.3
167.5°	273.1	273.5	273.5	272.3	271.3	269.8	267.1	264.8	262.0	259.2	257.0
170°	267.2	267.2	267.7	267.2	266.2	264.8	262.8	261.3	258.8	256.8	255.4
172.5°	261.3	262.1	262.6	262.1	261.5	260.5	259.2	258.1	256.1	254.5	253.8
175°	254.4	255.4	256.4	255.4	255.4	255.4	254.4	253.9	253.0	251.9	251.9
177.5°	250.4	251.2	251.9	251.6	251.9	251.6	251.6	251.2	250.8	250.4	250.4
180°	250.0	250.0	250.0	250.0	250.0	250.0	250.0	250.0	250.0	250.0	250.0



TEST NUMBER: P332501-935

CATALOG NUMBER: SA4XXDIP-C350D590U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9
2.5°	507.7	505.4	503.8	502.5	498.9	496.8	495.2	492.9	490.3	487.5	484.1
5°	536.5	529.6	524.5	516.8	509.5	503.3	497.0	491.3	484.4	476.8	471.3
7.5°	566.8	556.5	543.3	531.8	518.9	507.7	497.7	487.5	476.8	466.4	456.9
10°	586.1	572.8	558.1	540.8	524.5	510.1	496.6	483.5	470.9	458.3	447.5
12.5°	606.7	590.2	568.5	548.3	530.0	510.7	494.5	478.5	463.2	450.0	437.4
15°	634.6	610.7	585.7	558.5	534.5	511.9	489.7	469.5	452.4	434.8	422.6
17.5°	651.6	622.1	593.5	565.2	536.1	507.5	483.5	460.3	438.9	421.5	406.0
20°	662.9	633.5	597.9	569.6	534.9	505.6	477.9	451.9	429.6	411.0	395.1
22.5°	672.6	638.8	603.0	565.8	531.3	500.2	469.8	443.8	420.9	401.4	386.2
25°	678.0	639.0	600.3	563.2	524.1	487.2	459.7	429.1	404.7	384.1	367.8
27.5°	678.6	636.9	593.1	551.9	511.5	477.2	442.5	415.1	389.8	368.0	352.3
30°	676.7	633.4	586.3	541.7	501.1	463.8	433.6	403.9	378.0	356.4	340.1
32.5°	671.0	625.9	577.5	530.2	488.2	451.7	420.6	392.3	367.0	345.8	328.6
35°	654.5	609.8	558.4	509.2	466.2	429.4	401.2	372.5	347.2	327.1	310.6
37.5°	628.7	588.4	536.0	485.2	442.9	405.9	378.0	352.1	329.2	308.8	291.9
40°	606.2	570.8	518.1	468.6	423.0	387.8	361.7	337.9	315.2	295.8	279.7
42.5°	580.3	549.4	500.9	448.5	404.4	369.0	343.6	322.2	300.9	283.0	266.9
45°	534.1	513.7	468.0	419.6	373.7	340.3	316.1	297.3	279.4	261.8	248.4
47.5°	481.0	470.8	432.4	386.3	342.9	309.9	288.9	271.6	255.8	241.0	229.1
50°	445.2	440.3	407.2	362.7	321.2	290.2	269.0	254.1	240.6	227.6	216.4
52.5°	410.0	409.8	379.9	339.2	300.7	271.0	249.9	236.0	224.4	213.8	203.7
55°	356.2	361.9	338.5	302.2	267.8	240.8	221.9	209.5	201.3	192.6	185.0
57.5°	306.8	316.2	296.9	264.9	236.2	211.5	194.9	185.6	176.9	171.6	166.1
60°	274.5	283.4	268.4	241.5	214.4	193.2	177.5	169.1	161.6	157.9	154.0
62.5°	245.8	253.7	242.6	217.7	194.2	173.7	160.5	152.5	147.4	143.4	140.9
65°	204.8	211.5	201.9	183.8	163.6	147.3	136.6	130.2	125.4	123.7	120.8
67.5°	165.6	171.7	166.5	151.1	134.9	122.5	114.1	108.1	105.1	103.8	101.7
70°	142.2	148.4	142.8	129.4	116.9	106.6	98.6	95.1	92.1	91.5	88.7
72.5°	122.5	126.7	121.1	110.6	100.0	91.3	85.1	81.5	79.9	78.8	77.2
75°	91.9	95.6	91.9	83.8	76.2	70.1	64.8	63.4	61.6	61.0	59.9
77.5°	65.0	68.2	65.4	60.4	54.7	49.9	47.1	45.3	44.9	43.8	44.3
80°	49.7	51.7	49.1	45.6	41.2	37.9	35.9	34.9	33.7	33.2	34.0
82.5°	35.7	36.6	35.2	32.9	29.6	27.5	26.1	24.9	24.6	24.7	24.7
85°	18.5	18.3	18.2	16.1	15.1	13.7	12.8	12.7	12.4	12.8	13.3
87.5°	7.6	7.7	7.0	6.4	5.8	5.2	4.7	4.3	4.7	5.2	5.4
90°	6.9	6.9	4.0	4.0	3.4	2.9	1.5	0.5	1.5	2.9	3.4
92.5°	99.2	61.1	36.2	25.9	18.8	12.7	8.2	5.6	8.2	12.7	18.8
95°	184.7	104.1	61.4	40.7	29.0	22.6	17.7	16.2	17.7	22.6	29.0
97.5°	166.0	99.5	66.6	49.3	39.2	33.3	29.1	29.1	29.1	33.3	39.2
100°	156.2	100.7	71.7	56.0	46.7	40.7	37.4	37.4	37.4	40.7	46.7
102.5°	153.4	104.6	78.4	63.5	54.5	49.0	46.0	45.2	46.0	49.0	54.5
105°	154.7	113.9	90.4	76.1	67.3	61.4	59.0	57.4	59.0	61.4	67.3
107.5°	162.0	124.8	103.2	89.2	80.8	74.5	72.0	71.0	72.0	74.5	80.8
110°	167.5	133.1	111.5	98.2	89.4	83.5	81.0	80.1	81.0	83.5	89.4



TEST NUMBER: P332501-935

CATALOG NUMBER: SA4XXDIP-C350D590U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	173.4	140.9	120.1	106.9	98.1	92.6	89.7	88.7	89.7	92.6	98.1
115°	182.7	153.3	133.6	120.4	111.0	106.1	102.6	101.2	102.6	106.1	111.0
117.5°	192.3	165.1	146.5	132.7	124.0	118.6	115.5	114.2	115.5	118.6	124.0
120°	198.9	173.4	154.7	140.9	132.6	127.2	123.8	122.8	123.8	127.2	132.6
122.5°	205.2	181.2	162.6	149.2	140.1	135.1	131.6	130.6	131.6	135.1	140.1
125°	214.6	192.0	174.4	160.6	151.3	145.9	142.9	140.9	142.9	145.9	151.3
127.5°	222.8	202.1	184.9	171.1	161.4	155.2	151.7	150.1	151.7	155.2	161.4
130°	227.9	208.7	192.0	177.8	168.5	161.1	157.1	155.2	157.1	161.1	168.5
132.5°	233.0	214.2	197.5	184.1	174.0	167.0	161.9	160.3	161.9	167.0	174.0
135°	239.7	222.0	205.8	193.0	182.7	174.4	169.4	167.5	169.4	174.4	182.7
137.5°	244.4	227.9	212.8	200.6	189.9	181.9	176.5	174.7	176.5	181.9	189.9
140°	247.5	231.9	217.1	205.3	195.0	186.7	181.2	179.8	181.2	186.7	195.0
142.5°	249.9	235.4	221.0	209.7	199.7	191.7	186.8	185.3	186.8	191.7	199.7
145°	252.4	239.2	226.4	215.6	206.3	199.4	194.5	193.0	194.5	199.4	206.3
147.5°	254.7	243.1	231.2	221.4	213.6	206.6	202.2	201.7	202.2	206.6	213.6
150°	255.9	245.1	234.3	225.0	217.6	211.7	207.8	207.2	207.8	211.7	217.6
152.5°	256.7	246.7	237.0	228.5	221.9	216.4	212.5	212.4	212.5	216.4	221.9
155°	257.4	249.0	240.6	233.3	227.9	223.0	220.1	219.6	220.1	223.0	227.9
157.5°	257.4	250.7	243.6	237.8	233.1	229.3	226.5	226.5	226.5	229.3	233.1
160°	257.4	251.5	245.6	240.1	236.3	232.8	230.8	230.8	230.8	232.8	236.3
162.5°	257.4	252.3	246.8	242.5	239.0	235.9	234.4	234.8	234.4	235.9	239.0
165°	256.4	252.4	248.1	245.1	242.6	240.1	239.2	239.2	239.2	240.1	242.6
167.5°	255.2	252.4	249.1	246.8	245.5	243.6	243.1	243.6	243.1	243.6	245.5
170°	254.4	251.9	249.5	248.1	247.0	245.6	245.1	245.6	245.1	245.6	247.0
172.5°	253.7	251.6	249.9	248.8	248.2	247.1	247.0	247.5	247.0	247.1	248.2
175°	252.4	251.0	250.0	250.0	249.5	249.0	249.0	249.5	249.0	249.0	249.5
177.5°	251.2	250.4	250.0	250.0	250.0	249.6	250.0	250.4	250.0	249.6	250.0
180°	250.0	250.0	250.0	250.0	250.0	250.0	250.0	250.0	250.0	250.0	250.0



TEST NUMBER: P332501-935

CATALOG NUMBER: SA4XXDIP-C350D590U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9
2.5°	482.4	481.0	478.9	476.0	473.5	470.9	470.2	469.2	471.2	469.6	469.1
5°	466.7	462.4	456.8	450.6	446.9	441.6	440.6	438.5	436.4	436.3	434.2
7.5°	449.9	443.6	436.4	430.0	424.0	418.2	414.4	413.6	410.6	408.8	406.8
10°	439.1	431.4	423.0	416.9	410.0	403.9	399.6	397.2	395.1	392.9	390.8
12.5°	426.5	418.2	411.3	404.7	396.5	391.8	384.8	380.6	380.1	380.1	374.9
15°	411.6	403.5	392.9	383.5	379.0	370.1	366.2	361.3	358.3	355.2	352.8
17.5°	394.7	384.5	376.3	365.5	357.0	349.8	344.7	341.8	337.2	332.9	329.8
20°	384.1	373.3	364.5	353.1	343.8	335.0	330.7	326.7	323.2	319.5	316.1
22.5°	373.3	362.1	351.4	340.3	331.6	322.3	318.1	312.6	309.4	307.3	303.8
25°	356.4	344.1	331.9	321.3	312.4	304.2	298.8	294.5	290.8	289.1	286.9
27.5°	337.9	325.8	314.0	302.0	291.8	285.9	281.5	278.3	276.1	274.0	272.9
30°	326.2	313.6	301.0	289.7	280.4	274.5	270.4	268.2	266.6	265.5	264.5
32.5°	314.4	301.9	288.6	278.4	269.9	264.7	261.6	259.3	258.6	258.2	257.8
35°	295.2	282.7	270.4	261.2	253.3	251.2	248.6	247.4	246.9	248.4	249.0
37.5°	276.8	265.1	253.8	245.0	239.7	236.8	235.8	235.9	237.4	238.6	240.0
40°	264.9	253.5	242.9	235.1	230.2	228.4	228.0	229.0	230.7	232.1	233.8
42.5°	253.3	242.1	232.5	225.2	221.8	220.1	220.3	221.4	223.7	225.4	227.8
45°	235.4	226.0	216.6	210.7	207.8	208.3	208.3	210.1	212.3	215.0	217.7
47.5°	218.4	209.0	201.3	196.3	194.8	194.5	195.6	198.0	201.2	204.5	208.2
50°	207.1	198.0	191.3	186.8	185.2	185.8	187.4	189.7	193.6	197.7	201.6
52.5°	195.4	187.3	181.1	176.9	175.7	176.8	178.5	182.0	185.5	189.9	194.5
55°	177.5	170.6	165.7	162.6	162.2	162.8	164.6	168.5	173.4	178.9	183.4
57.5°	159.6	153.8	149.3	147.2	147.4	148.0	151.0	155.6	160.8	166.7	172.5
60°	147.5	142.2	138.5	136.9	137.2	138.4	142.1	146.3	152.8	158.5	164.6
62.5°	136.1	131.5	127.9	126.5	126.2	128.9	132.4	136.8	143.4	149.7	156.4
65°	117.8	114.1	111.2	110.5	111.1	113.1	117.6	123.5	129.0	135.7	142.7
67.5°	99.9	96.9	94.9	95.2	96.0	99.0	102.7	107.8	114.1	121.1	127.9
70°	88.4	85.6	83.9	84.1	85.4	89.0	92.3	97.4	104.1	111.2	116.9
72.5°	76.7	74.8	73.4	74.2	75.4	77.9	82.1	87.1	93.1	99.7	105.7
75°	58.9	58.9	58.1	58.7	60.5	62.9	66.0	71.3	77.2	82.6	87.4
77.5°	43.7	43.2	43.7	44.5	45.5	48.5	52.0	55.8	60.2	65.5	69.6
80°	33.4	33.7	34.6	35.9	36.2	38.5	42.2	45.6	49.1	53.6	57.4
82.5°	25.1	25.3	25.8	27.4	27.8	30.2	32.5	36.0	39.2	42.2	45.4
85°	13.7	13.7	14.6	15.3	16.3	17.9	19.4	21.4	24.3	26.3	29.4
87.5°	6.0	6.0	7.2	7.6	8.3	9.3	9.5	11.4	12.1	13.1	14.6
90°	4.0	4.0	6.9	6.9	7.8	8.9	8.4	8.9	9.3	9.8	9.8
92.5°	25.9	36.2	61.1	99.2	136.4	155.8	129.8	96.4	72.6	57.8	48.0
95°	40.7	61.4	104.1	184.7	302.0	400.3	411.6	363.9	287.8	222.0	174.4
97.5°	49.3	66.6	99.5	166.0	282.8	421.6	517.1	537.7	509.5	461.4	410.1
100°	56.0	71.7	100.7	156.2	256.4	394.9	520.6	592.4	602.2	578.1	541.7
102.5°	63.5	78.4	104.6	153.4	238.7	361.5	491.1	589.6	638.3	645.3	630.2
105°	76.1	90.4	113.9	154.7	223.5	322.2	437.6	550.1	635.1	683.7	703.9
107.5°	89.2	103.2	124.8	162.0	220.8	300.2	394.4	494.0	584.4	653.0	696.7
110°	98.2	111.5	133.1	167.5	221.5	292.7	372.8	460.2	545.2	616.4	670.5



TEST NUMBER: P332501-935

CATALOG NUMBER: SA4XXDIP-C350D590U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	106.9	120.1	140.9	173.4	223.9	289.2	360.6	435.5	510.6	577.9	631.9
115°	120.4	133.6	153.3	182.7	228.4	287.3	349.2	410.6	471.1	528.5	575.7
117.5°	132.7	146.5	165.1	192.3	233.2	286.8	344.1	398.4	448.4	493.6	533.6
120°	140.9	154.7	173.4	198.9	236.8	286.8	341.4	393.0	438.6	477.9	512.7
122.5°	149.2	162.6	181.2	205.2	240.3	286.5	338.2	388.2	432.3	468.0	498.6
125°	160.6	174.4	192.0	214.6	245.6	285.9	333.0	380.1	422.4	456.2	483.3
127.5°	171.1	184.9	202.1	222.8	249.8	284.7	326.1	370.3	410.7	444.5	470.1
130°	177.8	192.0	208.7	227.9	253.0	284.4	321.7	362.5	401.3	434.6	460.7
132.5°	184.1	197.5	214.2	233.0	255.7	284.0	317.8	354.2	390.6	423.3	449.3
135°	193.0	205.8	222.0	239.7	259.8	283.4	311.9	342.9	374.8	404.7	429.3
137.5°	200.6	212.8	227.9	244.4	262.3	283.3	306.8	332.5	359.6	384.8	407.0
140°	205.3	217.1	231.9	247.5	264.2	282.9	304.0	326.6	349.7	371.8	392.4
142.5°	209.7	221.0	235.4	249.9	265.8	282.9	301.7	321.2	341.5	360.4	378.3
145°	215.6	226.4	239.2	252.4	266.7	281.9	297.6	313.3	330.0	344.8	358.5
147.5°	221.4	231.2	243.1	254.7	267.2	280.2	294.0	306.9	320.2	332.0	342.9
150°	225.0	234.3	245.1	255.9	267.2	279.0	291.3	303.1	314.4	324.2	333.0
152.5°	228.5	237.0	246.7	256.7	266.4	277.0	288.1	298.7	308.4	317.5	324.8
155°	233.3	240.6	249.0	257.4	265.2	274.1	283.4	292.2	300.1	307.5	313.3
157.5°	237.8	243.6	250.7	257.4	264.0	271.0	278.6	285.2	291.9	298.0	302.7
160°	240.1	245.6	251.5	257.4	262.8	268.6	275.1	280.9	286.4	291.7	295.7
162.5°	242.5	246.8	252.3	257.4	261.6	266.3	271.9	276.6	281.2	285.4	289.0
165°	245.1	248.1	252.4	256.4	259.3	262.8	266.7	270.6	273.5	277.0	279.5
167.5°	246.8	249.1	252.4	255.2	257.0	259.2	262.0	264.8	267.1	269.8	271.3
170°	248.1	249.5	251.9	254.4	255.4	256.8	258.8	261.3	262.8	264.8	266.2
172.5°	248.8	249.9	251.6	253.7	253.8	254.5	256.1	258.1	259.2	260.5	261.5
175°	250.0	250.0	251.0	252.4	251.9	251.9	253.0	253.9	254.4	255.4	255.4
177.5°	250.0	250.0	250.4	251.2	250.4	250.4	250.8	251.2	251.6	251.6	251.9
180°	250.0	250.0	250.0	250.0	250.0	250.0	250.0	250.0	250.0	250.0	250.0



TEST NUMBER: P332501-935

CATALOG NUMBER: SA4XXDIP-C350D590U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9
2.5°	468.7	468.5	467.3	467.1	467.3	468.5	468.7	469.1	469.6	471.2	469.2
5°	433.0	432.0	431.4	433.6	431.4	432.0	433.0	434.2	436.3	436.4	438.5
7.5°	406.0	405.3	403.5	402.9	403.5	405.3	406.0	406.8	408.8	410.6	413.6
10°	388.8	388.0	386.3	385.9	386.3	388.0	388.8	390.8	392.9	395.1	397.2
12.5°	372.1	370.6	370.2	370.7	370.2	370.6	372.1	374.9	380.1	380.1	380.6
15°	350.1	349.2	347.0	347.7	347.0	349.2	350.1	352.8	355.2	358.3	361.3
17.5°	328.3	327.4	324.6	327.0	324.6	327.4	328.3	329.8	332.9	337.2	341.8
20°	314.6	313.0	311.6	311.3	311.6	313.0	314.6	316.1	319.5	323.2	326.7
22.5°	301.6	300.1	300.0	298.7	300.0	300.1	301.6	303.8	307.3	309.4	312.6
25°	285.2	283.9	283.4	282.4	283.4	283.9	285.2	286.9	289.1	290.8	294.5
27.5°	272.8	272.1	271.3	271.6	271.3	272.1	272.8	272.9	274.0	276.1	278.3
30°	265.1	264.9	264.5	264.5	264.5	264.9	265.1	264.5	265.5	266.6	268.2
32.5°	258.7	258.7	259.0	259.0	259.0	258.7	258.7	257.8	258.2	258.6	259.3
35°	249.9	250.5	250.8	250.2	250.8	250.5	249.9	249.0	248.4	246.9	247.4
37.5°	241.8	242.4	243.0	243.7	243.0	242.4	241.8	240.0	238.6	237.4	235.9
40°	235.6	236.9	237.4	238.4	237.4	236.9	235.6	233.8	232.1	230.7	229.0
42.5°	229.7	231.3	232.3	232.6	232.3	231.3	229.7	227.8	225.4	223.7	221.4
45°	220.7	222.3	223.8	223.8	223.8	222.3	220.7	217.7	215.0	212.3	210.1
47.5°	211.4	213.7	215.2	215.5	215.2	213.7	211.4	208.2	204.5	201.2	198.0
50°	205.0	207.8	209.3	210.3	209.3	207.8	205.0	201.6	197.7	193.6	189.7
52.5°	198.8	201.6	203.5	204.1	203.5	201.6	198.8	194.5	189.9	185.5	182.0
55°	188.0	192.2	194.4	195.2	194.4	192.2	188.0	183.4	178.9	173.4	168.5
57.5°	178.0	181.8	184.3	184.9	184.3	181.8	178.0	172.5	166.7	160.8	155.6
60°	170.1	174.3	177.5	178.1	177.5	174.3	170.1	164.6	158.5	152.8	146.3
62.5°	162.1	166.4	169.4	170.9	169.4	166.4	162.1	156.4	149.7	143.4	136.8
65°	148.4	152.7	155.5	156.1	155.5	152.7	148.4	142.7	135.7	129.0	123.5
67.5°	133.3	137.6	139.4	140.6	139.4	137.6	133.3	127.9	121.1	114.1	107.8
70°	122.7	126.1	128.2	129.2	128.2	126.1	122.7	116.9	111.2	104.1	97.4
72.5°	110.6	114.3	116.6	116.8	116.6	114.3	110.6	105.7	99.7	93.1	87.1
75°	92.1	95.4	96.6	96.6	96.6	95.4	92.1	87.4	82.6	77.2	71.3
77.5°	72.9	74.6	76.1	76.5	76.1	74.6	72.9	69.6	65.5	60.2	55.8
80°	60.5	61.6	62.8	62.8	62.8	61.6	60.5	57.4	53.6	49.1	45.6
82.5°	47.8	48.6	49.9	49.7	49.9	48.6	47.8	45.4	42.2	39.2	36.0
85°	28.9	30.7	30.6	30.1	30.6	30.7	28.9	29.4	26.3	24.3	21.4
87.5°	15.1	15.3	15.8	16.1	15.8	15.3	15.1	14.6	13.1	12.1	11.4
90°	10.3	10.8	10.3	10.3	10.3	10.8	10.3	9.8	9.8	9.3	8.9
92.5°	42.1	39.5	37.8	37.8	37.8	39.5	42.1	48.0	57.8	72.6	96.4
95°	150.3	135.1	126.2	119.9	126.2	135.1	150.3	174.4	222.0	287.8	363.9
97.5°	374.9	345.3	330.5	320.3	330.5	345.3	374.9	410.1	461.4	509.5	537.7
100°	499.0	469.1	454.3	450.4	454.3	469.1	499.0	541.7	578.1	602.2	592.4
102.5°	603.9	582.2	566.7	563.5	566.7	582.2	603.9	630.2	645.3	638.3	589.6
105°	704.8	700.9	694.0	691.0	694.0	700.9	704.8	703.9	683.7	635.1	550.1
107.5°	721.0	732.2	737.1	738.4	737.1	732.2	721.0	696.7	653.0	584.4	494.0
110°	705.3	725.9	734.8	739.2	734.8	725.9	705.3	670.5	616.4	545.2	460.2



TEST NUMBER: P332501-935

CATALOG NUMBER: SA4XXDIP-C350D590U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	671.5	696.5	708.9	716.0	708.9	696.5	671.5	631.9	577.9	510.6	435.5
115°	614.4	643.9	659.6	663.6	659.6	643.9	614.4	575.7	528.5	471.1	410.6
117.5°	566.7	591.4	607.3	610.4	607.3	591.4	566.7	533.6	493.6	448.4	398.4
120°	540.8	562.4	575.1	580.6	575.1	562.4	540.8	512.7	477.9	438.6	393.0
122.5°	522.3	540.8	551.6	557.0	551.6	540.8	522.3	498.6	468.0	432.3	388.2
125°	502.9	517.2	526.5	529.4	526.5	517.2	502.9	483.3	456.2	422.4	380.1
127.5°	489.9	502.6	510.4	513.3	510.4	502.6	489.9	470.1	444.5	410.7	370.3
130°	480.9	493.1	501.0	503.9	501.0	493.1	480.9	460.7	434.6	401.3	362.5
132.5°	469.1	482.9	490.3	493.4	490.3	482.9	469.1	449.3	423.3	390.6	354.2
135°	448.9	462.7	470.5	473.5	470.5	462.7	448.9	429.3	404.7	374.8	342.9
137.5°	425.3	438.9	445.4	448.9	445.4	438.9	425.3	407.0	384.8	359.6	332.5
140°	409.7	420.4	427.3	431.3	427.3	420.4	409.7	392.4	371.8	349.7	326.6
142.5°	393.5	403.6	409.7	412.3	409.7	403.6	393.5	378.3	360.4	341.5	321.2
145°	370.8	379.2	384.1	386.5	384.1	379.2	370.8	358.5	344.8	330.0	313.3
147.5°	351.9	359.0	362.7	363.7	362.7	359.0	351.9	342.9	332.0	320.2	306.9
150°	340.9	347.2	350.2	350.7	350.2	347.2	340.9	333.0	324.2	314.4	303.1
152.5°	331.4	336.7	338.4	338.9	338.4	336.7	331.4	324.8	317.5	308.4	298.7
155°	318.3	322.2	323.6	323.6	323.6	322.2	318.3	313.3	307.5	300.1	292.2
157.5°	306.5	309.4	310.3	310.3	310.3	309.4	306.5	302.7	298.0	291.9	285.2
160°	298.6	301.6	302.0	302.0	302.0	301.6	298.6	295.7	291.7	286.4	280.9
162.5°	291.2	294.1	294.6	294.2	294.6	294.1	291.2	289.0	285.4	281.2	276.6
165°	281.5	283.4	282.9	282.4	282.9	283.4	281.5	279.5	277.0	273.5	270.6
167.5°	272.3	273.5	273.5	273.1	273.5	273.5	272.3	271.3	269.8	267.1	264.8
170°	267.2	267.7	267.2	267.2	267.2	267.7	267.2	266.2	264.8	262.8	261.3
172.5°	262.1	262.6	262.1	261.3	262.1	262.6	262.1	261.5	260.5	259.2	258.1
175°	255.4	256.4	255.4	254.4	255.4	256.4	255.4	255.4	255.4	254.4	253.9
177.5°	251.6	251.9	251.2	250.4	251.2	251.9	251.6	251.9	251.6	251.6	251.2
180°	250.0	250.0	250.0	250.0	250.0	250.0	250.0	250.0	250.0	250.0	250.0



TEST NUMBER: P332501-935

CATALOG NUMBER: SA4XXDIP-C350D590U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9
2.5°	470.2	470.9	473.5	476.0	478.9	481.0	482.4	484.1	487.5	490.3	492.9
5°	440.6	441.6	446.9	450.6	456.8	462.4	466.7	471.3	476.8	484.4	491.3
7.5°	414.4	418.2	424.0	430.0	436.4	443.6	449.9	456.9	466.4	476.8	487.5
10°	399.6	403.9	410.0	416.9	423.0	431.4	439.1	447.5	458.3	470.9	483.5
12.5°	384.8	391.8	396.5	404.7	411.3	418.2	426.5	437.4	450.0	463.2	478.5
15°	366.2	370.1	379.0	383.5	392.9	403.5	411.6	422.6	434.8	452.4	469.5
17.5°	344.7	349.8	357.0	365.5	376.3	384.5	394.7	406.0	421.5	438.9	460.3
20°	330.7	335.0	343.8	353.1	364.5	373.3	384.1	395.1	411.0	429.6	451.9
22.5°	318.1	322.3	331.6	340.3	351.4	362.1	373.3	386.2	401.4	420.9	443.8
25°	298.8	304.2	312.4	321.3	331.9	344.1	356.4	367.8	384.1	404.7	429.1
27.5°	281.5	285.9	291.8	302.0	314.0	325.8	337.9	352.3	368.0	389.8	415.1
30°	270.4	274.5	280.4	289.7	301.0	313.6	326.2	340.1	356.4	378.0	403.9
32.5°	261.6	264.7	269.9	278.4	288.6	301.9	314.4	328.6	345.8	367.0	392.3
35°	248.6	251.2	253.3	261.2	270.4	282.7	295.2	310.6	327.1	347.2	372.5
37.5°	235.8	236.8	239.7	245.0	253.8	265.1	276.8	291.9	308.8	329.2	352.1
40°	228.0	228.4	230.2	235.1	242.9	253.5	264.9	279.7	295.8	315.2	337.9
42.5°	220.3	220.1	221.8	225.2	232.5	242.1	253.3	266.9	283.0	300.9	322.2
45°	208.3	208.3	207.8	210.7	216.6	226.0	235.4	248.4	261.8	279.4	297.3
47.5°	195.6	194.5	194.8	196.3	201.3	209.0	218.4	229.1	241.0	255.8	271.6
50°	187.4	185.8	185.2	186.8	191.3	198.0	207.1	216.4	227.6	240.6	254.1
52.5°	178.5	176.8	175.7	176.9	181.1	187.3	195.4	203.7	213.8	224.4	236.0
55°	164.6	162.8	162.2	162.6	165.7	170.6	177.5	185.0	192.6	201.3	209.5
57.5°	151.0	148.0	147.4	147.2	149.3	153.8	159.6	166.1	171.6	176.9	185.6
60°	142.1	138.4	137.2	136.9	138.5	142.2	147.5	154.0	157.9	161.6	169.1
62.5°	132.4	128.9	126.2	126.5	127.9	131.5	136.1	140.9	143.4	147.4	152.5
65°	117.6	113.1	111.1	110.5	111.2	114.1	117.8	120.8	123.7	125.4	130.2
67.5°	102.7	99.0	96.0	95.2	94.9	96.9	99.9	101.7	103.8	105.1	108.1
70°	92.3	89.0	85.4	84.1	83.9	85.6	88.4	88.7	91.5	92.1	95.1
72.5°	82.1	77.9	75.4	74.2	73.4	74.8	76.7	77.2	78.8	79.9	81.5
75°	66.0	62.9	60.5	58.7	58.1	58.9	58.9	59.9	61.0	61.6	63.4
77.5°	52.0	48.5	45.5	44.5	43.7	43.2	43.7	44.3	43.8	44.9	45.3
80°	42.2	38.5	36.2	35.9	34.6	33.7	33.4	34.0	33.2	33.7	34.9
82.5°	32.5	30.2	27.8	27.4	25.8	25.3	25.1	24.7	24.7	24.6	24.9
85°	19.4	17.9	16.3	15.3	14.6	13.7	13.7	13.3	12.8	12.4	12.7
87.5°	9.5	9.3	8.3	7.6	7.2	6.0	6.0	5.4	5.2	4.7	4.3
90°	8.4	8.9	7.8	6.9	6.9	4.0	4.0	3.4	2.9	1.5	0.5
92.5°	129.8	155.8	136.4	99.2	61.1	36.2	25.9	18.8	12.7	8.2	5.6
95°	411.6	400.3	302.0	184.7	104.1	61.4	40.7	29.0	22.6	17.7	16.2
97.5°	517.1	421.6	282.8	166.0	99.5	66.6	49.3	39.2	33.3	29.1	29.1
100°	520.6	394.9	256.4	156.2	100.7	71.7	56.0	46.7	40.7	37.4	37.4
102.5°	491.1	361.5	238.7	153.4	104.6	78.4	63.5	54.5	49.0	46.0	45.2
105°	437.6	322.2	223.5	154.7	113.9	90.4	76.1	67.3	61.4	59.0	57.4
107.5°	394.4	300.2	220.8	162.0	124.8	103.2	89.2	80.8	74.5	72.0	71.0
110°	372.8	292.7	221.5	167.5	133.1	111.5	98.2	89.4	83.5	81.0	80.1



TEST NUMBER: P332501-935

CATALOG NUMBER: SA4XXDIP-C350D590U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	360.6	289.2	223.9	173.4	140.9	120.1	106.9	98.1	92.6	89.7	88.7
115°	349.2	287.3	228.4	182.7	153.3	133.6	120.4	111.0	106.1	102.6	101.2
117.5°	344.1	286.8	233.2	192.3	165.1	146.5	132.7	124.0	118.6	115.5	114.2
120°	341.4	286.8	236.8	198.9	173.4	154.7	140.9	132.6	127.2	123.8	122.8
122.5°	338.2	286.5	240.3	205.2	181.2	162.6	149.2	140.1	135.1	131.6	130.6
125°	333.0	285.9	245.6	214.6	192.0	174.4	160.6	151.3	145.9	142.9	140.9
127.5°	326.1	284.7	249.8	222.8	202.1	184.9	171.1	161.4	155.2	151.7	150.1
130°	321.7	284.4	253.0	227.9	208.7	192.0	177.8	168.5	161.1	157.1	155.2
132.5°	317.8	284.0	255.7	233.0	214.2	197.5	184.1	174.0	167.0	161.9	160.3
135°	311.9	283.4	259.8	239.7	222.0	205.8	193.0	182.7	174.4	169.4	167.5
137.5°	306.8	283.3	262.3	244.4	227.9	212.8	200.6	189.9	181.9	176.5	174.7
140°	304.0	282.9	264.2	247.5	231.9	217.1	205.3	195.0	186.7	181.2	179.8
142.5°	301.7	282.9	265.8	249.9	235.4	221.0	209.7	199.7	191.7	186.8	185.3
145°	297.6	281.9	266.7	252.4	239.2	226.4	215.6	206.3	199.4	194.5	193.0
147.5°	294.0	280.2	267.2	254.7	243.1	231.2	221.4	213.6	206.6	202.2	201.7
150°	291.3	279.0	267.2	255.9	245.1	234.3	225.0	217.6	211.7	207.8	207.2
152.5°	288.1	277.0	266.4	256.7	246.7	237.0	228.5	221.9	216.4	212.5	212.4
155°	283.4	274.1	265.2	257.4	249.0	240.6	233.3	227.9	223.0	220.1	219.6
157.5°	278.6	271.0	264.0	257.4	250.7	243.6	237.8	233.1	229.3	226.5	226.5
160°	275.1	268.6	262.8	257.4	251.5	245.6	240.1	236.3	232.8	230.8	230.8
162.5°	271.9	266.3	261.6	257.4	252.3	246.8	242.5	239.0	235.9	234.4	234.8
165°	266.7	262.8	259.3	256.4	252.4	248.1	245.1	242.6	240.1	239.2	239.2
167.5°	262.0	259.2	257.0	255.2	252.4	249.1	246.8	245.5	243.6	243.1	243.6
170°	258.8	256.8	255.4	254.4	251.9	249.5	248.1	247.0	245.6	245.1	245.6
172.5°	256.1	254.5	253.8	253.7	251.6	249.9	248.8	248.2	247.1	247.0	247.5
175°	253.0	251.9	251.9	252.4	251.0	250.0	250.0	249.5	249.0	249.0	249.5
177.5°	250.8	250.4	250.4	251.2	250.4	250.0	250.0	250.0	249.6	250.0	250.4
180°	250.0	250.0	250.0	250.0	250.0	250.0	250.0	250.0	250.0	250.0	250.0



TEST NUMBER: P332501-935
 CATALOG NUMBER: SA4XXDIP-C350D590U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9
2.5°	495.2	496.8	498.9	502.5	503.8	505.4	507.7	507.6	508.2	510.7	515.8
5°	497.0	503.3	509.5	516.8	524.5	529.6	536.5	540.8	545.1	550.6	560.0
7.5°	497.7	507.7	518.9	531.8	543.3	556.5	566.8	576.5	585.3	596.8	608.0
10°	496.6	510.1	524.5	540.8	558.1	572.8	586.1	601.2	614.0	628.0	640.7
12.5°	494.5	510.7	530.0	548.3	568.5	590.2	606.7	622.0	639.0	655.2	674.8
15°	489.7	511.9	534.5	558.5	585.7	610.7	634.6	654.3	672.6	696.9	722.4
17.5°	483.5	507.5	536.1	565.2	593.5	622.1	651.6	681.3	704.5	734.6	754.5
20°	477.9	505.6	534.9	569.6	597.9	633.5	662.9	691.6	723.4	753.4	777.2
22.5°	469.8	500.2	531.3	565.8	603.0	638.8	672.6	703.8	735.6	768.2	797.0
25°	459.7	487.2	524.1	563.2	600.3	639.0	678.0	717.0	751.3	785.7	812.6
27.5°	442.5	477.2	511.5	551.9	593.1	636.9	678.6	719.5	755.4	783.7	800.3
30°	433.6	463.8	501.1	541.7	586.3	633.4	676.7	716.9	750.3	772.9	779.6
32.5°	420.6	451.7	488.2	530.2	577.5	625.9	671.0	708.9	736.8	748.6	740.5
35°	401.2	429.4	466.2	509.2	558.4	609.8	654.5	686.5	700.8	689.6	661.7
37.5°	378.0	405.9	442.9	485.2	536.0	588.4	628.7	651.8	647.0	619.1	577.6
40°	361.7	387.8	423.0	468.6	518.1	570.8	606.2	618.6	605.6	565.7	521.4
42.5°	343.6	369.0	404.4	448.5	500.9	549.4	580.3	581.3	559.5	511.7	467.4
45°	316.1	340.3	373.7	419.6	468.0	513.7	534.1	524.1	483.7	437.7	393.0
47.5°	288.9	309.9	342.9	386.3	432.4	470.8	481.0	463.0	420.0	375.2	333.9
50°	269.0	290.2	321.2	362.7	407.2	440.3	445.2	421.4	379.2	334.2	301.8
52.5°	249.9	271.0	300.7	339.2	379.9	409.8	410.0	382.5	340.4	300.3	270.2
55°	221.9	240.8	267.8	302.2	338.5	361.9	356.2	327.7	291.2	256.3	230.1
57.5°	194.9	211.5	236.2	264.9	296.9	316.2	306.8	279.3	246.8	217.1	197.3
60°	177.5	193.2	214.4	241.5	268.4	283.4	274.5	249.6	219.6	195.8	178.5
62.5°	160.5	173.7	194.2	217.7	242.6	253.7	245.8	221.3	195.4	173.8	159.7
65°	136.6	147.3	163.6	183.8	201.9	211.5	204.8	181.9	162.2	146.7	135.5
67.5°	114.1	122.5	134.9	151.1	166.5	171.7	165.6	149.6	132.9	120.5	112.6
70°	98.6	106.6	116.9	129.4	142.8	148.4	142.2	129.6	116.0	104.5	96.8
72.5°	85.1	91.3	100.0	110.6	121.1	126.7	122.5	110.4	98.8	90.3	83.8
75°	64.8	70.1	76.2	83.8	91.9	95.6	91.9	83.5	75.6	69.3	64.6
77.5°	47.1	49.9	54.7	60.4	65.4	68.2	65.0	59.4	54.5	50.2	47.9
80°	35.9	37.9	41.2	45.6	49.1	51.7	49.7	45.0	41.2	38.3	37.3
82.5°	26.1	27.5	29.6	32.9	35.2	36.6	35.7	32.3	30.7	28.2	27.2
85°	12.8	13.7	15.1	16.1	18.2	18.3	18.5	17.1	15.7	15.1	14.3
87.5°	4.7	5.2	5.8	6.4	7.0	7.7	7.6	7.7	7.3	7.1	6.5
90°	1.5	2.9	3.4	4.0	4.0	6.9	6.9	7.8	8.9	8.4	8.9
92.5°	8.2	12.7	18.8	25.9	36.2	61.1	99.2	136.4	155.8	129.8	96.4
95°	17.7	22.6	29.0	40.7	61.4	104.1	184.7	302.0	400.3	411.6	363.9
97.5°	29.1	33.3	39.2	49.3	66.6	99.5	166.0	282.8	421.6	517.1	537.7
100°	37.4	40.7	46.7	56.0	71.7	100.7	156.2	256.4	394.9	520.6	592.4
102.5°	46.0	49.0	54.5	63.5	78.4	104.6	153.4	238.7	361.5	491.1	589.6
105°	59.0	61.4	67.3	76.1	90.4	113.9	154.7	223.5	322.2	437.6	550.1
107.5°	72.0	74.5	80.8	89.2	103.2	124.8	162.0	220.8	300.2	394.4	494.0
110°	81.0	83.5	89.4	98.2	111.5	133.1	167.5	221.5	292.7	372.8	460.2



TEST NUMBER: P332501-935

CATALOG NUMBER: SA4XXDIP-C350D590U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	89.7	92.6	98.1	106.9	120.1	140.9	173.4	223.9	289.2	360.6	435.5
115°	102.6	106.1	111.0	120.4	133.6	153.3	182.7	228.4	287.3	349.2	410.6
117.5°	115.5	118.6	124.0	132.7	146.5	165.1	192.3	233.2	286.8	344.1	398.4
120°	123.8	127.2	132.6	140.9	154.7	173.4	198.9	236.8	286.8	341.4	393.0
122.5°	131.6	135.1	140.1	149.2	162.6	181.2	205.2	240.3	286.5	338.2	388.2
125°	142.9	145.9	151.3	160.6	174.4	192.0	214.6	245.6	285.9	333.0	380.1
127.5°	151.7	155.2	161.4	171.1	184.9	202.1	222.8	249.8	284.7	326.1	370.3
130°	157.1	161.1	168.5	177.8	192.0	208.7	227.9	253.0	284.4	321.7	362.5
132.5°	161.9	167.0	174.0	184.1	197.5	214.2	233.0	255.7	284.0	317.8	354.2
135°	169.4	174.4	182.7	193.0	205.8	222.0	239.7	259.8	283.4	311.9	342.9
137.5°	176.5	181.9	189.9	200.6	212.8	227.9	244.4	262.3	283.3	306.8	332.5
140°	181.2	186.7	195.0	205.3	217.1	231.9	247.5	264.2	282.9	304.0	326.6
142.5°	186.8	191.7	199.7	209.7	221.0	235.4	249.9	265.8	282.9	301.7	321.2
145°	194.5	199.4	206.3	215.6	226.4	239.2	252.4	266.7	281.9	297.6	313.3
147.5°	202.2	206.6	213.6	221.4	231.2	243.1	254.7	267.2	280.2	294.0	306.9
150°	207.8	211.7	217.6	225.0	234.3	245.1	255.9	267.2	279.0	291.3	303.1
152.5°	212.5	216.4	221.9	228.5	237.0	246.7	256.7	266.4	277.0	288.1	298.7
155°	220.1	223.0	227.9	233.3	240.6	249.0	257.4	265.2	274.1	283.4	292.2
157.5°	226.5	229.3	233.1	237.8	243.6	250.7	257.4	264.0	271.0	278.6	285.2
160°	230.8	232.8	236.3	240.1	245.6	251.5	257.4	262.8	268.6	275.1	280.9
162.5°	234.4	235.9	239.0	242.5	246.8	252.3	257.4	261.6	266.3	271.9	276.6
165°	239.2	240.1	242.6	245.1	248.1	252.4	256.4	259.3	262.8	266.7	270.6
167.5°	243.1	243.6	245.5	246.8	249.1	252.4	255.2	257.0	259.2	262.0	264.8
170°	245.1	245.6	247.0	248.1	249.5	251.9	254.4	255.4	256.8	258.8	261.3
172.5°	247.0	247.1	248.2	248.8	249.9	251.6	253.7	253.8	254.5	256.1	258.1
175°	249.0	249.0	249.5	250.0	250.0	251.0	252.4	251.9	251.9	253.0	253.9
177.5°	250.0	249.6	250.0	250.0	250.0	250.4	251.2	250.4	250.4	250.8	251.2
180°	250.0	250.0	250.0	250.0	250.0	250.0	250.0	250.0	250.0	250.0	250.0



TEST NUMBER: P332501-935

CATALOG NUMBER: SA4XXDIP-C350D590U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	491.9	491.9	491.9	491.9	491.9	491.9	491.9
2.5°	518.5	518.8	520.3	521.4	521.8	523.4	523.5
5°	564.0	567.5	574.2	574.8	575.8	581.2	577.0
7.5°	617.4	626.2	632.1	637.3	639.1	641.4	641.0
10°	651.7	664.7	671.2	681.7	682.0	684.7	683.0
12.5°	686.0	701.2	713.1	715.1	723.8	725.1	727.4
15°	734.8	750.9	767.4	773.4	785.3	788.2	792.6
17.5°	780.6	797.0	808.7	823.9	828.9	835.4	831.0
20°	805.7	823.6	838.4	850.3	855.4	859.1	858.7
22.5°	820.9	839.0	850.8	860.0	864.7	866.3	866.2
25°	830.3	840.8	844.5	847.9	842.6	840.8	841.5
27.5°	803.9	801.2	791.7	779.1	766.1	755.8	750.1
30°	767.6	751.7	737.3	712.0	699.0	691.2	684.2
32.5°	716.1	690.9	663.1	639.9	625.1	613.6	611.9
35°	627.8	590.0	555.9	527.5	512.9	500.5	497.6
37.5°	533.7	494.4	463.7	438.8	423.0	414.2	406.0
40°	471.3	437.5	407.3	386.2	374.1	367.8	362.7
42.5°	423.3	392.4	362.3	346.2	335.4	331.5	328.5
45°	356.8	328.0	307.3	295.1	288.8	282.2	279.1
47.5°	303.6	280.3	266.6	256.1	249.3	245.5	243.6
50°	273.5	254.3	242.1	234.1	228.0	225.0	223.3
52.5°	246.8	231.0	220.8	214.4	210.3	208.0	207.3
55°	212.5	200.5	194.0	188.5	185.5	183.4	182.6
57.5°	184.8	175.5	170.2	165.7	164.5	162.8	162.2
60°	166.5	159.4	154.9	151.8	150.8	148.8	149.1
62.5°	150.3	144.5	140.7	139.0	137.6	135.9	136.5
65°	127.2	122.9	120.8	119.2	117.6	116.6	117.4
67.5°	106.7	103.8	101.0	100.0	99.3	99.1	98.2
70°	93.3	90.9	88.4	87.8	87.8	87.0	86.8
72.5°	80.4	78.7	77.1	76.5	75.9	76.3	75.4
75°	62.2	60.7	60.1	59.5	59.3	59.3	58.7
77.5°	45.9	44.9	43.9	43.9	43.1	42.9	42.8
80°	34.9	34.4	33.7	33.7	33.2	33.4	33.0
82.5°	26.2	25.7	25.5	25.1	24.5	24.6	24.2
85°	14.0	13.4	13.3	12.7	12.2	12.7	12.2
87.5°	6.7	6.7	6.5	6.3	6.2	6.1	5.7
90°	9.3	9.8	9.8	10.3	10.8	10.3	10.3
92.5°	72.6	57.8	48.0	42.1	39.5	37.8	37.8
95°	287.8	222.0	174.4	150.3	135.1	126.2	119.9
97.5°	509.5	461.4	410.1	374.9	345.3	330.5	320.3
100°	602.2	578.1	541.7	499.0	469.1	454.3	450.4
102.5°	638.3	645.3	630.2	603.9	582.2	566.7	563.5
105°	635.1	683.7	703.9	704.8	700.9	694.0	691.0
107.5°	584.4	653.0	696.7	721.0	732.2	737.1	738.4
110°	545.2	616.4	670.5	705.3	725.9	734.8	739.2



TEST NUMBER: P332501-935

CATALOG NUMBER: SA4XXDIP-C350D590U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	510.6	577.9	631.9	671.5	696.5	708.9	716.0
115°	471.1	528.5	575.7	614.4	643.9	659.6	663.6
117.5°	448.4	493.6	533.6	566.7	591.4	607.3	610.4
120°	438.6	477.9	512.7	540.8	562.4	575.1	580.6
122.5°	432.3	468.0	498.6	522.3	540.8	551.6	557.0
125°	422.4	456.2	483.3	502.9	517.2	526.5	529.4
127.5°	410.7	444.5	470.1	489.9	502.6	510.4	513.3
130°	401.3	434.6	460.7	480.9	493.1	501.0	503.9
132.5°	390.6	423.3	449.3	469.1	482.9	490.3	493.4
135°	374.8	404.7	429.3	448.9	462.7	470.5	473.5
137.5°	359.6	384.8	407.0	425.3	438.9	445.4	448.9
140°	349.7	371.8	392.4	409.7	420.4	427.3	431.3
142.5°	341.5	360.4	378.3	393.5	403.6	409.7	412.3
145°	330.0	344.8	358.5	370.8	379.2	384.1	386.5
147.5°	320.2	332.0	342.9	351.9	359.0	362.7	363.7
150°	314.4	324.2	333.0	340.9	347.2	350.2	350.7
152.5°	308.4	317.5	324.8	331.4	336.7	338.4	338.9
155°	300.1	307.5	313.3	318.3	322.2	323.6	323.6
157.5°	291.9	298.0	302.7	306.5	309.4	310.3	310.3
160°	286.4	291.7	295.7	298.6	301.6	302.0	302.0
162.5°	281.2	285.4	289.0	291.2	294.1	294.6	294.2
165°	273.5	277.0	279.5	281.5	283.4	282.9	282.4
167.5°	267.1	269.8	271.3	272.3	273.5	273.5	273.1
170°	262.8	264.8	266.2	267.2	267.7	267.2	267.2
172.5°	259.2	260.5	261.5	262.1	262.6	262.1	261.3
175°	254.4	255.4	255.4	255.4	256.4	255.4	254.4
177.5°	251.6	251.6	251.9	251.6	251.9	251.2	250.4
180°	250.0	250.0	250.0	250.0	250.0	250.0	250.0

(END OF REPORT)