

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332959-935

Luminaire Tested: **SA4XXRDIP-C1020D365U935-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332959-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C1020D365U935-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4684.6 lumens
Efficiency: N/A
Efficacy: 107.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 43.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332959-935

CATALOG NUMBER: SA4XXRDIP-C1020D365U935-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332959-935

CATALOG NUMBER: SA4XXRDIP-C1020D365U935-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	114	114	114	114	108	108	108	108	98	98	98	89	89	89	81	81	81	77				77
1	104	100	96	92	99	95	92	89	87	84	82	79	77	75	72	70	69				65	
2	95	88	81	76	91	84	78	74	77	72	68	70	67	63	64	61	59				55	
3	87	78	70	64	83	74	67	62	68	63	58	62	58	54	57	53	50				47	
4	80	69	61	55	76	66	59	53	61	55	50	56	51	47	51	47	44				41	
5	74	62	53	47	70	59	52	46	55	48	43	50	45	41	46	42	38				36	
6	68	56	47	41	65	54	46	40	50	43	38	46	40	36	42	38	34				32	
7	63	51	42	37	60	49	41	36	45	39	34	42	36	32	39	34	30				28	
8	59	46	38	33	56	45	37	32	41	35	30	38	33	29	36	31	27				25	
9	55	42	35	29	52	41	34	29	38	32	27	35	30	26	33	28	25				23	
10	52	39	32	27	49	38	31	26	35	29	25	33	28	24	31	26	23				21	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12551	12551	12551
5°	12580	12426	12503
10°	12500	12276	12276
15°	12357	12018	11929
20°	12160	11679	11465
25°	11908	11282	10996
30°	11663	10864	10409
35°	11392	10430	9819
40°	11065	9936	9183
45°	10764	9445	8535
50°	10420	8881	7850
55°	10054	8294	7104
60°	9649	7650	6344
65°	9278	6844	5593
70°	8738	5958	4749
75°	8057	4938	3862
80°	7029	3761	3543
85°	5956	3418	3196



TEST NUMBER: P332959-935

CATALOG NUMBER: SA4XXRDIP-C1020D365U935-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	146.0	3.1
10°-20°	407.3	8.7
20°-30°	588.1	12.6
30°-40°	666.6	14.2
40°-50°	643.7	13.7
50°-60°	535.3	11.4
60°-70°	369.6	7.9
70°-80°	187.4	4.0
80°-90°	49.2	1.1
90°-100°	25.9	0.6
100°-110°	76.9	1.6
110°-120°	130.5	2.8
120°-130°	172.0	3.7
130°-140°	193.2	4.1
140°-150°	189.8	4.1
150°-160°	159.7	3.4
160°-170°	106.2	2.3
170°-180°	37.2	0.8
0°-30°	1141.4	24.4
0°-40°	1808.0	38.6
0°-60°	2987.0	63.8
0°-90°	3593.2	76.7
90°-120°	233.3	5.0
90°-150°	788.3	16.8
90°-180°	1091.0	23.3
0°-180°	4684.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1555	1555	1555	1555	1555	
5°	1552	1547	1533	1544	1543	147
15°	1478	1467	1438	1435	1427	416
25°	1337	1314	1267	1247	1234	616
35°	1156	1117	1058	1019	996	722
45°	943	897	827	771	748	727
55°	714	665	589	530	505	639
65°	486	433	358	309	293	479
75°	258	214	158	132	124	273
85°	64	42	37	35	34	72
90°	1	4	7	8	9	4
95°	18	21	23	24	24	20
105°	71	71	72	73	74	75
115°	133	133	132	132	132	131
125°	193	193	193	192	192	172
135°	249	251	251	250	250	193
145°	303	304	304	304	303	189
155°	347	347	347	348	347	160
165°	378	377	376	378	377	106
175°	393	391	391	393	391	37
180°	393	393	393	393	393	



TEST NUMBER: P332959-935

CATALOG NUMBER: SA4XXRDIP-C1020D365U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1554.7	1554.7	1554.7	1554.7	1554.7	1554.7	1554.7	1554.7	1554.7	1554.7	1554.7
2.5°	1558.5	1557.6	1556.8	1556.0	1555.1	1553.5	1551.2	1548.9	1546.5	1544.2	1546.5
5°	1552.3	1551.3	1550.2	1549.1	1548.1	1545.9	1542.8	1539.6	1536.5	1533.3	1535.9
7.5°	1538.3	1537.1	1536.0	1534.9	1533.8	1531.2	1527.1	1522.9	1518.8	1514.7	1516.4
10°	1524.9	1523.6	1522.2	1521.0	1519.7	1516.6	1511.8	1507.1	1502.3	1497.5	1498.6
12.5°	1507.8	1506.2	1504.7	1503.2	1501.7	1498.1	1492.5	1486.9	1481.3	1475.7	1476.3
15°	1478.5	1476.1	1473.8	1471.4	1469.0	1464.5	1457.8	1451.2	1444.7	1438.0	1437.5
17.5°	1443.0	1439.6	1436.1	1432.7	1429.3	1423.6	1415.7	1407.7	1399.8	1391.8	1390.3
20°	1415.4	1412.0	1408.5	1405.1	1401.6	1395.4	1386.5	1377.4	1368.5	1359.4	1357.4
22.5°	1384.9	1381.0	1377.2	1373.4	1369.5	1362.7	1353.1	1343.5	1333.9	1324.2	1321.0
25°	1336.9	1332.1	1327.3	1322.6	1317.8	1310.0	1299.2	1288.3	1277.5	1266.6	1262.1
27.5°	1286.3	1280.4	1274.5	1268.4	1262.5	1253.7	1242.1	1230.5	1218.9	1207.3	1201.8
30°	1251.1	1244.5	1237.9	1231.3	1224.7	1215.1	1202.7	1190.2	1177.8	1165.4	1158.8
32.5°	1214.0	1206.5	1199.0	1191.6	1184.1	1174.0	1161.1	1148.3	1135.4	1122.6	1114.9
35°	1155.9	1147.5	1138.9	1130.5	1122.1	1111.2	1097.9	1084.8	1071.5	1058.3	1049.3
37.5°	1093.7	1085.0	1076.3	1067.6	1058.9	1047.1	1032.5	1017.9	1003.2	988.5	978.4
40°	1050.0	1041.2	1032.5	1023.7	1015.0	1003.2	988.1	972.9	957.9	942.8	931.7
42.5°	1008.1	998.9	989.7	980.6	971.5	959.0	943.3	927.6	911.9	896.1	884.8
45°	942.8	933.1	923.3	913.4	903.6	890.8	874.9	859.1	843.2	827.3	814.4
47.5°	875.5	865.3	855.2	845.2	835.0	821.7	805.2	788.7	772.1	755.7	742.3
50°	829.7	819.4	809.1	798.7	788.4	774.8	757.9	741.0	724.0	707.1	693.9
52.5°	783.1	772.9	762.8	752.8	742.6	728.9	711.5	694.2	676.8	659.5	646.1
55°	714.3	703.7	693.1	682.5	671.9	658.1	640.8	623.6	606.5	589.3	575.5
57.5°	646.2	635.2	624.1	613.1	602.2	588.1	571.3	554.3	537.4	520.5	506.5
60°	597.6	587.0	576.4	565.8	555.3	541.5	524.6	507.6	490.7	473.8	460.0
62.5°	553.8	542.8	531.8	520.7	509.8	495.6	478.2	460.9	443.5	426.2	413.5
65°	485.7	474.3	463.0	451.6	440.2	426.0	409.1	392.2	375.2	358.3	347.0
67.5°	415.0	404.1	393.2	382.3	371.3	358.1	342.3	326.7	310.9	295.2	285.4
70°	370.2	359.1	348.0	336.9	325.8	312.7	297.6	282.5	267.4	252.4	243.7
72.5°	322.6	312.5	302.5	292.5	282.4	270.3	256.1	241.8	227.6	213.4	205.9
75°	258.3	248.6	238.8	228.9	219.2	208.0	195.6	183.2	170.7	158.3	152.2
77.5°	193.1	184.8	176.5	168.2	159.9	150.7	140.6	130.6	120.5	110.5	106.9
80°	151.2	143.5	135.9	128.2	120.5	112.7	104.8	96.9	88.9	80.9	80.2
82.5°	115.0	108.0	100.9	93.8	86.9	81.0	76.5	72.0	67.4	62.9	62.3
85°	64.3	59.0	53.7	48.4	43.1	40.0	39.3	38.5	37.7	36.9	36.3
87.5°	22.1	20.6	19.0	17.5	15.9	15.1	15.0	14.9	14.8	14.6	14.6
90°	0.9	1.6	2.4	3.2	3.9	4.6	5.1	5.6	6.1	6.7	7.1
92.5°	6.5	7.4	8.2	9.0	9.9	10.5	10.9	11.3	11.7	12.1	12.3
95°	18.3	18.9	19.5	20.1	20.7	21.3	21.7	22.2	22.6	23.2	23.3
97.5°	31.9	32.4	32.9	33.3	33.8	34.4	34.9	35.5	36.0	36.6	36.9
100°	42.6	42.9	43.1	43.4	43.7	44.1	44.7	45.4	46.0	46.6	46.7
102.5°	53.8	53.9	54.0	54.2	54.2	54.6	55.1	55.7	56.2	56.7	57.0
105°	70.9	70.9	71.0	71.1	71.1	71.3	71.6	71.9	72.2	72.4	72.6
107.5°	88.9	88.9	89.0	89.1	89.2	89.2	89.3	89.3	89.4	89.4	89.5
110°	101.0	101.2	101.3	101.4	101.5	101.6	101.5	101.4	101.3	101.3	101.2



TEST NUMBER: P332959-935

CATALOG NUMBER: SA4XXRDIP-C1020D365U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	113.7	113.7	113.7	113.7	113.7	113.7	113.6	113.5	113.4	113.2	113.2
115°	132.7	132.7	132.7	132.7	132.7	132.6	132.4	132.3	132.2	132.1	132.0
117.5°	150.5	150.6	150.7	150.7	150.8	150.8	150.7	150.6	150.4	150.3	150.2
120°	162.5	162.7	163.0	163.2	163.6	163.6	163.4	163.2	163.0	162.8	162.5
122.5°	174.9	175.0	175.1	175.2	175.3	175.3	175.2	175.1	175.0	175.0	174.7
125°	193.2	193.2	193.2	193.2	193.2	193.1	193.1	193.0	193.0	192.9	192.8
127.5°	209.8	210.0	210.3	210.4	210.6	210.7	210.6	210.4	210.3	210.3	210.1
130°	221.5	221.7	221.9	222.1	222.3	222.4	222.4	222.4	222.4	222.4	222.3
132.5°	233.4	233.6	233.7	233.8	234.0	234.0	234.0	233.9	233.9	233.8	233.7
135°	249.2	249.6	249.9	250.4	250.8	251.0	251.0	251.0	251.0	251.0	250.9
137.5°	266.3	266.6	266.7	266.9	267.1	267.3	267.3	267.4	267.6	267.7	267.5
140°	277.8	277.9	278.0	278.2	278.4	278.4	278.4	278.4	278.4	278.4	278.4
142.5°	288.3	288.3	288.5	288.6	288.8	288.9	288.8	288.7	288.7	288.6	288.6
145°	302.7	303.0	303.2	303.5	303.8	304.0	304.0	304.1	304.2	304.3	304.2
147.5°	317.1	317.5	317.7	318.1	318.4	318.5	318.5	318.4	318.4	318.3	318.2
150°	325.9	326.1	326.4	326.7	326.9	327.1	327.1	327.1	327.1	327.1	327.1
152.5°	334.2	334.3	334.4	334.6	334.8	334.8	334.9	335.0	335.0	335.1	335.3
155°	346.8	346.8	346.8	346.8	346.8	346.8	346.7	346.6	346.6	346.6	346.8
157.5°	357.6	357.4	357.3	357.2	357.1	357.0	357.0	357.0	357.0	357.0	357.1
160°	363.9	363.8	363.8	363.7	363.6	363.5	363.5	363.4	363.3	363.3	363.5
162.5°	369.7	369.5	369.4	369.2	369.0	368.9	368.9	368.8	368.7	368.6	369.0
165°	377.5	377.4	377.2	376.9	376.8	376.6	376.4	376.3	376.2	376.1	376.4
167.5°	383.6	383.3	383.1	382.7	382.5	382.3	382.4	382.4	382.4	382.4	382.8
170°	387.0	386.7	386.3	386.0	385.6	385.6	385.6	385.6	385.7	385.8	386.2
172.5°	389.4	389.2	388.8	388.6	388.3	388.1	388.1	388.2	388.2	388.2	388.7
175°	392.8	392.4	392.1	391.8	391.4	391.2	391.2	391.1	391.1	391.0	391.4
177.5°	393.9	393.6	393.3	393.0	392.8	392.7	392.7	392.7	392.7	392.7	393.0
180°	393.4	393.4	393.4	393.4	393.4	393.4	393.4	393.4	393.4	393.4	393.4



TEST NUMBER: P332959-935

CATALOG NUMBER: SA4XXRDIP-C1020D365U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1554.7	1554.7	1554.7	1554.7	1554.7	1554.7	1554.7	1554.7
2.5°	1548.9	1551.2	1553.5	1554.6	1554.4	1554.2	1553.9	1553.8
5°	1538.5	1541.2	1543.9	1544.9	1544.4	1543.9	1543.3	1542.8
7.5°	1518.1	1519.8	1521.5	1521.9	1521.0	1520.2	1519.3	1518.5
10°	1499.7	1500.7	1501.8	1501.8	1500.7	1499.7	1498.6	1497.5
12.5°	1476.9	1477.6	1478.2	1477.7	1476.3	1474.8	1473.3	1471.9
15°	1437.0	1436.4	1435.9	1434.7	1432.9	1431.0	1429.2	1427.3
17.5°	1388.9	1387.4	1386.0	1383.8	1381.0	1378.2	1375.4	1372.5
20°	1355.2	1353.1	1351.0	1348.2	1344.8	1341.4	1337.9	1334.5
22.5°	1317.8	1314.7	1311.6	1308.5	1305.7	1303.0	1300.1	1297.4
25°	1257.6	1253.1	1248.6	1245.0	1242.4	1239.8	1237.1	1234.5
27.5°	1196.2	1190.7	1185.1	1180.4	1176.6	1172.8	1169.0	1165.2
30°	1152.2	1145.6	1138.9	1133.5	1129.3	1125.1	1120.8	1116.6
32.5°	1107.2	1099.6	1091.9	1086.1	1082.0	1078.0	1074.0	1070.0
35°	1040.3	1031.3	1022.3	1015.5	1010.6	1005.9	1001.2	996.3
37.5°	968.5	958.4	948.3	940.9	936.2	931.3	926.6	921.9
40°	920.6	909.5	898.4	890.4	885.7	880.9	876.2	871.4
42.5°	873.5	862.2	850.8	842.7	837.8	832.8	827.8	822.9
45°	801.4	788.4	775.5	766.6	761.9	757.1	752.3	747.6
47.5°	728.8	715.4	701.9	692.6	687.3	682.1	676.8	671.7
50°	680.6	667.4	654.2	645.1	640.1	635.0	630.0	625.0
52.5°	632.6	619.1	605.7	596.4	591.2	585.9	580.7	575.5
55°	561.7	548.0	534.3	524.9	519.8	514.8	509.8	504.7
57.5°	492.5	478.5	464.6	455.7	451.9	448.1	444.3	440.5
60°	446.3	432.5	418.8	409.7	405.5	401.3	397.1	392.9
62.5°	400.8	388.1	375.4	367.3	363.9	360.6	357.1	353.8
65°	335.5	324.2	312.8	305.6	302.4	299.2	296.0	292.8
67.5°	275.6	265.9	256.1	249.4	245.9	242.5	238.9	235.5
70°	234.9	226.2	217.5	211.7	209.1	206.5	203.8	201.2
72.5°	198.4	191.0	183.5	178.6	176.1	173.7	171.3	168.8
75°	146.2	140.1	134.0	130.2	128.5	127.0	125.4	123.8
77.5°	103.4	99.9	96.3	94.3	93.8	93.3	92.8	92.4
80°	79.4	78.6	77.7	77.2	77.0	76.7	76.5	76.2
82.5°	61.6	61.1	60.5	60.1	59.8	59.6	59.3	59.1
85°	35.8	35.3	34.8	34.5	34.5	34.5	34.5	34.5
87.5°	14.4	14.3	14.1	14.2	14.5	14.7	14.9	15.2
90°	7.5	7.9	8.4	8.6	8.7	8.9	9.0	9.1
92.5°	12.6	12.7	13.0	13.2	13.3	13.3	13.4	13.5
95°	23.5	23.8	23.9	24.0	24.0	24.0	24.0	24.0
97.5°	37.0	37.3	37.5	37.6	37.6	37.6	37.6	37.6
100°	46.8	46.9	47.1	47.2	47.2	47.2	47.2	47.2
102.5°	57.2	57.3	57.5	57.7	57.7	57.8	57.8	57.9
105°	72.8	73.0	73.2	73.4	73.6	73.9	74.0	74.2
107.5°	89.8	90.0	90.1	90.2	90.2	90.2	90.2	90.1
110°	101.1	100.9	100.7	100.8	101.0	101.3	101.4	101.6



TEST NUMBER: P332959-935

CATALOG NUMBER: SA4XXRDIP-C1020D365U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	113.2	113.1	113.1	113.1	113.2	113.2	113.2	113.3
115°	131.9	131.8	131.7	131.7	131.6	131.6	131.5	131.5
117.5°	149.9	149.6	149.5	149.3	149.1	149.0	148.9	148.7
120°	162.1	161.8	161.4	161.4	161.4	161.6	161.7	161.9
122.5°	174.5	174.3	174.0	173.7	173.6	173.3	173.1	172.8
125°	192.6	192.5	192.3	192.2	192.1	191.9	191.8	191.7
127.5°	210.0	209.8	209.7	209.6	209.5	209.4	209.2	209.1
130°	222.1	222.0	221.9	221.6	221.4	221.1	220.8	220.6
132.5°	233.6	233.4	233.3	233.2	233.1	233.0	232.9	232.7
135°	250.7	250.6	250.5	250.3	250.1	249.9	249.7	249.5
137.5°	267.3	267.2	267.0	266.9	266.9	267.0	267.0	267.1
140°	278.3	278.2	278.1	278.0	278.0	277.9	277.8	277.8
142.5°	288.6	288.6	288.5	288.5	288.5	288.5	288.5	288.5
145°	304.1	304.0	304.0	303.8	303.7	303.4	303.2	303.1
147.5°	318.2	318.1	318.1	318.1	318.0	317.9	317.8	317.8
150°	327.1	327.1	327.1	327.0	327.0	326.9	326.8	326.7
152.5°	335.4	335.6	335.8	335.7	335.5	335.4	335.2	335.0
155°	347.1	347.3	347.6	347.6	347.3	347.1	346.8	346.6
157.5°	357.3	357.6	357.7	357.7	357.5	357.3	357.1	356.8
160°	363.7	363.9	364.1	364.0	363.7	363.3	363.0	362.7
162.5°	369.4	369.7	370.1	370.1	369.8	369.5	369.1	368.8
165°	376.9	377.3	377.6	377.7	377.5	377.2	376.9	376.7
167.5°	383.2	383.6	384.0	384.0	383.6	383.1	382.7	382.3
170°	386.6	387.0	387.4	387.4	386.9	386.4	386.0	385.5
172.5°	389.2	389.6	390.0	390.0	389.6	389.1	388.7	388.1
175°	391.9	392.4	392.9	392.9	392.4	391.9	391.4	391.0
177.5°	393.4	393.8	394.2	394.2	393.7	393.3	392.9	392.4
180°	393.4	393.4	393.4	393.4	393.4	393.4	393.4	393.4

(END OF REPORT)