

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332885-935

Luminaire Tested: **SA4XXRDIP-C350D1035U935-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332885-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C350D1035U935-4F0-1E-UDD-A4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4462.8 lumens
Efficiency: N/A
Efficacy: 119.6 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 37.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332885-935

CATALOG NUMBER: SA4XXRDIP-C350D1035U935-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332885-935

CATALOG NUMBER: SA4XXRDIP-C350D1035U935-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	72	72	72	53	53	53	37	37	37	29
1	93	89	86	82	83	80	77	74	63	61	59	47	46	45	33	32	31	25
2	85	78	72	68	76	70	65	61	55	52	49	42	40	38	29	28	27	21
3	78	69	62	56	69	62	56	51	49	45	42	37	34	32	26	24	23	18
4	71	61	53	48	64	55	49	44	44	39	36	33	30	28	23	22	20	16
5	65	54	47	41	58	49	42	37	39	34	31	30	27	24	21	19	18	14
6	60	49	41	35	54	44	37	32	35	30	27	27	24	21	19	17	15	12
7	55	44	36	31	50	40	33	28	32	27	23	24	21	19	18	15	14	11
8	51	40	32	27	46	36	30	25	29	24	21	22	19	17	16	14	12	10
9	48	36	29	24	43	33	27	22	26	22	19	20	17	15	15	13	11	9
10	45	33	26	22	40	30	24	20	24	20	17	19	16	13	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4083	4083	4083	4083
5°	4736	4095	3620	4095
10°	5603	4077	3231	4077
15°	6471	4040	2776	4040
20°	7205	3988	2510	3988
25°	7439	3937	2331	3937
30°	6511	3875	2222	3875
35°	5069	3783	2157	3783
40°	3801	3678	2121	3678
45°	3001	3511	2103	3511
50°	2533	3317	2042	3317
55°	2208	3103	1932	3103
60°	1986	2882	1711	2882
65°	1752	2644	1473	2644
70°	1577	2396	1327	2396
75°	1323	2121	1129	2121
80°	1116	1808	1060	1808
85°	945	1417	945	1417



TEST NUMBER: P332885-935

CATALOG NUMBER: SA4XXRDIP-C350D1035U935-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.0	1.1
10°-20°	147.8	3.3
20°-30°	231.2	5.2
30°-40°	257.0	5.8
40°-50°	228.0	5.1
50°-60°	177.7	4.0
60°-70°	116.3	2.6
70°-80°	57.2	1.3
80°-90°	16.5	0.4
90°-100°	316.0	7.1
100°-110°	657.7	14.7
110°-120°	589.1	13.2
120°-130°	495.5	11.1
130°-140°	413.2	9.3
140°-150°	315.7	7.1
150°-160°	221.9	5.0
160°-170°	130.5	2.9
170°-180°	42.5	1.0
0°-30°	428.0	9.6
0°-40°	685.0	15.3
0°-60°	1090.8	24.4
0°-90°	1280.8	28.7
90°-120°	1562.8	35.0
90°-150°	2787.1	62.5
90°-180°	3182.0	71.3
0°-180°	4462.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	506	506	506	506	506	
5°	584	505	447	505	584	59
15°	774	483	332	483	774	220
25°	835	442	262	442	835	370
35°	514	384	219	384	514	322
45°	263	308	184	308	263	208
55°	157	220	137	220	157	143
65°	92	138	77	138	92	92
75°	42	68	36	68	42	47
85°	10	15	10	15	10	12
90°	18	1	18	1	18	15
95°	210	28	210	28	210	325
105°	1209	101	1209	101	1209	1196
115°	1161	177	1161	177	1161	1153
125°	927	247	927	247	927	842
135°	829	293	829	293	829	640
145°	676	338	676	338	676	429
155°	566	384	566	384	566	264
165°	494	419	494	419	494	142
175°	445	437	445	437	445	43
180°	438	438	438	438	438	



TEST NUMBER: P332885-935

CATALOG NUMBER: SA4XXRDIP-C350D1035U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	533.5	534.9	533.5	533.3	531.7	531.2	530.5	528.4	524.5	522.2	522.7
5°	584.4	589.5	586.7	586.3	581.8	577.3	574.5	567.9	560.9	556.3	552.4
7.5°	643.3	646.3	644.5	641.6	634.4	630.3	623.6	615.1	602.6	593.1	584.4
10°	683.5	685.9	685.1	679.8	674.5	663.7	657.5	645.6	629.8	617.4	605.8
12.5°	722.9	725.5	718.3	718.6	708.5	700.0	690.3	675.2	657.1	641.1	626.5
15°	774.3	771.0	771.0	767.0	755.8	744.0	734.0	718.1	695.3	676.1	655.9
17.5°	814.6	815.7	814.1	804.4	795.7	783.4	765.1	746.6	725.4	699.6	679.1
20°	838.7	838.7	836.9	830.3	819.0	805.9	786.2	765.9	739.1	713.2	690.0
22.5°	848.5	849.1	847.0	841.6	831.4	818.6	801.8	781.3	753.5	724.4	695.7
25°	835.1	839.0	839.3	837.9	834.8	827.1	812.6	791.7	766.8	735.2	704.2
27.5°	766.6	771.5	775.8	782.9	792.3	797.1	797.8	787.1	765.4	735.0	703.9
30°	698.5	702.6	715.8	733.1	746.6	758.8	769.5	772.3	760.1	732.8	700.0
32.5°	622.8	628.4	641.7	660.3	682.7	703.4	727.2	739.3	739.0	722.6	692.3
35°	514.3	518.4	530.6	550.2	577.0	607.9	645.6	674.9	694.8	693.4	674.9
37.5°	414.8	419.4	431.7	448.0	474.1	512.1	548.6	589.1	625.9	646.7	640.5
40°	360.7	360.8	372.9	389.6	414.1	447.3	487.0	531.8	573.0	606.7	613.1
42.5°	318.0	318.0	326.0	344.0	361.5	392.8	430.8	475.3	523.5	562.3	579.5
45°	262.9	264.7	271.2	282.0	295.8	322.4	352.8	394.1	448.1	494.1	522.9
47.5°	222.6	225.3	229.5	238.2	249.3	266.9	292.1	329.2	373.2	423.8	464.7
50°	201.7	202.2	207.4	212.3	221.9	236.0	258.0	289.0	329.3	378.0	423.4
52.5°	183.8	183.7	186.9	193.1	200.9	211.8	229.6	257.8	293.6	337.3	384.2
55°	156.9	157.9	160.4	165.2	171.2	178.9	193.0	214.1	242.3	279.6	322.2
57.5°	136.5	137.0	138.9	140.9	146.4	152.1	162.6	177.3	201.0	231.5	271.2
60°	123.0	123.3	123.9	126.9	131.2	136.6	143.7	156.1	176.1	204.0	235.4
62.5°	110.0	110.4	111.3	113.6	116.9	120.5	128.0	138.0	154.5	178.4	206.6
65°	91.7	91.9	93.3	94.1	96.8	100.0	105.6	112.3	123.7	143.7	165.1
67.5°	76.6	76.6	76.7	77.8	79.6	81.8	85.1	90.5	99.1	111.3	130.2
70°	66.8	66.8	67.2	67.8	68.9	70.7	72.6	76.6	82.9	92.9	107.4
72.5°	57.7	57.9	58.3	58.4	58.9	60.4	61.8	64.4	69.1	76.6	88.3
75°	42.4	43.0	44.0	44.9	45.9	45.6	47.1	48.7	50.1	54.6	61.3
77.5°	31.5	31.3	31.3	32.0	32.1	32.4	33.4	34.6	35.7	37.8	40.2
80°	24.0	24.0	24.6	24.9	24.6	24.9	25.9	26.5	26.9	27.7	30.0
82.5°	18.2	18.5	18.3	18.5	18.6	18.9	19.7	19.8	20.2	20.6	21.4
85°	10.2	10.4	10.6	10.2	10.2	10.2	10.6	10.8	11.2	11.0	11.5
87.5°	7.2	7.1	7.4	7.2	7.1	7.1	7.0	7.1	6.6	7.0	6.6
90°	18.1	18.1	18.9	18.1	17.2	17.2	16.4	15.5	14.6	15.5	13.8
92.5°	66.2	66.2	69.1	73.8	83.9	101.1	127.1	168.8	227.1	272.7	238.6
95°	209.7	220.9	236.3	263.0	305.1	388.5	503.7	636.9	720.3	700.5	528.7
97.5°	560.6	578.5	604.2	656.0	717.7	807.4	891.5	941.1	904.9	737.8	494.7
100°	788.2	795.0	820.9	873.3	948.0	1011.7	1053.8	1036.6	911.1	691.0	448.7
102.5°	986.3	991.8	1018.9	1056.9	1102.8	1129.3	1117.1	1031.8	859.5	632.7	417.8
105°	1209.4	1214.5	1226.6	1233.5	1231.7	1196.4	1111.4	962.7	765.9	563.9	391.1
107.5°	1292.3	1290.0	1281.4	1261.8	1219.3	1142.7	1022.9	864.5	690.2	525.4	386.2
110°	1293.7	1285.9	1270.4	1234.3	1173.3	1078.7	954.1	805.4	652.4	512.3	387.6



TEST NUMBER: P332885-935

CATALOG NUMBER: SA4XXRDIP-C350D1035U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1253.0	1240.5	1218.8	1175.2	1105.9	1011.3	893.5	762.1	631.1	506.1	391.8
115°	1161.2	1154.3	1126.9	1075.3	1007.4	924.9	824.3	718.6	611.1	502.8	399.7
117.5°	1068.2	1062.9	1035.1	991.8	933.8	863.8	784.8	697.2	602.2	502.0	408.1
120°	1016.0	1006.5	984.2	946.3	897.3	836.4	767.6	687.6	597.4	502.0	414.3
122.5°	974.7	965.3	946.3	914.0	872.6	819.2	756.6	679.4	591.9	501.3	420.5
125°	926.6	921.4	905.1	880.2	845.8	798.5	739.2	665.3	582.8	500.2	429.8
127.5°	898.4	893.2	879.5	857.3	822.8	777.9	718.8	648.1	570.6	498.3	437.1
130°	881.9	876.8	863.0	841.5	806.2	760.7	702.2	634.4	563.0	497.7	442.6
132.5°	863.3	858.2	845.1	820.9	786.4	740.7	683.7	619.9	556.1	497.0	447.5
135°	828.6	823.5	809.7	785.7	751.2	708.3	655.8	599.9	545.8	495.9	454.7
137.5°	785.7	779.5	768.1	744.3	712.2	673.4	629.2	581.9	536.8	495.8	459.0
140°	754.7	747.8	735.8	716.9	686.7	650.7	612.0	571.6	532.1	495.1	462.4
142.5°	721.7	716.9	706.2	688.6	662.0	630.8	597.5	562.0	528.0	495.1	465.2
145°	676.5	672.2	663.6	648.9	627.5	603.4	577.6	548.4	520.9	493.4	466.7
147.5°	636.4	634.9	628.4	615.8	599.9	581.1	560.4	537.2	514.5	490.3	467.6
150°	613.7	612.9	607.7	596.5	582.8	567.3	550.1	530.4	509.7	488.2	467.6
152.5°	593.1	592.2	589.1	580.1	568.3	555.6	539.8	522.8	504.2	484.7	466.2
155°	566.5	566.5	563.9	557.0	548.4	538.0	525.2	511.4	495.9	479.7	464.2
157.5°	543.0	543.0	541.5	536.3	529.9	521.6	510.7	499.2	487.5	474.3	461.9
160°	528.7	528.7	527.8	522.6	517.5	510.6	501.1	491.6	481.4	470.2	459.9
162.5°	514.9	515.6	514.7	509.5	505.8	499.6	492.1	484.1	475.9	466.1	457.8
165°	494.2	495.1	495.9	492.5	489.0	484.7	478.8	473.6	466.7	459.9	453.8
167.5°	477.9	478.6	478.8	476.6	474.8	472.3	467.4	463.5	458.5	453.7	449.7
170°	467.6	467.6	468.5	467.6	465.9	463.3	459.9	457.3	453.0	449.5	446.9
172.5°	457.3	458.7	459.5	458.7	457.6	455.7	453.7	451.8	448.2	445.4	444.2
175°	445.2	446.9	448.7	446.9	446.9	446.9	445.2	444.4	442.6	440.9	440.9
177.5°	438.2	439.5	440.9	440.2	440.9	440.2	440.2	439.5	438.9	438.2	438.2
180°	437.5	437.5	437.5	437.5	437.5	437.5	437.5	437.5	437.5	437.5	437.5



TEST NUMBER: P332885-935

CATALOG NUMBER: SA4XXRDIP-C350D1035U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	521.1	518.8	517.6	515.1	512.0	510.3	508.9	506.7	503.9	501.0	498.9
5°	547.5	542.6	536.5	529.2	522.7	516.3	510.8	505.3	499.0	492.5	486.0
7.5°	574.6	565.1	554.7	542.6	531.0	520.3	510.5	501.2	490.6	481.0	472.4
10°	593.6	580.6	566.1	550.8	535.5	522.3	509.2	497.4	484.4	472.8	463.0
12.5°	608.9	593.6	576.2	557.2	538.7	522.7	507.7	492.3	477.5	464.9	451.9
15°	634.3	613.4	590.0	567.1	543.3	521.4	501.3	483.4	466.4	448.7	436.3
17.5°	651.9	626.9	598.4	571.0	542.9	517.1	493.9	472.5	453.0	434.9	420.1
20°	662.3	634.7	603.1	572.0	540.4	512.9	487.8	464.2	444.0	424.5	409.1
22.5°	668.1	637.7	603.1	570.5	537.8	508.0	480.5	455.9	433.9	414.3	397.4
25°	670.0	637.4	602.2	564.6	528.8	497.2	468.6	442.0	417.5	398.0	380.0
27.5°	667.4	629.0	592.9	554.4	517.4	484.1	454.2	426.1	401.7	380.6	362.2
30°	663.5	622.3	583.6	543.6	506.2	474.2	442.6	415.7	390.2	368.4	349.9
32.5°	655.0	614.2	572.5	531.6	493.6	460.6	430.7	403.6	378.7	356.4	336.7
35°	638.2	596.8	551.6	509.6	472.3	438.1	410.0	383.9	360.1	336.2	315.5
37.5°	616.0	573.9	528.8	482.8	445.5	413.2	387.4	362.9	339.7	317.9	294.9
40°	595.2	556.7	510.2	464.6	426.3	395.1	371.3	349.0	325.6	304.0	281.0
42.5°	570.0	537.2	490.2	444.4	406.6	376.5	354.3	332.6	311.3	290.3	266.3
45°	527.8	502.9	458.9	414.9	376.8	347.0	326.7	307.5	288.8	268.8	246.2
47.5°	479.4	462.6	424.6	379.5	344.3	317.5	297.8	282.1	266.3	246.3	226.5
50°	445.8	435.1	398.4	357.2	323.6	298.9	278.8	264.1	250.8	231.7	214.0
52.5°	410.0	404.2	373.2	333.9	301.4	277.2	260.0	246.8	233.4	217.5	201.0
55°	355.3	358.4	332.2	298.1	267.5	247.2	231.5	220.5	209.1	195.6	182.8
57.5°	299.5	310.7	293.1	263.2	234.5	215.7	203.9	194.7	185.0	173.9	162.9
60°	266.1	275.5	265.5	239.2	214.1	196.7	185.6	178.5	168.9	158.8	150.4
62.5°	233.5	243.6	237.6	216.4	193.1	178.1	168.3	161.7	154.5	145.7	137.0
65°	192.6	199.1	196.2	181.6	165.1	152.2	143.3	138.4	131.8	125.4	117.6
67.5°	147.5	160.1	158.4	150.6	136.4	126.3	120.5	116.1	110.2	105.4	100.1
70°	121.2	132.9	132.7	126.3	118.6	109.3	105.1	101.5	96.2	91.5	87.2
72.5°	99.3	109.9	111.5	106.6	101.3	94.2	90.3	87.8	82.7	79.5	75.9
75°	69.5	77.2	79.3	79.3	76.8	73.2	69.7	68.0	64.4	61.6	59.5
77.5°	45.5	50.5	53.6	54.3	54.8	53.5	50.6	49.5	46.7	45.7	43.7
80°	32.2	35.5	39.1	40.4	41.3	41.0	39.8	38.9	36.2	35.2	34.4
82.5°	22.2	24.0	27.0	29.8	29.4	30.6	29.4	28.8	26.8	26.4	25.7
85°	11.6	11.8	12.2	14.0	15.1	15.5	15.7	15.3	14.6	14.6	13.3
87.5°	6.3	6.1	5.4	5.4	5.4	5.9	5.9	5.7	5.6	5.6	5.3
90°	12.1	12.1	6.9	6.9	6.0	5.2	2.6	0.9	2.6	5.2	6.0
92.5°	173.7	106.9	63.3	45.4	32.8	22.4	14.3	9.8	14.3	22.4	32.8
95°	323.2	182.2	107.5	71.4	50.7	39.5	30.9	28.3	30.9	39.5	50.7
97.5°	290.5	174.2	116.6	86.3	68.6	58.3	50.9	50.9	50.9	58.3	68.6
100°	273.4	176.2	125.5	98.0	81.6	71.4	65.3	65.3	65.3	71.4	81.6
102.5°	268.5	183.0	137.2	111.1	95.4	85.8	80.4	79.0	80.4	85.8	95.4
105°	270.8	199.4	158.2	133.2	117.8	107.5	103.1	100.6	103.1	107.5	117.8
107.5°	283.4	218.5	180.6	156.1	141.3	130.3	126.1	124.3	126.1	130.3	141.3
110°	293.1	232.9	195.1	171.9	156.4	146.1	141.8	140.1	141.8	146.1	156.4



TEST NUMBER: P332885-935

CATALOG NUMBER: SA4XXRDIP-C350D1035U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	303.4	246.7	210.3	187.0	171.6	162.0	157.0	155.2	157.0	162.0	171.6
115°	319.8	268.2	233.8	210.6	194.2	185.6	179.6	177.1	179.6	185.6	194.2
117.5°	336.4	289.0	256.3	232.2	217.0	207.5	202.2	199.8	202.2	207.5	217.0
120°	348.1	303.4	270.8	246.7	232.0	222.7	216.6	214.9	216.6	222.7	232.0
122.5°	359.1	317.2	284.5	261.1	245.1	236.3	230.3	228.7	230.3	236.3	245.1
125°	375.7	336.0	305.1	281.0	264.8	255.3	250.1	246.7	250.1	255.3	264.8
127.5°	389.9	353.6	323.7	299.5	282.4	271.6	265.4	262.7	265.4	271.6	282.4
130°	398.8	365.3	336.0	311.2	294.8	281.9	275.1	271.6	275.1	281.9	294.8
132.5°	407.8	375.0	345.7	322.2	304.4	292.2	283.3	280.5	283.3	292.2	304.4
135°	419.5	388.5	360.2	337.8	319.8	305.1	296.5	293.1	296.5	305.1	319.8
137.5°	427.7	398.8	372.4	351.0	332.3	318.4	308.9	305.7	308.9	318.4	332.3
140°	433.2	405.7	380.0	359.3	341.2	326.7	317.2	314.6	317.2	326.7	341.2
142.5°	437.3	411.9	386.8	366.9	349.5	335.5	326.8	324.3	326.8	335.5	349.5
145°	441.8	418.6	396.2	377.4	361.0	349.0	340.4	337.8	340.4	349.0	361.0
147.5°	445.7	425.5	404.5	387.4	373.9	361.5	354.0	353.1	354.0	361.5	373.9
150°	447.8	429.0	410.0	393.6	380.8	370.5	363.6	362.7	363.6	370.5	380.8
152.5°	449.2	431.7	414.8	399.8	388.3	378.8	371.9	371.7	371.9	378.8	388.3
155°	450.4	435.8	421.2	408.3	398.8	390.2	385.0	384.2	385.0	390.2	398.8
157.5°	450.4	438.7	426.4	416.2	407.9	401.2	396.4	396.4	396.4	401.2	407.9
160°	450.4	440.1	429.8	420.3	413.5	407.4	404.0	404.0	404.0	407.4	413.5
162.5°	450.4	441.4	431.9	424.5	418.3	412.9	410.2	410.9	410.2	412.9	418.3
165°	448.7	441.8	434.0	429.0	424.6	420.3	418.6	418.6	418.6	420.3	424.6
167.5°	446.6	441.6	435.9	432.0	429.6	426.4	425.5	426.4	425.5	426.4	429.6
170°	445.2	440.9	436.6	434.0	432.4	429.8	429.0	429.8	429.0	429.8	432.4
172.5°	443.8	440.2	437.3	435.4	434.4	432.5	432.4	433.2	432.4	432.5	434.4
175°	441.8	439.2	437.5	437.5	436.6	435.8	435.8	436.6	435.8	435.8	436.6
177.5°	439.5	438.2	437.5	437.5	437.5	436.8	437.5	438.2	437.5	436.8	437.5
180°	437.5	437.5	437.5	437.5	437.5	437.5	437.5	437.5	437.5	437.5	437.5



TEST NUMBER: P332885-935

CATALOG NUMBER: SA4XXRDIP-C350D1035U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	496.6	495.0	492.9	490.4	487.5	484.9	483.7	484.7	485.3	483.9	483.7
5°	481.5	476.4	472.3	466.2	461.3	457.3	454.4	453.1	453.6	450.3	449.5
7.5°	464.5	458.5	451.8	444.5	437.8	431.8	428.7	427.0	423.4	422.0	419.5
10°	453.6	445.5	438.9	430.3	422.6	415.5	412.0	409.1	405.7	404.1	400.6
12.5°	442.4	432.9	425.7	416.8	408.9	400.4	397.0	391.8	386.3	382.9	378.4
15°	426.5	415.1	406.3	395.7	386.3	376.6	367.8	358.0	354.4	346.6	342.2
17.5°	407.9	396.4	385.6	371.3	356.9	344.7	335.4	326.0	320.4	315.5	313.1
20°	395.7	385.1	370.1	353.5	337.4	324.0	316.4	310.3	304.2	300.7	298.3
22.5°	384.2	370.6	353.1	335.3	319.2	308.7	302.3	296.0	291.0	287.7	284.5
25°	364.7	347.0	328.5	308.1	297.1	287.9	281.0	275.9	272.9	268.5	266.9
27.5°	344.8	323.3	302.9	289.2	277.8	269.3	263.3	259.5	255.6	252.9	250.7
30°	329.5	307.7	289.4	276.3	264.7	257.8	252.9	248.4	245.3	243.1	241.5
32.5°	314.4	292.6	277.2	263.1	253.9	247.2	241.9	238.6	236.2	233.3	232.3
35°	292.4	273.0	259.6	246.9	237.6	231.5	227.4	223.9	221.9	221.1	220.5
37.5°	271.3	255.5	241.0	230.7	222.3	217.5	212.7	210.9	209.6	208.1	208.8
40°	258.0	243.1	230.2	219.3	212.5	207.2	204.4	202.3	201.1	201.1	201.1
42.5°	246.4	231.9	219.3	209.5	202.8	198.3	195.1	193.4	193.0	192.8	193.8
45°	228.4	215.0	202.3	194.2	188.5	184.0	182.2	180.7	180.7	181.6	181.8
47.5°	210.6	198.0	187.9	178.7	173.5	170.7	169.1	168.4	168.5	169.3	170.2
50°	199.7	187.3	177.3	169.1	164.3	161.6	160.1	159.7	160.1	160.1	161.6
52.5°	187.8	176.7	166.9	160.0	154.5	152.0	151.2	150.6	150.8	151.5	152.1
55°	170.4	160.4	151.0	144.5	140.4	138.8	136.9	137.2	136.7	137.2	137.2
57.5°	152.8	143.9	135.2	130.0	126.4	124.1	122.1	122.6	122.0	121.9	121.6
60°	141.6	131.8	124.9	120.2	116.1	114.1	112.3	112.7	112.1	111.7	110.8
62.5°	129.4	121.2	114.6	110.1	106.9	104.5	102.6	102.3	100.8	99.4	97.6
65°	111.7	105.0	99.0	94.8	91.7	89.9	88.4	87.2	84.1	80.9	79.3
67.5°	94.5	89.5	84.0	80.4	77.9	75.6	72.8	70.8	67.9	66.1	65.1
70°	83.3	78.7	74.0	70.5	67.8	65.6	62.6	61.1	59.1	58.3	57.3
72.5°	72.8	68.4	64.1	60.9	58.1	56.3	53.9	52.5	51.6	51.2	50.3
75°	56.7	53.2	49.9	47.1	44.9	43.6	42.6	41.6	41.2	39.3	38.3
77.5°	41.3	39.0	37.0	35.0	33.4	32.5	30.6	29.4	28.8	27.9	27.6
80°	32.2	30.6	28.5	27.3	25.1	24.3	23.4	23.2	23.0	22.8	22.6
82.5°	24.2	22.6	20.6	19.8	19.2	18.7	18.3	18.0	17.8	17.9	17.9
85°	12.2	11.5	11.5	11.2	11.0	10.8	10.6	10.6	10.4	10.6	10.4
87.5°	5.4	5.3	6.3	6.0	6.5	6.8	6.5	6.7	7.0	6.9	6.9
90°	6.9	6.9	12.1	12.1	13.8	15.5	14.6	15.5	16.4	17.2	17.2
92.5°	45.4	63.3	106.9	173.7	238.6	272.7	227.1	168.8	127.1	101.1	83.9
95°	71.4	107.5	182.2	323.2	528.7	700.5	720.3	636.9	503.7	388.5	305.1
97.5°	86.3	116.6	174.2	290.5	494.7	737.8	904.9	941.1	891.5	807.4	717.7
100°	98.0	125.5	176.2	273.4	448.7	691.0	911.1	1036.6	1053.8	1011.7	948.0
102.5°	111.1	137.2	183.0	268.5	417.8	632.7	859.5	1031.8	1117.1	1129.3	1102.8
105°	133.2	158.2	199.4	270.8	391.1	563.9	765.9	962.7	1111.4	1196.4	1231.7
107.5°	156.1	180.6	218.5	283.4	386.2	525.4	690.2	864.5	1022.9	1142.7	1219.3
110°	171.9	195.1	232.9	293.1	387.6	512.3	652.4	805.4	954.1	1078.7	1173.3



TEST NUMBER: P332885-935

CATALOG NUMBER: SA4XXRDIP-C350D1035U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	187.0	210.3	246.7	303.4	391.8	506.1	631.1	762.1	893.5	1011.3	1105.9
115°	210.6	233.8	268.2	319.8	399.7	502.8	611.1	718.6	824.3	924.9	1007.4
117.5°	232.2	256.3	289.0	336.4	408.1	502.0	602.2	697.2	784.8	863.8	933.8
120°	246.7	270.8	303.4	348.1	414.3	502.0	597.4	687.6	767.6	836.4	897.3
122.5°	261.1	284.5	317.2	359.1	420.5	501.3	591.9	679.4	756.6	819.2	872.6
125°	281.0	305.1	336.0	375.7	429.8	500.2	582.8	665.3	739.2	798.5	845.8
127.5°	299.5	323.7	353.6	389.9	437.1	498.3	570.6	648.1	718.8	777.9	822.8
130°	311.2	336.0	365.3	398.8	442.6	497.7	563.0	634.4	702.2	760.7	806.2
132.5°	322.2	345.7	375.0	407.8	447.5	497.0	556.1	619.9	683.7	740.7	786.4
135°	337.8	360.2	388.5	419.5	454.7	495.9	545.8	599.9	655.8	708.3	751.2
137.5°	351.0	372.4	398.8	427.7	459.0	495.8	536.8	581.9	629.2	673.4	712.2
140°	359.3	380.0	405.7	433.2	462.4	495.1	532.1	571.6	612.0	650.7	686.7
142.5°	366.9	386.8	411.9	437.3	465.2	495.1	528.0	562.0	597.5	630.8	662.0
145°	377.4	396.2	418.6	441.8	466.7	493.4	520.9	548.4	577.6	603.4	627.5
147.5°	387.4	404.5	425.5	445.7	467.6	490.3	514.5	537.2	560.4	581.1	599.9
150°	393.6	410.0	429.0	447.8	467.6	488.2	509.7	530.4	550.1	567.3	582.8
152.5°	399.8	414.8	431.7	449.2	466.2	484.7	504.2	522.8	539.8	555.6	568.3
155°	408.3	421.2	435.8	450.4	464.2	479.7	495.9	511.4	525.2	538.0	548.4
157.5°	416.2	426.4	438.7	450.4	461.9	474.3	487.5	499.2	510.7	521.6	529.9
160°	420.3	429.8	440.1	450.4	459.9	470.2	481.4	491.6	501.1	510.6	517.5
162.5°	424.5	431.9	441.4	450.4	457.8	466.1	475.9	484.1	492.1	499.6	505.8
165°	429.0	434.0	441.8	448.7	453.8	459.9	466.7	473.6	478.8	484.7	489.0
167.5°	432.0	435.9	441.6	446.6	449.7	453.7	458.5	463.5	467.4	472.3	474.8
170°	434.0	436.6	440.9	445.2	446.9	449.5	453.0	457.3	459.9	463.3	465.9
172.5°	435.4	437.3	440.2	443.8	444.2	445.4	448.2	451.8	453.7	455.7	457.6
175°	437.5	437.5	439.2	441.8	440.9	440.9	442.6	444.4	445.2	446.9	446.9
177.5°	437.5	437.5	438.2	439.5	438.2	438.2	438.9	439.5	440.2	440.2	440.9
180°	437.5	437.5	437.5	437.5	437.5	437.5	437.5	437.5	437.5	437.5	437.5



TEST NUMBER: P332885-935

CATALOG NUMBER: SA4XXRDIP-C350D1035U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	482.8	483.1	482.0	481.6	482.0	483.1	482.8	483.7	483.9	485.3	484.7
5°	447.9	447.5	446.4	446.7	446.4	447.5	447.9	449.5	450.3	453.6	453.1
7.5°	418.0	416.5	416.9	415.3	416.9	416.5	418.0	419.5	422.0	423.4	427.0
10°	399.8	397.5	395.7	394.1	395.7	397.5	399.8	400.6	404.1	405.7	409.1
12.5°	374.9	372.9	370.5	370.9	370.5	372.9	374.9	378.4	382.9	386.3	391.8
15°	339.5	336.4	331.6	332.2	331.6	336.4	339.5	342.2	346.6	354.4	358.0
17.5°	309.5	309.5	307.3	307.9	307.3	309.5	309.5	313.1	315.5	320.4	326.0
20°	294.0	292.7	292.8	292.2	292.8	292.7	294.0	298.3	300.7	304.2	310.3
22.5°	283.3	281.5	280.1	278.9	280.1	281.5	283.3	284.5	287.7	291.0	296.0
25°	265.1	263.9	262.1	261.7	262.1	263.9	265.1	266.9	268.5	272.9	275.9
27.5°	249.1	248.9	248.1	247.2	248.1	248.9	249.1	250.7	252.9	255.6	259.5
30°	239.9	239.4	239.0	238.4	239.0	239.4	239.9	241.5	243.1	245.3	248.4
32.5°	231.5	231.3	230.8	230.9	230.8	231.3	231.5	232.3	233.3	236.2	238.6
35°	219.6	219.5	219.0	218.9	219.0	219.5	219.6	220.5	221.1	221.9	223.9
37.5°	208.6	209.1	208.9	208.8	208.9	209.1	208.6	208.8	208.1	209.6	210.9
40°	201.0	201.1	201.6	201.3	201.6	201.1	201.0	201.1	201.1	201.1	202.3
42.5°	194.6	194.6	195.2	194.5	195.2	194.6	194.6	193.8	192.8	193.0	193.4
45°	183.2	184.4	184.2	184.2	184.2	184.4	183.2	181.8	181.6	180.7	180.7
47.5°	170.7	171.9	172.1	172.0	172.1	171.9	170.7	170.2	169.3	168.5	168.4
50°	162.6	162.2	162.8	162.6	162.8	162.2	162.6	161.6	160.1	160.1	159.7
52.5°	152.7	152.7	152.7	152.5	152.7	152.7	152.7	152.1	151.5	150.8	150.6
55°	137.3	137.6	137.2	137.3	137.2	137.6	137.3	137.2	137.2	136.7	137.2
57.5°	120.7	119.8	120.1	119.7	120.1	119.8	120.7	121.6	121.9	122.0	122.6
60°	108.8	107.2	106.8	106.0	106.8	107.2	108.8	110.8	111.7	112.1	112.7
62.5°	95.5	94.3	92.9	93.6	92.9	94.3	95.5	97.6	99.4	100.8	102.3
65°	77.7	76.8	76.2	77.1	76.2	76.8	77.7	79.3	80.9	84.1	87.2
67.5°	64.2	63.8	63.8	63.5	63.8	63.8	64.2	65.1	66.1	67.9	70.8
70°	57.3	56.7	56.7	56.2	56.7	56.7	57.3	57.3	58.3	59.1	61.1
72.5°	50.1	49.5	49.7	49.4	49.7	49.5	50.1	50.3	51.2	51.6	52.5
75°	37.1	36.1	36.1	36.2	36.1	36.1	37.1	38.3	39.3	41.2	41.6
77.5°	27.6	27.5	27.7	27.4	27.7	27.5	27.6	27.6	27.9	28.8	29.4
80°	22.6	22.4	22.2	22.8	22.2	22.4	22.6	22.6	22.8	23.0	23.2
82.5°	17.6	17.6	17.5	18.3	17.5	17.6	17.6	17.9	17.9	17.8	18.0
85°	10.6	10.2	10.6	10.2	10.6	10.2	10.6	10.4	10.6	10.4	10.6
87.5°	7.3	7.4	7.1	7.2	7.1	7.4	7.3	6.9	6.9	7.0	6.7
90°	18.1	18.9	18.1	18.1	18.1	18.9	18.1	17.2	17.2	16.4	15.5
92.5°	73.8	69.1	66.2	66.2	66.2	69.1	73.8	83.9	101.1	127.1	168.8
95°	263.0	236.3	220.9	209.7	220.9	236.3	263.0	305.1	388.5	503.7	636.9
97.5°	656.0	604.2	578.5	560.6	578.5	604.2	656.0	717.7	807.4	891.5	941.1
100°	873.3	820.9	795.0	788.2	795.0	820.9	873.3	948.0	1011.7	1053.8	1036.6
102.5°	1056.9	1018.9	991.8	986.3	991.8	1018.9	1056.9	1102.8	1129.3	1117.1	1031.8
105°	1233.5	1226.6	1214.5	1209.4	1214.5	1226.6	1233.5	1231.7	1196.4	1111.4	962.7
107.5°	1261.8	1281.4	1290.0	1292.3	1290.0	1281.4	1261.8	1219.3	1142.7	1022.9	864.5
110°	1234.3	1270.4	1285.9	1293.7	1285.9	1270.4	1234.3	1173.3	1078.7	954.1	805.4



TEST NUMBER: P332885-935

CATALOG NUMBER: SA4XXRDIP-C350D1035U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1175.2	1218.8	1240.5	1253.0	1240.5	1218.8	1175.2	1105.9	1011.3	893.5	762.1
115°	1075.3	1126.9	1154.3	1161.2	1154.3	1126.9	1075.3	1007.4	924.9	824.3	718.6
117.5°	991.8	1035.1	1062.9	1068.2	1062.9	1035.1	991.8	933.8	863.8	784.8	697.2
120°	946.3	984.2	1006.5	1016.0	1006.5	984.2	946.3	897.3	836.4	767.6	687.6
122.5°	914.0	946.3	965.3	974.7	965.3	946.3	914.0	872.6	819.2	756.6	679.4
125°	880.2	905.1	921.4	926.6	921.4	905.1	880.2	845.8	798.5	739.2	665.3
127.5°	857.3	879.5	893.2	898.4	893.2	879.5	857.3	822.8	777.9	718.8	648.1
130°	841.5	863.0	876.8	881.9	876.8	863.0	841.5	806.2	760.7	702.2	634.4
132.5°	820.9	845.1	858.2	863.3	858.2	845.1	820.9	786.4	740.7	683.7	619.9
135°	785.7	809.7	823.5	828.6	823.5	809.7	785.7	751.2	708.3	655.8	599.9
137.5°	744.3	768.1	779.5	785.7	779.5	768.1	744.3	712.2	673.4	629.2	581.9
140°	716.9	735.8	747.8	754.7	747.8	735.8	716.9	686.7	650.7	612.0	571.6
142.5°	688.6	706.2	716.9	721.7	716.9	706.2	688.6	662.0	630.8	597.5	562.0
145°	648.9	663.6	672.2	676.5	672.2	663.6	648.9	627.5	603.4	577.6	548.4
147.5°	615.8	628.4	634.9	636.4	634.9	628.4	615.8	599.9	581.1	560.4	537.2
150°	596.5	607.7	612.9	613.7	612.9	607.7	596.5	582.8	567.3	550.1	530.4
152.5°	580.1	589.1	592.2	593.1	592.2	589.1	580.1	568.3	555.6	539.8	522.8
155°	557.0	563.9	566.5	566.5	566.5	563.9	557.0	548.4	538.0	525.2	511.4
157.5°	536.3	541.5	543.0	543.0	543.0	541.5	536.3	529.9	521.6	510.7	499.2
160°	522.6	527.8	528.7	528.7	528.7	527.8	522.6	517.5	510.6	501.1	491.6
162.5°	509.5	514.7	515.6	514.9	515.6	514.7	509.5	505.8	499.6	492.1	484.1
165°	492.5	495.9	495.1	494.2	495.1	495.9	492.5	489.0	484.7	478.8	473.6
167.5°	476.6	478.8	478.6	477.9	478.6	478.8	476.6	474.8	472.3	467.4	463.5
170°	467.6	468.5	467.6	467.6	467.6	468.5	467.6	465.9	463.3	459.9	457.3
172.5°	458.7	459.5	458.7	457.3	458.7	459.5	458.7	457.6	455.7	453.7	451.8
175°	446.9	448.7	446.9	445.2	446.9	448.7	446.9	446.9	446.9	445.2	444.4
177.5°	440.2	440.9	439.5	438.2	439.5	440.9	440.2	440.9	440.2	440.2	439.5
180°	437.5	437.5	437.5	437.5	437.5	437.5	437.5	437.5	437.5	437.5	437.5



TEST NUMBER: P332885-935

CATALOG NUMBER: SA4XXRDIP-C350D1035U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	483.7	484.9	487.5	490.4	492.9	495.0	496.6	498.9	501.0	503.9	506.7
5°	454.4	457.3	461.3	466.2	472.3	476.4	481.5	486.0	492.5	499.0	505.3
7.5°	428.7	431.8	437.8	444.5	451.8	458.5	464.5	472.4	481.0	490.6	501.2
10°	412.0	415.5	422.6	430.3	438.9	445.5	453.6	463.0	472.8	484.4	497.4
12.5°	397.0	400.4	408.9	416.8	425.7	432.9	442.4	451.9	464.9	477.5	492.3
15°	367.8	376.6	386.3	395.7	406.3	415.1	426.5	436.3	448.7	466.4	483.4
17.5°	335.4	344.7	356.9	371.3	385.6	396.4	407.9	420.1	434.9	453.0	472.5
20°	316.4	324.0	337.4	353.5	370.1	385.1	395.7	409.1	424.5	444.0	464.2
22.5°	302.3	308.7	319.2	335.3	353.1	370.6	384.2	397.4	414.3	433.9	455.9
25°	281.0	287.9	297.1	308.1	328.5	347.0	364.7	380.0	398.0	417.5	442.0
27.5°	263.3	269.3	277.8	289.2	302.9	323.3	344.8	362.2	380.6	401.7	426.1
30°	252.9	257.8	264.7	276.3	289.4	307.7	329.5	349.9	368.4	390.2	415.7
32.5°	241.9	247.2	253.9	263.1	277.2	292.6	314.4	336.7	356.4	378.7	403.6
35°	227.4	231.5	237.6	246.9	259.6	273.0	292.4	315.5	336.2	360.1	383.9
37.5°	212.7	217.5	222.3	230.7	241.0	255.5	271.3	294.9	317.9	339.7	362.9
40°	204.4	207.2	212.5	219.3	230.2	243.1	258.0	281.0	304.0	325.6	349.0
42.5°	195.1	198.3	202.8	209.5	219.3	231.9	246.4	266.3	290.3	311.3	332.6
45°	182.2	184.0	188.5	194.2	202.3	215.0	228.4	246.2	268.8	288.8	307.5
47.5°	169.1	170.7	173.5	178.7	187.9	198.0	210.6	226.5	246.3	266.3	282.1
50°	160.1	161.6	164.3	169.1	177.3	187.3	199.7	214.0	231.7	250.8	264.1
52.5°	151.2	152.0	154.5	160.0	166.9	176.7	187.8	201.0	217.5	233.4	246.8
55°	136.9	138.8	140.4	144.5	151.0	160.4	170.4	182.8	195.6	209.1	220.5
57.5°	122.1	124.1	126.4	130.0	135.2	143.9	152.8	162.9	173.9	185.0	194.7
60°	112.3	114.1	116.1	120.2	124.9	131.8	141.6	150.4	158.8	168.9	178.5
62.5°	102.6	104.5	106.9	110.1	114.6	121.2	129.4	137.0	145.7	154.5	161.7
65°	88.4	89.9	91.7	94.8	99.0	105.0	111.7	117.6	125.4	131.8	138.4
67.5°	72.8	75.6	77.9	80.4	84.0	89.5	94.5	100.1	105.4	110.2	116.1
70°	62.6	65.6	67.8	70.5	74.0	78.7	83.3	87.2	91.5	96.2	101.5
72.5°	53.9	56.3	58.1	60.9	64.1	68.4	72.8	75.9	79.5	82.7	87.8
75°	42.6	43.6	44.9	47.1	49.9	53.2	56.7	59.5	61.6	64.4	68.0
77.5°	30.6	32.5	33.4	35.0	37.0	39.0	41.3	43.7	45.7	46.7	49.5
80°	23.4	24.3	25.1	27.3	28.5	30.6	32.2	34.4	35.2	36.2	38.9
82.5°	18.3	18.7	19.2	19.8	20.6	22.6	24.2	25.7	26.4	26.8	28.8
85°	10.6	10.8	11.0	11.2	11.5	11.5	12.2	13.3	14.6	14.6	15.3
87.5°	6.5	6.8	6.5	6.0	6.3	5.3	5.4	5.3	5.6	5.6	5.7
90°	14.6	15.5	13.8	12.1	12.1	6.9	6.9	6.0	5.2	2.6	0.9
92.5°	227.1	272.7	238.6	173.7	106.9	63.3	45.4	32.8	22.4	14.3	9.8
95°	720.3	700.5	528.7	323.2	182.2	107.5	71.4	50.7	39.5	30.9	28.3
97.5°	904.9	737.8	494.7	290.5	174.2	116.6	86.3	68.6	58.3	50.9	50.9
100°	911.1	691.0	448.7	273.4	176.2	125.5	98.0	81.6	71.4	65.3	65.3
102.5°	859.5	632.7	417.8	268.5	183.0	137.2	111.1	95.4	85.8	80.4	79.0
105°	765.9	563.9	391.1	270.8	199.4	158.2	133.2	117.8	107.5	103.1	100.6
107.5°	690.2	525.4	386.2	283.4	218.5	180.6	156.1	141.3	130.3	126.1	124.3
110°	652.4	512.3	387.6	293.1	232.9	195.1	171.9	156.4	146.1	141.8	140.1



TEST NUMBER: P332885-935

CATALOG NUMBER: SA4XXRDIP-C350D1035U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	631.1	506.1	391.8	303.4	246.7	210.3	187.0	171.6	162.0	157.0	155.2
115°	611.1	502.8	399.7	319.8	268.2	233.8	210.6	194.2	185.6	179.6	177.1
117.5°	602.2	502.0	408.1	336.4	289.0	256.3	232.2	217.0	207.5	202.2	199.8
120°	597.4	502.0	414.3	348.1	303.4	270.8	246.7	232.0	222.7	216.6	214.9
122.5°	591.9	501.3	420.5	359.1	317.2	284.5	261.1	245.1	236.3	230.3	228.7
125°	582.8	500.2	429.8	375.7	336.0	305.1	281.0	264.8	255.3	250.1	246.7
127.5°	570.6	498.3	437.1	389.9	353.6	323.7	299.5	282.4	271.6	265.4	262.7
130°	563.0	497.7	442.6	398.8	365.3	336.0	311.2	294.8	281.9	275.1	271.6
132.5°	556.1	497.0	447.5	407.8	375.0	345.7	322.2	304.4	292.2	283.3	280.5
135°	545.8	495.9	454.7	419.5	388.5	360.2	337.8	319.8	305.1	296.5	293.1
137.5°	536.8	495.8	459.0	427.7	398.8	372.4	351.0	332.3	318.4	308.9	305.7
140°	532.1	495.1	462.4	433.2	405.7	380.0	359.3	341.2	326.7	317.2	314.6
142.5°	528.0	495.1	465.2	437.3	411.9	386.8	366.9	349.5	335.5	326.8	324.3
145°	520.9	493.4	466.7	441.8	418.6	396.2	377.4	361.0	349.0	340.4	337.8
147.5°	514.5	490.3	467.6	445.7	425.5	404.5	387.4	373.9	361.5	354.0	353.1
150°	509.7	488.2	467.6	447.8	429.0	410.0	393.6	380.8	370.5	363.6	362.7
152.5°	504.2	484.7	466.2	449.2	431.7	414.8	399.8	388.3	378.8	371.9	371.7
155°	495.9	479.7	464.2	450.4	435.8	421.2	408.3	398.8	390.2	385.0	384.2
157.5°	487.5	474.3	461.9	450.4	438.7	426.4	416.2	407.9	401.2	396.4	396.4
160°	481.4	470.2	459.9	450.4	440.1	429.8	420.3	413.5	407.4	404.0	404.0
162.5°	475.9	466.1	457.8	450.4	441.4	431.9	424.5	418.3	412.9	410.2	410.9
165°	466.7	459.9	453.8	448.7	441.8	434.0	429.0	424.6	420.3	418.6	418.6
167.5°	458.5	453.7	449.7	446.6	441.6	435.9	432.0	429.6	426.4	425.5	426.4
170°	453.0	449.5	446.9	445.2	440.9	436.6	434.0	432.4	429.8	429.0	429.8
172.5°	448.2	445.4	444.2	443.8	440.2	437.3	435.4	434.4	432.5	432.4	433.2
175°	442.6	440.9	440.9	441.8	439.2	437.5	437.5	436.6	435.8	435.8	436.6
177.5°	438.9	438.2	438.2	439.5	438.2	437.5	437.5	437.5	436.8	437.5	438.2
180°	437.5	437.5	437.5	437.5	437.5	437.5	437.5	437.5	437.5	437.5	437.5



TEST NUMBER: P332885-935

CATALOG NUMBER: SA4XXRDIP-C350D1035U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	508.9	510.3	512.0	515.1	517.6	518.8	521.1	522.7	522.2	524.5	528.4
5°	510.8	516.3	522.7	529.2	536.5	542.6	547.5	552.4	556.3	560.9	567.9
7.5°	510.5	520.3	531.0	542.6	554.7	565.1	574.6	584.4	593.1	602.6	615.1
10°	509.2	522.3	535.5	550.8	566.1	580.6	593.6	605.8	617.4	629.8	645.6
12.5°	507.7	522.7	538.7	557.2	576.2	593.6	608.9	626.5	641.1	657.1	675.2
15°	501.3	521.4	543.3	567.1	590.0	613.4	634.3	655.9	676.1	695.3	718.1
17.5°	493.9	517.1	542.9	571.0	598.4	626.9	651.9	679.1	699.6	725.4	746.6
20°	487.8	512.9	540.4	572.0	603.1	634.7	662.3	690.0	713.2	739.1	765.9
22.5°	480.5	508.0	537.8	570.5	603.1	637.7	668.1	695.7	724.4	753.5	781.3
25°	468.6	497.2	528.8	564.6	602.2	637.4	670.0	704.2	735.2	766.8	791.7
27.5°	454.2	484.1	517.4	554.4	592.9	629.0	667.4	703.9	735.0	765.4	787.1
30°	442.6	474.2	506.2	543.6	583.6	622.3	663.5	700.0	732.8	760.1	772.3
32.5°	430.7	460.6	493.6	531.6	572.5	614.2	655.0	692.3	722.6	739.0	739.3
35°	410.0	438.1	472.3	509.6	551.6	596.8	638.2	674.9	693.4	694.8	674.9
37.5°	387.4	413.2	445.5	482.8	528.8	573.9	616.0	640.5	646.7	625.9	589.1
40°	371.3	395.1	426.3	464.6	510.2	556.7	595.2	613.1	606.7	573.0	531.8
42.5°	354.3	376.5	406.6	444.4	490.2	537.2	570.0	579.5	562.3	523.5	475.3
45°	326.7	347.0	376.8	414.9	458.9	502.9	527.8	522.9	494.1	448.1	394.1
47.5°	297.8	317.5	344.3	379.5	424.6	462.6	479.4	464.7	423.8	373.2	329.2
50°	278.8	298.9	323.6	357.2	398.4	435.1	445.8	423.4	378.0	329.3	289.0
52.5°	260.0	277.2	301.4	333.9	373.2	404.2	410.0	384.2	337.3	293.6	257.8
55°	231.5	247.2	267.5	298.1	332.2	358.4	355.3	322.2	279.6	242.3	214.1
57.5°	203.9	215.7	234.5	263.2	293.1	310.7	299.5	271.2	231.5	201.0	177.3
60°	185.6	196.7	214.1	239.2	265.5	275.5	266.1	235.4	204.0	176.1	156.1
62.5°	168.3	178.1	193.1	216.4	237.6	243.6	233.5	206.6	178.4	154.5	138.0
65°	143.3	152.2	165.1	181.6	196.2	199.1	192.6	165.1	143.7	123.7	112.3
67.5°	120.5	126.3	136.4	150.6	158.4	160.1	147.5	130.2	111.3	99.1	90.5
70°	105.1	109.3	118.6	126.3	132.7	132.9	121.2	107.4	92.9	82.9	76.6
72.5°	90.3	94.2	101.3	106.6	111.5	109.9	99.3	88.3	76.6	69.1	64.4
75°	69.7	73.2	76.8	79.3	79.3	77.2	69.5	61.3	54.6	50.1	48.7
77.5°	50.6	53.5	54.8	54.3	53.6	50.5	45.5	40.2	37.8	35.7	34.6
80°	39.8	41.0	41.3	40.4	39.1	35.5	32.2	30.0	27.7	26.9	26.5
82.5°	29.4	30.6	29.4	29.8	27.0	24.0	22.2	21.4	20.6	20.2	19.8
85°	15.7	15.5	15.1	14.0	12.2	11.8	11.6	11.5	11.0	11.2	10.8
87.5°	5.9	5.9	5.4	5.4	5.4	6.1	6.3	6.6	7.0	6.6	7.1
90°	2.6	5.2	6.0	6.9	6.9	12.1	12.1	13.8	15.5	14.6	15.5
92.5°	14.3	22.4	32.8	45.4	63.3	106.9	173.7	238.6	272.7	227.1	168.8
95°	30.9	39.5	50.7	71.4	107.5	182.2	323.2	528.7	700.5	720.3	636.9
97.5°	50.9	58.3	68.6	86.3	116.6	174.2	290.5	494.7	737.8	904.9	941.1
100°	65.3	71.4	81.6	98.0	125.5	176.2	273.4	448.7	691.0	911.1	1036.6
102.5°	80.4	85.8	95.4	111.1	137.2	183.0	268.5	417.8	632.7	859.5	1031.8
105°	103.1	107.5	117.8	133.2	158.2	199.4	270.8	391.1	563.9	765.9	962.7
107.5°	126.1	130.3	141.3	156.1	180.6	218.5	283.4	386.2	525.4	690.2	864.5
110°	141.8	146.1	156.4	171.9	195.1	232.9	293.1	387.6	512.3	652.4	805.4



TEST NUMBER: P332885-935

CATALOG NUMBER: SA4XXRDIP-C350D1035U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	157.0	162.0	171.6	187.0	210.3	246.7	303.4	391.8	506.1	631.1	762.1
115°	179.6	185.6	194.2	210.6	233.8	268.2	319.8	399.7	502.8	611.1	718.6
117.5°	202.2	207.5	217.0	232.2	256.3	289.0	336.4	408.1	502.0	602.2	697.2
120°	216.6	222.7	232.0	246.7	270.8	303.4	348.1	414.3	502.0	597.4	687.6
122.5°	230.3	236.3	245.1	261.1	284.5	317.2	359.1	420.5	501.3	591.9	679.4
125°	250.1	255.3	264.8	281.0	305.1	336.0	375.7	429.8	500.2	582.8	665.3
127.5°	265.4	271.6	282.4	299.5	323.7	353.6	389.9	437.1	498.3	570.6	648.1
130°	275.1	281.9	294.8	311.2	336.0	365.3	398.8	442.6	497.7	563.0	634.4
132.5°	283.3	292.2	304.4	322.2	345.7	375.0	407.8	447.5	497.0	556.1	619.9
135°	296.5	305.1	319.8	337.8	360.2	388.5	419.5	454.7	495.9	545.8	599.9
137.5°	308.9	318.4	332.3	351.0	372.4	398.8	427.7	459.0	495.8	536.8	581.9
140°	317.2	326.7	341.2	359.3	380.0	405.7	433.2	462.4	495.1	532.1	571.6
142.5°	326.8	335.5	349.5	366.9	386.8	411.9	437.3	465.2	495.1	528.0	562.0
145°	340.4	349.0	361.0	377.4	396.2	418.6	441.8	466.7	493.4	520.9	548.4
147.5°	354.0	361.5	373.9	387.4	404.5	425.5	445.7	467.6	490.3	514.5	537.2
150°	363.6	370.5	380.8	393.6	410.0	429.0	447.8	467.6	488.2	509.7	530.4
152.5°	371.9	378.8	388.3	399.8	414.8	431.7	449.2	466.2	484.7	504.2	522.8
155°	385.0	390.2	398.8	408.3	421.2	435.8	450.4	464.2	479.7	495.9	511.4
157.5°	396.4	401.2	407.9	416.2	426.4	438.7	450.4	461.9	474.3	487.5	499.2
160°	404.0	407.4	413.5	420.3	429.8	440.1	450.4	459.9	470.2	481.4	491.6
162.5°	410.2	412.9	418.3	424.5	431.9	441.4	450.4	457.8	466.1	475.9	484.1
165°	418.6	420.3	424.6	429.0	434.0	441.8	448.7	453.8	459.9	466.7	473.6
167.5°	425.5	426.4	429.6	432.0	435.9	441.6	446.6	449.7	453.7	458.5	463.5
170°	429.0	429.8	432.4	434.0	436.6	440.9	445.2	446.9	449.5	453.0	457.3
172.5°	432.4	432.5	434.4	435.4	437.3	440.2	443.8	444.2	445.4	448.2	451.8
175°	435.8	435.8	436.6	437.5	437.5	439.2	441.8	440.9	440.9	442.6	444.4
177.5°	437.5	436.8	437.5	437.5	437.5	438.2	439.5	438.2	438.2	438.9	439.5
180°	437.5	437.5	437.5	437.5	437.5	437.5	437.5	437.5	437.5	437.5	437.5



TEST NUMBER: P332885-935

CATALOG NUMBER: SA4XXRDIP-C350D1035U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	530.5	531.2	531.7	533.3	533.5	534.9	533.5
5°	574.5	577.3	581.8	586.3	586.7	589.5	584.4
7.5°	623.6	630.3	634.4	641.6	644.5	646.3	643.3
10°	657.5	663.7	674.5	679.8	685.1	685.9	683.5
12.5°	690.3	700.0	708.5	718.6	718.3	725.5	722.9
15°	734.0	744.0	755.8	767.0	771.0	771.0	774.3
17.5°	765.1	783.4	795.7	804.4	814.1	815.7	814.6
20°	786.2	805.9	819.0	830.3	836.9	838.7	838.7
22.5°	801.8	818.6	831.4	841.6	847.0	849.1	848.5
25°	812.6	827.1	834.8	837.9	839.3	839.0	835.1
27.5°	797.8	797.1	792.3	782.9	775.8	771.5	766.6
30°	769.5	758.8	746.6	733.1	715.8	702.6	698.5
32.5°	727.2	703.4	682.7	660.3	641.7	628.4	622.8
35°	645.6	607.9	577.0	550.2	530.6	518.4	514.3
37.5°	548.6	512.1	474.1	448.0	431.7	419.4	414.8
40°	487.0	447.3	414.1	389.6	372.9	360.8	360.7
42.5°	430.8	392.8	361.5	344.0	326.0	318.0	318.0
45°	352.8	322.4	295.8	282.0	271.2	264.7	262.9
47.5°	292.1	266.9	249.3	238.2	229.5	225.3	222.6
50°	258.0	236.0	221.9	212.3	207.4	202.2	201.7
52.5°	229.6	211.8	200.9	193.1	186.9	183.7	183.8
55°	193.0	178.9	171.2	165.2	160.4	157.9	156.9
57.5°	162.6	152.1	146.4	140.9	138.9	137.0	136.5
60°	143.7	136.6	131.2	126.9	123.9	123.3	123.0
62.5°	128.0	120.5	116.9	113.6	111.3	110.4	110.0
65°	105.6	100.0	96.8	94.1	93.3	91.9	91.7
67.5°	85.1	81.8	79.6	77.8	76.7	76.6	76.6
70°	72.6	70.7	68.9	67.8	67.2	66.8	66.8
72.5°	61.8	60.4	58.9	58.4	58.3	57.9	57.7
75°	47.1	45.6	45.9	44.9	44.0	43.0	42.4
77.5°	33.4	32.4	32.1	32.0	31.3	31.3	31.5
80°	25.9	24.9	24.6	24.9	24.6	24.0	24.0
82.5°	19.7	18.9	18.6	18.5	18.3	18.5	18.2
85°	10.6	10.2	10.2	10.2	10.6	10.4	10.2
87.5°	7.0	7.1	7.1	7.2	7.4	7.1	7.2
90°	16.4	17.2	17.2	18.1	18.9	18.1	18.1
92.5°	127.1	101.1	83.9	73.8	69.1	66.2	66.2
95°	503.7	388.5	305.1	263.0	236.3	220.9	209.7
97.5°	891.5	807.4	717.7	656.0	604.2	578.5	560.6
100°	1053.8	1011.7	948.0	873.3	820.9	795.0	788.2
102.5°	1117.1	1129.3	1102.8	1056.9	1018.9	991.8	986.3
105°	1111.4	1196.4	1231.7	1233.5	1226.6	1214.5	1209.4
107.5°	1022.9	1142.7	1219.3	1261.8	1281.4	1290.0	1292.3
110°	954.1	1078.7	1173.3	1234.3	1270.4	1285.9	1293.7



TEST NUMBER: P332885-935

CATALOG NUMBER: SA4XXRDIP-C350D1035U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	893.5	1011.3	1105.9	1175.2	1218.8	1240.5	1253.0
115°	824.3	924.9	1007.4	1075.3	1126.9	1154.3	1161.2
117.5°	784.8	863.8	933.8	991.8	1035.1	1062.9	1068.2
120°	767.6	836.4	897.3	946.3	984.2	1006.5	1016.0
122.5°	756.6	819.2	872.6	914.0	946.3	965.3	974.7
125°	739.2	798.5	845.8	880.2	905.1	921.4	926.6
127.5°	718.8	777.9	822.8	857.3	879.5	893.2	898.4
130°	702.2	760.7	806.2	841.5	863.0	876.8	881.9
132.5°	683.7	740.7	786.4	820.9	845.1	858.2	863.3
135°	655.8	708.3	751.2	785.7	809.7	823.5	828.6
137.5°	629.2	673.4	712.2	744.3	768.1	779.5	785.7
140°	612.0	650.7	686.7	716.9	735.8	747.8	754.7
142.5°	597.5	630.8	662.0	688.6	706.2	716.9	721.7
145°	577.6	603.4	627.5	648.9	663.6	672.2	676.5
147.5°	560.4	581.1	599.9	615.8	628.4	634.9	636.4
150°	550.1	567.3	582.8	596.5	607.7	612.9	613.7
152.5°	539.8	555.6	568.3	580.1	589.1	592.2	593.1
155°	525.2	538.0	548.4	557.0	563.9	566.5	566.5
157.5°	510.7	521.6	529.9	536.3	541.5	543.0	543.0
160°	501.1	510.6	517.5	522.6	527.8	528.7	528.7
162.5°	492.1	499.6	505.8	509.5	514.7	515.6	514.9
165°	478.8	484.7	489.0	492.5	495.9	495.1	494.2
167.5°	467.4	472.3	474.8	476.6	478.8	478.6	477.9
170°	459.9	463.3	465.9	467.6	468.5	467.6	467.6
172.5°	453.7	455.7	457.6	458.7	459.5	458.7	457.3
175°	445.2	446.9	446.9	446.9	448.7	446.9	445.2
177.5°	440.2	440.2	440.9	440.2	440.9	439.5	438.2
180°	437.5	437.5	437.5	437.5	437.5	437.5	437.5

(END OF REPORT)