

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332871-935

Luminaire Tested: **SA4XXRDIP-C350D590U935-4F0-1E-UDD-A**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332871-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C350D590U935-4F0-1E-UDD-A
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 590 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3311.5 lumens
Efficiency: N/A
Efficacy: 129.4 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 25.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332871-935
CATALOG NUMBER: SA4XXRDIP-C350D590U935-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332871-935

CATALOG NUMBER: SA4XXRDIP-C350D590U935-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	95	95	95	95	77	77	77	61	61	61	46	46	46	39
1	96	91	88	84	87	83	80	77	68	66	64	54	52	51	41	40	39	33
2	87	80	74	70	79	73	68	64	60	56	53	48	45	43	36	35	34	28
3	80	71	64	58	72	65	59	54	53	49	45	42	39	37	33	31	29	24
4	73	63	55	49	66	57	51	46	47	43	39	38	35	32	29	27	25	21
5	67	56	48	42	61	51	45	39	42	37	34	34	31	28	27	24	22	19
6	62	50	42	37	56	46	39	34	38	33	29	31	27	24	24	22	20	17
7	57	45	38	32	52	42	35	30	35	30	26	28	24	22	22	19	17	15
8	53	41	34	29	48	38	31	27	32	27	23	26	22	19	20	18	16	13
9	49	38	30	25	45	35	28	24	29	24	21	24	20	17	19	16	14	12
10	46	34	27	23	42	32	26	21	27	22	18	22	18	16	17	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4083	4083	4083	4083
5°	4736	4095	3620	4095
10°	5603	4077	3231	4077
15°	6471	4040	2776	4040
20°	7205	3988	2510	3988
25°	7439	3937	2331	3937
30°	6511	3875	2222	3875
35°	5069	3783	2157	3783
40°	3801	3678	2121	3678
45°	3001	3511	2103	3511
50°	2533	3317	2042	3317
55°	2208	3103	1932	3103
60°	1986	2882	1711	2882
65°	1752	2644	1473	2644
70°	1577	2396	1327	2396
75°	1323	2121	1129	2121
80°	1116	1808	1060	1808
85°	945	1417	945	1417



TEST NUMBER: P332871-935

CATALOG NUMBER: SA4XXRDIP-C350D590U935-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.0	1.5
10°-20°	147.8	4.5
20°-30°	231.2	7.0
30°-40°	257.0	7.8
40°-50°	228.0	6.9
50°-60°	177.7	5.4
60°-70°	116.3	3.5
70°-80°	57.2	1.7
80°-90°	16.0	0.5
90°-100°	22.5	0.7
100°-110°	143.2	4.3
110°-120°	273.9	8.3
120°-130°	347.7	10.5
130°-140°	372.1	11.2
140°-150°	347.9	10.5
150°-160°	280.6	8.5
160°-170°	181.0	5.5
170°-180°	62.4	1.9
0°-30°	428.0	12.9
0°-40°	685.0	20.7
0°-60°	1090.8	32.9
0°-90°	1280.3	38.7
90°-120°	439.6	13.3
90°-150°	1507.3	45.5
90°-180°	2031.0	61.3
0°-180°	3311.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	506	506	506	506	506	
5°	584	505	447	505	584	59
15°	774	483	332	483	774	220
25°	835	442	262	442	835	370
35°	514	384	219	384	514	322
45°	263	308	184	308	263	208
55°	157	220	137	220	157	143
65°	92	138	77	138	92	92
75°	42	68	36	68	42	47
85°	10	15	10	15	10	12
90°	15	2	15	2	15	7
95°	14	27	14	27	14	11
105°	140	148	140	148	140	122
115°	278	276	278	276	278	275
125°	391	388	391	388	391	348
135°	485	481	485	481	485	373
145°	558	555	558	555	558	349
155°	608	609	608	609	608	280
165°	639	642	639	642	639	180
175°	653	657	653	657	653	62
180°	657	657	657	657	657	



TEST NUMBER: P332871-935

CATALOG NUMBER: SA4XXRDIP-C350D590U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	533.5	534.9	533.5	533.3	531.7	531.2	530.5	528.4	524.5	522.2	522.7
5°	584.4	589.5	586.7	586.3	581.8	577.3	574.5	567.9	560.9	556.3	552.4
7.5°	643.3	646.3	644.5	641.6	634.4	630.3	623.6	615.1	602.6	593.1	584.4
10°	683.5	685.9	685.1	679.8	674.5	663.7	657.5	645.6	629.8	617.4	605.8
12.5°	722.9	725.5	718.3	718.6	708.5	700.0	690.3	675.2	657.1	641.1	626.5
15°	774.3	771.0	771.0	767.0	755.8	744.0	734.0	718.1	695.3	676.1	655.9
17.5°	814.6	815.7	814.1	804.4	795.7	783.4	765.1	746.6	725.4	699.6	679.1
20°	838.7	838.7	836.9	830.3	819.0	805.9	786.2	765.9	739.1	713.2	690.0
22.5°	848.5	849.1	847.0	841.6	831.4	818.6	801.8	781.3	753.5	724.4	695.7
25°	835.1	839.0	839.3	837.9	834.8	827.1	812.6	791.7	766.8	735.2	704.2
27.5°	766.6	771.5	775.8	782.9	792.3	797.1	797.8	787.1	765.4	735.0	703.9
30°	698.5	702.6	715.8	733.1	746.6	758.8	769.5	772.3	760.1	732.8	700.0
32.5°	622.8	628.4	641.7	660.3	682.7	703.4	727.2	739.3	739.0	722.6	692.3
35°	514.3	518.4	530.6	550.2	577.0	607.9	645.6	674.9	694.8	693.4	674.9
37.5°	414.8	419.4	431.7	448.0	474.1	512.1	548.6	589.1	625.9	646.7	640.5
40°	360.7	360.8	372.9	389.6	414.1	447.3	487.0	531.8	573.0	606.7	613.1
42.5°	318.0	318.0	326.0	344.0	361.5	392.8	430.8	475.3	523.5	562.3	579.5
45°	262.9	264.7	271.2	282.0	295.8	322.4	352.8	394.1	448.1	494.1	522.9
47.5°	222.6	225.3	229.5	238.2	249.3	266.9	292.1	329.2	373.2	423.8	464.7
50°	201.7	202.2	207.4	212.3	221.9	236.0	258.0	289.0	329.3	378.0	423.4
52.5°	183.8	183.7	186.9	193.1	200.9	211.8	229.6	257.8	293.6	337.3	384.2
55°	156.9	157.9	160.4	165.2	171.2	178.9	193.0	214.1	242.3	279.6	322.2
57.5°	136.5	137.0	138.9	140.9	146.4	152.1	162.6	177.3	201.0	231.5	271.2
60°	123.0	123.3	123.9	126.9	131.2	136.6	143.7	156.1	176.1	204.0	235.4
62.5°	110.0	110.4	111.3	113.6	116.9	120.5	128.0	138.0	154.5	178.4	206.6
65°	91.7	91.9	93.3	94.1	96.8	100.0	105.6	112.3	123.7	143.7	165.1
67.5°	76.6	76.6	76.7	77.8	79.6	81.8	85.1	90.5	99.1	111.3	130.2
70°	66.8	66.8	67.2	67.8	68.9	70.7	72.6	76.6	82.9	92.9	107.4
72.5°	57.7	57.9	58.3	58.4	58.9	60.4	61.8	64.4	69.1	76.6	88.3
75°	42.4	43.0	44.0	44.9	45.9	45.6	47.1	48.7	50.1	54.6	61.3
77.5°	31.5	31.3	31.3	32.0	32.1	32.4	33.4	34.6	35.7	37.8	40.2
80°	24.0	24.0	24.6	24.9	24.6	24.9	25.9	26.5	26.9	27.7	30.0
82.5°	18.2	18.5	18.3	18.5	18.6	18.9	19.7	19.8	20.2	20.6	21.4
85°	10.2	10.4	10.6	10.2	10.2	10.2	10.6	10.8	11.2	11.0	11.5
87.5°	6.5	6.3	6.5	6.4	6.5	6.3	6.3	6.5	6.0	6.1	5.9
90°	14.7	14.6	14.3	14.1	13.9	13.4	12.7	12.1	11.5	10.8	9.9
92.5°	13.5	13.5	13.4	13.4	13.3	13.0	12.4	11.7	11.1	10.4	9.6
95°	14.2	14.1	14.0	13.9	13.8	13.4	12.7	12.1	11.5	10.8	10.7
97.5°	13.8	13.6	13.5	13.4	13.3	13.3	13.2	13.1	13.0	13.0	25.1
100°	13.8	13.6	13.5	13.4	13.3	14.2	16.0	17.9	19.7	21.6	36.7
102.5°	14.1	14.1	14.1	14.1	14.0	24.0	44.1	64.1	84.1	104.1	106.1
105°	140.0	143.9	147.8	151.8	155.7	157.1	156.2	155.2	154.2	153.3	152.7
107.5°	195.1	194.7	194.2	193.8	193.4	193.0	192.5	192.0	191.6	191.1	190.3
110°	219.0	218.7	218.3	218.1	217.7	217.5	217.2	217.1	216.8	216.6	215.9



TEST NUMBER: P332871-935

CATALOG NUMBER: SA4XXRDIP-C350D590U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	243.0	242.6	242.2	241.8	241.3	241.2	241.3	241.3	241.3	241.3	241.1
115°	278.0	278.0	278.0	278.0	278.0	277.8	277.7	277.4	277.2	277.0	277.1
117.5°	313.6	313.6	313.7	313.7	313.7	313.7	313.8	313.8	313.9	313.9	313.7
120°	336.0	336.1	336.4	336.6	336.8	336.8	336.6	336.4	336.1	336.0	336.0
122.5°	357.9	358.2	358.3	358.6	358.8	358.9	358.7	358.6	358.4	358.3	358.2
125°	391.0	390.8	390.7	390.6	390.5	390.3	389.9	389.6	389.3	389.0	389.2
127.5°	419.9	420.0	420.1	420.2	420.3	420.3	420.4	420.5	420.5	420.6	420.1
130°	439.5	439.5	439.5	439.5	439.5	439.5	439.4	439.3	439.2	439.1	438.8
132.5°	457.6	457.7	457.8	457.9	458.0	458.0	457.9	457.8	457.6	457.5	457.1
135°	484.7	484.6	484.3	484.1	483.9	483.6	483.5	483.2	483.0	482.8	482.3
137.5°	507.9	508.0	508.1	508.2	508.2	508.1	507.9	507.6	507.4	507.1	506.7
140°	524.0	523.9	523.8	523.7	523.6	523.4	523.1	522.7	522.4	522.1	521.9
142.5°	537.4	537.4	537.4	537.4	537.4	537.2	536.9	536.7	536.5	536.2	536.1
145°	557.9	557.8	557.5	557.2	557.1	556.9	556.8	556.6	556.6	556.5	556.5
147.5°	574.9	574.8	574.7	574.6	574.5	574.4	574.3	574.2	574.1	574.0	574.1
150°	585.9	585.8	585.7	585.6	585.5	585.4	585.4	585.4	585.4	585.4	585.6
152.5°	595.4	595.4	595.5	595.6	595.6	595.6	595.4	595.2	595.0	594.9	595.0
155°	608.0	608.4	608.6	609.0	609.3	609.2	608.8	608.4	608.0	607.5	607.9
157.5°	618.6	619.2	619.7	620.4	620.9	620.9	620.4	619.7	619.2	618.6	619.0
160°	625.7	626.4	627.0	627.7	628.4	628.4	627.7	627.0	626.4	625.7	625.8
162.5°	631.2	632.0	632.7	633.4	634.2	634.2	633.5	632.9	632.2	631.6	631.7
165°	638.9	640.0	640.9	641.9	642.9	643.0	642.0	641.2	640.3	639.5	639.5
167.5°	644.8	645.8	647.0	648.1	649.1	649.2	648.2	647.3	646.4	645.3	645.4
170°	648.3	649.4	650.5	651.6	652.6	652.8	651.9	651.0	650.1	649.3	649.2
172.5°	650.2	651.4	652.6	653.8	655.0	655.1	654.3	653.4	652.6	651.6	651.5
175°	652.7	654.0	655.3	656.7	658.0	658.1	657.1	656.2	655.1	654.2	654.1
177.5°	654.3	655.3	656.4	657.5	658.5	658.7	658.0	657.3	656.6	655.8	655.7
180°	656.7	656.7	656.7	656.7	656.7	656.7	656.7	656.7	656.7	656.7	656.7



TEST NUMBER: P332871-935

CATALOG NUMBER: SA4XXRDIP-C350D590U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	521.1	518.8	517.6	515.1	512.0	510.3	508.9	506.7	503.9	501.0	498.9
5°	547.5	542.6	536.5	529.2	522.7	516.3	510.8	505.3	499.0	492.5	486.0
7.5°	574.6	565.1	554.7	542.6	531.0	520.3	510.5	501.2	490.6	481.0	472.4
10°	593.6	580.6	566.1	550.8	535.5	522.3	509.2	497.4	484.4	472.8	463.0
12.5°	608.9	593.6	576.2	557.2	538.7	522.7	507.7	492.3	477.5	464.9	451.9
15°	634.3	613.4	590.0	567.1	543.3	521.4	501.3	483.4	466.4	448.7	436.3
17.5°	651.9	626.9	598.4	571.0	542.9	517.1	493.9	472.5	453.0	434.9	420.1
20°	662.3	634.7	603.1	572.0	540.4	512.9	487.8	464.2	444.0	424.5	409.1
22.5°	668.1	637.7	603.1	570.5	537.8	508.0	480.5	455.9	433.9	414.3	397.4
25°	670.0	637.4	602.2	564.6	528.8	497.2	468.6	442.0	417.5	398.0	380.0
27.5°	667.4	629.0	592.9	554.4	517.4	484.1	454.2	426.1	401.7	380.6	362.2
30°	663.5	622.3	583.6	543.6	506.2	474.2	442.6	415.7	390.2	368.4	349.9
32.5°	655.0	614.2	572.5	531.6	493.6	460.6	430.7	403.6	378.7	356.4	336.7
35°	638.2	596.8	551.6	509.6	472.3	438.1	410.0	383.9	360.1	336.2	315.5
37.5°	616.0	573.9	528.8	482.8	445.5	413.2	387.4	362.9	339.7	317.9	294.9
40°	595.2	556.7	510.2	464.6	426.3	395.1	371.3	349.0	325.6	304.0	281.0
42.5°	570.0	537.2	490.2	444.4	406.6	376.5	354.3	332.6	311.3	290.3	266.3
45°	527.8	502.9	458.9	414.9	376.8	347.0	326.7	307.5	288.8	268.8	246.2
47.5°	479.4	462.6	424.6	379.5	344.3	317.5	297.8	282.1	266.3	246.3	226.5
50°	445.8	435.1	398.4	357.2	323.6	298.9	278.8	264.1	250.8	231.7	214.0
52.5°	410.0	404.2	373.2	333.9	301.4	277.2	260.0	246.8	233.4	217.5	201.0
55°	355.3	358.4	332.2	298.1	267.5	247.2	231.5	220.5	209.1	195.6	182.8
57.5°	299.5	310.7	293.1	263.2	234.5	215.7	203.9	194.7	185.0	173.9	162.9
60°	266.1	275.5	265.5	239.2	214.1	196.7	185.6	178.5	168.9	158.8	150.4
62.5°	233.5	243.6	237.6	216.4	193.1	178.1	168.3	161.7	154.5	145.7	137.0
65°	192.6	199.1	196.2	181.6	165.1	152.2	143.3	138.4	131.8	125.4	117.6
67.5°	147.5	160.1	158.4	150.6	136.4	126.3	120.5	116.1	110.2	105.4	100.1
70°	121.2	132.9	132.7	126.3	118.6	109.3	105.1	101.5	96.2	91.5	87.2
72.5°	99.3	109.9	111.5	106.6	101.3	94.2	90.3	87.8	82.7	79.5	75.9
75°	69.5	77.2	79.3	79.3	76.8	73.2	69.7	68.0	64.4	61.6	59.5
77.5°	45.5	50.5	53.6	54.3	54.8	53.5	50.6	49.5	46.7	45.7	43.7
80°	32.2	35.5	39.1	40.4	41.3	41.0	39.8	38.9	36.2	35.2	34.4
82.5°	22.2	24.0	27.0	29.8	29.4	30.6	29.4	28.8	26.8	26.4	25.7
85°	11.6	11.8	12.2	14.0	15.1	15.5	15.7	15.3	14.6	14.6	13.3
87.5°	5.7	5.4	5.5	5.3	5.3	5.7	5.9	5.9	5.6	5.3	5.1
90°	9.0	8.2	7.3	6.3	5.1	3.9	2.7	1.5	2.7	3.9	5.1
92.5°	8.7	7.8	6.9	6.5	6.4	6.3	6.3	6.2	6.3	6.3	6.4
95°	10.6	10.5	10.3	12.1	15.8	19.6	23.3	27.0	23.3	19.6	15.8
97.5°	37.4	49.5	61.6	66.6	64.3	62.0	59.7	57.3	59.7	62.0	64.3
100°	51.7	66.8	81.9	88.4	86.4	84.5	82.5	80.5	82.5	84.5	86.4
102.5°	108.1	110.0	112.0	112.3	110.8	109.3	107.9	106.5	107.9	109.3	110.8
105°	152.1	151.6	151.0	150.4	149.8	149.1	148.5	147.8	148.5	149.1	149.8
107.5°	189.6	188.8	188.0	187.5	187.2	186.9	186.6	186.2	186.6	186.9	187.2
110°	215.2	214.6	214.0	213.4	213.2	212.8	212.5	212.2	212.5	212.8	213.2



TEST NUMBER: P332871-935

CATALOG NUMBER: SA4XXRDIP-C350D590U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	240.7	240.4	240.1	239.7	239.1	238.5	237.9	237.3	237.9	238.5	239.1
115°	277.2	277.3	277.4	277.3	277.0	276.6	276.4	276.0	276.4	276.6	277.0
117.5°	313.5	313.2	313.0	312.6	312.2	311.8	311.3	310.9	311.3	311.8	312.2
120°	336.1	336.3	336.4	336.2	335.8	335.4	334.9	334.5	334.9	335.4	335.8
122.5°	358.0	357.9	357.7	357.5	357.2	357.0	356.7	356.5	356.7	357.0	357.2
125°	389.4	389.6	389.9	389.8	389.3	388.9	388.4	388.0	388.4	388.9	389.3
127.5°	419.6	419.1	418.6	418.3	418.2	418.1	417.9	417.8	417.9	418.1	418.2
130°	438.4	438.1	437.7	437.6	437.5	437.3	437.2	437.1	437.2	437.3	437.5
132.5°	456.7	456.3	455.9	455.6	455.4	455.2	455.0	454.8	455.0	455.2	455.4
135°	481.9	481.5	481.0	480.9	481.0	481.1	481.2	481.3	481.2	481.1	481.0
137.5°	506.2	505.7	505.2	505.0	504.9	504.9	504.8	504.8	504.8	504.9	504.9
140°	521.7	521.4	521.2	521.0	520.7	520.6	520.3	520.1	520.3	520.6	520.7
142.5°	536.0	535.8	535.7	535.5	535.0	534.7	534.3	533.9	534.3	534.7	535.0
145°	556.5	556.5	556.5	556.3	555.9	555.6	555.3	555.0	555.3	555.6	555.9
147.5°	574.3	574.4	574.5	574.2	573.6	573.0	572.4	571.8	572.4	573.0	573.6
150°	585.7	585.7	585.9	585.7	585.3	584.9	584.4	583.9	584.4	584.9	585.3
152.5°	595.3	595.5	595.6	595.6	595.2	594.9	594.5	594.2	594.5	594.9	595.2
155°	608.2	608.6	608.8	609.0	608.8	608.7	608.6	608.6	608.6	608.7	608.8
157.5°	619.4	619.7	620.1	620.4	620.4	620.4	620.5	620.6	620.5	620.4	620.4
160°	625.9	626.0	626.1	626.4	626.7	627.0	627.3	627.7	627.3	627.0	626.7
162.5°	631.8	631.9	632.1	632.3	632.7	633.1	633.5	634.0	633.5	633.1	632.7
165°	639.5	639.5	639.5	639.7	640.2	640.8	641.4	641.9	641.4	640.8	640.2
167.5°	645.5	645.6	645.6	645.9	646.5	647.0	647.6	648.2	647.6	647.0	646.5
170°	649.0	648.9	648.8	649.1	649.8	650.4	651.1	651.8	651.1	650.4	649.8
172.5°	651.4	651.3	651.2	651.5	652.1	652.8	653.4	654.1	653.4	652.8	652.1
175°	654.0	653.8	653.8	654.0	654.7	655.3	656.0	656.7	656.0	655.3	654.7
177.5°	655.5	655.3	655.1	655.4	656.0	656.6	657.2	657.8	657.2	656.6	656.0
180°	656.7	656.7	656.7	656.7	656.7	656.7	656.7	656.7	656.7	656.7	656.7



TEST NUMBER: P332871-935

CATALOG NUMBER: SA4XXRDIP-C350D590U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	496.6	495.0	492.9	490.4	487.5	484.9	483.7	484.7	485.3	483.9	483.7
5°	481.5	476.4	472.3	466.2	461.3	457.3	454.4	453.1	453.6	450.3	449.5
7.5°	464.5	458.5	451.8	444.5	437.8	431.8	428.7	427.0	423.4	422.0	419.5
10°	453.6	445.5	438.9	430.3	422.6	415.5	412.0	409.1	405.7	404.1	400.6
12.5°	442.4	432.9	425.7	416.8	408.9	400.4	397.0	391.8	386.3	382.9	378.4
15°	426.5	415.1	406.3	395.7	386.3	376.6	367.8	358.0	354.4	346.6	342.2
17.5°	407.9	396.4	385.6	371.3	356.9	344.7	335.4	326.0	320.4	315.5	313.1
20°	395.7	385.1	370.1	353.5	337.4	324.0	316.4	310.3	304.2	300.7	298.3
22.5°	384.2	370.6	353.1	335.3	319.2	308.7	302.3	296.0	291.0	287.7	284.5
25°	364.7	347.0	328.5	308.1	297.1	287.9	281.0	275.9	272.9	268.5	266.9
27.5°	344.8	323.3	302.9	289.2	277.8	269.3	263.3	259.5	255.6	252.9	250.7
30°	329.5	307.7	289.4	276.3	264.7	257.8	252.9	248.4	245.3	243.1	241.5
32.5°	314.4	292.6	277.2	263.1	253.9	247.2	241.9	238.6	236.2	233.3	232.3
35°	292.4	273.0	259.6	246.9	237.6	231.5	227.4	223.9	221.9	221.1	220.5
37.5°	271.3	255.5	241.0	230.7	222.3	217.5	212.7	210.9	209.6	208.1	208.8
40°	258.0	243.1	230.2	219.3	212.5	207.2	204.4	202.3	201.1	201.1	201.1
42.5°	246.4	231.9	219.3	209.5	202.8	198.3	195.1	193.4	193.0	192.8	193.8
45°	228.4	215.0	202.3	194.2	188.5	184.0	182.2	180.7	180.7	181.6	181.8
47.5°	210.6	198.0	187.9	178.7	173.5	170.7	169.1	168.4	168.5	169.3	170.2
50°	199.7	187.3	177.3	169.1	164.3	161.6	160.1	159.7	160.1	160.1	161.6
52.5°	187.8	176.7	166.9	160.0	154.5	152.0	151.2	150.6	150.8	151.5	152.1
55°	170.4	160.4	151.0	144.5	140.4	138.8	136.9	137.2	136.7	137.2	137.2
57.5°	152.8	143.9	135.2	130.0	126.4	124.1	122.1	122.6	122.0	121.9	121.6
60°	141.6	131.8	124.9	120.2	116.1	114.1	112.3	112.7	112.1	111.7	110.8
62.5°	129.4	121.2	114.6	110.1	106.9	104.5	102.6	102.3	100.8	99.4	97.6
65°	111.7	105.0	99.0	94.8	91.7	89.9	88.4	87.2	84.1	80.9	79.3
67.5°	94.5	89.5	84.0	80.4	77.9	75.6	72.8	70.8	67.9	66.1	65.1
70°	83.3	78.7	74.0	70.5	67.8	65.6	62.6	61.1	59.1	58.3	57.3
72.5°	72.8	68.4	64.1	60.9	58.1	56.3	53.9	52.5	51.6	51.2	50.3
75°	56.7	53.2	49.9	47.1	44.9	43.6	42.6	41.6	41.2	39.3	38.3
77.5°	41.3	39.0	37.0	35.0	33.4	32.5	30.6	29.4	28.8	27.9	27.6
80°	32.2	30.6	28.5	27.3	25.1	24.3	23.4	23.2	23.0	22.8	22.6
82.5°	24.2	22.6	20.6	19.8	19.2	18.7	18.3	18.0	17.8	17.9	17.9
85°	12.2	11.5	11.5	11.2	11.0	10.8	10.6	10.6	10.4	10.6	10.4
87.5°	5.3	5.3	5.5	5.4	5.8	5.9	5.9	6.0	6.3	6.1	6.2
90°	6.3	7.3	8.2	9.0	9.9	10.8	11.5	12.1	12.7	13.4	13.9
92.5°	6.5	6.9	7.8	8.7	9.6	10.4	11.1	11.7	12.4	13.0	13.3
95°	12.1	10.3	10.5	10.6	10.7	10.8	11.5	12.1	12.7	13.4	13.8
97.5°	66.6	61.6	49.5	37.4	25.1	13.0	13.0	13.1	13.2	13.3	13.3
100°	88.4	81.9	66.8	51.7	36.7	21.6	19.7	17.9	16.0	14.2	13.3
102.5°	112.3	112.0	110.0	108.1	106.1	104.1	84.1	64.1	44.1	24.0	14.0
105°	150.4	151.0	151.6	152.1	152.7	153.3	154.2	155.2	156.2	157.1	155.7
107.5°	187.5	188.0	188.8	189.6	190.3	191.1	191.6	192.0	192.5	193.0	193.4
110°	213.4	214.0	214.6	215.2	215.9	216.6	216.8	217.1	217.2	217.5	217.7



TEST NUMBER: P332871-935

CATALOG NUMBER: SA4XXRDIP-C350D590U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	239.7	240.1	240.4	240.7	241.1	241.3	241.3	241.3	241.3	241.2	241.3
115°	277.3	277.4	277.3	277.2	277.1	277.0	277.2	277.4	277.7	277.8	278.0
117.5°	312.6	313.0	313.2	313.5	313.7	313.9	313.9	313.8	313.8	313.7	313.7
120°	336.2	336.4	336.3	336.1	336.0	336.0	336.1	336.4	336.6	336.8	336.8
122.5°	357.5	357.7	357.9	358.0	358.2	358.3	358.4	358.6	358.7	358.9	358.8
125°	389.8	389.9	389.6	389.4	389.2	389.0	389.3	389.6	389.9	390.3	390.5
127.5°	418.3	418.6	419.1	419.6	420.1	420.6	420.5	420.5	420.4	420.3	420.3
130°	437.6	437.7	438.1	438.4	438.8	439.1	439.2	439.3	439.4	439.5	439.5
132.5°	455.6	455.9	456.3	456.7	457.1	457.5	457.6	457.8	457.9	458.0	458.0
135°	480.9	481.0	481.5	481.9	482.3	482.8	483.0	483.2	483.5	483.6	483.9
137.5°	505.0	505.2	505.7	506.2	506.7	507.1	507.4	507.6	507.9	508.1	508.2
140°	521.0	521.2	521.4	521.7	521.9	522.1	522.4	522.7	523.1	523.4	523.6
142.5°	535.5	535.7	535.8	536.0	536.1	536.2	536.5	536.7	536.9	537.2	537.4
145°	556.3	556.5	556.5	556.5	556.5	556.5	556.6	556.6	556.8	556.9	557.1
147.5°	574.2	574.5	574.4	574.3	574.1	574.0	574.1	574.2	574.3	574.4	574.5
150°	585.7	585.9	585.7	585.7	585.6	585.4	585.4	585.4	585.4	585.4	585.5
152.5°	595.6	595.6	595.5	595.3	595.0	594.9	595.0	595.2	595.4	595.6	595.6
155°	609.0	608.8	608.6	608.2	607.9	607.5	608.0	608.4	608.8	609.2	609.3
157.5°	620.4	620.1	619.7	619.4	619.0	618.6	619.2	619.7	620.4	620.9	620.9
160°	626.4	626.1	626.0	625.9	625.8	625.7	626.4	627.0	627.7	628.4	628.4
162.5°	632.3	632.1	631.9	631.8	631.7	631.6	632.2	632.9	633.5	634.2	634.2
165°	639.7	639.5	639.5	639.5	639.5	639.5	640.3	641.2	642.0	643.0	642.9
167.5°	645.9	645.6	645.6	645.5	645.4	645.3	646.4	647.3	648.2	649.2	649.1
170°	649.1	648.8	648.9	649.0	649.2	649.3	650.1	651.0	651.9	652.8	652.6
172.5°	651.5	651.2	651.3	651.4	651.5	651.6	652.6	653.4	654.3	655.1	655.0
175°	654.0	653.8	653.8	654.0	654.1	654.2	655.1	656.2	657.1	658.1	658.0
177.5°	655.4	655.1	655.3	655.5	655.7	655.8	656.6	657.3	658.0	658.7	658.5
180°	656.7	656.7	656.7	656.7	656.7	656.7	656.7	656.7	656.7	656.7	656.7



TEST NUMBER: P332871-935

CATALOG NUMBER: SA4XXRDIP-C350D590U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	482.8	483.1	482.0	481.6	482.0	483.1	482.8	483.7	483.9	485.3	484.7
5°	447.9	447.5	446.4	446.7	446.4	447.5	447.9	449.5	450.3	453.6	453.1
7.5°	418.0	416.5	416.9	415.3	416.9	416.5	418.0	419.5	422.0	423.4	427.0
10°	399.8	397.5	395.7	394.1	395.7	397.5	399.8	400.6	404.1	405.7	409.1
12.5°	374.9	372.9	370.5	370.9	370.5	372.9	374.9	378.4	382.9	386.3	391.8
15°	339.5	336.4	331.6	332.2	331.6	336.4	339.5	342.2	346.6	354.4	358.0
17.5°	309.5	309.5	307.3	307.9	307.3	309.5	309.5	313.1	315.5	320.4	326.0
20°	294.0	292.7	292.8	292.2	292.8	292.7	294.0	298.3	300.7	304.2	310.3
22.5°	283.3	281.5	280.1	278.9	280.1	281.5	283.3	284.5	287.7	291.0	296.0
25°	265.1	263.9	262.1	261.7	262.1	263.9	265.1	266.9	268.5	272.9	275.9
27.5°	249.1	248.9	248.1	247.2	248.1	248.9	249.1	250.7	252.9	255.6	259.5
30°	239.9	239.4	239.0	238.4	239.0	239.4	239.9	241.5	243.1	245.3	248.4
32.5°	231.5	231.3	230.8	230.9	230.8	231.3	231.5	232.3	233.3	236.2	238.6
35°	219.6	219.5	219.0	218.9	219.0	219.5	219.6	220.5	221.1	221.9	223.9
37.5°	208.6	209.1	208.9	208.8	208.9	209.1	208.6	208.8	208.1	209.6	210.9
40°	201.0	201.1	201.6	201.3	201.6	201.1	201.0	201.1	201.1	201.1	202.3
42.5°	194.6	194.6	195.2	194.5	195.2	194.6	194.6	193.8	192.8	193.0	193.4
45°	183.2	184.4	184.2	184.2	184.2	184.4	183.2	181.8	181.6	180.7	180.7
47.5°	170.7	171.9	172.1	172.0	172.1	171.9	170.7	170.2	169.3	168.5	168.4
50°	162.6	162.2	162.8	162.6	162.8	162.2	162.6	161.6	160.1	160.1	159.7
52.5°	152.7	152.7	152.7	152.5	152.7	152.7	152.7	152.1	151.5	150.8	150.6
55°	137.3	137.6	137.2	137.3	137.2	137.6	137.3	137.2	137.2	136.7	137.2
57.5°	120.7	119.8	120.1	119.7	120.1	119.8	120.7	121.6	121.9	122.0	122.6
60°	108.8	107.2	106.8	106.0	106.8	107.2	108.8	110.8	111.7	112.1	112.7
62.5°	95.5	94.3	92.9	93.6	92.9	94.3	95.5	97.6	99.4	100.8	102.3
65°	77.7	76.8	76.2	77.1	76.2	76.8	77.7	79.3	80.9	84.1	87.2
67.5°	64.2	63.8	63.8	63.5	63.8	63.8	64.2	65.1	66.1	67.9	70.8
70°	57.3	56.7	56.7	56.2	56.7	56.7	57.3	57.3	58.3	59.1	61.1
72.5°	50.1	49.5	49.7	49.4	49.7	49.5	50.1	50.3	51.2	51.6	52.5
75°	37.1	36.1	36.1	36.2	36.1	36.1	37.1	38.3	39.3	41.2	41.6
77.5°	27.6	27.5	27.7	27.4	27.7	27.5	27.6	27.6	27.9	28.8	29.4
80°	22.6	22.4	22.2	22.8	22.2	22.4	22.6	22.6	22.8	23.0	23.2
82.5°	17.6	17.6	17.5	18.3	17.5	17.6	17.6	17.9	17.9	17.8	18.0
85°	10.6	10.2	10.6	10.2	10.6	10.2	10.6	10.4	10.6	10.4	10.6
87.5°	6.5	6.5	6.3	6.5	6.3	6.5	6.5	6.2	6.1	6.3	6.0
90°	14.1	14.3	14.6	14.7	14.6	14.3	14.1	13.9	13.4	12.7	12.1
92.5°	13.4	13.4	13.5	13.5	13.5	13.4	13.4	13.3	13.0	12.4	11.7
95°	13.9	14.0	14.1	14.2	14.1	14.0	13.9	13.8	13.4	12.7	12.1
97.5°	13.4	13.5	13.6	13.8	13.6	13.5	13.4	13.3	13.3	13.2	13.1
100°	13.4	13.5	13.6	13.8	13.6	13.5	13.4	13.3	14.2	16.0	17.9
102.5°	14.1	14.1	14.1	14.1	14.1	14.1	14.1	14.0	24.0	44.1	64.1
105°	151.8	147.8	143.9	140.0	143.9	147.8	151.8	155.7	157.1	156.2	155.2
107.5°	193.8	194.2	194.7	195.1	194.7	194.2	193.8	193.4	193.0	192.5	192.0
110°	218.1	218.3	218.7	219.0	218.7	218.3	218.1	217.7	217.5	217.2	217.1



TEST NUMBER: P332871-935

CATALOG NUMBER: SA4XXRDIP-C350D590U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	241.8	242.2	242.6	243.0	242.6	242.2	241.8	241.3	241.2	241.3	241.3
115°	278.0	278.0	278.0	278.0	278.0	278.0	278.0	278.0	277.8	277.7	277.4
117.5°	313.7	313.7	313.6	313.6	313.6	313.7	313.7	313.7	313.7	313.8	313.8
120°	336.6	336.4	336.1	336.0	336.1	336.4	336.6	336.8	336.8	336.6	336.4
122.5°	358.6	358.3	358.2	357.9	358.2	358.3	358.6	358.8	358.9	358.7	358.6
125°	390.6	390.7	390.8	391.0	390.8	390.7	390.6	390.5	390.3	389.9	389.6
127.5°	420.2	420.1	420.0	419.9	420.0	420.1	420.2	420.3	420.3	420.4	420.5
130°	439.5	439.5	439.5	439.5	439.5	439.5	439.5	439.5	439.5	439.4	439.3
132.5°	457.9	457.8	457.7	457.6	457.7	457.8	457.9	458.0	458.0	457.9	457.8
135°	484.1	484.3	484.6	484.7	484.6	484.3	484.1	483.9	483.6	483.5	483.2
137.5°	508.2	508.1	508.0	507.9	508.0	508.1	508.2	508.2	508.1	507.9	507.6
140°	523.7	523.8	523.9	524.0	523.9	523.8	523.7	523.6	523.4	523.1	522.7
142.5°	537.4	537.4	537.4	537.4	537.4	537.4	537.4	537.4	537.2	536.9	536.7
145°	557.2	557.5	557.8	557.9	557.8	557.5	557.2	557.1	556.9	556.8	556.6
147.5°	574.6	574.7	574.8	574.9	574.8	574.7	574.6	574.5	574.4	574.3	574.2
150°	585.6	585.7	585.8	585.9	585.8	585.7	585.6	585.5	585.4	585.4	585.4
152.5°	595.6	595.5	595.4	595.4	595.4	595.5	595.6	595.6	595.6	595.4	595.2
155°	609.0	608.6	608.4	608.0	608.4	608.6	609.0	609.3	609.2	608.8	608.4
157.5°	620.4	619.7	619.2	618.6	619.2	619.7	620.4	620.9	620.9	620.4	619.7
160°	627.7	627.0	626.4	625.7	626.4	627.0	627.7	628.4	628.4	627.7	627.0
162.5°	633.4	632.7	632.0	631.2	632.0	632.7	633.4	634.2	634.2	633.5	632.9
165°	641.9	640.9	640.0	638.9	640.0	640.9	641.9	642.9	643.0	642.0	641.2
167.5°	648.1	647.0	645.8	644.8	645.8	647.0	648.1	649.1	649.2	648.2	647.3
170°	651.6	650.5	649.4	648.3	649.4	650.5	651.6	652.6	652.8	651.9	651.0
172.5°	653.8	652.6	651.4	650.2	651.4	652.6	653.8	655.0	655.1	654.3	653.4
175°	656.7	655.3	654.0	652.7	654.0	655.3	656.7	658.0	658.1	657.1	656.2
177.5°	657.5	656.4	655.3	654.3	655.3	656.4	657.5	658.5	658.7	658.0	657.3
180°	656.7	656.7	656.7	656.7	656.7	656.7	656.7	656.7	656.7	656.7	656.7



TEST NUMBER: P332871-935

CATALOG NUMBER: SA4XXRDIP-C350D590U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	483.7	484.9	487.5	490.4	492.9	495.0	496.6	498.9	501.0	503.9	506.7
5°	454.4	457.3	461.3	466.2	472.3	476.4	481.5	486.0	492.5	499.0	505.3
7.5°	428.7	431.8	437.8	444.5	451.8	458.5	464.5	472.4	481.0	490.6	501.2
10°	412.0	415.5	422.6	430.3	438.9	445.5	453.6	463.0	472.8	484.4	497.4
12.5°	397.0	400.4	408.9	416.8	425.7	432.9	442.4	451.9	464.9	477.5	492.3
15°	367.8	376.6	386.3	395.7	406.3	415.1	426.5	436.3	448.7	466.4	483.4
17.5°	335.4	344.7	356.9	371.3	385.6	396.4	407.9	420.1	434.9	453.0	472.5
20°	316.4	324.0	337.4	353.5	370.1	385.1	395.7	409.1	424.5	444.0	464.2
22.5°	302.3	308.7	319.2	335.3	353.1	370.6	384.2	397.4	414.3	433.9	455.9
25°	281.0	287.9	297.1	308.1	328.5	347.0	364.7	380.0	398.0	417.5	442.0
27.5°	263.3	269.3	277.8	289.2	302.9	323.3	344.8	362.2	380.6	401.7	426.1
30°	252.9	257.8	264.7	276.3	289.4	307.7	329.5	349.9	368.4	390.2	415.7
32.5°	241.9	247.2	253.9	263.1	277.2	292.6	314.4	336.7	356.4	378.7	403.6
35°	227.4	231.5	237.6	246.9	259.6	273.0	292.4	315.5	336.2	360.1	383.9
37.5°	212.7	217.5	222.3	230.7	241.0	255.5	271.3	294.9	317.9	339.7	362.9
40°	204.4	207.2	212.5	219.3	230.2	243.1	258.0	281.0	304.0	325.6	349.0
42.5°	195.1	198.3	202.8	209.5	219.3	231.9	246.4	266.3	290.3	311.3	332.6
45°	182.2	184.0	188.5	194.2	202.3	215.0	228.4	246.2	268.8	288.8	307.5
47.5°	169.1	170.7	173.5	178.7	187.9	198.0	210.6	226.5	246.3	266.3	282.1
50°	160.1	161.6	164.3	169.1	177.3	187.3	199.7	214.0	231.7	250.8	264.1
52.5°	151.2	152.0	154.5	160.0	166.9	176.7	187.8	201.0	217.5	233.4	246.8
55°	136.9	138.8	140.4	144.5	151.0	160.4	170.4	182.8	195.6	209.1	220.5
57.5°	122.1	124.1	126.4	130.0	135.2	143.9	152.8	162.9	173.9	185.0	194.7
60°	112.3	114.1	116.1	120.2	124.9	131.8	141.6	150.4	158.8	168.9	178.5
62.5°	102.6	104.5	106.9	110.1	114.6	121.2	129.4	137.0	145.7	154.5	161.7
65°	88.4	89.9	91.7	94.8	99.0	105.0	111.7	117.6	125.4	131.8	138.4
67.5°	72.8	75.6	77.9	80.4	84.0	89.5	94.5	100.1	105.4	110.2	116.1
70°	62.6	65.6	67.8	70.5	74.0	78.7	83.3	87.2	91.5	96.2	101.5
72.5°	53.9	56.3	58.1	60.9	64.1	68.4	72.8	75.9	79.5	82.7	87.8
75°	42.6	43.6	44.9	47.1	49.9	53.2	56.7	59.5	61.6	64.4	68.0
77.5°	30.6	32.5	33.4	35.0	37.0	39.0	41.3	43.7	45.7	46.7	49.5
80°	23.4	24.3	25.1	27.3	28.5	30.6	32.2	34.4	35.2	36.2	38.9
82.5°	18.3	18.7	19.2	19.8	20.6	22.6	24.2	25.7	26.4	26.8	28.8
85°	10.6	10.8	11.0	11.2	11.5	11.5	12.2	13.3	14.6	14.6	15.3
87.5°	5.9	5.9	5.8	5.4	5.5	5.3	5.3	5.1	5.3	5.6	5.9
90°	11.5	10.8	9.9	9.0	8.2	7.3	6.3	5.1	3.9	2.7	1.5
92.5°	11.1	10.4	9.6	8.7	7.8	6.9	6.5	6.4	6.3	6.3	6.2
95°	11.5	10.8	10.7	10.6	10.5	10.3	12.1	15.8	19.6	23.3	27.0
97.5°	13.0	13.0	25.1	37.4	49.5	61.6	66.6	64.3	62.0	59.7	57.3
100°	19.7	21.6	36.7	51.7	66.8	81.9	88.4	86.4	84.5	82.5	80.5
102.5°	84.1	104.1	106.1	108.1	110.0	112.0	112.3	110.8	109.3	107.9	106.5
105°	154.2	153.3	152.7	152.1	151.6	151.0	150.4	149.8	149.1	148.5	147.8
107.5°	191.6	191.1	190.3	189.6	188.8	188.0	187.5	187.2	186.9	186.6	186.2
110°	216.8	216.6	215.9	215.2	214.6	214.0	213.4	213.2	212.8	212.5	212.2



TEST NUMBER: P332871-935

CATALOG NUMBER: SA4XXRDIP-C350D590U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	241.3	241.3	241.1	240.7	240.4	240.1	239.7	239.1	238.5	237.9	237.3
115°	277.2	277.0	277.1	277.2	277.3	277.4	277.3	277.0	276.6	276.4	276.0
117.5°	313.9	313.9	313.7	313.5	313.2	313.0	312.6	312.2	311.8	311.3	310.9
120°	336.1	336.0	336.0	336.1	336.3	336.4	336.2	335.8	335.4	334.9	334.5
122.5°	358.4	358.3	358.2	358.0	357.9	357.7	357.5	357.2	357.0	356.7	356.5
125°	389.3	389.0	389.2	389.4	389.6	389.9	389.8	389.3	388.9	388.4	388.0
127.5°	420.5	420.6	420.1	419.6	419.1	418.6	418.3	418.2	418.1	417.9	417.8
130°	439.2	439.1	438.8	438.4	438.1	437.7	437.6	437.5	437.3	437.2	437.1
132.5°	457.6	457.5	457.1	456.7	456.3	455.9	455.6	455.4	455.2	455.0	454.8
135°	483.0	482.8	482.3	481.9	481.5	481.0	480.9	481.0	481.1	481.2	481.3
137.5°	507.4	507.1	506.7	506.2	505.7	505.2	505.0	504.9	504.9	504.8	504.8
140°	522.4	522.1	521.9	521.7	521.4	521.2	521.0	520.7	520.6	520.3	520.1
142.5°	536.5	536.2	536.1	536.0	535.8	535.7	535.5	535.0	534.7	534.3	533.9
145°	556.6	556.5	556.5	556.5	556.5	556.5	556.3	555.9	555.6	555.3	555.0
147.5°	574.1	574.0	574.1	574.3	574.4	574.5	574.2	573.6	573.0	572.4	571.8
150°	585.4	585.4	585.6	585.7	585.7	585.9	585.7	585.3	584.9	584.4	583.9
152.5°	595.0	594.9	595.0	595.3	595.5	595.6	595.6	595.2	594.9	594.5	594.2
155°	608.0	607.5	607.9	608.2	608.6	608.8	609.0	608.8	608.7	608.6	608.6
157.5°	619.2	618.6	619.0	619.4	619.7	620.1	620.4	620.4	620.4	620.5	620.6
160°	626.4	625.7	625.8	625.9	626.0	626.1	626.4	626.7	627.0	627.3	627.7
162.5°	632.2	631.6	631.7	631.8	631.9	632.1	632.3	632.7	633.1	633.5	634.0
165°	640.3	639.5	639.5	639.5	639.5	639.5	639.7	640.2	640.8	641.4	641.9
167.5°	646.4	645.3	645.4	645.5	645.6	645.6	645.9	646.5	647.0	647.6	648.2
170°	650.1	649.3	649.2	649.0	648.9	648.8	649.1	649.8	650.4	651.1	651.8
172.5°	652.6	651.6	651.5	651.4	651.3	651.2	651.5	652.1	652.8	653.4	654.1
175°	655.1	654.2	654.1	654.0	653.8	653.8	654.0	654.7	655.3	656.0	656.7
177.5°	656.6	655.8	655.7	655.5	655.3	655.1	655.4	656.0	656.6	657.2	657.8
180°	656.7	656.7	656.7	656.7	656.7	656.7	656.7	656.7	656.7	656.7	656.7



TEST NUMBER: P332871-935

CATALOG NUMBER: SA4XXRDIP-C350D590U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	508.9	510.3	512.0	515.1	517.6	518.8	521.1	522.7	522.2	524.5	528.4
5°	510.8	516.3	522.7	529.2	536.5	542.6	547.5	552.4	556.3	560.9	567.9
7.5°	510.5	520.3	531.0	542.6	554.7	565.1	574.6	584.4	593.1	602.6	615.1
10°	509.2	522.3	535.5	550.8	566.1	580.6	593.6	605.8	617.4	629.8	645.6
12.5°	507.7	522.7	538.7	557.2	576.2	593.6	608.9	626.5	641.1	657.1	675.2
15°	501.3	521.4	543.3	567.1	590.0	613.4	634.3	655.9	676.1	695.3	718.1
17.5°	493.9	517.1	542.9	571.0	598.4	626.9	651.9	679.1	699.6	725.4	746.6
20°	487.8	512.9	540.4	572.0	603.1	634.7	662.3	690.0	713.2	739.1	765.9
22.5°	480.5	508.0	537.8	570.5	603.1	637.7	668.1	695.7	724.4	753.5	781.3
25°	468.6	497.2	528.8	564.6	602.2	637.4	670.0	704.2	735.2	766.8	791.7
27.5°	454.2	484.1	517.4	554.4	592.9	629.0	667.4	703.9	735.0	765.4	787.1
30°	442.6	474.2	506.2	543.6	583.6	622.3	663.5	700.0	732.8	760.1	772.3
32.5°	430.7	460.6	493.6	531.6	572.5	614.2	655.0	692.3	722.6	739.0	739.3
35°	410.0	438.1	472.3	509.6	551.6	596.8	638.2	674.9	693.4	694.8	674.9
37.5°	387.4	413.2	445.5	482.8	528.8	573.9	616.0	640.5	646.7	625.9	589.1
40°	371.3	395.1	426.3	464.6	510.2	556.7	595.2	613.1	606.7	573.0	531.8
42.5°	354.3	376.5	406.6	444.4	490.2	537.2	570.0	579.5	562.3	523.5	475.3
45°	326.7	347.0	376.8	414.9	458.9	502.9	527.8	522.9	494.1	448.1	394.1
47.5°	297.8	317.5	344.3	379.5	424.6	462.6	479.4	464.7	423.8	373.2	329.2
50°	278.8	298.9	323.6	357.2	398.4	435.1	445.8	423.4	378.0	329.3	289.0
52.5°	260.0	277.2	301.4	333.9	373.2	404.2	410.0	384.2	337.3	293.6	257.8
55°	231.5	247.2	267.5	298.1	332.2	358.4	355.3	322.2	279.6	242.3	214.1
57.5°	203.9	215.7	234.5	263.2	293.1	310.7	299.5	271.2	231.5	201.0	177.3
60°	185.6	196.7	214.1	239.2	265.5	275.5	266.1	235.4	204.0	176.1	156.1
62.5°	168.3	178.1	193.1	216.4	237.6	243.6	233.5	206.6	178.4	154.5	138.0
65°	143.3	152.2	165.1	181.6	196.2	199.1	192.6	165.1	143.7	123.7	112.3
67.5°	120.5	126.3	136.4	150.6	158.4	160.1	147.5	130.2	111.3	99.1	90.5
70°	105.1	109.3	118.6	126.3	132.7	132.9	121.2	107.4	92.9	82.9	76.6
72.5°	90.3	94.2	101.3	106.6	111.5	109.9	99.3	88.3	76.6	69.1	64.4
75°	69.7	73.2	76.8	79.3	79.3	77.2	69.5	61.3	54.6	50.1	48.7
77.5°	50.6	53.5	54.8	54.3	53.6	50.5	45.5	40.2	37.8	35.7	34.6
80°	39.8	41.0	41.3	40.4	39.1	35.5	32.2	30.0	27.7	26.9	26.5
82.5°	29.4	30.6	29.4	29.8	27.0	24.0	22.2	21.4	20.6	20.2	19.8
85°	15.7	15.5	15.1	14.0	12.2	11.8	11.6	11.5	11.0	11.2	10.8
87.5°	5.9	5.7	5.3	5.3	5.5	5.4	5.7	5.9	6.1	6.0	6.5
90°	2.7	3.9	5.1	6.3	7.3	8.2	9.0	9.9	10.8	11.5	12.1
92.5°	6.3	6.3	6.4	6.5	6.9	7.8	8.7	9.6	10.4	11.1	11.7
95°	23.3	19.6	15.8	12.1	10.3	10.5	10.6	10.7	10.8	11.5	12.1
97.5°	59.7	62.0	64.3	66.6	61.6	49.5	37.4	25.1	13.0	13.0	13.1
100°	82.5	84.5	86.4	88.4	81.9	66.8	51.7	36.7	21.6	19.7	17.9
102.5°	107.9	109.3	110.8	112.3	112.0	110.0	108.1	106.1	104.1	84.1	64.1
105°	148.5	149.1	149.8	150.4	151.0	151.6	152.1	152.7	153.3	154.2	155.2
107.5°	186.6	186.9	187.2	187.5	188.0	188.8	189.6	190.3	191.1	191.6	192.0
110°	212.5	212.8	213.2	213.4	214.0	214.6	215.2	215.9	216.6	216.8	217.1



TEST NUMBER: P332871-935

CATALOG NUMBER: SA4XXRDIP-C350D590U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	237.9	238.5	239.1	239.7	240.1	240.4	240.7	241.1	241.3	241.3	241.3
115°	276.4	276.6	277.0	277.3	277.4	277.3	277.2	277.1	277.0	277.2	277.4
117.5°	311.3	311.8	312.2	312.6	313.0	313.2	313.5	313.7	313.9	313.9	313.8
120°	334.9	335.4	335.8	336.2	336.4	336.3	336.1	336.0	336.0	336.1	336.4
122.5°	356.7	357.0	357.2	357.5	357.7	357.9	358.0	358.2	358.3	358.4	358.6
125°	388.4	388.9	389.3	389.8	389.9	389.6	389.4	389.2	389.0	389.3	389.6
127.5°	417.9	418.1	418.2	418.3	418.6	419.1	419.6	420.1	420.6	420.5	420.5
130°	437.2	437.3	437.5	437.6	437.7	438.1	438.4	438.8	439.1	439.2	439.3
132.5°	455.0	455.2	455.4	455.6	455.9	456.3	456.7	457.1	457.5	457.6	457.8
135°	481.2	481.1	481.0	480.9	481.0	481.5	481.9	482.3	482.8	483.0	483.2
137.5°	504.8	504.9	504.9	505.0	505.2	505.7	506.2	506.7	507.1	507.4	507.6
140°	520.3	520.6	520.7	521.0	521.2	521.4	521.7	521.9	522.1	522.4	522.7
142.5°	534.3	534.7	535.0	535.5	535.7	535.8	536.0	536.1	536.2	536.5	536.7
145°	555.3	555.6	555.9	556.3	556.5	556.5	556.5	556.5	556.5	556.6	556.6
147.5°	572.4	573.0	573.6	574.2	574.5	574.4	574.3	574.1	574.0	574.1	574.2
150°	584.4	584.9	585.3	585.7	585.9	585.7	585.7	585.6	585.4	585.4	585.4
152.5°	594.5	594.9	595.2	595.6	595.6	595.5	595.3	595.0	594.9	595.0	595.2
155°	608.6	608.7	608.8	609.0	608.8	608.6	608.2	607.9	607.5	608.0	608.4
157.5°	620.5	620.4	620.4	620.4	620.1	619.7	619.4	619.0	618.6	619.2	619.7
160°	627.3	627.0	626.7	626.4	626.1	626.0	625.9	625.8	625.7	626.4	627.0
162.5°	633.5	633.1	632.7	632.3	632.1	631.9	631.8	631.7	631.6	632.2	632.9
165°	641.4	640.8	640.2	639.7	639.5	639.5	639.5	639.5	639.5	640.3	641.2
167.5°	647.6	647.0	646.5	645.9	645.6	645.6	645.5	645.4	645.3	646.4	647.3
170°	651.1	650.4	649.8	649.1	648.8	648.9	649.0	649.2	649.3	650.1	651.0
172.5°	653.4	652.8	652.1	651.5	651.2	651.3	651.4	651.5	651.6	652.6	653.4
175°	656.0	655.3	654.7	654.0	653.8	653.8	654.0	654.1	654.2	655.1	656.2
177.5°	657.2	656.6	656.0	655.4	655.1	655.3	655.5	655.7	655.8	656.6	657.3
180°	656.7	656.7	656.7	656.7	656.7	656.7	656.7	656.7	656.7	656.7	656.7



TEST NUMBER: P332871-935
 CATALOG NUMBER: SA4XXRDIP-C350D590U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	530.5	531.2	531.7	533.3	533.5	534.9	533.5
5°	574.5	577.3	581.8	586.3	586.7	589.5	584.4
7.5°	623.6	630.3	634.4	641.6	644.5	646.3	643.3
10°	657.5	663.7	674.5	679.8	685.1	685.9	683.5
12.5°	690.3	700.0	708.5	718.6	718.3	725.5	722.9
15°	734.0	744.0	755.8	767.0	771.0	771.0	774.3
17.5°	765.1	783.4	795.7	804.4	814.1	815.7	814.6
20°	786.2	805.9	819.0	830.3	836.9	838.7	838.7
22.5°	801.8	818.6	831.4	841.6	847.0	849.1	848.5
25°	812.6	827.1	834.8	837.9	839.3	839.0	835.1
27.5°	797.8	797.1	792.3	782.9	775.8	771.5	766.6
30°	769.5	758.8	746.6	733.1	715.8	702.6	698.5
32.5°	727.2	703.4	682.7	660.3	641.7	628.4	622.8
35°	645.6	607.9	577.0	550.2	530.6	518.4	514.3
37.5°	548.6	512.1	474.1	448.0	431.7	419.4	414.8
40°	487.0	447.3	414.1	389.6	372.9	360.8	360.7
42.5°	430.8	392.8	361.5	344.0	326.0	318.0	318.0
45°	352.8	322.4	295.8	282.0	271.2	264.7	262.9
47.5°	292.1	266.9	249.3	238.2	229.5	225.3	222.6
50°	258.0	236.0	221.9	212.3	207.4	202.2	201.7
52.5°	229.6	211.8	200.9	193.1	186.9	183.7	183.8
55°	193.0	178.9	171.2	165.2	160.4	157.9	156.9
57.5°	162.6	152.1	146.4	140.9	138.9	137.0	136.5
60°	143.7	136.6	131.2	126.9	123.9	123.3	123.0
62.5°	128.0	120.5	116.9	113.6	111.3	110.4	110.0
65°	105.6	100.0	96.8	94.1	93.3	91.9	91.7
67.5°	85.1	81.8	79.6	77.8	76.7	76.6	76.6
70°	72.6	70.7	68.9	67.8	67.2	66.8	66.8
72.5°	61.8	60.4	58.9	58.4	58.3	57.9	57.7
75°	47.1	45.6	45.9	44.9	44.0	43.0	42.4
77.5°	33.4	32.4	32.1	32.0	31.3	31.3	31.5
80°	25.9	24.9	24.6	24.9	24.6	24.0	24.0
82.5°	19.7	18.9	18.6	18.5	18.3	18.5	18.2
85°	10.6	10.2	10.2	10.2	10.6	10.4	10.2
87.5°	6.3	6.3	6.5	6.4	6.5	6.3	6.5
90°	12.7	13.4	13.9	14.1	14.3	14.6	14.7
92.5°	12.4	13.0	13.3	13.4	13.4	13.5	13.5
95°	12.7	13.4	13.8	13.9	14.0	14.1	14.2
97.5°	13.2	13.3	13.3	13.4	13.5	13.6	13.8
100°	16.0	14.2	13.3	13.4	13.5	13.6	13.8
102.5°	44.1	24.0	14.0	14.1	14.1	14.1	14.1
105°	156.2	157.1	155.7	151.8	147.8	143.9	140.0
107.5°	192.5	193.0	193.4	193.8	194.2	194.7	195.1
110°	217.2	217.5	217.7	218.1	218.3	218.7	219.0



TEST NUMBER: P332871-935

CATALOG NUMBER: SA4XXRDIP-C350D590U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	241.3	241.2	241.3	241.8	242.2	242.6	243.0
115°	277.7	277.8	278.0	278.0	278.0	278.0	278.0
117.5°	313.8	313.7	313.7	313.7	313.7	313.6	313.6
120°	336.6	336.8	336.8	336.6	336.4	336.1	336.0
122.5°	358.7	358.9	358.8	358.6	358.3	358.2	357.9
125°	389.9	390.3	390.5	390.6	390.7	390.8	391.0
127.5°	420.4	420.3	420.3	420.2	420.1	420.0	419.9
130°	439.4	439.5	439.5	439.5	439.5	439.5	439.5
132.5°	457.9	458.0	458.0	457.9	457.8	457.7	457.6
135°	483.5	483.6	483.9	484.1	484.3	484.6	484.7
137.5°	507.9	508.1	508.2	508.2	508.1	508.0	507.9
140°	523.1	523.4	523.6	523.7	523.8	523.9	524.0
142.5°	536.9	537.2	537.4	537.4	537.4	537.4	537.4
145°	556.8	556.9	557.1	557.2	557.5	557.8	557.9
147.5°	574.3	574.4	574.5	574.6	574.7	574.8	574.9
150°	585.4	585.4	585.5	585.6	585.7	585.8	585.9
152.5°	595.4	595.6	595.6	595.6	595.5	595.4	595.4
155°	608.8	609.2	609.3	609.0	608.6	608.4	608.0
157.5°	620.4	620.9	620.9	620.4	619.7	619.2	618.6
160°	627.7	628.4	628.4	627.7	627.0	626.4	625.7
162.5°	633.5	634.2	634.2	633.4	632.7	632.0	631.2
165°	642.0	643.0	642.9	641.9	640.9	640.0	638.9
167.5°	648.2	649.2	649.1	648.1	647.0	645.8	644.8
170°	651.9	652.8	652.6	651.6	650.5	649.4	648.3
172.5°	654.3	655.1	655.0	653.8	652.6	651.4	650.2
175°	657.1	658.1	658.0	656.7	655.3	654.0	652.7
177.5°	658.0	658.7	658.5	657.5	656.4	655.3	654.3
180°	656.7	656.7	656.7	656.7	656.7	656.7	656.7

(END OF REPORT)