

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332911-935

Luminaire Tested: **SA4XXRDIP-C575D810U935-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332911-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C575D810U935-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 810 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4438.9 lumens
Efficiency: N/A
Efficacy: 115.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332911-935
CATALOG NUMBER: SA4XXRDIP-C575D810U935-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332911-935

CATALOG NUMBER: SA4XXRDIP-C575D810U935-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	46				46
1	97	93	89	86	89	85	82	79	71	69	67	58	57	55	46	45	44				39	
2	89	81	75	70	81	75	70	65	63	59	56	51	49	47	41	39	38				33	
3	81	72	65	59	74	66	60	55	55	51	47	46	42	40	37	34	32				28	
4	74	64	56	50	68	59	52	47	49	44	40	41	37	34	33	30	28				24	
5	68	57	49	43	62	52	45	40	44	39	35	37	33	30	30	27	25				21	
6	63	51	43	37	57	47	40	35	40	35	30	33	29	26	27	24	22				19	
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	25	22	19				17	
8	54	42	34	29	49	39	32	27	33	28	24	28	24	21	23	20	17				15	
9	50	38	31	26	46	35	29	24	30	25	21	26	21	19	21	18	16				14	
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	14				12	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7064	7064	7064
5°	7080	6994	7037
10°	7035	6909	6909
15°	6955	6764	6714
20°	6844	6574	6453
25°	6702	6350	6188
30°	6564	6114	5858
35°	6412	5870	5527
40°	6227	5592	5168
45°	6058	5316	4804
50°	5865	4999	4417
55°	5658	4669	3997
60°	5430	4306	3570
65°	5223	3851	3148
70°	4919	3354	2672
75°	4535	2779	2174
80°	3956	2115	1994
85°	3353	1927	1806



TEST NUMBER: P332911-935

CATALOG NUMBER: SA4XXRDIP-C575D810U935-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	82.2	1.9
10°-20°	229.2	5.2
20°-30°	331.0	7.5
30°-40°	375.2	8.5
40°-50°	362.3	8.2
50°-60°	301.3	6.8
60°-70°	208.0	4.7
70°-80°	105.4	2.4
80°-90°	29.7	0.7
90°-100°	57.4	1.3
100°-110°	170.1	3.8
110°-120°	288.6	6.5
120°-130°	380.6	8.6
130°-140°	427.4	9.6
140°-150°	420.0	9.5
150°-160°	353.3	8.0
160°-170°	235.0	5.3
170°-180°	82.3	1.9
0°-30°	642.4	14.5
0°-40°	1017.6	22.9
0°-60°	1681.1	37.9
0°-90°	2024.2	45.6
90°-120°	516.1	11.6
90°-150°	1744.1	39.3
90°-180°	2415.0	54.4
0°-180°	4438.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	875	875	875	875	875	
5°	874	871	863	869	868	83
15°	832	825	809	808	803	234
25°	752	740	713	702	695	347
35°	651	628	596	573	561	406
45°	531	505	466	434	421	409
55°	402	374	332	298	284	359
65°	273	244	202	174	165	270
75°	145	120	89	74	70	154
85°	36	23	21	20	20	41
90°	2	9	15	19	20	4
95°	40	46	51	53	53	45
105°	157	158	160	162	164	166
115°	294	293	292	291	291	289
125°	427	427	427	425	424	381
135°	551	555	555	554	552	426
145°	670	672	673	672	670	419
155°	767	767	767	769	767	353
165°	835	833	832	836	833	235
175°	869	866	865	869	865	82
180°	870	870	870	870	870	



TEST NUMBER: P332911-935

CATALOG NUMBER: SA4XXRDIP-C575D810U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	875.0	875.0	875.0	875.0	875.0	875.0	875.0	875.0	875.0	875.0	875.0
2.5°	877.2	876.7	876.2	875.7	875.3	874.3	873.1	871.8	870.4	869.1	870.4
5°	873.7	873.1	872.5	871.8	871.3	870.1	868.3	866.5	864.7	863.0	864.4
7.5°	865.7	865.1	864.5	863.9	863.2	861.8	859.5	857.1	854.8	852.5	853.4
10°	858.2	857.6	856.8	856.0	855.3	853.6	850.9	848.2	845.5	842.8	843.4
12.5°	848.6	847.7	846.9	846.0	845.2	843.2	840.0	836.8	833.7	830.5	830.9
15°	832.2	830.8	829.5	828.1	826.7	824.2	820.5	816.8	813.0	809.3	809.1
17.5°	812.2	810.2	808.3	806.3	804.4	801.2	796.8	792.3	787.8	783.3	782.6
20°	796.6	794.7	792.7	790.8	788.8	785.4	780.3	775.2	770.2	765.2	764.0
22.5°	779.5	777.3	775.2	772.9	770.8	767.0	761.6	756.1	750.7	745.3	743.5
25°	752.4	749.8	747.0	744.3	741.7	737.3	731.2	725.0	718.9	712.9	710.3
27.5°	724.0	720.7	717.3	713.9	710.5	705.6	699.0	692.6	686.0	679.5	676.4
30°	704.1	700.4	696.7	693.0	689.3	683.9	676.9	669.9	662.9	655.9	652.2
32.5°	683.3	679.1	674.9	670.6	666.5	660.7	653.5	646.3	639.0	631.8	627.5
35°	650.6	645.8	641.0	636.3	631.5	625.4	617.9	610.5	603.0	595.6	590.6
37.5°	615.6	610.7	605.8	600.9	595.9	589.4	581.1	572.8	564.6	556.4	550.7
40°	590.9	586.0	581.1	576.2	571.3	564.6	556.1	547.6	539.2	530.6	524.3
42.5°	567.3	562.2	557.1	551.9	546.7	539.8	530.9	522.0	513.2	504.4	498.0
45°	530.6	525.1	519.6	514.1	508.6	501.4	492.4	483.5	474.6	465.6	458.3
47.5°	492.8	487.1	481.3	475.6	469.9	462.4	453.1	443.9	434.6	425.3	417.8
50°	467.0	461.2	455.4	449.5	443.8	436.1	426.5	417.1	407.5	398.0	390.5
52.5°	440.7	435.1	429.4	423.7	417.9	410.3	400.5	390.7	380.9	371.2	363.6
55°	402.0	396.1	390.1	384.1	378.2	370.3	360.7	351.0	341.3	331.7	323.9
57.5°	363.7	357.5	351.3	345.1	338.9	331.1	321.5	311.9	302.5	292.9	285.1
60°	336.3	330.4	324.4	318.5	312.5	304.8	295.2	285.7	276.2	266.7	258.9
62.5°	311.7	305.5	299.3	293.1	286.9	279.0	269.1	259.4	249.6	239.9	232.7
65°	273.4	267.0	260.5	254.2	247.7	239.8	230.2	220.8	211.2	201.6	195.3
67.5°	233.6	227.4	221.3	215.2	209.1	201.6	192.7	183.8	175.0	166.2	160.7
70°	208.4	202.1	195.9	189.6	183.4	176.0	167.5	159.0	150.5	142.1	137.2
72.5°	181.6	175.9	170.2	164.6	158.9	152.1	144.1	136.1	128.0	120.0	115.9
75°	145.4	139.9	134.4	128.9	123.4	117.1	110.1	103.1	96.1	89.1	85.7
77.5°	108.7	104.0	99.4	94.6	90.0	84.8	79.1	73.5	67.8	62.2	60.2
80°	85.1	80.8	76.5	72.2	67.8	63.5	59.0	54.5	50.0	45.5	45.1
82.5°	64.7	60.8	56.8	52.9	48.9	45.6	43.0	40.5	38.0	35.4	35.0
85°	36.2	33.2	30.2	27.2	24.3	22.6	22.1	21.7	21.2	20.8	20.5
87.5°	12.7	12.1	11.5	10.8	10.2	10.0	10.1	10.2	10.3	10.5	10.5
90°	2.0	3.7	5.3	7.0	8.6	10.0	11.2	12.4	13.6	14.8	15.7
92.5°	14.4	16.3	18.2	20.1	22.0	23.3	24.1	25.0	25.8	26.7	27.2
95°	40.4	41.8	43.0	44.4	45.8	47.0	48.0	49.1	50.1	51.1	51.6
97.5°	70.5	71.6	72.7	73.8	74.8	76.0	77.2	78.4	79.6	80.9	81.5
100°	94.3	94.8	95.4	96.0	96.6	97.6	98.9	100.3	101.6	103.0	103.3
102.5°	119.0	119.2	119.5	119.8	119.9	120.7	121.9	123.1	124.4	125.6	126.1
105°	156.9	157.0	157.1	157.3	157.5	157.8	158.4	159.0	159.6	160.2	160.7
107.5°	196.6	196.7	196.9	197.1	197.3	197.4	197.5	197.6	197.7	197.8	198.2
110°	223.5	223.8	224.0	224.4	224.6	224.7	224.6	224.5	224.3	224.1	223.9



TEST NUMBER: P332911-935

CATALOG NUMBER: SA4XXRDIP-C575D810U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	251.5	251.5	251.6	251.7	251.8	251.6	251.3	251.1	250.8	250.6	250.5
115°	293.5	293.5	293.5	293.5	293.5	293.3	293.0	292.7	292.4	292.1	292.0
117.5°	333.0	333.2	333.3	333.4	333.6	333.5	333.3	333.0	332.9	332.7	332.2
120°	359.5	360.1	360.7	361.3	361.9	361.9	361.4	361.0	360.6	360.2	359.4
122.5°	386.9	387.1	387.4	387.6	387.9	387.9	387.7	387.4	387.3	387.0	386.5
125°	427.4	427.4	427.4	427.4	427.4	427.3	427.2	427.1	426.9	426.8	426.5
127.5°	464.2	464.6	465.1	465.5	466.0	466.1	465.8	465.6	465.4	465.1	464.9
130°	490.0	490.5	490.9	491.4	491.8	492.1	492.1	492.1	492.1	492.1	491.7
132.5°	516.4	516.8	517.1	517.4	517.7	517.8	517.7	517.6	517.5	517.4	517.0
135°	551.3	552.2	553.1	554.0	554.9	555.3	555.3	555.3	555.3	555.3	555.0
137.5°	589.3	589.7	590.0	590.5	590.9	591.2	591.5	591.8	591.9	592.2	591.9
140°	614.6	614.8	615.2	615.4	615.8	615.9	615.9	615.9	615.9	615.9	615.8
142.5°	637.7	638.0	638.3	638.6	638.9	639.0	638.9	638.8	638.6	638.5	638.5
145°	669.8	670.4	671.0	671.6	672.2	672.5	672.7	672.8	673.0	673.1	673.0
147.5°	701.5	702.2	702.9	703.7	704.4	704.7	704.6	704.5	704.3	704.2	704.1
150°	720.9	721.5	722.1	722.7	723.3	723.6	723.6	723.6	723.6	723.6	723.6
152.5°	739.3	739.6	739.9	740.3	740.6	740.9	741.0	741.1	741.2	741.4	741.8
155°	767.3	767.3	767.3	767.3	767.3	767.2	767.2	767.0	766.8	766.7	767.2
157.5°	791.1	790.7	790.5	790.2	790.0	789.8	789.8	789.8	789.7	789.7	790.1
160°	805.0	804.9	804.8	804.6	804.4	804.3	804.2	804.0	803.8	803.7	804.2
162.5°	817.9	817.6	817.2	816.8	816.4	816.1	816.0	815.9	815.7	815.5	816.4
165°	835.3	834.9	834.5	834.0	833.5	833.2	832.8	832.6	832.2	832.0	832.8
167.5°	848.7	848.0	847.4	846.8	846.2	845.8	845.8	845.9	845.9	845.9	846.9
170°	856.2	855.5	854.7	853.9	853.3	852.9	853.1	853.3	853.3	853.5	854.4
172.5°	861.6	861.0	860.3	859.7	859.1	858.8	858.8	858.8	858.8	858.9	859.9
175°	869.0	868.2	867.5	866.8	866.0	865.6	865.4	865.2	865.1	865.0	866.0
177.5°	871.4	870.8	870.2	869.6	869.0	868.7	868.7	868.7	868.7	868.7	869.5
180°	870.3	870.3	870.3	870.3	870.3	870.3	870.3	870.3	870.3	870.3	870.3



TEST NUMBER: P332911-935

CATALOG NUMBER: SA4XXRDIP-C575D810U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	875.0	875.0	875.0	875.0	875.0	875.0	875.0	875.0
2.5°	871.8	873.1	874.3	874.9	874.9	874.7	874.6	874.5
5°	865.9	867.5	868.9	869.5	869.2	868.9	868.6	868.3
7.5°	854.4	855.3	856.4	856.5	856.1	855.6	855.1	854.6
10°	844.0	844.6	845.2	845.2	844.6	844.0	843.4	842.8
12.5°	831.2	831.6	832.0	831.7	830.9	830.1	829.2	828.4
15°	808.7	808.5	808.1	807.5	806.4	805.4	804.3	803.3
17.5°	781.7	780.8	780.0	778.8	777.2	775.7	774.0	772.5
20°	762.8	761.6	760.3	758.8	756.9	754.9	753.0	751.1
22.5°	741.8	739.9	738.1	736.5	734.9	733.3	731.8	730.1
25°	707.8	705.2	702.7	700.8	699.2	697.8	696.3	694.7
27.5°	673.2	670.1	667.0	664.3	662.2	660.0	658.0	655.8
30°	648.5	644.7	641.0	638.0	635.6	633.2	630.9	628.4
32.5°	623.2	618.9	614.5	611.2	609.0	606.7	604.4	602.2
35°	585.5	580.4	575.4	571.5	568.9	566.1	563.4	560.8
37.5°	545.0	539.4	533.7	529.6	526.8	524.2	521.5	518.8
40°	518.1	511.9	505.6	501.2	498.4	495.8	493.1	490.4
42.5°	491.6	485.3	478.9	474.3	471.5	468.7	465.9	463.1
45°	451.1	443.8	436.4	431.4	428.8	426.1	423.4	420.8
47.5°	410.2	402.6	395.0	389.8	386.8	383.9	381.0	378.0
50°	383.1	375.7	368.2	363.1	360.2	357.4	354.6	351.7
52.5°	356.0	348.4	341.0	335.7	332.7	329.8	326.8	323.9
55°	316.2	308.4	300.7	295.4	292.6	289.7	286.9	284.0
57.5°	277.2	269.3	261.5	256.5	254.3	252.2	250.0	247.9
60°	251.2	243.4	235.7	230.7	228.3	225.8	223.5	221.1
62.5°	225.6	218.4	211.3	206.7	204.8	202.9	201.0	199.1
65°	188.9	182.4	176.1	171.9	170.2	168.4	166.6	164.8
67.5°	155.2	149.6	144.1	140.4	138.4	136.5	134.5	132.5
70°	132.2	127.3	122.3	119.2	117.7	116.2	114.7	113.2
72.5°	111.7	107.5	103.2	100.5	99.1	97.7	96.3	95.0
75°	82.2	78.9	75.4	73.3	72.3	71.5	70.6	69.7
77.5°	58.2	56.2	54.2	53.0	52.8	52.5	52.3	52.0
80°	44.7	44.3	43.7	43.5	43.3	43.1	43.0	42.9
82.5°	34.7	34.4	34.1	33.8	33.7	33.5	33.4	33.2
85°	20.1	19.9	19.5	19.5	19.5	19.5	19.5	19.5
87.5°	10.6	10.7	10.7	10.8	11.0	11.2	11.4	11.5
90°	16.6	17.5	18.4	19.0	19.3	19.6	19.9	20.2
92.5°	27.7	28.2	28.8	29.2	29.4	29.5	29.7	29.9
95°	52.1	52.5	53.0	53.2	53.2	53.2	53.2	53.2
97.5°	82.0	82.5	83.1	83.3	83.3	83.3	83.3	83.3
100°	103.6	103.9	104.2	104.4	104.4	104.4	104.4	104.4
102.5°	126.5	126.8	127.3	127.5	127.7	127.8	127.9	128.0
105°	161.1	161.5	162.0	162.5	162.9	163.3	163.8	164.3
107.5°	198.6	199.0	199.4	199.7	199.6	199.6	199.6	199.5
110°	223.5	223.3	222.9	223.0	223.5	223.9	224.4	224.8



TEST NUMBER: P332911-935

CATALOG NUMBER: SA4XXRDIP-C575D810U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	250.4	250.4	250.3	250.3	250.4	250.5	250.6	250.6
115°	291.8	291.7	291.5	291.4	291.3	291.1	290.9	290.8
117.5°	331.7	331.1	330.6	330.2	329.9	329.6	329.3	329.0
120°	358.6	357.8	357.1	356.9	357.2	357.5	357.8	358.1
122.5°	386.0	385.6	385.0	384.5	383.9	383.4	382.9	382.4
125°	426.2	425.9	425.6	425.2	425.0	424.6	424.4	424.0
127.5°	464.5	464.3	463.9	463.6	463.4	463.2	463.0	462.7
130°	491.5	491.1	490.9	490.4	489.8	489.2	488.6	488.0
132.5°	516.8	516.4	516.2	515.9	515.7	515.4	515.1	515.0
135°	554.7	554.4	554.1	553.7	553.3	552.8	552.4	552.0
137.5°	591.4	591.1	590.6	590.5	590.6	590.6	590.7	590.9
140°	615.6	615.4	615.3	615.2	615.0	614.8	614.7	614.6
142.5°	638.4	638.4	638.4	638.3	638.3	638.3	638.3	638.3
145°	672.8	672.7	672.5	672.2	671.8	671.3	670.9	670.5
147.5°	704.0	703.9	703.7	703.6	703.4	703.3	703.2	703.0
150°	723.6	723.6	723.6	723.5	723.4	723.2	723.1	722.9
152.5°	742.1	742.4	742.8	742.8	742.4	742.0	741.7	741.2
155°	767.8	768.4	769.0	769.0	768.4	767.8	767.2	766.7
157.5°	790.6	791.1	791.5	791.4	791.0	790.5	790.0	789.5
160°	804.6	805.0	805.5	805.4	804.6	803.8	803.1	802.4
162.5°	817.2	817.9	818.8	818.8	818.0	817.3	816.6	815.8
165°	833.8	834.7	835.6	835.7	835.1	834.5	833.9	833.4
167.5°	847.7	848.7	849.5	849.5	848.6	847.7	846.8	845.8
170°	855.3	856.2	857.1	857.0	856.0	855.0	853.9	852.8
172.5°	860.9	861.9	863.0	863.0	861.9	860.8	859.8	858.8
175°	867.0	868.1	869.2	869.2	868.1	867.0	866.0	865.0
177.5°	870.4	871.2	872.1	872.0	871.1	870.1	869.2	868.1
180°	870.3	870.3	870.3	870.3	870.3	870.3	870.3	870.3

(END OF REPORT)