

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332528-840

Luminaire Tested: **SA4XXDIP-C350D1205U840-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332528-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXDIP-C350D1205U840-4F0-1E-UDD-A4  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 350 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5939.2 lumens  
Efficiency: N/A  
Efficacy: 140.7 lumens/watt  
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 42.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332528-840  
CATALOG NUMBER: SA4XXDIP-C350D1205U840-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P332528-840

CATALOG NUMBER: SA4XXDIP-C350D1205U840-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	70	70	70	52	52	52	35	35	35	27
1	93	89	85	82	83	79	76	73	62	60	58	46	44	43	31	30	30	23
2	84	77	72	67	75	69	64	60	54	51	48	40	38	36	27	26	25	19
3	77	68	61	56	69	61	55	50	48	44	40	36	33	31	24	23	21	16
4	70	60	53	47	63	54	48	43	43	38	34	32	29	26	22	20	19	14
5	65	54	46	40	57	48	42	37	38	33	30	28	25	23	20	18	16	12
6	59	48	40	35	53	43	36	32	34	29	26	26	22	20	18	16	14	11
7	55	43	36	30	49	39	32	28	31	26	23	23	20	18	16	14	13	10
8	51	39	32	27	45	35	29	24	28	23	20	21	18	16	15	13	11	9
9	47	35	28	23	42	32	26	22	26	21	18	20	16	14	14	12	10	8
10	44	32	26	21	39	29	23	19	24	19	16	18	15	13	13	11	9	7

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	4657	4657	4657	4657
5°	5485	4669	4122	4669
10°	6567	4649	3710	4649
15°	7770	4603	3408	4603
20°	8652	4554	3137	4554
25°	8792	4483	2950	4483
30°	7481	4416	2892	4416
35°	5752	4306	2893	4306
40°	4484	4176	2947	4176
45°	3738	3981	2997	3981
50°	3291	3743	3097	3743
55°	3015	3458	3222	3458
60°	2824	3202	3371	3202
65°	2628	2917	3498	2917
70°	2403	2634	3576	2634
75°	2149	2318	3534	2318
80°	1799	1901	3422	1901
85°	1325	1371	3270	1371



TEST NUMBER: P332528-840

CATALOG NUMBER: SA4XXDIP-C350D1205U840-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	56.2	0.9
10°-20°	173.3	2.9
20°-30°	274.7	4.6
30°-40°	305.7	5.1
40°-50°	278.3	4.7
50°-60°	227.4	3.8
60°-70°	162.4	2.7
70°-80°	89.4	1.5
80°-90°	27.7	0.5
90°-100°	431.4	7.3
100°-110°	897.9	15.1
110°-120°	804.2	13.5
120°-130°	676.5	11.4
130°-140°	564.1	9.5
140°-150°	430.9	7.3
150°-160°	302.9	5.1
160°-170°	178.2	3.0
170°-180°	58.0	1.0
0°-30°	504.2	8.5
0°-40°	809.9	13.6
0°-60°	1315.6	22.2
0°-90°	1595.1	26.9
90°-120°	2133.5	35.9
90°-150°	3805.0	64.1
90°-180°	4344.0	73.1
0°-180°	5939.2	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	577	577	577	577	577	
5°	677	576	509	576	677	69
15°	930	551	408	551	930	263
25°	987	503	331	503	987	435
35°	584	437	294	437	584	370
45°	327	349	262	349	327	258
55°	214	246	229	246	214	193
65°	138	153	183	153	138	136
75°	69	74	113	74	69	73
85°	14	15	35	15	14	18
90°	25	1	25	1	25	20
95°	286	39	286	39	286	444
105°	1651	137	1651	137	1651	1632
115°	1585	242	1585	242	1585	1574
125°	1265	337	1265	337	1265	1149
135°	1131	400	1131	400	1131	873
145°	924	461	924	461	924	585
155°	773	524	773	524	773	361
165°	675	572	675	572	675	193
175°	608	596	608	596	608	59
180°	597	597	597	597	597	



TEST NUMBER: P332528-840

CATALOG NUMBER: SA4XXDIP-C350D1205U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9
2.5°	614.0	613.9	612.0	611.6	610.3	608.5	608.1	605.0	599.0	596.0	595.3
5°	676.8	681.7	675.4	674.2	673.5	665.6	661.6	656.8	645.8	639.3	634.3
7.5°	751.8	752.3	749.6	747.5	741.3	734.5	724.2	713.2	700.0	686.5	676.2
10°	801.1	803.0	799.9	799.5	787.3	779.6	764.4	751.4	736.6	720.1	705.1
12.5°	853.1	850.5	848.9	838.7	836.4	822.4	804.7	791.4	768.5	749.5	729.5
15°	929.7	924.4	921.1	907.1	900.1	880.7	861.8	847.3	817.4	788.9	767.4
17.5°	974.6	979.9	972.2	966.3	948.5	934.8	915.5	884.9	861.6	826.3	799.1
20°	1007.1	1007.6	1003.3	997.3	983.3	966.0	945.0	911.6	883.6	848.5	811.1
22.5°	1015.9	1016.0	1014.2	1008.7	997.9	984.0	962.8	934.8	901.0	862.8	825.5
25°	987.0	986.1	988.3	994.5	990.5	986.1	973.9	953.1	921.6	881.2	841.0
27.5°	879.8	886.5	898.6	913.8	928.6	939.8	942.9	938.7	919.2	886.0	843.8
30°	802.5	810.7	819.8	835.1	864.7	881.7	900.3	914.4	906.6	880.0	840.8
32.5°	717.7	719.7	733.2	750.5	777.7	810.3	839.9	868.6	878.1	864.1	831.4
35°	583.6	587.0	601.6	618.7	652.0	692.0	736.4	776.1	808.8	821.9	805.2
37.5°	476.3	485.8	496.1	514.6	543.9	579.9	626.0	677.4	726.2	758.9	764.5
40°	425.5	431.4	438.8	452.9	477.8	513.1	552.8	611.6	663.5	710.3	725.6
42.5°	385.3	388.8	393.3	406.1	425.0	460.2	496.4	548.2	600.2	656.2	681.9
45°	327.4	331.0	338.7	346.1	360.4	384.8	418.5	461.0	513.4	567.3	614.7
47.5°	285.7	287.9	292.5	300.4	312.7	328.7	356.1	391.6	440.1	492.6	543.0
50°	262.0	263.9	267.4	274.6	284.0	298.3	320.7	354.0	391.9	444.7	494.2
52.5°	243.2	244.0	246.6	251.5	258.9	270.9	289.4	316.9	352.2	399.3	448.6
55°	214.2	215.1	217.5	221.1	227.5	235.2	249.2	269.8	300.6	341.5	384.4
57.5°	190.3	191.0	192.9	194.3	199.7	205.8	216.7	231.4	254.7	289.4	327.6
60°	174.9	174.5	176.8	178.0	181.7	186.9	195.3	209.3	229.6	257.6	292.8
62.5°	160.1	159.4	161.4	163.0	165.0	169.5	176.3	187.3	203.9	229.1	259.5
65°	137.6	136.7	137.9	139.9	141.7	144.1	149.2	159.0	172.1	190.3	213.4
67.5°	115.2	116.2	116.4	117.3	118.5	121.7	125.1	132.1	141.4	155.9	175.5
70°	101.8	102.1	103.0	103.0	103.7	106.6	109.5	113.5	122.6	136.0	152.0
72.5°	88.5	89.5	89.1	89.8	90.4	92.3	94.3	98.3	105.9	115.9	129.5
75°	68.9	69.6	69.6	69.8	70.5	71.2	72.9	75.7	81.3	88.7	98.0
77.5°	50.2	50.3	50.6	51.5	51.5	52.6	53.8	56.1	58.9	63.9	69.7
80°	38.7	39.2	39.0	39.5	39.5	40.4	40.9	43.7	44.9	48.3	52.8
82.5°	28.4	28.9	28.8	29.5	29.9	30.1	30.7	31.9	33.1	36.1	37.9
85°	14.3	14.8	14.3	14.8	15.6	15.8	16.5	16.8	17.7	18.4	20.1
87.5°	9.1	9.7	9.9	9.9	10.0	10.2	10.2	9.8	10.3	10.7	11.0
90°	24.6	24.6	25.9	24.6	23.4	23.4	22.3	21.1	20.0	21.1	18.8
92.5°	90.4	90.4	94.3	100.7	114.5	138.0	173.4	230.5	310.0	372.2	325.8
95°	286.3	301.5	322.8	359.1	416.6	530.4	687.6	869.5	983.4	956.3	721.6
97.5°	765.4	789.7	825.0	895.5	979.9	1102.4	1217.1	1284.8	1235.5	1007.3	675.4
100°	1076.1	1085.5	1120.6	1192.2	1294.3	1381.2	1438.7	1415.2	1243.9	943.4	612.6
102.5°	1346.5	1353.9	1391.0	1442.9	1505.5	1541.7	1525.0	1408.7	1173.5	863.6	570.3
105°	1651.0	1658.1	1674.6	1683.9	1681.5	1633.5	1517.3	1314.2	1045.5	769.8	533.9
107.5°	1764.2	1761.1	1749.4	1722.6	1664.7	1560.0	1396.4	1180.2	942.3	717.2	527.4
110°	1766.1	1755.5	1734.3	1685.1	1601.7	1472.7	1302.5	1099.5	890.7	699.4	529.3



TEST NUMBER: P332528-840

CATALOG NUMBER: SA4XXDIP-C350D1205U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1710.7	1693.5	1664.0	1604.4	1509.7	1380.7	1219.9	1040.4	861.5	690.9	534.8
115°	1585.4	1576.0	1538.4	1468.0	1375.3	1262.6	1125.4	981.0	834.4	686.5	545.6
117.5°	1458.3	1451.1	1413.1	1353.9	1274.9	1179.3	1071.4	951.9	822.1	685.3	557.1
120°	1387.0	1374.1	1343.6	1292.0	1225.1	1141.8	1047.9	938.8	815.6	685.3	565.6
122.5°	1330.7	1317.8	1292.0	1247.9	1191.3	1118.3	1032.9	927.5	808.1	684.4	574.1
125°	1265.0	1258.0	1235.7	1201.6	1154.7	1090.1	1009.2	908.3	795.6	683.0	586.7
127.5°	1226.5	1219.5	1200.7	1170.4	1123.3	1062.0	981.3	884.7	778.9	680.3	596.8
130°	1204.0	1196.9	1178.1	1148.8	1100.8	1038.5	958.8	866.1	768.6	679.4	604.3
132.5°	1178.6	1171.5	1153.8	1120.6	1073.5	1011.3	933.4	846.3	759.2	678.5	610.9
135°	1131.3	1124.2	1105.4	1072.6	1025.6	966.9	895.3	819.1	745.2	677.1	620.8
137.5°	1072.6	1064.1	1048.6	1016.2	972.3	919.3	859.0	794.5	733.0	676.8	626.6
140°	1030.3	1020.9	1004.5	978.7	937.6	888.3	835.5	780.3	726.4	675.9	631.4
142.5°	985.2	978.7	964.1	940.2	903.8	861.1	815.8	767.2	720.7	675.9	635.1
145°	923.5	917.7	905.9	886.0	856.7	823.7	788.6	748.7	711.1	673.6	637.2
147.5°	868.8	866.8	857.8	840.7	819.1	793.2	765.1	733.5	702.5	669.3	638.3
150°	837.9	836.7	829.6	814.4	795.6	774.5	751.0	724.1	695.9	666.5	638.3
152.5°	809.7	808.5	804.3	791.8	775.9	758.5	736.9	713.7	688.3	661.9	636.5
155°	773.4	773.4	769.8	760.4	748.7	734.6	717.0	698.2	677.1	654.8	633.7
157.5°	741.4	741.4	739.3	732.3	723.4	712.1	697.3	681.6	665.6	647.5	630.7
160°	721.6	721.6	720.5	713.5	706.4	697.0	684.1	671.3	657.1	641.9	627.8
162.5°	702.9	703.9	702.7	695.6	690.4	682.1	672.0	660.9	649.6	636.2	625.0
165°	674.8	675.9	677.1	672.4	667.7	661.9	653.6	646.6	637.2	627.8	619.6
167.5°	652.5	653.4	653.6	650.6	648.2	644.7	638.1	632.8	625.9	619.4	614.0
170°	638.3	638.3	639.5	638.3	636.0	632.5	627.8	624.3	618.4	613.7	610.2
172.5°	624.3	626.1	627.3	626.1	624.7	622.2	619.4	616.7	611.9	608.0	606.4
175°	607.8	610.2	612.6	610.2	610.2	610.2	607.8	606.7	604.3	602.0	602.0
177.5°	598.2	600.1	602.0	601.1	602.0	601.1	601.1	600.1	599.2	598.2	598.2
180°	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3



TEST NUMBER: P332528-840

CATALOG NUMBER: SA4XXDIP-C350D1205U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9
2.5°	595.5	592.8	590.9	589.4	585.2	582.7	580.8	578.1	575.0	571.8	567.7
5°	629.2	621.2	615.2	606.1	597.5	590.4	582.9	576.2	568.2	559.3	552.8
7.5°	664.8	652.7	637.2	623.8	608.6	595.5	583.8	571.8	559.3	547.0	535.9
10°	687.4	671.9	654.6	634.3	615.2	598.2	582.5	567.1	552.3	537.6	524.8
12.5°	711.7	692.3	666.8	643.1	621.7	599.0	580.0	561.2	543.3	527.8	513.0
15°	744.3	716.3	686.9	655.1	626.9	600.4	574.3	550.7	530.6	510.0	495.6
17.5°	764.3	729.6	696.1	662.9	628.7	595.2	567.1	539.9	514.7	494.3	476.3
20°	777.5	743.1	701.3	668.0	627.4	593.0	560.5	530.1	503.8	482.1	463.4
22.5°	788.9	749.2	707.3	663.6	623.2	586.6	551.1	520.6	493.7	470.8	452.9
25°	795.2	749.5	704.1	660.6	614.7	571.5	539.2	503.3	474.6	450.5	431.4
27.5°	795.9	747.0	695.6	647.3	600.0	559.7	519.0	486.9	457.2	431.6	413.2
30°	793.8	742.9	687.6	635.3	587.7	544.0	508.6	473.7	443.3	418.0	398.9
32.5°	787.0	734.1	677.3	621.9	572.6	529.8	493.3	460.1	430.5	405.6	385.5
35°	767.7	715.3	654.9	597.2	546.8	503.6	470.6	436.9	407.3	383.6	364.3
37.5°	737.4	690.1	628.6	569.1	519.5	476.1	443.3	412.9	386.2	362.1	342.3
40°	711.0	669.4	607.7	549.7	496.1	454.8	424.2	396.3	369.7	347.0	328.1
42.5°	680.6	644.4	587.5	526.0	474.3	432.8	403.0	377.9	352.9	331.9	313.1
45°	626.4	602.5	549.0	492.1	438.3	399.1	370.7	348.7	327.7	307.1	291.3
47.5°	564.1	552.2	507.2	453.1	402.1	363.5	338.8	318.5	300.0	282.7	268.7
50°	522.2	516.4	477.6	425.5	376.7	340.3	315.5	298.0	282.3	267.0	253.8
52.5°	480.9	480.7	445.6	397.9	352.7	317.8	293.1	276.8	263.2	250.7	238.9
55°	417.8	424.4	397.0	354.5	314.1	282.5	260.2	245.7	236.1	225.9	217.0
57.5°	359.8	370.9	348.2	310.7	277.0	248.0	228.6	217.7	207.5	201.3	194.8
60°	321.9	332.4	314.8	283.3	251.5	226.6	208.1	198.3	189.6	185.2	180.7
62.5°	288.3	297.6	284.6	255.3	227.7	203.8	188.2	178.8	172.9	168.2	165.2
65°	240.2	248.1	236.8	215.6	191.9	172.8	160.2	152.7	147.0	145.1	141.7
67.5°	194.2	201.4	195.3	177.2	158.2	143.7	133.8	126.7	123.3	121.7	119.3
70°	166.8	174.0	167.5	151.8	137.1	125.0	115.6	111.6	108.1	107.3	104.0
72.5°	143.7	148.6	142.1	129.8	117.3	107.0	99.8	95.5	93.7	92.4	90.6
75°	107.8	112.1	107.8	98.3	89.4	82.2	76.0	74.3	72.2	71.5	70.3
77.5°	76.2	80.0	76.7	70.8	64.1	58.6	55.2	53.1	52.6	51.4	52.0
80°	58.3	60.7	57.6	53.5	48.3	44.4	42.1	40.9	39.5	39.0	39.9
82.5°	41.9	42.9	41.3	38.6	34.7	32.2	30.6	29.2	28.9	29.0	29.0
85°	21.7	21.5	21.3	18.9	17.7	16.1	15.0	14.8	14.5	15.0	15.6
87.5°	10.5	10.7	9.2	8.4	7.6	6.8	5.9	5.3	5.9	6.8	7.2
90°	16.5	16.5	9.4	9.4	8.2	7.1	3.5	1.2	3.5	7.1	8.2
92.5°	237.0	146.0	86.3	62.0	44.8	30.5	19.5	13.3	19.5	30.5	44.8
95°	441.2	248.7	146.7	97.4	69.3	54.0	42.2	38.7	42.2	54.0	69.3
97.5°	396.7	237.7	159.2	117.9	93.6	79.6	69.5	69.5	69.5	79.6	93.6
100°	373.1	240.5	171.4	133.8	111.5	97.4	89.2	89.2	89.2	97.4	111.5
102.5°	366.6	249.9	187.3	151.6	130.3	117.1	109.9	108.0	109.9	117.1	130.3
105°	369.6	272.3	215.9	181.9	160.8	146.7	140.8	137.3	140.8	146.7	160.8
107.5°	387.0	298.3	246.7	213.1	192.9	177.9	172.0	169.7	172.0	177.9	192.9
110°	400.1	318.0	266.4	234.7	213.6	199.4	193.6	191.3	193.6	199.4	213.6





TEST NUMBER: P332528-840

CATALOG NUMBER: SA4XXDIP-C350D1205U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	414.2	336.8	287.0	255.4	234.2	221.1	214.3	212.0	214.3	221.1	234.2
115°	436.6	366.1	319.2	287.5	265.2	253.5	245.3	241.8	245.3	253.5	265.2
117.5°	459.3	394.6	349.9	317.1	296.2	283.3	276.0	272.7	276.0	283.3	296.2
120°	475.2	414.2	369.6	336.8	316.8	304.0	295.7	293.4	295.7	304.0	316.8
122.5°	490.3	433.0	388.4	356.5	334.7	322.8	314.5	312.1	314.5	322.8	334.7
125°	512.8	458.8	416.6	383.7	361.4	348.5	341.4	336.8	341.4	348.5	361.4
127.5°	532.3	482.7	441.9	408.8	385.6	370.8	362.3	358.6	362.3	370.8	385.6
130°	544.5	498.8	458.8	424.7	402.5	384.9	375.5	370.8	375.5	384.9	402.5
132.5°	556.7	511.9	472.0	439.8	415.7	399.0	386.8	383.0	386.8	399.0	415.7
135°	572.7	530.4	491.7	461.2	436.6	416.6	404.9	400.1	404.9	416.6	436.6
137.5°	583.9	544.5	508.4	479.3	453.6	434.6	421.7	417.3	421.7	434.6	453.6
140°	591.4	553.9	518.7	490.5	465.9	446.0	433.0	429.5	433.0	446.0	465.9
142.5°	597.0	562.3	528.1	500.8	477.2	458.1	446.2	442.6	446.2	458.1	477.2
145°	603.2	571.5	541.0	515.1	492.8	476.5	464.7	461.2	464.7	476.5	492.8
147.5°	608.5	580.9	552.2	529.0	510.5	493.5	483.2	482.0	483.2	493.5	510.5
150°	611.4	585.5	559.8	537.5	519.9	505.7	496.3	495.2	496.3	505.7	519.9
152.5°	613.3	589.4	566.3	545.9	530.2	517.1	507.7	507.4	507.7	517.1	530.2
155°	614.9	594.9	575.0	557.4	544.5	532.7	525.7	524.5	525.7	532.7	544.5
157.5°	614.9	599.0	582.1	568.2	556.9	547.8	541.2	541.2	541.2	547.8	556.9
160°	614.9	600.8	586.7	573.8	564.4	556.2	551.5	551.5	551.5	556.2	564.4
162.5°	614.9	602.7	589.6	579.5	571.0	563.7	560.0	560.9	560.0	563.7	571.0
165°	612.6	603.2	592.6	585.5	579.7	573.8	571.5	571.5	571.5	573.8	579.7
167.5°	609.8	602.9	595.2	589.8	586.5	582.1	580.9	582.1	580.9	582.1	586.5
170°	607.8	602.0	596.1	592.6	590.3	586.7	585.5	586.7	585.5	586.7	590.3
172.5°	606.0	601.1	597.0	594.5	593.1	590.5	590.3	591.4	590.3	590.5	593.1
175°	603.2	599.7	597.3	597.3	596.1	594.9	594.9	596.1	594.9	594.9	596.1
177.5°	600.1	598.2	597.3	597.3	597.3	596.3	597.3	598.2	597.3	596.3	597.3
180°	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3



TEST NUMBER: P332528-840

CATALOG NUMBER: SA4XXDIP-C350D1205U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9
2.5°	565.8	564.1	561.7	558.3	555.3	552.3	551.5	550.4	552.7	550.8	550.2
5°	547.3	542.3	535.8	528.5	524.1	518.0	516.7	514.3	511.9	511.7	509.3
7.5°	527.7	520.3	511.8	504.3	497.4	490.5	486.0	485.1	481.6	479.5	477.2
10°	515.0	505.9	496.1	489.0	480.9	473.7	468.7	465.9	463.4	460.8	458.4
12.5°	500.2	490.5	482.4	474.6	465.0	459.6	451.3	446.4	445.9	445.9	439.7
15°	482.8	473.2	460.8	449.8	444.5	434.0	429.5	423.7	420.2	416.6	413.7
17.5°	462.9	451.0	441.3	428.7	418.7	410.3	404.3	400.9	395.5	390.4	386.8
20°	450.5	437.9	427.6	414.1	403.2	392.9	387.9	383.1	379.1	374.8	370.7
22.5°	437.9	424.6	412.1	399.1	388.9	378.0	373.1	366.7	362.8	360.4	356.4
25°	418.0	403.6	389.3	376.9	366.4	356.8	350.4	345.4	341.0	339.1	336.5
27.5°	396.4	382.1	368.3	354.2	342.2	335.3	330.1	326.4	323.9	321.3	320.1
30°	382.6	367.8	353.0	339.8	328.9	321.9	317.2	314.6	312.7	311.4	310.2
32.5°	368.7	354.1	338.5	326.5	316.6	310.4	306.8	304.2	303.3	302.9	302.4
35°	346.3	331.5	317.2	306.4	297.1	294.7	291.5	290.1	289.6	291.3	292.1
37.5°	324.7	310.9	297.7	287.3	281.1	277.7	276.6	276.7	278.4	279.8	281.6
40°	310.7	297.3	284.9	275.8	270.0	267.9	267.4	268.6	270.5	272.3	274.2
42.5°	297.1	284.0	272.7	264.2	260.1	258.1	258.4	259.6	262.4	264.4	267.2
45°	276.1	265.1	254.1	247.1	243.8	244.3	244.3	246.4	249.0	252.2	255.3
47.5°	256.2	245.1	236.1	230.2	228.5	228.1	229.4	232.3	236.0	239.8	244.2
50°	242.9	232.3	224.4	219.1	217.2	217.9	219.8	222.5	227.0	231.9	236.4
52.5°	229.2	219.6	212.4	207.5	206.1	207.4	209.3	213.5	217.5	222.7	228.1
55°	208.1	200.1	194.3	190.8	190.3	191.0	193.1	197.6	203.4	209.8	215.1
57.5°	187.2	180.4	175.1	172.7	172.9	173.6	177.1	182.5	188.6	195.5	202.3
60°	173.0	166.8	162.5	160.6	160.9	162.3	166.6	171.6	179.3	185.9	193.1
62.5°	159.7	154.2	150.1	148.3	148.0	151.2	155.3	160.5	168.1	175.6	183.4
65°	138.1	133.8	130.5	129.6	130.3	132.7	137.9	144.8	151.3	159.2	167.3
67.5°	117.1	113.6	111.3	111.7	112.6	116.1	120.5	126.4	133.8	142.0	150.0
70°	103.7	100.4	98.5	98.7	100.2	104.4	108.3	114.2	122.1	130.5	137.1
72.5°	90.0	87.8	86.0	87.1	88.5	91.4	96.2	102.2	109.2	116.9	124.0
75°	69.1	69.1	68.2	68.9	71.0	73.8	77.5	83.6	90.6	96.8	102.5
77.5°	51.2	50.7	51.3	52.2	53.4	56.9	61.0	65.4	70.6	76.9	81.6
80°	39.2	39.5	40.6	42.1	42.5	45.1	49.5	53.5	57.6	62.8	67.4
82.5°	29.5	29.7	30.3	32.1	32.6	35.4	38.2	42.2	45.9	49.5	53.2
85°	16.1	16.1	17.2	18.0	19.1	21.0	22.7	25.1	28.5	30.8	34.4
87.5°	8.0	8.0	10.2	10.5	11.6	13.0	13.1	15.6	16.5	17.7	19.4
90°	9.4	9.4	16.5	16.5	18.8	21.1	20.0	21.1	22.3	23.4	23.4
92.5°	62.0	86.3	146.0	237.0	325.8	372.2	310.0	230.5	173.4	138.0	114.5
95°	97.4	146.7	248.7	441.2	721.6	956.3	983.4	869.5	687.6	530.4	416.6
97.5°	117.9	159.2	237.7	396.7	675.4	1007.3	1235.5	1284.8	1217.1	1102.4	979.9
100°	133.8	171.4	240.5	373.1	612.6	943.4	1243.9	1415.2	1438.7	1381.2	1294.3
102.5°	151.6	187.3	249.9	366.6	570.3	863.6	1173.5	1408.7	1525.0	1541.7	1505.5
105°	181.9	215.9	272.3	369.6	533.9	769.8	1045.5	1314.2	1517.3	1633.5	1681.5
107.5°	213.1	246.7	298.3	387.0	527.4	717.2	942.3	1180.2	1396.4	1560.0	1664.7
110°	234.7	266.4	318.0	400.1	529.3	699.4	890.7	1099.5	1302.5	1472.7	1601.7



TEST NUMBER: P332528-840

CATALOG NUMBER: SA4XXDIP-C350D1205U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	255.4	287.0	336.8	414.2	534.8	690.9	861.5	1040.4	1219.9	1380.7	1509.7
115°	287.5	319.2	366.1	436.6	545.6	686.5	834.4	981.0	1125.4	1262.6	1375.3
117.5°	317.1	349.9	394.6	459.3	557.1	685.3	822.1	951.9	1071.4	1179.3	1274.9
120°	336.8	369.6	414.2	475.2	565.6	685.3	815.6	938.8	1047.9	1141.8	1225.1
122.5°	356.5	388.4	433.0	490.3	574.1	684.4	808.1	927.5	1032.9	1118.3	1191.3
125°	383.7	416.6	458.8	512.8	586.7	683.0	795.6	908.3	1009.2	1090.1	1154.7
127.5°	408.8	441.9	482.7	532.3	596.8	680.3	778.9	884.7	981.3	1062.0	1123.3
130°	424.7	458.8	498.8	544.5	604.3	679.4	768.6	866.1	958.8	1038.5	1100.8
132.5°	439.8	472.0	511.9	556.7	610.9	678.5	759.2	846.3	933.4	1011.3	1073.5
135°	461.2	491.7	530.4	572.7	620.8	677.1	745.2	819.1	895.3	966.9	1025.6
137.5°	479.3	508.4	544.5	583.9	626.6	676.8	733.0	794.5	859.0	919.3	972.3
140°	490.5	518.7	553.9	591.4	631.4	675.9	726.4	780.3	835.5	888.3	937.6
142.5°	500.8	528.1	562.3	597.0	635.1	675.9	720.7	767.2	815.8	861.1	903.8
145°	515.1	541.0	571.5	603.2	637.2	673.6	711.1	748.7	788.6	823.7	856.7
147.5°	529.0	552.2	580.9	608.5	638.3	669.3	702.5	733.5	765.1	793.2	819.1
150°	537.5	559.8	585.5	611.4	638.3	666.5	695.9	724.1	751.0	774.5	795.6
152.5°	545.9	566.3	589.4	613.3	636.5	661.9	688.3	713.7	736.9	758.5	775.9
155°	557.4	575.0	594.9	614.9	633.7	654.8	677.1	698.2	717.0	734.6	748.7
157.5°	568.2	582.1	599.0	614.9	630.7	647.5	665.6	681.6	697.3	712.1	723.4
160°	573.8	586.7	600.8	614.9	627.8	641.9	657.1	671.3	684.1	697.0	706.4
162.5°	579.5	589.6	602.7	614.9	625.0	636.2	649.6	660.9	672.0	682.1	690.4
165°	585.5	592.6	603.2	612.6	619.6	627.8	637.2	646.6	653.6	661.9	667.7
167.5°	589.8	595.2	602.9	609.8	614.0	619.4	625.9	632.8	638.1	644.7	648.2
170°	592.6	596.1	602.0	607.8	610.2	613.7	618.4	624.3	627.8	632.5	636.0
172.5°	594.5	597.0	601.1	606.0	606.4	608.0	611.9	616.7	619.4	622.2	624.7
175°	597.3	597.3	599.7	603.2	602.0	602.0	604.3	606.7	607.8	610.2	610.2
177.5°	597.3	597.3	598.2	600.1	598.2	598.2	599.2	600.1	601.1	601.1	602.0
180°	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3



TEST NUMBER: P332528-840

CATALOG NUMBER: SA4XXDIP-C350D1205U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9
2.5°	549.8	549.5	548.1	547.9	548.1	549.5	549.8	550.2	550.8	552.7	550.4
5°	507.9	506.6	505.9	508.6	505.9	506.6	507.9	509.3	511.7	511.9	514.3
7.5°	476.3	475.3	473.2	472.5	473.2	475.3	476.3	477.2	479.5	481.6	485.1
10°	456.1	455.0	453.1	452.6	453.1	455.0	456.1	458.4	460.8	463.4	465.9
12.5°	436.5	434.6	434.2	434.7	434.2	434.6	436.5	439.7	445.9	445.9	446.4
15°	410.6	409.6	407.0	407.8	407.0	409.6	410.6	413.7	416.6	420.2	423.7
17.5°	385.1	384.0	380.7	383.5	380.7	384.0	385.1	386.8	390.4	395.5	400.9
20°	369.0	367.1	365.5	365.2	365.5	367.1	369.0	370.7	374.8	379.1	383.1
22.5°	353.8	352.0	351.8	350.3	351.8	352.0	353.8	356.4	360.4	362.8	366.7
25°	334.6	333.0	332.4	331.2	332.4	333.0	334.6	336.5	339.1	341.0	345.4
27.5°	319.9	319.1	318.2	318.6	318.2	319.1	319.9	320.1	321.3	323.9	326.4
30°	310.9	310.7	310.2	310.2	310.2	310.7	310.9	310.2	311.4	312.7	314.6
32.5°	303.5	303.5	303.8	303.8	303.8	303.5	303.5	302.4	302.9	303.3	304.2
35°	293.1	293.8	294.2	293.5	294.2	293.8	293.1	292.1	291.3	289.6	290.1
37.5°	283.6	284.3	285.0	285.8	285.0	284.3	283.6	281.6	279.8	278.4	276.7
40°	276.3	277.9	278.4	279.6	278.4	277.9	276.3	274.2	272.3	270.5	268.6
42.5°	269.4	271.2	272.5	272.8	272.5	271.2	269.4	267.2	264.4	262.4	259.6
45°	258.8	260.7	262.5	262.5	262.5	260.7	258.8	255.3	252.2	249.0	246.4
47.5°	247.9	250.6	252.4	252.8	252.4	250.6	247.9	244.2	239.8	236.0	232.3
50°	240.4	243.8	245.5	246.6	245.5	243.8	240.4	236.4	231.9	227.0	222.5
52.5°	233.2	236.5	238.7	239.3	238.7	236.5	233.2	228.1	222.7	217.5	213.5
55°	220.6	225.4	228.0	228.9	228.0	225.4	220.6	215.1	209.8	203.4	197.6
57.5°	208.7	213.2	216.2	216.9	216.2	213.2	208.7	202.3	195.5	188.6	182.5
60°	199.5	204.4	208.1	208.8	208.1	204.4	199.5	193.1	185.9	179.3	171.6
62.5°	190.2	195.2	198.6	200.5	198.6	195.2	190.2	183.4	175.6	168.1	160.5
65°	174.0	179.0	182.4	183.1	182.4	179.0	174.0	167.3	159.2	151.3	144.8
67.5°	156.3	161.4	163.5	164.9	163.5	161.4	156.3	150.0	142.0	133.8	126.4
70°	143.9	147.9	150.4	151.5	150.4	147.9	143.9	137.1	130.5	122.1	114.2
72.5°	129.8	134.0	136.7	137.0	136.7	134.0	129.8	124.0	116.9	109.2	102.2
75°	108.1	111.9	113.3	113.3	113.3	111.9	108.1	102.5	96.8	90.6	83.6
77.5°	85.5	87.5	89.3	89.7	89.3	87.5	85.5	81.6	76.9	70.6	65.4
80°	71.0	72.2	73.6	73.6	73.6	72.2	71.0	67.4	62.8	57.6	53.5
82.5°	56.0	57.1	58.5	58.3	58.5	57.1	56.0	53.2	49.5	45.9	42.2
85°	33.9	36.1	35.9	35.3	35.9	36.1	33.9	34.4	30.8	28.5	25.1
87.5°	20.2	20.6	21.0	21.4	21.0	20.6	20.2	19.4	17.7	16.5	15.6
90°	24.6	25.9	24.6	24.6	24.6	25.9	24.6	23.4	23.4	22.3	21.1
92.5°	100.7	94.3	90.4	90.4	90.4	94.3	100.7	114.5	138.0	173.4	230.5
95°	359.1	322.8	301.5	286.3	301.5	322.8	359.1	416.6	530.4	687.6	869.5
97.5°	895.5	825.0	789.7	765.4	789.7	825.0	895.5	979.9	1102.4	1217.1	1284.8
100°	1192.2	1120.6	1085.5	1076.1	1085.5	1120.6	1192.2	1294.3	1381.2	1438.7	1415.2
102.5°	1442.9	1391.0	1353.9	1346.5	1353.9	1391.0	1442.9	1505.5	1541.7	1525.0	1408.7
105°	1683.9	1674.6	1658.1	1651.0	1658.1	1674.6	1683.9	1681.5	1633.5	1517.3	1314.2
107.5°	1722.6	1749.4	1761.1	1764.2	1761.1	1749.4	1722.6	1664.7	1560.0	1396.4	1180.2
110°	1685.1	1734.3	1755.5	1766.1	1755.5	1734.3	1685.1	1601.7	1472.7	1302.5	1099.5



TEST NUMBER: P332528-840

CATALOG NUMBER: SA4XXDIP-C350D1205U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1604.4	1664.0	1693.5	1710.7	1693.5	1664.0	1604.4	1509.7	1380.7	1219.9	1040.4
115°	1468.0	1538.4	1576.0	1585.4	1576.0	1538.4	1468.0	1375.3	1262.6	1125.4	981.0
117.5°	1353.9	1413.1	1451.1	1458.3	1451.1	1413.1	1353.9	1274.9	1179.3	1071.4	951.9
120°	1292.0	1343.6	1374.1	1387.0	1374.1	1343.6	1292.0	1225.1	1141.8	1047.9	938.8
122.5°	1247.9	1292.0	1317.8	1330.7	1317.8	1292.0	1247.9	1191.3	1118.3	1032.9	927.5
125°	1201.6	1235.7	1258.0	1265.0	1258.0	1235.7	1201.6	1154.7	1090.1	1009.2	908.3
127.5°	1170.4	1200.7	1219.5	1226.5	1219.5	1200.7	1170.4	1123.3	1062.0	981.3	884.7
130°	1148.8	1178.1	1196.9	1204.0	1196.9	1178.1	1148.8	1100.8	1038.5	958.8	866.1
132.5°	1120.6	1153.8	1171.5	1178.6	1171.5	1153.8	1120.6	1073.5	1011.3	933.4	846.3
135°	1072.6	1105.4	1124.2	1131.3	1124.2	1105.4	1072.6	1025.6	966.9	895.3	819.1
137.5°	1016.2	1048.6	1064.1	1072.6	1064.1	1048.6	1016.2	972.3	919.3	859.0	794.5
140°	978.7	1004.5	1020.9	1030.3	1020.9	1004.5	978.7	937.6	888.3	835.5	780.3
142.5°	940.2	964.1	978.7	985.2	978.7	964.1	940.2	903.8	861.1	815.8	767.2
145°	886.0	905.9	917.7	923.5	917.7	905.9	886.0	856.7	823.7	788.6	748.7
147.5°	840.7	857.8	866.8	868.8	866.8	857.8	840.7	819.1	793.2	765.1	733.5
150°	814.4	829.6	836.7	837.9	836.7	829.6	814.4	795.6	774.5	751.0	724.1
152.5°	791.8	804.3	808.5	809.7	808.5	804.3	791.8	775.9	758.5	736.9	713.7
155°	760.4	769.8	773.4	773.4	773.4	769.8	760.4	748.7	734.6	717.0	698.2
157.5°	732.3	739.3	741.4	741.4	741.4	739.3	732.3	723.4	712.1	697.3	681.6
160°	713.5	720.5	721.6	721.6	721.6	720.5	713.5	706.4	697.0	684.1	671.3
162.5°	695.6	702.7	703.9	702.9	703.9	702.7	695.6	690.4	682.1	672.0	660.9
165°	672.4	677.1	675.9	674.8	675.9	677.1	672.4	667.7	661.9	653.6	646.6
167.5°	650.6	653.6	653.4	652.5	653.4	653.6	650.6	648.2	644.7	638.1	632.8
170°	638.3	639.5	638.3	638.3	638.3	639.5	638.3	636.0	632.5	627.8	624.3
172.5°	626.1	627.3	626.1	624.3	626.1	627.3	626.1	624.7	622.2	619.4	616.7
175°	610.2	612.6	610.2	607.8	610.2	612.6	610.2	610.2	610.2	607.8	606.7
177.5°	601.1	602.0	600.1	598.2	600.1	602.0	601.1	602.0	601.1	601.1	600.1
180°	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3



TEST NUMBER: P332528-840

CATALOG NUMBER: SA4XXDIP-C350D1205U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9
2.5°	551.5	552.3	555.3	558.3	561.7	564.1	565.8	567.7	571.8	575.0	578.1
5°	516.7	518.0	524.1	528.5	535.8	542.3	547.3	552.8	559.3	568.2	576.2
7.5°	486.0	490.5	497.4	504.3	511.8	520.3	527.7	535.9	547.0	559.3	571.8
10°	468.7	473.7	480.9	489.0	496.1	505.9	515.0	524.8	537.6	552.3	567.1
12.5°	451.3	459.6	465.0	474.6	482.4	490.5	500.2	513.0	527.8	543.3	561.2
15°	429.5	434.0	444.5	449.8	460.8	473.2	482.8	495.6	510.0	530.6	550.7
17.5°	404.3	410.3	418.7	428.7	441.3	451.0	462.9	476.3	494.3	514.7	539.9
20°	387.9	392.9	403.2	414.1	427.6	437.9	450.5	463.4	482.1	503.8	530.1
22.5°	373.1	378.0	388.9	399.1	412.1	424.6	437.9	452.9	470.8	493.7	520.6
25°	350.4	356.8	366.4	376.9	389.3	403.6	418.0	431.4	450.5	474.6	503.3
27.5°	330.1	335.3	342.2	354.2	368.3	382.1	396.4	413.2	431.6	457.2	486.9
30°	317.2	321.9	328.9	339.8	353.0	367.8	382.6	398.9	418.0	443.3	473.7
32.5°	306.8	310.4	316.6	326.5	338.5	354.1	368.7	385.5	405.6	430.5	460.1
35°	291.5	294.7	297.1	306.4	317.2	331.5	346.3	364.3	383.6	407.3	436.9
37.5°	276.6	277.7	281.1	287.3	297.7	310.9	324.7	342.3	362.1	386.2	412.9
40°	267.4	267.9	270.0	275.8	284.9	297.3	310.7	328.1	347.0	369.7	396.3
42.5°	258.4	258.1	260.1	264.2	272.7	284.0	297.1	313.1	331.9	352.9	377.9
45°	244.3	244.3	243.8	247.1	254.1	265.1	276.1	291.3	307.1	327.7	348.7
47.5°	229.4	228.1	228.5	230.2	236.1	245.1	256.2	268.7	282.7	300.0	318.5
50°	219.8	217.9	217.2	219.1	224.4	232.3	242.9	253.8	267.0	282.3	298.0
52.5°	209.3	207.4	206.1	207.5	212.4	219.6	229.2	238.9	250.7	263.2	276.8
55°	193.1	191.0	190.3	190.8	194.3	200.1	208.1	217.0	225.9	236.1	245.7
57.5°	177.1	173.6	172.9	172.7	175.1	180.4	187.2	194.8	201.3	207.5	217.7
60°	166.6	162.3	160.9	160.6	162.5	166.8	173.0	180.7	185.2	189.6	198.3
62.5°	155.3	151.2	148.0	148.3	150.1	154.2	159.7	165.2	168.2	172.9	178.8
65°	137.9	132.7	130.3	129.6	130.5	133.8	138.1	141.7	145.1	147.0	152.7
67.5°	120.5	116.1	112.6	111.7	111.3	113.6	117.1	119.3	121.7	123.3	126.7
70°	108.3	104.4	100.2	98.7	98.5	100.4	103.7	104.0	107.3	108.1	111.6
72.5°	96.2	91.4	88.5	87.1	86.0	87.8	90.0	90.6	92.4	93.7	95.5
75°	77.5	73.8	71.0	68.9	68.2	69.1	69.1	70.3	71.5	72.2	74.3
77.5°	61.0	56.9	53.4	52.2	51.3	50.7	51.2	52.0	51.4	52.6	53.1
80°	49.5	45.1	42.5	42.1	40.6	39.5	39.2	39.9	39.0	39.5	40.9
82.5°	38.2	35.4	32.6	32.1	30.3	29.7	29.5	29.0	29.0	28.9	29.2
85°	22.7	21.0	19.1	18.0	17.2	16.1	16.1	15.6	15.0	14.5	14.8
87.5°	13.1	13.0	11.6	10.5	10.2	8.0	8.0	7.2	6.8	5.9	5.3
90°	20.0	21.1	18.8	16.5	16.5	9.4	9.4	8.2	7.1	3.5	1.2
92.5°	310.0	372.2	325.8	237.0	146.0	86.3	62.0	44.8	30.5	19.5	13.3
95°	983.4	956.3	721.6	441.2	248.7	146.7	97.4	69.3	54.0	42.2	38.7
97.5°	1235.5	1007.3	675.4	396.7	237.7	159.2	117.9	93.6	79.6	69.5	69.5
100°	1243.9	943.4	612.6	373.1	240.5	171.4	133.8	111.5	97.4	89.2	89.2
102.5°	1173.5	863.6	570.3	366.6	249.9	187.3	151.6	130.3	117.1	109.9	108.0
105°	1045.5	769.8	533.9	369.6	272.3	215.9	181.9	160.8	146.7	140.8	137.3
107.5°	942.3	717.2	527.4	387.0	298.3	246.7	213.1	192.9	177.9	172.0	169.7
110°	890.7	699.4	529.3	400.1	318.0	266.4	234.7	213.6	199.4	193.6	191.3



TEST NUMBER: P332528-840

CATALOG NUMBER: SA4XXDIP-C350D1205U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	861.5	690.9	534.8	414.2	336.8	287.0	255.4	234.2	221.1	214.3	212.0
115°	834.4	686.5	545.6	436.6	366.1	319.2	287.5	265.2	253.5	245.3	241.8
117.5°	822.1	685.3	557.1	459.3	394.6	349.9	317.1	296.2	283.3	276.0	272.7
120°	815.6	685.3	565.6	475.2	414.2	369.6	336.8	316.8	304.0	295.7	293.4
122.5°	808.1	684.4	574.1	490.3	433.0	388.4	356.5	334.7	322.8	314.5	312.1
125°	795.6	683.0	586.7	512.8	458.8	416.6	383.7	361.4	348.5	341.4	336.8
127.5°	778.9	680.3	596.8	532.3	482.7	441.9	408.8	385.6	370.8	362.3	358.6
130°	768.6	679.4	604.3	544.5	498.8	458.8	424.7	402.5	384.9	375.5	370.8
132.5°	759.2	678.5	610.9	556.7	511.9	472.0	439.8	415.7	399.0	386.8	383.0
135°	745.2	677.1	620.8	572.7	530.4	491.7	461.2	436.6	416.6	404.9	400.1
137.5°	733.0	676.8	626.6	583.9	544.5	508.4	479.3	453.6	434.6	421.7	417.3
140°	726.4	675.9	631.4	591.4	553.9	518.7	490.5	465.9	446.0	433.0	429.5
142.5°	720.7	675.9	635.1	597.0	562.3	528.1	500.8	477.2	458.1	446.2	442.6
145°	711.1	673.6	637.2	603.2	571.5	541.0	515.1	492.8	476.5	464.7	461.2
147.5°	702.5	669.3	638.3	608.5	580.9	552.2	529.0	510.5	493.5	483.2	482.0
150°	695.9	666.5	638.3	611.4	585.5	559.8	537.5	519.9	505.7	496.3	495.2
152.5°	688.3	661.9	636.5	613.3	589.4	566.3	545.9	530.2	517.1	507.7	507.4
155°	677.1	654.8	633.7	614.9	594.9	575.0	557.4	544.5	532.7	525.7	524.5
157.5°	665.6	647.5	630.7	614.9	599.0	582.1	568.2	556.9	547.8	541.2	541.2
160°	657.1	641.9	627.8	614.9	600.8	586.7	573.8	564.4	556.2	551.5	551.5
162.5°	649.6	636.2	625.0	614.9	602.7	589.6	579.5	571.0	563.7	560.0	560.9
165°	637.2	627.8	619.6	612.6	603.2	592.6	585.5	579.7	573.8	571.5	571.5
167.5°	625.9	619.4	614.0	609.8	602.9	595.2	589.8	586.5	582.1	580.9	582.1
170°	618.4	613.7	610.2	607.8	602.0	596.1	592.6	590.3	586.7	585.5	586.7
172.5°	611.9	608.0	606.4	606.0	601.1	597.0	594.5	593.1	590.5	590.3	591.4
175°	604.3	602.0	602.0	603.2	599.7	597.3	597.3	596.1	594.9	594.9	596.1
177.5°	599.2	598.2	598.2	600.1	598.2	597.3	597.3	597.3	596.3	597.3	598.2
180°	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3





TEST NUMBER: P332528-840

CATALOG NUMBER: SA4XXDIP-C350D1205U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9
2.5°	580.8	582.7	585.2	589.4	590.9	592.8	595.5	595.3	596.0	599.0	605.0
5°	582.9	590.4	597.5	606.1	615.2	621.2	629.2	634.3	639.3	645.8	656.8
7.5°	583.8	595.5	608.6	623.8	637.2	652.7	664.8	676.2	686.5	700.0	713.2
10°	582.5	598.2	615.2	634.3	654.6	671.9	687.4	705.1	720.1	736.6	751.4
12.5°	580.0	599.0	621.7	643.1	666.8	692.3	711.7	729.5	749.5	768.5	791.4
15°	574.3	600.4	626.9	655.1	686.9	716.3	744.3	767.4	788.9	817.4	847.3
17.5°	567.1	595.2	628.7	662.9	696.1	729.6	764.3	799.1	826.3	861.6	884.9
20°	560.5	593.0	627.4	668.0	701.3	743.1	777.5	811.1	848.5	883.6	911.6
22.5°	551.1	586.6	623.2	663.6	707.3	749.2	788.9	825.5	862.8	901.0	934.8
25°	539.2	571.5	614.7	660.6	704.1	749.5	795.2	841.0	881.2	921.6	953.1
27.5°	519.0	559.7	600.0	647.3	695.6	747.0	795.9	843.8	886.0	919.2	938.7
30°	508.6	544.0	587.7	635.3	687.6	742.9	793.8	840.8	880.0	906.6	914.4
32.5°	493.3	529.8	572.6	621.9	677.3	734.1	787.0	831.4	864.1	878.1	868.6
35°	470.6	503.6	546.8	597.2	654.9	715.3	767.7	805.2	821.9	808.8	776.1
37.5°	443.3	476.1	519.5	569.1	628.6	690.1	737.4	764.5	758.9	726.2	677.4
40°	424.2	454.8	496.1	549.7	607.7	669.4	711.0	725.6	710.3	663.5	611.6
42.5°	403.0	432.8	474.3	526.0	587.5	644.4	680.6	681.9	656.2	600.2	548.2
45°	370.7	399.1	438.3	492.1	549.0	602.5	626.4	614.7	567.3	513.4	461.0
47.5°	338.8	363.5	402.1	453.1	507.2	552.2	564.1	543.0	492.6	440.1	391.6
50°	315.5	340.3	376.7	425.5	477.6	516.4	522.2	494.2	444.7	391.9	354.0
52.5°	293.1	317.8	352.7	397.9	445.6	480.7	480.9	448.6	399.3	352.2	316.9
55°	260.2	282.5	314.1	354.5	397.0	424.4	417.8	384.4	341.5	300.6	269.8
57.5°	228.6	248.0	277.0	310.7	348.2	370.9	359.8	327.6	289.4	254.7	231.4
60°	208.1	226.6	251.5	283.3	314.8	332.4	321.9	292.8	257.6	229.6	209.3
62.5°	188.2	203.8	227.7	255.3	284.6	297.6	288.3	259.5	229.1	203.9	187.3
65°	160.2	172.8	191.9	215.6	236.8	248.1	240.2	213.4	190.3	172.1	159.0
67.5°	133.8	143.7	158.2	177.2	195.3	201.4	194.2	175.5	155.9	141.4	132.1
70°	115.6	125.0	137.1	151.8	167.5	174.0	166.8	152.0	136.0	122.6	113.5
72.5°	99.8	107.0	117.3	129.8	142.1	148.6	143.7	129.5	115.9	105.9	98.3
75°	76.0	82.2	89.4	98.3	107.8	112.1	107.8	98.0	88.7	81.3	75.7
77.5°	55.2	58.6	64.1	70.8	76.7	80.0	76.2	69.7	63.9	58.9	56.1
80°	42.1	44.4	48.3	53.5	57.6	60.7	58.3	52.8	48.3	44.9	43.7
82.5°	30.6	32.2	34.7	38.6	41.3	42.9	41.9	37.9	36.1	33.1	31.9
85°	15.0	16.1	17.7	18.9	21.3	21.5	21.7	20.1	18.4	17.7	16.8
87.5°	5.9	6.8	7.6	8.4	9.2	10.7	10.5	11.0	10.7	10.3	9.8
90°	3.5	7.1	8.2	9.4	9.4	16.5	16.5	18.8	21.1	20.0	21.1
92.5°	19.5	30.5	44.8	62.0	86.3	146.0	237.0	325.8	372.2	310.0	230.5
95°	42.2	54.0	69.3	97.4	146.7	248.7	441.2	721.6	956.3	983.4	869.5
97.5°	69.5	79.6	93.6	117.9	159.2	237.7	396.7	675.4	1007.3	1235.5	1284.8
100°	89.2	97.4	111.5	133.8	171.4	240.5	373.1	612.6	943.4	1243.9	1415.2
102.5°	109.9	117.1	130.3	151.6	187.3	249.9	366.6	570.3	863.6	1173.5	1408.7
105°	140.8	146.7	160.8	181.9	215.9	272.3	369.6	533.9	769.8	1045.5	1314.2
107.5°	172.0	177.9	192.9	213.1	246.7	298.3	387.0	527.4	717.2	942.3	1180.2
110°	193.6	199.4	213.6	234.7	266.4	318.0	400.1	529.3	699.4	890.7	1099.5





TEST NUMBER: P332528-840

CATALOG NUMBER: SA4XXDIP-C350D1205U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	214.3	221.1	234.2	255.4	287.0	336.8	414.2	534.8	690.9	861.5	1040.4
115°	245.3	253.5	265.2	287.5	319.2	366.1	436.6	545.6	686.5	834.4	981.0
117.5°	276.0	283.3	296.2	317.1	349.9	394.6	459.3	557.1	685.3	822.1	951.9
120°	295.7	304.0	316.8	336.8	369.6	414.2	475.2	565.6	685.3	815.6	938.8
122.5°	314.5	322.8	334.7	356.5	388.4	433.0	490.3	574.1	684.4	808.1	927.5
125°	341.4	348.5	361.4	383.7	416.6	458.8	512.8	586.7	683.0	795.6	908.3
127.5°	362.3	370.8	385.6	408.8	441.9	482.7	532.3	596.8	680.3	778.9	884.7
130°	375.5	384.9	402.5	424.7	458.8	498.8	544.5	604.3	679.4	768.6	866.1
132.5°	386.8	399.0	415.7	439.8	472.0	511.9	556.7	610.9	678.5	759.2	846.3
135°	404.9	416.6	436.6	461.2	491.7	530.4	572.7	620.8	677.1	745.2	819.1
137.5°	421.7	434.6	453.6	479.3	508.4	544.5	583.9	626.6	676.8	733.0	794.5
140°	433.0	446.0	465.9	490.5	518.7	553.9	591.4	631.4	675.9	726.4	780.3
142.5°	446.2	458.1	477.2	500.8	528.1	562.3	597.0	635.1	675.9	720.7	767.2
145°	464.7	476.5	492.8	515.1	541.0	571.5	603.2	637.2	673.6	711.1	748.7
147.5°	483.2	493.5	510.5	529.0	552.2	580.9	608.5	638.3	669.3	702.5	733.5
150°	496.3	505.7	519.9	537.5	559.8	585.5	611.4	638.3	666.5	695.9	724.1
152.5°	507.7	517.1	530.2	545.9	566.3	589.4	613.3	636.5	661.9	688.3	713.7
155°	525.7	532.7	544.5	557.4	575.0	594.9	614.9	633.7	654.8	677.1	698.2
157.5°	541.2	547.8	556.9	568.2	582.1	599.0	614.9	630.7	647.5	665.6	681.6
160°	551.5	556.2	564.4	573.8	586.7	600.8	614.9	627.8	641.9	657.1	671.3
162.5°	560.0	563.7	571.0	579.5	589.6	602.7	614.9	625.0	636.2	649.6	660.9
165°	571.5	573.8	579.7	585.5	592.6	603.2	612.6	619.6	627.8	637.2	646.6
167.5°	580.9	582.1	586.5	589.8	595.2	602.9	609.8	614.0	619.4	625.9	632.8
170°	585.5	586.7	590.3	592.6	596.1	602.0	607.8	610.2	613.7	618.4	624.3
172.5°	590.3	590.5	593.1	594.5	597.0	601.1	606.0	606.4	608.0	611.9	616.7
175°	594.9	594.9	596.1	597.3	597.3	599.7	603.2	602.0	602.0	604.3	606.7
177.5°	597.3	596.3	597.3	597.3	597.3	598.2	600.1	598.2	598.2	599.2	600.1
180°	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3



TEST NUMBER: P332528-840

CATALOG NUMBER: SA4XXDIP-C350D1205U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	576.9	576.9	576.9	576.9	576.9	576.9	576.9
2.5°	608.1	608.5	610.3	611.6	612.0	613.9	614.0
5°	661.6	665.6	673.5	674.2	675.4	681.7	676.8
7.5°	724.2	734.5	741.3	747.5	749.6	752.3	751.8
10°	764.4	779.6	787.3	799.5	799.9	803.0	801.1
12.5°	804.7	822.4	836.4	838.7	848.9	850.5	853.1
15°	861.8	880.7	900.1	907.1	921.1	924.4	929.7
17.5°	915.5	934.8	948.5	966.3	972.2	979.9	974.6
20°	945.0	966.0	983.3	997.3	1003.3	1007.6	1007.1
22.5°	962.8	984.0	997.9	1008.7	1014.2	1016.0	1015.9
25°	973.9	986.1	990.5	994.5	988.3	986.1	987.0
27.5°	942.9	939.8	928.6	913.8	898.6	886.5	879.8
30°	900.3	881.7	864.7	835.1	819.8	810.7	802.5
32.5°	839.9	810.3	777.7	750.5	733.2	719.7	717.7
35°	736.4	692.0	652.0	618.7	601.6	587.0	583.6
37.5°	626.0	579.9	543.9	514.6	496.1	485.8	476.3
40°	552.8	513.1	477.8	452.9	438.8	431.4	425.5
42.5°	496.4	460.2	425.0	406.1	393.3	388.8	385.3
45°	418.5	384.8	360.4	346.1	338.7	331.0	327.4
47.5°	356.1	328.7	312.7	300.4	292.5	287.9	285.7
50°	320.7	298.3	284.0	274.6	267.4	263.9	262.0
52.5°	289.4	270.9	258.9	251.5	246.6	244.0	243.2
55°	249.2	235.2	227.5	221.1	217.5	215.1	214.2
57.5°	216.7	205.8	199.7	194.3	192.9	191.0	190.3
60°	195.3	186.9	181.7	178.0	176.8	174.5	174.9
62.5°	176.3	169.5	165.0	163.0	161.4	159.4	160.1
65°	149.2	144.1	141.7	139.9	137.9	136.7	137.6
67.5°	125.1	121.7	118.5	117.3	116.4	116.2	115.2
70°	109.5	106.6	103.7	103.0	103.0	102.1	101.8
72.5°	94.3	92.3	90.4	89.8	89.1	89.5	88.5
75°	72.9	71.2	70.5	69.8	69.6	69.6	68.9
77.5°	53.8	52.6	51.5	51.5	50.6	50.3	50.2
80°	40.9	40.4	39.5	39.5	39.0	39.2	38.7
82.5°	30.7	30.1	29.9	29.5	28.8	28.9	28.4
85°	16.5	15.8	15.6	14.8	14.3	14.8	14.3
87.5°	10.2	10.2	10.0	9.9	9.9	9.7	9.1
90°	22.3	23.4	23.4	24.6	25.9	24.6	24.6
92.5°	173.4	138.0	114.5	100.7	94.3	90.4	90.4
95°	687.6	530.4	416.6	359.1	322.8	301.5	286.3
97.5°	1217.1	1102.4	979.9	895.5	825.0	789.7	765.4
100°	1438.7	1381.2	1294.3	1192.2	1120.6	1085.5	1076.1
102.5°	1525.0	1541.7	1505.5	1442.9	1391.0	1353.9	1346.5
105°	1517.3	1633.5	1681.5	1683.9	1674.6	1658.1	1651.0
107.5°	1396.4	1560.0	1664.7	1722.6	1749.4	1761.1	1764.2
110°	1302.5	1472.7	1601.7	1685.1	1734.3	1755.5	1766.1



TEST NUMBER: P332528-840

CATALOG NUMBER: SA4XXDIP-C350D1205U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	1219.9	1380.7	1509.7	1604.4	1664.0	1693.5	1710.7
115°	1125.4	1262.6	1375.3	1468.0	1538.4	1576.0	1585.4
117.5°	1071.4	1179.3	1274.9	1353.9	1413.1	1451.1	1458.3
120°	1047.9	1141.8	1225.1	1292.0	1343.6	1374.1	1387.0
122.5°	1032.9	1118.3	1191.3	1247.9	1292.0	1317.8	1330.7
125°	1009.2	1090.1	1154.7	1201.6	1235.7	1258.0	1265.0
127.5°	981.3	1062.0	1123.3	1170.4	1200.7	1219.5	1226.5
130°	958.8	1038.5	1100.8	1148.8	1178.1	1196.9	1204.0
132.5°	933.4	1011.3	1073.5	1120.6	1153.8	1171.5	1178.6
135°	895.3	966.9	1025.6	1072.6	1105.4	1124.2	1131.3
137.5°	859.0	919.3	972.3	1016.2	1048.6	1064.1	1072.6
140°	835.5	888.3	937.6	978.7	1004.5	1020.9	1030.3
142.5°	815.8	861.1	903.8	940.2	964.1	978.7	985.2
145°	788.6	823.7	856.7	886.0	905.9	917.7	923.5
147.5°	765.1	793.2	819.1	840.7	857.8	866.8	868.8
150°	751.0	774.5	795.6	814.4	829.6	836.7	837.9
152.5°	736.9	758.5	775.9	791.8	804.3	808.5	809.7
155°	717.0	734.6	748.7	760.4	769.8	773.4	773.4
157.5°	697.3	712.1	723.4	732.3	739.3	741.4	741.4
160°	684.1	697.0	706.4	713.5	720.5	721.6	721.6
162.5°	672.0	682.1	690.4	695.6	702.7	703.9	702.9
165°	653.6	661.9	667.7	672.4	677.1	675.9	674.8
167.5°	638.1	644.7	648.2	650.6	653.6	653.4	652.5
170°	627.8	632.5	636.0	638.3	639.5	638.3	638.3
172.5°	619.4	622.2	624.7	626.1	627.3	626.1	624.3
175°	607.8	610.2	610.2	610.2	612.6	610.2	607.8
177.5°	601.1	601.1	602.0	601.1	602.0	600.1	598.2
180°	597.3	597.3	597.3	597.3	597.3	597.3	597.3

(END OF REPORT)