

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332544-840

Luminaire Tested: **SA4XXDIP-C575D590U840-4F0-1E-UDD-A**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332544-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXDIP-C575D590U840-4F0-1E-UDD-A  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 575 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 590 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5001.6 lumens  
Efficiency: N/A  
Efficacy: 152.5 lumens/watt  
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 32.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332544-840  
CATALOG NUMBER: SA4XXDIP-C575D590U840-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P332544-840

CATALOG NUMBER: SA4XXDIP-C575D590U840-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58	52
1	99	94	90	87	91	87	84	81	75	72	70	63	61	60	52	51	50	45
2	90	83	77	71	83	77	71	67	66	62	58	55	53	50	46	44	42	38
3	82	73	66	60	76	68	61	56	58	53	49	49	46	43	41	38	36	32
4	75	65	57	51	69	60	53	48	52	46	42	44	40	37	37	34	31	28
5	69	58	50	44	64	54	47	41	46	41	37	40	35	32	33	30	27	24
6	64	52	44	38	59	48	41	36	42	36	32	36	31	28	30	27	24	21
7	59	47	39	33	55	44	37	32	38	32	28	33	28	25	28	24	22	19
8	55	43	35	30	51	40	33	28	35	29	25	30	26	22	25	22	19	17
9	51	39	31	26	47	37	30	25	32	26	23	28	23	20	23	20	18	15
10	48	36	29	24	44	34	27	23	29	24	20	25	21	18	22	18	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	7657	7657	7657	7657
5°	9018	7678	6776	7678
10°	10797	7643	6101	7643
15°	12774	7565	5602	7565
20°	14225	7487	5158	7487
25°	14455	7371	4851	7371
30°	12299	7260	4754	7260
35°	9456	7078	4755	7078
40°	7371	6866	4845	6866
45°	6146	6545	4925	6545
50°	5408	6154	5093	6154
55°	4954	5685	5298	5685
60°	4644	5265	5546	5265
65°	4323	4797	5748	4797
70°	3949	4331	5880	4331
75°	3531	3812	5808	3812
80°	2957	3124	5625	3124
85°	2177	2251	5391	2251



TEST NUMBER: P332544-840

CATALOG NUMBER: SA4XXDIP-C575D590U840-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	92.4	1.8
10°-20°	284.8	5.7
20°-30°	451.7	9.0
30°-40°	502.6	10.0
40°-50°	457.5	9.1
50°-60°	373.9	7.5
60°-70°	266.9	5.3
70°-80°	147.0	2.9
80°-90°	42.3	0.8
90°-100°	26.3	0.5
100°-110°	168.0	3.4
110°-120°	321.3	6.4
120°-130°	407.9	8.2
130°-140°	436.4	8.7
140°-150°	408.1	8.2
150°-160°	329.1	6.6
160°-170°	212.2	4.2
170°-180°	73.2	1.5
0°-30°	828.9	16.6
0°-40°	1331.5	26.6
0°-60°	2162.9	43.2
0°-90°	2619.2	52.4
90°-120°	515.6	10.3
90°-150°	1767.9	35.3
90°-180°	2382.0	47.6
0°-180°	5001.6	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	948	948	948	948	948	
5°	1113	947	836	947	1113	113
15°	1528	905	670	905	1528	432
25°	1623	828	545	828	1623	715
35°	960	718	482	718	960	609
45°	538	573	431	573	538	424
55°	352	404	376	404	352	318
65°	226	251	301	251	226	224
75°	113	122	186	122	113	120
85°	24	24	58	24	24	29
90°	17	2	17	2	17	8
95°	17	32	17	32	17	13
105°	164	173	164	173	164	143
115°	326	324	326	324	326	323
125°	459	455	459	455	459	408
135°	569	564	569	564	569	438
145°	654	651	654	651	654	409
155°	713	714	713	714	713	329
165°	749	753	749	753	749	212
175°	766	770	766	770	766	73
180°	770	770	770	770	770	



TEST NUMBER: P332544-840

CATALOG NUMBER: SA4XXDIP-C575D590U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	948.5	948.5	948.5	948.5	948.5	948.5	948.5	948.5	948.5	948.5	948.5
2.5°	1009.5	1009.2	1006.0	1005.4	1003.2	1000.4	999.8	994.7	984.6	980.0	978.7
5°	1112.8	1120.6	1110.3	1108.4	1107.2	1094.3	1087.6	1079.7	1061.7	1051.1	1042.8
7.5°	1236.0	1236.9	1232.4	1228.8	1218.8	1207.5	1190.5	1172.5	1150.9	1128.5	1111.7
10°	1317.1	1320.2	1315.1	1314.3	1294.2	1281.7	1256.6	1235.4	1210.9	1183.9	1159.1
12.5°	1402.6	1398.2	1395.5	1378.8	1375.0	1352.1	1322.9	1301.0	1263.4	1232.2	1199.3
15°	1528.4	1519.8	1514.3	1491.2	1479.8	1447.9	1416.8	1392.9	1343.8	1297.1	1261.6
17.5°	1602.4	1610.9	1598.2	1588.7	1559.2	1536.9	1505.2	1454.9	1416.4	1358.4	1313.7
20°	1655.8	1656.6	1649.5	1639.6	1616.5	1588.2	1553.6	1498.6	1452.6	1394.8	1333.5
22.5°	1670.2	1670.4	1667.4	1658.2	1640.6	1617.7	1582.9	1536.9	1481.3	1418.5	1357.2
25°	1622.8	1621.2	1624.8	1635.0	1628.3	1621.2	1601.1	1567.0	1515.1	1448.7	1382.7
27.5°	1446.4	1457.2	1477.2	1502.4	1526.6	1545.0	1550.2	1543.3	1511.1	1456.4	1387.4
30°	1319.4	1332.8	1347.7	1372.9	1421.6	1449.5	1480.2	1503.3	1490.4	1446.7	1382.3
32.5°	1179.8	1183.2	1205.3	1234.0	1278.6	1332.2	1380.8	1427.8	1443.5	1420.7	1366.9
35°	959.5	965.0	989.0	1017.2	1071.9	1137.5	1210.6	1275.8	1329.7	1351.3	1323.7
37.5°	783.0	798.8	815.7	846.1	894.2	953.3	1029.3	1113.6	1193.9	1247.6	1256.7
40°	699.4	709.2	721.4	744.6	785.5	843.6	908.8	1005.5	1090.8	1167.8	1193.0
42.5°	633.4	639.1	646.6	667.5	698.7	756.5	816.1	901.1	986.7	1078.8	1121.0
45°	538.3	544.2	556.7	569.0	592.5	632.6	688.0	757.9	843.9	932.8	1010.6
47.5°	469.6	473.4	480.9	493.9	513.9	540.4	585.4	643.8	723.6	809.8	892.7
50°	430.6	433.7	439.7	451.5	466.8	490.4	527.3	581.9	644.4	731.2	812.5
52.5°	399.8	401.1	405.5	413.4	425.7	445.5	475.7	520.9	579.1	656.4	737.4
55°	352.0	353.7	357.6	363.5	374.1	386.7	409.8	443.6	494.3	561.5	631.8
57.5°	312.8	313.9	317.2	319.4	328.2	338.4	356.2	380.3	418.8	475.7	538.6
60°	287.6	286.8	290.7	292.8	298.6	307.3	321.0	344.2	377.6	423.5	481.3
62.5°	263.1	262.0	265.3	267.9	271.2	278.6	289.9	308.0	335.2	376.8	426.7
65°	226.3	224.8	226.7	229.8	233.0	236.9	245.2	261.3	282.9	312.8	350.8
67.5°	189.3	191.1	191.4	192.9	194.7	200.1	205.7	217.1	232.4	256.3	288.5
70°	167.3	167.7	169.4	169.4	170.6	175.2	180.0	186.6	201.6	223.6	249.9
72.5°	145.4	147.0	146.4	147.6	148.6	151.7	155.1	161.5	174.2	190.6	212.8
75°	113.2	114.3	114.3	114.7	115.9	117.0	119.9	124.5	133.6	145.7	161.1
77.5°	82.5	82.7	83.2	84.6	84.6	86.5	88.6	92.3	96.8	105.1	114.5
80°	63.6	64.4	64.0	64.8	64.8	66.4	67.2	71.9	73.8	79.4	86.8
82.5°	46.7	47.5	47.4	48.5	49.1	49.4	50.5	52.4	54.3	59.3	62.3
85°	23.5	24.3	23.5	24.3	25.5	26.0	27.1	27.5	29.1	30.3	33.0
87.5°	10.4	11.3	11.2	11.5	12.0	12.2	12.4	11.9	13.0	13.2	14.2
90°	17.3	17.1	16.8	16.6	16.3	15.8	14.9	14.2	13.4	12.6	11.6
92.5°	15.9	15.9	15.8	15.8	15.7	15.2	14.5	13.7	13.0	12.2	11.2
95°	16.7	16.6	16.5	16.4	16.2	15.8	14.9	14.2	13.4	12.6	12.5
97.5°	16.2	16.0	15.9	15.8	15.7	15.6	15.5	15.3	15.2	15.2	29.5
100°	16.2	16.0	15.9	15.8	15.7	16.7	18.8	21.0	23.1	25.3	43.0
102.5°	16.6	16.6	16.6	16.6	16.5	28.2	51.7	75.1	98.7	122.1	124.4
105°	164.2	168.7	173.4	178.0	182.6	184.3	183.2	182.1	180.9	179.8	179.0
107.5°	228.8	228.3	227.8	227.3	226.8	226.3	225.8	225.2	224.7	224.1	223.2
110°	256.9	256.5	256.1	255.8	255.4	255.1	254.8	254.6	254.3	254.1	253.3



TEST NUMBER: P332544-840

CATALOG NUMBER: SA4XXDIP-C575D590U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	285.0	284.6	284.1	283.6	283.1	282.9	283.0	283.0	283.1	283.1	282.8
115°	326.1	326.1	326.1	326.1	326.1	325.9	325.7	325.4	325.2	324.9	325.0
117.5°	367.8	367.8	367.9	367.9	368.0	368.0	368.1	368.1	368.2	368.2	367.9
120°	394.0	394.3	394.6	394.8	395.1	395.1	394.8	394.6	394.3	394.0	394.2
122.5°	419.8	420.1	420.3	420.6	420.8	420.9	420.7	420.6	420.4	420.3	420.1
125°	458.6	458.4	458.3	458.2	458.1	457.8	457.4	457.0	456.7	456.3	456.5
127.5°	492.5	492.6	492.7	492.8	492.9	493.0	493.1	493.2	493.2	493.3	492.7
130°	515.5	515.5	515.5	515.5	515.5	515.5	515.3	515.2	515.1	515.0	514.6
132.5°	536.7	536.8	536.9	537.0	537.1	537.1	537.0	536.9	536.7	536.6	536.1
135°	568.6	568.4	568.0	567.7	567.5	567.2	567.0	566.7	566.5	566.2	565.7
137.5°	595.7	595.8	595.9	596.0	596.0	595.9	595.7	595.4	595.1	594.8	594.3
140°	614.6	614.5	614.4	614.3	614.1	613.9	613.5	613.1	612.7	612.4	612.1
142.5°	630.4	630.3	630.3	630.3	630.3	630.1	629.8	629.4	629.2	628.9	628.7
145°	654.4	654.2	653.9	653.6	653.4	653.2	653.1	652.9	652.8	652.7	652.7
147.5°	674.3	674.2	674.1	674.0	673.8	673.7	673.6	673.5	673.4	673.3	673.4
150°	687.2	687.1	687.0	686.8	686.7	686.6	686.6	686.6	686.6	686.6	686.8
152.5°	698.3	698.3	698.4	698.5	698.6	698.5	698.3	698.1	697.9	697.7	697.9
155°	713.2	713.6	713.9	714.3	714.7	714.6	714.1	713.6	713.1	712.6	713.0
157.5°	725.6	726.3	726.9	727.6	728.2	728.2	727.6	726.9	726.3	725.6	726.0
160°	733.9	734.7	735.4	736.2	737.0	737.0	736.2	735.4	734.7	733.9	734.0
162.5°	740.3	741.2	742.0	743.0	743.9	743.9	743.1	742.4	741.5	740.8	740.9
165°	749.4	750.6	751.7	752.9	754.1	754.2	753.1	752.0	751.0	750.0	750.0
167.5°	756.3	757.5	758.8	760.1	761.3	761.4	760.3	759.2	758.1	756.9	757.0
170°	760.4	761.6	763.0	764.3	765.5	765.7	764.6	763.6	762.5	761.5	761.4
172.5°	762.7	764.1	765.5	766.9	768.2	768.4	767.4	766.4	765.4	764.3	764.2
175°	765.6	767.1	768.6	770.2	771.7	771.9	770.7	769.6	768.4	767.3	767.2
177.5°	767.4	768.6	769.9	771.1	772.3	772.5	771.7	770.9	770.1	769.2	769.0
180°	770.2	770.2	770.2	770.2	770.2	770.2	770.2	770.2	770.2	770.2	770.2



TEST NUMBER: P332544-840

CATALOG NUMBER: SA4XXDIP-C575D590U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	948.5	948.5	948.5	948.5	948.5	948.5	948.5	948.5	948.5	948.5	948.5
2.5°	979.0	974.6	971.5	969.0	962.0	958.0	954.8	950.4	945.3	940.0	933.4
5°	1034.6	1021.2	1011.4	996.4	982.3	970.5	958.4	947.4	933.9	919.5	908.8
7.5°	1093.0	1073.1	1047.6	1025.5	1000.7	979.1	959.8	940.0	919.4	899.4	881.1
10°	1130.0	1104.5	1076.2	1042.8	1011.4	983.5	957.6	932.4	908.1	883.6	862.8
12.5°	1169.9	1138.1	1096.3	1057.2	1022.1	984.7	953.4	922.6	893.2	867.7	843.3
15°	1223.6	1177.6	1129.2	1077.0	1030.7	987.0	944.2	905.2	872.3	838.5	815.0
17.5°	1256.5	1199.6	1144.4	1089.7	1033.6	978.6	932.4	887.6	846.2	812.6	782.9
20°	1278.2	1221.6	1152.9	1098.2	1031.4	974.8	921.4	871.5	828.3	792.5	761.8
22.5°	1297.1	1231.6	1162.9	1091.0	1024.5	964.4	905.9	855.8	811.6	774.0	744.6
25°	1307.3	1232.2	1157.5	1086.0	1010.6	939.5	886.5	827.5	780.3	740.6	709.2
27.5°	1308.4	1228.1	1143.7	1064.2	986.3	920.1	853.1	800.4	751.5	709.5	679.3
30°	1304.8	1221.2	1130.4	1044.4	966.2	894.2	836.2	778.8	728.8	687.2	655.8
32.5°	1293.8	1206.7	1113.5	1022.4	941.4	871.0	811.0	756.5	707.8	666.8	633.8
35°	1262.0	1176.0	1076.6	981.9	899.0	827.9	773.7	718.2	669.5	630.7	598.8
37.5°	1212.3	1134.5	1033.5	935.4	854.0	782.6	728.8	678.8	634.9	595.3	562.7
40°	1168.9	1100.6	999.2	903.7	815.7	747.7	697.4	651.5	607.8	570.5	539.5
42.5°	1118.9	1059.3	965.8	864.7	779.8	711.6	662.6	621.3	580.2	545.7	514.6
45°	1029.9	990.6	902.5	809.0	720.6	656.2	609.5	573.3	538.7	504.9	479.0
47.5°	927.4	907.9	833.7	745.0	661.1	597.5	557.0	523.6	493.3	464.6	441.8
50°	858.5	849.1	785.1	699.4	619.2	559.6	518.7	490.0	464.0	438.9	417.3
52.5°	790.6	790.3	732.6	654.1	580.0	522.4	481.9	455.0	432.6	412.1	392.7
55°	686.8	697.8	652.7	582.7	516.3	464.4	427.9	403.9	388.2	371.3	356.8
57.5°	591.5	609.8	572.5	510.9	455.4	407.7	375.9	357.9	341.1	330.9	320.3
60°	529.3	546.5	517.5	465.6	413.3	372.4	342.2	326.1	311.5	304.5	297.0
62.5°	473.9	489.4	467.8	419.7	374.4	335.1	309.5	294.1	284.3	276.5	271.6
65°	394.9	407.9	389.4	354.5	315.5	284.1	263.3	251.1	241.7	238.5	233.0
67.5°	319.2	331.0	321.0	291.3	260.1	236.3	220.0	208.3	202.8	200.0	196.1
70°	274.3	286.1	275.4	249.5	225.5	205.5	190.2	183.5	177.6	176.4	171.0
72.5°	236.2	244.3	233.6	213.4	192.9	175.9	164.1	157.1	154.0	151.9	149.0
75°	177.2	184.3	177.2	161.5	146.9	135.1	124.9	122.2	118.7	117.4	115.5
77.5°	125.4	131.6	126.1	116.3	105.4	96.3	90.9	87.4	86.5	84.5	85.4
80°	95.8	99.8	94.7	88.1	79.4	73.1	69.2	67.2	64.8	64.0	65.6
82.5°	68.9	70.6	68.0	63.5	57.1	52.9	50.3	48.0	47.6	47.7	47.7
85°	35.7	35.3	34.9	31.0	29.1	26.4	24.7	24.3	23.9	24.7	25.5
87.5°	14.0	14.1	13.6	12.1	10.9	9.7	9.1	8.5	9.1	9.7	10.3
90°	10.6	9.6	8.6	7.4	6.0	4.5	3.1	1.7	3.1	4.5	6.0
92.5°	10.2	9.2	8.1	7.6	7.5	7.4	7.4	7.3	7.4	7.4	7.5
95°	12.4	12.3	12.1	14.2	18.6	23.0	27.4	31.7	27.4	23.0	18.6
97.5°	43.8	58.1	72.3	78.2	75.4	72.7	70.0	67.3	70.0	72.7	75.4
100°	60.7	78.4	96.0	103.7	101.4	99.1	96.7	94.4	96.7	99.1	101.4
102.5°	126.7	129.1	131.4	131.7	130.0	128.3	126.5	124.9	126.5	128.3	130.0
105°	178.4	177.8	177.1	176.4	175.7	174.9	174.2	173.4	174.2	174.9	175.7
107.5°	222.4	221.5	220.6	219.9	219.5	219.2	218.8	218.4	218.8	219.2	219.5
110°	252.5	251.8	251.0	250.3	250.0	249.6	249.2	248.8	249.2	249.6	250.0





TEST NUMBER: P332544-840

CATALOG NUMBER: SA4XXDIP-C575D590U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	282.4	282.0	281.7	281.1	280.4	279.7	279.0	278.3	279.0	279.7	280.4
115°	325.2	325.3	325.4	325.3	324.9	324.5	324.2	323.8	324.2	324.5	324.9
117.5°	367.7	367.4	367.1	366.7	366.2	365.7	365.2	364.7	365.2	365.7	366.2
120°	394.3	394.5	394.6	394.4	393.8	393.3	392.8	392.3	392.8	393.3	393.8
122.5°	419.9	419.8	419.6	419.3	419.0	418.7	418.4	418.1	418.4	418.7	419.0
125°	456.8	457.0	457.3	457.2	456.7	456.2	455.6	455.0	455.6	456.2	456.7
127.5°	492.1	491.6	491.0	490.6	490.5	490.4	490.2	490.1	490.2	490.4	490.5
130°	514.2	513.8	513.4	513.2	513.1	512.9	512.8	512.7	512.8	512.9	513.1
132.5°	535.6	535.2	534.7	534.3	534.1	533.9	533.6	533.4	533.6	533.9	534.1
135°	565.2	564.7	564.2	564.0	564.1	564.3	564.4	564.5	564.4	564.3	564.1
137.5°	593.7	593.1	592.6	592.3	592.2	592.2	592.1	592.1	592.1	592.2	592.2
140°	611.9	611.6	611.3	611.1	610.8	610.6	610.3	610.1	610.3	610.6	610.8
142.5°	628.6	628.4	628.3	628.0	627.5	627.1	626.6	626.2	626.6	627.1	627.5
145°	652.7	652.7	652.7	652.5	652.1	651.7	651.4	651.0	651.4	651.7	652.1
147.5°	673.6	673.7	673.8	673.5	672.8	672.1	671.4	670.7	671.4	672.1	672.8
150°	686.9	687.0	687.2	687.0	686.5	686.0	685.4	684.9	685.4	686.0	686.5
152.5°	698.2	698.4	698.6	698.5	698.1	697.7	697.3	696.9	697.3	697.7	698.1
155°	713.4	713.8	714.1	714.3	714.1	714.0	713.9	713.8	713.9	714.0	714.1
157.5°	726.5	726.9	727.3	727.6	727.7	727.7	727.8	727.9	727.8	727.7	727.7
160°	734.2	734.3	734.4	734.7	735.1	735.4	735.8	736.2	735.8	735.4	735.1
162.5°	741.0	741.1	741.3	741.6	742.1	742.6	743.1	743.6	743.1	742.6	742.1
165°	750.0	750.0	750.0	750.3	750.9	751.6	752.2	752.9	752.2	751.6	750.9
167.5°	757.1	757.2	757.2	757.6	758.3	758.9	759.6	760.2	759.6	758.9	758.3
170°	761.2	761.1	761.0	761.3	762.1	762.9	763.7	764.5	763.7	762.9	762.1
172.5°	764.1	764.0	763.8	764.2	764.9	765.7	766.4	767.2	766.4	765.7	764.9
175°	767.1	766.9	766.8	767.1	767.9	768.6	769.4	770.2	769.4	768.6	767.9
177.5°	768.8	768.6	768.4	768.7	769.4	770.1	770.8	771.5	770.8	770.1	769.4
180°	770.2	770.2	770.2	770.2	770.2	770.2	770.2	770.2	770.2	770.2	770.2



TEST NUMBER: P332544-840

CATALOG NUMBER: SA4XXDIP-C575D590U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	948.5	948.5	948.5	948.5	948.5	948.5	948.5	948.5	948.5	948.5	948.5
2.5°	930.3	927.5	923.3	917.7	913.0	908.0	906.7	904.8	908.6	905.4	904.5
5°	899.8	891.5	880.9	868.8	861.7	851.4	849.5	845.6	841.6	841.2	837.3
7.5°	867.5	855.4	841.5	829.1	817.6	806.5	799.1	797.6	791.7	788.4	784.5
10°	846.8	831.8	815.7	804.0	790.5	778.8	770.5	765.8	761.8	757.5	753.7
12.5°	822.2	806.4	793.0	780.3	764.5	755.5	741.9	733.8	733.0	733.1	722.9
15°	793.7	778.0	757.5	739.5	730.8	713.6	706.1	696.6	690.7	684.9	680.1
17.5°	761.1	741.5	725.6	704.8	688.3	674.6	664.7	659.0	650.3	641.9	635.8
20°	740.6	719.8	703.0	681.0	662.9	646.0	637.7	629.9	623.2	616.1	609.5
22.5°	719.9	698.1	677.5	656.1	639.2	621.5	613.5	602.8	596.4	592.5	585.8
25°	687.2	663.7	640.1	619.7	602.4	586.6	576.0	567.7	560.7	557.5	553.2
27.5°	651.7	628.2	605.5	582.3	562.7	551.3	542.8	536.5	532.5	528.4	526.3
30°	629.0	604.7	580.4	558.8	540.7	529.3	521.4	517.1	513.9	512.0	510.0
32.5°	606.1	582.1	556.4	536.7	520.6	510.4	504.4	500.1	498.6	497.9	497.2
35°	569.4	545.0	521.4	503.7	488.4	484.4	479.4	477.0	476.3	479.0	480.2
37.5°	533.7	511.1	489.4	472.3	462.2	456.5	454.7	454.8	457.7	460.1	462.9
40°	510.8	488.8	468.4	453.4	444.0	440.5	439.7	441.6	444.7	447.6	450.7
42.5°	488.5	466.8	448.3	434.2	427.7	424.4	425.0	426.9	431.3	434.6	439.4
45°	453.8	435.8	417.7	406.3	400.8	401.5	401.5	405.1	409.4	414.5	419.6
47.5°	421.2	402.9	388.1	378.5	375.7	375.0	377.2	381.8	388.1	394.4	401.5
50°	399.2	381.9	368.9	360.3	357.2	358.3	361.5	365.8	373.2	381.1	388.6
52.5°	376.9	361.1	349.1	341.1	338.9	341.0	344.2	351.0	357.6	366.1	375.1
55°	342.2	328.9	319.4	313.6	312.8	314.0	317.5	325.0	334.4	345.0	353.7
57.5°	307.7	296.6	287.9	283.9	284.3	285.4	291.1	300.0	310.1	321.4	332.5
60°	284.5	274.3	267.2	264.1	264.5	266.8	273.9	282.2	294.7	305.7	317.5
62.5°	262.5	253.5	246.7	243.9	243.4	248.5	255.3	263.9	276.5	288.7	301.4
65°	227.1	220.0	214.5	213.0	214.1	218.0	226.7	238.1	248.7	261.7	275.1
67.5°	192.5	186.7	183.0	183.7	185.1	190.9	198.1	207.9	219.9	233.4	246.6
70°	170.6	165.0	161.9	162.3	164.6	171.7	178.0	187.8	200.8	214.5	225.5
72.5°	147.9	144.3	141.5	143.1	145.4	150.4	158.1	168.0	179.5	192.2	203.9
75°	113.5	113.5	112.0	113.2	116.7	121.4	127.3	137.5	149.0	159.2	168.5
77.5°	84.2	83.4	84.4	85.8	87.9	93.4	100.2	107.6	116.0	126.3	134.1
80°	64.4	64.8	66.8	69.2	70.0	74.2	81.3	88.1	94.7	103.3	110.8
82.5°	48.4	48.8	49.8	52.8	53.6	58.3	62.8	69.5	75.5	81.3	87.6
85°	26.4	26.4	28.3	29.5	31.4	34.5	37.4	41.3	46.8	50.7	56.6
87.5°	11.5	11.8	13.2	14.0	15.2	17.0	17.8	21.4	22.8	24.5	27.5
90°	7.4	8.6	9.6	10.6	11.6	12.6	13.4	14.2	14.9	15.8	16.3
92.5°	7.6	8.1	9.2	10.2	11.2	12.2	13.0	13.7	14.5	15.2	15.7
95°	14.2	12.1	12.3	12.4	12.5	12.6	13.4	14.2	14.9	15.8	16.2
97.5°	78.2	72.3	58.1	43.8	29.5	15.2	15.2	15.3	15.5	15.6	15.7
100°	103.7	96.0	78.4	60.7	43.0	25.3	23.1	21.0	18.8	16.7	15.7
102.5°	131.7	131.4	129.1	126.7	124.4	122.1	98.7	75.1	51.7	28.2	16.5
105°	176.4	177.1	177.8	178.4	179.0	179.8	180.9	182.1	183.2	184.3	182.6
107.5°	219.9	220.6	221.5	222.4	223.2	224.1	224.7	225.2	225.8	226.3	226.8
110°	250.3	251.0	251.8	252.5	253.3	254.1	254.3	254.6	254.8	255.1	255.4



TEST NUMBER: P332544-840

CATALOG NUMBER: SA4XXDIP-C575D590U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	281.1	281.7	282.0	282.4	282.8	283.1	283.1	283.0	283.0	282.9	283.1
115°	325.3	325.4	325.3	325.2	325.0	324.9	325.2	325.4	325.7	325.9	326.1
117.5°	366.7	367.1	367.4	367.7	367.9	368.2	368.2	368.1	368.1	368.0	368.0
120°	394.4	394.6	394.5	394.3	394.2	394.0	394.3	394.6	394.8	395.1	395.1
122.5°	419.3	419.6	419.8	419.9	420.1	420.3	420.4	420.6	420.7	420.9	420.8
125°	457.2	457.3	457.0	456.8	456.5	456.3	456.7	457.0	457.4	457.8	458.1
127.5°	490.6	491.0	491.6	492.1	492.7	493.3	493.2	493.2	493.1	493.0	492.9
130°	513.2	513.4	513.8	514.2	514.6	515.0	515.1	515.2	515.3	515.5	515.5
132.5°	534.3	534.7	535.2	535.6	536.1	536.6	536.7	536.9	537.0	537.1	537.1
135°	564.0	564.2	564.7	565.2	565.7	566.2	566.5	566.7	567.0	567.2	567.5
137.5°	592.3	592.6	593.1	593.7	594.3	594.8	595.1	595.4	595.7	595.9	596.0
140°	611.1	611.3	611.6	611.9	612.1	612.4	612.7	613.1	613.5	613.9	614.1
142.5°	628.0	628.3	628.4	628.6	628.7	628.9	629.2	629.4	629.8	630.1	630.3
145°	652.5	652.7	652.7	652.7	652.7	652.7	652.8	652.9	653.1	653.2	653.4
147.5°	673.5	673.8	673.7	673.6	673.4	673.3	673.4	673.5	673.6	673.7	673.8
150°	687.0	687.2	687.0	686.9	686.8	686.6	686.6	686.6	686.6	686.6	686.7
152.5°	698.5	698.6	698.4	698.2	697.9	697.7	697.9	698.1	698.3	698.5	698.6
155°	714.3	714.1	713.8	713.4	713.0	712.6	713.1	713.6	714.1	714.6	714.7
157.5°	727.6	727.3	726.9	726.5	726.0	725.6	726.3	726.9	727.6	728.2	728.2
160°	734.7	734.4	734.3	734.2	734.0	733.9	734.7	735.4	736.2	737.0	737.0
162.5°	741.6	741.3	741.1	741.0	740.9	740.8	741.5	742.4	743.1	743.9	743.9
165°	750.3	750.0	750.0	750.0	750.0	750.0	751.0	752.0	753.1	754.2	754.1
167.5°	757.6	757.2	757.2	757.1	757.0	756.9	758.1	759.2	760.3	761.4	761.3
170°	761.3	761.0	761.1	761.2	761.4	761.5	762.5	763.6	764.6	765.7	765.5
172.5°	764.2	763.8	764.0	764.1	764.2	764.3	765.4	766.4	767.4	768.4	768.2
175°	767.1	766.8	766.9	767.1	767.2	767.3	768.4	769.6	770.7	771.9	771.7
177.5°	768.7	768.4	768.6	768.8	769.0	769.2	770.1	770.9	771.7	772.5	772.3
180°	770.2	770.2	770.2	770.2	770.2	770.2	770.2	770.2	770.2	770.2	770.2



TEST NUMBER: P332544-840  
 CATALOG NUMBER: SA4XXDIP-C575D590U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	948.5	948.5	948.5	948.5	948.5	948.5	948.5	948.5	948.5	948.5	948.5
2.5°	903.8	903.2	901.0	900.7	901.0	903.2	903.8	904.5	905.4	908.6	904.8
5°	835.0	833.0	831.8	836.2	831.8	833.0	835.0	837.3	841.2	841.6	845.6
7.5°	783.0	781.4	778.0	776.9	778.0	781.4	783.0	784.5	788.4	791.7	797.6
10°	749.7	748.1	745.0	744.2	745.0	748.1	749.7	753.7	757.5	761.8	765.8
12.5°	717.6	714.5	713.9	714.7	713.9	714.5	717.6	722.9	733.1	733.0	733.8
15°	675.0	673.5	669.1	670.3	669.1	673.5	675.0	680.1	684.9	690.7	696.6
17.5°	633.1	631.2	625.9	630.6	625.9	631.2	633.1	635.8	641.9	650.3	659.0
20°	606.6	603.5	600.8	600.4	600.8	603.5	606.6	609.5	616.1	623.2	629.9
22.5°	581.5	578.7	578.5	575.8	578.5	578.7	581.5	585.8	592.5	596.4	602.8
25°	550.1	547.3	546.5	544.6	546.5	547.3	550.1	553.2	557.5	560.7	567.7
27.5°	525.9	524.6	523.2	523.8	523.2	524.6	525.9	526.3	528.4	532.5	536.5
30°	511.2	510.8	510.0	510.0	510.0	510.8	511.2	510.0	512.0	513.9	517.1
32.5°	499.0	498.9	499.3	499.3	499.3	498.9	499.0	497.2	497.9	498.6	500.1
35°	481.7	482.9	483.7	482.5	483.7	482.9	481.7	480.2	479.0	476.3	477.0
37.5°	466.2	467.4	468.5	469.8	468.5	467.4	466.2	462.9	460.1	457.7	454.8
40°	454.2	457.0	457.8	459.7	457.8	457.0	454.2	450.7	447.6	444.7	441.6
42.5°	442.9	446.0	448.0	448.4	448.0	446.0	442.9	439.4	434.6	431.3	426.9
45°	425.6	428.7	431.4	431.4	431.4	428.7	425.6	419.6	414.5	409.4	405.1
47.5°	407.6	412.1	414.9	415.6	414.9	412.1	407.6	401.5	394.4	388.1	381.8
50°	395.3	400.8	403.5	405.5	403.5	400.8	395.3	388.6	381.1	373.2	365.8
52.5°	383.3	388.8	392.5	393.5	392.5	388.8	383.3	375.1	366.1	357.6	351.0
55°	362.6	370.5	374.9	376.4	374.9	370.5	362.6	353.7	345.0	334.4	325.0
57.5°	343.2	350.4	355.5	356.6	355.5	350.4	343.2	332.5	321.4	310.1	300.0
60°	328.1	336.0	342.2	343.5	342.2	336.0	328.1	317.5	305.7	294.7	282.2
62.5°	312.7	320.8	326.5	329.6	326.5	320.8	312.7	301.4	288.7	276.5	263.9
65°	286.1	294.3	299.8	300.9	299.8	294.3	286.1	275.1	261.7	248.7	238.1
67.5°	257.0	265.2	268.8	271.1	268.8	265.2	257.0	246.6	233.4	219.9	207.9
70°	236.5	243.2	247.1	249.1	247.1	243.2	236.5	225.5	214.5	200.8	187.8
72.5°	213.3	220.3	224.8	225.2	224.8	220.3	213.3	203.9	192.2	179.5	168.0
75°	177.6	183.9	186.2	186.2	186.2	183.9	177.6	168.5	159.2	149.0	137.5
77.5°	140.6	143.8	146.8	147.4	146.8	143.8	140.6	134.1	126.3	116.0	107.6
80°	116.7	118.7	121.0	121.0	121.0	118.7	116.7	110.8	103.3	94.7	88.1
82.5°	92.2	93.8	96.1	95.8	96.1	93.8	92.2	87.6	81.3	75.5	69.5
85°	55.7	59.4	59.0	58.2	59.0	59.4	55.7	56.6	50.7	46.8	41.3
87.5°	28.5	28.8	29.8	30.5	29.8	28.8	28.5	27.5	24.5	22.8	21.4
90°	16.6	16.8	17.1	17.3	17.1	16.8	16.6	16.3	15.8	14.9	14.2
92.5°	15.8	15.8	15.9	15.9	15.9	15.8	15.8	15.7	15.2	14.5	13.7
95°	16.4	16.5	16.6	16.7	16.6	16.5	16.4	16.2	15.8	14.9	14.2
97.5°	15.8	15.9	16.0	16.2	16.0	15.9	15.8	15.7	15.6	15.5	15.3
100°	15.8	15.9	16.0	16.2	16.0	15.9	15.8	15.7	16.7	18.8	21.0
102.5°	16.6	16.6	16.6	16.6	16.6	16.6	16.6	16.5	28.2	51.7	75.1
105°	178.0	173.4	168.7	164.2	168.7	173.4	178.0	182.6	184.3	183.2	182.1
107.5°	227.3	227.8	228.3	228.8	228.3	227.8	227.3	226.8	226.3	225.8	225.2
110°	255.8	256.1	256.5	256.9	256.5	256.1	255.8	255.4	255.1	254.8	254.6



TEST NUMBER: P332544-840

CATALOG NUMBER: SA4XXDIP-C575D590U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	283.6	284.1	284.6	285.0	284.6	284.1	283.6	283.1	282.9	283.0	283.0
115°	326.1	326.1	326.1	326.1	326.1	326.1	326.1	326.1	325.9	325.7	325.4
117.5°	367.9	367.9	367.8	367.8	367.8	367.9	367.9	368.0	368.0	368.1	368.1
120°	394.8	394.6	394.3	394.0	394.3	394.6	394.8	395.1	395.1	394.8	394.6
122.5°	420.6	420.3	420.1	419.8	420.1	420.3	420.6	420.8	420.9	420.7	420.6
125°	458.2	458.3	458.4	458.6	458.4	458.3	458.2	458.1	457.8	457.4	457.0
127.5°	492.8	492.7	492.6	492.5	492.6	492.7	492.8	492.9	493.0	493.1	493.2
130°	515.5	515.5	515.5	515.5	515.5	515.5	515.5	515.5	515.5	515.3	515.2
132.5°	537.0	536.9	536.8	536.7	536.8	536.9	537.0	537.1	537.1	537.0	536.9
135°	567.7	568.0	568.4	568.6	568.4	568.0	567.7	567.5	567.2	567.0	566.7
137.5°	596.0	595.9	595.8	595.7	595.8	595.9	596.0	596.0	595.9	595.7	595.4
140°	614.3	614.4	614.5	614.6	614.5	614.4	614.3	614.1	613.9	613.5	613.1
142.5°	630.3	630.3	630.3	630.4	630.3	630.3	630.3	630.3	630.1	629.8	629.4
145°	653.6	653.9	654.2	654.4	654.2	653.9	653.6	653.4	653.2	653.1	652.9
147.5°	674.0	674.1	674.2	674.3	674.2	674.1	674.0	673.8	673.7	673.6	673.5
150°	686.8	687.0	687.1	687.2	687.1	687.0	686.8	686.7	686.6	686.6	686.6
152.5°	698.5	698.4	698.3	698.3	698.3	698.4	698.5	698.6	698.5	698.3	698.1
155°	714.3	713.9	713.6	713.2	713.6	713.9	714.3	714.7	714.6	714.1	713.6
157.5°	727.6	726.9	726.3	725.6	726.3	726.9	727.6	728.2	728.2	727.6	726.9
160°	736.2	735.4	734.7	733.9	734.7	735.4	736.2	737.0	737.0	736.2	735.4
162.5°	743.0	742.0	741.2	740.3	741.2	742.0	743.0	743.9	743.9	743.1	742.4
165°	752.9	751.7	750.6	749.4	750.6	751.7	752.9	754.1	754.2	753.1	752.0
167.5°	760.1	758.8	757.5	756.3	757.5	758.8	760.1	761.3	761.4	760.3	759.2
170°	764.3	763.0	761.6	760.4	761.6	763.0	764.3	765.5	765.7	764.6	763.6
172.5°	766.9	765.5	764.1	762.7	764.1	765.5	766.9	768.2	768.4	767.4	766.4
175°	770.2	768.6	767.1	765.6	767.1	768.6	770.2	771.7	771.9	770.7	769.6
177.5°	771.1	769.9	768.6	767.4	768.6	769.9	771.1	772.3	772.5	771.7	770.9
180°	770.2	770.2	770.2	770.2	770.2	770.2	770.2	770.2	770.2	770.2	770.2



TEST NUMBER: P332544-840

CATALOG NUMBER: SA4XXDIP-C575D590U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	948.5	948.5	948.5	948.5	948.5	948.5	948.5	948.5	948.5	948.5	948.5
2.5°	906.7	908.0	913.0	917.7	923.3	927.5	930.3	933.4	940.0	945.3	950.4
5°	849.5	851.4	861.7	868.8	880.9	891.5	899.8	908.8	919.5	933.9	947.4
7.5°	799.1	806.5	817.6	829.1	841.5	855.4	867.5	881.1	899.4	919.4	940.0
10°	770.5	778.8	790.5	804.0	815.7	831.8	846.8	862.8	883.6	908.1	932.4
12.5°	741.9	755.5	764.5	780.3	793.0	806.4	822.2	843.3	867.7	893.2	922.6
15°	706.1	713.6	730.8	739.5	757.5	778.0	793.7	815.0	838.5	872.3	905.2
17.5°	664.7	674.6	688.3	704.8	725.6	741.5	761.1	782.9	812.6	846.2	887.6
20°	637.7	646.0	662.9	681.0	703.0	719.8	740.6	761.8	792.5	828.3	871.5
22.5°	613.5	621.5	639.2	656.1	677.5	698.1	719.9	744.6	774.0	811.6	855.8
25°	576.0	586.6	602.4	619.7	640.1	663.7	687.2	709.2	740.6	780.3	827.5
27.5°	542.8	551.3	562.7	582.3	605.5	628.2	651.7	679.3	709.5	751.5	800.4
30°	521.4	529.3	540.7	558.8	580.4	604.7	629.0	655.8	687.2	728.8	778.8
32.5°	504.4	510.4	520.6	536.7	556.4	582.1	606.1	633.8	666.8	707.8	756.5
35°	479.4	484.4	488.4	503.7	521.4	545.0	569.4	598.8	630.7	669.5	718.2
37.5°	454.7	456.5	462.2	472.3	489.4	511.1	533.7	562.7	595.3	634.9	678.8
40°	439.7	440.5	444.0	453.4	468.4	488.8	510.8	539.5	570.5	607.8	651.5
42.5°	425.0	424.4	427.7	434.2	448.3	466.8	488.5	514.6	545.7	580.2	621.3
45°	401.5	401.5	400.8	406.3	417.7	435.8	453.8	479.0	504.9	538.7	573.3
47.5°	377.2	375.0	375.7	378.5	388.1	402.9	421.2	441.8	464.6	493.3	523.6
50°	361.5	358.3	357.2	360.3	368.9	381.9	399.2	417.3	438.9	464.0	490.0
52.5°	344.2	341.0	338.9	341.1	349.1	361.1	376.9	392.7	412.1	432.6	455.0
55°	317.5	314.0	312.8	313.6	319.4	328.9	342.2	356.8	371.3	388.2	403.9
57.5°	291.1	285.4	284.3	283.9	287.9	296.6	307.7	320.3	330.9	341.1	357.9
60°	273.9	266.8	264.5	264.1	267.2	274.3	284.5	297.0	304.5	311.5	326.1
62.5°	255.3	248.5	243.4	243.9	246.7	253.5	262.5	271.6	276.5	284.3	294.1
65°	226.7	218.0	214.1	213.0	214.5	220.0	227.1	233.0	238.5	241.7	251.1
67.5°	198.1	190.9	185.1	183.7	183.0	186.7	192.5	196.1	200.0	202.8	208.3
70°	178.0	171.7	164.6	162.3	161.9	165.0	170.6	171.0	176.4	177.6	183.5
72.5°	158.1	150.4	145.4	143.1	141.5	144.3	147.9	149.0	151.9	154.0	157.1
75°	127.3	121.4	116.7	113.2	112.0	113.5	113.5	115.5	117.4	118.7	122.2
77.5°	100.2	93.4	87.9	85.8	84.4	83.4	84.2	85.4	84.5	86.5	87.4
80°	81.3	74.2	70.0	69.2	66.8	64.8	64.4	65.6	64.0	64.8	67.2
82.5°	62.8	58.3	53.6	52.8	49.8	48.8	48.4	47.7	47.7	47.6	48.0
85°	37.4	34.5	31.4	29.5	28.3	26.4	26.4	25.5	24.7	23.9	24.3
87.5°	17.8	17.0	15.2	14.0	13.2	11.8	11.5	10.3	9.7	9.1	8.5
90°	13.4	12.6	11.6	10.6	9.6	8.6	7.4	6.0	4.5	3.1	1.7
92.5°	13.0	12.2	11.2	10.2	9.2	8.1	7.6	7.5	7.4	7.4	7.3
95°	13.4	12.6	12.5	12.4	12.3	12.1	14.2	18.6	23.0	27.4	31.7
97.5°	15.2	15.2	29.5	43.8	58.1	72.3	78.2	75.4	72.7	70.0	67.3
100°	23.1	25.3	43.0	60.7	78.4	96.0	103.7	101.4	99.1	96.7	94.4
102.5°	98.7	122.1	124.4	126.7	129.1	131.4	131.7	130.0	128.3	126.5	124.9
105°	180.9	179.8	179.0	178.4	177.8	177.1	176.4	175.7	174.9	174.2	173.4
107.5°	224.7	224.1	223.2	222.4	221.5	220.6	219.9	219.5	219.2	218.8	218.4
110°	254.3	254.1	253.3	252.5	251.8	251.0	250.3	250.0	249.6	249.2	248.8



TEST NUMBER: P332544-840

CATALOG NUMBER: SA4XXDIP-C575D590U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	283.1	283.1	282.8	282.4	282.0	281.7	281.1	280.4	279.7	279.0	278.3
115°	325.2	324.9	325.0	325.2	325.3	325.4	325.3	324.9	324.5	324.2	323.8
117.5°	368.2	368.2	367.9	367.7	367.4	367.1	366.7	366.2	365.7	365.2	364.7
120°	394.3	394.0	394.2	394.3	394.5	394.6	394.4	393.8	393.3	392.8	392.3
122.5°	420.4	420.3	420.1	419.9	419.8	419.6	419.3	419.0	418.7	418.4	418.1
125°	456.7	456.3	456.5	456.8	457.0	457.3	457.2	456.7	456.2	455.6	455.0
127.5°	493.2	493.3	492.7	492.1	491.6	491.0	490.6	490.5	490.4	490.2	490.1
130°	515.1	515.0	514.6	514.2	513.8	513.4	513.2	513.1	512.9	512.8	512.7
132.5°	536.7	536.6	536.1	535.6	535.2	534.7	534.3	534.1	533.9	533.6	533.4
135°	566.5	566.2	565.7	565.2	564.7	564.2	564.0	564.1	564.3	564.4	564.5
137.5°	595.1	594.8	594.3	593.7	593.1	592.6	592.3	592.2	592.2	592.1	592.1
140°	612.7	612.4	612.1	611.9	611.6	611.3	611.1	610.8	610.6	610.3	610.1
142.5°	629.2	628.9	628.7	628.6	628.4	628.3	628.0	627.5	627.1	626.6	626.2
145°	652.8	652.7	652.7	652.7	652.7	652.7	652.5	652.1	651.7	651.4	651.0
147.5°	673.4	673.3	673.4	673.6	673.7	673.8	673.5	672.8	672.1	671.4	670.7
150°	686.6	686.6	686.8	686.9	687.0	687.2	687.0	686.5	686.0	685.4	684.9
152.5°	697.9	697.7	697.9	698.2	698.4	698.6	698.5	698.1	697.7	697.3	696.9
155°	713.1	712.6	713.0	713.4	713.8	714.1	714.3	714.1	714.0	713.9	713.8
157.5°	726.3	725.6	726.0	726.5	726.9	727.3	727.6	727.7	727.7	727.8	727.9
160°	734.7	733.9	734.0	734.2	734.3	734.4	734.7	735.1	735.4	735.8	736.2
162.5°	741.5	740.8	740.9	741.0	741.1	741.3	741.6	742.1	742.6	743.1	743.6
165°	751.0	750.0	750.0	750.0	750.0	750.0	750.3	750.9	751.6	752.2	752.9
167.5°	758.1	756.9	757.0	757.1	757.2	757.2	757.6	758.3	758.9	759.6	760.2
170°	762.5	761.5	761.4	761.2	761.1	761.0	761.3	762.1	762.9	763.7	764.5
172.5°	765.4	764.3	764.2	764.1	764.0	763.8	764.2	764.9	765.7	766.4	767.2
175°	768.4	767.3	767.2	767.1	766.9	766.8	767.1	767.9	768.6	769.4	770.2
177.5°	770.1	769.2	769.0	768.8	768.6	768.4	768.7	769.4	770.1	770.8	771.5
180°	770.2	770.2	770.2	770.2	770.2	770.2	770.2	770.2	770.2	770.2	770.2



TEST NUMBER: P332544-840

CATALOG NUMBER: SA4XXDIP-C575D590U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	948.5	948.5	948.5	948.5	948.5	948.5	948.5	948.5	948.5	948.5	948.5
2.5°	954.8	958.0	962.0	969.0	971.5	974.6	979.0	978.7	980.0	984.6	994.7
5°	958.4	970.5	982.3	996.4	1011.4	1021.2	1034.6	1042.8	1051.1	1061.7	1079.7
7.5°	959.8	979.1	1000.7	1025.5	1047.6	1073.1	1093.0	1111.7	1128.5	1150.9	1172.5
10°	957.6	983.5	1011.4	1042.8	1076.2	1104.5	1130.0	1159.1	1183.9	1210.9	1235.4
12.5°	953.4	984.7	1022.1	1057.2	1096.3	1138.1	1169.9	1199.3	1232.2	1263.4	1301.0
15°	944.2	987.0	1030.7	1077.0	1129.2	1177.6	1223.6	1261.6	1297.1	1343.8	1392.9
17.5°	932.4	978.6	1033.6	1089.7	1144.4	1199.6	1256.5	1313.7	1358.4	1416.4	1454.9
20°	921.4	974.8	1031.4	1098.2	1152.9	1221.6	1278.2	1333.5	1394.8	1452.6	1498.6
22.5°	905.9	964.4	1024.5	1091.0	1162.9	1231.6	1297.1	1357.2	1418.5	1481.3	1536.9
25°	886.5	939.5	1010.6	1086.0	1157.5	1232.2	1307.3	1382.7	1448.7	1515.1	1567.0
27.5°	853.1	920.1	986.3	1064.2	1143.7	1228.1	1308.4	1387.4	1456.4	1511.1	1543.3
30°	836.2	894.2	966.2	1044.4	1130.4	1221.2	1304.8	1382.3	1446.7	1490.4	1503.3
32.5°	811.0	871.0	941.4	1022.4	1113.5	1206.7	1293.8	1366.9	1420.7	1443.5	1427.8
35°	773.7	827.9	899.0	981.9	1076.6	1176.0	1262.0	1323.7	1351.3	1329.7	1275.8
37.5°	728.8	782.6	854.0	935.4	1033.5	1134.5	1212.3	1256.7	1247.6	1193.9	1113.6
40°	697.4	747.7	815.7	903.7	999.2	1100.6	1168.9	1193.0	1167.8	1090.8	1005.5
42.5°	662.6	711.6	779.8	864.7	965.8	1059.3	1118.9	1121.0	1078.8	986.7	901.1
45°	609.5	656.2	720.6	809.0	902.5	990.6	1029.9	1010.6	932.8	843.9	757.9
47.5°	557.0	597.5	661.1	745.0	833.7	907.9	927.4	892.7	809.8	723.6	643.8
50°	518.7	559.6	619.2	699.4	785.1	849.1	858.5	812.5	731.2	644.4	581.9
52.5°	481.9	522.4	580.0	654.1	732.6	790.3	790.6	737.4	656.4	579.1	520.9
55°	427.9	464.4	516.3	582.7	652.7	697.8	686.8	631.8	561.5	494.3	443.6
57.5°	375.9	407.7	455.4	510.9	572.5	609.8	591.5	538.6	475.7	418.8	380.3
60°	342.2	372.4	413.3	465.6	517.5	546.5	529.3	481.3	423.5	377.6	344.2
62.5°	309.5	335.1	374.4	419.7	467.8	489.4	473.9	426.7	376.8	335.2	308.0
65°	263.3	284.1	315.5	354.5	389.4	407.9	394.9	350.8	312.8	282.9	261.3
67.5°	220.0	236.3	260.1	291.3	321.0	331.0	319.2	288.5	256.3	232.4	217.1
70°	190.2	205.5	225.5	249.5	275.4	286.1	274.3	249.9	223.6	201.6	186.6
72.5°	164.1	175.9	192.9	213.4	233.6	244.3	236.2	212.8	190.6	174.2	161.5
75°	124.9	135.1	146.9	161.5	177.2	184.3	177.2	161.1	145.7	133.6	124.5
77.5°	90.9	96.3	105.4	116.3	126.1	131.6	125.4	114.5	105.1	96.8	92.3
80°	69.2	73.1	79.4	88.1	94.7	99.8	95.8	86.8	79.4	73.8	71.9
82.5°	50.3	52.9	57.1	63.5	68.0	70.6	68.9	62.3	59.3	54.3	52.4
85°	24.7	26.4	29.1	31.0	34.9	35.3	35.7	33.0	30.3	29.1	27.5
87.5°	9.1	9.7	10.9	12.1	13.6	14.1	14.0	14.2	13.2	13.0	11.9
90°	3.1	4.5	6.0	7.4	8.6	9.6	10.6	11.6	12.6	13.4	14.2
92.5°	7.4	7.4	7.5	7.6	8.1	9.2	10.2	11.2	12.2	13.0	13.7
95°	27.4	23.0	18.6	14.2	12.1	12.3	12.4	12.5	12.6	13.4	14.2
97.5°	70.0	72.7	75.4	78.2	72.3	58.1	43.8	29.5	15.2	15.2	15.3
100°	96.7	99.1	101.4	103.7	96.0	78.4	60.7	43.0	25.3	23.1	21.0
102.5°	126.5	128.3	130.0	131.7	131.4	129.1	126.7	124.4	122.1	98.7	75.1
105°	174.2	174.9	175.7	176.4	177.1	177.8	178.4	179.0	179.8	180.9	182.1
107.5°	218.8	219.2	219.5	219.9	220.6	221.5	222.4	223.2	224.1	224.7	225.2
110°	249.2	249.6	250.0	250.3	251.0	251.8	252.5	253.3	254.1	254.3	254.6





TEST NUMBER: P332544-840

CATALOG NUMBER: SA4XXDIP-C575D590U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	279.0	279.7	280.4	281.1	281.7	282.0	282.4	282.8	283.1	283.1	283.0
115°	324.2	324.5	324.9	325.3	325.4	325.3	325.2	325.0	324.9	325.2	325.4
117.5°	365.2	365.7	366.2	366.7	367.1	367.4	367.7	367.9	368.2	368.2	368.1
120°	392.8	393.3	393.8	394.4	394.6	394.5	394.3	394.2	394.0	394.3	394.6
122.5°	418.4	418.7	419.0	419.3	419.6	419.8	419.9	420.1	420.3	420.4	420.6
125°	455.6	456.2	456.7	457.2	457.3	457.0	456.8	456.5	456.3	456.7	457.0
127.5°	490.2	490.4	490.5	490.6	491.0	491.6	492.1	492.7	493.3	493.2	493.2
130°	512.8	512.9	513.1	513.2	513.4	513.8	514.2	514.6	515.0	515.1	515.2
132.5°	533.6	533.9	534.1	534.3	534.7	535.2	535.6	536.1	536.6	536.7	536.9
135°	564.4	564.3	564.1	564.0	564.2	564.7	565.2	565.7	566.2	566.5	566.7
137.5°	592.1	592.2	592.2	592.3	592.6	593.1	593.7	594.3	594.8	595.1	595.4
140°	610.3	610.6	610.8	611.1	611.3	611.6	611.9	612.1	612.4	612.7	613.1
142.5°	626.6	627.1	627.5	628.0	628.3	628.4	628.6	628.7	628.9	629.2	629.4
145°	651.4	651.7	652.1	652.5	652.7	652.7	652.7	652.7	652.7	652.8	652.9
147.5°	671.4	672.1	672.8	673.5	673.8	673.7	673.6	673.4	673.3	673.4	673.5
150°	685.4	686.0	686.5	687.0	687.2	687.0	686.9	686.8	686.6	686.6	686.6
152.5°	697.3	697.7	698.1	698.5	698.6	698.4	698.2	697.9	697.7	697.9	698.1
155°	713.9	714.0	714.1	714.3	714.1	713.8	713.4	713.0	712.6	713.1	713.6
157.5°	727.8	727.7	727.7	727.6	727.3	726.9	726.5	726.0	725.6	726.3	726.9
160°	735.8	735.4	735.1	734.7	734.4	734.3	734.2	734.0	733.9	734.7	735.4
162.5°	743.1	742.6	742.1	741.6	741.3	741.1	741.0	740.9	740.8	741.5	742.4
165°	752.2	751.6	750.9	750.3	750.0	750.0	750.0	750.0	750.0	751.0	752.0
167.5°	759.6	758.9	758.3	757.6	757.2	757.2	757.1	757.0	756.9	758.1	759.2
170°	763.7	762.9	762.1	761.3	761.0	761.1	761.2	761.4	761.5	762.5	763.6
172.5°	766.4	765.7	764.9	764.2	763.8	764.0	764.1	764.2	764.3	765.4	766.4
175°	769.4	768.6	767.9	767.1	766.8	766.9	767.1	767.2	767.3	768.4	769.6
177.5°	770.8	770.1	769.4	768.7	768.4	768.6	768.8	769.0	769.2	770.1	770.9
180°	770.2	770.2	770.2	770.2	770.2	770.2	770.2	770.2	770.2	770.2	770.2



TEST NUMBER: P332544-840  
 CATALOG NUMBER: SA4XXDIP-C575D590U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	948.5	948.5	948.5	948.5	948.5	948.5	948.5
2.5°	999.8	1000.4	1003.2	1005.4	1006.0	1009.2	1009.5
5°	1087.6	1094.3	1107.2	1108.4	1110.3	1120.6	1112.8
7.5°	1190.5	1207.5	1218.8	1228.8	1232.4	1236.9	1236.0
10°	1256.6	1281.7	1294.2	1314.3	1315.1	1320.2	1317.1
12.5°	1322.9	1352.1	1375.0	1378.8	1395.5	1398.2	1402.6
15°	1416.8	1447.9	1479.8	1491.2	1514.3	1519.8	1528.4
17.5°	1505.2	1536.9	1559.2	1588.7	1598.2	1610.9	1602.4
20°	1553.6	1588.2	1616.5	1639.6	1649.5	1656.6	1655.8
22.5°	1582.9	1617.7	1640.6	1658.2	1667.4	1670.4	1670.2
25°	1601.1	1621.2	1628.3	1635.0	1624.8	1621.2	1622.8
27.5°	1550.2	1545.0	1526.6	1502.4	1477.2	1457.2	1446.4
30°	1480.2	1449.5	1421.6	1372.9	1347.7	1332.8	1319.4
32.5°	1380.8	1332.2	1278.6	1234.0	1205.3	1183.2	1179.8
35°	1210.6	1137.5	1071.9	1017.2	989.0	965.0	959.5
37.5°	1029.3	953.3	894.2	846.1	815.7	798.8	783.0
40°	908.8	843.6	785.5	744.6	721.4	709.2	699.4
42.5°	816.1	756.5	698.7	667.5	646.6	639.1	633.4
45°	688.0	632.6	592.5	569.0	556.7	544.2	538.3
47.5°	585.4	540.4	513.9	493.9	480.9	473.4	469.6
50°	527.3	490.4	466.8	451.5	439.7	433.7	430.6
52.5°	475.7	445.5	425.7	413.4	405.5	401.1	399.8
55°	409.8	386.7	374.1	363.5	357.6	353.7	352.0
57.5°	356.2	338.4	328.2	319.4	317.2	313.9	312.8
60°	321.0	307.3	298.6	292.8	290.7	286.8	287.6
62.5°	289.9	278.6	271.2	267.9	265.3	262.0	263.1
65°	245.2	236.9	233.0	229.8	226.7	224.8	226.3
67.5°	205.7	200.1	194.7	192.9	191.4	191.1	189.3
70°	180.0	175.2	170.6	169.4	169.4	167.7	167.3
72.5°	155.1	151.7	148.6	147.6	146.4	147.0	145.4
75°	119.9	117.0	115.9	114.7	114.3	114.3	113.2
77.5°	88.6	86.5	84.6	84.6	83.2	82.7	82.5
80°	67.2	66.4	64.8	64.8	64.0	64.4	63.6
82.5°	50.5	49.4	49.1	48.5	47.4	47.5	46.7
85°	27.1	26.0	25.5	24.3	23.5	24.3	23.5
87.5°	12.4	12.2	12.0	11.5	11.2	11.3	10.4
90°	14.9	15.8	16.3	16.6	16.8	17.1	17.3
92.5°	14.5	15.2	15.7	15.8	15.8	15.9	15.9
95°	14.9	15.8	16.2	16.4	16.5	16.6	16.7
97.5°	15.5	15.6	15.7	15.8	15.9	16.0	16.2
100°	18.8	16.7	15.7	15.8	15.9	16.0	16.2
102.5°	51.7	28.2	16.5	16.6	16.6	16.6	16.6
105°	183.2	184.3	182.6	178.0	173.4	168.7	164.2
107.5°	225.8	226.3	226.8	227.3	227.8	228.3	228.8
110°	254.8	255.1	255.4	255.8	256.1	256.5	256.9



TEST NUMBER: P332544-840

CATALOG NUMBER: SA4XXDIP-C575D590U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	283.0	282.9	283.1	283.6	284.1	284.6	285.0
115°	325.7	325.9	326.1	326.1	326.1	326.1	326.1
117.5°	368.1	368.0	368.0	367.9	367.9	367.8	367.8
120°	394.8	395.1	395.1	394.8	394.6	394.3	394.0
122.5°	420.7	420.9	420.8	420.6	420.3	420.1	419.8
125°	457.4	457.8	458.1	458.2	458.3	458.4	458.6
127.5°	493.1	493.0	492.9	492.8	492.7	492.6	492.5
130°	515.3	515.5	515.5	515.5	515.5	515.5	515.5
132.5°	537.0	537.1	537.1	537.0	536.9	536.8	536.7
135°	567.0	567.2	567.5	567.7	568.0	568.4	568.6
137.5°	595.7	595.9	596.0	596.0	595.9	595.8	595.7
140°	613.5	613.9	614.1	614.3	614.4	614.5	614.6
142.5°	629.8	630.1	630.3	630.3	630.3	630.3	630.4
145°	653.1	653.2	653.4	653.6	653.9	654.2	654.4
147.5°	673.6	673.7	673.8	674.0	674.1	674.2	674.3
150°	686.6	686.6	686.7	686.8	687.0	687.1	687.2
152.5°	698.3	698.5	698.6	698.5	698.4	698.3	698.3
155°	714.1	714.6	714.7	714.3	713.9	713.6	713.2
157.5°	727.6	728.2	728.2	727.6	726.9	726.3	725.6
160°	736.2	737.0	737.0	736.2	735.4	734.7	733.9
162.5°	743.1	743.9	743.9	743.0	742.0	741.2	740.3
165°	753.1	754.2	754.1	752.9	751.7	750.6	749.4
167.5°	760.3	761.4	761.3	760.1	758.8	757.5	756.3
170°	764.6	765.7	765.5	764.3	763.0	761.6	760.4
172.5°	767.4	768.4	768.2	766.9	765.5	764.1	762.7
175°	770.7	771.9	771.7	770.2	768.6	767.1	765.6
177.5°	771.7	772.5	772.3	771.1	769.9	768.6	767.4
180°	770.2	770.2	770.2	770.2	770.2	770.2	770.2

(END OF REPORT)