

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332891-840

Luminaire Tested: **SA4XXRDIP-C350D1205U840-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332891-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C350D1205U840-4F0-1E-UDD-A4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5846.8 lumens
Efficiency: N/A
Efficacy: 138.6 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 42.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332891-840

CATALOG NUMBER: SA4XXRDIP-C350D1205U840-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332891-840

CATALOG NUMBER: SA4XXRDIP-C350D1205U840-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	34	34	34	26
1	93	88	85	82	82	79	76	73	61	59	58	45	44	43	30	30	29	22
2	84	77	72	67	75	69	65	60	54	51	48	40	38	36	27	26	25	19
3	77	68	61	56	69	61	55	51	48	44	41	35	33	31	24	22	21	16
4	71	60	53	47	63	54	48	43	42	38	35	32	29	26	22	20	18	14
5	65	54	46	40	57	48	42	37	38	33	30	28	25	23	19	18	16	12
6	60	48	40	35	53	43	37	32	34	29	26	26	22	20	18	16	14	11
7	55	43	36	30	49	39	33	28	31	26	23	23	20	18	16	14	13	10
8	51	39	32	27	45	35	29	25	28	23	20	21	18	16	15	13	11	9
9	47	36	29	24	42	32	26	22	26	21	18	19	16	14	14	12	10	8
10	44	33	26	21	39	29	23	19	24	19	16	18	15	13	13	11	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4789	4789	4789	4789
5°	5555	4803	4246	4803
10°	6571	4782	3789	4782
15°	7590	4738	3256	4738
20°	8451	4677	2944	4677
25°	8725	4618	2734	4618
30°	7637	4545	2606	4545
35°	5945	4438	2530	4438
40°	4458	4314	2488	4314
45°	3520	4117	2466	4117
50°	2972	3890	2396	3890
55°	2590	3640	2267	3640
60°	2330	3379	2007	3379
65°	2055	3100	1727	3100
70°	1851	2811	1555	2811
75°	1550	2489	1326	2489
80°	1311	2120	1246	2120
85°	1102	1667	1102	1667



TEST NUMBER: P332891-840

CATALOG NUMBER: SA4XXRDIP-C350D1205U840-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	57.5	1.0
10°-20°	173.4	3.0
20°-30°	271.2	4.6
30°-40°	301.5	5.2
40°-50°	267.5	4.6
50°-60°	208.4	3.6
60°-70°	136.5	2.3
70°-80°	67.1	1.1
80°-90°	19.8	0.3
90°-100°	431.4	7.4
100°-110°	897.9	15.4
110°-120°	804.2	13.8
120°-130°	676.5	11.6
130°-140°	564.1	9.6
140°-150°	430.9	7.4
150°-160°	302.9	5.2
160°-170°	178.2	3.0
170°-180°	58.0	1.0
0°-30°	502.0	8.6
0°-40°	803.5	13.7
0°-60°	1279.4	21.9
0°-90°	1502.8	25.7
90°-120°	2133.5	36.5
90°-150°	3805.0	65.1
90°-180°	4344.0	74.3
0°-180°	5846.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	593	593	593	593	593	
5°	686	593	524	593	686	69
15°	908	567	390	567	908	258
25°	980	518	307	518	980	435
35°	603	450	257	450	603	378
45°	308	361	216	361	308	244
55°	184	259	161	259	184	167
65°	108	162	90	162	108	108
75°	50	80	42	80	50	55
85°	12	18	12	18	12	14
90°	25	1	25	1	25	20
95°	286	39	286	39	286	444
105°	1651	137	1651	137	1651	1632
115°	1585	242	1585	242	1585	1574
125°	1265	337	1265	337	1265	1149
135°	1131	400	1131	400	1131	873
145°	924	461	924	461	924	585
155°	773	524	773	524	773	361
165°	675	572	675	572	675	193
175°	608	596	608	596	608	59
180°	597	597	597	597	597	



TEST NUMBER: P332891-840

CATALOG NUMBER: SA4XXRDIP-C350D1205U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2
2.5°	625.7	627.4	625.7	625.5	623.6	623.0	622.3	619.8	615.2	612.5	613.1
5°	685.5	691.5	688.1	687.6	682.4	677.1	673.8	666.1	657.9	652.5	647.9
7.5°	754.6	758.0	755.9	752.6	744.1	739.2	731.4	721.4	706.8	695.7	685.5
10°	801.6	804.5	803.5	797.3	791.1	778.4	771.2	757.2	738.7	724.2	710.5
12.5°	847.9	850.9	842.5	842.8	831.0	821.0	809.7	791.9	770.7	751.9	734.9
15°	908.2	904.3	904.3	899.6	886.5	872.6	860.9	842.2	815.5	793.0	769.3
17.5°	955.4	956.7	954.8	943.5	933.2	918.9	897.4	875.7	850.8	820.6	796.5
20°	983.7	983.7	981.6	973.9	960.6	945.2	922.1	898.4	866.9	836.5	809.3
22.5°	995.2	995.9	993.4	987.1	975.1	960.2	940.4	916.4	883.8	849.7	816.0
25°	979.5	984.0	984.4	982.8	979.2	970.1	953.1	928.6	899.4	862.3	826.0
27.5°	899.2	904.9	910.0	918.3	929.3	934.9	935.7	923.2	897.8	862.1	825.6
30°	819.3	824.0	839.6	859.9	875.7	890.0	902.5	905.8	891.5	859.5	821.0
32.5°	730.5	737.1	752.7	774.5	800.7	825.1	852.9	867.2	866.8	847.6	812.0
35°	603.2	608.0	622.4	645.3	676.8	713.0	757.2	791.5	815.0	813.3	791.5
37.5°	486.6	491.9	506.3	525.4	556.0	600.7	643.5	690.9	734.2	758.5	751.2
40°	423.0	423.2	437.4	457.0	485.6	524.6	571.2	623.8	672.1	711.6	719.1
42.5°	372.9	372.9	382.3	403.4	424.0	460.7	505.2	557.4	614.0	659.5	679.7
45°	308.3	310.4	318.1	330.7	347.0	378.1	413.7	462.2	525.5	579.6	613.3
47.5°	261.1	264.3	269.1	279.4	292.4	313.1	342.5	386.2	437.7	497.1	545.0
50°	236.6	237.1	243.3	249.0	260.2	276.8	302.6	338.9	386.3	443.3	496.7
52.5°	215.6	215.5	219.2	226.5	235.6	248.4	269.3	302.4	344.4	395.6	450.6
55°	184.0	185.2	188.1	193.8	200.8	209.8	226.3	251.2	284.2	327.9	377.9
57.5°	160.1	160.7	162.9	165.3	171.7	178.3	190.7	207.9	235.7	271.6	318.1
60°	144.3	144.6	145.3	148.9	153.9	160.2	168.5	183.1	206.5	239.2	276.1
62.5°	129.1	129.5	130.6	133.2	137.1	141.4	150.2	161.9	181.3	209.2	242.4
65°	107.6	107.8	109.5	110.4	113.5	117.3	123.8	131.7	145.1	168.5	193.6
67.5°	89.9	89.9	90.0	91.3	93.4	95.9	99.8	106.1	116.2	130.6	152.7
70°	78.4	78.4	78.9	79.6	80.8	82.9	85.1	89.9	97.3	109.0	125.9
72.5°	67.7	67.9	68.4	68.5	69.1	70.9	72.5	75.5	81.0	89.9	103.6
75°	49.7	50.4	51.6	52.6	53.8	53.5	55.2	57.2	58.8	64.0	71.9
77.5°	37.0	36.7	36.8	37.6	37.7	38.0	39.2	40.6	41.9	44.3	47.2
80°	28.2	28.2	28.9	29.2	28.9	29.2	30.4	31.1	31.5	32.5	35.1
82.5°	21.3	21.7	21.5	21.7	21.8	22.1	23.1	23.2	23.7	24.1	25.1
85°	11.9	12.2	12.4	11.9	11.9	11.9	12.4	12.6	13.1	12.9	13.4
87.5°	9.1	9.0	9.4	9.1	9.1	8.9	8.9	9.0	8.4	8.8	8.4
90°	24.6	24.6	25.9	24.6	23.4	23.4	22.3	21.1	20.0	21.1	18.8
92.5°	90.4	90.4	94.3	100.7	114.5	138.0	173.4	230.5	310.0	372.2	325.8
95°	286.3	301.5	322.8	359.1	416.6	530.4	687.6	869.5	983.4	956.3	721.6
97.5°	765.4	789.7	825.0	895.5	979.9	1102.4	1217.1	1284.8	1235.5	1007.3	675.4
100°	1076.1	1085.5	1120.6	1192.2	1294.3	1381.2	1438.7	1415.2	1243.9	943.4	612.6
102.5°	1346.5	1353.9	1391.0	1442.9	1505.5	1541.7	1525.0	1408.7	1173.5	863.6	570.3
105°	1651.0	1658.1	1674.6	1683.9	1681.5	1633.5	1517.3	1314.2	1045.5	769.8	533.9
107.5°	1764.2	1761.1	1749.4	1722.6	1664.7	1560.0	1396.4	1180.2	942.3	717.2	527.4
110°	1766.1	1755.5	1734.3	1685.1	1601.7	1472.7	1302.5	1099.5	890.7	699.4	529.3



TEST NUMBER: P332891-840

CATALOG NUMBER: SA4XXRDIP-C350D1205U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1710.7	1693.5	1664.0	1604.4	1509.7	1380.7	1219.9	1040.4	861.5	690.9	534.8
115°	1585.4	1576.0	1538.4	1468.0	1375.3	1262.6	1125.4	981.0	834.4	686.5	545.6
117.5°	1458.3	1451.1	1413.1	1353.9	1274.9	1179.3	1071.4	951.9	822.1	685.3	557.1
120°	1387.0	1374.1	1343.6	1292.0	1225.1	1141.8	1047.9	938.8	815.6	685.3	565.6
122.5°	1330.7	1317.8	1292.0	1247.9	1191.3	1118.3	1032.9	927.5	808.1	684.4	574.1
125°	1265.0	1258.0	1235.7	1201.6	1154.7	1090.1	1009.2	908.3	795.6	683.0	586.7
127.5°	1226.5	1219.5	1200.7	1170.4	1123.3	1062.0	981.3	884.7	778.9	680.3	596.8
130°	1204.0	1196.9	1178.1	1148.8	1100.8	1038.5	958.8	866.1	768.6	679.4	604.3
132.5°	1178.6	1171.5	1153.8	1120.6	1073.5	1011.3	933.4	846.3	759.2	678.5	610.9
135°	1131.3	1124.2	1105.4	1072.6	1025.6	966.9	895.3	819.1	745.2	677.1	620.8
137.5°	1072.6	1064.1	1048.6	1016.2	972.3	919.3	859.0	794.5	733.0	676.8	626.6
140°	1030.3	1020.9	1004.5	978.7	937.6	888.3	835.5	780.3	726.4	675.9	631.4
142.5°	985.2	978.7	964.1	940.2	903.8	861.1	815.8	767.2	720.7	675.9	635.1
145°	923.5	917.7	905.9	886.0	856.7	823.7	788.6	748.7	711.1	673.6	637.2
147.5°	868.8	866.8	857.8	840.7	819.1	793.2	765.1	733.5	702.5	669.3	638.3
150°	837.9	836.7	829.6	814.4	795.6	774.5	751.0	724.1	695.9	666.5	638.3
152.5°	809.7	808.5	804.3	791.8	775.9	758.5	736.9	713.7	688.3	661.9	636.5
155°	773.4	773.4	769.8	760.4	748.7	734.6	717.0	698.2	677.1	654.8	633.7
157.5°	741.4	741.4	739.3	732.3	723.4	712.1	697.3	681.6	665.6	647.5	630.7
160°	721.6	721.6	720.5	713.5	706.4	697.0	684.1	671.3	657.1	641.9	627.8
162.5°	702.9	703.9	702.7	695.6	690.4	682.1	672.0	660.9	649.6	636.2	625.0
165°	674.8	675.9	677.1	672.4	667.7	661.9	653.6	646.6	637.2	627.8	619.6
167.5°	652.5	653.4	653.6	650.6	648.2	644.7	638.1	632.8	625.9	619.4	614.0
170°	638.3	638.3	639.5	638.3	636.0	632.5	627.8	624.3	618.4	613.7	610.2
172.5°	624.3	626.1	627.3	626.1	624.7	622.2	619.4	616.7	611.9	608.0	606.4
175°	607.8	610.2	612.6	610.2	610.2	610.2	607.8	606.7	604.3	602.0	602.0
177.5°	598.2	600.1	602.0	601.1	602.0	601.1	601.1	600.1	599.2	598.2	598.2
180°	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3



TEST NUMBER: P332891-840

CATALOG NUMBER: SA4XXRDIP-C350D1205U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2
2.5°	611.2	608.5	607.1	604.1	600.5	598.5	596.8	594.3	591.1	587.6	585.2
5°	642.2	636.4	629.2	620.7	613.1	605.6	599.2	592.7	585.3	577.6	570.1
7.5°	674.0	662.8	650.6	636.4	622.8	610.3	598.7	587.8	575.4	564.2	554.1
10°	696.2	681.0	664.0	646.0	628.1	612.6	597.2	583.4	568.2	554.5	543.0
12.5°	714.2	696.2	675.8	653.5	631.9	613.1	595.5	577.4	560.1	545.3	530.0
15°	744.0	719.4	692.0	665.1	637.2	611.6	587.9	566.9	547.0	526.2	511.7
17.5°	764.6	735.3	701.9	669.7	636.7	606.5	579.3	554.2	531.3	510.1	492.7
20°	776.8	744.5	707.4	670.9	633.8	601.6	572.2	544.4	520.8	497.9	479.9
22.5°	783.7	747.9	707.4	669.1	630.8	595.8	563.6	534.7	509.0	485.9	466.2
25°	785.9	747.6	706.3	662.3	620.3	583.2	549.7	518.4	489.7	466.8	445.8
27.5°	782.7	737.7	695.4	650.3	606.8	567.8	532.7	499.8	471.1	446.5	424.9
30°	778.2	729.9	684.5	637.6	593.7	556.1	519.1	487.6	457.7	432.1	410.4
32.5°	768.2	720.3	671.5	623.5	579.0	540.3	505.1	473.4	444.1	418.0	394.9
35°	748.5	700.0	647.0	597.7	554.0	513.8	480.9	450.3	422.3	394.4	370.0
37.5°	722.6	673.1	620.3	566.3	522.5	484.6	454.4	425.7	398.4	372.8	345.9
40°	698.1	653.0	598.4	544.9	500.0	463.4	435.5	409.4	381.9	356.6	329.6
42.5°	668.5	630.1	574.9	521.2	476.9	441.6	415.6	390.1	365.1	340.5	312.4
45°	619.0	589.9	538.3	486.7	441.9	407.0	383.1	360.6	338.7	315.3	288.7
47.5°	562.3	542.6	498.1	445.1	403.8	372.4	349.3	330.9	312.4	288.9	265.7
50°	522.9	510.3	467.3	419.0	379.5	350.6	327.0	309.7	294.2	271.8	251.0
52.5°	480.9	474.1	437.8	391.6	353.6	325.2	305.0	289.5	273.8	255.1	235.7
55°	416.8	420.4	389.6	349.6	313.8	289.9	271.6	258.6	245.2	229.4	214.4
57.5°	351.3	364.5	343.8	308.7	275.1	253.0	239.1	228.3	217.0	204.0	191.1
60°	312.1	323.2	311.4	280.5	251.2	230.7	217.7	209.3	198.1	186.2	176.4
62.5°	273.9	285.7	278.7	253.8	226.5	208.8	197.4	189.7	181.3	170.9	160.7
65°	225.9	233.5	230.1	213.0	193.6	178.5	168.0	162.3	154.6	147.0	137.9
67.5°	173.0	187.7	185.8	176.6	160.0	148.1	141.3	136.2	129.3	123.6	117.4
70°	142.2	155.8	155.6	148.1	139.1	128.2	123.3	119.1	112.8	107.3	102.3
72.5°	116.4	128.9	130.8	125.0	118.9	110.5	105.9	103.0	96.9	93.2	89.1
75°	81.5	90.6	93.0	93.0	90.1	85.8	81.7	79.8	75.5	72.2	69.8
77.5°	53.4	59.2	62.9	63.7	64.2	62.7	59.4	58.1	54.7	53.6	51.3
80°	37.8	41.6	45.8	47.4	48.5	48.1	46.7	45.6	42.5	41.3	40.4
82.5°	26.1	28.2	31.7	34.9	34.5	35.9	34.5	33.8	31.4	31.0	30.1
85°	13.6	13.8	14.3	16.5	17.7	18.2	18.4	18.0	17.2	17.2	15.6
87.5°	7.9	7.7	6.7	6.7	6.6	7.2	7.0	6.8	6.7	6.8	6.5
90°	16.5	16.5	9.4	9.4	8.2	7.1	3.5	1.2	3.5	7.1	8.2
92.5°	237.0	146.0	86.3	62.0	44.8	30.5	19.5	13.3	19.5	30.5	44.8
95°	441.2	248.7	146.7	97.4	69.3	54.0	42.2	38.7	42.2	54.0	69.3
97.5°	396.7	237.7	159.2	117.9	93.6	79.6	69.5	69.5	69.5	79.6	93.6
100°	373.1	240.5	171.4	133.8	111.5	97.4	89.2	89.2	89.2	97.4	111.5
102.5°	366.6	249.9	187.3	151.6	130.3	117.1	109.9	108.0	109.9	117.1	130.3
105°	369.6	272.3	215.9	181.9	160.8	146.7	140.8	137.3	140.8	146.7	160.8
107.5°	387.0	298.3	246.7	213.1	192.9	177.9	172.0	169.7	172.0	177.9	192.9
110°	400.1	318.0	266.4	234.7	213.6	199.4	193.6	191.3	193.6	199.4	213.6



TEST NUMBER: P332891-840

CATALOG NUMBER: SA4XXRDIP-C350D1205U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	414.2	336.8	287.0	255.4	234.2	221.1	214.3	212.0	214.3	221.1	234.2
115°	436.6	366.1	319.2	287.5	265.2	253.5	245.3	241.8	245.3	253.5	265.2
117.5°	459.3	394.6	349.9	317.1	296.2	283.3	276.0	272.7	276.0	283.3	296.2
120°	475.2	414.2	369.6	336.8	316.8	304.0	295.7	293.4	295.7	304.0	316.8
122.5°	490.3	433.0	388.4	356.5	334.7	322.8	314.5	312.1	314.5	322.8	334.7
125°	512.8	458.8	416.6	383.7	361.4	348.5	341.4	336.8	341.4	348.5	361.4
127.5°	532.3	482.7	441.9	408.8	385.6	370.8	362.3	358.6	362.3	370.8	385.6
130°	544.5	498.8	458.8	424.7	402.5	384.9	375.5	370.8	375.5	384.9	402.5
132.5°	556.7	511.9	472.0	439.8	415.7	399.0	386.8	383.0	386.8	399.0	415.7
135°	572.7	530.4	491.7	461.2	436.6	416.6	404.9	400.1	404.9	416.6	436.6
137.5°	583.9	544.5	508.4	479.3	453.6	434.6	421.7	417.3	421.7	434.6	453.6
140°	591.4	553.9	518.7	490.5	465.9	446.0	433.0	429.5	433.0	446.0	465.9
142.5°	597.0	562.3	528.1	500.8	477.2	458.1	446.2	442.6	446.2	458.1	477.2
145°	603.2	571.5	541.0	515.1	492.8	476.5	464.7	461.2	464.7	476.5	492.8
147.5°	608.5	580.9	552.2	529.0	510.5	493.5	483.2	482.0	483.2	493.5	510.5
150°	611.4	585.5	559.8	537.5	519.9	505.7	496.3	495.2	496.3	505.7	519.9
152.5°	613.3	589.4	566.3	545.9	530.2	517.1	507.7	507.4	507.7	517.1	530.2
155°	614.9	594.9	575.0	557.4	544.5	532.7	525.7	524.5	525.7	532.7	544.5
157.5°	614.9	599.0	582.1	568.2	556.9	547.8	541.2	541.2	541.2	547.8	556.9
160°	614.9	600.8	586.7	573.8	564.4	556.2	551.5	551.5	551.5	556.2	564.4
162.5°	614.9	602.7	589.6	579.5	571.0	563.7	560.0	560.9	560.0	563.7	571.0
165°	612.6	603.2	592.6	585.5	579.7	573.8	571.5	571.5	571.5	573.8	579.7
167.5°	609.8	602.9	595.2	589.8	586.5	582.1	580.9	582.1	580.9	582.1	586.5
170°	607.8	602.0	596.1	592.6	590.3	586.7	585.5	586.7	585.5	586.7	590.3
172.5°	606.0	601.1	597.0	594.5	593.1	590.5	590.3	591.4	590.3	590.5	593.1
175°	603.2	599.7	597.3	597.3	596.1	594.9	594.9	596.1	594.9	594.9	596.1
177.5°	600.1	598.2	597.3	597.3	597.3	596.3	597.3	598.2	597.3	596.3	597.3
180°	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3



TEST NUMBER: P332891-840

CATALOG NUMBER: SA4XXRDIP-C350D1205U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2
2.5°	582.5	580.6	578.1	575.2	571.8	568.8	567.3	568.6	569.2	567.5	567.3
5°	564.7	558.8	554.0	546.8	541.1	536.3	533.0	531.5	532.0	528.2	527.3
7.5°	544.8	537.8	529.9	521.4	513.5	506.4	502.8	500.8	496.7	494.9	492.0
10°	532.0	522.5	514.8	504.7	495.6	487.4	483.2	479.9	475.8	473.9	469.9
12.5°	518.9	507.8	499.3	488.9	479.6	469.6	465.6	459.5	453.1	449.1	443.8
15°	500.2	486.9	476.6	464.1	453.1	441.7	431.4	419.9	415.7	406.6	401.3
17.5°	478.5	464.9	452.2	435.6	418.6	404.2	393.3	382.3	375.8	370.0	367.3
20°	464.1	451.7	434.0	414.7	395.8	380.0	371.1	364.0	356.8	352.7	349.9
22.5°	450.6	434.6	414.1	393.2	374.4	362.0	354.6	347.2	341.3	337.5	333.7
25°	427.8	407.0	385.3	361.3	348.5	337.7	329.6	323.6	320.0	315.0	313.1
27.5°	404.5	379.2	355.3	339.2	325.8	315.9	308.8	304.4	299.8	296.6	294.1
30°	386.5	360.9	339.4	324.1	310.4	302.4	296.6	291.3	287.7	285.1	283.3
32.5°	368.7	343.2	325.1	308.6	297.8	289.9	283.8	279.8	277.0	273.7	272.5
35°	343.0	320.2	304.5	289.6	278.7	271.6	266.7	262.7	260.2	259.3	258.6
37.5°	318.2	299.6	282.7	270.5	260.7	255.1	249.4	247.4	245.8	244.1	244.9
40°	302.6	285.1	270.0	257.2	249.2	243.1	239.7	237.3	235.9	235.9	235.9
42.5°	289.0	272.0	257.2	245.7	237.8	232.6	228.8	226.8	226.3	226.1	227.3
45°	267.9	252.2	237.3	227.7	221.1	215.8	213.7	212.0	212.0	213.0	213.2
47.5°	247.0	232.3	220.4	209.6	203.5	200.3	198.3	197.5	197.6	198.5	199.7
50°	234.2	219.6	207.9	198.3	192.7	189.6	187.8	187.3	187.8	187.8	189.6
52.5°	220.3	207.2	195.7	187.6	181.2	178.2	177.3	176.6	176.9	177.7	178.4
55°	199.9	188.1	177.1	169.5	164.7	162.8	160.6	160.9	160.4	160.9	160.9
57.5°	179.3	168.7	158.5	152.5	148.2	145.5	143.2	143.8	143.1	143.0	142.6
60°	166.1	154.6	146.5	141.0	136.2	133.8	131.7	132.2	131.5	131.0	130.0
62.5°	151.8	142.2	134.4	129.2	125.3	122.6	120.4	120.0	118.3	116.6	114.5
65°	131.0	123.1	116.1	111.2	107.6	105.4	103.7	102.3	98.7	94.9	93.0
67.5°	110.8	105.0	98.6	94.3	91.4	88.7	85.4	83.0	79.7	77.6	76.3
70°	97.8	92.3	86.7	82.7	79.6	77.0	73.4	71.7	69.3	68.4	67.2
72.5°	85.3	80.2	75.1	71.4	68.2	66.0	63.2	61.6	60.5	60.1	59.0
75°	66.4	62.4	58.6	55.2	52.6	51.1	50.0	48.8	48.3	46.2	44.9
77.5°	48.5	45.7	43.4	41.0	39.2	38.2	35.9	34.5	33.7	32.7	32.4
80°	37.8	35.9	33.4	32.0	29.4	28.5	27.5	27.3	27.0	26.8	26.6
82.5°	28.4	26.5	24.1	23.2	22.5	21.9	21.4	21.1	20.9	21.0	21.0
85°	14.3	13.4	13.4	13.1	12.9	12.6	12.4	12.4	12.2	12.4	12.2
87.5°	6.7	6.5	7.9	7.5	8.2	8.6	8.2	8.4	8.9	8.7	8.7
90°	9.4	9.4	16.5	16.5	18.8	21.1	20.0	21.1	22.3	23.4	23.4
92.5°	62.0	86.3	146.0	237.0	325.8	372.2	310.0	230.5	173.4	138.0	114.5
95°	97.4	146.7	248.7	441.2	721.6	956.3	983.4	869.5	687.6	530.4	416.6
97.5°	117.9	159.2	237.7	396.7	675.4	1007.3	1235.5	1284.8	1217.1	1102.4	979.9
100°	133.8	171.4	240.5	373.1	612.6	943.4	1243.9	1415.2	1438.7	1381.2	1294.3
102.5°	151.6	187.3	249.9	366.6	570.3	863.6	1173.5	1408.7	1525.0	1541.7	1505.5
105°	181.9	215.9	272.3	369.6	533.9	769.8	1045.5	1314.2	1517.3	1633.5	1681.5
107.5°	213.1	246.7	298.3	387.0	527.4	717.2	942.3	1180.2	1396.4	1560.0	1664.7
110°	234.7	266.4	318.0	400.1	529.3	699.4	890.7	1099.5	1302.5	1472.7	1601.7



TEST NUMBER: P332891-840

CATALOG NUMBER: SA4XXRDIP-C350D1205U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	255.4	287.0	336.8	414.2	534.8	690.9	861.5	1040.4	1219.9	1380.7	1509.7
115°	287.5	319.2	366.1	436.6	545.6	686.5	834.4	981.0	1125.4	1262.6	1375.3
117.5°	317.1	349.9	394.6	459.3	557.1	685.3	822.1	951.9	1071.4	1179.3	1274.9
120°	336.8	369.6	414.2	475.2	565.6	685.3	815.6	938.8	1047.9	1141.8	1225.1
122.5°	356.5	388.4	433.0	490.3	574.1	684.4	808.1	927.5	1032.9	1118.3	1191.3
125°	383.7	416.6	458.8	512.8	586.7	683.0	795.6	908.3	1009.2	1090.1	1154.7
127.5°	408.8	441.9	482.7	532.3	596.8	680.3	778.9	884.7	981.3	1062.0	1123.3
130°	424.7	458.8	498.8	544.5	604.3	679.4	768.6	866.1	958.8	1038.5	1100.8
132.5°	439.8	472.0	511.9	556.7	610.9	678.5	759.2	846.3	933.4	1011.3	1073.5
135°	461.2	491.7	530.4	572.7	620.8	677.1	745.2	819.1	895.3	966.9	1025.6
137.5°	479.3	508.4	544.5	583.9	626.6	676.8	733.0	794.5	859.0	919.3	972.3
140°	490.5	518.7	553.9	591.4	631.4	675.9	726.4	780.3	835.5	888.3	937.6
142.5°	500.8	528.1	562.3	597.0	635.1	675.9	720.7	767.2	815.8	861.1	903.8
145°	515.1	541.0	571.5	603.2	637.2	673.6	711.1	748.7	788.6	823.7	856.7
147.5°	529.0	552.2	580.9	608.5	638.3	669.3	702.5	733.5	765.1	793.2	819.1
150°	537.5	559.8	585.5	611.4	638.3	666.5	695.9	724.1	751.0	774.5	795.6
152.5°	545.9	566.3	589.4	613.3	636.5	661.9	688.3	713.7	736.9	758.5	775.9
155°	557.4	575.0	594.9	614.9	633.7	654.8	677.1	698.2	717.0	734.6	748.7
157.5°	568.2	582.1	599.0	614.9	630.7	647.5	665.6	681.6	697.3	712.1	723.4
160°	573.8	586.7	600.8	614.9	627.8	641.9	657.1	671.3	684.1	697.0	706.4
162.5°	579.5	589.6	602.7	614.9	625.0	636.2	649.6	660.9	672.0	682.1	690.4
165°	585.5	592.6	603.2	612.6	619.6	627.8	637.2	646.6	653.6	661.9	667.7
167.5°	589.8	595.2	602.9	609.8	614.0	619.4	625.9	632.8	638.1	644.7	648.2
170°	592.6	596.1	602.0	607.8	610.2	613.7	618.4	624.3	627.8	632.5	636.0
172.5°	594.5	597.0	601.1	606.0	606.4	608.0	611.9	616.7	619.4	622.2	624.7
175°	597.3	597.3	599.7	603.2	602.0	602.0	604.3	606.7	607.8	610.2	610.2
177.5°	597.3	597.3	598.2	600.1	598.2	598.2	599.2	600.1	601.1	601.1	602.0
180°	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3



TEST NUMBER: P332891-840

CATALOG NUMBER: SA4XXRDIP-C350D1205U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2
2.5°	566.2	566.6	565.3	564.9	565.3	566.6	566.2	567.3	567.5	569.2	568.6
5°	525.3	524.8	523.6	523.9	523.6	524.8	525.3	527.3	528.2	532.0	531.5
7.5°	490.3	488.5	489.0	487.1	489.0	488.5	490.3	492.0	494.9	496.7	500.8
10°	468.9	466.3	464.1	462.2	464.1	466.3	468.9	469.9	473.9	475.8	479.9
12.5°	439.7	437.4	434.5	435.0	434.5	437.4	439.7	443.8	449.1	453.1	459.5
15°	398.2	394.6	388.9	389.6	388.9	394.6	398.2	401.3	406.6	415.7	419.9
17.5°	363.0	363.0	360.4	361.1	360.4	363.0	363.0	367.3	370.0	375.8	382.3
20°	344.9	343.3	343.5	342.7	343.5	343.3	344.9	349.9	352.7	356.8	364.0
22.5°	332.2	330.2	328.5	327.1	328.5	330.2	332.2	333.7	337.5	341.3	347.2
25°	310.9	309.5	307.4	306.9	307.4	309.5	310.9	313.1	315.0	320.0	323.6
27.5°	292.2	292.0	291.0	289.9	291.0	292.0	292.2	294.1	296.6	299.8	304.4
30°	281.3	280.8	280.3	279.6	280.3	280.8	281.3	283.3	285.1	287.7	291.3
32.5°	271.6	271.2	270.7	270.8	270.7	271.2	271.6	272.5	273.7	277.0	279.8
35°	257.6	257.4	256.9	256.7	256.9	257.4	257.6	258.6	259.3	260.2	262.7
37.5°	244.7	245.3	245.0	244.9	245.0	245.3	244.7	244.9	244.1	245.8	247.4
40°	235.7	235.9	236.4	236.1	236.4	235.9	235.7	235.9	235.9	235.9	237.3
42.5°	228.2	228.2	228.9	228.1	228.9	228.2	228.2	227.3	226.1	226.3	226.8
45°	214.9	216.3	216.0	216.0	216.0	216.3	214.9	213.2	213.0	212.0	212.0
47.5°	200.3	201.6	201.9	201.8	201.9	201.6	200.3	199.7	198.5	197.6	197.5
50°	190.8	190.3	191.0	190.8	191.0	190.3	190.8	189.6	187.8	187.8	187.3
52.5°	179.0	179.2	179.2	178.8	179.2	179.2	179.0	178.4	177.7	176.9	176.6
55°	161.1	161.4	160.9	161.1	160.9	161.4	161.1	160.9	160.9	160.4	160.9
57.5°	141.6	140.5	140.9	140.4	140.9	140.5	141.6	142.6	143.0	143.1	143.8
60°	127.6	125.7	125.2	124.3	125.2	125.7	127.6	130.0	131.0	131.5	132.2
62.5°	112.0	110.6	109.0	109.8	109.0	110.6	112.0	114.5	116.6	118.3	120.0
65°	91.1	90.1	89.4	90.4	89.4	90.1	91.1	93.0	94.9	98.7	102.3
67.5°	75.3	74.8	74.8	74.4	74.8	74.8	75.3	76.3	77.6	79.7	83.0
70°	67.2	66.4	66.4	65.9	66.4	66.4	67.2	67.2	68.4	69.3	71.7
72.5°	58.8	58.1	58.3	58.0	58.3	58.1	58.8	59.0	60.1	60.5	61.6
75°	43.5	42.3	42.3	42.5	42.3	42.3	43.5	44.9	46.2	48.3	48.8
77.5°	32.4	32.2	32.5	32.1	32.5	32.2	32.4	32.4	32.7	33.7	34.5
80°	26.6	26.3	26.1	26.8	26.1	26.3	26.6	26.6	26.8	27.0	27.3
82.5°	20.6	20.6	20.5	21.4	20.5	20.6	20.6	21.0	21.0	20.9	21.1
85°	12.4	11.9	12.4	11.9	12.4	11.9	12.4	12.2	12.4	12.2	12.4
87.5°	9.3	9.4	9.0	9.1	9.0	9.4	9.3	8.7	8.7	8.9	8.4
90°	24.6	25.9	24.6	24.6	24.6	25.9	24.6	23.4	23.4	22.3	21.1
92.5°	100.7	94.3	90.4	90.4	90.4	94.3	100.7	114.5	138.0	173.4	230.5
95°	359.1	322.8	301.5	286.3	301.5	322.8	359.1	416.6	530.4	687.6	869.5
97.5°	895.5	825.0	789.7	765.4	789.7	825.0	895.5	979.9	1102.4	1217.1	1284.8
100°	1192.2	1120.6	1085.5	1076.1	1085.5	1120.6	1192.2	1294.3	1381.2	1438.7	1415.2
102.5°	1442.9	1391.0	1353.9	1346.5	1353.9	1391.0	1442.9	1505.5	1541.7	1525.0	1408.7
105°	1683.9	1674.6	1658.1	1651.0	1658.1	1674.6	1683.9	1681.5	1633.5	1517.3	1314.2
107.5°	1722.6	1749.4	1761.1	1764.2	1761.1	1749.4	1722.6	1664.7	1560.0	1396.4	1180.2
110°	1685.1	1734.3	1755.5	1766.1	1755.5	1734.3	1685.1	1601.7	1472.7	1302.5	1099.5



TEST NUMBER: P332891-840

CATALOG NUMBER: SA4XXRDIP-C350D1205U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1604.4	1664.0	1693.5	1710.7	1693.5	1664.0	1604.4	1509.7	1380.7	1219.9	1040.4
115°	1468.0	1538.4	1576.0	1585.4	1576.0	1538.4	1468.0	1375.3	1262.6	1125.4	981.0
117.5°	1353.9	1413.1	1451.1	1458.3	1451.1	1413.1	1353.9	1274.9	1179.3	1071.4	951.9
120°	1292.0	1343.6	1374.1	1387.0	1374.1	1343.6	1292.0	1225.1	1141.8	1047.9	938.8
122.5°	1247.9	1292.0	1317.8	1330.7	1317.8	1292.0	1247.9	1191.3	1118.3	1032.9	927.5
125°	1201.6	1235.7	1258.0	1265.0	1258.0	1235.7	1201.6	1154.7	1090.1	1009.2	908.3
127.5°	1170.4	1200.7	1219.5	1226.5	1219.5	1200.7	1170.4	1123.3	1062.0	981.3	884.7
130°	1148.8	1178.1	1196.9	1204.0	1196.9	1178.1	1148.8	1100.8	1038.5	958.8	866.1
132.5°	1120.6	1153.8	1171.5	1178.6	1171.5	1153.8	1120.6	1073.5	1011.3	933.4	846.3
135°	1072.6	1105.4	1124.2	1131.3	1124.2	1105.4	1072.6	1025.6	966.9	895.3	819.1
137.5°	1016.2	1048.6	1064.1	1072.6	1064.1	1048.6	1016.2	972.3	919.3	859.0	794.5
140°	978.7	1004.5	1020.9	1030.3	1020.9	1004.5	978.7	937.6	888.3	835.5	780.3
142.5°	940.2	964.1	978.7	985.2	978.7	964.1	940.2	903.8	861.1	815.8	767.2
145°	886.0	905.9	917.7	923.5	917.7	905.9	886.0	856.7	823.7	788.6	748.7
147.5°	840.7	857.8	866.8	868.8	866.8	857.8	840.7	819.1	793.2	765.1	733.5
150°	814.4	829.6	836.7	837.9	836.7	829.6	814.4	795.6	774.5	751.0	724.1
152.5°	791.8	804.3	808.5	809.7	808.5	804.3	791.8	775.9	758.5	736.9	713.7
155°	760.4	769.8	773.4	773.4	773.4	769.8	760.4	748.7	734.6	717.0	698.2
157.5°	732.3	739.3	741.4	741.4	741.4	739.3	732.3	723.4	712.1	697.3	681.6
160°	713.5	720.5	721.6	721.6	721.6	720.5	713.5	706.4	697.0	684.1	671.3
162.5°	695.6	702.7	703.9	702.9	703.9	702.7	695.6	690.4	682.1	672.0	660.9
165°	672.4	677.1	675.9	674.8	675.9	677.1	672.4	667.7	661.9	653.6	646.6
167.5°	650.6	653.6	653.4	652.5	653.4	653.6	650.6	648.2	644.7	638.1	632.8
170°	638.3	639.5	638.3	638.3	638.3	639.5	638.3	636.0	632.5	627.8	624.3
172.5°	626.1	627.3	626.1	624.3	626.1	627.3	626.1	624.7	622.2	619.4	616.7
175°	610.2	612.6	610.2	607.8	610.2	612.6	610.2	610.2	610.2	607.8	606.7
177.5°	601.1	602.0	600.1	598.2	600.1	602.0	601.1	602.0	601.1	601.1	600.1
180°	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3



TEST NUMBER: P332891-840

CATALOG NUMBER: SA4XXRDIP-C350D1205U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2
2.5°	567.3	568.8	571.8	575.2	578.1	580.6	582.5	585.2	587.6	591.1	594.3
5°	533.0	536.3	541.1	546.8	554.0	558.8	564.7	570.1	577.6	585.3	592.7
7.5°	502.8	506.4	513.5	521.4	529.9	537.8	544.8	554.1	564.2	575.4	587.8
10°	483.2	487.4	495.6	504.7	514.8	522.5	532.0	543.0	554.5	568.2	583.4
12.5°	465.6	469.6	479.6	488.9	499.3	507.8	518.9	530.0	545.3	560.1	577.4
15°	431.4	441.7	453.1	464.1	476.6	486.9	500.2	511.7	526.2	547.0	566.9
17.5°	393.3	404.2	418.6	435.6	452.2	464.9	478.5	492.7	510.1	531.3	554.2
20°	371.1	380.0	395.8	414.7	434.0	451.7	464.1	479.9	497.9	520.8	544.4
22.5°	354.6	362.0	374.4	393.2	414.1	434.6	450.6	466.2	485.9	509.0	534.7
25°	329.6	337.7	348.5	361.3	385.3	407.0	427.8	445.8	466.8	489.7	518.4
27.5°	308.8	315.9	325.8	339.2	355.3	379.2	404.5	424.9	446.5	471.1	499.8
30°	296.6	302.4	310.4	324.1	339.4	360.9	386.5	410.4	432.1	457.7	487.6
32.5°	283.8	289.9	297.8	308.6	325.1	343.2	368.7	394.9	418.0	444.1	473.4
35°	266.7	271.6	278.7	289.6	304.5	320.2	343.0	370.0	394.4	422.3	450.3
37.5°	249.4	255.1	260.7	270.5	282.7	299.6	318.2	345.9	372.8	398.4	425.7
40°	239.7	243.1	249.2	257.2	270.0	285.1	302.6	329.6	356.6	381.9	409.4
42.5°	228.8	232.6	237.8	245.7	257.2	272.0	289.0	312.4	340.5	365.1	390.1
45°	213.7	215.8	221.1	227.7	237.3	252.2	267.9	288.7	315.3	338.7	360.6
47.5°	198.3	200.3	203.5	209.6	220.4	232.3	247.0	265.7	288.9	312.4	330.9
50°	187.8	189.6	192.7	198.3	207.9	219.6	234.2	251.0	271.8	294.2	309.7
52.5°	177.3	178.2	181.2	187.6	195.7	207.2	220.3	235.7	255.1	273.8	289.5
55°	160.6	162.8	164.7	169.5	177.1	188.1	199.9	214.4	229.4	245.2	258.6
57.5°	143.2	145.5	148.2	152.5	158.5	168.7	179.3	191.1	204.0	217.0	228.3
60°	131.7	133.8	136.2	141.0	146.5	154.6	166.1	176.4	186.2	198.1	209.3
62.5°	120.4	122.6	125.3	129.2	134.4	142.2	151.8	160.7	170.9	181.3	189.7
65°	103.7	105.4	107.6	111.2	116.1	123.1	131.0	137.9	147.0	154.6	162.3
67.5°	85.4	88.7	91.4	94.3	98.6	105.0	110.8	117.4	123.6	129.3	136.2
70°	73.4	77.0	79.6	82.7	86.7	92.3	97.8	102.3	107.3	112.8	119.1
72.5°	63.2	66.0	68.2	71.4	75.1	80.2	85.3	89.1	93.2	96.9	103.0
75°	50.0	51.1	52.6	55.2	58.6	62.4	66.4	69.8	72.2	75.5	79.8
77.5°	35.9	38.2	39.2	41.0	43.4	45.7	48.5	51.3	53.6	54.7	58.1
80°	27.5	28.5	29.4	32.0	33.4	35.9	37.8	40.4	41.3	42.5	45.6
82.5°	21.4	21.9	22.5	23.2	24.1	26.5	28.4	30.1	31.0	31.4	33.8
85°	12.4	12.6	12.9	13.1	13.4	13.4	14.3	15.6	17.2	17.2	18.0
87.5°	8.2	8.6	8.2	7.5	7.9	6.5	6.7	6.5	6.8	6.7	6.8
90°	20.0	21.1	18.8	16.5	16.5	9.4	9.4	8.2	7.1	3.5	1.2
92.5°	310.0	372.2	325.8	237.0	146.0	86.3	62.0	44.8	30.5	19.5	13.3
95°	983.4	956.3	721.6	441.2	248.7	146.7	97.4	69.3	54.0	42.2	38.7
97.5°	1235.5	1007.3	675.4	396.7	237.7	159.2	117.9	93.6	79.6	69.5	69.5
100°	1243.9	943.4	612.6	373.1	240.5	171.4	133.8	111.5	97.4	89.2	89.2
102.5°	1173.5	863.6	570.3	366.6	249.9	187.3	151.6	130.3	117.1	109.9	108.0
105°	1045.5	769.8	533.9	369.6	272.3	215.9	181.9	160.8	146.7	140.8	137.3
107.5°	942.3	717.2	527.4	387.0	298.3	246.7	213.1	192.9	177.9	172.0	169.7
110°	890.7	699.4	529.3	400.1	318.0	266.4	234.7	213.6	199.4	193.6	191.3



TEST NUMBER: P332891-840

CATALOG NUMBER: SA4XXRDIP-C350D1205U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	861.5	690.9	534.8	414.2	336.8	287.0	255.4	234.2	221.1	214.3	212.0
115°	834.4	686.5	545.6	436.6	366.1	319.2	287.5	265.2	253.5	245.3	241.8
117.5°	822.1	685.3	557.1	459.3	394.6	349.9	317.1	296.2	283.3	276.0	272.7
120°	815.6	685.3	565.6	475.2	414.2	369.6	336.8	316.8	304.0	295.7	293.4
122.5°	808.1	684.4	574.1	490.3	433.0	388.4	356.5	334.7	322.8	314.5	312.1
125°	795.6	683.0	586.7	512.8	458.8	416.6	383.7	361.4	348.5	341.4	336.8
127.5°	778.9	680.3	596.8	532.3	482.7	441.9	408.8	385.6	370.8	362.3	358.6
130°	768.6	679.4	604.3	544.5	498.8	458.8	424.7	402.5	384.9	375.5	370.8
132.5°	759.2	678.5	610.9	556.7	511.9	472.0	439.8	415.7	399.0	386.8	383.0
135°	745.2	677.1	620.8	572.7	530.4	491.7	461.2	436.6	416.6	404.9	400.1
137.5°	733.0	676.8	626.6	583.9	544.5	508.4	479.3	453.6	434.6	421.7	417.3
140°	726.4	675.9	631.4	591.4	553.9	518.7	490.5	465.9	446.0	433.0	429.5
142.5°	720.7	675.9	635.1	597.0	562.3	528.1	500.8	477.2	458.1	446.2	442.6
145°	711.1	673.6	637.2	603.2	571.5	541.0	515.1	492.8	476.5	464.7	461.2
147.5°	702.5	669.3	638.3	608.5	580.9	552.2	529.0	510.5	493.5	483.2	482.0
150°	695.9	666.5	638.3	611.4	585.5	559.8	537.5	519.9	505.7	496.3	495.2
152.5°	688.3	661.9	636.5	613.3	589.4	566.3	545.9	530.2	517.1	507.7	507.4
155°	677.1	654.8	633.7	614.9	594.9	575.0	557.4	544.5	532.7	525.7	524.5
157.5°	665.6	647.5	630.7	614.9	599.0	582.1	568.2	556.9	547.8	541.2	541.2
160°	657.1	641.9	627.8	614.9	600.8	586.7	573.8	564.4	556.2	551.5	551.5
162.5°	649.6	636.2	625.0	614.9	602.7	589.6	579.5	571.0	563.7	560.0	560.9
165°	637.2	627.8	619.6	612.6	603.2	592.6	585.5	579.7	573.8	571.5	571.5
167.5°	625.9	619.4	614.0	609.8	602.9	595.2	589.8	586.5	582.1	580.9	582.1
170°	618.4	613.7	610.2	607.8	602.0	596.1	592.6	590.3	586.7	585.5	586.7
172.5°	611.9	608.0	606.4	606.0	601.1	597.0	594.5	593.1	590.5	590.3	591.4
175°	604.3	602.0	602.0	603.2	599.7	597.3	597.3	596.1	594.9	594.9	596.1
177.5°	599.2	598.2	598.2	600.1	598.2	597.3	597.3	597.3	596.3	597.3	598.2
180°	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3



TEST NUMBER: P332891-840

CATALOG NUMBER: SA4XXRDIP-C350D1205U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2
2.5°	596.8	598.5	600.5	604.1	607.1	608.5	611.2	613.1	612.5	615.2	619.8
5°	599.2	605.6	613.1	620.7	629.2	636.4	642.2	647.9	652.5	657.9	666.1
7.5°	598.7	610.3	622.8	636.4	650.6	662.8	674.0	685.5	695.7	706.8	721.4
10°	597.2	612.6	628.1	646.0	664.0	681.0	696.2	710.5	724.2	738.7	757.2
12.5°	595.5	613.1	631.9	653.5	675.8	696.2	714.2	734.9	751.9	770.7	791.9
15°	587.9	611.6	637.2	665.1	692.0	719.4	744.0	769.3	793.0	815.5	842.2
17.5°	579.3	606.5	636.7	669.7	701.9	735.3	764.6	796.5	820.6	850.8	875.7
20°	572.2	601.6	633.8	670.9	707.4	744.5	776.8	809.3	836.5	866.9	898.4
22.5°	563.6	595.8	630.8	669.1	707.4	747.9	783.7	816.0	849.7	883.8	916.4
25°	549.7	583.2	620.3	662.3	706.3	747.6	785.9	826.0	862.3	899.4	928.6
27.5°	532.7	567.8	606.8	650.3	695.4	737.7	782.7	825.6	862.1	897.8	923.2
30°	519.1	556.1	593.7	637.6	684.5	729.9	778.2	821.0	859.5	891.5	905.8
32.5°	505.1	540.3	579.0	623.5	671.5	720.3	768.2	812.0	847.6	866.8	867.2
35°	480.9	513.8	554.0	597.7	647.0	700.0	748.5	791.5	813.3	815.0	791.5
37.5°	454.4	484.6	522.5	566.3	620.3	673.1	722.6	751.2	758.5	734.2	690.9
40°	435.5	463.4	500.0	544.9	598.4	653.0	698.1	719.1	711.6	672.1	623.8
42.5°	415.6	441.6	476.9	521.2	574.9	630.1	668.5	679.7	659.5	614.0	557.4
45°	383.1	407.0	441.9	486.7	538.3	589.9	619.0	613.3	579.6	525.5	462.2
47.5°	349.3	372.4	403.8	445.1	498.1	542.6	562.3	545.0	497.1	437.7	386.2
50°	327.0	350.6	379.5	419.0	467.3	510.3	522.9	496.7	443.3	386.3	338.9
52.5°	305.0	325.2	353.6	391.6	437.8	474.1	480.9	450.6	395.6	344.4	302.4
55°	271.6	289.9	313.8	349.6	389.6	420.4	416.8	377.9	327.9	284.2	251.2
57.5°	239.1	253.0	275.1	308.7	343.8	364.5	351.3	318.1	271.6	235.7	207.9
60°	217.7	230.7	251.2	280.5	311.4	323.2	312.1	276.1	239.2	206.5	183.1
62.5°	197.4	208.8	226.5	253.8	278.7	285.7	273.9	242.4	209.2	181.3	161.9
65°	168.0	178.5	193.6	213.0	230.1	233.5	225.9	193.6	168.5	145.1	131.7
67.5°	141.3	148.1	160.0	176.6	185.8	187.7	173.0	152.7	130.6	116.2	106.1
70°	123.3	128.2	139.1	148.1	155.6	155.8	142.2	125.9	109.0	97.3	89.9
72.5°	105.9	110.5	118.9	125.0	130.8	128.9	116.4	103.6	89.9	81.0	75.5
75°	81.7	85.8	90.1	93.0	93.0	90.6	81.5	71.9	64.0	58.8	57.2
77.5°	59.4	62.7	64.2	63.7	62.9	59.2	53.4	47.2	44.3	41.9	40.6
80°	46.7	48.1	48.5	47.4	45.8	41.6	37.8	35.1	32.5	31.5	31.1
82.5°	34.5	35.9	34.5	34.9	31.7	28.2	26.1	25.1	24.1	23.7	23.2
85°	18.4	18.2	17.7	16.5	14.3	13.8	13.6	13.4	12.9	13.1	12.6
87.5°	7.0	7.2	6.6	6.7	6.7	7.7	7.9	8.4	8.8	8.4	9.0
90°	3.5	7.1	8.2	9.4	9.4	16.5	16.5	18.8	21.1	20.0	21.1
92.5°	19.5	30.5	44.8	62.0	86.3	146.0	237.0	325.8	372.2	310.0	230.5
95°	42.2	54.0	69.3	97.4	146.7	248.7	441.2	721.6	956.3	983.4	869.5
97.5°	69.5	79.6	93.6	117.9	159.2	237.7	396.7	675.4	1007.3	1235.5	1284.8
100°	89.2	97.4	111.5	133.8	171.4	240.5	373.1	612.6	943.4	1243.9	1415.2
102.5°	109.9	117.1	130.3	151.6	187.3	249.9	366.6	570.3	863.6	1173.5	1408.7
105°	140.8	146.7	160.8	181.9	215.9	272.3	369.6	533.9	769.8	1045.5	1314.2
107.5°	172.0	177.9	192.9	213.1	246.7	298.3	387.0	527.4	717.2	942.3	1180.2
110°	193.6	199.4	213.6	234.7	266.4	318.0	400.1	529.3	699.4	890.7	1099.5



TEST NUMBER: P332891-840

CATALOG NUMBER: SA4XXRDIP-C350D1205U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	214.3	221.1	234.2	255.4	287.0	336.8	414.2	534.8	690.9	861.5	1040.4
115°	245.3	253.5	265.2	287.5	319.2	366.1	436.6	545.6	686.5	834.4	981.0
117.5°	276.0	283.3	296.2	317.1	349.9	394.6	459.3	557.1	685.3	822.1	951.9
120°	295.7	304.0	316.8	336.8	369.6	414.2	475.2	565.6	685.3	815.6	938.8
122.5°	314.5	322.8	334.7	356.5	388.4	433.0	490.3	574.1	684.4	808.1	927.5
125°	341.4	348.5	361.4	383.7	416.6	458.8	512.8	586.7	683.0	795.6	908.3
127.5°	362.3	370.8	385.6	408.8	441.9	482.7	532.3	596.8	680.3	778.9	884.7
130°	375.5	384.9	402.5	424.7	458.8	498.8	544.5	604.3	679.4	768.6	866.1
132.5°	386.8	399.0	415.7	439.8	472.0	511.9	556.7	610.9	678.5	759.2	846.3
135°	404.9	416.6	436.6	461.2	491.7	530.4	572.7	620.8	677.1	745.2	819.1
137.5°	421.7	434.6	453.6	479.3	508.4	544.5	583.9	626.6	676.8	733.0	794.5
140°	433.0	446.0	465.9	490.5	518.7	553.9	591.4	631.4	675.9	726.4	780.3
142.5°	446.2	458.1	477.2	500.8	528.1	562.3	597.0	635.1	675.9	720.7	767.2
145°	464.7	476.5	492.8	515.1	541.0	571.5	603.2	637.2	673.6	711.1	748.7
147.5°	483.2	493.5	510.5	529.0	552.2	580.9	608.5	638.3	669.3	702.5	733.5
150°	496.3	505.7	519.9	537.5	559.8	585.5	611.4	638.3	666.5	695.9	724.1
152.5°	507.7	517.1	530.2	545.9	566.3	589.4	613.3	636.5	661.9	688.3	713.7
155°	525.7	532.7	544.5	557.4	575.0	594.9	614.9	633.7	654.8	677.1	698.2
157.5°	541.2	547.8	556.9	568.2	582.1	599.0	614.9	630.7	647.5	665.6	681.6
160°	551.5	556.2	564.4	573.8	586.7	600.8	614.9	627.8	641.9	657.1	671.3
162.5°	560.0	563.7	571.0	579.5	589.6	602.7	614.9	625.0	636.2	649.6	660.9
165°	571.5	573.8	579.7	585.5	592.6	603.2	612.6	619.6	627.8	637.2	646.6
167.5°	580.9	582.1	586.5	589.8	595.2	602.9	609.8	614.0	619.4	625.9	632.8
170°	585.5	586.7	590.3	592.6	596.1	602.0	607.8	610.2	613.7	618.4	624.3
172.5°	590.3	590.5	593.1	594.5	597.0	601.1	606.0	606.4	608.0	611.9	616.7
175°	594.9	594.9	596.1	597.3	597.3	599.7	603.2	602.0	602.0	604.3	606.7
177.5°	597.3	596.3	597.3	597.3	597.3	598.2	600.1	598.2	598.2	599.2	600.1
180°	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3



TEST NUMBER: P332891-840

CATALOG NUMBER: SA4XXRDIP-C350D1205U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	593.2	593.2	593.2	593.2	593.2	593.2	593.2
2.5°	622.3	623.0	623.6	625.5	625.7	627.4	625.7
5°	673.8	677.1	682.4	687.6	688.1	691.5	685.5
7.5°	731.4	739.2	744.1	752.6	755.9	758.0	754.6
10°	771.2	778.4	791.1	797.3	803.5	804.5	801.6
12.5°	809.7	821.0	831.0	842.8	842.5	850.9	847.9
15°	860.9	872.6	886.5	899.6	904.3	904.3	908.2
17.5°	897.4	918.9	933.2	943.5	954.8	956.7	955.4
20°	922.1	945.2	960.6	973.9	981.6	983.7	983.7
22.5°	940.4	960.2	975.1	987.1	993.4	995.9	995.2
25°	953.1	970.1	979.2	982.8	984.4	984.0	979.5
27.5°	935.7	934.9	929.3	918.3	910.0	904.9	899.2
30°	902.5	890.0	875.7	859.9	839.6	824.0	819.3
32.5°	852.9	825.1	800.7	774.5	752.7	737.1	730.5
35°	757.2	713.0	676.8	645.3	622.4	608.0	603.2
37.5°	643.5	600.7	556.0	525.4	506.3	491.9	486.6
40°	571.2	524.6	485.6	457.0	437.4	423.2	423.0
42.5°	505.2	460.7	424.0	403.4	382.3	372.9	372.9
45°	413.7	378.1	347.0	330.7	318.1	310.4	308.3
47.5°	342.5	313.1	292.4	279.4	269.1	264.3	261.1
50°	302.6	276.8	260.2	249.0	243.3	237.1	236.6
52.5°	269.3	248.4	235.6	226.5	219.2	215.5	215.6
55°	226.3	209.8	200.8	193.8	188.1	185.2	184.0
57.5°	190.7	178.3	171.7	165.3	162.9	160.7	160.1
60°	168.5	160.2	153.9	148.9	145.3	144.6	144.3
62.5°	150.2	141.4	137.1	133.2	130.6	129.5	129.1
65°	123.8	117.3	113.5	110.4	109.5	107.8	107.6
67.5°	99.8	95.9	93.4	91.3	90.0	89.9	89.9
70°	85.1	82.9	80.8	79.6	78.9	78.4	78.4
72.5°	72.5	70.9	69.1	68.5	68.4	67.9	67.7
75°	55.2	53.5	53.8	52.6	51.6	50.4	49.7
77.5°	39.2	38.0	37.7	37.6	36.8	36.7	37.0
80°	30.4	29.2	28.9	29.2	28.9	28.2	28.2
82.5°	23.1	22.1	21.8	21.7	21.5	21.7	21.3
85°	12.4	11.9	11.9	11.9	12.4	12.2	11.9
87.5°	8.9	8.9	9.1	9.1	9.4	9.0	9.1
90°	22.3	23.4	23.4	24.6	25.9	24.6	24.6
92.5°	173.4	138.0	114.5	100.7	94.3	90.4	90.4
95°	687.6	530.4	416.6	359.1	322.8	301.5	286.3
97.5°	1217.1	1102.4	979.9	895.5	825.0	789.7	765.4
100°	1438.7	1381.2	1294.3	1192.2	1120.6	1085.5	1076.1
102.5°	1525.0	1541.7	1505.5	1442.9	1391.0	1353.9	1346.5
105°	1517.3	1633.5	1681.5	1683.9	1674.6	1658.1	1651.0
107.5°	1396.4	1560.0	1664.7	1722.6	1749.4	1761.1	1764.2
110°	1302.5	1472.7	1601.7	1685.1	1734.3	1755.5	1766.1



TEST NUMBER: P332891-840

CATALOG NUMBER: SA4XXRDIP-C350D1205U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1219.9	1380.7	1509.7	1604.4	1664.0	1693.5	1710.7
115°	1125.4	1262.6	1375.3	1468.0	1538.4	1576.0	1585.4
117.5°	1071.4	1179.3	1274.9	1353.9	1413.1	1451.1	1458.3
120°	1047.9	1141.8	1225.1	1292.0	1343.6	1374.1	1387.0
122.5°	1032.9	1118.3	1191.3	1247.9	1292.0	1317.8	1330.7
125°	1009.2	1090.1	1154.7	1201.6	1235.7	1258.0	1265.0
127.5°	981.3	1062.0	1123.3	1170.4	1200.7	1219.5	1226.5
130°	958.8	1038.5	1100.8	1148.8	1178.1	1196.9	1204.0
132.5°	933.4	1011.3	1073.5	1120.6	1153.8	1171.5	1178.6
135°	895.3	966.9	1025.6	1072.6	1105.4	1124.2	1131.3
137.5°	859.0	919.3	972.3	1016.2	1048.6	1064.1	1072.6
140°	835.5	888.3	937.6	978.7	1004.5	1020.9	1030.3
142.5°	815.8	861.1	903.8	940.2	964.1	978.7	985.2
145°	788.6	823.7	856.7	886.0	905.9	917.7	923.5
147.5°	765.1	793.2	819.1	840.7	857.8	866.8	868.8
150°	751.0	774.5	795.6	814.4	829.6	836.7	837.9
152.5°	736.9	758.5	775.9	791.8	804.3	808.5	809.7
155°	717.0	734.6	748.7	760.4	769.8	773.4	773.4
157.5°	697.3	712.1	723.4	732.3	739.3	741.4	741.4
160°	684.1	697.0	706.4	713.5	720.5	721.6	721.6
162.5°	672.0	682.1	690.4	695.6	702.7	703.9	702.9
165°	653.6	661.9	667.7	672.4	677.1	675.9	674.8
167.5°	638.1	644.7	648.2	650.6	653.6	653.4	652.5
170°	627.8	632.5	636.0	638.3	639.5	638.3	638.3
172.5°	619.4	622.2	624.7	626.1	627.3	626.1	624.3
175°	607.8	610.2	610.2	610.2	612.6	610.2	607.8
177.5°	601.1	601.1	602.0	601.1	602.0	600.1	598.2
180°	597.3	597.3	597.3	597.3	597.3	597.3	597.3

(END OF REPORT)