

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332914-840

Luminaire Tested: **SA4XXRDIP-C575D1035U840-4F0-1E-UDD-A1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332914-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C575D1035U840-4F0-1E-UDD-A1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1035 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6085.0 lumens
Efficiency: N/A
Efficacy: 136.7 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 44.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332914-840

CATALOG NUMBER: SA4XXRDIP-C575D1035U840-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P332914-840

CATALOG NUMBER: SA4XXRDIP-C575D1035U840-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	47	47	47	41				41
1	96	92	88	85	87	84	81	78	69	67	65	55	54	52	43	42	41				35	
2	88	81	75	70	80	74	69	65	61	57	54	49	46	44	38	36	35				30	
3	80	71	64	59	73	65	59	54	54	50	46	44	40	38	34	32	30				26	
4	74	63	56	50	67	58	51	46	48	43	39	39	35	33	30	28	26				22	
5	68	56	49	43	61	52	45	40	43	38	34	35	31	28	28	25	23				20	
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	25	22	20				17	
7	58	46	38	33	52	42	35	30	35	30	26	29	25	22	23	20	18				15	
8	53	41	34	29	49	38	32	27	32	27	23	26	23	20	21	18	16				14	
9	50	38	31	26	45	35	29	24	30	24	21	24	21	18	19	17	15				13	
10	46	35	28	23	42	32	26	22	27	22	19	22	19	16	18	15	13				11	

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	7873	7873	7873	7873
5°	9132	7896	6980	7896
10°	10803	7862	6229	7862
15°	12479	7789	5353	7789
20°	13894	7689	4840	7689
25°	14343	7591	4494	7591
30°	12557	7471	4285	7471
35°	9773	7295	4159	7295
40°	7330	7093	4091	7093
45°	5787	6769	4055	6769
50°	4886	6395	3939	6395
55°	4259	5985	3727	5985
60°	3831	5557	3299	5557
65°	3377	5096	2839	5096
70°	3043	4619	2561	4619
75°	2548	4095	2183	4095
80°	2157	3487	2046	3487
85°	1825	2732	1825	2732



TEST NUMBER: P332914-840

CATALOG NUMBER: SA4XXRDIP-C575D1035U840-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.5	1.6
10°-20°	285.0	4.7
20°-30°	445.8	7.3
30°-40°	495.6	8.1
40°-50°	439.7	7.2
50°-60°	342.6	5.6
60°-70°	224.3	3.7
70°-80°	110.3	1.8
80°-90°	31.1	0.5
90°-100°	86.0	1.4
100°-110°	254.7	4.2
110°-120°	432.2	7.1
120°-130°	569.9	9.4
130°-140°	640.1	10.5
140°-150°	629.0	10.3
150°-160°	529.0	8.7
160°-170°	352.0	5.8
170°-180°	123.2	2.0
0°-30°	825.3	13.6
0°-40°	1320.9	21.7
0°-60°	2103.3	34.6
0°-90°	2469.0	40.6
90°-120°	772.9	12.7
90°-150°	2611.8	42.9
90°-180°	3616.0	59.4
0°-180°	6085.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	975	975	975	975	975	
5°	1127	974	861	974	1127	114
15°	1493	932	640	932	1493	425
25°	1610	852	504	852	1610	714
35°	992	740	422	740	992	622
45°	507	593	355	593	507	401
55°	303	425	265	425	303	275
65°	177	267	149	267	177	178
75°	82	131	70	131	82	90
85°	20	30	20	30	20	23
90°	30	3	30	3	30	16
95°	80	60	80	60	80	83
105°	246	235	246	235	246	259
115°	436	440	436	440	436	430
125°	635	640	635	640	635	566
135°	827	826	827	826	827	638
145°	1004	1003	1004	1003	1004	628
155°	1148	1149	1148	1149	1148	528
165°	1248	1251	1248	1251	1248	351
175°	1295	1301	1295	1301	1295	123
180°	1303	1303	1303	1303	1303	



TEST NUMBER: P332914-840

CATALOG NUMBER: SA4XXRDIP-C575D1035U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2
2.5°	1028.6	1031.5	1028.6	1028.3	1025.2	1024.3	1023.0	1019.0	1011.4	1006.9	1007.9
5°	1126.9	1136.7	1131.3	1130.4	1121.8	1113.2	1107.6	1095.1	1081.7	1072.7	1065.2
7.5°	1240.5	1246.2	1242.7	1237.2	1223.2	1215.3	1202.5	1186.0	1162.1	1143.7	1127.0
10°	1317.9	1322.5	1321.0	1310.8	1300.6	1279.7	1268.0	1244.8	1214.5	1190.5	1168.1
12.5°	1393.9	1399.0	1385.1	1385.6	1366.2	1349.8	1331.1	1302.0	1267.0	1236.1	1208.1
15°	1493.1	1486.8	1486.8	1478.9	1457.3	1434.5	1415.3	1384.6	1340.6	1303.7	1264.9
17.5°	1570.7	1573.0	1569.7	1551.2	1534.2	1510.7	1475.3	1439.6	1398.7	1349.1	1309.4
20°	1617.3	1617.3	1613.8	1601.1	1579.1	1554.0	1515.9	1477.0	1425.1	1375.2	1330.4
22.5°	1636.1	1637.4	1633.3	1622.9	1603.1	1578.5	1546.1	1506.5	1453.1	1396.9	1341.4
25°	1610.2	1617.6	1618.4	1615.7	1609.8	1594.9	1567.0	1526.5	1478.5	1417.6	1358.0
27.5°	1478.3	1487.7	1496.0	1509.5	1527.6	1537.1	1538.3	1517.7	1475.9	1417.3	1357.3
30°	1347.0	1354.7	1380.3	1413.7	1439.7	1463.2	1483.7	1489.1	1465.6	1412.9	1349.7
32.5°	1201.0	1211.7	1237.3	1273.2	1316.5	1356.3	1402.3	1425.6	1425.0	1393.4	1334.9
35°	991.7	999.6	1023.2	1060.9	1112.8	1172.0	1244.8	1301.3	1339.9	1337.1	1301.3
37.5°	799.8	808.7	832.5	863.8	914.1	987.5	1057.9	1135.9	1207.1	1247.1	1235.1
40°	695.5	695.9	719.0	751.2	798.4	862.4	939.1	1025.5	1104.9	1169.7	1182.2
42.5°	613.1	613.2	628.5	663.3	697.2	757.5	830.6	916.5	1009.4	1084.2	1117.5
45°	506.9	510.4	523.0	543.8	570.5	621.6	680.1	759.9	864.0	952.8	1008.2
47.5°	429.2	434.4	442.4	459.4	480.7	514.7	563.1	634.8	719.5	817.2	896.1
50°	389.0	389.8	400.0	409.4	427.9	455.0	497.5	557.1	635.0	728.8	816.5
52.5°	354.5	354.3	360.4	372.3	387.4	408.5	442.7	497.2	566.1	650.3	740.7
55°	302.6	304.5	309.2	318.6	330.0	345.0	372.1	412.9	467.2	539.1	621.2
57.5°	263.1	264.1	267.8	271.9	282.3	293.2	313.5	341.8	387.6	446.5	523.0
60°	237.3	237.7	238.9	244.8	253.1	263.3	277.0	300.9	339.5	393.3	453.8
62.5°	212.2	212.9	214.7	219.0	225.4	232.5	246.8	266.1	298.0	344.0	398.5
65°	176.8	177.2	180.0	181.6	186.6	192.9	203.5	216.5	238.5	277.0	318.3
67.5°	147.7	147.7	147.8	150.1	153.6	157.7	164.1	174.5	191.1	214.7	251.1
70°	128.9	128.9	129.7	130.9	132.8	136.3	139.9	147.7	160.0	179.2	207.0
72.5°	111.3	111.6	112.4	112.6	113.6	116.5	119.2	124.1	133.2	147.7	170.3
75°	81.7	82.9	84.8	86.4	88.4	88.1	90.8	93.9	96.6	105.3	118.3
77.5°	60.8	60.2	60.4	61.8	62.0	62.4	64.3	66.8	68.9	72.9	77.6
80°	46.4	46.4	47.6	48.0	47.6	48.0	49.9	51.1	51.9	53.4	57.8
82.5°	35.0	35.6	35.2	35.6	36.0	36.4	38.0	38.2	39.0	39.6	41.4
85°	19.7	20.0	20.4	19.7	19.7	19.7	20.4	20.8	21.6	21.2	22.0
87.5°	12.9	12.5	12.8	12.7	12.9	12.4	12.4	12.8	11.9	12.0	11.6
90°	30.2	29.8	29.4	28.9	28.5	27.6	26.3	24.8	23.5	22.2	20.4
92.5°	44.7	44.5	44.2	43.9	43.7	43.1	42.3	41.5	40.7	39.9	38.7
95°	79.7	79.7	79.7	79.7	79.7	79.3	78.7	78.0	77.3	76.6	75.0
97.5°	124.8	124.8	124.8	124.8	124.8	124.4	123.6	122.8	122.0	121.2	119.4
100°	156.2	156.2	156.2	156.2	156.2	156.0	155.5	155.1	154.7	154.2	152.2
102.5°	191.7	191.6	191.4	191.2	191.0	190.6	190.0	189.3	188.7	188.1	186.2
105°	245.9	245.3	244.6	243.9	243.3	242.6	242.0	241.3	240.5	239.9	239.0
107.5°	298.7	298.8	298.8	298.9	298.9	298.6	298.0	297.4	296.8	296.2	296.0
110°	336.7	336.0	335.3	334.7	334.0	333.9	334.3	334.8	335.2	335.7	335.9



TEST NUMBER: P332914-840

CATALOG NUMBER: SA4XXRDIP-C575D1035U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	375.4	375.3	375.1	375.0	374.9	374.9	374.9	375.0	375.1	375.2	375.6
115°	435.5	435.7	435.9	436.2	436.4	436.6	436.8	437.0	437.3	437.5	437.9
117.5°	492.7	493.1	493.6	494.0	494.5	495.1	495.8	496.7	497.4	498.2	498.5
120°	536.2	535.8	535.3	534.9	534.4	534.8	535.9	537.0	538.2	539.3	540.0
122.5°	572.5	573.3	574.1	574.9	575.7	576.5	577.3	578.0	578.9	579.6	579.9
125°	635.0	635.5	635.9	636.4	636.8	637.2	637.7	638.1	638.6	639.0	639.2
127.5°	692.9	693.3	693.6	694.0	694.3	694.7	695.2	695.6	696.1	696.5	696.9
130°	730.7	731.6	732.6	733.5	734.4	735.1	735.5	736.0	736.4	736.8	736.8
132.5°	771.1	771.4	771.8	772.1	772.5	773.0	773.4	773.9	774.3	774.8	774.9
135°	826.6	827.2	827.9	828.6	829.2	829.8	830.2	830.7	831.1	831.6	831.6
137.5°	884.8	884.6	884.5	884.4	884.2	884.5	885.0	885.7	886.3	886.9	886.5
140°	920.3	920.5	920.7	921.0	921.2	921.4	921.6	921.9	922.1	922.3	922.3
142.5°	955.7	955.8	955.8	955.9	955.9	956.0	956.0	956.0	956.1	956.1	956.3
145°	1003.9	1004.6	1005.3	1005.9	1006.6	1007.0	1007.3	1007.5	1007.7	1007.9	1007.7
147.5°	1052.8	1053.0	1053.2	1053.4	1053.6	1053.8	1054.0	1054.2	1054.4	1054.6	1054.7
150°	1082.6	1082.8	1083.0	1083.3	1083.5	1083.6	1083.6	1083.6	1083.6	1083.6	1083.6
152.5°	1109.9	1110.5	1111.2	1111.8	1112.4	1112.4	1111.8	1111.3	1110.8	1110.1	1110.0
155°	1148.1	1149.0	1149.9	1150.7	1151.7	1151.7	1150.7	1149.9	1149.0	1148.1	1148.3
157.5°	1182.1	1183.0	1183.7	1184.5	1185.2	1185.3	1184.6	1183.9	1183.3	1182.6	1182.7
160°	1201.5	1202.6	1203.8	1204.9	1206.0	1206.2	1205.6	1204.9	1204.2	1203.6	1203.8
162.5°	1221.6	1222.8	1224.0	1225.1	1226.2	1226.1	1224.9	1223.7	1222.4	1221.2	1221.5
165°	1247.9	1248.8	1249.7	1250.6	1251.4	1251.2	1249.9	1248.6	1247.2	1245.9	1246.3
167.5°	1266.7	1268.0	1269.4	1270.8	1272.2	1272.2	1270.9	1269.5	1268.2	1266.9	1266.8
170°	1277.1	1278.7	1280.2	1281.8	1283.3	1283.5	1282.1	1280.8	1279.5	1278.1	1277.9
172.5°	1286.0	1287.6	1289.1	1290.7	1292.2	1292.3	1290.7	1289.2	1287.7	1286.2	1286.2
175°	1295.3	1296.9	1298.4	1300.0	1301.5	1301.5	1300.0	1298.4	1296.9	1295.3	1295.5
177.5°	1300.1	1301.5	1302.9	1304.4	1305.9	1306.0	1304.6	1303.4	1302.1	1300.9	1300.9
180°	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3



TEST NUMBER: P332914-840

CATALOG NUMBER: SA4XXRDIP-C575D1035U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2
2.5°	1004.8	1000.4	998.2	993.1	987.1	984.0	981.2	977.1	971.8	966.1	962.0
5°	1055.8	1046.3	1034.5	1020.4	1007.8	995.6	985.0	974.4	962.3	949.7	937.2
7.5°	1108.1	1089.5	1069.5	1046.3	1023.8	1003.3	984.4	966.3	945.9	927.6	910.9
10°	1144.6	1119.4	1091.6	1062.1	1032.6	1007.0	981.9	959.1	933.9	911.6	892.7
12.5°	1174.2	1144.6	1111.1	1074.3	1038.8	1007.9	979.1	949.4	920.8	896.5	871.3
15°	1223.1	1182.7	1137.5	1093.5	1047.5	1005.5	966.5	932.0	899.4	865.3	841.2
17.5°	1256.9	1208.8	1154.0	1101.1	1046.7	997.1	952.3	911.1	873.4	838.6	810.0
20°	1277.0	1224.0	1163.1	1102.9	1042.0	989.0	940.7	895.0	856.2	818.5	789.0
22.5°	1288.3	1229.6	1163.1	1100.0	1037.0	979.6	926.6	879.1	836.7	799.0	766.4
25°	1291.9	1229.0	1161.0	1088.7	1019.7	958.8	903.7	852.2	805.1	767.4	732.8
27.5°	1286.9	1212.8	1143.3	1069.0	997.7	933.5	875.8	821.6	774.5	734.0	698.5
30°	1279.3	1200.0	1125.3	1048.3	976.0	914.3	853.4	801.5	752.5	710.4	674.7
32.5°	1263.0	1184.3	1104.0	1025.0	951.8	888.3	830.5	778.3	730.1	687.1	649.1
35°	1230.6	1150.8	1063.6	982.7	910.8	844.8	790.5	740.2	694.3	648.3	608.2
37.5°	1187.9	1106.5	1019.7	931.1	859.1	796.8	747.0	699.8	654.9	613.0	568.6
40°	1147.7	1073.5	983.9	895.9	822.0	761.8	715.9	673.1	627.9	586.2	541.8
42.5°	1099.0	1035.7	945.2	856.9	784.0	726.0	683.2	641.4	600.3	559.9	513.5
45°	1017.6	969.8	884.8	800.0	726.5	669.1	629.9	592.9	556.7	518.3	474.6
47.5°	924.4	892.0	818.8	731.8	663.9	612.3	574.3	544.1	513.5	475.0	436.8
50°	859.7	838.9	768.2	688.8	624.0	576.4	537.6	509.2	483.7	446.8	412.5
52.5°	790.5	779.5	719.7	643.8	581.2	534.6	501.4	475.9	450.1	419.4	387.4
55°	685.3	691.2	640.5	574.8	515.9	476.7	446.4	425.2	403.1	377.2	352.4
57.5°	577.5	599.2	565.1	507.5	452.2	416.0	393.1	375.3	356.9	335.3	314.2
60°	513.1	531.2	512.0	461.3	412.9	379.2	358.0	344.2	325.7	306.1	289.9
62.5°	450.3	469.6	458.2	417.3	372.4	343.4	324.7	311.8	298.1	280.9	264.2
65°	371.3	383.8	378.4	350.1	318.3	293.5	276.2	266.8	254.2	241.7	226.7
67.5°	284.4	308.7	305.5	290.4	263.0	243.6	232.3	224.0	212.5	203.2	193.0
70°	233.8	256.2	255.8	243.6	228.6	210.6	202.8	195.7	185.4	176.4	168.1
72.5°	191.4	211.9	214.9	205.6	195.4	181.7	174.1	169.3	159.4	153.2	146.4
75°	134.0	149.0	152.9	152.9	148.1	141.1	134.4	131.3	124.1	118.7	114.7
77.5°	87.9	97.3	103.4	104.8	105.5	103.2	97.7	95.4	90.1	88.1	84.3
80°	62.1	68.4	75.4	77.8	79.8	79.0	76.6	75.0	70.0	68.0	66.4
82.5°	42.9	46.4	52.2	57.4	56.9	58.9	56.9	55.5	51.7	51.0	49.4
85°	22.4	22.8	23.5	27.1	29.1	29.9	30.3	29.5	28.3	28.3	25.5
87.5°	11.3	10.6	10.9	10.4	10.3	11.0	11.5	11.3	10.8	10.4	9.9
90°	18.6	16.8	15.0	12.9	10.4	8.0	5.5	3.0	5.5	8.0	10.4
92.5°	37.4	36.2	34.9	32.8	30.0	27.2	24.4	21.6	24.4	27.2	30.0
95°	73.5	71.9	70.3	68.6	66.6	64.5	62.5	60.5	62.5	64.5	66.6
97.5°	117.4	115.6	113.8	112.1	110.5	108.9	107.2	105.6	107.2	108.9	110.5
100°	150.2	148.1	146.1	144.7	143.8	142.9	142.0	141.1	142.0	142.9	143.8
102.5°	184.4	182.6	180.8	179.7	179.3	178.9	178.5	178.2	178.5	178.9	179.3
105°	238.1	237.2	236.3	235.8	235.5	235.3	235.1	234.9	235.1	235.3	235.5
107.5°	295.9	295.8	295.6	295.4	295.2	294.9	294.6	294.4	294.6	294.9	295.2
110°	336.1	336.3	336.6	336.5	336.0	335.6	335.1	334.7	335.1	335.6	336.0



TEST NUMBER: P332914-840

CATALOG NUMBER: SA4XXRDIP-C575D1035U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	376.0	376.4	376.8	377.0	376.9	376.8	376.7	376.6	376.7	376.8	376.9
115°	438.4	438.8	439.3	439.5	439.5	439.5	439.5	439.5	439.5	439.5	439.5
117.5°	498.8	499.1	499.4	499.5	499.3	499.1	499.0	498.8	499.0	499.1	499.3
120°	540.6	541.3	542.0	541.9	541.0	540.1	539.2	538.3	539.2	540.1	541.0
122.5°	580.2	580.6	580.9	580.8	580.5	580.1	579.8	579.4	579.8	580.1	580.5
125°	639.5	639.7	640.0	640.1	640.1	640.1	640.1	640.1	640.1	640.1	640.1
127.5°	697.2	697.6	697.9	697.8	697.1	696.4	695.8	695.1	695.8	696.4	697.1
130°	736.8	736.8	736.8	736.5	735.8	735.2	734.5	733.8	734.5	735.2	735.8
132.5°	775.1	775.3	775.5	775.3	774.8	774.3	773.9	773.4	773.9	774.3	774.8
135°	831.6	831.6	831.6	830.9	829.6	828.2	826.9	825.6	826.9	828.2	829.6
137.5°	886.2	885.8	885.3	884.9	884.2	883.6	883.0	882.4	883.0	883.6	884.2
140°	922.3	922.3	922.3	922.1	921.6	921.2	920.7	920.3	920.7	921.2	921.6
142.5°	956.5	956.7	956.8	956.7	956.3	955.8	955.4	954.9	955.4	955.8	956.3
145°	1007.5	1007.3	1007.0	1006.5	1005.6	1004.7	1003.8	1002.9	1003.8	1004.7	1005.6
147.5°	1054.9	1055.1	1055.3	1054.8	1053.8	1052.7	1051.6	1050.6	1051.6	1052.7	1053.8
150°	1083.6	1083.6	1083.6	1083.2	1082.3	1081.4	1080.5	1079.5	1080.5	1081.4	1082.3
152.5°	1109.8	1109.6	1109.4	1109.1	1108.6	1108.0	1107.5	1107.0	1107.5	1108.0	1108.6
155°	1148.5	1148.7	1149.0	1149.1	1149.1	1149.1	1149.1	1149.1	1149.1	1149.1	1149.1
157.5°	1182.7	1182.7	1182.8	1183.0	1183.4	1183.8	1184.2	1184.6	1184.2	1183.8	1183.4
160°	1204.0	1204.2	1204.5	1204.7	1204.9	1205.1	1205.3	1205.6	1205.3	1205.1	1204.9
162.5°	1221.7	1221.9	1222.1	1222.5	1223.1	1223.8	1224.4	1224.9	1224.4	1223.8	1223.1
165°	1246.8	1247.2	1247.7	1248.2	1248.9	1249.6	1250.2	1250.9	1250.2	1249.6	1248.9
167.5°	1266.8	1266.7	1266.7	1267.1	1268.1	1269.0	1269.9	1270.9	1269.9	1269.0	1268.1
170°	1277.7	1277.5	1277.2	1277.7	1278.8	1279.9	1281.0	1282.1	1281.0	1279.9	1278.8
172.5°	1286.1	1286.1	1286.0	1286.5	1287.4	1288.4	1289.3	1290.2	1289.3	1288.4	1287.4
175°	1295.7	1296.0	1296.2	1296.9	1298.0	1299.1	1300.2	1301.3	1300.2	1299.1	1298.0
177.5°	1300.9	1300.9	1300.9	1301.3	1302.2	1303.1	1304.0	1304.9	1304.0	1303.1	1302.2
180°	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3



TEST NUMBER: P332914-840

CATALOG NUMBER: SA4XXRDIP-C575D1035U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2
2.5°	957.7	954.5	950.4	945.6	940.0	935.0	932.8	934.6	935.6	933.1	932.8
5°	928.5	918.7	910.8	899.0	889.6	881.7	876.2	873.8	874.6	868.4	866.8
7.5°	895.6	884.0	871.2	857.2	844.1	832.6	826.6	823.2	816.6	813.7	808.9
10°	874.6	858.9	846.4	829.8	815.0	801.1	794.5	789.0	782.3	779.1	772.4
12.5°	852.9	834.8	820.9	803.8	788.5	771.9	765.6	755.4	744.9	738.3	729.7
15°	822.3	800.4	783.5	763.1	745.0	726.1	709.2	690.3	683.3	668.3	659.7
17.5°	786.6	764.3	743.4	716.0	688.1	664.7	646.6	628.6	617.7	608.2	603.8
20°	763.1	742.7	713.6	681.8	650.7	624.7	610.2	598.4	586.6	580.0	575.2
22.5°	740.7	714.7	680.9	646.5	615.5	595.2	582.9	570.8	561.2	554.8	548.6
25°	703.4	669.1	633.4	594.1	572.9	555.2	541.8	532.0	526.1	517.9	514.7
27.5°	664.9	623.5	584.0	557.6	535.5	519.4	507.8	500.4	492.9	487.6	483.5
30°	635.3	593.3	558.0	532.8	510.4	497.1	487.6	479.0	473.1	468.8	465.6
32.5°	606.1	564.1	534.3	507.4	489.7	476.7	466.6	460.1	455.4	449.9	448.0
35°	563.8	526.5	500.6	476.3	458.2	446.4	438.5	431.8	427.9	426.4	425.2
37.5°	523.2	492.6	464.7	444.7	428.7	419.4	410.1	406.9	404.1	401.3	402.6
40°	497.5	468.8	444.0	422.8	409.8	399.6	394.0	390.2	387.8	387.8	387.8
42.5°	475.1	447.1	422.9	403.9	390.9	382.3	376.2	372.8	372.1	371.7	373.7
45°	440.5	414.5	390.2	374.5	363.5	354.8	351.2	348.5	348.5	350.1	350.5
47.5°	406.2	381.8	362.2	344.7	334.6	329.2	326.1	324.7	324.9	326.4	328.2
50°	385.1	361.1	341.8	326.1	316.7	311.5	308.8	308.0	308.8	308.8	311.5
52.5°	362.1	340.6	321.7	308.5	297.8	293.1	291.5	290.4	290.9	292.2	293.4
55°	328.5	309.2	291.1	278.6	270.7	267.6	264.1	264.5	263.7	264.5	264.5
57.5°	294.8	277.5	260.6	250.6	243.8	239.2	235.4	236.4	235.3	235.1	234.5
60°	273.1	254.2	240.9	231.9	224.0	220.0	216.5	217.3	216.1	215.3	213.8
62.5°	249.5	233.8	221.1	212.4	206.0	201.5	197.9	197.1	194.4	191.8	188.2
65°	215.3	202.4	191.0	182.7	176.8	173.3	170.6	168.1	162.3	156.0	152.9
67.5°	182.1	172.7	162.1	155.1	150.4	145.7	140.5	136.4	130.9	127.4	125.5
70°	160.7	151.7	142.6	135.9	130.9	126.5	120.6	117.9	113.9	112.4	110.4
72.5°	140.3	131.9	123.4	117.4	112.0	108.6	104.0	101.2	99.5	98.9	96.8
75°	109.3	102.6	96.2	90.8	86.4	84.1	82.1	80.2	79.4	75.8	73.8
77.5°	79.7	75.2	71.4	67.5	64.3	62.8	59.0	56.8	55.4	53.7	53.3
80°	62.1	59.0	55.0	52.6	48.4	46.8	45.1	44.8	44.4	44.0	43.6
82.5°	46.7	43.5	39.6	38.2	37.1	36.1	35.1	34.7	34.3	34.5	34.5
85°	23.5	22.0	22.0	21.6	21.2	20.8	20.4	20.4	20.0	20.4	20.0
87.5°	10.4	10.5	10.9	10.6	11.3	11.7	11.6	11.9	12.4	12.1	12.3
90°	12.9	15.0	16.8	18.6	20.4	22.2	23.5	24.8	26.3	27.6	28.5
92.5°	32.8	34.9	36.2	37.4	38.7	39.9	40.7	41.5	42.3	43.1	43.7
95°	68.6	70.3	71.9	73.5	75.0	76.6	77.3	78.0	78.7	79.3	79.7
97.5°	112.1	113.8	115.6	117.4	119.4	121.2	122.0	122.8	123.6	124.4	124.8
100°	144.7	146.1	148.1	150.2	152.2	154.2	154.7	155.1	155.5	156.0	156.2
102.5°	179.7	180.8	182.6	184.4	186.2	188.1	188.7	189.3	190.0	190.6	191.0
105°	235.8	236.3	237.2	238.1	239.0	239.9	240.5	241.3	242.0	242.6	243.3
107.5°	295.4	295.6	295.8	295.9	296.0	296.2	296.8	297.4	298.0	298.6	298.9
110°	336.5	336.6	336.3	336.1	335.9	335.7	335.2	334.8	334.3	333.9	334.0



TEST NUMBER: P332914-840

CATALOG NUMBER: SA4XXRDIP-C575D1035U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	377.0	376.8	376.4	376.0	375.6	375.2	375.1	375.0	374.9	374.9	374.9
115°	439.5	439.3	438.8	438.4	437.9	437.5	437.3	437.0	436.8	436.6	436.4
117.5°	499.5	499.4	499.1	498.8	498.5	498.2	497.4	496.7	495.8	495.1	494.5
120°	541.9	542.0	541.3	540.6	540.0	539.3	538.2	537.0	535.9	534.8	534.4
122.5°	580.8	580.9	580.6	580.2	579.9	579.6	578.9	578.0	577.3	576.5	575.7
125°	640.1	640.0	639.7	639.5	639.2	639.0	638.6	638.1	637.7	637.2	636.8
127.5°	697.8	697.9	697.6	697.2	696.9	696.5	696.1	695.6	695.2	694.7	694.3
130°	736.5	736.8	736.8	736.8	736.8	736.8	736.4	736.0	735.5	735.1	734.4
132.5°	775.3	775.5	775.3	775.1	774.9	774.8	774.3	773.9	773.4	773.0	772.5
135°	830.9	831.6	831.6	831.6	831.6	831.6	831.1	830.7	830.2	829.8	829.2
137.5°	884.9	885.3	885.8	886.2	886.5	886.9	886.3	885.7	885.0	884.5	884.2
140°	922.1	922.3	922.3	922.3	922.3	922.3	922.1	921.9	921.6	921.4	921.2
142.5°	956.7	956.8	956.7	956.5	956.3	956.1	956.1	956.0	956.0	956.0	955.9
145°	1006.5	1007.0	1007.3	1007.5	1007.7	1007.9	1007.7	1007.5	1007.3	1007.0	1006.6
147.5°	1054.8	1055.3	1055.1	1054.9	1054.7	1054.6	1054.4	1054.2	1054.0	1053.8	1053.6
150°	1083.2	1083.6	1083.6	1083.6	1083.6	1083.6	1083.6	1083.6	1083.6	1083.6	1083.5
152.5°	1109.1	1109.4	1109.6	1109.8	1110.0	1110.1	1110.8	1111.3	1111.8	1112.4	1112.4
155°	1149.1	1149.0	1148.7	1148.5	1148.3	1148.1	1149.0	1149.9	1150.7	1151.7	1151.7
157.5°	1183.0	1182.8	1182.7	1182.7	1182.7	1182.6	1183.3	1183.9	1184.6	1185.3	1185.2
160°	1204.7	1204.5	1204.2	1204.0	1203.8	1203.6	1204.2	1204.9	1205.6	1206.2	1206.0
162.5°	1222.5	1222.1	1221.9	1221.7	1221.5	1221.2	1222.4	1223.7	1224.9	1226.1	1226.2
165°	1248.2	1247.7	1247.2	1246.8	1246.3	1245.9	1247.2	1248.6	1249.9	1251.2	1251.4
167.5°	1267.1	1266.7	1266.7	1266.8	1266.8	1266.9	1268.2	1269.5	1270.9	1272.2	1272.2
170°	1277.7	1277.2	1277.5	1277.7	1277.9	1278.1	1279.5	1280.8	1282.1	1283.5	1283.3
172.5°	1286.5	1286.0	1286.1	1286.1	1286.2	1286.2	1287.7	1289.2	1290.7	1292.3	1292.2
175°	1296.9	1296.2	1296.0	1295.7	1295.5	1295.3	1296.9	1298.4	1300.0	1301.5	1301.5
177.5°	1301.3	1300.9	1300.9	1300.9	1300.9	1300.9	1302.1	1303.4	1304.6	1306.0	1305.9
180°	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3



TEST NUMBER: P332914-840

CATALOG NUMBER: SA4XXRDIP-C575D1035U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2
2.5°	930.9	931.5	929.4	928.7	929.4	931.5	930.9	932.8	933.1	935.6	934.6
5°	863.6	862.8	860.9	861.3	860.9	862.8	863.6	866.8	868.4	874.6	873.8
7.5°	806.1	803.0	804.0	800.7	804.0	803.0	806.1	808.9	813.7	816.6	823.2
10°	770.9	766.6	763.1	759.9	763.1	766.6	770.9	772.4	779.1	782.3	789.0
12.5°	722.9	719.1	714.3	715.3	714.3	719.1	722.9	729.7	738.3	744.9	755.4
15°	654.6	648.7	639.2	640.5	639.2	648.7	654.6	659.7	668.3	683.3	690.3
17.5°	596.8	596.9	592.6	593.6	592.6	596.9	596.8	603.8	608.2	617.7	628.6
20°	566.9	564.2	564.6	563.4	564.6	564.2	566.9	575.2	580.0	586.6	598.4
22.5°	546.2	542.9	540.1	537.7	540.1	542.9	546.2	548.6	554.8	561.2	570.8
25°	511.2	508.9	505.3	504.5	505.3	508.9	511.2	514.7	517.9	526.1	532.0
27.5°	480.4	479.9	478.5	476.7	478.5	479.9	480.4	483.5	487.6	492.9	500.4
30°	462.4	461.7	460.9	459.7	460.9	461.7	462.4	465.6	468.8	473.1	479.0
32.5°	446.5	446.0	445.1	445.2	445.1	446.0	446.5	448.0	449.9	455.4	460.1
35°	423.5	423.1	422.4	422.0	422.4	423.1	423.5	425.2	426.4	427.9	431.8
37.5°	402.2	403.2	402.7	402.6	402.7	403.2	402.2	402.6	401.3	404.1	406.9
40°	387.4	387.8	388.6	388.2	388.6	387.8	387.4	387.8	387.8	387.8	390.2
42.5°	375.2	375.3	376.4	375.0	376.4	375.3	375.2	373.7	371.7	372.1	372.8
45°	353.3	355.6	355.2	355.2	355.2	355.6	353.3	350.5	350.1	348.5	348.5
47.5°	329.2	331.3	331.8	331.7	331.8	331.3	329.2	328.2	326.4	324.9	324.7
50°	313.6	312.8	314.0	313.6	314.0	312.8	313.6	311.5	308.8	308.8	308.0
52.5°	294.4	294.6	294.5	294.1	294.5	294.6	294.4	293.4	292.2	290.9	290.4
55°	264.8	265.2	264.5	264.8	264.5	265.2	264.8	264.5	264.5	263.7	264.5
57.5°	232.8	230.9	231.7	230.8	231.7	230.9	232.8	234.5	235.1	235.3	236.4
60°	209.8	206.7	205.9	204.3	205.9	206.7	209.8	213.8	215.3	216.1	217.3
62.5°	184.0	181.9	179.2	180.5	179.2	181.9	184.0	188.2	191.8	194.4	197.1
65°	149.7	148.1	146.9	148.6	146.9	148.1	149.7	152.9	156.0	162.3	168.1
67.5°	123.9	123.1	123.1	122.3	123.1	123.1	123.9	125.5	127.4	130.9	136.4
70°	110.4	109.3	109.3	108.5	109.3	109.3	110.4	110.4	112.4	113.9	117.9
72.5°	96.5	95.4	95.7	95.2	95.7	95.4	96.5	96.8	98.9	99.5	101.2
75°	71.5	69.6	69.6	70.0	69.6	69.6	71.5	73.8	75.8	79.4	80.2
77.5°	53.3	52.9	53.5	52.8	53.5	52.9	53.3	53.3	53.7	55.4	56.8
80°	43.6	43.2	42.8	44.0	42.8	43.2	43.6	43.6	44.0	44.4	44.8
82.5°	33.8	33.8	33.7	35.2	33.7	33.8	33.8	34.5	34.5	34.3	34.7
85°	20.4	19.7	20.4	19.7	20.4	19.7	20.4	20.0	20.4	20.0	20.4
87.5°	13.0	12.8	12.5	12.9	12.5	12.8	13.0	12.3	12.1	12.4	11.9
90°	28.9	29.4	29.8	30.2	29.8	29.4	28.9	28.5	27.6	26.3	24.8
92.5°	43.9	44.2	44.5	44.7	44.5	44.2	43.9	43.7	43.1	42.3	41.5
95°	79.7	79.7	79.7	79.7	79.7	79.7	79.7	79.7	79.3	78.7	78.0
97.5°	124.8	124.8	124.8	124.8	124.8	124.8	124.8	124.8	124.4	123.6	122.8
100°	156.2	156.2	156.2	156.2	156.2	156.2	156.2	156.2	156.0	155.5	155.1
102.5°	191.2	191.4	191.6	191.7	191.6	191.4	191.2	191.0	190.6	190.0	189.3
105°	243.9	244.6	245.3	245.9	245.3	244.6	243.9	243.3	242.6	242.0	241.3
107.5°	298.9	298.8	298.8	298.7	298.8	298.8	298.9	298.9	298.6	298.0	297.4
110°	334.7	335.3	336.0	336.7	336.0	335.3	334.7	334.0	333.9	334.3	334.8



TEST NUMBER: P332914-840

CATALOG NUMBER: SA4XXRDIP-C575D1035U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	375.0	375.1	375.3	375.4	375.3	375.1	375.0	374.9	374.9	374.9	375.0
115°	436.2	435.9	435.7	435.5	435.7	435.9	436.2	436.4	436.6	436.8	437.0
117.5°	494.0	493.6	493.1	492.7	493.1	493.6	494.0	494.5	495.1	495.8	496.7
120°	534.9	535.3	535.8	536.2	535.8	535.3	534.9	534.4	534.8	535.9	537.0
122.5°	574.9	574.1	573.3	572.5	573.3	574.1	574.9	575.7	576.5	577.3	578.0
125°	636.4	635.9	635.5	635.0	635.5	635.9	636.4	636.8	637.2	637.7	638.1
127.5°	694.0	693.6	693.3	692.9	693.3	693.6	694.0	694.3	694.7	695.2	695.6
130°	733.5	732.6	731.6	730.7	731.6	732.6	733.5	734.4	735.1	735.5	736.0
132.5°	772.1	771.8	771.4	771.1	771.4	771.8	772.1	772.5	773.0	773.4	773.9
135°	828.6	827.9	827.2	826.6	827.2	827.9	828.6	829.2	829.8	830.2	830.7
137.5°	884.4	884.5	884.6	884.8	884.6	884.5	884.4	884.2	884.5	885.0	885.7
140°	921.0	920.7	920.5	920.3	920.5	920.7	921.0	921.2	921.4	921.6	921.9
142.5°	955.9	955.8	955.8	955.7	955.8	955.8	955.9	955.9	956.0	956.0	956.0
145°	1005.9	1005.3	1004.6	1003.9	1004.6	1005.3	1005.9	1006.6	1007.0	1007.3	1007.5
147.5°	1053.4	1053.2	1053.0	1052.8	1053.0	1053.2	1053.4	1053.6	1053.8	1054.0	1054.2
150°	1083.3	1083.0	1082.8	1082.6	1082.8	1083.0	1083.3	1083.5	1083.6	1083.6	1083.6
152.5°	1111.8	1111.2	1110.5	1109.9	1110.5	1111.2	1111.8	1112.4	1112.4	1111.8	1111.3
155°	1150.7	1149.9	1149.0	1148.1	1149.0	1149.9	1150.7	1151.7	1151.7	1150.7	1149.9
157.5°	1184.5	1183.7	1183.0	1182.1	1183.0	1183.7	1184.5	1185.2	1185.3	1184.6	1183.9
160°	1204.9	1203.8	1202.6	1201.5	1202.6	1203.8	1204.9	1206.0	1206.2	1205.6	1204.9
162.5°	1225.1	1224.0	1222.8	1221.6	1222.8	1224.0	1225.1	1226.2	1226.1	1224.9	1223.7
165°	1250.6	1249.7	1248.8	1247.9	1248.8	1249.7	1250.6	1251.4	1251.2	1249.9	1248.6
167.5°	1270.8	1269.4	1268.0	1266.7	1268.0	1269.4	1270.8	1272.2	1272.2	1270.9	1269.5
170°	1281.8	1280.2	1278.7	1277.1	1278.7	1280.2	1281.8	1283.3	1283.5	1282.1	1280.8
172.5°	1290.7	1289.1	1287.6	1286.0	1287.6	1289.1	1290.7	1292.2	1292.3	1290.7	1289.2
175°	1300.0	1298.4	1296.9	1295.3	1296.9	1298.4	1300.0	1301.5	1301.5	1300.0	1298.4
177.5°	1304.4	1302.9	1301.5	1300.1	1301.5	1302.9	1304.4	1305.9	1306.0	1304.6	1303.4
180°	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3



TEST NUMBER: P332914-840

CATALOG NUMBER: SA4XXRDIP-C575D1035U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2
2.5°	932.8	935.0	940.0	945.6	950.4	954.5	957.7	962.0	966.1	971.8	977.1
5°	876.2	881.7	889.6	899.0	910.8	918.7	928.5	937.2	949.7	962.3	974.4
7.5°	826.6	832.6	844.1	857.2	871.2	884.0	895.6	910.9	927.6	945.9	966.3
10°	794.5	801.1	815.0	829.8	846.4	858.9	874.6	892.7	911.6	933.9	959.1
12.5°	765.6	771.9	788.5	803.8	820.9	834.8	852.9	871.3	896.5	920.8	949.4
15°	709.2	726.1	745.0	763.1	783.5	800.4	822.3	841.2	865.3	899.4	932.0
17.5°	646.6	664.7	688.1	716.0	743.4	764.3	786.6	810.0	838.6	873.4	911.1
20°	610.2	624.7	650.7	681.8	713.6	742.7	763.1	789.0	818.5	856.2	895.0
22.5°	582.9	595.2	615.5	646.5	680.9	714.7	740.7	766.4	799.0	836.7	879.1
25°	541.8	555.2	572.9	594.1	633.4	669.1	703.4	732.8	767.4	805.1	852.2
27.5°	507.8	519.4	535.5	557.6	584.0	623.5	664.9	698.5	734.0	774.5	821.6
30°	487.6	497.1	510.4	532.8	558.0	593.3	635.3	674.7	710.4	752.5	801.5
32.5°	466.6	476.7	489.7	507.4	534.3	564.1	606.1	649.1	687.1	730.1	778.3
35°	438.5	446.4	458.2	476.3	500.6	526.5	563.8	608.2	648.3	694.3	740.2
37.5°	410.1	419.4	428.7	444.7	464.7	492.6	523.2	568.6	613.0	654.9	699.8
40°	394.0	399.6	409.8	422.8	444.0	468.8	497.5	541.8	586.2	627.9	673.1
42.5°	376.2	382.3	390.9	403.9	422.9	447.1	475.1	513.5	559.9	600.3	641.4
45°	351.2	354.8	363.5	374.5	390.2	414.5	440.5	474.6	518.3	556.7	592.9
47.5°	326.1	329.2	334.6	344.7	362.2	381.8	406.2	436.8	475.0	513.5	544.1
50°	308.8	311.5	316.7	326.1	341.8	361.1	385.1	412.5	446.8	483.7	509.2
52.5°	291.5	293.1	297.8	308.5	321.7	340.6	362.1	387.4	419.4	450.1	475.9
55°	264.1	267.6	270.7	278.6	291.1	309.2	328.5	352.4	377.2	403.1	425.2
57.5°	235.4	239.2	243.8	250.6	260.6	277.5	294.8	314.2	335.3	356.9	375.3
60°	216.5	220.0	224.0	231.9	240.9	254.2	273.1	289.9	306.1	325.7	344.2
62.5°	197.9	201.5	206.0	212.4	221.1	233.8	249.5	264.2	280.9	298.1	311.8
65°	170.6	173.3	176.8	182.7	191.0	202.4	215.3	226.7	241.7	254.2	266.8
67.5°	140.5	145.7	150.4	155.1	162.1	172.7	182.1	193.0	203.2	212.5	224.0
70°	120.6	126.5	130.9	135.9	142.6	151.7	160.7	168.1	176.4	185.4	195.7
72.5°	104.0	108.6	112.0	117.4	123.4	131.9	140.3	146.4	153.2	159.4	169.3
75°	82.1	84.1	86.4	90.8	96.2	102.6	109.3	114.7	118.7	124.1	131.3
77.5°	59.0	62.8	64.3	67.5	71.4	75.2	79.7	84.3	88.1	90.1	95.4
80°	45.1	46.8	48.4	52.6	55.0	59.0	62.1	66.4	68.0	70.0	75.0
82.5°	35.1	36.1	37.1	38.2	39.6	43.5	46.7	49.4	51.0	51.7	55.5
85°	20.4	20.8	21.2	21.6	22.0	22.0	23.5	25.5	28.3	28.3	29.5
87.5°	11.6	11.7	11.3	10.6	10.9	10.5	10.4	9.9	10.4	10.8	11.3
90°	23.5	22.2	20.4	18.6	16.8	15.0	12.9	10.4	8.0	5.5	3.0
92.5°	40.7	39.9	38.7	37.4	36.2	34.9	32.8	30.0	27.2	24.4	21.6
95°	77.3	76.6	75.0	73.5	71.9	70.3	68.6	66.6	64.5	62.5	60.5
97.5°	122.0	121.2	119.4	117.4	115.6	113.8	112.1	110.5	108.9	107.2	105.6
100°	154.7	154.2	152.2	150.2	148.1	146.1	144.7	143.8	142.9	142.0	141.1
102.5°	188.7	188.1	186.2	184.4	182.6	180.8	179.7	179.3	178.9	178.5	178.2
105°	240.5	239.9	239.0	238.1	237.2	236.3	235.8	235.5	235.3	235.1	234.9
107.5°	296.8	296.2	296.0	295.9	295.8	295.6	295.4	295.2	294.9	294.6	294.4
110°	335.2	335.7	335.9	336.1	336.3	336.6	336.5	336.0	335.6	335.1	334.7



TEST NUMBER: P332914-840

CATALOG NUMBER: SA4XXRDIP-C575D1035U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	375.1	375.2	375.6	376.0	376.4	376.8	377.0	376.9	376.8	376.7	376.6
115°	437.3	437.5	437.9	438.4	438.8	439.3	439.5	439.5	439.5	439.5	439.5
117.5°	497.4	498.2	498.5	498.8	499.1	499.4	499.5	499.3	499.1	499.0	498.8
120°	538.2	539.3	540.0	540.6	541.3	542.0	541.9	541.0	540.1	539.2	538.3
122.5°	578.9	579.6	579.9	580.2	580.6	580.9	580.8	580.5	580.1	579.8	579.4
125°	638.6	639.0	639.2	639.5	639.7	640.0	640.1	640.1	640.1	640.1	640.1
127.5°	696.1	696.5	696.9	697.2	697.6	697.9	697.8	697.1	696.4	695.8	695.1
130°	736.4	736.8	736.8	736.8	736.8	736.8	736.5	735.8	735.2	734.5	733.8
132.5°	774.3	774.8	774.9	775.1	775.3	775.5	775.3	774.8	774.3	773.9	773.4
135°	831.1	831.6	831.6	831.6	831.6	831.6	830.9	829.6	828.2	826.9	825.6
137.5°	886.3	886.9	886.5	886.2	885.8	885.3	884.9	884.2	883.6	883.0	882.4
140°	922.1	922.3	922.3	922.3	922.3	922.3	922.1	921.6	921.2	920.7	920.3
142.5°	956.1	956.1	956.3	956.5	956.7	956.8	956.7	956.3	955.8	955.4	954.9
145°	1007.7	1007.9	1007.7	1007.5	1007.3	1007.0	1006.5	1005.6	1004.7	1003.8	1002.9
147.5°	1054.4	1054.6	1054.7	1054.9	1055.1	1055.3	1054.8	1053.8	1052.7	1051.6	1050.6
150°	1083.6	1083.6	1083.6	1083.6	1083.6	1083.6	1083.2	1082.3	1081.4	1080.5	1079.5
152.5°	1110.8	1110.1	1110.0	1109.8	1109.6	1109.4	1109.1	1108.6	1108.0	1107.5	1107.0
155°	1149.0	1148.1	1148.3	1148.5	1148.7	1149.0	1149.1	1149.1	1149.1	1149.1	1149.1
157.5°	1183.3	1182.6	1182.7	1182.7	1182.7	1182.8	1183.0	1183.4	1183.8	1184.2	1184.6
160°	1204.2	1203.6	1203.8	1204.0	1204.2	1204.5	1204.7	1204.9	1205.1	1205.3	1205.6
162.5°	1222.4	1221.2	1221.5	1221.7	1221.9	1222.1	1222.5	1223.1	1223.8	1224.4	1224.9
165°	1247.2	1245.9	1246.3	1246.8	1247.2	1247.7	1248.2	1248.9	1249.6	1250.2	1250.9
167.5°	1268.2	1266.9	1266.8	1266.8	1266.7	1266.7	1267.1	1268.1	1269.0	1269.9	1270.9
170°	1279.5	1278.1	1277.9	1277.7	1277.5	1277.2	1277.7	1278.8	1279.9	1281.0	1282.1
172.5°	1287.7	1286.2	1286.2	1286.1	1286.1	1286.0	1286.5	1287.4	1288.4	1289.3	1290.2
175°	1296.9	1295.3	1295.5	1295.7	1296.0	1296.2	1296.9	1298.0	1299.1	1300.2	1301.3
177.5°	1302.1	1300.9	1300.9	1300.9	1300.9	1300.9	1301.3	1302.2	1303.1	1304.0	1304.9
180°	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3



TEST NUMBER: P332914-840

CATALOG NUMBER: SA4XXRDIP-C575D1035U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2
2.5°	981.2	984.0	987.1	993.1	998.2	1000.4	1004.8	1007.9	1006.9	1011.4	1019.0
5°	985.0	995.6	1007.8	1020.4	1034.5	1046.3	1055.8	1065.2	1072.7	1081.7	1095.1
7.5°	984.4	1003.3	1023.8	1046.3	1069.5	1089.5	1108.1	1127.0	1143.7	1162.1	1186.0
10°	981.9	1007.0	1032.6	1062.1	1091.6	1119.4	1144.6	1168.1	1190.5	1214.5	1244.8
12.5°	979.1	1007.9	1038.8	1074.3	1111.1	1144.6	1174.2	1208.1	1236.1	1267.0	1302.0
15°	966.5	1005.5	1047.5	1093.5	1137.5	1182.7	1223.1	1264.9	1303.7	1340.6	1384.6
17.5°	952.3	997.1	1046.7	1101.1	1154.0	1208.8	1256.9	1309.4	1349.1	1398.7	1439.6
20°	940.7	989.0	1042.0	1102.9	1163.1	1224.0	1277.0	1330.4	1375.2	1425.1	1477.0
22.5°	926.6	979.6	1037.0	1100.0	1163.1	1229.6	1288.3	1341.4	1396.9	1453.1	1506.5
25°	903.7	958.8	1019.7	1088.7	1161.0	1229.0	1291.9	1358.0	1417.6	1478.5	1526.5
27.5°	875.8	933.5	997.7	1069.0	1143.3	1212.8	1286.9	1357.3	1417.3	1475.9	1517.7
30°	853.4	914.3	976.0	1048.3	1125.3	1200.0	1279.3	1349.7	1412.9	1465.6	1489.1
32.5°	830.5	888.3	951.8	1025.0	1104.0	1184.3	1263.0	1334.9	1393.4	1425.0	1425.6
35°	790.5	844.8	910.8	982.7	1063.6	1150.8	1230.6	1301.3	1337.1	1339.9	1301.3
37.5°	747.0	796.8	859.1	931.1	1019.7	1106.5	1187.9	1235.1	1247.1	1207.1	1135.9
40°	715.9	761.8	822.0	895.9	983.9	1073.5	1147.7	1182.2	1169.7	1104.9	1025.5
42.5°	683.2	726.0	784.0	856.9	945.2	1035.7	1099.0	1117.5	1084.2	1009.4	916.5
45°	629.9	669.1	726.5	800.0	884.8	969.8	1017.6	1008.2	952.8	864.0	759.9
47.5°	574.3	612.3	663.9	731.8	818.8	892.0	924.4	896.1	817.2	719.5	634.8
50°	537.6	576.4	624.0	688.8	768.2	838.9	859.7	816.5	728.8	635.0	557.1
52.5°	501.4	534.6	581.2	643.8	719.7	779.5	790.5	740.7	650.3	566.1	497.2
55°	446.4	476.7	515.9	574.8	640.5	691.2	685.3	621.2	539.1	467.2	412.9
57.5°	393.1	416.0	452.2	507.5	565.1	599.2	577.5	523.0	446.5	387.6	341.8
60°	358.0	379.2	412.9	461.3	512.0	531.2	513.1	453.8	393.3	339.5	300.9
62.5°	324.7	343.4	372.4	417.3	458.2	469.6	450.3	398.5	344.0	298.0	266.1
65°	276.2	293.5	318.3	350.1	378.4	383.8	371.3	318.3	277.0	238.5	216.5
67.5°	232.3	243.6	263.0	290.4	305.5	308.7	284.4	251.1	214.7	191.1	174.5
70°	202.8	210.6	228.6	243.6	255.8	256.2	233.8	207.0	179.2	160.0	147.7
72.5°	174.1	181.7	195.4	205.6	214.9	211.9	191.4	170.3	147.7	133.2	124.1
75°	134.4	141.1	148.1	152.9	152.9	149.0	134.0	118.3	105.3	96.6	93.9
77.5°	97.7	103.2	105.5	104.8	103.4	97.3	87.9	77.6	72.9	68.9	66.8
80°	76.6	79.0	79.8	77.8	75.4	68.4	62.1	57.8	53.4	51.9	51.1
82.5°	56.9	58.9	56.9	57.4	52.2	46.4	42.9	41.4	39.6	39.0	38.2
85°	30.3	29.9	29.1	27.1	23.5	22.8	22.4	22.0	21.2	21.6	20.8
87.5°	11.5	11.0	10.3	10.4	10.9	10.6	11.3	11.6	12.0	11.9	12.8
90°	5.5	8.0	10.4	12.9	15.0	16.8	18.6	20.4	22.2	23.5	24.8
92.5°	24.4	27.2	30.0	32.8	34.9	36.2	37.4	38.7	39.9	40.7	41.5
95°	62.5	64.5	66.6	68.6	70.3	71.9	73.5	75.0	76.6	77.3	78.0
97.5°	107.2	108.9	110.5	112.1	113.8	115.6	117.4	119.4	121.2	122.0	122.8
100°	142.0	142.9	143.8	144.7	146.1	148.1	150.2	152.2	154.2	154.7	155.1
102.5°	178.5	178.9	179.3	179.7	180.8	182.6	184.4	186.2	188.1	188.7	189.3
105°	235.1	235.3	235.5	235.8	236.3	237.2	238.1	239.0	239.9	240.5	241.3
107.5°	294.6	294.9	295.2	295.4	295.6	295.8	295.9	296.0	296.2	296.8	297.4
110°	335.1	335.6	336.0	336.5	336.6	336.3	336.1	335.9	335.7	335.2	334.8



TEST NUMBER: P332914-840

CATALOG NUMBER: SA4XXRDIP-C575D1035U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	376.7	376.8	376.9	377.0	376.8	376.4	376.0	375.6	375.2	375.1	375.0
115°	439.5	439.5	439.5	439.5	439.3	438.8	438.4	437.9	437.5	437.3	437.0
117.5°	499.0	499.1	499.3	499.5	499.4	499.1	498.8	498.5	498.2	497.4	496.7
120°	539.2	540.1	541.0	541.9	542.0	541.3	540.6	540.0	539.3	538.2	537.0
122.5°	579.8	580.1	580.5	580.8	580.9	580.6	580.2	579.9	579.6	578.9	578.0
125°	640.1	640.1	640.1	640.1	640.0	639.7	639.5	639.2	639.0	638.6	638.1
127.5°	695.8	696.4	697.1	697.8	697.9	697.6	697.2	696.9	696.5	696.1	695.6
130°	734.5	735.2	735.8	736.5	736.8	736.8	736.8	736.8	736.8	736.4	736.0
132.5°	773.9	774.3	774.8	775.3	775.5	775.3	775.1	774.9	774.8	774.3	773.9
135°	826.9	828.2	829.6	830.9	831.6	831.6	831.6	831.6	831.6	831.1	830.7
137.5°	883.0	883.6	884.2	884.9	885.3	885.8	886.2	886.5	886.9	886.3	885.7
140°	920.7	921.2	921.6	922.1	922.3	922.3	922.3	922.3	922.3	922.1	921.9
142.5°	955.4	955.8	956.3	956.7	956.8	956.7	956.5	956.3	956.1	956.1	956.0
145°	1003.8	1004.7	1005.6	1006.5	1007.0	1007.3	1007.5	1007.7	1007.9	1007.7	1007.5
147.5°	1051.6	1052.7	1053.8	1054.8	1055.3	1055.1	1054.9	1054.7	1054.6	1054.4	1054.2
150°	1080.5	1081.4	1082.3	1083.2	1083.6	1083.6	1083.6	1083.6	1083.6	1083.6	1083.6
152.5°	1107.5	1108.0	1108.6	1109.1	1109.4	1109.6	1109.8	1110.0	1110.1	1110.8	1111.3
155°	1149.1	1149.1	1149.1	1149.1	1149.0	1148.7	1148.5	1148.3	1148.1	1149.0	1149.9
157.5°	1184.2	1183.8	1183.4	1183.0	1182.8	1182.7	1182.7	1182.7	1182.6	1183.3	1183.9
160°	1205.3	1205.1	1204.9	1204.7	1204.5	1204.2	1204.0	1203.8	1203.6	1204.2	1204.9
162.5°	1224.4	1223.8	1223.1	1222.5	1222.1	1221.9	1221.7	1221.5	1221.2	1222.4	1223.7
165°	1250.2	1249.6	1248.9	1248.2	1247.7	1247.2	1246.8	1246.3	1245.9	1247.2	1248.6
167.5°	1269.9	1269.0	1268.1	1267.1	1266.7	1266.7	1266.8	1266.8	1266.9	1268.2	1269.5
170°	1281.0	1279.9	1278.8	1277.7	1277.2	1277.5	1277.7	1277.9	1278.1	1279.5	1280.8
172.5°	1289.3	1288.4	1287.4	1286.5	1286.0	1286.1	1286.1	1286.2	1286.2	1287.7	1289.2
175°	1300.2	1299.1	1298.0	1296.9	1296.2	1296.0	1295.7	1295.5	1295.3	1296.9	1298.4
177.5°	1304.0	1303.1	1302.2	1301.3	1300.9	1300.9	1300.9	1300.9	1300.9	1302.1	1303.4
180°	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3



TEST NUMBER: P332914-840

CATALOG NUMBER: SA4XXRDIP-C575D1035U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	975.2	975.2	975.2	975.2	975.2	975.2	975.2
2.5°	1023.0	1024.3	1025.2	1028.3	1028.6	1031.5	1028.6
5°	1107.6	1113.2	1121.8	1130.4	1131.3	1136.7	1126.9
7.5°	1202.5	1215.3	1223.2	1237.2	1242.7	1246.2	1240.5
10°	1268.0	1279.7	1300.6	1310.8	1321.0	1322.5	1317.9
12.5°	1331.1	1349.8	1366.2	1385.6	1385.1	1399.0	1393.9
15°	1415.3	1434.5	1457.3	1478.9	1486.8	1486.8	1493.1
17.5°	1475.3	1510.7	1534.2	1551.2	1569.7	1573.0	1570.7
20°	1515.9	1554.0	1579.1	1601.1	1613.8	1617.3	1617.3
22.5°	1546.1	1578.5	1603.1	1622.9	1633.3	1637.4	1636.1
25°	1567.0	1594.9	1609.8	1615.7	1618.4	1617.6	1610.2
27.5°	1538.3	1537.1	1527.6	1509.5	1496.0	1487.7	1478.3
30°	1483.7	1463.2	1439.7	1413.7	1380.3	1354.7	1347.0
32.5°	1402.3	1356.3	1316.5	1273.2	1237.3	1211.7	1201.0
35°	1244.8	1172.0	1112.8	1060.9	1023.2	999.6	991.7
37.5°	1057.9	987.5	914.1	863.8	832.5	808.7	799.8
40°	939.1	862.4	798.4	751.2	719.0	695.9	695.5
42.5°	830.6	757.5	697.2	663.3	628.5	613.2	613.1
45°	680.1	621.6	570.5	543.8	523.0	510.4	506.9
47.5°	563.1	514.7	480.7	459.4	442.4	434.4	429.2
50°	497.5	455.0	427.9	409.4	400.0	389.8	389.0
52.5°	442.7	408.5	387.4	372.3	360.4	354.3	354.5
55°	372.1	345.0	330.0	318.6	309.2	304.5	302.6
57.5°	313.5	293.2	282.3	271.9	267.8	264.1	263.1
60°	277.0	263.3	253.1	244.8	238.9	237.7	237.3
62.5°	246.8	232.5	225.4	219.0	214.7	212.9	212.2
65°	203.5	192.9	186.6	181.6	180.0	177.2	176.8
67.5°	164.1	157.7	153.6	150.1	147.8	147.7	147.7
70°	139.9	136.3	132.8	130.9	129.7	128.9	128.9
72.5°	119.2	116.5	113.6	112.6	112.4	111.6	111.3
75°	90.8	88.1	88.4	86.4	84.8	82.9	81.7
77.5°	64.3	62.4	62.0	61.8	60.4	60.2	60.8
80°	49.9	48.0	47.6	48.0	47.6	46.4	46.4
82.5°	38.0	36.4	36.0	35.6	35.2	35.6	35.0
85°	20.4	19.7	19.7	19.7	20.4	20.0	19.7
87.5°	12.4	12.4	12.9	12.7	12.8	12.5	12.9
90°	26.3	27.6	28.5	28.9	29.4	29.8	30.2
92.5°	42.3	43.1	43.7	43.9	44.2	44.5	44.7
95°	78.7	79.3	79.7	79.7	79.7	79.7	79.7
97.5°	123.6	124.4	124.8	124.8	124.8	124.8	124.8
100°	155.5	156.0	156.2	156.2	156.2	156.2	156.2
102.5°	190.0	190.6	191.0	191.2	191.4	191.6	191.7
105°	242.0	242.6	243.3	243.9	244.6	245.3	245.9
107.5°	298.0	298.6	298.9	298.9	298.8	298.8	298.7
110°	334.3	333.9	334.0	334.7	335.3	336.0	336.7



TEST NUMBER: P332914-840

CATALOG NUMBER: SA4XXRDIP-C575D1035U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	374.9	374.9	374.9	375.0	375.1	375.3	375.4
115°	436.8	436.6	436.4	436.2	435.9	435.7	435.5
117.5°	495.8	495.1	494.5	494.0	493.6	493.1	492.7
120°	535.9	534.8	534.4	534.9	535.3	535.8	536.2
122.5°	577.3	576.5	575.7	574.9	574.1	573.3	572.5
125°	637.7	637.2	636.8	636.4	635.9	635.5	635.0
127.5°	695.2	694.7	694.3	694.0	693.6	693.3	692.9
130°	735.5	735.1	734.4	733.5	732.6	731.6	730.7
132.5°	773.4	773.0	772.5	772.1	771.8	771.4	771.1
135°	830.2	829.8	829.2	828.6	827.9	827.2	826.6
137.5°	885.0	884.5	884.2	884.4	884.5	884.6	884.8
140°	921.6	921.4	921.2	921.0	920.7	920.5	920.3
142.5°	956.0	956.0	955.9	955.9	955.8	955.8	955.7
145°	1007.3	1007.0	1006.6	1005.9	1005.3	1004.6	1003.9
147.5°	1054.0	1053.8	1053.6	1053.4	1053.2	1053.0	1052.8
150°	1083.6	1083.6	1083.5	1083.3	1083.0	1082.8	1082.6
152.5°	1111.8	1112.4	1112.4	1111.8	1111.2	1110.5	1109.9
155°	1150.7	1151.7	1151.7	1150.7	1149.9	1149.0	1148.1
157.5°	1184.6	1185.3	1185.2	1184.5	1183.7	1183.0	1182.1
160°	1205.6	1206.2	1206.0	1204.9	1203.8	1202.6	1201.5
162.5°	1224.9	1226.1	1226.2	1225.1	1224.0	1222.8	1221.6
165°	1249.9	1251.2	1251.4	1250.6	1249.7	1248.8	1247.9
167.5°	1270.9	1272.2	1272.2	1270.8	1269.4	1268.0	1266.7
170°	1282.1	1283.5	1283.3	1281.8	1280.2	1278.7	1277.1
172.5°	1290.7	1292.3	1292.2	1290.7	1289.1	1287.6	1286.0
175°	1300.0	1301.5	1301.5	1300.0	1298.4	1296.9	1295.3
177.5°	1304.6	1306.0	1305.9	1304.4	1302.9	1301.5	1300.1
180°	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3

(END OF REPORT)