

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332919-840

Luminaire Tested: **SA4XXRDIP-C575D1205U840-4F0-1E-UDD-A**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332919-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C575D1205U840-4F0-1E-UDD-A
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1205 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7322.6 lumens
Efficiency: N/A
Efficacy: 148.2 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 49.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332919-840
CATALOG NUMBER: SA4XXRDIP-C575D1205U840-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332919-840

CATALOG NUMBER: SA4XXRDIP-C575D1205U840-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	34
1	94	90	87	83	85	82	79	76	65	63	61	51	49	48	37	36	35	29
2	86	79	73	69	78	72	67	63	58	54	51	45	42	41	33	31	30	25
3	79	70	63	57	71	63	57	53	51	47	43	40	37	35	29	28	26	21
4	72	62	54	49	65	56	50	45	46	41	37	36	32	30	26	24	23	19
5	66	55	47	42	60	50	43	38	41	36	32	32	29	26	24	22	20	16
6	61	49	42	36	55	45	38	33	37	32	28	29	25	23	22	19	18	14
7	56	45	37	32	51	41	34	29	33	28	25	26	23	20	20	17	16	13
8	52	40	33	28	47	37	30	26	30	25	22	24	21	18	18	16	14	12
9	49	37	30	25	44	34	27	23	28	23	20	22	19	16	17	14	13	10
10	45	34	27	22	41	31	25	21	25	21	18	20	17	15	16	13	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	7873	7873	7873	7873
5°	9132	7896	6980	7896
10°	10803	7862	6229	7862
15°	12479	7789	5353	7789
20°	13894	7689	4840	7689
25°	14343	7591	4494	7591
30°	12557	7471	4285	7471
35°	9773	7295	4159	7295
40°	7330	7093	4091	7093
45°	5787	6769	4055	6769
50°	4886	6395	3939	6395
55°	4259	5985	3727	5985
60°	3831	5557	3299	5557
65°	3377	5096	2839	5096
70°	3043	4619	2561	4619
75°	2548	4095	2183	4095
80°	2157	3487	2046	3487
85°	1825	2732	1825	2732



TEST NUMBER: P332919-840

CATALOG NUMBER: SA4XXRDIP-C575D1205U840-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.5	1.3
10°-20°	285.0	3.9
20°-30°	445.8	6.1
30°-40°	495.6	6.8
40°-50°	439.7	6.0
50°-60°	342.6	4.7
60°-70°	224.3	3.1
70°-80°	110.3	1.5
80°-90°	31.7	0.4
90°-100°	53.7	0.7
100°-110°	342.1	4.7
110°-120°	654.5	8.9
120°-130°	830.8	11.3
130°-140°	888.9	12.1
140°-150°	831.2	11.4
150°-160°	670.3	9.2
160°-170°	432.4	5.9
170°-180°	149.0	2.0
0°-30°	825.3	11.3
0°-40°	1320.9	18.0
0°-60°	2103.3	28.7
0°-90°	2469.7	33.7
90°-120°	1050.3	14.3
90°-150°	3601.3	49.2
90°-180°	4853.0	66.3
0°-180°	7322.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	975	975	975	975	975	
5°	1127	974	861	974	1127	114
15°	1493	932	640	932	1493	425
25°	1610	852	504	852	1610	714
35°	992	740	422	740	992	622
45°	507	593	355	593	507	401
55°	303	425	265	425	303	275
65°	177	267	149	267	177	178
75°	82	131	70	131	82	90
85°	20	30	20	30	20	23
90°	35	4	35	4	35	16
95°	34	64	34	64	34	27
105°	334	353	334	353	334	292
115°	664	659	664	659	664	657
125°	934	927	934	927	934	832
135°	1158	1150	1158	1150	1158	891
145°	1333	1326	1333	1326	1333	833
155°	1453	1454	1453	1454	1453	670
165°	1527	1534	1527	1534	1527	431
175°	1559	1569	1559	1569	1559	149
180°	1569	1569	1569	1569	1569	



TEST NUMBER: P332919-840

CATALOG NUMBER: SA4XXRDIP-C575D1205U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2
2.5°	1028.6	1031.5	1028.6	1028.3	1025.2	1024.3	1023.0	1019.0	1011.4	1006.9	1007.9
5°	1126.9	1136.7	1131.3	1130.4	1121.8	1113.2	1107.6	1095.1	1081.7	1072.7	1065.2
7.5°	1240.5	1246.2	1242.7	1237.2	1223.2	1215.3	1202.5	1186.0	1162.1	1143.7	1127.0
10°	1317.9	1322.5	1321.0	1310.8	1300.6	1279.7	1268.0	1244.8	1214.5	1190.5	1168.1
12.5°	1393.9	1399.0	1385.1	1385.6	1366.2	1349.8	1331.1	1302.0	1267.0	1236.1	1208.1
15°	1493.1	1486.8	1486.8	1478.9	1457.3	1434.5	1415.3	1384.6	1340.6	1303.7	1264.9
17.5°	1570.7	1573.0	1569.7	1551.2	1534.2	1510.7	1475.3	1439.6	1398.7	1349.1	1309.4
20°	1617.3	1617.3	1613.8	1601.1	1579.1	1554.0	1515.9	1477.0	1425.1	1375.2	1330.4
22.5°	1636.1	1637.4	1633.3	1622.9	1603.1	1578.5	1546.1	1506.5	1453.1	1396.9	1341.4
25°	1610.2	1617.6	1618.4	1615.7	1609.8	1594.9	1567.0	1526.5	1478.5	1417.6	1358.0
27.5°	1478.3	1487.7	1496.0	1509.5	1527.6	1537.1	1538.3	1517.7	1475.9	1417.3	1357.3
30°	1347.0	1354.7	1380.3	1413.7	1439.7	1463.2	1483.7	1489.1	1465.6	1412.9	1349.7
32.5°	1201.0	1211.7	1237.3	1273.2	1316.5	1356.3	1402.3	1425.6	1425.0	1393.4	1334.9
35°	991.7	999.6	1023.2	1060.9	1112.8	1172.0	1244.8	1301.3	1339.9	1337.1	1301.3
37.5°	799.8	808.7	832.5	863.8	914.1	987.5	1057.9	1135.9	1207.1	1247.1	1235.1
40°	695.5	695.9	719.0	751.2	798.4	862.4	939.1	1025.5	1104.9	1169.7	1182.2
42.5°	613.1	613.2	628.5	663.3	697.2	757.5	830.6	916.5	1009.4	1084.2	1117.5
45°	506.9	510.4	523.0	543.8	570.5	621.6	680.1	759.9	864.0	952.8	1008.2
47.5°	429.2	434.4	442.4	459.4	480.7	514.7	563.1	634.8	719.5	817.2	896.1
50°	389.0	389.8	400.0	409.4	427.9	455.0	497.5	557.1	635.0	728.8	816.5
52.5°	354.5	354.3	360.4	372.3	387.4	408.5	442.7	497.2	566.1	650.3	740.7
55°	302.6	304.5	309.2	318.6	330.0	345.0	372.1	412.9	467.2	539.1	621.2
57.5°	263.1	264.1	267.8	271.9	282.3	293.2	313.5	341.8	387.6	446.5	523.0
60°	237.3	237.7	238.9	244.8	253.1	263.3	277.0	300.9	339.5	393.3	453.8
62.5°	212.2	212.9	214.7	219.0	225.4	232.5	246.8	266.1	298.0	344.0	398.5
65°	176.8	177.2	180.0	181.6	186.6	192.9	203.5	216.5	238.5	277.0	318.3
67.5°	147.7	147.7	147.8	150.1	153.6	157.7	164.1	174.5	191.1	214.7	251.1
70°	128.9	128.9	129.7	130.9	132.8	136.3	139.9	147.7	160.0	179.2	207.0
72.5°	111.3	111.6	112.4	112.6	113.6	116.5	119.2	124.1	133.2	147.7	170.3
75°	81.7	82.9	84.8	86.4	88.4	88.1	90.8	93.9	96.6	105.3	118.3
77.5°	60.8	60.2	60.4	61.8	62.0	62.4	64.3	66.8	68.9	72.9	77.6
80°	46.4	46.4	47.6	48.0	47.6	48.0	49.9	51.1	51.9	53.4	57.8
82.5°	35.0	35.6	35.2	35.6	36.0	36.4	38.0	38.2	39.0	39.6	41.4
85°	19.7	20.0	20.4	19.7	19.7	19.7	20.4	20.8	21.6	21.2	22.0
87.5°	13.9	13.5	13.7	13.6	13.8	13.3	13.3	13.6	12.7	12.7	12.3
90°	35.2	34.6	34.1	33.6	33.1	32.1	30.5	29.0	27.4	25.9	23.7
92.5°	32.4	32.3	32.2	32.1	32.0	31.1	29.6	28.0	26.5	24.8	22.8
95°	34.0	33.7	33.5	33.2	33.0	32.1	30.5	29.0	27.4	25.9	25.5
97.5°	32.8	32.6	32.3	32.1	31.8	31.6	31.4	31.3	31.1	31.0	60.1
100°	32.8	32.6	32.3	32.1	31.8	33.9	38.4	42.7	47.2	51.6	87.7
102.5°	33.8	33.7	33.7	33.6	33.6	57.5	105.3	153.1	201.0	248.7	253.5
105°	334.5	343.9	353.1	362.5	371.9	375.5	373.1	370.8	368.5	366.1	364.8
107.5°	466.1	465.0	464.1	463.1	462.1	461.0	459.9	458.8	457.6	456.5	454.6
110°	523.3	522.6	521.8	521.0	520.2	519.6	519.1	518.6	518.0	517.5	515.9



TEST NUMBER: P332919-840

CATALOG NUMBER: SA4XXRDIP-C575D1205U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	580.6	579.7	578.7	577.6	576.6	576.2	576.3	576.4	576.5	576.6	575.9
115°	664.2	664.2	664.2	664.2	664.2	663.9	663.4	662.9	662.4	661.8	662.1
117.5°	749.1	749.2	749.3	749.4	749.5	749.6	749.7	749.8	749.9	750.0	749.5
120°	802.6	803.1	803.7	804.2	804.7	804.7	804.2	803.7	803.1	802.6	802.8
122.5°	855.2	855.7	856.3	856.8	857.3	857.4	857.1	856.8	856.5	856.2	855.8
125°	934.0	933.8	933.5	933.2	933.0	932.5	931.7	930.9	930.1	929.4	929.9
127.5°	1003.3	1003.5	1003.7	1003.9	1004.1	1004.3	1004.4	1004.6	1004.7	1004.9	1003.7
130°	1050.2	1050.2	1050.2	1050.2	1050.2	1050.1	1049.9	1049.6	1049.2	1049.0	1048.2
132.5°	1093.4	1093.6	1093.8	1094.0	1094.2	1094.2	1094.0	1093.7	1093.4	1093.2	1092.2
135°	1158.1	1157.6	1157.1	1156.6	1156.1	1155.6	1155.0	1154.5	1154.0	1153.5	1152.5
137.5°	1213.6	1213.7	1213.9	1214.1	1214.2	1214.0	1213.4	1212.8	1212.2	1211.6	1210.5
140°	1252.0	1251.7	1251.5	1251.2	1251.0	1250.5	1249.7	1248.9	1248.1	1247.4	1246.8
142.5°	1283.9	1283.9	1283.8	1283.8	1283.7	1283.4	1282.8	1282.3	1281.7	1281.1	1280.8
145°	1333.0	1332.5	1331.9	1331.4	1330.9	1330.5	1330.3	1330.0	1329.8	1329.5	1329.5
147.5°	1373.6	1373.3	1373.1	1372.8	1372.5	1372.3	1372.1	1371.9	1371.7	1371.5	1371.7
150°	1399.9	1399.7	1399.4	1399.1	1398.9	1398.7	1398.7	1398.7	1398.7	1398.7	1399.0
152.5°	1422.4	1422.6	1422.7	1422.9	1423.0	1422.9	1422.5	1422.1	1421.7	1421.3	1421.7
155°	1452.7	1453.5	1454.2	1455.0	1455.8	1455.7	1454.6	1453.6	1452.6	1451.5	1452.3
157.5°	1478.0	1479.4	1480.8	1482.1	1483.5	1483.5	1482.1	1480.8	1479.4	1478.0	1478.9
160°	1494.9	1496.5	1498.0	1499.6	1501.2	1501.2	1499.6	1498.0	1496.5	1494.9	1495.2
162.5°	1508.0	1509.8	1511.7	1513.4	1515.2	1515.3	1513.7	1512.2	1510.6	1509.0	1509.2
165°	1526.6	1528.9	1531.3	1533.7	1536.0	1536.1	1534.1	1532.0	1529.8	1527.8	1527.8
167.5°	1540.4	1543.1	1545.7	1548.3	1550.8	1551.1	1548.7	1546.5	1544.2	1541.9	1542.1
170°	1548.9	1551.6	1554.1	1556.7	1559.3	1559.6	1557.5	1555.4	1553.4	1551.3	1551.0
172.5°	1553.6	1556.4	1559.2	1562.1	1564.9	1565.2	1563.2	1561.0	1558.9	1556.9	1556.6
175°	1559.4	1562.6	1565.7	1568.8	1572.0	1572.4	1570.0	1567.7	1565.3	1563.0	1562.8
177.5°	1563.3	1565.7	1568.2	1570.7	1573.3	1573.7	1572.0	1570.3	1568.6	1567.0	1566.6
180°	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8



TEST NUMBER: P332919-840

CATALOG NUMBER: SA4XXRDIP-C575D1205U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2
2.5°	1004.8	1000.4	998.2	993.1	987.1	984.0	981.2	977.1	971.8	966.1	962.0
5°	1055.8	1046.3	1034.5	1020.4	1007.8	995.6	985.0	974.4	962.3	949.7	937.2
7.5°	1108.1	1089.5	1069.5	1046.3	1023.8	1003.3	984.4	966.3	945.9	927.6	910.9
10°	1144.6	1119.4	1091.6	1062.1	1032.6	1007.0	981.9	959.1	933.9	911.6	892.7
12.5°	1174.2	1144.6	1111.1	1074.3	1038.8	1007.9	979.1	949.4	920.8	896.5	871.3
15°	1223.1	1182.7	1137.5	1093.5	1047.5	1005.5	966.5	932.0	899.4	865.3	841.2
17.5°	1256.9	1208.8	1154.0	1101.1	1046.7	997.1	952.3	911.1	873.4	838.6	810.0
20°	1277.0	1224.0	1163.1	1102.9	1042.0	989.0	940.7	895.0	856.2	818.5	789.0
22.5°	1288.3	1229.6	1163.1	1100.0	1037.0	979.6	926.6	879.1	836.7	799.0	766.4
25°	1291.9	1229.0	1161.0	1088.7	1019.7	958.8	903.7	852.2	805.1	767.4	732.8
27.5°	1286.9	1212.8	1143.3	1069.0	997.7	933.5	875.8	821.6	774.5	734.0	698.5
30°	1279.3	1200.0	1125.3	1048.3	976.0	914.3	853.4	801.5	752.5	710.4	674.7
32.5°	1263.0	1184.3	1104.0	1025.0	951.8	888.3	830.5	778.3	730.1	687.1	649.1
35°	1230.6	1150.8	1063.6	982.7	910.8	844.8	790.5	740.2	694.3	648.3	608.2
37.5°	1187.9	1106.5	1019.7	931.1	859.1	796.8	747.0	699.8	654.9	613.0	568.6
40°	1147.7	1073.5	983.9	895.9	822.0	761.8	715.9	673.1	627.9	586.2	541.8
42.5°	1099.0	1035.7	945.2	856.9	784.0	726.0	683.2	641.4	600.3	559.9	513.5
45°	1017.6	969.8	884.8	800.0	726.5	669.1	629.9	592.9	556.7	518.3	474.6
47.5°	924.4	892.0	818.8	731.8	663.9	612.3	574.3	544.1	513.5	475.0	436.8
50°	859.7	838.9	768.2	688.8	624.0	576.4	537.6	509.2	483.7	446.8	412.5
52.5°	790.5	779.5	719.7	643.8	581.2	534.6	501.4	475.9	450.1	419.4	387.4
55°	685.3	691.2	640.5	574.8	515.9	476.7	446.4	425.2	403.1	377.2	352.4
57.5°	577.5	599.2	565.1	507.5	452.2	416.0	393.1	375.3	356.9	335.3	314.2
60°	513.1	531.2	512.0	461.3	412.9	379.2	358.0	344.2	325.7	306.1	289.9
62.5°	450.3	469.6	458.2	417.3	372.4	343.4	324.7	311.8	298.1	280.9	264.2
65°	371.3	383.8	378.4	350.1	318.3	293.5	276.2	266.8	254.2	241.7	226.7
67.5°	284.4	308.7	305.5	290.4	263.0	243.6	232.3	224.0	212.5	203.2	193.0
70°	233.8	256.2	255.8	243.6	228.6	210.6	202.8	195.7	185.4	176.4	168.1
72.5°	191.4	211.9	214.9	205.6	195.4	181.7	174.1	169.3	159.4	153.2	146.4
75°	134.0	149.0	152.9	152.9	148.1	141.1	134.4	131.3	124.1	118.7	114.7
77.5°	87.9	97.3	103.4	104.8	105.5	103.2	97.7	95.4	90.1	88.1	84.3
80°	62.1	68.4	75.4	77.8	79.8	79.0	76.6	75.0	70.0	68.0	66.4
82.5°	42.9	46.4	52.2	57.4	56.9	58.9	56.9	55.5	51.7	51.0	49.4
85°	22.4	22.8	23.5	27.1	29.1	29.9	30.3	29.5	28.3	28.3	25.5
87.5°	11.9	11.1	11.3	10.9	10.6	11.3	11.6	11.4	11.0	10.6	10.3
90°	21.6	19.6	17.5	14.9	12.1	9.3	6.4	3.5	6.4	9.3	12.1
92.5°	20.7	18.6	16.6	15.5	15.2	15.1	14.9	14.7	14.9	15.1	15.2
95°	25.2	25.0	24.7	29.1	38.0	46.8	55.6	64.5	55.6	46.8	38.0
97.5°	89.2	118.3	147.3	159.2	153.6	148.1	142.6	137.0	142.6	148.1	153.6
100°	123.6	159.6	195.6	211.3	206.5	201.9	197.1	192.5	197.1	201.9	206.5
102.5°	258.1	262.9	267.5	268.1	264.7	261.3	257.8	254.4	257.8	261.3	264.7
105°	363.5	362.2	360.9	359.4	357.9	356.3	354.8	353.1	354.8	356.3	357.9
107.5°	452.9	451.1	449.4	448.1	447.3	446.6	445.8	444.9	445.8	446.6	447.3
110°	514.3	512.8	511.2	510.1	509.3	508.5	507.7	507.0	507.7	508.5	509.3



TEST NUMBER: P332919-840

CATALOG NUMBER: SA4XXRDIP-C575D1205U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	575.1	574.4	573.7	572.6	571.2	569.8	568.5	567.0	568.5	569.8	571.2
115°	662.4	662.6	662.9	662.6	661.8	661.1	660.2	659.4	660.2	661.1	661.8
117.5°	748.9	748.3	747.7	746.9	745.9	744.9	743.8	742.8	743.8	744.9	745.9
120°	803.1	803.4	803.7	803.2	802.2	801.2	800.1	799.1	800.1	801.2	802.2
122.5°	855.4	855.1	854.6	854.1	853.5	852.9	852.3	851.6	852.3	852.9	853.5
125°	930.4	930.9	931.4	931.2	930.1	929.1	928.1	927.0	928.1	929.1	930.1
127.5°	1002.5	1001.3	1000.1	999.4	999.2	998.9	998.6	998.4	998.6	998.9	999.2
130°	1047.4	1046.7	1045.9	1045.4	1045.1	1044.9	1044.6	1044.3	1044.6	1044.9	1045.1
132.5°	1091.2	1090.1	1089.2	1088.4	1088.0	1087.5	1087.0	1086.6	1087.0	1087.5	1088.0
135°	1151.3	1150.3	1149.3	1148.9	1149.1	1149.4	1149.7	1149.9	1149.7	1149.4	1149.1
137.5°	1209.4	1208.2	1207.1	1206.5	1206.4	1206.3	1206.2	1206.1	1206.2	1206.3	1206.4
140°	1246.3	1245.8	1245.3	1244.8	1244.3	1243.6	1243.1	1242.6	1243.1	1243.6	1244.3
142.5°	1280.5	1280.2	1279.9	1279.3	1278.3	1277.4	1276.5	1275.5	1276.5	1277.4	1278.3
145°	1329.5	1329.5	1329.5	1329.1	1328.3	1327.6	1326.8	1326.0	1326.8	1327.6	1328.3
147.5°	1372.0	1372.3	1372.5	1371.9	1370.5	1369.0	1367.6	1366.0	1367.6	1369.0	1370.5
150°	1399.3	1399.5	1399.8	1399.4	1398.4	1397.2	1396.2	1395.2	1396.2	1397.2	1398.4
152.5°	1422.2	1422.7	1423.1	1422.9	1422.1	1421.3	1420.5	1419.6	1420.5	1421.3	1422.1
155°	1453.1	1453.9	1454.6	1454.9	1454.6	1454.4	1454.1	1453.9	1454.1	1454.4	1454.6
157.5°	1479.9	1480.7	1481.6	1482.1	1482.3	1482.4	1482.6	1482.7	1482.6	1482.4	1482.3
160°	1495.4	1495.7	1496.0	1496.5	1497.3	1498.0	1498.8	1499.6	1498.8	1498.0	1497.3
162.5°	1509.5	1509.7	1510.1	1510.7	1511.7	1512.7	1513.7	1514.6	1513.7	1512.7	1511.7
165°	1527.8	1527.8	1527.8	1528.4	1529.7	1531.1	1532.4	1533.7	1532.4	1531.1	1529.7
167.5°	1542.2	1542.4	1542.5	1543.3	1544.6	1546.0	1547.3	1548.6	1547.3	1546.0	1544.6
170°	1550.7	1550.4	1550.2	1550.8	1552.5	1554.0	1555.6	1557.1	1555.6	1554.0	1552.5
172.5°	1556.4	1556.1	1555.8	1556.5	1558.0	1559.6	1561.2	1562.8	1561.2	1559.6	1558.0
175°	1562.5	1562.2	1562.0	1562.6	1564.2	1565.7	1567.3	1568.8	1567.3	1565.7	1564.2
177.5°	1566.1	1565.7	1565.3	1565.8	1567.3	1568.7	1570.2	1571.7	1570.2	1568.7	1567.3
180°	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8



TEST NUMBER: P332919-840

CATALOG NUMBER: SA4XXRDIP-C575D1205U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2
2.5°	957.7	954.5	950.4	945.6	940.0	935.0	932.8	934.6	935.6	933.1	932.8
5°	928.5	918.7	910.8	899.0	889.6	881.7	876.2	873.8	874.6	868.4	866.8
7.5°	895.6	884.0	871.2	857.2	844.1	832.6	826.6	823.2	816.6	813.7	808.9
10°	874.6	858.9	846.4	829.8	815.0	801.1	794.5	789.0	782.3	779.1	772.4
12.5°	852.9	834.8	820.9	803.8	788.5	771.9	765.6	755.4	744.9	738.3	729.7
15°	822.3	800.4	783.5	763.1	745.0	726.1	709.2	690.3	683.3	668.3	659.7
17.5°	786.6	764.3	743.4	716.0	688.1	664.7	646.6	628.6	617.7	608.2	603.8
20°	763.1	742.7	713.6	681.8	650.7	624.7	610.2	598.4	586.6	580.0	575.2
22.5°	740.7	714.7	680.9	646.5	615.5	595.2	582.9	570.8	561.2	554.8	548.6
25°	703.4	669.1	633.4	594.1	572.9	555.2	541.8	532.0	526.1	517.9	514.7
27.5°	664.9	623.5	584.0	557.6	535.5	519.4	507.8	500.4	492.9	487.6	483.5
30°	635.3	593.3	558.0	532.8	510.4	497.1	487.6	479.0	473.1	468.8	465.6
32.5°	606.1	564.1	534.3	507.4	489.7	476.7	466.6	460.1	455.4	449.9	448.0
35°	563.8	526.5	500.6	476.3	458.2	446.4	438.5	431.8	427.9	426.4	425.2
37.5°	523.2	492.6	464.7	444.7	428.7	419.4	410.1	406.9	404.1	401.3	402.6
40°	497.5	468.8	444.0	422.8	409.8	399.6	394.0	390.2	387.8	387.8	387.8
42.5°	475.1	447.1	422.9	403.9	390.9	382.3	376.2	372.8	372.1	371.7	373.7
45°	440.5	414.5	390.2	374.5	363.5	354.8	351.2	348.5	348.5	350.1	350.5
47.5°	406.2	381.8	362.2	344.7	334.6	329.2	326.1	324.7	324.9	326.4	328.2
50°	385.1	361.1	341.8	326.1	316.7	311.5	308.8	308.0	308.8	308.8	311.5
52.5°	362.1	340.6	321.7	308.5	297.8	293.1	291.5	290.4	290.9	292.2	293.4
55°	328.5	309.2	291.1	278.6	270.7	267.6	264.1	264.5	263.7	264.5	264.5
57.5°	294.8	277.5	260.6	250.6	243.8	239.2	235.4	236.4	235.3	235.1	234.5
60°	273.1	254.2	240.9	231.9	224.0	220.0	216.5	217.3	216.1	215.3	213.8
62.5°	249.5	233.8	221.1	212.4	206.0	201.5	197.9	197.1	194.4	191.8	188.2
65°	215.3	202.4	191.0	182.7	176.8	173.3	170.6	168.1	162.3	156.0	152.9
67.5°	182.1	172.7	162.1	155.1	150.4	145.7	140.5	136.4	130.9	127.4	125.5
70°	160.7	151.7	142.6	135.9	130.9	126.5	120.6	117.9	113.9	112.4	110.4
72.5°	140.3	131.9	123.4	117.4	112.0	108.6	104.0	101.2	99.5	98.9	96.8
75°	109.3	102.6	96.2	90.8	86.4	84.1	82.1	80.2	79.4	75.8	73.8
77.5°	79.7	75.2	71.4	67.5	64.3	62.8	59.0	56.8	55.4	53.7	53.3
80°	62.1	59.0	55.0	52.6	48.4	46.8	45.1	44.8	44.4	44.0	43.6
82.5°	46.7	43.5	39.6	38.2	37.1	36.1	35.1	34.7	34.3	34.5	34.5
85°	23.5	22.0	22.0	21.6	21.2	20.8	20.4	20.4	20.0	20.4	20.0
87.5°	10.9	11.0	11.4	11.2	12.0	12.4	12.4	12.7	13.3	13.0	13.2
90°	14.9	17.5	19.6	21.6	23.7	25.9	27.4	29.0	30.5	32.1	33.1
92.5°	15.5	16.6	18.6	20.7	22.8	24.8	26.5	28.0	29.6	31.1	32.0
95°	29.1	24.7	25.0	25.2	25.5	25.9	27.4	29.0	30.5	32.1	33.0
97.5°	159.2	147.3	118.3	89.2	60.1	31.0	31.1	31.3	31.4	31.6	31.8
100°	211.3	195.6	159.6	123.6	87.7	51.6	47.2	42.7	38.4	33.9	31.8
102.5°	268.1	267.5	262.9	258.1	253.5	248.7	201.0	153.1	105.3	57.5	33.6
105°	359.4	360.9	362.2	363.5	364.8	366.1	368.5	370.8	373.1	375.5	371.9
107.5°	448.1	449.4	451.1	452.9	454.6	456.5	457.6	458.8	459.9	461.0	462.1
110°	510.1	511.2	512.8	514.3	515.9	517.5	518.0	518.6	519.1	519.6	520.2



TEST NUMBER: P332919-840

CATALOG NUMBER: SA4XXRDIP-C575D1205U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	572.6	573.7	574.4	575.1	575.9	576.6	576.5	576.4	576.3	576.2	576.6
115°	662.6	662.9	662.6	662.4	662.1	661.8	662.4	662.9	663.4	663.9	664.2
117.5°	746.9	747.7	748.3	748.9	749.5	750.0	749.9	749.8	749.7	749.6	749.5
120°	803.2	803.7	803.4	803.1	802.8	802.6	803.1	803.7	804.2	804.7	804.7
122.5°	854.1	854.6	855.1	855.4	855.8	856.2	856.5	856.8	857.1	857.4	857.3
125°	931.2	931.4	930.9	930.4	929.9	929.4	930.1	930.9	931.7	932.5	933.0
127.5°	999.4	1000.1	1001.3	1002.5	1003.7	1004.9	1004.7	1004.6	1004.4	1004.3	1004.1
130°	1045.4	1045.9	1046.7	1047.4	1048.2	1049.0	1049.2	1049.6	1049.9	1050.1	1050.2
132.5°	1088.4	1089.2	1090.1	1091.2	1092.2	1093.2	1093.4	1093.7	1094.0	1094.2	1094.2
135°	1148.9	1149.3	1150.3	1151.3	1152.5	1153.5	1154.0	1154.5	1155.0	1155.6	1156.1
137.5°	1206.5	1207.1	1208.2	1209.4	1210.5	1211.6	1212.2	1212.8	1213.4	1214.0	1214.2
140°	1244.8	1245.3	1245.8	1246.3	1246.8	1247.4	1248.1	1248.9	1249.7	1250.5	1251.0
142.5°	1279.3	1279.9	1280.2	1280.5	1280.8	1281.1	1281.7	1282.3	1282.8	1283.4	1283.7
145°	1329.1	1329.5	1329.5	1329.5	1329.5	1329.5	1329.8	1330.0	1330.3	1330.5	1330.9
147.5°	1371.9	1372.5	1372.3	1372.0	1371.7	1371.5	1371.7	1371.9	1372.1	1372.3	1372.5
150°	1399.4	1399.8	1399.5	1399.3	1399.0	1398.7	1398.7	1398.7	1398.7	1398.7	1398.9
152.5°	1422.9	1423.1	1422.7	1422.2	1421.7	1421.3	1421.7	1422.1	1422.5	1422.9	1423.0
155°	1454.9	1454.6	1453.9	1453.1	1452.3	1451.5	1452.6	1453.6	1454.6	1455.7	1455.8
157.5°	1482.1	1481.6	1480.7	1479.9	1478.9	1478.0	1479.4	1480.8	1482.1	1483.5	1483.5
160°	1496.5	1496.0	1495.7	1495.4	1495.2	1494.9	1496.5	1498.0	1499.6	1501.2	1501.2
162.5°	1510.7	1510.1	1509.7	1509.5	1509.2	1509.0	1510.6	1512.2	1513.7	1515.3	1515.2
165°	1528.4	1527.8	1527.8	1527.8	1527.8	1527.8	1529.8	1532.0	1534.1	1536.1	1536.0
167.5°	1543.3	1542.5	1542.4	1542.2	1542.1	1541.9	1544.2	1546.5	1548.7	1551.1	1550.8
170°	1550.8	1550.2	1550.4	1550.7	1551.0	1551.3	1553.4	1555.4	1557.5	1559.6	1559.3
172.5°	1556.5	1555.8	1556.1	1556.4	1556.6	1556.9	1558.9	1561.0	1563.2	1565.2	1564.9
175°	1562.6	1562.0	1562.2	1562.5	1562.8	1563.0	1565.3	1567.7	1570.0	1572.4	1572.0
177.5°	1565.8	1565.3	1565.7	1566.1	1566.6	1567.0	1568.6	1570.3	1572.0	1573.7	1573.3
180°	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8



TEST NUMBER: P332919-840

CATALOG NUMBER: SA4XXRDIP-C575D1205U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2
2.5°	930.9	931.5	929.4	928.7	929.4	931.5	930.9	932.8	933.1	935.6	934.6
5°	863.6	862.8	860.9	861.3	860.9	862.8	863.6	866.8	868.4	874.6	873.8
7.5°	806.1	803.0	804.0	800.7	804.0	803.0	806.1	808.9	813.7	816.6	823.2
10°	770.9	766.6	763.1	759.9	763.1	766.6	770.9	772.4	779.1	782.3	789.0
12.5°	722.9	719.1	714.3	715.3	714.3	719.1	722.9	729.7	738.3	744.9	755.4
15°	654.6	648.7	639.2	640.5	639.2	648.7	654.6	659.7	668.3	683.3	690.3
17.5°	596.8	596.9	592.6	593.6	592.6	596.9	596.8	603.8	608.2	617.7	628.6
20°	566.9	564.2	564.6	563.4	564.6	564.2	566.9	575.2	580.0	586.6	598.4
22.5°	546.2	542.9	540.1	537.7	540.1	542.9	546.2	548.6	554.8	561.2	570.8
25°	511.2	508.9	505.3	504.5	505.3	508.9	511.2	514.7	517.9	526.1	532.0
27.5°	480.4	479.9	478.5	476.7	478.5	479.9	480.4	483.5	487.6	492.9	500.4
30°	462.4	461.7	460.9	459.7	460.9	461.7	462.4	465.6	468.8	473.1	479.0
32.5°	446.5	446.0	445.1	445.2	445.1	446.0	446.5	448.0	449.9	455.4	460.1
35°	423.5	423.1	422.4	422.0	422.4	423.1	423.5	425.2	426.4	427.9	431.8
37.5°	402.2	403.2	402.7	402.6	402.7	403.2	402.2	402.6	401.3	404.1	406.9
40°	387.4	387.8	388.6	388.2	388.6	387.8	387.4	387.8	387.8	387.8	390.2
42.5°	375.2	375.3	376.4	375.0	376.4	375.3	375.2	373.7	371.7	372.1	372.8
45°	353.3	355.6	355.2	355.2	355.2	355.6	353.3	350.5	350.1	348.5	348.5
47.5°	329.2	331.3	331.8	331.7	331.8	331.3	329.2	328.2	326.4	324.9	324.7
50°	313.6	312.8	314.0	313.6	314.0	312.8	313.6	311.5	308.8	308.8	308.0
52.5°	294.4	294.6	294.5	294.1	294.5	294.6	294.4	293.4	292.2	290.9	290.4
55°	264.8	265.2	264.5	264.8	264.5	265.2	264.8	264.5	264.5	263.7	264.5
57.5°	232.8	230.9	231.7	230.8	231.7	230.9	232.8	234.5	235.1	235.3	236.4
60°	209.8	206.7	205.9	204.3	205.9	206.7	209.8	213.8	215.3	216.1	217.3
62.5°	184.0	181.9	179.2	180.5	179.2	181.9	184.0	188.2	191.8	194.4	197.1
65°	149.7	148.1	146.9	148.6	146.9	148.1	149.7	152.9	156.0	162.3	168.1
67.5°	123.9	123.1	123.1	122.3	123.1	123.1	123.9	125.5	127.4	130.9	136.4
70°	110.4	109.3	109.3	108.5	109.3	109.3	110.4	110.4	112.4	113.9	117.9
72.5°	96.5	95.4	95.7	95.2	95.7	95.4	96.5	96.8	98.9	99.5	101.2
75°	71.5	69.6	69.6	70.0	69.6	69.6	71.5	73.8	75.8	79.4	80.2
77.5°	53.3	52.9	53.5	52.8	53.5	52.9	53.3	53.3	53.7	55.4	56.8
80°	43.6	43.2	42.8	44.0	42.8	43.2	43.6	43.6	44.0	44.4	44.8
82.5°	33.8	33.8	33.7	35.2	33.7	33.8	33.8	34.5	34.5	34.3	34.7
85°	20.4	19.7	20.4	19.7	20.4	19.7	20.4	20.0	20.4	20.0	20.4
87.5°	13.9	13.7	13.5	13.9	13.5	13.7	13.9	13.2	13.0	13.3	12.7
90°	33.6	34.1	34.6	35.2	34.6	34.1	33.6	33.1	32.1	30.5	29.0
92.5°	32.1	32.2	32.3	32.4	32.3	32.2	32.1	32.0	31.1	29.6	28.0
95°	33.2	33.5	33.7	34.0	33.7	33.5	33.2	33.0	32.1	30.5	29.0
97.5°	32.1	32.3	32.6	32.8	32.6	32.3	32.1	31.8	31.6	31.4	31.3
100°	32.1	32.3	32.6	32.8	32.6	32.3	32.1	31.8	33.9	38.4	42.7
102.5°	33.6	33.7	33.7	33.8	33.7	33.7	33.6	33.6	57.5	105.3	153.1
105°	362.5	353.1	343.9	334.5	343.9	353.1	362.5	371.9	375.5	373.1	370.8
107.5°	463.1	464.1	465.0	466.1	465.0	464.1	463.1	462.1	461.0	459.9	458.8
110°	521.0	521.8	522.6	523.3	522.6	521.8	521.0	520.2	519.6	519.1	518.6



TEST NUMBER: P332919-840

CATALOG NUMBER: SA4XXRDIP-C575D1205U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	577.6	578.7	579.7	580.6	579.7	578.7	577.6	576.6	576.2	576.3	576.4
115°	664.2	664.2	664.2	664.2	664.2	664.2	664.2	664.2	663.9	663.4	662.9
117.5°	749.4	749.3	749.2	749.1	749.2	749.3	749.4	749.5	749.6	749.7	749.8
120°	804.2	803.7	803.1	802.6	803.1	803.7	804.2	804.7	804.7	804.2	803.7
122.5°	856.8	856.3	855.7	855.2	855.7	856.3	856.8	857.3	857.4	857.1	856.8
125°	933.2	933.5	933.8	934.0	933.8	933.5	933.2	933.0	932.5	931.7	930.9
127.5°	1003.9	1003.7	1003.5	1003.3	1003.5	1003.7	1003.9	1004.1	1004.3	1004.4	1004.6
130°	1050.2	1050.2	1050.2	1050.2	1050.2	1050.2	1050.2	1050.2	1050.1	1049.9	1049.6
132.5°	1094.0	1093.8	1093.6	1093.4	1093.6	1093.8	1094.0	1094.2	1094.2	1094.0	1093.7
135°	1156.6	1157.1	1157.6	1158.1	1157.6	1157.1	1156.6	1156.1	1155.6	1155.0	1154.5
137.5°	1214.1	1213.9	1213.7	1213.6	1213.7	1213.9	1214.1	1214.2	1214.0	1213.4	1212.8
140°	1251.2	1251.5	1251.7	1252.0	1251.7	1251.5	1251.2	1251.0	1250.5	1249.7	1248.9
142.5°	1283.8	1283.8	1283.9	1283.9	1283.9	1283.8	1283.8	1283.7	1283.4	1282.8	1282.3
145°	1331.4	1331.9	1332.5	1333.0	1332.5	1331.9	1331.4	1330.9	1330.5	1330.3	1330.0
147.5°	1372.8	1373.1	1373.3	1373.6	1373.3	1373.1	1372.8	1372.5	1372.3	1372.1	1371.9
150°	1399.1	1399.4	1399.7	1399.9	1399.7	1399.4	1399.1	1398.9	1398.7	1398.7	1398.7
152.5°	1422.9	1422.7	1422.6	1422.4	1422.6	1422.7	1422.9	1423.0	1422.9	1422.5	1422.1
155°	1455.0	1454.2	1453.5	1452.7	1453.5	1454.2	1455.0	1455.8	1455.7	1454.6	1453.6
157.5°	1482.1	1480.8	1479.4	1478.0	1479.4	1480.8	1482.1	1483.5	1483.5	1482.1	1480.8
160°	1499.6	1498.0	1496.5	1494.9	1496.5	1498.0	1499.6	1501.2	1501.2	1499.6	1498.0
162.5°	1513.4	1511.7	1509.8	1508.0	1509.8	1511.7	1513.4	1515.2	1515.3	1513.7	1512.2
165°	1533.7	1531.3	1528.9	1526.6	1528.9	1531.3	1533.7	1536.0	1536.1	1534.1	1532.0
167.5°	1548.3	1545.7	1543.1	1540.4	1543.1	1545.7	1548.3	1550.8	1551.1	1548.7	1546.5
170°	1556.7	1554.1	1551.6	1548.9	1551.6	1554.1	1556.7	1559.3	1559.6	1557.5	1555.4
172.5°	1562.1	1559.2	1556.4	1553.6	1556.4	1559.2	1562.1	1564.9	1565.2	1563.2	1561.0
175°	1568.8	1565.7	1562.6	1559.4	1562.6	1565.7	1568.8	1572.0	1572.4	1570.0	1567.7
177.5°	1570.7	1568.2	1565.7	1563.3	1565.7	1568.2	1570.7	1573.3	1573.7	1572.0	1570.3
180°	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8



TEST NUMBER: P332919-840

CATALOG NUMBER: SA4XXRDIP-C575D1205U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2
2.5°	932.8	935.0	940.0	945.6	950.4	954.5	957.7	962.0	966.1	971.8	977.1
5°	876.2	881.7	889.6	899.0	910.8	918.7	928.5	937.2	949.7	962.3	974.4
7.5°	826.6	832.6	844.1	857.2	871.2	884.0	895.6	910.9	927.6	945.9	966.3
10°	794.5	801.1	815.0	829.8	846.4	858.9	874.6	892.7	911.6	933.9	959.1
12.5°	765.6	771.9	788.5	803.8	820.9	834.8	852.9	871.3	896.5	920.8	949.4
15°	709.2	726.1	745.0	763.1	783.5	800.4	822.3	841.2	865.3	899.4	932.0
17.5°	646.6	664.7	688.1	716.0	743.4	764.3	786.6	810.0	838.6	873.4	911.1
20°	610.2	624.7	650.7	681.8	713.6	742.7	763.1	789.0	818.5	856.2	895.0
22.5°	582.9	595.2	615.5	646.5	680.9	714.7	740.7	766.4	799.0	836.7	879.1
25°	541.8	555.2	572.9	594.1	633.4	669.1	703.4	732.8	767.4	805.1	852.2
27.5°	507.8	519.4	535.5	557.6	584.0	623.5	664.9	698.5	734.0	774.5	821.6
30°	487.6	497.1	510.4	532.8	558.0	593.3	635.3	674.7	710.4	752.5	801.5
32.5°	466.6	476.7	489.7	507.4	534.3	564.1	606.1	649.1	687.1	730.1	778.3
35°	438.5	446.4	458.2	476.3	500.6	526.5	563.8	608.2	648.3	694.3	740.2
37.5°	410.1	419.4	428.7	444.7	464.7	492.6	523.2	568.6	613.0	654.9	699.8
40°	394.0	399.6	409.8	422.8	444.0	468.8	497.5	541.8	586.2	627.9	673.1
42.5°	376.2	382.3	390.9	403.9	422.9	447.1	475.1	513.5	559.9	600.3	641.4
45°	351.2	354.8	363.5	374.5	390.2	414.5	440.5	474.6	518.3	556.7	592.9
47.5°	326.1	329.2	334.6	344.7	362.2	381.8	406.2	436.8	475.0	513.5	544.1
50°	308.8	311.5	316.7	326.1	341.8	361.1	385.1	412.5	446.8	483.7	509.2
52.5°	291.5	293.1	297.8	308.5	321.7	340.6	362.1	387.4	419.4	450.1	475.9
55°	264.1	267.6	270.7	278.6	291.1	309.2	328.5	352.4	377.2	403.1	425.2
57.5°	235.4	239.2	243.8	250.6	260.6	277.5	294.8	314.2	335.3	356.9	375.3
60°	216.5	220.0	224.0	231.9	240.9	254.2	273.1	289.9	306.1	325.7	344.2
62.5°	197.9	201.5	206.0	212.4	221.1	233.8	249.5	264.2	280.9	298.1	311.8
65°	170.6	173.3	176.8	182.7	191.0	202.4	215.3	226.7	241.7	254.2	266.8
67.5°	140.5	145.7	150.4	155.1	162.1	172.7	182.1	193.0	203.2	212.5	224.0
70°	120.6	126.5	130.9	135.9	142.6	151.7	160.7	168.1	176.4	185.4	195.7
72.5°	104.0	108.6	112.0	117.4	123.4	131.9	140.3	146.4	153.2	159.4	169.3
75°	82.1	84.1	86.4	90.8	96.2	102.6	109.3	114.7	118.7	124.1	131.3
77.5°	59.0	62.8	64.3	67.5	71.4	75.2	79.7	84.3	88.1	90.1	95.4
80°	45.1	46.8	48.4	52.6	55.0	59.0	62.1	66.4	68.0	70.0	75.0
82.5°	35.1	36.1	37.1	38.2	39.6	43.5	46.7	49.4	51.0	51.7	55.5
85°	20.4	20.8	21.2	21.6	22.0	22.0	23.5	25.5	28.3	28.3	29.5
87.5°	12.4	12.4	12.0	11.2	11.4	11.0	10.9	10.3	10.6	11.0	11.4
90°	27.4	25.9	23.7	21.6	19.6	17.5	14.9	12.1	9.3	6.4	3.5
92.5°	26.5	24.8	22.8	20.7	18.6	16.6	15.5	15.2	15.1	14.9	14.7
95°	27.4	25.9	25.5	25.2	25.0	24.7	29.1	38.0	46.8	55.6	64.5
97.5°	31.1	31.0	60.1	89.2	118.3	147.3	159.2	153.6	148.1	142.6	137.0
100°	47.2	51.6	87.7	123.6	159.6	195.6	211.3	206.5	201.9	197.1	192.5
102.5°	201.0	248.7	253.5	258.1	262.9	267.5	268.1	264.7	261.3	257.8	254.4
105°	368.5	366.1	364.8	363.5	362.2	360.9	359.4	357.9	356.3	354.8	353.1
107.5°	457.6	456.5	454.6	452.9	451.1	449.4	448.1	447.3	446.6	445.8	444.9
110°	518.0	517.5	515.9	514.3	512.8	511.2	510.1	509.3	508.5	507.7	507.0



TEST NUMBER: P332919-840

CATALOG NUMBER: SA4XXRDIP-C575D1205U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	576.5	576.6	575.9	575.1	574.4	573.7	572.6	571.2	569.8	568.5	567.0
115°	662.4	661.8	662.1	662.4	662.6	662.9	662.6	661.8	661.1	660.2	659.4
117.5°	749.9	750.0	749.5	748.9	748.3	747.7	746.9	745.9	744.9	743.8	742.8
120°	803.1	802.6	802.8	803.1	803.4	803.7	803.2	802.2	801.2	800.1	799.1
122.5°	856.5	856.2	855.8	855.4	855.1	854.6	854.1	853.5	852.9	852.3	851.6
125°	930.1	929.4	929.9	930.4	930.9	931.4	931.2	930.1	929.1	928.1	927.0
127.5°	1004.7	1004.9	1003.7	1002.5	1001.3	1000.1	999.4	999.2	998.9	998.6	998.4
130°	1049.2	1049.0	1048.2	1047.4	1046.7	1045.9	1045.4	1045.1	1044.9	1044.6	1044.3
132.5°	1093.4	1093.2	1092.2	1091.2	1090.1	1089.2	1088.4	1088.0	1087.5	1087.0	1086.6
135°	1154.0	1153.5	1152.5	1151.3	1150.3	1149.3	1148.9	1149.1	1149.4	1149.7	1149.9
137.5°	1212.2	1211.6	1210.5	1209.4	1208.2	1207.1	1206.5	1206.4	1206.3	1206.2	1206.1
140°	1248.1	1247.4	1246.8	1246.3	1245.8	1245.3	1244.8	1244.3	1243.6	1243.1	1242.6
142.5°	1281.7	1281.1	1280.8	1280.5	1280.2	1279.9	1279.3	1278.3	1277.4	1276.5	1275.5
145°	1329.8	1329.5	1329.5	1329.5	1329.5	1329.5	1329.1	1328.3	1327.6	1326.8	1326.0
147.5°	1371.7	1371.5	1371.7	1372.0	1372.3	1372.5	1371.9	1370.5	1369.0	1367.6	1366.0
150°	1398.7	1398.7	1399.0	1399.3	1399.5	1399.8	1399.4	1398.4	1397.2	1396.2	1395.2
152.5°	1421.7	1421.3	1421.7	1422.2	1422.7	1423.1	1422.9	1422.1	1421.3	1420.5	1419.6
155°	1452.6	1451.5	1452.3	1453.1	1453.9	1454.6	1454.9	1454.6	1454.4	1454.1	1453.9
157.5°	1479.4	1478.0	1478.9	1479.9	1480.7	1481.6	1482.1	1482.3	1482.4	1482.6	1482.7
160°	1496.5	1494.9	1495.2	1495.4	1495.7	1496.0	1496.5	1497.3	1498.0	1498.8	1499.6
162.5°	1510.6	1509.0	1509.2	1509.5	1509.7	1510.1	1510.7	1511.7	1512.7	1513.7	1514.6
165°	1529.8	1527.8	1527.8	1527.8	1527.8	1527.8	1528.4	1529.7	1531.1	1532.4	1533.7
167.5°	1544.2	1541.9	1542.1	1542.2	1542.4	1542.5	1543.3	1544.6	1546.0	1547.3	1548.6
170°	1553.4	1551.3	1551.0	1550.7	1550.4	1550.2	1550.8	1552.5	1554.0	1555.6	1557.1
172.5°	1558.9	1556.9	1556.6	1556.4	1556.1	1555.8	1556.5	1558.0	1559.6	1561.2	1562.8
175°	1565.3	1563.0	1562.8	1562.5	1562.2	1562.0	1562.6	1564.2	1565.7	1567.3	1568.8
177.5°	1568.6	1567.0	1566.6	1566.1	1565.7	1565.3	1565.8	1567.3	1568.7	1570.2	1571.7
180°	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8



TEST NUMBER: P332919-840

CATALOG NUMBER: SA4XXRDIP-C575D1205U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2
2.5°	981.2	984.0	987.1	993.1	998.2	1000.4	1004.8	1007.9	1006.9	1011.4	1019.0
5°	985.0	995.6	1007.8	1020.4	1034.5	1046.3	1055.8	1065.2	1072.7	1081.7	1095.1
7.5°	984.4	1003.3	1023.8	1046.3	1069.5	1089.5	1108.1	1127.0	1143.7	1162.1	1186.0
10°	981.9	1007.0	1032.6	1062.1	1091.6	1119.4	1144.6	1168.1	1190.5	1214.5	1244.8
12.5°	979.1	1007.9	1038.8	1074.3	1111.1	1144.6	1174.2	1208.1	1236.1	1267.0	1302.0
15°	966.5	1005.5	1047.5	1093.5	1137.5	1182.7	1223.1	1264.9	1303.7	1340.6	1384.6
17.5°	952.3	997.1	1046.7	1101.1	1154.0	1208.8	1256.9	1309.4	1349.1	1398.7	1439.6
20°	940.7	989.0	1042.0	1102.9	1163.1	1224.0	1277.0	1330.4	1375.2	1425.1	1477.0
22.5°	926.6	979.6	1037.0	1100.0	1163.1	1229.6	1288.3	1341.4	1396.9	1453.1	1506.5
25°	903.7	958.8	1019.7	1088.7	1161.0	1229.0	1291.9	1358.0	1417.6	1478.5	1526.5
27.5°	875.8	933.5	997.7	1069.0	1143.3	1212.8	1286.9	1357.3	1417.3	1475.9	1517.7
30°	853.4	914.3	976.0	1048.3	1125.3	1200.0	1279.3	1349.7	1412.9	1465.6	1489.1
32.5°	830.5	888.3	951.8	1025.0	1104.0	1184.3	1263.0	1334.9	1393.4	1425.0	1425.6
35°	790.5	844.8	910.8	982.7	1063.6	1150.8	1230.6	1301.3	1337.1	1339.9	1301.3
37.5°	747.0	796.8	859.1	931.1	1019.7	1106.5	1187.9	1235.1	1247.1	1207.1	1135.9
40°	715.9	761.8	822.0	895.9	983.9	1073.5	1147.7	1182.2	1169.7	1104.9	1025.5
42.5°	683.2	726.0	784.0	856.9	945.2	1035.7	1099.0	1117.5	1084.2	1009.4	916.5
45°	629.9	669.1	726.5	800.0	884.8	969.8	1017.6	1008.2	952.8	864.0	759.9
47.5°	574.3	612.3	663.9	731.8	818.8	892.0	924.4	896.1	817.2	719.5	634.8
50°	537.6	576.4	624.0	688.8	768.2	838.9	859.7	816.5	728.8	635.0	557.1
52.5°	501.4	534.6	581.2	643.8	719.7	779.5	790.5	740.7	650.3	566.1	497.2
55°	446.4	476.7	515.9	574.8	640.5	691.2	685.3	621.2	539.1	467.2	412.9
57.5°	393.1	416.0	452.2	507.5	565.1	599.2	577.5	523.0	446.5	387.6	341.8
60°	358.0	379.2	412.9	461.3	512.0	531.2	513.1	453.8	393.3	339.5	300.9
62.5°	324.7	343.4	372.4	417.3	458.2	469.6	450.3	398.5	344.0	298.0	266.1
65°	276.2	293.5	318.3	350.1	378.4	383.8	371.3	318.3	277.0	238.5	216.5
67.5°	232.3	243.6	263.0	290.4	305.5	308.7	284.4	251.1	214.7	191.1	174.5
70°	202.8	210.6	228.6	243.6	255.8	256.2	233.8	207.0	179.2	160.0	147.7
72.5°	174.1	181.7	195.4	205.6	214.9	211.9	191.4	170.3	147.7	133.2	124.1
75°	134.4	141.1	148.1	152.9	152.9	149.0	134.0	118.3	105.3	96.6	93.9
77.5°	97.7	103.2	105.5	104.8	103.4	97.3	87.9	77.6	72.9	68.9	66.8
80°	76.6	79.0	79.8	77.8	75.4	68.4	62.1	57.8	53.4	51.9	51.1
82.5°	56.9	58.9	56.9	57.4	52.2	46.4	42.9	41.4	39.6	39.0	38.2
85°	30.3	29.9	29.1	27.1	23.5	22.8	22.4	22.0	21.2	21.6	20.8
87.5°	11.6	11.3	10.6	10.9	11.3	11.1	11.9	12.3	12.7	12.7	13.6
90°	6.4	9.3	12.1	14.9	17.5	19.6	21.6	23.7	25.9	27.4	29.0
92.5°	14.9	15.1	15.2	15.5	16.6	18.6	20.7	22.8	24.8	26.5	28.0
95°	55.6	46.8	38.0	29.1	24.7	25.0	25.2	25.5	25.9	27.4	29.0
97.5°	142.6	148.1	153.6	159.2	147.3	118.3	89.2	60.1	31.0	31.1	31.3
100°	197.1	201.9	206.5	211.3	195.6	159.6	123.6	87.7	51.6	47.2	42.7
102.5°	257.8	261.3	264.7	268.1	267.5	262.9	258.1	253.5	248.7	201.0	153.1
105°	354.8	356.3	357.9	359.4	360.9	362.2	363.5	364.8	366.1	368.5	370.8
107.5°	445.8	446.6	447.3	448.1	449.4	451.1	452.9	454.6	456.5	457.6	458.8
110°	507.7	508.5	509.3	510.1	511.2	512.8	514.3	515.9	517.5	518.0	518.6



TEST NUMBER: P332919-840

CATALOG NUMBER: SA4XXRDIP-C575D1205U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	568.5	569.8	571.2	572.6	573.7	574.4	575.1	575.9	576.6	576.5	576.4
115°	660.2	661.1	661.8	662.6	662.9	662.6	662.4	662.1	661.8	662.4	662.9
117.5°	743.8	744.9	745.9	746.9	747.7	748.3	748.9	749.5	750.0	749.9	749.8
120°	800.1	801.2	802.2	803.2	803.7	803.4	803.1	802.8	802.6	803.1	803.7
122.5°	852.3	852.9	853.5	854.1	854.6	855.1	855.4	855.8	856.2	856.5	856.8
125°	928.1	929.1	930.1	931.2	931.4	930.9	930.4	929.9	929.4	930.1	930.9
127.5°	998.6	998.9	999.2	999.4	1000.1	1001.3	1002.5	1003.7	1004.9	1004.7	1004.6
130°	1044.6	1044.9	1045.1	1045.4	1045.9	1046.7	1047.4	1048.2	1049.0	1049.2	1049.6
132.5°	1087.0	1087.5	1088.0	1088.4	1089.2	1090.1	1091.2	1092.2	1093.2	1093.4	1093.7
135°	1149.7	1149.4	1149.1	1148.9	1149.3	1150.3	1151.3	1152.5	1153.5	1154.0	1154.5
137.5°	1206.2	1206.3	1206.4	1206.5	1207.1	1208.2	1209.4	1210.5	1211.6	1212.2	1212.8
140°	1243.1	1243.6	1244.3	1244.8	1245.3	1245.8	1246.3	1246.8	1247.4	1248.1	1248.9
142.5°	1276.5	1277.4	1278.3	1279.3	1279.9	1280.2	1280.5	1280.8	1281.1	1281.7	1282.3
145°	1326.8	1327.6	1328.3	1329.1	1329.5	1329.5	1329.5	1329.5	1329.5	1329.8	1330.0
147.5°	1367.6	1369.0	1370.5	1371.9	1372.5	1372.3	1372.0	1371.7	1371.5	1371.7	1371.9
150°	1396.2	1397.2	1398.4	1399.4	1399.8	1399.5	1399.3	1399.0	1398.7	1398.7	1398.7
152.5°	1420.5	1421.3	1422.1	1422.9	1423.1	1422.7	1422.2	1421.7	1421.3	1421.7	1422.1
155°	1454.1	1454.4	1454.6	1454.9	1454.6	1453.9	1453.1	1452.3	1451.5	1452.6	1453.6
157.5°	1482.6	1482.4	1482.3	1482.1	1481.6	1480.7	1479.9	1478.9	1478.0	1479.4	1480.8
160°	1498.8	1498.0	1497.3	1496.5	1496.0	1495.7	1495.4	1495.2	1494.9	1496.5	1498.0
162.5°	1513.7	1512.7	1511.7	1510.7	1510.1	1509.7	1509.5	1509.2	1509.0	1510.6	1512.2
165°	1532.4	1531.1	1529.7	1528.4	1527.8	1527.8	1527.8	1527.8	1527.8	1529.8	1532.0
167.5°	1547.3	1546.0	1544.6	1543.3	1542.5	1542.4	1542.2	1542.1	1541.9	1544.2	1546.5
170°	1555.6	1554.0	1552.5	1550.8	1550.2	1550.4	1550.7	1551.0	1551.3	1553.4	1555.4
172.5°	1561.2	1559.6	1558.0	1556.5	1555.8	1556.1	1556.4	1556.6	1556.9	1558.9	1561.0
175°	1567.3	1565.7	1564.2	1562.6	1562.0	1562.2	1562.5	1562.8	1563.0	1565.3	1567.7
177.5°	1570.2	1568.7	1567.3	1565.8	1565.3	1565.7	1566.1	1566.6	1567.0	1568.6	1570.3
180°	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8



TEST NUMBER: P332919-840
 CATALOG NUMBER: SA4XXRDIP-C575D1205U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	975.2	975.2	975.2	975.2	975.2	975.2	975.2
2.5°	1023.0	1024.3	1025.2	1028.3	1028.6	1031.5	1028.6
5°	1107.6	1113.2	1121.8	1130.4	1131.3	1136.7	1126.9
7.5°	1202.5	1215.3	1223.2	1237.2	1242.7	1246.2	1240.5
10°	1268.0	1279.7	1300.6	1310.8	1321.0	1322.5	1317.9
12.5°	1331.1	1349.8	1366.2	1385.6	1385.1	1399.0	1393.9
15°	1415.3	1434.5	1457.3	1478.9	1486.8	1486.8	1493.1
17.5°	1475.3	1510.7	1534.2	1551.2	1569.7	1573.0	1570.7
20°	1515.9	1554.0	1579.1	1601.1	1613.8	1617.3	1617.3
22.5°	1546.1	1578.5	1603.1	1622.9	1633.3	1637.4	1636.1
25°	1567.0	1594.9	1609.8	1615.7	1618.4	1617.6	1610.2
27.5°	1538.3	1537.1	1527.6	1509.5	1496.0	1487.7	1478.3
30°	1483.7	1463.2	1439.7	1413.7	1380.3	1354.7	1347.0
32.5°	1402.3	1356.3	1316.5	1273.2	1237.3	1211.7	1201.0
35°	1244.8	1172.0	1112.8	1060.9	1023.2	999.6	991.7
37.5°	1057.9	987.5	914.1	863.8	832.5	808.7	799.8
40°	939.1	862.4	798.4	751.2	719.0	695.9	695.5
42.5°	830.6	757.5	697.2	663.3	628.5	613.2	613.1
45°	680.1	621.6	570.5	543.8	523.0	510.4	506.9
47.5°	563.1	514.7	480.7	459.4	442.4	434.4	429.2
50°	497.5	455.0	427.9	409.4	400.0	389.8	389.0
52.5°	442.7	408.5	387.4	372.3	360.4	354.3	354.5
55°	372.1	345.0	330.0	318.6	309.2	304.5	302.6
57.5°	313.5	293.2	282.3	271.9	267.8	264.1	263.1
60°	277.0	263.3	253.1	244.8	238.9	237.7	237.3
62.5°	246.8	232.5	225.4	219.0	214.7	212.9	212.2
65°	203.5	192.9	186.6	181.6	180.0	177.2	176.8
67.5°	164.1	157.7	153.6	150.1	147.8	147.7	147.7
70°	139.9	136.3	132.8	130.9	129.7	128.9	128.9
72.5°	119.2	116.5	113.6	112.6	112.4	111.6	111.3
75°	90.8	88.1	88.4	86.4	84.8	82.9	81.7
77.5°	64.3	62.4	62.0	61.8	60.4	60.2	60.8
80°	49.9	48.0	47.6	48.0	47.6	46.4	46.4
82.5°	38.0	36.4	36.0	35.6	35.2	35.6	35.0
85°	20.4	19.7	19.7	19.7	20.4	20.0	19.7
87.5°	13.3	13.3	13.8	13.6	13.7	13.5	13.9
90°	30.5	32.1	33.1	33.6	34.1	34.6	35.2
92.5°	29.6	31.1	32.0	32.1	32.2	32.3	32.4
95°	30.5	32.1	33.0	33.2	33.5	33.7	34.0
97.5°	31.4	31.6	31.8	32.1	32.3	32.6	32.8
100°	38.4	33.9	31.8	32.1	32.3	32.6	32.8
102.5°	105.3	57.5	33.6	33.6	33.7	33.7	33.8
105°	373.1	375.5	371.9	362.5	353.1	343.9	334.5
107.5°	459.9	461.0	462.1	463.1	464.1	465.0	466.1
110°	519.1	519.6	520.2	521.0	521.8	522.6	523.3



TEST NUMBER: P332919-840

CATALOG NUMBER: SA4XXRDIP-C575D1205U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	576.3	576.2	576.6	577.6	578.7	579.7	580.6
115°	663.4	663.9	664.2	664.2	664.2	664.2	664.2
117.5°	749.7	749.6	749.5	749.4	749.3	749.2	749.1
120°	804.2	804.7	804.7	804.2	803.7	803.1	802.6
122.5°	857.1	857.4	857.3	856.8	856.3	855.7	855.2
125°	931.7	932.5	933.0	933.2	933.5	933.8	934.0
127.5°	1004.4	1004.3	1004.1	1003.9	1003.7	1003.5	1003.3
130°	1049.9	1050.1	1050.2	1050.2	1050.2	1050.2	1050.2
132.5°	1094.0	1094.2	1094.2	1094.0	1093.8	1093.6	1093.4
135°	1155.0	1155.6	1156.1	1156.6	1157.1	1157.6	1158.1
137.5°	1213.4	1214.0	1214.2	1214.1	1213.9	1213.7	1213.6
140°	1249.7	1250.5	1251.0	1251.2	1251.5	1251.7	1252.0
142.5°	1282.8	1283.4	1283.7	1283.8	1283.8	1283.9	1283.9
145°	1330.3	1330.5	1330.9	1331.4	1331.9	1332.5	1333.0
147.5°	1372.1	1372.3	1372.5	1372.8	1373.1	1373.3	1373.6
150°	1398.7	1398.7	1398.9	1399.1	1399.4	1399.7	1399.9
152.5°	1422.5	1422.9	1423.0	1422.9	1422.7	1422.6	1422.4
155°	1454.6	1455.7	1455.8	1455.0	1454.2	1453.5	1452.7
157.5°	1482.1	1483.5	1483.5	1482.1	1480.8	1479.4	1478.0
160°	1499.6	1501.2	1501.2	1499.6	1498.0	1496.5	1494.9
162.5°	1513.7	1515.3	1515.2	1513.4	1511.7	1509.8	1508.0
165°	1534.1	1536.1	1536.0	1533.7	1531.3	1528.9	1526.6
167.5°	1548.7	1551.1	1550.8	1548.3	1545.7	1543.1	1540.4
170°	1557.5	1559.6	1559.3	1556.7	1554.1	1551.6	1548.9
172.5°	1563.2	1565.2	1564.9	1562.1	1559.2	1556.4	1553.6
175°	1570.0	1572.4	1572.0	1568.8	1565.7	1562.6	1559.4
177.5°	1572.0	1573.7	1573.3	1570.7	1568.2	1565.7	1563.3
180°	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8

(END OF REPORT)