

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332922-840

Luminaire Tested: **SA4XXRDIP-C575D1205U840-4F0-1E-UDD-F**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332922-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXRDIP-C575D1205U840-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1205 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7228.7 lumens  
Efficiency: N/A  
Efficacy: 146.3 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 49.4  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332922-840  
CATALOG NUMBER: SA4XXRDIP-C575D1205U840-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332922-840

CATALOG NUMBER: SA4XXRDIP-C575D1205U840-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40	33
1	94	90	86	83	85	81	78	75	65	63	61	50	48	47	36	35	34	28
2	86	79	73	68	77	71	66	62	57	54	51	44	42	40	32	30	29	24
3	78	69	62	57	70	63	57	52	50	46	43	39	36	34	28	27	25	20
4	72	61	54	48	64	56	49	44	45	40	36	35	32	29	25	23	22	18
5	66	55	47	41	59	50	43	38	40	35	31	31	28	25	23	21	19	15
6	61	49	41	36	54	44	38	33	36	31	27	28	25	22	21	19	17	14
7	56	44	36	31	50	40	33	29	33	28	24	26	22	19	19	17	15	12
8	52	40	32	27	47	36	30	25	30	25	21	23	20	17	17	15	13	11
9	48	36	29	24	43	33	27	23	27	22	19	21	18	16	16	14	12	10
10	45	33	26	22	41	30	24	20	25	20	17	20	16	14	15	13	11	9

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	8285	8285	8285
5°	8304	8203	8253
10°	8252	8104	8104
15°	8157	7934	7875
20°	8027	7710	7568
25°	7861	7448	7259
30°	7699	7171	6871
35°	7521	6885	6482
40°	7304	6559	6062
45°	7106	6235	5634
50°	6880	5863	5181
55°	6636	5475	4690
60°	6370	5050	4187
65°	6124	4518	3692
70°	5769	3932	3135
75°	5321	3260	2548
80°	4640	2483	2338
85°	3927	2251	2112



TEST NUMBER: P332922-840

CATALOG NUMBER: SA4XXRDIP-C575D1205U840-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	96.4	1.3
10°-20°	268.8	3.7
20°-30°	388.2	5.4
30°-40°	440.0	6.1
40°-50°	424.9	5.9
50°-60°	353.4	4.9
60°-70°	244.0	3.4
70°-80°	123.7	1.7
80°-90°	36.3	0.5
90°-100°	53.7	0.7
100°-110°	342.1	4.7
110°-120°	654.5	9.1
120°-130°	830.8	11.5
130°-140°	888.9	12.3
140°-150°	831.2	11.5
150°-160°	670.3	9.3
160°-170°	432.4	6.0
170°-180°	149.0	2.1
0°-30°	753.5	10.4
0°-40°	1193.5	16.5
0°-60°	1971.8	27.3
0°-90°	2375.7	32.9
90°-120°	1050.3	14.5
90°-150°	3601.3	49.8
90°-180°	4853.0	67.1
0°-180°	7228.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1026	1026	1026	1026	1026	
5°	1025	1021	1012	1020	1018	97
15°	976	968	949	948	942	275
25°	882	867	836	823	815	406
35°	763	737	699	673	658	477
45°	622	592	546	509	494	480
55°	472	439	389	350	333	422
65°	321	286	236	204	193	317
75°	171	141	104	87	82	180
85°	42	28	24	23	23	48
90°	4	16	26	33	35	5
95°	64	27	26	33	34	83
105°	353	360	366	374	334	370
115°	659	663	662	664	664	649
125°	927	931	929	933	934	827
135°	1150	1149	1154	1156	1158	886
145°	1326	1329	1330	1331	1333	828
155°	1454	1455	1452	1456	1453	670
165°	1534	1528	1528	1536	1527	433
175°	1569	1562	1563	1572	1559	149
180°	1569	1569	1569	1569	1569	



TEST NUMBER: P332922-840

CATALOG NUMBER: SA4XXRDIP-C575D1205U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1026.3	1026.3	1026.3	1026.3	1026.3	1026.3	1026.3	1026.3	1026.3	1026.3	1026.3
2.5°	1028.9	1028.2	1027.7	1027.1	1026.6	1025.5	1024.0	1022.5	1020.9	1019.4	1020.9
5°	1024.7	1024.0	1023.3	1022.6	1022.0	1020.6	1018.4	1016.3	1014.2	1012.2	1013.9
7.5°	1015.4	1014.7	1014.0	1013.3	1012.5	1010.8	1008.0	1005.3	1002.6	999.9	1001.0
10°	1006.6	1005.8	1004.9	1004.0	1003.2	1001.2	998.0	994.8	991.7	988.6	989.3
12.5°	995.3	994.3	993.3	992.3	991.3	989.0	985.2	981.5	977.9	974.1	974.5
15°	976.0	974.4	972.9	971.3	969.7	966.7	962.4	958.1	953.6	949.3	949.0
17.5°	952.6	950.3	948.1	945.7	943.5	939.8	934.5	929.3	924.0	918.8	917.9
20°	934.3	932.1	929.8	927.6	925.2	921.2	915.2	909.3	903.3	897.5	896.1
22.5°	914.2	911.7	909.2	906.6	904.0	899.6	893.2	886.9	880.5	874.1	872.0
25°	882.5	879.4	876.2	873.0	869.9	864.7	857.6	850.4	843.2	836.2	833.1
27.5°	849.2	845.3	841.3	837.4	833.3	827.6	819.9	812.3	804.7	797.0	793.3
30°	825.9	821.5	817.2	812.8	808.5	802.1	794.0	785.8	777.5	769.3	765.0
32.5°	801.4	796.5	791.5	786.6	781.7	775.0	766.5	758.0	749.5	741.0	736.0
35°	763.1	757.5	751.8	746.3	740.7	733.6	724.8	716.1	707.3	698.6	692.7
37.5°	722.1	716.3	710.5	704.8	698.9	691.3	681.6	671.9	662.3	652.6	645.9
40°	693.1	687.3	681.6	675.8	670.0	662.2	652.3	642.3	632.4	622.4	615.0
42.5°	665.4	659.4	653.4	647.3	641.3	633.1	622.7	612.3	602.0	591.6	584.1
45°	622.4	615.9	609.5	603.0	596.5	588.0	577.5	567.1	556.6	546.1	537.6
47.5°	577.9	571.3	564.5	557.8	551.2	542.4	531.5	520.7	509.8	498.9	490.0
50°	547.8	540.9	534.1	527.3	520.5	511.5	500.3	489.2	478.0	466.8	458.1
52.5°	516.9	510.3	503.6	497.0	490.2	481.2	469.7	458.3	446.8	435.4	426.5
55°	471.5	464.5	457.6	450.5	443.5	434.3	423.0	411.7	400.3	389.0	379.9
57.5°	426.6	419.3	412.0	404.8	397.5	388.3	377.1	365.9	354.8	343.6	334.4
60°	394.5	387.5	380.5	373.5	366.6	357.5	346.3	335.1	324.0	312.8	303.7
62.5°	365.6	358.3	351.0	343.8	336.5	327.2	315.7	304.3	292.8	281.3	273.0
65°	320.6	313.2	305.6	298.1	290.5	281.2	270.0	258.9	247.7	236.5	229.0
67.5°	274.0	266.7	259.5	252.4	245.2	236.4	226.0	215.6	205.3	194.9	188.4
70°	244.4	237.0	229.7	222.4	215.1	206.4	196.4	186.5	176.5	166.6	160.9
72.5°	213.0	206.3	199.7	193.1	186.4	178.4	169.1	159.7	150.2	140.8	135.9
75°	170.6	164.1	157.6	151.2	144.7	137.3	129.2	120.9	112.7	104.5	100.5
77.5°	127.4	122.0	116.5	111.0	105.5	99.5	92.8	86.2	79.6	72.9	70.6
80°	99.8	94.7	89.7	84.6	79.6	74.4	69.2	63.9	58.7	53.4	52.9
82.5°	75.9	71.3	66.7	62.0	57.4	53.5	50.5	47.5	44.5	41.5	41.1
85°	42.4	39.0	35.4	31.9	28.5	26.5	26.0	25.4	24.8	24.3	24.0
87.5°	15.1	14.6	14.0	13.5	13.0	12.8	13.1	13.4	13.7	13.9	14.1
90°	3.5	6.4	9.3	12.1	14.9	17.5	19.6	21.6	23.7	25.9	27.4
92.5°	14.7	14.9	15.1	15.2	15.5	16.6	18.6	20.7	22.8	24.8	26.5
95°	64.5	55.6	46.8	38.0	29.1	24.7	25.0	25.2	25.5	25.9	27.4
97.5°	137.0	142.6	148.1	153.6	159.2	147.3	118.3	89.2	60.1	31.0	31.1
100°	192.5	197.1	201.9	206.5	211.3	195.6	159.6	123.6	87.7	51.6	47.2
102.5°	254.4	257.8	261.3	264.7	268.1	267.5	262.9	258.1	253.5	248.7	201.0
105°	353.1	354.8	356.3	357.9	359.4	360.9	362.2	363.5	364.8	366.1	368.5
107.5°	444.9	445.8	446.6	447.3	448.1	449.4	451.1	452.9	454.6	456.5	457.6
110°	507.0	507.7	508.5	509.3	510.1	511.2	512.8	514.3	515.9	517.5	518.0



TEST NUMBER: P332922-840

CATALOG NUMBER: SA4XXRDIP-C575D1205U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	567.0	568.5	569.8	571.2	572.6	573.7	574.4	575.1	575.9	576.6	576.5
115°	659.4	660.2	661.1	661.8	662.6	662.9	662.6	662.4	662.1	661.8	662.4
117.5°	742.8	743.8	744.9	745.9	746.9	747.7	748.3	748.9	749.5	750.0	749.9
120°	799.1	800.1	801.2	802.2	803.2	803.7	803.4	803.1	802.8	802.6	803.1
122.5°	851.6	852.3	852.9	853.5	854.1	854.6	855.1	855.4	855.8	856.2	856.5
125°	927.0	928.1	929.1	930.1	931.2	931.4	930.9	930.4	929.9	929.4	930.1
127.5°	998.4	998.6	998.9	999.2	999.4	1000.1	1001.3	1002.5	1003.7	1004.9	1004.7
130°	1044.3	1044.6	1044.9	1045.1	1045.4	1045.9	1046.7	1047.4	1048.2	1049.0	1049.2
132.5°	1086.6	1087.0	1087.5	1088.0	1088.4	1089.2	1090.1	1091.2	1092.2	1093.2	1093.4
135°	1149.9	1149.7	1149.4	1149.1	1148.9	1149.3	1150.3	1151.3	1152.5	1153.5	1154.0
137.5°	1206.1	1206.2	1206.3	1206.4	1206.5	1207.1	1208.2	1209.4	1210.5	1211.6	1212.2
140°	1242.6	1243.1	1243.6	1244.3	1244.8	1245.3	1245.8	1246.3	1246.8	1247.4	1248.1
142.5°	1275.5	1276.5	1277.4	1278.3	1279.3	1279.9	1280.2	1280.5	1280.8	1281.1	1281.7
145°	1326.0	1326.8	1327.6	1328.3	1329.1	1329.5	1329.5	1329.5	1329.5	1329.5	1329.8
147.5°	1366.0	1367.6	1369.0	1370.5	1371.9	1372.5	1372.3	1372.0	1371.7	1371.5	1371.7
150°	1395.2	1396.2	1397.2	1398.4	1399.4	1399.8	1399.5	1399.3	1399.0	1398.7	1398.7
152.5°	1419.6	1420.5	1421.3	1422.1	1422.9	1423.1	1422.7	1422.2	1421.7	1421.3	1421.7
155°	1453.9	1454.1	1454.4	1454.6	1454.9	1454.6	1453.9	1453.1	1452.3	1451.5	1452.6
157.5°	1482.7	1482.6	1482.4	1482.3	1482.1	1481.6	1480.7	1479.9	1478.9	1478.0	1479.4
160°	1499.6	1498.8	1498.0	1497.3	1496.5	1496.0	1495.7	1495.4	1495.2	1494.9	1496.5
162.5°	1514.6	1513.7	1512.7	1511.7	1510.7	1510.1	1509.7	1509.5	1509.2	1509.0	1510.6
165°	1533.7	1532.4	1531.1	1529.7	1528.4	1527.8	1527.8	1527.8	1527.8	1527.8	1529.8
167.5°	1548.6	1547.3	1546.0	1544.6	1543.3	1542.5	1542.4	1542.2	1542.1	1541.9	1544.2
170°	1557.1	1555.6	1554.0	1552.5	1550.8	1550.2	1550.4	1550.7	1551.0	1551.3	1553.4
172.5°	1562.8	1561.2	1559.6	1558.0	1556.5	1555.8	1556.1	1556.4	1556.6	1556.9	1558.9
175°	1568.8	1567.3	1565.7	1564.2	1562.6	1562.0	1562.2	1562.5	1562.8	1563.0	1565.3
177.5°	1571.7	1570.2	1568.7	1567.3	1565.8	1565.3	1565.7	1566.1	1566.6	1567.0	1568.6
180°	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8



TEST NUMBER: P332922-840

CATALOG NUMBER: SA4XXRDIP-C575D1205U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1026.3	1026.3	1026.3	1026.3	1026.3	1026.3	1026.3	1026.3
2.5°	1022.5	1024.0	1025.5	1026.2	1026.1	1025.9	1025.8	1025.7
5°	1015.6	1017.4	1019.2	1019.9	1019.5	1019.2	1018.8	1018.4
7.5°	1002.1	1003.2	1004.4	1004.6	1004.1	1003.5	1003.0	1002.4
10°	990.0	990.7	991.4	991.4	990.7	990.0	989.3	988.6
12.5°	974.9	975.3	975.8	975.5	974.5	973.6	972.6	971.6
15°	948.6	948.3	947.9	947.2	945.8	944.6	943.4	942.2
17.5°	916.9	915.8	914.8	913.4	911.6	909.8	907.9	906.1
20°	894.6	893.2	891.8	890.0	887.8	885.4	883.2	880.9
22.5°	870.0	867.9	865.8	863.8	861.9	860.1	858.3	856.4
25°	830.2	827.2	824.3	821.9	820.1	818.4	816.7	814.9
27.5°	789.6	786.0	782.3	779.2	776.7	774.2	771.7	769.2
30°	760.6	756.2	751.8	748.3	745.5	742.7	739.9	737.1
32.5°	730.9	725.9	720.7	716.9	714.3	711.7	708.9	706.3
35°	686.7	680.8	674.9	670.3	667.2	664.0	660.9	657.7
37.5°	639.2	632.7	626.0	621.2	617.9	614.8	611.7	608.5
40°	607.7	600.4	593.0	587.8	584.6	581.5	578.3	575.2
42.5°	576.6	569.2	561.7	556.3	553.0	549.8	546.4	543.2
45°	529.1	520.5	511.9	506.0	502.9	499.8	496.7	493.5
47.5°	481.1	472.2	463.3	457.2	453.7	450.3	446.9	443.3
50°	449.3	440.6	431.8	425.9	422.5	419.2	415.9	412.5
52.5°	417.6	408.7	399.9	393.7	390.2	386.8	383.3	379.9
55°	370.8	361.7	352.6	346.5	343.2	339.8	336.5	333.2
57.5°	325.1	315.9	306.7	300.8	298.3	295.8	293.3	290.7
60°	294.6	285.5	276.4	270.5	267.7	264.9	262.2	259.3
62.5°	264.6	256.2	247.8	242.5	240.2	238.0	235.8	233.6
65°	221.6	214.0	206.5	201.7	199.7	197.5	195.4	193.3
67.5°	182.0	175.5	169.1	164.7	162.4	160.1	157.7	155.4
70°	155.1	149.4	143.5	139.8	138.0	136.3	134.5	132.8
72.5°	131.0	126.0	121.1	117.9	116.2	114.6	113.0	111.4
75°	96.4	92.5	88.5	85.9	84.8	83.8	82.8	81.7
77.5°	68.3	65.9	63.5	62.2	61.9	61.6	61.3	61.0
80°	52.4	51.9	51.3	51.0	50.8	50.6	50.5	50.3
82.5°	40.7	40.3	40.0	39.7	39.5	39.3	39.2	39.0
85°	23.6	23.3	22.9	22.8	22.8	22.8	22.8	22.8
87.5°	14.3	14.4	14.6	14.8	15.1	15.3	15.6	15.9
90°	29.0	30.5	32.1	33.1	33.6	34.1	34.6	35.2
92.5°	28.0	29.6	31.1	32.0	32.1	32.2	32.3	32.4
95°	29.0	30.5	32.1	33.0	33.2	33.5	33.7	34.0
97.5°	31.3	31.4	31.6	31.8	32.1	32.3	32.6	32.8
100°	42.7	38.4	33.9	31.8	32.1	32.3	32.6	32.8
102.5°	153.1	105.3	57.5	33.6	33.6	33.7	33.7	33.8
105°	370.8	373.1	375.5	371.9	362.5	353.1	343.9	334.5
107.5°	458.8	459.9	461.0	462.1	463.1	464.1	465.0	466.1
110°	518.6	519.1	519.6	520.2	521.0	521.8	522.6	523.3





TEST NUMBER: P332922-840

CATALOG NUMBER: SA4XXRDIP-C575D1205U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	576.4	576.3	576.2	576.6	577.6	578.7	579.7	580.6
115°	662.9	663.4	663.9	664.2	664.2	664.2	664.2	664.2
117.5°	749.8	749.7	749.6	749.5	749.4	749.3	749.2	749.1
120°	803.7	804.2	804.7	804.7	804.2	803.7	803.1	802.6
122.5°	856.8	857.1	857.4	857.3	856.8	856.3	855.7	855.2
125°	930.9	931.7	932.5	933.0	933.2	933.5	933.8	934.0
127.5°	1004.6	1004.4	1004.3	1004.1	1003.9	1003.7	1003.5	1003.3
130°	1049.6	1049.9	1050.1	1050.2	1050.2	1050.2	1050.2	1050.2
132.5°	1093.7	1094.0	1094.2	1094.2	1094.0	1093.8	1093.6	1093.4
135°	1154.5	1155.0	1155.6	1156.1	1156.6	1157.1	1157.6	1158.1
137.5°	1212.8	1213.4	1214.0	1214.2	1214.1	1213.9	1213.7	1213.6
140°	1248.9	1249.7	1250.5	1251.0	1251.2	1251.5	1251.7	1252.0
142.5°	1282.3	1282.8	1283.4	1283.7	1283.8	1283.8	1283.9	1283.9
145°	1330.0	1330.3	1330.5	1330.9	1331.4	1331.9	1332.5	1333.0
147.5°	1371.9	1372.1	1372.3	1372.5	1372.8	1373.1	1373.3	1373.6
150°	1398.7	1398.7	1398.7	1398.9	1399.1	1399.4	1399.7	1399.9
152.5°	1422.1	1422.5	1422.9	1423.0	1422.9	1422.7	1422.6	1422.4
155°	1453.6	1454.6	1455.7	1455.8	1455.0	1454.2	1453.5	1452.7
157.5°	1480.8	1482.1	1483.5	1483.5	1482.1	1480.8	1479.4	1478.0
160°	1498.0	1499.6	1501.2	1501.2	1499.6	1498.0	1496.5	1494.9
162.5°	1512.2	1513.7	1515.3	1515.2	1513.4	1511.7	1509.8	1508.0
165°	1532.0	1534.1	1536.1	1536.0	1533.7	1531.3	1528.9	1526.6
167.5°	1546.5	1548.7	1551.1	1550.8	1548.3	1545.7	1543.1	1540.4
170°	1555.4	1557.5	1559.6	1559.3	1556.7	1554.1	1551.6	1548.9
172.5°	1561.0	1563.2	1565.2	1564.9	1562.1	1559.2	1556.4	1553.6
175°	1567.7	1570.0	1572.4	1572.0	1568.8	1565.7	1562.6	1559.4
177.5°	1570.3	1572.0	1573.7	1573.3	1570.7	1568.2	1565.7	1563.3
180°	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8	1568.8

(END OF REPORT)