

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332509-940

Luminaire Tested: **SA4XXDIP-C350D810U940-4F0-1E-UDD-A1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332509-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C350D810U940-4F0-1E-UDD-A1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 810 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3909.1 lumens
Efficiency: N/A
Efficacy: 125.3 lumens/watt
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332509-940

CATALOG NUMBER: SA4XXDIP-C350D810U940-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P332509-940

CATALOG NUMBER: SA4XXDIP-C350D810U940-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	43	43	43	36
1	95	91	87	83	86	82	79	76	66	64	62	52	50	49	38	38	37	31
2	86	79	73	68	78	72	67	63	58	55	52	46	43	41	34	33	31	26
3	79	70	63	57	71	63	57	53	52	47	44	41	38	35	30	28	27	22
4	72	62	54	48	65	56	50	45	46	41	37	36	33	30	27	25	23	19
5	66	55	47	41	60	50	43	38	41	36	32	32	29	26	25	22	20	17
6	61	49	41	36	55	45	38	33	37	32	28	29	26	23	22	20	18	15
7	56	44	37	31	51	41	34	29	33	28	25	27	23	20	20	18	16	13
8	52	40	33	28	47	37	30	26	30	25	22	24	21	18	19	16	14	12
9	49	37	29	25	44	34	27	23	28	23	19	22	19	16	17	15	13	11
10	45	34	27	22	41	31	25	20	26	21	17	21	17	15	16	13	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4112	4112	4112	4112
5°	4843	4123	3639	4123
10°	5799	4105	3277	4105
15°	6861	4064	3010	4064
20°	7640	4021	2770	4021
25°	7764	3958	2605	3958
30°	6605	3899	2553	3899
35°	5078	3802	2553	3802
40°	3959	3687	2602	3687
45°	3301	3515	2646	3515
50°	2905	3304	2735	3304
55°	2662	3054	2846	3054
60°	2493	2827	2977	2827
65°	2321	2575	3089	2575
70°	2122	2325	3158	2325
75°	1896	2046	3119	2046
80°	1590	1678	3022	1678
85°	1176	1213	2890	1213



TEST NUMBER: P332509-940

CATALOG NUMBER: SA4XXDIP-C350D810U940-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.6	1.3
10°-20°	153.0	3.9
20°-30°	242.6	6.2
30°-40°	270.0	6.9
40°-50°	245.7	6.3
50°-60°	200.8	5.1
60°-70°	143.4	3.7
70°-80°	78.9	2.0
80°-90°	24.2	0.6
90°-100°	59.5	1.5
100°-110°	176.1	4.5
110°-120°	298.9	7.6
120°-130°	394.2	10.1
130°-140°	442.7	11.3
140°-150°	435.0	11.1
150°-160°	365.9	9.4
160°-170°	243.4	6.2
170°-180°	85.2	2.2
0°-30°	445.2	11.4
0°-40°	715.2	18.3
0°-60°	1161.7	29.7
0°-90°	1408.3	36.0
90°-120°	534.5	13.7
90°-150°	1806.3	46.2
90°-180°	2501.0	64.0
0°-180°	3909.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	509	509	509	509	509	
5°	598	509	449	509	598	61
15°	821	486	360	486	821	232
25°	872	444	292	444	872	384
35°	515	386	259	386	515	327
45°	289	308	232	308	289	228
55°	189	217	202	217	189	171
65°	122	135	162	135	122	120
75°	61	66	100	66	61	65
85°	13	13	31	13	13	16
90°	21	2	21	2	21	11
95°	55	42	55	42	55	57
105°	170	162	170	162	170	179
115°	301	304	301	304	301	298
125°	439	443	439	443	439	392
135°	572	571	572	571	572	441
145°	694	694	694	694	694	435
155°	794	795	794	795	794	366
165°	863	865	863	865	863	243
175°	896	900	896	900	896	85
180°	901	901	901	901	901	



TEST NUMBER: P332509-940

CATALOG NUMBER: SA4XXDIP-C350D810U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4
2.5°	542.2	542.1	540.4	540.0	538.9	537.3	537.0	534.2	528.9	526.3	525.7
5°	597.6	601.9	596.4	595.3	594.7	587.7	584.2	580.0	570.2	564.5	560.1
7.5°	663.9	664.3	661.9	660.0	654.6	648.5	639.4	629.7	618.1	606.2	597.1
10°	707.4	709.1	706.3	706.0	695.2	688.4	674.9	663.5	650.4	635.9	622.6
12.5°	753.3	751.0	749.6	740.6	738.5	726.2	710.5	698.8	678.6	661.8	644.2
15°	820.9	816.3	813.3	800.9	794.8	777.7	761.0	748.1	721.8	696.6	677.6
17.5°	860.6	865.2	858.4	853.3	837.5	825.5	808.4	781.4	760.8	729.6	705.6
20°	889.3	889.7	885.9	880.7	868.3	853.0	834.5	804.9	780.2	749.2	716.2
22.5°	897.1	897.2	895.5	890.6	881.2	868.9	850.2	825.5	795.6	761.9	728.9
25°	871.6	870.8	872.6	878.2	874.6	870.8	860.0	841.6	813.8	778.1	742.6
27.5°	776.9	782.7	793.4	806.9	819.9	829.8	832.6	828.8	811.6	782.3	745.1
30°	708.6	715.9	723.9	737.4	763.6	778.6	795.0	807.4	800.5	777.0	742.4
32.5°	633.7	635.5	647.4	662.7	686.7	715.5	741.6	767.0	775.3	763.0	734.1
35°	515.3	518.4	531.2	546.4	575.7	611.0	650.2	685.3	714.2	725.8	711.0
37.5°	420.5	429.0	438.1	454.4	480.3	512.0	552.8	598.2	641.2	670.1	675.0
40°	375.7	380.9	387.4	399.9	421.9	453.1	488.1	540.0	585.9	627.2	640.7
42.5°	340.2	343.3	347.3	358.6	375.2	406.4	438.4	484.0	529.9	579.4	602.1
45°	289.1	292.3	299.1	305.6	318.3	339.7	369.5	407.1	453.3	501.0	542.8
47.5°	252.3	254.2	258.2	265.3	276.1	290.3	314.4	345.8	388.6	435.0	479.5
50°	231.3	233.0	236.1	242.5	250.7	263.4	283.2	312.5	346.1	392.7	436.4
52.5°	214.7	215.4	217.8	222.0	228.6	239.2	255.6	279.8	311.0	352.6	396.1
55°	189.1	189.9	192.1	195.2	200.9	207.7	220.1	238.3	265.5	301.6	339.4
57.5°	168.0	168.6	170.3	171.6	176.3	181.7	191.4	204.3	224.9	255.6	289.3
60°	154.4	154.1	156.1	157.2	160.4	165.1	172.5	184.9	202.8	227.5	258.5
62.5°	141.3	140.7	142.5	143.9	145.7	149.6	155.7	165.4	180.0	202.3	229.2
65°	121.5	120.7	121.8	123.5	125.1	127.2	131.7	140.4	151.9	168.0	188.4
67.5°	101.7	102.6	102.8	103.6	104.6	107.5	110.5	116.6	124.8	137.7	155.0
70°	89.9	90.2	91.0	91.0	91.6	94.2	96.7	100.2	108.3	120.1	134.2
72.5°	78.1	79.0	78.6	79.3	79.8	81.5	83.3	86.8	93.5	102.4	114.3
75°	60.8	61.4	61.4	61.6	62.2	62.9	64.4	66.9	71.8	78.3	86.5
77.5°	44.3	44.4	44.7	45.5	45.5	46.5	47.5	49.6	52.0	56.4	61.5
80°	34.2	34.6	34.4	34.9	34.9	35.7	36.1	38.6	39.7	42.6	46.6
82.5°	25.1	25.5	25.4	26.0	26.4	26.6	27.1	28.2	29.2	31.8	33.4
85°	12.7	13.1	12.7	13.1	13.7	13.9	14.5	14.8	15.6	16.2	17.7
87.5°	7.9	8.4	8.3	8.4	8.6	8.7	8.6	8.3	8.8	8.8	9.3
90°	21.0	20.6	20.3	20.0	19.7	19.1	18.1	17.2	16.2	15.3	14.1
92.5°	30.9	30.8	30.6	30.4	30.2	29.9	29.2	28.7	28.2	27.6	26.8
95°	55.1	55.1	55.1	55.1	55.1	54.8	54.4	53.9	53.4	53.0	51.9
97.5°	86.3	86.3	86.3	86.3	86.3	86.1	85.4	84.9	84.4	83.8	82.5
100°	108.1	108.1	108.1	108.1	108.1	107.9	107.6	107.3	107.0	106.6	105.2
102.5°	132.6	132.5	132.3	132.2	132.1	131.8	131.3	131.0	130.5	130.1	128.9
105°	170.1	169.6	169.2	168.7	168.3	167.7	167.3	166.8	166.4	165.9	165.3
107.5°	206.6	206.7	206.7	206.7	206.8	206.5	206.1	205.7	205.3	204.8	204.7
110°	232.8	232.4	231.9	231.5	231.0	230.9	231.2	231.5	231.8	232.1	232.3



TEST NUMBER: P332509-940

CATALOG NUMBER: SA4XXDIP-C350D810U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	259.6	259.5	259.4	259.3	259.2	259.2	259.3	259.3	259.4	259.5	259.8
115°	301.1	301.3	301.5	301.7	301.8	301.9	302.1	302.2	302.4	302.6	302.8
117.5°	340.7	341.1	341.3	341.7	342.0	342.4	343.0	343.5	344.0	344.6	344.7
120°	370.9	370.6	370.2	370.0	369.6	369.9	370.6	371.4	372.2	373.0	373.4
122.5°	396.0	396.5	397.1	397.6	398.2	398.8	399.3	399.8	400.3	400.8	401.1
125°	439.2	439.5	439.8	440.1	440.4	440.8	441.0	441.4	441.7	442.0	442.1
127.5°	479.2	479.5	479.7	479.9	480.2	480.5	480.8	481.1	481.4	481.7	482.0
130°	505.4	506.0	506.7	507.3	507.9	508.4	508.6	509.0	509.3	509.6	509.6
132.5°	533.3	533.5	533.8	534.0	534.3	534.6	534.8	535.2	535.5	535.8	535.9
135°	571.7	572.1	572.6	573.0	573.5	573.9	574.2	574.5	574.8	575.2	575.2
137.5°	612.0	611.8	611.7	611.6	611.5	611.7	612.2	612.5	613.0	613.3	613.1
140°	636.5	636.6	636.8	636.9	637.1	637.2	637.4	637.6	637.8	637.8	637.8
142.5°	661.0	661.0	661.1	661.1	661.1	661.2	661.2	661.2	661.3	661.3	661.4
145°	694.4	694.8	695.3	695.7	696.2	696.5	696.7	696.8	697.0	697.1	697.0
147.5°	728.1	728.3	728.3	728.5	728.7	728.8	729.0	729.1	729.2	729.3	729.4
150°	748.7	748.9	749.0	749.2	749.3	749.4	749.4	749.4	749.4	749.4	749.4
152.5°	767.7	768.1	768.5	768.9	769.3	769.3	768.9	768.6	768.2	767.9	767.7
155°	794.1	794.6	795.2	795.9	796.5	796.5	795.9	795.2	794.6	794.1	794.2
157.5°	817.6	818.1	818.7	819.2	819.7	819.7	819.3	818.8	818.3	817.9	817.9
160°	831.0	831.8	832.5	833.3	834.1	834.2	833.7	833.3	832.9	832.4	832.5
162.5°	844.9	845.7	846.5	847.2	848.0	848.0	847.1	846.3	845.5	844.6	844.8
165°	863.1	863.6	864.2	864.9	865.5	865.4	864.4	863.5	862.6	861.7	861.9
167.5°	876.0	877.0	877.9	878.9	879.9	879.9	879.0	878.0	877.1	876.1	876.1
170°	883.2	884.3	885.5	886.5	887.6	887.7	886.7	885.8	884.8	884.0	883.8
172.5°	889.4	890.5	891.5	892.7	893.8	893.8	892.7	891.6	890.6	889.6	889.5
175°	895.8	896.9	898.0	899.0	900.2	900.2	899.0	898.0	896.9	895.8	896.0
177.5°	899.1	900.2	901.2	902.1	903.1	903.2	902.3	901.4	900.5	899.7	899.7
180°	901.3	901.3	901.3	901.3	901.3	901.3	901.3	901.3	901.3	901.3	901.3



TEST NUMBER: P332509-940

CATALOG NUMBER: SA4XXDIP-C350D810U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4
2.5°	525.8	523.4	521.7	520.4	516.7	514.5	512.8	510.5	507.7	504.9	501.3
5°	555.6	548.5	543.2	535.2	527.6	521.3	514.7	508.8	501.7	493.8	488.1
7.5°	587.0	576.3	562.7	550.8	537.4	525.8	515.5	504.9	493.8	483.0	473.2
10°	607.0	593.3	578.0	560.1	543.2	528.2	514.3	500.8	487.7	474.7	463.4
12.5°	628.4	611.3	588.8	567.8	548.9	528.9	512.1	495.5	479.7	466.0	453.0
15°	657.2	632.5	606.5	578.5	553.6	530.1	507.1	486.2	468.5	450.3	437.7
17.5°	674.8	644.3	614.7	585.3	555.2	525.6	500.8	476.7	454.5	436.5	420.5
20°	686.5	656.1	619.2	589.9	554.0	523.6	494.9	468.1	444.9	425.7	409.2
22.5°	696.6	661.6	624.6	585.9	550.3	518.0	486.6	459.7	436.0	415.7	399.9
25°	702.1	661.8	621.7	583.3	542.8	504.6	476.1	444.4	419.1	397.8	380.9
27.5°	702.8	659.6	614.2	571.6	529.8	494.2	458.3	429.9	403.7	381.1	364.9
30°	700.9	655.9	607.2	561.0	519.0	480.4	449.1	418.3	391.5	369.1	352.2
32.5°	694.9	648.2	598.1	549.1	505.6	467.8	435.6	406.3	380.1	358.1	340.4
35°	677.9	631.6	578.3	527.4	482.9	444.7	415.5	385.8	359.6	338.8	321.6
37.5°	651.1	609.4	555.1	502.5	458.7	420.4	391.5	364.6	341.0	319.8	302.3
40°	627.9	591.1	536.6	485.4	438.1	401.6	374.6	349.9	326.5	306.4	289.7
42.5°	601.0	569.0	518.8	464.5	418.8	382.2	355.9	333.7	311.7	293.1	276.4
45°	553.1	532.0	484.7	434.5	387.0	352.4	327.3	307.9	289.4	271.2	257.3
47.5°	498.1	487.6	447.8	400.1	355.1	320.9	299.2	281.2	264.9	249.6	237.3
50°	461.1	456.0	421.7	375.7	332.6	300.5	278.6	263.1	249.2	235.8	224.1
52.5°	424.6	424.5	393.4	351.3	311.5	280.6	258.8	244.4	232.4	221.4	211.0
55°	368.9	374.8	350.5	313.0	277.3	249.4	229.8	217.0	208.5	199.5	191.6
57.5°	317.7	327.5	307.5	274.4	244.6	219.0	201.9	192.3	183.2	177.7	172.0
60°	284.3	293.6	277.9	250.1	222.0	200.1	183.8	175.1	167.4	163.5	159.5
62.5°	254.6	262.8	251.3	225.4	201.1	179.9	166.2	157.9	152.7	148.6	145.9
65°	212.1	219.1	209.1	190.4	169.4	152.6	141.4	134.8	129.8	128.1	125.1
67.5°	171.5	177.8	172.5	156.5	139.7	126.9	118.2	111.9	108.9	107.5	105.3
70°	147.3	153.6	147.9	134.0	121.1	110.4	102.1	98.5	95.4	94.8	91.8
72.5°	126.9	131.2	125.5	114.6	103.6	94.5	88.1	84.4	82.8	81.6	80.0
75°	95.1	99.0	95.1	86.8	78.9	72.6	67.1	65.6	63.8	63.1	62.1
77.5°	67.3	70.6	67.8	62.5	56.6	51.7	48.8	46.9	46.5	45.4	45.9
80°	51.5	53.6	50.8	47.3	42.6	39.2	37.2	36.1	34.9	34.4	35.2
82.5°	37.0	37.9	36.5	34.1	30.7	28.4	27.0	25.8	25.5	25.6	25.6
85°	19.2	19.0	18.8	16.7	15.6	14.2	13.3	13.1	12.8	13.3	13.7
87.5°	9.0	8.9	8.5	7.5	6.7	5.8	5.4	4.8	5.4	5.8	6.3
90°	12.8	11.6	10.3	8.9	7.2	5.5	3.8	2.1	3.8	5.5	7.2
92.5°	25.9	25.0	24.2	22.7	20.8	18.8	16.9	14.9	16.9	18.8	20.8
95°	50.8	49.8	48.7	47.4	46.0	44.6	43.2	41.8	43.2	44.6	46.0
97.5°	81.2	80.0	78.7	77.5	76.4	75.3	74.2	73.0	74.2	75.3	76.4
100°	103.9	102.5	101.1	100.0	99.4	98.8	98.2	97.6	98.2	98.8	99.4
102.5°	127.5	126.3	125.0	124.2	124.0	123.8	123.5	123.2	123.5	123.8	124.0
105°	164.7	164.1	163.5	163.1	162.9	162.7	162.6	162.5	162.6	162.7	162.9
107.5°	204.6	204.6	204.5	204.3	204.1	203.9	203.8	203.6	203.8	203.9	204.1
110°	232.5	232.6	232.7	232.6	232.4	232.0	231.8	231.5	231.8	232.0	232.4



TEST NUMBER: P332509-940

CATALOG NUMBER: SA4XXDIP-C350D810U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	260.0	260.3	260.6	260.7	260.6	260.6	260.5	260.5	260.5	260.6	260.6
115°	303.2	303.4	303.8	304.0	304.0	304.0	304.0	304.0	304.0	304.0	304.0
117.5°	344.9	345.2	345.4	345.4	345.3	345.2	345.1	344.9	345.1	345.2	345.3
120°	373.9	374.3	374.8	374.8	374.2	373.5	372.9	372.3	372.9	373.5	374.2
122.5°	401.3	401.5	401.7	401.7	401.4	401.2	400.9	400.7	400.9	401.2	401.4
125°	442.3	442.5	442.6	442.6	442.6	442.6	442.6	442.6	442.6	442.6	442.6
127.5°	482.2	482.4	482.7	482.6	482.1	481.7	481.2	480.7	481.2	481.7	482.1
130°	509.6	509.6	509.6	509.3	508.9	508.5	508.0	507.5	508.0	508.5	508.9
132.5°	536.1	536.2	536.3	536.2	535.8	535.6	535.2	534.8	535.2	535.6	535.8
135°	575.2	575.2	575.2	574.7	573.7	572.8	571.9	571.0	571.9	572.8	573.7
137.5°	612.9	612.6	612.3	612.0	611.5	611.1	610.7	610.3	610.7	611.1	611.5
140°	637.8	637.8	637.8	637.8	637.4	637.1	636.8	636.5	636.8	637.1	637.4
142.5°	661.6	661.6	661.8	661.7	661.4	661.1	660.8	660.5	660.8	661.1	661.4
145°	696.8	696.7	696.5	696.2	695.5	694.9	694.3	693.7	694.3	694.9	695.5
147.5°	729.6	729.7	729.9	729.5	728.8	728.0	727.3	726.6	727.3	728.0	728.8
150°	749.4	749.4	749.4	749.1	748.5	747.9	747.3	746.6	747.3	747.9	748.5
152.5°	767.6	767.4	767.3	767.0	766.7	766.3	766.0	765.6	766.0	766.3	766.7
155°	794.3	794.5	794.6	794.7	794.7	794.7	794.7	794.7	794.7	794.7	794.7
157.5°	818.0	818.0	818.0	818.1	818.4	818.7	818.9	819.3	818.9	818.7	818.4
160°	832.7	832.9	832.9	833.1	833.3	833.5	833.6	833.7	833.6	833.5	833.3
162.5°	845.0	845.1	845.3	845.5	846.0	846.3	846.8	847.1	846.8	846.3	846.0
165°	862.3	862.6	862.9	863.3	863.7	864.2	864.7	865.1	864.7	864.2	863.7
167.5°	876.1	876.0	876.0	876.4	877.0	877.6	878.2	879.0	878.2	877.6	877.0
170°	883.7	883.5	883.3	883.7	884.4	885.2	886.0	886.7	886.0	885.2	884.4
172.5°	889.5	889.5	889.4	889.7	890.4	891.0	891.7	892.3	891.7	891.0	890.4
175°	896.1	896.3	896.4	896.9	897.7	898.4	899.2	900.0	899.2	898.4	897.7
177.5°	899.7	899.7	899.7	900.0	900.6	901.3	901.9	902.5	901.9	901.3	900.6
180°	901.3	901.3	901.3	901.3	901.3	901.3	901.3	901.3	901.3	901.3	901.3



TEST NUMBER: P332509-940

CATALOG NUMBER: SA4XXDIP-C350D810U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4
2.5°	499.6	498.1	496.0	492.9	490.4	487.7	487.0	486.0	488.0	486.3	485.8
5°	483.3	478.8	473.1	466.6	462.8	457.4	456.3	454.1	452.0	451.8	449.7
7.5°	465.9	459.4	451.9	445.3	439.2	433.1	429.2	428.4	425.3	423.4	421.3
10°	454.8	446.7	438.1	431.8	424.6	418.3	413.8	411.3	409.2	406.9	404.7
12.5°	441.7	433.1	426.0	419.1	410.6	405.8	398.5	394.1	393.7	393.7	388.3
15°	426.3	417.9	406.9	397.2	392.5	383.3	379.2	374.2	371.0	367.8	365.3
17.5°	408.8	398.2	389.7	378.5	369.7	362.3	357.0	354.0	349.2	344.7	341.5
20°	397.8	386.6	377.6	365.7	356.1	347.0	342.5	338.3	334.7	330.9	327.3
22.5°	386.6	375.0	363.9	352.4	343.4	333.8	329.5	323.8	320.4	318.3	314.7
25°	369.1	356.4	343.8	332.8	323.5	315.0	309.4	305.0	301.1	299.4	297.1
27.5°	350.0	337.4	325.2	312.7	302.2	296.0	291.5	288.2	286.0	283.7	282.7
30°	337.9	324.8	311.7	300.1	290.4	284.3	280.1	277.8	276.1	275.0	273.9
32.5°	325.6	312.6	298.9	288.3	279.6	274.1	270.9	268.6	267.8	267.4	267.0
35°	305.8	292.7	280.1	270.5	262.3	260.2	257.4	256.2	255.7	257.3	257.9
37.5°	286.7	274.6	262.9	253.7	248.3	245.2	244.2	244.3	245.8	247.1	248.6
40°	274.4	262.5	251.6	243.5	238.4	236.6	236.1	237.2	238.9	240.4	242.1
42.5°	262.3	250.7	240.8	233.3	229.7	227.9	228.2	229.3	231.7	233.4	235.9
45°	243.8	234.1	224.4	218.2	215.3	215.7	215.7	217.6	219.9	222.7	225.4
47.5°	226.2	216.4	208.5	203.3	201.8	201.4	202.6	205.1	208.4	211.8	215.6
50°	214.5	205.1	198.1	193.5	191.8	192.4	194.1	196.4	200.5	204.7	208.7
52.5°	202.4	193.9	187.5	183.2	182.0	183.2	184.9	188.5	192.1	196.6	201.4
55°	183.8	176.6	171.6	168.4	168.0	168.6	170.5	174.5	179.6	185.3	189.9
57.5°	165.3	159.3	154.6	152.5	152.7	153.3	156.4	161.1	166.6	172.6	178.6
60°	152.8	147.3	143.5	141.8	142.0	143.3	147.1	151.5	158.3	164.2	170.5
62.5°	141.0	136.2	132.5	131.0	130.7	133.5	137.1	141.7	148.5	155.1	161.9
65°	122.0	118.2	115.2	114.4	115.0	117.2	121.8	127.9	133.6	140.5	147.8
67.5°	103.4	100.3	98.3	98.6	99.4	102.5	106.4	111.6	118.2	125.4	132.4
70°	91.6	88.6	86.9	87.1	88.5	92.2	95.6	100.9	107.8	115.2	121.1
72.5°	79.5	77.5	76.0	76.9	78.1	80.7	85.0	90.2	96.4	103.3	109.5
75°	61.0	61.0	60.2	60.8	62.7	65.2	68.4	73.8	80.0	85.5	90.5
77.5°	45.2	44.8	45.3	46.1	47.2	50.2	53.9	57.8	62.3	67.9	72.1
80°	34.6	34.9	35.8	37.2	37.5	39.9	43.7	47.3	50.8	55.5	59.5
82.5°	26.0	26.2	26.8	28.4	28.8	31.3	33.7	37.3	40.6	43.7	47.0
85°	14.2	14.2	15.2	15.9	16.9	18.5	20.1	22.2	25.1	27.2	30.4
87.5°	7.2	7.5	8.4	9.0	9.7	10.8	11.3	13.4	14.3	15.2	16.9
90°	8.9	10.3	11.6	12.8	14.1	15.3	16.2	17.2	18.1	19.1	19.7
92.5°	22.7	24.2	25.0	25.9	26.8	27.6	28.2	28.7	29.2	29.9	30.2
95°	47.4	48.7	49.8	50.8	51.9	53.0	53.4	53.9	54.4	54.8	55.1
97.5°	77.5	78.7	80.0	81.2	82.5	83.8	84.4	84.9	85.4	86.1	86.3
100°	100.0	101.1	102.5	103.9	105.2	106.6	107.0	107.3	107.6	107.9	108.1
102.5°	124.2	125.0	126.3	127.5	128.9	130.1	130.5	131.0	131.3	131.8	132.1
105°	163.1	163.5	164.1	164.7	165.3	165.9	166.4	166.8	167.3	167.7	168.3
107.5°	204.3	204.5	204.6	204.6	204.7	204.8	205.3	205.7	206.1	206.5	206.8
110°	232.6	232.7	232.6	232.5	232.3	232.1	231.8	231.5	231.2	230.9	231.0



TEST NUMBER: P332509-940

CATALOG NUMBER: SA4XXDIP-C350D810U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	260.7	260.6	260.3	260.0	259.8	259.5	259.4	259.3	259.3	259.2	259.2
115°	304.0	303.8	303.4	303.2	302.8	302.6	302.4	302.2	302.1	301.9	301.8
117.5°	345.4	345.4	345.2	344.9	344.7	344.6	344.0	343.5	343.0	342.4	342.0
120°	374.8	374.8	374.3	373.9	373.4	373.0	372.2	371.4	370.6	369.9	369.6
122.5°	401.7	401.7	401.5	401.3	401.1	400.8	400.3	399.8	399.3	398.8	398.2
125°	442.6	442.6	442.5	442.3	442.1	442.0	441.7	441.4	441.0	440.8	440.4
127.5°	482.6	482.7	482.4	482.2	482.0	481.7	481.4	481.1	480.8	480.5	480.2
130°	509.3	509.6	509.6	509.6	509.6	509.6	509.3	509.0	508.6	508.4	507.9
132.5°	536.2	536.3	536.2	536.1	535.9	535.8	535.5	535.2	534.8	534.6	534.3
135°	574.7	575.2	575.2	575.2	575.2	575.2	574.8	574.5	574.2	573.9	573.5
137.5°	612.0	612.3	612.6	612.9	613.1	613.3	613.0	612.5	612.2	611.7	611.5
140°	637.8	637.8	637.8	637.8	637.8	637.8	637.8	637.6	637.4	637.2	637.1
142.5°	661.7	661.8	661.6	661.6	661.4	661.3	661.3	661.2	661.2	661.2	661.1
145°	696.2	696.5	696.7	696.8	697.0	697.1	697.0	696.8	696.7	696.5	696.2
147.5°	729.5	729.9	729.7	729.6	729.4	729.3	729.2	729.1	729.0	728.8	728.7
150°	749.1	749.4	749.4	749.4	749.4	749.4	749.4	749.4	749.4	749.4	749.3
152.5°	767.0	767.3	767.4	767.6	767.7	767.9	768.2	768.6	768.9	769.3	769.3
155°	794.7	794.6	794.5	794.3	794.2	794.1	794.6	795.2	795.9	796.5	796.5
157.5°	818.1	818.0	818.0	818.0	817.9	817.9	818.3	818.8	819.3	819.7	819.7
160°	833.1	832.9	832.9	832.7	832.5	832.4	832.9	833.3	833.7	834.2	834.1
162.5°	845.5	845.3	845.1	845.0	844.8	844.6	845.5	846.3	847.1	848.0	848.0
165°	863.3	862.9	862.6	862.3	861.9	861.7	862.6	863.5	864.4	865.4	865.5
167.5°	876.4	876.0	876.0	876.1	876.1	876.1	877.1	878.0	879.0	879.9	879.9
170°	883.7	883.3	883.5	883.7	883.8	884.0	884.8	885.8	886.7	887.7	887.6
172.5°	889.7	889.4	889.5	889.5	889.5	889.6	890.6	891.6	892.7	893.8	893.8
175°	896.9	896.4	896.3	896.1	896.0	895.8	896.9	898.0	899.0	900.2	900.2
177.5°	900.0	899.7	899.7	899.7	899.7	899.7	900.5	901.4	902.3	903.2	903.1
180°	901.3	901.3	901.3	901.3	901.3	901.3	901.3	901.3	901.3	901.3	901.3



TEST NUMBER: P332509-940

CATALOG NUMBER: SA4XXDIP-C350D810U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4
2.5°	485.4	485.2	483.9	483.8	483.9	485.2	485.4	485.8	486.3	488.0	486.0
5°	448.4	447.4	446.7	449.1	446.7	447.4	448.4	449.7	451.8	452.0	454.1
7.5°	420.5	419.7	417.9	417.2	417.9	419.7	420.5	421.3	423.4	425.3	428.4
10°	402.7	401.8	400.1	399.7	400.1	401.8	402.7	404.7	406.9	409.2	411.3
12.5°	385.4	383.8	383.4	383.9	383.4	383.8	385.4	388.3	393.7	393.7	394.1
15°	362.6	361.7	359.4	360.1	359.4	361.7	362.6	365.3	367.8	371.0	374.2
17.5°	340.0	339.0	336.2	338.7	336.2	339.0	340.0	341.5	344.7	349.2	354.0
20°	325.8	324.1	322.7	322.4	322.7	324.1	325.8	327.3	330.9	334.7	338.3
22.5°	312.4	310.9	310.7	309.3	310.7	310.9	312.4	314.7	318.3	320.4	323.8
25°	295.4	294.0	293.6	292.5	293.6	294.0	295.4	297.1	299.4	301.1	305.0
27.5°	282.5	281.8	281.0	281.3	281.0	281.8	282.5	282.7	283.7	286.0	288.2
30°	274.6	274.4	273.9	273.9	273.9	274.4	274.6	273.9	275.0	276.1	277.8
32.5°	268.0	268.0	268.2	268.2	268.2	268.0	268.0	267.0	267.4	267.8	268.6
35°	258.8	259.4	259.8	259.1	259.8	259.4	258.8	257.9	257.3	255.7	256.2
37.5°	250.4	251.0	251.6	252.4	251.6	251.0	250.4	248.6	247.1	245.8	244.3
40°	244.0	245.4	245.8	246.9	245.8	245.4	244.0	242.1	240.4	238.9	237.2
42.5°	237.9	239.5	240.6	240.9	240.6	239.5	237.9	235.9	233.4	231.7	229.3
45°	228.5	230.2	231.8	231.8	231.8	230.2	228.5	225.4	222.7	219.9	217.6
47.5°	218.9	221.3	222.8	223.2	222.8	221.3	218.9	215.6	211.8	208.4	205.1
50°	212.3	215.3	216.8	217.8	216.8	215.3	212.3	208.7	204.7	200.5	196.4
52.5°	205.9	208.8	210.8	211.3	210.8	208.8	205.9	201.4	196.6	192.1	188.5
55°	194.7	199.0	201.3	202.2	201.3	199.0	194.7	189.9	185.3	179.6	174.5
57.5°	184.3	188.2	190.9	191.5	190.9	188.2	184.3	178.6	172.6	166.6	161.1
60°	176.2	180.5	183.8	184.4	183.8	180.5	176.2	170.5	164.2	158.3	151.5
62.5°	167.9	172.4	175.4	177.0	175.4	172.4	167.9	161.9	155.1	148.5	141.7
65°	153.6	158.1	161.0	161.7	161.0	158.1	153.6	147.8	140.5	133.6	127.9
67.5°	138.0	142.5	144.4	145.6	144.4	142.5	138.0	132.4	125.4	118.2	111.6
70°	127.1	130.6	132.8	133.8	132.8	130.6	127.1	121.1	115.2	107.8	100.9
72.5°	114.6	118.3	120.7	121.0	120.7	118.3	114.6	109.5	103.3	96.4	90.2
75°	95.4	98.8	100.0	100.0	100.0	98.8	95.4	90.5	85.5	80.0	73.8
77.5°	75.5	77.2	78.8	79.2	78.8	77.2	75.5	72.1	67.9	62.3	57.8
80°	62.7	63.8	65.0	65.0	65.0	63.8	62.7	59.5	55.5	50.8	47.3
82.5°	49.5	50.4	51.6	51.5	51.6	50.4	49.5	47.0	43.7	40.6	37.3
85°	30.0	31.8	31.7	31.2	31.7	31.8	30.0	30.4	27.2	25.1	22.2
87.5°	17.5	17.7	18.3	18.7	18.3	17.7	17.5	16.9	15.2	14.3	13.4
90°	20.0	20.3	20.6	21.0	20.6	20.3	20.0	19.7	19.1	18.1	17.2
92.5°	30.4	30.6	30.8	30.9	30.8	30.6	30.4	30.2	29.9	29.2	28.7
95°	55.1	55.1	55.1	55.1	55.1	55.1	55.1	55.1	54.8	54.4	53.9
97.5°	86.3	86.3	86.3	86.3	86.3	86.3	86.3	86.3	86.1	85.4	84.9
100°	108.1	108.1	108.1	108.1	108.1	108.1	108.1	108.1	107.9	107.6	107.3
102.5°	132.2	132.3	132.5	132.6	132.5	132.3	132.2	132.1	131.8	131.3	131.0
105°	168.7	169.2	169.6	170.1	169.6	169.2	168.7	168.3	167.7	167.3	166.8
107.5°	206.7	206.7	206.7	206.6	206.7	206.7	206.7	206.8	206.5	206.1	205.7
110°	231.5	231.9	232.4	232.8	232.4	231.9	231.5	231.0	230.9	231.2	231.5



TEST NUMBER: P332509-940

CATALOG NUMBER: SA4XXDIP-C350D810U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	259.3	259.4	259.5	259.6	259.5	259.4	259.3	259.2	259.2	259.3	259.3
115°	301.7	301.5	301.3	301.1	301.3	301.5	301.7	301.8	301.9	302.1	302.2
117.5°	341.7	341.3	341.1	340.7	341.1	341.3	341.7	342.0	342.4	343.0	343.5
120°	370.0	370.2	370.6	370.9	370.6	370.2	370.0	369.6	369.9	370.6	371.4
122.5°	397.6	397.1	396.5	396.0	396.5	397.1	397.6	398.2	398.8	399.3	399.8
125°	440.1	439.8	439.5	439.2	439.5	439.8	440.1	440.4	440.8	441.0	441.4
127.5°	479.9	479.7	479.5	479.2	479.5	479.7	479.9	480.2	480.5	480.8	481.1
130°	507.3	506.7	506.0	505.4	506.0	506.7	507.3	507.9	508.4	508.6	509.0
132.5°	534.0	533.8	533.5	533.3	533.5	533.8	534.0	534.3	534.6	534.8	535.2
135°	573.0	572.6	572.1	571.7	572.1	572.6	573.0	573.5	573.9	574.2	574.5
137.5°	611.6	611.7	611.8	612.0	611.8	611.7	611.6	611.5	611.7	612.2	612.5
140°	636.9	636.8	636.6	636.5	636.6	636.8	636.9	637.1	637.2	637.4	637.6
142.5°	661.1	661.1	661.0	661.0	661.0	661.1	661.1	661.1	661.2	661.2	661.2
145°	695.7	695.3	694.8	694.4	694.8	695.3	695.7	696.2	696.5	696.7	696.8
147.5°	728.5	728.3	728.3	728.1	728.3	728.3	728.5	728.7	728.8	729.0	729.1
150°	749.2	749.0	748.9	748.7	748.9	749.0	749.2	749.3	749.4	749.4	749.4
152.5°	768.9	768.5	768.1	767.7	768.1	768.5	768.9	769.3	769.3	768.9	768.6
155°	795.9	795.2	794.6	794.1	794.6	795.2	795.9	796.5	796.5	795.9	795.2
157.5°	819.2	818.7	818.1	817.6	818.1	818.7	819.2	819.7	819.7	819.3	818.8
160°	833.3	832.5	831.8	831.0	831.8	832.5	833.3	834.1	834.2	833.7	833.3
162.5°	847.2	846.5	845.7	844.9	845.7	846.5	847.2	848.0	848.0	847.1	846.3
165°	864.9	864.2	863.6	863.1	863.6	864.2	864.9	865.5	865.4	864.4	863.5
167.5°	878.9	877.9	877.0	876.0	877.0	877.9	878.9	879.9	879.9	879.0	878.0
170°	886.5	885.5	884.3	883.2	884.3	885.5	886.5	887.6	887.7	886.7	885.8
172.5°	892.7	891.5	890.5	889.4	890.5	891.5	892.7	893.8	893.8	892.7	891.6
175°	899.0	898.0	896.9	895.8	896.9	898.0	899.0	900.2	900.2	899.0	898.0
177.5°	902.1	901.2	900.2	899.1	900.2	901.2	902.1	903.1	903.2	902.3	901.4
180°	901.3	901.3	901.3	901.3	901.3	901.3	901.3	901.3	901.3	901.3	901.3



TEST NUMBER: P332509-940

CATALOG NUMBER: SA4XXDIP-C350D810U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4
2.5°	487.0	487.7	490.4	492.9	496.0	498.1	499.6	501.3	504.9	507.7	510.5
5°	456.3	457.4	462.8	466.6	473.1	478.8	483.3	488.1	493.8	501.7	508.8
7.5°	429.2	433.1	439.2	445.3	451.9	459.4	465.9	473.2	483.0	493.8	504.9
10°	413.8	418.3	424.6	431.8	438.1	446.7	454.8	463.4	474.7	487.7	500.8
12.5°	398.5	405.8	410.6	419.1	426.0	433.1	441.7	453.0	466.0	479.7	495.5
15°	379.2	383.3	392.5	397.2	406.9	417.9	426.3	437.7	450.3	468.5	486.2
17.5°	357.0	362.3	369.7	378.5	389.7	398.2	408.8	420.5	436.5	454.5	476.7
20°	342.5	347.0	356.1	365.7	377.6	386.6	397.8	409.2	425.7	444.9	468.1
22.5°	329.5	333.8	343.4	352.4	363.9	375.0	386.6	399.9	415.7	436.0	459.7
25°	309.4	315.0	323.5	332.8	343.8	356.4	369.1	380.9	397.8	419.1	444.4
27.5°	291.5	296.0	302.2	312.7	325.2	337.4	350.0	364.9	381.1	403.7	429.9
30°	280.1	284.3	290.4	300.1	311.7	324.8	337.9	352.2	369.1	391.5	418.3
32.5°	270.9	274.1	279.6	288.3	298.9	312.6	325.6	340.4	358.1	380.1	406.3
35°	257.4	260.2	262.3	270.5	280.1	292.7	305.8	321.6	338.8	359.6	385.8
37.5°	244.2	245.2	248.3	253.7	262.9	274.6	286.7	302.3	319.8	341.0	364.6
40°	236.1	236.6	238.4	243.5	251.6	262.5	274.4	289.7	306.4	326.5	349.9
42.5°	228.2	227.9	229.7	233.3	240.8	250.7	262.3	276.4	293.1	311.7	333.7
45°	215.7	215.7	215.3	218.2	224.4	234.1	243.8	257.3	271.2	289.4	307.9
47.5°	202.6	201.4	201.8	203.3	208.5	216.4	226.2	237.3	249.6	264.9	281.2
50°	194.1	192.4	191.8	193.5	198.1	205.1	214.5	224.1	235.8	249.2	263.1
52.5°	184.9	183.2	182.0	183.2	187.5	193.9	202.4	211.0	221.4	232.4	244.4
55°	170.5	168.6	168.0	168.4	171.6	176.6	183.8	191.6	199.5	208.5	217.0
57.5°	156.4	153.3	152.7	152.5	154.6	159.3	165.3	172.0	177.7	183.2	192.3
60°	147.1	143.3	142.0	141.8	143.5	147.3	152.8	159.5	163.5	167.4	175.1
62.5°	137.1	133.5	130.7	131.0	132.5	136.2	141.0	145.9	148.6	152.7	157.9
65°	121.8	117.2	115.0	114.4	115.2	118.2	122.0	125.1	128.1	129.8	134.8
67.5°	106.4	102.5	99.4	98.6	98.3	100.3	103.4	105.3	107.5	108.9	111.9
70°	95.6	92.2	88.5	87.1	86.9	88.6	91.6	91.8	94.8	95.4	98.5
72.5°	85.0	80.7	78.1	76.9	76.0	77.5	79.5	80.0	81.6	82.8	84.4
75°	68.4	65.2	62.7	60.8	60.2	61.0	61.0	62.1	63.1	63.8	65.6
77.5°	53.9	50.2	47.2	46.1	45.3	44.8	45.2	45.9	45.4	46.5	46.9
80°	43.7	39.9	37.5	37.2	35.8	34.9	34.6	35.2	34.4	34.9	36.1
82.5°	33.7	31.3	28.8	28.4	26.8	26.2	26.0	25.6	25.6	25.5	25.8
85°	20.1	18.5	16.9	15.9	15.2	14.2	14.2	13.7	13.3	12.8	13.1
87.5°	11.3	10.8	9.7	9.0	8.4	7.5	7.2	6.3	5.8	5.4	4.8
90°	16.2	15.3	14.1	12.8	11.6	10.3	8.9	7.2	5.5	3.8	2.1
92.5°	28.2	27.6	26.8	25.9	25.0	24.2	22.7	20.8	18.8	16.9	14.9
95°	53.4	53.0	51.9	50.8	49.8	48.7	47.4	46.0	44.6	43.2	41.8
97.5°	84.4	83.8	82.5	81.2	80.0	78.7	77.5	76.4	75.3	74.2	73.0
100°	107.0	106.6	105.2	103.9	102.5	101.1	100.0	99.4	98.8	98.2	97.6
102.5°	130.5	130.1	128.9	127.5	126.3	125.0	124.2	124.0	123.8	123.5	123.2
105°	166.4	165.9	165.3	164.7	164.1	163.5	163.1	162.9	162.7	162.6	162.5
107.5°	205.3	204.8	204.7	204.6	204.6	204.5	204.3	204.1	203.9	203.8	203.6
110°	231.8	232.1	232.3	232.5	232.6	232.7	232.6	232.4	232.0	231.8	231.5



TEST NUMBER: P332509-940

CATALOG NUMBER: SA4XXDIP-C350D810U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	259.4	259.5	259.8	260.0	260.3	260.6	260.7	260.6	260.6	260.5	260.5
115°	302.4	302.6	302.8	303.2	303.4	303.8	304.0	304.0	304.0	304.0	304.0
117.5°	344.0	344.6	344.7	344.9	345.2	345.4	345.4	345.3	345.2	345.1	344.9
120°	372.2	373.0	373.4	373.9	374.3	374.8	374.8	374.2	373.5	372.9	372.3
122.5°	400.3	400.8	401.1	401.3	401.5	401.7	401.7	401.4	401.2	400.9	400.7
125°	441.7	442.0	442.1	442.3	442.5	442.6	442.6	442.6	442.6	442.6	442.6
127.5°	481.4	481.7	482.0	482.2	482.4	482.7	482.6	482.1	481.7	481.2	480.7
130°	509.3	509.6	509.6	509.6	509.6	509.6	509.3	508.9	508.5	508.0	507.5
132.5°	535.5	535.8	535.9	536.1	536.2	536.3	536.2	535.8	535.6	535.2	534.8
135°	574.8	575.2	575.2	575.2	575.2	575.2	574.7	573.7	572.8	571.9	571.0
137.5°	613.0	613.3	613.1	612.9	612.6	612.3	612.0	611.5	611.1	610.7	610.3
140°	637.8	637.8	637.8	637.8	637.8	637.8	637.8	637.4	637.1	636.8	636.5
142.5°	661.3	661.3	661.4	661.6	661.6	661.8	661.7	661.4	661.1	660.8	660.5
145°	697.0	697.1	697.0	696.8	696.7	696.5	696.2	695.5	694.9	694.3	693.7
147.5°	729.2	729.3	729.4	729.6	729.7	729.9	729.5	728.8	728.0	727.3	726.6
150°	749.4	749.4	749.4	749.4	749.4	749.4	749.1	748.5	747.9	747.3	746.6
152.5°	768.2	767.9	767.7	767.6	767.4	767.3	767.0	766.7	766.3	766.0	765.6
155°	794.6	794.1	794.2	794.3	794.5	794.6	794.7	794.7	794.7	794.7	794.7
157.5°	818.3	817.9	817.9	818.0	818.0	818.0	818.1	818.4	818.7	818.9	819.3
160°	832.9	832.4	832.5	832.7	832.9	832.9	833.1	833.3	833.5	833.6	833.7
162.5°	845.5	844.6	844.8	845.0	845.1	845.3	845.5	846.0	846.3	846.8	847.1
165°	862.6	861.7	861.9	862.3	862.6	862.9	863.3	863.7	864.2	864.7	865.1
167.5°	877.1	876.1	876.1	876.1	876.0	876.0	876.4	877.0	877.6	878.2	879.0
170°	884.8	884.0	883.8	883.7	883.5	883.3	883.7	884.4	885.2	886.0	886.7
172.5°	890.6	889.6	889.5	889.5	889.5	889.4	889.7	890.4	891.0	891.7	892.3
175°	896.9	895.8	896.0	896.1	896.3	896.4	896.9	897.7	898.4	899.2	900.0
177.5°	900.5	899.7	899.7	899.7	899.7	899.7	900.0	900.6	901.3	901.9	902.5
180°	901.3	901.3	901.3	901.3	901.3	901.3	901.3	901.3	901.3	901.3	901.3



TEST NUMBER: P332509-940

CATALOG NUMBER: SA4XXDIP-C350D810U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4
2.5°	512.8	514.5	516.7	520.4	521.7	523.4	525.8	525.7	526.3	528.9	534.2
5°	514.7	521.3	527.6	535.2	543.2	548.5	555.6	560.1	564.5	570.2	580.0
7.5°	515.5	525.8	537.4	550.8	562.7	576.3	587.0	597.1	606.2	618.1	629.7
10°	514.3	528.2	543.2	560.1	578.0	593.3	607.0	622.6	635.9	650.4	663.5
12.5°	512.1	528.9	548.9	567.8	588.8	611.3	628.4	644.2	661.8	678.6	698.8
15°	507.1	530.1	553.6	578.5	606.5	632.5	657.2	677.6	696.6	721.8	748.1
17.5°	500.8	525.6	555.2	585.3	614.7	644.3	674.8	705.6	729.6	760.8	781.4
20°	494.9	523.6	554.0	589.9	619.2	656.1	686.5	716.2	749.2	780.2	804.9
22.5°	486.6	518.0	550.3	585.9	624.6	661.6	696.6	728.9	761.9	795.6	825.5
25°	476.1	504.6	542.8	583.3	621.7	661.8	702.1	742.6	778.1	813.8	841.6
27.5°	458.3	494.2	529.8	571.6	614.2	659.6	702.8	745.1	782.3	811.6	828.8
30°	449.1	480.4	519.0	561.0	607.2	655.9	700.9	742.4	777.0	800.5	807.4
32.5°	435.6	467.8	505.6	549.1	598.1	648.2	694.9	734.1	763.0	775.3	767.0
35°	415.5	444.7	482.9	527.4	578.3	631.6	677.9	711.0	725.8	714.2	685.3
37.5°	391.5	420.4	458.7	502.5	555.1	609.4	651.1	675.0	670.1	641.2	598.2
40°	374.6	401.6	438.1	485.4	536.6	591.1	627.9	640.7	627.2	585.9	540.0
42.5°	355.9	382.2	418.8	464.5	518.8	569.0	601.0	602.1	579.4	529.9	484.0
45°	327.3	352.4	387.0	434.5	484.7	532.0	553.1	542.8	501.0	453.3	407.1
47.5°	299.2	320.9	355.1	400.1	447.8	487.6	498.1	479.5	435.0	388.6	345.8
50°	278.6	300.5	332.6	375.7	421.7	456.0	461.1	436.4	392.7	346.1	312.5
52.5°	258.8	280.6	311.5	351.3	393.4	424.5	424.6	396.1	352.6	311.0	279.8
55°	229.8	249.4	277.3	313.0	350.5	374.8	368.9	339.4	301.6	265.5	238.3
57.5°	201.9	219.0	244.6	274.4	307.5	327.5	317.7	289.3	255.6	224.9	204.3
60°	183.8	200.1	222.0	250.1	277.9	293.6	284.3	258.5	227.5	202.8	184.9
62.5°	166.2	179.9	201.1	225.4	251.3	262.8	254.6	229.2	202.3	180.0	165.4
65°	141.4	152.6	169.4	190.4	209.1	219.1	212.1	188.4	168.0	151.9	140.4
67.5°	118.2	126.9	139.7	156.5	172.5	177.8	171.5	155.0	137.7	124.8	116.6
70°	102.1	110.4	121.1	134.0	147.9	153.6	147.3	134.2	120.1	108.3	100.2
72.5°	88.1	94.5	103.6	114.6	125.5	131.2	126.9	114.3	102.4	93.5	86.8
75°	67.1	72.6	78.9	86.8	95.1	99.0	95.1	86.5	78.3	71.8	66.9
77.5°	48.8	51.7	56.6	62.5	67.8	70.6	67.3	61.5	56.4	52.0	49.6
80°	37.2	39.2	42.6	47.3	50.8	53.6	51.5	46.6	42.6	39.7	38.6
82.5°	27.0	28.4	30.7	34.1	36.5	37.9	37.0	33.4	31.8	29.2	28.2
85°	13.3	14.2	15.6	16.7	18.8	19.0	19.2	17.7	16.2	15.6	14.8
87.5°	5.4	5.8	6.7	7.5	8.5	8.9	9.0	9.3	8.8	8.8	8.3
90°	3.8	5.5	7.2	8.9	10.3	11.6	12.8	14.1	15.3	16.2	17.2
92.5°	16.9	18.8	20.8	22.7	24.2	25.0	25.9	26.8	27.6	28.2	28.7
95°	43.2	44.6	46.0	47.4	48.7	49.8	50.8	51.9	53.0	53.4	53.9
97.5°	74.2	75.3	76.4	77.5	78.7	80.0	81.2	82.5	83.8	84.4	84.9
100°	98.2	98.8	99.4	100.0	101.1	102.5	103.9	105.2	106.6	107.0	107.3
102.5°	123.5	123.8	124.0	124.2	125.0	126.3	127.5	128.9	130.1	130.5	131.0
105°	162.6	162.7	162.9	163.1	163.5	164.1	164.7	165.3	165.9	166.4	166.8
107.5°	203.8	203.9	204.1	204.3	204.5	204.6	204.6	204.7	204.8	205.3	205.7
110°	231.8	232.0	232.4	232.6	232.7	232.6	232.5	232.3	232.1	231.8	231.5



TEST NUMBER: P332509-940

CATALOG NUMBER: SA4XXDIP-C350D810U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	260.5	260.6	260.6	260.7	260.6	260.3	260.0	259.8	259.5	259.4	259.3
115°	304.0	304.0	304.0	304.0	303.8	303.4	303.2	302.8	302.6	302.4	302.2
117.5°	345.1	345.2	345.3	345.4	345.4	345.2	344.9	344.7	344.6	344.0	343.5
120°	372.9	373.5	374.2	374.8	374.8	374.3	373.9	373.4	373.0	372.2	371.4
122.5°	400.9	401.2	401.4	401.7	401.7	401.5	401.3	401.1	400.8	400.3	399.8
125°	442.6	442.6	442.6	442.6	442.6	442.5	442.3	442.1	442.0	441.7	441.4
127.5°	481.2	481.7	482.1	482.6	482.7	482.4	482.2	482.0	481.7	481.4	481.1
130°	508.0	508.5	508.9	509.3	509.6	509.6	509.6	509.6	509.6	509.3	509.0
132.5°	535.2	535.6	535.8	536.2	536.3	536.2	536.1	535.9	535.8	535.5	535.2
135°	571.9	572.8	573.7	574.7	575.2	575.2	575.2	575.2	575.2	574.8	574.5
137.5°	610.7	611.1	611.5	612.0	612.3	612.6	612.9	613.1	613.3	613.0	612.5
140°	636.8	637.1	637.4	637.8	637.8	637.8	637.8	637.8	637.8	637.8	637.6
142.5°	660.8	661.1	661.4	661.7	661.8	661.6	661.6	661.4	661.3	661.3	661.2
145°	694.3	694.9	695.5	696.2	696.5	696.7	696.8	697.0	697.1	697.0	696.8
147.5°	727.3	728.0	728.8	729.5	729.9	729.7	729.6	729.4	729.3	729.2	729.1
150°	747.3	747.9	748.5	749.1	749.4	749.4	749.4	749.4	749.4	749.4	749.4
152.5°	766.0	766.3	766.7	767.0	767.3	767.4	767.6	767.7	767.9	768.2	768.6
155°	794.7	794.7	794.7	794.7	794.6	794.5	794.3	794.2	794.1	794.6	795.2
157.5°	818.9	818.7	818.4	818.1	818.0	818.0	818.0	817.9	817.9	818.3	818.8
160°	833.6	833.5	833.3	833.1	832.9	832.9	832.7	832.5	832.4	832.9	833.3
162.5°	846.8	846.3	846.0	845.5	845.3	845.1	845.0	844.8	844.6	845.5	846.3
165°	864.7	864.2	863.7	863.3	862.9	862.6	862.3	861.9	861.7	862.6	863.5
167.5°	878.2	877.6	877.0	876.4	876.0	876.0	876.1	876.1	876.1	877.1	878.0
170°	886.0	885.2	884.4	883.7	883.3	883.5	883.7	883.8	884.0	884.8	885.8
172.5°	891.7	891.0	890.4	889.7	889.4	889.5	889.5	889.5	889.6	890.6	891.6
175°	899.2	898.4	897.7	896.9	896.4	896.3	896.1	896.0	895.8	896.9	898.0
177.5°	901.9	901.3	900.6	900.0	899.7	899.7	899.7	899.7	899.7	900.5	901.4
180°	901.3	901.3	901.3	901.3	901.3	901.3	901.3	901.3	901.3	901.3	901.3



TEST NUMBER: P332509-940

CATALOG NUMBER: SA4XXDIP-C350D810U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	509.4	509.4	509.4	509.4	509.4	509.4	509.4
2.5°	537.0	537.3	538.9	540.0	540.4	542.1	542.2
5°	584.2	587.7	594.7	595.3	596.4	601.9	597.6
7.5°	639.4	648.5	654.6	660.0	661.9	664.3	663.9
10°	674.9	688.4	695.2	706.0	706.3	709.1	707.4
12.5°	710.5	726.2	738.5	740.6	749.6	751.0	753.3
15°	761.0	777.7	794.8	800.9	813.3	816.3	820.9
17.5°	808.4	825.5	837.5	853.3	858.4	865.2	860.6
20°	834.5	853.0	868.3	880.7	885.9	889.7	889.3
22.5°	850.2	868.9	881.2	890.6	895.5	897.2	897.1
25°	860.0	870.8	874.6	878.2	872.6	870.8	871.6
27.5°	832.6	829.8	819.9	806.9	793.4	782.7	776.9
30°	795.0	778.6	763.6	737.4	723.9	715.9	708.6
32.5°	741.6	715.5	686.7	662.7	647.4	635.5	633.7
35°	650.2	611.0	575.7	546.4	531.2	518.4	515.3
37.5°	552.8	512.0	480.3	454.4	438.1	429.0	420.5
40°	488.1	453.1	421.9	399.9	387.4	380.9	375.7
42.5°	438.4	406.4	375.2	358.6	347.3	343.3	340.2
45°	369.5	339.7	318.3	305.6	299.1	292.3	289.1
47.5°	314.4	290.3	276.1	265.3	258.2	254.2	252.3
50°	283.2	263.4	250.7	242.5	236.1	233.0	231.3
52.5°	255.6	239.2	228.6	222.0	217.8	215.4	214.7
55°	220.1	207.7	200.9	195.2	192.1	189.9	189.1
57.5°	191.4	181.7	176.3	171.6	170.3	168.6	168.0
60°	172.5	165.1	160.4	157.2	156.1	154.1	154.4
62.5°	155.7	149.6	145.7	143.9	142.5	140.7	141.3
65°	131.7	127.2	125.1	123.5	121.8	120.7	121.5
67.5°	110.5	107.5	104.6	103.6	102.8	102.6	101.7
70°	96.7	94.2	91.6	91.0	91.0	90.2	89.9
72.5°	83.3	81.5	79.8	79.3	78.6	79.0	78.1
75°	64.4	62.9	62.2	61.6	61.4	61.4	60.8
77.5°	47.5	46.5	45.5	45.5	44.7	44.4	44.3
80°	36.1	35.7	34.9	34.9	34.4	34.6	34.2
82.5°	27.1	26.6	26.4	26.0	25.4	25.5	25.1
85°	14.5	13.9	13.7	13.1	12.7	13.1	12.7
87.5°	8.6	8.7	8.6	8.4	8.3	8.4	7.9
90°	18.1	19.1	19.7	20.0	20.3	20.6	21.0
92.5°	29.2	29.9	30.2	30.4	30.6	30.8	30.9
95°	54.4	54.8	55.1	55.1	55.1	55.1	55.1
97.5°	85.4	86.1	86.3	86.3	86.3	86.3	86.3
100°	107.6	107.9	108.1	108.1	108.1	108.1	108.1
102.5°	131.3	131.8	132.1	132.2	132.3	132.5	132.6
105°	167.3	167.7	168.3	168.7	169.2	169.6	170.1
107.5°	206.1	206.5	206.8	206.7	206.7	206.7	206.6
110°	231.2	230.9	231.0	231.5	231.9	232.4	232.8



TEST NUMBER: P332509-940

CATALOG NUMBER: SA4XXDIP-C350D810U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	259.3	259.2	259.2	259.3	259.4	259.5	259.6
115°	302.1	301.9	301.8	301.7	301.5	301.3	301.1
117.5°	343.0	342.4	342.0	341.7	341.3	341.1	340.7
120°	370.6	369.9	369.6	370.0	370.2	370.6	370.9
122.5°	399.3	398.8	398.2	397.6	397.1	396.5	396.0
125°	441.0	440.8	440.4	440.1	439.8	439.5	439.2
127.5°	480.8	480.5	480.2	479.9	479.7	479.5	479.2
130°	508.6	508.4	507.9	507.3	506.7	506.0	505.4
132.5°	534.8	534.6	534.3	534.0	533.8	533.5	533.3
135°	574.2	573.9	573.5	573.0	572.6	572.1	571.7
137.5°	612.2	611.7	611.5	611.6	611.7	611.8	612.0
140°	637.4	637.2	637.1	636.9	636.8	636.6	636.5
142.5°	661.2	661.2	661.1	661.1	661.1	661.0	661.0
145°	696.7	696.5	696.2	695.7	695.3	694.8	694.4
147.5°	729.0	728.8	728.7	728.5	728.3	728.3	728.1
150°	749.4	749.4	749.3	749.2	749.0	748.9	748.7
152.5°	768.9	769.3	769.3	768.9	768.5	768.1	767.7
155°	795.9	796.5	796.5	795.9	795.2	794.6	794.1
157.5°	819.3	819.7	819.7	819.2	818.7	818.1	817.6
160°	833.7	834.2	834.1	833.3	832.5	831.8	831.0
162.5°	847.1	848.0	848.0	847.2	846.5	845.7	844.9
165°	864.4	865.4	865.5	864.9	864.2	863.6	863.1
167.5°	879.0	879.9	879.9	878.9	877.9	877.0	876.0
170°	886.7	887.7	887.6	886.5	885.5	884.3	883.2
172.5°	892.7	893.8	893.8	892.7	891.5	890.5	889.4
175°	899.0	900.2	900.2	899.0	898.0	896.9	895.8
177.5°	902.3	903.2	903.1	902.1	901.2	900.2	899.1
180°	901.3	901.3	901.3	901.3	901.3	901.3	901.3

(END OF REPORT)