

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332564-940

Luminaire Tested: **SA4XXDIP-C575D1035U940-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332564-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C575D1035U940-4F0-1E-UDD-A4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5608.7 lumens
Efficiency: N/A
Efficacy: 126.0 lumens/watt
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 44.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332564-940
CATALOG NUMBER: SA4XXDIP-C575D1035U940-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332564-940

CATALOG NUMBER: SA4XXDIP-C575D1035U940-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	96	96	96	96	78	78	78	63	63	63	48	48	48	41				
1	96	92	88	85	87	84	81	78	69	67	65	55	54	52	43	42	41	35				
2	88	80	74	69	80	73	68	64	61	57	54	49	46	44	38	36	35	30				
3	80	71	64	58	73	65	59	54	54	49	45	43	40	37	34	32	30	25				
4	73	63	55	49	67	58	51	46	48	43	39	39	35	32	30	28	26	22				
5	67	56	48	42	61	51	44	39	43	38	34	35	31	28	27	25	23	19				
6	62	50	42	37	56	46	39	34	39	33	29	31	28	25	25	22	20	17				
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15				
8	53	41	33	28	48	38	31	26	32	27	23	26	22	19	21	18	16	13				
9	49	37	30	25	45	35	28	24	29	24	20	24	20	17	19	16	14	12				
10	46	34	27	23	42	32	25	21	27	22	18	22	18	16	18	15	13	11				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	6761	6761	6761	6761
5°	7963	6779	5983	6779
10°	9534	6749	5387	6749
15°	11280	6680	4947	6680
20°	12560	6611	4554	6611
25°	12764	6509	4284	6509
30°	10860	6411	4198	6411
35°	8349	6250	4199	6250
40°	6509	6062	4278	6062
45°	5426	5779	4349	5779
50°	4775	5434	4496	5434
55°	4376	5020	4677	5020
60°	4101	4648	4897	4648
65°	3817	4235	5075	4235
70°	3489	3824	5193	3824
75°	3119	3366	5128	3366
80°	2613	2757	4965	2757
85°	1927	1991	4761	1991



TEST NUMBER: P332564-940

CATALOG NUMBER: SA4XXDIP-C575D1035U940-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.6	1.5
10°-20°	251.5	4.5
20°-30°	398.8	7.1
30°-40°	443.8	7.9
40°-50°	404.0	7.2
50°-60°	330.1	5.9
60°-70°	235.7	4.2
70°-80°	129.8	2.3
80°-90°	37.9	0.7
90°-100°	327.3	5.8
100°-110°	681.1	12.1
110°-120°	610.1	10.9
120°-130°	513.2	9.2
130°-140°	427.9	7.6
140°-150°	326.9	5.8
150°-160°	229.8	4.1
160°-170°	135.2	2.4
170°-180°	44.0	0.8
0°-30°	731.9	13.0
0°-40°	1175.7	21.0
0°-60°	1909.9	34.1
0°-90°	2313.3	41.2
90°-120°	1618.5	28.9
90°-150°	2886.5	51.5
90°-180°	3295.0	58.7
0°-180°	5608.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	838	838	838	838	838	
5°	983	836	738	836	983	100
15°	1350	799	592	799	1350	381
25°	1433	731	481	731	1433	632
35°	847	634	426	634	847	538
45°	475	506	381	506	475	374
55°	311	357	332	357	311	281
65°	200	222	266	222	200	198
75°	100	108	164	108	100	106
85°	21	22	51	22	21	26
90°	19	1	19	1	19	16
95°	217	29	217	29	217	337
105°	1252	104	1252	104	1252	1238
115°	1203	183	1203	183	1203	1194
125°	960	256	960	256	960	872
135°	858	304	858	304	858	662
145°	701	350	701	350	701	444
155°	587	398	587	398	587	274
165°	512	434	512	434	512	147
175°	461	452	461	452	461	45
180°	453	453	453	453	453	



TEST NUMBER: P332564-940

CATALOG NUMBER: SA4XXDIP-C575D1035U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5
2.5°	891.4	891.1	888.3	887.8	885.8	883.3	882.8	878.3	869.4	865.3	864.2
5°	982.6	989.5	980.4	978.7	977.7	966.3	960.4	953.4	937.5	928.1	920.8
7.5°	1091.4	1092.2	1088.2	1085.0	1076.2	1066.2	1051.2	1035.3	1016.3	996.5	981.6
10°	1163.0	1165.7	1161.3	1160.6	1142.8	1131.8	1109.6	1090.8	1069.3	1045.4	1023.5
12.5°	1238.5	1234.6	1232.3	1217.5	1214.2	1193.9	1168.1	1148.8	1115.6	1088.1	1059.0
15°	1349.6	1342.0	1337.1	1316.7	1306.6	1278.5	1251.1	1229.9	1186.6	1145.3	1114.0
17.5°	1414.9	1422.5	1411.2	1402.8	1376.8	1357.1	1329.1	1284.7	1250.7	1199.4	1160.0
20°	1462.0	1462.8	1456.5	1447.8	1427.4	1402.4	1371.8	1323.3	1282.6	1231.6	1177.5
22.5°	1474.8	1475.0	1472.3	1464.2	1448.7	1428.4	1397.7	1357.1	1308.0	1252.5	1198.4
25°	1432.9	1431.6	1434.7	1443.7	1437.8	1431.6	1413.8	1383.7	1337.8	1279.2	1220.9
27.5°	1277.2	1286.7	1304.4	1326.6	1348.0	1364.2	1368.9	1362.7	1334.3	1286.0	1225.0
30°	1165.0	1176.9	1190.0	1212.3	1255.3	1279.9	1307.0	1327.4	1316.0	1277.5	1220.6
32.5°	1041.8	1044.7	1064.3	1089.6	1129.0	1176.3	1219.2	1260.8	1274.6	1254.5	1206.9
35°	847.2	852.1	873.3	898.2	946.5	1004.4	1069.0	1126.5	1174.1	1193.2	1168.9
37.5°	691.4	705.3	720.2	747.1	789.6	841.8	908.8	983.3	1054.2	1101.6	1109.6
40°	617.6	626.2	637.0	657.5	693.6	744.9	802.5	887.9	963.1	1031.2	1053.4
42.5°	559.3	564.4	571.0	589.4	617.0	668.0	720.6	795.7	871.3	952.6	989.8
45°	475.3	480.5	491.6	502.4	523.2	558.6	607.5	669.2	745.2	823.7	892.3
47.5°	414.6	418.0	424.6	436.1	453.8	477.2	516.9	568.5	638.9	715.1	788.3
50°	380.2	383.0	388.3	398.7	412.1	433.0	465.6	513.8	569.0	645.7	717.5
52.5°	353.0	354.2	358.0	365.1	375.9	393.3	420.1	459.9	511.3	579.6	651.1
55°	310.9	312.3	315.8	320.9	330.3	341.4	361.9	391.7	436.5	495.8	557.9
57.5°	276.2	277.1	280.1	282.0	289.8	298.8	314.5	335.8	369.8	420.1	475.5
60°	254.0	253.2	256.7	258.5	263.7	271.3	283.5	303.9	333.4	374.0	425.0
62.5°	232.3	231.3	234.3	236.6	239.5	246.0	256.0	272.0	296.0	332.7	376.7
65°	199.8	198.5	200.2	203.0	205.7	209.2	216.5	230.7	249.8	276.2	309.8
67.5°	167.2	168.7	169.0	170.3	171.9	176.6	181.6	191.7	205.2	226.3	254.8
70°	147.8	148.1	149.5	149.5	150.6	154.7	158.9	164.8	178.0	197.4	220.7
72.5°	128.4	129.8	129.3	130.4	131.2	133.9	137.0	142.6	153.8	168.3	187.9
75°	100.0	100.9	100.9	101.3	102.4	103.3	105.8	109.9	118.0	128.7	142.2
77.5°	72.9	73.0	73.5	74.7	74.7	76.4	78.2	81.5	85.5	92.8	101.1
80°	56.2	56.9	56.5	57.2	57.2	58.7	59.3	63.5	65.2	70.1	76.7
82.5°	41.2	41.9	41.8	42.8	43.3	43.6	44.6	46.3	48.0	52.3	55.0
85°	20.8	21.5	20.8	21.5	22.6	22.9	23.9	24.3	25.7	26.8	29.2
87.5°	9.8	10.7	10.9	11.0	11.3	11.6	11.7	11.2	12.2	12.7	13.4
90°	18.7	18.7	19.6	18.7	17.8	17.8	16.9	16.1	15.2	16.1	14.3
92.5°	68.6	68.6	71.6	76.4	86.9	104.7	131.6	174.9	235.2	282.4	247.1
95°	217.2	228.8	244.8	272.4	316.0	402.3	521.7	659.6	746.0	725.5	547.5
97.5°	580.6	599.1	625.8	679.4	743.3	836.2	923.3	974.6	937.2	764.1	512.4
100°	816.4	823.4	850.2	904.5	981.9	1047.8	1091.4	1073.6	943.6	715.7	464.7
102.5°	1021.5	1027.2	1055.3	1094.6	1142.1	1169.6	1156.9	1068.6	890.2	655.2	432.7
105°	1252.5	1257.8	1270.3	1277.5	1275.7	1239.1	1151.0	997.0	793.2	584.0	405.0
107.5°	1338.4	1336.1	1327.1	1306.8	1262.8	1183.5	1059.4	895.4	714.8	544.1	400.0
110°	1339.8	1331.8	1315.7	1278.4	1215.1	1117.2	988.1	834.1	675.6	530.6	401.4



TEST NUMBER: P332564-940

CATALOG NUMBER: SA4XXDIP-C575D1035U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1297.7	1284.8	1262.3	1217.1	1145.3	1047.4	925.4	789.3	653.6	524.1	405.7
115°	1202.7	1195.5	1167.1	1113.7	1043.3	957.9	853.7	744.2	632.9	520.8	413.9
117.5°	1106.3	1100.8	1072.0	1027.2	967.1	894.7	812.8	722.1	623.7	519.9	422.7
120°	1052.2	1042.4	1019.3	980.1	929.3	866.2	795.0	712.1	618.7	519.9	429.1
122.5°	1009.5	999.7	980.1	946.6	903.7	848.4	783.5	703.6	613.0	519.2	435.5
125°	959.7	954.3	937.4	911.6	875.9	827.0	765.5	689.0	603.6	518.1	445.1
127.5°	930.4	925.1	910.9	887.9	852.1	805.7	744.4	671.2	590.9	516.1	452.7
130°	913.4	908.0	893.8	871.5	835.0	787.8	727.3	657.0	583.1	515.4	458.4
132.5°	894.1	888.8	875.2	850.2	814.4	767.1	708.1	642.0	576.0	514.7	463.4
135°	858.2	852.8	838.6	813.7	778.0	733.5	679.2	621.3	565.3	513.6	470.9
137.5°	813.7	807.3	795.5	770.9	737.6	697.4	651.7	602.7	556.0	513.4	475.4
140°	781.6	774.5	762.1	742.4	711.2	673.9	633.8	592.0	551.1	512.7	478.9
142.5°	747.4	742.4	731.4	713.2	685.6	653.3	618.8	582.0	546.8	512.7	481.8
145°	700.6	696.2	687.2	672.1	649.9	624.9	598.2	567.9	539.5	511.0	483.4
147.5°	659.1	657.5	650.8	637.8	621.3	601.8	580.4	556.3	532.9	507.7	484.3
150°	635.6	634.7	629.4	617.8	603.6	587.5	569.7	549.3	527.9	505.6	484.3
152.5°	614.2	613.3	610.1	600.7	588.6	575.4	559.0	541.4	522.2	502.0	482.9
155°	586.7	586.7	584.0	576.8	567.9	557.2	543.9	529.7	513.6	496.8	480.7
157.5°	562.4	562.4	560.8	555.4	548.8	540.2	529.0	517.0	504.9	491.2	478.4
160°	547.5	547.5	546.6	541.3	535.9	528.8	519.0	509.2	498.6	487.0	476.3
162.5°	533.2	534.0	533.1	527.7	523.8	517.4	509.7	501.3	492.8	482.7	474.1
165°	511.8	512.7	513.6	510.1	506.5	502.0	495.9	490.5	483.4	476.3	470.0
167.5°	495.0	495.7	495.9	493.6	491.8	489.1	484.1	480.0	474.8	469.8	465.7
170°	484.3	484.3	485.2	484.3	482.5	479.8	476.3	473.6	469.1	465.6	462.9
172.5°	473.6	475.0	475.9	475.0	473.9	472.0	469.8	467.9	464.1	461.3	460.0
175°	461.1	462.9	464.7	462.9	462.9	462.9	461.1	460.2	458.4	456.6	456.6
177.5°	453.8	455.2	456.6	455.9	456.6	455.9	455.9	455.2	454.5	453.8	453.8
180°	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1



TEST NUMBER: P332564-940

CATALOG NUMBER: SA4XXDIP-C575D1035U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5
2.5°	864.4	860.6	857.8	855.6	849.4	845.9	843.1	839.2	834.7	830.0	824.2
5°	913.6	901.7	893.0	879.9	867.4	856.9	846.2	836.5	824.7	811.9	802.5
7.5°	965.1	947.5	925.1	905.5	883.6	864.5	847.5	830.0	811.8	794.2	778.0
10°	997.8	975.3	950.3	920.8	893.0	868.4	845.5	823.3	801.8	780.2	761.9
12.5°	1033.0	1005.0	968.0	933.5	902.5	869.5	841.9	814.7	788.7	766.2	744.7
15°	1080.4	1039.8	997.1	951.0	910.1	871.6	833.7	799.3	770.3	740.4	719.6
17.5°	1109.5	1059.3	1010.5	962.2	912.7	864.1	823.3	783.7	747.2	717.6	691.3
20°	1128.6	1078.7	1018.0	969.7	910.7	860.8	813.6	769.5	731.4	699.8	672.7
22.5°	1145.3	1087.5	1026.8	963.3	904.6	851.6	800.0	755.6	716.7	683.4	657.5
25°	1154.3	1088.1	1022.1	958.9	892.3	829.6	782.7	730.7	689.0	654.0	626.2
27.5°	1155.3	1084.4	1009.9	939.7	870.9	812.4	753.3	706.8	663.6	626.5	599.9
30°	1152.2	1078.3	998.2	922.2	853.2	789.6	738.3	687.7	643.5	606.8	579.1
32.5°	1142.5	1065.5	983.2	902.8	831.3	769.1	716.1	668.0	625.0	588.8	559.6
35°	1114.4	1038.4	950.7	867.0	793.8	731.0	683.1	634.2	591.2	556.9	528.8
37.5°	1070.5	1001.7	912.6	826.0	754.1	691.1	643.5	599.4	560.6	525.7	496.9
40°	1032.2	971.8	882.3	798.0	720.2	660.2	615.8	575.2	536.7	503.7	476.4
42.5°	988.0	935.4	852.8	763.6	688.6	628.3	585.1	548.6	512.3	481.9	454.4
45°	909.4	874.7	796.9	714.3	636.3	579.4	538.1	506.2	475.6	445.9	422.9
47.5°	818.9	801.6	736.2	657.8	583.7	527.6	491.9	462.4	435.6	410.3	390.1
50°	758.0	749.8	693.2	617.6	546.8	494.1	458.0	432.7	409.7	387.5	368.5
52.5°	698.1	697.9	646.8	577.6	512.1	461.3	425.5	401.8	382.0	363.9	346.8
55°	606.5	616.2	576.3	514.5	455.9	410.1	377.8	356.7	342.8	327.9	315.0
57.5°	522.3	538.4	505.5	451.1	402.2	360.0	331.9	316.0	301.2	292.2	282.9
60°	467.3	482.6	456.9	411.2	365.0	328.9	302.2	287.9	275.1	268.9	262.3
62.5°	418.5	432.1	413.0	370.6	330.6	295.9	273.3	259.7	251.0	244.2	239.8
65°	348.7	360.2	343.8	313.0	278.6	250.8	232.5	221.7	213.4	210.6	205.7
67.5°	281.9	292.3	283.5	257.3	229.7	208.7	194.3	184.0	179.1	176.6	173.2
70°	242.2	252.6	243.2	220.3	199.1	181.5	167.9	162.0	156.9	155.8	151.0
72.5°	208.6	215.7	206.3	188.4	170.3	155.3	144.9	138.8	136.0	134.1	131.5
75°	156.5	162.7	156.5	142.6	129.7	119.3	110.3	107.9	104.8	103.7	102.0
77.5°	110.8	116.2	111.4	102.7	93.1	85.1	80.3	77.1	76.4	74.6	75.4
80°	84.6	88.1	83.6	77.8	70.1	64.6	61.1	59.3	57.2	56.5	58.0
82.5°	60.8	62.3	60.0	56.1	50.4	46.7	44.4	42.4	42.0	42.1	42.1
85°	31.6	31.2	30.9	27.4	25.7	23.3	21.8	21.5	21.1	21.8	22.6
87.5°	13.0	13.3	11.9	10.9	9.8	8.8	8.0	7.4	8.0	8.8	9.3
90°	12.5	12.5	7.1	7.1	6.2	5.4	2.7	0.9	2.7	5.4	6.2
92.5°	179.9	110.8	65.5	47.0	34.0	23.2	14.8	10.2	14.8	23.2	34.0
95°	334.7	188.7	111.3	73.9	52.5	40.9	32.0	29.3	32.0	40.9	52.5
97.5°	300.9	180.4	120.7	89.3	71.1	60.4	52.7	52.7	52.7	60.4	71.1
100°	283.1	182.5	130.0	101.5	84.5	73.9	67.7	67.7	67.7	73.9	84.5
102.5°	278.1	189.6	142.0	115.0	98.8	88.8	83.3	81.9	83.3	88.8	98.8
105°	280.4	206.5	163.8	137.9	122.0	111.3	106.8	104.2	106.8	111.3	122.0
107.5°	293.6	226.3	187.1	161.7	146.3	134.9	130.5	128.8	130.5	134.9	146.3
110°	303.5	241.2	202.1	178.1	162.0	151.3	146.9	145.1	146.9	151.3	162.0



TEST NUMBER: P332564-940

CATALOG NUMBER: SA4XXDIP-C575D1035U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	314.2	255.5	217.8	193.7	177.7	167.7	162.6	160.8	162.6	167.7	177.7
115°	331.2	277.8	242.1	218.1	201.2	192.3	186.0	183.4	186.0	192.3	201.2
117.5°	348.4	299.3	265.5	240.5	224.7	214.9	209.4	206.9	209.4	214.9	224.7
120°	360.5	314.2	280.4	255.5	240.3	230.6	224.4	222.6	224.4	230.6	240.3
122.5°	371.9	328.5	294.6	270.5	253.9	244.8	238.5	236.8	238.5	244.8	253.9
125°	389.1	348.0	316.0	291.1	274.2	264.4	259.0	255.5	259.0	264.4	274.2
127.5°	403.8	366.2	335.3	310.1	292.5	281.3	274.9	272.1	274.9	281.3	292.5
130°	413.0	378.4	348.0	322.3	305.3	291.9	284.9	281.3	284.9	291.9	305.3
132.5°	422.3	388.3	358.0	333.7	315.3	302.6	293.4	290.5	293.4	302.6	315.3
135°	434.4	402.3	373.0	349.8	331.2	316.0	307.1	303.5	307.1	316.0	331.2
137.5°	443.0	413.0	385.7	363.6	344.1	329.8	319.9	316.6	319.9	329.8	344.1
140°	448.6	420.2	393.5	372.1	353.4	338.3	328.5	325.8	328.5	338.3	353.4
142.5°	452.9	426.6	400.6	380.0	361.9	347.5	338.5	335.8	338.5	347.5	361.9
145°	457.5	433.5	410.4	390.8	373.9	361.4	352.5	349.8	352.5	361.4	373.9
147.5°	461.6	440.7	418.9	401.3	387.3	374.4	366.6	365.7	366.6	374.4	387.3
150°	463.8	444.3	424.6	407.7	394.4	383.7	376.6	375.7	376.6	383.7	394.4
152.5°	465.2	447.1	429.6	414.1	402.2	392.3	385.1	385.0	385.1	392.3	402.2
155°	466.5	451.3	436.2	422.8	413.0	404.1	398.8	397.9	398.8	404.1	413.0
157.5°	466.5	454.3	441.6	431.1	422.5	415.5	410.5	410.5	410.5	415.5	422.5
160°	466.5	455.8	445.1	435.3	428.2	422.0	418.4	418.4	418.4	422.0	428.2
162.5°	466.5	457.2	447.3	439.6	433.2	427.7	424.8	425.5	424.8	427.7	433.2
165°	464.7	457.5	449.5	444.3	439.8	435.3	433.5	433.5	433.5	435.3	439.8
167.5°	462.5	457.4	451.5	447.5	445.0	441.6	440.7	441.6	440.7	441.6	445.0
170°	461.1	456.6	452.2	449.5	447.8	445.1	444.3	445.1	444.3	445.1	447.8
172.5°	459.7	455.9	452.9	450.9	449.9	447.9	447.8	448.6	447.8	447.9	449.9
175°	457.5	454.9	453.1	453.1	452.2	451.3	451.3	452.2	451.3	451.3	452.2
177.5°	455.2	453.8	453.1	453.1	453.1	452.4	453.1	453.8	453.1	452.4	453.1
180°	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1



TEST NUMBER: P332564-940

CATALOG NUMBER: SA4XXDIP-C575D1035U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5
2.5°	821.4	818.9	815.3	810.3	806.2	801.7	800.6	799.0	802.3	799.5	798.7
5°	794.5	787.2	777.8	767.1	760.9	751.8	750.1	746.6	743.2	742.8	739.3
7.5°	766.0	755.3	743.1	732.1	721.9	712.1	705.6	704.3	699.1	696.2	692.7
10°	747.7	734.5	720.2	709.9	698.0	687.7	680.4	676.2	672.7	668.9	665.5
12.5°	726.0	712.0	700.3	689.0	675.0	667.1	655.1	647.9	647.2	647.3	638.3
15°	700.8	687.0	668.9	653.0	645.3	630.1	623.5	615.1	609.9	604.8	600.6
17.5°	672.1	654.8	640.7	622.3	607.8	595.7	586.9	581.9	574.2	566.8	561.4
20°	654.0	635.6	620.7	601.3	585.3	570.4	563.1	556.2	550.3	544.0	538.1
22.5°	635.7	616.4	598.2	579.3	564.5	548.8	541.7	532.3	526.6	523.2	517.3
25°	606.8	586.0	565.2	547.2	531.9	518.0	508.6	501.3	495.1	492.3	488.5
27.5°	575.4	554.7	534.7	514.2	496.9	486.8	479.3	473.8	470.2	466.5	464.8
30°	555.4	534.0	512.5	493.4	477.4	467.3	460.4	456.6	453.8	452.1	450.3
32.5°	535.2	514.0	491.3	473.9	459.7	450.7	445.4	441.6	440.2	439.6	439.0
35°	502.7	481.3	460.4	444.8	431.2	427.8	423.3	421.2	420.5	422.9	424.0
37.5°	471.3	451.3	432.1	417.1	408.1	403.1	401.5	401.6	404.1	406.3	408.8
40°	451.0	431.6	413.6	400.4	392.1	389.0	388.3	389.9	392.7	395.2	398.0
42.5°	431.3	412.1	395.8	383.4	377.6	374.8	375.2	376.9	380.8	383.8	388.0
45°	400.7	384.8	368.8	358.7	353.9	354.5	354.5	357.7	361.5	366.0	370.5
47.5°	371.9	355.8	342.7	334.2	331.7	331.1	333.1	337.2	342.7	348.2	354.5
50°	352.5	337.2	325.7	318.2	315.4	316.4	319.2	323.0	329.6	336.5	343.1
52.5°	332.8	318.9	308.3	301.2	299.3	301.1	303.9	310.0	315.8	323.2	331.2
55°	302.2	290.4	282.0	276.9	276.2	277.2	280.4	287.0	295.2	304.6	312.3
57.5°	271.7	261.9	254.2	250.7	251.0	252.0	257.1	264.9	273.8	283.8	293.6
60°	251.2	242.2	235.9	233.2	233.5	235.6	241.8	249.1	260.2	269.9	280.4
62.5°	231.8	223.8	217.8	215.3	214.9	219.5	225.4	233.0	244.2	254.9	266.2
65°	200.5	194.3	189.4	188.1	189.0	192.5	200.2	210.3	219.6	231.0	242.9
67.5°	170.0	164.9	161.6	162.2	163.5	168.5	175.0	183.6	194.2	206.1	217.8
70°	150.6	145.7	142.9	143.3	145.3	151.6	157.2	165.9	177.3	189.4	199.1
72.5°	130.6	127.4	124.9	126.4	128.4	132.8	139.6	148.4	158.5	169.7	180.0
75°	100.2	100.2	98.9	100.0	103.1	107.2	112.4	121.5	131.5	140.5	148.8
77.5°	74.4	73.7	74.5	75.8	77.6	82.5	88.5	95.0	102.5	111.6	118.4
80°	56.9	57.2	58.9	61.1	61.8	65.5	71.8	77.8	83.6	91.2	97.8
82.5°	42.7	43.1	44.0	46.6	47.3	51.5	55.5	61.3	66.7	71.8	77.3
85°	23.3	23.3	25.0	26.0	27.7	30.5	33.0	36.5	41.3	44.8	49.9
87.5°	10.3	10.3	12.5	13.0	14.3	16.0	16.3	19.6	20.9	22.5	25.0
90°	7.1	7.1	12.5	12.5	14.3	16.1	15.2	16.1	16.9	17.8	17.8
92.5°	47.0	65.5	110.8	179.9	247.1	282.4	235.2	174.9	131.6	104.7	86.9
95°	73.9	111.3	188.7	334.7	547.5	725.5	746.0	659.6	521.7	402.3	316.0
97.5°	89.3	120.7	180.4	300.9	512.4	764.1	937.2	974.6	923.3	836.2	743.3
100°	101.5	130.0	182.5	283.1	464.7	715.7	943.6	1073.6	1091.4	1047.8	981.9
102.5°	115.0	142.0	189.6	278.1	432.7	655.2	890.2	1068.6	1156.9	1169.6	1142.1
105°	137.9	163.8	206.5	280.4	405.0	584.0	793.2	997.0	1151.0	1239.1	1275.7
107.5°	161.7	187.1	226.3	293.6	400.0	544.1	714.8	895.4	1059.4	1183.5	1262.8
110°	178.1	202.1	241.2	303.5	401.4	530.6	675.6	834.1	988.1	1117.2	1215.1



TEST NUMBER: P332564-940

CATALOG NUMBER: SA4XXDIP-C575D1035U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	193.7	217.8	255.5	314.2	405.7	524.1	653.6	789.3	925.4	1047.4	1145.3
115°	218.1	242.1	277.8	331.2	413.9	520.8	632.9	744.2	853.7	957.9	1043.3
117.5°	240.5	265.5	299.3	348.4	422.7	519.9	623.7	722.1	812.8	894.7	967.1
120°	255.5	280.4	314.2	360.5	429.1	519.9	618.7	712.1	795.0	866.2	929.3
122.5°	270.5	294.6	328.5	371.9	435.5	519.2	613.0	703.6	783.5	848.4	903.7
125°	291.1	316.0	348.0	389.1	445.1	518.1	603.6	689.0	765.5	827.0	875.9
127.5°	310.1	335.3	366.2	403.8	452.7	516.1	590.9	671.2	744.4	805.7	852.1
130°	322.3	348.0	378.4	413.0	458.4	515.4	583.1	657.0	727.3	787.8	835.0
132.5°	333.7	358.0	388.3	422.3	463.4	514.7	576.0	642.0	708.1	767.1	814.4
135°	349.8	373.0	402.3	434.4	470.9	513.6	565.3	621.3	679.2	733.5	778.0
137.5°	363.6	385.7	413.0	443.0	475.4	513.4	556.0	602.7	651.7	697.4	737.6
140°	372.1	393.5	420.2	448.6	478.9	512.7	551.1	592.0	633.8	673.9	711.2
142.5°	380.0	400.6	426.6	452.9	481.8	512.7	546.8	582.0	618.8	653.3	685.6
145°	390.8	410.4	433.5	457.5	483.4	511.0	539.5	567.9	598.2	624.9	649.9
147.5°	401.3	418.9	440.7	461.6	484.3	507.7	532.9	556.3	580.4	601.8	621.3
150°	407.7	424.6	444.3	463.8	484.3	505.6	527.9	549.3	569.7	587.5	603.6
152.5°	414.1	429.6	447.1	465.2	482.9	502.0	522.2	541.4	559.0	575.4	588.6
155°	422.8	436.2	451.3	466.5	480.7	496.8	513.6	529.7	543.9	557.2	567.9
157.5°	431.1	441.6	454.3	466.5	478.4	491.2	504.9	517.0	529.0	540.2	548.8
160°	435.3	445.1	455.8	466.5	476.3	487.0	498.6	509.2	519.0	528.8	535.9
162.5°	439.6	447.3	457.2	466.5	474.1	482.7	492.8	501.3	509.7	517.4	523.8
165°	444.3	449.5	457.5	464.7	470.0	476.3	483.4	490.5	495.9	502.0	506.5
167.5°	447.5	451.5	457.4	462.5	465.7	469.8	474.8	480.0	484.1	489.1	491.8
170°	449.5	452.2	456.6	461.1	462.9	465.6	469.1	473.6	476.3	479.8	482.5
172.5°	450.9	452.9	455.9	459.7	460.0	461.3	464.1	467.9	469.8	472.0	473.9
175°	453.1	453.1	454.9	457.5	456.6	456.6	458.4	460.2	461.1	462.9	462.9
177.5°	453.1	453.1	453.8	455.2	453.8	453.8	454.5	455.2	455.9	455.9	456.6
180°	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1



TEST NUMBER: P332564-940

CATALOG NUMBER: SA4XXDIP-C575D1035U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5
2.5°	798.1	797.5	795.6	795.3	795.6	797.5	798.1	798.7	799.5	802.3	799.0
5°	737.3	735.6	734.5	738.3	734.5	735.6	737.3	739.3	742.8	743.2	746.6
7.5°	691.4	690.0	687.0	686.0	687.0	690.0	691.4	692.7	696.2	699.1	704.3
10°	662.0	660.6	657.8	657.1	657.8	660.6	662.0	665.5	668.9	672.7	676.2
12.5°	633.6	630.9	630.4	631.1	630.4	630.9	633.6	638.3	647.3	647.2	647.9
15°	596.0	594.7	590.8	591.9	590.8	594.7	596.0	600.6	604.8	609.9	615.1
17.5°	559.0	557.3	552.7	556.8	552.7	557.3	559.0	561.4	566.8	574.2	581.9
20°	535.7	532.9	530.5	530.1	530.5	532.9	535.7	538.1	544.0	550.3	556.2
22.5°	513.4	511.0	510.8	508.5	510.8	511.0	513.4	517.3	523.2	526.6	532.3
25°	485.7	483.3	482.6	480.9	482.6	483.3	485.7	488.5	492.3	495.1	501.3
27.5°	464.4	463.2	462.0	462.5	462.0	463.2	464.4	464.8	466.5	470.2	473.8
30°	451.4	451.0	450.3	450.3	450.3	451.0	451.4	450.3	452.1	453.8	456.6
32.5°	440.6	440.5	440.9	440.9	440.9	440.5	440.6	439.0	439.6	440.2	441.6
35°	425.3	426.4	427.1	426.1	427.1	426.4	425.3	424.0	422.9	420.5	421.2
37.5°	411.6	412.7	413.7	414.8	413.7	412.7	411.6	408.8	406.3	404.1	401.6
40°	401.1	403.5	404.2	405.9	404.2	403.5	401.1	398.0	395.2	392.7	389.9
42.5°	391.1	393.8	395.6	395.9	395.6	393.8	391.1	388.0	383.8	380.8	376.9
45°	375.8	378.5	380.9	380.9	380.9	378.5	375.8	370.5	366.0	361.5	357.7
47.5°	359.9	363.9	366.3	366.9	366.3	363.9	359.9	354.5	348.2	342.7	337.2
50°	349.0	353.9	356.3	358.0	356.3	353.9	349.0	343.1	336.5	329.6	323.0
52.5°	338.5	343.3	346.6	347.5	346.6	343.3	338.5	331.2	323.2	315.8	310.0
55°	320.2	327.2	331.0	332.3	331.0	327.2	320.2	312.3	304.6	295.2	287.0
57.5°	303.0	309.4	313.9	314.9	313.9	309.4	303.0	293.6	283.8	273.8	264.9
60°	289.7	296.7	302.2	303.3	302.2	296.7	289.7	280.4	269.9	260.2	249.1
62.5°	276.1	283.3	288.3	291.1	288.3	283.3	276.1	266.2	254.9	244.2	233.0
65°	252.6	259.8	264.7	265.7	264.7	259.8	252.6	242.9	231.0	219.6	210.3
67.5°	226.9	234.2	237.4	239.4	237.4	234.2	226.9	217.8	206.1	194.2	183.6
70°	208.8	214.7	218.2	220.0	218.2	214.7	208.8	199.1	189.4	177.3	165.9
72.5°	188.3	194.5	198.5	198.9	198.5	194.5	188.3	180.0	169.7	158.5	148.4
75°	156.9	162.4	164.4	164.4	164.4	162.4	156.9	148.8	140.5	131.5	121.5
77.5°	124.1	127.0	129.7	130.2	129.7	127.0	124.1	118.4	111.6	102.5	95.0
80°	103.1	104.8	106.8	106.8	106.8	104.8	103.1	97.8	91.2	83.6	77.8
82.5°	81.4	82.8	84.9	84.6	84.9	82.8	81.4	77.3	71.8	66.7	61.3
85°	49.2	52.4	52.1	51.4	52.1	52.4	49.2	49.9	44.8	41.3	36.5
87.5°	25.9	26.4	27.0	27.6	27.0	26.4	25.9	25.0	22.5	20.9	19.6
90°	18.7	19.6	18.7	18.7	18.7	19.6	18.7	17.8	17.8	16.9	16.1
92.5°	76.4	71.6	68.6	68.6	68.6	71.6	76.4	86.9	104.7	131.6	174.9
95°	272.4	244.8	228.8	217.2	228.8	244.8	272.4	316.0	402.3	521.7	659.6
97.5°	679.4	625.8	599.1	580.6	599.1	625.8	679.4	743.3	836.2	923.3	974.6
100°	904.5	850.2	823.4	816.4	823.4	850.2	904.5	981.9	1047.8	1091.4	1073.6
102.5°	1094.6	1055.3	1027.2	1021.5	1027.2	1055.3	1094.6	1142.1	1169.6	1156.9	1068.6
105°	1277.5	1270.3	1257.8	1252.5	1257.8	1270.3	1277.5	1275.7	1239.1	1151.0	997.0
107.5°	1306.8	1327.1	1336.1	1338.4	1336.1	1327.1	1306.8	1262.8	1183.5	1059.4	895.4
110°	1278.4	1315.7	1331.8	1339.8	1331.8	1315.7	1278.4	1215.1	1117.2	988.1	834.1



TEST NUMBER: P332564-940

CATALOG NUMBER: SA4XXDIP-C575D1035U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1217.1	1262.3	1284.8	1297.7	1284.8	1262.3	1217.1	1145.3	1047.4	925.4	789.3
115°	1113.7	1167.1	1195.5	1202.7	1195.5	1167.1	1113.7	1043.3	957.9	853.7	744.2
117.5°	1027.2	1072.0	1100.8	1106.3	1100.8	1072.0	1027.2	967.1	894.7	812.8	722.1
120°	980.1	1019.3	1042.4	1052.2	1042.4	1019.3	980.1	929.3	866.2	795.0	712.1
122.5°	946.6	980.1	999.7	1009.5	999.7	980.1	946.6	903.7	848.4	783.5	703.6
125°	911.6	937.4	954.3	959.7	954.3	937.4	911.6	875.9	827.0	765.5	689.0
127.5°	887.9	910.9	925.1	930.4	925.1	910.9	887.9	852.1	805.7	744.4	671.2
130°	871.5	893.8	908.0	913.4	908.0	893.8	871.5	835.0	787.8	727.3	657.0
132.5°	850.2	875.2	888.8	894.1	888.8	875.2	850.2	814.4	767.1	708.1	642.0
135°	813.7	838.6	852.8	858.2	852.8	838.6	813.7	778.0	733.5	679.2	621.3
137.5°	770.9	795.5	807.3	813.7	807.3	795.5	770.9	737.6	697.4	651.7	602.7
140°	742.4	762.1	774.5	781.6	774.5	762.1	742.4	711.2	673.9	633.8	592.0
142.5°	713.2	731.4	742.4	747.4	742.4	731.4	713.2	685.6	653.3	618.8	582.0
145°	672.1	687.2	696.2	700.6	696.2	687.2	672.1	649.9	624.9	598.2	567.9
147.5°	637.8	650.8	657.5	659.1	657.5	650.8	637.8	621.3	601.8	580.4	556.3
150°	617.8	629.4	634.7	635.6	634.7	629.4	617.8	603.6	587.5	569.7	549.3
152.5°	600.7	610.1	613.3	614.2	613.3	610.1	600.7	588.6	575.4	559.0	541.4
155°	576.8	584.0	586.7	586.7	586.7	584.0	576.8	567.9	557.2	543.9	529.7
157.5°	555.4	560.8	562.4	562.4	562.4	560.8	555.4	548.8	540.2	529.0	517.0
160°	541.3	546.6	547.5	547.5	547.5	546.6	541.3	535.9	528.8	519.0	509.2
162.5°	527.7	533.1	534.0	533.2	534.0	533.1	527.7	523.8	517.4	509.7	501.3
165°	510.1	513.6	512.7	511.8	512.7	513.6	510.1	506.5	502.0	495.9	490.5
167.5°	493.6	495.9	495.7	495.0	495.7	495.9	493.6	491.8	489.1	484.1	480.0
170°	484.3	485.2	484.3	484.3	484.3	485.2	484.3	482.5	479.8	476.3	473.6
172.5°	475.0	475.9	475.0	473.6	475.0	475.9	475.0	473.9	472.0	469.8	467.9
175°	462.9	464.7	462.9	461.1	462.9	464.7	462.9	462.9	462.9	461.1	460.2
177.5°	455.9	456.6	455.2	453.8	455.2	456.6	455.9	456.6	455.9	455.9	455.2
180°	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1



TEST NUMBER: P332564-940

CATALOG NUMBER: SA4XXDIP-C575D1035U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5
2.5°	800.6	801.7	806.2	810.3	815.3	818.9	821.4	824.2	830.0	834.7	839.2
5°	750.1	751.8	760.9	767.1	777.8	787.2	794.5	802.5	811.9	824.7	836.5
7.5°	705.6	712.1	721.9	732.1	743.1	755.3	766.0	778.0	794.2	811.8	830.0
10°	680.4	687.7	698.0	709.9	720.2	734.5	747.7	761.9	780.2	801.8	823.3
12.5°	655.1	667.1	675.0	689.0	700.3	712.0	726.0	744.7	766.2	788.7	814.7
15°	623.5	630.1	645.3	653.0	668.9	687.0	700.8	719.6	740.4	770.3	799.3
17.5°	586.9	595.7	607.8	622.3	640.7	654.8	672.1	691.3	717.6	747.2	783.7
20°	563.1	570.4	585.3	601.3	620.7	635.6	654.0	672.7	699.8	731.4	769.5
22.5°	541.7	548.8	564.5	579.3	598.2	616.4	635.7	657.5	683.4	716.7	755.6
25°	508.6	518.0	531.9	547.2	565.2	586.0	606.8	626.2	654.0	689.0	730.7
27.5°	479.3	486.8	496.9	514.2	534.7	554.7	575.4	599.9	626.5	663.6	706.8
30°	460.4	467.3	477.4	493.4	512.5	534.0	555.4	579.1	606.8	643.5	687.7
32.5°	445.4	450.7	459.7	473.9	491.3	514.0	535.2	559.6	588.8	625.0	668.0
35°	423.3	427.8	431.2	444.8	460.4	481.3	502.7	528.8	556.9	591.2	634.2
37.5°	401.5	403.1	408.1	417.1	432.1	451.3	471.3	496.9	525.7	560.6	599.4
40°	388.3	389.0	392.1	400.4	413.6	431.6	451.0	476.4	503.7	536.7	575.2
42.5°	375.2	374.8	377.6	383.4	395.8	412.1	431.3	454.4	481.9	512.3	548.6
45°	354.5	354.5	353.9	358.7	368.8	384.8	400.7	422.9	445.9	475.6	506.2
47.5°	333.1	331.1	331.7	334.2	342.7	355.8	371.9	390.1	410.3	435.6	462.4
50°	319.2	316.4	315.4	318.2	325.7	337.2	352.5	368.5	387.5	409.7	432.7
52.5°	303.9	301.1	299.3	301.2	308.3	318.9	332.8	346.8	363.9	382.0	401.8
55°	280.4	277.2	276.2	276.9	282.0	290.4	302.2	315.0	327.9	342.8	356.7
57.5°	257.1	252.0	251.0	250.7	254.2	261.9	271.7	282.9	292.2	301.2	316.0
60°	241.8	235.6	233.5	233.2	235.9	242.2	251.2	262.3	268.9	275.1	287.9
62.5°	225.4	219.5	214.9	215.3	217.8	223.8	231.8	239.8	244.2	251.0	259.7
65°	200.2	192.5	189.0	188.1	189.4	194.3	200.5	205.7	210.6	213.4	221.7
67.5°	175.0	168.5	163.5	162.2	161.6	164.9	170.0	173.2	176.6	179.1	184.0
70°	157.2	151.6	145.3	143.3	142.9	145.7	150.6	151.0	155.8	156.9	162.0
72.5°	139.6	132.8	128.4	126.4	124.9	127.4	130.6	131.5	134.1	136.0	138.8
75°	112.4	107.2	103.1	100.0	98.9	100.2	100.2	102.0	103.7	104.8	107.9
77.5°	88.5	82.5	77.6	75.8	74.5	73.7	74.4	75.4	74.6	76.4	77.1
80°	71.8	65.5	61.8	61.1	58.9	57.2	56.9	58.0	56.5	57.2	59.3
82.5°	55.5	51.5	47.3	46.6	44.0	43.1	42.7	42.1	42.1	42.0	42.4
85°	33.0	30.5	27.7	26.0	25.0	23.3	23.3	22.6	21.8	21.1	21.5
87.5°	16.3	16.0	14.3	13.0	12.5	10.3	10.3	9.3	8.8	8.0	7.4
90°	15.2	16.1	14.3	12.5	12.5	7.1	7.1	6.2	5.4	2.7	0.9
92.5°	235.2	282.4	247.1	179.9	110.8	65.5	47.0	34.0	23.2	14.8	10.2
95°	746.0	725.5	547.5	334.7	188.7	111.3	73.9	52.5	40.9	32.0	29.3
97.5°	937.2	764.1	512.4	300.9	180.4	120.7	89.3	71.1	60.4	52.7	52.7
100°	943.6	715.7	464.7	283.1	182.5	130.0	101.5	84.5	73.9	67.7	67.7
102.5°	890.2	655.2	432.7	278.1	189.6	142.0	115.0	98.8	88.8	83.3	81.9
105°	793.2	584.0	405.0	280.4	206.5	163.8	137.9	122.0	111.3	106.8	104.2
107.5°	714.8	544.1	400.0	293.6	226.3	187.1	161.7	146.3	134.9	130.5	128.8
110°	675.6	530.6	401.4	303.5	241.2	202.1	178.1	162.0	151.3	146.9	145.1



TEST NUMBER: P332564-940

CATALOG NUMBER: SA4XXDIP-C575D1035U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	653.6	524.1	405.7	314.2	255.5	217.8	193.7	177.7	167.7	162.6	160.8
115°	632.9	520.8	413.9	331.2	277.8	242.1	218.1	201.2	192.3	186.0	183.4
117.5°	623.7	519.9	422.7	348.4	299.3	265.5	240.5	224.7	214.9	209.4	206.9
120°	618.7	519.9	429.1	360.5	314.2	280.4	255.5	240.3	230.6	224.4	222.6
122.5°	613.0	519.2	435.5	371.9	328.5	294.6	270.5	253.9	244.8	238.5	236.8
125°	603.6	518.1	445.1	389.1	348.0	316.0	291.1	274.2	264.4	259.0	255.5
127.5°	590.9	516.1	452.7	403.8	366.2	335.3	310.1	292.5	281.3	274.9	272.1
130°	583.1	515.4	458.4	413.0	378.4	348.0	322.3	305.3	291.9	284.9	281.3
132.5°	576.0	514.7	463.4	422.3	388.3	358.0	333.7	315.3	302.6	293.4	290.5
135°	565.3	513.6	470.9	434.4	402.3	373.0	349.8	331.2	316.0	307.1	303.5
137.5°	556.0	513.4	475.4	443.0	413.0	385.7	363.6	344.1	329.8	319.9	316.6
140°	551.1	512.7	478.9	448.6	420.2	393.5	372.1	353.4	338.3	328.5	325.8
142.5°	546.8	512.7	481.8	452.9	426.6	400.6	380.0	361.9	347.5	338.5	335.8
145°	539.5	511.0	483.4	457.5	433.5	410.4	390.8	373.9	361.4	352.5	349.8
147.5°	532.9	507.7	484.3	461.6	440.7	418.9	401.3	387.3	374.4	366.6	365.7
150°	527.9	505.6	484.3	463.8	444.3	424.6	407.7	394.4	383.7	376.6	375.7
152.5°	522.2	502.0	482.9	465.2	447.1	429.6	414.1	402.2	392.3	385.1	385.0
155°	513.6	496.8	480.7	466.5	451.3	436.2	422.8	413.0	404.1	398.8	397.9
157.5°	504.9	491.2	478.4	466.5	454.3	441.6	431.1	422.5	415.5	410.5	410.5
160°	498.6	487.0	476.3	466.5	455.8	445.1	435.3	428.2	422.0	418.4	418.4
162.5°	492.8	482.7	474.1	466.5	457.2	447.3	439.6	433.2	427.7	424.8	425.5
165°	483.4	476.3	470.0	464.7	457.5	449.5	444.3	439.8	435.3	433.5	433.5
167.5°	474.8	469.8	465.7	462.5	457.4	451.5	447.5	445.0	441.6	440.7	441.6
170°	469.1	465.6	462.9	461.1	456.6	452.2	449.5	447.8	445.1	444.3	445.1
172.5°	464.1	461.3	460.0	459.7	455.9	452.9	450.9	449.9	447.9	447.8	448.6
175°	458.4	456.6	456.6	457.5	454.9	453.1	453.1	452.2	451.3	451.3	452.2
177.5°	454.5	453.8	453.8	455.2	453.8	453.1	453.1	453.1	452.4	453.1	453.8
180°	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1



TEST NUMBER: P332564-940

CATALOG NUMBER: SA4XXDIP-C575D1035U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5
2.5°	843.1	845.9	849.4	855.6	857.8	860.6	864.4	864.2	865.3	869.4	878.3
5°	846.2	856.9	867.4	879.9	893.0	901.7	913.6	920.8	928.1	937.5	953.4
7.5°	847.5	864.5	883.6	905.5	925.1	947.5	965.1	981.6	996.5	1016.3	1035.3
10°	845.5	868.4	893.0	920.8	950.3	975.3	997.8	1023.5	1045.4	1069.3	1090.8
12.5°	841.9	869.5	902.5	933.5	968.0	1005.0	1033.0	1059.0	1088.1	1115.6	1148.8
15°	833.7	871.6	910.1	951.0	997.1	1039.8	1080.4	1114.0	1145.3	1186.6	1229.9
17.5°	823.3	864.1	912.7	962.2	1010.5	1059.3	1109.5	1160.0	1199.4	1250.7	1284.7
20°	813.6	860.8	910.7	969.7	1018.0	1078.7	1128.6	1177.5	1231.6	1282.6	1323.3
22.5°	800.0	851.6	904.6	963.3	1026.8	1087.5	1145.3	1198.4	1252.5	1308.0	1357.1
25°	782.7	829.6	892.3	958.9	1022.1	1088.1	1154.3	1220.9	1279.2	1337.8	1383.7
27.5°	753.3	812.4	870.9	939.7	1009.9	1084.4	1155.3	1225.0	1286.0	1334.3	1362.7
30°	738.3	789.6	853.2	922.2	998.2	1078.3	1152.2	1220.6	1277.5	1316.0	1327.4
32.5°	716.1	769.1	831.3	902.8	983.2	1065.5	1142.5	1206.9	1254.5	1274.6	1260.8
35°	683.1	731.0	793.8	867.0	950.7	1038.4	1114.4	1168.9	1193.2	1174.1	1126.5
37.5°	643.5	691.1	754.1	826.0	912.6	1001.7	1070.5	1109.6	1101.6	1054.2	983.3
40°	615.8	660.2	720.2	798.0	882.3	971.8	1032.2	1053.4	1031.2	963.1	887.9
42.5°	585.1	628.3	688.6	763.6	852.8	935.4	988.0	989.8	952.6	871.3	795.7
45°	538.1	579.4	636.3	714.3	796.9	874.7	909.4	892.3	823.7	745.2	669.2
47.5°	491.9	527.6	583.7	657.8	736.2	801.6	818.9	788.3	715.1	638.9	568.5
50°	458.0	494.1	546.8	617.6	693.2	749.8	758.0	717.5	645.7	569.0	513.8
52.5°	425.5	461.3	512.1	577.6	646.8	697.9	698.1	651.1	579.6	511.3	459.9
55°	377.8	410.1	455.9	514.5	576.3	616.2	606.5	557.9	495.8	436.5	391.7
57.5°	331.9	360.0	402.2	451.1	505.5	538.4	522.3	475.5	420.1	369.8	335.8
60°	302.2	328.9	365.0	411.2	456.9	482.6	467.3	425.0	374.0	333.4	303.9
62.5°	273.3	295.9	330.6	370.6	413.0	432.1	418.5	376.7	332.7	296.0	272.0
65°	232.5	250.8	278.6	313.0	343.8	360.2	348.7	309.8	276.2	249.8	230.7
67.5°	194.3	208.7	229.7	257.3	283.5	292.3	281.9	254.8	226.3	205.2	191.7
70°	167.9	181.5	199.1	220.3	243.2	252.6	242.2	220.7	197.4	178.0	164.8
72.5°	144.9	155.3	170.3	188.4	206.3	215.7	208.6	187.9	168.3	153.8	142.6
75°	110.3	119.3	129.7	142.6	156.5	162.7	156.5	142.2	128.7	118.0	109.9
77.5°	80.3	85.1	93.1	102.7	111.4	116.2	110.8	101.1	92.8	85.5	81.5
80°	61.1	64.6	70.1	77.8	83.6	88.1	84.6	76.7	70.1	65.2	63.5
82.5°	44.4	46.7	50.4	56.1	60.0	62.3	60.8	55.0	52.3	48.0	46.3
85°	21.8	23.3	25.7	27.4	30.9	31.2	31.6	29.2	26.8	25.7	24.3
87.5°	8.0	8.8	9.8	10.9	11.9	13.3	13.0	13.4	12.7	12.2	11.2
90°	2.7	5.4	6.2	7.1	7.1	12.5	12.5	14.3	16.1	15.2	16.1
92.5°	14.8	23.2	34.0	47.0	65.5	110.8	179.9	247.1	282.4	235.2	174.9
95°	32.0	40.9	52.5	73.9	111.3	188.7	334.7	547.5	725.5	746.0	659.6
97.5°	52.7	60.4	71.1	89.3	120.7	180.4	300.9	512.4	764.1	937.2	974.6
100°	67.7	73.9	84.5	101.5	130.0	182.5	283.1	464.7	715.7	943.6	1073.6
102.5°	83.3	88.8	98.8	115.0	142.0	189.6	278.1	432.7	655.2	890.2	1068.6
105°	106.8	111.3	122.0	137.9	163.8	206.5	280.4	405.0	584.0	793.2	997.0
107.5°	130.5	134.9	146.3	161.7	187.1	226.3	293.6	400.0	544.1	714.8	895.4
110°	146.9	151.3	162.0	178.1	202.1	241.2	303.5	401.4	530.6	675.6	834.1



TEST NUMBER: P332564-940

CATALOG NUMBER: SA4XXDIP-C575D1035U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	162.6	167.7	177.7	193.7	217.8	255.5	314.2	405.7	524.1	653.6	789.3
115°	186.0	192.3	201.2	218.1	242.1	277.8	331.2	413.9	520.8	632.9	744.2
117.5°	209.4	214.9	224.7	240.5	265.5	299.3	348.4	422.7	519.9	623.7	722.1
120°	224.4	230.6	240.3	255.5	280.4	314.2	360.5	429.1	519.9	618.7	712.1
122.5°	238.5	244.8	253.9	270.5	294.6	328.5	371.9	435.5	519.2	613.0	703.6
125°	259.0	264.4	274.2	291.1	316.0	348.0	389.1	445.1	518.1	603.6	689.0
127.5°	274.9	281.3	292.5	310.1	335.3	366.2	403.8	452.7	516.1	590.9	671.2
130°	284.9	291.9	305.3	322.3	348.0	378.4	413.0	458.4	515.4	583.1	657.0
132.5°	293.4	302.6	315.3	333.7	358.0	388.3	422.3	463.4	514.7	576.0	642.0
135°	307.1	316.0	331.2	349.8	373.0	402.3	434.4	470.9	513.6	565.3	621.3
137.5°	319.9	329.8	344.1	363.6	385.7	413.0	443.0	475.4	513.4	556.0	602.7
140°	328.5	338.3	353.4	372.1	393.5	420.2	448.6	478.9	512.7	551.1	592.0
142.5°	338.5	347.5	361.9	380.0	400.6	426.6	452.9	481.8	512.7	546.8	582.0
145°	352.5	361.4	373.9	390.8	410.4	433.5	457.5	483.4	511.0	539.5	567.9
147.5°	366.6	374.4	387.3	401.3	418.9	440.7	461.6	484.3	507.7	532.9	556.3
150°	376.6	383.7	394.4	407.7	424.6	444.3	463.8	484.3	505.6	527.9	549.3
152.5°	385.1	392.3	402.2	414.1	429.6	447.1	465.2	482.9	502.0	522.2	541.4
155°	398.8	404.1	413.0	422.8	436.2	451.3	466.5	480.7	496.8	513.6	529.7
157.5°	410.5	415.5	422.5	431.1	441.6	454.3	466.5	478.4	491.2	504.9	517.0
160°	418.4	422.0	428.2	435.3	445.1	455.8	466.5	476.3	487.0	498.6	509.2
162.5°	424.8	427.7	433.2	439.6	447.3	457.2	466.5	474.1	482.7	492.8	501.3
165°	433.5	435.3	439.8	444.3	449.5	457.5	464.7	470.0	476.3	483.4	490.5
167.5°	440.7	441.6	445.0	447.5	451.5	457.4	462.5	465.7	469.8	474.8	480.0
170°	444.3	445.1	447.8	449.5	452.2	456.6	461.1	462.9	465.6	469.1	473.6
172.5°	447.8	447.9	449.9	450.9	452.9	455.9	459.7	460.0	461.3	464.1	467.9
175°	451.3	451.3	452.2	453.1	453.1	454.9	457.5	456.6	456.6	458.4	460.2
177.5°	453.1	452.4	453.1	453.1	453.1	453.8	455.2	453.8	453.8	454.5	455.2
180°	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1



TEST NUMBER: P332564-940

CATALOG NUMBER: SA4XXDIP-C575D1035U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	837.5	837.5	837.5	837.5	837.5	837.5	837.5
2.5°	882.8	883.3	885.8	887.8	888.3	891.1	891.4
5°	960.4	966.3	977.7	978.7	980.4	989.5	982.6
7.5°	1051.2	1066.2	1076.2	1085.0	1088.2	1092.2	1091.4
10°	1109.6	1131.8	1142.8	1160.6	1161.3	1165.7	1163.0
12.5°	1168.1	1193.9	1214.2	1217.5	1232.3	1234.6	1238.5
15°	1251.1	1278.5	1306.6	1316.7	1337.1	1342.0	1349.6
17.5°	1329.1	1357.1	1376.8	1402.8	1411.2	1422.5	1414.9
20°	1371.8	1402.4	1427.4	1447.8	1456.5	1462.8	1462.0
22.5°	1397.7	1428.4	1448.7	1464.2	1472.3	1475.0	1474.8
25°	1413.8	1431.6	1437.8	1443.7	1434.7	1431.6	1432.9
27.5°	1368.9	1364.2	1348.0	1326.6	1304.4	1286.7	1277.2
30°	1307.0	1279.9	1255.3	1212.3	1190.0	1176.9	1165.0
32.5°	1219.2	1176.3	1129.0	1089.6	1064.3	1044.7	1041.8
35°	1069.0	1004.4	946.5	898.2	873.3	852.1	847.2
37.5°	908.8	841.8	789.6	747.1	720.2	705.3	691.4
40°	802.5	744.9	693.6	657.5	637.0	626.2	617.6
42.5°	720.6	668.0	617.0	589.4	571.0	564.4	559.3
45°	607.5	558.6	523.2	502.4	491.6	480.5	475.3
47.5°	516.9	477.2	453.8	436.1	424.6	418.0	414.6
50°	465.6	433.0	412.1	398.7	388.3	383.0	380.2
52.5°	420.1	393.3	375.9	365.1	358.0	354.2	353.0
55°	361.9	341.4	330.3	320.9	315.8	312.3	310.9
57.5°	314.5	298.8	289.8	282.0	280.1	277.1	276.2
60°	283.5	271.3	263.7	258.5	256.7	253.2	254.0
62.5°	256.0	246.0	239.5	236.6	234.3	231.3	232.3
65°	216.5	209.2	205.7	203.0	200.2	198.5	199.8
67.5°	181.6	176.6	171.9	170.3	169.0	168.7	167.2
70°	158.9	154.7	150.6	149.5	149.5	148.1	147.8
72.5°	137.0	133.9	131.2	130.4	129.3	129.8	128.4
75°	105.8	103.3	102.4	101.3	100.9	100.9	100.0
77.5°	78.2	76.4	74.7	74.7	73.5	73.0	72.9
80°	59.3	58.7	57.2	57.2	56.5	56.9	56.2
82.5°	44.6	43.6	43.3	42.8	41.8	41.9	41.2
85°	23.9	22.9	22.6	21.5	20.8	21.5	20.8
87.5°	11.7	11.6	11.3	11.0	10.9	10.7	9.8
90°	16.9	17.8	17.8	18.7	19.6	18.7	18.7
92.5°	131.6	104.7	86.9	76.4	71.6	68.6	68.6
95°	521.7	402.3	316.0	272.4	244.8	228.8	217.2
97.5°	923.3	836.2	743.3	679.4	625.8	599.1	580.6
100°	1091.4	1047.8	981.9	904.5	850.2	823.4	816.4
102.5°	1156.9	1169.6	1142.1	1094.6	1055.3	1027.2	1021.5
105°	1151.0	1239.1	1275.7	1277.5	1270.3	1257.8	1252.5
107.5°	1059.4	1183.5	1262.8	1306.8	1327.1	1336.1	1338.4
110°	988.1	1117.2	1215.1	1278.4	1315.7	1331.8	1339.8



TEST NUMBER: P332564-940

CATALOG NUMBER: SA4XXDIP-C575D1035U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	925.4	1047.4	1145.3	1217.1	1262.3	1284.8	1297.7
115°	853.7	957.9	1043.3	1113.7	1167.1	1195.5	1202.7
117.5°	812.8	894.7	967.1	1027.2	1072.0	1100.8	1106.3
120°	795.0	866.2	929.3	980.1	1019.3	1042.4	1052.2
122.5°	783.5	848.4	903.7	946.6	980.1	999.7	1009.5
125°	765.5	827.0	875.9	911.6	937.4	954.3	959.7
127.5°	744.4	805.7	852.1	887.9	910.9	925.1	930.4
130°	727.3	787.8	835.0	871.5	893.8	908.0	913.4
132.5°	708.1	767.1	814.4	850.2	875.2	888.8	894.1
135°	679.2	733.5	778.0	813.7	838.6	852.8	858.2
137.5°	651.7	697.4	737.6	770.9	795.5	807.3	813.7
140°	633.8	673.9	711.2	742.4	762.1	774.5	781.6
142.5°	618.8	653.3	685.6	713.2	731.4	742.4	747.4
145°	598.2	624.9	649.9	672.1	687.2	696.2	700.6
147.5°	580.4	601.8	621.3	637.8	650.8	657.5	659.1
150°	569.7	587.5	603.6	617.8	629.4	634.7	635.6
152.5°	559.0	575.4	588.6	600.7	610.1	613.3	614.2
155°	543.9	557.2	567.9	576.8	584.0	586.7	586.7
157.5°	529.0	540.2	548.8	555.4	560.8	562.4	562.4
160°	519.0	528.8	535.9	541.3	546.6	547.5	547.5
162.5°	509.7	517.4	523.8	527.7	533.1	534.0	533.2
165°	495.9	502.0	506.5	510.1	513.6	512.7	511.8
167.5°	484.1	489.1	491.8	493.6	495.9	495.7	495.0
170°	476.3	479.8	482.5	484.3	485.2	484.3	484.3
172.5°	469.8	472.0	473.9	475.0	475.9	475.0	473.6
175°	461.1	462.9	462.9	462.9	464.7	462.9	461.1
177.5°	455.9	455.9	456.6	455.9	456.6	455.2	453.8
180°	453.1	453.1	453.1	453.1	453.1	453.1	453.1

(END OF REPORT)