

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332553-940

Luminaire Tested: **SA4XXDIP-C575D810U940-4F0-1E-UDD-A**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332553-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C575D810U940-4F0-1E-UDD-A
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 810 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5197.0 lumens
Efficiency: N/A
Efficacy: 135.3 lumens/watt
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332553-940
CATALOG NUMBER: SA4XXDIP-C575D810U940-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332553-940

CATALOG NUMBER: SA4XXDIP-C575D810U940-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20				
RC	80					70					50					30				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	45		
1	97	93	89	85	88	85	82	79	71	68	66	58	56	55	45	44	43	38		
2	88	81	75	70	81	74	69	65	62	58	55	51	48	46	40	38	37	32		
3	81	71	64	59	74	66	59	54	55	50	47	45	42	39	36	34	32	27		
4	74	63	56	50	67	58	52	46	49	44	40	40	37	34	32	30	27	24		
5	68	56	48	43	62	52	45	40	44	39	34	36	32	29	29	26	24	21		
6	62	51	43	37	57	47	40	35	40	34	30	33	29	26	26	23	21	18		
7	58	46	38	32	53	42	35	30	36	30	27	30	26	23	24	21	19	16		
8	54	41	34	29	49	38	32	27	33	27	24	27	23	20	22	19	17	15		
9	50	38	30	26	46	35	29	24	30	25	21	25	21	18	20	17	15	13		
10	47	35	28	23	43	32	26	22	28	23	19	23	19	16	19	16	14	12		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	6761	6761	6761	6761
5°	7963	6779	5983	6779
10°	9534	6749	5387	6749
15°	11280	6680	4947	6680
20°	12560	6611	4554	6611
25°	12764	6509	4284	6509
30°	10860	6411	4198	6411
35°	8349	6250	4199	6250
40°	6509	6062	4278	6062
45°	5426	5779	4349	5779
50°	4775	5434	4496	5434
55°	4376	5020	4677	5020
60°	4101	4648	4897	4648
65°	3817	4235	5075	4235
70°	3489	3824	5193	3824
75°	3119	3366	5128	3366
80°	2613	2757	4965	2757
85°	1927	1991	4761	1991



TEST NUMBER: P332553-940

CATALOG NUMBER: SA4XXDIP-C575D810U940-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.6	1.6
10°-20°	251.5	4.8
20°-30°	398.8	7.7
30°-40°	443.8	8.5
40°-50°	404.0	7.8
50°-60°	330.1	6.4
60°-70°	235.7	4.5
70°-80°	129.8	2.5
80°-90°	38.1	0.7
90°-100°	31.9	0.6
100°-110°	203.3	3.9
110°-120°	388.9	7.5
120°-130°	493.7	9.5
130°-140°	528.2	10.2
140°-150°	493.9	9.5
150°-160°	398.3	7.7
160°-170°	256.9	4.9
170°-180°	88.5	1.7
0°-30°	731.9	14.1
0°-40°	1175.7	22.6
0°-60°	1909.9	36.7
0°-90°	2313.5	44.5
90°-120°	624.1	12.0
90°-150°	2139.8	41.2
90°-180°	2884.0	55.5
0°-180°	5197.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	838	838	838	838	838	
5°	983	836	738	836	983	100
15°	1350	799	592	799	1350	381
25°	1433	731	481	731	1433	632
35°	847	634	426	634	847	538
45°	475	506	381	506	475	374
55°	311	357	332	357	311	281
65°	200	222	266	222	200	198
75°	100	108	164	108	100	106
85°	21	22	51	22	21	26
90°	21	2	21	2	21	10
95°	20	38	20	38	20	16
105°	199	210	199	210	199	173
115°	395	392	395	392	395	391
125°	555	551	555	551	555	494
135°	688	683	688	683	688	530
145°	792	788	792	788	792	495
155°	863	864	863	864	863	398
165°	907	911	907	911	907	256
175°	927	932	927	932	927	88
180°	932	932	932	932	932	



TEST NUMBER: P332553-940

CATALOG NUMBER: SA4XXDIP-C575D810U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5
2.5°	891.4	891.1	888.3	887.8	885.8	883.3	882.8	878.3	869.4	865.3	864.2
5°	982.6	989.5	980.4	978.7	977.7	966.3	960.4	953.4	937.5	928.1	920.8
7.5°	1091.4	1092.2	1088.2	1085.0	1076.2	1066.2	1051.2	1035.3	1016.3	996.5	981.6
10°	1163.0	1165.7	1161.3	1160.6	1142.8	1131.8	1109.6	1090.8	1069.3	1045.4	1023.5
12.5°	1238.5	1234.6	1232.3	1217.5	1214.2	1193.9	1168.1	1148.8	1115.6	1088.1	1059.0
15°	1349.6	1342.0	1337.1	1316.7	1306.6	1278.5	1251.1	1229.9	1186.6	1145.3	1114.0
17.5°	1414.9	1422.5	1411.2	1402.8	1376.8	1357.1	1329.1	1284.7	1250.7	1199.4	1160.0
20°	1462.0	1462.8	1456.5	1447.8	1427.4	1402.4	1371.8	1323.3	1282.6	1231.6	1177.5
22.5°	1474.8	1475.0	1472.3	1464.2	1448.7	1428.4	1397.7	1357.1	1308.0	1252.5	1198.4
25°	1432.9	1431.6	1434.7	1443.7	1437.8	1431.6	1413.8	1383.7	1337.8	1279.2	1220.9
27.5°	1277.2	1286.7	1304.4	1326.6	1348.0	1364.2	1368.9	1362.7	1334.3	1286.0	1225.0
30°	1165.0	1176.9	1190.0	1212.3	1255.3	1279.9	1307.0	1327.4	1316.0	1277.5	1220.6
32.5°	1041.8	1044.7	1064.3	1089.6	1129.0	1176.3	1219.2	1260.8	1274.6	1254.5	1206.9
35°	847.2	852.1	873.3	898.2	946.5	1004.4	1069.0	1126.5	1174.1	1193.2	1168.9
37.5°	691.4	705.3	720.2	747.1	789.6	841.8	908.8	983.3	1054.2	1101.6	1109.6
40°	617.6	626.2	637.0	657.5	693.6	744.9	802.5	887.9	963.1	1031.2	1053.4
42.5°	559.3	564.4	571.0	589.4	617.0	668.0	720.6	795.7	871.3	952.6	989.8
45°	475.3	480.5	491.6	502.4	523.2	558.6	607.5	669.2	745.2	823.7	892.3
47.5°	414.6	418.0	424.6	436.1	453.8	477.2	516.9	568.5	638.9	715.1	788.3
50°	380.2	383.0	388.3	398.7	412.1	433.0	465.6	513.8	569.0	645.7	717.5
52.5°	353.0	354.2	358.0	365.1	375.9	393.3	420.1	459.9	511.3	579.6	651.1
55°	310.9	312.3	315.8	320.9	330.3	341.4	361.9	391.7	436.5	495.8	557.9
57.5°	276.2	277.1	280.1	282.0	289.8	298.8	314.5	335.8	369.8	420.1	475.5
60°	254.0	253.2	256.7	258.5	263.7	271.3	283.5	303.9	333.4	374.0	425.0
62.5°	232.3	231.3	234.3	236.6	239.5	246.0	256.0	272.0	296.0	332.7	376.7
65°	199.8	198.5	200.2	203.0	205.7	209.2	216.5	230.7	249.8	276.2	309.8
67.5°	167.2	168.7	169.0	170.3	171.9	176.6	181.6	191.7	205.2	226.3	254.8
70°	147.8	148.1	149.5	149.5	150.6	154.7	158.9	164.8	178.0	197.4	220.7
72.5°	128.4	129.8	129.3	130.4	131.2	133.9	137.0	142.6	153.8	168.3	187.9
75°	100.0	100.9	100.9	101.3	102.4	103.3	105.8	109.9	118.0	128.7	142.2
77.5°	72.9	73.0	73.5	74.7	74.7	76.4	78.2	81.5	85.5	92.8	101.1
80°	56.2	56.9	56.5	57.2	57.2	58.7	59.3	63.5	65.2	70.1	76.7
82.5°	41.2	41.9	41.8	42.8	43.3	43.6	44.6	46.3	48.0	52.3	55.0
85°	20.8	21.5	20.8	21.5	22.6	22.9	23.9	24.3	25.7	26.8	29.2
87.5°	10.3	11.1	11.0	11.2	11.7	11.9	11.9	11.5	12.4	12.5	13.4
90°	21.0	20.6	20.3	20.0	19.7	19.1	18.1	17.2	16.2	15.3	14.1
92.5°	19.3	19.2	19.1	19.1	19.0	18.5	17.6	16.7	15.7	14.8	13.6
95°	20.2	20.1	19.9	19.8	19.6	19.1	18.1	17.2	16.2	15.3	15.2
97.5°	19.5	19.4	19.2	19.1	18.9	18.8	18.7	18.6	18.5	18.4	35.7
100°	19.5	19.4	19.2	19.1	18.9	20.2	22.7	25.4	28.0	30.7	52.1
102.5°	20.1	20.1	20.0	20.0	20.0	34.2	62.6	91.0	119.4	147.8	150.6
105°	198.7	204.3	209.8	215.4	221.1	223.1	221.7	220.3	218.9	217.5	216.8
107.5°	277.0	276.3	275.7	275.2	274.6	273.9	273.2	272.6	271.9	271.3	270.2
110°	310.9	310.5	310.0	309.6	309.1	308.7	308.4	308.1	307.8	307.5	306.6



TEST NUMBER: P332553-940

CATALOG NUMBER: SA4XXDIP-C575D810U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	345.0	344.4	343.8	343.2	342.6	342.3	342.4	342.5	342.6	342.6	342.1
115°	394.7	394.7	394.7	394.7	394.7	394.5	394.1	393.9	393.5	393.2	393.4
117.5°	445.1	445.1	445.2	445.3	445.3	445.4	445.5	445.5	445.6	445.7	445.3
120°	476.9	477.2	477.5	477.9	478.1	478.1	477.9	477.5	477.2	476.9	477.1
122.5°	508.1	508.5	508.7	509.1	509.3	509.4	509.3	509.1	508.9	508.7	508.5
125°	555.0	554.8	554.6	554.6	554.4	554.0	553.6	553.1	552.7	552.2	552.5
127.5°	596.1	596.3	596.4	596.5	596.6	596.7	596.8	596.9	597.0	597.1	596.4
130°	624.0	624.0	624.0	624.0	624.0	623.9	623.8	623.7	623.5	623.3	622.9
132.5°	649.7	649.8	649.9	650.1	650.1	650.1	650.0	649.9	649.7	649.5	648.9
135°	688.1	687.9	687.5	687.2	686.9	686.6	686.3	686.0	685.6	685.4	684.7
137.5°	721.0	721.1	721.2	721.3	721.4	721.3	720.9	720.6	720.3	720.0	719.3
140°	744.0	743.8	743.6	743.5	743.3	743.0	742.5	742.1	741.6	741.1	740.8
142.5°	762.9	762.9	762.9	762.8	762.8	762.6	762.2	761.9	761.6	761.3	761.1
145°	792.0	791.8	791.4	791.1	790.8	790.6	790.4	790.2	790.1	790.0	790.0
147.5°	816.2	816.0	815.8	815.7	815.6	815.4	815.3	815.2	815.0	814.9	815.0
150°	831.8	831.6	831.4	831.3	831.2	831.1	831.1	831.1	831.1	831.1	831.3
152.5°	845.2	845.3	845.3	845.4	845.5	845.4	845.3	845.0	844.7	844.5	844.7
155°	863.2	863.6	864.1	864.5	865.0	865.0	864.3	863.7	863.1	862.5	862.9
157.5°	878.2	879.0	879.9	880.7	881.5	881.5	880.7	879.9	879.0	878.2	878.8
160°	888.2	889.2	890.1	891.1	892.0	892.0	891.1	890.1	889.2	888.2	888.4
162.5°	896.1	897.2	898.1	899.2	900.3	900.4	899.4	898.5	897.6	896.6	896.8
165°	907.0	908.5	909.9	911.2	912.7	912.8	911.5	910.3	909.0	907.8	907.8
167.5°	915.3	916.9	918.4	920.0	921.5	921.6	920.2	918.9	917.5	916.1	916.2
170°	920.3	921.9	923.5	925.0	926.5	926.7	925.4	924.2	922.9	921.8	921.6
172.5°	923.1	924.8	926.5	928.2	929.8	930.1	928.8	927.6	926.3	925.1	924.9
175°	926.6	928.4	930.3	932.2	934.1	934.2	932.9	931.5	930.1	928.7	928.5
177.5°	928.8	930.3	931.8	933.3	934.8	935.0	934.1	933.1	932.0	931.0	930.9
180°	932.2	932.2	932.2	932.2	932.2	932.2	932.2	932.2	932.2	932.2	932.2



TEST NUMBER: P332553-940

CATALOG NUMBER: SA4XXDIP-C575D810U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5
2.5°	864.4	860.6	857.8	855.6	849.4	845.9	843.1	839.2	834.7	830.0	824.2
5°	913.6	901.7	893.0	879.9	867.4	856.9	846.2	836.5	824.7	811.9	802.5
7.5°	965.1	947.5	925.1	905.5	883.6	864.5	847.5	830.0	811.8	794.2	778.0
10°	997.8	975.3	950.3	920.8	893.0	868.4	845.5	823.3	801.8	780.2	761.9
12.5°	1033.0	1005.0	968.0	933.5	902.5	869.5	841.9	814.7	788.7	766.2	744.7
15°	1080.4	1039.8	997.1	951.0	910.1	871.6	833.7	799.3	770.3	740.4	719.6
17.5°	1109.5	1059.3	1010.5	962.2	912.7	864.1	823.3	783.7	747.2	717.6	691.3
20°	1128.6	1078.7	1018.0	969.7	910.7	860.8	813.6	769.5	731.4	699.8	672.7
22.5°	1145.3	1087.5	1026.8	963.3	904.6	851.6	800.0	755.6	716.7	683.4	657.5
25°	1154.3	1088.1	1022.1	958.9	892.3	829.6	782.7	730.7	689.0	654.0	626.2
27.5°	1155.3	1084.4	1009.9	939.7	870.9	812.4	753.3	706.8	663.6	626.5	599.9
30°	1152.2	1078.3	998.2	922.2	853.2	789.6	738.3	687.7	643.5	606.8	579.1
32.5°	1142.5	1065.5	983.2	902.8	831.3	769.1	716.1	668.0	625.0	588.8	559.6
35°	1114.4	1038.4	950.7	867.0	793.8	731.0	683.1	634.2	591.2	556.9	528.8
37.5°	1070.5	1001.7	912.6	826.0	754.1	691.1	643.5	599.4	560.6	525.7	496.9
40°	1032.2	971.8	882.3	798.0	720.2	660.2	615.8	575.2	536.7	503.7	476.4
42.5°	988.0	935.4	852.8	763.6	688.6	628.3	585.1	548.6	512.3	481.9	454.4
45°	909.4	874.7	796.9	714.3	636.3	579.4	538.1	506.2	475.6	445.9	422.9
47.5°	818.9	801.6	736.2	657.8	583.7	527.6	491.9	462.4	435.6	410.3	390.1
50°	758.0	749.8	693.2	617.6	546.8	494.1	458.0	432.7	409.7	387.5	368.5
52.5°	698.1	697.9	646.8	577.6	512.1	461.3	425.5	401.8	382.0	363.9	346.8
55°	606.5	616.2	576.3	514.5	455.9	410.1	377.8	356.7	342.8	327.9	315.0
57.5°	522.3	538.4	505.5	451.1	402.2	360.0	331.9	316.0	301.2	292.2	282.9
60°	467.3	482.6	456.9	411.2	365.0	328.9	302.2	287.9	275.1	268.9	262.3
62.5°	418.5	432.1	413.0	370.6	330.6	295.9	273.3	259.7	251.0	244.2	239.8
65°	348.7	360.2	343.8	313.0	278.6	250.8	232.5	221.7	213.4	210.6	205.7
67.5°	281.9	292.3	283.5	257.3	229.7	208.7	194.3	184.0	179.1	176.6	173.2
70°	242.2	252.6	243.2	220.3	199.1	181.5	167.9	162.0	156.9	155.8	151.0
72.5°	208.6	215.7	206.3	188.4	170.3	155.3	144.9	138.8	136.0	134.1	131.5
75°	156.5	162.7	156.5	142.6	129.7	119.3	110.3	107.9	104.8	103.7	102.0
77.5°	110.8	116.2	111.4	102.7	93.1	85.1	80.3	77.1	76.4	74.6	75.4
80°	84.6	88.1	83.6	77.8	70.1	64.6	61.1	59.3	57.2	56.5	58.0
82.5°	60.8	62.3	60.0	56.1	50.4	46.7	44.4	42.4	42.0	42.1	42.1
85°	31.6	31.2	30.9	27.4	25.7	23.3	21.8	21.5	21.1	21.8	22.6
87.5°	13.1	13.1	12.7	11.2	10.1	8.8	8.3	7.7	8.3	8.8	9.5
90°	12.8	11.6	10.3	8.9	7.2	5.5	3.8	2.1	3.8	5.5	7.2
92.5°	12.3	11.1	9.8	9.2	9.1	9.0	8.9	8.8	8.9	9.0	9.1
95°	15.1	14.9	14.7	17.3	22.6	27.8	33.1	38.3	33.1	27.8	22.6
97.5°	53.0	70.3	87.6	94.6	91.3	88.0	84.7	81.4	84.7	88.0	91.3
100°	73.5	94.8	116.2	125.5	122.7	119.9	117.2	114.3	117.2	119.9	122.7
102.5°	153.4	156.1	159.0	159.3	157.3	155.2	153.2	151.1	153.2	155.2	157.3
105°	216.0	215.2	214.5	213.6	212.7	211.7	210.8	209.8	210.8	211.7	212.7
107.5°	269.1	268.0	267.0	266.3	265.8	265.3	264.8	264.4	264.8	265.3	265.8
110°	305.6	304.7	303.7	303.1	302.6	302.1	301.7	301.2	301.7	302.1	302.6



TEST NUMBER: P332553-940

CATALOG NUMBER: SA4XXDIP-C575D810U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	341.7	341.3	340.9	340.3	339.4	338.6	337.7	336.9	337.7	338.6	339.4
115°	393.5	393.7	393.9	393.7	393.2	392.8	392.3	391.8	392.3	392.8	393.2
117.5°	445.0	444.6	444.3	443.8	443.2	442.6	441.9	441.3	441.9	442.6	443.2
120°	477.2	477.3	477.5	477.2	476.7	476.1	475.5	474.8	475.5	476.1	476.7
122.5°	508.3	508.0	507.8	507.6	507.1	506.8	506.4	506.0	506.4	506.8	507.1
125°	552.9	553.1	553.4	553.3	552.7	552.1	551.4	550.8	551.4	552.1	552.7
127.5°	595.7	594.9	594.2	593.8	593.7	593.5	593.3	593.2	593.3	593.5	593.7
130°	622.4	621.9	621.4	621.2	621.0	620.8	620.7	620.5	620.7	620.8	621.0
132.5°	648.4	647.7	647.2	646.8	646.5	646.2	645.9	645.6	645.9	646.2	646.5
135°	684.1	683.5	682.9	682.7	682.8	683.0	683.1	683.3	683.1	683.0	682.8
137.5°	718.6	717.9	717.2	716.8	716.8	716.8	716.7	716.6	716.7	716.8	716.8
140°	740.6	740.2	739.9	739.6	739.3	739.0	738.7	738.3	738.7	739.0	739.3
142.5°	760.9	760.6	760.5	760.1	759.6	759.0	758.4	757.9	758.4	759.0	759.6
145°	790.0	790.0	790.0	789.7	789.3	788.8	788.4	787.8	788.4	788.8	789.3
147.5°	815.2	815.4	815.6	815.2	814.3	813.4	812.6	811.7	812.6	813.4	814.3
150°	831.4	831.5	831.7	831.4	830.9	830.3	829.6	829.0	829.6	830.3	830.9
152.5°	845.1	845.3	845.6	845.5	845.0	844.5	844.0	843.5	844.0	844.5	845.0
155°	863.4	863.9	864.3	864.5	864.3	864.2	864.0	863.9	864.0	864.2	864.3
157.5°	879.3	879.8	880.3	880.7	880.7	880.8	880.9	881.0	880.9	880.8	880.7
160°	888.6	888.8	888.9	889.2	889.7	890.1	890.6	891.1	890.6	890.1	889.7
162.5°	897.0	897.1	897.2	897.6	898.2	898.8	899.4	900.0	899.4	898.8	898.2
165°	907.8	907.8	907.8	908.2	908.9	909.7	910.5	911.2	910.5	909.7	908.9
167.5°	916.3	916.4	916.5	916.9	917.7	918.6	919.4	920.2	919.4	918.6	917.7
170°	921.4	921.2	921.1	921.5	922.4	923.4	924.3	925.2	924.3	923.4	922.4
172.5°	924.8	924.6	924.4	924.9	925.8	926.7	927.6	928.5	927.6	926.7	925.8
175°	928.4	928.3	928.1	928.4	929.4	930.3	931.2	932.2	931.2	930.3	929.4
177.5°	930.6	930.3	930.1	930.4	931.2	932.1	933.0	933.9	933.0	932.1	931.2
180°	932.2	932.2	932.2	932.2	932.2	932.2	932.2	932.2	932.2	932.2	932.2



TEST NUMBER: P332553-940

CATALOG NUMBER: SA4XXDIP-C575D810U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5
2.5°	821.4	818.9	815.3	810.3	806.2	801.7	800.6	799.0	802.3	799.5	798.7
5°	794.5	787.2	777.8	767.1	760.9	751.8	750.1	746.6	743.2	742.8	739.3
7.5°	766.0	755.3	743.1	732.1	721.9	712.1	705.6	704.3	699.1	696.2	692.7
10°	747.7	734.5	720.2	709.9	698.0	687.7	680.4	676.2	672.7	668.9	665.5
12.5°	726.0	712.0	700.3	689.0	675.0	667.1	655.1	647.9	647.2	647.3	638.3
15°	700.8	687.0	668.9	653.0	645.3	630.1	623.5	615.1	609.9	604.8	600.6
17.5°	672.1	654.8	640.7	622.3	607.8	595.7	586.9	581.9	574.2	566.8	561.4
20°	654.0	635.6	620.7	601.3	585.3	570.4	563.1	556.2	550.3	544.0	538.1
22.5°	635.7	616.4	598.2	579.3	564.5	548.8	541.7	532.3	526.6	523.2	517.3
25°	606.8	586.0	565.2	547.2	531.9	518.0	508.6	501.3	495.1	492.3	488.5
27.5°	575.4	554.7	534.7	514.2	496.9	486.8	479.3	473.8	470.2	466.5	464.8
30°	555.4	534.0	512.5	493.4	477.4	467.3	460.4	456.6	453.8	452.1	450.3
32.5°	535.2	514.0	491.3	473.9	459.7	450.7	445.4	441.6	440.2	439.6	439.0
35°	502.7	481.3	460.4	444.8	431.2	427.8	423.3	421.2	420.5	422.9	424.0
37.5°	471.3	451.3	432.1	417.1	408.1	403.1	401.5	401.6	404.1	406.3	408.8
40°	451.0	431.6	413.6	400.4	392.1	389.0	388.3	389.9	392.7	395.2	398.0
42.5°	431.3	412.1	395.8	383.4	377.6	374.8	375.2	376.9	380.8	383.8	388.0
45°	400.7	384.8	368.8	358.7	353.9	354.5	354.5	357.7	361.5	366.0	370.5
47.5°	371.9	355.8	342.7	334.2	331.7	331.1	333.1	337.2	342.7	348.2	354.5
50°	352.5	337.2	325.7	318.2	315.4	316.4	319.2	323.0	329.6	336.5	343.1
52.5°	332.8	318.9	308.3	301.2	299.3	301.1	303.9	310.0	315.8	323.2	331.2
55°	302.2	290.4	282.0	276.9	276.2	277.2	280.4	287.0	295.2	304.6	312.3
57.5°	271.7	261.9	254.2	250.7	251.0	252.0	257.1	264.9	273.8	283.8	293.6
60°	251.2	242.2	235.9	233.2	233.5	235.6	241.8	249.1	260.2	269.9	280.4
62.5°	231.8	223.8	217.8	215.3	214.9	219.5	225.4	233.0	244.2	254.9	266.2
65°	200.5	194.3	189.4	188.1	189.0	192.5	200.2	210.3	219.6	231.0	242.9
67.5°	170.0	164.9	161.6	162.2	163.5	168.5	175.0	183.6	194.2	206.1	217.8
70°	150.6	145.7	142.9	143.3	145.3	151.6	157.2	165.9	177.3	189.4	199.1
72.5°	130.6	127.4	124.9	126.4	128.4	132.8	139.6	148.4	158.5	169.7	180.0
75°	100.2	100.2	98.9	100.0	103.1	107.2	112.4	121.5	131.5	140.5	148.8
77.5°	74.4	73.7	74.5	75.8	77.6	82.5	88.5	95.0	102.5	111.6	118.4
80°	56.9	57.2	58.9	61.1	61.8	65.5	71.8	77.8	83.6	91.2	97.8
82.5°	42.7	43.1	44.0	46.6	47.3	51.5	55.5	61.3	66.7	71.8	77.3
85°	23.3	23.3	25.0	26.0	27.7	30.5	33.0	36.5	41.3	44.8	49.9
87.5°	10.7	11.0	12.3	13.1	14.2	15.9	16.6	19.8	21.1	22.6	25.3
90°	8.9	10.3	11.6	12.8	14.1	15.3	16.2	17.2	18.1	19.1	19.7
92.5°	9.2	9.8	11.1	12.3	13.6	14.8	15.7	16.7	17.6	18.5	19.0
95°	17.3	14.7	14.9	15.1	15.2	15.3	16.2	17.2	18.1	19.1	19.6
97.5°	94.6	87.6	70.3	53.0	35.7	18.4	18.5	18.6	18.7	18.8	18.9
100°	125.5	116.2	94.8	73.5	52.1	30.7	28.0	25.4	22.7	20.2	18.9
102.5°	159.3	159.0	156.1	153.4	150.6	147.8	119.4	91.0	62.6	34.2	20.0
105°	213.6	214.5	215.2	216.0	216.8	217.5	218.9	220.3	221.7	223.1	221.1
107.5°	266.3	267.0	268.0	269.1	270.2	271.3	271.9	272.6	273.2	273.9	274.6
110°	303.1	303.7	304.7	305.6	306.6	307.5	307.8	308.1	308.4	308.7	309.1



TEST NUMBER: P332553-940

CATALOG NUMBER: SA4XXDIP-C575D810U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	340.3	340.9	341.3	341.7	342.1	342.6	342.6	342.5	342.4	342.3	342.6
115°	393.7	393.9	393.7	393.5	393.4	393.2	393.5	393.9	394.1	394.5	394.7
117.5°	443.8	444.3	444.6	445.0	445.3	445.7	445.6	445.5	445.5	445.4	445.3
120°	477.2	477.5	477.3	477.2	477.1	476.9	477.2	477.5	477.9	478.1	478.1
122.5°	507.6	507.8	508.0	508.3	508.5	508.7	508.9	509.1	509.3	509.4	509.3
125°	553.3	553.4	553.1	552.9	552.5	552.2	552.7	553.1	553.6	554.0	554.4
127.5°	593.8	594.2	594.9	595.7	596.4	597.1	597.0	596.9	596.8	596.7	596.6
130°	621.2	621.4	621.9	622.4	622.9	623.3	623.5	623.7	623.8	623.9	624.0
132.5°	646.8	647.2	647.7	648.4	648.9	649.5	649.7	649.9	650.0	650.1	650.1
135°	682.7	682.9	683.5	684.1	684.7	685.4	685.6	686.0	686.3	686.6	686.9
137.5°	716.8	717.2	717.9	718.6	719.3	720.0	720.3	720.6	720.9	721.3	721.4
140°	739.6	739.9	740.2	740.6	740.8	741.1	741.6	742.1	742.5	743.0	743.3
142.5°	760.1	760.5	760.6	760.9	761.1	761.3	761.6	761.9	762.2	762.6	762.8
145°	789.7	790.0	790.0	790.0	790.0	790.0	790.1	790.2	790.4	790.6	790.8
147.5°	815.2	815.6	815.4	815.2	815.0	814.9	815.0	815.2	815.3	815.4	815.6
150°	831.4	831.7	831.5	831.4	831.3	831.1	831.1	831.1	831.1	831.1	831.2
152.5°	845.5	845.6	845.3	845.1	844.7	844.5	844.7	845.0	845.3	845.4	845.5
155°	864.5	864.3	863.9	863.4	862.9	862.5	863.1	863.7	864.3	865.0	865.0
157.5°	880.7	880.3	879.8	879.3	878.8	878.2	879.0	879.9	880.7	881.5	881.5
160°	889.2	888.9	888.8	888.6	888.4	888.2	889.2	890.1	891.1	892.0	892.0
162.5°	897.6	897.2	897.1	897.0	896.8	896.6	897.6	898.5	899.4	900.4	900.3
165°	908.2	907.8	907.8	907.8	907.8	907.8	909.0	910.3	911.5	912.8	912.7
167.5°	916.9	916.5	916.4	916.3	916.2	916.1	917.5	918.9	920.2	921.6	921.5
170°	921.5	921.1	921.2	921.4	921.6	921.8	922.9	924.2	925.4	926.7	926.5
172.5°	924.9	924.4	924.6	924.8	924.9	925.1	926.3	927.6	928.8	930.1	929.8
175°	928.4	928.1	928.3	928.4	928.5	928.7	930.1	931.5	932.9	934.2	934.1
177.5°	930.4	930.1	930.3	930.6	930.9	931.0	932.0	933.1	934.1	935.0	934.8
180°	932.2	932.2	932.2	932.2	932.2	932.2	932.2	932.2	932.2	932.2	932.2



TEST NUMBER: P332553-940

CATALOG NUMBER: SA4XXDIP-C575D810U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5
2.5°	798.1	797.5	795.6	795.3	795.6	797.5	798.1	798.7	799.5	802.3	799.0
5°	737.3	735.6	734.5	738.3	734.5	735.6	737.3	739.3	742.8	743.2	746.6
7.5°	691.4	690.0	687.0	686.0	687.0	690.0	691.4	692.7	696.2	699.1	704.3
10°	662.0	660.6	657.8	657.1	657.8	660.6	662.0	665.5	668.9	672.7	676.2
12.5°	633.6	630.9	630.4	631.1	630.4	630.9	633.6	638.3	647.3	647.2	647.9
15°	596.0	594.7	590.8	591.9	590.8	594.7	596.0	600.6	604.8	609.9	615.1
17.5°	559.0	557.3	552.7	556.8	552.7	557.3	559.0	561.4	566.8	574.2	581.9
20°	535.7	532.9	530.5	530.1	530.5	532.9	535.7	538.1	544.0	550.3	556.2
22.5°	513.4	511.0	510.8	508.5	510.8	511.0	513.4	517.3	523.2	526.6	532.3
25°	485.7	483.3	482.6	480.9	482.6	483.3	485.7	488.5	492.3	495.1	501.3
27.5°	464.4	463.2	462.0	462.5	462.0	463.2	464.4	464.8	466.5	470.2	473.8
30°	451.4	451.0	450.3	450.3	450.3	451.0	451.4	450.3	452.1	453.8	456.6
32.5°	440.6	440.5	440.9	440.9	440.9	440.5	440.6	439.0	439.6	440.2	441.6
35°	425.3	426.4	427.1	426.1	427.1	426.4	425.3	424.0	422.9	420.5	421.2
37.5°	411.6	412.7	413.7	414.8	413.7	412.7	411.6	408.8	406.3	404.1	401.6
40°	401.1	403.5	404.2	405.9	404.2	403.5	401.1	398.0	395.2	392.7	389.9
42.5°	391.1	393.8	395.6	395.9	395.6	393.8	391.1	388.0	383.8	380.8	376.9
45°	375.8	378.5	380.9	380.9	380.9	378.5	375.8	370.5	366.0	361.5	357.7
47.5°	359.9	363.9	366.3	366.9	366.3	363.9	359.9	354.5	348.2	342.7	337.2
50°	349.0	353.9	356.3	358.0	356.3	353.9	349.0	343.1	336.5	329.6	323.0
52.5°	338.5	343.3	346.6	347.5	346.6	343.3	338.5	331.2	323.2	315.8	310.0
55°	320.2	327.2	331.0	332.3	331.0	327.2	320.2	312.3	304.6	295.2	287.0
57.5°	303.0	309.4	313.9	314.9	313.9	309.4	303.0	293.6	283.8	273.8	264.9
60°	289.7	296.7	302.2	303.3	302.2	296.7	289.7	280.4	269.9	260.2	249.1
62.5°	276.1	283.3	288.3	291.1	288.3	283.3	276.1	266.2	254.9	244.2	233.0
65°	252.6	259.8	264.7	265.7	264.7	259.8	252.6	242.9	231.0	219.6	210.3
67.5°	226.9	234.2	237.4	239.4	237.4	234.2	226.9	217.8	206.1	194.2	183.6
70°	208.8	214.7	218.2	220.0	218.2	214.7	208.8	199.1	189.4	177.3	165.9
72.5°	188.3	194.5	198.5	198.9	198.5	194.5	188.3	180.0	169.7	158.5	148.4
75°	156.9	162.4	164.4	164.4	164.4	162.4	156.9	148.8	140.5	131.5	121.5
77.5°	124.1	127.0	129.7	130.2	129.7	127.0	124.1	118.4	111.6	102.5	95.0
80°	103.1	104.8	106.8	106.8	106.8	104.8	103.1	97.8	91.2	83.6	77.8
82.5°	81.4	82.8	84.9	84.6	84.9	82.8	81.4	77.3	71.8	66.7	61.3
85°	49.2	52.4	52.1	51.4	52.1	52.4	49.2	49.9	44.8	41.3	36.5
87.5°	26.2	26.6	27.5	28.1	27.5	26.6	26.2	25.3	22.6	21.1	19.8
90°	20.0	20.3	20.6	21.0	20.6	20.3	20.0	19.7	19.1	18.1	17.2
92.5°	19.1	19.1	19.2	19.3	19.2	19.1	19.1	19.0	18.5	17.6	16.7
95°	19.8	19.9	20.1	20.2	20.1	19.9	19.8	19.6	19.1	18.1	17.2
97.5°	19.1	19.2	19.4	19.5	19.4	19.2	19.1	18.9	18.8	18.7	18.6
100°	19.1	19.2	19.4	19.5	19.4	19.2	19.1	18.9	20.2	22.7	25.4
102.5°	20.0	20.0	20.1	20.1	20.1	20.0	20.0	20.0	34.2	62.6	91.0
105°	215.4	209.8	204.3	198.7	204.3	209.8	215.4	221.1	223.1	221.7	220.3
107.5°	275.2	275.7	276.3	277.0	276.3	275.7	275.2	274.6	273.9	273.2	272.6
110°	309.6	310.0	310.5	310.9	310.5	310.0	309.6	309.1	308.7	308.4	308.1



TEST NUMBER: P332553-940

CATALOG NUMBER: SA4XXDIP-C575D810U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	343.2	343.8	344.4	345.0	344.4	343.8	343.2	342.6	342.3	342.4	342.5
115°	394.7	394.7	394.7	394.7	394.7	394.7	394.7	394.7	394.5	394.1	393.9
117.5°	445.3	445.2	445.1	445.1	445.1	445.2	445.3	445.3	445.4	445.5	445.5
120°	477.9	477.5	477.2	476.9	477.2	477.5	477.9	478.1	478.1	477.9	477.5
122.5°	509.1	508.7	508.5	508.1	508.5	508.7	509.1	509.3	509.4	509.3	509.1
125°	554.6	554.6	554.8	555.0	554.8	554.6	554.6	554.4	554.0	553.6	553.1
127.5°	596.5	596.4	596.3	596.1	596.3	596.4	596.5	596.6	596.7	596.8	596.9
130°	624.0	624.0	624.0	624.0	624.0	624.0	624.0	624.0	623.9	623.8	623.7
132.5°	650.1	649.9	649.8	649.7	649.8	649.9	650.1	650.1	650.1	650.0	649.9
135°	687.2	687.5	687.9	688.1	687.9	687.5	687.2	686.9	686.6	686.3	686.0
137.5°	721.3	721.2	721.1	721.0	721.1	721.2	721.3	721.4	721.3	720.9	720.6
140°	743.5	743.6	743.8	744.0	743.8	743.6	743.5	743.3	743.0	742.5	742.1
142.5°	762.8	762.9	762.9	762.9	762.9	762.9	762.8	762.8	762.6	762.2	761.9
145°	791.1	791.4	791.8	792.0	791.8	791.4	791.1	790.8	790.6	790.4	790.2
147.5°	815.7	815.8	816.0	816.2	816.0	815.8	815.7	815.6	815.4	815.3	815.2
150°	831.3	831.4	831.6	831.8	831.6	831.4	831.3	831.2	831.1	831.1	831.1
152.5°	845.4	845.3	845.3	845.2	845.3	845.3	845.4	845.5	845.4	845.3	845.0
155°	864.5	864.1	863.6	863.2	863.6	864.1	864.5	865.0	865.0	864.3	863.7
157.5°	880.7	879.9	879.0	878.2	879.0	879.9	880.7	881.5	881.5	880.7	879.9
160°	891.1	890.1	889.2	888.2	889.2	890.1	891.1	892.0	892.0	891.1	890.1
162.5°	899.2	898.1	897.2	896.1	897.2	898.1	899.2	900.3	900.4	899.4	898.5
165°	911.2	909.9	908.5	907.0	908.5	909.9	911.2	912.7	912.8	911.5	910.3
167.5°	920.0	918.4	916.9	915.3	916.9	918.4	920.0	921.5	921.6	920.2	918.9
170°	925.0	923.5	921.9	920.3	921.9	923.5	925.0	926.5	926.7	925.4	924.2
172.5°	928.2	926.5	924.8	923.1	924.8	926.5	928.2	929.8	930.1	928.8	927.6
175°	932.2	930.3	928.4	926.6	928.4	930.3	932.2	934.1	934.2	932.9	931.5
177.5°	933.3	931.8	930.3	928.8	930.3	931.8	933.3	934.8	935.0	934.1	933.1
180°	932.2	932.2	932.2	932.2	932.2	932.2	932.2	932.2	932.2	932.2	932.2



TEST NUMBER: P332553-940

CATALOG NUMBER: SA4XXDIP-C575D810U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5
2.5°	800.6	801.7	806.2	810.3	815.3	818.9	821.4	824.2	830.0	834.7	839.2
5°	750.1	751.8	760.9	767.1	777.8	787.2	794.5	802.5	811.9	824.7	836.5
7.5°	705.6	712.1	721.9	732.1	743.1	755.3	766.0	778.0	794.2	811.8	830.0
10°	680.4	687.7	698.0	709.9	720.2	734.5	747.7	761.9	780.2	801.8	823.3
12.5°	655.1	667.1	675.0	689.0	700.3	712.0	726.0	744.7	766.2	788.7	814.7
15°	623.5	630.1	645.3	653.0	668.9	687.0	700.8	719.6	740.4	770.3	799.3
17.5°	586.9	595.7	607.8	622.3	640.7	654.8	672.1	691.3	717.6	747.2	783.7
20°	563.1	570.4	585.3	601.3	620.7	635.6	654.0	672.7	699.8	731.4	769.5
22.5°	541.7	548.8	564.5	579.3	598.2	616.4	635.7	657.5	683.4	716.7	755.6
25°	508.6	518.0	531.9	547.2	565.2	586.0	606.8	626.2	654.0	689.0	730.7
27.5°	479.3	486.8	496.9	514.2	534.7	554.7	575.4	599.9	626.5	663.6	706.8
30°	460.4	467.3	477.4	493.4	512.5	534.0	555.4	579.1	606.8	643.5	687.7
32.5°	445.4	450.7	459.7	473.9	491.3	514.0	535.2	559.6	588.8	625.0	668.0
35°	423.3	427.8	431.2	444.8	460.4	481.3	502.7	528.8	556.9	591.2	634.2
37.5°	401.5	403.1	408.1	417.1	432.1	451.3	471.3	496.9	525.7	560.6	599.4
40°	388.3	389.0	392.1	400.4	413.6	431.6	451.0	476.4	503.7	536.7	575.2
42.5°	375.2	374.8	377.6	383.4	395.8	412.1	431.3	454.4	481.9	512.3	548.6
45°	354.5	354.5	353.9	358.7	368.8	384.8	400.7	422.9	445.9	475.6	506.2
47.5°	333.1	331.1	331.7	334.2	342.7	355.8	371.9	390.1	410.3	435.6	462.4
50°	319.2	316.4	315.4	318.2	325.7	337.2	352.5	368.5	387.5	409.7	432.7
52.5°	303.9	301.1	299.3	301.2	308.3	318.9	332.8	346.8	363.9	382.0	401.8
55°	280.4	277.2	276.2	276.9	282.0	290.4	302.2	315.0	327.9	342.8	356.7
57.5°	257.1	252.0	251.0	250.7	254.2	261.9	271.7	282.9	292.2	301.2	316.0
60°	241.8	235.6	233.5	233.2	235.9	242.2	251.2	262.3	268.9	275.1	287.9
62.5°	225.4	219.5	214.9	215.3	217.8	223.8	231.8	239.8	244.2	251.0	259.7
65°	200.2	192.5	189.0	188.1	189.4	194.3	200.5	205.7	210.6	213.4	221.7
67.5°	175.0	168.5	163.5	162.2	161.6	164.9	170.0	173.2	176.6	179.1	184.0
70°	157.2	151.6	145.3	143.3	142.9	145.7	150.6	151.0	155.8	156.9	162.0
72.5°	139.6	132.8	128.4	126.4	124.9	127.4	130.6	131.5	134.1	136.0	138.8
75°	112.4	107.2	103.1	100.0	98.9	100.2	100.2	102.0	103.7	104.8	107.9
77.5°	88.5	82.5	77.6	75.8	74.5	73.7	74.4	75.4	74.6	76.4	77.1
80°	71.8	65.5	61.8	61.1	58.9	57.2	56.9	58.0	56.5	57.2	59.3
82.5°	55.5	51.5	47.3	46.6	44.0	43.1	42.7	42.1	42.1	42.0	42.4
85°	33.0	30.5	27.7	26.0	25.0	23.3	23.3	22.6	21.8	21.1	21.5
87.5°	16.6	15.9	14.2	13.1	12.3	11.0	10.7	9.5	8.8	8.3	7.7
90°	16.2	15.3	14.1	12.8	11.6	10.3	8.9	7.2	5.5	3.8	2.1
92.5°	15.7	14.8	13.6	12.3	11.1	9.8	9.2	9.1	9.0	8.9	8.8
95°	16.2	15.3	15.2	15.1	14.9	14.7	17.3	22.6	27.8	33.1	38.3
97.5°	18.5	18.4	35.7	53.0	70.3	87.6	94.6	91.3	88.0	84.7	81.4
100°	28.0	30.7	52.1	73.5	94.8	116.2	125.5	122.7	119.9	117.2	114.3
102.5°	119.4	147.8	150.6	153.4	156.1	159.0	159.3	157.3	155.2	153.2	151.1
105°	218.9	217.5	216.8	216.0	215.2	214.5	213.6	212.7	211.7	210.8	209.8
107.5°	271.9	271.3	270.2	269.1	268.0	267.0	266.3	265.8	265.3	264.8	264.4
110°	307.8	307.5	306.6	305.6	304.7	303.7	303.1	302.6	302.1	301.7	301.2



TEST NUMBER: P332553-940

CATALOG NUMBER: SA4XXDIP-C575D810U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	342.6	342.6	342.1	341.7	341.3	340.9	340.3	339.4	338.6	337.7	336.9
115°	393.5	393.2	393.4	393.5	393.7	393.9	393.7	393.2	392.8	392.3	391.8
117.5°	445.6	445.7	445.3	445.0	444.6	444.3	443.8	443.2	442.6	441.9	441.3
120°	477.2	476.9	477.1	477.2	477.3	477.5	477.2	476.7	476.1	475.5	474.8
122.5°	508.9	508.7	508.5	508.3	508.0	507.8	507.6	507.1	506.8	506.4	506.0
125°	552.7	552.2	552.5	552.9	553.1	553.4	553.3	552.7	552.1	551.4	550.8
127.5°	597.0	597.1	596.4	595.7	594.9	594.2	593.8	593.7	593.5	593.3	593.2
130°	623.5	623.3	622.9	622.4	621.9	621.4	621.2	621.0	620.8	620.7	620.5
132.5°	649.7	649.5	648.9	648.4	647.7	647.2	646.8	646.5	646.2	645.9	645.6
135°	685.6	685.4	684.7	684.1	683.5	682.9	682.7	682.8	683.0	683.1	683.3
137.5°	720.3	720.0	719.3	718.6	717.9	717.2	716.8	716.8	716.8	716.7	716.6
140°	741.6	741.1	740.8	740.6	740.2	739.9	739.6	739.3	739.0	738.7	738.3
142.5°	761.6	761.3	761.1	760.9	760.6	760.5	760.1	759.6	759.0	758.4	757.9
145°	790.1	790.0	790.0	790.0	790.0	790.0	789.7	789.3	788.8	788.4	787.8
147.5°	815.0	814.9	815.0	815.2	815.4	815.6	815.2	814.3	813.4	812.6	811.7
150°	831.1	831.1	831.3	831.4	831.5	831.7	831.4	830.9	830.3	829.6	829.0
152.5°	844.7	844.5	844.7	845.1	845.3	845.6	845.5	845.0	844.5	844.0	843.5
155°	863.1	862.5	862.9	863.4	863.9	864.3	864.5	864.3	864.2	864.0	863.9
157.5°	879.0	878.2	878.8	879.3	879.8	880.3	880.7	880.7	880.8	880.9	881.0
160°	889.2	888.2	888.4	888.6	888.8	888.9	889.2	889.7	890.1	890.6	891.1
162.5°	897.6	896.6	896.8	897.0	897.1	897.2	897.6	898.2	898.8	899.4	900.0
165°	909.0	907.8	907.8	907.8	907.8	907.8	908.2	908.9	909.7	910.5	911.2
167.5°	917.5	916.1	916.2	916.3	916.4	916.5	916.9	917.7	918.6	919.4	920.2
170°	922.9	921.8	921.6	921.4	921.2	921.1	921.5	922.4	923.4	924.3	925.2
172.5°	926.3	925.1	924.9	924.8	924.6	924.4	924.9	925.8	926.7	927.6	928.5
175°	930.1	928.7	928.5	928.4	928.3	928.1	928.4	929.4	930.3	931.2	932.2
177.5°	932.0	931.0	930.9	930.6	930.3	930.1	930.4	931.2	932.1	933.0	933.9
180°	932.2	932.2	932.2	932.2	932.2	932.2	932.2	932.2	932.2	932.2	932.2



TEST NUMBER: P332553-940

CATALOG NUMBER: SA4XXDIP-C575D810U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5
2.5°	843.1	845.9	849.4	855.6	857.8	860.6	864.4	864.2	865.3	869.4	878.3
5°	846.2	856.9	867.4	879.9	893.0	901.7	913.6	920.8	928.1	937.5	953.4
7.5°	847.5	864.5	883.6	905.5	925.1	947.5	965.1	981.6	996.5	1016.3	1035.3
10°	845.5	868.4	893.0	920.8	950.3	975.3	997.8	1023.5	1045.4	1069.3	1090.8
12.5°	841.9	869.5	902.5	933.5	968.0	1005.0	1033.0	1059.0	1088.1	1115.6	1148.8
15°	833.7	871.6	910.1	951.0	997.1	1039.8	1080.4	1114.0	1145.3	1186.6	1229.9
17.5°	823.3	864.1	912.7	962.2	1010.5	1059.3	1109.5	1160.0	1199.4	1250.7	1284.7
20°	813.6	860.8	910.7	969.7	1018.0	1078.7	1128.6	1177.5	1231.6	1282.6	1323.3
22.5°	800.0	851.6	904.6	963.3	1026.8	1087.5	1145.3	1198.4	1252.5	1308.0	1357.1
25°	782.7	829.6	892.3	958.9	1022.1	1088.1	1154.3	1220.9	1279.2	1337.8	1383.7
27.5°	753.3	812.4	870.9	939.7	1009.9	1084.4	1155.3	1225.0	1286.0	1334.3	1362.7
30°	738.3	789.6	853.2	922.2	998.2	1078.3	1152.2	1220.6	1277.5	1316.0	1327.4
32.5°	716.1	769.1	831.3	902.8	983.2	1065.5	1142.5	1206.9	1254.5	1274.6	1260.8
35°	683.1	731.0	793.8	867.0	950.7	1038.4	1114.4	1168.9	1193.2	1174.1	1126.5
37.5°	643.5	691.1	754.1	826.0	912.6	1001.7	1070.5	1109.6	1101.6	1054.2	983.3
40°	615.8	660.2	720.2	798.0	882.3	971.8	1032.2	1053.4	1031.2	963.1	887.9
42.5°	585.1	628.3	688.6	763.6	852.8	935.4	988.0	989.8	952.6	871.3	795.7
45°	538.1	579.4	636.3	714.3	796.9	874.7	909.4	892.3	823.7	745.2	669.2
47.5°	491.9	527.6	583.7	657.8	736.2	801.6	818.9	788.3	715.1	638.9	568.5
50°	458.0	494.1	546.8	617.6	693.2	749.8	758.0	717.5	645.7	569.0	513.8
52.5°	425.5	461.3	512.1	577.6	646.8	697.9	698.1	651.1	579.6	511.3	459.9
55°	377.8	410.1	455.9	514.5	576.3	616.2	606.5	557.9	495.8	436.5	391.7
57.5°	331.9	360.0	402.2	451.1	505.5	538.4	522.3	475.5	420.1	369.8	335.8
60°	302.2	328.9	365.0	411.2	456.9	482.6	467.3	425.0	374.0	333.4	303.9
62.5°	273.3	295.9	330.6	370.6	413.0	432.1	418.5	376.7	332.7	296.0	272.0
65°	232.5	250.8	278.6	313.0	343.8	360.2	348.7	309.8	276.2	249.8	230.7
67.5°	194.3	208.7	229.7	257.3	283.5	292.3	281.9	254.8	226.3	205.2	191.7
70°	167.9	181.5	199.1	220.3	243.2	252.6	242.2	220.7	197.4	178.0	164.8
72.5°	144.9	155.3	170.3	188.4	206.3	215.7	208.6	187.9	168.3	153.8	142.6
75°	110.3	119.3	129.7	142.6	156.5	162.7	156.5	142.2	128.7	118.0	109.9
77.5°	80.3	85.1	93.1	102.7	111.4	116.2	110.8	101.1	92.8	85.5	81.5
80°	61.1	64.6	70.1	77.8	83.6	88.1	84.6	76.7	70.1	65.2	63.5
82.5°	44.4	46.7	50.4	56.1	60.0	62.3	60.8	55.0	52.3	48.0	46.3
85°	21.8	23.3	25.7	27.4	30.9	31.2	31.6	29.2	26.8	25.7	24.3
87.5°	8.3	8.8	10.1	11.2	12.7	13.1	13.1	13.4	12.5	12.4	11.5
90°	3.8	5.5	7.2	8.9	10.3	11.6	12.8	14.1	15.3	16.2	17.2
92.5°	8.9	9.0	9.1	9.2	9.8	11.1	12.3	13.6	14.8	15.7	16.7
95°	33.1	27.8	22.6	17.3	14.7	14.9	15.1	15.2	15.3	16.2	17.2
97.5°	84.7	88.0	91.3	94.6	87.6	70.3	53.0	35.7	18.4	18.5	18.6
100°	117.2	119.9	122.7	125.5	116.2	94.8	73.5	52.1	30.7	28.0	25.4
102.5°	153.2	155.2	157.3	159.3	159.0	156.1	153.4	150.6	147.8	119.4	91.0
105°	210.8	211.7	212.7	213.6	214.5	215.2	216.0	216.8	217.5	218.9	220.3
107.5°	264.8	265.3	265.8	266.3	267.0	268.0	269.1	270.2	271.3	271.9	272.6
110°	301.7	302.1	302.6	303.1	303.7	304.7	305.6	306.6	307.5	307.8	308.1



TEST NUMBER: P332553-940

CATALOG NUMBER: SA4XXDIP-C575D810U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	337.7	338.6	339.4	340.3	340.9	341.3	341.7	342.1	342.6	342.6	342.5
115°	392.3	392.8	393.2	393.7	393.9	393.7	393.5	393.4	393.2	393.5	393.9
117.5°	441.9	442.6	443.2	443.8	444.3	444.6	445.0	445.3	445.7	445.6	445.5
120°	475.5	476.1	476.7	477.2	477.5	477.3	477.2	477.1	476.9	477.2	477.5
122.5°	506.4	506.8	507.1	507.6	507.8	508.0	508.3	508.5	508.7	508.9	509.1
125°	551.4	552.1	552.7	553.3	553.4	553.1	552.9	552.5	552.2	552.7	553.1
127.5°	593.3	593.5	593.7	593.8	594.2	594.9	595.7	596.4	597.1	597.0	596.9
130°	620.7	620.8	621.0	621.2	621.4	621.9	622.4	622.9	623.3	623.5	623.7
132.5°	645.9	646.2	646.5	646.8	647.2	647.7	648.4	648.9	649.5	649.7	649.9
135°	683.1	683.0	682.8	682.7	682.9	683.5	684.1	684.7	685.4	685.6	686.0
137.5°	716.7	716.8	716.8	716.8	717.2	717.9	718.6	719.3	720.0	720.3	720.6
140°	738.7	739.0	739.3	739.6	739.9	740.2	740.6	740.8	741.1	741.6	742.1
142.5°	758.4	759.0	759.6	760.1	760.5	760.6	760.9	761.1	761.3	761.6	761.9
145°	788.4	788.8	789.3	789.7	790.0	790.0	790.0	790.0	790.0	790.1	790.2
147.5°	812.6	813.4	814.3	815.2	815.6	815.4	815.2	815.0	814.9	815.0	815.2
150°	829.6	830.3	830.9	831.4	831.7	831.5	831.4	831.3	831.1	831.1	831.1
152.5°	844.0	844.5	845.0	845.5	845.6	845.3	845.1	844.7	844.5	844.7	845.0
155°	864.0	864.2	864.3	864.5	864.3	863.9	863.4	862.9	862.5	863.1	863.7
157.5°	880.9	880.8	880.7	880.7	880.3	879.8	879.3	878.8	878.2	879.0	879.9
160°	890.6	890.1	889.7	889.2	888.9	888.8	888.6	888.4	888.2	889.2	890.1
162.5°	899.4	898.8	898.2	897.6	897.2	897.1	897.0	896.8	896.6	897.6	898.5
165°	910.5	909.7	908.9	908.2	907.8	907.8	907.8	907.8	907.8	909.0	910.3
167.5°	919.4	918.6	917.7	916.9	916.5	916.4	916.3	916.2	916.1	917.5	918.9
170°	924.3	923.4	922.4	921.5	921.1	921.2	921.4	921.6	921.8	922.9	924.2
172.5°	927.6	926.7	925.8	924.9	924.4	924.6	924.8	924.9	925.1	926.3	927.6
175°	931.2	930.3	929.4	928.4	928.1	928.3	928.4	928.5	928.7	930.1	931.5
177.5°	933.0	932.1	931.2	930.4	930.1	930.3	930.6	930.9	931.0	932.0	933.1
180°	932.2	932.2	932.2	932.2	932.2	932.2	932.2	932.2	932.2	932.2	932.2



TEST NUMBER: P332553-940

CATALOG NUMBER: SA4XXDIP-C575D810U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	837.5	837.5	837.5	837.5	837.5	837.5	837.5
2.5°	882.8	883.3	885.8	887.8	888.3	891.1	891.4
5°	960.4	966.3	977.7	978.7	980.4	989.5	982.6
7.5°	1051.2	1066.2	1076.2	1085.0	1088.2	1092.2	1091.4
10°	1109.6	1131.8	1142.8	1160.6	1161.3	1165.7	1163.0
12.5°	1168.1	1193.9	1214.2	1217.5	1232.3	1234.6	1238.5
15°	1251.1	1278.5	1306.6	1316.7	1337.1	1342.0	1349.6
17.5°	1329.1	1357.1	1376.8	1402.8	1411.2	1422.5	1414.9
20°	1371.8	1402.4	1427.4	1447.8	1456.5	1462.8	1462.0
22.5°	1397.7	1428.4	1448.7	1464.2	1472.3	1475.0	1474.8
25°	1413.8	1431.6	1437.8	1443.7	1434.7	1431.6	1432.9
27.5°	1368.9	1364.2	1348.0	1326.6	1304.4	1286.7	1277.2
30°	1307.0	1279.9	1255.3	1212.3	1190.0	1176.9	1165.0
32.5°	1219.2	1176.3	1129.0	1089.6	1064.3	1044.7	1041.8
35°	1069.0	1004.4	946.5	898.2	873.3	852.1	847.2
37.5°	908.8	841.8	789.6	747.1	720.2	705.3	691.4
40°	802.5	744.9	693.6	657.5	637.0	626.2	617.6
42.5°	720.6	668.0	617.0	589.4	571.0	564.4	559.3
45°	607.5	558.6	523.2	502.4	491.6	480.5	475.3
47.5°	516.9	477.2	453.8	436.1	424.6	418.0	414.6
50°	465.6	433.0	412.1	398.7	388.3	383.0	380.2
52.5°	420.1	393.3	375.9	365.1	358.0	354.2	353.0
55°	361.9	341.4	330.3	320.9	315.8	312.3	310.9
57.5°	314.5	298.8	289.8	282.0	280.1	277.1	276.2
60°	283.5	271.3	263.7	258.5	256.7	253.2	254.0
62.5°	256.0	246.0	239.5	236.6	234.3	231.3	232.3
65°	216.5	209.2	205.7	203.0	200.2	198.5	199.8
67.5°	181.6	176.6	171.9	170.3	169.0	168.7	167.2
70°	158.9	154.7	150.6	149.5	149.5	148.1	147.8
72.5°	137.0	133.9	131.2	130.4	129.3	129.8	128.4
75°	105.8	103.3	102.4	101.3	100.9	100.9	100.0
77.5°	78.2	76.4	74.7	74.7	73.5	73.0	72.9
80°	59.3	58.7	57.2	57.2	56.5	56.9	56.2
82.5°	44.6	43.6	43.3	42.8	41.8	41.9	41.2
85°	23.9	22.9	22.6	21.5	20.8	21.5	20.8
87.5°	11.9	11.9	11.7	11.2	11.0	11.1	10.3
90°	18.1	19.1	19.7	20.0	20.3	20.6	21.0
92.5°	17.6	18.5	19.0	19.1	19.1	19.2	19.3
95°	18.1	19.1	19.6	19.8	19.9	20.1	20.2
97.5°	18.7	18.8	18.9	19.1	19.2	19.4	19.5
100°	22.7	20.2	18.9	19.1	19.2	19.4	19.5
102.5°	62.6	34.2	20.0	20.0	20.0	20.1	20.1
105°	221.7	223.1	221.1	215.4	209.8	204.3	198.7
107.5°	273.2	273.9	274.6	275.2	275.7	276.3	277.0
110°	308.4	308.7	309.1	309.6	310.0	310.5	310.9



TEST NUMBER: P332553-940

CATALOG NUMBER: SA4XXDIP-C575D810U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	342.4	342.3	342.6	343.2	343.8	344.4	345.0
115°	394.1	394.5	394.7	394.7	394.7	394.7	394.7
117.5°	445.5	445.4	445.3	445.3	445.2	445.1	445.1
120°	477.9	478.1	478.1	477.9	477.5	477.2	476.9
122.5°	509.3	509.4	509.3	509.1	508.7	508.5	508.1
125°	553.6	554.0	554.4	554.6	554.6	554.8	555.0
127.5°	596.8	596.7	596.6	596.5	596.4	596.3	596.1
130°	623.8	623.9	624.0	624.0	624.0	624.0	624.0
132.5°	650.0	650.1	650.1	650.1	649.9	649.8	649.7
135°	686.3	686.6	686.9	687.2	687.5	687.9	688.1
137.5°	720.9	721.3	721.4	721.3	721.2	721.1	721.0
140°	742.5	743.0	743.3	743.5	743.6	743.8	744.0
142.5°	762.2	762.6	762.8	762.8	762.9	762.9	762.9
145°	790.4	790.6	790.8	791.1	791.4	791.8	792.0
147.5°	815.3	815.4	815.6	815.7	815.8	816.0	816.2
150°	831.1	831.1	831.2	831.3	831.4	831.6	831.8
152.5°	845.3	845.4	845.5	845.4	845.3	845.3	845.2
155°	864.3	865.0	865.0	864.5	864.1	863.6	863.2
157.5°	880.7	881.5	881.5	880.7	879.9	879.0	878.2
160°	891.1	892.0	892.0	891.1	890.1	889.2	888.2
162.5°	899.4	900.4	900.3	899.2	898.1	897.2	896.1
165°	911.5	912.8	912.7	911.2	909.9	908.5	907.0
167.5°	920.2	921.6	921.5	920.0	918.4	916.9	915.3
170°	925.4	926.7	926.5	925.0	923.5	921.9	920.3
172.5°	928.8	930.1	929.8	928.2	926.5	924.8	923.1
175°	932.9	934.2	934.1	932.2	930.3	928.4	926.6
177.5°	934.1	935.0	934.8	933.3	931.8	930.3	928.8
180°	932.2	932.2	932.2	932.2	932.2	932.2	932.2

(END OF REPORT)