

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332958-940

Luminaire Tested: **SA4XXRDIP-C1020D365U940-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332958-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C1020D365U940-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 365 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5024.7 lumens
Efficiency: N/A
Efficacy: 115.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 43.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332958-940
CATALOG NUMBER: SA4XXRDIP-C1020D365U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332958-940

CATALOG NUMBER: SA4XXRDIP-C1020D365U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	113	113	113	113	107	107	107	107	97	97	97	87	87	87	78	78	78	74				74
1	104	99	95	92	98	95	91	88	86	83	81	77	75	74	70	68	67				63	
2	95	87	81	76	90	83	78	73	75	71	67	68	65	62	62	59	57				54	
3	87	77	70	64	82	74	67	61	67	62	57	61	57	53	55	52	49				46	
4	80	69	60	54	75	65	58	53	60	54	49	55	50	46	50	46	42				40	
5	73	61	53	47	69	59	51	46	54	48	43	49	44	40	45	41	37				35	
6	68	55	47	41	64	53	45	40	49	42	38	45	39	35	41	36	33				31	
7	63	50	42	36	60	48	41	35	44	38	33	41	35	31	37	33	29				27	
8	58	46	38	32	55	44	37	32	41	34	30	37	32	28	34	30	27				24	
9	55	42	34	29	52	40	33	28	37	31	27	35	29	26	32	27	24				22	
10	51	39	31	26	49	37	30	26	35	29	24	32	27	23	30	25	22				20	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12999	12999	12999
5°	13028	12869	12949
10°	12946	12714	12714
15°	12797	12447	12354
20°	12594	12095	11874
25°	12333	11685	11388
30°	12078	11251	10781
35°	11798	10801	10170
40°	11460	10290	9511
45°	11147	9782	8840
50°	10792	9198	8130
55°	10412	8590	7357
60°	9993	7923	6570
65°	9608	7089	5794
70°	9050	6170	4919
75°	8344	5115	3999
80°	7280	3896	3668
85°	6169	3548	3316



TEST NUMBER: P332958-940

CATALOG NUMBER: SA4XXRDIP-C1020D365U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	151.3	3.0
10°-20°	421.8	8.4
20°-30°	609.1	12.1
30°-40°	690.4	13.7
40°-50°	666.7	13.3
50°-60°	554.4	11.0
60°-70°	382.8	7.6
70°-80°	194.0	3.9
80°-90°	51.0	1.0
90°-100°	14.4	0.3
100°-110°	91.9	1.8
110°-120°	175.8	3.5
120°-130°	223.1	4.4
130°-140°	238.7	4.8
140°-150°	223.2	4.4
150°-160°	180.0	3.6
160°-170°	116.1	2.3
170°-180°	40.0	0.8
0°-30°	1182.1	23.5
0°-40°	1872.5	37.3
0°-60°	3093.5	61.6
0°-90°	3721.3	74.1
90°-120°	282.1	5.6
90°-150°	967.2	19.2
90°-180°	1303.0	25.9
0°-180°	5024.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1610	1610	1610	1610	1610	
5°	1608	1602	1588	1599	1598	152
15°	1531	1519	1489	1486	1478	431
25°	1385	1361	1312	1291	1278	638
35°	1197	1156	1096	1055	1032	748
45°	976	929	857	799	774	753
55°	740	689	610	548	523	661
65°	503	449	371	320	303	497
75°	268	221	164	137	128	282
85°	67	43	38	36	36	75
90°	1	4	7	9	10	4
95°	17	7	7	9	9	22
105°	95	97	98	100	90	99
115°	177	178	178	178	178	174
125°	249	250	250	250	251	222
135°	309	309	310	310	311	238
145°	356	357	357	357	358	222
155°	390	391	390	391	390	180
165°	412	410	410	413	410	116
175°	421	420	420	422	419	40
180°	421	421	421	421	421	



TEST NUMBER: P332958-940

CATALOG NUMBER: SA4XXRDIP-C1020D365U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1610.2	1610.2	1610.2	1610.2	1610.2	1610.2	1610.2	1610.2	1610.2	1610.2	1610.2
2.5°	1614.1	1613.2	1612.3	1611.5	1610.6	1608.9	1606.5	1604.1	1601.7	1599.3	1601.7
5°	1607.7	1606.6	1605.5	1604.4	1603.3	1601.1	1597.9	1594.6	1591.3	1588.0	1590.7
7.5°	1593.1	1592.0	1590.8	1589.7	1588.5	1585.8	1581.5	1577.3	1573.0	1568.7	1570.5
10°	1579.3	1578.0	1576.5	1575.2	1573.9	1570.7	1565.8	1560.9	1555.9	1551.0	1552.0
12.5°	1561.6	1560.0	1558.4	1556.8	1555.2	1551.5	1545.7	1539.9	1534.1	1528.3	1528.9
15°	1531.2	1528.7	1526.3	1523.8	1521.3	1516.7	1509.8	1503.0	1496.2	1489.3	1488.8
17.5°	1494.5	1490.9	1487.4	1483.8	1480.2	1474.4	1466.2	1457.9	1449.7	1441.5	1439.9
20°	1465.9	1462.3	1458.7	1455.2	1451.6	1445.2	1435.9	1426.6	1417.3	1407.9	1405.8
22.5°	1434.3	1430.3	1426.3	1422.4	1418.4	1411.3	1401.4	1391.4	1381.4	1371.5	1368.2
25°	1384.6	1379.6	1374.7	1369.8	1364.8	1356.7	1345.5	1334.3	1323.0	1311.8	1307.2
27.5°	1332.2	1326.1	1319.9	1313.7	1307.5	1298.4	1286.4	1274.4	1262.4	1250.4	1244.6
30°	1295.7	1288.9	1282.1	1275.2	1268.4	1258.5	1245.6	1232.7	1219.9	1207.0	1200.2
32.5°	1257.3	1249.6	1241.8	1234.1	1226.4	1215.8	1202.6	1189.3	1175.9	1162.6	1154.7
35°	1197.1	1188.4	1179.6	1170.8	1162.1	1150.8	1137.1	1123.5	1109.7	1096.0	1086.7
37.5°	1132.7	1123.7	1114.7	1105.6	1096.6	1084.5	1069.3	1054.2	1038.9	1023.8	1013.3
40°	1087.4	1078.3	1069.3	1060.2	1051.2	1038.9	1023.3	1007.6	992.0	976.4	964.9
42.5°	1044.0	1034.6	1025.0	1015.6	1006.1	993.2	977.0	960.6	944.4	928.1	916.4
45°	976.4	966.3	956.2	946.0	935.9	922.6	906.2	889.7	873.3	856.8	843.5
47.5°	906.7	896.2	885.7	875.3	864.8	851.0	833.9	816.8	799.7	782.7	768.7
50°	859.3	848.6	837.9	827.2	816.5	802.5	785.0	767.4	749.8	732.4	718.6
52.5°	811.0	800.5	790.1	779.6	769.1	754.9	736.9	719.0	701.0	683.1	669.1
55°	739.8	728.8	717.8	706.9	695.9	681.5	663.7	645.9	628.1	610.3	596.0
57.5°	669.2	657.8	646.4	635.0	623.7	609.1	591.7	574.1	556.5	539.0	524.6
60°	618.9	608.0	597.0	586.0	575.1	560.8	543.3	525.8	508.2	490.7	476.4
62.5°	573.5	562.1	550.7	539.3	528.0	513.3	495.3	477.3	459.3	441.4	428.2
65°	503.0	491.2	479.5	467.7	455.9	441.2	423.7	406.2	388.6	371.1	359.4
67.5°	429.8	418.5	407.2	395.9	384.6	370.9	354.5	338.3	322.0	305.8	295.6
70°	383.4	371.9	360.4	348.9	337.4	323.9	308.3	292.6	277.0	261.4	252.4
72.5°	334.1	323.7	313.3	302.9	292.5	279.9	265.2	250.4	235.7	221.0	213.2
75°	267.5	257.4	247.3	237.1	227.0	215.4	202.6	189.8	176.8	164.0	157.7
77.5°	200.0	191.4	182.8	174.2	165.6	156.0	145.6	135.3	124.8	114.4	110.8
80°	156.6	148.6	140.7	132.8	124.8	116.7	108.5	100.3	92.0	83.8	83.0
82.5°	119.1	111.8	104.5	97.2	90.0	83.9	79.3	74.5	69.8	65.1	64.5
85°	66.6	61.1	55.6	50.1	44.7	41.5	40.7	39.9	39.1	38.3	37.6
87.5°	22.9	21.3	19.7	18.1	16.5	15.6	15.5	15.4	15.3	15.2	15.1
90°	1.0	1.7	2.5	3.3	4.0	4.7	5.3	5.8	6.3	7.0	7.3
92.5°	4.0	4.0	4.0	4.1	4.1	4.5	5.0	5.5	6.2	6.7	7.1
95°	17.3	15.0	12.6	10.2	7.8	6.7	6.7	6.8	6.9	7.0	7.3
97.5°	36.8	38.3	39.8	41.3	42.7	39.6	31.7	24.0	16.1	8.3	8.4
100°	51.7	53.0	54.2	55.5	56.7	52.5	42.9	33.2	23.5	13.9	12.7
102.5°	68.3	69.3	70.2	71.1	72.1	71.9	70.6	69.4	68.0	66.8	53.9
105°	94.9	95.2	95.7	96.1	96.6	96.9	97.3	97.6	98.0	98.4	99.0
107.5°	119.5	119.7	119.9	120.1	120.4	120.6	121.2	121.6	122.1	122.6	122.9
110°	136.2	136.3	136.5	136.8	137.0	137.3	137.7	138.1	138.6	139.0	139.1



TEST NUMBER: P332958-940

CATALOG NUMBER: SA4XXRDIP-C1020D365U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	152.3	152.7	153.0	153.4	153.8	154.1	154.3	154.4	154.6	154.9	154.8
115°	177.1	177.4	177.5	177.7	178.0	178.0	178.0	177.9	177.8	177.7	177.9
117.5°	199.5	199.7	200.0	200.4	200.6	200.8	201.0	201.2	201.3	201.4	201.4
120°	214.6	214.9	215.2	215.4	215.7	215.8	215.8	215.7	215.6	215.5	215.7
122.5°	228.7	228.9	229.1	229.3	229.4	229.5	229.6	229.7	229.8	230.0	230.0
125°	249.0	249.2	249.5	249.8	250.1	250.1	250.0	249.9	249.8	249.6	249.8
127.5°	268.1	268.2	268.2	268.3	268.4	268.6	268.9	269.2	269.6	269.9	269.8
130°	280.4	280.5	280.6	280.7	280.8	280.9	281.1	281.3	281.5	281.8	281.8
132.5°	291.9	291.9	292.0	292.2	292.3	292.5	292.7	293.0	293.3	293.6	293.6
135°	308.8	308.8	308.7	308.6	308.5	308.6	309.0	309.2	309.5	309.8	310.0
137.5°	323.9	324.0	324.0	324.0	324.0	324.2	324.5	324.8	325.1	325.4	325.6
140°	333.8	333.9	334.0	334.1	334.3	334.4	334.6	334.7	334.8	335.0	335.2
142.5°	342.6	342.8	343.0	343.3	343.6	343.8	343.8	343.9	344.0	344.1	344.2
145°	356.1	356.3	356.5	356.8	357.0	357.0	357.0	357.0	357.0	357.0	357.1
147.5°	366.8	367.3	367.7	368.1	368.5	368.6	368.5	368.5	368.4	368.4	368.4
150°	374.7	375.0	375.2	375.6	375.9	375.9	375.9	375.8	375.7	375.7	375.7
152.5°	381.3	381.5	381.7	381.9	382.2	382.2	382.1	381.9	381.8	381.7	381.8
155°	390.5	390.6	390.6	390.7	390.7	390.7	390.5	390.2	390.0	389.9	390.1
157.5°	398.2	398.1	398.1	398.1	398.1	397.9	397.7	397.4	397.2	397.0	397.3
160°	402.8	402.5	402.3	402.2	401.9	401.8	401.7	401.6	401.5	401.4	401.9
162.5°	406.8	406.5	406.3	406.0	405.7	405.6	405.5	405.4	405.4	405.3	405.7
165°	411.9	411.5	411.2	410.8	410.5	410.3	410.3	410.3	410.3	410.3	410.9
167.5°	415.9	415.5	415.2	414.8	414.5	414.3	414.2	414.2	414.1	414.1	414.7
170°	418.2	417.8	417.3	417.0	416.5	416.3	416.4	416.5	416.5	416.6	417.1
172.5°	419.7	419.3	418.8	418.5	418.0	417.9	417.9	418.0	418.0	418.1	418.7
175°	421.3	420.9	420.5	420.1	419.6	419.5	419.5	419.6	419.7	419.7	420.4
177.5°	422.1	421.7	421.3	420.9	420.5	420.4	420.5	420.6	420.7	420.8	421.3
180°	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3



TEST NUMBER: P332958-940

CATALOG NUMBER: SA4XXRDIP-C1020D365U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1610.2	1610.2	1610.2	1610.2	1610.2	1610.2	1610.2	1610.2
2.5°	1604.1	1606.5	1608.9	1610.1	1609.8	1609.6	1609.4	1609.2
5°	1593.4	1596.2	1598.9	1600.0	1599.5	1598.9	1598.4	1597.9
7.5°	1572.3	1574.0	1575.7	1576.2	1575.3	1574.4	1573.5	1572.6
10°	1553.2	1554.3	1555.3	1555.3	1554.3	1553.2	1552.0	1551.0
12.5°	1529.6	1530.3	1530.9	1530.4	1528.9	1527.4	1525.9	1524.4
15°	1488.3	1487.6	1487.1	1485.9	1484.0	1482.0	1480.2	1478.2
17.5°	1438.4	1436.9	1435.4	1433.2	1430.2	1427.4	1424.4	1421.5
20°	1403.6	1401.4	1399.2	1396.3	1392.8	1389.2	1385.6	1382.1
22.5°	1364.9	1361.6	1358.3	1355.2	1352.3	1349.4	1346.5	1343.6
25°	1302.4	1297.8	1293.2	1289.4	1286.7	1284.0	1281.2	1278.5
27.5°	1238.9	1233.1	1227.4	1222.5	1218.6	1214.6	1210.7	1206.8
30°	1193.3	1186.4	1179.6	1173.9	1169.6	1165.2	1160.8	1156.5
32.5°	1146.7	1138.8	1130.9	1124.8	1120.6	1116.4	1112.3	1108.1
35°	1077.4	1068.1	1058.7	1051.7	1046.7	1041.8	1036.9	1031.9
37.5°	1003.0	992.6	982.1	974.5	969.6	964.6	959.7	954.8
40°	953.4	941.9	930.4	922.2	917.3	912.3	907.4	902.5
42.5°	904.6	893.0	881.2	872.8	867.6	862.5	857.3	852.2
45°	830.0	816.5	803.2	794.0	789.1	784.1	779.2	774.3
47.5°	754.8	740.9	726.9	717.3	711.9	706.4	701.0	695.6
50°	704.9	691.3	677.5	668.1	662.9	657.6	652.5	647.3
52.5°	655.1	641.2	627.3	617.7	612.2	606.8	601.4	596.0
55°	581.8	567.6	553.3	543.6	538.3	533.2	528.0	522.7
57.5°	510.1	495.6	481.2	472.0	468.0	464.0	460.1	456.2
60°	462.2	447.9	433.7	424.4	420.0	415.6	411.3	406.9
62.5°	415.1	401.9	388.8	380.4	376.9	373.4	369.9	366.4
65°	347.5	335.7	324.0	316.5	313.2	309.9	306.6	303.3
67.5°	285.4	275.4	265.2	258.3	254.7	251.1	247.4	243.9
70°	243.3	234.3	225.2	219.3	216.6	213.8	211.1	208.4
72.5°	205.5	197.8	190.0	184.9	182.4	179.9	177.4	174.9
75°	151.4	145.1	138.8	134.8	133.1	131.5	129.8	128.2
77.5°	107.1	103.4	99.7	97.6	97.1	96.7	96.1	95.7
80°	82.2	81.4	80.5	80.0	79.7	79.5	79.2	78.9
82.5°	63.8	63.3	62.7	62.2	62.0	61.7	61.4	61.2
85°	37.1	36.6	36.0	35.8	35.8	35.8	35.8	35.8
87.5°	14.9	14.8	14.6	14.7	15.0	15.2	15.4	15.7
90°	7.8	8.2	8.6	8.9	9.0	9.2	9.3	9.5
92.5°	7.5	7.9	8.4	8.6	8.6	8.6	8.6	8.7
95°	7.8	8.2	8.6	8.8	8.9	9.0	9.1	9.1
97.5°	8.4	8.5	8.5	8.6	8.6	8.6	8.7	8.8
100°	11.5	10.3	9.1	8.6	8.6	8.6	8.7	8.8
102.5°	41.1	28.3	15.4	9.0	9.0	9.0	9.1	9.1
105°	99.6	100.2	100.9	99.9	97.4	94.9	92.3	89.8
107.5°	123.2	123.5	123.9	124.1	124.4	124.7	124.9	125.2
110°	139.3	139.4	139.6	139.7	139.9	140.2	140.4	140.5



TEST NUMBER: P332958-940

CATALOG NUMBER: SA4XXRDIP-C1020D365U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	154.8	154.8	154.7	154.9	155.2	155.4	155.7	156.0
115°	178.0	178.2	178.3	178.3	178.3	178.3	178.3	178.3
117.5°	201.3	201.3	201.3	201.3	201.3	201.3	201.3	201.2
120°	215.8	216.0	216.2	216.2	216.0	215.8	215.7	215.5
122.5°	230.1	230.2	230.2	230.2	230.1	230.0	229.8	229.7
125°	250.0	250.2	250.4	250.6	250.7	250.7	250.7	250.8
127.5°	269.8	269.7	269.7	269.7	269.7	269.6	269.5	269.5
130°	281.9	282.0	282.0	282.0	282.0	282.0	282.0	282.0
132.5°	293.7	293.8	293.9	293.9	293.8	293.7	293.7	293.6
135°	310.0	310.2	310.3	310.5	310.6	310.8	310.9	311.0
137.5°	325.7	325.9	326.0	326.1	326.0	326.0	325.9	325.9
140°	335.4	335.6	335.8	336.0	336.1	336.1	336.2	336.3
142.5°	344.4	344.6	344.6	344.7	344.8	344.8	344.8	344.8
145°	357.2	357.3	357.3	357.4	357.6	357.8	357.8	358.0
147.5°	368.5	368.5	368.5	368.6	368.7	368.7	368.8	368.9
150°	375.7	375.7	375.7	375.7	375.8	375.9	375.9	375.9
152.5°	381.9	382.0	382.2	382.2	382.1	382.1	382.1	382.0
155°	390.4	390.7	390.9	391.0	390.7	390.6	390.4	390.1
157.5°	397.7	398.1	398.4	398.4	398.1	397.7	397.3	397.0
160°	402.3	402.8	403.1	403.1	402.8	402.3	401.9	401.4
162.5°	406.1	406.5	407.0	406.9	406.4	406.0	405.5	405.0
165°	411.4	412.0	412.6	412.5	411.9	411.3	410.6	410.0
167.5°	415.4	416.0	416.5	416.5	415.8	415.1	414.4	413.8
170°	417.8	418.3	418.8	418.7	418.1	417.4	416.7	416.0
172.5°	419.3	419.8	420.4	420.3	419.5	418.7	418.0	417.2
175°	421.1	421.7	422.3	422.2	421.3	420.5	419.6	418.8
177.5°	421.8	422.2	422.7	422.5	421.9	421.2	420.5	419.8
180°	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3

(END OF REPORT)