

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332964-940

Luminaire Tested: **SA4XXRDIP-C1020D590U940-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332964-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C1020D590U940-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 590 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5825.7 lumens
Efficiency: N/A
Efficacy: 119.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 48.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332964-940
CATALOG NUMBER: SA4XXRDIP-C1020D590U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332964-940

CATALOG NUMBER: SA4XXRDIP-C1020D590U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	104	104	104	104	91	91	91	79	79	79	69	69	69	64
1	101	97	93	90	95	91	88	85	80	78	76	71	69	67	61	60	59	55
2	92	85	79	74	87	80	75	70	71	67	63	62	59	57	54	52	50	46
3	85	75	68	62	79	71	64	59	63	58	54	55	51	48	49	46	43	40
4	78	67	59	53	73	63	56	50	56	50	46	50	45	42	44	40	37	34
5	71	60	52	45	67	56	49	44	50	44	40	45	40	36	39	36	33	30
6	66	54	46	40	62	51	44	38	46	40	35	41	36	32	36	32	29	26
7	61	49	41	35	57	46	39	34	41	35	31	37	32	28	33	29	26	23
8	57	44	37	31	53	42	35	30	38	32	28	34	29	26	30	26	23	21
9	53	41	33	28	50	39	32	27	35	29	25	31	27	23	28	24	21	19
10	50	37	30	25	47	36	29	24	32	27	23	29	24	21	26	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12999	12999	12999
5°	13028	12869	12949
10°	12946	12714	12714
15°	12797	12447	12354
20°	12594	12095	11874
25°	12333	11685	11388
30°	12078	11251	10781
35°	11798	10801	10170
40°	11460	10290	9511
45°	11147	9782	8840
50°	10792	9198	8130
55°	10412	8590	7357
60°	9993	7923	6570
65°	9608	7089	5794
70°	9050	6170	4919
75°	8344	5115	3999
80°	7280	3896	3668
85°	6169	3548	3316



TEST NUMBER: P332964-940

CATALOG NUMBER: SA4XXRDIP-C1020D590U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	151.3	2.6
10°-20°	421.8	7.2
20°-30°	609.1	10.5
30°-40°	690.4	11.9
40°-50°	666.7	11.4
50°-60°	554.4	9.5
60°-70°	382.8	6.6
70°-80°	194.0	3.3
80°-90°	51.8	0.9
90°-100°	23.3	0.4
100°-110°	148.3	2.5
110°-120°	283.7	4.9
120°-130°	360.1	6.2
130°-140°	385.3	6.6
140°-150°	360.3	6.2
150°-160°	290.6	5.0
160°-170°	187.4	3.2
170°-180°	64.6	1.1
0°-30°	1182.1	20.3
0°-40°	1872.5	32.1
0°-60°	3093.5	53.1
0°-90°	3722.1	63.9
90°-120°	455.3	7.8
90°-150°	1561.1	26.8
90°-180°	2104.0	36.1
0°-180°	5825.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1610	1610	1610	1610	1610	
5°	1608	1602	1588	1599	1598	152
15°	1531	1519	1489	1486	1478	431
25°	1385	1361	1312	1291	1278	638
35°	1197	1156	1096	1055	1032	748
45°	976	929	857	799	774	753
55°	740	689	610	548	523	661
65°	503	449	371	320	303	497
75°	268	221	164	137	128	282
85°	67	43	38	36	36	75
90°	2	7	11	14	15	4
95°	28	12	11	14	15	36
105°	153	156	159	162	145	160
115°	286	287	287	288	288	281
125°	402	404	403	404	405	359
135°	498	498	500	501	502	384
145°	575	576	576	577	578	359
155°	630	631	629	631	630	290
165°	665	662	662	666	662	188
175°	680	677	678	682	676	65
180°	680	680	680	680	680	



TEST NUMBER: P332964-940

CATALOG NUMBER: SA4XXRDIP-C1020D590U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1610.2	1610.2	1610.2	1610.2	1610.2	1610.2	1610.2	1610.2	1610.2	1610.2	1610.2
2.5°	1614.1	1613.2	1612.3	1611.5	1610.6	1608.9	1606.5	1604.1	1601.7	1599.3	1601.7
5°	1607.7	1606.6	1605.5	1604.4	1603.3	1601.1	1597.9	1594.6	1591.3	1588.0	1590.7
7.5°	1593.1	1592.0	1590.8	1589.7	1588.5	1585.8	1581.5	1577.3	1573.0	1568.7	1570.5
10°	1579.3	1578.0	1576.5	1575.2	1573.9	1570.7	1565.8	1560.9	1555.9	1551.0	1552.0
12.5°	1561.6	1560.0	1558.4	1556.8	1555.2	1551.5	1545.7	1539.9	1534.1	1528.3	1528.9
15°	1531.2	1528.7	1526.3	1523.8	1521.3	1516.7	1509.8	1503.0	1496.2	1489.3	1488.8
17.5°	1494.5	1490.9	1487.4	1483.8	1480.2	1474.4	1466.2	1457.9	1449.7	1441.5	1439.9
20°	1465.9	1462.3	1458.7	1455.2	1451.6	1445.2	1435.9	1426.6	1417.3	1407.9	1405.8
22.5°	1434.3	1430.3	1426.3	1422.4	1418.4	1411.3	1401.4	1391.4	1381.4	1371.5	1368.2
25°	1384.6	1379.6	1374.7	1369.8	1364.8	1356.7	1345.5	1334.3	1323.0	1311.8	1307.2
27.5°	1332.2	1326.1	1319.9	1313.7	1307.5	1298.4	1286.4	1274.4	1262.4	1250.4	1244.6
30°	1295.7	1288.9	1282.1	1275.2	1268.4	1258.5	1245.6	1232.7	1219.9	1207.0	1200.2
32.5°	1257.3	1249.6	1241.8	1234.1	1226.4	1215.8	1202.6	1189.3	1175.9	1162.6	1154.7
35°	1197.1	1188.4	1179.6	1170.8	1162.1	1150.8	1137.1	1123.5	1109.7	1096.0	1086.7
37.5°	1132.7	1123.7	1114.7	1105.6	1096.6	1084.5	1069.3	1054.2	1038.9	1023.8	1013.3
40°	1087.4	1078.3	1069.3	1060.2	1051.2	1038.9	1023.3	1007.6	992.0	976.4	964.9
42.5°	1044.0	1034.6	1025.0	1015.6	1006.1	993.2	977.0	960.6	944.4	928.1	916.4
45°	976.4	966.3	956.2	946.0	935.9	922.6	906.2	889.7	873.3	856.8	843.5
47.5°	906.7	896.2	885.7	875.3	864.8	851.0	833.9	816.8	799.7	782.7	768.7
50°	859.3	848.6	837.9	827.2	816.5	802.5	785.0	767.4	749.8	732.4	718.6
52.5°	811.0	800.5	790.1	779.6	769.1	754.9	736.9	719.0	701.0	683.1	669.1
55°	739.8	728.8	717.8	706.9	695.9	681.5	663.7	645.9	628.1	610.3	596.0
57.5°	669.2	657.8	646.4	635.0	623.7	609.1	591.7	574.1	556.5	539.0	524.6
60°	618.9	608.0	597.0	586.0	575.1	560.8	543.3	525.8	508.2	490.7	476.4
62.5°	573.5	562.1	550.7	539.3	528.0	513.3	495.3	477.3	459.3	441.4	428.2
65°	503.0	491.2	479.5	467.7	455.9	441.2	423.7	406.2	388.6	371.1	359.4
67.5°	429.8	418.5	407.2	395.9	384.6	370.9	354.5	338.3	322.0	305.8	295.6
70°	383.4	371.9	360.4	348.9	337.4	323.9	308.3	292.6	277.0	261.4	252.4
72.5°	334.1	323.7	313.3	302.9	292.5	279.9	265.2	250.4	235.7	221.0	213.2
75°	267.5	257.4	247.3	237.1	227.0	215.4	202.6	189.8	176.8	164.0	157.7
77.5°	200.0	191.4	182.8	174.2	165.6	156.0	145.6	135.3	124.8	114.4	110.8
80°	156.6	148.6	140.7	132.8	124.8	116.7	108.5	100.3	92.0	83.8	83.0
82.5°	119.1	111.8	104.5	97.2	90.0	83.9	79.3	74.5	69.8	65.1	64.5
85°	66.6	61.1	55.6	50.1	44.7	41.5	40.7	39.9	39.1	38.3	37.6
87.5°	23.0	21.5	20.0	18.5	16.9	16.2	16.1	16.1	16.1	16.1	16.0
90°	1.5	2.8	4.0	5.3	6.5	7.6	8.5	9.4	10.3	11.1	11.9
92.5°	6.4	6.5	6.5	6.6	6.7	7.1	8.1	9.0	9.9	10.8	11.5
95°	28.0	24.2	20.3	16.4	12.6	10.7	10.9	11.0	11.1	11.1	11.9
97.5°	59.4	61.8	64.2	66.6	69.0	63.8	51.3	38.7	26.0	13.5	13.5
100°	83.4	85.4	87.5	89.5	91.6	84.8	69.2	53.6	38.0	22.4	20.4
102.5°	110.3	111.7	113.2	114.8	116.3	116.0	114.0	111.9	109.9	107.8	87.1
105°	153.1	153.8	154.4	155.2	155.8	156.4	157.0	157.6	158.1	158.7	159.7
107.5°	192.9	193.2	193.6	193.9	194.2	194.7	195.6	196.4	197.1	197.9	198.4
110°	219.7	220.1	220.4	220.8	221.1	221.6	222.3	222.9	223.6	224.4	224.5



TEST NUMBER: P332964-940

CATALOG NUMBER: SA4XXRDIP-C1020D590U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	245.8	246.4	247.0	247.6	248.3	248.7	249.0	249.3	249.7	249.9	249.9
115°	285.9	286.2	286.5	286.9	287.2	287.3	287.2	287.1	287.0	286.9	287.1
117.5°	322.0	322.4	322.9	323.3	323.8	324.1	324.4	324.7	324.9	325.1	325.1
120°	346.4	346.9	347.3	347.8	348.2	348.4	348.3	348.1	348.0	347.9	348.1
122.5°	369.2	369.4	369.7	370.0	370.2	370.5	370.7	370.8	371.0	371.1	371.2
125°	401.8	402.3	402.8	403.2	403.7	403.8	403.5	403.3	403.1	402.9	403.2
127.5°	432.7	432.8	433.0	433.1	433.2	433.5	434.1	434.5	435.1	435.6	435.5
130°	452.7	452.8	452.9	453.1	453.2	453.3	453.7	454.1	454.4	454.8	454.9
132.5°	471.0	471.2	471.4	471.6	471.8	472.2	472.6	473.0	473.4	473.9	473.9
135°	498.5	498.4	498.3	498.1	498.0	498.2	498.6	499.1	499.5	500.0	500.2
137.5°	522.8	522.8	522.9	522.9	523.0	523.3	523.7	524.2	524.8	525.2	525.5
140°	538.7	538.9	539.1	539.3	539.6	539.8	540.0	540.3	540.5	540.7	541.0
142.5°	552.9	553.3	553.8	554.1	554.6	554.8	554.9	555.1	555.2	555.4	555.6
145°	574.8	575.2	575.4	575.8	576.1	576.3	576.3	576.3	576.3	576.3	576.4
147.5°	592.2	592.8	593.4	594.1	594.7	594.9	594.9	594.8	594.6	594.5	594.6
150°	604.8	605.2	605.7	606.2	606.6	606.8	606.6	606.5	606.5	606.3	606.3
152.5°	615.4	615.7	616.1	616.4	616.8	616.9	616.7	616.5	616.3	616.1	616.3
155°	630.3	630.4	630.4	630.5	630.7	630.5	630.3	629.9	629.5	629.2	629.6
157.5°	642.7	642.7	642.6	642.6	642.5	642.2	641.9	641.5	641.1	640.7	641.3
160°	650.1	649.7	649.3	649.1	648.7	648.5	648.4	648.3	648.1	648.0	648.7
162.5°	656.6	656.1	655.7	655.3	654.9	654.6	654.4	654.3	654.2	654.2	654.8
165°	664.8	664.2	663.7	663.1	662.5	662.3	662.3	662.3	662.3	662.3	663.2
167.5°	671.3	670.7	670.1	669.6	669.0	668.6	668.6	668.5	668.4	668.3	669.4
170°	675.0	674.3	673.6	673.0	672.3	672.0	672.1	672.2	672.3	672.4	673.3
172.5°	677.4	676.7	676.1	675.4	674.8	674.4	674.6	674.7	674.8	674.8	675.8
175°	680.1	679.4	678.7	678.1	677.3	677.1	677.2	677.3	677.4	677.5	678.5
177.5°	681.3	680.6	680.0	679.4	678.8	678.5	678.7	678.9	679.0	679.2	680.0
180°	680.1	680.1	680.1	680.1	680.1	680.1	680.1	680.1	680.1	680.1	680.1



TEST NUMBER: P332964-940

CATALOG NUMBER: SA4XXRDIP-C1020D590U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1610.2	1610.2	1610.2	1610.2	1610.2	1610.2	1610.2	1610.2
2.5°	1604.1	1606.5	1608.9	1610.1	1609.8	1609.6	1609.4	1609.2
5°	1593.4	1596.2	1598.9	1600.0	1599.5	1598.9	1598.4	1597.9
7.5°	1572.3	1574.0	1575.7	1576.2	1575.3	1574.4	1573.5	1572.6
10°	1553.2	1554.3	1555.3	1555.3	1554.3	1553.2	1552.0	1551.0
12.5°	1529.6	1530.3	1530.9	1530.4	1528.9	1527.4	1525.9	1524.4
15°	1488.3	1487.6	1487.1	1485.9	1484.0	1482.0	1480.2	1478.2
17.5°	1438.4	1436.9	1435.4	1433.2	1430.2	1427.4	1424.4	1421.5
20°	1403.6	1401.4	1399.2	1396.3	1392.8	1389.2	1385.6	1382.1
22.5°	1364.9	1361.6	1358.3	1355.2	1352.3	1349.4	1346.5	1343.6
25°	1302.4	1297.8	1293.2	1289.4	1286.7	1284.0	1281.2	1278.5
27.5°	1238.9	1233.1	1227.4	1222.5	1218.6	1214.6	1210.7	1206.8
30°	1193.3	1186.4	1179.6	1173.9	1169.6	1165.2	1160.8	1156.5
32.5°	1146.7	1138.8	1130.9	1124.8	1120.6	1116.4	1112.3	1108.1
35°	1077.4	1068.1	1058.7	1051.7	1046.7	1041.8	1036.9	1031.9
37.5°	1003.0	992.6	982.1	974.5	969.6	964.6	959.7	954.8
40°	953.4	941.9	930.4	922.2	917.3	912.3	907.4	902.5
42.5°	904.6	893.0	881.2	872.8	867.6	862.5	857.3	852.2
45°	830.0	816.5	803.2	794.0	789.1	784.1	779.2	774.3
47.5°	754.8	740.9	726.9	717.3	711.9	706.4	701.0	695.6
50°	704.9	691.3	677.5	668.1	662.9	657.6	652.5	647.3
52.5°	655.1	641.2	627.3	617.7	612.2	606.8	601.4	596.0
55°	581.8	567.6	553.3	543.6	538.3	533.2	528.0	522.7
57.5°	510.1	495.6	481.2	472.0	468.0	464.0	460.1	456.2
60°	462.2	447.9	433.7	424.4	420.0	415.6	411.3	406.9
62.5°	415.1	401.9	388.8	380.4	376.9	373.4	369.9	366.4
65°	347.5	335.7	324.0	316.5	313.2	309.9	306.6	303.3
67.5°	285.4	275.4	265.2	258.3	254.7	251.1	247.4	243.9
70°	243.3	234.3	225.2	219.3	216.6	213.8	211.1	208.4
72.5°	205.5	197.8	190.0	184.9	182.4	179.9	177.4	174.9
75°	151.4	145.1	138.8	134.8	133.1	131.5	129.8	128.2
77.5°	107.1	103.4	99.7	97.6	97.1	96.7	96.1	95.7
80°	82.2	81.4	80.5	80.0	79.7	79.5	79.2	78.9
82.5°	63.8	63.3	62.7	62.2	62.0	61.7	61.4	61.2
85°	37.1	36.6	36.0	35.8	35.8	35.8	35.8	35.8
87.5°	15.9	15.8	15.7	15.8	16.1	16.3	16.6	16.9
90°	12.6	13.2	13.9	14.4	14.6	14.8	15.1	15.2
92.5°	12.1	12.8	13.5	13.8	13.9	13.9	14.0	14.0
95°	12.6	13.2	13.9	14.3	14.4	14.5	14.6	14.7
97.5°	13.6	13.6	13.7	13.8	13.9	14.0	14.1	14.3
100°	18.5	16.6	14.7	13.8	13.9	14.0	14.1	14.3
102.5°	66.3	45.7	24.9	14.5	14.6	14.6	14.6	14.6
105°	160.8	161.8	162.7	161.2	157.2	153.1	149.0	145.0
107.5°	198.9	199.4	199.8	200.3	200.7	201.2	201.6	202.1
110°	224.8	225.0	225.2	225.5	225.9	226.1	226.5	226.9



TEST NUMBER: P332964-940

CATALOG NUMBER: SA4XXRDIP-C1020D590U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	249.9	249.9	249.8	249.9	250.4	250.8	251.3	251.6
115°	287.3	287.6	287.8	287.9	287.9	287.9	287.9	287.9
117.5°	325.0	325.0	324.9	324.9	324.9	324.9	324.8	324.8
120°	348.4	348.6	348.8	348.8	348.6	348.4	348.1	347.9
122.5°	371.4	371.5	371.7	371.6	371.4	371.1	371.0	370.7
125°	403.5	403.9	404.2	404.5	404.6	404.7	404.7	404.9
127.5°	435.5	435.4	435.3	435.2	435.2	435.1	435.0	434.9
130°	455.0	455.0	455.2	455.2	455.2	455.2	455.2	455.2
132.5°	474.1	474.2	474.3	474.3	474.2	474.1	474.0	473.9
135°	500.4	500.7	500.9	501.1	501.3	501.6	501.9	502.0
137.5°	525.8	526.0	526.2	526.3	526.3	526.2	526.1	526.0
140°	541.4	541.7	542.1	542.2	542.4	542.5	542.6	542.7
142.5°	555.8	556.1	556.3	556.5	556.5	556.5	556.5	556.6
145°	576.5	576.7	576.8	576.9	577.1	577.4	577.7	577.8
147.5°	594.7	594.8	594.9	594.9	595.1	595.2	595.3	595.4
150°	606.3	606.3	606.3	606.4	606.5	606.6	606.7	606.8
152.5°	616.4	616.6	616.8	616.9	616.8	616.7	616.6	616.6
155°	630.1	630.5	631.0	631.1	630.7	630.4	630.1	629.7
157.5°	641.9	642.5	643.0	643.0	642.5	641.9	641.3	640.7
160°	649.3	650.1	650.8	650.8	650.1	649.3	648.7	648.0
162.5°	655.5	656.1	656.8	656.8	656.0	655.2	654.5	653.7
165°	664.1	664.9	665.9	665.8	664.8	663.8	662.8	661.7
167.5°	670.4	671.4	672.3	672.3	671.2	670.0	668.9	667.8
170°	674.2	675.1	676.1	675.9	674.8	673.7	672.5	671.5
172.5°	676.7	677.6	678.5	678.3	677.2	675.9	674.7	673.4
175°	679.6	680.6	681.6	681.4	680.1	678.7	677.3	676.0
177.5°	680.7	681.4	682.2	682.0	680.9	679.8	678.7	677.6
180°	680.1	680.1	680.1	680.1	680.1	680.1	680.1	680.1

(END OF REPORT)