

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331984-830

Luminaire Tested: **S123DIP-S775D1025U830-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331984-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S775D1025U830-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1025 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6574.2 lumens
Efficiency: N/A
Efficacy: 126.4 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331984-830

CATALOG NUMBER: S123DIP-S775D1025U830-4F0-1E-UDD-A4

Luminous Intensity Polar Plot



TEST NUMBER: P331984-830

CATALOG NUMBER: S123DIP-S775D1025U830-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	53	53	53
1	97	93	89	86	89	86	82	80	72	70	67	59	58	56	47	46	45
2	89	82	76	71	81	75	70	66	63	59	56	52	50	47	42	40	39
3	81	72	65	59	74	66	60	55	56	51	48	46	43	40	37	35	33
4	74	64	56	50	68	59	52	47	50	45	41	41	38	35	34	31	29
5	68	57	49	43	62	53	46	40	45	39	35	37	33	30	30	27	25
6	63	51	43	37	58	47	40	35	40	35	31	34	30	26	28	24	22
7	58	46	38	33	53	43	36	31	36	31	27	31	26	23	25	22	20
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	23	20	18
9	50	38	31	26	46	35	29	24	30	25	21	26	22	19	21	18	16
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10962	10962	10962	10962
5°	13073	11010	9757	11010
10°	16363	10954	8813	10954
15°	20070	10866	8204	10866
20°	23909	10727	7811	10727
25°	25388	10561	7725	10561
30°	21760	10438	7764	10438
35°	15134	10264	7846	10264
40°	11398	10061	7821	10061
45°	9464	9758	7722	9758
50°	8477	9138	7651	9138
55°	7927	8473	7557	8473
60°	7436	7776	7479	7776
65°	6989	7088	7238	7088
70°	6552	6304	6892	6304
75°	5868	5519	6317	5519
80°	5139	4525	5442	4525
85°	4026	3298	3656	3298

TEST NUMBER: P331984-830

CATALOG NUMBER: S123DIP-S775D1025U830-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.3	1.5
10°-20°	321.7	4.9
20°-30°	539.9	8.2
30°-40°	611.3	9.3
40°-50°	548.2	8.3
50°-60°	442.4	6.7
60°-70°	308.3	4.7
70°-80°	162.0	2.5
80°-90°	43.2	0.7
90°-100°	258.6	3.9
100°-110°	732.4	11.1
110°-120°	720.5	11.0
120°-130°	574.7	8.7
130°-140°	453.1	6.9
140°-150°	338.2	5.1
150°-160°	235.7	3.6
160°-170°	138.5	2.1
170°-180°	45.1	0.7
0°-30°	961.9	14.6
0°-40°	1573.3	23.9
0°-60°	2563.9	39.0
0°-90°	3077.5	46.8
90°-120°	1711.5	26.0
90°-150°	3077.4	46.8
90°-180°	3497.0	53.2
0°-180°	6574.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1018	1018	1018	1018	1018	
5°	1210	1019	903	1019	1210	125
15°	1801	975	736	975	1801	520
25°	2138	889	650	889	2138	937
35°	1152	781	597	781	1152	748
45°	622	641	507	641	622	492
55°	422	452	403	452	422	379
65°	274	278	284	278	274	273
75°	141	133	152	133	141	151
85°	33	27	30	27	33	39
90°	27	2	27	2	27	16
95°	109	32	109	32	109	197
105°	1197	109	1197	109	1197	1181
115°	1456	193	1456	193	1456	1414
125°	1148	268	1148	268	1148	1040
135°	930	314	930	314	930	722
145°	727	358	727	358	727	463
155°	603	407	603	407	603	281
165°	526	445	526	445	526	150
175°	473	464	473	464	473	46
180°	465	465	465	465	465	

TEST NUMBER: P331984-830

CATALOG NUMBER: S123DIP-S775D1025U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4
2.5°	1080.8	1080.1	1078.1	1079.7	1076.5	1072.1	1071.8	1067.8	1056.3	1055.6	1052.4
5°	1209.9	1206.0	1205.5	1204.9	1198.1	1188.7	1170.9	1169.4	1145.8	1133.9	1119.6
7.5°	1377.1	1379.1	1372.0	1365.6	1344.5	1330.6	1311.5	1287.1	1258.1	1228.6	1208.9
10°	1497.1	1513.3	1493.2	1479.3	1466.5	1442.3	1414.2	1379.1	1344.2	1303.2	1272.1
12.5°	1625.8	1633.8	1629.8	1616.7	1596.8	1560.0	1510.1	1471.5	1439.3	1371.0	1343.5
15°	1801.0	1831.2	1811.9	1767.5	1768.5	1733.4	1668.3	1596.8	1558.8	1499.0	1417.7
17.5°	1987.7	1991.5	1983.3	1946.4	1921.7	1873.5	1813.4	1744.8	1667.8	1595.5	1509.2
20°	2087.3	2084.2	2067.0	2047.8	2005.4	1967.8	1902.2	1825.7	1727.0	1656.0	1561.7
22.5°	2142.5	2137.6	2129.4	2113.3	2077.9	2037.7	1978.8	1895.2	1801.3	1703.4	1594.5
25°	2137.6	2144.0	2144.9	2140.5	2128.2	2104.0	2057.7	1991.0	1897.2	1771.4	1657.9
27.5°	1944.2	1953.2	1979.6	2003.0	2029.1	2055.8	2052.2	2019.1	1949.7	1841.2	1702.3
30°	1750.7	1731.0	1779.8	1841.5	1883.5	1957.5	1998.9	2001.4	1962.4	1869.2	1733.9
32.5°	1482.2	1504.0	1525.6	1601.5	1693.2	1776.3	1858.8	1925.2	1932.8	1870.8	1752.5
35°	1151.7	1178.8	1218.3	1257.7	1356.5	1441.3	1586.4	1712.7	1813.4	1826.7	1754.2
37.5°	928.0	941.5	966.5	1006.0	1070.5	1171.2	1283.5	1443.1	1588.9	1697.4	1702.1
40°	811.2	815.2	843.3	873.4	925.7	1008.6	1109.7	1250.8	1425.5	1577.1	1640.2
42.5°	723.6	732.3	744.2	773.1	814.7	877.1	971.2	1087.8	1247.9	1422.3	1545.9
45°	621.7	631.6	639.0	658.3	687.9	729.8	795.4	902.0	1023.9	1204.0	1370.3
47.5°	554.4	555.3	560.7	575.2	595.4	626.9	673.3	741.8	853.7	999.7	1170.4
50°	506.2	514.2	516.1	527.4	543.3	566.5	604.9	663.2	755.0	883.3	1040.2
52.5°	472.3	474.7	480.2	488.4	502.2	520.3	553.6	599.3	671.3	780.6	924.9
55°	422.4	422.4	427.8	434.2	442.1	458.4	480.6	514.2	568.9	653.8	773.3
57.5°	376.2	378.6	382.5	384.5	391.2	402.0	420.5	446.0	486.8	552.1	647.1
60°	345.4	349.9	349.4	353.3	359.2	367.6	383.4	404.2	440.6	492.9	572.9
62.5°	318.6	318.3	318.2	322.9	328.9	336.9	347.0	365.0	396.1	442.4	510.5
65°	274.4	273.3	276.8	279.7	281.7	287.7	295.6	311.3	332.1	366.6	419.4
67.5°	235.1	232.2	234.1	235.1	238.5	243.1	250.4	260.2	276.7	304.4	344.2
70°	208.2	205.8	205.3	206.2	209.2	212.6	218.1	227.4	242.8	264.9	294.1
72.5°	180.6	178.9	178.8	181.0	182.4	184.6	188.5	197.1	209.2	225.9	253.1
75°	141.1	141.1	141.1	141.6	143.1	145.1	148.1	152.5	161.8	173.7	191.9
77.5°	105.8	105.7	105.1	105.0	107.2	108.1	108.8	112.9	118.1	126.1	139.4
80°	82.9	80.4	81.4	82.9	83.9	84.4	85.9	86.8	91.3	95.8	105.1
82.5°	61.5	59.5	59.7	62.0	62.2	62.7	64.2	65.5	67.2	71.3	76.3
85°	32.6	32.6	33.1	33.1	33.6	33.1	34.5	35.1	35.1	37.5	40.4
87.5°	17.3	16.7	16.9	17.2	16.9	17.0	17.2	17.3	17.5	18.1	18.0
90°	27.2	28.2	27.2	26.3	27.2	25.4	24.5	23.6	22.6	23.6	20.7
92.5°	45.3	47.0	46.1	48.9	50.6	55.5	62.9	79.2	109.1	144.7	159.2
95°	109.1	112.9	119.5	128.0	145.8	179.7	229.6	338.7	452.5	557.9	496.7
97.5°	297.1	305.2	330.6	373.0	442.3	554.9	676.3	844.3	925.0	864.6	633.0
100°	589.9	589.0	625.7	694.4	789.4	922.9	1033.0	1109.3	1076.3	891.0	602.1
102.5°	865.3	887.0	917.7	972.0	1046.0	1130.7	1194.9	1197.3	1083.8	842.1	556.9
105°	1196.7	1201.5	1231.5	1267.2	1310.6	1335.0	1317.2	1223.0	1026.4	756.4	501.4
107.5°	1387.5	1396.2	1406.4	1418.4	1417.7	1384.1	1301.7	1149.0	926.0	680.8	466.1
110°	1465.8	1467.7	1469.6	1462.1	1435.7	1369.8	1251.3	1078.2	862.7	637.9	452.5

TEST NUMBER: P331984-830

CATALOG NUMBER: S123DIP-S775D1025U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1481.6	1481.2	1474.0	1450.8	1402.6	1317.9	1185.1	1008.1	807.8	609.3	445.0
115°	1455.5	1450.8	1431.9	1390.5	1319.9	1217.4	1079.1	915.4	741.4	578.6	442.1
117.5°	1372.2	1365.9	1338.8	1291.4	1217.8	1113.7	989.6	848.3	701.3	560.5	443.8
120°	1303.1	1297.4	1274.8	1222.1	1147.8	1052.8	939.9	812.8	680.2	552.2	446.9
122.5°	1238.3	1231.1	1206.4	1159.0	1092.9	1004.7	900.0	785.0	662.9	547.0	452.1
125°	1147.8	1141.2	1117.7	1076.3	1016.1	940.8	850.6	748.0	640.7	540.1	460.1
127.5°	1073.3	1067.2	1046.0	1010.6	957.0	888.5	807.0	715.6	621.1	536.7	469.1
130°	1031.1	1023.6	1003.9	970.0	920.1	856.1	780.0	695.3	610.6	534.4	475.1
132.5°	989.8	984.5	967.0	933.1	886.3	825.3	754.3	676.5	600.8	533.7	479.7
135°	930.5	923.9	906.9	878.7	832.6	779.0	717.8	651.0	588.1	532.5	486.4
137.5°	867.8	863.5	849.2	820.6	781.8	735.4	682.7	627.9	576.9	530.5	490.9
140°	824.2	825.1	810.0	783.7	748.0	707.5	662.3	614.3	570.1	529.7	493.9
142.5°	783.5	784.5	770.9	747.6	717.1	681.9	642.8	601.5	564.1	528.2	496.2
145°	727.3	725.4	717.8	698.0	674.6	647.2	617.2	586.2	556.0	525.9	497.7
147.5°	681.0	680.2	673.1	659.7	641.9	622.5	598.1	573.5	548.1	522.4	497.7
150°	653.8	653.8	648.2	637.9	623.8	605.9	586.2	564.5	542.8	519.3	497.7
152.5°	631.3	631.3	627.9	618.3	607.2	592.4	574.9	556.2	536.9	515.6	495.4
155°	603.0	602.1	600.2	592.8	584.3	573.0	558.8	543.8	527.8	509.0	492.9
157.5°	577.3	577.5	576.0	570.3	563.0	554.1	543.2	530.7	517.6	503.1	489.8
160°	560.7	561.7	561.7	556.0	549.4	542.8	533.5	523.1	510.9	498.6	488.3
162.5°	545.6	546.6	546.6	541.8	537.4	531.6	522.9	514.1	504.1	494.1	485.3
165°	525.9	525.9	526.9	523.1	519.3	514.6	508.0	502.4	494.8	487.4	480.8
167.5°	507.1	507.1	508.0	505.4	503.7	500.3	496.5	492.2	486.1	480.6	476.3
170°	495.8	495.8	496.7	494.8	493.9	492.0	488.3	485.5	480.8	476.1	473.3
172.5°	485.3	486.1	487.8	485.9	485.7	484.6	481.5	479.5	475.5	472.3	471.0
175°	473.3	474.2	475.1	474.2	474.2	474.2	472.3	471.4	469.5	467.6	467.6
177.5°	466.3	466.3	467.8	467.0	467.8	467.8	467.0	466.3	465.5	464.8	465.5
180°	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8

TEST NUMBER: P331984-830

CATALOG NUMBER: S123DIP-S775D1025U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4
2.5°	1050.0	1046.9	1043.7	1038.2	1033.5	1026.7	1024.7	1022.4	1015.3	1009.0	1004.3
5°	1114.2	1102.3	1085.1	1069.3	1056.5	1039.2	1029.4	1019.0	1004.2	990.8	980.0
7.5°	1181.3	1158.0	1131.1	1102.1	1075.1	1049.0	1028.0	1009.3	988.5	968.9	953.7
10°	1234.5	1201.0	1163.6	1123.0	1088.5	1055.0	1026.8	1002.2	975.5	952.3	933.1
12.5°	1295.3	1245.7	1193.9	1144.8	1103.9	1057.3	1023.3	991.9	961.7	933.8	912.2
15°	1367.3	1304.2	1242.9	1175.4	1113.2	1055.0	1014.6	975.1	940.0	911.3	883.7
17.5°	1432.9	1361.3	1280.6	1198.4	1123.4	1054.4	997.8	953.1	909.3	874.3	846.8
20°	1470.0	1388.6	1297.2	1211.9	1129.0	1052.0	989.9	936.5	889.2	852.2	821.0
22.5°	1501.9	1406.7	1312.2	1221.0	1128.6	1045.7	975.2	920.4	869.0	832.8	799.7
25°	1535.1	1421.1	1326.3	1219.3	1116.2	1030.3	951.3	889.2	837.8	795.4	761.4
27.5°	1563.5	1420.1	1307.7	1192.5	1096.6	1010.6	926.2	859.6	805.1	759.0	724.4
30°	1582.4	1422.1	1288.4	1174.4	1077.7	988.8	906.9	839.8	782.6	735.7	703.1
32.5°	1594.3	1420.9	1270.6	1149.1	1047.6	969.1	886.0	816.5	757.7	711.6	680.2
35°	1601.2	1412.2	1240.0	1096.9	999.2	922.7	853.2	781.1	719.4	676.5	641.0
37.5°	1587.4	1393.9	1204.5	1046.6	939.6	864.3	805.8	744.4	685.4	638.1	607.6
40°	1565.7	1382.1	1176.9	1011.1	898.5	826.0	776.2	716.0	657.7	612.8	584.2
42.5°	1524.2	1358.0	1146.4	971.6	855.9	783.3	737.5	687.2	632.1	589.9	561.4
45°	1423.1	1305.6	1100.9	912.4	793.0	717.9	677.5	641.0	591.2	550.2	525.5
47.5°	1282.7	1226.8	1034.9	849.9	727.3	655.1	613.0	583.6	547.2	514.2	490.5
50°	1185.2	1162.1	990.3	807.3	683.4	612.8	572.4	545.7	519.6	486.5	464.9
52.5°	1072.7	1087.0	938.2	763.1	638.8	569.4	531.3	510.2	486.4	459.3	440.4
55°	914.4	966.1	848.2	688.8	572.4	506.2	470.2	451.5	437.7	417.5	401.1
57.5°	766.0	832.0	750.9	612.4	507.2	450.2	415.6	395.1	386.3	375.7	362.9
60°	678.0	743.1	681.5	561.0	463.4	409.1	378.4	361.2	352.3	344.9	334.0
62.5°	599.5	665.3	613.5	509.0	420.3	369.9	343.4	326.5	319.5	315.7	306.4
65°	491.4	548.2	513.7	427.8	358.7	314.3	290.1	278.3	271.9	270.4	264.5
67.5°	400.0	443.2	418.0	354.9	300.5	262.1	241.6	231.5	226.6	226.1	221.7
70°	340.0	380.4	361.2	304.0	257.1	227.0	209.2	200.3	197.4	196.9	194.4
72.5°	293.4	321.6	306.3	258.5	222.3	195.0	182.0	172.7	169.4	170.0	168.3
75°	217.1	238.4	229.4	196.4	167.3	149.5	138.6	132.7	129.8	131.3	129.3
77.5°	156.2	169.7	161.6	138.7	120.8	107.9	100.0	96.3	93.7	93.6	92.7
80°	117.9	125.8	121.4	107.5	92.7	81.9	75.5	73.0	71.5	71.1	70.6
82.5°	84.0	90.7	85.5	76.0	65.9	59.4	55.8	52.5	51.5	51.7	51.2
85°	42.4	44.9	42.9	37.0	33.1	30.1	28.1	26.7	25.6	26.1	25.2
87.5°	18.2	18.0	16.3	14.3	13.1	11.4	11.0	9.9	9.4	9.8	10.0
90°	17.9	15.1	12.3	10.4	8.5	5.7	3.8	1.9	3.8	5.7	8.5
92.5°	119.5	79.0	54.4	40.4	32.5	25.3	17.3	11.7	17.3	25.3	32.5
95°	342.4	202.3	122.3	85.6	61.2	45.1	34.8	32.0	34.8	45.1	61.2
97.5°	375.8	217.7	141.3	101.6	77.5	63.6	55.5	54.6	55.5	63.6	77.5
100°	354.7	215.5	149.6	112.9	90.3	77.2	70.6	69.7	70.6	77.2	90.3
102.5°	336.6	218.5	159.4	125.7	105.4	92.9	87.1	85.4	87.1	92.9	105.4
105°	323.7	226.8	176.0	146.8	128.9	117.6	112.0	109.1	112.0	117.6	128.9
107.5°	322.7	242.1	197.6	170.5	153.7	142.6	137.1	134.3	137.1	142.6	153.7
110°	326.5	255.0	212.6	186.2	170.3	159.9	155.2	152.4	155.2	159.9	170.3

TEST NUMBER: P331984-830

CATALOG NUMBER: S123DIP-S775D1025U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	334.0	267.8	228.5	202.8	186.8	176.5	171.8	169.0	171.8	176.5	186.8
115°	346.2	288.8	253.1	227.7	211.7	202.3	196.6	192.8	196.6	202.3	211.7
117.5°	362.4	311.2	275.9	252.3	234.4	225.8	221.1	216.8	221.1	225.8	234.4
120°	374.5	325.6	291.6	268.2	250.2	240.8	236.1	233.3	236.1	240.8	250.2
122.5°	385.8	340.5	307.5	282.5	265.3	255.1	250.4	247.6	250.4	255.1	265.3
125°	403.6	362.2	329.3	303.9	286.0	275.7	270.0	268.2	270.0	275.7	286.0
127.5°	418.3	381.1	349.2	323.9	304.1	293.5	286.5	283.8	286.5	293.5	304.1
130°	428.1	392.3	361.3	335.8	316.1	304.8	296.3	293.5	296.3	304.8	316.1
132.5°	437.2	402.1	371.8	347.1	327.4	313.9	304.6	301.0	304.6	313.9	327.4
135°	448.7	416.8	387.6	362.2	342.4	328.4	318.0	314.2	318.0	328.4	342.4
137.5°	457.4	427.0	398.9	375.4	355.8	340.7	330.6	326.7	330.6	340.7	355.8
140°	461.9	433.8	406.4	383.0	364.1	349.0	339.6	335.0	339.6	349.0	364.1
142.5°	466.5	439.0	412.5	390.4	371.6	358.1	347.9	343.9	347.9	358.1	371.6
145°	471.4	445.9	421.5	399.8	383.9	369.8	361.3	358.4	361.3	369.8	383.9
147.5°	474.4	451.6	429.2	410.8	395.3	383.1	374.8	373.2	374.8	383.1	395.3
150°	475.1	455.3	433.8	416.8	403.6	391.3	383.9	383.0	383.9	391.3	403.6
152.5°	476.6	457.6	439.0	422.8	411.1	400.4	392.9	392.7	392.9	400.4	411.1
155°	477.0	461.9	445.9	432.8	422.4	413.0	407.4	407.4	407.4	413.0	422.4
157.5°	478.0	464.4	451.6	441.4	432.6	424.3	419.8	419.1	419.8	424.3	432.6
160°	478.0	466.7	455.3	445.9	439.3	431.9	428.1	428.1	428.1	431.9	439.3
162.5°	477.2	467.4	457.6	449.7	443.8	437.9	434.9	434.9	434.9	437.9	443.8
165°	475.1	468.5	461.0	454.4	450.6	445.9	444.0	445.0	444.0	445.9	450.6
167.5°	473.6	468.3	462.9	458.7	456.1	452.5	451.6	452.7	451.6	452.5	456.1
170°	471.4	467.6	462.9	461.0	459.1	456.3	455.3	457.2	455.3	456.3	459.1
172.5°	470.6	467.6	463.6	462.5	461.4	459.3	459.1	460.2	459.1	459.3	461.4
175°	468.5	466.7	464.8	463.8	463.8	461.9	462.9	463.8	462.9	461.9	463.8
177.5°	467.0	465.5	464.8	464.8	464.8	464.0	464.8	465.5	464.8	464.0	464.8
180°	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8

TEST NUMBER: P331984-830

CATALOG NUMBER: S123DIP-S775D1025U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4
2.5°	1001.5	998.7	994.8	988.8	984.1	976.6	976.6	977.8	977.8	977.4	976.6
5°	971.1	963.7	954.8	944.4	933.6	922.7	920.8	916.8	913.9	911.9	909.4
7.5°	939.1	925.9	912.9	898.4	885.2	874.3	866.7	860.4	856.3	852.0	848.9
10°	917.3	901.0	885.7	870.4	853.7	840.4	832.0	826.0	821.6	817.7	815.7
12.5°	891.6	873.0	856.1	841.6	823.2	809.5	801.5	798.8	793.5	785.2	780.9
15°	854.1	836.9	816.6	794.5	785.5	768.7	759.4	755.0	752.0	745.6	743.6
17.5°	822.1	799.5	776.7	760.2	743.7	730.1	724.8	719.3	715.4	710.1	708.6
20°	796.4	776.2	755.4	737.7	720.4	705.6	701.2	697.2	693.2	690.8	688.8
22.5°	770.3	750.2	732.9	716.3	698.0	688.2	683.4	679.1	676.3	674.7	672.7
25°	733.8	716.0	696.7	681.9	667.1	660.7	657.7	655.3	653.3	650.8	650.4
27.5°	701.0	681.6	666.0	652.2	641.6	636.2	633.4	632.2	632.6	633.5	634.0
30°	676.5	658.7	645.9	634.0	624.2	619.3	618.8	618.8	620.8	621.2	622.3
32.5°	654.0	639.4	626.6	615.1	607.7	604.3	606.1	606.1	607.8	609.0	610.8
35°	621.2	608.4	598.5	588.7	582.3	583.7	584.8	585.7	588.1	591.2	593.1
37.5°	589.9	578.8	568.5	560.8	557.9	560.5	562.9	565.0	567.9	570.1	572.1
40°	567.4	559.0	549.2	542.2	543.3	544.8	546.8	549.2	551.7	553.2	555.2
42.5°	546.5	537.7	530.3	524.5	525.9	527.8	529.0	530.3	533.1	535.7	537.0
45°	514.6	507.7	500.9	497.4	498.4	499.4	500.3	501.8	504.3	506.2	506.8
47.5°	478.8	474.0	469.4	466.0	467.6	467.2	468.4	471.6	472.4	473.6	476.4
50°	455.9	451.5	446.1	445.1	445.1	445.1	445.5	449.5	449.5	451.5	453.5
52.5°	430.6	427.8	424.3	422.5	421.8	421.8	423.9	425.8	426.6	429.4	431.4
55°	393.2	390.3	387.4	385.9	384.8	385.9	389.8	390.8	393.2	394.7	396.2
57.5°	354.3	352.0	349.7	348.8	348.6	350.0	352.1	355.1	355.7	360.2	362.5
60°	328.7	325.2	323.2	323.2	322.3	326.7	325.6	330.6	331.6	334.5	338.0
62.5°	302.2	297.6	296.7	296.7	298.1	299.4	300.8	302.9	305.6	309.2	312.0
65°	259.6	257.1	260.5	260.0	259.0	262.0	262.0	264.5	267.4	270.9	276.4
67.5°	219.1	217.9	218.2	218.2	219.7	221.4	222.7	224.9	228.5	232.1	235.6
70°	191.9	193.4	191.0	192.9	194.4	194.9	195.9	198.9	202.8	205.3	209.2
72.5°	165.5	165.4	165.7	166.5	168.0	168.8	169.8	173.2	177.6	179.6	182.8
75°	127.3	126.8	128.3	128.3	130.7	131.8	132.7	134.2	138.2	141.1	143.5
77.5°	92.9	93.6	93.2	94.9	94.3	94.4	97.5	99.0	99.3	105.2	106.5
80°	70.0	71.1	71.5	72.0	72.6	71.5	75.0	76.4	76.4	79.9	82.4
82.5°	50.3	50.9	52.2	52.7	52.8	53.8	54.1	55.1	56.4	57.9	61.1
85°	25.2	26.7	27.1	26.7	27.1	26.1	27.6	28.1	28.7	28.7	28.7
87.5°	10.0	10.7	10.9	11.9	12.1	13.0	12.8	12.2	12.3	13.8	12.5
90°	10.4	12.3	15.1	17.9	20.7	23.6	22.6	23.6	24.5	25.4	27.2
92.5°	40.4	54.4	79.0	119.5	159.2	144.7	109.1	79.2	62.9	55.5	50.6
95°	85.6	122.3	202.3	342.4	496.7	557.9	452.5	338.7	229.6	179.7	145.8
97.5°	101.6	141.3	217.7	375.8	633.0	864.6	925.0	844.3	676.3	554.9	442.3
100°	112.9	149.6	215.5	354.7	602.1	891.0	1076.3	1109.3	1033.0	922.9	789.4
102.5°	125.7	159.4	218.5	336.6	556.9	842.1	1083.8	1197.3	1194.9	1130.7	1046.0
105°	146.8	176.0	226.8	323.7	501.4	756.4	1026.4	1223.0	1317.2	1335.0	1310.6
107.5°	170.5	197.6	242.1	322.7	466.1	680.8	926.0	1149.0	1301.7	1384.1	1417.7
110°	186.2	212.6	255.0	326.5	452.5	637.9	862.7	1078.2	1251.3	1369.8	1435.7

TEST NUMBER: P331984-830

CATALOG NUMBER: S123DIP-S775D1025U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	202.8	228.5	267.8	334.0	445.0	609.3	807.8	1008.1	1185.1	1317.9	1402.6
115°	227.7	253.1	288.8	346.2	442.1	578.6	741.4	915.4	1079.1	1217.4	1319.9
117.5°	252.3	275.9	311.2	362.4	443.8	560.5	701.3	848.3	989.6	1113.7	1217.8
120°	268.2	291.6	325.6	374.5	446.9	552.2	680.2	812.8	939.9	1052.8	1147.8
122.5°	282.5	307.5	340.5	385.8	452.1	547.0	662.9	785.0	900.0	1004.7	1092.9
125°	303.9	329.3	362.2	403.6	460.1	540.1	640.7	748.0	850.6	940.8	1016.1
127.5°	323.9	349.2	381.1	418.3	469.1	536.7	621.1	715.6	807.0	888.5	957.0
130°	335.8	361.3	392.3	428.1	475.1	534.4	610.6	695.3	780.0	856.1	920.1
132.5°	347.1	371.8	402.1	437.2	479.7	533.7	600.8	676.5	754.3	825.3	886.3
135°	362.2	387.6	416.8	448.7	486.4	532.5	588.1	651.0	717.8	779.0	832.6
137.5°	375.4	398.9	427.0	457.4	490.9	530.5	576.9	627.9	682.7	735.4	781.8
140°	383.0	406.4	433.8	461.9	493.9	529.7	570.1	614.3	662.3	707.5	748.0
142.5°	390.4	412.5	439.0	466.5	496.2	528.2	564.1	601.5	642.8	681.9	717.1
145°	399.8	421.5	445.9	471.4	497.7	525.9	556.0	586.2	617.2	647.2	674.6
147.5°	410.8	429.2	451.6	474.4	497.7	522.4	548.1	573.5	598.1	622.5	641.9
150°	416.8	433.8	455.3	475.1	497.7	519.3	542.8	564.5	586.2	605.9	623.8
152.5°	422.8	439.0	457.6	476.6	495.4	515.6	536.9	556.2	574.9	592.4	607.2
155°	432.8	445.9	461.9	477.0	492.9	509.0	527.8	543.8	558.8	573.0	584.3
157.5°	441.4	451.6	464.4	478.0	489.8	503.1	517.6	530.7	543.2	554.1	563.0
160°	445.9	455.3	466.7	478.0	488.3	498.6	510.9	523.1	533.5	542.8	549.4
162.5°	449.7	457.6	467.4	477.2	485.3	494.1	504.1	514.1	522.9	531.6	537.4
165°	454.4	461.0	468.5	475.1	480.8	487.4	494.8	502.4	508.0	514.6	519.3
167.5°	458.7	462.9	468.3	473.6	476.3	480.6	486.1	492.2	496.5	500.3	503.7
170°	461.0	462.9	467.6	471.4	473.3	476.1	480.8	485.5	488.3	492.0	493.9
172.5°	462.5	463.6	467.6	470.6	471.0	472.3	475.5	479.5	481.5	484.6	485.7
175°	463.8	464.8	466.7	468.5	467.6	467.6	469.5	471.4	472.3	474.2	474.2
177.5°	464.8	464.8	465.5	467.0	465.5	464.8	465.5	466.3	467.0	467.8	467.8
180°	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8

TEST NUMBER: P331984-830

CATALOG NUMBER: S123DIP-S775D1025U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4
2.5°	973.8	973.5	976.2	974.2	976.2	973.5	973.8	976.6	977.4	977.8	977.8
5°	906.4	908.0	903.0	903.0	903.0	908.0	906.4	909.4	911.9	913.9	916.8
7.5°	846.4	844.2	844.4	841.8	844.4	844.2	846.4	848.9	852.0	856.3	860.4
10°	809.7	806.8	805.8	806.3	805.8	806.8	809.7	815.7	817.7	821.6	826.0
12.5°	779.3	778.7	772.2	772.3	772.2	778.7	779.3	780.9	785.2	793.5	798.8
15°	743.6	734.2	733.2	736.2	733.2	734.2	743.6	743.6	745.6	752.0	755.0
17.5°	707.8	702.9	703.1	701.6	703.1	702.9	707.8	708.6	710.1	715.4	719.3
20°	688.8	685.9	685.4	681.9	685.4	685.9	688.8	688.8	690.8	693.2	697.2
22.5°	671.5	670.5	670.8	666.9	670.8	670.5	671.5	672.7	674.7	676.3	679.1
25°	649.9	652.3	650.4	650.4	650.4	652.3	649.9	650.4	650.8	653.3	655.3
27.5°	635.3	635.2	634.1	634.1	634.1	635.2	635.3	634.0	633.5	632.6	632.2
30°	624.2	623.7	624.7	624.7	624.7	623.7	624.2	622.3	621.2	620.8	618.8
32.5°	613.1	613.9	614.1	614.4	614.1	613.9	613.1	610.8	609.0	607.8	606.1
35°	596.1	596.5	598.0	597.1	598.0	596.5	596.1	593.1	591.2	588.1	585.7
37.5°	573.0	575.2	574.8	575.5	574.8	575.2	573.0	572.1	570.1	567.9	565.0
40°	555.6	557.1	556.6	556.6	556.6	557.1	555.6	555.2	553.2	551.7	549.2
42.5°	537.8	538.9	537.6	536.9	537.6	538.9	537.8	537.0	535.7	533.1	530.3
45°	508.7	507.7	509.3	507.3	509.3	507.7	508.7	506.8	506.2	504.3	501.8
47.5°	476.2	477.1	477.6	479.0	477.6	477.1	476.2	476.4	473.6	472.4	471.6
50°	454.5	457.4	457.4	456.9	457.4	457.4	454.5	453.5	451.5	449.5	449.5
52.5°	433.1	434.5	436.5	436.4	436.5	434.5	433.1	431.4	429.4	426.6	425.8
55°	400.2	401.1	402.2	402.7	402.2	401.1	400.2	396.2	394.7	393.2	390.8
57.5°	366.0	365.6	368.0	368.7	368.0	365.6	366.0	362.5	360.2	355.7	355.1
60°	342.0	342.0	345.9	347.4	345.9	342.0	342.0	338.0	334.5	331.6	330.6
62.5°	316.3	317.9	321.8	319.7	321.8	317.9	316.3	312.0	309.2	305.6	302.9
65°	278.8	282.8	282.3	284.2	282.3	282.8	278.8	276.4	270.9	267.4	264.5
67.5°	239.6	242.0	245.6	245.9	245.6	242.0	239.6	235.6	232.1	228.5	224.9
70°	213.2	215.7	217.6	219.0	217.6	215.7	213.2	209.2	205.3	202.8	198.9
72.5°	187.5	188.8	193.5	191.4	193.5	188.8	187.5	182.8	179.6	177.6	173.2
75°	147.0	150.5	153.4	151.9	153.4	150.5	147.0	143.5	141.1	138.2	134.2
77.5°	108.8	112.2	113.6	112.4	113.6	112.2	108.8	106.5	105.2	99.3	99.0
80°	85.9	85.4	88.3	87.8	88.3	85.4	85.9	82.4	79.9	76.4	76.4
82.5°	63.0	62.5	63.8	64.2	63.8	62.5	63.0	61.1	57.9	56.4	55.1
85°	30.6	32.0	30.1	29.6	30.1	32.0	30.6	28.7	28.7	28.7	28.1
87.5°	12.3	12.5	12.3	11.8	12.3	12.5	12.3	12.5	13.8	12.3	12.2
90°	26.3	27.2	28.2	27.2	28.2	27.2	26.3	27.2	25.4	24.5	23.6
92.5°	48.9	46.1	47.0	45.3	47.0	46.1	48.9	50.6	55.5	62.9	79.2
95°	128.0	119.5	112.9	109.1	112.9	119.5	128.0	145.8	179.7	229.6	338.7
97.5°	373.0	330.6	305.2	297.1	305.2	330.6	373.0	442.3	554.9	676.3	844.3
100°	694.4	625.7	589.0	589.9	589.0	625.7	694.4	789.4	922.9	1033.0	1109.3
102.5°	972.0	917.7	887.0	865.3	887.0	917.7	972.0	1046.0	1130.7	1194.9	1197.3
105°	1267.2	1231.5	1201.5	1196.7	1201.5	1231.5	1267.2	1310.6	1335.0	1317.2	1223.0
107.5°	1418.4	1406.4	1396.2	1387.5	1396.2	1406.4	1418.4	1417.7	1384.1	1301.7	1149.0
110°	1462.1	1469.6	1467.7	1465.8	1467.7	1469.6	1462.1	1435.7	1369.8	1251.3	1078.2

TEST NUMBER: P331984-830

CATALOG NUMBER: S123DIP-S775D1025U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1450.8	1474.0	1481.2	1481.6	1481.2	1474.0	1450.8	1402.6	1317.9	1185.1	1008.1
115°	1390.5	1431.9	1450.8	1455.5	1450.8	1431.9	1390.5	1319.9	1217.4	1079.1	915.4
117.5°	1291.4	1338.8	1365.9	1372.2	1365.9	1338.8	1291.4	1217.8	1113.7	989.6	848.3
120°	1222.1	1274.8	1297.4	1303.1	1297.4	1274.8	1222.1	1147.8	1052.8	939.9	812.8
122.5°	1159.0	1206.4	1231.1	1238.3	1231.1	1206.4	1159.0	1092.9	1004.7	900.0	785.0
125°	1076.3	1117.7	1141.2	1147.8	1141.2	1117.7	1076.3	1016.1	940.8	850.6	748.0
127.5°	1010.6	1046.0	1067.2	1073.3	1067.2	1046.0	1010.6	957.0	888.5	807.0	715.6
130°	970.0	1003.9	1023.6	1031.1	1023.6	1003.9	970.0	920.1	856.1	780.0	695.3
132.5°	933.1	967.0	984.5	989.8	984.5	967.0	933.1	886.3	825.3	754.3	676.5
135°	878.7	906.9	923.9	930.5	923.9	906.9	878.7	832.6	779.0	717.8	651.0
137.5°	820.6	849.2	863.5	867.8	863.5	849.2	820.6	781.8	735.4	682.7	627.9
140°	783.7	810.0	825.1	824.2	825.1	810.0	783.7	748.0	707.5	662.3	614.3
142.5°	747.6	770.9	784.5	783.5	784.5	770.9	747.6	717.1	681.9	642.8	601.5
145°	698.0	717.8	725.4	727.3	725.4	717.8	698.0	674.6	647.2	617.2	586.2
147.5°	659.7	673.1	680.2	681.0	680.2	673.1	659.7	641.9	622.5	598.1	573.5
150°	637.9	648.2	653.8	653.8	653.8	648.2	637.9	623.8	605.9	586.2	564.5
152.5°	618.3	627.9	631.3	631.3	631.3	627.9	618.3	607.2	592.4	574.9	556.2
155°	592.8	600.2	602.1	603.0	602.1	600.2	592.8	584.3	573.0	558.8	543.8
157.5°	570.3	576.0	577.5	577.3	577.5	576.0	570.3	563.0	554.1	543.2	530.7
160°	556.0	561.7	561.7	560.7	561.7	561.7	556.0	549.4	542.8	533.5	523.1
162.5°	541.8	546.6	546.6	545.6	546.6	546.6	541.8	537.4	531.6	522.9	514.1
165°	523.1	526.9	525.9	525.9	525.9	526.9	523.1	519.3	514.6	508.0	502.4
167.5°	505.4	508.0	507.1	507.1	507.1	508.0	505.4	503.7	500.3	496.5	492.2
170°	494.8	496.7	495.8	495.8	495.8	496.7	494.8	493.9	492.0	488.3	485.5
172.5°	485.9	487.8	486.1	485.3	486.1	487.8	485.9	485.7	484.6	481.5	479.5
175°	474.2	475.1	474.2	473.3	474.2	475.1	474.2	474.2	474.2	472.3	471.4
177.5°	467.0	467.8	466.3	466.3	466.3	467.8	467.0	467.8	467.8	467.0	466.3
180°	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8

TEST NUMBER: P331984-830

CATALOG NUMBER: S123DIP-S775D1025U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4
2.5°	976.6	976.6	984.1	988.8	994.8	998.7	1001.5	1004.3	1009.0	1015.3	1022.4
5°	920.8	922.7	933.6	944.4	954.8	963.7	971.1	980.0	990.8	1004.2	1019.0
7.5°	866.7	874.3	885.2	898.4	912.9	925.9	939.1	953.7	968.9	988.5	1009.3
10°	832.0	840.4	853.7	870.4	885.7	901.0	917.3	933.1	952.3	975.5	1002.2
12.5°	801.5	809.5	823.2	841.6	856.1	873.0	891.6	912.2	933.8	961.7	991.9
15°	759.4	768.7	785.5	794.5	816.6	836.9	854.1	883.7	911.3	940.0	975.1
17.5°	724.8	730.1	743.7	760.2	776.7	799.5	822.1	846.8	874.3	909.3	953.1
20°	701.2	705.6	720.4	737.7	755.4	776.2	796.4	821.0	852.2	889.2	936.5
22.5°	683.4	688.2	698.0	716.3	732.9	750.2	770.3	799.7	832.8	869.0	920.4
25°	657.7	660.7	667.1	681.9	696.7	716.0	733.8	761.4	795.4	837.8	889.2
27.5°	633.4	636.2	641.6	652.2	666.0	681.6	701.0	724.4	759.0	805.1	859.6
30°	618.8	619.3	624.2	634.0	645.9	658.7	676.5	703.1	735.7	782.6	839.8
32.5°	606.1	604.3	607.7	615.1	626.6	639.4	654.0	680.2	711.6	757.7	816.5
35°	584.8	583.7	582.3	588.7	598.5	608.4	621.2	641.0	676.5	719.4	781.1
37.5°	562.9	560.5	557.9	560.8	568.5	578.8	589.9	607.6	638.1	685.4	744.4
40°	546.8	544.8	543.3	542.2	549.2	559.0	567.4	584.2	612.8	657.7	716.0
42.5°	529.0	527.8	525.9	524.5	530.3	537.7	546.5	561.4	589.9	632.1	687.2
45°	500.3	499.4	498.4	497.4	500.9	507.7	514.6	525.5	550.2	591.2	641.0
47.5°	468.4	467.2	467.6	466.0	469.4	474.0	478.8	490.5	514.2	547.2	583.6
50°	445.5	445.1	445.1	445.1	446.1	451.5	455.9	464.9	486.5	519.6	545.7
52.5°	423.9	421.8	421.8	422.5	424.3	427.8	430.6	440.4	459.3	486.4	510.2
55°	389.8	385.9	384.8	385.9	387.4	390.3	393.2	401.1	417.5	437.7	451.5
57.5°	352.1	350.0	348.6	348.8	349.7	352.0	354.3	362.9	375.7	386.3	395.1
60°	325.6	326.7	322.3	323.2	323.2	325.2	328.7	334.0	344.9	352.3	361.2
62.5°	300.8	299.4	298.1	296.7	296.7	297.6	302.2	306.4	315.7	319.5	326.5
65°	262.0	262.0	259.0	260.0	260.5	257.1	259.6	264.5	270.4	271.9	278.3
67.5°	222.7	221.4	219.7	218.2	218.2	217.9	219.1	221.7	226.1	226.6	231.5
70°	195.9	194.9	194.4	192.9	191.0	193.4	191.9	194.4	196.9	197.4	200.3
72.5°	169.8	168.8	168.0	166.5	165.7	165.4	165.5	168.3	170.0	169.4	172.7
75°	132.7	131.8	130.7	128.3	128.3	126.8	127.3	129.3	131.3	129.8	132.7
77.5°	97.5	94.4	94.3	94.9	93.2	93.6	92.9	92.7	93.6	93.7	96.3
80°	75.0	71.5	72.6	72.0	71.5	71.1	70.0	70.6	71.1	71.5	73.0
82.5°	54.1	53.8	52.8	52.7	52.2	50.9	50.3	51.2	51.7	51.5	52.5
85°	27.6	26.1	27.1	26.7	27.1	26.7	25.2	25.2	26.1	25.6	26.7
87.5°	12.8	13.0	12.1	11.9	10.9	10.7	10.0	10.0	9.8	9.4	9.9
90°	22.6	23.6	20.7	17.9	15.1	12.3	10.4	8.5	5.7	3.8	1.9
92.5°	109.1	144.7	159.2	119.5	79.0	54.4	40.4	32.5	25.3	17.3	11.7
95°	452.5	557.9	496.7	342.4	202.3	122.3	85.6	61.2	45.1	34.8	32.0
97.5°	925.0	864.6	633.0	375.8	217.7	141.3	101.6	77.5	63.6	55.5	54.6
100°	1076.3	891.0	602.1	354.7	215.5	149.6	112.9	90.3	77.2	70.6	69.7
102.5°	1083.8	842.1	556.9	336.6	218.5	159.4	125.7	105.4	92.9	87.1	85.4
105°	1026.4	756.4	501.4	323.7	226.8	176.0	146.8	128.9	117.6	112.0	109.1
107.5°	926.0	680.8	466.1	322.7	242.1	197.6	170.5	153.7	142.6	137.1	134.3
110°	862.7	637.9	452.5	326.5	255.0	212.6	186.2	170.3	159.9	155.2	152.4

TEST NUMBER: P331984-830

CATALOG NUMBER: S123DIP-S775D1025U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	807.8	609.3	445.0	334.0	267.8	228.5	202.8	186.8	176.5	171.8	169.0
115°	741.4	578.6	442.1	346.2	288.8	253.1	227.7	211.7	202.3	196.6	192.8
117.5°	701.3	560.5	443.8	362.4	311.2	275.9	252.3	234.4	225.8	221.1	216.8
120°	680.2	552.2	446.9	374.5	325.6	291.6	268.2	250.2	240.8	236.1	233.3
122.5°	662.9	547.0	452.1	385.8	340.5	307.5	282.5	265.3	255.1	250.4	247.6
125°	640.7	540.1	460.1	403.6	362.2	329.3	303.9	286.0	275.7	270.0	268.2
127.5°	621.1	536.7	469.1	418.3	381.1	349.2	323.9	304.1	293.5	286.5	283.8
130°	610.6	534.4	475.1	428.1	392.3	361.3	335.8	316.1	304.8	296.3	293.5
132.5°	600.8	533.7	479.7	437.2	402.1	371.8	347.1	327.4	313.9	304.6	301.0
135°	588.1	532.5	486.4	448.7	416.8	387.6	362.2	342.4	328.4	318.0	314.2
137.5°	576.9	530.5	490.9	457.4	427.0	398.9	375.4	355.8	340.7	330.6	326.7
140°	570.1	529.7	493.9	461.9	433.8	406.4	383.0	364.1	349.0	339.6	335.0
142.5°	564.1	528.2	496.2	466.5	439.0	412.5	390.4	371.6	358.1	347.9	343.9
145°	556.0	525.9	497.7	471.4	445.9	421.5	399.8	383.9	369.8	361.3	358.4
147.5°	548.1	522.4	497.7	474.4	451.6	429.2	410.8	395.3	383.1	374.8	373.2
150°	542.8	519.3	497.7	475.1	455.3	433.8	416.8	403.6	391.3	383.9	383.0
152.5°	536.9	515.6	495.4	476.6	457.6	439.0	422.8	411.1	400.4	392.9	392.7
155°	527.8	509.0	492.9	477.0	461.9	445.9	432.8	422.4	413.0	407.4	407.4
157.5°	517.6	503.1	489.8	478.0	464.4	451.6	441.4	432.6	424.3	419.8	419.1
160°	510.9	498.6	488.3	478.0	466.7	455.3	445.9	439.3	431.9	428.1	428.1
162.5°	504.1	494.1	485.3	477.2	467.4	457.6	449.7	443.8	437.9	434.9	434.9
165°	494.8	487.4	480.8	475.1	468.5	461.0	454.4	450.6	445.9	444.0	445.0
167.5°	486.1	480.6	476.3	473.6	468.3	462.9	458.7	456.1	452.5	451.6	452.7
170°	480.8	476.1	473.3	471.4	467.6	462.9	461.0	459.1	456.3	455.3	457.2
172.5°	475.5	472.3	471.0	470.6	467.6	463.6	462.5	461.4	459.3	459.1	460.2
175°	469.5	467.6	467.6	468.5	466.7	464.8	463.8	463.8	461.9	462.9	463.8
177.5°	465.5	464.8	465.5	467.0	465.5	464.8	464.8	464.8	464.0	464.8	465.5
180°	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8

TEST NUMBER: P331984-830

CATALOG NUMBER: S123DIP-S775D1025U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4
2.5°	1024.7	1026.7	1033.5	1038.2	1043.7	1046.9	1050.0	1052.4	1055.6	1056.3	1067.8
5°	1029.4	1039.2	1056.5	1069.3	1085.1	1102.3	1114.2	1119.6	1133.9	1145.8	1169.4
7.5°	1028.0	1049.0	1075.1	1102.1	1131.1	1158.0	1181.3	1208.9	1228.6	1258.1	1287.1
10°	1026.8	1055.0	1088.5	1123.0	1163.6	1201.0	1234.5	1272.1	1303.2	1344.2	1379.1
12.5°	1023.3	1057.3	1103.9	1144.8	1193.9	1245.7	1295.3	1343.5	1371.0	1439.3	1471.5
15°	1014.6	1055.0	1113.2	1175.4	1242.9	1304.2	1367.3	1417.7	1499.0	1558.8	1596.8
17.5°	997.8	1054.4	1123.4	1198.4	1280.6	1361.3	1432.9	1509.2	1595.5	1667.8	1744.8
20°	989.9	1052.0	1129.0	1211.9	1297.2	1388.6	1470.0	1561.7	1656.0	1727.0	1825.7
22.5°	975.2	1045.7	1128.6	1221.0	1312.2	1406.7	1501.9	1594.5	1703.4	1801.3	1895.2
25°	951.3	1030.3	1116.2	1219.3	1326.3	1421.1	1535.1	1657.9	1771.4	1897.2	1991.0
27.5°	926.2	1010.6	1096.6	1192.5	1307.7	1420.1	1563.5	1702.3	1841.2	1949.7	2019.1
30°	906.9	988.8	1077.7	1174.4	1288.4	1422.1	1582.4	1733.9	1869.2	1962.4	2001.4
32.5°	886.0	969.1	1047.6	1149.1	1270.6	1420.9	1594.3	1752.5	1870.8	1932.8	1925.2
35°	853.2	922.7	999.2	1096.9	1240.0	1412.2	1601.2	1754.2	1826.7	1813.4	1712.7
37.5°	805.8	864.3	939.6	1046.6	1204.5	1393.9	1587.4	1702.1	1697.4	1588.9	1443.1
40°	776.2	826.0	898.5	1011.1	1176.9	1382.1	1565.7	1640.2	1577.1	1425.5	1250.8
42.5°	737.5	783.3	855.9	971.6	1146.4	1358.0	1524.2	1545.9	1422.3	1247.9	1087.8
45°	677.5	717.9	793.0	912.4	1100.9	1305.6	1423.1	1370.3	1204.0	1023.9	902.0
47.5°	613.0	655.1	727.3	849.9	1034.9	1226.8	1282.7	1170.4	999.7	853.7	741.8
50°	572.4	612.8	683.4	807.3	990.3	1162.1	1185.2	1040.2	883.3	755.0	663.2
52.5°	531.3	569.4	638.8	763.1	938.2	1087.0	1072.7	924.9	780.6	671.3	599.3
55°	470.2	506.2	572.4	688.8	848.2	966.1	914.4	773.3	653.8	568.9	514.2
57.5°	415.6	450.2	507.2	612.4	750.9	832.0	766.0	647.1	552.1	486.8	446.0
60°	378.4	409.1	463.4	561.0	681.5	743.1	678.0	572.9	492.9	440.6	404.2
62.5°	343.4	369.9	420.3	509.0	613.5	665.3	599.5	510.5	442.4	396.1	365.0
65°	290.1	314.3	358.7	427.8	513.7	548.2	491.4	419.4	366.6	332.1	311.3
67.5°	241.6	262.1	300.5	354.9	418.0	443.2	400.0	344.2	304.4	276.7	260.2
70°	209.2	227.0	257.1	304.0	361.2	380.4	340.0	294.1	264.9	242.8	227.4
72.5°	182.0	195.0	222.3	258.5	306.3	321.6	293.4	253.1	225.9	209.2	197.1
75°	138.6	149.5	167.3	196.4	229.4	238.4	217.1	191.9	173.7	161.8	152.5
77.5°	100.0	107.9	120.8	138.7	161.6	169.7	156.2	139.4	126.1	118.1	112.9
80°	75.5	81.9	92.7	107.5	121.4	125.8	117.9	105.1	95.8	91.3	86.8
82.5°	55.8	59.4	65.9	76.0	85.5	90.7	84.0	76.3	71.3	67.2	65.5
85°	28.1	30.1	33.1	37.0	42.9	44.9	42.4	40.4	37.5	35.1	35.1
87.5°	11.0	11.4	13.1	14.3	16.3	18.0	18.2	18.0	18.1	17.5	17.3
90°	3.8	5.7	8.5	10.4	12.3	15.1	17.9	20.7	23.6	22.6	23.6
92.5°	17.3	25.3	32.5	40.4	54.4	79.0	119.5	159.2	144.7	109.1	79.2
95°	34.8	45.1	61.2	85.6	122.3	202.3	342.4	496.7	557.9	452.5	338.7
97.5°	55.5	63.6	77.5	101.6	141.3	217.7	375.8	633.0	864.6	925.0	844.3
100°	70.6	77.2	90.3	112.9	149.6	215.5	354.7	602.1	891.0	1076.3	1109.3
102.5°	87.1	92.9	105.4	125.7	159.4	218.5	336.6	556.9	842.1	1083.8	1197.3
105°	112.0	117.6	128.9	146.8	176.0	226.8	323.7	501.4	756.4	1026.4	1223.0
107.5°	137.1	142.6	153.7	170.5	197.6	242.1	322.7	466.1	680.8	926.0	1149.0
110°	155.2	159.9	170.3	186.2	212.6	255.0	326.5	452.5	637.9	862.7	1078.2

TEST NUMBER: P331984-830

CATALOG NUMBER: S123DIP-S775D1025U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	171.8	176.5	186.8	202.8	228.5	267.8	334.0	445.0	609.3	807.8	1008.1
115°	196.6	202.3	211.7	227.7	253.1	288.8	346.2	442.1	578.6	741.4	915.4
117.5°	221.1	225.8	234.4	252.3	275.9	311.2	362.4	443.8	560.5	701.3	848.3
120°	236.1	240.8	250.2	268.2	291.6	325.6	374.5	446.9	552.2	680.2	812.8
122.5°	250.4	255.1	265.3	282.5	307.5	340.5	385.8	452.1	547.0	662.9	785.0
125°	270.0	275.7	286.0	303.9	329.3	362.2	403.6	460.1	540.1	640.7	748.0
127.5°	286.5	293.5	304.1	323.9	349.2	381.1	418.3	469.1	536.7	621.1	715.6
130°	296.3	304.8	316.1	335.8	361.3	392.3	428.1	475.1	534.4	610.6	695.3
132.5°	304.6	313.9	327.4	347.1	371.8	402.1	437.2	479.7	533.7	600.8	676.5
135°	318.0	328.4	342.4	362.2	387.6	416.8	448.7	486.4	532.5	588.1	651.0
137.5°	330.6	340.7	355.8	375.4	398.9	427.0	457.4	490.9	530.5	576.9	627.9
140°	339.6	349.0	364.1	383.0	406.4	433.8	461.9	493.9	529.7	570.1	614.3
142.5°	347.9	358.1	371.6	390.4	412.5	439.0	466.5	496.2	528.2	564.1	601.5
145°	361.3	369.8	383.9	399.8	421.5	445.9	471.4	497.7	525.9	556.0	586.2
147.5°	374.8	383.1	395.3	410.8	429.2	451.6	474.4	497.7	522.4	548.1	573.5
150°	383.9	391.3	403.6	416.8	433.8	455.3	475.1	497.7	519.3	542.8	564.5
152.5°	392.9	400.4	411.1	422.8	439.0	457.6	476.6	495.4	515.6	536.9	556.2
155°	407.4	413.0	422.4	432.8	445.9	461.9	477.0	492.9	509.0	527.8	543.8
157.5°	419.8	424.3	432.6	441.4	451.6	464.4	478.0	489.8	503.1	517.6	530.7
160°	428.1	431.9	439.3	445.9	455.3	466.7	478.0	488.3	498.6	510.9	523.1
162.5°	434.9	437.9	443.8	449.7	457.6	467.4	477.2	485.3	494.1	504.1	514.1
165°	444.0	445.9	450.6	454.4	461.0	468.5	475.1	480.8	487.4	494.8	502.4
167.5°	451.6	452.5	456.1	458.7	462.9	468.3	473.6	476.3	480.6	486.1	492.2
170°	455.3	456.3	459.1	461.0	462.9	467.6	471.4	473.3	476.1	480.8	485.5
172.5°	459.1	459.3	461.4	462.5	463.6	467.6	470.6	471.0	472.3	475.5	479.5
175°	462.9	461.9	463.8	463.8	464.8	466.7	468.5	467.6	467.6	469.5	471.4
177.5°	464.8	464.0	464.8	464.8	464.8	465.5	467.0	465.5	464.8	465.5	466.3
180°	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8

TEST NUMBER: P331984-830

CATALOG NUMBER: S123DIP-S775D1025U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4
2.5°	1071.8	1072.1	1076.5	1079.7	1078.1	1080.1	1080.8
5°	1170.9	1188.7	1198.1	1204.9	1205.5	1206.0	1209.9
7.5°	1311.5	1330.6	1344.5	1365.6	1372.0	1379.1	1377.1
10°	1414.2	1442.3	1466.5	1479.3	1493.2	1513.3	1497.1
12.5°	1510.1	1560.0	1596.8	1616.7	1629.8	1633.8	1625.8
15°	1668.3	1733.4	1768.5	1767.5	1811.9	1831.2	1801.0
17.5°	1813.4	1873.5	1921.7	1946.4	1983.3	1991.5	1987.7
20°	1902.2	1967.8	2005.4	2047.8	2067.0	2084.2	2087.3
22.5°	1978.8	2037.7	2077.9	2113.3	2129.4	2137.6	2142.5
25°	2057.7	2104.0	2128.2	2140.5	2144.9	2144.0	2137.6
27.5°	2052.2	2055.8	2029.1	2003.0	1979.6	1953.2	1944.2
30°	1998.9	1957.5	1883.5	1841.5	1779.8	1731.0	1750.7
32.5°	1858.8	1776.3	1693.2	1601.5	1525.6	1504.0	1482.2
35°	1586.4	1441.3	1356.5	1257.7	1218.3	1178.8	1151.7
37.5°	1283.5	1171.2	1070.5	1006.0	966.5	941.5	928.0
40°	1109.7	1008.6	925.7	873.4	843.3	815.2	811.2
42.5°	971.2	877.1	814.7	773.1	744.2	732.3	723.6
45°	795.4	729.8	687.9	658.3	639.0	631.6	621.7
47.5°	673.3	626.9	595.4	575.2	560.7	555.3	554.4
50°	604.9	566.5	543.3	527.4	516.1	514.2	506.2
52.5°	553.6	520.3	502.2	488.4	480.2	474.7	472.3
55°	480.6	458.4	442.1	434.2	427.8	422.4	422.4
57.5°	420.5	402.0	391.2	384.5	382.5	378.6	376.2
60°	383.4	367.6	359.2	353.3	349.4	349.9	345.4
62.5°	347.0	336.9	328.9	322.9	318.2	318.3	318.6
65°	295.6	287.7	281.7	279.7	276.8	273.3	274.4
67.5°	250.4	243.1	238.5	235.1	234.1	232.2	235.1
70°	218.1	212.6	209.2	206.2	205.3	205.8	208.2
72.5°	188.5	184.6	182.4	181.0	178.8	178.9	180.6
75°	148.1	145.1	143.1	141.6	141.1	141.1	141.1
77.5°	108.8	108.1	107.2	105.0	105.1	105.7	105.8
80°	85.9	84.4	83.9	82.9	81.4	80.4	82.9
82.5°	64.2	62.7	62.2	62.0	59.7	59.5	61.5
85°	34.5	33.1	33.6	33.1	33.1	32.6	32.6
87.5°	17.2	17.0	16.9	17.2	16.9	16.7	17.3
90°	24.5	25.4	27.2	26.3	27.2	28.2	27.2
92.5°	62.9	55.5	50.6	48.9	46.1	47.0	45.3
95°	229.6	179.7	145.8	128.0	119.5	112.9	109.1
97.5°	676.3	554.9	442.3	373.0	330.6	305.2	297.1
100°	1033.0	922.9	789.4	694.4	625.7	589.0	589.9
102.5°	1194.9	1130.7	1046.0	972.0	917.7	887.0	865.3
105°	1317.2	1335.0	1310.6	1267.2	1231.5	1201.5	1196.7
107.5°	1301.7	1384.1	1417.7	1418.4	1406.4	1396.2	1387.5
110°	1251.3	1369.8	1435.7	1462.1	1469.6	1467.7	1465.8

TEST NUMBER: P331984-830

CATALOG NUMBER: S123DIP-S775D1025U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1185.1	1317.9	1402.6	1450.8	1474.0	1481.2	1481.6
115°	1079.1	1217.4	1319.9	1390.5	1431.9	1450.8	1455.5
117.5°	989.6	1113.7	1217.8	1291.4	1338.8	1365.9	1372.2
120°	939.9	1052.8	1147.8	1222.1	1274.8	1297.4	1303.1
122.5°	900.0	1004.7	1092.9	1159.0	1206.4	1231.1	1238.3
125°	850.6	940.8	1016.1	1076.3	1117.7	1141.2	1147.8
127.5°	807.0	888.5	957.0	1010.6	1046.0	1067.2	1073.3
130°	780.0	856.1	920.1	970.0	1003.9	1023.6	1031.1
132.5°	754.3	825.3	886.3	933.1	967.0	984.5	989.8
135°	717.8	779.0	832.6	878.7	906.9	923.9	930.5
137.5°	682.7	735.4	781.8	820.6	849.2	863.5	867.8
140°	662.3	707.5	748.0	783.7	810.0	825.1	824.2
142.5°	642.8	681.9	717.1	747.6	770.9	784.5	783.5
145°	617.2	647.2	674.6	698.0	717.8	725.4	727.3
147.5°	598.1	622.5	641.9	659.7	673.1	680.2	681.0
150°	586.2	605.9	623.8	637.9	648.2	653.8	653.8
152.5°	574.9	592.4	607.2	618.3	627.9	631.3	631.3
155°	558.8	573.0	584.3	592.8	600.2	602.1	603.0
157.5°	543.2	554.1	563.0	570.3	576.0	577.5	577.3
160°	533.5	542.8	549.4	556.0	561.7	561.7	560.7
162.5°	522.9	531.6	537.4	541.8	546.6	546.6	545.6
165°	508.0	514.6	519.3	523.1	526.9	525.9	525.9
167.5°	496.5	500.3	503.7	505.4	508.0	507.1	507.1
170°	488.3	492.0	493.9	494.8	496.7	495.8	495.8
172.5°	481.5	484.6	485.7	485.9	487.8	486.1	485.3
175°	472.3	474.2	474.2	474.2	475.1	474.2	473.3
177.5°	467.0	467.8	467.8	467.0	467.8	466.3	466.3
180°	464.8	464.8	464.8	464.8	464.8	464.8	464.8

(END OF REPORT)