

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332246-830

Luminaire Tested: **S123RDIP-S340D585U830-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332246-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S340D585U830-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 585 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3485.8 lumens
Efficiency: N/A
Efficacy: 136.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 25.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332246-830

CATALOG NUMBER: S123RDIP-S340D585U830-4F0-1E-UDD-A

Luminous Intensity Polar Plot



CATALOG NUMBER: S123RDIP-S340D585U830-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	37			
1	95	91	87	84	86	83	80	77	67	65	63	53	51	50	39	39	38	32			
2	87	80	74	69	79	73	68	64	59	56	53	47	44	42	35	34	33	27			
3	80	71	64	58	72	64	59	54	53	48	45	42	39	36	32	30	28	24			
4	73	63	55	50	66	57	51	46	47	42	39	37	34	31	28	26	25	21			
5	67	56	48	43	61	51	45	40	42	37	33	34	30	27	26	24	22	18			
6	62	50	43	37	56	46	39	34	38	33	29	31	27	24	24	21	19	16			
7	57	45	38	33	52	42	35	30	35	30	26	28	24	21	22	19	17	14			
8	53	41	34	29	48	38	31	27	32	27	23	26	22	19	20	17	15	13			
9	49	38	30	26	45	35	28	24	29	24	21	23	20	17	18	16	14	12			
10	46	34	28	23	42	32	26	21	27	22	19	22	18	16	17	15	13	11			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5521	5521	5521	5521
5°	6582	5545	4883	5545
10°	8218	5513	4411	5513
15°	9646	5457	4023	5457
20°	10766	5372	3692	5372
25°	10594	5284	3489	5284
30°	7615	5203	3280	5203
35°	5084	5096	3144	5096
40°	3746	4967	3006	4967
45°	3142	4743	2868	4743
50°	2773	4449	2678	4449
55°	2432	4112	2415	4112
60°	2166	3791	2211	3791
65°	1900	3446	2058	3446
70°	1492	3138	1882	3138
75°	1314	2741	1718	2741
80°	1147	2325	1686	2325
85°	914	1877	1791	1877

TEST NUMBER: P332246-830

CATALOG NUMBER: S123RDIP-S340D585U830-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.4	1.4
10°-20°	157.6	4.5
20°-30°	247.6	7.1
30°-40°	258.3	7.4
40°-50°	221.1	6.3
50°-60°	168.5	4.8
60°-70°	108.0	3.1
70°-80°	52.0	1.5
80°-90°	15.8	0.5
90°-100°	26.3	0.8
100°-110°	125.4	3.6
110°-120°	301.2	8.6
120°-130°	383.5	11.0
130°-140°	409.8	11.8
140°-150°	383.2	11.0
150°-160°	309.1	8.9
160°-170°	199.5	5.7
170°-180°	68.7	2.0
0°-30°	455.6	13.1
0°-40°	714.0	20.5
0°-60°	1103.5	31.7
0°-90°	1279.2	36.7
90°-120°	452.8	13.0
90°-150°	1629.3	46.7
90°-180°	2207.0	63.3
0°-180°	3485.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	513	513	513	513	513	
5°	609	513	452	513	609	63
15°	866	490	361	490	866	245
25°	892	445	294	445	892	383
35°	387	388	239	388	387	254
45°	206	312	188	312	206	162
55°	130	219	129	219	130	117
65°	75	135	81	135	75	73
75°	32	66	41	66	32	34
85°	7	15	14	15	7	9
90°	16	1	16	1	16	8
95°	20	33	20	33	20	17
105°	24	160	24	160	24	54
115°	316	300	316	300	316	292
125°	432	424	432	424	432	386
135°	533	527	533	527	533	411
145°	614	608	614	608	614	384
155°	669	670	669	670	669	309
165°	705	707	705	707	705	199
175°	721	724	721	724	721	69
180°	724	724	724	724	724	

TEST NUMBER: P332246-830

CATALOG NUMBER: S123RDIP-S340D585U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9
2.5°	546.4	547.1	544.8	544.4	541.8	541.1	541.1	537.3	535.1	532.2	530.4
5°	609.2	612.7	610.9	607.0	600.4	598.8	594.7	588.1	580.6	571.4	567.0
7.5°	687.6	692.4	690.5	684.5	677.5	671.9	660.2	649.2	634.0	620.5	609.0
10°	751.9	746.9	742.9	737.0	730.6	720.3	707.9	691.1	671.6	656.1	639.0
12.5°	800.0	799.2	794.2	788.1	779.1	769.3	754.1	733.6	710.9	688.6	669.0
15°	865.6	867.0	863.7	857.3	844.5	827.2	804.4	795.8	763.3	739.1	715.0
17.5°	911.1	910.8	910.3	901.5	888.5	876.2	855.0	832.5	803.0	769.0	736.5
20°	939.9	937.6	938.1	928.2	918.6	904.3	883.6	850.9	826.8	787.5	753.8
22.5°	939.1	938.7	940.4	937.0	930.0	919.1	902.8	875.2	844.3	804.6	766.9
25°	892.0	890.2	900.5	903.4	914.6	916.6	911.7	896.6	867.4	826.5	779.8
27.5°	746.5	745.6	764.7	788.7	819.1	842.7	865.5	876.6	867.4	838.1	791.3
30°	612.7	633.3	643.0	677.7	716.3	762.4	802.9	841.2	850.7	837.9	799.6
32.5°	508.7	526.7	534.8	564.5	600.6	654.6	715.2	769.6	808.0	817.7	794.7
35°	386.9	387.1	405.6	418.8	452.1	507.7	566.6	639.4	711.9	766.9	772.5
37.5°	308.8	309.8	321.0	334.1	359.2	388.5	440.4	501.0	584.7	668.9	718.4
40°	266.6	268.5	276.9	289.8	307.8	330.1	370.4	427.5	497.4	591.2	667.8
42.5°	239.5	242.7	247.0	257.0	268.2	289.0	321.6	365.7	429.2	517.9	606.3
45°	206.4	208.2	211.5	216.1	226.2	240.6	262.6	292.3	345.0	416.3	504.8
47.5°	182.1	181.2	184.6	188.3	195.1	205.0	219.7	243.8	281.4	338.7	413.8
50°	165.6	165.3	167.8	170.6	177.0	184.3	196.3	214.5	244.4	291.8	360.6
52.5°	150.1	150.9	152.7	156.2	160.8	166.6	177.5	190.7	216.3	257.2	314.5
55°	129.6	130.3	132.6	134.6	137.9	143.8	150.6	161.6	179.2	207.7	255.0
57.5°	112.2	111.9	114.1	114.7	118.4	123.2	128.5	137.0	149.8	171.0	202.7
60°	100.6	99.9	101.9	103.4	105.4	109.3	113.8	122.1	132.2	147.8	175.0
62.5°	90.0	89.7	91.1	92.7	94.3	97.9	101.6	108.0	116.0	129.1	150.8
65°	74.6	75.3	76.0	76.6	77.5	79.7	83.2	87.7	93.1	102.4	117.9
67.5°	58.7	59.4	59.6	60.9	62.8	64.2	66.4	70.2	74.1	81.8	90.7
70°	47.4	47.2	47.4	48.1	50.5	52.9	55.8	58.6	61.1	66.5	74.0
72.5°	40.7	40.3	40.9	41.1	42.2	42.9	44.7	47.4	50.5	54.2	59.6
75°	31.6	31.6	31.6	31.6	32.5	32.9	33.6	34.2	35.3	37.1	41.1
77.5°	23.4	23.4	23.8	23.9	24.1	24.4	24.8	25.4	25.8	26.8	28.5
80°	18.5	18.7	18.5	18.7	18.7	19.1	19.3	20.0	20.2	21.3	22.0
82.5°	13.9	13.8	13.9	14.1	14.1	14.5	14.6	15.1	15.1	15.6	16.3
85°	7.4	7.1	7.4	7.3	7.7	7.3	7.4	7.9	7.9	8.1	9.0
87.5°	5.0	5.3	4.9	5.0	5.0	5.1	5.0	4.9	5.1	4.9	4.7
90°	16.1	15.9	15.6	15.5	15.2	14.8	14.3	13.9	13.4	12.9	11.3
92.5°	17.8	17.7	17.5	17.4	17.2	16.8	16.0	15.3	14.5	13.8	12.6
95°	20.5	20.5	20.5	20.5	20.5	20.0	19.1	18.4	17.5	16.7	15.4
97.5°	22.1	22.1	21.9	21.8	21.7	21.1	20.2	19.2	18.3	17.3	25.9
100°	22.6	22.4	22.3	22.2	22.1	21.6	20.6	19.6	18.7	17.7	36.4
102.5°	23.0	22.8	22.6	22.3	22.1	23.6	26.5	29.4	32.4	35.3	55.7
105°	23.7	23.4	23.2	22.9	22.7	33.2	54.3	75.4	96.6	117.7	128.5
107.5°	74.3	90.2	106.1	122.1	138.1	153.7	169.3	184.7	200.3	215.7	214.1
110°	147.8	164.9	182.0	199.1	216.1	226.7	230.6	234.6	238.5	242.4	241.1

TEST NUMBER: P332246-830

CATALOG NUMBER: S123RDIP-S340D585U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	253.6	257.2	260.8	264.5	268.1	269.8	269.8	269.7	269.7	269.6	268.2
115°	316.1	315.7	315.2	314.6	314.1	313.4	312.2	310.9	309.8	308.6	307.5
117.5°	351.2	351.1	351.0	350.9	350.8	350.2	349.3	348.4	347.4	346.4	345.9
120°	375.2	375.2	375.2	375.2	375.2	374.8	373.8	372.9	371.9	370.9	370.6
122.5°	398.9	398.8	398.7	398.6	398.5	398.1	397.5	396.8	396.2	395.5	395.0
125°	432.3	432.0	431.8	431.5	431.3	431.0	430.7	430.6	430.3	430.1	429.6
127.5°	464.3	464.5	464.8	465.0	465.2	465.1	464.8	464.4	464.0	463.6	463.1
130°	484.9	485.1	485.4	485.6	485.9	485.7	485.2	484.7	484.3	483.8	483.3
132.5°	503.8	504.2	504.4	504.8	505.2	505.1	504.6	504.2	503.7	503.2	502.8
135°	532.7	533.1	533.5	533.9	534.1	534.1	533.9	533.5	533.1	532.7	532.3
137.5°	560.0	560.2	560.4	560.6	560.9	560.7	560.2	559.6	559.0	558.5	558.2
140°	576.3	576.6	576.7	577.0	577.2	577.1	576.6	576.2	575.7	575.2	574.9
142.5°	591.4	591.6	592.0	592.4	592.7	592.7	592.3	591.9	591.5	591.2	590.8
145°	614.4	614.4	614.4	614.4	614.4	614.3	614.1	613.9	613.6	613.4	613.1
147.5°	631.7	632.3	632.7	633.3	633.9	634.0	633.8	633.6	633.3	633.1	632.8
150°	644.6	644.9	645.3	645.6	646.0	646.0	645.8	645.5	645.4	645.1	644.9
152.5°	654.9	655.4	656.0	656.6	657.0	657.1	656.7	656.3	655.8	655.4	655.3
155°	669.3	670.1	670.7	671.5	672.1	672.2	671.7	671.0	670.4	669.9	669.7
157.5°	681.5	682.4	683.3	684.2	685.1	685.3	684.6	683.8	683.2	682.4	682.5
160°	689.2	690.0	690.9	691.7	692.5	692.6	691.8	691.2	690.4	689.8	689.8
162.5°	696.5	697.2	698.0	698.7	699.5	699.5	698.6	697.8	697.0	696.2	696.3
165°	705.3	706.2	707.0	707.8	708.7	708.6	707.7	706.7	705.8	704.7	704.9
167.5°	711.6	712.7	713.6	714.5	715.5	715.5	714.5	713.6	712.7	711.6	711.6
170°	715.5	716.5	717.5	718.4	719.3	719.3	718.4	717.5	716.5	715.5	715.5
172.5°	717.7	718.7	719.8	720.9	721.9	721.9	721.0	720.0	719.1	718.1	718.0
175°	720.9	721.9	722.8	723.8	724.7	724.8	724.0	723.1	722.3	721.4	721.3
177.5°	721.9	722.8	723.8	724.7	725.7	725.8	725.0	724.2	723.5	722.7	722.6
180°	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6

TEST NUMBER: P332246-830

CATALOG NUMBER: S123RDIP-S340D585U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9
2.5°	529.6	529.1	526.7	523.9	520.2	517.7	515.8	514.7	511.5	507.7	505.1
5°	562.4	555.8	548.7	540.2	532.3	524.1	519.2	513.2	506.0	497.9	492.1
7.5°	597.4	584.5	570.6	556.2	542.1	529.3	518.0	508.4	496.9	485.2	477.1
10°	624.3	605.4	585.9	565.9	547.7	530.6	517.4	504.4	490.6	477.2	467.0
12.5°	648.8	623.9	601.3	576.7	553.5	533.0	514.1	498.8	482.1	467.9	456.4
15°	679.7	654.1	627.0	589.6	558.6	532.7	509.6	489.7	469.5	451.9	440.7
17.5°	708.5	670.2	633.6	602.5	562.2	529.9	501.7	477.9	455.6	437.1	423.2
20°	720.5	683.3	643.7	603.9	564.4	528.1	495.4	469.0	446.0	424.9	412.2
22.5°	727.6	685.7	643.8	601.1	559.1	521.4	489.1	460.1	435.1	415.1	399.4
25°	736.0	686.0	639.9	597.8	554.9	514.1	475.6	444.9	417.9	396.6	379.9
27.5°	741.6	682.7	628.2	581.4	537.9	497.3	462.0	429.4	402.0	379.5	361.6
30°	742.6	680.0	619.3	568.5	524.4	487.0	449.7	418.6	389.6	365.6	348.9
32.5°	744.0	673.5	607.1	553.3	508.0	471.1	437.2	407.5	377.8	354.2	337.1
35°	738.3	670.0	588.7	526.8	481.5	445.7	415.3	387.8	358.6	335.7	318.4
37.5°	713.3	655.7	569.7	497.0	449.7	416.6	391.7	367.8	341.0	316.3	300.0
40°	688.2	641.7	554.9	478.9	429.5	395.5	373.1	353.5	327.6	304.5	287.0
42.5°	650.8	622.5	540.8	460.0	406.7	373.9	355.0	336.7	314.0	290.5	274.0
45°	582.1	585.9	512.1	429.7	375.0	342.1	324.3	311.6	291.4	272.1	255.1
47.5°	496.1	530.9	478.3	397.6	341.8	310.9	295.3	284.2	270.5	251.6	236.1
50°	439.9	489.7	451.3	376.0	320.8	290.1	274.8	265.7	253.8	238.9	224.2
52.5°	388.0	441.6	418.6	351.9	298.1	270.0	255.1	247.6	238.2	224.1	210.8
55°	316.4	370.7	365.4	315.6	264.2	238.9	227.5	219.1	212.8	202.3	191.7
57.5°	256.0	307.4	310.1	275.1	234.2	209.2	199.4	193.1	189.0	181.1	171.3
60°	217.8	265.0	274.3	247.9	212.8	190.9	181.2	176.1	172.9	166.5	159.0
62.5°	186.2	226.4	236.9	217.9	192.3	171.6	164.1	159.3	157.0	151.6	145.0
65°	142.5	175.9	186.0	175.5	162.0	145.6	139.4	135.3	133.3	130.3	125.4
67.5°	107.2	131.5	142.6	135.2	130.3	119.9	116.0	113.8	112.0	109.9	105.8
70°	86.1	104.1	115.5	113.6	109.6	104.1	101.2	99.7	97.9	96.1	92.7
72.5°	69.2	81.6	92.3	93.3	90.1	89.0	86.4	85.8	84.7	82.7	80.7
75°	45.9	54.5	61.9	64.8	66.1	67.2	66.1	65.9	65.7	63.9	62.8
77.5°	30.1	34.7	39.4	44.3	46.4	47.8	48.2	49.0	48.4	47.5	46.9
80°	23.1	24.1	27.4	31.6	34.9	36.2	37.1	37.5	37.3	37.1	36.2
82.5°	16.8	17.6	19.2	22.1	24.9	27.1	27.6	27.5	28.0	28.2	27.4
85°	9.0	9.2	9.7	10.1	11.6	14.0	14.7	15.2	15.6	15.6	14.2
87.5°	4.8	4.2	4.3	4.1	4.3	4.2	5.1	5.7	6.1	5.7	5.9
90°	9.8	8.2	6.7	5.3	4.1	2.9	1.7	0.6	1.7	2.9	4.1
92.5°	11.4	10.3	9.0	8.7	9.0	9.3	9.7	10.0	9.7	9.3	9.0
95°	14.0	12.7	11.4	13.2	18.1	23.0	27.9	32.8	27.9	23.0	18.1
97.5°	34.5	43.1	51.7	57.1	59.3	61.5	63.7	65.9	63.7	61.5	59.3
100°	55.0	73.6	92.3	100.4	98.0	95.7	93.2	90.9	93.2	95.7	98.0
102.5°	76.1	96.4	116.8	126.1	124.4	122.7	120.9	119.2	120.9	122.7	124.4
105°	139.2	150.0	160.7	165.4	164.1	162.9	161.6	160.2	161.6	162.9	164.1
107.5°	212.4	210.7	209.0	207.6	206.6	205.6	204.4	203.4	204.4	205.6	206.6
110°	239.8	238.5	237.2	236.0	235.1	234.1	233.2	232.2	233.2	234.1	235.1

TEST NUMBER: P332246-830

CATALOG NUMBER: S123RDIP-S340D585U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	266.9	265.6	264.3	263.2	262.3	261.5	260.6	259.8	260.6	261.5	262.3
115°	306.4	305.4	304.3	303.4	302.7	301.9	301.2	300.5	301.2	301.9	302.7
117.5°	345.3	344.8	344.2	343.5	342.6	341.8	340.8	340.0	340.8	341.8	342.6
120°	370.2	369.9	369.5	368.8	367.7	366.6	365.5	364.5	365.5	366.6	367.7
122.5°	394.5	394.1	393.6	392.9	392.1	391.2	390.3	389.5	390.3	391.2	392.1
125°	429.1	428.7	428.2	427.4	426.5	425.6	424.6	423.6	424.6	425.6	426.5
127.5°	462.5	461.8	461.3	460.5	459.6	458.6	457.7	456.8	457.7	458.6	459.6
130°	482.9	482.4	481.9	481.2	480.2	479.3	478.3	477.4	478.3	479.3	480.2
132.5°	502.4	502.0	501.6	501.0	500.0	499.1	498.1	497.2	498.1	499.1	500.0
135°	531.8	531.3	530.8	530.3	529.5	528.8	528.1	527.4	528.1	528.8	529.5
137.5°	557.9	557.6	557.4	556.8	555.9	555.0	554.1	553.2	554.1	555.0	555.9
140°	574.5	574.1	573.8	573.3	572.5	571.8	571.1	570.3	571.1	571.8	572.5
142.5°	590.4	590.0	589.7	589.2	588.4	587.8	587.0	586.3	587.0	587.8	588.4
145°	612.9	612.7	612.5	611.9	611.1	610.2	609.4	608.5	609.4	610.2	611.1
147.5°	632.5	632.4	632.1	631.7	631.1	630.7	630.1	629.5	630.1	630.7	631.1
150°	644.6	644.4	644.1	643.9	643.5	643.1	642.8	642.4	642.8	643.1	643.5
152.5°	655.2	655.0	654.9	654.7	654.5	654.3	654.2	654.0	654.2	654.3	654.5
155°	669.6	669.5	669.4	669.4	669.7	669.9	670.1	670.3	670.1	669.9	669.7
157.5°	682.7	682.8	682.9	683.0	683.0	683.0	683.1	683.1	683.1	683.0	683.0
160°	689.9	690.0	690.2	690.3	690.4	690.6	690.7	690.8	690.7	690.6	690.4
162.5°	696.4	696.5	696.6	696.8	697.2	697.5	697.8	698.1	697.8	697.5	697.2
165°	705.0	705.1	705.2	705.5	705.9	706.2	706.5	706.9	706.5	706.2	705.9
167.5°	711.6	711.6	711.6	711.9	712.4	712.8	713.3	713.8	713.3	712.8	712.4
170°	715.5	715.5	715.5	715.8	716.2	716.7	717.2	717.7	717.2	716.7	716.2
172.5°	717.9	717.8	717.7	717.9	718.5	719.1	719.7	720.3	719.7	719.1	718.5
175°	721.2	721.0	721.0	721.2	721.8	722.4	723.0	723.6	723.0	722.4	721.8
177.5°	722.6	722.5	722.4	722.6	723.0	723.5	724.0	724.4	724.0	723.5	723.0
180°	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6

TEST NUMBER: P332246-830

CATALOG NUMBER: S123RDIP-S340D585U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9
2.5°	504.2	501.9	500.3	496.8	494.6	492.1	489.7	491.2	491.0	490.9	490.9
5°	487.3	482.2	477.6	471.6	468.0	463.4	459.9	459.4	460.2	457.2	455.4
7.5°	470.5	463.6	457.0	450.5	443.6	438.0	434.6	432.9	430.7	428.9	426.9
10°	458.7	450.6	444.2	436.1	428.7	422.1	417.9	415.0	413.5	412.0	409.1
12.5°	446.6	438.7	430.6	421.3	414.2	406.6	403.5	400.3	397.4	395.6	391.7
15°	428.9	418.6	410.0	400.3	392.4	384.9	380.6	374.2	373.3	371.1	367.1
17.5°	411.0	399.9	388.0	380.9	372.0	364.2	357.5	355.4	349.1	346.8	343.3
20°	397.0	386.7	377.7	368.3	355.3	348.1	342.8	340.0	334.9	331.8	329.6
22.5°	384.9	374.4	364.0	353.0	342.3	334.1	330.3	325.8	323.1	318.8	316.4
25°	367.6	356.2	343.7	331.8	324.1	318.0	311.8	307.8	303.9	301.9	297.6
27.5°	347.5	335.5	323.9	314.8	305.4	299.4	293.8	290.3	285.5	282.2	279.7
30°	336.4	322.3	312.3	304.2	292.1	286.3	282.2	277.8	274.3	270.8	268.3
32.5°	323.6	310.8	301.2	291.2	281.9	275.6	270.2	266.4	263.3	260.0	257.6
35°	303.5	292.8	282.9	272.8	265.9	259.6	253.2	249.9	247.0	243.9	241.8
37.5°	285.3	275.2	265.8	256.3	247.8	242.6	237.5	235.0	231.1	229.0	226.9
40°	274.1	264.2	254.1	244.9	236.1	232.1	227.5	223.8	220.3	218.7	216.3
42.5°	261.7	251.8	243.4	233.5	226.2	220.8	216.6	212.5	209.9	207.6	206.3
45°	243.6	234.8	226.4	216.5	209.7	205.1	200.3	196.5	194.2	192.6	190.2
47.5°	225.8	217.1	208.6	200.0	193.4	188.1	183.2	180.7	177.5	175.6	174.0
50°	213.0	205.1	196.1	188.2	181.6	176.3	172.4	169.1	166.3	163.8	162.7
52.5°	201.2	192.8	185.0	177.7	170.7	164.8	161.2	157.7	155.5	152.8	151.5
55°	181.8	173.7	167.1	159.9	153.1	148.0	143.6	140.5	138.4	135.3	133.6
57.5°	163.6	156.3	148.5	142.1	135.2	130.9	127.2	123.1	120.4	118.0	116.2
60°	151.3	143.0	136.1	130.3	124.0	118.6	115.3	112.0	109.1	106.7	105.2
62.5°	138.5	131.2	124.7	118.3	112.6	107.8	104.1	101.3	98.8	97.3	95.7
65°	118.8	113.1	106.5	101.2	96.0	92.5	89.4	87.0	85.2	84.1	82.8
67.5°	100.7	95.2	89.4	84.3	80.7	78.0	76.1	74.0	73.0	71.6	70.8
70°	89.0	83.2	78.1	74.2	70.7	68.7	67.4	65.9	65.0	63.2	62.4
72.5°	76.2	72.0	68.3	65.1	62.3	60.5	58.8	56.9	55.5	53.5	52.7
75°	59.9	56.2	53.3	51.2	49.4	47.0	44.6	42.6	41.9	41.3	41.1
77.5°	44.4	42.0	40.0	38.1	35.9	34.2	33.6	33.2	33.1	32.7	32.7
80°	34.9	32.7	31.2	29.0	27.7	27.7	27.7	27.2	27.4	27.4	27.4
82.5°	25.9	23.9	23.1	22.3	22.1	22.2	22.2	22.3	22.1	22.5	22.3
85°	13.4	13.6	14.0	13.9	14.0	14.0	14.5	14.2	14.5	14.0	14.5
87.5°	5.9	6.8	7.3	7.7	8.2	8.4	8.7	8.8	9.0	9.1	9.1
90°	5.3	6.7	8.2	9.8	11.3	12.9	13.4	13.9	14.3	14.8	15.2
92.5°	8.7	9.0	10.3	11.4	12.6	13.8	14.5	15.3	16.0	16.8	17.2
95°	13.2	11.4	12.7	14.0	15.4	16.7	17.5	18.4	19.1	20.0	20.5
97.5°	57.1	51.7	43.1	34.5	25.9	17.3	18.3	19.2	20.2	21.1	21.7
100°	100.4	92.3	73.6	55.0	36.4	17.7	18.7	19.6	20.6	21.6	22.1
102.5°	126.1	116.8	96.4	76.1	55.7	35.3	32.4	29.4	26.5	23.6	22.1
105°	165.4	160.7	150.0	139.2	128.5	117.7	96.6	75.4	54.3	33.2	22.7
107.5°	207.6	209.0	210.7	212.4	214.1	215.7	200.3	184.7	169.3	153.7	138.1
110°	236.0	237.2	238.5	239.8	241.1	242.4	238.5	234.6	230.6	226.7	216.1

TEST NUMBER: P332246-830

CATALOG NUMBER: S123RDIP-S340D585U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	263.2	264.3	265.6	266.9	268.2	269.6	269.7	269.7	269.8	269.8	268.1
115°	303.4	304.3	305.4	306.4	307.5	308.6	309.8	310.9	312.2	313.4	314.1
117.5°	343.5	344.2	344.8	345.3	345.9	346.4	347.4	348.4	349.3	350.2	350.8
120°	368.8	369.5	369.9	370.2	370.6	370.9	371.9	372.9	373.8	374.8	375.2
122.5°	392.9	393.6	394.1	394.5	395.0	395.5	396.2	396.8	397.5	398.1	398.5
125°	427.4	428.2	428.7	429.1	429.6	430.1	430.3	430.6	430.7	431.0	431.3
127.5°	460.5	461.3	461.8	462.5	463.1	463.6	464.0	464.4	464.8	465.1	465.2
130°	481.2	481.9	482.4	482.9	483.3	483.8	484.3	484.7	485.2	485.7	485.9
132.5°	501.0	501.6	502.0	502.4	502.8	503.2	503.7	504.2	504.6	505.1	505.2
135°	530.3	530.8	531.3	531.8	532.3	532.7	533.1	533.5	533.9	534.1	534.1
137.5°	556.8	557.4	557.6	557.9	558.2	558.5	559.0	559.6	560.2	560.7	560.9
140°	573.3	573.8	574.1	574.5	574.9	575.2	575.7	576.2	576.6	577.1	577.2
142.5°	589.2	589.7	590.0	590.4	590.8	591.2	591.5	591.9	592.3	592.7	592.7
145°	611.9	612.5	612.7	612.9	613.1	613.4	613.6	613.9	614.1	614.3	614.4
147.5°	631.7	632.1	632.4	632.5	632.8	633.1	633.3	633.6	633.8	634.0	633.9
150°	643.9	644.1	644.4	644.6	644.9	645.1	645.4	645.5	645.8	646.0	646.0
152.5°	654.7	654.9	655.0	655.2	655.3	655.4	655.8	656.3	656.7	657.1	657.0
155°	669.4	669.4	669.5	669.6	669.7	669.9	670.4	671.0	671.7	672.2	672.1
157.5°	683.0	682.9	682.8	682.7	682.5	682.4	683.2	683.8	684.6	685.3	685.1
160°	690.3	690.2	690.0	689.9	689.8	689.8	690.4	691.2	691.8	692.6	692.5
162.5°	696.8	696.6	696.5	696.4	696.3	696.2	697.0	697.8	698.6	699.5	699.5
165°	705.5	705.2	705.1	705.0	704.9	704.7	705.8	706.7	707.7	708.6	708.7
167.5°	711.9	711.6	711.6	711.6	711.6	711.6	712.7	713.6	714.5	715.5	715.5
170°	715.8	715.5	715.5	715.5	715.5	715.5	716.5	717.5	718.4	719.3	719.3
172.5°	717.9	717.7	717.8	717.9	718.0	718.1	719.1	720.0	721.0	721.9	721.9
175°	721.2	721.0	721.0	721.2	721.3	721.4	722.3	723.1	724.0	724.8	724.7
177.5°	722.6	722.4	722.5	722.6	722.6	722.7	723.5	724.2	725.0	725.8	725.7
180°	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6

TEST NUMBER: P332246-830

CATALOG NUMBER: S123RDIP-S340D585U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9
2.5°	488.7	488.5	488.7	488.0	488.7	488.5	488.7	490.9	490.9	491.0	491.2
5°	454.8	454.6	453.9	451.9	453.9	454.6	454.8	455.4	457.2	460.2	459.4
7.5°	425.1	424.8	422.9	422.9	422.9	424.8	425.1	426.9	428.9	430.7	432.9
10°	407.6	407.7	405.1	403.6	405.1	407.7	407.6	409.1	412.0	413.5	415.0
12.5°	390.5	389.6	387.4	385.7	387.4	389.6	390.5	391.7	395.6	397.4	400.3
15°	368.1	365.8	360.6	361.0	360.6	365.8	368.1	367.1	371.1	373.3	374.2
17.5°	341.6	340.0	339.9	336.8	339.9	340.0	341.6	343.3	346.8	349.1	355.4
20°	326.1	325.0	325.5	322.3	325.5	325.0	326.1	329.6	331.8	334.9	340.0
22.5°	314.0	312.8	311.0	310.1	311.0	312.8	314.0	316.4	318.8	323.1	325.8
25°	296.2	294.5	292.8	293.8	292.8	294.5	296.2	297.6	301.9	303.9	307.8
27.5°	278.5	277.2	275.4	275.2	275.4	277.2	278.5	279.7	282.2	285.5	290.3
30°	267.2	265.9	265.0	263.9	265.0	265.9	267.2	268.3	270.8	274.3	277.8
32.5°	255.8	255.5	254.0	253.7	254.0	255.5	255.8	257.6	260.0	263.3	266.4
35°	240.9	239.6	239.1	239.3	239.1	239.6	240.9	241.8	243.9	247.0	249.9
37.5°	226.7	225.0	224.1	223.4	224.1	225.0	226.7	226.9	229.0	231.1	235.0
40°	216.5	214.8	214.3	213.9	214.3	214.8	216.5	216.3	218.7	220.3	223.8
42.5°	205.1	204.4	204.2	203.3	204.2	204.4	205.1	206.3	207.6	209.9	212.5
45°	189.5	189.3	187.9	188.4	187.9	189.3	189.5	190.2	192.6	194.2	196.5
47.5°	173.1	172.1	171.2	171.8	171.2	172.1	173.1	174.0	175.6	177.5	180.7
50°	161.8	161.4	159.4	159.9	159.4	161.4	161.8	162.7	163.8	166.3	169.1
52.5°	150.6	148.9	148.2	147.9	148.2	148.9	150.6	151.5	152.8	155.5	157.7
55°	132.0	130.0	129.1	128.7	129.1	130.0	132.0	133.6	135.3	138.4	140.5
57.5°	113.7	113.2	112.4	112.9	112.4	113.2	113.7	116.2	118.0	120.4	123.1
60°	103.0	103.0	103.0	102.7	103.0	103.0	103.0	105.2	106.7	109.1	112.0
62.5°	94.7	94.2	94.1	94.3	94.1	94.2	94.7	95.7	97.3	98.8	101.3
65°	82.1	81.9	81.1	80.8	81.1	81.9	82.1	82.8	84.1	85.2	87.0
67.5°	70.2	69.5	69.2	68.9	69.2	69.5	70.2	70.8	71.6	73.0	74.0
70°	61.3	60.8	59.5	59.8	59.5	60.8	61.3	62.4	63.2	65.0	65.9
72.5°	51.7	51.2	50.9	50.6	50.9	51.2	51.7	52.7	53.5	55.5	56.9
75°	40.8	40.6	40.4	41.3	40.4	40.6	40.8	41.1	41.3	41.9	42.6
77.5°	32.7	32.7	32.9	32.5	32.9	32.7	32.7	32.7	32.7	33.1	33.2
80°	27.4	27.4	27.2	27.2	27.2	27.4	27.4	27.4	27.4	27.4	27.2
82.5°	22.0	22.1	22.3	22.0	22.3	22.1	22.0	22.3	22.5	22.1	22.3
85°	14.5	14.2	14.7	14.5	14.7	14.2	14.5	14.5	14.0	14.5	14.2
87.5°	9.6	9.2	9.3	9.5	9.3	9.2	9.6	9.1	9.1	9.0	8.8
90°	15.5	15.6	15.9	16.1	15.9	15.6	15.5	15.2	14.8	14.3	13.9
92.5°	17.4	17.5	17.7	17.8	17.7	17.5	17.4	17.2	16.8	16.0	15.3
95°	20.5	20.5	20.5	20.5	20.5	20.5	20.5	20.5	20.0	19.1	18.4
97.5°	21.8	21.9	22.1	22.1	22.1	21.9	21.8	21.7	21.1	20.2	19.2
100°	22.2	22.3	22.4	22.6	22.4	22.3	22.2	22.1	21.6	20.6	19.6
102.5°	22.3	22.6	22.8	23.0	22.8	22.6	22.3	22.1	23.6	26.5	29.4
105°	22.9	23.2	23.4	23.7	23.4	23.2	22.9	22.7	33.2	54.3	75.4
107.5°	122.1	106.1	90.2	74.3	90.2	106.1	122.1	138.1	153.7	169.3	184.7
110°	199.1	182.0	164.9	147.8	164.9	182.0	199.1	216.1	226.7	230.6	234.6

TEST NUMBER: P332246-830

CATALOG NUMBER: S123RDIP-S340D585U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	264.5	260.8	257.2	253.6	257.2	260.8	264.5	268.1	269.8	269.8	269.7
115°	314.6	315.2	315.7	316.1	315.7	315.2	314.6	314.1	313.4	312.2	310.9
117.5°	350.9	351.0	351.1	351.2	351.1	351.0	350.9	350.8	350.2	349.3	348.4
120°	375.2	375.2	375.2	375.2	375.2	375.2	375.2	375.2	374.8	373.8	372.9
122.5°	398.6	398.7	398.8	398.9	398.8	398.7	398.6	398.5	398.1	397.5	396.8
125°	431.5	431.8	432.0	432.3	432.0	431.8	431.5	431.3	431.0	430.7	430.6
127.5°	465.0	464.8	464.5	464.3	464.5	464.8	465.0	465.2	465.1	464.8	464.4
130°	485.6	485.4	485.1	484.9	485.1	485.4	485.6	485.9	485.7	485.2	484.7
132.5°	504.8	504.4	504.2	503.8	504.2	504.4	504.8	505.2	505.1	504.6	504.2
135°	533.9	533.5	533.1	532.7	533.1	533.5	533.9	534.1	534.1	533.9	533.5
137.5°	560.6	560.4	560.2	560.0	560.2	560.4	560.6	560.9	560.7	560.2	559.6
140°	577.0	576.7	576.6	576.3	576.6	576.7	577.0	577.2	577.1	576.6	576.2
142.5°	592.4	592.0	591.6	591.4	591.6	592.0	592.4	592.7	592.7	592.3	591.9
145°	614.4	614.4	614.4	614.4	614.4	614.4	614.4	614.4	614.3	614.1	613.9
147.5°	633.3	632.7	632.3	631.7	632.3	632.7	633.3	633.9	634.0	633.8	633.6
150°	645.6	645.3	644.9	644.6	644.9	645.3	645.6	646.0	646.0	645.8	645.5
152.5°	656.6	656.0	655.4	654.9	655.4	656.0	656.6	657.0	657.1	656.7	656.3
155°	671.5	670.7	670.1	669.3	670.1	670.7	671.5	672.1	672.2	671.7	671.0
157.5°	684.2	683.3	682.4	681.5	682.4	683.3	684.2	685.1	685.3	684.6	683.8
160°	691.7	690.9	690.0	689.2	690.0	690.9	691.7	692.5	692.6	691.8	691.2
162.5°	698.7	698.0	697.2	696.5	697.2	698.0	698.7	699.5	699.5	698.6	697.8
165°	707.8	707.0	706.2	705.3	706.2	707.0	707.8	708.7	708.6	707.7	706.7
167.5°	714.5	713.6	712.7	711.6	712.7	713.6	714.5	715.5	715.5	714.5	713.6
170°	718.4	717.5	716.5	715.5	716.5	717.5	718.4	719.3	719.3	718.4	717.5
172.5°	720.9	719.8	718.7	717.7	718.7	719.8	720.9	721.9	721.9	721.0	720.0
175°	723.8	722.8	721.9	720.9	721.9	722.8	723.8	724.7	724.8	724.0	723.1
177.5°	724.7	723.8	722.8	721.9	722.8	723.8	724.7	725.7	725.8	725.0	724.2
180°	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6

TEST NUMBER: P332246-830

CATALOG NUMBER: S123RDIP-S340D585U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9
2.5°	489.7	492.1	494.6	496.8	500.3	501.9	504.2	505.1	507.7	511.5	514.7
5°	459.9	463.4	468.0	471.6	477.6	482.2	487.3	492.1	497.9	506.0	513.2
7.5°	434.6	438.0	443.6	450.5	457.0	463.6	470.5	477.1	485.2	496.9	508.4
10°	417.9	422.1	428.7	436.1	444.2	450.6	458.7	467.0	477.2	490.6	504.4
12.5°	403.5	406.6	414.2	421.3	430.6	438.7	446.6	456.4	467.9	482.1	498.8
15°	380.6	384.9	392.4	400.3	410.0	418.6	428.9	440.7	451.9	469.5	489.7
17.5°	357.5	364.2	372.0	380.9	388.0	399.9	411.0	423.2	437.1	455.6	477.9
20°	342.8	348.1	355.3	368.3	377.7	386.7	397.0	412.2	424.9	446.0	469.0
22.5°	330.3	334.1	342.3	353.0	364.0	374.4	384.9	399.4	415.1	435.1	460.1
25°	311.8	318.0	324.1	331.8	343.7	356.2	367.6	379.9	396.6	417.9	444.9
27.5°	293.8	299.4	305.4	314.8	323.9	335.5	347.5	361.6	379.5	402.0	429.4
30°	282.2	286.3	292.1	304.2	312.3	322.3	336.4	348.9	365.6	389.6	418.6
32.5°	270.2	275.6	281.9	291.2	301.2	310.8	323.6	337.1	354.2	377.8	407.5
35°	253.2	259.6	265.9	272.8	282.9	292.8	303.5	318.4	335.7	358.6	387.8
37.5°	237.5	242.6	247.8	256.3	265.8	275.2	285.3	300.0	316.3	341.0	367.8
40°	227.5	232.1	236.1	244.9	254.1	264.2	274.1	287.0	304.5	327.6	353.5
42.5°	216.6	220.8	226.2	233.5	243.4	251.8	261.7	274.0	290.5	314.0	336.7
45°	200.3	205.1	209.7	216.5	226.4	234.8	243.6	255.1	272.1	291.4	311.6
47.5°	183.2	188.1	193.4	200.0	208.6	217.1	225.8	236.1	251.6	270.5	284.2
50°	172.4	176.3	181.6	188.2	196.1	205.1	213.0	224.2	238.9	253.8	265.7
52.5°	161.2	164.8	170.7	177.7	185.0	192.8	201.2	210.8	224.1	238.2	247.6
55°	143.6	148.0	153.1	159.9	167.1	173.7	181.8	191.7	202.3	212.8	219.1
57.5°	127.2	130.9	135.2	142.1	148.5	156.3	163.6	171.3	181.1	189.0	193.1
60°	115.3	118.6	124.0	130.3	136.1	143.0	151.3	159.0	166.5	172.9	176.1
62.5°	104.1	107.8	112.6	118.3	124.7	131.2	138.5	145.0	151.6	157.0	159.3
65°	89.4	92.5	96.0	101.2	106.5	113.1	118.8	125.4	130.3	133.3	135.3
67.5°	76.1	78.0	80.7	84.3	89.4	95.2	100.7	105.8	109.9	112.0	113.8
70°	67.4	68.7	70.7	74.2	78.1	83.2	89.0	92.7	96.1	97.9	99.7
72.5°	58.8	60.5	62.3	65.1	68.3	72.0	76.2	80.7	82.7	84.7	85.8
75°	44.6	47.0	49.4	51.2	53.3	56.2	59.9	62.8	63.9	65.7	65.9
77.5°	33.6	34.2	35.9	38.1	40.0	42.0	44.4	46.9	47.5	48.4	49.0
80°	27.7	27.7	27.7	29.0	31.2	32.7	34.9	36.2	37.1	37.3	37.5
82.5°	22.2	22.2	22.1	22.3	23.1	23.9	25.9	27.4	28.2	28.0	27.5
85°	14.5	14.0	14.0	13.9	14.0	13.6	13.4	14.2	15.6	15.6	15.2
87.5°	8.7	8.4	8.2	7.7	7.3	6.8	5.9	5.9	5.7	6.1	5.7
90°	13.4	12.9	11.3	9.8	8.2	6.7	5.3	4.1	2.9	1.7	0.6
92.5°	14.5	13.8	12.6	11.4	10.3	9.0	8.7	9.0	9.3	9.7	10.0
95°	17.5	16.7	15.4	14.0	12.7	11.4	13.2	18.1	23.0	27.9	32.8
97.5°	18.3	17.3	25.9	34.5	43.1	51.7	57.1	59.3	61.5	63.7	65.9
100°	18.7	17.7	36.4	55.0	73.6	92.3	100.4	98.0	95.7	93.2	90.9
102.5°	32.4	35.3	55.7	76.1	96.4	116.8	126.1	124.4	122.7	120.9	119.2
105°	96.6	117.7	128.5	139.2	150.0	160.7	165.4	164.1	162.9	161.6	160.2
107.5°	200.3	215.7	214.1	212.4	210.7	209.0	207.6	206.6	205.6	204.4	203.4
110°	238.5	242.4	241.1	239.8	238.5	237.2	236.0	235.1	234.1	233.2	232.2

TEST NUMBER: P332246-830

CATALOG NUMBER: S123RDIP-S340D585U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	269.7	269.6	268.2	266.9	265.6	264.3	263.2	262.3	261.5	260.6	259.8
115°	309.8	308.6	307.5	306.4	305.4	304.3	303.4	302.7	301.9	301.2	300.5
117.5°	347.4	346.4	345.9	345.3	344.8	344.2	343.5	342.6	341.8	340.8	340.0
120°	371.9	370.9	370.6	370.2	369.9	369.5	368.8	367.7	366.6	365.5	364.5
122.5°	396.2	395.5	395.0	394.5	394.1	393.6	392.9	392.1	391.2	390.3	389.5
125°	430.3	430.1	429.6	429.1	428.7	428.2	427.4	426.5	425.6	424.6	423.6
127.5°	464.0	463.6	463.1	462.5	461.8	461.3	460.5	459.6	458.6	457.7	456.8
130°	484.3	483.8	483.3	482.9	482.4	481.9	481.2	480.2	479.3	478.3	477.4
132.5°	503.7	503.2	502.8	502.4	502.0	501.6	501.0	500.0	499.1	498.1	497.2
135°	533.1	532.7	532.3	531.8	531.3	530.8	530.3	529.5	528.8	528.1	527.4
137.5°	559.0	558.5	558.2	557.9	557.6	557.4	556.8	555.9	555.0	554.1	553.2
140°	575.7	575.2	574.9	574.5	574.1	573.8	573.3	572.5	571.8	571.1	570.3
142.5°	591.5	591.2	590.8	590.4	590.0	589.7	589.2	588.4	587.8	587.0	586.3
145°	613.6	613.4	613.1	612.9	612.7	612.5	611.9	611.1	610.2	609.4	608.5
147.5°	633.3	633.1	632.8	632.5	632.4	632.1	631.7	631.1	630.7	630.1	629.5
150°	645.4	645.1	644.9	644.6	644.4	644.1	643.9	643.5	643.1	642.8	642.4
152.5°	655.8	655.4	655.3	655.2	655.0	654.9	654.7	654.5	654.3	654.2	654.0
155°	670.4	669.9	669.7	669.6	669.5	669.4	669.4	669.7	669.9	670.1	670.3
157.5°	683.2	682.4	682.5	682.7	682.8	682.9	683.0	683.0	683.0	683.1	683.1
160°	690.4	689.8	689.8	689.9	690.0	690.2	690.3	690.4	690.6	690.7	690.8
162.5°	697.0	696.2	696.3	696.4	696.5	696.6	696.8	697.2	697.5	697.8	698.1
165°	705.8	704.7	704.9	705.0	705.1	705.2	705.5	705.9	706.2	706.5	706.9
167.5°	712.7	711.6	711.6	711.6	711.6	711.6	711.9	712.4	712.8	713.3	713.8
170°	716.5	715.5	715.5	715.5	715.5	715.5	715.8	716.2	716.7	717.2	717.7
172.5°	719.1	718.1	718.0	717.9	717.8	717.7	717.9	718.5	719.1	719.7	720.3
175°	722.3	721.4	721.3	721.2	721.0	721.0	721.2	721.8	722.4	723.0	723.6
177.5°	723.5	722.7	722.6	722.6	722.5	722.4	722.6	723.0	723.5	724.0	724.4
180°	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6

TEST NUMBER: P332246-830

CATALOG NUMBER: S123RDIP-S340D585U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9
2.5°	515.8	517.7	520.2	523.9	526.7	529.1	529.6	530.4	532.2	535.1	537.3
5°	519.2	524.1	532.3	540.2	548.7	555.8	562.4	567.0	571.4	580.6	588.1
7.5°	518.0	529.3	542.1	556.2	570.6	584.5	597.4	609.0	620.5	634.0	649.2
10°	517.4	530.6	547.7	565.9	585.9	605.4	624.3	639.0	656.1	671.6	691.1
12.5°	514.1	533.0	553.5	576.7	601.3	623.9	648.8	669.0	688.6	710.9	733.6
15°	509.6	532.7	558.6	589.6	627.0	654.1	679.7	715.0	739.1	763.3	795.8
17.5°	501.7	529.9	562.2	602.5	633.6	670.2	708.5	736.5	769.0	803.0	832.5
20°	495.4	528.1	564.4	603.9	643.7	683.3	720.5	753.8	787.5	826.8	850.9
22.5°	489.1	521.4	559.1	601.1	643.8	685.7	727.6	766.9	804.6	844.3	875.2
25°	475.6	514.1	554.9	597.8	639.9	686.0	736.0	779.8	826.5	867.4	896.6
27.5°	462.0	497.3	537.9	581.4	628.2	682.7	741.6	791.3	838.1	867.4	876.6
30°	449.7	487.0	524.4	568.5	619.3	680.0	742.6	799.6	837.9	850.7	841.2
32.5°	437.2	471.1	508.0	553.3	607.1	673.5	744.0	794.7	817.7	808.0	769.6
35°	415.3	445.7	481.5	526.8	588.7	670.0	738.3	772.5	766.9	711.9	639.4
37.5°	391.7	416.6	449.7	497.0	569.7	655.7	713.3	718.4	668.9	584.7	501.0
40°	373.1	395.5	429.5	478.9	554.9	641.7	688.2	667.8	591.2	497.4	427.5
42.5°	355.0	373.9	406.7	460.0	540.8	622.5	650.8	606.3	517.9	429.2	365.7
45°	324.3	342.1	375.0	429.7	512.1	585.9	582.1	504.8	416.3	345.0	292.3
47.5°	295.3	310.9	341.8	397.6	478.3	530.9	496.1	413.8	338.7	281.4	243.8
50°	274.8	290.1	320.8	376.0	451.3	489.7	439.9	360.6	291.8	244.4	214.5
52.5°	255.1	270.0	298.1	351.9	418.6	441.6	388.0	314.5	257.2	216.3	190.7
55°	227.5	238.9	264.2	315.6	365.4	370.7	316.4	255.0	207.7	179.2	161.6
57.5°	199.4	209.2	234.2	275.1	310.1	307.4	256.0	202.7	171.0	149.8	137.0
60°	181.2	190.9	212.8	247.9	274.3	265.0	217.8	175.0	147.8	132.2	122.1
62.5°	164.1	171.6	192.3	217.9	236.9	226.4	186.2	150.8	129.1	116.0	108.0
65°	139.4	145.6	162.0	175.5	186.0	175.9	142.5	117.9	102.4	93.1	87.7
67.5°	116.0	119.9	130.3	135.2	142.6	131.5	107.2	90.7	81.8	74.1	70.2
70°	101.2	104.1	109.6	113.6	115.5	104.1	86.1	74.0	66.5	61.1	58.6
72.5°	86.4	89.0	90.1	93.3	92.3	81.6	69.2	59.6	54.2	50.5	47.4
75°	66.1	67.2	66.1	64.8	61.9	54.5	45.9	41.1	37.1	35.3	34.2
77.5°	48.2	47.8	46.4	44.3	39.4	34.7	30.1	28.5	26.8	25.8	25.4
80°	37.1	36.2	34.9	31.6	27.4	24.1	23.1	22.0	21.3	20.2	20.0
82.5°	27.6	27.1	24.9	22.1	19.2	17.6	16.8	16.3	15.6	15.1	15.1
85°	14.7	14.0	11.6	10.1	9.7	9.2	9.0	9.0	8.1	7.9	7.9
87.5°	5.1	4.2	4.3	4.1	4.3	4.2	4.8	4.7	4.9	5.1	4.9
90°	1.7	2.9	4.1	5.3	6.7	8.2	9.8	11.3	12.9	13.4	13.9
92.5°	9.7	9.3	9.0	8.7	9.0	10.3	11.4	12.6	13.8	14.5	15.3
95°	27.9	23.0	18.1	13.2	11.4	12.7	14.0	15.4	16.7	17.5	18.4
97.5°	63.7	61.5	59.3	57.1	51.7	43.1	34.5	25.9	17.3	18.3	19.2
100°	93.2	95.7	98.0	100.4	92.3	73.6	55.0	36.4	17.7	18.7	19.6
102.5°	120.9	122.7	124.4	126.1	116.8	96.4	76.1	55.7	35.3	32.4	29.4
105°	161.6	162.9	164.1	165.4	160.7	150.0	139.2	128.5	117.7	96.6	75.4
107.5°	204.4	205.6	206.6	207.6	209.0	210.7	212.4	214.1	215.7	200.3	184.7
110°	233.2	234.1	235.1	236.0	237.2	238.5	239.8	241.1	242.4	238.5	234.6

TEST NUMBER: P332246-830

CATALOG NUMBER: S123RDIP-S340D585U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	260.6	261.5	262.3	263.2	264.3	265.6	266.9	268.2	269.6	269.7	269.7
115°	301.2	301.9	302.7	303.4	304.3	305.4	306.4	307.5	308.6	309.8	310.9
117.5°	340.8	341.8	342.6	343.5	344.2	344.8	345.3	345.9	346.4	347.4	348.4
120°	365.5	366.6	367.7	368.8	369.5	369.9	370.2	370.6	370.9	371.9	372.9
122.5°	390.3	391.2	392.1	392.9	393.6	394.1	394.5	395.0	395.5	396.2	396.8
125°	424.6	425.6	426.5	427.4	428.2	428.7	429.1	429.6	430.1	430.3	430.6
127.5°	457.7	458.6	459.6	460.5	461.3	461.8	462.5	463.1	463.6	464.0	464.4
130°	478.3	479.3	480.2	481.2	481.9	482.4	482.9	483.3	483.8	484.3	484.7
132.5°	498.1	499.1	500.0	501.0	501.6	502.0	502.4	502.8	503.2	503.7	504.2
135°	528.1	528.8	529.5	530.3	530.8	531.3	531.8	532.3	532.7	533.1	533.5
137.5°	554.1	555.0	555.9	556.8	557.4	557.6	557.9	558.2	558.5	559.0	559.6
140°	571.1	571.8	572.5	573.3	573.8	574.1	574.5	574.9	575.2	575.7	576.2
142.5°	587.0	587.8	588.4	589.2	589.7	590.0	590.4	590.8	591.2	591.5	591.9
145°	609.4	610.2	611.1	611.9	612.5	612.7	612.9	613.1	613.4	613.6	613.9
147.5°	630.1	630.7	631.1	631.7	632.1	632.4	632.5	632.8	633.1	633.3	633.6
150°	642.8	643.1	643.5	643.9	644.1	644.4	644.6	644.9	645.1	645.4	645.5
152.5°	654.2	654.3	654.5	654.7	654.9	655.0	655.2	655.3	655.4	655.8	656.3
155°	670.1	669.9	669.7	669.4	669.4	669.5	669.6	669.7	669.9	670.4	671.0
157.5°	683.1	683.0	683.0	683.0	682.9	682.8	682.7	682.5	682.4	683.2	683.8
160°	690.7	690.6	690.4	690.3	690.2	690.0	689.9	689.8	689.8	690.4	691.2
162.5°	697.8	697.5	697.2	696.8	696.6	696.5	696.4	696.3	696.2	697.0	697.8
165°	706.5	706.2	705.9	705.5	705.2	705.1	705.0	704.9	704.7	705.8	706.7
167.5°	713.3	712.8	712.4	711.9	711.6	711.6	711.6	711.6	711.6	712.7	713.6
170°	717.2	716.7	716.2	715.8	715.5	715.5	715.5	715.5	715.5	716.5	717.5
172.5°	719.7	719.1	718.5	717.9	717.7	717.8	717.9	718.0	718.1	719.1	720.0
175°	723.0	722.4	721.8	721.2	721.0	721.0	721.2	721.3	721.4	722.3	723.1
177.5°	724.0	723.5	723.0	722.6	722.4	722.5	722.6	722.6	722.7	723.5	724.2
180°	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6

TEST NUMBER: P332246-830

CATALOG NUMBER: S123RDIP-S340D585U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	512.9	512.9	512.9	512.9	512.9	512.9	512.9
2.5°	541.1	541.1	541.8	544.4	544.8	547.1	546.4
5°	594.7	598.8	600.4	607.0	610.9	612.7	609.2
7.5°	660.2	671.9	677.5	684.5	690.5	692.4	687.6
10°	707.9	720.3	730.6	737.0	742.9	746.9	751.9
12.5°	754.1	769.3	779.1	788.1	794.2	799.2	800.0
15°	804.4	827.2	844.5	857.3	863.7	867.0	865.6
17.5°	855.0	876.2	888.5	901.5	910.3	910.8	911.1
20°	883.6	904.3	918.6	928.2	938.1	937.6	939.9
22.5°	902.8	919.1	930.0	937.0	940.4	938.7	939.1
25°	911.7	916.6	914.6	903.4	900.5	890.2	892.0
27.5°	865.5	842.7	819.1	788.7	764.7	745.6	746.5
30°	802.9	762.4	716.3	677.7	643.0	633.3	612.7
32.5°	715.2	654.6	600.6	564.5	534.8	526.7	508.7
35°	566.6	507.7	452.1	418.8	405.6	387.1	386.9
37.5°	440.4	388.5	359.2	334.1	321.0	309.8	308.8
40°	370.4	330.1	307.8	289.8	276.9	268.5	266.6
42.5°	321.6	289.0	268.2	257.0	247.0	242.7	239.5
45°	262.6	240.6	226.2	216.1	211.5	208.2	206.4
47.5°	219.7	205.0	195.1	188.3	184.6	181.2	182.1
50°	196.3	184.3	177.0	170.6	167.8	165.3	165.6
52.5°	177.5	166.6	160.8	156.2	152.7	150.9	150.1
55°	150.6	143.8	137.9	134.6	132.6	130.3	129.6
57.5°	128.5	123.2	118.4	114.7	114.1	111.9	112.2
60°	113.8	109.3	105.4	103.4	101.9	99.9	100.6
62.5°	101.6	97.9	94.3	92.7	91.1	89.7	90.0
65°	83.2	79.7	77.5	76.6	76.0	75.3	74.6
67.5°	66.4	64.2	62.8	60.9	59.6	59.4	58.7
70°	55.8	52.9	50.5	48.1	47.4	47.2	47.4
72.5°	44.7	42.9	42.2	41.1	40.9	40.3	40.7
75°	33.6	32.9	32.5	31.6	31.6	31.6	31.6
77.5°	24.8	24.4	24.1	23.9	23.8	23.4	23.4
80°	19.3	19.1	18.7	18.7	18.5	18.7	18.5
82.5°	14.6	14.5	14.1	14.1	13.9	13.8	13.9
85°	7.4	7.3	7.7	7.3	7.4	7.1	7.4
87.5°	5.0	5.1	5.0	5.0	4.9	5.3	5.0
90°	14.3	14.8	15.2	15.5	15.6	15.9	16.1
92.5°	16.0	16.8	17.2	17.4	17.5	17.7	17.8
95°	19.1	20.0	20.5	20.5	20.5	20.5	20.5
97.5°	20.2	21.1	21.7	21.8	21.9	22.1	22.1
100°	20.6	21.6	22.1	22.2	22.3	22.4	22.6
102.5°	26.5	23.6	22.1	22.3	22.6	22.8	23.0
105°	54.3	33.2	22.7	22.9	23.2	23.4	23.7
107.5°	169.3	153.7	138.1	122.1	106.1	90.2	74.3
110°	230.6	226.7	216.1	199.1	182.0	164.9	147.8

TEST NUMBER: P332246-830

CATALOG NUMBER: S123RDIP-S340D585U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	269.8	269.8	268.1	264.5	260.8	257.2	253.6
115°	312.2	313.4	314.1	314.6	315.2	315.7	316.1
117.5°	349.3	350.2	350.8	350.9	351.0	351.1	351.2
120°	373.8	374.8	375.2	375.2	375.2	375.2	375.2
122.5°	397.5	398.1	398.5	398.6	398.7	398.8	398.9
125°	430.7	431.0	431.3	431.5	431.8	432.0	432.3
127.5°	464.8	465.1	465.2	465.0	464.8	464.5	464.3
130°	485.2	485.7	485.9	485.6	485.4	485.1	484.9
132.5°	504.6	505.1	505.2	504.8	504.4	504.2	503.8
135°	533.9	534.1	534.1	533.9	533.5	533.1	532.7
137.5°	560.2	560.7	560.9	560.6	560.4	560.2	560.0
140°	576.6	577.1	577.2	577.0	576.7	576.6	576.3
142.5°	592.3	592.7	592.7	592.4	592.0	591.6	591.4
145°	614.1	614.3	614.4	614.4	614.4	614.4	614.4
147.5°	633.8	634.0	633.9	633.3	632.7	632.3	631.7
150°	645.8	646.0	646.0	645.6	645.3	644.9	644.6
152.5°	656.7	657.1	657.0	656.6	656.0	655.4	654.9
155°	671.7	672.2	672.1	671.5	670.7	670.1	669.3
157.5°	684.6	685.3	685.1	684.2	683.3	682.4	681.5
160°	691.8	692.6	692.5	691.7	690.9	690.0	689.2
162.5°	698.6	699.5	699.5	698.7	698.0	697.2	696.5
165°	707.7	708.6	708.7	707.8	707.0	706.2	705.3
167.5°	714.5	715.5	715.5	714.5	713.6	712.7	711.6
170°	718.4	719.3	719.3	718.4	717.5	716.5	715.5
172.5°	721.0	721.9	721.9	720.9	719.8	718.7	717.7
175°	724.0	724.8	724.7	723.8	722.8	721.9	720.9
177.5°	725.0	725.8	725.7	724.7	723.8	722.8	721.9
180°	723.6	723.6	723.6	723.6	723.6	723.6	723.6

(END OF REPORT)