

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332359-930

Luminaire Tested: **S123RDIP-S1000D1195U930-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332359-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1000D1195U930-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1195 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6615.1 lumens
Efficiency: N/A
Efficacy: 101.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 65.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332359-930

CATALOG NUMBER: S123RDIP-S1000D1195U930-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332359-930

CATALOG NUMBER: S123RDIP-S1000D1195U930-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	53	53	53	47
1	97	93	89	86	89	86	83	80	72	70	68	59	58	56	47	46	45	40
2	89	82	76	71	81	75	70	66	63	60	56	52	50	47	42	40	39	34
3	81	72	65	59	74	67	60	55	56	52	48	46	43	40	38	35	33	29
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	34	31	29	25
5	68	57	49	43	63	53	46	41	45	40	35	37	33	30	31	28	25	22
6	63	51	43	38	58	48	41	35	41	35	31	34	30	27	28	25	22	20
7	58	46	39	33	54	43	36	31	37	31	27	31	27	24	25	22	20	17
8	54	42	34	29	50	39	32	28	34	28	24	28	24	21	23	20	18	16
9	50	38	31	26	46	36	29	25	31	26	22	26	22	19	22	19	16	14
10	47	35	28	23	43	33	27	22	28	23	20	24	20	17	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14727	14727	14727
5°	14783	14579	14664
10°	14700	14397	14348
15°	14542	14060	13912
20°	14325	13639	13321
25°	14101	13166	12744
30°	13806	12621	11931
35°	13502	12073	11184
40°	13222	11428	10260
45°	12855	10794	9426
50°	12450	10071	8492
55°	12037	9246	7621
60°	11657	8361	6665
65°	11163	7404	5708
70°	10546	6216	4611
75°	9649	4891	4338
80°	8598	4333	3986
85°	7262	3841	3569



TEST NUMBER: P332359-930

CATALOG NUMBER: S123RDIP-S1000D1195U930-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.5	1.9
10°-20°	357.5	5.4
20°-30°	514.7	7.8
30°-40°	579.8	8.8
40°-50°	554.7	8.4
50°-60°	454.2	6.9
60°-70°	306.5	4.6
70°-80°	154.2	2.3
80°-90°	44.4	0.7
90°-100°	260.4	3.9
100°-110°	737.4	11.1
110°-120°	725.4	11.0
120°-130°	578.6	8.7
130°-140°	456.2	6.9
140°-150°	340.5	5.1
150°-160°	237.3	3.6
160°-170°	139.4	2.1
170°-180°	45.4	0.7
0°-30°	1000.7	15.1
0°-40°	1580.5	23.9
0°-60°	2589.5	39.1
0°-90°	3094.5	46.8
90°-120°	1723.2	26.0
90°-150°	3098.5	46.8
90°-180°	3521.0	53.2
0°-180°	6615.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1368	1368	1368	1368	1368	
5°	1368	1362	1349	1359	1357	130
15°	1305	1292	1262	1256	1248	367
25°	1187	1158	1109	1086	1073	546
35°	1028	986	919	873	851	643
45°	844	793	709	648	619	651
55°	641	585	493	431	406	575
65°	438	376	291	239	224	434
75°	232	178	118	107	104	247
85°	59	36	31	29	29	66
90°	2	11	24	27	28	5
95°	32	105	562	164	110	35
105°	110	162	762	1332	1205	117
115°	194	242	582	1277	1465	192
125°	270	319	544	985	1156	239
135°	316	378	536	811	937	244
145°	361	414	530	665	732	226
155°	410	442	512	583	607	189
165°	448	461	491	520	530	126
175°	467	468	471	477	476	44
180°	468	468	468	468	468	



TEST NUMBER: P332359-930

CATALOG NUMBER: S123RDIP-S1000D1195U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2
2.5°	1372.6	1371.8	1371.1	1370.3	1369.5	1367.9	1365.5	1363.2	1360.8	1358.5	1360.6
5°	1368.2	1366.9	1365.7	1364.5	1363.3	1361.1	1358.2	1355.3	1352.3	1349.3	1351.5
7.5°	1355.5	1354.2	1352.9	1351.5	1350.2	1347.6	1343.8	1339.9	1336.1	1332.3	1333.5
10°	1344.9	1343.2	1341.4	1339.7	1338.0	1334.9	1330.5	1326.0	1321.6	1317.2	1317.4
12.5°	1329.8	1327.9	1326.0	1324.0	1322.1	1318.4	1313.0	1307.6	1302.2	1296.7	1296.6
15°	1305.0	1302.3	1299.5	1296.8	1294.1	1289.3	1282.4	1275.5	1268.6	1261.7	1260.5
17.5°	1273.7	1270.5	1267.4	1264.2	1261.0	1255.1	1246.3	1237.5	1228.7	1219.9	1217.3
20°	1250.6	1246.7	1242.7	1238.8	1234.8	1228.2	1218.8	1209.4	1200.0	1190.7	1187.5
22.5°	1224.8	1220.3	1215.8	1211.2	1206.7	1199.5	1189.4	1179.5	1169.5	1159.6	1155.6
25°	1187.3	1181.2	1175.0	1168.8	1162.7	1153.9	1142.6	1131.2	1119.9	1108.6	1103.3
27.5°	1141.8	1135.1	1128.2	1121.4	1114.6	1104.9	1092.3	1079.6	1067.0	1054.4	1047.2
30°	1110.8	1103.3	1096.0	1088.6	1081.2	1070.6	1056.8	1042.9	1029.2	1015.4	1007.0
32.5°	1079.7	1071.3	1062.9	1054.5	1046.2	1034.7	1020.1	1005.5	990.8	976.2	967.1
35°	1027.5	1018.6	1009.7	1000.9	992.1	979.9	964.7	949.3	934.1	918.8	908.2
37.5°	974.7	964.8	955.0	945.1	935.2	922.2	905.9	889.5	873.2	856.9	844.8
40°	941.0	930.2	919.2	908.4	897.6	883.4	865.9	848.4	830.9	813.3	800.5
42.5°	902.8	891.9	881.1	870.3	859.4	845.0	826.9	808.8	790.7	772.6	758.6
45°	844.5	833.3	822.2	811.1	800.1	785.1	766.1	747.1	728.1	709.1	695.0
47.5°	786.1	773.9	761.7	749.5	737.4	721.8	702.8	683.8	664.8	645.8	630.6
50°	743.5	731.9	720.3	708.7	697.1	681.3	661.4	641.4	621.4	601.4	586.1
52.5°	705.3	692.8	680.1	667.6	655.0	638.8	619.1	599.2	579.5	559.7	543.8
55°	641.4	629.3	617.2	605.1	593.0	576.5	555.5	534.6	513.6	492.7	478.4
57.5°	582.4	569.2	556.0	542.8	529.7	512.6	491.5	470.4	449.4	428.4	414.8
60°	541.5	528.0	514.4	500.8	487.2	470.3	449.8	429.3	408.9	388.4	375.0
62.5°	500.7	487.1	473.5	460.0	446.5	429.4	409.0	388.5	368.0	347.6	335.0
65°	438.3	424.8	411.2	397.6	384.1	367.7	348.5	329.2	310.0	290.7	278.7
67.5°	375.9	362.2	348.5	334.8	321.1	305.0	286.6	268.2	249.7	231.2	222.3
70°	335.1	321.8	308.5	295.1	281.8	266.6	249.3	232.0	214.7	197.5	188.9
72.5°	294.2	281.2	268.1	254.9	241.8	227.4	211.7	196.1	180.3	164.7	157.6
75°	232.0	220.0	208.2	196.4	184.6	171.9	158.3	144.7	131.2	117.6	115.1
77.5°	175.1	164.4	153.7	143.0	132.3	122.5	113.8	105.1	96.4	87.6	86.3
80°	138.7	128.6	118.5	108.4	98.2	90.7	85.4	80.2	75.1	69.9	69.1
82.5°	104.1	95.4	86.7	77.9	69.1	63.6	61.1	58.8	56.3	53.9	53.2
85°	58.8	53.4	47.9	42.6	37.1	34.0	33.3	32.5	31.8	31.1	30.6
87.5°	21.7	19.9	18.1	16.5	14.7	14.0	14.6	15.2	15.7	16.3	15.9
90°	1.9	3.8	5.7	8.6	10.4	12.3	15.2	18.0	20.9	23.6	22.7
92.5°	11.7	17.4	25.4	32.8	40.8	54.8	79.6	120.3	160.3	145.7	109.9
95°	32.2	35.1	45.5	61.6	86.2	123.1	203.7	344.8	500.2	561.7	455.6
97.5°	55.0	55.8	64.0	78.0	102.3	142.3	219.2	378.3	637.3	870.5	931.3
100°	70.1	71.0	77.7	90.9	113.7	150.6	217.0	357.1	606.3	897.1	1083.7
102.5°	86.0	87.7	93.6	106.1	126.5	160.5	220.0	338.9	560.8	847.8	1091.2
105°	109.9	112.8	118.4	129.8	147.7	177.2	228.3	325.9	504.9	761.6	1033.5
107.5°	135.3	138.1	143.6	154.7	171.6	198.9	243.9	324.9	469.3	685.4	932.3
110°	153.4	156.3	161.0	171.5	187.5	214.1	256.7	328.7	455.6	642.2	868.6



TEST NUMBER: P332359-930

CATALOG NUMBER: S123RDIP-S1000D1195U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	170.2	173.0	177.7	188.1	204.2	230.0	269.6	336.3	448.1	613.4	813.3
115°	194.2	198.0	203.7	213.1	229.3	254.8	290.8	348.6	445.2	582.5	746.4
117.5°	218.3	222.6	227.3	236.0	254.0	277.8	313.3	364.8	446.9	564.4	706.0
120°	234.9	237.7	242.5	252.0	269.9	293.7	327.8	377.0	450.0	556.0	684.9
122.5°	249.3	252.2	256.9	267.1	284.4	309.6	342.9	388.4	455.3	550.7	667.4
125°	269.9	271.9	277.5	288.0	306.0	331.5	364.7	406.3	463.2	543.7	645.1
127.5°	285.7	288.5	295.5	306.1	326.0	351.6	383.6	421.2	472.3	540.3	625.4
130°	295.5	298.4	306.9	318.3	338.2	363.7	395.0	431.0	478.3	538.0	614.7
132.5°	303.1	306.7	316.0	329.6	349.5	374.4	404.9	440.1	482.9	537.3	605.0
135°	316.4	320.2	330.6	344.8	364.7	390.3	419.6	451.8	489.8	536.1	592.1
137.5°	328.9	332.9	343.1	358.2	378.0	401.6	429.8	460.6	494.3	534.0	580.8
140°	337.2	341.9	351.4	366.6	385.6	409.2	436.7	465.1	497.3	533.3	574.1
142.5°	346.3	350.3	360.5	374.1	393.1	415.3	442.0	469.6	499.6	531.8	567.9
145°	360.9	363.7	372.3	386.5	402.6	424.4	449.0	474.6	501.1	529.5	559.9
147.5°	375.7	377.4	385.7	398.0	413.6	432.1	454.7	477.6	501.1	525.9	551.9
150°	385.6	386.5	394.0	406.3	419.6	436.7	458.4	478.3	501.1	522.9	546.6
152.5°	395.4	395.6	403.2	413.9	425.7	442.0	460.7	479.9	498.8	519.1	540.5
155°	410.2	410.2	415.9	425.3	435.7	449.0	465.1	480.3	496.4	512.5	531.4
157.5°	421.9	422.7	427.2	435.5	444.4	454.7	467.6	481.2	493.2	506.6	521.1
160°	431.0	431.0	434.8	442.4	449.0	458.4	469.9	481.2	491.6	502.1	514.4
162.5°	437.8	437.8	440.8	446.9	452.8	460.7	470.6	480.5	488.6	497.5	507.5
165°	448.1	447.1	449.0	453.7	457.5	464.1	471.7	478.3	484.0	490.6	498.2
167.5°	455.8	454.7	455.6	459.3	461.9	466.0	471.6	476.9	479.5	483.9	489.3
170°	460.4	458.4	459.4	462.3	464.1	466.0	470.8	474.6	476.5	479.3	484.0
172.5°	463.4	462.3	462.4	464.6	465.7	466.8	470.8	473.9	474.2	475.5	478.7
175°	467.0	466.0	465.1	467.0	467.0	468.0	469.9	471.7	470.8	470.8	472.7
177.5°	468.7	468.0	467.2	468.0	468.0	468.0	468.7	470.2	468.7	468.0	468.7
180°	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0



TEST NUMBER: P332359-930

CATALOG NUMBER: S123RDIP-S1000D1195U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2
2.5°	1362.8	1365.0	1367.1	1368.0	1367.6	1367.3	1366.8	1366.4
5°	1353.8	1356.0	1358.2	1359.1	1358.6	1358.1	1357.6	1357.1
7.5°	1334.7	1335.9	1337.2	1337.4	1336.5	1335.7	1334.9	1334.0
10°	1317.7	1317.9	1318.2	1317.7	1316.4	1315.2	1313.9	1312.7
12.5°	1296.4	1296.3	1296.2	1295.3	1294.0	1292.5	1291.1	1289.6
15°	1259.2	1258.0	1256.8	1255.2	1253.5	1251.8	1250.1	1248.4
17.5°	1214.7	1212.1	1209.5	1206.9	1204.4	1201.8	1199.2	1196.6
20°	1184.2	1181.0	1177.9	1174.8	1171.8	1168.8	1165.9	1162.9
22.5°	1151.6	1147.6	1143.6	1140.2	1137.5	1134.7	1132.0	1129.2
25°	1098.2	1093.0	1087.9	1083.9	1081.2	1078.5	1075.8	1073.0
27.5°	1040.0	1032.8	1025.6	1019.9	1015.8	1011.6	1007.5	1003.4
30°	998.6	990.2	981.8	975.7	971.7	967.8	963.8	959.9
32.5°	957.9	948.8	939.6	932.9	928.8	924.6	920.5	916.3
35°	897.6	887.0	876.4	868.9	864.5	860.0	855.6	851.1
37.5°	832.8	820.8	808.8	800.0	794.5	789.0	783.6	778.1
40°	787.7	774.9	762.1	752.8	747.1	741.5	735.8	730.2
42.5°	744.5	730.5	716.5	706.9	701.9	696.8	691.7	686.6
45°	680.9	666.9	652.8	642.9	636.9	631.0	625.1	619.2
47.5°	615.2	600.0	584.7	574.4	569.1	563.9	558.6	553.3
50°	570.9	555.5	540.3	529.8	524.2	518.4	512.8	507.1
52.5°	528.0	512.1	496.2	485.7	480.6	475.6	470.5	465.4
55°	464.1	449.8	435.5	425.8	420.9	416.0	411.1	406.1
57.5°	401.3	387.8	374.3	365.4	361.3	357.0	352.9	348.6
60°	361.7	348.5	335.1	326.4	322.2	318.0	313.8	309.6
62.5°	322.5	310.0	297.4	288.9	284.6	280.2	275.8	271.4
65°	266.6	254.5	242.4	235.0	232.3	229.6	226.9	224.1
67.5°	213.2	204.2	195.2	189.1	186.3	183.4	180.4	177.6
70°	180.3	171.6	163.0	157.4	154.6	151.9	149.2	146.5
72.5°	150.6	143.5	136.5	132.4	131.3	130.1	129.0	127.8
75°	112.7	110.2	107.8	106.3	105.8	105.3	104.8	104.3
77.5°	85.0	83.6	82.3	81.4	81.0	80.5	80.0	79.5
80°	68.4	67.7	66.9	66.4	65.9	65.4	64.8	64.3
82.5°	52.4	51.7	51.0	50.5	50.5	50.4	50.2	50.1
85°	30.1	29.6	29.1	28.9	28.9	28.9	28.9	28.9
87.5°	15.9	15.9	15.9	16.1	15.7	15.7	15.7	15.2
90°	23.6	24.6	25.6	27.5	26.5	27.5	28.5	27.5
92.5°	79.7	63.3	55.8	51.0	49.2	46.4	47.4	45.7
95°	341.0	231.1	180.9	146.8	128.8	120.3	113.7	109.9
97.5°	850.0	680.9	558.7	445.4	375.5	332.9	307.3	299.1
100°	1116.8	1040.1	929.3	794.8	699.0	629.9	593.0	593.9
102.5°	1205.5	1203.0	1138.4	1053.1	978.7	924.0	893.1	871.3
105°	1231.4	1326.2	1344.2	1319.6	1275.9	1240.0	1209.7	1204.9
107.5°	1156.7	1310.6	1393.6	1427.3	1428.1	1415.9	1405.7	1397.0
110°	1085.6	1259.9	1379.2	1445.5	1472.0	1479.6	1477.7	1475.9



TEST NUMBER: P332359-930

CATALOG NUMBER: S123RDIP-S1000D1195U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	1015.0	1193.2	1326.9	1412.2	1460.7	1484.2	1491.3	1491.8
115°	921.7	1086.5	1225.7	1329.0	1400.0	1441.7	1460.7	1465.4
117.5°	854.0	996.3	1121.4	1226.1	1300.2	1347.9	1375.2	1381.7
120°	818.4	946.3	1060.0	1155.7	1230.4	1283.5	1306.3	1312.0
122.5°	790.4	906.1	1011.5	1100.3	1166.9	1214.6	1239.6	1246.8
125°	753.1	856.3	947.2	1023.0	1083.7	1125.4	1149.0	1155.7
127.5°	720.5	812.5	894.5	963.5	1017.6	1053.1	1074.6	1080.6
130°	700.0	785.3	862.0	926.4	976.6	1010.7	1030.6	1038.2
132.5°	681.1	759.5	831.0	892.3	939.5	973.5	991.2	996.5
135°	655.5	722.8	784.3	838.3	884.8	913.1	930.2	936.9
137.5°	632.2	687.3	740.4	787.2	826.2	855.0	869.4	873.8
140°	618.6	666.8	712.3	753.1	789.0	815.6	830.7	829.8
142.5°	605.7	647.2	686.6	722.0	752.7	776.2	789.8	788.9
145°	590.1	621.4	651.8	679.1	702.9	722.8	730.3	732.2
147.5°	577.5	602.3	626.7	646.2	664.2	677.7	684.9	685.6
150°	568.3	590.1	610.0	628.0	642.2	652.6	658.4	658.4
152.5°	560.0	578.8	596.4	611.4	622.6	632.2	635.6	635.6
155°	547.5	562.6	576.9	588.2	596.8	604.4	606.3	607.2
157.5°	534.3	547.0	557.9	566.8	574.2	579.9	581.4	581.2
160°	526.7	537.1	546.6	553.2	559.9	565.5	565.5	564.6
162.5°	517.6	526.5	535.2	541.0	545.4	550.3	550.3	549.4
165°	505.8	511.5	518.1	522.9	526.7	530.4	529.5	529.5
167.5°	495.6	499.9	503.8	507.2	508.8	511.5	510.5	510.5
170°	488.8	491.6	495.4	497.3	498.2	500.2	499.2	499.2
172.5°	482.7	484.8	487.9	488.9	489.2	491.1	489.3	488.6
175°	474.6	475.5	477.4	477.4	477.4	478.3	477.4	476.5
177.5°	469.4	470.2	471.0	471.0	470.2	471.0	469.4	469.4
180°	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0

(END OF REPORT)