

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332320-930

Luminaire Tested: **S123RDIP-S775D1025U930-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332320-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S775D1025U930-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1025 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5510.4 lumens
Efficiency: N/A
Efficacy: 106.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332320-930

CATALOG NUMBER: S123RDIP-S775D1025U930-4F0-1E-UDD-A4

Luminous Intensity Polar Plot



TEST NUMBER: P332320-930

CATALOG NUMBER: S123RDIP-S775D1025U930-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	106	106	106	106	97	97	97	97	81	81	81		66	66	66		52
1	97	93	89	86	89	86	82	80	71	69	67		58	57	56		46
2	89	82	76	71	81	75	70	66	63	60	56		52	49	47		41
3	81	72	65	60	74	67	61	56	56	52	48		46	43	41		37
4	75	64	57	51	68	59	53	48	50	45	41		42	38	35		34
5	69	58	50	44	63	53	46	41	45	40	36		38	34	31		30
6	63	52	44	38	58	48	41	36	41	36	32		34	30	27		28
7	59	47	39	34	54	44	37	32	37	32	28		31	27	24		26
8	55	43	35	30	50	40	33	28	34	29	25		29	25	22		24
9	51	39	32	27	47	36	30	25	31	26	22		26	22	20		22
10	47	36	29	24	44	33	27	23	29	24	20		24	20	18		20

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10733	10733	10733	10733
5°	12794	10778	9492	10778
10°	15974	10717	8576	10717
15°	18750	10608	7819	10608
20°	20927	10443	7178	10443
25°	20593	10271	6783	10271
30°	14802	10112	6377	10112
35°	9883	9905	6114	9905
40°	7281	9656	5841	9656
45°	6107	9220	5574	9220
50°	5390	8649	5203	8649
55°	4725	7994	4693	7994
60°	4209	7369	4299	7369
65°	3696	6696	4001	6696
70°	2902	6099	3654	6099
75°	2558	5327	3335	5327
80°	2225	4525	3279	4525
85°	1791	3631	3483	3631

TEST NUMBER: P332320-930

CATALOG NUMBER: S123RDIP-S775D1025U930-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	98.1	1.8
10°-20°	306.3	5.6
20°-30°	481.3	8.7
30°-40°	502.1	9.1
40°-50°	429.7	7.8
50°-60°	327.5	5.9
60°-70°	209.9	3.8
70°-80°	101.0	1.8
80°-90°	29.8	0.5
90°-100°	223.7	4.1
100°-110°	633.5	11.5
110°-120°	623.2	11.3
120°-130°	497.1	9.0
130°-140°	391.9	7.1
140°-150°	292.5	5.3
150°-160°	203.9	3.7
160°-170°	119.8	2.2
170°-180°	39.0	0.7
0°-30°	885.7	16.1
0°-40°	1387.8	25.2
0°-60°	2145.0	38.9
0°-90°	2485.8	45.1
90°-120°	1480.5	26.9
90°-150°	2662.0	48.3
90°-180°	3025.0	54.9
0°-180°	5510.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	997	997	997	997	997	
5°	1184	998	878	998	1184	122
15°	1683	952	702	952	1683	477
25°	1734	865	571	865	1734	745
35°	752	754	465	754	752	493
45°	401	606	366	606	401	315
55°	252	426	250	426	252	228
65°	145	263	157	263	145	143
75°	62	128	80	128	62	66
85°	14	29	28	29	14	17
90°	24	2	24	2	24	13
95°	94	28	94	28	94	170
105°	1035	94	1035	94	1035	1021
115°	1259	167	1259	167	1259	1223
125°	993	232	993	232	993	900
135°	805	272	805	272	805	624
145°	629	310	629	310	629	400
155°	522	352	522	352	522	243
165°	455	385	455	385	455	130
175°	409	401	409	401	409	40
180°	402	402	402	402	402	

TEST NUMBER: P332320-930

CATALOG NUMBER: S123RDIP-S775D1025U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1
2.5°	1062.0	1063.4	1058.9	1058.3	1053.1	1051.7	1051.7	1044.6	1040.2	1034.4	1030.9
5°	1184.1	1190.9	1187.5	1179.8	1167.0	1164.0	1155.9	1143.1	1128.6	1110.7	1102.1
7.5°	1336.5	1345.9	1342.3	1330.4	1317.0	1306.2	1283.3	1262.0	1232.2	1206.1	1183.7
10°	1461.5	1451.7	1444.1	1432.5	1420.2	1400.0	1376.1	1343.3	1305.3	1275.5	1242.1
12.5°	1555.1	1553.5	1543.8	1531.9	1514.4	1495.3	1466.0	1426.0	1381.8	1338.6	1300.6
15°	1682.6	1685.2	1678.8	1666.4	1641.7	1607.9	1563.6	1546.9	1483.8	1436.8	1389.8
17.5°	1770.9	1770.4	1769.5	1752.4	1727.1	1703.2	1662.0	1618.2	1561.0	1494.9	1431.6
20°	1826.9	1822.7	1823.5	1804.3	1785.5	1757.8	1717.7	1654.1	1607.1	1530.7	1465.3
22.5°	1825.5	1824.7	1828.0	1821.4	1807.7	1786.5	1754.9	1701.2	1641.3	1564.2	1490.6
25°	1733.9	1730.5	1750.5	1756.1	1777.8	1781.7	1772.3	1742.9	1686.0	1606.6	1515.7
27.5°	1451.2	1449.3	1486.5	1533.1	1592.1	1638.1	1682.5	1703.9	1686.0	1629.2	1538.1
30°	1190.9	1231.0	1249.9	1317.3	1392.4	1482.1	1560.6	1635.2	1653.6	1628.9	1554.1
32.5°	988.8	1023.8	1039.4	1097.3	1167.3	1272.4	1390.2	1495.9	1570.7	1589.6	1544.6
35°	752.1	752.5	788.4	814.0	878.9	986.8	1101.3	1243.0	1383.8	1490.5	1501.6
37.5°	600.1	602.3	623.9	649.5	698.1	755.3	856.0	973.8	1136.5	1300.3	1396.4
40°	518.2	522.0	538.3	563.5	598.4	641.6	720.1	831.1	966.8	1149.1	1298.0
42.5°	465.6	471.8	480.2	499.6	521.3	561.7	625.2	710.9	834.3	1006.7	1178.5
45°	401.2	404.6	411.1	420.0	439.7	467.8	510.5	568.1	670.6	809.3	981.3
47.5°	353.9	352.1	358.9	366.2	379.2	398.4	427.1	474.1	547.1	658.4	804.4
50°	321.9	321.4	326.1	331.7	344.1	358.2	381.6	417.0	475.1	567.3	700.9
52.5°	291.8	293.4	296.8	303.7	312.6	324.0	345.0	370.6	420.4	500.0	611.4
55°	251.8	253.2	257.8	261.6	268.1	279.6	292.9	314.1	348.3	403.8	495.5
57.5°	218.0	217.4	221.9	222.9	230.2	239.5	249.8	266.4	291.1	332.3	394.1
60°	195.5	194.2	198.0	201.1	204.9	212.5	221.1	237.3	257.0	287.2	340.2
62.5°	175.0	174.4	177.2	180.2	183.4	190.4	197.5	210.0	225.5	251.1	293.1
65°	145.1	146.4	147.7	149.0	150.7	154.9	161.8	170.3	181.0	198.9	229.2
67.5°	114.1	115.4	115.8	118.4	122.1	124.7	128.9	136.5	143.9	159.1	176.3
70°	92.2	91.8	92.2	93.5	98.2	102.9	108.4	114.0	118.6	129.3	143.8
72.5°	79.2	78.4	79.6	79.8	82.1	83.4	86.9	92.1	98.2	105.4	115.9
75°	61.5	61.5	61.5	61.5	63.2	64.0	65.3	66.6	68.7	72.2	79.8
77.5°	45.4	45.5	46.1	46.6	46.9	47.4	48.2	49.4	50.2	52.0	55.4
80°	35.9	36.3	35.9	36.3	36.3	37.1	37.6	38.8	39.3	41.4	42.7
82.5°	27.0	26.7	27.0	27.4	27.4	28.3	28.4	29.3	29.4	30.5	31.8
85°	14.5	13.7	14.5	14.1	14.9	14.1	14.5	15.3	15.3	15.8	17.5
87.5°	8.2	9.0	8.2	8.3	8.5	8.5	8.3	8.2	8.7	8.5	8.4
90°	23.6	24.4	23.6	22.7	23.6	22.0	21.2	20.4	19.6	20.4	17.9
92.5°	39.2	40.7	39.9	42.3	43.8	48.0	54.4	68.5	94.4	125.1	137.7
95°	94.4	97.7	103.4	110.7	126.1	155.5	198.6	292.9	391.4	482.6	429.7
97.5°	257.0	264.0	286.0	322.6	382.6	480.0	585.0	730.3	800.1	747.9	547.6
100°	510.3	509.5	541.2	600.6	682.8	798.3	893.6	959.5	931.0	770.7	520.8
102.5°	748.5	767.3	793.8	840.8	904.8	978.0	1033.6	1035.7	937.5	728.4	481.8
105°	1035.2	1039.3	1065.3	1096.2	1133.7	1154.8	1139.4	1057.9	887.9	654.3	433.7
107.5°	1200.2	1207.7	1216.5	1226.9	1226.3	1197.3	1126.0	993.8	801.0	588.9	403.2
110°	1268.0	1269.6	1271.2	1264.7	1241.9	1184.9	1082.4	932.6	746.2	551.8	391.4

TEST NUMBER: P332320-930

CATALOG NUMBER: S123RDIP-S775D1025U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1281.6	1281.2	1275.0	1254.9	1213.2	1140.0	1025.1	872.0	698.7	527.0	384.9
115°	1259.0	1254.9	1238.6	1202.8	1141.7	1053.0	933.4	791.8	641.3	500.5	382.5
117.5°	1187.0	1181.5	1158.1	1117.0	1053.4	963.4	856.0	733.8	606.6	484.9	383.9
120°	1127.2	1122.3	1102.7	1057.1	992.9	910.7	813.0	703.1	588.4	477.7	386.5
122.5°	1071.1	1064.9	1043.5	1002.5	945.3	869.0	778.5	679.1	573.4	473.1	391.1
125°	992.9	987.2	966.8	931.0	878.9	813.8	735.7	647.0	554.2	467.2	397.9
127.5°	928.4	923.2	904.8	874.2	827.8	768.6	698.1	619.0	537.3	464.2	405.8
130°	891.9	885.4	868.4	839.0	795.9	740.5	674.7	601.4	528.2	462.3	411.0
132.5°	856.1	851.6	836.4	807.1	766.6	713.9	652.5	585.1	519.7	461.6	414.9
135°	804.9	799.2	784.5	760.1	720.2	673.8	620.9	563.1	508.7	460.6	420.8
137.5°	750.6	746.9	734.6	709.8	676.3	636.1	590.5	543.2	499.0	458.9	424.6
140°	712.9	713.7	700.7	677.9	647.0	612.0	572.9	531.4	493.2	458.2	427.2
142.5°	677.8	678.6	666.8	646.7	620.3	589.9	556.0	520.3	488.0	456.9	429.2
145°	629.1	627.5	620.9	603.8	583.5	559.9	533.9	507.0	480.9	454.9	430.5
147.5°	589.1	588.4	582.2	570.6	555.2	538.4	517.4	496.1	474.1	451.8	430.5
150°	565.6	565.6	560.7	551.8	539.6	524.1	507.0	488.3	469.5	449.2	430.5
152.5°	546.1	546.1	543.2	534.8	525.2	512.4	497.3	481.1	464.4	446.0	428.5
155°	521.6	520.8	519.2	512.7	505.4	495.6	483.4	470.3	456.6	440.3	426.4
157.5°	499.4	499.5	498.2	493.3	487.0	479.3	469.9	459.0	447.8	435.2	423.7
160°	485.0	485.8	485.8	480.9	475.2	469.5	461.5	452.5	441.9	431.3	422.4
162.5°	472.0	472.8	472.8	468.6	464.9	459.8	452.3	444.7	436.0	427.4	419.8
165°	454.9	454.9	455.8	452.5	449.2	445.2	439.4	434.6	428.0	421.6	415.9
167.5°	438.6	438.6	439.4	437.2	435.7	432.8	429.5	425.7	420.4	415.7	412.0
170°	428.8	428.8	429.7	428.0	427.2	425.6	422.4	420.0	415.9	411.8	409.4
172.5°	419.8	420.4	421.9	420.3	420.1	419.1	416.5	414.7	411.3	408.5	407.4
175°	409.4	410.2	411.0	410.2	410.2	410.2	408.5	407.7	406.1	404.5	404.5
177.5°	403.3	403.3	404.6	404.0	404.6	404.6	404.0	403.3	402.7	402.0	402.7
180°	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0

TEST NUMBER: P332320-930

CATALOG NUMBER: S123RDIP-S775D1025U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1
2.5°	1029.6	1028.5	1023.8	1018.3	1011.1	1006.3	1002.6	1000.5	994.4	986.8	981.8
5°	1093.2	1080.4	1066.7	1050.0	1034.7	1018.9	1009.1	997.5	983.5	967.7	956.6
7.5°	1161.3	1136.2	1109.1	1081.2	1053.6	1028.9	1007.1	988.3	965.9	943.2	927.4
10°	1213.6	1176.8	1138.8	1100.0	1064.5	1031.3	1005.7	980.5	953.6	927.6	907.9
12.5°	1261.0	1212.7	1168.9	1121.2	1075.9	1036.1	999.1	969.6	937.2	909.5	887.0
15°	1321.1	1271.6	1218.6	1146.1	1085.9	1035.5	990.8	951.9	912.6	878.5	856.7
17.5°	1377.3	1302.8	1231.7	1171.1	1092.9	1030.0	975.3	928.8	885.7	849.5	822.7
20°	1400.5	1328.4	1251.1	1173.9	1097.0	1026.5	963.0	911.7	866.9	826.0	801.2
22.5°	1414.5	1332.8	1251.4	1168.4	1086.8	1013.6	950.7	894.3	845.8	806.8	776.2
25°	1430.8	1333.5	1243.8	1161.9	1078.6	999.2	924.5	864.8	812.3	770.9	738.4
27.5°	1441.5	1327.1	1221.2	1130.0	1045.6	966.5	898.1	834.8	781.5	737.7	702.9
30°	1443.6	1321.9	1203.7	1105.1	1019.3	946.7	874.2	813.6	757.2	710.7	678.2
32.5°	1446.3	1309.3	1180.1	1075.4	987.6	915.7	849.9	792.1	734.3	688.5	655.4
35°	1435.1	1302.4	1144.4	1024.0	936.0	866.5	807.1	753.8	697.1	652.6	618.9
37.5°	1386.6	1274.6	1107.3	966.1	874.2	809.8	761.4	714.9	662.8	614.9	583.2
40°	1337.7	1247.2	1078.6	931.0	834.9	768.7	725.2	687.2	636.8	592.1	557.9
42.5°	1265.0	1210.1	1051.3	894.1	790.5	726.8	690.1	654.4	610.3	564.8	532.6
45°	1131.6	1138.8	995.4	835.4	729.0	665.0	630.5	605.7	566.5	528.9	496.0
47.5°	964.3	1032.1	929.8	772.7	664.2	604.1	574.0	552.4	525.9	489.0	459.0
50°	855.0	951.9	877.2	730.8	623.6	563.9	534.0	516.5	493.4	464.4	435.8
52.5°	754.2	858.3	813.7	684.0	579.6	525.0	495.8	481.4	463.0	435.7	409.9
55°	615.1	720.6	710.3	613.3	513.5	464.4	442.2	426.0	413.6	393.1	372.7
57.5°	497.6	597.5	602.8	534.8	455.3	406.8	387.7	375.4	367.4	351.9	333.0
60°	423.5	515.2	533.1	481.9	413.6	371.0	352.1	342.3	335.9	323.6	309.1
62.5°	362.0	440.1	460.4	423.5	373.7	333.7	319.0	309.6	305.2	294.5	281.7
65°	277.0	341.9	361.5	341.0	315.0	283.0	271.1	262.9	259.1	253.2	243.7
67.5°	208.3	255.6	277.1	262.7	253.3	233.1	225.4	221.1	217.7	213.6	205.8
70°	167.3	202.4	224.5	220.7	213.0	202.4	196.8	193.8	190.4	186.9	180.1
72.5°	134.5	158.7	179.4	181.4	175.1	172.9	168.1	166.8	164.8	160.7	156.9
75°	89.2	105.8	120.3	125.9	128.5	130.6	128.5	128.1	127.6	124.3	122.1
77.5°	58.5	67.4	76.6	86.0	90.1	92.9	93.7	95.2	94.1	92.3	91.2
80°	44.8	47.0	53.3	61.5	67.8	70.4	72.2	73.0	72.6	72.2	70.4
82.5°	32.5	34.3	37.3	43.0	48.4	52.7	53.7	53.6	54.5	54.7	53.3
85°	17.5	17.9	18.8	19.6	22.6	27.3	28.6	29.4	30.3	30.3	27.7
87.5°	8.6	7.7	7.9	7.6	8.3	8.2	9.9	11.3	11.9	10.8	11.3
90°	15.5	13.0	10.6	9.0	7.3	4.9	3.3	1.6	3.3	4.9	7.3
92.5°	103.4	68.3	47.0	35.0	28.1	21.9	15.0	10.1	15.0	21.9	28.1
95°	296.2	175.0	105.8	74.0	52.9	39.1	30.1	27.6	30.1	39.1	52.9
97.5°	325.1	188.3	122.2	87.9	67.0	55.0	48.0	47.2	48.0	55.0	67.0
100°	306.8	186.4	129.4	97.7	78.1	66.8	61.1	60.3	61.1	66.8	78.1
102.5°	291.1	189.0	137.9	108.8	91.2	80.4	75.3	73.9	75.3	80.4	91.2
105°	280.0	196.2	152.2	126.9	111.5	101.7	96.9	94.4	96.9	101.7	111.5
107.5°	279.2	209.5	170.9	147.5	133.0	123.4	118.6	116.2	118.6	123.4	133.0
110°	282.4	220.5	183.9	161.1	147.3	138.4	134.3	131.8	134.3	138.4	147.3

TEST NUMBER: P332320-930

CATALOG NUMBER: S123RDIP-S775D1025U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	288.9	231.6	197.6	175.5	161.6	152.7	148.6	146.2	148.6	152.7	161.6
115°	299.5	249.8	218.9	197.0	183.1	175.0	170.1	166.8	170.1	175.0	183.1
117.5°	313.5	269.2	238.6	218.3	202.8	195.3	191.3	187.5	191.3	195.3	202.8
120°	323.9	281.6	252.3	232.0	216.5	208.3	204.2	201.8	204.2	208.3	216.5
122.5°	333.7	294.6	266.0	244.3	229.5	220.7	216.6	214.2	216.6	220.7	229.5
125°	349.1	313.3	284.9	262.9	247.4	238.5	233.6	232.0	233.6	238.5	247.4
127.5°	361.8	329.6	302.1	280.1	263.0	253.9	247.9	245.5	247.9	253.9	263.0
130°	370.3	339.3	312.5	290.5	273.5	263.7	256.3	253.9	256.3	263.7	273.5
132.5°	378.1	347.8	321.6	300.3	283.2	271.5	263.5	260.4	263.5	271.5	283.2
135°	388.2	360.5	335.3	313.3	296.2	284.1	275.1	271.8	275.1	284.1	296.2
137.5°	395.7	369.3	345.0	324.7	307.8	294.7	286.0	282.6	286.0	294.7	307.8
140°	399.6	375.2	351.6	331.3	315.0	301.9	293.8	289.8	293.8	301.9	315.0
142.5°	403.5	379.8	356.8	337.7	321.5	309.7	300.9	297.5	300.9	309.7	321.5
145°	407.7	385.7	364.6	345.8	332.1	319.8	312.5	310.1	312.5	319.8	332.1
147.5°	410.3	390.6	371.3	355.3	341.9	331.4	324.2	322.8	324.2	331.4	341.9
150°	411.0	393.9	375.2	360.5	349.1	338.5	332.1	331.3	332.1	338.5	349.1
152.5°	412.3	395.8	379.8	365.7	355.6	346.3	339.8	339.7	339.8	346.3	355.6
155°	412.6	399.6	385.7	374.4	365.4	357.3	352.4	352.4	352.4	357.3	365.4
157.5°	413.4	401.7	390.6	381.8	374.2	367.0	363.1	362.5	363.1	367.0	374.2
160°	413.4	403.7	393.9	385.7	380.0	373.6	370.3	370.3	370.3	373.6	380.0
162.5°	412.8	404.3	395.8	389.0	383.9	378.8	376.2	376.2	376.2	378.8	383.9
165°	411.0	405.3	398.8	393.1	389.8	385.7	384.1	384.9	384.1	385.7	389.8
167.5°	409.7	405.1	400.4	396.8	394.5	391.4	390.6	391.6	390.6	391.4	394.5
170°	407.7	404.5	400.4	398.8	397.1	394.7	393.9	395.5	393.9	394.7	397.1
172.5°	407.1	404.5	401.0	400.1	399.1	397.3	397.1	398.1	397.1	397.3	399.1
175°	405.3	403.7	402.0	401.2	401.2	399.6	400.4	401.2	400.4	399.6	401.2
177.5°	404.0	402.7	402.0	402.0	402.0	401.4	402.0	402.7	402.0	401.4	402.0
180°	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0

TEST NUMBER: P332320-930

CATALOG NUMBER: S123RDIP-S775D1025U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1
2.5°	980.1	975.6	972.6	965.7	961.2	956.5	951.7	954.8	954.5	954.1	954.1
5°	947.2	937.3	928.4	916.9	909.6	900.7	893.8	893.0	894.7	888.7	885.3
7.5°	914.6	901.2	888.4	875.7	862.3	851.5	844.7	841.6	837.2	833.6	829.7
10°	891.7	875.9	863.5	847.7	833.2	820.4	812.3	806.7	803.7	800.8	795.2
12.5°	868.1	852.6	836.9	819.0	805.2	790.4	784.3	778.0	772.3	769.0	761.4
15°	833.6	813.6	797.0	778.1	762.8	748.3	739.7	727.3	725.6	721.4	713.7
17.5°	799.1	777.3	754.3	740.5	723.1	708.0	695.0	690.8	678.6	674.0	667.3
20°	771.8	751.7	734.2	715.8	690.6	676.5	666.3	660.8	650.9	645.0	640.7
22.5°	748.2	727.8	707.5	686.2	665.4	649.5	642.0	633.4	628.1	619.7	615.1
25°	714.5	692.4	668.1	645.0	630.1	618.1	606.1	598.4	590.8	586.9	578.4
27.5°	675.5	652.2	629.5	612.0	593.7	581.9	571.0	564.2	555.0	548.5	543.8
30°	654.0	626.6	607.0	591.2	567.7	556.6	548.5	540.0	533.1	526.3	521.6
32.5°	629.0	604.1	585.5	565.9	547.9	535.8	525.3	517.8	511.9	505.5	500.8
35°	589.9	569.0	549.8	530.1	516.9	504.5	492.2	485.8	480.2	474.3	469.9
37.5°	554.6	535.0	516.7	498.1	481.8	471.7	461.7	456.8	449.3	445.3	440.9
40°	532.7	513.5	493.8	476.0	458.9	451.2	442.2	435.0	428.1	425.2	420.4
42.5°	508.8	489.6	473.0	453.7	439.8	429.3	421.0	413.1	408.0	403.7	401.0
45°	473.4	456.3	440.1	420.9	407.6	398.7	389.3	382.0	377.3	374.4	369.7
47.5°	439.0	421.9	405.4	388.7	375.9	365.7	356.3	351.2	345.0	341.3	338.2
50°	414.0	398.7	381.2	365.8	353.0	342.8	335.1	328.6	323.1	318.5	316.3
52.5°	391.2	374.8	359.6	345.4	331.8	320.2	313.2	306.5	302.3	296.9	294.4
55°	353.4	337.6	324.8	310.7	297.5	287.7	279.2	273.2	268.9	262.9	259.5
57.5°	318.0	303.9	288.5	276.3	262.7	254.4	247.3	239.2	234.0	229.3	226.0
60°	294.1	277.9	264.6	253.2	241.2	230.5	224.1	217.7	212.1	207.4	204.5
62.5°	269.2	255.0	242.5	229.9	219.0	209.7	202.3	196.9	192.0	189.0	186.1
65°	230.9	219.8	207.0	196.8	186.5	179.7	173.7	169.0	165.6	163.5	160.9
67.5°	195.8	185.0	173.8	163.7	156.9	151.7	147.8	143.7	142.0	139.3	137.6
70°	172.8	161.8	152.0	144.3	137.5	133.6	131.0	128.1	126.4	122.9	121.2
72.5°	148.0	139.9	132.8	126.5	121.1	117.6	114.3	110.6	107.9	104.1	102.5
75°	116.5	109.3	103.7	99.5	96.0	91.3	86.7	82.8	81.5	80.2	79.8
77.5°	86.3	81.7	77.7	74.1	69.9	66.4	65.4	64.6	64.2	63.6	63.6
80°	67.8	63.6	60.6	56.3	53.8	53.8	53.8	52.9	53.3	53.3	53.3
82.5°	50.5	46.6	44.9	43.4	42.9	43.2	43.2	43.4	43.1	43.8	43.5
85°	26.0	26.5	27.3	26.9	27.3	27.3	28.2	27.7	28.2	27.3	28.2
87.5°	11.3	12.7	13.5	14.3	15.2	15.3	15.5	15.7	16.1	16.3	16.6
90°	9.0	10.6	13.0	15.5	17.9	20.4	19.6	20.4	21.2	22.0	23.6
92.5°	35.0	47.0	68.3	103.4	137.7	125.1	94.4	68.5	54.4	48.0	43.8
95°	74.0	105.8	175.0	296.2	429.7	482.6	391.4	292.9	198.6	155.5	126.1
97.5°	87.9	122.2	188.3	325.1	547.6	747.9	800.1	730.3	585.0	480.0	382.6
100°	97.7	129.4	186.4	306.8	520.8	770.7	931.0	959.5	893.6	798.3	682.8
102.5°	108.8	137.9	189.0	291.1	481.8	728.4	937.5	1035.7	1033.6	978.0	904.8
105°	126.9	152.2	196.2	280.0	433.7	654.3	887.9	1057.9	1139.4	1154.8	1133.7
107.5°	147.5	170.9	209.5	279.2	403.2	588.9	801.0	993.8	1126.0	1197.3	1226.3
110°	161.1	183.9	220.5	282.4	391.4	551.8	746.2	932.6	1082.4	1184.9	1241.9

TEST NUMBER: P332320-930

CATALOG NUMBER: S123RDIP-S775D1025U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	175.5	197.6	231.6	288.9	384.9	527.0	698.7	872.0	1025.1	1140.0	1213.2
115°	197.0	218.9	249.8	299.5	382.5	500.5	641.3	791.8	933.4	1053.0	1141.7
117.5°	218.3	238.6	269.2	313.5	383.9	484.9	606.6	733.8	856.0	963.4	1053.4
120°	232.0	252.3	281.6	323.9	386.5	477.7	588.4	703.1	813.0	910.7	992.9
122.5°	244.3	266.0	294.6	333.7	391.1	473.1	573.4	679.1	778.5	869.0	945.3
125°	262.9	284.9	313.3	349.1	397.9	467.2	554.2	647.0	735.7	813.8	878.9
127.5°	280.1	302.1	329.6	361.8	405.8	464.2	537.3	619.0	698.1	768.6	827.8
130°	290.5	312.5	339.3	370.3	411.0	462.3	528.2	601.4	674.7	740.5	795.9
132.5°	300.3	321.6	347.8	378.1	414.9	461.6	519.7	585.1	652.5	713.9	766.6
135°	313.3	335.3	360.5	388.2	420.8	460.6	508.7	563.1	620.9	673.8	720.2
137.5°	324.7	345.0	369.3	395.7	424.6	458.9	499.0	543.2	590.5	636.1	676.3
140°	331.3	351.6	375.2	399.6	427.2	458.2	493.2	531.4	572.9	612.0	647.0
142.5°	337.7	356.8	379.8	403.5	429.2	456.9	488.0	520.3	556.0	589.9	620.3
145°	345.8	364.6	385.7	407.7	430.5	454.9	480.9	507.0	533.9	559.9	583.5
147.5°	355.3	371.3	390.6	410.3	430.5	451.8	474.1	496.1	517.4	538.4	555.2
150°	360.5	375.2	393.9	411.0	430.5	449.2	469.5	488.3	507.0	524.1	539.6
152.5°	365.7	379.8	395.8	412.3	428.5	446.0	464.4	481.1	497.3	512.4	525.2
155°	374.4	385.7	399.6	412.6	426.4	440.3	456.6	470.3	483.4	495.6	505.4
157.5°	381.8	390.6	401.7	413.4	423.7	435.2	447.8	459.0	469.9	479.3	487.0
160°	385.7	393.9	403.7	413.4	422.4	431.3	441.9	452.5	461.5	469.5	475.2
162.5°	389.0	395.8	404.3	412.8	419.8	427.4	436.0	444.7	452.3	459.8	464.9
165°	393.1	398.8	405.3	411.0	415.9	421.6	428.0	434.6	439.4	445.2	449.2
167.5°	396.8	400.4	405.1	409.7	412.0	415.7	420.4	425.7	429.5	432.8	435.7
170°	398.8	400.4	404.5	407.7	409.4	411.8	415.9	420.0	422.4	425.6	427.2
172.5°	400.1	401.0	404.5	407.1	407.4	408.5	411.3	414.7	416.5	419.1	420.1
175°	401.2	402.0	403.7	405.3	404.5	404.5	406.1	407.7	408.5	410.2	410.2
177.5°	402.0	402.0	402.7	404.0	402.7	402.0	402.7	403.3	404.0	404.6	404.6
180°	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0

TEST NUMBER: P332320-930

CATALOG NUMBER: S123RDIP-S775D1025U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1
2.5°	950.0	949.7	950.0	948.6	950.0	949.7	950.0	954.1	954.1	954.5	954.8
5°	884.0	883.5	882.3	878.5	882.3	883.5	884.0	885.3	888.7	894.7	893.0
7.5°	826.4	825.8	822.1	822.1	822.1	825.8	826.4	829.7	833.6	837.2	841.6
10°	792.2	792.6	787.6	784.6	787.6	792.6	792.2	795.2	800.8	803.7	806.7
12.5°	759.1	757.2	753.0	749.7	753.0	757.2	759.1	761.4	769.0	772.3	778.0
15°	715.4	711.1	700.9	701.7	700.9	711.1	715.4	713.7	721.4	725.6	727.3
17.5°	663.9	660.8	660.6	654.6	660.6	660.8	663.9	667.3	674.0	678.6	690.8
20°	633.9	631.8	632.6	626.6	632.6	631.8	633.9	640.7	645.0	650.9	660.8
22.5°	610.3	608.2	604.6	602.8	604.6	608.2	610.3	615.1	619.7	628.1	633.4
25°	575.8	572.4	569.0	571.1	569.0	572.4	575.8	578.4	586.9	590.8	598.4
27.5°	541.4	538.7	535.3	534.9	535.3	538.7	541.4	543.8	548.5	555.0	564.2
30°	519.5	516.9	515.2	513.1	515.2	516.9	519.5	521.6	526.3	533.1	540.0
32.5°	497.3	496.8	493.7	493.3	493.7	496.8	497.3	500.8	505.5	511.9	517.8
35°	468.2	465.7	464.8	465.3	464.8	465.7	468.2	469.9	474.3	480.2	485.8
37.5°	440.7	437.2	435.7	434.2	435.7	437.2	440.7	440.9	445.3	449.3	456.8
40°	420.9	417.4	416.6	415.7	416.6	417.4	420.9	420.4	425.2	428.1	435.0
42.5°	398.7	397.3	396.8	395.3	396.8	397.3	398.7	401.0	403.7	408.0	413.1
45°	368.4	367.9	365.4	366.2	365.4	367.9	368.4	369.7	374.4	377.3	382.0
47.5°	336.5	334.6	332.8	333.9	332.8	334.6	336.5	338.2	341.3	345.0	351.2
50°	314.6	313.7	309.9	310.7	309.9	313.7	314.6	316.3	318.5	323.1	328.6
52.5°	292.8	289.5	288.0	287.6	288.0	289.5	292.8	294.4	296.9	302.3	306.5
55°	256.6	252.7	250.9	250.1	250.9	252.7	256.6	259.5	262.9	268.9	273.2
57.5°	221.0	220.0	218.7	219.6	218.7	220.0	221.0	226.0	229.3	234.0	239.2
60°	200.2	200.2	200.2	199.7	200.2	200.2	200.2	204.5	207.4	212.1	217.7
62.5°	184.2	183.1	182.8	183.4	182.8	183.1	184.2	186.1	189.0	192.0	196.9
65°	159.6	159.2	157.5	157.1	157.5	159.2	159.6	160.9	163.5	165.6	169.0
67.5°	136.5	134.9	134.4	133.9	134.4	134.9	136.5	137.6	139.3	142.0	143.7
70°	119.1	118.2	115.7	116.1	115.7	118.2	119.1	121.2	122.9	126.4	128.1
72.5°	100.3	99.5	99.0	98.3	99.0	99.5	100.3	102.5	104.1	107.9	110.6
75°	79.4	79.0	78.5	80.2	78.5	79.0	79.4	79.8	80.2	81.5	82.8
77.5°	63.6	63.6	63.8	63.2	63.8	63.6	63.6	63.6	63.6	64.2	64.6
80°	53.3	53.3	52.9	52.9	52.9	53.3	53.3	53.3	53.3	53.3	52.9
82.5°	42.8	43.1	43.4	42.7	43.4	43.1	42.8	43.5	43.8	43.1	43.4
85°	28.2	27.7	28.6	28.2	28.6	27.7	28.2	28.2	27.3	28.2	27.7
87.5°	17.2	16.6	16.8	17.0	16.8	16.6	17.2	16.6	16.3	16.1	15.7
90°	22.7	23.6	24.4	23.6	24.4	23.6	22.7	23.6	22.0	21.2	20.4
92.5°	42.3	39.9	40.7	39.2	40.7	39.9	42.3	43.8	48.0	54.4	68.5
95°	110.7	103.4	97.7	94.4	97.7	103.4	110.7	126.1	155.5	198.6	292.9
97.5°	322.6	286.0	264.0	257.0	264.0	286.0	322.6	382.6	480.0	585.0	730.3
100°	600.6	541.2	509.5	510.3	509.5	541.2	600.6	682.8	798.3	893.6	959.5
102.5°	840.8	793.8	767.3	748.5	767.3	793.8	840.8	904.8	978.0	1033.6	1035.7
105°	1096.2	1065.3	1039.3	1035.2	1039.3	1065.3	1096.2	1133.7	1154.8	1139.4	1057.9
107.5°	1226.9	1216.5	1207.7	1200.2	1207.7	1216.5	1226.9	1226.3	1197.3	1126.0	993.8
110°	1264.7	1271.2	1269.6	1268.0	1269.6	1271.2	1264.7	1241.9	1184.9	1082.4	932.6

TEST NUMBER: P332320-930

CATALOG NUMBER: S123RDIP-S775D1025U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1254.9	1275.0	1281.2	1281.6	1281.2	1275.0	1254.9	1213.2	1140.0	1025.1	872.0
115°	1202.8	1238.6	1254.9	1259.0	1254.9	1238.6	1202.8	1141.7	1053.0	933.4	791.8
117.5°	1117.0	1158.1	1181.5	1187.0	1181.5	1158.1	1117.0	1053.4	963.4	856.0	733.8
120°	1057.1	1102.7	1122.3	1127.2	1122.3	1102.7	1057.1	992.9	910.7	813.0	703.1
122.5°	1002.5	1043.5	1064.9	1071.1	1064.9	1043.5	1002.5	945.3	869.0	778.5	679.1
125°	931.0	966.8	987.2	992.9	987.2	966.8	931.0	878.9	813.8	735.7	647.0
127.5°	874.2	904.8	923.2	928.4	923.2	904.8	874.2	827.8	768.6	698.1	619.0
130°	839.0	868.4	885.4	891.9	885.4	868.4	839.0	795.9	740.5	674.7	601.4
132.5°	807.1	836.4	851.6	856.1	851.6	836.4	807.1	766.6	713.9	652.5	585.1
135°	760.1	784.5	799.2	804.9	799.2	784.5	760.1	720.2	673.8	620.9	563.1
137.5°	709.8	734.6	746.9	750.6	746.9	734.6	709.8	676.3	636.1	590.5	543.2
140°	677.9	700.7	713.7	712.9	713.7	700.7	677.9	647.0	612.0	572.9	531.4
142.5°	646.7	666.8	678.6	677.8	678.6	666.8	646.7	620.3	589.9	556.0	520.3
145°	603.8	620.9	627.5	629.1	627.5	620.9	603.8	583.5	559.9	533.9	507.0
147.5°	570.6	582.2	588.4	589.1	588.4	582.2	570.6	555.2	538.4	517.4	496.1
150°	551.8	560.7	565.6	565.6	565.6	560.7	551.8	539.6	524.1	507.0	488.3
152.5°	534.8	543.2	546.1	546.1	546.1	543.2	534.8	525.2	512.4	497.3	481.1
155°	512.7	519.2	520.8	521.6	520.8	519.2	512.7	505.4	495.6	483.4	470.3
157.5°	493.3	498.2	499.5	499.4	499.5	498.2	493.3	487.0	479.3	469.9	459.0
160°	480.9	485.8	485.8	485.0	485.8	485.8	480.9	475.2	469.5	461.5	452.5
162.5°	468.6	472.8	472.8	472.0	472.8	472.8	468.6	464.9	459.8	452.3	444.7
165°	452.5	455.8	454.9	454.9	454.9	455.8	452.5	449.2	445.2	439.4	434.6
167.5°	437.2	439.4	438.6	438.6	438.6	439.4	437.2	435.7	432.8	429.5	425.7
170°	428.0	429.7	428.8	428.8	428.8	429.7	428.0	427.2	425.6	422.4	420.0
172.5°	420.3	421.9	420.4	419.8	420.4	421.9	420.3	420.1	419.1	416.5	414.7
175°	410.2	411.0	410.2	409.4	410.2	411.0	410.2	410.2	410.2	408.5	407.7
177.5°	404.0	404.6	403.3	403.3	403.3	404.6	404.0	404.6	404.6	404.0	403.3
180°	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0

TEST NUMBER: P332320-930

CATALOG NUMBER: S123RDIP-S775D1025U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1
2.5°	951.7	956.5	961.2	965.7	972.6	975.6	980.1	981.8	986.8	994.4	1000.5
5°	893.8	900.7	909.6	916.9	928.4	937.3	947.2	956.6	967.7	983.5	997.5
7.5°	844.7	851.5	862.3	875.7	888.4	901.2	914.6	927.4	943.2	965.9	988.3
10°	812.3	820.4	833.2	847.7	863.5	875.9	891.7	907.9	927.6	953.6	980.5
12.5°	784.3	790.4	805.2	819.0	836.9	852.6	868.1	887.0	909.5	937.2	969.6
15°	739.7	748.3	762.8	778.1	797.0	813.6	833.6	856.7	878.5	912.6	951.9
17.5°	695.0	708.0	723.1	740.5	754.3	777.3	799.1	822.7	849.5	885.7	928.8
20°	666.3	676.5	690.6	715.8	734.2	751.7	771.8	801.2	826.0	866.9	911.7
22.5°	642.0	649.5	665.4	686.2	707.5	727.8	748.2	776.2	806.8	845.8	894.3
25°	606.1	618.1	630.1	645.0	668.1	692.4	714.5	738.4	770.9	812.3	864.8
27.5°	571.0	581.9	593.7	612.0	629.5	652.2	675.5	702.9	737.7	781.5	834.8
30°	548.5	556.6	567.7	591.2	607.0	626.6	654.0	678.2	710.7	757.2	813.6
32.5°	525.3	535.8	547.9	565.9	585.5	604.1	629.0	655.4	688.5	734.3	792.1
35°	492.2	504.5	516.9	530.1	549.8	569.0	589.9	618.9	652.6	697.1	753.8
37.5°	461.7	471.7	481.8	498.1	516.7	535.0	554.6	583.2	614.9	662.8	714.9
40°	442.2	451.2	458.9	476.0	493.8	513.5	532.7	557.9	592.1	636.8	687.2
42.5°	421.0	429.3	439.8	453.7	473.0	489.6	508.8	532.6	564.8	610.3	654.4
45°	389.3	398.7	407.6	420.9	440.1	456.3	473.4	496.0	528.9	566.5	605.7
47.5°	356.3	365.7	375.9	388.7	405.4	421.9	439.0	459.0	489.0	525.9	552.4
50°	335.1	342.8	353.0	365.8	381.2	398.7	414.0	435.8	464.4	493.4	516.5
52.5°	313.2	320.2	331.8	345.4	359.6	374.8	391.2	409.9	435.7	463.0	481.4
55°	279.2	287.7	297.5	310.7	324.8	337.6	353.4	372.7	393.1	413.6	426.0
57.5°	247.3	254.4	262.7	276.3	288.5	303.9	318.0	333.0	351.9	367.4	375.4
60°	224.1	230.5	241.2	253.2	264.6	277.9	294.1	309.1	323.6	335.9	342.3
62.5°	202.3	209.7	219.0	229.9	242.5	255.0	269.2	281.7	294.5	305.2	309.6
65°	173.7	179.7	186.5	196.8	207.0	219.8	230.9	243.7	253.2	259.1	262.9
67.5°	147.8	151.7	156.9	163.7	173.8	185.0	195.8	205.8	213.6	217.7	221.1
70°	131.0	133.6	137.5	144.3	152.0	161.8	172.8	180.1	186.9	190.4	193.8
72.5°	114.3	117.6	121.1	126.5	132.8	139.9	148.0	156.9	160.7	164.8	166.8
75°	86.7	91.3	96.0	99.5	103.7	109.3	116.5	122.1	124.3	127.6	128.1
77.5°	65.4	66.4	69.9	74.1	77.7	81.7	86.3	91.2	92.3	94.1	95.2
80°	53.8	53.8	53.8	56.3	60.6	63.6	67.8	70.4	72.2	72.6	73.0
82.5°	43.2	43.2	42.9	43.4	44.9	46.6	50.5	53.3	54.7	54.5	53.6
85°	28.2	27.3	27.3	26.9	27.3	26.5	26.0	27.7	30.3	30.3	29.4
87.5°	15.5	15.3	15.2	14.3	13.5	12.7	11.3	11.3	10.8	11.9	11.3
90°	19.6	20.4	17.9	15.5	13.0	10.6	9.0	7.3	4.9	3.3	1.6
92.5°	94.4	125.1	137.7	103.4	68.3	47.0	35.0	28.1	21.9	15.0	10.1
95°	391.4	482.6	429.7	296.2	175.0	105.8	74.0	52.9	39.1	30.1	27.6
97.5°	800.1	747.9	547.6	325.1	188.3	122.2	87.9	67.0	55.0	48.0	47.2
100°	931.0	770.7	520.8	306.8	186.4	129.4	97.7	78.1	66.8	61.1	60.3
102.5°	937.5	728.4	481.8	291.1	189.0	137.9	108.8	91.2	80.4	75.3	73.9
105°	887.9	654.3	433.7	280.0	196.2	152.2	126.9	111.5	101.7	96.9	94.4
107.5°	801.0	588.9	403.2	279.2	209.5	170.9	147.5	133.0	123.4	118.6	116.2
110°	746.2	551.8	391.4	282.4	220.5	183.9	161.1	147.3	138.4	134.3	131.8

TEST NUMBER: P332320-930

CATALOG NUMBER: S123RDIP-S775D1025U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	698.7	527.0	384.9	288.9	231.6	197.6	175.5	161.6	152.7	148.6	146.2
115°	641.3	500.5	382.5	299.5	249.8	218.9	197.0	183.1	175.0	170.1	166.8
117.5°	606.6	484.9	383.9	313.5	269.2	238.6	218.3	202.8	195.3	191.3	187.5
120°	588.4	477.7	386.5	323.9	281.6	252.3	232.0	216.5	208.3	204.2	201.8
122.5°	573.4	473.1	391.1	333.7	294.6	266.0	244.3	229.5	220.7	216.6	214.2
125°	554.2	467.2	397.9	349.1	313.3	284.9	262.9	247.4	238.5	233.6	232.0
127.5°	537.3	464.2	405.8	361.8	329.6	302.1	280.1	263.0	253.9	247.9	245.5
130°	528.2	462.3	411.0	370.3	339.3	312.5	290.5	273.5	263.7	256.3	253.9
132.5°	519.7	461.6	414.9	378.1	347.8	321.6	300.3	283.2	271.5	263.5	260.4
135°	508.7	460.6	420.8	388.2	360.5	335.3	313.3	296.2	284.1	275.1	271.8
137.5°	499.0	458.9	424.6	395.7	369.3	345.0	324.7	307.8	294.7	286.0	282.6
140°	493.2	458.2	427.2	399.6	375.2	351.6	331.3	315.0	301.9	293.8	289.8
142.5°	488.0	456.9	429.2	403.5	379.8	356.8	337.7	321.5	309.7	300.9	297.5
145°	480.9	454.9	430.5	407.7	385.7	364.6	345.8	332.1	319.8	312.5	310.1
147.5°	474.1	451.8	430.5	410.3	390.6	371.3	355.3	341.9	331.4	324.2	322.8
150°	469.5	449.2	430.5	411.0	393.9	375.2	360.5	349.1	338.5	332.1	331.3
152.5°	464.4	446.0	428.5	412.3	395.8	379.8	365.7	355.6	346.3	339.8	339.7
155°	456.6	440.3	426.4	412.6	399.6	385.7	374.4	365.4	357.3	352.4	352.4
157.5°	447.8	435.2	423.7	413.4	401.7	390.6	381.8	374.2	367.0	363.1	362.5
160°	441.9	431.3	422.4	413.4	403.7	393.9	385.7	380.0	373.6	370.3	370.3
162.5°	436.0	427.4	419.8	412.8	404.3	395.8	389.0	383.9	378.8	376.2	376.2
165°	428.0	421.6	415.9	411.0	405.3	398.8	393.1	389.8	385.7	384.1	384.9
167.5°	420.4	415.7	412.0	409.7	405.1	400.4	396.8	394.5	391.4	390.6	391.6
170°	415.9	411.8	409.4	407.7	404.5	400.4	398.8	397.1	394.7	393.9	395.5
172.5°	411.3	408.5	407.4	407.1	404.5	401.0	400.1	399.1	397.3	397.1	398.1
175°	406.1	404.5	404.5	405.3	403.7	402.0	401.2	401.2	399.6	400.4	401.2
177.5°	402.7	402.0	402.7	404.0	402.7	402.0	402.0	402.0	401.4	402.0	402.7
180°	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0

TEST NUMBER: P332320-930

CATALOG NUMBER: S123RDIP-S775D1025U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1	997.1
2.5°	1002.6	1006.3	1011.1	1018.3	1023.8	1028.5	1029.6	1030.9	1034.4	1040.2	1044.6
5°	1009.1	1018.9	1034.7	1050.0	1066.7	1080.4	1093.2	1102.1	1110.7	1128.6	1143.1
7.5°	1007.1	1028.9	1053.6	1081.2	1109.1	1136.2	1161.3	1183.7	1206.1	1232.2	1262.0
10°	1005.7	1031.3	1064.5	1100.0	1138.8	1176.8	1213.6	1242.1	1275.5	1305.3	1343.3
12.5°	999.1	1036.1	1075.9	1121.2	1168.9	1212.7	1261.0	1300.6	1338.6	1381.8	1426.0
15°	990.8	1035.5	1085.9	1146.1	1218.6	1271.6	1321.1	1389.8	1436.8	1483.8	1546.9
17.5°	975.3	1030.0	1092.9	1171.1	1231.7	1302.8	1377.3	1431.6	1494.9	1561.0	1618.2
20°	963.0	1026.5	1097.0	1173.9	1251.1	1328.4	1400.5	1465.3	1530.7	1607.1	1654.1
22.5°	950.7	1013.6	1086.8	1168.4	1251.4	1332.8	1414.5	1490.6	1564.2	1641.3	1701.2
25°	924.5	999.2	1078.6	1161.9	1243.8	1333.5	1430.8	1515.7	1606.6	1686.0	1742.9
27.5°	898.1	966.5	1045.6	1130.0	1221.2	1327.1	1441.5	1538.1	1629.2	1686.0	1703.9
30°	874.2	946.7	1019.3	1105.1	1203.7	1321.9	1443.6	1554.1	1628.9	1653.6	1635.2
32.5°	849.9	915.7	987.6	1075.4	1180.1	1309.3	1446.3	1544.6	1589.6	1570.7	1495.9
35°	807.1	866.5	936.0	1024.0	1144.4	1302.4	1435.1	1501.6	1490.5	1383.8	1243.0
37.5°	761.4	809.8	874.2	966.1	1107.3	1274.6	1386.6	1396.4	1300.3	1136.5	973.8
40°	725.2	768.7	834.9	931.0	1078.6	1247.2	1337.7	1298.0	1149.1	966.8	831.1
42.5°	690.1	726.8	790.5	894.1	1051.3	1210.1	1265.0	1178.5	1006.7	834.3	710.9
45°	630.5	665.0	729.0	835.4	995.4	1138.8	1131.6	981.3	809.3	670.6	568.1
47.5°	574.0	604.1	664.2	772.7	929.8	1032.1	964.3	804.4	658.4	547.1	474.1
50°	534.0	563.9	623.6	730.8	877.2	951.9	855.0	700.9	567.3	475.1	417.0
52.5°	495.8	525.0	579.6	684.0	813.7	858.3	754.2	611.4	500.0	420.4	370.6
55°	442.2	464.4	513.5	613.3	710.3	720.6	615.1	495.5	403.8	348.3	314.1
57.5°	387.7	406.8	455.3	534.8	602.8	597.5	497.6	394.1	332.3	291.1	266.4
60°	352.1	371.0	413.6	481.9	533.1	515.2	423.5	340.2	287.2	257.0	237.3
62.5°	319.0	333.7	373.7	423.5	460.4	440.1	362.0	293.1	251.1	225.5	210.0
65°	271.1	283.0	315.0	341.0	361.5	341.9	277.0	229.2	198.9	181.0	170.3
67.5°	225.4	233.1	253.3	262.7	277.1	255.6	208.3	176.3	159.1	143.9	136.5
70°	196.8	202.4	213.0	220.7	224.5	202.4	167.3	143.8	129.3	118.6	114.0
72.5°	168.1	172.9	175.1	181.4	179.4	158.7	134.5	115.9	105.4	98.2	92.1
75°	128.5	130.6	128.5	125.9	120.3	105.8	89.2	79.8	72.2	68.7	66.6
77.5°	93.7	92.9	90.1	86.0	76.6	67.4	58.5	55.4	52.0	50.2	49.4
80°	72.2	70.4	67.8	61.5	53.3	47.0	44.8	42.7	41.4	39.3	38.8
82.5°	53.7	52.7	48.4	43.0	37.3	34.3	32.5	31.8	30.5	29.4	29.3
85°	28.6	27.3	22.6	19.6	18.8	17.9	17.5	17.5	15.8	15.3	15.3
87.5°	9.9	8.2	8.3	7.6	7.9	7.7	8.6	8.4	8.5	8.7	8.2
90°	3.3	4.9	7.3	9.0	10.6	13.0	15.5	17.9	20.4	19.6	20.4
92.5°	15.0	21.9	28.1	35.0	47.0	68.3	103.4	137.7	125.1	94.4	68.5
95°	30.1	39.1	52.9	74.0	105.8	175.0	296.2	429.7	482.6	391.4	292.9
97.5°	48.0	55.0	67.0	87.9	122.2	188.3	325.1	547.6	747.9	800.1	730.3
100°	61.1	66.8	78.1	97.7	129.4	186.4	306.8	520.8	770.7	931.0	959.5
102.5°	75.3	80.4	91.2	108.8	137.9	189.0	291.1	481.8	728.4	937.5	1035.7
105°	96.9	101.7	111.5	126.9	152.2	196.2	280.0	433.7	654.3	887.9	1057.9
107.5°	118.6	123.4	133.0	147.5	170.9	209.5	279.2	403.2	588.9	801.0	993.8
110°	134.3	138.4	147.3	161.1	183.9	220.5	282.4	391.4	551.8	746.2	932.6

TEST NUMBER: P332320-930

CATALOG NUMBER: S123RDIP-S775D1025U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	148.6	152.7	161.6	175.5	197.6	231.6	288.9	384.9	527.0	698.7	872.0
115°	170.1	175.0	183.1	197.0	218.9	249.8	299.5	382.5	500.5	641.3	791.8
117.5°	191.3	195.3	202.8	218.3	238.6	269.2	313.5	383.9	484.9	606.6	733.8
120°	204.2	208.3	216.5	232.0	252.3	281.6	323.9	386.5	477.7	588.4	703.1
122.5°	216.6	220.7	229.5	244.3	266.0	294.6	333.7	391.1	473.1	573.4	679.1
125°	233.6	238.5	247.4	262.9	284.9	313.3	349.1	397.9	467.2	554.2	647.0
127.5°	247.9	253.9	263.0	280.1	302.1	329.6	361.8	405.8	464.2	537.3	619.0
130°	256.3	263.7	273.5	290.5	312.5	339.3	370.3	411.0	462.3	528.2	601.4
132.5°	263.5	271.5	283.2	300.3	321.6	347.8	378.1	414.9	461.6	519.7	585.1
135°	275.1	284.1	296.2	313.3	335.3	360.5	388.2	420.8	460.6	508.7	563.1
137.5°	286.0	294.7	307.8	324.7	345.0	369.3	395.7	424.6	458.9	499.0	543.2
140°	293.8	301.9	315.0	331.3	351.6	375.2	399.6	427.2	458.2	493.2	531.4
142.5°	300.9	309.7	321.5	337.7	356.8	379.8	403.5	429.2	456.9	488.0	520.3
145°	312.5	319.8	332.1	345.8	364.6	385.7	407.7	430.5	454.9	480.9	507.0
147.5°	324.2	331.4	341.9	355.3	371.3	390.6	410.3	430.5	451.8	474.1	496.1
150°	332.1	338.5	349.1	360.5	375.2	393.9	411.0	430.5	449.2	469.5	488.3
152.5°	339.8	346.3	355.6	365.7	379.8	395.8	412.3	428.5	446.0	464.4	481.1
155°	352.4	357.3	365.4	374.4	385.7	399.6	412.6	426.4	440.3	456.6	470.3
157.5°	363.1	367.0	374.2	381.8	390.6	401.7	413.4	423.7	435.2	447.8	459.0
160°	370.3	373.6	380.0	385.7	393.9	403.7	413.4	422.4	431.3	441.9	452.5
162.5°	376.2	378.8	383.9	389.0	395.8	404.3	412.8	419.8	427.4	436.0	444.7
165°	384.1	385.7	389.8	393.1	398.8	405.3	411.0	415.9	421.6	428.0	434.6
167.5°	390.6	391.4	394.5	396.8	400.4	405.1	409.7	412.0	415.7	420.4	425.7
170°	393.9	394.7	397.1	398.8	400.4	404.5	407.7	409.4	411.8	415.9	420.0
172.5°	397.1	397.3	399.1	400.1	401.0	404.5	407.1	407.4	408.5	411.3	414.7
175°	400.4	399.6	401.2	401.2	402.0	403.7	405.3	404.5	404.5	406.1	407.7
177.5°	402.0	401.4	402.0	402.0	402.0	402.7	404.0	402.7	402.0	402.7	403.3
180°	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0

TEST NUMBER: P332320-930

CATALOG NUMBER: S123RDIP-S775D1025U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	997.1	997.1	997.1	997.1	997.1	997.1	997.1
2.5°	1051.7	1051.7	1053.1	1058.3	1058.9	1063.4	1062.0
5°	1155.9	1164.0	1167.0	1179.8	1187.5	1190.9	1184.1
7.5°	1283.3	1306.2	1317.0	1330.4	1342.3	1345.9	1336.5
10°	1376.1	1400.0	1420.2	1432.5	1444.1	1451.7	1461.5
12.5°	1466.0	1495.3	1514.4	1531.9	1543.8	1553.5	1555.1
15°	1563.6	1607.9	1641.7	1666.4	1678.8	1685.2	1682.6
17.5°	1662.0	1703.2	1727.1	1752.4	1769.5	1770.4	1770.9
20°	1717.7	1757.8	1785.5	1804.3	1823.5	1822.7	1826.9
22.5°	1754.9	1786.5	1807.7	1821.4	1828.0	1824.7	1825.5
25°	1772.3	1781.7	1777.8	1756.1	1750.5	1730.5	1733.9
27.5°	1682.5	1638.1	1592.1	1533.1	1486.5	1449.3	1451.2
30°	1560.6	1482.1	1392.4	1317.3	1249.9	1231.0	1190.9
32.5°	1390.2	1272.4	1167.3	1097.3	1039.4	1023.8	988.8
35°	1101.3	986.8	878.9	814.0	788.4	752.5	752.1
37.5°	856.0	755.3	698.1	649.5	623.9	602.3	600.1
40°	720.1	641.6	598.4	563.5	538.3	522.0	518.2
42.5°	625.2	561.7	521.3	499.6	480.2	471.8	465.6
45°	510.5	467.8	439.7	420.0	411.1	404.6	401.2
47.5°	427.1	398.4	379.2	366.2	358.9	352.1	353.9
50°	381.6	358.2	344.1	331.7	326.1	321.4	321.9
52.5°	345.0	324.0	312.6	303.7	296.8	293.4	291.8
55°	292.9	279.6	268.1	261.6	257.8	253.2	251.8
57.5°	249.8	239.5	230.2	222.9	221.9	217.4	218.0
60°	221.1	212.5	204.9	201.1	198.0	194.2	195.5
62.5°	197.5	190.4	183.4	180.2	177.2	174.4	175.0
65°	161.8	154.9	150.7	149.0	147.7	146.4	145.1
67.5°	128.9	124.7	122.1	118.4	115.8	115.4	114.1
70°	108.4	102.9	98.2	93.5	92.2	91.8	92.2
72.5°	86.9	83.4	82.1	79.8	79.6	78.4	79.2
75°	65.3	64.0	63.2	61.5	61.5	61.5	61.5
77.5°	48.2	47.4	46.9	46.6	46.1	45.5	45.4
80°	37.6	37.1	36.3	36.3	35.9	36.3	35.9
82.5°	28.4	28.3	27.4	27.4	27.0	26.7	27.0
85°	14.5	14.1	14.9	14.1	14.5	13.7	14.5
87.5°	8.3	8.5	8.5	8.3	8.2	9.0	8.2
90°	21.2	22.0	23.6	22.7	23.6	24.4	23.6
92.5°	54.4	48.0	43.8	42.3	39.9	40.7	39.2
95°	198.6	155.5	126.1	110.7	103.4	97.7	94.4
97.5°	585.0	480.0	382.6	322.6	286.0	264.0	257.0
100°	893.6	798.3	682.8	600.6	541.2	509.5	510.3
102.5°	1033.6	978.0	904.8	840.8	793.8	767.3	748.5
105°	1139.4	1154.8	1133.7	1096.2	1065.3	1039.3	1035.2
107.5°	1126.0	1197.3	1226.3	1226.9	1216.5	1207.7	1200.2
110°	1082.4	1184.9	1241.9	1264.7	1271.2	1269.6	1268.0

TEST NUMBER: P332320-930

CATALOG NUMBER: S123RDIP-S775D1025U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1025.1	1140.0	1213.2	1254.9	1275.0	1281.2	1281.6
115°	933.4	1053.0	1141.7	1202.8	1238.6	1254.9	1259.0
117.5°	856.0	963.4	1053.4	1117.0	1158.1	1181.5	1187.0
120°	813.0	910.7	992.9	1057.1	1102.7	1122.3	1127.2
122.5°	778.5	869.0	945.3	1002.5	1043.5	1064.9	1071.1
125°	735.7	813.8	878.9	931.0	966.8	987.2	992.9
127.5°	698.1	768.6	827.8	874.2	904.8	923.2	928.4
130°	674.7	740.5	795.9	839.0	868.4	885.4	891.9
132.5°	652.5	713.9	766.6	807.1	836.4	851.6	856.1
135°	620.9	673.8	720.2	760.1	784.5	799.2	804.9
137.5°	590.5	636.1	676.3	709.8	734.6	746.9	750.6
140°	572.9	612.0	647.0	677.9	700.7	713.7	712.9
142.5°	556.0	589.9	620.3	646.7	666.8	678.6	677.8
145°	533.9	559.9	583.5	603.8	620.9	627.5	629.1
147.5°	517.4	538.4	555.2	570.6	582.2	588.4	589.1
150°	507.0	524.1	539.6	551.8	560.7	565.6	565.6
152.5°	497.3	512.4	525.2	534.8	543.2	546.1	546.1
155°	483.4	495.6	505.4	512.7	519.2	520.8	521.6
157.5°	469.9	479.3	487.0	493.3	498.2	499.5	499.4
160°	461.5	469.5	475.2	480.9	485.8	485.8	485.0
162.5°	452.3	459.8	464.9	468.6	472.8	472.8	472.0
165°	439.4	445.2	449.2	452.5	455.8	454.9	454.9
167.5°	429.5	432.8	435.7	437.2	439.4	438.6	438.6
170°	422.4	425.6	427.2	428.0	429.7	428.8	428.8
172.5°	416.5	419.1	420.1	420.3	421.9	420.4	419.8
175°	408.5	410.2	410.2	410.2	411.0	410.2	409.4
177.5°	404.0	404.6	404.6	404.0	404.6	403.3	403.3
180°	402.0	402.0	402.0	402.0	402.0	402.0	402.0

(END OF REPORT)