

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332242-935

Luminaire Tested: **S123RDIP-S340D365U935-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332242-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S340D365U935-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2298.7 lumens
Efficiency: N/A
Efficacy: 113.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 20.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332242-935

CATALOG NUMBER: S123RDIP-S340D365U935-4F0-1E-UDD-A4

Luminous Intensity Polar Plot



TEST NUMBER: P332242-935

CATALOG NUMBER: S123RDIP-S340D365U935-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57
1	99	94	91	87	91	87	84	81	74	72	70	62	61	59	51	50	49
2	90	83	77	72	83	77	72	68	66	62	59	55	53	50	46	44	42
3	83	74	67	61	76	68	62	57	59	54	50	49	46	43	41	39	37
4	76	66	58	52	70	61	54	49	52	47	43	44	41	38	37	34	32
5	70	59	51	45	64	55	48	43	47	42	38	40	36	33	34	31	28
6	65	53	45	39	60	49	42	37	43	37	33	37	32	29	31	28	25
7	60	48	40	35	55	45	38	33	39	33	29	33	29	26	28	25	23
8	56	44	36	31	51	41	34	29	36	30	26	31	26	23	26	23	20
9	52	40	33	28	48	37	31	26	33	27	24	28	24	21	24	21	18
10	48	37	30	25	45	34	28	24	30	25	21	26	22	19	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5044	5044	5044	5044
5°	6013	5065	4460	5065
10°	7507	5037	4030	5037
15°	8811	4985	3675	4985
20°	9835	4907	3373	4907
25°	9678	4827	3188	4827
30°	6955	4753	2997	4753
35°	4644	4654	2872	4654
40°	3421	4539	2746	4539
45°	2871	4332	2620	4332
50°	2534	4064	2445	4064
55°	2222	3757	2205	3757
60°	1978	3462	2019	3462
65°	1737	3148	1880	3148
70°	1363	2867	1718	2867
75°	1198	2504	1568	2504
80°	1048	2126	1543	2126
85°	840	1717	1643	1717

TEST NUMBER: P332242-935

CATALOG NUMBER: S123RDIP-S340D365U935-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.1	2.0
10°-20°	144.0	6.3
20°-30°	226.2	9.8
30°-40°	236.0	10.3
40°-50°	201.9	8.8
50°-60°	153.9	6.7
60°-70°	98.7	4.3
70°-80°	47.5	2.1
80°-90°	13.7	0.6
90°-100°	83.7	3.6
100°-110°	236.9	10.3
110°-120°	233.0	10.1
120°-130°	185.8	8.1
130°-140°	146.5	6.4
140°-150°	109.4	4.8
150°-160°	76.2	3.3
160°-170°	44.8	1.9
170°-180°	14.6	0.6
0°-30°	416.2	18.1
0°-40°	652.2	28.4
0°-60°	1008.0	43.9
0°-90°	1167.9	50.8
90°-120°	553.5	24.1
90°-150°	995.3	43.3
90°-180°	1131.0	49.2
0°-180°	2298.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	469	469	469	469	469	
5°	556	469	413	469	556	57
15°	791	447	330	447	791	224
25°	815	406	268	406	815	350
35°	353	354	219	354	353	232
45°	189	285	172	285	189	148
55°	118	200	118	200	118	107
65°	68	124	74	124	68	67
75°	29	60	38	60	29	31
85°	7	14	13	14	7	8
90°	9	1	9	1	9	5
95°	35	10	35	10	35	64
105°	387	35	387	35	387	382
115°	471	62	471	62	471	457
125°	371	87	371	87	371	336
135°	301	102	301	102	301	233
145°	235	116	235	116	235	150
155°	195	132	195	132	195	91
165°	170	144	170	144	170	49
175°	153	150	153	150	153	15
180°	150	150	150	150	150	

TEST NUMBER: P332242-935

CATALOG NUMBER: S123RDIP-S340D365U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6
2.5°	499.1	499.7	497.7	497.3	494.9	494.3	494.3	490.9	488.8	486.1	484.5
5°	556.5	559.6	558.0	554.5	548.5	547.0	543.2	537.2	530.4	521.9	518.0
7.5°	628.1	632.5	630.8	625.3	618.9	613.8	603.0	593.1	579.1	566.8	556.3
10°	686.8	682.3	678.6	673.2	667.4	658.0	646.7	631.3	613.5	599.3	583.8
12.5°	730.8	730.0	725.5	719.9	711.7	702.7	688.9	670.1	649.4	629.0	611.1
15°	790.7	791.9	788.9	783.2	771.5	755.6	734.8	726.9	697.2	675.2	653.2
17.5°	832.2	832.0	831.6	823.5	811.7	800.4	781.0	760.4	733.6	702.5	672.8
20°	858.6	856.5	857.0	847.9	839.1	826.0	807.2	777.3	755.3	719.4	688.6
22.5°	857.9	857.5	859.0	855.9	849.5	839.6	824.7	799.4	771.3	735.0	700.5
25°	814.9	813.2	822.6	825.3	835.5	837.3	832.8	819.1	792.4	755.0	712.3
27.5°	681.9	681.1	698.5	720.5	748.2	769.8	790.7	800.7	792.4	765.6	722.8
30°	559.6	578.5	587.4	619.1	654.4	696.5	733.4	768.4	777.1	765.4	730.4
32.5°	464.7	481.1	488.5	515.7	548.6	598.0	653.3	703.0	738.1	747.0	725.9
35°	353.4	353.6	370.5	382.5	413.0	463.7	517.5	584.1	650.3	700.5	705.7
37.5°	282.1	283.0	293.3	305.2	328.1	354.9	402.3	457.6	534.1	611.1	656.3
40°	243.5	245.3	253.0	264.8	281.2	301.5	338.4	390.5	454.3	540.0	610.0
42.5°	218.8	221.7	225.7	234.8	245.0	264.0	293.8	334.1	392.1	473.1	553.9
45°	188.6	190.2	193.2	197.4	206.6	219.8	239.9	267.0	315.1	380.3	461.2
47.5°	166.3	165.5	168.7	172.0	178.2	187.3	200.7	222.7	257.1	309.4	378.0
50°	151.3	151.0	153.3	155.8	161.7	168.3	179.3	196.0	223.3	266.6	329.4
52.5°	137.2	137.8	139.5	142.7	146.9	152.2	162.1	174.2	197.6	235.0	287.3
55°	118.4	119.0	121.1	123.0	126.0	131.4	137.6	147.7	163.7	189.8	232.9
57.5°	102.5	102.2	104.3	104.8	108.1	112.5	117.4	125.2	136.8	156.2	185.2
60°	91.9	91.3	93.1	94.5	96.3	99.9	103.9	111.5	120.8	135.0	159.9
62.5°	82.2	82.0	83.3	84.7	86.2	89.5	92.8	98.7	106.0	118.0	137.8
65°	68.2	68.8	69.4	70.0	70.8	72.8	76.0	80.1	85.1	93.5	107.7
67.5°	53.6	54.2	54.4	55.6	57.3	58.6	60.6	64.1	67.7	74.7	82.8
70°	43.3	43.1	43.3	43.9	46.1	48.3	51.0	53.6	55.8	60.8	67.6
72.5°	37.2	36.9	37.4	37.5	38.6	39.2	40.8	43.3	46.1	49.5	54.4
75°	28.8	28.8	28.8	28.8	29.7	30.0	30.7	31.3	32.3	33.9	37.5
77.5°	21.4	21.4	21.7	21.9	22.0	22.3	22.6	23.2	23.6	24.5	26.0
80°	16.9	17.0	16.9	17.0	17.0	17.5	17.7	18.3	18.4	19.5	20.1
82.5°	12.7	12.6	12.7	12.9	12.9	13.3	13.3	13.8	13.8	14.3	14.9
85°	6.8	6.5	6.8	6.6	7.1	6.6	6.8	7.2	7.2	7.4	8.3
87.5°	3.4	3.8	3.4	3.4	3.5	3.5	3.5	3.4	3.7	3.6	3.6
90°	8.8	9.1	8.8	8.5	8.8	8.2	7.9	7.6	7.3	7.6	6.7
92.5°	14.6	15.2	14.9	15.8	16.4	17.9	20.3	25.7	35.3	46.8	51.5
95°	35.3	36.5	38.7	41.4	47.2	58.1	74.2	109.5	146.4	180.5	160.7
97.5°	96.1	98.7	106.9	120.6	143.1	179.4	218.7	273.0	299.1	279.7	204.7
100°	190.8	190.5	202.3	224.5	255.3	298.5	334.1	358.7	348.1	288.2	194.8
102.5°	279.8	286.9	296.8	314.4	338.3	365.7	386.4	387.2	350.5	272.3	180.1
105°	387.0	388.6	398.3	409.8	423.9	431.7	425.9	395.5	331.9	244.6	162.2
107.5°	448.8	451.5	454.8	458.7	458.5	447.6	420.9	371.5	299.5	220.2	150.8
110°	474.1	474.7	475.3	472.9	464.3	443.0	404.7	348.7	279.1	206.3	146.4

TEST NUMBER: P332242-935

CATALOG NUMBER: S123RDIP-S340D365U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	479.1	479.1	476.7	469.2	453.6	426.2	383.2	326.1	261.2	197.0	143.9
115°	470.7	469.2	463.0	449.7	426.9	393.7	349.0	296.0	239.8	187.1	143.0
117.5°	443.8	441.7	433.0	417.7	393.8	360.2	320.0	274.3	226.8	181.2	143.5
120°	421.4	419.6	412.2	395.2	371.2	340.4	303.9	262.9	220.0	178.6	144.6
122.5°	400.5	398.1	390.1	374.8	353.4	324.9	291.0	253.9	214.4	176.9	146.2
125°	371.2	369.1	361.4	348.1	328.6	304.3	275.1	241.9	207.2	174.6	148.8
127.5°	347.1	345.2	338.3	326.8	309.5	287.3	261.0	231.4	200.9	173.6	151.7
130°	333.5	331.1	324.7	313.7	297.6	276.9	252.3	224.8	197.4	172.8	153.7
132.5°	320.1	318.4	312.7	301.8	286.6	266.9	243.9	218.8	194.3	172.5	155.2
135°	300.9	298.8	293.3	284.2	269.2	251.9	232.1	210.5	190.2	172.2	157.3
137.5°	280.7	279.2	274.7	265.4	252.9	237.8	220.8	203.0	186.6	171.5	158.8
140°	266.6	266.8	262.0	253.5	241.9	228.8	214.2	198.7	184.3	171.3	159.7
142.5°	253.4	253.7	249.3	241.8	231.9	220.5	207.8	194.6	182.4	170.8	160.5
145°	235.2	234.6	232.1	225.8	218.2	209.3	199.6	189.6	179.8	170.0	160.9
147.5°	220.2	220.0	217.7	213.4	207.6	201.3	193.5	185.5	177.3	168.9	160.9
150°	211.5	211.5	209.7	206.3	201.7	196.0	189.6	182.5	175.6	168.0	160.9
152.5°	204.1	204.1	203.0	199.9	196.4	191.6	185.9	179.9	173.6	166.8	160.2
155°	195.0	194.8	194.2	191.7	188.9	185.3	180.7	175.9	170.7	164.6	159.5
157.5°	186.7	186.8	186.2	184.4	182.1	179.2	175.6	171.6	167.4	162.7	158.4
160°	181.3	181.7	181.7	179.8	177.7	175.6	172.5	169.2	165.2	161.3	157.9
162.5°	176.5	176.8	176.8	175.2	173.8	171.9	169.1	166.3	163.0	159.8	157.0
165°	170.0	170.0	170.4	169.2	168.0	166.4	164.3	162.5	160.1	157.6	155.5
167.5°	164.0	164.0	164.3	163.4	162.9	161.8	160.6	159.2	157.2	155.4	154.0
170°	160.3	160.3	160.7	160.1	159.7	159.1	157.9	157.0	155.5	153.9	153.1
172.5°	157.0	157.2	157.7	157.1	157.0	156.7	155.8	155.1	153.8	152.7	152.3
175°	153.1	153.3	153.7	153.3	153.3	153.3	152.7	152.4	151.8	151.2	151.2
177.5°	150.8	150.8	151.3	151.0	151.3	151.3	151.0	150.8	150.6	150.3	150.6
180°	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3

TEST NUMBER: P332242-935

CATALOG NUMBER: S123RDIP-S340D365U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6
2.5°	483.8	483.4	481.1	478.5	475.2	472.9	471.1	470.2	467.3	463.7	461.4
5°	513.8	507.7	501.3	493.4	486.2	478.8	474.2	468.8	462.2	454.8	449.5
7.5°	545.7	533.9	521.2	508.1	495.2	483.5	473.2	464.4	453.9	443.2	435.8
10°	570.3	553.0	535.2	516.9	500.3	484.7	472.6	460.8	448.2	435.9	426.6
12.5°	592.6	569.9	549.3	526.8	505.6	486.9	469.6	455.6	440.4	427.4	416.9
15°	620.9	597.5	572.7	538.6	510.3	486.6	465.5	447.3	428.9	412.8	402.6
17.5°	647.2	612.3	578.8	550.4	513.6	484.1	458.3	436.5	416.2	399.2	386.6
20°	658.1	624.2	588.0	551.6	515.6	482.4	452.5	428.4	407.4	388.1	376.5
22.5°	664.7	626.4	588.1	549.1	510.7	476.3	446.8	420.3	397.4	379.2	364.8
25°	672.4	626.6	584.5	546.0	506.9	469.6	434.5	406.4	381.8	362.3	347.1
27.5°	677.4	623.6	573.9	531.1	491.4	454.3	422.1	392.3	367.2	346.6	330.3
30°	678.4	621.2	565.7	519.4	479.1	444.9	410.8	382.4	355.9	334.0	318.7
32.5°	679.7	615.3	554.6	505.4	464.1	430.3	399.4	372.2	345.1	323.6	308.0
35°	674.4	612.0	537.8	481.2	439.9	407.2	379.4	354.2	327.6	306.7	290.8
37.5°	651.6	599.0	520.4	454.0	410.8	380.6	357.8	336.0	311.5	289.0	274.1
40°	628.7	586.2	506.9	437.5	392.4	361.3	340.8	323.0	299.3	278.2	262.2
42.5°	594.5	568.6	494.0	420.2	371.5	341.6	324.3	307.5	286.8	265.4	250.3
45°	531.8	535.2	467.8	392.5	342.6	312.5	296.3	284.6	266.2	248.6	233.1
47.5°	453.1	485.0	437.0	363.2	312.2	284.0	269.8	259.6	247.1	229.8	215.7
50°	401.8	447.3	412.2	343.5	293.1	265.0	251.0	242.7	231.9	218.3	204.8
52.5°	354.5	403.4	382.4	321.4	272.3	246.7	233.0	226.2	217.6	204.7	192.6
55°	289.0	338.6	333.8	288.3	241.3	218.3	207.8	200.2	194.4	184.8	175.1
57.5°	233.8	280.8	283.3	251.3	214.0	191.1	182.2	176.4	172.6	165.4	156.4
60°	199.0	242.1	250.6	226.4	194.4	174.4	165.5	160.8	157.9	152.1	145.3
62.5°	170.1	206.8	216.4	199.1	175.6	156.8	149.9	145.5	143.4	138.4	132.4
65°	130.2	160.7	169.9	160.3	148.0	133.0	127.3	123.6	121.7	119.0	114.5
67.5°	97.9	120.1	130.3	123.5	119.0	109.5	106.0	103.9	102.3	100.4	96.7
70°	78.6	95.1	105.5	103.8	100.1	95.1	92.5	91.1	89.5	87.8	84.6
72.5°	63.2	74.6	84.3	85.2	82.3	81.3	79.0	78.4	77.4	75.5	73.7
75°	41.9	49.8	56.6	59.2	60.4	61.4	60.4	60.2	60.0	58.4	57.3
77.5°	27.5	31.7	36.0	40.5	42.4	43.7	44.0	44.8	44.2	43.4	42.9
80°	21.1	22.0	25.1	28.8	31.9	33.1	33.9	34.3	34.1	33.9	33.1
82.5°	15.3	16.1	17.6	20.2	22.7	24.7	25.2	25.1	25.6	25.7	25.1
85°	8.3	8.4	8.9	9.2	10.6	12.8	13.4	13.9	14.2	14.2	13.0
87.5°	3.7	3.4	3.5	3.4	3.8	3.7	4.6	5.3	5.5	5.0	5.2
90°	5.8	4.9	4.0	3.4	2.8	1.8	1.2	0.6	1.2	1.8	2.8
92.5°	38.7	25.6	17.6	13.1	10.5	8.2	5.6	3.8	5.6	8.2	10.5
95°	110.7	65.4	39.5	27.7	19.8	14.6	11.3	10.3	11.3	14.6	19.8
97.5°	121.5	70.4	45.7	32.9	25.1	20.6	17.9	17.7	17.9	20.6	25.1
100°	114.7	69.7	48.4	36.5	29.2	25.0	22.8	22.6	22.8	25.0	29.2
102.5°	108.8	70.7	51.6	40.6	34.1	30.0	28.2	27.6	28.2	30.0	34.1
105°	104.7	73.4	56.9	47.4	41.7	38.1	36.2	35.3	36.2	38.1	41.7
107.5°	104.4	78.4	63.9	55.1	49.7	46.1	44.3	43.5	44.3	46.1	49.7
110°	105.6	82.5	68.8	60.3	55.1	51.7	50.2	49.2	50.2	51.7	55.1

TEST NUMBER: P332242-935

CATALOG NUMBER: S123RDIP-S340D365U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	108.1	86.6	73.9	65.6	60.4	57.1	55.5	54.7	55.5	57.1	60.4
115°	111.9	93.4	81.9	73.6	68.4	65.4	63.6	62.3	63.6	65.4	68.4
117.5°	117.2	100.7	89.2	81.6	75.9	73.0	71.5	70.1	71.5	73.0	75.9
120°	121.1	105.3	94.3	86.7	80.9	77.9	76.4	75.4	76.4	77.9	80.9
122.5°	124.8	110.1	99.4	91.4	85.8	82.5	81.0	80.1	81.0	82.5	85.8
125°	130.5	117.2	106.5	98.2	92.5	89.1	87.3	86.7	87.3	89.1	92.5
127.5°	135.3	123.2	113.0	104.7	98.3	95.0	92.6	91.8	92.6	95.0	98.3
130°	138.4	126.9	116.8	108.7	102.2	98.6	95.8	95.0	95.8	98.6	102.2
132.5°	141.4	130.0	120.3	112.3	105.9	101.5	98.5	97.4	98.5	101.5	105.9
135°	145.2	134.7	125.4	117.2	110.7	106.2	102.8	101.6	102.8	106.2	110.7
137.5°	147.9	138.1	129.0	121.4	115.0	110.2	106.9	105.6	106.9	110.2	115.0
140°	149.4	140.3	131.5	123.8	117.8	112.9	109.9	108.3	109.9	112.9	117.8
142.5°	150.8	142.0	133.4	126.3	120.2	115.8	112.5	111.2	112.5	115.8	120.2
145°	152.4	144.2	136.3	129.3	124.2	119.6	116.8	115.9	116.8	119.6	124.2
147.5°	153.4	146.0	138.8	132.9	127.9	123.9	121.2	120.7	121.2	123.9	127.9
150°	153.7	147.2	140.3	134.7	130.5	126.6	124.2	123.8	124.2	126.6	130.5
152.5°	154.1	148.0	142.0	136.7	132.9	129.5	127.1	127.0	127.1	129.5	132.9
155°	154.3	149.4	144.2	140.0	136.6	133.5	131.7	131.7	131.7	133.5	136.6
157.5°	154.5	150.2	146.0	142.8	139.9	137.2	135.8	135.5	135.8	137.2	139.9
160°	154.5	150.9	147.2	144.2	142.1	139.7	138.4	138.4	138.4	139.7	142.1
162.5°	154.3	151.2	148.0	145.4	143.5	141.6	140.6	140.6	140.6	141.6	143.5
165°	153.7	151.5	149.1	147.0	145.8	144.2	143.6	143.9	143.6	144.2	145.8
167.5°	153.2	151.4	149.7	148.4	147.5	146.4	146.0	146.4	146.0	146.4	147.5
170°	152.4	151.2	149.7	149.1	148.4	147.6	147.2	147.8	147.2	147.6	148.4
172.5°	152.2	151.2	149.9	149.6	149.2	148.5	148.4	148.9	148.4	148.5	149.2
175°	151.5	150.9	150.3	150.0	150.0	149.4	149.7	150.0	149.7	149.4	150.0
177.5°	151.0	150.6	150.3	150.3	150.3	150.1	150.3	150.6	150.3	150.1	150.3
180°	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3

TEST NUMBER: P332242-935

CATALOG NUMBER: S123RDIP-S340D365U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6
2.5°	460.5	458.5	457.0	453.8	451.8	449.5	447.3	448.7	448.5	448.4	448.4
5°	445.1	440.5	436.3	430.8	427.5	423.3	420.1	419.7	420.4	417.7	416.0
7.5°	429.8	423.5	417.5	411.6	405.2	400.1	397.0	395.5	393.5	391.8	389.9
10°	419.0	411.6	405.8	398.4	391.6	385.6	381.8	379.1	377.7	376.3	373.7
12.5°	407.9	400.7	393.3	384.9	378.4	371.4	368.6	365.7	363.0	361.4	357.8
15°	391.8	382.4	374.5	365.7	358.4	351.6	347.7	341.8	341.0	339.0	335.4
17.5°	375.5	365.3	354.5	347.9	339.8	332.7	326.6	324.7	318.9	316.8	313.6
20°	362.7	353.3	345.0	336.4	324.6	318.0	313.1	310.6	305.9	303.1	301.1
22.5°	351.6	342.0	332.5	322.4	312.7	305.2	301.7	297.6	295.2	291.2	289.0
25°	335.8	325.4	313.9	303.1	296.1	290.5	284.8	281.2	277.6	275.8	271.8
27.5°	317.5	306.5	295.8	287.6	279.0	273.5	268.4	265.2	260.8	257.8	255.5
30°	307.3	294.5	285.2	277.8	266.8	261.6	257.8	253.7	250.6	247.4	245.1
32.5°	295.6	283.9	275.2	266.0	257.5	251.8	246.8	243.3	240.6	237.5	235.3
35°	277.2	267.4	258.4	249.2	242.9	237.1	231.3	228.3	225.7	222.8	220.8
37.5°	260.6	251.4	242.8	234.1	226.4	221.6	217.0	214.6	211.1	209.2	207.2
40°	250.4	241.3	232.1	223.7	215.7	212.1	207.8	204.4	201.2	199.8	197.6
42.5°	239.1	230.1	222.3	213.3	206.6	201.7	197.9	194.2	191.7	189.7	188.5
45°	222.5	214.5	206.8	197.8	191.6	187.4	183.0	179.5	177.4	175.9	173.7
47.5°	206.3	198.3	190.5	182.7	176.7	171.9	167.4	165.1	162.1	160.4	158.9
50°	194.6	187.4	179.2	171.9	165.9	161.1	157.5	154.5	151.9	149.6	148.6
52.5°	183.8	176.2	169.0	162.3	155.9	150.5	147.2	144.0	142.1	139.6	138.4
55°	166.1	158.7	152.7	146.0	139.8	135.2	131.2	128.4	126.4	123.6	122.0
57.5°	149.5	142.8	135.6	129.8	123.5	119.6	116.2	112.4	109.9	107.8	106.2
60°	138.2	130.6	124.3	119.0	113.3	108.3	105.3	102.3	99.7	97.5	96.1
62.5°	126.5	119.9	113.9	108.1	102.9	98.5	95.1	92.6	90.2	88.9	87.4
65°	108.5	103.3	97.3	92.5	87.6	84.5	81.6	79.5	77.8	76.8	75.6
67.5°	92.0	87.0	81.7	77.0	73.7	71.3	69.5	67.6	66.7	65.4	64.7
70°	81.3	76.0	71.4	67.8	64.6	62.8	61.6	60.2	59.4	57.8	57.0
72.5°	69.6	65.8	62.4	59.5	56.9	55.3	53.7	52.0	50.7	48.9	48.1
75°	54.8	51.3	48.7	46.8	45.1	43.0	40.7	38.9	38.3	37.7	37.5
77.5°	40.6	38.4	36.5	34.8	32.8	31.3	30.7	30.3	30.2	29.9	29.9
80°	31.9	29.9	28.5	26.5	25.3	25.3	25.3	24.9	25.1	25.1	25.1
82.5°	23.7	21.9	21.1	20.4	20.1	20.3	20.3	20.4	20.2	20.6	20.4
85°	12.2	12.4	12.8	12.7	12.8	12.8	13.3	13.0	13.3	12.8	13.3
87.5°	5.2	5.8	6.1	6.5	6.8	6.8	6.9	7.0	7.2	7.2	7.4
90°	3.4	4.0	4.9	5.8	6.7	7.6	7.3	7.6	7.9	8.2	8.8
92.5°	13.1	17.6	25.6	38.7	51.5	46.8	35.3	25.7	20.3	17.9	16.4
95°	27.7	39.5	65.4	110.7	160.7	180.5	146.4	109.5	74.2	58.1	47.2
97.5°	32.9	45.7	70.4	121.5	204.7	279.7	299.1	273.0	218.7	179.4	143.1
100°	36.5	48.4	69.7	114.7	194.8	288.2	348.1	358.7	334.1	298.5	255.3
102.5°	40.6	51.6	70.7	108.8	180.1	272.3	350.5	387.2	386.4	365.7	338.3
105°	47.4	56.9	73.4	104.7	162.2	244.6	331.9	395.5	425.9	431.7	423.9
107.5°	55.1	63.9	78.4	104.4	150.8	220.2	299.5	371.5	420.9	447.6	458.5
110°	60.3	68.8	82.5	105.6	146.4	206.3	279.1	348.7	404.7	443.0	464.3

TEST NUMBER: P332242-935

CATALOG NUMBER: S123RDIP-S340D365U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	65.6	73.9	86.6	108.1	143.9	197.0	261.2	326.1	383.2	426.2	453.6
115°	73.6	81.9	93.4	111.9	143.0	187.1	239.8	296.0	349.0	393.7	426.9
117.5°	81.6	89.2	100.7	117.2	143.5	181.2	226.8	274.3	320.0	360.2	393.8
120°	86.7	94.3	105.3	121.1	144.6	178.6	220.0	262.9	303.9	340.4	371.2
122.5°	91.4	99.4	110.1	124.8	146.2	176.9	214.4	253.9	291.0	324.9	353.4
125°	98.2	106.5	117.2	130.5	148.8	174.6	207.2	241.9	275.1	304.3	328.6
127.5°	104.7	113.0	123.2	135.3	151.7	173.6	200.9	231.4	261.0	287.3	309.5
130°	108.7	116.8	126.9	138.4	153.7	172.8	197.4	224.8	252.3	276.9	297.6
132.5°	112.3	120.3	130.0	141.4	155.2	172.5	194.3	218.8	243.9	266.9	286.6
135°	117.2	125.4	134.7	145.2	157.3	172.2	190.2	210.5	232.1	251.9	269.2
137.5°	121.4	129.0	138.1	147.9	158.8	171.5	186.6	203.0	220.8	237.8	252.9
140°	123.8	131.5	140.3	149.4	159.7	171.3	184.3	198.7	214.2	228.8	241.9
142.5°	126.3	133.4	142.0	150.8	160.5	170.8	182.4	194.6	207.8	220.5	231.9
145°	129.3	136.3	144.2	152.4	160.9	170.0	179.8	189.6	199.6	209.3	218.2
147.5°	132.9	138.8	146.0	153.4	160.9	168.9	177.3	185.5	193.5	201.3	207.6
150°	134.7	140.3	147.2	153.7	160.9	168.0	175.6	182.5	189.6	196.0	201.7
152.5°	136.7	142.0	148.0	154.1	160.2	166.8	173.6	179.9	185.9	191.6	196.4
155°	140.0	144.2	149.4	154.3	159.5	164.6	170.7	175.9	180.7	185.3	188.9
157.5°	142.8	146.0	150.2	154.5	158.4	162.7	167.4	171.6	175.6	179.2	182.1
160°	144.2	147.2	150.9	154.5	157.9	161.3	165.2	169.2	172.5	175.6	177.7
162.5°	145.4	148.0	151.2	154.3	157.0	159.8	163.0	166.3	169.1	171.9	173.8
165°	147.0	149.1	151.5	153.7	155.5	157.6	160.1	162.5	164.3	166.4	168.0
167.5°	148.4	149.7	151.4	153.2	154.0	155.4	157.2	159.2	160.6	161.8	162.9
170°	149.1	149.7	151.2	152.4	153.1	153.9	155.5	157.0	157.9	159.1	159.7
172.5°	149.6	149.9	151.2	152.2	152.3	152.7	153.8	155.1	155.8	156.7	157.0
175°	150.0	150.3	150.9	151.5	151.2	151.2	151.8	152.4	152.7	153.3	153.3
177.5°	150.3	150.3	150.6	151.0	150.6	150.3	150.6	150.8	151.0	151.3	151.3
180°	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3

TEST NUMBER: P332242-935

CATALOG NUMBER: S123RDIP-S340D365U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6
2.5°	446.4	446.3	446.4	445.8	446.4	446.3	446.4	448.4	448.4	448.5	448.7
5°	415.4	415.3	414.7	412.8	414.7	415.3	415.4	416.0	417.7	420.4	419.7
7.5°	388.3	388.1	386.3	386.3	386.3	388.1	388.3	389.9	391.8	393.5	395.5
10°	372.3	372.5	370.1	368.7	370.1	372.5	372.3	373.7	376.3	377.7	379.1
12.5°	356.7	355.9	353.9	352.3	353.9	355.9	356.7	357.8	361.4	363.0	365.7
15°	336.2	334.2	329.4	329.8	329.4	334.2	336.2	335.4	339.0	341.0	341.8
17.5°	312.0	310.6	310.5	307.6	310.5	310.6	312.0	313.6	316.8	318.9	324.7
20°	297.9	296.9	297.3	294.5	297.3	296.9	297.9	301.1	303.1	305.9	310.6
22.5°	286.8	285.8	284.1	283.3	284.1	285.8	286.8	289.0	291.2	295.2	297.6
25°	270.6	269.0	267.4	268.4	267.4	269.0	270.6	271.8	275.8	277.6	281.2
27.5°	254.4	253.2	251.6	251.4	251.6	253.2	254.4	255.5	257.8	260.8	265.2
30°	244.1	242.9	242.1	241.1	242.1	242.9	244.1	245.1	247.4	250.6	253.7
32.5°	233.7	233.4	232.0	231.8	232.0	233.4	233.7	235.3	237.5	240.6	243.3
35°	220.1	218.9	218.4	218.6	218.4	218.9	220.1	220.8	222.8	225.7	228.3
37.5°	207.1	205.5	204.7	204.1	204.7	205.5	207.1	207.2	209.2	211.1	214.6
40°	197.8	196.2	195.8	195.4	195.8	196.2	197.8	197.6	199.8	201.2	204.4
42.5°	187.4	186.8	186.5	185.7	186.5	186.8	187.4	188.5	189.7	191.7	194.2
45°	173.1	172.9	171.7	172.1	171.7	172.9	173.1	173.7	175.9	177.4	179.5
47.5°	158.1	157.2	156.4	157.0	156.4	157.2	158.1	158.9	160.4	162.1	165.1
50°	147.8	147.4	145.6	146.0	145.6	147.4	147.8	148.6	149.6	151.9	154.5
52.5°	137.6	136.0	135.3	135.1	135.3	136.0	137.6	138.4	139.6	142.1	144.0
55°	120.5	118.7	118.0	117.5	118.0	118.7	120.5	122.0	123.6	126.4	128.4
57.5°	103.8	103.4	102.7	103.1	102.7	103.4	103.8	106.2	107.8	109.9	112.4
60°	94.1	94.1	94.1	93.8	94.1	94.1	94.1	96.1	97.5	99.7	102.3
62.5°	86.5	86.0	85.9	86.2	85.9	86.0	86.5	87.4	88.9	90.2	92.6
65°	75.0	74.8	74.0	73.8	74.0	74.8	75.0	75.6	76.8	77.8	79.5
67.5°	64.1	63.5	63.2	62.9	63.2	63.5	64.1	64.7	65.4	66.7	67.6
70°	56.0	55.5	54.3	54.6	54.3	55.5	56.0	57.0	57.8	59.4	60.2
72.5°	47.2	46.8	46.5	46.2	46.5	46.8	47.2	48.1	48.9	50.7	52.0
75°	37.3	37.1	36.9	37.7	36.9	37.1	37.3	37.5	37.7	38.3	38.9
77.5°	29.9	29.9	30.0	29.7	30.0	29.9	29.9	29.9	29.9	30.2	30.3
80°	25.1	25.1	24.9	24.9	24.9	25.1	25.1	25.1	25.1	25.1	24.9
82.5°	20.1	20.2	20.4	20.1	20.4	20.2	20.1	20.4	20.6	20.2	20.4
85°	13.3	13.0	13.4	13.3	13.4	13.0	13.3	13.3	12.8	13.3	13.0
87.5°	7.7	7.4	7.4	7.6	7.4	7.4	7.7	7.4	7.2	7.2	7.0
90°	8.5	8.8	9.1	8.8	9.1	8.8	8.5	8.8	8.2	7.9	7.6
92.5°	15.8	14.9	15.2	14.6	15.2	14.9	15.8	16.4	17.9	20.3	25.7
95°	41.4	38.7	36.5	35.3	36.5	38.7	41.4	47.2	58.1	74.2	109.5
97.5°	120.6	106.9	98.7	96.1	98.7	106.9	120.6	143.1	179.4	218.7	273.0
100°	224.5	202.3	190.5	190.8	190.5	202.3	224.5	255.3	298.5	334.1	358.7
102.5°	314.4	296.8	286.9	279.8	286.9	296.8	314.4	338.3	365.7	386.4	387.2
105°	409.8	398.3	388.6	387.0	388.6	398.3	409.8	423.9	431.7	425.9	395.5
107.5°	458.7	454.8	451.5	448.8	451.5	454.8	458.7	458.5	447.6	420.9	371.5
110°	472.9	475.3	474.7	474.1	474.7	475.3	472.9	464.3	443.0	404.7	348.7

TEST NUMBER: P332242-935

CATALOG NUMBER: S123RDIP-S340D365U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	469.2	476.7	479.1	479.1	479.1	476.7	469.2	453.6	426.2	383.2	326.1
115°	449.7	463.0	469.2	470.7	469.2	463.0	449.7	426.9	393.7	349.0	296.0
117.5°	417.7	433.0	441.7	443.8	441.7	433.0	417.7	393.8	360.2	320.0	274.3
120°	395.2	412.2	419.6	421.4	419.6	412.2	395.2	371.2	340.4	303.9	262.9
122.5°	374.8	390.1	398.1	400.5	398.1	390.1	374.8	353.4	324.9	291.0	253.9
125°	348.1	361.4	369.1	371.2	369.1	361.4	348.1	328.6	304.3	275.1	241.9
127.5°	326.8	338.3	345.2	347.1	345.2	338.3	326.8	309.5	287.3	261.0	231.4
130°	313.7	324.7	331.1	333.5	331.1	324.7	313.7	297.6	276.9	252.3	224.8
132.5°	301.8	312.7	318.4	320.1	318.4	312.7	301.8	286.6	266.9	243.9	218.8
135°	284.2	293.3	298.8	300.9	298.8	293.3	284.2	269.2	251.9	232.1	210.5
137.5°	265.4	274.7	279.2	280.7	279.2	274.7	265.4	252.9	237.8	220.8	203.0
140°	253.5	262.0	266.8	266.6	266.8	262.0	253.5	241.9	228.8	214.2	198.7
142.5°	241.8	249.3	253.7	253.4	253.7	249.3	241.8	231.9	220.5	207.8	194.6
145°	225.8	232.1	234.6	235.2	234.6	232.1	225.8	218.2	209.3	199.6	189.6
147.5°	213.4	217.7	220.0	220.2	220.0	217.7	213.4	207.6	201.3	193.5	185.5
150°	206.3	209.7	211.5	211.5	211.5	209.7	206.3	201.7	196.0	189.6	182.5
152.5°	199.9	203.0	204.1	204.1	204.1	203.0	199.9	196.4	191.6	185.9	179.9
155°	191.7	194.2	194.8	195.0	194.8	194.2	191.7	188.9	185.3	180.7	175.9
157.5°	184.4	186.2	186.8	186.7	186.8	186.2	184.4	182.1	179.2	175.6	171.6
160°	179.8	181.7	181.7	181.3	181.7	181.7	179.8	177.7	175.6	172.5	169.2
162.5°	175.2	176.8	176.8	176.5	176.8	176.8	175.2	173.8	171.9	169.1	166.3
165°	169.2	170.4	170.0	170.0	170.0	170.4	169.2	168.0	166.4	164.3	162.5
167.5°	163.4	164.3	164.0	164.0	164.0	164.3	163.4	162.9	161.8	160.6	159.2
170°	160.1	160.7	160.3	160.3	160.3	160.7	160.1	159.7	159.1	157.9	157.0
172.5°	157.1	157.7	157.2	157.0	157.2	157.7	157.1	157.0	156.7	155.8	155.1
175°	153.3	153.7	153.3	153.1	153.3	153.7	153.3	153.3	153.3	152.7	152.4
177.5°	151.0	151.3	150.8	150.8	150.8	151.3	151.0	151.3	151.3	151.0	150.8
180°	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3

TEST NUMBER: P332242-935

CATALOG NUMBER: S123RDIP-S340D365U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6
2.5°	447.3	449.5	451.8	453.8	457.0	458.5	460.5	461.4	463.7	467.3	470.2
5°	420.1	423.3	427.5	430.8	436.3	440.5	445.1	449.5	454.8	462.2	468.8
7.5°	397.0	400.1	405.2	411.6	417.5	423.5	429.8	435.8	443.2	453.9	464.4
10°	381.8	385.6	391.6	398.4	405.8	411.6	419.0	426.6	435.9	448.2	460.8
12.5°	368.6	371.4	378.4	384.9	393.3	400.7	407.9	416.9	427.4	440.4	455.6
15°	347.7	351.6	358.4	365.7	374.5	382.4	391.8	402.6	412.8	428.9	447.3
17.5°	326.6	332.7	339.8	347.9	354.5	365.3	375.5	386.6	399.2	416.2	436.5
20°	313.1	318.0	324.6	336.4	345.0	353.3	362.7	376.5	388.1	407.4	428.4
22.5°	301.7	305.2	312.7	322.4	332.5	342.0	351.6	364.8	379.2	397.4	420.3
25°	284.8	290.5	296.1	303.1	313.9	325.4	335.8	347.1	362.3	381.8	406.4
27.5°	268.4	273.5	279.0	287.6	295.8	306.5	317.5	330.3	346.6	367.2	392.3
30°	257.8	261.6	266.8	277.8	285.2	294.5	307.3	318.7	334.0	355.9	382.4
32.5°	246.8	251.8	257.5	266.0	275.2	283.9	295.6	308.0	323.6	345.1	372.2
35°	231.3	237.1	242.9	249.2	258.4	267.4	277.2	290.8	306.7	327.6	354.2
37.5°	217.0	221.6	226.4	234.1	242.8	251.4	260.6	274.1	289.0	311.5	336.0
40°	207.8	212.1	215.7	223.7	232.1	241.3	250.4	262.2	278.2	299.3	323.0
42.5°	197.9	201.7	206.6	213.3	222.3	230.1	239.1	250.3	265.4	286.8	307.5
45°	183.0	187.4	191.6	197.8	206.8	214.5	222.5	233.1	248.6	266.2	284.6
47.5°	167.4	171.9	176.7	182.7	190.5	198.3	206.3	215.7	229.8	247.1	259.6
50°	157.5	161.1	165.9	171.9	179.2	187.4	194.6	204.8	218.3	231.9	242.7
52.5°	147.2	150.5	155.9	162.3	169.0	176.2	183.8	192.6	204.7	217.6	226.2
55°	131.2	135.2	139.8	146.0	152.7	158.7	166.1	175.1	184.8	194.4	200.2
57.5°	116.2	119.6	123.5	129.8	135.6	142.8	149.5	156.4	165.4	172.6	176.4
60°	105.3	108.3	113.3	119.0	124.3	130.6	138.2	145.3	152.1	157.9	160.8
62.5°	95.1	98.5	102.9	108.1	113.9	119.9	126.5	132.4	138.4	143.4	145.5
65°	81.6	84.5	87.6	92.5	97.3	103.3	108.5	114.5	119.0	121.7	123.6
67.5°	69.5	71.3	73.7	77.0	81.7	87.0	92.0	96.7	100.4	102.3	103.9
70°	61.6	62.8	64.6	67.8	71.4	76.0	81.3	84.6	87.8	89.5	91.1
72.5°	53.7	55.3	56.9	59.5	62.4	65.8	69.6	73.7	75.5	77.4	78.4
75°	40.7	43.0	45.1	46.8	48.7	51.3	54.8	57.3	58.4	60.0	60.2
77.5°	30.7	31.3	32.8	34.8	36.5	38.4	40.6	42.9	43.4	44.2	44.8
80°	25.3	25.3	25.3	26.5	28.5	29.9	31.9	33.1	33.9	34.1	34.3
82.5°	20.3	20.3	20.1	20.4	21.1	21.9	23.7	25.1	25.7	25.6	25.1
85°	13.3	12.8	12.8	12.7	12.8	12.4	12.2	13.0	14.2	14.2	13.9
87.5°	6.9	6.8	6.8	6.5	6.1	5.8	5.2	5.2	5.0	5.5	5.3
90°	7.3	7.6	6.7	5.8	4.9	4.0	3.4	2.8	1.8	1.2	0.6
92.5°	35.3	46.8	51.5	38.7	25.6	17.6	13.1	10.5	8.2	5.6	3.8
95°	146.4	180.5	160.7	110.7	65.4	39.5	27.7	19.8	14.6	11.3	10.3
97.5°	299.1	279.7	204.7	121.5	70.4	45.7	32.9	25.1	20.6	17.9	17.7
100°	348.1	288.2	194.8	114.7	69.7	48.4	36.5	29.2	25.0	22.8	22.6
102.5°	350.5	272.3	180.1	108.8	70.7	51.6	40.6	34.1	30.0	28.2	27.6
105°	331.9	244.6	162.2	104.7	73.4	56.9	47.4	41.7	38.1	36.2	35.3
107.5°	299.5	220.2	150.8	104.4	78.4	63.9	55.1	49.7	46.1	44.3	43.5
110°	279.1	206.3	146.4	105.6	82.5	68.8	60.3	55.1	51.7	50.2	49.2

TEST NUMBER: P332242-935

CATALOG NUMBER: S123RDIP-S340D365U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	261.2	197.0	143.9	108.1	86.6	73.9	65.6	60.4	57.1	55.5	54.7
115°	239.8	187.1	143.0	111.9	93.4	81.9	73.6	68.4	65.4	63.6	62.3
117.5°	226.8	181.2	143.5	117.2	100.7	89.2	81.6	75.9	73.0	71.5	70.1
120°	220.0	178.6	144.6	121.1	105.3	94.3	86.7	80.9	77.9	76.4	75.4
122.5°	214.4	176.9	146.2	124.8	110.1	99.4	91.4	85.8	82.5	81.0	80.1
125°	207.2	174.6	148.8	130.5	117.2	106.5	98.2	92.5	89.1	87.3	86.7
127.5°	200.9	173.6	151.7	135.3	123.2	113.0	104.7	98.3	95.0	92.6	91.8
130°	197.4	172.8	153.7	138.4	126.9	116.8	108.7	102.2	98.6	95.8	95.0
132.5°	194.3	172.5	155.2	141.4	130.0	120.3	112.3	105.9	101.5	98.5	97.4
135°	190.2	172.2	157.3	145.2	134.7	125.4	117.2	110.7	106.2	102.8	101.6
137.5°	186.6	171.5	158.8	147.9	138.1	129.0	121.4	115.0	110.2	106.9	105.6
140°	184.3	171.3	159.7	149.4	140.3	131.5	123.8	117.8	112.9	109.9	108.3
142.5°	182.4	170.8	160.5	150.8	142.0	133.4	126.3	120.2	115.8	112.5	111.2
145°	179.8	170.0	160.9	152.4	144.2	136.3	129.3	124.2	119.6	116.8	115.9
147.5°	177.3	168.9	160.9	153.4	146.0	138.8	132.9	127.9	123.9	121.2	120.7
150°	175.6	168.0	160.9	153.7	147.2	140.3	134.7	130.5	126.6	124.2	123.8
152.5°	173.6	166.8	160.2	154.1	148.0	142.0	136.7	132.9	129.5	127.1	127.0
155°	170.7	164.6	159.5	154.3	149.4	144.2	140.0	136.6	133.5	131.7	131.7
157.5°	167.4	162.7	158.4	154.5	150.2	146.0	142.8	139.9	137.2	135.8	135.5
160°	165.2	161.3	157.9	154.5	150.9	147.2	144.2	142.1	139.7	138.4	138.4
162.5°	163.0	159.8	157.0	154.3	151.2	148.0	145.4	143.5	141.6	140.6	140.6
165°	160.1	157.6	155.5	153.7	151.5	149.1	147.0	145.8	144.2	143.6	143.9
167.5°	157.2	155.4	154.0	153.2	151.4	149.7	148.4	147.5	146.4	146.0	146.4
170°	155.5	153.9	153.1	152.4	151.2	149.7	149.1	148.4	147.6	147.2	147.8
172.5°	153.8	152.7	152.3	152.2	151.2	149.9	149.6	149.2	148.5	148.4	148.9
175°	151.8	151.2	151.2	151.5	150.9	150.3	150.0	150.0	149.4	149.7	150.0
177.5°	150.6	150.3	150.6	151.0	150.6	150.3	150.3	150.3	150.1	150.3	150.6
180°	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3

TEST NUMBER: P332242-935

CATALOG NUMBER: S123RDIP-S340D365U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6
2.5°	471.1	472.9	475.2	478.5	481.1	483.4	483.8	484.5	486.1	488.8	490.9
5°	474.2	478.8	486.2	493.4	501.3	507.7	513.8	518.0	521.9	530.4	537.2
7.5°	473.2	483.5	495.2	508.1	521.2	533.9	545.7	556.3	566.8	579.1	593.1
10°	472.6	484.7	500.3	516.9	535.2	553.0	570.3	583.8	599.3	613.5	631.3
12.5°	469.6	486.9	505.6	526.8	549.3	569.9	592.6	611.1	629.0	649.4	670.1
15°	465.5	486.6	510.3	538.6	572.7	597.5	620.9	653.2	675.2	697.2	726.9
17.5°	458.3	484.1	513.6	550.4	578.8	612.3	647.2	672.8	702.5	733.6	760.4
20°	452.5	482.4	515.6	551.6	588.0	624.2	658.1	688.6	719.4	755.3	777.3
22.5°	446.8	476.3	510.7	549.1	588.1	626.4	664.7	700.5	735.0	771.3	799.4
25°	434.5	469.6	506.9	546.0	584.5	626.6	672.4	712.3	755.0	792.4	819.1
27.5°	422.1	454.3	491.4	531.1	573.9	623.6	677.4	722.8	765.6	792.4	800.7
30°	410.8	444.9	479.1	519.4	565.7	621.2	678.4	730.4	765.4	777.1	768.4
32.5°	399.4	430.3	464.1	505.4	554.6	615.3	679.7	725.9	747.0	738.1	703.0
35°	379.4	407.2	439.9	481.2	537.8	612.0	674.4	705.7	700.5	650.3	584.1
37.5°	357.8	380.6	410.8	454.0	520.4	599.0	651.6	656.3	611.1	534.1	457.6
40°	340.8	361.3	392.4	437.5	506.9	586.2	628.7	610.0	540.0	454.3	390.5
42.5°	324.3	341.6	371.5	420.2	494.0	568.6	594.5	553.9	473.1	392.1	334.1
45°	296.3	312.5	342.6	392.5	467.8	535.2	531.8	461.2	380.3	315.1	267.0
47.5°	269.8	284.0	312.2	363.2	437.0	485.0	453.1	378.0	309.4	257.1	222.7
50°	251.0	265.0	293.1	343.5	412.2	447.3	401.8	329.4	266.6	223.3	196.0
52.5°	233.0	246.7	272.3	321.4	382.4	403.4	354.5	287.3	235.0	197.6	174.2
55°	207.8	218.3	241.3	288.3	333.8	338.6	289.0	232.9	189.8	163.7	147.7
57.5°	182.2	191.1	214.0	251.3	283.3	280.8	233.8	185.2	156.2	136.8	125.2
60°	165.5	174.4	194.4	226.4	250.6	242.1	199.0	159.9	135.0	120.8	111.5
62.5°	149.9	156.8	175.6	199.1	216.4	206.8	170.1	137.8	118.0	106.0	98.7
65°	127.3	133.0	148.0	160.3	169.9	160.7	130.2	107.7	93.5	85.1	80.1
67.5°	106.0	109.5	119.0	123.5	130.3	120.1	97.9	82.8	74.7	67.7	64.1
70°	92.5	95.1	100.1	103.8	105.5	95.1	78.6	67.6	60.8	55.8	53.6
72.5°	79.0	81.3	82.3	85.2	84.3	74.6	63.2	54.4	49.5	46.1	43.3
75°	60.4	61.4	60.4	59.2	56.6	49.8	41.9	37.5	33.9	32.3	31.3
77.5°	44.0	43.7	42.4	40.5	36.0	31.7	27.5	26.0	24.5	23.6	23.2
80°	33.9	33.1	31.9	28.8	25.1	22.0	21.1	20.1	19.5	18.4	18.3
82.5°	25.2	24.7	22.7	20.2	17.6	16.1	15.3	14.9	14.3	13.8	13.8
85°	13.4	12.8	10.6	9.2	8.9	8.4	8.3	8.3	7.4	7.2	7.2
87.5°	4.6	3.7	3.8	3.4	3.5	3.4	3.7	3.6	3.6	3.7	3.4
90°	1.2	1.8	2.8	3.4	4.0	4.9	5.8	6.7	7.6	7.3	7.6
92.5°	5.6	8.2	10.5	13.1	17.6	25.6	38.7	51.5	46.8	35.3	25.7
95°	11.3	14.6	19.8	27.7	39.5	65.4	110.7	160.7	180.5	146.4	109.5
97.5°	17.9	20.6	25.1	32.9	45.7	70.4	121.5	204.7	279.7	299.1	273.0
100°	22.8	25.0	29.2	36.5	48.4	69.7	114.7	194.8	288.2	348.1	358.7
102.5°	28.2	30.0	34.1	40.6	51.6	70.7	108.8	180.1	272.3	350.5	387.2
105°	36.2	38.1	41.7	47.4	56.9	73.4	104.7	162.2	244.6	331.9	395.5
107.5°	44.3	46.1	49.7	55.1	63.9	78.4	104.4	150.8	220.2	299.5	371.5
110°	50.2	51.7	55.1	60.3	68.8	82.5	105.6	146.4	206.3	279.1	348.7

TEST NUMBER: P332242-935

CATALOG NUMBER: S123RDIP-S340D365U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	55.5	57.1	60.4	65.6	73.9	86.6	108.1	143.9	197.0	261.2	326.1
115°	63.6	65.4	68.4	73.6	81.9	93.4	111.9	143.0	187.1	239.8	296.0
117.5°	71.5	73.0	75.9	81.6	89.2	100.7	117.2	143.5	181.2	226.8	274.3
120°	76.4	77.9	80.9	86.7	94.3	105.3	121.1	144.6	178.6	220.0	262.9
122.5°	81.0	82.5	85.8	91.4	99.4	110.1	124.8	146.2	176.9	214.4	253.9
125°	87.3	89.1	92.5	98.2	106.5	117.2	130.5	148.8	174.6	207.2	241.9
127.5°	92.6	95.0	98.3	104.7	113.0	123.2	135.3	151.7	173.6	200.9	231.4
130°	95.8	98.6	102.2	108.7	116.8	126.9	138.4	153.7	172.8	197.4	224.8
132.5°	98.5	101.5	105.9	112.3	120.3	130.0	141.4	155.2	172.5	194.3	218.8
135°	102.8	106.2	110.7	117.2	125.4	134.7	145.2	157.3	172.2	190.2	210.5
137.5°	106.9	110.2	115.0	121.4	129.0	138.1	147.9	158.8	171.5	186.6	203.0
140°	109.9	112.9	117.8	123.8	131.5	140.3	149.4	159.7	171.3	184.3	198.7
142.5°	112.5	115.8	120.2	126.3	133.4	142.0	150.8	160.5	170.8	182.4	194.6
145°	116.8	119.6	124.2	129.3	136.3	144.2	152.4	160.9	170.0	179.8	189.6
147.5°	121.2	123.9	127.9	132.9	138.8	146.0	153.4	160.9	168.9	177.3	185.5
150°	124.2	126.6	130.5	134.7	140.3	147.2	153.7	160.9	168.0	175.6	182.5
152.5°	127.1	129.5	132.9	136.7	142.0	148.0	154.1	160.2	166.8	173.6	179.9
155°	131.7	133.5	136.6	140.0	144.2	149.4	154.3	159.5	164.6	170.7	175.9
157.5°	135.8	137.2	139.9	142.8	146.0	150.2	154.5	158.4	162.7	167.4	171.6
160°	138.4	139.7	142.1	144.2	147.2	150.9	154.5	157.9	161.3	165.2	169.2
162.5°	140.6	141.6	143.5	145.4	148.0	151.2	154.3	157.0	159.8	163.0	166.3
165°	143.6	144.2	145.8	147.0	149.1	151.5	153.7	155.5	157.6	160.1	162.5
167.5°	146.0	146.4	147.5	148.4	149.7	151.4	153.2	154.0	155.4	157.2	159.2
170°	147.2	147.6	148.4	149.1	149.7	151.2	152.4	153.1	153.9	155.5	157.0
172.5°	148.4	148.5	149.2	149.6	149.9	151.2	152.2	152.3	152.7	153.8	155.1
175°	149.7	149.4	150.0	150.0	150.3	150.9	151.5	151.2	151.2	151.8	152.4
177.5°	150.3	150.1	150.3	150.3	150.3	150.6	151.0	150.6	150.3	150.6	150.8
180°	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3

TEST NUMBER: P332242-935

CATALOG NUMBER: S123RDIP-S340D365U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	468.6	468.6	468.6	468.6	468.6	468.6	468.6
2.5°	494.3	494.3	494.9	497.3	497.7	499.7	499.1
5°	543.2	547.0	548.5	554.5	558.0	559.6	556.5
7.5°	603.0	613.8	618.9	625.3	630.8	632.5	628.1
10°	646.7	658.0	667.4	673.2	678.6	682.3	686.8
12.5°	688.9	702.7	711.7	719.9	725.5	730.0	730.8
15°	734.8	755.6	771.5	783.2	788.9	791.9	790.7
17.5°	781.0	800.4	811.7	823.5	831.6	832.0	832.2
20°	807.2	826.0	839.1	847.9	857.0	856.5	858.6
22.5°	824.7	839.6	849.5	855.9	859.0	857.5	857.9
25°	832.8	837.3	835.5	825.3	822.6	813.2	814.9
27.5°	790.7	769.8	748.2	720.5	698.5	681.1	681.9
30°	733.4	696.5	654.4	619.1	587.4	578.5	559.6
32.5°	653.3	598.0	548.6	515.7	488.5	481.1	464.7
35°	517.5	463.7	413.0	382.5	370.5	353.6	353.4
37.5°	402.3	354.9	328.1	305.2	293.3	283.0	282.1
40°	338.4	301.5	281.2	264.8	253.0	245.3	243.5
42.5°	293.8	264.0	245.0	234.8	225.7	221.7	218.8
45°	239.9	219.8	206.6	197.4	193.2	190.2	188.6
47.5°	200.7	187.3	178.2	172.0	168.7	165.5	166.3
50°	179.3	168.3	161.7	155.8	153.3	151.0	151.3
52.5°	162.1	152.2	146.9	142.7	139.5	137.8	137.2
55°	137.6	131.4	126.0	123.0	121.1	119.0	118.4
57.5°	117.4	112.5	108.1	104.8	104.3	102.2	102.5
60°	103.9	99.9	96.3	94.5	93.1	91.3	91.9
62.5°	92.8	89.5	86.2	84.7	83.3	82.0	82.2
65°	76.0	72.8	70.8	70.0	69.4	68.8	68.2
67.5°	60.6	58.6	57.3	55.6	54.4	54.2	53.6
70°	51.0	48.3	46.1	43.9	43.3	43.1	43.3
72.5°	40.8	39.2	38.6	37.5	37.4	36.9	37.2
75°	30.7	30.0	29.7	28.8	28.8	28.8	28.8
77.5°	22.6	22.3	22.0	21.9	21.7	21.4	21.4
80°	17.7	17.5	17.0	17.0	16.9	17.0	16.9
82.5°	13.3	13.3	12.9	12.9	12.7	12.6	12.7
85°	6.8	6.6	7.1	6.6	6.8	6.5	6.8
87.5°	3.5	3.5	3.5	3.4	3.4	3.8	3.4
90°	7.9	8.2	8.8	8.5	8.8	9.1	8.8
92.5°	20.3	17.9	16.4	15.8	14.9	15.2	14.6
95°	74.2	58.1	47.2	41.4	38.7	36.5	35.3
97.5°	218.7	179.4	143.1	120.6	106.9	98.7	96.1
100°	334.1	298.5	255.3	224.5	202.3	190.5	190.8
102.5°	386.4	365.7	338.3	314.4	296.8	286.9	279.8
105°	425.9	431.7	423.9	409.8	398.3	388.6	387.0
107.5°	420.9	447.6	458.5	458.7	454.8	451.5	448.8
110°	404.7	443.0	464.3	472.9	475.3	474.7	474.1

TEST NUMBER: P332242-935

CATALOG NUMBER: S123RDIP-S340D365U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	383.2	426.2	453.6	469.2	476.7	479.1	479.1
115°	349.0	393.7	426.9	449.7	463.0	469.2	470.7
117.5°	320.0	360.2	393.8	417.7	433.0	441.7	443.8
120°	303.9	340.4	371.2	395.2	412.2	419.6	421.4
122.5°	291.0	324.9	353.4	374.8	390.1	398.1	400.5
125°	275.1	304.3	328.6	348.1	361.4	369.1	371.2
127.5°	261.0	287.3	309.5	326.8	338.3	345.2	347.1
130°	252.3	276.9	297.6	313.7	324.7	331.1	333.5
132.5°	243.9	266.9	286.6	301.8	312.7	318.4	320.1
135°	232.1	251.9	269.2	284.2	293.3	298.8	300.9
137.5°	220.8	237.8	252.9	265.4	274.7	279.2	280.7
140°	214.2	228.8	241.9	253.5	262.0	266.8	266.6
142.5°	207.8	220.5	231.9	241.8	249.3	253.7	253.4
145°	199.6	209.3	218.2	225.8	232.1	234.6	235.2
147.5°	193.5	201.3	207.6	213.4	217.7	220.0	220.2
150°	189.6	196.0	201.7	206.3	209.7	211.5	211.5
152.5°	185.9	191.6	196.4	199.9	203.0	204.1	204.1
155°	180.7	185.3	188.9	191.7	194.2	194.8	195.0
157.5°	175.6	179.2	182.1	184.4	186.2	186.8	186.7
160°	172.5	175.6	177.7	179.8	181.7	181.7	181.3
162.5°	169.1	171.9	173.8	175.2	176.8	176.8	176.5
165°	164.3	166.4	168.0	169.2	170.4	170.0	170.0
167.5°	160.6	161.8	162.9	163.4	164.3	164.0	164.0
170°	157.9	159.1	159.7	160.1	160.7	160.3	160.3
172.5°	155.8	156.7	157.0	157.1	157.7	157.2	157.0
175°	152.7	153.3	153.3	153.3	153.7	153.3	153.1
177.5°	151.0	151.3	151.3	151.0	151.3	150.8	150.8
180°	150.3	150.3	150.3	150.3	150.3	150.3	150.3

(END OF REPORT)