

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332248-935

Luminaire Tested: **S123RDIP-S340D585U935-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332248-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S340D585U935-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 585 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2993.8 lumens
Efficiency: N/A
Efficacy: 116.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 25.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332248-935

CATALOG NUMBER: S123RDIP-S340D585U935-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332248-935

CATALOG NUMBER: S123RDIP-S340D585U935-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39
1	96	92	88	85	87	84	80	78	68	66	64	54	53	52	41	41	40	34
2	88	81	75	70	79	74	69	64	60	57	54	48	46	44	37	35	34	29
3	80	71	64	59	73	65	59	54	54	49	46	43	40	38	33	31	30	25
4	73	63	56	50	67	58	51	46	48	43	39	39	35	32	30	28	26	22
5	68	56	49	43	61	52	45	40	43	38	34	35	31	28	27	25	23	19
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	25	22	20	17
7	58	46	38	33	52	42	35	31	35	30	26	29	25	22	23	20	18	15
8	53	42	34	29	49	38	32	27	32	27	24	26	23	20	21	18	16	14
9	50	38	31	26	45	35	29	24	30	25	21	24	21	18	19	17	15	13
10	46	35	28	23	42	32	26	22	27	22	19	22	19	16	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5044	5044	5044	5044
5°	6013	5065	4460	5065
10°	7507	5037	4030	5037
15°	8811	4985	3675	4985
20°	9835	4907	3373	4907
25°	9678	4827	3188	4827
30°	6955	4753	2997	4753
35°	4644	4654	2872	4654
40°	3421	4539	2746	4539
45°	2871	4332	2620	4332
50°	2534	4064	2445	4064
55°	2222	3757	2205	3757
60°	1978	3462	2019	3462
65°	1737	3148	1880	3148
70°	1363	2867	1718	2867
75°	1198	2504	1568	2504
80°	1048	2126	1543	2126
85°	840	1717	1643	1717



TEST NUMBER: P332248-935

CATALOG NUMBER: S123RDIP-S340D585U935-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.1	1.5
10°-20°	144.0	4.8
20°-30°	226.2	7.6
30°-40°	236.0	7.9
40°-50°	201.9	6.7
50°-60°	153.9	5.1
60°-70°	98.7	3.3
70°-80°	47.5	1.6
80°-90°	14.4	0.5
90°-100°	135.0	4.5
100°-110°	382.3	12.8
110°-120°	376.1	12.6
120°-130°	300.0	10.0
130°-140°	236.5	7.9
140°-150°	176.5	5.9
150°-160°	123.0	4.1
160°-170°	72.3	2.4
170°-180°	23.5	0.8
0°-30°	416.2	13.9
0°-40°	652.2	21.8
0°-60°	1008.0	33.7
0°-90°	1168.6	39.0
90°-120°	893.4	29.8
90°-150°	1606.4	53.7
90°-180°	1825.0	61.0
0°-180°	2993.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	469	469	469	469	469	
5°	556	469	413	469	556	57
15°	791	447	330	447	791	224
25°	815	406	268	406	815	350
35°	353	354	219	354	353	232
45°	189	285	172	285	189	148
55°	118	200	118	200	118	107
65°	68	124	74	124	68	67
75°	29	60	38	60	29	31
85°	7	14	13	14	7	8
90°	14	1	14	1	14	8
95°	57	17	57	17	57	103
105°	625	57	625	57	625	616
115°	760	101	760	101	760	738
125°	599	140	599	140	599	543
135°	486	164	486	164	486	377
145°	380	187	380	187	380	241
155°	315	213	315	213	315	147
165°	274	232	274	232	274	78
175°	247	242	247	242	247	24
180°	243	243	243	243	243	



TEST NUMBER: P332248-935

CATALOG NUMBER: S123RDIP-S340D585U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6
2.5°	499.1	499.7	497.7	497.3	494.9	494.3	494.3	490.9	488.8	486.1	484.5
5°	556.5	559.6	558.0	554.5	548.5	547.0	543.2	537.2	530.4	521.9	518.0
7.5°	628.1	632.5	630.8	625.3	618.9	613.8	603.0	593.1	579.1	566.8	556.3
10°	686.8	682.3	678.6	673.2	667.4	658.0	646.7	631.3	613.5	599.3	583.8
12.5°	730.8	730.0	725.5	719.9	711.7	702.7	688.9	670.1	649.4	629.0	611.1
15°	790.7	791.9	788.9	783.2	771.5	755.6	734.8	726.9	697.2	675.2	653.2
17.5°	832.2	832.0	831.6	823.5	811.7	800.4	781.0	760.4	733.6	702.5	672.8
20°	858.6	856.5	857.0	847.9	839.1	826.0	807.2	777.3	755.3	719.4	688.6
22.5°	857.9	857.5	859.0	855.9	849.5	839.6	824.7	799.4	771.3	735.0	700.5
25°	814.9	813.2	822.6	825.3	835.5	837.3	832.8	819.1	792.4	755.0	712.3
27.5°	681.9	681.1	698.5	720.5	748.2	769.8	790.7	800.7	792.4	765.6	722.8
30°	559.6	578.5	587.4	619.1	654.4	696.5	733.4	768.4	777.1	765.4	730.4
32.5°	464.7	481.1	488.5	515.7	548.6	598.0	653.3	703.0	738.1	747.0	725.9
35°	353.4	353.6	370.5	382.5	413.0	463.7	517.5	584.1	650.3	700.5	705.7
37.5°	282.1	283.0	293.3	305.2	328.1	354.9	402.3	457.6	534.1	611.1	656.3
40°	243.5	245.3	253.0	264.8	281.2	301.5	338.4	390.5	454.3	540.0	610.0
42.5°	218.8	221.7	225.7	234.8	245.0	264.0	293.8	334.1	392.1	473.1	553.9
45°	188.6	190.2	193.2	197.4	206.6	219.8	239.9	267.0	315.1	380.3	461.2
47.5°	166.3	165.5	168.7	172.0	178.2	187.3	200.7	222.7	257.1	309.4	378.0
50°	151.3	151.0	153.3	155.8	161.7	168.3	179.3	196.0	223.3	266.6	329.4
52.5°	137.2	137.8	139.5	142.7	146.9	152.2	162.1	174.2	197.6	235.0	287.3
55°	118.4	119.0	121.1	123.0	126.0	131.4	137.6	147.7	163.7	189.8	232.9
57.5°	102.5	102.2	104.3	104.8	108.1	112.5	117.4	125.2	136.8	156.2	185.2
60°	91.9	91.3	93.1	94.5	96.3	99.9	103.9	111.5	120.8	135.0	159.9
62.5°	82.2	82.0	83.3	84.7	86.2	89.5	92.8	98.7	106.0	118.0	137.8
65°	68.2	68.8	69.4	70.0	70.8	72.8	76.0	80.1	85.1	93.5	107.7
67.5°	53.6	54.2	54.4	55.6	57.3	58.6	60.6	64.1	67.7	74.7	82.8
70°	43.3	43.1	43.3	43.9	46.1	48.3	51.0	53.6	55.8	60.8	67.6
72.5°	37.2	36.9	37.4	37.5	38.6	39.2	40.8	43.3	46.1	49.5	54.4
75°	28.8	28.8	28.8	28.8	29.7	30.0	30.7	31.3	32.3	33.9	37.5
77.5°	21.4	21.4	21.7	21.9	22.0	22.3	22.6	23.2	23.6	24.5	26.0
80°	16.9	17.0	16.9	17.0	17.0	17.5	17.7	18.3	18.4	19.5	20.1
82.5°	12.7	12.6	12.7	12.9	12.9	13.3	13.3	13.8	13.8	14.3	14.9
85°	6.8	6.5	6.8	6.6	7.1	6.6	6.8	7.2	7.2	7.4	8.3
87.5°	4.5	4.9	4.5	4.5	4.6	4.6	4.5	4.4	4.6	4.6	4.4
90°	14.2	14.7	14.2	13.8	14.2	13.3	12.7	12.3	11.8	12.3	10.8
92.5°	23.7	24.5	24.0	25.6	26.4	29.0	32.8	41.3	57.0	75.5	83.1
95°	57.0	58.9	62.3	66.8	76.1	93.8	119.9	176.8	236.2	291.2	259.3
97.5°	155.1	159.3	172.5	194.7	230.9	289.6	353.0	440.7	482.8	451.3	330.4
100°	307.9	307.5	326.6	362.4	412.0	481.7	539.2	579.0	561.8	465.0	314.3
102.5°	451.7	463.0	479.0	507.4	546.0	590.2	623.7	625.0	565.8	439.5	290.8
105°	624.7	627.2	642.8	661.5	684.1	696.9	687.5	638.4	535.8	394.9	261.7
107.5°	724.3	728.8	734.1	740.4	739.9	722.5	679.5	599.7	483.4	355.3	243.3
110°	765.1	766.1	767.1	763.2	749.4	715.1	653.2	562.7	450.3	332.9	236.2



TEST NUMBER: P332248-935

CATALOG NUMBER: S123RDIP-S340D585U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	773.4	773.2	769.5	757.2	732.1	687.9	618.5	526.2	421.6	318.1	232.3
115°	759.7	757.2	747.4	725.8	689.0	635.5	563.3	477.9	387.0	302.0	230.8
117.5°	716.3	713.0	698.8	674.1	635.7	581.3	516.5	442.7	366.1	292.6	231.7
120°	680.2	677.2	665.5	637.9	599.2	549.5	490.6	424.3	355.1	288.3	233.2
122.5°	646.4	642.7	629.6	604.9	570.4	524.3	469.8	409.7	346.0	285.5	236.0
125°	599.2	595.7	583.4	561.8	530.4	491.1	443.9	390.4	334.4	281.9	240.1
127.5°	560.3	557.1	546.0	527.5	499.6	463.8	421.3	373.5	324.3	280.1	244.9
130°	538.2	534.3	524.0	506.4	480.3	446.9	407.1	362.9	318.7	279.0	248.0
132.5°	516.6	513.8	504.7	487.1	462.6	430.8	393.7	353.1	313.6	278.5	250.4
135°	485.7	482.2	473.4	458.7	434.6	406.7	374.7	339.8	306.9	277.9	253.9
137.5°	453.0	450.7	443.2	428.3	408.1	383.8	356.4	327.8	301.2	276.9	256.2
140°	430.2	430.7	422.8	409.1	390.4	369.3	345.7	320.7	297.6	276.5	257.8
142.5°	409.0	409.5	402.4	390.2	374.3	355.9	335.5	314.0	294.5	275.7	259.0
145°	379.6	378.7	374.7	364.4	352.1	337.9	322.2	305.9	290.2	274.5	259.8
147.5°	355.4	355.1	351.3	344.3	335.0	324.9	312.2	299.4	286.1	272.7	259.8
150°	341.3	341.3	338.4	332.9	325.6	316.2	305.9	294.6	283.4	271.0	259.8
152.5°	329.5	329.5	327.8	322.7	316.9	309.2	300.1	290.3	280.3	269.1	258.6
155°	314.8	314.3	313.3	309.4	305.0	299.1	291.7	283.9	275.5	265.7	257.4
157.5°	301.4	301.4	300.7	297.7	293.9	289.3	283.5	277.0	270.2	262.6	255.6
160°	292.7	293.2	293.2	290.2	286.8	283.4	278.4	273.0	266.7	260.3	254.9
162.5°	284.8	285.3	285.3	282.8	280.5	277.5	272.9	268.4	263.1	258.0	253.3
165°	274.5	274.5	275.0	273.0	271.0	268.6	265.2	262.3	258.3	254.4	251.0
167.5°	264.7	264.7	265.2	263.8	262.9	261.1	259.2	256.9	253.7	250.8	248.6
170°	258.8	258.8	259.3	258.3	257.8	256.8	254.9	253.4	251.0	248.5	247.0
172.5°	253.3	253.7	254.6	253.6	253.5	252.9	251.3	250.3	248.2	246.5	245.8
175°	247.0	247.5	248.0	247.5	247.5	247.5	246.5	246.1	245.0	244.1	244.1
177.5°	243.4	243.4	244.2	243.7	244.2	244.2	243.7	243.4	243.0	242.6	243.0
180°	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6



TEST NUMBER: P332248-935

CATALOG NUMBER: S123RDIP-S340D585U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6
2.5°	483.8	483.4	481.1	478.5	475.2	472.9	471.1	470.2	467.3	463.7	461.4
5°	513.8	507.7	501.3	493.4	486.2	478.8	474.2	468.8	462.2	454.8	449.5
7.5°	545.7	533.9	521.2	508.1	495.2	483.5	473.2	464.4	453.9	443.2	435.8
10°	570.3	553.0	535.2	516.9	500.3	484.7	472.6	460.8	448.2	435.9	426.6
12.5°	592.6	569.9	549.3	526.8	505.6	486.9	469.6	455.6	440.4	427.4	416.9
15°	620.9	597.5	572.7	538.6	510.3	486.6	465.5	447.3	428.9	412.8	402.6
17.5°	647.2	612.3	578.8	550.4	513.6	484.1	458.3	436.5	416.2	399.2	386.6
20°	658.1	624.2	588.0	551.6	515.6	482.4	452.5	428.4	407.4	388.1	376.5
22.5°	664.7	626.4	588.1	549.1	510.7	476.3	446.8	420.3	397.4	379.2	364.8
25°	672.4	626.6	584.5	546.0	506.9	469.6	434.5	406.4	381.8	362.3	347.1
27.5°	677.4	623.6	573.9	531.1	491.4	454.3	422.1	392.3	367.2	346.6	330.3
30°	678.4	621.2	565.7	519.4	479.1	444.9	410.8	382.4	355.9	334.0	318.7
32.5°	679.7	615.3	554.6	505.4	464.1	430.3	399.4	372.2	345.1	323.6	308.0
35°	674.4	612.0	537.8	481.2	439.9	407.2	379.4	354.2	327.6	306.7	290.8
37.5°	651.6	599.0	520.4	454.0	410.8	380.6	357.8	336.0	311.5	289.0	274.1
40°	628.7	586.2	506.9	437.5	392.4	361.3	340.8	323.0	299.3	278.2	262.2
42.5°	594.5	568.6	494.0	420.2	371.5	341.6	324.3	307.5	286.8	265.4	250.3
45°	531.8	535.2	467.8	392.5	342.6	312.5	296.3	284.6	266.2	248.6	233.1
47.5°	453.1	485.0	437.0	363.2	312.2	284.0	269.8	259.6	247.1	229.8	215.7
50°	401.8	447.3	412.2	343.5	293.1	265.0	251.0	242.7	231.9	218.3	204.8
52.5°	354.5	403.4	382.4	321.4	272.3	246.7	233.0	226.2	217.6	204.7	192.6
55°	289.0	338.6	333.8	288.3	241.3	218.3	207.8	200.2	194.4	184.8	175.1
57.5°	233.8	280.8	283.3	251.3	214.0	191.1	182.2	176.4	172.6	165.4	156.4
60°	199.0	242.1	250.6	226.4	194.4	174.4	165.5	160.8	157.9	152.1	145.3
62.5°	170.1	206.8	216.4	199.1	175.6	156.8	149.9	145.5	143.4	138.4	132.4
65°	130.2	160.7	169.9	160.3	148.0	133.0	127.3	123.6	121.7	119.0	114.5
67.5°	97.9	120.1	130.3	123.5	119.0	109.5	106.0	103.9	102.3	100.4	96.7
70°	78.6	95.1	105.5	103.8	100.1	95.1	92.5	91.1	89.5	87.8	84.6
72.5°	63.2	74.6	84.3	85.2	82.3	81.3	79.0	78.4	77.4	75.5	73.7
75°	41.9	49.8	56.6	59.2	60.4	61.4	60.4	60.2	60.0	58.4	57.3
77.5°	27.5	31.7	36.0	40.5	42.4	43.7	44.0	44.8	44.2	43.4	42.9
80°	21.1	22.0	25.1	28.8	31.9	33.1	33.9	34.3	34.1	33.9	33.1
82.5°	15.3	16.1	17.6	20.2	22.7	24.7	25.2	25.1	25.6	25.7	25.1
85°	8.3	8.4	8.9	9.2	10.6	12.8	13.4	13.9	14.2	14.2	13.0
87.5°	4.4	4.0	4.0	3.8	4.1	4.0	4.7	5.3	5.7	5.3	5.5
90°	9.3	7.8	6.4	5.4	4.4	2.9	2.0	0.9	2.0	2.9	4.4
92.5°	62.3	41.2	28.4	21.1	17.0	13.2	9.0	6.1	9.0	13.2	17.0
95°	178.7	105.6	63.8	44.7	31.9	23.6	18.2	16.7	18.2	23.6	31.9
97.5°	196.1	113.7	73.8	53.0	40.5	33.2	29.0	28.5	29.0	33.2	40.5
100°	185.1	112.4	78.1	58.9	47.2	40.3	36.9	36.3	36.9	40.3	47.2
102.5°	175.7	114.0	83.2	65.6	55.0	48.6	45.5	44.6	45.5	48.6	55.0
105°	168.9	118.4	91.9	76.6	67.2	61.4	58.5	57.0	58.5	61.4	67.2
107.5°	168.4	126.4	103.1	89.0	80.2	74.5	71.6	70.1	71.6	74.5	80.2
110°	170.4	133.1	111.0	97.2	88.9	83.5	81.0	79.6	81.0	83.5	88.9



TEST NUMBER: P332248-935

CATALOG NUMBER: S123RDIP-S340D585U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	174.4	139.7	119.2	105.9	97.6	92.1	89.7	88.2	89.7	92.1	97.6
115°	180.7	150.8	132.1	118.8	110.5	105.6	102.6	100.7	102.6	105.6	110.5
117.5°	189.2	162.5	144.0	131.7	122.3	117.9	115.4	113.1	115.4	117.9	122.3
120°	195.4	169.9	152.2	140.0	130.6	125.7	123.3	121.8	123.3	125.7	130.6
122.5°	201.4	177.8	160.5	147.4	138.4	133.2	130.7	129.2	130.7	133.2	138.4
125°	210.7	189.1	171.9	158.6	149.3	143.9	140.9	140.0	140.9	143.9	149.3
127.5°	218.3	198.9	182.3	169.0	158.7	153.3	149.6	148.1	149.6	153.3	158.7
130°	223.4	204.7	188.6	175.3	165.0	159.1	154.7	153.3	154.7	159.1	165.0
132.5°	228.2	209.9	194.1	181.2	170.9	163.8	159.0	157.1	159.0	163.8	170.9
135°	234.3	217.6	202.3	189.1	178.7	171.4	166.0	164.0	166.0	171.4	178.7
137.5°	238.8	222.8	208.2	196.0	185.7	177.9	172.5	170.5	172.5	177.9	185.7
140°	241.2	226.4	212.2	199.8	190.0	182.2	177.3	174.9	177.3	182.2	190.0
142.5°	243.5	229.1	215.3	203.8	194.0	186.9	181.6	179.5	181.6	186.9	194.0
145°	246.1	232.8	220.0	208.7	200.4	193.0	188.6	187.1	188.6	193.0	200.4
147.5°	247.6	235.7	224.0	214.4	206.4	200.0	195.6	194.8	195.6	200.0	206.4
150°	248.0	237.7	226.4	217.6	210.7	204.3	200.4	199.8	200.4	204.3	210.7
152.5°	248.8	238.8	229.1	220.7	214.6	209.1	205.1	205.0	205.1	209.1	214.6
155°	249.0	241.2	232.8	225.9	220.5	215.6	212.7	212.7	212.7	215.6	220.5
157.5°	249.5	242.4	235.7	230.4	225.8	221.4	219.1	218.7	219.1	221.4	225.8
160°	249.5	243.6	237.7	232.8	229.4	225.4	223.4	223.4	223.4	225.4	229.4
162.5°	249.1	244.0	238.8	234.7	231.7	228.6	227.0	227.0	227.0	228.6	231.7
165°	248.0	244.5	240.6	237.2	235.2	232.8	231.8	232.3	231.8	232.8	235.2
167.5°	247.2	244.4	241.6	239.4	238.1	236.2	235.7	236.3	235.7	236.2	238.1
170°	246.1	244.1	241.6	240.6	239.6	238.2	237.7	238.7	237.7	238.2	239.6
172.5°	245.6	244.1	242.0	241.4	240.8	239.8	239.6	240.2	239.6	239.8	240.8
175°	244.5	243.6	242.6	242.1	242.1	241.2	241.6	242.1	241.6	241.2	242.1
177.5°	243.7	243.0	242.6	242.6	242.6	242.2	242.6	243.0	242.6	242.2	242.6
180°	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6



TEST NUMBER: P332248-935

CATALOG NUMBER: S123RDIP-S340D585U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6
2.5°	460.5	458.5	457.0	453.8	451.8	449.5	447.3	448.7	448.5	448.4	448.4
5°	445.1	440.5	436.3	430.8	427.5	423.3	420.1	419.7	420.4	417.7	416.0
7.5°	429.8	423.5	417.5	411.6	405.2	400.1	397.0	395.5	393.5	391.8	389.9
10°	419.0	411.6	405.8	398.4	391.6	385.6	381.8	379.1	377.7	376.3	373.7
12.5°	407.9	400.7	393.3	384.9	378.4	371.4	368.6	365.7	363.0	361.4	357.8
15°	391.8	382.4	374.5	365.7	358.4	351.6	347.7	341.8	341.0	339.0	335.4
17.5°	375.5	365.3	354.5	347.9	339.8	332.7	326.6	324.7	318.9	316.8	313.6
20°	362.7	353.3	345.0	336.4	324.6	318.0	313.1	310.6	305.9	303.1	301.1
22.5°	351.6	342.0	332.5	322.4	312.7	305.2	301.7	297.6	295.2	291.2	289.0
25°	335.8	325.4	313.9	303.1	296.1	290.5	284.8	281.2	277.6	275.8	271.8
27.5°	317.5	306.5	295.8	287.6	279.0	273.5	268.4	265.2	260.8	257.8	255.5
30°	307.3	294.5	285.2	277.8	266.8	261.6	257.8	253.7	250.6	247.4	245.1
32.5°	295.6	283.9	275.2	266.0	257.5	251.8	246.8	243.3	240.6	237.5	235.3
35°	277.2	267.4	258.4	249.2	242.9	237.1	231.3	228.3	225.7	222.8	220.8
37.5°	260.6	251.4	242.8	234.1	226.4	221.6	217.0	214.6	211.1	209.2	207.2
40°	250.4	241.3	232.1	223.7	215.7	212.1	207.8	204.4	201.2	199.8	197.6
42.5°	239.1	230.1	222.3	213.3	206.6	201.7	197.9	194.2	191.7	189.7	188.5
45°	222.5	214.5	206.8	197.8	191.6	187.4	183.0	179.5	177.4	175.9	173.7
47.5°	206.3	198.3	190.5	182.7	176.7	171.9	167.4	165.1	162.1	160.4	158.9
50°	194.6	187.4	179.2	171.9	165.9	161.1	157.5	154.5	151.9	149.6	148.6
52.5°	183.8	176.2	169.0	162.3	155.9	150.5	147.2	144.0	142.1	139.6	138.4
55°	166.1	158.7	152.7	146.0	139.8	135.2	131.2	128.4	126.4	123.6	122.0
57.5°	149.5	142.8	135.6	129.8	123.5	119.6	116.2	112.4	109.9	107.8	106.2
60°	138.2	130.6	124.3	119.0	113.3	108.3	105.3	102.3	99.7	97.5	96.1
62.5°	126.5	119.9	113.9	108.1	102.9	98.5	95.1	92.6	90.2	88.9	87.4
65°	108.5	103.3	97.3	92.5	87.6	84.5	81.6	79.5	77.8	76.8	75.6
67.5°	92.0	87.0	81.7	77.0	73.7	71.3	69.5	67.6	66.7	65.4	64.7
70°	81.3	76.0	71.4	67.8	64.6	62.8	61.6	60.2	59.4	57.8	57.0
72.5°	69.6	65.8	62.4	59.5	56.9	55.3	53.7	52.0	50.7	48.9	48.1
75°	54.8	51.3	48.7	46.8	45.1	43.0	40.7	38.9	38.3	37.7	37.5
77.5°	40.6	38.4	36.5	34.8	32.8	31.3	30.7	30.3	30.2	29.9	29.9
80°	31.9	29.9	28.5	26.5	25.3	25.3	25.3	24.9	25.1	25.1	25.1
82.5°	23.7	21.9	21.1	20.4	20.1	20.3	20.3	20.4	20.2	20.6	20.4
85°	12.2	12.4	12.8	12.7	12.8	12.8	13.3	13.0	13.3	12.8	13.3
87.5°	5.6	6.3	6.7	7.1	7.6	7.7	7.8	7.9	8.2	8.3	8.4
90°	5.4	6.4	7.8	9.3	10.8	12.3	11.8	12.3	12.7	13.3	14.2
92.5°	21.1	28.4	41.2	62.3	83.1	75.5	57.0	41.3	32.8	29.0	26.4
95°	44.7	63.8	105.6	178.7	259.3	291.2	236.2	176.8	119.9	93.8	76.1
97.5°	53.0	73.8	113.7	196.1	330.4	451.3	482.8	440.7	353.0	289.6	230.9
100°	58.9	78.1	112.4	185.1	314.3	465.0	561.8	579.0	539.2	481.7	412.0
102.5°	65.6	83.2	114.0	175.7	290.8	439.5	565.8	625.0	623.7	590.2	546.0
105°	76.6	91.9	118.4	168.9	261.7	394.9	535.8	638.4	687.5	696.9	684.1
107.5°	89.0	103.1	126.4	168.4	243.3	355.3	483.4	599.7	679.5	722.5	739.9
110°	97.2	111.0	133.1	170.4	236.2	332.9	450.3	562.7	653.2	715.1	749.4



TEST NUMBER: P332248-935

CATALOG NUMBER: S123RDIP-S340D585U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	105.9	119.2	139.7	174.4	232.3	318.1	421.6	526.2	618.5	687.9	732.1
115°	118.8	132.1	150.8	180.7	230.8	302.0	387.0	477.9	563.3	635.5	689.0
117.5°	131.7	144.0	162.5	189.2	231.7	292.6	366.1	442.7	516.5	581.3	635.7
120°	140.0	152.2	169.9	195.4	233.2	288.3	355.1	424.3	490.6	549.5	599.2
122.5°	147.4	160.5	177.8	201.4	236.0	285.5	346.0	409.7	469.8	524.3	570.4
125°	158.6	171.9	189.1	210.7	240.1	281.9	334.4	390.4	443.9	491.1	530.4
127.5°	169.0	182.3	198.9	218.3	244.9	280.1	324.3	373.5	421.3	463.8	499.6
130°	175.3	188.6	204.7	223.4	248.0	279.0	318.7	362.9	407.1	446.9	480.3
132.5°	181.2	194.1	209.9	228.2	250.4	278.5	313.6	353.1	393.7	430.8	462.6
135°	189.1	202.3	217.6	234.3	253.9	277.9	306.9	339.8	374.7	406.7	434.6
137.5°	196.0	208.2	222.8	238.8	256.2	276.9	301.2	327.8	356.4	383.8	408.1
140°	199.8	212.2	226.4	241.2	257.8	276.5	297.6	320.7	345.7	369.3	390.4
142.5°	203.8	215.3	229.1	243.5	259.0	275.7	294.5	314.0	335.5	355.9	374.3
145°	208.7	220.0	232.8	246.1	259.8	274.5	290.2	305.9	322.2	337.9	352.1
147.5°	214.4	224.0	235.7	247.6	259.8	272.7	286.1	299.4	312.2	324.9	335.0
150°	217.6	226.4	237.7	248.0	259.8	271.0	283.4	294.6	305.9	316.2	325.6
152.5°	220.7	229.1	238.8	248.8	258.6	269.1	280.3	290.3	300.1	309.2	316.9
155°	225.9	232.8	241.2	249.0	257.4	265.7	275.5	283.9	291.7	299.1	305.0
157.5°	230.4	235.7	242.4	249.5	255.6	262.6	270.2	277.0	283.5	289.3	293.9
160°	232.8	237.7	243.6	249.5	254.9	260.3	266.7	273.0	278.4	283.4	286.8
162.5°	234.7	238.8	244.0	249.1	253.3	258.0	263.1	268.4	272.9	277.5	280.5
165°	237.2	240.6	244.5	248.0	251.0	254.4	258.3	262.3	265.2	268.6	271.0
167.5°	239.4	241.6	244.4	247.2	248.6	250.8	253.7	256.9	259.2	261.1	262.9
170°	240.6	241.6	244.1	246.1	247.0	248.5	251.0	253.4	254.9	256.8	257.8
172.5°	241.4	242.0	244.1	245.6	245.8	246.5	248.2	250.3	251.3	252.9	253.5
175°	242.1	242.6	243.6	244.5	244.1	244.1	245.0	246.1	246.5	247.5	247.5
177.5°	242.6	242.6	243.0	243.7	243.0	242.6	243.0	243.4	243.7	244.2	244.2
180°	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6



TEST NUMBER: P332248-935

CATALOG NUMBER: S123RDIP-S340D585U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6
2.5°	446.4	446.3	446.4	445.8	446.4	446.3	446.4	448.4	448.4	448.5	448.7
5°	415.4	415.3	414.7	412.8	414.7	415.3	415.4	416.0	417.7	420.4	419.7
7.5°	388.3	388.1	386.3	386.3	386.3	388.1	388.3	389.9	391.8	393.5	395.5
10°	372.3	372.5	370.1	368.7	370.1	372.5	372.3	373.7	376.3	377.7	379.1
12.5°	356.7	355.9	353.9	352.3	353.9	355.9	356.7	357.8	361.4	363.0	365.7
15°	336.2	334.2	329.4	329.8	329.4	334.2	336.2	335.4	339.0	341.0	341.8
17.5°	312.0	310.6	310.5	307.6	310.5	310.6	312.0	313.6	316.8	318.9	324.7
20°	297.9	296.9	297.3	294.5	297.3	296.9	297.9	301.1	303.1	305.9	310.6
22.5°	286.8	285.8	284.1	283.3	284.1	285.8	286.8	289.0	291.2	295.2	297.6
25°	270.6	269.0	267.4	268.4	267.4	269.0	270.6	271.8	275.8	277.6	281.2
27.5°	254.4	253.2	251.6	251.4	251.6	253.2	254.4	255.5	257.8	260.8	265.2
30°	244.1	242.9	242.1	241.1	242.1	242.9	244.1	245.1	247.4	250.6	253.7
32.5°	233.7	233.4	232.0	231.8	232.0	233.4	233.7	235.3	237.5	240.6	243.3
35°	220.1	218.9	218.4	218.6	218.4	218.9	220.1	220.8	222.8	225.7	228.3
37.5°	207.1	205.5	204.7	204.1	204.7	205.5	207.1	207.2	209.2	211.1	214.6
40°	197.8	196.2	195.8	195.4	195.8	196.2	197.8	197.6	199.8	201.2	204.4
42.5°	187.4	186.8	186.5	185.7	186.5	186.8	187.4	188.5	189.7	191.7	194.2
45°	173.1	172.9	171.7	172.1	171.7	172.9	173.1	173.7	175.9	177.4	179.5
47.5°	158.1	157.2	156.4	157.0	156.4	157.2	158.1	158.9	160.4	162.1	165.1
50°	147.8	147.4	145.6	146.0	145.6	147.4	147.8	148.6	149.6	151.9	154.5
52.5°	137.6	136.0	135.3	135.1	135.3	136.0	137.6	138.4	139.6	142.1	144.0
55°	120.5	118.7	118.0	117.5	118.0	118.7	120.5	122.0	123.6	126.4	128.4
57.5°	103.8	103.4	102.7	103.1	102.7	103.4	103.8	106.2	107.8	109.9	112.4
60°	94.1	94.1	94.1	93.8	94.1	94.1	94.1	96.1	97.5	99.7	102.3
62.5°	86.5	86.0	85.9	86.2	85.9	86.0	86.5	87.4	88.9	90.2	92.6
65°	75.0	74.8	74.0	73.8	74.0	74.8	75.0	75.6	76.8	77.8	79.5
67.5°	64.1	63.5	63.2	62.9	63.2	63.5	64.1	64.7	65.4	66.7	67.6
70°	56.0	55.5	54.3	54.6	54.3	55.5	56.0	57.0	57.8	59.4	60.2
72.5°	47.2	46.8	46.5	46.2	46.5	46.8	47.2	48.1	48.9	50.7	52.0
75°	37.3	37.1	36.9	37.7	36.9	37.1	37.3	37.5	37.7	38.3	38.9
77.5°	29.9	29.9	30.0	29.7	30.0	29.9	29.9	29.9	29.9	30.2	30.3
80°	25.1	25.1	24.9	24.9	24.9	25.1	25.1	25.1	25.1	25.1	24.9
82.5°	20.1	20.2	20.4	20.1	20.4	20.2	20.1	20.4	20.6	20.2	20.4
85°	13.3	13.0	13.4	13.3	13.4	13.0	13.3	13.3	12.8	13.3	13.0
87.5°	8.7	8.4	8.5	8.6	8.5	8.4	8.7	8.4	8.3	8.2	7.9
90°	13.8	14.2	14.7	14.2	14.7	14.2	13.8	14.2	13.3	12.7	12.3
92.5°	25.6	24.0	24.5	23.7	24.5	24.0	25.6	26.4	29.0	32.8	41.3
95°	66.8	62.3	58.9	57.0	58.9	62.3	66.8	76.1	93.8	119.9	176.8
97.5°	194.7	172.5	159.3	155.1	159.3	172.5	194.7	230.9	289.6	353.0	440.7
100°	362.4	326.6	307.5	307.9	307.5	326.6	362.4	412.0	481.7	539.2	579.0
102.5°	507.4	479.0	463.0	451.7	463.0	479.0	507.4	546.0	590.2	623.7	625.0
105°	661.5	642.8	627.2	624.7	627.2	642.8	661.5	684.1	696.9	687.5	638.4
107.5°	740.4	734.1	728.8	724.3	728.8	734.1	740.4	739.9	722.5	679.5	599.7
110°	763.2	767.1	766.1	765.1	766.1	767.1	763.2	749.4	715.1	653.2	562.7



TEST NUMBER: P332248-935

CATALOG NUMBER: S123RDIP-S340D585U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	757.2	769.5	773.2	773.4	773.2	769.5	757.2	732.1	687.9	618.5	526.2
115°	725.8	747.4	757.2	759.7	757.2	747.4	725.8	689.0	635.5	563.3	477.9
117.5°	674.1	698.8	713.0	716.3	713.0	698.8	674.1	635.7	581.3	516.5	442.7
120°	637.9	665.5	677.2	680.2	677.2	665.5	637.9	599.2	549.5	490.6	424.3
122.5°	604.9	629.6	642.7	646.4	642.7	629.6	604.9	570.4	524.3	469.8	409.7
125°	561.8	583.4	595.7	599.2	595.7	583.4	561.8	530.4	491.1	443.9	390.4
127.5°	527.5	546.0	557.1	560.3	557.1	546.0	527.5	499.6	463.8	421.3	373.5
130°	506.4	524.0	534.3	538.2	534.3	524.0	506.4	480.3	446.9	407.1	362.9
132.5°	487.1	504.7	513.8	516.6	513.8	504.7	487.1	462.6	430.8	393.7	353.1
135°	458.7	473.4	482.2	485.7	482.2	473.4	458.7	434.6	406.7	374.7	339.8
137.5°	428.3	443.2	450.7	453.0	450.7	443.2	428.3	408.1	383.8	356.4	327.8
140°	409.1	422.8	430.7	430.2	430.7	422.8	409.1	390.4	369.3	345.7	320.7
142.5°	390.2	402.4	409.5	409.0	409.5	402.4	390.2	374.3	355.9	335.5	314.0
145°	364.4	374.7	378.7	379.6	378.7	374.7	364.4	352.1	337.9	322.2	305.9
147.5°	344.3	351.3	355.1	355.4	355.1	351.3	344.3	335.0	324.9	312.2	299.4
150°	332.9	338.4	341.3	341.3	341.3	338.4	332.9	325.6	316.2	305.9	294.6
152.5°	322.7	327.8	329.5	329.5	329.5	327.8	322.7	316.9	309.2	300.1	290.3
155°	309.4	313.3	314.3	314.8	314.3	313.3	309.4	305.0	299.1	291.7	283.9
157.5°	297.7	300.7	301.4	301.4	301.4	300.7	297.7	293.9	289.3	283.5	277.0
160°	290.2	293.2	293.2	292.7	293.2	293.2	290.2	286.8	283.4	278.4	273.0
162.5°	282.8	285.3	285.3	284.8	285.3	285.3	282.8	280.5	277.5	272.9	268.4
165°	273.0	275.0	274.5	274.5	274.5	275.0	273.0	271.0	268.6	265.2	262.3
167.5°	263.8	265.2	264.7	264.7	264.7	265.2	263.8	262.9	261.1	259.2	256.9
170°	258.3	259.3	258.8	258.8	258.8	259.3	258.3	257.8	256.8	254.9	253.4
172.5°	253.6	254.6	253.7	253.3	253.7	254.6	253.6	253.5	252.9	251.3	250.3
175°	247.5	248.0	247.5	247.0	247.5	248.0	247.5	247.5	247.5	246.5	246.1
177.5°	243.7	244.2	243.4	243.4	243.4	244.2	243.7	244.2	244.2	243.7	243.4
180°	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6



TEST NUMBER: P332248-935

CATALOG NUMBER: S123RDIP-S340D585U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6
2.5°	447.3	449.5	451.8	453.8	457.0	458.5	460.5	461.4	463.7	467.3	470.2
5°	420.1	423.3	427.5	430.8	436.3	440.5	445.1	449.5	454.8	462.2	468.8
7.5°	397.0	400.1	405.2	411.6	417.5	423.5	429.8	435.8	443.2	453.9	464.4
10°	381.8	385.6	391.6	398.4	405.8	411.6	419.0	426.6	435.9	448.2	460.8
12.5°	368.6	371.4	378.4	384.9	393.3	400.7	407.9	416.9	427.4	440.4	455.6
15°	347.7	351.6	358.4	365.7	374.5	382.4	391.8	402.6	412.8	428.9	447.3
17.5°	326.6	332.7	339.8	347.9	354.5	365.3	375.5	386.6	399.2	416.2	436.5
20°	313.1	318.0	324.6	336.4	345.0	353.3	362.7	376.5	388.1	407.4	428.4
22.5°	301.7	305.2	312.7	322.4	332.5	342.0	351.6	364.8	379.2	397.4	420.3
25°	284.8	290.5	296.1	303.1	313.9	325.4	335.8	347.1	362.3	381.8	406.4
27.5°	268.4	273.5	279.0	287.6	295.8	306.5	317.5	330.3	346.6	367.2	392.3
30°	257.8	261.6	266.8	277.8	285.2	294.5	307.3	318.7	334.0	355.9	382.4
32.5°	246.8	251.8	257.5	266.0	275.2	283.9	295.6	308.0	323.6	345.1	372.2
35°	231.3	237.1	242.9	249.2	258.4	267.4	277.2	290.8	306.7	327.6	354.2
37.5°	217.0	221.6	226.4	234.1	242.8	251.4	260.6	274.1	289.0	311.5	336.0
40°	207.8	212.1	215.7	223.7	232.1	241.3	250.4	262.2	278.2	299.3	323.0
42.5°	197.9	201.7	206.6	213.3	222.3	230.1	239.1	250.3	265.4	286.8	307.5
45°	183.0	187.4	191.6	197.8	206.8	214.5	222.5	233.1	248.6	266.2	284.6
47.5°	167.4	171.9	176.7	182.7	190.5	198.3	206.3	215.7	229.8	247.1	259.6
50°	157.5	161.1	165.9	171.9	179.2	187.4	194.6	204.8	218.3	231.9	242.7
52.5°	147.2	150.5	155.9	162.3	169.0	176.2	183.8	192.6	204.7	217.6	226.2
55°	131.2	135.2	139.8	146.0	152.7	158.7	166.1	175.1	184.8	194.4	200.2
57.5°	116.2	119.6	123.5	129.8	135.6	142.8	149.5	156.4	165.4	172.6	176.4
60°	105.3	108.3	113.3	119.0	124.3	130.6	138.2	145.3	152.1	157.9	160.8
62.5°	95.1	98.5	102.9	108.1	113.9	119.9	126.5	132.4	138.4	143.4	145.5
65°	81.6	84.5	87.6	92.5	97.3	103.3	108.5	114.5	119.0	121.7	123.6
67.5°	69.5	71.3	73.7	77.0	81.7	87.0	92.0	96.7	100.4	102.3	103.9
70°	61.6	62.8	64.6	67.8	71.4	76.0	81.3	84.6	87.8	89.5	91.1
72.5°	53.7	55.3	56.9	59.5	62.4	65.8	69.6	73.7	75.5	77.4	78.4
75°	40.7	43.0	45.1	46.8	48.7	51.3	54.8	57.3	58.4	60.0	60.2
77.5°	30.7	31.3	32.8	34.8	36.5	38.4	40.6	42.9	43.4	44.2	44.8
80°	25.3	25.3	25.3	26.5	28.5	29.9	31.9	33.1	33.9	34.1	34.3
82.5°	20.3	20.3	20.1	20.4	21.1	21.9	23.7	25.1	25.7	25.6	25.1
85°	13.3	12.8	12.8	12.7	12.8	12.4	12.2	13.0	14.2	14.2	13.9
87.5°	7.8	7.7	7.6	7.1	6.7	6.3	5.6	5.5	5.3	5.7	5.3
90°	11.8	12.3	10.8	9.3	7.8	6.4	5.4	4.4	2.9	2.0	0.9
92.5°	57.0	75.5	83.1	62.3	41.2	28.4	21.1	17.0	13.2	9.0	6.1
95°	236.2	291.2	259.3	178.7	105.6	63.8	44.7	31.9	23.6	18.2	16.7
97.5°	482.8	451.3	330.4	196.1	113.7	73.8	53.0	40.5	33.2	29.0	28.5
100°	561.8	465.0	314.3	185.1	112.4	78.1	58.9	47.2	40.3	36.9	36.3
102.5°	565.8	439.5	290.8	175.7	114.0	83.2	65.6	55.0	48.6	45.5	44.6
105°	535.8	394.9	261.7	168.9	118.4	91.9	76.6	67.2	61.4	58.5	57.0
107.5°	483.4	355.3	243.3	168.4	126.4	103.1	89.0	80.2	74.5	71.6	70.1
110°	450.3	332.9	236.2	170.4	133.1	111.0	97.2	88.9	83.5	81.0	79.6



TEST NUMBER: P332248-935

CATALOG NUMBER: S123RDIP-S340D585U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	421.6	318.1	232.3	174.4	139.7	119.2	105.9	97.6	92.1	89.7	88.2
115°	387.0	302.0	230.8	180.7	150.8	132.1	118.8	110.5	105.6	102.6	100.7
117.5°	366.1	292.6	231.7	189.2	162.5	144.0	131.7	122.3	117.9	115.4	113.1
120°	355.1	288.3	233.2	195.4	169.9	152.2	140.0	130.6	125.7	123.3	121.8
122.5°	346.0	285.5	236.0	201.4	177.8	160.5	147.4	138.4	133.2	130.7	129.2
125°	334.4	281.9	240.1	210.7	189.1	171.9	158.6	149.3	143.9	140.9	140.0
127.5°	324.3	280.1	244.9	218.3	198.9	182.3	169.0	158.7	153.3	149.6	148.1
130°	318.7	279.0	248.0	223.4	204.7	188.6	175.3	165.0	159.1	154.7	153.3
132.5°	313.6	278.5	250.4	228.2	209.9	194.1	181.2	170.9	163.8	159.0	157.1
135°	306.9	277.9	253.9	234.3	217.6	202.3	189.1	178.7	171.4	166.0	164.0
137.5°	301.2	276.9	256.2	238.8	222.8	208.2	196.0	185.7	177.9	172.5	170.5
140°	297.6	276.5	257.8	241.2	226.4	212.2	199.8	190.0	182.2	177.3	174.9
142.5°	294.5	275.7	259.0	243.5	229.1	215.3	203.8	194.0	186.9	181.6	179.5
145°	290.2	274.5	259.8	246.1	232.8	220.0	208.7	200.4	193.0	188.6	187.1
147.5°	286.1	272.7	259.8	247.6	235.7	224.0	214.4	206.4	200.0	195.6	194.8
150°	283.4	271.0	259.8	248.0	237.7	226.4	217.6	210.7	204.3	200.4	199.8
152.5°	280.3	269.1	258.6	248.8	238.8	229.1	220.7	214.6	209.1	205.1	205.0
155°	275.5	265.7	257.4	249.0	241.2	232.8	225.9	220.5	215.6	212.7	212.7
157.5°	270.2	262.6	255.6	249.5	242.4	235.7	230.4	225.8	221.4	219.1	218.7
160°	266.7	260.3	254.9	249.5	243.6	237.7	232.8	229.4	225.4	223.4	223.4
162.5°	263.1	258.0	253.3	249.1	244.0	238.8	234.7	231.7	228.6	227.0	227.0
165°	258.3	254.4	251.0	248.0	244.5	240.6	237.2	235.2	232.8	231.8	232.3
167.5°	253.7	250.8	248.6	247.2	244.4	241.6	239.4	238.1	236.2	235.7	236.3
170°	251.0	248.5	247.0	246.1	244.1	241.6	240.6	239.6	238.2	237.7	238.7
172.5°	248.2	246.5	245.8	245.6	244.1	242.0	241.4	240.8	239.8	239.6	240.2
175°	245.0	244.1	244.1	244.5	243.6	242.6	242.1	242.1	241.2	241.6	242.1
177.5°	243.0	242.6	243.0	243.7	243.0	242.6	242.6	242.6	242.2	242.6	243.0
180°	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6



TEST NUMBER: P332248-935

CATALOG NUMBER: S123RDIP-S340D585U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6
2.5°	471.1	472.9	475.2	478.5	481.1	483.4	483.8	484.5	486.1	488.8	490.9
5°	474.2	478.8	486.2	493.4	501.3	507.7	513.8	518.0	521.9	530.4	537.2
7.5°	473.2	483.5	495.2	508.1	521.2	533.9	545.7	556.3	566.8	579.1	593.1
10°	472.6	484.7	500.3	516.9	535.2	553.0	570.3	583.8	599.3	613.5	631.3
12.5°	469.6	486.9	505.6	526.8	549.3	569.9	592.6	611.1	629.0	649.4	670.1
15°	465.5	486.6	510.3	538.6	572.7	597.5	620.9	653.2	675.2	697.2	726.9
17.5°	458.3	484.1	513.6	550.4	578.8	612.3	647.2	672.8	702.5	733.6	760.4
20°	452.5	482.4	515.6	551.6	588.0	624.2	658.1	688.6	719.4	755.3	777.3
22.5°	446.8	476.3	510.7	549.1	588.1	626.4	664.7	700.5	735.0	771.3	799.4
25°	434.5	469.6	506.9	546.0	584.5	626.6	672.4	712.3	755.0	792.4	819.1
27.5°	422.1	454.3	491.4	531.1	573.9	623.6	677.4	722.8	765.6	792.4	800.7
30°	410.8	444.9	479.1	519.4	565.7	621.2	678.4	730.4	765.4	777.1	768.4
32.5°	399.4	430.3	464.1	505.4	554.6	615.3	679.7	725.9	747.0	738.1	703.0
35°	379.4	407.2	439.9	481.2	537.8	612.0	674.4	705.7	700.5	650.3	584.1
37.5°	357.8	380.6	410.8	454.0	520.4	599.0	651.6	656.3	611.1	534.1	457.6
40°	340.8	361.3	392.4	437.5	506.9	586.2	628.7	610.0	540.0	454.3	390.5
42.5°	324.3	341.6	371.5	420.2	494.0	568.6	594.5	553.9	473.1	392.1	334.1
45°	296.3	312.5	342.6	392.5	467.8	535.2	531.8	461.2	380.3	315.1	267.0
47.5°	269.8	284.0	312.2	363.2	437.0	485.0	453.1	378.0	309.4	257.1	222.7
50°	251.0	265.0	293.1	343.5	412.2	447.3	401.8	329.4	266.6	223.3	196.0
52.5°	233.0	246.7	272.3	321.4	382.4	403.4	354.5	287.3	235.0	197.6	174.2
55°	207.8	218.3	241.3	288.3	333.8	338.6	289.0	232.9	189.8	163.7	147.7
57.5°	182.2	191.1	214.0	251.3	283.3	280.8	233.8	185.2	156.2	136.8	125.2
60°	165.5	174.4	194.4	226.4	250.6	242.1	199.0	159.9	135.0	120.8	111.5
62.5°	149.9	156.8	175.6	199.1	216.4	206.8	170.1	137.8	118.0	106.0	98.7
65°	127.3	133.0	148.0	160.3	169.9	160.7	130.2	107.7	93.5	85.1	80.1
67.5°	106.0	109.5	119.0	123.5	130.3	120.1	97.9	82.8	74.7	67.7	64.1
70°	92.5	95.1	100.1	103.8	105.5	95.1	78.6	67.6	60.8	55.8	53.6
72.5°	79.0	81.3	82.3	85.2	84.3	74.6	63.2	54.4	49.5	46.1	43.3
75°	60.4	61.4	60.4	59.2	56.6	49.8	41.9	37.5	33.9	32.3	31.3
77.5°	44.0	43.7	42.4	40.5	36.0	31.7	27.5	26.0	24.5	23.6	23.2
80°	33.9	33.1	31.9	28.8	25.1	22.0	21.1	20.1	19.5	18.4	18.3
82.5°	25.2	24.7	22.7	20.2	17.6	16.1	15.3	14.9	14.3	13.8	13.8
85°	13.4	12.8	10.6	9.2	8.9	8.4	8.3	8.3	7.4	7.2	7.2
87.5°	4.7	4.0	4.1	3.8	4.0	4.0	4.4	4.4	4.6	4.6	4.4
90°	2.0	2.9	4.4	5.4	6.4	7.8	9.3	10.8	12.3	11.8	12.3
92.5°	9.0	13.2	17.0	21.1	28.4	41.2	62.3	83.1	75.5	57.0	41.3
95°	18.2	23.6	31.9	44.7	63.8	105.6	178.7	259.3	291.2	236.2	176.8
97.5°	29.0	33.2	40.5	53.0	73.8	113.7	196.1	330.4	451.3	482.8	440.7
100°	36.9	40.3	47.2	58.9	78.1	112.4	185.1	314.3	465.0	561.8	579.0
102.5°	45.5	48.6	55.0	65.6	83.2	114.0	175.7	290.8	439.5	565.8	625.0
105°	58.5	61.4	67.2	76.6	91.9	118.4	168.9	261.7	394.9	535.8	638.4
107.5°	71.6	74.5	80.2	89.0	103.1	126.4	168.4	243.3	355.3	483.4	599.7
110°	81.0	83.5	88.9	97.2	111.0	133.1	170.4	236.2	332.9	450.3	562.7



TEST NUMBER: P332248-935

CATALOG NUMBER: S123RDIP-S340D585U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	89.7	92.1	97.6	105.9	119.2	139.7	174.4	232.3	318.1	421.6	526.2
115°	102.6	105.6	110.5	118.8	132.1	150.8	180.7	230.8	302.0	387.0	477.9
117.5°	115.4	117.9	122.3	131.7	144.0	162.5	189.2	231.7	292.6	366.1	442.7
120°	123.3	125.7	130.6	140.0	152.2	169.9	195.4	233.2	288.3	355.1	424.3
122.5°	130.7	133.2	138.4	147.4	160.5	177.8	201.4	236.0	285.5	346.0	409.7
125°	140.9	143.9	149.3	158.6	171.9	189.1	210.7	240.1	281.9	334.4	390.4
127.5°	149.6	153.3	158.7	169.0	182.3	198.9	218.3	244.9	280.1	324.3	373.5
130°	154.7	159.1	165.0	175.3	188.6	204.7	223.4	248.0	279.0	318.7	362.9
132.5°	159.0	163.8	170.9	181.2	194.1	209.9	228.2	250.4	278.5	313.6	353.1
135°	166.0	171.4	178.7	189.1	202.3	217.6	234.3	253.9	277.9	306.9	339.8
137.5°	172.5	177.9	185.7	196.0	208.2	222.8	238.8	256.2	276.9	301.2	327.8
140°	177.3	182.2	190.0	199.8	212.2	226.4	241.2	257.8	276.5	297.6	320.7
142.5°	181.6	186.9	194.0	203.8	215.3	229.1	243.5	259.0	275.7	294.5	314.0
145°	188.6	193.0	200.4	208.7	220.0	232.8	246.1	259.8	274.5	290.2	305.9
147.5°	195.6	200.0	206.4	214.4	224.0	235.7	247.6	259.8	272.7	286.1	299.4
150°	200.4	204.3	210.7	217.6	226.4	237.7	248.0	259.8	271.0	283.4	294.6
152.5°	205.1	209.1	214.6	220.7	229.1	238.8	248.8	258.6	269.1	280.3	290.3
155°	212.7	215.6	220.5	225.9	232.8	241.2	249.0	257.4	265.7	275.5	283.9
157.5°	219.1	221.4	225.8	230.4	235.7	242.4	249.5	255.6	262.6	270.2	277.0
160°	223.4	225.4	229.4	232.8	237.7	243.6	249.5	254.9	260.3	266.7	273.0
162.5°	227.0	228.6	231.7	234.7	238.8	244.0	249.1	253.3	258.0	263.1	268.4
165°	231.8	232.8	235.2	237.2	240.6	244.5	248.0	251.0	254.4	258.3	262.3
167.5°	235.7	236.2	238.1	239.4	241.6	244.4	247.2	248.6	250.8	253.7	256.9
170°	237.7	238.2	239.6	240.6	241.6	244.1	246.1	247.0	248.5	251.0	253.4
172.5°	239.6	239.8	240.8	241.4	242.0	244.1	245.6	245.8	246.5	248.2	250.3
175°	241.6	241.2	242.1	242.1	242.6	243.6	244.5	244.1	244.1	245.0	246.1
177.5°	242.6	242.2	242.6	242.6	242.6	243.0	243.7	243.0	242.6	243.0	243.4
180°	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6



TEST NUMBER: P332248-935

CATALOG NUMBER: S123RDIP-S340D585U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	468.6	468.6	468.6	468.6	468.6	468.6	468.6
2.5°	494.3	494.3	494.9	497.3	497.7	499.7	499.1
5°	543.2	547.0	548.5	554.5	558.0	559.6	556.5
7.5°	603.0	613.8	618.9	625.3	630.8	632.5	628.1
10°	646.7	658.0	667.4	673.2	678.6	682.3	686.8
12.5°	688.9	702.7	711.7	719.9	725.5	730.0	730.8
15°	734.8	755.6	771.5	783.2	788.9	791.9	790.7
17.5°	781.0	800.4	811.7	823.5	831.6	832.0	832.2
20°	807.2	826.0	839.1	847.9	857.0	856.5	858.6
22.5°	824.7	839.6	849.5	855.9	859.0	857.5	857.9
25°	832.8	837.3	835.5	825.3	822.6	813.2	814.9
27.5°	790.7	769.8	748.2	720.5	698.5	681.1	681.9
30°	733.4	696.5	654.4	619.1	587.4	578.5	559.6
32.5°	653.3	598.0	548.6	515.7	488.5	481.1	464.7
35°	517.5	463.7	413.0	382.5	370.5	353.6	353.4
37.5°	402.3	354.9	328.1	305.2	293.3	283.0	282.1
40°	338.4	301.5	281.2	264.8	253.0	245.3	243.5
42.5°	293.8	264.0	245.0	234.8	225.7	221.7	218.8
45°	239.9	219.8	206.6	197.4	193.2	190.2	188.6
47.5°	200.7	187.3	178.2	172.0	168.7	165.5	166.3
50°	179.3	168.3	161.7	155.8	153.3	151.0	151.3
52.5°	162.1	152.2	146.9	142.7	139.5	137.8	137.2
55°	137.6	131.4	126.0	123.0	121.1	119.0	118.4
57.5°	117.4	112.5	108.1	104.8	104.3	102.2	102.5
60°	103.9	99.9	96.3	94.5	93.1	91.3	91.9
62.5°	92.8	89.5	86.2	84.7	83.3	82.0	82.2
65°	76.0	72.8	70.8	70.0	69.4	68.8	68.2
67.5°	60.6	58.6	57.3	55.6	54.4	54.2	53.6
70°	51.0	48.3	46.1	43.9	43.3	43.1	43.3
72.5°	40.8	39.2	38.6	37.5	37.4	36.9	37.2
75°	30.7	30.0	29.7	28.8	28.8	28.8	28.8
77.5°	22.6	22.3	22.0	21.9	21.7	21.4	21.4
80°	17.7	17.5	17.0	17.0	16.9	17.0	16.9
82.5°	13.3	13.3	12.9	12.9	12.7	12.6	12.7
85°	6.8	6.6	7.1	6.6	6.8	6.5	6.8
87.5°	4.5	4.6	4.6	4.5	4.5	4.9	4.5
90°	12.7	13.3	14.2	13.8	14.2	14.7	14.2
92.5°	32.8	29.0	26.4	25.6	24.0	24.5	23.7
95°	119.9	93.8	76.1	66.8	62.3	58.9	57.0
97.5°	353.0	289.6	230.9	194.7	172.5	159.3	155.1
100°	539.2	481.7	412.0	362.4	326.6	307.5	307.9
102.5°	623.7	590.2	546.0	507.4	479.0	463.0	451.7
105°	687.5	696.9	684.1	661.5	642.8	627.2	624.7
107.5°	679.5	722.5	739.9	740.4	734.1	728.8	724.3
110°	653.2	715.1	749.4	763.2	767.1	766.1	765.1



TEST NUMBER: P332248-935

CATALOG NUMBER: S123RDIP-S340D585U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	618.5	687.9	732.1	757.2	769.5	773.2	773.4
115°	563.3	635.5	689.0	725.8	747.4	757.2	759.7
117.5°	516.5	581.3	635.7	674.1	698.8	713.0	716.3
120°	490.6	549.5	599.2	637.9	665.5	677.2	680.2
122.5°	469.8	524.3	570.4	604.9	629.6	642.7	646.4
125°	443.9	491.1	530.4	561.8	583.4	595.7	599.2
127.5°	421.3	463.8	499.6	527.5	546.0	557.1	560.3
130°	407.1	446.9	480.3	506.4	524.0	534.3	538.2
132.5°	393.7	430.8	462.6	487.1	504.7	513.8	516.6
135°	374.7	406.7	434.6	458.7	473.4	482.2	485.7
137.5°	356.4	383.8	408.1	428.3	443.2	450.7	453.0
140°	345.7	369.3	390.4	409.1	422.8	430.7	430.2
142.5°	335.5	355.9	374.3	390.2	402.4	409.5	409.0
145°	322.2	337.9	352.1	364.4	374.7	378.7	379.6
147.5°	312.2	324.9	335.0	344.3	351.3	355.1	355.4
150°	305.9	316.2	325.6	332.9	338.4	341.3	341.3
152.5°	300.1	309.2	316.9	322.7	327.8	329.5	329.5
155°	291.7	299.1	305.0	309.4	313.3	314.3	314.8
157.5°	283.5	289.3	293.9	297.7	300.7	301.4	301.4
160°	278.4	283.4	286.8	290.2	293.2	293.2	292.7
162.5°	272.9	277.5	280.5	282.8	285.3	285.3	284.8
165°	265.2	268.6	271.0	273.0	275.0	274.5	274.5
167.5°	259.2	261.1	262.9	263.8	265.2	264.7	264.7
170°	254.9	256.8	257.8	258.3	259.3	258.8	258.8
172.5°	251.3	252.9	253.5	253.6	254.6	253.7	253.3
175°	246.5	247.5	247.5	247.5	248.0	247.5	247.0
177.5°	243.7	244.2	244.2	243.7	244.2	243.4	243.4
180°	242.6	242.6	242.6	242.6	242.6	242.6	242.6

(END OF REPORT)