

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332296-935

Luminaire Tested: **S123RDIP-S560D1195U935-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332296-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S560D1195U935-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1195 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5639.8 lumens
Efficiency: N/A
Efficacy: 114.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 49.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332296-935

CATALOG NUMBER: S123RDIP-S560D1195U935-4F0-1E-UDD-A4

Luminous Intensity Polar Plot



TEST NUMBER: P332296-935

CATALOG NUMBER: S123RDIP-S560D1195U935-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	34			
1	95	91	87	84	85	82	79	76	66	64	62	51	50	48	37	36	36	29			
2	86	79	74	69	78	72	67	63	58	55	52	45	43	41	33	32	31	25			
3	79	70	63	58	71	64	58	53	52	47	44	40	37	35	30	28	27	22			
4	72	62	55	49	65	57	50	45	46	41	38	36	33	30	27	25	23	19			
5	67	56	48	42	60	51	44	39	41	36	33	32	29	26	24	22	20	17			
6	61	50	42	37	55	45	39	34	37	32	29	29	26	23	22	20	18	15			
7	57	45	37	32	51	41	34	30	34	29	25	27	23	21	20	18	16	13			
8	53	41	33	28	47	37	31	26	31	26	22	25	21	18	19	16	15	12			
9	49	37	30	25	44	34	28	23	28	23	20	23	19	17	17	15	13	11			
10	46	34	27	23	41	31	25	21	26	21	18	21	17	15	16	14	12	10			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8291	8291	8291	8291
5°	9884	8327	7333	8327
10°	12342	8279	6625	8279
15°	14487	8195	6042	8195
20°	16167	8069	5545	8069
25°	15909	7935	5241	7935
30°	11436	7812	4927	7812
35°	7636	7653	4724	7653
40°	5626	7461	4513	7461
45°	4719	7124	4306	7124
50°	4165	6683	4019	6683
55°	3652	6178	3626	6178
60°	3251	5694	3324	5694
65°	2855	5173	3092	5173
70°	2241	4711	2823	4711
75°	1975	4113	2578	4113
80°	1717	3496	2535	3496
85°	1383	2803	2692	2803

TEST NUMBER: P332296-935

CATALOG NUMBER: S123RDIP-S560D1195U935-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	75.8	1.3
10°-20°	236.7	4.2
20°-30°	371.8	6.6
30°-40°	387.9	6.9
40°-50°	332.0	5.9
50°-60°	253.0	4.5
60°-70°	162.2	2.9
70°-80°	78.0	1.4
80°-90°	24.5	0.4
90°-100°	275.0	4.9
100°-110°	778.7	13.8
110°-120°	766.1	13.6
120°-130°	611.0	10.8
130°-140°	481.8	8.5
140°-150°	359.6	6.4
150°-160°	250.6	4.4
160°-170°	147.2	2.6
170°-180°	47.9	0.8
0°-30°	684.3	12.1
0°-40°	1072.2	19.0
0°-60°	1657.2	29.4
0°-90°	1921.9	34.1
90°-120°	1819.8	32.3
90°-150°	3272.2	58.0
90°-180°	3718.0	65.9
0°-180°	5639.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	770	770	770	770	770	
5°	915	771	679	771	915	94
15°	1300	735	542	735	1300	369
25°	1340	668	441	668	1340	576
35°	581	582	360	582	581	381
45°	310	468	283	468	310	244
55°	195	329	193	329	195	176
65°	112	203	121	203	112	110
75°	48	99	62	99	48	51
85°	11	23	22	23	11	14
90°	29	2	29	2	29	16
95°	116	34	116	34	116	209
105°	1272	116	1272	116	1272	1255
115°	1548	205	1548	205	1548	1504
125°	1220	285	1220	285	1220	1106
135°	989	334	989	334	989	767
145°	773	381	773	381	773	492
155°	641	433	641	433	641	299
165°	559	473	559	473	559	160
175°	503	493	503	493	503	49
180°	494	494	494	494	494	

TEST NUMBER: P332296-935

CATALOG NUMBER: S123RDIP-S560D1195U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3
2.5°	820.4	821.6	818.1	817.6	813.6	812.6	812.6	807.0	803.6	799.1	796.5
5°	914.8	920.1	917.5	911.5	901.6	899.3	893.0	883.1	871.9	858.1	851.5
7.5°	1032.6	1039.8	1037.0	1027.9	1017.5	1009.1	991.4	975.0	952.0	931.9	914.6
10°	1129.2	1121.5	1115.7	1106.7	1097.2	1081.7	1063.2	1037.8	1008.5	985.4	959.7
12.5°	1201.4	1200.2	1192.7	1183.5	1170.0	1155.3	1132.6	1101.6	1067.6	1034.1	1004.8
15°	1300.0	1302.0	1297.0	1287.5	1268.3	1242.3	1208.0	1195.2	1146.3	1110.0	1073.8
17.5°	1368.2	1367.8	1367.1	1353.8	1334.4	1315.8	1284.0	1250.2	1206.0	1154.9	1106.0
20°	1411.4	1408.2	1408.9	1394.0	1379.5	1358.1	1327.1	1277.9	1241.6	1182.6	1132.1
22.5°	1410.4	1409.7	1412.2	1407.1	1396.6	1380.2	1355.8	1314.3	1268.0	1208.4	1151.7
25°	1339.5	1337.0	1352.5	1356.7	1373.6	1376.5	1369.2	1346.5	1302.6	1241.3	1171.0
27.5°	1121.1	1119.6	1148.4	1184.4	1230.1	1265.6	1299.9	1316.4	1302.6	1258.7	1188.4
30°	920.1	951.1	965.6	1017.7	1075.7	1145.0	1205.7	1263.3	1277.6	1258.4	1200.8
32.5°	763.9	790.9	803.1	847.8	901.9	983.0	1074.0	1155.7	1213.5	1228.1	1193.3
35°	581.1	581.4	609.1	628.9	679.0	762.4	850.8	960.3	1069.1	1151.6	1160.2
37.5°	463.6	465.3	482.1	501.8	539.4	583.5	661.3	752.3	878.0	1004.6	1078.8
40°	400.4	403.3	415.9	435.3	462.4	495.7	556.4	642.0	746.9	887.8	1002.9
42.5°	359.7	364.5	371.0	386.0	402.7	433.9	483.0	549.2	644.5	777.7	910.5
45°	310.0	312.6	317.5	324.5	339.7	361.4	394.4	438.9	518.1	625.3	758.2
47.5°	273.5	272.1	277.2	282.9	293.0	307.8	329.9	366.3	422.8	508.7	621.5
50°	248.7	248.3	251.9	256.2	265.8	276.7	294.8	322.2	367.0	438.2	541.5
52.5°	225.4	226.7	229.3	234.6	241.5	250.3	266.6	286.3	324.9	386.3	472.3
55°	194.6	195.5	199.1	202.2	207.1	216.0	226.3	242.7	269.1	311.9	382.9
57.5°	168.4	168.0	171.5	172.2	177.8	185.0	193.0	205.8	224.9	256.8	304.5
60°	151.0	150.1	153.0	155.3	158.3	164.2	170.8	183.4	198.5	222.0	262.9
62.5°	135.2	134.7	136.9	139.2	141.6	147.1	152.7	162.2	174.3	194.0	226.4
65°	112.1	113.1	114.1	115.1	116.4	119.7	125.0	131.6	139.8	153.7	177.1
67.5°	88.1	89.1	89.5	91.4	94.3	96.3	99.6	105.5	111.2	122.9	136.2
70°	71.2	70.9	71.2	72.2	75.9	79.5	83.8	88.1	91.7	100.0	111.2
72.5°	61.2	60.6	61.5	61.6	63.5	64.4	67.2	71.2	75.9	81.5	89.5
75°	47.5	47.5	47.5	47.5	48.8	49.5	50.5	51.5	53.1	55.7	61.6
77.5°	35.1	35.1	35.6	35.9	36.2	36.6	37.2	38.2	38.7	40.2	42.7
80°	27.7	28.1	27.7	28.1	28.1	28.7	29.0	30.0	30.3	32.0	33.0
82.5°	20.8	20.7	20.8	21.2	21.2	21.9	21.9	22.6	22.7	23.5	24.5
85°	11.2	10.6	11.2	10.8	11.5	10.8	11.2	11.9	11.9	12.2	13.5
87.5°	8.4	9.1	8.4	8.5	8.7	8.6	8.4	8.2	8.5	8.4	8.1
90°	29.0	30.0	29.0	28.0	29.0	27.0	26.0	25.0	24.0	25.0	22.0
92.5°	48.2	50.0	49.0	52.0	53.8	59.0	66.8	84.2	116.1	153.9	169.3
95°	116.1	120.0	127.1	136.0	155.1	191.1	244.1	360.2	481.1	593.2	528.2
97.5°	315.9	324.5	351.5	396.6	470.4	590.0	719.0	897.7	983.5	919.3	673.0
100°	627.2	626.2	665.2	738.2	839.3	981.4	1098.4	1179.4	1144.4	947.4	640.2
102.5°	920.2	943.1	975.8	1033.5	1112.2	1202.2	1270.4	1273.1	1152.4	895.4	592.2
105°	1272.5	1277.5	1309.5	1347.5	1393.5	1419.5	1400.5	1300.5	1091.4	804.3	533.2
107.5°	1475.3	1484.5	1495.3	1508.1	1507.4	1471.7	1384.1	1221.6	984.6	723.8	495.6
110°	1558.6	1560.6	1562.5	1554.5	1526.6	1456.6	1330.5	1146.4	917.3	678.2	481.1

TEST NUMBER: P332296-935

CATALOG NUMBER: S123RDIP-S560D1195U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1575.4	1574.9	1567.4	1542.6	1491.3	1401.3	1260.1	1071.9	858.9	647.8	473.2
115°	1547.6	1542.6	1522.5	1478.5	1403.5	1294.4	1147.4	973.4	788.2	615.2	470.2
117.5°	1459.1	1452.3	1423.5	1373.1	1294.9	1184.2	1052.1	901.9	745.6	596.0	472.0
120°	1385.5	1379.5	1355.5	1299.4	1220.5	1119.4	999.4	864.3	723.2	587.2	475.2
122.5°	1316.6	1309.1	1282.6	1232.3	1162.0	1068.2	956.9	834.7	704.8	581.6	480.8
125°	1220.5	1213.4	1188.4	1144.4	1080.4	1000.3	904.3	795.3	681.2	574.2	489.1
127.5°	1141.2	1134.8	1112.2	1074.6	1017.5	944.7	858.1	760.9	660.5	570.6	498.8
130°	1096.4	1088.4	1067.4	1031.4	978.4	910.3	829.3	739.3	649.2	568.2	505.1
132.5°	1052.4	1046.8	1028.1	992.1	942.4	877.5	802.1	719.3	638.9	567.4	510.0
135°	989.4	982.3	964.3	934.4	885.3	828.3	763.3	692.2	625.3	566.2	517.2
137.5°	922.7	918.1	902.9	872.5	831.3	781.9	725.8	667.6	613.4	564.0	522.0
140°	876.3	877.3	861.3	833.3	795.3	752.3	704.2	653.2	606.2	563.2	525.2
142.5°	833.1	834.1	819.7	794.9	762.5	725.0	683.5	639.6	599.8	561.6	527.6
145°	773.3	771.3	763.3	742.3	717.2	688.3	656.3	623.2	591.2	559.2	529.2
147.5°	724.0	723.2	715.7	701.5	682.4	661.9	636.0	609.8	582.8	555.4	529.2
150°	695.3	695.3	689.2	678.2	663.2	644.2	623.2	600.2	577.2	552.2	529.2
152.5°	671.2	671.2	667.6	657.5	645.7	629.8	611.2	591.4	570.8	548.2	526.8
155°	641.2	640.2	638.3	630.3	621.2	609.2	594.2	578.2	561.2	541.2	524.2
157.5°	613.8	614.0	612.4	606.4	598.6	589.2	577.6	564.2	550.4	535.0	520.8
160°	596.2	597.2	597.2	591.2	584.2	577.2	567.2	556.2	543.2	530.2	519.2
162.5°	580.2	581.2	581.2	576.0	571.4	565.2	556.0	546.6	536.0	525.4	516.0
165°	559.2	559.2	560.2	556.2	552.2	547.2	540.2	534.2	526.2	518.1	511.2
167.5°	539.2	539.2	540.2	537.4	535.6	532.0	528.0	523.4	516.8	511.0	506.4
170°	527.2	527.2	528.2	526.2	525.2	523.1	519.2	516.2	511.2	506.2	503.2
172.5°	516.0	516.8	518.6	516.6	516.3	515.2	512.0	509.8	505.6	502.1	500.8
175°	503.2	504.2	505.1	504.2	504.2	504.2	502.1	501.2	499.2	497.1	497.1
177.5°	495.8	495.8	497.4	496.5	497.4	497.4	496.5	495.8	495.0	494.2	495.0
180°	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2

TEST NUMBER: P332296-935

CATALOG NUMBER: S123RDIP-S560D1195U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3
2.5°	795.4	794.6	790.9	786.7	781.2	777.5	774.6	773.0	768.3	762.4	758.5
5°	844.6	834.7	824.1	811.2	799.4	787.2	779.6	770.7	759.8	747.6	739.0
7.5°	897.2	877.8	856.9	835.3	814.0	794.9	778.0	763.5	746.2	728.8	716.4
10°	937.5	909.2	879.9	849.8	822.4	796.8	777.0	757.5	736.8	716.6	701.5
12.5°	974.2	936.9	903.1	866.2	831.2	800.5	772.0	749.1	724.1	702.7	685.4
15°	1020.6	982.4	941.5	885.5	839.0	800.0	765.4	735.4	705.1	678.7	661.9
17.5°	1064.0	1006.5	951.6	904.7	844.4	795.7	753.5	717.6	684.3	656.3	635.6
20°	1082.0	1026.3	966.6	906.9	847.6	793.2	744.0	704.4	669.8	638.1	619.0
22.5°	1092.8	1029.7	966.8	902.7	839.6	783.1	734.5	691.0	653.4	623.4	599.8
25°	1105.4	1030.2	961.0	897.7	833.4	772.0	714.3	668.1	627.6	595.6	570.5
27.5°	1113.7	1025.3	943.4	873.1	807.8	746.7	693.9	644.9	603.7	569.9	543.0
30°	1115.3	1021.3	930.0	853.8	787.5	731.4	675.4	628.5	585.0	549.1	524.0
32.5°	1117.4	1011.6	911.8	830.9	763.0	707.5	656.7	611.9	567.3	531.9	506.4
35°	1108.7	1006.2	884.2	791.2	723.2	669.4	623.6	582.4	538.6	504.2	478.2
37.5°	1071.3	984.7	855.5	746.4	675.4	625.6	588.2	552.3	512.1	475.1	450.6
40°	1033.5	963.6	833.4	719.3	645.1	593.9	560.3	531.0	492.1	457.4	431.0
42.5°	977.3	934.9	812.3	690.8	610.7	561.5	533.1	505.6	471.5	436.3	411.5
45°	874.3	879.9	769.0	645.4	563.3	513.8	487.1	468.0	437.6	408.6	383.2
47.5°	744.9	797.4	718.3	597.0	513.2	466.7	443.4	426.7	406.3	377.8	354.6
50°	660.6	735.4	677.7	564.6	481.8	435.7	412.6	399.1	381.3	358.8	336.7
52.5°	582.7	663.1	628.6	528.4	447.8	405.5	383.0	371.9	357.7	336.7	316.7
55°	475.2	556.6	548.7	473.9	396.7	358.8	341.6	329.2	319.5	303.8	287.9
57.5°	384.4	461.6	465.7	413.2	351.7	314.3	299.5	290.1	283.8	271.9	257.3
60°	327.2	398.0	411.9	372.3	319.5	286.5	272.1	264.5	259.5	249.9	238.8
62.5°	279.7	340.0	355.7	327.2	288.7	257.8	246.5	239.2	235.8	227.6	217.7
65°	214.0	264.2	279.3	263.5	243.4	218.6	209.4	203.1	200.2	195.5	188.3
67.5°	160.9	197.5	214.1	202.9	195.7	180.0	174.2	170.8	168.2	165.1	158.9
70°	129.2	156.4	173.5	170.5	164.5	156.4	152.1	149.7	147.1	144.5	139.1
72.5°	103.9	122.5	138.6	140.2	135.3	133.6	129.8	128.9	127.3	124.2	121.2
75°	69.0	81.8	93.0	97.3	99.3	100.9	99.3	98.9	98.6	96.0	94.3
77.5°	45.2	52.1	59.2	66.5	69.6	71.8	72.3	73.5	72.7	71.3	70.5
80°	34.6	36.2	41.2	47.5	52.4	54.4	55.7	56.4	56.1	55.7	54.4
82.5°	25.1	26.5	28.8	33.2	37.4	40.7	41.5	41.3	42.1	42.3	41.2
85°	13.5	13.9	14.6	15.2	17.5	21.1	22.1	22.7	23.4	23.4	21.4
87.5°	8.0	7.1	7.1	6.7	7.1	6.7	7.9	8.9	9.5	8.9	9.5
90°	19.0	16.0	13.0	11.0	9.0	6.0	4.0	2.0	4.0	6.0	9.0
92.5°	127.1	84.0	57.9	43.0	34.6	26.8	18.4	12.4	18.4	26.8	34.6
95°	364.1	215.1	130.0	91.0	65.0	48.0	37.0	34.0	37.0	48.0	65.0
97.5°	399.5	231.5	150.2	108.1	82.4	67.6	59.0	58.0	59.0	67.6	82.4
100°	377.1	229.1	159.0	120.0	96.0	82.1	75.0	74.0	75.0	82.1	96.0
102.5°	357.9	232.3	169.4	133.6	112.0	98.8	92.6	90.8	92.6	98.8	112.0
105°	344.1	241.1	187.1	156.0	137.1	125.0	119.1	116.1	119.1	125.0	137.1
107.5°	343.1	257.5	210.1	181.2	163.4	151.6	145.9	142.8	145.9	151.6	163.4
110°	347.2	271.1	226.1	198.0	181.1	170.0	165.1	162.0	165.1	170.0	181.1

TEST NUMBER: P332296-935

CATALOG NUMBER: S123RDIP-S560D1195U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	355.2	284.7	242.9	215.7	198.6	187.7	182.7	179.7	182.7	187.7	198.6
115°	368.2	307.1	269.1	242.1	225.1	215.1	209.1	205.1	209.1	215.1	225.1
117.5°	385.3	330.9	293.3	268.3	249.3	240.0	235.1	230.5	235.1	240.0	249.3
120°	398.1	346.1	310.1	285.1	266.1	256.1	251.1	248.1	251.1	256.1	266.1
122.5°	410.2	362.1	326.9	300.3	282.1	271.3	266.3	263.3	266.3	271.3	282.1
125°	429.1	385.1	350.1	323.1	304.1	293.1	287.1	285.1	287.1	293.1	304.1
127.5°	444.8	405.1	371.3	344.3	323.3	312.1	304.7	301.7	304.7	312.1	323.3
130°	455.1	417.2	384.1	357.1	336.1	324.1	315.1	312.1	315.1	324.1	336.1
132.5°	464.8	427.6	395.4	369.1	348.1	333.7	323.9	320.1	323.9	333.7	348.1
135°	477.2	443.2	412.2	385.1	364.1	349.1	338.1	334.2	338.1	349.1	364.1
137.5°	486.4	453.9	424.1	399.2	378.3	362.3	351.5	347.3	351.5	362.3	378.3
140°	491.2	461.2	432.1	407.2	387.1	371.1	361.1	356.1	361.1	371.1	387.1
142.5°	495.9	466.7	438.6	415.2	395.1	380.7	370.0	365.8	370.0	380.7	395.1
145°	501.2	474.2	448.2	425.2	408.1	393.1	384.1	381.2	384.1	393.1	408.1
147.5°	504.4	480.2	456.3	436.8	420.3	407.3	398.6	396.7	398.6	407.3	420.3
150°	505.1	484.1	461.2	443.2	429.1	416.1	408.1	407.2	408.1	416.1	429.1
152.5°	506.8	486.6	466.7	449.5	437.1	425.8	417.8	417.6	417.8	425.8	437.1
155°	507.2	491.2	474.2	460.1	449.2	439.2	433.2	433.2	433.2	439.2	449.2
157.5°	508.2	493.8	480.2	469.3	459.9	451.2	446.3	445.6	446.3	451.2	459.9
160°	508.2	496.2	484.1	474.2	467.2	459.2	455.1	455.1	455.1	459.2	467.2
162.5°	507.4	497.0	486.6	478.2	472.0	465.5	462.4	462.4	462.4	465.5	472.0
165°	505.1	498.2	490.2	483.2	479.1	474.2	472.2	473.2	472.2	474.2	479.1
167.5°	503.6	498.0	492.1	487.8	485.0	481.1	480.2	481.4	480.2	481.1	485.0
170°	501.2	497.1	492.1	490.2	488.2	485.2	484.1	486.2	484.1	485.2	488.2
172.5°	500.4	497.1	493.0	491.8	490.6	488.4	488.2	489.4	488.2	488.4	490.6
175°	498.2	496.2	494.2	493.2	493.2	491.2	492.1	493.2	492.1	491.2	493.2
177.5°	496.5	495.0	494.2	494.2	494.2	493.4	494.2	495.0	494.2	493.4	494.2
180°	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2

TEST NUMBER: P332296-935

CATALOG NUMBER: S123RDIP-S560D1195U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3
2.5°	757.2	753.7	751.4	746.1	742.7	739.0	735.3	737.6	737.4	737.1	737.1
5°	731.8	724.2	717.3	708.3	702.7	695.9	690.5	689.9	691.2	686.6	684.0
7.5°	706.6	696.2	686.4	676.6	666.2	657.8	652.6	650.2	646.9	644.0	641.0
10°	688.9	676.7	667.1	655.0	643.8	633.9	627.6	623.3	621.0	618.6	614.4
12.5°	670.7	658.8	646.5	632.7	622.1	610.6	606.0	601.2	596.7	594.1	588.2
15°	644.0	628.5	615.7	601.2	589.4	578.1	571.5	562.0	560.6	557.3	551.4
17.5°	617.3	600.5	582.8	572.0	558.6	547.0	536.9	533.7	524.3	520.7	515.6
20°	596.2	580.7	567.2	553.0	533.6	522.7	514.8	510.5	502.9	498.3	495.0
22.5°	578.1	562.2	546.6	530.1	514.0	501.9	496.0	489.4	485.3	478.8	475.2
25°	552.1	534.9	516.1	498.3	486.7	477.5	468.3	462.4	456.4	453.4	446.9
27.5°	521.9	503.9	486.4	472.9	458.7	449.5	441.2	435.9	428.8	423.8	420.2
30°	505.2	484.1	469.0	456.8	438.6	430.1	423.8	417.2	411.9	406.7	402.9
32.5°	485.9	466.7	452.3	437.2	423.3	414.0	405.8	400.0	395.5	390.5	386.9
35°	455.7	439.6	424.7	409.6	399.3	389.8	380.2	375.3	371.0	366.4	363.1
37.5°	428.4	413.4	399.2	384.9	372.2	364.4	356.7	352.9	347.2	344.1	340.7
40°	411.6	396.7	381.6	367.7	354.5	348.6	341.6	336.0	330.8	328.5	324.9
42.5°	393.1	378.2	365.5	350.5	339.8	331.7	325.3	319.2	315.2	311.9	309.8
45°	365.8	352.5	340.0	325.2	315.0	308.0	300.7	295.2	291.5	289.2	285.6
47.5°	339.1	326.0	313.2	300.3	290.4	282.5	275.3	271.3	266.6	263.7	261.2
50°	319.9	308.0	294.5	282.6	272.8	264.8	258.9	253.9	249.6	246.0	244.4
52.5°	302.2	289.6	277.8	266.8	256.4	247.4	242.0	236.8	233.6	229.4	227.5
55°	273.0	260.9	251.0	240.0	229.9	222.3	215.7	211.0	207.8	203.1	200.5
57.5°	245.6	234.7	222.9	213.5	202.9	196.6	191.1	184.8	180.8	177.2	174.6
60°	227.2	214.6	204.5	195.5	186.3	178.1	173.1	168.2	163.9	160.2	158.0
62.5°	207.9	197.0	187.4	177.6	169.2	162.0	156.3	152.1	148.4	146.0	143.7
65°	178.4	169.9	160.0	152.1	144.1	138.9	134.2	130.6	127.9	126.3	124.3
67.5°	151.3	142.9	134.3	126.5	121.2	117.2	114.2	111.1	109.8	107.6	106.3
70°	133.5	125.0	117.4	111.5	106.2	103.2	101.3	98.9	97.6	95.0	93.7
72.5°	114.3	108.1	102.6	97.7	93.5	90.8	88.3	85.5	83.3	80.5	79.1
75°	90.1	84.5	80.2	76.8	74.2	70.6	67.0	64.0	63.0	62.0	61.6
77.5°	66.6	63.1	60.0	57.3	54.0	51.3	50.5	49.9	49.7	49.2	49.2
80°	52.4	49.2	46.8	43.6	41.6	41.6	41.6	40.9	41.2	41.2	41.2
82.5°	39.0	35.9	34.7	33.5	33.1	33.4	33.4	33.5	33.3	33.8	33.6
85°	20.1	20.4	21.1	20.8	21.1	21.1	21.8	21.4	21.8	21.1	21.8
87.5°	9.6	10.8	11.6	12.5	13.3	13.7	13.8	13.9	14.5	14.6	15.1
90°	11.0	13.0	16.0	19.0	22.0	25.0	24.0	25.0	26.0	27.0	29.0
92.5°	43.0	57.9	84.0	127.1	169.3	153.9	116.1	84.2	66.8	59.0	53.8
95°	91.0	130.0	215.1	364.1	528.2	593.2	481.1	360.2	244.1	191.1	155.1
97.5°	108.1	150.2	231.5	399.5	673.0	919.3	983.5	897.7	719.0	590.0	470.4
100°	120.0	159.0	229.1	377.1	640.2	947.4	1144.4	1179.4	1098.4	981.4	839.3
102.5°	133.6	169.4	232.3	357.9	592.2	895.4	1152.4	1273.1	1270.4	1202.2	1112.2
105°	156.0	187.1	241.1	344.1	533.2	804.3	1091.4	1300.5	1400.5	1419.5	1393.5
107.5°	181.2	210.1	257.5	343.1	495.6	723.8	984.6	1221.6	1384.1	1471.7	1507.4
110°	198.0	226.1	271.1	347.2	481.1	678.2	917.3	1146.4	1330.5	1456.6	1526.6

TEST NUMBER: P332296-935

CATALOG NUMBER: S123RDIP-S560D1195U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	215.7	242.9	284.7	355.2	473.2	647.8	858.9	1071.9	1260.1	1401.3	1491.3
115°	242.1	269.1	307.1	368.2	470.2	615.2	788.2	973.4	1147.4	1294.4	1403.5
117.5°	268.3	293.3	330.9	385.3	472.0	596.0	745.6	901.9	1052.1	1184.2	1294.9
120°	285.1	310.1	346.1	398.1	475.2	587.2	723.2	864.3	999.4	1119.4	1220.5
122.5°	300.3	326.9	362.1	410.2	480.8	581.6	704.8	834.7	956.9	1068.2	1162.0
125°	323.1	350.1	385.1	429.1	489.1	574.2	681.2	795.3	904.3	1000.3	1080.4
127.5°	344.3	371.3	405.1	444.8	498.8	570.6	660.5	760.9	858.1	944.7	1017.5
130°	357.1	384.1	417.2	455.1	505.1	568.2	649.2	739.3	829.3	910.3	978.4
132.5°	369.1	395.4	427.6	464.8	510.0	567.4	638.9	719.3	802.1	877.5	942.4
135°	385.1	412.2	443.2	477.2	517.2	566.2	625.3	692.2	763.3	828.3	885.3
137.5°	399.2	424.1	453.9	486.4	522.0	564.0	613.4	667.6	725.8	781.9	831.3
140°	407.2	432.1	461.2	491.2	525.2	563.2	606.2	653.2	704.2	752.3	795.3
142.5°	415.2	438.6	466.7	495.9	527.6	561.6	599.8	639.6	683.5	725.0	762.5
145°	425.2	448.2	474.2	501.2	529.2	559.2	591.2	623.2	656.3	688.3	717.2
147.5°	436.8	456.3	480.2	504.4	529.2	555.4	582.8	609.8	636.0	661.9	682.4
150°	443.2	461.2	484.1	505.1	529.2	552.2	577.2	600.2	623.2	644.2	663.2
152.5°	449.5	466.7	486.6	506.8	526.8	548.2	570.8	591.4	611.2	629.8	645.7
155°	460.1	474.2	491.2	507.2	524.2	541.2	561.2	578.2	594.2	609.2	621.2
157.5°	469.3	480.2	493.8	508.2	520.8	535.0	550.4	564.2	577.6	589.2	598.6
160°	474.2	484.1	496.2	508.2	519.2	530.2	543.2	556.2	567.2	577.2	584.2
162.5°	478.2	486.6	497.0	507.4	516.0	525.4	536.0	546.6	556.0	565.2	571.4
165°	483.2	490.2	498.2	505.1	511.2	518.1	526.2	534.2	540.2	547.2	552.2
167.5°	487.8	492.1	498.0	503.6	506.4	511.0	516.8	523.4	528.0	532.0	535.6
170°	490.2	492.1	497.1	501.2	503.2	506.2	511.2	516.2	519.2	523.1	525.2
172.5°	491.8	493.0	497.1	500.4	500.8	502.1	505.6	509.8	512.0	515.2	516.3
175°	493.2	494.2	496.2	498.2	497.1	497.1	499.2	501.2	502.1	504.2	504.2
177.5°	494.2	494.2	495.0	496.5	495.0	494.2	495.0	495.8	496.5	497.4	497.4
180°	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2

TEST NUMBER: P332296-935

CATALOG NUMBER: S123RDIP-S560D1195U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3
2.5°	733.9	733.7	733.9	732.9	733.9	733.7	733.9	737.1	737.1	737.4	737.6
5°	682.9	682.6	681.7	678.7	681.7	682.6	682.9	684.0	686.6	691.2	689.9
7.5°	638.4	638.0	635.1	635.2	635.1	638.0	638.4	641.0	644.0	646.9	650.2
10°	612.1	612.4	608.5	606.1	608.5	612.4	612.1	614.4	618.6	621.0	623.3
12.5°	586.5	585.0	581.8	579.2	581.8	585.0	586.5	588.2	594.1	596.7	601.2
15°	552.7	549.4	541.5	542.2	541.5	549.4	552.7	551.4	557.3	560.6	562.0
17.5°	512.9	510.5	510.4	505.8	510.4	510.5	512.9	515.6	520.7	524.3	533.7
20°	489.7	488.1	488.7	484.1	488.7	488.1	489.7	495.0	498.3	502.9	510.5
22.5°	471.5	469.8	467.1	465.6	467.1	469.8	471.5	475.2	478.8	485.3	489.4
25°	444.9	442.2	439.6	441.3	439.6	442.2	444.9	446.9	453.4	456.4	462.4
27.5°	418.2	416.2	413.6	413.3	413.6	416.2	418.2	420.2	423.8	428.8	435.9
30°	401.3	399.3	398.0	396.4	398.0	399.3	401.3	402.9	406.7	411.9	417.2
32.5°	384.2	383.8	381.4	381.1	381.4	383.8	384.2	386.9	390.5	395.5	400.0
35°	361.8	359.8	359.1	359.5	359.1	359.8	361.8	363.1	366.4	371.0	375.3
37.5°	340.4	337.9	336.7	335.4	336.7	337.9	340.4	340.7	344.1	347.2	352.9
40°	325.2	322.5	321.8	321.2	321.8	322.5	325.2	324.9	328.5	330.8	336.0
42.5°	308.0	306.9	306.6	305.4	306.6	306.9	308.0	309.8	311.9	315.2	319.2
45°	284.6	284.3	282.3	282.9	282.3	284.3	284.6	285.6	289.2	291.5	295.2
47.5°	259.9	258.5	257.1	258.0	257.1	258.5	259.9	261.2	263.7	266.6	271.3
50°	243.1	242.4	239.4	240.0	239.4	242.4	243.1	244.4	246.0	249.6	253.9
52.5°	226.2	223.7	222.6	222.1	222.6	223.7	226.2	227.5	229.4	233.6	236.8
55°	198.2	195.2	193.9	193.2	193.9	195.2	198.2	200.5	203.1	207.8	211.0
57.5°	170.7	170.0	168.9	169.6	168.9	170.0	170.7	174.6	177.2	180.8	184.8
60°	154.6	154.6	154.6	154.4	154.6	154.6	154.6	158.0	160.2	163.9	168.2
62.5°	142.2	141.5	141.2	141.6	141.2	141.5	142.2	143.7	146.0	148.4	152.1
65°	123.3	123.0	121.7	121.4	121.7	123.0	123.3	124.3	126.3	127.9	130.6
67.5°	105.5	104.3	103.9	103.4	103.9	104.3	105.5	106.3	107.6	109.8	111.1
70°	92.0	91.4	89.4	89.7	89.4	91.4	92.0	93.7	95.0	97.6	98.9
72.5°	77.5	76.8	76.5	75.9	76.5	76.8	77.5	79.1	80.5	83.3	85.5
75°	61.3	61.0	60.7	62.0	60.7	61.0	61.3	61.6	62.0	63.0	64.0
77.5°	49.2	49.2	49.3	48.8	49.3	49.2	49.2	49.2	49.2	49.7	49.9
80°	41.2	41.2	40.9	40.9	40.9	41.2	41.2	41.2	41.2	41.2	40.9
82.5°	33.1	33.3	33.5	33.0	33.5	33.3	33.1	33.6	33.8	33.3	33.5
85°	21.8	21.4	22.1	21.8	22.1	21.4	21.8	21.8	21.1	21.8	21.4
87.5°	15.3	15.1	15.2	15.3	15.2	15.1	15.3	15.1	14.6	14.5	13.9
90°	28.0	29.0	30.0	29.0	30.0	29.0	28.0	29.0	27.0	26.0	25.0
92.5°	52.0	49.0	50.0	48.2	50.0	49.0	52.0	53.8	59.0	66.8	84.2
95°	136.0	127.1	120.0	116.1	120.0	127.1	136.0	155.1	191.1	244.1	360.2
97.5°	396.6	351.5	324.5	315.9	324.5	351.5	396.6	470.4	590.0	719.0	897.7
100°	738.2	665.2	626.2	627.2	626.2	665.2	738.2	839.3	981.4	1098.4	1179.4
102.5°	1033.5	975.8	943.1	920.2	943.1	975.8	1033.5	1112.2	1202.2	1270.4	1273.1
105°	1347.5	1309.5	1277.5	1272.5	1277.5	1309.5	1347.5	1393.5	1419.5	1400.5	1300.5
107.5°	1508.1	1495.3	1484.5	1475.3	1484.5	1495.3	1508.1	1507.4	1471.7	1384.1	1221.6
110°	1554.5	1562.5	1560.6	1558.6	1560.6	1562.5	1554.5	1526.6	1456.6	1330.5	1146.4

TEST NUMBER: P332296-935

CATALOG NUMBER: S123RDIP-S560D1195U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1542.6	1567.4	1574.9	1575.4	1574.9	1567.4	1542.6	1491.3	1401.3	1260.1	1071.9
115°	1478.5	1522.5	1542.6	1547.6	1542.6	1522.5	1478.5	1403.5	1294.4	1147.4	973.4
117.5°	1373.1	1423.5	1452.3	1459.1	1452.3	1423.5	1373.1	1294.9	1184.2	1052.1	901.9
120°	1299.4	1355.5	1379.5	1385.5	1379.5	1355.5	1299.4	1220.5	1119.4	999.4	864.3
122.5°	1232.3	1282.6	1309.1	1316.6	1309.1	1282.6	1232.3	1162.0	1068.2	956.9	834.7
125°	1144.4	1188.4	1213.4	1220.5	1213.4	1188.4	1144.4	1080.4	1000.3	904.3	795.3
127.5°	1074.6	1112.2	1134.8	1141.2	1134.8	1112.2	1074.6	1017.5	944.7	858.1	760.9
130°	1031.4	1067.4	1088.4	1096.4	1088.4	1067.4	1031.4	978.4	910.3	829.3	739.3
132.5°	992.1	1028.1	1046.8	1052.4	1046.8	1028.1	992.1	942.4	877.5	802.1	719.3
135°	934.4	964.3	982.3	989.4	982.3	964.3	934.4	885.3	828.3	763.3	692.2
137.5°	872.5	902.9	918.1	922.7	918.1	902.9	872.5	831.3	781.9	725.8	667.6
140°	833.3	861.3	877.3	876.3	877.3	861.3	833.3	795.3	752.3	704.2	653.2
142.5°	794.9	819.7	834.1	833.1	834.1	819.7	794.9	762.5	725.0	683.5	639.6
145°	742.3	763.3	771.3	773.3	771.3	763.3	742.3	717.2	688.3	656.3	623.2
147.5°	701.5	715.7	723.2	724.0	723.2	715.7	701.5	682.4	661.9	636.0	609.8
150°	678.2	689.2	695.3	695.3	695.3	689.2	678.2	663.2	644.2	623.2	600.2
152.5°	657.5	667.6	671.2	671.2	671.2	667.6	657.5	645.7	629.8	611.2	591.4
155°	630.3	638.3	640.2	641.2	640.2	638.3	630.3	621.2	609.2	594.2	578.2
157.5°	606.4	612.4	614.0	613.8	614.0	612.4	606.4	598.6	589.2	577.6	564.2
160°	591.2	597.2	597.2	596.2	597.2	597.2	591.2	584.2	577.2	567.2	556.2
162.5°	576.0	581.2	581.2	580.2	581.2	581.2	576.0	571.4	565.2	556.0	546.6
165°	556.2	560.2	559.2	559.2	559.2	560.2	556.2	552.2	547.2	540.2	534.2
167.5°	537.4	540.2	539.2	539.2	539.2	540.2	537.4	535.6	532.0	528.0	523.4
170°	526.2	528.2	527.2	527.2	527.2	528.2	526.2	525.2	523.1	519.2	516.2
172.5°	516.6	518.6	516.8	516.0	516.8	518.6	516.6	516.3	515.2	512.0	509.8
175°	504.2	505.1	504.2	503.2	504.2	505.1	504.2	504.2	504.2	502.1	501.2
177.5°	496.5	497.4	495.8	495.8	495.8	497.4	496.5	497.4	497.4	496.5	495.8
180°	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2

TEST NUMBER: P332296-935

CATALOG NUMBER: S123RDIP-S560D1195U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3
2.5°	735.3	739.0	742.7	746.1	751.4	753.7	757.2	758.5	762.4	768.3	773.0
5°	690.5	695.9	702.7	708.3	717.3	724.2	731.8	739.0	747.6	759.8	770.7
7.5°	652.6	657.8	666.2	676.6	686.4	696.2	706.6	716.4	728.8	746.2	763.5
10°	627.6	633.9	643.8	655.0	667.1	676.7	688.9	701.5	716.6	736.8	757.5
12.5°	606.0	610.6	622.1	632.7	646.5	658.8	670.7	685.4	702.7	724.1	749.1
15°	571.5	578.1	589.4	601.2	615.7	628.5	644.0	661.9	678.7	705.1	735.4
17.5°	536.9	547.0	558.6	572.0	582.8	600.5	617.3	635.6	656.3	684.3	717.6
20°	514.8	522.7	533.6	553.0	567.2	580.7	596.2	619.0	638.1	669.8	704.4
22.5°	496.0	501.9	514.0	530.1	546.6	562.2	578.1	599.8	623.4	653.4	691.0
25°	468.3	477.5	486.7	498.3	516.1	534.9	552.1	570.5	595.6	627.6	668.1
27.5°	441.2	449.5	458.7	472.9	486.4	503.9	521.9	543.0	569.9	603.7	644.9
30°	423.8	430.1	438.6	456.8	469.0	484.1	505.2	524.0	549.1	585.0	628.5
32.5°	405.8	414.0	423.3	437.2	452.3	466.7	485.9	506.4	531.9	567.3	611.9
35°	380.2	389.8	399.3	409.6	424.7	439.6	455.7	478.2	504.2	538.6	582.4
37.5°	356.7	364.4	372.2	384.9	399.2	413.4	428.4	450.6	475.1	512.1	552.3
40°	341.6	348.6	354.5	367.7	381.6	396.7	411.6	431.0	457.4	492.1	531.0
42.5°	325.3	331.7	339.8	350.5	365.5	378.2	393.1	411.5	436.3	471.5	505.6
45°	300.7	308.0	315.0	325.2	340.0	352.5	365.8	383.2	408.6	437.6	468.0
47.5°	275.3	282.5	290.4	300.3	313.2	326.0	339.1	354.6	377.8	406.3	426.7
50°	258.9	264.8	272.8	282.6	294.5	308.0	319.9	336.7	358.8	381.3	399.1
52.5°	242.0	247.4	256.4	266.8	277.8	289.6	302.2	316.7	336.7	357.7	371.9
55°	215.7	222.3	229.9	240.0	251.0	260.9	273.0	287.9	303.8	319.5	329.2
57.5°	191.1	196.6	202.9	213.5	222.9	234.7	245.6	257.3	271.9	283.8	290.1
60°	173.1	178.1	186.3	195.5	204.5	214.6	227.2	238.8	249.9	259.5	264.5
62.5°	156.3	162.0	169.2	177.6	187.4	197.0	207.9	217.7	227.6	235.8	239.2
65°	134.2	138.9	144.1	152.1	160.0	169.9	178.4	188.3	195.5	200.2	203.1
67.5°	114.2	117.2	121.2	126.5	134.3	142.9	151.3	158.9	165.1	168.2	170.8
70°	101.3	103.2	106.2	111.5	117.4	125.0	133.5	139.1	144.5	147.1	149.7
72.5°	88.3	90.8	93.5	97.7	102.6	108.1	114.3	121.2	124.2	127.3	128.9
75°	67.0	70.6	74.2	76.8	80.2	84.5	90.1	94.3	96.0	98.6	98.9
77.5°	50.5	51.3	54.0	57.3	60.0	63.1	66.6	70.5	71.3	72.7	73.5
80°	41.6	41.6	41.6	43.6	46.8	49.2	52.4	54.4	55.7	56.1	56.4
82.5°	33.4	33.4	33.1	33.5	34.7	35.9	39.0	41.2	42.3	42.1	41.3
85°	21.8	21.1	21.1	20.8	21.1	20.4	20.1	21.4	23.4	23.4	22.7
87.5°	13.8	13.7	13.3	12.5	11.6	10.8	9.6	9.5	8.9	9.5	8.9
90°	24.0	25.0	22.0	19.0	16.0	13.0	11.0	9.0	6.0	4.0	2.0
92.5°	116.1	153.9	169.3	127.1	84.0	57.9	43.0	34.6	26.8	18.4	12.4
95°	481.1	593.2	528.2	364.1	215.1	130.0	91.0	65.0	48.0	37.0	34.0
97.5°	983.5	919.3	673.0	399.5	231.5	150.2	108.1	82.4	67.6	59.0	58.0
100°	1144.4	947.4	640.2	377.1	229.1	159.0	120.0	96.0	82.1	75.0	74.0
102.5°	1152.4	895.4	592.2	357.9	232.3	169.4	133.6	112.0	98.8	92.6	90.8
105°	1091.4	804.3	533.2	344.1	241.1	187.1	156.0	137.1	125.0	119.1	116.1
107.5°	984.6	723.8	495.6	343.1	257.5	210.1	181.2	163.4	151.6	145.9	142.8
110°	917.3	678.2	481.1	347.2	271.1	226.1	198.0	181.1	170.0	165.1	162.0

TEST NUMBER: P332296-935

CATALOG NUMBER: S123RDIP-S560D1195U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	858.9	647.8	473.2	355.2	284.7	242.9	215.7	198.6	187.7	182.7	179.7
115°	788.2	615.2	470.2	368.2	307.1	269.1	242.1	225.1	215.1	209.1	205.1
117.5°	745.6	596.0	472.0	385.3	330.9	293.3	268.3	249.3	240.0	235.1	230.5
120°	723.2	587.2	475.2	398.1	346.1	310.1	285.1	266.1	256.1	251.1	248.1
122.5°	704.8	581.6	480.8	410.2	362.1	326.9	300.3	282.1	271.3	266.3	263.3
125°	681.2	574.2	489.1	429.1	385.1	350.1	323.1	304.1	293.1	287.1	285.1
127.5°	660.5	570.6	498.8	444.8	405.1	371.3	344.3	323.3	312.1	304.7	301.7
130°	649.2	568.2	505.1	455.1	417.2	384.1	357.1	336.1	324.1	315.1	312.1
132.5°	638.9	567.4	510.0	464.8	427.6	395.4	369.1	348.1	333.7	323.9	320.1
135°	625.3	566.2	517.2	477.2	443.2	412.2	385.1	364.1	349.1	338.1	334.2
137.5°	613.4	564.0	522.0	486.4	453.9	424.1	399.2	378.3	362.3	351.5	347.3
140°	606.2	563.2	525.2	491.2	461.2	432.1	407.2	387.1	371.1	361.1	356.1
142.5°	599.8	561.6	527.6	495.9	466.7	438.6	415.2	395.1	380.7	370.0	365.8
145°	591.2	559.2	529.2	501.2	474.2	448.2	425.2	408.1	393.1	384.1	381.2
147.5°	582.8	555.4	529.2	504.4	480.2	456.3	436.8	420.3	407.3	398.6	396.7
150°	577.2	552.2	529.2	505.1	484.1	461.2	443.2	429.1	416.1	408.1	407.2
152.5°	570.8	548.2	526.8	506.8	486.6	466.7	449.5	437.1	425.8	417.8	417.6
155°	561.2	541.2	524.2	507.2	491.2	474.2	460.1	449.2	439.2	433.2	433.2
157.5°	550.4	535.0	520.8	508.2	493.8	480.2	469.3	459.9	451.2	446.3	445.6
160°	543.2	530.2	519.2	508.2	496.2	484.1	474.2	467.2	459.2	455.1	455.1
162.5°	536.0	525.4	516.0	507.4	497.0	486.6	478.2	472.0	465.5	462.4	462.4
165°	526.2	518.1	511.2	505.1	498.2	490.2	483.2	479.1	474.2	472.2	473.2
167.5°	516.8	511.0	506.4	503.6	498.0	492.1	487.8	485.0	481.1	480.2	481.4
170°	511.2	506.2	503.2	501.2	497.1	492.1	490.2	488.2	485.2	484.1	486.2
172.5°	505.6	502.1	500.8	500.4	497.1	493.0	491.8	490.6	488.4	488.2	489.4
175°	499.2	497.1	497.1	498.2	496.2	494.2	493.2	493.2	491.2	492.1	493.2
177.5°	495.0	494.2	495.0	496.5	495.0	494.2	494.2	494.2	493.4	494.2	495.0
180°	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2

TEST NUMBER: P332296-935

CATALOG NUMBER: S123RDIP-S560D1195U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3	770.3
2.5°	774.6	777.5	781.2	786.7	790.9	794.6	795.4	796.5	799.1	803.6	807.0
5°	779.6	787.2	799.4	811.2	824.1	834.7	844.6	851.5	858.1	871.9	883.1
7.5°	778.0	794.9	814.0	835.3	856.9	877.8	897.2	914.6	931.9	952.0	975.0
10°	777.0	796.8	822.4	849.8	879.9	909.2	937.5	959.7	985.4	1008.5	1037.8
12.5°	772.0	800.5	831.2	866.2	903.1	936.9	974.2	1004.8	1034.1	1067.6	1101.6
15°	765.4	800.0	839.0	885.5	941.5	982.4	1020.6	1073.8	1110.0	1146.3	1195.2
17.5°	753.5	795.7	844.4	904.7	951.6	1006.5	1064.0	1106.0	1154.9	1206.0	1250.2
20°	744.0	793.2	847.6	906.9	966.6	1026.3	1082.0	1132.1	1182.6	1241.6	1277.9
22.5°	734.5	783.1	839.6	902.7	966.8	1029.7	1092.8	1151.7	1208.4	1268.0	1314.3
25°	714.3	772.0	833.4	897.7	961.0	1030.2	1105.4	1171.0	1241.3	1302.6	1346.5
27.5°	693.9	746.7	807.8	873.1	943.4	1025.3	1113.7	1188.4	1258.7	1302.6	1316.4
30°	675.4	731.4	787.5	853.8	930.0	1021.3	1115.3	1200.8	1258.4	1277.6	1263.3
32.5°	656.7	707.5	763.0	830.9	911.8	1011.6	1117.4	1193.3	1228.1	1213.5	1155.7
35°	623.6	669.4	723.2	791.2	884.2	1006.2	1108.7	1160.2	1151.6	1069.1	960.3
37.5°	588.2	625.6	675.4	746.4	855.5	984.7	1071.3	1078.8	1004.6	878.0	752.3
40°	560.3	593.9	645.1	719.3	833.4	963.6	1033.5	1002.9	887.8	746.9	642.0
42.5°	533.1	561.5	610.7	690.8	812.3	934.9	977.3	910.5	777.7	644.5	549.2
45°	487.1	513.8	563.3	645.4	769.0	879.9	874.3	758.2	625.3	518.1	438.9
47.5°	443.4	466.7	513.2	597.0	718.3	797.4	744.9	621.5	508.7	422.8	366.3
50°	412.6	435.7	481.8	564.6	677.7	735.4	660.6	541.5	438.2	367.0	322.2
52.5°	383.0	405.5	447.8	528.4	628.6	663.1	582.7	472.3	386.3	324.9	286.3
55°	341.6	358.8	396.7	473.9	548.7	556.6	475.2	382.9	311.9	269.1	242.7
57.5°	299.5	314.3	351.7	413.2	465.7	461.6	384.4	304.5	256.8	224.9	205.8
60°	272.1	286.5	319.5	372.3	411.9	398.0	327.2	262.9	222.0	198.5	183.4
62.5°	246.5	257.8	288.7	327.2	355.7	340.0	279.7	226.4	194.0	174.3	162.2
65°	209.4	218.6	243.4	263.5	279.3	264.2	214.0	177.1	153.7	139.8	131.6
67.5°	174.2	180.0	195.7	202.9	214.1	197.5	160.9	136.2	122.9	111.2	105.5
70°	152.1	156.4	164.5	170.5	173.5	156.4	129.2	111.2	100.0	91.7	88.1
72.5°	129.8	133.6	135.3	140.2	138.6	122.5	103.9	89.5	81.5	75.9	71.2
75°	99.3	100.9	99.3	97.3	93.0	81.8	69.0	61.6	55.7	53.1	51.5
77.5°	72.3	71.8	69.6	66.5	59.2	52.1	45.2	42.7	40.2	38.7	38.2
80°	55.7	54.4	52.4	47.5	41.2	36.2	34.6	33.0	32.0	30.3	30.0
82.5°	41.5	40.7	37.4	33.2	28.8	26.5	25.1	24.5	23.5	22.7	22.6
85°	22.1	21.1	17.5	15.2	14.6	13.9	13.5	13.5	12.2	11.9	11.9
87.5°	7.9	6.7	7.1	6.7	7.1	7.1	8.0	8.1	8.4	8.5	8.2
90°	4.0	6.0	9.0	11.0	13.0	16.0	19.0	22.0	25.0	24.0	25.0
92.5°	18.4	26.8	34.6	43.0	57.9	84.0	127.1	169.3	153.9	116.1	84.2
95°	37.0	48.0	65.0	91.0	130.0	215.1	364.1	528.2	593.2	481.1	360.2
97.5°	59.0	67.6	82.4	108.1	150.2	231.5	399.5	673.0	919.3	983.5	897.7
100°	75.0	82.1	96.0	120.0	159.0	229.1	377.1	640.2	947.4	1144.4	1179.4
102.5°	92.6	98.8	112.0	133.6	169.4	232.3	357.9	592.2	895.4	1152.4	1273.1
105°	119.1	125.0	137.1	156.0	187.1	241.1	344.1	533.2	804.3	1091.4	1300.5
107.5°	145.9	151.6	163.4	181.2	210.1	257.5	343.1	495.6	723.8	984.6	1221.6
110°	165.1	170.0	181.1	198.0	226.1	271.1	347.2	481.1	678.2	917.3	1146.4

TEST NUMBER: P332296-935

CATALOG NUMBER: S123RDIP-S560D1195U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	182.7	187.7	198.6	215.7	242.9	284.7	355.2	473.2	647.8	858.9	1071.9
115°	209.1	215.1	225.1	242.1	269.1	307.1	368.2	470.2	615.2	788.2	973.4
117.5°	235.1	240.0	249.3	268.3	293.3	330.9	385.3	472.0	596.0	745.6	901.9
120°	251.1	256.1	266.1	285.1	310.1	346.1	398.1	475.2	587.2	723.2	864.3
122.5°	266.3	271.3	282.1	300.3	326.9	362.1	410.2	480.8	581.6	704.8	834.7
125°	287.1	293.1	304.1	323.1	350.1	385.1	429.1	489.1	574.2	681.2	795.3
127.5°	304.7	312.1	323.3	344.3	371.3	405.1	444.8	498.8	570.6	660.5	760.9
130°	315.1	324.1	336.1	357.1	384.1	417.2	455.1	505.1	568.2	649.2	739.3
132.5°	323.9	333.7	348.1	369.1	395.4	427.6	464.8	510.0	567.4	638.9	719.3
135°	338.1	349.1	364.1	385.1	412.2	443.2	477.2	517.2	566.2	625.3	692.2
137.5°	351.5	362.3	378.3	399.2	424.1	453.9	486.4	522.0	564.0	613.4	667.6
140°	361.1	371.1	387.1	407.2	432.1	461.2	491.2	525.2	563.2	606.2	653.2
142.5°	370.0	380.7	395.1	415.2	438.6	466.7	495.9	527.6	561.6	599.8	639.6
145°	384.1	393.1	408.1	425.2	448.2	474.2	501.2	529.2	559.2	591.2	623.2
147.5°	398.6	407.3	420.3	436.8	456.3	480.2	504.4	529.2	555.4	582.8	609.8
150°	408.1	416.1	429.1	443.2	461.2	484.1	505.1	529.2	552.2	577.2	600.2
152.5°	417.8	425.8	437.1	449.5	466.7	486.6	506.8	526.8	548.2	570.8	591.4
155°	433.2	439.2	449.2	460.1	474.2	491.2	507.2	524.2	541.2	561.2	578.2
157.5°	446.3	451.2	459.9	469.3	480.2	493.8	508.2	520.8	535.0	550.4	564.2
160°	455.1	459.2	467.2	474.2	484.1	496.2	508.2	519.2	530.2	543.2	556.2
162.5°	462.4	465.5	472.0	478.2	486.6	497.0	507.4	516.0	525.4	536.0	546.6
165°	472.2	474.2	479.1	483.2	490.2	498.2	505.1	511.2	518.1	526.2	534.2
167.5°	480.2	481.1	485.0	487.8	492.1	498.0	503.6	506.4	511.0	516.8	523.4
170°	484.1	485.2	488.2	490.2	492.1	497.1	501.2	503.2	506.2	511.2	516.2
172.5°	488.2	488.4	490.6	491.8	493.0	497.1	500.4	500.8	502.1	505.6	509.8
175°	492.1	491.2	493.2	493.2	494.2	496.2	498.2	497.1	497.1	499.2	501.2
177.5°	494.2	493.4	494.2	494.2	494.2	495.0	496.5	495.0	494.2	495.0	495.8
180°	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2

TEST NUMBER: P332296-935

CATALOG NUMBER: S123RDIP-S560D1195U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	770.3	770.3	770.3	770.3	770.3	770.3	770.3
2.5°	812.6	812.6	813.6	817.6	818.1	821.6	820.4
5°	893.0	899.3	901.6	911.5	917.5	920.1	914.8
7.5°	991.4	1009.1	1017.5	1027.9	1037.0	1039.8	1032.6
10°	1063.2	1081.7	1097.2	1106.7	1115.7	1121.5	1129.2
12.5°	1132.6	1155.3	1170.0	1183.5	1192.7	1200.2	1201.4
15°	1208.0	1242.3	1268.3	1287.5	1297.0	1302.0	1300.0
17.5°	1284.0	1315.8	1334.4	1353.8	1367.1	1367.8	1368.2
20°	1327.1	1358.1	1379.5	1394.0	1408.9	1408.2	1411.4
22.5°	1355.8	1380.2	1396.6	1407.1	1412.2	1409.7	1410.4
25°	1369.2	1376.5	1373.6	1356.7	1352.5	1337.0	1339.5
27.5°	1299.9	1265.6	1230.1	1184.4	1148.4	1119.6	1121.1
30°	1205.7	1145.0	1075.7	1017.7	965.6	951.1	920.1
32.5°	1074.0	983.0	901.9	847.8	803.1	790.9	763.9
35°	850.8	762.4	679.0	628.9	609.1	581.4	581.1
37.5°	661.3	583.5	539.4	501.8	482.1	465.3	463.6
40°	556.4	495.7	462.4	435.3	415.9	403.3	400.4
42.5°	483.0	433.9	402.7	386.0	371.0	364.5	359.7
45°	394.4	361.4	339.7	324.5	317.5	312.6	310.0
47.5°	329.9	307.8	293.0	282.9	277.2	272.1	273.5
50°	294.8	276.7	265.8	256.2	251.9	248.3	248.7
52.5°	266.6	250.3	241.5	234.6	229.3	226.7	225.4
55°	226.3	216.0	207.1	202.2	199.1	195.5	194.6
57.5°	193.0	185.0	177.8	172.2	171.5	168.0	168.4
60°	170.8	164.2	158.3	155.3	153.0	150.1	151.0
62.5°	152.7	147.1	141.6	139.2	136.9	134.7	135.2
65°	125.0	119.7	116.4	115.1	114.1	113.1	112.1
67.5°	99.6	96.3	94.3	91.4	89.5	89.1	88.1
70°	83.8	79.5	75.9	72.2	71.2	70.9	71.2
72.5°	67.2	64.4	63.5	61.6	61.5	60.6	61.2
75°	50.5	49.5	48.8	47.5	47.5	47.5	47.5
77.5°	37.2	36.6	36.2	35.9	35.6	35.1	35.1
80°	29.0	28.7	28.1	28.1	27.7	28.1	27.7
82.5°	21.9	21.9	21.2	21.2	20.8	20.7	20.8
85°	11.2	10.8	11.5	10.8	11.2	10.6	11.2
87.5°	8.4	8.6	8.7	8.5	8.4	9.1	8.4
90°	26.0	27.0	29.0	28.0	29.0	30.0	29.0
92.5°	66.8	59.0	53.8	52.0	49.0	50.0	48.2
95°	244.1	191.1	155.1	136.0	127.1	120.0	116.1
97.5°	719.0	590.0	470.4	396.6	351.5	324.5	315.9
100°	1098.4	981.4	839.3	738.2	665.2	626.2	627.2
102.5°	1270.4	1202.2	1112.2	1033.5	975.8	943.1	920.2
105°	1400.5	1419.5	1393.5	1347.5	1309.5	1277.5	1272.5
107.5°	1384.1	1471.7	1507.4	1508.1	1495.3	1484.5	1475.3
110°	1330.5	1456.6	1526.6	1554.5	1562.5	1560.6	1558.6

TEST NUMBER: P332296-935

CATALOG NUMBER: S123RDIP-S560D1195U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1260.1	1401.3	1491.3	1542.6	1567.4	1574.9	1575.4
115°	1147.4	1294.4	1403.5	1478.5	1522.5	1542.6	1547.6
117.5°	1052.1	1184.2	1294.9	1373.1	1423.5	1452.3	1459.1
120°	999.4	1119.4	1220.5	1299.4	1355.5	1379.5	1385.5
122.5°	956.9	1068.2	1162.0	1232.3	1282.6	1309.1	1316.6
125°	904.3	1000.3	1080.4	1144.4	1188.4	1213.4	1220.5
127.5°	858.1	944.7	1017.5	1074.6	1112.2	1134.8	1141.2
130°	829.3	910.3	978.4	1031.4	1067.4	1088.4	1096.4
132.5°	802.1	877.5	942.4	992.1	1028.1	1046.8	1052.4
135°	763.3	828.3	885.3	934.4	964.3	982.3	989.4
137.5°	725.8	781.9	831.3	872.5	902.9	918.1	922.7
140°	704.2	752.3	795.3	833.3	861.3	877.3	876.3
142.5°	683.5	725.0	762.5	794.9	819.7	834.1	833.1
145°	656.3	688.3	717.2	742.3	763.3	771.3	773.3
147.5°	636.0	661.9	682.4	701.5	715.7	723.2	724.0
150°	623.2	644.2	663.2	678.2	689.2	695.3	695.3
152.5°	611.2	629.8	645.7	657.5	667.6	671.2	671.2
155°	594.2	609.2	621.2	630.3	638.3	640.2	641.2
157.5°	577.6	589.2	598.6	606.4	612.4	614.0	613.8
160°	567.2	577.2	584.2	591.2	597.2	597.2	596.2
162.5°	556.0	565.2	571.4	576.0	581.2	581.2	580.2
165°	540.2	547.2	552.2	556.2	560.2	559.2	559.2
167.5°	528.0	532.0	535.6	537.4	540.2	539.2	539.2
170°	519.2	523.1	525.2	526.2	528.2	527.2	527.2
172.5°	512.0	515.2	516.3	516.6	518.6	516.8	516.0
175°	502.1	504.2	504.2	504.2	505.1	504.2	503.2
177.5°	496.5	497.4	497.4	496.5	497.4	495.8	495.8
180°	494.2	494.2	494.2	494.2	494.2	494.2	494.2

(END OF REPORT)