

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332270-840

Luminaire Tested: **S123RDIP-S560D365U840-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332270-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S560D365U840-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 365 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3715.8 lumens
Efficiency: N/A
Efficacy: 135.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 27.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332270-840

CATALOG NUMBER: S123RDIP-S560D365U840-4F0-1E-UDD-A

Luminous Intensity Polar Plot



TEST NUMBER: P332270-840

CATALOG NUMBER: S123RDIP-S560D365U840-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66	61		
1	101	97	93	90	94	91	87	85	79	77	75	69	67	66	59	58	57	52		
2	92	85	79	74	86	80	75	71	70	66	63	61	58	56	53	51	49	45		
3	85	76	69	63	79	71	65	60	63	58	54	55	51	48	48	45	43	39		
4	78	67	60	54	73	64	57	51	56	51	47	49	45	42	43	40	37	34		
5	72	60	53	47	67	57	50	45	51	45	41	45	40	37	39	36	33	30		
6	66	55	47	41	62	52	44	39	46	40	36	41	36	33	36	32	29	27		
7	62	50	42	36	58	47	40	35	42	36	32	37	33	29	33	29	26	24		
8	57	45	38	32	54	43	36	31	38	33	29	34	30	26	30	27	24	22		
9	53	41	34	29	50	39	33	28	35	30	26	32	27	24	28	24	22	20		
10	50	38	31	26	47	36	30	25	33	27	23	29	25	22	26	22	20	18		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9725	9725	9725	9725
5°	11594	9767	8602	9767
10°	14476	9711	7770	9711
15°	16992	9611	7086	9611
20°	18963	9464	6504	9464
25°	18659	9308	6147	9308
30°	13412	9163	5778	9163
35°	8956	8976	5540	8976
40°	6598	8751	5295	8751
45°	5535	8356	5051	8356
50°	4883	7839	4716	7839
55°	4282	7246	4252	7246
60°	3813	6678	3899	6678
65°	3349	6067	3627	6067
70°	2628	5526	3311	5526
75°	2316	4824	3023	4824
80°	2015	4097	2975	4097
85°	1618	3298	3149	3298

TEST NUMBER: P332270-840

CATALOG NUMBER: S123RDIP-S560D365U840-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.9	2.4
10°-20°	277.6	7.5
20°-30°	436.1	11.7
30°-40°	455.0	12.2
40°-50°	389.4	10.5
50°-60°	296.8	8.0
60°-70°	190.2	5.1
70°-80°	91.5	2.5
80°-90°	25.6	0.7
90°-100°	17.5	0.5
100°-110°	83.2	2.2
110°-120°	199.9	5.4
120°-130°	254.6	6.9
130°-140°	272.0	7.3
140°-150°	254.4	6.8
150°-160°	205.2	5.5
160°-170°	132.4	3.6
170°-180°	45.6	1.2
0°-30°	802.6	21.6
0°-40°	1257.6	33.8
0°-60°	1943.7	52.3
0°-90°	2251.1	60.6
90°-120°	300.6	8.1
90°-150°	1081.5	29.1
90°-180°	1465.0	39.4
0°-180°	3715.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	904	904	904	904	904	
5°	1073	904	796	904	1073	111
15°	1525	862	636	862	1525	432
25°	1571	784	518	784	1571	675
35°	682	683	422	683	682	447
45°	364	549	332	549	364	286
55°	228	386	227	386	228	206
65°	132	238	142	238	132	129
75°	56	116	73	116	56	60
85°	13	27	26	27	13	15
90°	11	0	11	0	11	5
95°	14	22	14	22	14	11
105°	16	106	16	106	16	36
115°	210	199	210	199	210	194
125°	287	281	287	281	287	256
135°	354	350	354	350	354	273
145°	408	404	408	404	408	255
155°	444	445	444	445	444	205
165°	468	469	468	469	468	132
175°	479	480	479	480	479	46
180°	480	480	480	480	480	

TEST NUMBER: P332270-840

CATALOG NUMBER: S123RDIP-S560D365U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5
2.5°	962.3	963.6	959.6	959.0	954.3	953.1	953.1	946.5	942.5	937.3	934.2
5°	1073.0	1079.1	1076.1	1069.1	1057.5	1054.8	1047.4	1035.8	1022.7	1006.4	998.8
7.5°	1211.1	1219.6	1216.3	1205.6	1193.5	1183.6	1162.9	1143.6	1116.6	1093.0	1072.7
10°	1324.4	1315.5	1308.6	1298.1	1286.9	1268.7	1247.1	1217.3	1182.9	1155.8	1125.6
12.5°	1409.2	1407.8	1398.9	1388.2	1372.3	1355.0	1328.4	1292.1	1252.1	1212.9	1178.5
15°	1524.8	1527.1	1521.3	1510.1	1487.6	1457.0	1416.8	1401.8	1344.5	1301.9	1259.4
17.5°	1604.8	1604.3	1603.5	1587.9	1565.1	1543.3	1506.0	1466.3	1414.5	1354.5	1297.3
20°	1655.5	1651.6	1652.4	1635.0	1618.0	1592.9	1556.5	1498.8	1456.3	1387.0	1327.9
22.5°	1654.3	1653.5	1656.4	1650.4	1638.1	1618.8	1590.2	1541.6	1487.2	1417.3	1350.8
25°	1571.1	1568.1	1586.3	1591.2	1611.0	1614.5	1606.0	1579.3	1527.8	1455.9	1373.5
27.5°	1314.9	1313.2	1347.0	1389.2	1442.8	1484.4	1524.6	1544.0	1527.8	1476.3	1393.8
30°	1079.1	1115.5	1132.6	1193.7	1261.7	1342.9	1414.1	1481.8	1498.4	1476.0	1408.4
32.5°	896.0	927.7	941.9	994.4	1057.8	1153.0	1259.7	1355.5	1423.3	1440.5	1399.7
35°	681.6	682.0	714.4	737.6	796.4	894.2	997.9	1126.3	1253.9	1350.7	1360.8
37.5°	543.8	545.7	565.4	588.5	632.7	684.4	775.7	882.4	1029.9	1178.3	1265.4
40°	469.6	473.0	487.8	510.6	542.3	581.4	652.6	753.1	876.1	1041.3	1176.3
42.5°	421.9	427.6	435.2	452.7	472.3	509.0	566.5	644.2	756.0	912.2	1067.9
45°	363.6	366.7	372.4	380.6	398.4	423.9	462.6	514.8	607.6	733.4	889.3
47.5°	320.7	319.1	325.2	331.8	343.7	361.0	387.0	429.6	495.8	596.6	728.9
50°	291.6	291.2	295.5	300.5	311.7	324.6	345.8	377.9	430.5	514.0	635.1
52.5°	264.4	265.9	268.9	275.2	283.3	293.6	312.7	335.8	381.0	453.1	554.0
55°	228.2	229.3	233.6	237.1	242.9	253.4	265.4	284.7	315.6	365.9	449.1
57.5°	197.5	197.0	201.2	202.0	208.5	217.0	226.3	241.4	263.8	301.1	357.2
60°	177.1	176.0	179.5	182.2	185.6	192.6	200.4	215.1	232.9	260.3	308.3
62.5°	158.5	158.0	160.6	163.3	166.1	172.5	179.0	190.3	204.4	227.5	265.6
65°	131.5	132.7	133.8	135.0	136.5	140.4	146.6	154.3	164.0	180.3	207.7
67.5°	103.3	104.5	104.9	107.2	110.6	113.0	116.8	123.7	130.5	144.1	159.8
70°	83.5	83.1	83.5	84.7	89.0	93.2	98.3	103.3	107.6	117.2	130.4
72.5°	71.8	71.1	72.1	72.3	74.4	75.5	78.8	83.5	89.0	95.5	105.0
75°	55.7	55.7	55.7	55.7	57.3	58.1	59.2	60.4	62.3	65.3	72.3
77.5°	41.2	41.2	41.8	42.1	42.5	42.9	43.6	44.8	45.4	47.2	50.1
80°	32.5	32.9	32.5	32.9	32.9	33.6	34.0	35.2	35.5	37.6	38.7
82.5°	24.4	24.2	24.4	24.8	24.8	25.7	25.7	26.6	26.7	27.6	28.8
85°	13.1	12.4	13.1	12.7	13.5	12.7	13.1	13.9	13.9	14.3	15.9
87.5°	5.3	5.9	5.2	5.5	5.5	5.7	5.7	5.6	6.1	5.8	5.9
90°	10.7	10.5	10.4	10.2	10.1	9.8	9.5	9.2	8.9	8.6	7.6
92.5°	11.8	11.7	11.6	11.5	11.5	11.2	10.7	10.2	9.6	9.1	8.4
95°	13.5	13.5	13.5	13.5	13.5	13.3	12.7	12.2	11.6	11.1	10.2
97.5°	14.7	14.6	14.5	14.4	14.3	14.0	13.4	12.7	12.1	11.5	17.2
100°	14.9	14.9	14.8	14.7	14.6	14.3	13.6	13.0	12.4	11.8	24.1
102.5°	15.2	15.1	14.9	14.8	14.7	15.7	17.6	19.6	21.5	23.5	37.0
105°	15.7	15.6	15.3	15.2	15.0	22.0	36.1	50.1	64.1	78.2	85.3
107.5°	49.3	59.9	70.5	81.1	91.6	102.1	112.4	122.7	132.9	143.2	142.1
110°	98.2	109.5	120.8	132.2	143.5	150.5	153.1	155.7	158.3	161.0	160.1

TEST NUMBER: P332270-840

CATALOG NUMBER: S123RDIP-S560D365U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	168.3	170.8	173.2	175.5	177.9	179.2	179.0	179.0	178.9	178.9	178.0
115°	209.8	209.5	209.2	208.8	208.5	208.0	207.2	206.4	205.6	204.8	204.1
117.5°	233.1	233.1	233.0	232.9	232.9	232.5	231.9	231.3	230.6	229.9	229.6
120°	249.1	249.1	249.1	249.1	249.1	248.7	248.1	247.5	246.9	246.2	246.0
122.5°	264.8	264.7	264.7	264.6	264.5	264.3	263.9	263.4	263.0	262.5	262.2
125°	286.9	286.8	286.6	286.4	286.3	286.1	286.0	285.8	285.7	285.5	285.2
127.5°	308.2	308.3	308.5	308.6	308.8	308.8	308.5	308.2	308.0	307.7	307.4
130°	321.8	322.0	322.2	322.3	322.6	322.4	322.1	321.8	321.4	321.1	320.8
132.5°	334.5	334.7	334.9	335.1	335.4	335.3	335.0	334.7	334.4	334.1	333.8
135°	353.7	353.9	354.2	354.4	354.6	354.6	354.4	354.2	353.9	353.7	353.4
137.5°	371.7	371.8	372.0	372.1	372.3	372.2	371.8	371.4	371.1	370.7	370.5
140°	382.5	382.7	382.8	383.0	383.1	383.1	382.7	382.4	382.1	381.8	381.6
142.5°	392.5	392.7	392.9	393.2	393.4	393.4	393.1	392.9	392.6	392.4	392.1
145°	407.9	407.9	407.9	407.9	407.9	407.8	407.7	407.5	407.4	407.2	407.0
147.5°	419.3	419.7	420.0	420.4	420.8	420.9	420.7	420.5	420.4	420.2	420.1
150°	427.9	428.1	428.4	428.6	428.8	428.9	428.7	428.6	428.4	428.2	428.1
152.5°	434.7	435.0	435.5	435.9	436.2	436.3	436.0	435.7	435.4	435.0	434.9
155°	444.2	444.7	445.2	445.8	446.2	446.3	445.9	445.5	445.0	444.6	444.5
157.5°	452.3	452.9	453.6	454.2	454.8	454.9	454.4	453.9	453.4	453.0	453.0
160°	457.5	458.1	458.6	459.2	459.7	459.8	459.3	458.8	458.3	457.9	458.0
162.5°	462.3	462.8	463.3	463.8	464.3	464.2	463.7	463.2	462.6	462.1	462.2
165°	468.2	468.8	469.3	469.9	470.4	470.4	469.8	469.1	468.5	467.9	467.9
167.5°	472.4	473.0	473.6	474.3	474.9	474.9	474.3	473.6	473.0	472.4	472.4
170°	474.9	475.6	476.3	476.9	477.5	477.5	476.9	476.3	475.6	474.9	474.9
172.5°	476.4	477.1	477.8	478.5	479.2	479.2	478.6	478.0	477.4	476.7	476.7
175°	478.6	479.2	479.8	480.5	481.1	481.1	480.6	480.0	479.5	478.9	478.8
177.5°	479.2	479.8	480.5	481.1	481.7	481.8	481.3	480.8	480.3	479.8	479.7
180°	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3

TEST NUMBER: P332270-840

CATALOG NUMBER: S123RDIP-S560D365U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5
2.5°	932.9	932.0	927.7	922.7	916.3	911.9	908.5	906.7	901.1	894.2	889.6
5°	990.6	979.0	966.6	951.5	937.6	923.3	914.4	903.9	891.2	876.9	866.8
7.5°	1052.3	1029.6	1005.0	979.8	954.7	932.3	912.5	895.5	875.3	854.7	840.3
10°	1099.6	1066.4	1032.0	996.7	964.6	934.5	911.3	888.5	864.1	840.5	822.7
12.5°	1142.7	1098.9	1059.2	1015.9	974.9	938.9	905.4	878.6	849.3	824.2	803.9
15°	1197.1	1152.3	1104.3	1038.5	984.0	938.4	897.8	862.5	827.0	796.1	776.3
17.5°	1248.0	1180.5	1116.1	1061.2	990.4	933.3	883.7	841.6	802.6	769.8	745.5
20°	1269.1	1203.8	1133.7	1063.7	994.1	930.3	872.6	826.2	785.6	748.4	726.0
22.5°	1281.7	1207.7	1134.0	1058.7	984.8	918.5	861.5	810.4	766.4	731.1	703.5
25°	1296.6	1208.3	1127.1	1052.9	977.4	905.4	837.8	783.7	736.1	698.5	669.1
27.5°	1306.3	1202.5	1106.5	1024.0	947.5	875.9	813.9	756.4	708.1	668.4	636.9
30°	1308.2	1197.9	1090.8	1001.4	923.6	857.9	792.1	737.2	686.2	644.0	614.6
32.5°	1310.6	1186.5	1069.4	974.5	894.9	829.8	770.2	717.7	665.4	623.9	593.9
35°	1300.4	1180.1	1037.0	928.0	848.3	785.2	731.4	683.1	631.7	591.4	560.9
37.5°	1256.5	1155.0	1003.4	875.5	792.1	733.8	689.9	647.8	600.7	557.2	528.5
40°	1212.2	1130.2	977.4	843.6	756.6	696.6	657.1	622.8	577.1	536.4	505.5
42.5°	1146.3	1096.5	952.7	810.2	716.3	658.5	625.3	593.0	553.0	511.7	482.6
45°	1025.4	1032.0	902.0	757.0	660.7	602.6	571.3	548.9	513.3	479.3	449.5
47.5°	873.7	935.2	842.5	700.2	602.0	547.4	520.1	500.5	476.6	443.1	416.0
50°	774.8	862.5	794.9	662.2	565.1	511.0	483.9	468.1	447.2	420.8	395.0
52.5°	683.5	777.8	737.3	619.8	525.2	475.6	449.2	436.2	419.6	394.9	371.4
55°	557.3	652.9	643.6	555.8	465.3	420.8	400.7	386.1	374.8	356.3	337.7
57.5°	450.8	541.4	546.2	484.6	412.5	368.6	351.3	340.2	332.9	318.9	301.7
60°	383.7	466.9	483.1	436.7	374.8	336.1	319.1	310.2	304.4	293.2	280.0
62.5°	328.0	398.8	417.2	383.7	338.6	302.4	289.1	280.5	276.6	266.9	255.3
65°	251.1	309.8	327.6	309.0	285.5	256.4	245.6	238.2	234.8	229.3	220.9
67.5°	188.7	231.7	251.2	238.0	229.5	211.2	204.3	200.4	197.2	193.6	186.4
70°	151.6	183.4	203.5	200.0	193.0	183.4	178.3	175.6	172.5	169.5	163.2
72.5°	121.9	143.7	162.6	164.4	158.6	156.7	152.3	151.2	149.3	145.6	142.2
75°	80.9	95.9	109.1	114.1	116.4	118.4	116.4	116.0	115.6	112.6	110.6
77.5°	53.0	61.1	69.4	78.0	81.6	84.2	84.8	86.2	85.2	83.6	82.7
80°	40.6	42.5	48.4	55.7	61.5	63.8	65.3	66.1	65.7	65.3	63.8
82.5°	29.5	31.1	33.8	39.0	43.8	47.8	48.7	48.5	49.4	49.6	48.4
85°	15.9	16.3	17.1	17.8	20.5	24.7	26.0	26.7	27.5	27.5	25.1
87.5°	6.3	5.8	6.2	6.0	6.8	6.9	8.6	10.0	10.4	9.4	9.5
90°	6.5	5.5	4.4	3.5	2.7	1.9	1.1	0.4	1.1	1.9	2.7
92.5°	7.6	6.8	6.1	5.8	6.0	6.2	6.5	6.7	6.5	6.2	6.0
95°	9.3	8.5	7.6	8.8	12.0	15.2	18.5	21.8	18.5	15.2	12.0
97.5°	22.9	28.6	34.3	37.9	39.4	40.8	42.3	43.7	42.3	40.8	39.4
100°	36.6	48.9	61.3	66.7	65.0	63.5	61.9	60.3	61.9	63.5	65.0
102.5°	50.5	64.0	77.6	83.7	82.6	81.4	80.3	79.2	80.3	81.4	82.6
105°	92.4	99.6	106.7	109.9	109.0	108.1	107.2	106.3	107.2	108.1	109.0
107.5°	141.0	139.9	138.8	137.8	137.1	136.4	135.7	135.0	135.7	136.4	137.1
110°	159.2	158.3	157.4	156.7	156.0	155.4	154.8	154.2	154.8	155.4	156.0

TEST NUMBER: P332270-840

CATALOG NUMBER: S123RDIP-S560D365U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	177.2	176.3	175.4	174.7	174.1	173.6	173.0	172.4	173.0	173.6	174.1
115°	203.4	202.7	202.0	201.4	200.9	200.5	200.0	199.4	200.0	200.5	200.9
117.5°	229.2	228.8	228.5	228.0	227.4	226.8	226.3	225.7	226.3	226.8	227.4
120°	245.8	245.5	245.3	244.8	244.1	243.4	242.7	242.0	242.7	243.4	244.1
122.5°	261.9	261.6	261.3	260.8	260.2	259.6	259.1	258.5	259.1	259.6	260.2
125°	284.9	284.6	284.2	283.8	283.1	282.5	281.9	281.2	281.9	282.5	283.1
127.5°	307.0	306.6	306.2	305.7	305.1	304.5	303.9	303.2	303.9	304.5	305.1
130°	320.5	320.2	319.9	319.4	318.8	318.1	317.5	316.9	317.5	318.1	318.8
132.5°	333.6	333.3	333.0	332.5	331.9	331.3	330.6	330.0	330.6	331.3	331.9
135°	353.0	352.6	352.3	351.9	351.5	351.0	350.5	350.1	350.5	351.0	351.5
137.5°	370.3	370.2	370.0	369.6	369.0	368.4	367.8	367.2	367.8	368.4	369.0
140°	381.3	381.1	380.9	380.5	380.0	379.6	379.1	378.6	379.1	379.6	380.0
142.5°	391.9	391.7	391.4	391.1	390.6	390.1	389.7	389.2	389.7	390.1	390.6
145°	406.9	406.7	406.6	406.2	405.7	405.1	404.6	403.9	404.6	405.1	405.7
147.5°	419.9	419.8	419.6	419.3	419.0	418.6	418.3	417.9	418.3	418.6	419.0
150°	427.9	427.8	427.6	427.4	427.2	426.9	426.7	426.5	426.7	426.9	427.2
152.5°	434.8	434.7	434.7	434.5	434.4	434.3	434.2	434.1	434.2	434.3	434.4
155°	444.4	444.4	444.3	444.3	444.5	444.6	444.8	445.0	444.8	444.6	444.5
157.5°	453.1	453.2	453.3	453.3	453.3	453.4	453.4	453.4	453.4	453.4	453.3
160°	458.0	458.1	458.2	458.3	458.3	458.4	458.5	458.6	458.5	458.4	458.3
162.5°	462.3	462.3	462.4	462.6	462.8	463.0	463.2	463.4	463.2	463.0	462.8
165°	468.0	468.1	468.2	468.3	468.6	468.8	469.0	469.3	469.0	468.8	468.6
167.5°	472.4	472.4	472.4	472.5	472.9	473.2	473.5	473.8	473.5	473.2	472.9
170°	474.9	474.9	474.9	475.1	475.4	475.7	476.1	476.4	476.1	475.7	475.4
172.5°	476.6	476.5	476.5	476.6	477.0	477.4	477.8	478.1	477.8	477.4	477.0
175°	478.8	478.7	478.6	478.8	479.2	479.5	479.9	480.3	479.9	479.5	479.2
177.5°	479.6	479.6	479.5	479.6	480.0	480.3	480.6	480.9	480.6	480.3	480.0
180°	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3

TEST NUMBER: P332270-840

CATALOG NUMBER: S123RDIP-S560D365U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5
2.5°	888.1	884.0	881.3	875.0	871.1	866.8	862.4	865.2	864.8	864.5	864.5
5°	858.3	849.4	841.3	830.8	824.3	816.2	809.9	809.2	810.7	805.3	802.2
7.5°	828.8	816.6	805.1	793.6	781.3	771.5	765.5	762.7	758.7	755.4	751.8
10°	808.0	793.8	782.4	768.2	755.1	743.5	736.1	731.0	728.3	725.6	720.6
12.5°	786.7	772.6	758.3	742.1	729.6	716.2	710.7	705.1	699.8	696.8	689.9
15°	755.4	737.2	722.2	705.1	691.3	678.0	670.3	659.1	657.5	653.7	646.7
17.5°	724.1	704.4	683.6	671.0	655.2	641.6	629.8	626.0	614.9	610.8	604.7
20°	699.3	681.2	665.3	648.6	625.8	613.1	603.8	598.7	589.9	584.4	580.6
22.5°	678.0	659.4	641.2	621.8	602.9	588.7	581.8	574.0	569.2	561.6	557.3
25°	647.5	627.4	605.3	584.4	570.9	560.1	549.3	542.3	535.3	531.8	524.1
27.5°	612.1	591.1	570.5	554.6	538.0	527.3	517.5	511.3	502.9	497.1	492.8
30°	592.6	567.8	550.1	535.7	514.4	504.4	497.1	489.3	483.1	477.0	472.6
32.5°	570.0	547.3	530.5	512.8	496.4	485.5	475.9	469.2	463.9	458.1	453.8
35°	534.5	515.6	498.2	480.4	468.4	457.2	446.0	440.2	435.2	429.7	425.9
37.5°	502.5	484.8	468.3	451.4	436.6	427.4	418.4	413.9	407.2	403.5	399.6
40°	482.7	465.3	447.6	431.3	415.8	408.9	400.7	394.2	388.0	385.3	381.0
42.5°	461.1	443.6	428.7	411.1	398.5	389.0	381.5	374.4	369.7	365.8	363.3
45°	429.0	413.4	398.8	381.4	369.4	361.2	352.7	346.2	341.9	339.2	335.0
47.5°	397.8	382.3	367.4	352.2	340.6	331.3	322.9	318.2	312.7	309.3	306.4
50°	375.2	361.2	345.4	331.4	319.9	310.6	303.7	297.8	292.8	288.5	286.6
52.5°	354.5	339.6	325.9	313.0	300.7	290.1	283.9	277.7	274.0	269.0	266.8
55°	320.2	306.0	294.4	281.6	269.6	260.7	253.0	247.5	243.7	238.2	235.2
57.5°	288.1	275.3	261.5	250.4	238.0	230.6	224.1	216.7	212.1	207.8	204.8
60°	266.5	251.8	239.8	229.3	218.5	208.8	203.1	197.2	192.3	187.9	185.3
62.5°	243.9	231.1	219.7	208.3	198.4	190.0	183.3	178.3	174.0	171.3	168.5
65°	209.2	199.2	187.6	178.3	169.1	162.9	157.4	153.2	150.1	148.1	145.8
67.5°	177.4	167.6	157.5	148.3	142.2	137.4	133.9	130.3	128.8	126.2	124.7
70°	156.6	146.6	137.7	130.8	124.5	121.1	118.8	116.0	114.5	111.4	109.9
72.5°	134.1	126.8	120.4	114.6	109.7	106.5	103.6	100.3	97.8	94.4	92.8
75°	105.6	99.1	94.0	90.1	87.1	82.8	78.6	75.0	73.9	72.7	72.3
77.5°	78.2	74.0	70.4	67.2	63.3	60.2	59.3	58.5	58.3	57.7	57.7
80°	61.5	57.7	54.9	51.1	48.8	48.8	48.8	48.0	48.4	48.4	48.4
82.5°	45.7	42.1	40.7	39.3	38.9	39.2	39.2	39.3	39.1	39.7	39.4
85°	23.6	23.9	24.7	24.3	24.7	24.7	25.5	25.1	25.5	24.7	25.5
87.5°	9.4	10.5	11.0	11.5	12.0	11.9	12.3	12.3	12.7	12.8	12.8
90°	3.5	4.4	5.5	6.5	7.6	8.6	8.9	9.2	9.5	9.8	10.1
92.5°	5.8	6.1	6.8	7.6	8.4	9.1	9.6	10.2	10.7	11.2	11.5
95°	8.8	7.6	8.5	9.3	10.2	11.1	11.6	12.2	12.7	13.3	13.5
97.5°	37.9	34.3	28.6	22.9	17.2	11.5	12.1	12.7	13.4	14.0	14.3
100°	66.7	61.3	48.9	36.6	24.1	11.8	12.4	13.0	13.6	14.3	14.6
102.5°	83.7	77.6	64.0	50.5	37.0	23.5	21.5	19.6	17.6	15.7	14.7
105°	109.9	106.7	99.6	92.4	85.3	78.2	64.1	50.1	36.1	22.0	15.0
107.5°	137.8	138.8	139.9	141.0	142.1	143.2	132.9	122.7	112.4	102.1	91.6
110°	156.7	157.4	158.3	159.2	160.1	161.0	158.3	155.7	153.1	150.5	143.5

TEST NUMBER: P332270-840

CATALOG NUMBER: S123RDIP-S560D365U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	174.7	175.4	176.3	177.2	178.0	178.9	178.9	179.0	179.0	179.2	177.9
115°	201.4	202.0	202.7	203.4	204.1	204.8	205.6	206.4	207.2	208.0	208.5
117.5°	228.0	228.5	228.8	229.2	229.6	229.9	230.6	231.3	231.9	232.5	232.9
120°	244.8	245.3	245.5	245.8	246.0	246.2	246.9	247.5	248.1	248.7	249.1
122.5°	260.8	261.3	261.6	261.9	262.2	262.5	263.0	263.4	263.9	264.3	264.5
125°	283.8	284.2	284.6	284.9	285.2	285.5	285.7	285.8	286.0	286.1	286.3
127.5°	305.7	306.2	306.6	307.0	307.4	307.7	308.0	308.2	308.5	308.8	308.8
130°	319.4	319.9	320.2	320.5	320.8	321.1	321.4	321.8	322.1	322.4	322.6
132.5°	332.5	333.0	333.3	333.6	333.8	334.1	334.4	334.7	335.0	335.3	335.4
135°	351.9	352.3	352.6	353.0	353.4	353.7	353.9	354.2	354.4	354.6	354.6
137.5°	369.6	370.0	370.2	370.3	370.5	370.7	371.1	371.4	371.8	372.2	372.3
140°	380.5	380.9	381.1	381.3	381.6	381.8	382.1	382.4	382.7	383.1	383.1
142.5°	391.1	391.4	391.7	391.9	392.1	392.4	392.6	392.9	393.1	393.4	393.4
145°	406.2	406.6	406.7	406.9	407.0	407.2	407.4	407.5	407.7	407.8	407.9
147.5°	419.3	419.6	419.8	419.9	420.1	420.2	420.4	420.5	420.7	420.9	420.8
150°	427.4	427.6	427.8	427.9	428.1	428.2	428.4	428.6	428.7	428.9	428.8
152.5°	434.5	434.7	434.7	434.8	434.9	435.0	435.4	435.7	436.0	436.3	436.2
155°	444.3	444.3	444.4	444.4	444.5	444.6	445.0	445.5	445.9	446.3	446.2
157.5°	453.3	453.3	453.2	453.1	453.0	453.0	453.4	453.9	454.4	454.9	454.8
160°	458.3	458.2	458.1	458.0	458.0	457.9	458.3	458.8	459.3	459.8	459.7
162.5°	462.6	462.4	462.3	462.3	462.2	462.1	462.6	463.2	463.7	464.2	464.3
165°	468.3	468.2	468.1	468.0	467.9	467.9	468.5	469.1	469.8	470.4	470.4
167.5°	472.5	472.4	472.4	472.4	472.4	472.4	473.0	473.6	474.3	474.9	474.9
170°	475.1	474.9	474.9	474.9	474.9	474.9	475.6	476.3	476.9	477.5	477.5
172.5°	476.6	476.5	476.5	476.6	476.7	476.7	477.4	478.0	478.6	479.2	479.2
175°	478.8	478.6	478.7	478.8	478.8	478.9	479.5	480.0	480.6	481.1	481.1
177.5°	479.6	479.5	479.6	479.6	479.7	479.8	480.3	480.8	481.3	481.8	481.7
180°	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3

TEST NUMBER: P332270-840

CATALOG NUMBER: S123RDIP-S560D365U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5
2.5°	860.8	860.5	860.8	859.6	860.8	860.5	860.8	864.5	864.5	864.8	865.2
5°	801.0	800.6	799.5	796.1	799.5	800.6	801.0	802.2	805.3	810.7	809.2
7.5°	748.8	748.3	744.9	745.0	744.9	748.3	748.8	751.8	755.4	758.7	762.7
10°	717.9	718.3	713.7	710.9	713.7	718.3	717.9	720.6	725.6	728.3	731.0
12.5°	687.9	686.1	682.4	679.3	682.4	686.1	687.9	689.9	696.8	699.8	705.1
15°	648.2	644.4	635.1	635.9	635.1	644.4	648.2	646.7	653.7	657.5	659.1
17.5°	601.6	598.7	598.6	593.2	598.6	598.7	601.6	604.7	610.8	614.9	626.0
20°	574.4	572.5	573.2	567.8	573.2	572.5	574.4	580.6	584.4	589.9	598.7
22.5°	553.0	551.1	547.9	546.1	547.9	551.1	553.0	557.3	561.6	569.2	574.0
25°	521.8	518.7	515.6	517.6	515.6	518.7	521.8	524.1	531.8	535.3	542.3
27.5°	490.5	488.2	485.1	484.7	485.1	488.2	490.5	492.8	497.1	502.9	511.3
30°	470.7	468.4	466.9	464.9	466.9	468.4	470.7	472.6	477.0	483.1	489.3
32.5°	450.6	450.2	447.4	447.0	447.4	450.2	450.6	453.8	458.1	463.9	469.2
35°	424.3	422.0	421.2	421.6	421.2	422.0	424.3	425.9	429.7	435.2	440.2
37.5°	399.3	396.3	394.9	393.4	394.9	396.3	399.3	399.6	403.5	407.2	413.9
40°	381.4	378.3	377.5	376.8	377.5	378.3	381.4	381.0	385.3	388.0	394.2
42.5°	361.2	360.0	359.6	358.2	359.6	360.0	361.2	363.3	365.8	369.7	374.4
45°	333.8	333.5	331.1	331.8	331.1	333.5	333.8	335.0	339.2	341.9	346.2
47.5°	304.9	303.2	301.5	302.7	301.5	303.2	304.9	306.4	309.3	312.7	318.2
50°	285.1	284.3	280.8	281.6	280.8	284.3	285.1	286.6	288.5	292.8	297.8
52.5°	265.3	262.4	261.1	260.5	261.1	262.4	265.3	266.8	269.0	274.0	277.7
55°	232.5	228.9	227.4	226.6	227.4	228.9	232.5	235.2	238.2	243.7	247.5
57.5°	200.3	199.3	198.1	198.9	198.1	199.3	200.3	204.8	207.8	212.1	216.7
60°	181.4	181.4	181.4	181.1	181.4	181.4	181.4	185.3	187.9	192.3	197.2
62.5°	166.8	165.9	165.6	166.1	165.6	165.9	166.8	168.5	171.3	174.0	178.3
65°	144.6	144.3	142.7	142.4	142.7	144.3	144.6	145.8	148.1	150.1	153.2
67.5°	123.7	122.3	121.9	121.3	121.9	122.3	123.7	124.7	126.2	128.8	130.3
70°	108.0	107.1	104.8	105.2	104.8	107.1	108.0	109.9	111.4	114.5	116.0
72.5°	90.9	90.1	89.7	89.1	89.7	90.1	90.9	92.8	94.4	97.8	100.3
75°	71.9	71.6	71.2	72.7	71.2	71.6	71.9	72.3	72.7	73.9	75.0
77.5°	57.7	57.7	57.9	57.3	57.9	57.7	57.7	57.7	57.7	58.3	58.5
80°	48.4	48.4	48.0	48.0	48.0	48.4	48.4	48.4	48.4	48.4	48.0
82.5°	38.8	39.1	39.3	38.7	39.3	39.1	38.8	39.4	39.7	39.1	39.3
85°	25.5	25.1	26.0	25.5	26.0	25.1	25.5	25.5	24.7	25.5	25.1
87.5°	13.5	12.9	12.9	13.3	12.9	12.9	13.5	12.8	12.8	12.7	12.3
90°	10.2	10.4	10.5	10.7	10.5	10.4	10.2	10.1	9.8	9.5	9.2
92.5°	11.5	11.6	11.7	11.8	11.7	11.6	11.5	11.5	11.2	10.7	10.2
95°	13.5	13.5	13.5	13.5	13.5	13.5	13.5	13.5	13.3	12.7	12.2
97.5°	14.4	14.5	14.6	14.7	14.6	14.5	14.4	14.3	14.0	13.4	12.7
100°	14.7	14.8	14.9	14.9	14.9	14.8	14.7	14.6	14.3	13.6	13.0
102.5°	14.8	14.9	15.1	15.2	15.1	14.9	14.8	14.7	15.7	17.6	19.6
105°	15.2	15.3	15.6	15.7	15.6	15.3	15.2	15.0	22.0	36.1	50.1
107.5°	81.1	70.5	59.9	49.3	59.9	70.5	81.1	91.6	102.1	112.4	122.7
110°	132.2	120.8	109.5	98.2	109.5	120.8	132.2	143.5	150.5	153.1	155.7

TEST NUMBER: P332270-840

CATALOG NUMBER: S123RDIP-S560D365U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	175.5	173.2	170.8	168.3	170.8	173.2	175.5	177.9	179.2	179.0	179.0
115°	208.8	209.2	209.5	209.8	209.5	209.2	208.8	208.5	208.0	207.2	206.4
117.5°	232.9	233.0	233.1	233.1	233.1	233.0	232.9	232.9	232.5	231.9	231.3
120°	249.1	249.1	249.1	249.1	249.1	249.1	249.1	249.1	248.7	248.1	247.5
122.5°	264.6	264.7	264.7	264.8	264.7	264.7	264.6	264.5	264.3	263.9	263.4
125°	286.4	286.6	286.8	286.9	286.8	286.6	286.4	286.3	286.1	286.0	285.8
127.5°	308.6	308.5	308.3	308.2	308.3	308.5	308.6	308.8	308.8	308.5	308.2
130°	322.3	322.2	322.0	321.8	322.0	322.2	322.3	322.6	322.4	322.1	321.8
132.5°	335.1	334.9	334.7	334.5	334.7	334.9	335.1	335.4	335.3	335.0	334.7
135°	354.4	354.2	353.9	353.7	353.9	354.2	354.4	354.6	354.6	354.4	354.2
137.5°	372.1	372.0	371.8	371.7	371.8	372.0	372.1	372.3	372.2	371.8	371.4
140°	383.0	382.8	382.7	382.5	382.7	382.8	383.0	383.1	383.1	382.7	382.4
142.5°	393.2	392.9	392.7	392.5	392.7	392.9	393.2	393.4	393.4	393.1	392.9
145°	407.9	407.9	407.9	407.9	407.9	407.9	407.9	407.9	407.8	407.7	407.5
147.5°	420.4	420.0	419.7	419.3	419.7	420.0	420.4	420.8	420.9	420.7	420.5
150°	428.6	428.4	428.1	427.9	428.1	428.4	428.6	428.8	428.9	428.7	428.6
152.5°	435.9	435.5	435.0	434.7	435.0	435.5	435.9	436.2	436.3	436.0	435.7
155°	445.8	445.2	444.7	444.2	444.7	445.2	445.8	446.2	446.3	445.9	445.5
157.5°	454.2	453.6	452.9	452.3	452.9	453.6	454.2	454.8	454.9	454.4	453.9
160°	459.2	458.6	458.1	457.5	458.1	458.6	459.2	459.7	459.8	459.3	458.8
162.5°	463.8	463.3	462.8	462.3	462.8	463.3	463.8	464.3	464.2	463.7	463.2
165°	469.9	469.3	468.8	468.2	468.8	469.3	469.9	470.4	470.4	469.8	469.1
167.5°	474.3	473.6	473.0	472.4	473.0	473.6	474.3	474.9	474.9	474.3	473.6
170°	476.9	476.3	475.6	474.9	475.6	476.3	476.9	477.5	477.5	476.9	476.3
172.5°	478.5	477.8	477.1	476.4	477.1	477.8	478.5	479.2	479.2	478.6	478.0
175°	480.5	479.8	479.2	478.6	479.2	479.8	480.5	481.1	481.1	480.6	480.0
177.5°	481.1	480.5	479.8	479.2	479.8	480.5	481.1	481.7	481.8	481.3	480.8
180°	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3

TEST NUMBER: P332270-840

CATALOG NUMBER: S123RDIP-S560D365U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5
2.5°	862.4	866.8	871.1	875.0	881.3	884.0	888.1	889.6	894.2	901.1	906.7
5°	809.9	816.2	824.3	830.8	841.3	849.4	858.3	866.8	876.9	891.2	903.9
7.5°	765.5	771.5	781.3	793.6	805.1	816.6	828.8	840.3	854.7	875.3	895.5
10°	736.1	743.5	755.1	768.2	782.4	793.8	808.0	822.7	840.5	864.1	888.5
12.5°	710.7	716.2	729.6	742.1	758.3	772.6	786.7	803.9	824.2	849.3	878.6
15°	670.3	678.0	691.3	705.1	722.2	737.2	755.4	776.3	796.1	827.0	862.5
17.5°	629.8	641.6	655.2	671.0	683.6	704.4	724.1	745.5	769.8	802.6	841.6
20°	603.8	613.1	625.8	648.6	665.3	681.2	699.3	726.0	748.4	785.6	826.2
22.5°	581.8	588.7	602.9	621.8	641.2	659.4	678.0	703.5	731.1	766.4	810.4
25°	549.3	560.1	570.9	584.4	605.3	627.4	647.5	669.1	698.5	736.1	783.7
27.5°	517.5	527.3	538.0	554.6	570.5	591.1	612.1	636.9	668.4	708.1	756.4
30°	497.1	504.4	514.4	535.7	550.1	567.8	592.6	614.6	644.0	686.2	737.2
32.5°	475.9	485.5	496.4	512.8	530.5	547.3	570.0	593.9	623.9	665.4	717.7
35°	446.0	457.2	468.4	480.4	498.2	515.6	534.5	560.9	591.4	631.7	683.1
37.5°	418.4	427.4	436.6	451.4	468.3	484.8	502.5	528.5	557.2	600.7	647.8
40°	400.7	408.9	415.8	431.3	447.6	465.3	482.7	505.5	536.4	577.1	622.8
42.5°	381.5	389.0	398.5	411.1	428.7	443.6	461.1	482.6	511.7	553.0	593.0
45°	352.7	361.2	369.4	381.4	398.8	413.4	429.0	449.5	479.3	513.3	548.9
47.5°	322.9	331.3	340.6	352.2	367.4	382.3	397.8	416.0	443.1	476.6	500.5
50°	303.7	310.6	319.9	331.4	345.4	361.2	375.2	395.0	420.8	447.2	468.1
52.5°	283.9	290.1	300.7	313.0	325.9	339.6	354.5	371.4	394.9	419.6	436.2
55°	253.0	260.7	269.6	281.6	294.4	306.0	320.2	337.7	356.3	374.8	386.1
57.5°	224.1	230.6	238.0	250.4	261.5	275.3	288.1	301.7	318.9	332.9	340.2
60°	203.1	208.8	218.5	229.3	239.8	251.8	266.5	280.0	293.2	304.4	310.2
62.5°	183.3	190.0	198.4	208.3	219.7	231.1	243.9	255.3	266.9	276.6	280.5
65°	157.4	162.9	169.1	178.3	187.6	199.2	209.2	220.9	229.3	234.8	238.2
67.5°	133.9	137.4	142.2	148.3	157.5	167.6	177.4	186.4	193.6	197.2	200.4
70°	118.8	121.1	124.5	130.8	137.7	146.6	156.6	163.2	169.5	172.5	175.6
72.5°	103.6	106.5	109.7	114.6	120.4	126.8	134.1	142.2	145.6	149.3	151.2
75°	78.6	82.8	87.1	90.1	94.0	99.1	105.6	110.6	112.6	115.6	116.0
77.5°	59.3	60.2	63.3	67.2	70.4	74.0	78.2	82.7	83.6	85.2	86.2
80°	48.8	48.8	48.8	51.1	54.9	57.7	61.5	63.8	65.3	65.7	66.1
82.5°	39.2	39.2	38.9	39.3	40.7	42.1	45.7	48.4	49.6	49.4	48.5
85°	25.5	24.7	24.7	24.3	24.7	23.9	23.6	25.1	27.5	27.5	26.7
87.5°	12.3	11.9	12.0	11.5	11.0	10.5	9.4	9.5	9.4	10.4	10.0
90°	8.9	8.6	7.6	6.5	5.5	4.4	3.5	2.7	1.9	1.1	0.4
92.5°	9.6	9.1	8.4	7.6	6.8	6.1	5.8	6.0	6.2	6.5	6.7
95°	11.6	11.1	10.2	9.3	8.5	7.6	8.8	12.0	15.2	18.5	21.8
97.5°	12.1	11.5	17.2	22.9	28.6	34.3	37.9	39.4	40.8	42.3	43.7
100°	12.4	11.8	24.1	36.6	48.9	61.3	66.7	65.0	63.5	61.9	60.3
102.5°	21.5	23.5	37.0	50.5	64.0	77.6	83.7	82.6	81.4	80.3	79.2
105°	64.1	78.2	85.3	92.4	99.6	106.7	109.9	109.0	108.1	107.2	106.3
107.5°	132.9	143.2	142.1	141.0	139.9	138.8	137.8	137.1	136.4	135.7	135.0
110°	158.3	161.0	160.1	159.2	158.3	157.4	156.7	156.0	155.4	154.8	154.2

TEST NUMBER: P332270-840

CATALOG NUMBER: S123RDIP-S560D365U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	178.9	178.9	178.0	177.2	176.3	175.4	174.7	174.1	173.6	173.0	172.4
115°	205.6	204.8	204.1	203.4	202.7	202.0	201.4	200.9	200.5	200.0	199.4
117.5°	230.6	229.9	229.6	229.2	228.8	228.5	228.0	227.4	226.8	226.3	225.7
120°	246.9	246.2	246.0	245.8	245.5	245.3	244.8	244.1	243.4	242.7	242.0
122.5°	263.0	262.5	262.2	261.9	261.6	261.3	260.8	260.2	259.6	259.1	258.5
125°	285.7	285.5	285.2	284.9	284.6	284.2	283.8	283.1	282.5	281.9	281.2
127.5°	308.0	307.7	307.4	307.0	306.6	306.2	305.7	305.1	304.5	303.9	303.2
130°	321.4	321.1	320.8	320.5	320.2	319.9	319.4	318.8	318.1	317.5	316.9
132.5°	334.4	334.1	333.8	333.6	333.3	333.0	332.5	331.9	331.3	330.6	330.0
135°	353.9	353.7	353.4	353.0	352.6	352.3	351.9	351.5	351.0	350.5	350.1
137.5°	371.1	370.7	370.5	370.3	370.2	370.0	369.6	369.0	368.4	367.8	367.2
140°	382.1	381.8	381.6	381.3	381.1	380.9	380.5	380.0	379.6	379.1	378.6
142.5°	392.6	392.4	392.1	391.9	391.7	391.4	391.1	390.6	390.1	389.7	389.2
145°	407.4	407.2	407.0	406.9	406.7	406.6	406.2	405.7	405.1	404.6	403.9
147.5°	420.4	420.2	420.1	419.9	419.8	419.6	419.3	419.0	418.6	418.3	417.9
150°	428.4	428.2	428.1	427.9	427.8	427.6	427.4	427.2	426.9	426.7	426.5
152.5°	435.4	435.0	434.9	434.8	434.7	434.7	434.5	434.4	434.3	434.2	434.1
155°	445.0	444.6	444.5	444.4	444.4	444.3	444.3	444.5	444.6	444.8	445.0
157.5°	453.4	453.0	453.0	453.1	453.2	453.3	453.3	453.3	453.4	453.4	453.4
160°	458.3	457.9	458.0	458.0	458.1	458.2	458.3	458.3	458.4	458.5	458.6
162.5°	462.6	462.1	462.2	462.3	462.3	462.4	462.6	462.8	463.0	463.2	463.4
165°	468.5	467.9	467.9	468.0	468.1	468.2	468.3	468.6	468.8	469.0	469.3
167.5°	473.0	472.4	472.4	472.4	472.4	472.4	472.5	472.9	473.2	473.5	473.8
170°	475.6	474.9	474.9	474.9	474.9	474.9	475.1	475.4	475.7	476.1	476.4
172.5°	477.4	476.7	476.7	476.6	476.5	476.5	476.6	477.0	477.4	477.8	478.1
175°	479.5	478.9	478.8	478.8	478.7	478.6	478.8	479.2	479.5	479.9	480.3
177.5°	480.3	479.8	479.7	479.6	479.6	479.5	479.6	480.0	480.3	480.6	480.9
180°	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3

TEST NUMBER: P332270-840

CATALOG NUMBER: S123RDIP-S560D365U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5
2.5°	908.5	911.9	916.3	922.7	927.7	932.0	932.9	934.2	937.3	942.5	946.5
5°	914.4	923.3	937.6	951.5	966.6	979.0	990.6	998.8	1006.4	1022.7	1035.8
7.5°	912.5	932.3	954.7	979.8	1005.0	1029.6	1052.3	1072.7	1093.0	1116.6	1143.6
10°	911.3	934.5	964.6	996.7	1032.0	1066.4	1099.6	1125.6	1155.8	1182.9	1217.3
12.5°	905.4	938.9	974.9	1015.9	1059.2	1098.9	1142.7	1178.5	1212.9	1252.1	1292.1
15°	897.8	938.4	984.0	1038.5	1104.3	1152.3	1197.1	1259.4	1301.9	1344.5	1401.8
17.5°	883.7	933.3	990.4	1061.2	1116.1	1180.5	1248.0	1297.3	1354.5	1414.5	1466.3
20°	872.6	930.3	994.1	1063.7	1133.7	1203.8	1269.1	1327.9	1387.0	1456.3	1498.8
22.5°	861.5	918.5	984.8	1058.7	1134.0	1207.7	1281.7	1350.8	1417.3	1487.2	1541.6
25°	837.8	905.4	977.4	1052.9	1127.1	1208.3	1296.6	1373.5	1455.9	1527.8	1579.3
27.5°	813.9	875.9	947.5	1024.0	1106.5	1202.5	1306.3	1393.8	1476.3	1527.8	1544.0
30°	792.1	857.9	923.6	1001.4	1090.8	1197.9	1308.2	1408.4	1476.0	1498.4	1481.8
32.5°	770.2	829.8	894.9	974.5	1069.4	1186.5	1310.6	1399.7	1440.5	1423.3	1355.5
35°	731.4	785.2	848.3	928.0	1037.0	1180.1	1300.4	1360.8	1350.7	1253.9	1126.3
37.5°	689.9	733.8	792.1	875.5	1003.4	1155.0	1256.5	1265.4	1178.3	1029.9	882.4
40°	657.1	696.6	756.6	843.6	977.4	1130.2	1212.2	1176.3	1041.3	876.1	753.1
42.5°	625.3	658.5	716.3	810.2	952.7	1096.5	1146.3	1067.9	912.2	756.0	644.2
45°	571.3	602.6	660.7	757.0	902.0	1032.0	1025.4	889.3	733.4	607.6	514.8
47.5°	520.1	547.4	602.0	700.2	842.5	935.2	873.7	728.9	596.6	495.8	429.6
50°	483.9	511.0	565.1	662.2	794.9	862.5	774.8	635.1	514.0	430.5	377.9
52.5°	449.2	475.6	525.2	619.8	737.3	777.8	683.5	554.0	453.1	381.0	335.8
55°	400.7	420.8	465.3	555.8	643.6	652.9	557.3	449.1	365.9	315.6	284.7
57.5°	351.3	368.6	412.5	484.6	546.2	541.4	450.8	357.2	301.1	263.8	241.4
60°	319.1	336.1	374.8	436.7	483.1	466.9	383.7	308.3	260.3	232.9	215.1
62.5°	289.1	302.4	338.6	383.7	417.2	398.8	328.0	265.6	227.5	204.4	190.3
65°	245.6	256.4	285.5	309.0	327.6	309.8	251.1	207.7	180.3	164.0	154.3
67.5°	204.3	211.2	229.5	238.0	251.2	231.7	188.7	159.8	144.1	130.5	123.7
70°	178.3	183.4	193.0	200.0	203.5	183.4	151.6	130.4	117.2	107.6	103.3
72.5°	152.3	156.7	158.6	164.4	162.6	143.7	121.9	105.0	95.5	89.0	83.5
75°	116.4	118.4	116.4	114.1	109.1	95.9	80.9	72.3	65.3	62.3	60.4
77.5°	84.8	84.2	81.6	78.0	69.4	61.1	53.0	50.1	47.2	45.4	44.8
80°	65.3	63.8	61.5	55.7	48.4	42.5	40.6	38.7	37.6	35.5	35.2
82.5°	48.7	47.8	43.8	39.0	33.8	31.1	29.5	28.8	27.6	26.7	26.6
85°	26.0	24.7	20.5	17.8	17.1	16.3	15.9	15.9	14.3	13.9	13.9
87.5°	8.6	6.9	6.8	6.0	6.2	5.8	6.3	5.9	5.8	6.1	5.6
90°	1.1	1.9	2.7	3.5	4.4	5.5	6.5	7.6	8.6	8.9	9.2
92.5°	6.5	6.2	6.0	5.8	6.1	6.8	7.6	8.4	9.1	9.6	10.2
95°	18.5	15.2	12.0	8.8	7.6	8.5	9.3	10.2	11.1	11.6	12.2
97.5°	42.3	40.8	39.4	37.9	34.3	28.6	22.9	17.2	11.5	12.1	12.7
100°	61.9	63.5	65.0	66.7	61.3	48.9	36.6	24.1	11.8	12.4	13.0
102.5°	80.3	81.4	82.6	83.7	77.6	64.0	50.5	37.0	23.5	21.5	19.6
105°	107.2	108.1	109.0	109.9	106.7	99.6	92.4	85.3	78.2	64.1	50.1
107.5°	135.7	136.4	137.1	137.8	138.8	139.9	141.0	142.1	143.2	132.9	122.7
110°	154.8	155.4	156.0	156.7	157.4	158.3	159.2	160.1	161.0	158.3	155.7

TEST NUMBER: P332270-840

CATALOG NUMBER: S123RDIP-S560D365U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	173.0	173.6	174.1	174.7	175.4	176.3	177.2	178.0	178.9	178.9	179.0
115°	200.0	200.5	200.9	201.4	202.0	202.7	203.4	204.1	204.8	205.6	206.4
117.5°	226.3	226.8	227.4	228.0	228.5	228.8	229.2	229.6	229.9	230.6	231.3
120°	242.7	243.4	244.1	244.8	245.3	245.5	245.8	246.0	246.2	246.9	247.5
122.5°	259.1	259.6	260.2	260.8	261.3	261.6	261.9	262.2	262.5	263.0	263.4
125°	281.9	282.5	283.1	283.8	284.2	284.6	284.9	285.2	285.5	285.7	285.8
127.5°	303.9	304.5	305.1	305.7	306.2	306.6	307.0	307.4	307.7	308.0	308.2
130°	317.5	318.1	318.8	319.4	319.9	320.2	320.5	320.8	321.1	321.4	321.8
132.5°	330.6	331.3	331.9	332.5	333.0	333.3	333.6	333.8	334.1	334.4	334.7
135°	350.5	351.0	351.5	351.9	352.3	352.6	353.0	353.4	353.7	353.9	354.2
137.5°	367.8	368.4	369.0	369.6	370.0	370.2	370.3	370.5	370.7	371.1	371.4
140°	379.1	379.6	380.0	380.5	380.9	381.1	381.3	381.6	381.8	382.1	382.4
142.5°	389.7	390.1	390.6	391.1	391.4	391.7	391.9	392.1	392.4	392.6	392.9
145°	404.6	405.1	405.7	406.2	406.6	406.7	406.9	407.0	407.2	407.4	407.5
147.5°	418.3	418.6	419.0	419.3	419.6	419.8	419.9	420.1	420.2	420.4	420.5
150°	426.7	426.9	427.2	427.4	427.6	427.8	427.9	428.1	428.2	428.4	428.6
152.5°	434.2	434.3	434.4	434.5	434.7	434.7	434.8	434.9	435.0	435.4	435.7
155°	444.8	444.6	444.5	444.3	444.3	444.4	444.4	444.5	444.6	445.0	445.5
157.5°	453.4	453.4	453.3	453.3	453.3	453.2	453.1	453.0	453.0	453.4	453.9
160°	458.5	458.4	458.3	458.3	458.2	458.1	458.0	458.0	457.9	458.3	458.8
162.5°	463.2	463.0	462.8	462.6	462.4	462.3	462.3	462.2	462.1	462.6	463.2
165°	469.0	468.8	468.6	468.3	468.2	468.1	468.0	467.9	467.9	468.5	469.1
167.5°	473.5	473.2	472.9	472.5	472.4	472.4	472.4	472.4	472.4	473.0	473.6
170°	476.1	475.7	475.4	475.1	474.9	474.9	474.9	474.9	474.9	475.6	476.3
172.5°	477.8	477.4	477.0	476.6	476.5	476.5	476.6	476.7	476.7	477.4	478.0
175°	479.9	479.5	479.2	478.8	478.6	478.7	478.8	478.8	478.9	479.5	480.0
177.5°	480.6	480.3	480.0	479.6	479.5	479.6	479.6	479.7	479.8	480.3	480.8
180°	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3

TEST NUMBER: P332270-840

CATALOG NUMBER: S123RDIP-S560D365U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	903.5	903.5	903.5	903.5	903.5	903.5	903.5
2.5°	953.1	953.1	954.3	959.0	959.6	963.6	962.3
5°	1047.4	1054.8	1057.5	1069.1	1076.1	1079.1	1073.0
7.5°	1162.9	1183.6	1193.5	1205.6	1216.3	1219.6	1211.1
10°	1247.1	1268.7	1286.9	1298.1	1308.6	1315.5	1324.4
12.5°	1328.4	1355.0	1372.3	1388.2	1398.9	1407.8	1409.2
15°	1416.8	1457.0	1487.6	1510.1	1521.3	1527.1	1524.8
17.5°	1506.0	1543.3	1565.1	1587.9	1603.5	1604.3	1604.8
20°	1556.5	1592.9	1618.0	1635.0	1652.4	1651.6	1655.5
22.5°	1590.2	1618.8	1638.1	1650.4	1656.4	1653.5	1654.3
25°	1606.0	1614.5	1611.0	1591.2	1586.3	1568.1	1571.1
27.5°	1524.6	1484.4	1442.8	1389.2	1347.0	1313.2	1314.9
30°	1414.1	1342.9	1261.7	1193.7	1132.6	1115.5	1079.1
32.5°	1259.7	1153.0	1057.8	994.4	941.9	927.7	896.0
35°	997.9	894.2	796.4	737.6	714.4	682.0	681.6
37.5°	775.7	684.4	632.7	588.5	565.4	545.7	543.8
40°	652.6	581.4	542.3	510.6	487.8	473.0	469.6
42.5°	566.5	509.0	472.3	452.7	435.2	427.6	421.9
45°	462.6	423.9	398.4	380.6	372.4	366.7	363.6
47.5°	387.0	361.0	343.7	331.8	325.2	319.1	320.7
50°	345.8	324.6	311.7	300.5	295.5	291.2	291.6
52.5°	312.7	293.6	283.3	275.2	268.9	265.9	264.4
55°	265.4	253.4	242.9	237.1	233.6	229.3	228.2
57.5°	226.3	217.0	208.5	202.0	201.2	197.0	197.5
60°	200.4	192.6	185.6	182.2	179.5	176.0	177.1
62.5°	179.0	172.5	166.1	163.3	160.6	158.0	158.5
65°	146.6	140.4	136.5	135.0	133.8	132.7	131.5
67.5°	116.8	113.0	110.6	107.2	104.9	104.5	103.3
70°	98.3	93.2	89.0	84.7	83.5	83.1	83.5
72.5°	78.8	75.5	74.4	72.3	72.1	71.1	71.8
75°	59.2	58.1	57.3	55.7	55.7	55.7	55.7
77.5°	43.6	42.9	42.5	42.1	41.8	41.2	41.2
80°	34.0	33.6	32.9	32.9	32.5	32.9	32.5
82.5°	25.7	25.7	24.8	24.8	24.4	24.2	24.4
85°	13.1	12.7	13.5	12.7	13.1	12.4	13.1
87.5°	5.7	5.7	5.5	5.5	5.2	5.9	5.3
90°	9.5	9.8	10.1	10.2	10.4	10.5	10.7
92.5°	10.7	11.2	11.5	11.5	11.6	11.7	11.8
95°	12.7	13.3	13.5	13.5	13.5	13.5	13.5
97.5°	13.4	14.0	14.3	14.4	14.5	14.6	14.7
100°	13.6	14.3	14.6	14.7	14.8	14.9	14.9
102.5°	17.6	15.7	14.7	14.8	14.9	15.1	15.2
105°	36.1	22.0	15.0	15.2	15.3	15.6	15.7
107.5°	112.4	102.1	91.6	81.1	70.5	59.9	49.3
110°	153.1	150.5	143.5	132.2	120.8	109.5	98.2

TEST NUMBER: P332270-840

CATALOG NUMBER: S123RDIP-S560D365U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	179.0	179.2	177.9	175.5	173.2	170.8	168.3
115°	207.2	208.0	208.5	208.8	209.2	209.5	209.8
117.5°	231.9	232.5	232.9	232.9	233.0	233.1	233.1
120°	248.1	248.7	249.1	249.1	249.1	249.1	249.1
122.5°	263.9	264.3	264.5	264.6	264.7	264.7	264.8
125°	286.0	286.1	286.3	286.4	286.6	286.8	286.9
127.5°	308.5	308.8	308.8	308.6	308.5	308.3	308.2
130°	322.1	322.4	322.6	322.3	322.2	322.0	321.8
132.5°	335.0	335.3	335.4	335.1	334.9	334.7	334.5
135°	354.4	354.6	354.6	354.4	354.2	353.9	353.7
137.5°	371.8	372.2	372.3	372.1	372.0	371.8	371.7
140°	382.7	383.1	383.1	383.0	382.8	382.7	382.5
142.5°	393.1	393.4	393.4	393.2	392.9	392.7	392.5
145°	407.7	407.8	407.9	407.9	407.9	407.9	407.9
147.5°	420.7	420.9	420.8	420.4	420.0	419.7	419.3
150°	428.7	428.9	428.8	428.6	428.4	428.1	427.9
152.5°	436.0	436.3	436.2	435.9	435.5	435.0	434.7
155°	445.9	446.3	446.2	445.8	445.2	444.7	444.2
157.5°	454.4	454.9	454.8	454.2	453.6	452.9	452.3
160°	459.3	459.8	459.7	459.2	458.6	458.1	457.5
162.5°	463.7	464.2	464.3	463.8	463.3	462.8	462.3
165°	469.8	470.4	470.4	469.9	469.3	468.8	468.2
167.5°	474.3	474.9	474.9	474.3	473.6	473.0	472.4
170°	476.9	477.5	477.5	476.9	476.3	475.6	474.9
172.5°	478.6	479.2	479.2	478.5	477.8	477.1	476.4
175°	480.6	481.1	481.1	480.5	479.8	479.2	478.6
177.5°	481.3	481.8	481.7	481.1	480.5	479.8	479.2
180°	480.3	480.3	480.3	480.3	480.3	480.3	480.3

(END OF REPORT)