

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332326-840

Luminaire Tested: **S123RDIP-S775D1195U840-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332326-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S775D1195U840-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1195 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7440.4 lumens
Efficiency: N/A
Efficacy: 130.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 56.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332326-840

CATALOG NUMBER: S123RDIP-S775D1195U840-4F0-1E-UDD-A4

Luminous Intensity Polar Plot



TEST NUMBER: P332326-840

CATALOG NUMBER: S123RDIP-S775D1195U840-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	48	48	48
1	96	92	89	85	88	84	81	78	70	67	65	56	54	53	43	42	42
2	88	81	75	70	80	74	69	65	61	58	55	50	47	45	39	37	36
3	81	72	65	59	73	66	60	55	55	50	47	44	41	39	35	33	31
4	74	64	56	50	67	59	52	47	49	44	40	40	36	34	31	29	27
5	68	57	49	43	62	52	46	41	44	39	35	36	32	29	28	26	24
6	63	51	43	38	57	47	40	35	40	34	31	33	29	26	26	23	21
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	24	21	19
8	54	42	35	29	49	39	32	28	33	28	24	27	23	21	22	19	17
9	50	38	31	26	46	36	29	25	30	25	22	25	21	19	20	18	16
10	47	35	28	24	43	33	26	22	28	23	19	23	19	17	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13295	13295	13295	13295
5°	15847	13351	11757	13351
10°	19787	13274	10622	13274
15°	23226	13138	9686	13138
20°	25921	12936	8891	12936
25°	25508	12722	8402	12722
30°	18334	12525	7899	12525
35°	12242	12269	7573	12269
40°	9020	11960	7235	11960
45°	7566	11420	6905	11420
50°	6677	10712	6445	10712
55°	5853	9903	5814	9903
60°	5214	9128	5326	9128
65°	4579	8295	4956	8295
70°	3594	7553	4526	7553
75°	3165	6596	4134	6596
80°	2752	5604	4060	5604
85°	2223	4508	4310	4508

TEST NUMBER: P332326-840

CATALOG NUMBER: S123RDIP-S775D1195U840-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	121.5	1.6
10°-20°	379.5	5.1
20°-30°	596.1	8.0
30°-40°	621.9	8.4
40°-50°	532.3	7.2
50°-60°	405.7	5.5
60°-70°	260.0	3.5
70°-80°	125.1	1.7
80°-90°	37.6	0.5
90°-100°	322.6	4.3
100°-110°	913.4	12.3
110°-120°	898.5	12.1
120°-130°	716.7	9.6
130°-140°	565.1	7.6
140°-150°	421.7	5.7
150°-160°	294.0	4.0
160°-170°	172.7	2.3
170°-180°	56.2	0.8
0°-30°	1097.0	14.7
0°-40°	1719.0	23.1
0°-60°	2656.9	35.7
0°-90°	3079.6	41.4
90°-120°	2134.4	28.7
90°-150°	3837.9	51.6
90°-180°	4361.0	58.6
0°-180°	7440.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1235	1235	1235	1235	1235	
5°	1467	1236	1088	1236	1467	151
15°	2084	1179	869	1179	2084	591
25°	2148	1071	707	1071	2148	923
35°	932	934	576	934	932	611
45°	497	750	454	750	497	391
55°	312	528	310	528	312	282
65°	180	326	195	326	180	177
75°	76	159	99	159	76	82
85°	18	36	35	36	18	22
90°	34	2	34	2	34	19
95°	136	40	136	40	136	245
105°	1492	136	1492	136	1492	1472
115°	1815	240	1815	240	1815	1764
125°	1432	334	1432	334	1432	1297
135°	1160	392	1160	392	1160	900
145°	907	447	907	447	907	577
155°	752	508	752	508	752	351
165°	656	555	656	555	656	187
175°	590	578	590	578	590	57
180°	580	580	580	580	580	

TEST NUMBER: P332326-840

CATALOG NUMBER: S123RDIP-S775D1195U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1
2.5°	1315.5	1317.2	1311.6	1310.8	1304.4	1302.7	1302.7	1293.8	1288.4	1281.2	1277.0
5°	1466.6	1475.1	1470.9	1461.4	1445.5	1441.8	1431.8	1415.9	1398.0	1375.7	1365.1
7.5°	1655.5	1667.1	1662.6	1647.9	1631.3	1617.9	1589.5	1563.2	1526.3	1493.9	1466.2
10°	1810.3	1798.2	1788.7	1774.3	1759.1	1734.1	1704.6	1663.9	1616.8	1579.8	1538.5
12.5°	1926.2	1924.2	1912.2	1897.4	1875.8	1852.2	1815.8	1766.3	1711.5	1658.1	1610.9
15°	2084.2	2087.4	2079.4	2064.1	2033.5	1991.7	1936.7	1916.0	1837.9	1779.7	1721.5
17.5°	2193.5	2192.9	2191.8	2170.6	2139.3	2109.6	2058.6	2004.4	1933.5	1851.6	1773.2
20°	2262.9	2257.7	2258.7	2234.8	2211.6	2177.3	2127.6	2048.8	1990.6	1896.0	1815.0
22.5°	2261.2	2260.2	2264.2	2256.0	2239.1	2212.8	2173.6	2107.2	2033.0	1937.4	1846.3
25°	2147.7	2143.4	2168.3	2175.1	2202.1	2206.9	2195.2	2158.8	2088.4	1990.0	1877.4
27.5°	1797.5	1795.1	1841.2	1899.0	1972.1	2029.0	2084.0	2110.5	2088.4	2018.0	1905.2
30°	1475.1	1524.8	1548.1	1631.6	1724.6	1835.7	1933.0	2025.5	2048.2	2017.6	1925.0
32.5°	1224.8	1268.1	1287.5	1359.2	1445.9	1576.0	1721.9	1852.9	1945.5	1968.9	1913.2
35°	931.6	932.1	976.5	1008.2	1088.6	1222.3	1364.1	1539.6	1714.0	1846.2	1860.0
37.5°	743.4	746.0	772.8	804.5	864.7	935.5	1060.3	1206.2	1407.8	1610.6	1729.6
40°	641.9	646.6	666.7	697.9	741.2	794.7	891.9	1029.5	1197.5	1423.3	1607.8
42.5°	576.7	584.4	594.8	618.8	645.7	695.7	774.4	880.5	1033.4	1246.9	1459.8
45°	497.0	501.2	509.2	520.3	544.6	579.5	632.4	703.7	830.6	1002.5	1215.5
47.5°	438.4	436.2	444.5	453.5	469.7	493.5	529.0	587.2	677.7	815.6	996.3
50°	398.7	398.1	403.9	410.8	426.2	443.6	472.7	516.5	588.4	702.7	868.2
52.5°	361.4	363.5	367.6	376.2	387.2	401.3	427.4	459.0	520.8	619.4	757.3
55°	311.9	313.6	319.3	324.1	332.0	346.3	362.7	389.1	431.4	500.2	613.8
57.5°	270.0	269.3	274.9	276.1	285.1	296.7	309.4	329.9	360.6	411.6	488.2
60°	242.2	240.5	245.3	249.0	253.8	263.3	273.9	294.0	318.3	355.8	421.4
62.5°	216.8	216.0	219.5	223.2	227.1	235.8	244.7	260.1	279.3	311.0	363.0
65°	179.8	181.4	182.9	184.5	186.6	191.9	200.4	211.0	224.2	246.4	283.9
67.5°	141.3	142.9	143.4	146.6	151.2	154.5	159.7	169.1	178.2	197.0	218.3
70°	114.2	113.7	114.2	115.8	121.6	127.4	134.3	141.2	146.9	160.2	178.1
72.5°	98.2	97.1	98.6	98.9	101.7	103.3	107.7	114.1	121.6	130.6	143.5
75°	76.1	76.1	76.1	76.1	78.3	79.3	80.9	82.5	85.1	89.4	98.9
77.5°	56.2	56.4	57.1	57.7	58.1	58.7	59.7	61.2	62.2	64.4	68.6
80°	44.4	44.9	44.4	44.9	44.9	45.9	46.6	48.1	48.7	51.3	52.9
82.5°	33.4	33.1	33.4	33.9	33.9	35.0	35.1	36.3	36.4	37.8	39.4
85°	18.0	17.0	18.0	17.5	18.5	17.5	18.0	19.0	19.0	19.6	21.7
87.5°	11.0	12.1	11.0	11.2	11.4	11.4	11.2	10.9	11.5	11.4	11.1
90°	34.0	35.2	34.0	32.8	34.0	31.7	30.5	29.3	28.2	29.3	25.9
92.5°	56.6	58.7	57.5	61.0	63.1	69.2	78.4	98.8	136.1	180.5	198.5
95°	136.1	140.8	149.1	159.6	181.9	224.1	286.3	422.4	564.3	695.8	619.6
97.5°	370.5	380.6	412.3	465.1	551.7	692.1	843.3	1052.9	1153.6	1078.2	789.4
100°	735.7	734.5	780.2	865.9	984.4	1151.0	1288.3	1383.3	1342.3	1111.2	750.9
102.5°	1079.2	1106.2	1144.5	1212.2	1304.4	1410.1	1490.1	1493.2	1351.6	1050.2	694.6
105°	1492.5	1498.3	1535.9	1580.4	1634.5	1665.0	1642.6	1525.3	1280.1	943.3	625.4
107.5°	1730.4	1741.2	1753.8	1768.9	1768.0	1726.2	1623.4	1432.8	1154.8	849.0	581.3
110°	1828.1	1830.4	1832.7	1823.3	1790.5	1708.4	1560.5	1344.6	1075.9	795.5	564.3

TEST NUMBER: P332326-840

CATALOG NUMBER: S123RDIP-S775D1195U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1847.8	1847.2	1838.4	1809.3	1749.2	1643.6	1477.9	1257.3	1007.4	759.8	555.0
115°	1815.1	1809.3	1785.7	1734.1	1646.2	1518.2	1345.7	1141.7	924.5	721.5	551.5
117.5°	1711.4	1703.4	1669.6	1610.5	1518.7	1389.0	1234.1	1057.8	874.5	699.0	553.6
120°	1625.1	1618.0	1589.8	1524.1	1431.5	1312.9	1172.2	1013.7	848.3	688.7	557.3
122.5°	1544.3	1535.4	1504.4	1445.3	1362.9	1252.8	1122.4	979.0	826.7	682.2	563.9
125°	1431.5	1423.2	1393.9	1342.3	1267.2	1173.3	1060.7	932.8	799.0	673.5	573.7
127.5°	1338.5	1331.0	1304.4	1260.4	1193.5	1108.0	1006.4	892.4	774.7	669.2	585.0
130°	1286.0	1276.6	1251.9	1209.7	1147.5	1067.7	972.7	867.1	761.4	666.4	592.5
132.5°	1234.4	1227.8	1205.9	1163.7	1105.3	1029.3	940.8	843.6	749.3	665.5	598.1
135°	1160.4	1152.2	1131.0	1095.9	1038.3	971.5	895.2	811.9	733.4	664.1	606.6
137.5°	1082.3	1076.8	1059.0	1023.4	975.0	917.1	851.3	783.0	719.4	661.5	612.3
140°	1027.8	1029.0	1010.3	977.3	932.8	882.3	826.0	766.2	711.0	660.6	616.0
142.5°	977.1	978.3	961.4	932.3	894.3	850.4	801.6	750.2	703.5	658.7	618.8
145°	907.0	904.6	895.2	870.6	841.2	807.3	769.7	730.9	693.5	655.9	620.7
147.5°	849.2	848.3	839.4	822.7	800.4	776.3	746.0	715.3	683.6	651.5	620.7
150°	815.5	815.5	808.4	795.5	777.9	755.6	730.9	704.0	677.0	647.6	620.7
152.5°	787.3	787.3	783.0	771.1	757.3	738.7	716.9	693.7	669.5	643.0	617.8
155°	752.0	750.9	748.6	739.2	728.6	714.6	696.9	678.1	658.2	634.8	614.8
157.5°	719.9	720.1	718.3	711.2	702.1	691.1	677.5	661.8	645.5	627.5	610.9
160°	699.3	700.4	700.4	693.5	685.2	677.0	665.3	652.4	637.1	621.9	608.9
162.5°	680.5	681.7	681.7	675.6	670.1	662.9	652.2	641.1	628.6	616.2	605.2
165°	655.9	655.9	657.0	652.4	647.6	641.8	633.6	626.5	617.1	607.7	599.6
167.5°	632.4	632.4	633.6	630.3	628.2	624.0	619.2	613.9	606.1	599.4	593.9
170°	618.3	618.3	619.6	617.1	616.0	613.6	608.9	605.4	599.6	593.7	590.2
172.5°	605.2	606.1	608.2	605.9	605.6	604.3	600.5	597.9	593.0	589.0	587.3
175°	590.2	591.4	592.5	591.4	591.4	591.4	589.0	587.8	585.5	583.1	583.1
177.5°	581.5	581.5	583.4	582.4	583.4	583.4	582.4	581.5	580.6	579.7	580.6
180°	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7

TEST NUMBER: P332326-840

CATALOG NUMBER: S123RDIP-S775D1195U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1
2.5°	1275.3	1273.9	1268.1	1261.3	1252.4	1246.5	1241.8	1239.3	1231.7	1222.3	1216.1
5°	1354.0	1338.2	1321.3	1300.6	1281.6	1262.0	1249.9	1235.6	1218.2	1198.6	1184.9
7.5°	1438.5	1407.3	1373.8	1339.3	1305.0	1274.4	1247.4	1224.2	1196.4	1168.3	1148.7
10°	1503.2	1457.6	1410.6	1362.5	1318.6	1277.4	1245.7	1214.5	1181.1	1148.9	1124.6
12.5°	1562.0	1502.1	1447.8	1388.8	1332.6	1283.3	1237.6	1200.9	1160.8	1126.5	1098.7
15°	1636.4	1575.1	1509.4	1419.6	1345.0	1282.6	1227.2	1179.0	1130.4	1088.1	1061.2
17.5°	1706.0	1613.7	1525.6	1450.6	1353.7	1275.8	1208.0	1150.4	1097.1	1052.3	1019.1
20°	1734.7	1645.4	1549.6	1454.0	1358.8	1271.5	1192.8	1129.3	1073.8	1023.1	992.4
22.5°	1752.0	1650.8	1550.0	1447.2	1346.2	1255.5	1177.6	1107.7	1047.6	999.4	961.5
25°	1772.2	1651.7	1540.7	1439.2	1336.1	1237.7	1145.2	1071.2	1006.1	954.8	914.6
27.5°	1785.5	1643.8	1512.6	1399.7	1295.2	1197.2	1112.4	1034.0	968.0	913.7	870.6
30°	1788.1	1637.4	1491.0	1368.9	1262.5	1172.7	1082.8	1007.7	938.0	880.3	840.1
32.5°	1791.5	1621.7	1461.8	1332.0	1223.2	1134.2	1052.8	981.1	909.6	852.8	811.8
35°	1777.6	1613.2	1417.4	1268.4	1159.4	1073.3	999.8	933.7	863.4	808.4	766.6
37.5°	1717.5	1578.7	1371.6	1196.7	1082.8	1003.0	943.1	885.4	821.0	761.6	722.4
40°	1657.0	1544.9	1336.1	1153.2	1034.2	952.2	898.3	851.2	788.8	733.4	691.1
42.5°	1566.9	1498.8	1302.2	1107.4	979.2	900.2	854.7	810.6	755.9	699.5	659.7
45°	1401.6	1410.6	1232.9	1034.7	903.0	823.7	780.9	750.2	701.7	655.1	614.4
47.5°	1194.4	1278.4	1151.7	957.2	822.7	748.3	710.9	684.2	651.4	605.7	568.6
50°	1059.0	1179.0	1086.5	905.1	772.4	698.4	661.5	639.7	611.2	575.2	539.8
52.5°	934.2	1063.2	1007.8	847.2	717.9	650.3	614.1	596.2	573.5	539.7	507.7
55°	761.8	892.5	879.8	759.7	636.0	575.2	547.8	527.7	512.3	487.0	461.6
57.5°	616.3	740.1	746.7	662.5	563.9	503.8	480.2	465.0	455.0	435.9	412.4
60°	524.5	638.1	660.4	596.9	512.3	459.5	436.2	424.0	416.1	400.8	382.8
62.5°	448.4	545.1	570.3	524.6	462.8	413.3	395.2	383.4	378.0	364.8	348.9
65°	343.2	423.5	447.8	422.4	390.2	350.5	335.8	325.7	320.9	313.6	301.8
67.5°	258.0	316.6	343.3	325.4	313.8	288.7	279.2	273.9	269.6	264.6	254.9
70°	207.2	250.6	278.1	273.4	263.9	250.6	243.8	240.0	235.8	231.6	223.1
72.5°	166.6	196.5	222.3	224.7	216.9	214.2	208.2	206.6	204.1	199.0	194.4
75°	110.5	131.1	149.1	155.9	159.2	161.8	159.2	158.6	158.0	153.9	151.2
77.5°	72.4	83.5	94.8	106.5	111.6	115.1	116.0	118.0	116.5	114.3	113.0
80°	55.5	58.2	66.0	76.1	84.0	87.3	89.4	90.4	89.9	89.4	87.3
82.5°	40.3	42.5	46.3	53.3	60.0	65.2	66.6	66.3	67.5	67.8	66.0
85°	21.7	22.2	23.2	24.3	28.0	33.8	35.4	36.5	37.6	37.6	34.3
87.5°	11.2	10.1	10.2	9.8	10.6	10.3	12.3	14.0	14.9	13.6	14.3
90°	22.3	18.8	15.2	12.9	10.6	7.1	4.6	2.3	4.6	7.1	10.6
92.5°	149.1	98.6	67.9	50.5	40.6	31.4	21.6	14.5	21.6	31.4	40.6
95°	427.1	252.3	152.5	106.7	76.2	56.4	43.4	39.9	43.4	56.4	76.2
97.5°	468.6	271.6	176.2	126.7	96.6	79.3	69.2	68.1	69.2	79.3	96.6
100°	442.3	268.7	186.5	140.8	112.6	96.2	88.0	86.8	88.0	96.2	112.6
102.5°	419.8	272.5	198.7	156.7	131.4	115.9	108.7	106.5	108.7	115.9	131.4
105°	403.6	282.8	219.4	183.0	160.8	146.6	139.7	136.1	139.7	146.6	160.8
107.5°	402.4	302.1	246.4	212.6	191.7	177.8	171.1	167.5	171.1	177.8	191.7
110°	407.2	318.0	265.2	232.3	212.4	199.4	193.6	190.1	193.6	199.4	212.4

TEST NUMBER: P332326-840

CATALOG NUMBER: S123RDIP-S775D1195U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	416.6	334.0	284.9	253.0	233.0	220.2	214.3	210.8	214.3	220.2	233.0
115°	431.8	360.2	315.6	284.0	264.0	252.3	245.2	240.5	245.2	252.3	264.0
117.5°	451.9	388.1	344.1	314.7	292.4	281.6	275.7	270.3	275.7	281.6	292.4
120°	467.0	406.0	363.8	334.4	312.1	300.3	294.5	290.9	294.5	300.3	312.1
122.5°	481.1	424.7	383.4	352.2	330.8	318.2	312.4	308.8	312.4	318.2	330.8
125°	503.3	451.7	410.6	379.0	356.7	343.8	336.8	334.4	336.8	343.8	356.7
127.5°	521.7	475.1	435.6	403.8	379.2	366.1	357.4	353.9	357.4	366.1	379.2
130°	533.8	489.3	450.5	418.9	394.3	380.1	369.6	366.1	369.6	380.1	394.3
132.5°	545.1	501.5	463.7	432.9	408.3	391.4	379.9	375.5	379.9	391.4	408.3
135°	559.7	519.8	483.4	451.7	427.1	409.5	396.6	391.9	396.6	409.5	427.1
137.5°	570.5	532.4	497.5	468.2	443.7	425.0	412.3	407.4	412.3	425.0	443.7
140°	576.1	540.9	506.9	477.6	454.0	435.3	423.5	417.7	423.5	435.3	454.0
142.5°	581.7	547.4	514.4	487.0	463.4	446.6	433.9	429.0	433.9	446.6	463.4
145°	587.8	556.1	525.6	498.7	478.7	461.1	450.5	447.1	450.5	461.1	478.7
147.5°	591.6	563.2	535.2	512.3	493.0	477.8	467.5	465.3	467.5	477.8	493.0
150°	592.5	567.8	540.9	519.8	503.3	488.1	478.7	477.6	478.7	488.1	503.3
152.5°	594.4	570.7	547.4	527.3	512.7	499.4	490.0	489.8	490.0	499.4	512.7
155°	594.9	576.1	556.1	539.7	526.8	515.1	508.1	508.1	508.1	515.1	526.8
157.5°	596.0	579.2	563.2	550.5	539.5	529.2	523.5	522.6	523.5	529.2	539.5
160°	596.0	582.0	567.8	556.1	548.0	538.6	533.8	533.8	533.8	538.6	548.0
162.5°	595.1	582.9	570.7	560.9	553.6	546.0	542.3	542.3	542.3	546.0	553.6
165°	592.5	584.3	574.9	566.7	562.0	556.1	553.8	555.0	553.8	556.1	562.0
167.5°	590.7	584.1	577.2	572.1	568.9	564.3	563.2	564.6	563.2	564.3	568.9
170°	587.8	583.1	577.2	574.9	572.6	569.1	567.8	570.3	567.8	569.1	572.6
172.5°	586.9	583.1	578.2	576.8	575.4	572.8	572.6	574.0	572.6	572.8	575.4
175°	584.3	582.0	579.7	578.5	578.5	576.1	577.2	578.5	577.2	576.1	578.5
177.5°	582.4	580.6	579.7	579.7	579.7	578.7	579.7	580.6	579.7	578.7	579.7
180°	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7

TEST NUMBER: P332326-840

CATALOG NUMBER: S123RDIP-S775D1195U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1
2.5°	1214.0	1208.4	1204.7	1196.2	1190.6	1184.8	1178.8	1182.7	1182.2	1181.7	1181.7
5°	1173.3	1161.0	1149.9	1135.7	1126.7	1115.6	1107.1	1106.1	1108.2	1100.8	1096.5
7.5°	1132.9	1116.2	1100.4	1084.7	1068.0	1054.7	1046.3	1042.4	1037.0	1032.5	1027.7
10°	1104.5	1084.9	1069.5	1050.1	1032.1	1016.2	1006.1	999.3	995.5	991.9	985.0
12.5°	1075.3	1056.1	1036.6	1014.5	997.3	979.0	971.5	963.7	956.6	952.5	943.1
15°	1032.6	1007.7	987.1	963.8	944.8	926.9	916.3	900.9	898.8	893.5	884.0
17.5°	989.8	962.8	934.3	917.2	895.6	877.0	860.8	855.7	840.5	834.9	826.6
20°	955.9	931.1	909.4	886.7	855.5	838.0	825.4	818.5	806.3	798.9	793.6
22.5°	926.8	901.5	876.4	849.9	824.2	804.6	795.3	784.6	778.0	767.6	761.8
25°	885.0	857.6	827.5	798.9	780.4	765.6	750.7	741.2	731.7	727.0	716.4
27.5°	836.7	807.9	779.7	758.1	735.4	720.7	707.3	698.8	687.4	679.4	673.6
30°	810.0	776.2	751.8	732.3	703.2	689.4	679.4	668.8	660.4	651.9	646.1
32.5°	779.1	748.2	725.2	700.9	678.6	663.7	650.7	641.4	634.1	626.1	620.3
35°	730.6	704.8	681.0	656.6	640.3	624.9	609.7	601.7	594.8	587.4	582.1
37.5°	686.9	662.7	640.1	617.0	596.7	584.2	571.9	565.8	556.5	551.6	546.1
40°	659.8	636.0	611.7	589.6	568.4	558.9	547.8	538.8	530.3	526.6	520.8
42.5°	630.3	606.4	585.9	562.0	544.7	531.8	521.5	511.7	505.3	500.0	496.7
45°	586.3	565.2	545.1	521.3	504.9	493.8	482.2	473.2	467.4	463.7	457.9
47.5°	543.7	522.6	502.2	481.4	465.5	452.9	441.3	435.0	427.3	422.7	418.9
50°	512.8	493.8	472.1	453.1	437.3	424.5	415.1	407.1	400.2	394.5	391.8
52.5°	484.5	464.2	445.5	427.8	411.0	396.7	388.0	379.6	374.5	367.8	364.7
55°	437.8	418.2	402.3	384.9	368.5	356.4	345.8	338.4	333.1	325.7	321.4
57.5°	393.8	376.4	357.4	342.2	325.4	315.1	306.3	296.3	289.8	284.1	279.9
60°	364.3	344.2	327.8	313.6	298.7	285.5	277.6	269.6	262.8	256.9	253.3
62.5°	333.5	315.9	300.3	284.8	271.2	259.7	250.5	243.9	237.8	234.1	230.5
65°	286.0	272.3	256.4	243.8	231.1	222.6	215.2	209.3	205.1	202.5	199.3
67.5°	242.5	229.1	215.3	202.8	194.4	187.9	183.1	178.0	175.9	172.6	170.5
70°	214.1	200.4	188.2	178.7	170.3	165.5	162.3	158.6	156.5	152.3	150.2
72.5°	183.3	173.3	164.5	156.7	150.0	145.6	141.6	137.0	133.7	129.0	126.9
75°	144.3	135.3	128.5	123.2	119.0	113.1	107.3	102.6	101.0	99.4	98.9
77.5°	106.9	101.2	96.2	91.8	86.5	82.3	81.0	80.0	79.6	78.8	78.8
80°	84.0	78.8	75.0	69.8	66.7	66.7	66.7	65.5	66.0	66.0	66.0
82.5°	62.5	57.7	55.6	53.7	53.1	53.5	53.5	53.7	53.4	54.2	53.8
85°	32.2	32.8	33.8	33.3	33.8	33.8	34.9	34.3	34.9	33.8	34.9
87.5°	14.4	16.2	17.3	18.4	19.6	19.8	20.0	20.2	20.9	21.1	21.6
90°	12.9	15.2	18.8	22.3	25.9	29.3	28.2	29.3	30.5	31.7	34.0
92.5°	50.5	67.9	98.6	149.1	198.5	180.5	136.1	98.8	78.4	69.2	63.1
95°	106.7	152.5	252.3	427.1	619.6	695.8	564.3	422.4	286.3	224.1	181.9
97.5°	126.7	176.2	271.6	468.6	789.4	1078.2	1153.6	1052.9	843.3	692.1	551.7
100°	140.8	186.5	268.7	442.3	750.9	1111.2	1342.3	1383.3	1288.3	1151.0	984.4
102.5°	156.7	198.7	272.5	419.8	694.6	1050.2	1351.6	1493.2	1490.1	1410.1	1304.4
105°	183.0	219.4	282.8	403.6	625.4	943.3	1280.1	1525.3	1642.6	1665.0	1634.5
107.5°	212.6	246.4	302.1	402.4	581.3	849.0	1154.8	1432.8	1623.4	1726.2	1768.0
110°	232.3	265.2	318.0	407.2	564.3	795.5	1075.9	1344.6	1560.5	1708.4	1790.5

TEST NUMBER: P332326-840

CATALOG NUMBER: S123RDIP-S775D1195U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	253.0	284.9	334.0	416.6	555.0	759.8	1007.4	1257.3	1477.9	1643.6	1749.2
115°	284.0	315.6	360.2	431.8	551.5	721.5	924.5	1141.7	1345.7	1518.2	1646.2
117.5°	314.7	344.1	388.1	451.9	553.6	699.0	874.5	1057.8	1234.1	1389.0	1518.7
120°	334.4	363.8	406.0	467.0	557.3	688.7	848.3	1013.7	1172.2	1312.9	1431.5
122.5°	352.2	383.4	424.7	481.1	563.9	682.2	826.7	979.0	1122.4	1252.8	1362.9
125°	379.0	410.6	451.7	503.3	573.7	673.5	799.0	932.8	1060.7	1173.3	1267.2
127.5°	403.8	435.6	475.1	521.7	585.0	669.2	774.7	892.4	1006.4	1108.0	1193.5
130°	418.9	450.5	489.3	533.8	592.5	666.4	761.4	867.1	972.7	1067.7	1147.5
132.5°	432.9	463.7	501.5	545.1	598.1	665.5	749.3	843.6	940.8	1029.3	1105.3
135°	451.7	483.4	519.8	559.7	606.6	664.1	733.4	811.9	895.2	971.5	1038.3
137.5°	468.2	497.5	532.4	570.5	612.3	661.5	719.4	783.0	851.3	917.1	975.0
140°	477.6	506.9	540.9	576.1	616.0	660.6	711.0	766.2	826.0	882.3	932.8
142.5°	487.0	514.4	547.4	581.7	618.8	658.7	703.5	750.2	801.6	850.4	894.3
145°	498.7	525.6	556.1	587.8	620.7	655.9	693.5	730.9	769.7	807.3	841.2
147.5°	512.3	535.2	563.2	591.6	620.7	651.5	683.6	715.3	746.0	776.3	800.4
150°	519.8	540.9	567.8	592.5	620.7	647.6	677.0	704.0	730.9	755.6	777.9
152.5°	527.3	547.4	570.7	594.4	617.8	643.0	669.5	693.7	716.9	738.7	757.3
155°	539.7	556.1	576.1	594.9	614.8	634.8	658.2	678.1	696.9	714.6	728.6
157.5°	550.5	563.2	579.2	596.0	610.9	627.5	645.5	661.8	677.5	691.1	702.1
160°	556.1	567.8	582.0	596.0	608.9	621.9	637.1	652.4	665.3	677.0	685.2
162.5°	560.9	570.7	582.9	595.1	605.2	616.2	628.6	641.1	652.2	662.9	670.1
165°	566.7	574.9	584.3	592.5	599.6	607.7	617.1	626.5	633.6	641.8	647.6
167.5°	572.1	577.2	584.1	590.7	593.9	599.4	606.1	613.9	619.2	624.0	628.2
170°	574.9	577.2	583.1	587.8	590.2	593.7	599.6	605.4	608.9	613.6	616.0
172.5°	576.8	578.2	583.1	586.9	587.3	589.0	593.0	597.9	600.5	604.3	605.6
175°	578.5	579.7	582.0	584.3	583.1	583.1	585.5	587.8	589.0	591.4	591.4
177.5°	579.7	579.7	580.6	582.4	580.6	579.7	580.6	581.5	582.4	583.4	583.4
180°	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7

TEST NUMBER: P332326-840

CATALOG NUMBER: S123RDIP-S775D1195U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1
2.5°	1176.7	1176.3	1176.7	1175.0	1176.7	1176.3	1176.7	1181.7	1181.7	1182.2	1182.7
5°	1095.0	1094.4	1092.9	1088.1	1092.9	1094.4	1095.0	1096.5	1100.8	1108.2	1106.1
7.5°	1023.6	1022.9	1018.2	1018.3	1018.2	1022.9	1023.6	1027.7	1032.5	1037.0	1042.4
10°	981.3	981.8	975.5	971.8	975.5	981.8	981.3	985.0	991.9	995.5	999.3
12.5°	940.3	937.9	932.7	928.7	932.7	937.9	940.3	943.1	952.5	956.6	963.7
15°	886.2	880.8	868.2	869.2	868.2	880.8	886.2	884.0	893.5	898.8	900.9
17.5°	822.3	818.5	818.2	810.8	818.2	818.5	822.3	826.6	834.9	840.5	855.7
20°	785.2	782.5	783.6	776.2	783.6	782.5	785.2	793.6	798.9	806.3	818.5
22.5°	756.0	753.4	748.9	746.6	748.9	753.4	756.0	761.8	767.6	778.0	784.6
25°	713.3	709.0	704.8	707.4	704.8	709.0	713.3	716.4	727.0	731.7	741.2
27.5°	670.6	667.3	663.1	662.6	663.1	667.3	670.6	673.6	679.4	687.4	698.8
30°	643.5	640.3	638.1	635.5	638.1	640.3	643.5	646.1	651.9	660.4	668.8
32.5°	615.9	615.3	611.5	611.0	611.5	615.3	615.9	620.3	626.1	634.1	641.4
35°	580.0	576.8	575.7	576.3	575.7	576.8	580.0	582.1	587.4	594.8	601.7
37.5°	545.8	541.6	539.7	537.9	539.7	541.6	545.8	546.1	551.6	556.5	565.8
40°	521.3	517.1	516.0	514.9	516.0	517.1	521.3	520.8	526.6	530.3	538.8
42.5°	493.8	492.1	491.5	489.6	491.5	492.1	493.8	496.7	500.0	505.3	511.7
45°	456.3	455.8	452.6	453.6	452.6	455.8	456.3	457.9	463.7	467.4	473.2
47.5°	416.8	414.4	412.2	413.6	412.2	414.4	416.8	418.9	422.7	427.3	435.0
50°	389.7	388.6	383.8	384.9	383.8	388.6	389.7	391.8	394.5	400.2	407.1
52.5°	362.6	358.6	356.8	356.2	356.8	358.6	362.6	364.7	367.8	374.5	379.6
55°	317.8	313.0	310.8	309.8	310.8	313.0	317.8	321.4	325.7	333.1	338.4
57.5°	273.8	272.5	270.8	272.0	270.8	272.5	273.8	279.9	284.1	289.8	296.3
60°	247.9	247.9	247.9	247.4	247.9	247.9	247.9	253.3	256.9	262.8	269.6
62.5°	228.1	226.8	226.4	227.1	226.4	226.8	228.1	230.5	234.1	237.8	243.9
65°	197.7	197.2	195.1	194.6	195.1	197.2	197.7	199.3	202.5	205.1	209.3
67.5°	169.1	167.1	166.5	165.8	166.5	167.1	169.1	170.5	172.6	175.9	178.0
70°	147.5	146.4	143.3	143.8	143.3	146.4	147.5	150.2	152.3	156.5	158.6
72.5°	124.2	123.2	122.6	121.8	122.6	123.2	124.2	126.9	129.0	133.7	137.0
75°	98.4	97.9	97.3	99.4	97.3	97.9	98.4	98.9	99.4	101.0	102.6
77.5°	78.8	78.8	79.1	78.3	79.1	78.8	78.8	78.8	78.8	79.6	80.0
80°	66.0	66.0	65.5	65.5	65.5	66.0	66.0	66.0	66.0	66.0	65.5
82.5°	53.0	53.4	53.7	52.9	53.7	53.4	53.0	53.8	54.2	53.4	53.7
85°	34.9	34.3	35.4	34.9	35.4	34.3	34.9	34.9	33.8	34.9	34.3
87.5°	22.2	21.6	21.8	22.0	21.8	21.6	22.2	21.6	21.1	20.9	20.2
90°	32.8	34.0	35.2	34.0	35.2	34.0	32.8	34.0	31.7	30.5	29.3
92.5°	61.0	57.5	58.7	56.6	58.7	57.5	61.0	63.1	69.2	78.4	98.8
95°	159.6	149.1	140.8	136.1	140.8	149.1	159.6	181.9	224.1	286.3	422.4
97.5°	465.1	412.3	380.6	370.5	380.6	412.3	465.1	551.7	692.1	843.3	1052.9
100°	865.9	780.2	734.5	735.7	734.5	780.2	865.9	984.4	1151.0	1288.3	1383.3
102.5°	1212.2	1144.5	1106.2	1079.2	1106.2	1144.5	1212.2	1304.4	1410.1	1490.1	1493.2
105°	1580.4	1535.9	1498.3	1492.5	1498.3	1535.9	1580.4	1634.5	1665.0	1642.6	1525.3
107.5°	1768.9	1753.8	1741.2	1730.4	1741.2	1753.8	1768.9	1768.0	1726.2	1623.4	1432.8
110°	1823.3	1832.7	1830.4	1828.1	1830.4	1832.7	1823.3	1790.5	1708.4	1560.5	1344.6

TEST NUMBER: P332326-840

CATALOG NUMBER: S123RDIP-S775D1195U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1809.3	1838.4	1847.2	1847.8	1847.2	1838.4	1809.3	1749.2	1643.6	1477.9	1257.3
115°	1734.1	1785.7	1809.3	1815.1	1809.3	1785.7	1734.1	1646.2	1518.2	1345.7	1141.7
117.5°	1610.5	1669.6	1703.4	1711.4	1703.4	1669.6	1610.5	1518.7	1389.0	1234.1	1057.8
120°	1524.1	1589.8	1618.0	1625.1	1618.0	1589.8	1524.1	1431.5	1312.9	1172.2	1013.7
122.5°	1445.3	1504.4	1535.4	1544.3	1535.4	1504.4	1445.3	1362.9	1252.8	1122.4	979.0
125°	1342.3	1393.9	1423.2	1431.5	1423.2	1393.9	1342.3	1267.2	1173.3	1060.7	932.8
127.5°	1260.4	1304.4	1331.0	1338.5	1331.0	1304.4	1260.4	1193.5	1108.0	1006.4	892.4
130°	1209.7	1251.9	1276.6	1286.0	1276.6	1251.9	1209.7	1147.5	1067.7	972.7	867.1
132.5°	1163.7	1205.9	1227.8	1234.4	1227.8	1205.9	1163.7	1105.3	1029.3	940.8	843.6
135°	1095.9	1131.0	1152.2	1160.4	1152.2	1131.0	1095.9	1038.3	971.5	895.2	811.9
137.5°	1023.4	1059.0	1076.8	1082.3	1076.8	1059.0	1023.4	975.0	917.1	851.3	783.0
140°	977.3	1010.3	1029.0	1027.8	1029.0	1010.3	977.3	932.8	882.3	826.0	766.2
142.5°	932.3	961.4	978.3	977.1	978.3	961.4	932.3	894.3	850.4	801.6	750.2
145°	870.6	895.2	904.6	907.0	904.6	895.2	870.6	841.2	807.3	769.7	730.9
147.5°	822.7	839.4	848.3	849.2	848.3	839.4	822.7	800.4	776.3	746.0	715.3
150°	795.5	808.4	815.5	815.5	815.5	808.4	795.5	777.9	755.6	730.9	704.0
152.5°	771.1	783.0	787.3	787.3	787.3	783.0	771.1	757.3	738.7	716.9	693.7
155°	739.2	748.6	750.9	752.0	750.9	748.6	739.2	728.6	714.6	696.9	678.1
157.5°	711.2	718.3	720.1	719.9	720.1	718.3	711.2	702.1	691.1	677.5	661.8
160°	693.5	700.4	700.4	699.3	700.4	700.4	693.5	685.2	677.0	665.3	652.4
162.5°	675.6	681.7	681.7	680.5	681.7	681.7	675.6	670.1	662.9	652.2	641.1
165°	652.4	657.0	655.9	655.9	655.9	657.0	652.4	647.6	641.8	633.6	626.5
167.5°	630.3	633.6	632.4	632.4	632.4	633.6	630.3	628.2	624.0	619.2	613.9
170°	617.1	619.6	618.3	618.3	618.3	619.6	617.1	616.0	613.6	608.9	605.4
172.5°	605.9	608.2	606.1	605.2	606.1	608.2	605.9	605.6	604.3	600.5	597.9
175°	591.4	592.5	591.4	590.2	591.4	592.5	591.4	591.4	591.4	589.0	587.8
177.5°	582.4	583.4	581.5	581.5	581.5	583.4	582.4	583.4	583.4	582.4	581.5
180°	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7

TEST NUMBER: P332326-840

CATALOG NUMBER: S123RDIP-S775D1195U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1
2.5°	1178.8	1184.8	1190.6	1196.2	1204.7	1208.4	1214.0	1216.1	1222.3	1231.7	1239.3
5°	1107.1	1115.6	1126.7	1135.7	1149.9	1161.0	1173.3	1184.9	1198.6	1218.2	1235.6
7.5°	1046.3	1054.7	1068.0	1084.7	1100.4	1116.2	1132.9	1148.7	1168.3	1196.4	1224.2
10°	1006.1	1016.2	1032.1	1050.1	1069.5	1084.9	1104.5	1124.6	1148.9	1181.1	1214.5
12.5°	971.5	979.0	997.3	1014.5	1036.6	1056.1	1075.3	1098.7	1126.5	1160.8	1200.9
15°	916.3	926.9	944.8	963.8	987.1	1007.7	1032.6	1061.2	1088.1	1130.4	1179.0
17.5°	860.8	877.0	895.6	917.2	934.3	962.8	989.8	1019.1	1052.3	1097.1	1150.4
20°	825.4	838.0	855.5	886.7	909.4	931.1	955.9	992.4	1023.1	1073.8	1129.3
22.5°	795.3	804.6	824.2	849.9	876.4	901.5	926.8	961.5	999.4	1047.6	1107.7
25°	750.7	765.6	780.4	798.9	827.5	857.6	885.0	914.6	954.8	1006.1	1071.2
27.5°	707.3	720.7	735.4	758.1	779.7	807.9	836.7	870.6	913.7	968.0	1034.0
30°	679.4	689.4	703.2	732.3	751.8	776.2	810.0	840.1	880.3	938.0	1007.7
32.5°	650.7	663.7	678.6	700.9	725.2	748.2	779.1	811.8	852.8	909.6	981.1
35°	609.7	624.9	640.3	656.6	681.0	704.8	730.6	766.6	808.4	863.4	933.7
37.5°	571.9	584.2	596.7	617.0	640.1	662.7	686.9	722.4	761.6	821.0	885.4
40°	547.8	558.9	568.4	589.6	611.7	636.0	659.8	691.1	733.4	788.8	851.2
42.5°	521.5	531.8	544.7	562.0	585.9	606.4	630.3	659.7	699.5	755.9	810.6
45°	482.2	493.8	504.9	521.3	545.1	565.2	586.3	614.4	655.1	701.7	750.2
47.5°	441.3	452.9	465.5	481.4	502.2	522.6	543.7	568.6	605.7	651.4	684.2
50°	415.1	424.5	437.3	453.1	472.1	493.8	512.8	539.8	575.2	611.2	639.7
52.5°	388.0	396.7	411.0	427.8	445.5	464.2	484.5	507.7	539.7	573.5	596.2
55°	345.8	356.4	368.5	384.9	402.3	418.2	437.8	461.6	487.0	512.3	527.7
57.5°	306.3	315.1	325.4	342.2	357.4	376.4	393.8	412.4	435.9	455.0	465.0
60°	277.6	285.5	298.7	313.6	327.8	344.2	364.3	382.8	400.8	416.1	424.0
62.5°	250.5	259.7	271.2	284.8	300.3	315.9	333.5	348.9	364.8	378.0	383.4
65°	215.2	222.6	231.1	243.8	256.4	272.3	286.0	301.8	313.6	320.9	325.7
67.5°	183.1	187.9	194.4	202.8	215.3	229.1	242.5	254.9	264.6	269.6	273.9
70°	162.3	165.5	170.3	178.7	188.2	200.4	214.1	223.1	231.6	235.8	240.0
72.5°	141.6	145.6	150.0	156.7	164.5	173.3	183.3	194.4	199.0	204.1	206.6
75°	107.3	113.1	119.0	123.2	128.5	135.3	144.3	151.2	153.9	158.0	158.6
77.5°	81.0	82.3	86.5	91.8	96.2	101.2	106.9	113.0	114.3	116.5	118.0
80°	66.7	66.7	66.7	69.8	75.0	78.8	84.0	87.3	89.4	89.9	90.4
82.5°	53.5	53.5	53.1	53.7	55.6	57.7	62.5	66.0	67.8	67.5	66.3
85°	34.9	33.8	33.8	33.3	33.8	32.8	32.2	34.3	37.6	37.6	36.5
87.5°	20.0	19.8	19.6	18.4	17.3	16.2	14.4	14.3	13.6	14.9	14.0
90°	28.2	29.3	25.9	22.3	18.8	15.2	12.9	10.6	7.1	4.6	2.3
92.5°	136.1	180.5	198.5	149.1	98.6	67.9	50.5	40.6	31.4	21.6	14.5
95°	564.3	695.8	619.6	427.1	252.3	152.5	106.7	76.2	56.4	43.4	39.9
97.5°	1153.6	1078.2	789.4	468.6	271.6	176.2	126.7	96.6	79.3	69.2	68.1
100°	1342.3	1111.2	750.9	442.3	268.7	186.5	140.8	112.6	96.2	88.0	86.8
102.5°	1351.6	1050.2	694.6	419.8	272.5	198.7	156.7	131.4	115.9	108.7	106.5
105°	1280.1	943.3	625.4	403.6	282.8	219.4	183.0	160.8	146.6	139.7	136.1
107.5°	1154.8	849.0	581.3	402.4	302.1	246.4	212.6	191.7	177.8	171.1	167.5
110°	1075.9	795.5	564.3	407.2	318.0	265.2	232.3	212.4	199.4	193.6	190.1

TEST NUMBER: P332326-840

CATALOG NUMBER: S123RDIP-S775D1195U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	1007.4	759.8	555.0	416.6	334.0	284.9	253.0	233.0	220.2	214.3	210.8
115°	924.5	721.5	551.5	431.8	360.2	315.6	284.0	264.0	252.3	245.2	240.5
117.5°	874.5	699.0	553.6	451.9	388.1	344.1	314.7	292.4	281.6	275.7	270.3
120°	848.3	688.7	557.3	467.0	406.0	363.8	334.4	312.1	300.3	294.5	290.9
122.5°	826.7	682.2	563.9	481.1	424.7	383.4	352.2	330.8	318.2	312.4	308.8
125°	799.0	673.5	573.7	503.3	451.7	410.6	379.0	356.7	343.8	336.8	334.4
127.5°	774.7	669.2	585.0	521.7	475.1	435.6	403.8	379.2	366.1	357.4	353.9
130°	761.4	666.4	592.5	533.8	489.3	450.5	418.9	394.3	380.1	369.6	366.1
132.5°	749.3	665.5	598.1	545.1	501.5	463.7	432.9	408.3	391.4	379.9	375.5
135°	733.4	664.1	606.6	559.7	519.8	483.4	451.7	427.1	409.5	396.6	391.9
137.5°	719.4	661.5	612.3	570.5	532.4	497.5	468.2	443.7	425.0	412.3	407.4
140°	711.0	660.6	616.0	576.1	540.9	506.9	477.6	454.0	435.3	423.5	417.7
142.5°	703.5	658.7	618.8	581.7	547.4	514.4	487.0	463.4	446.6	433.9	429.0
145°	693.5	655.9	620.7	587.8	556.1	525.6	498.7	478.7	461.1	450.5	447.1
147.5°	683.6	651.5	620.7	591.6	563.2	535.2	512.3	493.0	477.8	467.5	465.3
150°	677.0	647.6	620.7	592.5	567.8	540.9	519.8	503.3	488.1	478.7	477.6
152.5°	669.5	643.0	617.8	594.4	570.7	547.4	527.3	512.7	499.4	490.0	489.8
155°	658.2	634.8	614.8	594.9	576.1	556.1	539.7	526.8	515.1	508.1	508.1
157.5°	645.5	627.5	610.9	596.0	579.2	563.2	550.5	539.5	529.2	523.5	522.6
160°	637.1	621.9	608.9	596.0	582.0	567.8	556.1	548.0	538.6	533.8	533.8
162.5°	628.6	616.2	605.2	595.1	582.9	570.7	560.9	553.6	546.0	542.3	542.3
165°	617.1	607.7	599.6	592.5	584.3	574.9	566.7	562.0	556.1	553.8	555.0
167.5°	606.1	599.4	593.9	590.7	584.1	577.2	572.1	568.9	564.3	563.2	564.6
170°	599.6	593.7	590.2	587.8	583.1	577.2	574.9	572.6	569.1	567.8	570.3
172.5°	593.0	589.0	587.3	586.9	583.1	578.2	576.8	575.4	572.8	572.6	574.0
175°	585.5	583.1	583.1	584.3	582.0	579.7	578.5	578.5	576.1	577.2	578.5
177.5°	580.6	579.7	580.6	582.4	580.6	579.7	579.7	579.7	578.7	579.7	580.6
180°	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7

TEST NUMBER: P332326-840

CATALOG NUMBER: S123RDIP-S775D1195U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1
2.5°	1241.8	1246.5	1252.4	1261.3	1268.1	1273.9	1275.3	1277.0	1281.2	1288.4	1293.8
5°	1249.9	1262.0	1281.6	1300.6	1321.3	1338.2	1354.0	1365.1	1375.7	1398.0	1415.9
7.5°	1247.4	1274.4	1305.0	1339.3	1373.8	1407.3	1438.5	1466.2	1493.9	1526.3	1563.2
10°	1245.7	1277.4	1318.6	1362.5	1410.6	1457.6	1503.2	1538.5	1579.8	1616.8	1663.9
12.5°	1237.6	1283.3	1332.6	1388.8	1447.8	1502.1	1562.0	1610.9	1658.1	1711.5	1766.3
15°	1227.2	1282.6	1345.0	1419.6	1509.4	1575.1	1636.4	1721.5	1779.7	1837.9	1916.0
17.5°	1208.0	1275.8	1353.7	1450.6	1525.6	1613.7	1706.0	1773.2	1851.6	1933.5	2004.4
20°	1192.8	1271.5	1358.8	1454.0	1549.6	1645.4	1734.7	1815.0	1896.0	1990.6	2048.8
22.5°	1177.6	1255.5	1346.2	1447.2	1550.0	1650.8	1752.0	1846.3	1937.4	2033.0	2107.2
25°	1145.2	1237.7	1336.1	1439.2	1540.7	1651.7	1772.2	1877.4	1990.0	2088.4	2158.8
27.5°	1112.4	1197.2	1295.2	1399.7	1512.6	1643.8	1785.5	1905.2	2018.0	2088.4	2110.5
30°	1082.8	1172.7	1262.5	1368.9	1491.0	1637.4	1788.1	1925.0	2017.6	2048.2	2025.5
32.5°	1052.8	1134.2	1223.2	1332.0	1461.8	1621.7	1791.5	1913.2	1968.9	1945.5	1852.9
35°	999.8	1073.3	1159.4	1268.4	1417.4	1613.2	1777.6	1860.0	1846.2	1714.0	1539.6
37.5°	943.1	1003.0	1082.8	1196.7	1371.6	1578.7	1717.5	1729.6	1610.6	1407.8	1206.2
40°	898.3	952.2	1034.2	1153.2	1336.1	1544.9	1657.0	1607.8	1423.3	1197.5	1029.5
42.5°	854.7	900.2	979.2	1107.4	1302.2	1498.8	1566.9	1459.8	1246.9	1033.4	880.5
45°	780.9	823.7	903.0	1034.7	1232.9	1410.6	1401.6	1215.5	1002.5	830.6	703.7
47.5°	710.9	748.3	822.7	957.2	1151.7	1278.4	1194.4	996.3	815.6	677.7	587.2
50°	661.5	698.4	772.4	905.1	1086.5	1179.0	1059.0	868.2	702.7	588.4	516.5
52.5°	614.1	650.3	717.9	847.2	1007.8	1063.2	934.2	757.3	619.4	520.8	459.0
55°	547.8	575.2	636.0	759.7	879.8	892.5	761.8	613.8	500.2	431.4	389.1
57.5°	480.2	503.8	563.9	662.5	746.7	740.1	616.3	488.2	411.6	360.6	329.9
60°	436.2	459.5	512.3	596.9	660.4	638.1	524.5	421.4	355.8	318.3	294.0
62.5°	395.2	413.3	462.8	524.6	570.3	545.1	448.4	363.0	311.0	279.3	260.1
65°	335.8	350.5	390.2	422.4	447.8	423.5	343.2	283.9	246.4	224.2	211.0
67.5°	279.2	288.7	313.8	325.4	343.3	316.6	258.0	218.3	197.0	178.2	169.1
70°	243.8	250.6	263.9	273.4	278.1	250.6	207.2	178.1	160.2	146.9	141.2
72.5°	208.2	214.2	216.9	224.7	222.3	196.5	166.6	143.5	130.6	121.6	114.1
75°	159.2	161.8	159.2	155.9	149.1	131.1	110.5	98.9	89.4	85.1	82.5
77.5°	116.0	115.1	111.6	106.5	94.8	83.5	72.4	68.6	64.4	62.2	61.2
80°	89.4	87.3	84.0	76.1	66.0	58.2	55.5	52.9	51.3	48.7	48.1
82.5°	66.6	65.2	60.0	53.3	46.3	42.5	40.3	39.4	37.8	36.4	36.3
85°	35.4	33.8	28.0	24.3	23.2	22.2	21.7	21.7	19.6	19.0	19.0
87.5°	12.3	10.3	10.6	9.8	10.2	10.1	11.2	11.1	11.4	11.5	10.9
90°	4.6	7.1	10.6	12.9	15.2	18.8	22.3	25.9	29.3	28.2	29.3
92.5°	21.6	31.4	40.6	50.5	67.9	98.6	149.1	198.5	180.5	136.1	98.8
95°	43.4	56.4	76.2	106.7	152.5	252.3	427.1	619.6	695.8	564.3	422.4
97.5°	69.2	79.3	96.6	126.7	176.2	271.6	468.6	789.4	1078.2	1153.6	1052.9
100°	88.0	96.2	112.6	140.8	186.5	268.7	442.3	750.9	1111.2	1342.3	1383.3
102.5°	108.7	115.9	131.4	156.7	198.7	272.5	419.8	694.6	1050.2	1351.6	1493.2
105°	139.7	146.6	160.8	183.0	219.4	282.8	403.6	625.4	943.3	1280.1	1525.3
107.5°	171.1	177.8	191.7	212.6	246.4	302.1	402.4	581.3	849.0	1154.8	1432.8
110°	193.6	199.4	212.4	232.3	265.2	318.0	407.2	564.3	795.5	1075.9	1344.6

TEST NUMBER: P332326-840

CATALOG NUMBER: S123RDIP-S775D1195U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	214.3	220.2	233.0	253.0	284.9	334.0	416.6	555.0	759.8	1007.4	1257.3
115°	245.2	252.3	264.0	284.0	315.6	360.2	431.8	551.5	721.5	924.5	1141.7
117.5°	275.7	281.6	292.4	314.7	344.1	388.1	451.9	553.6	699.0	874.5	1057.8
120°	294.5	300.3	312.1	334.4	363.8	406.0	467.0	557.3	688.7	848.3	1013.7
122.5°	312.4	318.2	330.8	352.2	383.4	424.7	481.1	563.9	682.2	826.7	979.0
125°	336.8	343.8	356.7	379.0	410.6	451.7	503.3	573.7	673.5	799.0	932.8
127.5°	357.4	366.1	379.2	403.8	435.6	475.1	521.7	585.0	669.2	774.7	892.4
130°	369.6	380.1	394.3	418.9	450.5	489.3	533.8	592.5	666.4	761.4	867.1
132.5°	379.9	391.4	408.3	432.9	463.7	501.5	545.1	598.1	665.5	749.3	843.6
135°	396.6	409.5	427.1	451.7	483.4	519.8	559.7	606.6	664.1	733.4	811.9
137.5°	412.3	425.0	443.7	468.2	497.5	532.4	570.5	612.3	661.5	719.4	783.0
140°	423.5	435.3	454.0	477.6	506.9	540.9	576.1	616.0	660.6	711.0	766.2
142.5°	433.9	446.6	463.4	487.0	514.4	547.4	581.7	618.8	658.7	703.5	750.2
145°	450.5	461.1	478.7	498.7	525.6	556.1	587.8	620.7	655.9	693.5	730.9
147.5°	467.5	477.8	493.0	512.3	535.2	563.2	591.6	620.7	651.5	683.6	715.3
150°	478.7	488.1	503.3	519.8	540.9	567.8	592.5	620.7	647.6	677.0	704.0
152.5°	490.0	499.4	512.7	527.3	547.4	570.7	594.4	617.8	643.0	669.5	693.7
155°	508.1	515.1	526.8	539.7	556.1	576.1	594.9	614.8	634.8	658.2	678.1
157.5°	523.5	529.2	539.5	550.5	563.2	579.2	596.0	610.9	627.5	645.5	661.8
160°	533.8	538.6	548.0	556.1	567.8	582.0	596.0	608.9	621.9	637.1	652.4
162.5°	542.3	546.0	553.6	560.9	570.7	582.9	595.1	605.2	616.2	628.6	641.1
165°	553.8	556.1	562.0	566.7	574.9	584.3	592.5	599.6	607.7	617.1	626.5
167.5°	563.2	564.3	568.9	572.1	577.2	584.1	590.7	593.9	599.4	606.1	613.9
170°	567.8	569.1	572.6	574.9	577.2	583.1	587.8	590.2	593.7	599.6	605.4
172.5°	572.6	572.8	575.4	576.8	578.2	583.1	586.9	587.3	589.0	593.0	597.9
175°	577.2	576.1	578.5	578.5	579.7	582.0	584.3	583.1	583.1	585.5	587.8
177.5°	579.7	578.7	579.7	579.7	579.7	580.6	582.4	580.6	579.7	580.6	581.5
180°	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7

TEST NUMBER: P332326-840

CATALOG NUMBER: S123RDIP-S775D1195U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1
2.5°	1302.7	1302.7	1304.4	1310.8	1311.6	1317.2	1315.5
5°	1431.8	1441.8	1445.5	1461.4	1470.9	1475.1	1466.6
7.5°	1589.5	1617.9	1631.3	1647.9	1662.6	1667.1	1655.5
10°	1704.6	1734.1	1759.1	1774.3	1788.7	1798.2	1810.3
12.5°	1815.8	1852.2	1875.8	1897.4	1912.2	1924.2	1926.2
15°	1936.7	1991.7	2033.5	2064.1	2079.4	2087.4	2084.2
17.5°	2058.6	2109.6	2139.3	2170.6	2191.8	2192.9	2193.5
20°	2127.6	2177.3	2211.6	2234.8	2258.7	2257.7	2262.9
22.5°	2173.6	2212.8	2239.1	2256.0	2264.2	2260.2	2261.2
25°	2195.2	2206.9	2202.1	2175.1	2168.3	2143.4	2147.7
27.5°	2084.0	2029.0	1972.1	1899.0	1841.2	1795.1	1797.5
30°	1933.0	1835.7	1724.6	1631.6	1548.1	1524.8	1475.1
32.5°	1721.9	1576.0	1445.9	1359.2	1287.5	1268.1	1224.8
35°	1364.1	1222.3	1088.6	1008.2	976.5	932.1	931.6
37.5°	1060.3	935.5	864.7	804.5	772.8	746.0	743.4
40°	891.9	794.7	741.2	697.9	666.7	646.6	641.9
42.5°	774.4	695.7	645.7	618.8	594.8	584.4	576.7
45°	632.4	579.5	544.6	520.3	509.2	501.2	497.0
47.5°	529.0	493.5	469.7	453.5	444.5	436.2	438.4
50°	472.7	443.6	426.2	410.8	403.9	398.1	398.7
52.5°	427.4	401.3	387.2	376.2	367.6	363.5	361.4
55°	362.7	346.3	332.0	324.1	319.3	313.6	311.9
57.5°	309.4	296.7	285.1	276.1	274.9	269.3	270.0
60°	273.9	263.3	253.8	249.0	245.3	240.5	242.2
62.5°	244.7	235.8	227.1	223.2	219.5	216.0	216.8
65°	200.4	191.9	186.6	184.5	182.9	181.4	179.8
67.5°	159.7	154.5	151.2	146.6	143.4	142.9	141.3
70°	134.3	127.4	121.6	115.8	114.2	113.7	114.2
72.5°	107.7	103.3	101.7	98.9	98.6	97.1	98.2
75°	80.9	79.3	78.3	76.1	76.1	76.1	76.1
77.5°	59.7	58.7	58.1	57.7	57.1	56.4	56.2
80°	46.6	45.9	44.9	44.9	44.4	44.9	44.4
82.5°	35.1	35.0	33.9	33.9	33.4	33.1	33.4
85°	18.0	17.5	18.5	17.5	18.0	17.0	18.0
87.5°	11.2	11.4	11.4	11.2	11.0	12.1	11.0
90°	30.5	31.7	34.0	32.8	34.0	35.2	34.0
92.5°	78.4	69.2	63.1	61.0	57.5	58.7	56.6
95°	286.3	224.1	181.9	159.6	149.1	140.8	136.1
97.5°	843.3	692.1	551.7	465.1	412.3	380.6	370.5
100°	1288.3	1151.0	984.4	865.9	780.2	734.5	735.7
102.5°	1490.1	1410.1	1304.4	1212.2	1144.5	1106.2	1079.2
105°	1642.6	1665.0	1634.5	1580.4	1535.9	1498.3	1492.5
107.5°	1623.4	1726.2	1768.0	1768.9	1753.8	1741.2	1730.4
110°	1560.5	1708.4	1790.5	1823.3	1832.7	1830.4	1828.1

TEST NUMBER: P332326-840

CATALOG NUMBER: S123RDIP-S775D1195U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1477.9	1643.6	1749.2	1809.3	1838.4	1847.2	1847.8
115°	1345.7	1518.2	1646.2	1734.1	1785.7	1809.3	1815.1
117.5°	1234.1	1389.0	1518.7	1610.5	1669.6	1703.4	1711.4
120°	1172.2	1312.9	1431.5	1524.1	1589.8	1618.0	1625.1
122.5°	1122.4	1252.8	1362.9	1445.3	1504.4	1535.4	1544.3
125°	1060.7	1173.3	1267.2	1342.3	1393.9	1423.2	1431.5
127.5°	1006.4	1108.0	1193.5	1260.4	1304.4	1331.0	1338.5
130°	972.7	1067.7	1147.5	1209.7	1251.9	1276.6	1286.0
132.5°	940.8	1029.3	1105.3	1163.7	1205.9	1227.8	1234.4
135°	895.2	971.5	1038.3	1095.9	1131.0	1152.2	1160.4
137.5°	851.3	917.1	975.0	1023.4	1059.0	1076.8	1082.3
140°	826.0	882.3	932.8	977.3	1010.3	1029.0	1027.8
142.5°	801.6	850.4	894.3	932.3	961.4	978.3	977.1
145°	769.7	807.3	841.2	870.6	895.2	904.6	907.0
147.5°	746.0	776.3	800.4	822.7	839.4	848.3	849.2
150°	730.9	755.6	777.9	795.5	808.4	815.5	815.5
152.5°	716.9	738.7	757.3	771.1	783.0	787.3	787.3
155°	696.9	714.6	728.6	739.2	748.6	750.9	752.0
157.5°	677.5	691.1	702.1	711.2	718.3	720.1	719.9
160°	665.3	677.0	685.2	693.5	700.4	700.4	699.3
162.5°	652.2	662.9	670.1	675.6	681.7	681.7	680.5
165°	633.6	641.8	647.6	652.4	657.0	655.9	655.9
167.5°	619.2	624.0	628.2	630.3	633.6	632.4	632.4
170°	608.9	613.6	616.0	617.1	619.6	618.3	618.3
172.5°	600.5	604.3	605.6	605.9	608.2	606.1	605.2
175°	589.0	591.4	591.4	591.4	592.5	591.4	590.2
177.5°	582.4	583.4	583.4	582.4	583.4	581.5	581.5
180°	579.7	579.7	579.7	579.7	579.7	579.7	579.7

(END OF REPORT)