

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331484-927

Luminaire Tested: **S122DIW-S290D1240U927-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331484-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S290D1240U927-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1240 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4441.4 lumens
Efficiency: N/A
Efficacy: 95.3 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 46.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331484-927

CATALOG NUMBER: S122DIW-S290D1240U927-4F0-1E-UDD-A1

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - · - · 90°-270° - · - · 135°-315°



TEST NUMBER: P331484-927

CATALOG NUMBER: S122DIW-S290D1240U927-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	69	69	69	49	49	49	32	32	32	23
1	92	88	84	81	82	78	75	73	60	58	56	44	42	41	28	28	27	20
2	84	77	71	66	74	69	64	60	53	50	47	38	36	35	25	24	23	17
3	77	68	61	55	68	61	55	50	47	43	40	34	32	30	22	21	20	15
4	70	60	53	47	62	54	47	43	42	37	34	31	28	25	20	19	17	13
5	64	53	46	40	57	48	41	36	37	33	29	27	24	22	18	17	15	11
6	59	48	40	35	52	43	36	32	34	29	25	25	22	19	17	15	13	10
7	55	43	36	30	48	39	32	28	30	26	22	23	19	17	15	13	12	9
8	51	39	32	27	45	35	29	24	28	23	20	21	17	15	14	12	11	8
9	47	35	28	24	42	32	26	22	25	21	18	19	16	14	13	11	10	7
10	44	32	26	21	39	29	23	19	23	19	16	17	14	12	12	10	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	7561	7561	7561	7561
5°	8475	7609	6744	7609
10°	9712	7547	5835	7547
15°	10745	7408	5157	7408
20°	10581	7261	4699	7261
25°	9540	7062	4411	7062
30°	7884	6747	4200	6747
35°	5746	6416	4050	6416
40°	4591	6028	3967	6028
45°	4010	5576	3854	5576
50°	3770	5139	3778	5139
55°	3474	4695	3676	4695
60°	3184	4224	3523	4224
65°	2904	3801	3370	3801
70°	2634	3389	3144	3389
75°	2339	2932	2782	2932
80°	2008	2427	2241	2427
85°	1797	1797	1334	1797



TEST NUMBER: P331484-927

CATALOG NUMBER: S122DIW-S290D1240U927-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.6	1.0
10°-20°	129.6	2.9
20°-30°	188.1	4.2
30°-40°	198.5	4.5
40°-50°	175.8	4.0
50°-60°	140.3	3.2
60°-70°	95.4	2.1
70°-80°	48.9	1.1
80°-90°	16.6	0.4
90°-100°	77.1	1.7
100°-110°	239.6	5.4
110°-120°	409.5	9.2
120°-130°	538.5	12.1
130°-140°	604.4	13.6
140°-150°	592.6	13.3
150°-160°	497.0	11.2
160°-170°	329.7	7.4
170°-180°	115.2	2.6
0°-30°	362.4	8.2
0°-40°	560.9	12.6
0°-60°	877.0	19.7
0°-90°	1037.9	23.4
90°-120°	726.2	16.3
90°-150°	2461.6	55.4
90°-180°	3404.0	76.6
0°-180°	4441.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	468	468	468	468	468	
5°	523	470	416	470	523	52
15°	643	443	308	443	643	177
25°	536	396	248	396	536	242
35°	292	326	206	326	292	190
45°	176	244	169	244	176	138
55°	123	167	131	167	123	111
65°	76	100	88	100	76	76
75°	38	47	45	47	38	40
85°	10	10	7	10	10	12
90°	35	1	35	1	35	16
95°	64	53	64	53	64	71
105°	228	221	228	221	228	240
115°	411	411	411	411	411	406
125°	600	598	600	598	600	535
135°	783	774	783	774	783	602
145°	949	939	949	939	949	593
155°	1082	1073	1082	1073	1082	498
165°	1169	1168	1169	1168	1169	330
175°	1211	1215	1211	1215	1211	115
180°	1217	1217	1217	1217	1217	



TEST NUMBER: P331484-927

CATALOG NUMBER: S122DIW-S290D1240U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3
2.5°	489.8	490.0	490.3	488.0	487.7	487.7	485.7	483.9	481.9	479.2	479.5
5°	522.9	524.9	525.6	523.5	520.2	519.9	516.8	511.8	507.1	503.4	500.7
7.5°	562.4	563.2	561.5	558.6	556.3	551.9	546.2	540.7	532.8	525.7	520.4
10°	592.4	593.5	590.4	586.3	582.9	577.8	569.6	561.1	550.9	541.0	533.1
12.5°	615.1	617.8	613.9	613.4	607.5	600.6	590.7	586.5	572.0	558.3	549.7
15°	642.8	642.6	643.0	639.5	635.3	634.1	623.8	612.4	592.1	583.9	569.9
17.5°	634.8	637.5	638.8	638.7	638.7	637.9	634.6	627.5	617.3	604.1	588.0
20°	615.8	619.4	620.0	624.1	626.5	629.5	630.7	628.8	622.5	611.5	597.5
22.5°	586.5	587.5	589.1	595.6	600.6	608.3	612.3	619.0	616.6	611.2	599.4
25°	535.5	533.8	540.0	543.3	555.0	567.2	576.1	585.7	594.4	599.6	596.2
27.5°	474.4	471.7	481.2	489.8	499.2	512.5	526.2	542.5	556.0	572.9	578.7
30°	422.9	424.5	433.5	442.7	457.1	475.8	491.3	509.1	528.4	547.2	560.4
32.5°	367.3	373.5	379.2	393.3	406.0	426.8	449.6	471.8	495.8	517.3	537.7
35°	291.5	298.7	306.7	316.9	334.7	355.4	377.6	407.6	440.4	469.7	493.8
37.5°	245.4	244.2	248.7	256.2	270.6	287.3	312.8	342.5	381.0	415.5	449.6
40°	217.8	217.1	220.2	227.1	238.1	250.3	272.7	298.7	334.5	376.7	417.2
42.5°	198.8	199.2	201.0	205.8	213.3	223.4	240.1	262.3	295.1	334.8	378.3
45°	175.6	176.9	178.9	181.3	185.5	193.8	203.2	219.0	244.9	278.1	320.8
47.5°	159.0	159.1	161.1	163.1	165.6	170.3	178.0	187.9	206.2	233.1	270.0
50°	150.1	148.9	150.3	151.9	154.6	157.8	162.9	172.2	184.4	206.2	237.0
52.5°	139.1	139.2	140.5	141.1	143.5	146.7	151.3	157.8	168.9	185.9	211.2
55°	123.4	124.4	125.1	126.1	128.3	130.6	134.3	138.6	147.2	159.9	178.7
57.5°	108.7	109.0	109.7	111.8	113.1	115.3	118.7	122.6	128.3	137.7	151.8
60°	98.6	98.6	100.1	100.9	102.7	104.9	107.6	111.4	116.5	124.1	135.5
62.5°	89.4	89.3	89.8	91.3	92.7	94.7	97.4	100.6	105.4	112.3	121.5
65°	76.0	75.6	76.7	77.0	78.4	80.4	82.6	86.0	89.8	94.8	103.1
67.5°	63.0	63.5	64.0	64.6	65.4	67.6	69.0	71.4	74.6	78.8	84.4
70°	55.8	55.8	55.8	56.3	57.4	58.5	59.9	61.9	65.0	68.5	73.6
72.5°	47.7	48.3	48.9	48.6	49.9	50.5	52.3	53.4	56.3	58.6	63.1
75°	37.5	37.5	37.5	38.3	38.9	39.4	40.5	41.6	43.0	45.9	48.2
77.5°	28.0	27.9	28.0	28.3	28.8	29.5	29.8	30.7	32.1	33.4	35.4
80°	21.6	21.9	22.1	22.5	22.5	22.8	23.1	24.3	25.2	26.1	27.3
82.5°	16.7	16.8	16.8	16.9	17.0	17.3	17.7	18.1	18.5	19.2	20.1
85°	9.7	9.5	9.5	9.9	9.7	9.7	10.1	10.5	10.5	10.6	11.2
87.5°	10.7	10.7	10.8	10.6	10.5	10.7	10.8	10.8	11.0	11.2	10.4
90°	34.9	34.7	34.5	34.2	34.0	34.1	34.6	35.0	35.5	36.0	30.9
92.5°	33.3	33.3	33.2	33.1	33.1	33.0	33.0	32.9	32.7	32.6	31.4
95°	63.7	64.2	64.6	65.0	65.5	65.8	65.8	65.8	65.8	65.8	65.3
97.5°	110.4	110.4	110.4	110.4	110.5	110.5	110.5	110.5	110.5	110.5	109.6
100°	140.7	140.9	141.2	141.4	141.6	141.7	141.7	141.7	141.7	141.7	141.1
102.5°	175.2	175.5	175.7	175.9	176.2	176.2	176.0	175.8	175.6	175.5	174.6
105°	228.1	228.1	228.1	228.1	228.1	227.8	227.4	226.9	226.4	226.0	225.5
107.5°	277.7	278.8	279.9	280.9	281.9	282.4	282.2	282.0	281.9	281.6	281.6
110°	316.4	317.0	317.7	318.5	319.1	319.5	319.5	319.5	319.5	319.5	319.5



TEST NUMBER: P331484-927

CATALOG NUMBER: S122DIW-S290D1240U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	353.3	353.9	354.3	354.8	355.4	355.8	356.4	357.0	357.5	358.1	358.2
115°	410.9	411.5	412.3	413.0	413.6	414.1	414.3	414.5	414.8	414.9	415.4
117.5°	465.7	466.4	467.1	467.8	468.5	469.1	469.6	470.2	470.7	471.3	472.5
120°	504.4	505.0	505.7	506.4	507.1	507.4	507.4	507.4	507.4	507.4	509.2
122.5°	542.2	542.6	543.1	543.7	544.2	544.7	545.3	545.8	546.3	546.8	548.1
125°	599.8	600.1	600.3	600.6	600.8	601.3	601.9	602.6	603.3	604.0	604.7
127.5°	652.4	653.2	653.9	654.7	655.4	656.2	657.0	657.8	658.6	659.4	660.3
130°	690.2	691.2	692.1	693.0	694.0	694.6	695.1	695.5	695.9	696.4	696.9
132.5°	726.4	727.1	727.9	728.6	729.4	730.2	731.2	732.2	733.2	734.2	734.1
135°	782.7	783.4	784.1	784.7	785.4	785.9	786.2	786.4	786.6	786.8	786.4
137.5°	833.7	834.6	835.5	836.4	837.3	837.9	838.0	838.2	838.4	838.6	838.0
140°	869.0	869.9	870.8	871.7	872.7	873.1	873.1	873.1	873.1	873.1	872.0
142.5°	901.0	902.0	902.9	903.8	904.7	905.1	904.9	904.7	904.5	904.4	903.6
145°	949.1	950.1	950.9	951.9	952.8	953.1	952.9	952.7	952.4	952.2	950.9
147.5°	992.0	992.9	993.8	994.7	995.5	995.7	995.2	994.7	994.2	993.7	992.8
150°	1020.0	1020.6	1021.4	1022.1	1022.7	1022.7	1022.1	1021.4	1020.6	1020.0	1019.1
152.5°	1046.3	1047.2	1048.1	1048.8	1049.7	1049.7	1048.8	1048.1	1047.2	1046.3	1045.2
155°	1081.6	1082.3	1083.0	1083.7	1084.3	1084.1	1083.0	1081.9	1080.7	1079.6	1078.9
157.5°	1112.0	1113.1	1114.2	1115.3	1116.4	1116.2	1114.6	1113.1	1111.5	1110.0	1109.5
160°	1130.9	1131.9	1132.7	1133.7	1134.6	1134.3	1133.0	1131.6	1130.2	1128.9	1128.6
162.5°	1147.4	1148.4	1149.5	1150.6	1151.8	1151.5	1149.9	1148.4	1146.8	1145.3	1145.1
165°	1168.9	1170.1	1171.2	1172.4	1173.5	1173.3	1171.6	1170.1	1168.5	1166.9	1166.9
167.5°	1186.6	1187.8	1189.0	1190.2	1191.4	1191.1	1189.5	1188.0	1186.4	1184.7	1184.8
170°	1195.6	1197.0	1198.4	1199.8	1201.1	1201.0	1199.4	1197.8	1196.2	1194.6	1194.8
172.5°	1203.0	1204.4	1205.8	1207.1	1208.5	1208.4	1206.8	1205.2	1203.6	1202.0	1202.2
175°	1211.0	1212.4	1213.8	1215.1	1216.6	1216.4	1214.8	1213.2	1211.6	1210.0	1210.5
177.5°	1214.7	1215.8	1217.0	1218.1	1219.1	1219.1	1218.1	1217.0	1215.8	1214.7	1215.1
180°	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2



TEST NUMBER: P331484-927

CATALOG NUMBER: S122DIW-S290D1240U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3
2.5°	480.5	479.3	478.6	476.0	473.7	471.4	470.7	471.0	467.8	464.8	463.5
5°	499.2	495.6	492.2	487.4	481.6	475.2	472.1	469.5	463.2	456.4	452.4
7.5°	515.9	510.8	504.2	495.1	486.7	476.8	470.5	464.9	455.7	446.1	440.1
10°	526.2	519.2	510.7	499.6	489.3	477.2	468.8	460.3	449.6	438.0	430.8
12.5°	535.0	525.5	517.2	502.9	490.8	475.6	465.6	453.7	442.4	428.6	421.6
15°	555.9	538.4	522.6	506.4	491.5	470.4	459.2	443.2	428.3	411.4	403.3
17.5°	572.0	552.4	527.5	506.9	489.5	466.1	449.8	430.6	413.0	393.6	382.6
20°	581.2	558.7	532.0	507.5	486.6	459.9	442.1	422.6	401.9	380.1	368.2
22.5°	586.7	563.1	536.5	505.3	480.9	455.0	432.5	411.0	390.1	366.5	354.1
25°	588.4	566.9	538.8	503.5	473.6	444.3	417.3	396.4	371.1	349.1	331.0
27.5°	579.9	564.4	537.4	500.1	465.3	431.0	400.9	377.3	350.5	326.7	308.4
30°	569.3	560.4	534.1	496.7	458.7	421.8	388.7	361.9	335.3	311.2	292.4
32.5°	553.1	551.2	528.1	491.8	451.6	410.2	375.9	348.8	319.2	295.6	277.7
35°	521.2	529.8	515.2	480.9	438.4	393.6	356.5	325.5	294.9	272.3	255.6
37.5°	478.3	499.8	496.0	464.9	420.4	375.5	334.5	302.2	273.1	250.2	233.8
40°	448.8	476.2	480.1	452.6	407.8	361.6	318.1	286.0	257.5	236.6	220.1
42.5°	417.2	449.1	459.9	437.9	394.0	346.8	303.5	270.1	241.9	221.7	207.0
45°	364.1	406.3	426.0	413.4	370.9	322.7	278.1	244.2	218.6	199.6	188.2
47.5°	314.4	360.6	387.0	382.5	345.2	297.5	253.3	220.9	196.0	180.8	170.6
50°	279.3	326.8	358.6	360.1	326.8	279.5	235.2	204.6	181.7	167.5	159.2
52.5°	248.7	294.1	328.8	336.5	306.2	260.8	219.0	188.5	168.3	155.3	147.9
55°	208.9	247.2	285.7	299.8	275.5	232.3	193.6	166.8	147.9	138.9	132.5
57.5°	173.7	205.7	241.2	256.7	241.8	204.8	168.5	145.2	129.9	122.0	117.0
60°	155.1	180.3	212.0	230.5	217.5	184.7	153.0	130.8	118.2	111.2	106.5
62.5°	137.8	160.2	187.0	203.9	196.9	165.8	137.4	117.9	107.0	100.4	97.0
65°	113.8	131.3	152.1	167.7	163.0	139.5	116.2	99.5	90.9	85.6	82.9
67.5°	93.6	106.4	120.7	134.4	130.7	114.0	95.4	82.3	75.9	71.4	69.7
70°	81.0	90.7	103.5	114.5	111.4	97.8	82.9	71.8	66.2	62.4	60.8
72.5°	68.9	76.8	86.7	95.6	93.6	82.1	69.9	61.5	57.1	53.6	52.4
75°	52.0	58.1	64.1	70.0	69.5	60.7	53.5	47.0	43.6	40.9	40.3
77.5°	38.4	41.8	45.9	49.4	48.4	43.3	37.7	34.0	31.5	29.7	29.4
80°	29.3	31.3	34.2	36.7	35.5	33.3	28.8	26.1	24.3	22.5	21.8
82.5°	21.3	23.2	25.0	26.4	25.3	23.4	20.6	18.8	17.7	16.5	16.2
85°	11.2	12.2	13.0	13.3	13.0	11.7	10.5	9.7	8.8	8.2	8.1
87.5°	9.5	8.5	7.5	7.0	6.0	5.5	4.4	3.4	3.8	4.2	4.4
90°	25.9	20.9	15.8	12.0	9.3	6.5	3.8	1.0	3.8	6.5	9.3
92.5°	30.3	29.1	27.9	26.3	24.3	22.3	20.3	18.3	20.3	22.3	24.3
95°	64.8	64.4	63.9	62.6	60.3	58.0	55.7	53.4	55.7	58.0	60.3
97.5°	108.8	107.9	107.0	105.6	103.6	101.6	99.6	97.6	99.6	101.6	103.6
100°	140.4	139.7	139.0	137.8	135.9	134.1	132.3	130.5	132.3	134.1	135.9
102.5°	173.7	172.9	172.0	170.8	169.4	167.9	166.4	164.9	166.4	167.9	169.4
105°	225.1	224.6	224.2	223.6	222.9	222.2	221.5	220.9	221.5	222.2	222.9
107.5°	281.6	281.6	281.6	281.1	280.1	279.2	278.1	277.1	278.1	279.2	280.1
110°	319.5	319.5	319.5	318.8	317.4	316.0	314.7	313.3	314.7	316.0	317.4



TEST NUMBER: P331484-927

CATALOG NUMBER: S122DIW-S290D1240U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	358.5	358.6	358.8	358.2	356.9	355.5	354.1	352.8	354.1	355.5	356.9
115°	415.9	416.4	416.8	416.4	414.9	413.6	412.3	410.9	412.3	413.6	414.9
117.5°	473.8	475.1	476.4	476.1	474.3	472.5	470.6	468.8	470.6	472.5	474.3
120°	511.1	512.9	514.8	514.8	512.9	511.1	509.2	507.4	509.2	511.1	512.9
122.5°	549.5	550.7	552.0	551.5	549.3	547.2	544.9	542.7	544.9	547.2	549.3
125°	605.4	606.0	606.7	606.0	604.0	601.9	599.8	597.8	599.8	601.9	604.0
127.5°	661.1	661.9	662.7	661.9	659.3	656.6	654.0	651.4	654.0	656.6	659.3
130°	697.4	697.8	698.2	697.0	694.0	691.1	688.1	685.2	688.1	691.1	694.0
132.5°	734.0	734.0	733.9	732.6	730.2	727.8	725.3	722.9	725.3	727.8	730.2
135°	785.9	785.4	785.0	783.5	781.0	778.5	775.9	773.5	775.9	778.5	781.0
137.5°	837.4	836.8	836.2	834.9	832.8	830.8	828.7	826.6	828.7	830.8	832.8
140°	870.8	869.7	868.5	867.0	864.9	862.8	860.8	858.7	860.8	862.8	864.9
142.5°	902.8	902.0	901.2	899.8	897.8	895.7	893.7	891.6	893.7	895.7	897.8
145°	949.4	948.1	946.7	945.2	943.6	942.1	940.5	938.8	940.5	942.1	943.6
147.5°	991.9	990.9	990.1	988.6	986.7	984.8	982.9	981.0	982.9	984.8	986.7
150°	1018.2	1017.2	1016.4	1015.2	1013.8	1012.5	1011.1	1009.7	1011.1	1012.5	1013.8
152.5°	1044.1	1043.0	1041.9	1040.7	1039.3	1037.9	1036.6	1035.2	1036.6	1037.9	1039.3
155°	1078.2	1077.5	1076.8	1076.2	1075.5	1074.8	1074.1	1073.4	1074.1	1074.8	1075.5
157.5°	1109.1	1108.7	1108.3	1107.9	1107.5	1107.0	1106.5	1106.0	1106.5	1107.0	1107.5
160°	1128.4	1128.1	1128.0	1127.6	1127.2	1126.7	1126.2	1125.8	1126.2	1126.7	1127.2
162.5°	1144.9	1144.6	1144.4	1144.2	1144.1	1144.1	1144.0	1143.8	1144.0	1144.1	1144.1
165°	1166.9	1166.9	1166.9	1167.0	1167.2	1167.4	1167.7	1167.9	1167.7	1167.4	1167.2
167.5°	1184.9	1184.9	1184.9	1185.3	1186.0	1186.7	1187.3	1188.0	1187.3	1186.7	1186.0
170°	1195.1	1195.3	1195.6	1196.0	1196.7	1197.4	1198.0	1198.7	1198.0	1197.4	1196.7
172.5°	1202.5	1202.7	1202.9	1203.4	1204.0	1204.8	1205.5	1206.1	1205.5	1204.8	1204.0
175°	1210.9	1211.4	1211.9	1212.4	1213.1	1213.8	1214.5	1215.1	1214.5	1213.8	1213.1
177.5°	1215.4	1215.8	1216.2	1216.6	1217.2	1217.7	1218.3	1218.9	1218.3	1217.7	1217.2
180°	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2



TEST NUMBER: P331484-927

CATALOG NUMBER: S122DIW-S290D1240U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3
2.5°	462.1	461.2	458.2	456.6	454.0	451.5	450.0	450.7	451.2	451.0	450.5
5°	448.8	445.4	440.1	435.7	432.5	426.5	424.0	422.7	421.6	420.4	419.1
7.5°	433.0	427.6	420.2	413.8	407.7	400.3	396.1	393.6	391.0	388.2	385.6
10°	421.8	414.2	406.3	397.4	390.1	383.5	377.6	373.6	369.9	366.5	364.1
12.5°	410.0	401.3	391.5	379.2	371.3	361.7	360.8	353.9	348.2	346.1	343.2
15°	391.3	379.0	366.5	352.0	345.7	337.1	331.7	326.2	321.4	318.0	317.1
17.5°	369.9	354.0	341.7	331.2	320.9	312.0	307.0	302.8	298.7	294.2	293.6
20°	353.6	339.9	326.5	317.3	306.7	297.6	291.5	287.2	283.8	281.1	278.8
22.5°	338.2	323.2	310.9	300.9	290.4	283.1	278.3	274.1	271.2	268.3	266.1
25°	313.5	301.8	288.3	276.9	268.3	263.6	259.7	256.1	254.3	252.3	249.8
27.5°	291.8	278.8	266.3	257.5	249.9	245.7	242.9	240.4	238.8	237.6	236.1
30°	276.6	263.5	253.6	244.9	238.6	234.5	232.7	231.2	229.3	228.5	227.8
32.5°	261.9	250.1	241.6	234.1	228.1	225.4	223.8	222.4	220.9	220.2	218.7
35°	241.1	231.2	223.0	218.8	214.0	211.6	210.4	208.6	207.2	206.4	206.2
37.5°	221.6	213.0	207.6	202.2	200.2	198.8	197.0	195.8	195.4	195.3	195.0
40°	208.9	201.9	197.0	192.7	191.9	189.6	188.2	187.2	187.2	187.4	187.2
42.5°	197.4	191.1	186.8	183.1	182.0	180.8	179.3	179.3	179.5	180.1	179.5
45°	180.0	175.5	172.4	170.6	168.7	167.4	167.2	167.7	167.9	168.1	168.7
47.5°	163.9	160.9	158.1	156.1	155.3	155.1	154.9	155.8	156.7	157.0	157.8
50°	154.4	151.0	148.6	147.3	146.6	146.3	146.6	147.7	148.5	149.3	149.9
52.5°	143.8	141.3	139.7	138.7	138.5	138.7	138.7	140.0	141.1	141.5	141.7
55°	129.0	127.2	126.9	125.2	126.0	125.8	126.7	127.4	128.5	129.6	129.8
57.5°	114.3	112.9	111.9	112.1	112.3	113.1	113.8	115.1	116.2	117.4	117.5
60°	104.6	103.9	103.3	103.3	103.6	104.7	105.6	106.9	107.6	108.4	108.8
62.5°	95.6	94.9	94.3	94.7	95.6	96.3	97.3	98.0	98.7	99.4	99.7
65°	81.5	81.2	81.7	82.1	82.2	83.1	84.4	84.9	85.6	86.0	87.3
67.5°	68.5	68.6	68.5	69.0	70.1	70.3	71.5	72.7	72.9	73.6	74.4
70°	59.7	60.1	60.4	60.8	61.7	62.1	63.0	63.5	64.2	64.8	65.4
72.5°	51.7	51.7	52.1	52.0	52.8	53.6	54.3	54.9	55.6	56.3	56.8
75°	39.8	39.8	40.2	40.3	41.2	42.1	41.9	42.3	43.0	43.7	44.1
77.5°	29.1	28.7	29.1	29.2	29.5	30.3	30.4	30.9	31.8	31.5	31.9
80°	22.1	21.6	22.1	22.3	22.3	23.2	23.2	23.6	24.1	23.6	24.1
82.5°	15.8	15.5	15.9	16.0	16.2	16.3	16.6	16.6	17.2	17.0	17.2
85°	7.9	7.8	7.9	7.8	7.9	8.1	8.1	7.9	7.9	8.2	7.8
87.5°	4.8	5.5	6.3	7.4	8.2	9.0	8.8	8.7	8.6	8.2	8.2
90°	12.0	15.8	20.9	25.9	30.9	36.0	35.5	35.0	34.6	34.1	34.0
92.5°	26.3	27.9	29.1	30.3	31.4	32.6	32.7	32.9	33.0	33.0	33.1
95°	62.6	63.9	64.4	64.8	65.3	65.8	65.8	65.8	65.8	65.8	65.5
97.5°	105.6	107.0	107.9	108.8	109.6	110.5	110.5	110.5	110.5	110.5	110.5
100°	137.8	139.0	139.7	140.4	141.1	141.7	141.7	141.7	141.7	141.7	141.6
102.5°	170.8	172.0	172.9	173.7	174.6	175.5	175.6	175.8	176.0	176.2	176.2
105°	223.6	224.2	224.6	225.1	225.5	226.0	226.4	226.9	227.4	227.8	228.1
107.5°	281.1	281.6	281.6	281.6	281.6	281.6	281.9	282.0	282.2	282.4	281.9
110°	318.8	319.5	319.5	319.5	319.5	319.5	319.5	319.5	319.5	319.5	319.1



TEST NUMBER: P331484-927

CATALOG NUMBER: S122DIW-S290D1240U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	358.2	358.8	358.6	358.5	358.2	358.1	357.5	357.0	356.4	355.8	355.4
115°	416.4	416.8	416.4	415.9	415.4	414.9	414.8	414.5	414.3	414.1	413.6
117.5°	476.1	476.4	475.1	473.8	472.5	471.3	470.7	470.2	469.6	469.1	468.5
120°	514.8	514.8	512.9	511.1	509.2	507.4	507.4	507.4	507.4	507.4	507.1
122.5°	551.5	552.0	550.7	549.5	548.1	546.8	546.3	545.8	545.3	544.7	544.2
125°	606.0	606.7	606.0	605.4	604.7	604.0	603.3	602.6	601.9	601.3	600.8
127.5°	661.9	662.7	661.9	661.1	660.3	659.4	658.6	657.8	657.0	656.2	655.4
130°	697.0	698.2	697.8	697.4	696.9	696.4	695.9	695.5	695.1	694.6	694.0
132.5°	732.6	733.9	734.0	734.0	734.1	734.2	733.2	732.2	731.2	730.2	729.4
135°	783.5	785.0	785.4	785.9	786.4	786.8	786.6	786.4	786.2	785.9	785.4
137.5°	834.9	836.2	836.8	837.4	838.0	838.6	838.4	838.2	838.0	837.9	837.3
140°	867.0	868.5	869.7	870.8	872.0	873.1	873.1	873.1	873.1	873.1	872.7
142.5°	899.8	901.2	902.0	902.8	903.6	904.4	904.5	904.7	904.9	905.1	904.7
145°	945.2	946.7	948.1	949.4	950.9	952.2	952.4	952.7	952.9	953.1	952.8
147.5°	988.6	990.1	990.9	991.9	992.8	993.7	994.2	994.7	995.2	995.7	995.5
150°	1015.2	1016.4	1017.2	1018.2	1019.1	1020.0	1020.6	1021.4	1022.1	1022.7	1022.7
152.5°	1040.7	1041.9	1043.0	1044.1	1045.2	1046.3	1047.2	1048.1	1048.8	1049.7	1049.7
155°	1076.2	1076.8	1077.5	1078.2	1078.9	1079.6	1080.7	1081.9	1083.0	1084.1	1084.3
157.5°	1107.9	1108.3	1108.7	1109.1	1109.5	1110.0	1111.5	1113.1	1114.6	1116.2	1116.4
160°	1127.6	1128.0	1128.1	1128.4	1128.6	1128.9	1130.2	1131.6	1133.0	1134.3	1134.6
162.5°	1144.2	1144.4	1144.6	1144.9	1145.1	1145.3	1146.8	1148.4	1149.9	1151.5	1151.8
165°	1167.0	1166.9	1166.9	1166.9	1166.9	1166.9	1168.5	1170.1	1171.6	1173.3	1173.5
167.5°	1185.3	1184.9	1184.9	1184.9	1184.8	1184.7	1186.4	1188.0	1189.5	1191.1	1191.4
170°	1196.0	1195.6	1195.3	1195.1	1194.8	1194.6	1196.2	1197.8	1199.4	1201.0	1201.1
172.5°	1203.4	1202.9	1202.7	1202.5	1202.2	1202.0	1203.6	1205.2	1206.8	1208.4	1208.5
175°	1212.4	1211.9	1211.4	1210.9	1210.5	1210.0	1211.6	1213.2	1214.8	1216.4	1216.6
177.5°	1216.6	1216.2	1215.8	1215.4	1215.1	1214.7	1215.8	1217.0	1218.1	1219.1	1219.1
180°	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2



TEST NUMBER: P331484-927

CATALOG NUMBER: S122DIW-S290D1240U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3
2.5°	449.1	448.8	448.8	447.5	448.8	448.8	449.1	450.5	451.0	451.2	450.7
5°	416.6	416.1	415.2	416.1	415.2	416.1	416.6	419.1	420.4	421.6	422.7
7.5°	384.4	382.3	382.0	379.9	382.0	382.3	384.4	385.6	388.2	391.0	393.6
10°	361.0	359.6	359.3	355.9	359.3	359.6	361.0	364.1	366.5	369.9	373.6
12.5°	343.2	339.7	340.4	338.4	340.4	339.7	343.2	343.2	346.1	348.2	353.9
15°	312.2	312.2	311.5	308.5	311.5	312.2	312.2	317.1	318.0	321.4	326.2
17.5°	290.0	289.6	288.0	288.8	288.0	289.6	290.0	293.6	294.2	298.7	302.8
20°	276.8	275.7	273.5	273.5	273.5	275.7	276.8	278.8	281.1	283.8	287.2
22.5°	264.3	264.2	261.9	262.6	261.9	264.2	264.3	266.1	268.3	271.2	274.1
25°	249.6	248.2	247.1	247.6	247.1	248.2	249.6	249.8	252.3	254.3	256.1
27.5°	235.7	234.9	234.8	233.4	234.8	234.9	235.7	236.1	237.6	238.8	240.4
30°	227.7	225.9	226.2	225.3	226.2	225.9	227.7	227.8	228.5	229.3	231.2
32.5°	218.4	217.8	217.5	216.7	217.5	217.8	218.4	218.7	220.2	220.9	222.4
35°	205.9	206.0	205.2	205.5	205.2	206.0	205.9	206.2	206.4	207.2	208.6
37.5°	194.9	195.4	195.0	195.1	195.0	195.4	194.9	195.0	195.3	195.4	195.8
40°	187.7	187.7	187.7	188.2	187.7	187.7	187.7	187.2	187.4	187.2	187.2
42.5°	180.8	180.5	180.2	180.1	180.2	180.5	180.8	179.5	180.1	179.5	179.3
45°	169.0	169.5	169.7	168.8	169.7	169.5	169.0	168.7	168.1	167.9	167.7
47.5°	158.3	158.4	158.3	159.1	158.3	158.4	158.3	157.8	157.0	156.7	155.8
50°	150.8	150.4	150.8	150.4	150.8	150.4	150.8	149.9	149.3	148.5	147.7
52.5°	142.9	143.0	142.8	142.7	142.8	143.0	142.9	141.7	141.5	141.1	140.0
55°	130.5	130.8	130.6	130.6	130.6	130.8	130.5	129.8	129.6	128.5	127.4
57.5°	117.6	118.0	118.2	117.4	118.2	118.0	117.6	117.5	117.4	116.2	115.1
60°	108.7	109.6	109.4	109.1	109.4	109.6	108.7	108.8	108.4	107.6	106.9
62.5°	100.4	100.8	100.8	100.7	100.8	100.8	100.4	99.7	99.4	98.7	98.0
65°	87.9	88.2	87.6	88.2	87.6	88.2	87.9	87.3	86.0	85.6	84.9
67.5°	74.1	74.3	74.7	74.9	74.7	74.3	74.1	74.4	73.6	72.9	72.7
70°	65.7	65.5	66.1	66.6	66.1	65.5	65.7	65.4	64.8	64.2	63.5
72.5°	56.7	57.1	57.0	57.4	57.0	57.1	56.7	56.8	56.3	55.6	54.9
75°	43.7	44.3	44.1	44.6	44.1	44.3	43.7	44.1	43.7	43.0	42.3
77.5°	31.6	31.7	31.6	31.9	31.6	31.7	31.6	31.9	31.5	31.8	30.9
80°	24.1	23.8	23.4	24.1	23.4	23.8	24.1	24.1	23.6	24.1	23.6
82.5°	16.8	17.0	16.6	16.6	16.6	17.0	16.8	17.2	17.0	17.2	16.6
85°	7.8	7.5	7.2	7.2	7.2	7.5	7.8	7.8	8.2	7.9	7.9
87.5°	8.3	8.2	8.2	8.2	8.2	8.2	8.3	8.2	8.2	8.6	8.7
90°	34.2	34.5	34.7	34.9	34.7	34.5	34.2	34.0	34.1	34.6	35.0
92.5°	33.1	33.2	33.3	33.3	33.3	33.2	33.1	33.1	33.0	33.0	32.9
95°	65.0	64.6	64.2	63.7	64.2	64.6	65.0	65.5	65.8	65.8	65.8
97.5°	110.4	110.4	110.4	110.4	110.4	110.4	110.4	110.5	110.5	110.5	110.5
100°	141.4	141.2	140.9	140.7	140.9	141.2	141.4	141.6	141.7	141.7	141.7
102.5°	175.9	175.7	175.5	175.2	175.5	175.7	175.9	176.2	176.2	176.0	175.8
105°	228.1	228.1	228.1	228.1	228.1	228.1	228.1	228.1	227.8	227.4	226.9
107.5°	280.9	279.9	278.8	277.7	278.8	279.9	280.9	281.9	282.4	282.2	282.0
110°	318.5	317.7	317.0	316.4	317.0	317.7	318.5	319.1	319.5	319.5	319.5



TEST NUMBER: P331484-927

CATALOG NUMBER: S122DIW-S290D1240U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	354.8	354.3	353.9	353.3	353.9	354.3	354.8	355.4	355.8	356.4	357.0
115°	413.0	412.3	411.5	410.9	411.5	412.3	413.0	413.6	414.1	414.3	414.5
117.5°	467.8	467.1	466.4	465.7	466.4	467.1	467.8	468.5	469.1	469.6	470.2
120°	506.4	505.7	505.0	504.4	505.0	505.7	506.4	507.1	507.4	507.4	507.4
122.5°	543.7	543.1	542.6	542.2	542.6	543.1	543.7	544.2	544.7	545.3	545.8
125°	600.6	600.3	600.1	599.8	600.1	600.3	600.6	600.8	601.3	601.9	602.6
127.5°	654.7	653.9	653.2	652.4	653.2	653.9	654.7	655.4	656.2	657.0	657.8
130°	693.0	692.1	691.2	690.2	691.2	692.1	693.0	694.0	694.6	695.1	695.5
132.5°	728.6	727.9	727.1	726.4	727.1	727.9	728.6	729.4	730.2	731.2	732.2
135°	784.7	784.1	783.4	782.7	783.4	784.1	784.7	785.4	785.9	786.2	786.4
137.5°	836.4	835.5	834.6	833.7	834.6	835.5	836.4	837.3	837.9	838.0	838.2
140°	871.7	870.8	869.9	869.0	869.9	870.8	871.7	872.7	873.1	873.1	873.1
142.5°	903.8	902.9	902.0	901.0	902.0	902.9	903.8	904.7	905.1	904.9	904.7
145°	951.9	950.9	950.1	949.1	950.1	950.9	951.9	952.8	953.1	952.9	952.7
147.5°	994.7	993.8	992.9	992.0	992.9	993.8	994.7	995.5	995.7	995.2	994.7
150°	1022.1	1021.4	1020.6	1020.0	1020.6	1021.4	1022.1	1022.7	1022.7	1022.1	1021.4
152.5°	1048.8	1048.1	1047.2	1046.3	1047.2	1048.1	1048.8	1049.7	1049.7	1048.8	1048.1
155°	1083.7	1083.0	1082.3	1081.6	1082.3	1083.0	1083.7	1084.3	1084.1	1083.0	1081.9
157.5°	1115.3	1114.2	1113.1	1112.0	1113.1	1114.2	1115.3	1116.4	1116.2	1114.6	1113.1
160°	1133.7	1132.7	1131.9	1130.9	1131.9	1132.7	1133.7	1134.6	1134.3	1133.0	1131.6
162.5°	1150.6	1149.5	1148.4	1147.4	1148.4	1149.5	1150.6	1151.8	1151.5	1149.9	1148.4
165°	1172.4	1171.2	1170.1	1168.9	1170.1	1171.2	1172.4	1173.5	1173.3	1171.6	1170.1
167.5°	1190.2	1189.0	1187.8	1186.6	1187.8	1189.0	1190.2	1191.4	1191.1	1189.5	1188.0
170°	1199.8	1198.4	1197.0	1195.6	1197.0	1198.4	1199.8	1201.1	1201.0	1199.4	1197.8
172.5°	1207.1	1205.8	1204.4	1203.0	1204.4	1205.8	1207.1	1208.5	1208.4	1206.8	1205.2
175°	1215.1	1213.8	1212.4	1211.0	1212.4	1213.8	1215.1	1216.6	1216.4	1214.8	1213.2
177.5°	1218.1	1217.0	1215.8	1214.7	1215.8	1217.0	1218.1	1219.1	1219.1	1218.1	1217.0
180°	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2



TEST NUMBER: P331484-927

CATALOG NUMBER: S122DIW-S290D1240U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3
2.5°	450.0	451.5	454.0	456.6	458.2	461.2	462.1	463.5	464.8	467.8	471.0
5°	424.0	426.5	432.5	435.7	440.1	445.4	448.8	452.4	456.4	463.2	469.5
7.5°	396.1	400.3	407.7	413.8	420.2	427.6	433.0	440.1	446.1	455.7	464.9
10°	377.6	383.5	390.1	397.4	406.3	414.2	421.8	430.8	438.0	449.6	460.3
12.5°	360.8	361.7	371.3	379.2	391.5	401.3	410.0	421.6	428.6	442.4	453.7
15°	331.7	337.1	345.7	352.0	366.5	379.0	391.3	403.3	411.4	428.3	443.2
17.5°	307.0	312.0	320.9	331.2	341.7	354.0	369.9	382.6	393.6	413.0	430.6
20°	291.5	297.6	306.7	317.3	326.5	339.9	353.6	368.2	380.1	401.9	422.6
22.5°	278.3	283.1	290.4	300.9	310.9	323.2	338.2	354.1	366.5	390.1	411.0
25°	259.7	263.6	268.3	276.9	288.3	301.8	313.5	331.0	349.1	371.1	396.4
27.5°	242.9	245.7	249.9	257.5	266.3	278.8	291.8	308.4	326.7	350.5	377.3
30°	232.7	234.5	238.6	244.9	253.6	263.5	276.6	292.4	311.2	335.3	361.9
32.5°	223.8	225.4	228.1	234.1	241.6	250.1	261.9	277.7	295.6	319.2	348.8
35°	210.4	211.6	214.0	218.8	223.0	231.2	241.1	255.6	272.3	294.9	325.5
37.5°	197.0	198.8	200.2	202.2	207.6	213.0	221.6	233.8	250.2	273.1	302.2
40°	188.2	189.6	191.9	192.7	197.0	201.9	208.9	220.1	236.6	257.5	286.0
42.5°	179.3	180.8	182.0	183.1	186.8	191.1	197.4	207.0	221.7	241.9	270.1
45°	167.2	167.4	168.7	170.6	172.4	175.5	180.0	188.2	199.6	218.6	244.2
47.5°	154.9	155.1	155.3	156.1	158.1	160.9	163.9	170.6	180.8	196.0	220.9
50°	146.6	146.3	146.6	147.3	148.6	151.0	154.4	159.2	167.5	181.7	204.6
52.5°	138.7	138.7	138.5	138.7	139.7	141.3	143.8	147.9	155.3	168.3	188.5
55°	126.7	125.8	126.0	125.2	126.9	127.2	129.0	132.5	138.9	147.9	166.8
57.5°	113.8	113.1	112.3	112.1	111.9	112.9	114.3	117.0	122.0	129.9	145.2
60°	105.6	104.7	103.6	103.3	103.3	103.9	104.6	106.5	111.2	118.2	130.8
62.5°	97.3	96.3	95.6	94.7	94.3	94.9	95.6	97.0	100.4	107.0	117.9
65°	84.4	83.1	82.2	82.1	81.7	81.2	81.5	82.9	85.6	90.9	99.5
67.5°	71.5	70.3	70.1	69.0	68.5	68.6	68.5	69.7	71.4	75.9	82.3
70°	63.0	62.1	61.7	60.8	60.4	60.1	59.7	60.8	62.4	66.2	71.8
72.5°	54.3	53.6	52.8	52.0	52.1	51.7	51.7	52.4	53.6	57.1	61.5
75°	41.9	42.1	41.2	40.3	40.2	39.8	39.8	40.3	40.9	43.6	47.0
77.5°	30.4	30.3	29.5	29.2	29.1	28.7	29.1	29.4	29.7	31.5	34.0
80°	23.2	23.2	22.3	22.3	22.1	21.6	22.1	21.8	22.5	24.3	26.1
82.5°	16.6	16.3	16.2	16.0	15.9	15.5	15.8	16.2	16.5	17.7	18.8
85°	8.1	8.1	7.9	7.8	7.9	7.8	7.9	8.1	8.2	8.8	9.7
87.5°	8.8	9.0	8.2	7.4	6.3	5.5	4.8	4.4	4.2	3.8	3.4
90°	35.5	36.0	30.9	25.9	20.9	15.8	12.0	9.3	6.5	3.8	1.0
92.5°	32.7	32.6	31.4	30.3	29.1	27.9	26.3	24.3	22.3	20.3	18.3
95°	65.8	65.8	65.3	64.8	64.4	63.9	62.6	60.3	58.0	55.7	53.4
97.5°	110.5	110.5	109.6	108.8	107.9	107.0	105.6	103.6	101.6	99.6	97.6
100°	141.7	141.7	141.1	140.4	139.7	139.0	137.8	135.9	134.1	132.3	130.5
102.5°	175.6	175.5	174.6	173.7	172.9	172.0	170.8	169.4	167.9	166.4	164.9
105°	226.4	226.0	225.5	225.1	224.6	224.2	223.6	222.9	222.2	221.5	220.9
107.5°	281.9	281.6	281.6	281.6	281.6	281.6	281.1	280.1	279.2	278.1	277.1
110°	319.5	319.5	319.5	319.5	319.5	319.5	318.8	317.4	316.0	314.7	313.3



TEST NUMBER: P331484-927

CATALOG NUMBER: S122DIW-S290D1240U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	357.5	358.1	358.2	358.5	358.6	358.8	358.2	356.9	355.5	354.1	352.8
115°	414.8	414.9	415.4	415.9	416.4	416.8	416.4	414.9	413.6	412.3	410.9
117.5°	470.7	471.3	472.5	473.8	475.1	476.4	476.1	474.3	472.5	470.6	468.8
120°	507.4	507.4	509.2	511.1	512.9	514.8	514.8	512.9	511.1	509.2	507.4
122.5°	546.3	546.8	548.1	549.5	550.7	552.0	551.5	549.3	547.2	544.9	542.7
125°	603.3	604.0	604.7	605.4	606.0	606.7	606.0	604.0	601.9	599.8	597.8
127.5°	658.6	659.4	660.3	661.1	661.9	662.7	661.9	659.3	656.6	654.0	651.4
130°	695.9	696.4	696.9	697.4	697.8	698.2	697.0	694.0	691.1	688.1	685.2
132.5°	733.2	734.2	734.1	734.0	734.0	733.9	732.6	730.2	727.8	725.3	722.9
135°	786.6	786.8	786.4	785.9	785.4	785.0	783.5	781.0	778.5	775.9	773.5
137.5°	838.4	838.6	838.0	837.4	836.8	836.2	834.9	832.8	830.8	828.7	826.6
140°	873.1	873.1	872.0	870.8	869.7	868.5	867.0	864.9	862.8	860.8	858.7
142.5°	904.5	904.4	903.6	902.8	902.0	901.2	899.8	897.8	895.7	893.7	891.6
145°	952.4	952.2	950.9	949.4	948.1	946.7	945.2	943.6	942.1	940.5	938.8
147.5°	994.2	993.7	992.8	991.9	990.9	990.1	988.6	986.7	984.8	982.9	981.0
150°	1020.6	1020.0	1019.1	1018.2	1017.2	1016.4	1015.2	1013.8	1012.5	1011.1	1009.7
152.5°	1047.2	1046.3	1045.2	1044.1	1043.0	1041.9	1040.7	1039.3	1037.9	1036.6	1035.2
155°	1080.7	1079.6	1078.9	1078.2	1077.5	1076.8	1076.2	1075.5	1074.8	1074.1	1073.4
157.5°	1111.5	1110.0	1109.5	1109.1	1108.7	1108.3	1107.9	1107.5	1107.0	1106.5	1106.0
160°	1130.2	1128.9	1128.6	1128.4	1128.1	1128.0	1127.6	1127.2	1126.7	1126.2	1125.8
162.5°	1146.8	1145.3	1145.1	1144.9	1144.6	1144.4	1144.2	1144.1	1144.1	1144.0	1143.8
165°	1168.5	1166.9	1166.9	1166.9	1166.9	1166.9	1167.0	1167.2	1167.4	1167.7	1167.9
167.5°	1186.4	1184.7	1184.8	1184.9	1184.9	1184.9	1185.3	1186.0	1186.7	1187.3	1188.0
170°	1196.2	1194.6	1194.8	1195.1	1195.3	1195.6	1196.0	1196.7	1197.4	1198.0	1198.7
172.5°	1203.6	1202.0	1202.2	1202.5	1202.7	1202.9	1203.4	1204.0	1204.8	1205.5	1206.1
175°	1211.6	1210.0	1210.5	1210.9	1211.4	1211.9	1212.4	1213.1	1213.8	1214.5	1215.1
177.5°	1215.8	1214.7	1215.1	1215.4	1215.8	1216.2	1216.6	1217.2	1217.7	1218.3	1218.9
180°	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2



TEST NUMBER: P331484-927

CATALOG NUMBER: S122DIW-S290D1240U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3
2.5°	470.7	471.4	473.7	476.0	478.6	479.3	480.5	479.5	479.2	481.9	483.9
5°	472.1	475.2	481.6	487.4	492.2	495.6	499.2	500.7	503.4	507.1	511.8
7.5°	470.5	476.8	486.7	495.1	504.2	510.8	515.9	520.4	525.7	532.8	540.7
10°	468.8	477.2	489.3	499.6	510.7	519.2	526.2	533.1	541.0	550.9	561.1
12.5°	465.6	475.6	490.8	502.9	517.2	525.5	535.0	549.7	558.3	572.0	586.5
15°	459.2	470.4	491.5	506.4	522.6	538.4	555.9	569.9	583.9	592.1	612.4
17.5°	449.8	466.1	489.5	506.9	527.5	552.4	572.0	588.0	604.1	617.3	627.5
20°	442.1	459.9	486.6	507.5	532.0	558.7	581.2	597.5	611.5	622.5	628.8
22.5°	432.5	455.0	480.9	505.3	536.5	563.1	586.7	599.4	611.2	616.6	619.0
25°	417.3	444.3	473.6	503.5	538.8	566.9	588.4	596.2	599.6	594.4	585.7
27.5°	400.9	431.0	465.3	500.1	537.4	564.4	579.9	578.7	572.9	556.0	542.5
30°	388.7	421.8	458.7	496.7	534.1	560.4	569.3	560.4	547.2	528.4	509.1
32.5°	375.9	410.2	451.6	491.8	528.1	551.2	553.1	537.7	517.3	495.8	471.8
35°	356.5	393.6	438.4	480.9	515.2	529.8	521.2	493.8	469.7	440.4	407.6
37.5°	334.5	375.5	420.4	464.9	496.0	499.8	478.3	449.6	415.5	381.0	342.5
40°	318.1	361.6	407.8	452.6	480.1	476.2	448.8	417.2	376.7	334.5	298.7
42.5°	303.5	346.8	394.0	437.9	459.9	449.1	417.2	378.3	334.8	295.1	262.3
45°	278.1	322.7	370.9	413.4	426.0	406.3	364.1	320.8	278.1	244.9	219.0
47.5°	253.3	297.5	345.2	382.5	387.0	360.6	314.4	270.0	233.1	206.2	187.9
50°	235.2	279.5	326.8	360.1	358.6	326.8	279.3	237.0	206.2	184.4	172.2
52.5°	219.0	260.8	306.2	336.5	328.8	294.1	248.7	211.2	185.9	168.9	157.8
55°	193.6	232.3	275.5	299.8	285.7	247.2	208.9	178.7	159.9	147.2	138.6
57.5°	168.5	204.8	241.8	256.7	241.2	205.7	173.7	151.8	137.7	128.3	122.6
60°	153.0	184.7	217.5	230.5	212.0	180.3	155.1	135.5	124.1	116.5	111.4
62.5°	137.4	165.8	196.9	203.9	187.0	160.2	137.8	121.5	112.3	105.4	100.6
65°	116.2	139.5	163.0	167.7	152.1	131.3	113.8	103.1	94.8	89.8	86.0
67.5°	95.4	114.0	130.7	134.4	120.7	106.4	93.6	84.4	78.8	74.6	71.4
70°	82.9	97.8	111.4	114.5	103.5	90.7	81.0	73.6	68.5	65.0	61.9
72.5°	69.9	82.1	93.6	95.6	86.7	76.8	68.9	63.1	58.6	56.3	53.4
75°	53.5	60.7	69.5	70.0	64.1	58.1	52.0	48.2	45.9	43.0	41.6
77.5°	37.7	43.3	48.4	49.4	45.9	41.8	38.4	35.4	33.4	32.1	30.7
80°	28.8	33.3	35.5	36.7	34.2	31.3	29.3	27.3	26.1	25.2	24.3
82.5°	20.6	23.4	25.3	26.4	25.0	23.2	21.3	20.1	19.2	18.5	18.1
85°	10.5	11.7	13.0	13.3	13.0	12.2	11.2	11.2	10.6	10.5	10.5
87.5°	4.4	5.5	6.0	7.0	7.5	8.5	9.5	10.4	11.2	11.0	10.8
90°	3.8	6.5	9.3	12.0	15.8	20.9	25.9	30.9	36.0	35.5	35.0
92.5°	20.3	22.3	24.3	26.3	27.9	29.1	30.3	31.4	32.6	32.7	32.9
95°	55.7	58.0	60.3	62.6	63.9	64.4	64.8	65.3	65.8	65.8	65.8
97.5°	99.6	101.6	103.6	105.6	107.0	107.9	108.8	109.6	110.5	110.5	110.5
100°	132.3	134.1	135.9	137.8	139.0	139.7	140.4	141.1	141.7	141.7	141.7
102.5°	166.4	167.9	169.4	170.8	172.0	172.9	173.7	174.6	175.5	175.6	175.8
105°	221.5	222.2	222.9	223.6	224.2	224.6	225.1	225.5	226.0	226.4	226.9
107.5°	278.1	279.2	280.1	281.1	281.6	281.6	281.6	281.6	281.6	281.9	282.0
110°	314.7	316.0	317.4	318.8	319.5	319.5	319.5	319.5	319.5	319.5	319.5



TEST NUMBER: P331484-927

CATALOG NUMBER: S122DIW-S290D1240U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	354.1	355.5	356.9	358.2	358.8	358.6	358.5	358.2	358.1	357.5	357.0
115°	412.3	413.6	414.9	416.4	416.8	416.4	415.9	415.4	414.9	414.8	414.5
117.5°	470.6	472.5	474.3	476.1	476.4	475.1	473.8	472.5	471.3	470.7	470.2
120°	509.2	511.1	512.9	514.8	514.8	512.9	511.1	509.2	507.4	507.4	507.4
122.5°	544.9	547.2	549.3	551.5	552.0	550.7	549.5	548.1	546.8	546.3	545.8
125°	599.8	601.9	604.0	606.0	606.7	606.0	605.4	604.7	604.0	603.3	602.6
127.5°	654.0	656.6	659.3	661.9	662.7	661.9	661.1	660.3	659.4	658.6	657.8
130°	688.1	691.1	694.0	697.0	698.2	697.8	697.4	696.9	696.4	695.9	695.5
132.5°	725.3	727.8	730.2	732.6	733.9	734.0	734.0	734.1	734.2	733.2	732.2
135°	775.9	778.5	781.0	783.5	785.0	785.4	785.9	786.4	786.8	786.6	786.4
137.5°	828.7	830.8	832.8	834.9	836.2	836.8	837.4	838.0	838.6	838.4	838.2
140°	860.8	862.8	864.9	867.0	868.5	869.7	870.8	872.0	873.1	873.1	873.1
142.5°	893.7	895.7	897.8	899.8	901.2	902.0	902.8	903.6	904.4	904.5	904.7
145°	940.5	942.1	943.6	945.2	946.7	948.1	949.4	950.9	952.2	952.4	952.7
147.5°	982.9	984.8	986.7	988.6	990.1	990.9	991.9	992.8	993.7	994.2	994.7
150°	1011.1	1012.5	1013.8	1015.2	1016.4	1017.2	1018.2	1019.1	1020.0	1020.6	1021.4
152.5°	1036.6	1037.9	1039.3	1040.7	1041.9	1043.0	1044.1	1045.2	1046.3	1047.2	1048.1
155°	1074.1	1074.8	1075.5	1076.2	1076.8	1077.5	1078.2	1078.9	1079.6	1080.7	1081.9
157.5°	1106.5	1107.0	1107.5	1107.9	1108.3	1108.7	1109.1	1109.5	1110.0	1111.5	1113.1
160°	1126.2	1126.7	1127.2	1127.6	1128.0	1128.1	1128.4	1128.6	1128.9	1130.2	1131.6
162.5°	1144.0	1144.1	1144.1	1144.2	1144.4	1144.6	1144.9	1145.1	1145.3	1146.8	1148.4
165°	1167.7	1167.4	1167.2	1167.0	1166.9	1166.9	1166.9	1166.9	1166.9	1168.5	1170.1
167.5°	1187.3	1186.7	1186.0	1185.3	1184.9	1184.9	1184.9	1184.8	1184.7	1186.4	1188.0
170°	1198.0	1197.4	1196.7	1196.0	1195.6	1195.3	1195.1	1194.8	1194.6	1196.2	1197.8
172.5°	1205.5	1204.8	1204.0	1203.4	1202.9	1202.7	1202.5	1202.2	1202.0	1203.6	1205.2
175°	1214.5	1213.8	1213.1	1212.4	1211.9	1211.4	1210.9	1210.5	1210.0	1211.6	1213.2
177.5°	1218.3	1217.7	1217.2	1216.6	1216.2	1215.8	1215.4	1215.1	1214.7	1215.8	1217.0
180°	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2



TEST NUMBER: P331484-927

CATALOG NUMBER: S122DIW-S290D1240U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	468.3	468.3	468.3	468.3	468.3	468.3	468.3
2.5°	485.7	487.7	487.7	488.0	490.3	490.0	489.8
5°	516.8	519.9	520.2	523.5	525.6	524.9	522.9
7.5°	546.2	551.9	556.3	558.6	561.5	563.2	562.4
10°	569.6	577.8	582.9	586.3	590.4	593.5	592.4
12.5°	590.7	600.6	607.5	613.4	613.9	617.8	615.1
15°	623.8	634.1	635.3	639.5	643.0	642.6	642.8
17.5°	634.6	637.9	638.7	638.7	638.8	637.5	634.8
20°	630.7	629.5	626.5	624.1	620.0	619.4	615.8
22.5°	612.3	608.3	600.6	595.6	589.1	587.5	586.5
25°	576.1	567.2	555.0	543.3	540.0	533.8	535.5
27.5°	526.2	512.5	499.2	489.8	481.2	471.7	474.4
30°	491.3	475.8	457.1	442.7	433.5	424.5	422.9
32.5°	449.6	426.8	406.0	393.3	379.2	373.5	367.3
35°	377.6	355.4	334.7	316.9	306.7	298.7	291.5
37.5°	312.8	287.3	270.6	256.2	248.7	244.2	245.4
40°	272.7	250.3	238.1	227.1	220.2	217.1	217.8
42.5°	240.1	223.4	213.3	205.8	201.0	199.2	198.8
45°	203.2	193.8	185.5	181.3	178.9	176.9	175.6
47.5°	178.0	170.3	165.6	163.1	161.1	159.1	159.0
50°	162.9	157.8	154.6	151.9	150.3	148.9	150.1
52.5°	151.3	146.7	143.5	141.1	140.5	139.2	139.1
55°	134.3	130.6	128.3	126.1	125.1	124.4	123.4
57.5°	118.7	115.3	113.1	111.8	109.7	109.0	108.7
60°	107.6	104.9	102.7	100.9	100.1	98.6	98.6
62.5°	97.4	94.7	92.7	91.3	89.8	89.3	89.4
65°	82.6	80.4	78.4	77.0	76.7	75.6	76.0
67.5°	69.0	67.6	65.4	64.6	64.0	63.5	63.0
70°	59.9	58.5	57.4	56.3	55.8	55.8	55.8
72.5°	52.3	50.5	49.9	48.6	48.9	48.3	47.7
75°	40.5	39.4	38.9	38.3	37.5	37.5	37.5
77.5°	29.8	29.5	28.8	28.3	28.0	27.9	28.0
80°	23.1	22.8	22.5	22.5	22.1	21.9	21.6
82.5°	17.7	17.3	17.0	16.9	16.8	16.8	16.7
85°	10.1	9.7	9.7	9.9	9.5	9.5	9.7
87.5°	10.8	10.7	10.5	10.6	10.8	10.7	10.7
90°	34.6	34.1	34.0	34.2	34.5	34.7	34.9
92.5°	33.0	33.0	33.1	33.1	33.2	33.3	33.3
95°	65.8	65.8	65.5	65.0	64.6	64.2	63.7
97.5°	110.5	110.5	110.5	110.4	110.4	110.4	110.4
100°	141.7	141.7	141.6	141.4	141.2	140.9	140.7
102.5°	176.0	176.2	176.2	175.9	175.7	175.5	175.2
105°	227.4	227.8	228.1	228.1	228.1	228.1	228.1
107.5°	282.2	282.4	281.9	280.9	279.9	278.8	277.7
110°	319.5	319.5	319.1	318.5	317.7	317.0	316.4



TEST NUMBER: P331484-927

CATALOG NUMBER: S122DIW-S290D1240U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	356.4	355.8	355.4	354.8	354.3	353.9	353.3
115°	414.3	414.1	413.6	413.0	412.3	411.5	410.9
117.5°	469.6	469.1	468.5	467.8	467.1	466.4	465.7
120°	507.4	507.4	507.1	506.4	505.7	505.0	504.4
122.5°	545.3	544.7	544.2	543.7	543.1	542.6	542.2
125°	601.9	601.3	600.8	600.6	600.3	600.1	599.8
127.5°	657.0	656.2	655.4	654.7	653.9	653.2	652.4
130°	695.1	694.6	694.0	693.0	692.1	691.2	690.2
132.5°	731.2	730.2	729.4	728.6	727.9	727.1	726.4
135°	786.2	785.9	785.4	784.7	784.1	783.4	782.7
137.5°	838.0	837.9	837.3	836.4	835.5	834.6	833.7
140°	873.1	873.1	872.7	871.7	870.8	869.9	869.0
142.5°	904.9	905.1	904.7	903.8	902.9	902.0	901.0
145°	952.9	953.1	952.8	951.9	950.9	950.1	949.1
147.5°	995.2	995.7	995.5	994.7	993.8	992.9	992.0
150°	1022.1	1022.7	1022.7	1022.1	1021.4	1020.6	1020.0
152.5°	1048.8	1049.7	1049.7	1048.8	1048.1	1047.2	1046.3
155°	1083.0	1084.1	1084.3	1083.7	1083.0	1082.3	1081.6
157.5°	1114.6	1116.2	1116.4	1115.3	1114.2	1113.1	1112.0
160°	1133.0	1134.3	1134.6	1133.7	1132.7	1131.9	1130.9
162.5°	1149.9	1151.5	1151.8	1150.6	1149.5	1148.4	1147.4
165°	1171.6	1173.3	1173.5	1172.4	1171.2	1170.1	1168.9
167.5°	1189.5	1191.1	1191.4	1190.2	1189.0	1187.8	1186.6
170°	1199.4	1201.0	1201.1	1199.8	1198.4	1197.0	1195.6
172.5°	1206.8	1208.4	1208.5	1207.1	1205.8	1204.4	1203.0
175°	1214.8	1216.4	1216.6	1215.1	1213.8	1212.4	1211.0
177.5°	1218.1	1219.1	1219.1	1218.1	1217.0	1215.8	1214.7
180°	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2

(END OF REPORT)