

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331531-927

Luminaire Tested: **S122DIW-S675D710U927-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331531-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S675D710U927-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 710 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4569.3 lumens
Efficiency: N/A
Efficacy: 101.5 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331531-927

CATALOG NUMBER: S122DIW-S675D710U927-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331531-927

CATALOG NUMBER: S122DIW-S675D710U927-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	98	94	91	87	91	87	84	81	74	72	70	62	61	59	51	50	49	44
2	90	83	77	72	83	77	72	67	66	62	59	55	52	50	46	44	42	37
3	82	73	66	61	76	68	62	57	58	54	50	49	46	43	41	38	36	32
4	76	65	58	52	70	61	54	49	52	47	43	44	40	37	37	34	32	28
5	70	58	50	45	64	54	47	42	47	41	37	40	36	33	33	30	28	25
6	64	53	45	39	59	49	42	37	42	37	33	36	32	29	30	27	25	22
7	60	48	40	34	55	45	38	33	39	33	29	33	29	26	28	25	22	20
8	55	43	36	31	51	41	34	29	35	30	26	30	26	23	26	23	20	18
9	52	40	32	27	48	37	31	26	33	27	23	28	24	21	24	21	18	16
10	48	37	29	25	45	34	28	24	30	25	21	26	22	19	22	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	16990	16990	16990	16990
5°	19047	17099	15152	17099
10°	21827	16959	13114	16959
15°	24145	16649	11587	16649
20°	23778	16314	10562	16314
25°	21440	15871	9912	15871
30°	17717	15163	9439	15163
35°	12912	14420	9102	14420
40°	10313	13544	8916	13544
45°	9012	12529	8661	12529
50°	8470	11549	8493	11549
55°	7809	10553	8265	10553
60°	7156	9494	7915	9494
65°	6518	8542	7568	8542
70°	5915	7619	7062	7619
75°	5246	6581	6257	6581
80°	4519	5449	5040	5449
85°	4057	4057	3001	4057



TEST NUMBER: P331531-927

CATALOG NUMBER: S122DIW-S675D710U927-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.2	2.2
10°-20°	291.3	6.4
20°-30°	422.8	9.3
30°-40°	446.2	9.8
40°-50°	395.0	8.6
50°-60°	315.3	6.9
60°-70°	214.3	4.7
70°-80°	109.9	2.4
80°-90°	28.4	0.6
90°-100°	25.6	0.6
100°-110°	93.8	2.1
110°-120°	250.6	5.5
120°-130°	413.7	9.1
130°-140°	440.0	9.6
140°-150°	408.9	8.9
150°-160°	328.8	7.2
160°-170°	211.9	4.6
170°-180°	72.9	1.6
0°-30°	814.3	17.8
0°-40°	1260.5	27.6
0°-60°	1970.8	43.1
0°-90°	2323.3	50.8
90°-120°	369.9	8.1
90°-150°	1632.5	35.7
90°-180°	2246.0	49.2
0°-180°	4569.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1052	1052	1052	1052	1052	
5°	1175	1055	935	1055	1175	117
15°	1444	996	693	996	1444	399
25°	1204	891	556	891	1204	544
35°	655	732	462	732	655	426
45°	395	549	379	549	395	310
55°	277	375	294	375	277	249
65°	171	224	198	224	171	170
75°	84	106	100	106	84	90
85°	22	22	16	22	22	24
90°	15	1	15	1	15	8
95°	24	36	24	36	24	22
105°	42	169	42	169	42	44
115°	46	319	46	319	46	114
125°	474	451	474	451	474	410
135°	576	558	576	558	576	444
145°	657	647	657	647	657	411
155°	713	713	713	713	713	329
165°	749	751	749	751	749	212
175°	764	768	764	768	764	73
180°	766	766	766	766	766	



TEST NUMBER: P331531-927

CATALOG NUMBER: S122DIW-S675D710U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3
2.5°	1100.7	1101.1	1101.8	1096.5	1095.9	1095.9	1091.4	1087.5	1083.0	1076.8	1077.4
5°	1175.2	1179.6	1181.2	1176.4	1169.1	1168.3	1161.4	1150.1	1139.6	1131.1	1125.1
7.5°	1264.0	1265.7	1261.8	1255.4	1250.0	1240.3	1227.5	1215.0	1197.4	1181.3	1169.3
10°	1331.3	1333.7	1326.8	1317.6	1309.9	1298.5	1279.9	1260.9	1237.9	1215.6	1197.8
12.5°	1382.4	1388.4	1379.6	1378.3	1365.2	1349.6	1327.5	1317.9	1285.4	1254.4	1235.3
15°	1444.5	1444.1	1444.9	1437.3	1427.5	1425.1	1401.6	1376.2	1330.5	1312.2	1280.7
17.5°	1426.6	1432.7	1435.5	1435.4	1435.2	1433.7	1426.2	1410.1	1387.2	1357.6	1321.2
20°	1383.9	1391.9	1393.1	1402.5	1407.7	1414.6	1417.4	1412.9	1398.8	1374.1	1342.6
22.5°	1317.9	1320.1	1323.9	1338.4	1349.8	1367.0	1376.0	1391.0	1385.5	1373.5	1347.1
25°	1203.5	1199.4	1213.6	1220.8	1247.1	1274.6	1294.5	1316.3	1335.7	1347.4	1339.7
27.5°	1066.1	1060.1	1081.2	1100.6	1122.0	1151.8	1182.6	1219.1	1249.4	1287.4	1300.4
30°	950.3	953.9	974.2	994.8	1027.1	1069.2	1104.0	1144.1	1187.3	1229.8	1259.3
32.5°	825.5	839.5	852.2	883.8	912.3	959.3	1010.2	1060.3	1114.2	1162.4	1208.2
35°	655.1	671.3	689.1	712.2	752.2	798.7	848.4	915.9	989.6	1055.5	1109.7
37.5°	551.4	548.8	559.0	575.7	608.2	645.6	702.9	769.7	856.3	933.7	1010.2
40°	489.3	487.7	495.0	510.3	535.0	562.5	612.7	671.3	751.8	846.4	937.4
42.5°	446.6	447.6	451.6	462.5	479.3	502.0	539.6	589.5	663.1	752.3	850.0
45°	394.7	397.5	402.0	407.3	416.9	435.5	456.5	492.2	550.4	624.8	721.0
47.5°	357.4	357.4	361.9	366.5	372.3	382.8	400.0	422.2	463.3	523.9	606.7
50°	337.2	334.5	337.7	341.3	347.4	354.7	366.0	387.0	414.5	463.4	532.6
52.5°	312.7	312.8	315.7	317.0	322.5	329.7	340.1	354.7	379.5	417.8	474.7
55°	277.4	279.4	281.1	283.4	288.4	293.6	301.7	311.4	330.8	359.5	401.6
57.5°	244.2	244.9	246.5	251.1	254.2	259.0	266.7	275.5	288.2	309.4	341.0
60°	221.6	221.6	224.8	226.9	230.9	235.8	241.9	250.3	261.7	279.0	304.5
62.5°	200.9	200.6	201.8	205.2	208.3	212.8	218.9	226.1	236.7	252.2	273.1
65°	170.6	169.8	172.3	173.1	176.3	180.8	185.6	193.3	201.8	213.1	231.7
67.5°	141.6	142.5	143.8	145.4	147.1	151.8	155.0	160.5	167.6	177.1	189.6
70°	125.3	125.3	125.3	126.6	129.0	131.4	134.7	139.1	146.0	154.1	165.4
72.5°	107.3	108.5	109.8	109.1	112.2	113.6	117.5	120.0	126.6	131.7	141.8
75°	84.1	84.1	84.1	86.1	87.4	88.6	91.0	93.4	96.6	103.1	108.4
77.5°	62.7	62.6	63.0	63.5	64.8	66.2	66.9	69.2	72.2	75.1	79.6
80°	48.6	49.4	49.7	50.5	50.5	51.3	51.7	54.6	56.6	58.6	61.5
82.5°	37.5	37.7	37.8	37.9	38.3	38.7	39.8	40.7	41.4	43.1	45.3
85°	21.9	21.5	21.5	22.3	21.9	21.9	22.7	23.4	23.4	23.8	25.0
87.5°	11.4	11.3	11.6	11.2	11.2	11.4	11.3	10.9	11.1	11.2	11.4
90°	15.0	14.7	14.5	14.3	14.0	13.5	12.9	12.4	11.7	11.1	10.1
92.5°	15.0	14.8	14.7	14.5	14.4	14.2	13.9	13.5	13.2	12.8	12.4
95°	23.8	24.0	24.1	24.2	24.3	24.1	23.4	22.9	22.3	21.6	20.8
97.5°	31.8	31.7	31.5	31.4	31.2	30.9	30.4	29.9	29.5	28.9	26.9
100°	37.2	36.9	36.7	36.4	36.2	35.6	34.5	33.6	32.6	31.6	29.5
102.5°	39.8	39.5	39.1	38.8	38.4	37.6	36.4	35.1	33.7	32.5	50.0
105°	42.1	41.7	41.2	40.6	40.2	39.2	37.9	36.5	35.2	33.8	67.5
107.5°	43.3	42.9	42.4	41.9	41.4	41.8	43.3	44.6	45.9	47.4	87.7
110°	43.8	43.3	42.9	42.3	41.8	47.8	60.0	72.4	84.8	97.0	132.7



TEST NUMBER: P331531-927

CATALOG NUMBER: S122DIW-S675D710U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	44.3	43.9	43.5	43.1	42.7	65.0	110.0	154.9	199.9	244.8	253.6
115°	45.5	54.3	63.2	72.1	81.0	113.9	171.0	228.1	285.1	342.1	339.1
117.5°	185.7	214.8	244.0	273.1	302.3	323.8	337.5	351.4	365.2	379.0	376.8
120°	338.3	354.9	371.5	388.2	404.8	412.4	410.9	409.5	408.0	406.5	404.3
122.5°	422.2	425.4	428.6	431.8	435.1	436.3	435.3	434.4	433.6	432.7	430.2
125°	474.1	473.8	473.4	473.0	472.7	472.1	471.2	470.3	469.4	468.6	466.3
127.5°	507.0	506.9	506.8	506.8	506.7	506.0	504.8	503.5	502.2	501.0	499.2
130°	527.4	527.5	527.7	527.8	527.9	527.3	525.9	524.6	523.2	521.9	520.5
132.5°	547.4	547.5	547.6	547.7	547.9	547.3	546.2	545.0	543.8	542.7	541.4
135°	576.2	576.5	576.7	576.9	577.2	576.7	575.4	574.3	573.0	571.8	570.7
137.5°	602.5	602.9	603.3	603.7	604.2	603.8	602.5	601.3	600.2	599.0	597.7
140°	618.9	619.5	620.1	620.8	621.4	621.2	620.0	618.9	617.8	616.7	615.3
142.5°	634.9	635.5	636.1	636.8	637.3	637.2	636.1	635.1	634.1	633.1	631.5
145°	657.2	657.7	658.4	659.0	659.7	659.5	658.6	657.7	657.0	656.1	653.9
147.5°	676.8	677.3	677.9	678.3	678.9	678.8	678.2	677.6	676.9	676.2	674.1
150°	688.8	689.4	690.0	690.6	691.3	691.2	690.5	689.7	689.0	688.2	686.3
152.5°	698.9	699.8	700.6	701.4	702.3	702.3	701.6	700.8	700.1	699.3	697.4
155°	713.2	714.2	715.2	716.1	717.1	717.2	716.5	715.7	715.0	714.3	712.8
157.5°	726.1	727.1	728.1	729.0	730.0	730.1	729.2	728.4	727.5	726.7	725.6
160°	733.7	734.6	735.4	736.3	737.1	737.2	736.5	735.7	735.0	734.3	733.5
162.5°	739.9	740.9	742.0	743.1	744.2	744.3	743.4	742.6	741.7	740.9	740.3
165°	749.2	750.1	751.0	751.8	752.7	752.7	751.8	751.0	750.1	749.2	748.8
167.5°	755.1	756.2	757.3	758.4	759.5	759.6	758.8	758.0	757.1	756.2	755.9
170°	758.7	759.8	760.9	762.0	763.1	763.2	762.3	761.5	760.7	759.8	759.5
172.5°	761.3	762.4	763.5	764.6	765.7	765.9	765.0	764.1	763.3	762.4	762.2
175°	763.7	764.9	766.1	767.3	768.6	768.7	767.9	767.1	766.2	765.3	765.1
177.5°	765.1	766.0	766.8	767.8	768.7	768.7	768.0	767.4	766.7	766.0	765.9
180°	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4



TEST NUMBER: P331531-927

CATALOG NUMBER: S122DIW-S675D710U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3
2.5°	1079.7	1077.1	1075.5	1069.7	1064.5	1059.4	1057.7	1058.4	1051.3	1044.5	1041.6
5°	1121.8	1113.7	1106.0	1095.1	1082.2	1068.0	1060.7	1055.0	1040.9	1025.6	1016.7
7.5°	1159.5	1148.0	1133.1	1112.5	1093.8	1071.5	1057.3	1044.8	1024.1	1002.4	989.1
10°	1182.5	1166.6	1147.6	1122.6	1099.5	1072.5	1053.4	1034.4	1010.2	984.3	968.1
12.5°	1202.2	1180.9	1162.2	1130.0	1102.8	1068.9	1046.3	1019.5	994.0	963.3	947.5
15°	1249.2	1210.0	1174.3	1138.0	1104.4	1057.1	1032.1	996.0	962.4	924.5	906.3
17.5°	1285.5	1241.4	1185.3	1139.1	1099.9	1047.6	1010.7	967.7	928.0	884.5	859.8
20°	1306.2	1255.6	1195.4	1140.4	1093.4	1033.6	993.6	949.5	903.0	854.1	827.4
22.5°	1318.5	1265.4	1205.8	1135.5	1080.5	1022.3	971.9	923.6	876.5	823.7	795.7
25°	1322.4	1273.8	1210.8	1131.5	1064.4	998.5	937.8	890.9	833.9	784.5	743.7
27.5°	1303.1	1268.4	1207.7	1123.9	1045.7	968.6	901.0	847.9	787.7	734.1	693.1
30°	1279.5	1259.3	1200.2	1116.1	1030.8	947.9	873.5	813.3	753.4	699.2	657.1
32.5°	1242.9	1238.6	1186.7	1105.1	1014.9	921.7	844.7	783.8	717.5	664.2	624.2
35°	1171.2	1190.6	1157.8	1080.5	985.1	884.4	801.1	731.6	662.8	611.9	574.3
37.5°	1074.9	1123.1	1114.5	1044.6	944.8	843.8	751.9	679.1	613.6	562.2	525.3
40°	1008.5	1070.0	1079.0	1017.1	916.4	812.5	714.9	642.6	578.7	531.8	494.6
42.5°	937.4	1009.2	1033.6	984.0	885.3	779.4	682.0	607.0	543.8	498.1	465.2
45°	818.1	913.1	957.2	928.9	833.5	725.1	624.8	548.7	491.3	448.5	423.0
47.5°	706.5	810.4	869.7	859.7	775.8	668.4	569.3	496.4	440.5	406.2	383.4
50°	627.6	734.4	806.0	809.2	734.4	628.0	528.5	459.8	408.4	376.5	357.9
52.5°	559.0	660.9	739.0	756.1	688.1	586.0	492.0	423.6	378.3	349.0	332.3
55°	469.5	555.6	642.1	673.8	619.1	522.0	435.1	374.9	332.4	312.2	297.6
57.5°	390.3	462.2	542.1	576.9	543.3	460.2	378.7	326.4	291.9	274.2	263.0
60°	348.6	405.2	476.3	518.0	488.9	414.9	343.7	294.0	265.7	249.9	239.4
62.5°	309.7	359.9	420.1	458.2	442.4	372.6	308.8	264.9	240.4	225.6	218.1
65°	255.6	295.2	341.7	376.9	366.4	313.4	261.3	223.6	204.2	192.5	186.4
67.5°	210.5	239.1	271.3	302.1	293.7	256.1	214.3	185.0	170.5	160.4	156.8
70°	182.0	203.8	232.5	257.2	250.3	219.6	186.4	161.4	148.9	140.3	136.7
72.5°	154.8	172.8	194.6	214.8	210.2	184.7	157.0	138.1	128.4	120.6	117.6
75°	116.8	130.6	143.9	157.3	156.1	136.3	120.1	105.5	97.8	91.8	90.5
77.5°	86.3	94.0	103.1	111.0	108.8	97.4	84.8	76.4	70.7	66.7	66.1
80°	65.9	70.3	76.8	82.5	79.7	74.8	64.7	58.6	54.6	50.5	49.0
82.5°	47.8	52.3	56.2	59.2	57.0	52.5	46.3	42.1	39.7	37.0	36.3
85°	25.0	27.5	29.2	29.9	29.2	26.3	23.4	21.9	19.8	18.6	18.2
87.5°	11.6	11.3	11.2	11.6	10.3	10.1	8.5	7.2	7.2	7.1	6.7
90°	9.1	8.2	7.1	5.9	4.6	3.2	1.9	0.6	1.9	3.2	4.6
92.5°	11.9	11.4	10.9	10.7	10.9	10.9	11.1	11.2	11.1	10.9	10.9
95°	19.9	19.0	18.1	19.8	23.8	27.9	32.0	36.0	32.0	27.9	23.8
97.5°	25.0	23.0	21.0	25.7	37.2	48.6	60.0	71.5	60.0	48.6	37.2
100°	27.4	25.3	23.2	30.7	47.5	64.4	81.3	98.2	81.3	64.4	47.5
102.5°	67.6	85.1	102.6	113.1	116.7	120.3	123.9	127.5	123.9	120.3	116.7
105°	101.1	134.8	168.4	183.4	179.7	176.0	172.3	168.6	172.3	176.0	179.7
107.5°	128.1	168.4	208.7	227.4	224.4	221.5	218.5	215.5	218.5	221.5	224.4
110°	168.3	203.9	239.5	256.0	253.4	250.9	248.3	245.7	248.3	250.9	253.4



TEST NUMBER: P331531-927

CATALOG NUMBER: S122DIW-S675D710U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	262.4	271.2	280.0	283.2	280.9	278.7	276.4	274.1	276.4	278.7	280.9
115°	336.0	333.0	329.9	327.3	325.2	323.1	321.0	318.9	321.0	323.1	325.2
117.5°	374.8	372.6	370.5	368.3	365.9	363.6	361.2	358.9	361.2	363.6	365.9
120°	402.0	399.8	397.6	395.6	393.7	391.9	390.1	388.2	390.1	391.9	393.7
122.5°	427.9	425.4	423.0	420.8	418.9	416.9	415.0	413.0	415.0	416.9	418.9
125°	463.9	461.6	459.2	457.2	455.7	454.1	452.5	450.8	452.5	454.1	455.7
127.5°	497.5	495.7	494.0	492.3	490.4	488.7	486.9	485.1	486.9	488.7	490.4
130°	519.1	517.8	516.4	514.8	512.8	510.8	508.8	506.8	508.8	510.8	512.8
132.5°	540.0	538.6	537.3	535.8	534.1	532.4	530.8	529.1	530.8	532.4	534.1
135°	569.6	568.5	567.4	565.8	563.8	561.8	559.8	557.9	559.8	561.8	563.8
137.5°	596.4	595.2	593.9	592.6	591.2	589.9	588.4	587.1	588.4	589.9	591.2
140°	613.9	612.6	611.2	610.1	609.1	608.1	607.1	606.2	607.1	608.1	609.1
142.5°	630.0	628.4	626.9	625.7	624.8	623.9	623.0	622.1	623.0	623.9	624.8
145°	651.9	649.7	647.7	646.7	646.8	647.0	647.1	647.2	647.1	647.0	646.8
147.5°	672.1	670.0	668.0	667.2	667.7	668.1	668.6	669.0	668.6	668.1	667.7
150°	684.3	682.3	680.3	679.8	680.6	681.5	682.4	683.3	682.4	681.5	680.6
152.5°	695.5	693.7	691.8	691.3	692.3	693.3	694.3	695.2	694.3	693.3	692.3
155°	711.3	709.9	708.4	708.2	709.3	710.4	711.5	712.6	711.5	710.4	709.3
157.5°	724.6	723.6	722.5	722.5	723.4	724.4	725.3	726.3	725.3	724.4	723.4
160°	732.8	732.1	731.3	731.3	732.1	732.8	733.5	734.3	733.5	732.8	732.1
162.5°	739.7	738.9	738.3	738.4	739.1	739.9	740.6	741.3	740.6	739.9	739.1
165°	748.5	748.1	747.7	747.9	748.7	749.4	750.1	750.9	750.1	749.4	748.7
167.5°	755.5	755.2	754.9	755.0	755.7	756.5	757.2	758.0	757.2	756.5	755.7
170°	759.3	759.0	758.8	759.0	759.8	760.5	761.2	762.0	761.2	760.5	759.8
172.5°	761.9	761.7	761.4	761.7	762.4	763.2	763.9	764.6	763.9	763.2	762.4
175°	764.9	764.5	764.3	764.6	765.5	766.4	767.2	768.1	767.2	766.4	765.5
177.5°	765.8	765.6	765.6	765.9	766.6	767.2	767.9	768.7	767.9	767.2	766.6
180°	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4



TEST NUMBER: P331531-927

CATALOG NUMBER: S122DIW-S675D710U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3
2.5°	1038.3	1036.4	1029.6	1026.0	1020.2	1014.7	1011.1	1012.8	1014.1	1013.4	1012.4
5°	1008.5	1000.8	989.1	979.1	971.8	958.4	952.8	949.9	947.5	944.7	941.8
7.5°	973.1	961.0	944.2	929.8	916.2	899.6	890.2	884.5	878.7	872.3	866.6
10°	947.9	930.9	913.1	892.9	876.7	861.7	848.4	839.6	831.5	823.8	818.1
12.5°	921.4	901.8	879.8	852.2	834.3	812.9	810.9	795.2	782.6	777.8	771.2
15°	879.2	851.7	823.8	791.0	776.8	757.4	745.3	733.2	722.2	714.5	712.6
17.5°	831.2	795.6	767.9	744.3	721.1	701.2	690.1	680.3	671.4	661.1	659.7
20°	794.6	763.9	733.6	713.0	689.1	668.8	655.1	645.4	637.7	631.7	626.4
22.5°	760.0	726.4	698.6	676.0	652.5	636.2	625.3	616.0	609.6	602.9	597.9
25°	704.5	678.2	647.8	622.3	602.9	592.5	583.5	575.4	571.4	567.0	561.3
27.5°	655.8	626.6	598.3	578.5	561.5	552.2	545.8	540.3	536.5	533.9	530.8
30°	621.5	592.0	569.8	550.4	536.2	527.0	522.9	519.7	515.2	513.6	512.0
32.5°	588.6	562.0	543.0	526.1	512.6	506.5	502.8	499.9	496.5	494.8	491.5
35°	541.9	519.7	501.1	491.7	480.9	475.5	472.8	468.7	465.5	463.8	463.4
37.5°	498.0	478.6	466.4	454.5	449.9	446.6	442.8	440.0	439.0	438.8	438.4
40°	469.5	453.8	442.8	433.1	431.1	426.2	423.0	420.6	420.6	421.0	420.6
42.5°	443.6	429.4	419.9	411.5	409.1	406.2	402.9	402.7	403.5	404.8	403.5
45°	404.4	394.3	387.4	383.3	378.9	376.0	375.7	376.9	377.3	377.7	378.9
47.5°	368.3	361.6	355.4	350.9	349.0	348.5	348.0	350.1	352.0	352.8	354.7
50°	347.0	339.3	334.1	331.2	329.5	328.8	329.5	332.0	333.6	335.6	336.8
52.5°	323.1	317.6	313.9	311.8	311.2	311.6	311.8	314.6	317.1	317.8	318.5
55°	289.9	285.9	285.1	281.5	283.0	282.7	284.7	286.3	288.8	291.1	291.6
57.5°	257.0	253.7	251.5	251.8	252.3	254.1	255.8	258.6	261.3	263.8	264.0
60°	235.0	233.3	232.1	232.1	232.9	235.4	237.4	240.2	241.9	243.4	244.6
62.5°	214.9	213.3	212.1	212.7	214.8	216.3	218.6	220.1	221.7	223.4	223.9
65°	183.2	182.4	183.6	184.4	184.8	186.8	189.6	190.8	192.5	193.3	196.1
67.5°	154.0	154.2	154.0	155.1	157.5	158.0	160.7	163.4	163.7	165.3	167.2
70°	134.3	135.1	135.9	136.7	138.7	139.5	141.6	142.8	144.3	145.6	146.8
72.5°	116.1	116.3	117.1	116.9	118.7	120.4	122.2	123.3	124.9	126.5	127.7
75°	89.4	89.4	90.2	90.5	92.6	94.7	94.2	95.1	96.6	98.2	99.1
77.5°	65.3	64.4	65.3	65.7	66.3	68.0	68.4	69.5	71.3	70.7	71.7
80°	49.7	48.6	49.7	50.1	50.1	52.2	52.2	53.0	54.2	53.0	54.2
82.5°	35.5	34.9	35.8	35.9	36.5	36.6	37.3	37.5	38.7	38.1	38.7
85°	17.8	17.4	17.8	17.4	17.8	18.2	18.2	17.8	17.8	18.6	17.4
87.5°	6.7	6.6	6.5	6.7	6.6	6.4	6.3	6.3	6.5	5.9	6.0
90°	5.9	7.1	8.2	9.1	10.1	11.1	11.7	12.4	12.9	13.5	14.0
92.5°	10.7	10.9	11.4	11.9	12.4	12.8	13.2	13.5	13.9	14.2	14.4
95°	19.8	18.1	19.0	19.9	20.8	21.6	22.3	22.9	23.4	24.1	24.3
97.5°	25.7	21.0	23.0	25.0	26.9	28.9	29.5	29.9	30.4	30.9	31.2
100°	30.7	23.2	25.3	27.4	29.5	31.6	32.6	33.6	34.5	35.6	36.2
102.5°	113.1	102.6	85.1	67.6	50.0	32.5	33.7	35.1	36.4	37.6	38.4
105°	183.4	168.4	134.8	101.1	67.5	33.8	35.2	36.5	37.9	39.2	40.2
107.5°	227.4	208.7	168.4	128.1	87.7	47.4	45.9	44.6	43.3	41.8	41.4
110°	256.0	239.5	203.9	168.3	132.7	97.0	84.8	72.4	60.0	47.8	41.8



TEST NUMBER: P331531-927

CATALOG NUMBER: S122DIW-S675D710U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	283.2	280.0	271.2	262.4	253.6	244.8	199.9	154.9	110.0	65.0	42.7
115°	327.3	329.9	333.0	336.0	339.1	342.1	285.1	228.1	171.0	113.9	81.0
117.5°	368.3	370.5	372.6	374.8	376.8	379.0	365.2	351.4	337.5	323.8	302.3
120°	395.6	397.6	399.8	402.0	404.3	406.5	408.0	409.5	410.9	412.4	404.8
122.5°	420.8	423.0	425.4	427.9	430.2	432.7	433.6	434.4	435.3	436.3	435.1
125°	457.2	459.2	461.6	463.9	466.3	468.6	469.4	470.3	471.2	472.1	472.7
127.5°	492.3	494.0	495.7	497.5	499.2	501.0	502.2	503.5	504.8	506.0	506.7
130°	514.8	516.4	517.8	519.1	520.5	521.9	523.2	524.6	525.9	527.3	527.9
132.5°	535.8	537.3	538.6	540.0	541.4	542.7	543.8	545.0	546.2	547.3	547.9
135°	565.8	567.4	568.5	569.6	570.7	571.8	573.0	574.3	575.4	576.7	577.2
137.5°	592.6	593.9	595.2	596.4	597.7	599.0	600.2	601.3	602.5	603.8	604.2
140°	610.1	611.2	612.6	613.9	615.3	616.7	617.8	618.9	620.0	621.2	621.4
142.5°	625.7	626.9	628.4	630.0	631.5	633.1	634.1	635.1	636.1	637.2	637.3
145°	646.7	647.7	649.7	651.9	653.9	656.1	657.0	657.7	658.6	659.5	659.7
147.5°	667.2	668.0	670.0	672.1	674.1	676.2	676.9	677.6	678.2	678.8	678.9
150°	679.8	680.3	682.3	684.3	686.3	688.2	689.0	689.7	690.5	691.2	691.3
152.5°	691.3	691.8	693.7	695.5	697.4	699.3	700.1	700.8	701.6	702.3	702.3
155°	708.2	708.4	709.9	711.3	712.8	714.3	715.0	715.7	716.5	717.2	717.1
157.5°	722.5	722.5	723.6	724.6	725.6	726.7	727.5	728.4	729.2	730.1	730.0
160°	731.3	731.3	732.1	732.8	733.5	734.3	735.0	735.7	736.5	737.2	737.1
162.5°	738.4	738.3	738.9	739.7	740.3	740.9	741.7	742.6	743.4	744.3	744.2
165°	747.9	747.7	748.1	748.5	748.8	749.2	750.1	751.0	751.8	752.7	752.7
167.5°	755.0	754.9	755.2	755.5	755.9	756.2	757.1	758.0	758.8	759.6	759.5
170°	759.0	758.8	759.0	759.3	759.5	759.8	760.7	761.5	762.3	763.2	763.1
172.5°	761.7	761.4	761.7	761.9	762.2	762.4	763.3	764.1	765.0	765.9	765.7
175°	764.6	764.3	764.5	764.9	765.1	765.3	766.2	767.1	767.9	768.7	768.6
177.5°	765.9	765.6	765.6	765.8	765.9	766.0	766.7	767.4	768.0	768.7	768.7
180°	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4



TEST NUMBER: P331531-927

CATALOG NUMBER: S122DIW-S675D710U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3
2.5°	1009.2	1008.5	1008.5	1005.7	1008.5	1008.5	1009.2	1012.4	1013.4	1014.1	1012.8
5°	936.2	934.9	933.0	934.9	933.0	934.9	936.2	941.8	944.7	947.5	949.9
7.5°	864.0	859.1	858.4	853.6	858.4	859.1	864.0	866.6	872.3	878.7	884.5
10°	811.2	807.9	807.6	799.9	807.6	807.9	811.2	818.1	823.8	831.5	839.6
12.5°	771.1	763.3	764.9	760.4	764.9	763.3	771.1	771.2	777.8	782.6	795.2
15°	701.6	701.6	700.0	693.2	700.0	701.6	701.6	712.6	714.5	722.2	733.2
17.5°	651.7	650.9	647.1	649.0	647.1	650.9	651.7	659.7	661.1	671.4	680.3
20°	621.9	619.6	614.7	614.7	614.7	619.6	621.9	626.4	631.7	637.7	645.4
22.5°	593.8	593.7	588.5	590.1	588.5	593.7	593.8	597.9	602.9	609.6	616.0
25°	560.9	557.7	555.2	556.4	555.2	557.7	560.9	561.3	567.0	571.4	575.4
27.5°	529.7	527.9	527.8	524.4	527.8	527.9	529.7	530.8	533.9	536.5	540.3
30°	511.6	507.6	508.3	506.3	508.3	507.6	511.6	512.0	513.6	515.2	519.7
32.5°	490.8	489.4	488.6	486.9	488.6	489.4	490.8	491.5	494.8	496.5	499.9
35°	462.6	463.0	461.1	461.8	461.1	463.0	462.6	463.4	463.8	465.5	468.7
37.5°	438.0	439.3	438.3	438.6	438.3	439.3	438.0	438.4	438.8	439.0	440.0
40°	421.8	421.8	421.8	423.0	421.8	421.8	421.8	420.6	421.0	420.6	420.6
42.5°	406.2	405.6	405.0	404.9	405.0	405.6	406.2	403.5	404.8	403.5	402.7
45°	379.7	381.0	381.4	379.3	381.4	381.0	379.7	378.9	377.7	377.3	376.9
47.5°	355.7	355.8	355.7	357.5	355.7	355.8	355.7	354.7	352.8	352.0	350.1
50°	338.9	338.1	338.9	338.1	338.9	338.1	338.9	336.8	335.6	333.6	332.0
52.5°	321.1	321.2	320.8	320.6	320.8	321.2	321.1	318.5	317.8	317.1	314.6
55°	293.2	294.0	293.6	293.6	293.6	294.0	293.2	291.6	291.1	288.8	286.3
57.5°	264.4	265.1	265.6	263.8	265.6	265.1	264.4	264.0	263.8	261.3	258.6
60°	244.2	246.3	245.9	245.1	245.9	246.3	244.2	244.6	243.4	241.9	240.2
62.5°	225.9	226.6	226.5	226.3	226.5	226.6	225.9	223.9	223.4	221.7	220.1
65°	197.3	198.1	196.9	198.1	196.9	198.1	197.3	196.1	193.3	192.5	190.8
67.5°	166.7	166.9	167.9	168.4	167.9	166.9	166.7	167.2	165.3	163.7	163.4
70°	147.6	147.2	148.4	149.6	148.4	147.2	147.6	146.8	145.6	144.3	142.8
72.5°	127.5	128.4	128.0	128.9	128.0	128.4	127.5	127.7	126.5	124.9	123.3
75°	98.2	99.5	99.1	100.3	99.1	99.5	98.2	99.1	98.2	96.6	95.1
77.5°	71.0	71.1	71.0	71.7	71.0	71.1	71.0	71.7	70.7	71.3	69.5
80°	54.2	53.4	52.6	54.2	52.6	53.4	54.2	54.2	53.0	54.2	53.0
82.5°	37.7	38.2	37.4	37.4	37.4	38.2	37.7	38.7	38.1	38.7	37.5
85°	17.4	17.0	16.2	16.2	16.2	17.0	17.4	17.4	18.6	17.8	17.8
87.5°	6.1	5.8	5.9	5.5	5.9	5.8	6.1	6.0	5.9	6.5	6.3
90°	14.3	14.5	14.7	15.0	14.7	14.5	14.3	14.0	13.5	12.9	12.4
92.5°	14.5	14.7	14.8	15.0	14.8	14.7	14.5	14.4	14.2	13.9	13.5
95°	24.2	24.1	24.0	23.8	24.0	24.1	24.2	24.3	24.1	23.4	22.9
97.5°	31.4	31.5	31.7	31.8	31.7	31.5	31.4	31.2	30.9	30.4	29.9
100°	36.4	36.7	36.9	37.2	36.9	36.7	36.4	36.2	35.6	34.5	33.6
102.5°	38.8	39.1	39.5	39.8	39.5	39.1	38.8	38.4	37.6	36.4	35.1
105°	40.6	41.2	41.7	42.1	41.7	41.2	40.6	40.2	39.2	37.9	36.5
107.5°	41.9	42.4	42.9	43.3	42.9	42.4	41.9	41.4	41.8	43.3	44.6
110°	42.3	42.9	43.3	43.8	43.3	42.9	42.3	41.8	47.8	60.0	72.4



TEST NUMBER: P331531-927

CATALOG NUMBER: S122DIW-S675D710U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	43.1	43.5	43.9	44.3	43.9	43.5	43.1	42.7	65.0	110.0	154.9
115°	72.1	63.2	54.3	45.5	54.3	63.2	72.1	81.0	113.9	171.0	228.1
117.5°	273.1	244.0	214.8	185.7	214.8	244.0	273.1	302.3	323.8	337.5	351.4
120°	388.2	371.5	354.9	338.3	354.9	371.5	388.2	404.8	412.4	410.9	409.5
122.5°	431.8	428.6	425.4	422.2	425.4	428.6	431.8	435.1	436.3	435.3	434.4
125°	473.0	473.4	473.8	474.1	473.8	473.4	473.0	472.7	472.1	471.2	470.3
127.5°	506.8	506.8	506.9	507.0	506.9	506.8	506.8	506.7	506.0	504.8	503.5
130°	527.8	527.7	527.5	527.4	527.5	527.7	527.8	527.9	527.3	525.9	524.6
132.5°	547.7	547.6	547.5	547.4	547.5	547.6	547.7	547.9	547.3	546.2	545.0
135°	576.9	576.7	576.5	576.2	576.5	576.7	576.9	577.2	576.7	575.4	574.3
137.5°	603.7	603.3	602.9	602.5	602.9	603.3	603.7	604.2	603.8	602.5	601.3
140°	620.8	620.1	619.5	618.9	619.5	620.1	620.8	621.4	621.2	620.0	618.9
142.5°	636.8	636.1	635.5	634.9	635.5	636.1	636.8	637.3	637.2	636.1	635.1
145°	659.0	658.4	657.7	657.2	657.7	658.4	659.0	659.7	659.5	658.6	657.7
147.5°	678.3	677.9	677.3	676.8	677.3	677.9	678.3	678.9	678.8	678.2	677.6
150°	690.6	690.0	689.4	688.8	689.4	690.0	690.6	691.3	691.2	690.5	689.7
152.5°	701.4	700.6	699.8	698.9	699.8	700.6	701.4	702.3	702.3	701.6	700.8
155°	716.1	715.2	714.2	713.2	714.2	715.2	716.1	717.1	717.2	716.5	715.7
157.5°	729.0	728.1	727.1	726.1	727.1	728.1	729.0	730.0	730.1	729.2	728.4
160°	736.3	735.4	734.6	733.7	734.6	735.4	736.3	737.1	737.2	736.5	735.7
162.5°	743.1	742.0	740.9	739.9	740.9	742.0	743.1	744.2	744.3	743.4	742.6
165°	751.8	751.0	750.1	749.2	750.1	751.0	751.8	752.7	752.7	751.8	751.0
167.5°	758.4	757.3	756.2	755.1	756.2	757.3	758.4	759.5	759.6	758.8	758.0
170°	762.0	760.9	759.8	758.7	759.8	760.9	762.0	763.1	763.2	762.3	761.5
172.5°	764.6	763.5	762.4	761.3	762.4	763.5	764.6	765.7	765.9	765.0	764.1
175°	767.3	766.1	764.9	763.7	764.9	766.1	767.3	768.6	768.7	767.9	767.1
177.5°	767.8	766.8	766.0	765.1	766.0	766.8	767.8	768.7	768.7	768.0	767.4
180°	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4



TEST NUMBER: P331531-927

CATALOG NUMBER: S122DIW-S675D710U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3
2.5°	1011.1	1014.7	1020.2	1026.0	1029.6	1036.4	1038.3	1041.6	1044.5	1051.3	1058.4
5°	952.8	958.4	971.8	979.1	989.1	1000.8	1008.5	1016.7	1025.6	1040.9	1055.0
7.5°	890.2	899.6	916.2	929.8	944.2	961.0	973.1	989.1	1002.4	1024.1	1044.8
10°	848.4	861.7	876.7	892.9	913.1	930.9	947.9	968.1	984.3	1010.2	1034.4
12.5°	810.9	812.9	834.3	852.2	879.8	901.8	921.4	947.5	963.3	994.0	1019.5
15°	745.3	757.4	776.8	791.0	823.8	851.7	879.2	906.3	924.5	962.4	996.0
17.5°	690.1	701.2	721.1	744.3	767.9	795.6	831.2	859.8	884.5	928.0	967.7
20°	655.1	668.8	689.1	713.0	733.6	763.9	794.6	827.4	854.1	903.0	949.5
22.5°	625.3	636.2	652.5	676.0	698.6	726.4	760.0	795.7	823.7	876.5	923.6
25°	583.5	592.5	602.9	622.3	647.8	678.2	704.5	743.7	784.5	833.9	890.9
27.5°	545.8	552.2	561.5	578.5	598.3	626.6	655.8	693.1	734.1	787.7	847.9
30°	522.9	527.0	536.2	550.4	569.8	592.0	621.5	657.1	699.2	753.4	813.3
32.5°	502.8	506.5	512.6	526.1	543.0	562.0	588.6	624.2	664.2	717.5	783.8
35°	472.8	475.5	480.9	491.7	501.1	519.7	541.9	574.3	611.9	662.8	731.6
37.5°	442.8	446.6	449.9	454.5	466.4	478.6	498.0	525.3	562.2	613.6	679.1
40°	423.0	426.2	431.1	433.1	442.8	453.8	469.5	494.6	531.8	578.7	642.6
42.5°	402.9	406.2	409.1	411.5	419.9	429.4	443.6	465.2	498.1	543.8	607.0
45°	375.7	376.0	378.9	383.3	387.4	394.3	404.4	423.0	448.5	491.3	548.7
47.5°	348.0	348.5	349.0	350.9	355.4	361.6	368.3	383.4	406.2	440.5	496.4
50°	329.5	328.8	329.5	331.2	334.1	339.3	347.0	357.9	376.5	408.4	459.8
52.5°	311.8	311.6	311.2	311.8	313.9	317.6	323.1	332.3	349.0	378.3	423.6
55°	284.7	282.7	283.0	281.5	285.1	285.9	289.9	297.6	312.2	332.4	374.9
57.5°	255.8	254.1	252.3	251.8	251.5	253.7	257.0	263.0	274.2	291.9	326.4
60°	237.4	235.4	232.9	232.1	232.1	233.3	235.0	239.4	249.9	265.7	294.0
62.5°	218.6	216.3	214.8	212.7	212.1	213.3	214.9	218.1	225.6	240.4	264.9
65°	189.6	186.8	184.8	184.4	183.6	182.4	183.2	186.4	192.5	204.2	223.6
67.5°	160.7	158.0	157.5	155.1	154.0	154.2	154.0	156.8	160.4	170.5	185.0
70°	141.6	139.5	138.7	136.7	135.9	135.1	134.3	136.7	140.3	148.9	161.4
72.5°	122.2	120.4	118.7	116.9	117.1	116.3	116.1	117.6	120.6	128.4	138.1
75°	94.2	94.7	92.6	90.5	90.2	89.4	89.4	90.5	91.8	97.8	105.5
77.5°	68.4	68.0	66.3	65.7	65.3	64.4	65.3	66.1	66.7	70.7	76.4
80°	52.2	52.2	50.1	50.1	49.7	48.6	49.7	49.0	50.5	54.6	58.6
82.5°	37.3	36.6	36.5	35.9	35.8	34.9	35.5	36.3	37.0	39.7	42.1
85°	18.2	18.2	17.8	17.4	17.8	17.4	17.8	18.2	18.6	19.8	21.9
87.5°	6.3	6.4	6.6	6.7	6.5	6.6	6.7	6.7	7.1	7.2	7.2
90°	11.7	11.1	10.1	9.1	8.2	7.1	5.9	4.6	3.2	1.9	0.6
92.5°	13.2	12.8	12.4	11.9	11.4	10.9	10.7	10.9	10.9	11.1	11.2
95°	22.3	21.6	20.8	19.9	19.0	18.1	19.8	23.8	27.9	32.0	36.0
97.5°	29.5	28.9	26.9	25.0	23.0	21.0	25.7	37.2	48.6	60.0	71.5
100°	32.6	31.6	29.5	27.4	25.3	23.2	30.7	47.5	64.4	81.3	98.2
102.5°	33.7	32.5	50.0	67.6	85.1	102.6	113.1	116.7	120.3	123.9	127.5
105°	35.2	33.8	67.5	101.1	134.8	168.4	183.4	179.7	176.0	172.3	168.6
107.5°	45.9	47.4	87.7	128.1	168.4	208.7	227.4	224.4	221.5	218.5	215.5
110°	84.8	97.0	132.7	168.3	203.9	239.5	256.0	253.4	250.9	248.3	245.7



TEST NUMBER: P331531-927

CATALOG NUMBER: S122DIW-S675D710U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	199.9	244.8	253.6	262.4	271.2	280.0	283.2	280.9	278.7	276.4	274.1
115°	285.1	342.1	339.1	336.0	333.0	329.9	327.3	325.2	323.1	321.0	318.9
117.5°	365.2	379.0	376.8	374.8	372.6	370.5	368.3	365.9	363.6	361.2	358.9
120°	408.0	406.5	404.3	402.0	399.8	397.6	395.6	393.7	391.9	390.1	388.2
122.5°	433.6	432.7	430.2	427.9	425.4	423.0	420.8	418.9	416.9	415.0	413.0
125°	469.4	468.6	466.3	463.9	461.6	459.2	457.2	455.7	454.1	452.5	450.8
127.5°	502.2	501.0	499.2	497.5	495.7	494.0	492.3	490.4	488.7	486.9	485.1
130°	523.2	521.9	520.5	519.1	517.8	516.4	514.8	512.8	510.8	508.8	506.8
132.5°	543.8	542.7	541.4	540.0	538.6	537.3	535.8	534.1	532.4	530.8	529.1
135°	573.0	571.8	570.7	569.6	568.5	567.4	565.8	563.8	561.8	559.8	557.9
137.5°	600.2	599.0	597.7	596.4	595.2	593.9	592.6	591.2	589.9	588.4	587.1
140°	617.8	616.7	615.3	613.9	612.6	611.2	610.1	609.1	608.1	607.1	606.2
142.5°	634.1	633.1	631.5	630.0	628.4	626.9	625.7	624.8	623.9	623.0	622.1
145°	657.0	656.1	653.9	651.9	649.7	647.7	646.7	646.8	647.0	647.1	647.2
147.5°	676.9	676.2	674.1	672.1	670.0	668.0	667.2	667.7	668.1	668.6	669.0
150°	689.0	688.2	686.3	684.3	682.3	680.3	679.8	680.6	681.5	682.4	683.3
152.5°	700.1	699.3	697.4	695.5	693.7	691.8	691.3	692.3	693.3	694.3	695.2
155°	715.0	714.3	712.8	711.3	709.9	708.4	708.2	709.3	710.4	711.5	712.6
157.5°	727.5	726.7	725.6	724.6	723.6	722.5	722.5	723.4	724.4	725.3	726.3
160°	735.0	734.3	733.5	732.8	732.1	731.3	731.3	732.1	732.8	733.5	734.3
162.5°	741.7	740.9	740.3	739.7	738.9	738.3	738.4	739.1	739.9	740.6	741.3
165°	750.1	749.2	748.8	748.5	748.1	747.7	747.9	748.7	749.4	750.1	750.9
167.5°	757.1	756.2	755.9	755.5	755.2	754.9	755.0	755.7	756.5	757.2	758.0
170°	760.7	759.8	759.5	759.3	759.0	758.8	759.0	759.8	760.5	761.2	762.0
172.5°	763.3	762.4	762.2	761.9	761.7	761.4	761.7	762.4	763.2	763.9	764.6
175°	766.2	765.3	765.1	764.9	764.5	764.3	764.6	765.5	766.4	767.2	768.1
177.5°	766.7	766.0	765.9	765.8	765.6	765.6	765.9	766.6	767.2	767.9	768.7
180°	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4



TEST NUMBER: P331531-927

CATALOG NUMBER: S122DIW-S675D710U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3
2.5°	1057.7	1059.4	1064.5	1069.7	1075.5	1077.1	1079.7	1077.4	1076.8	1083.0	1087.5
5°	1060.7	1068.0	1082.2	1095.1	1106.0	1113.7	1121.8	1125.1	1131.1	1139.6	1150.1
7.5°	1057.3	1071.5	1093.8	1112.5	1133.1	1148.0	1159.5	1169.3	1181.3	1197.4	1215.0
10°	1053.4	1072.5	1099.5	1122.6	1147.6	1166.6	1182.5	1197.8	1215.6	1237.9	1260.9
12.5°	1046.3	1068.9	1102.8	1130.0	1162.2	1180.9	1202.2	1235.3	1254.4	1285.4	1317.9
15°	1032.1	1057.1	1104.4	1138.0	1174.3	1210.0	1249.2	1280.7	1312.2	1330.5	1376.2
17.5°	1010.7	1047.6	1099.9	1139.1	1185.3	1241.4	1285.5	1321.2	1357.6	1387.2	1410.1
20°	993.6	1033.6	1093.4	1140.4	1195.4	1255.6	1306.2	1342.6	1374.1	1398.8	1412.9
22.5°	971.9	1022.3	1080.5	1135.5	1205.8	1265.4	1318.5	1347.1	1373.5	1385.5	1391.0
25°	937.8	998.5	1064.4	1131.5	1210.8	1273.8	1322.4	1339.7	1347.4	1335.7	1316.3
27.5°	901.0	968.6	1045.7	1123.9	1207.7	1268.4	1303.1	1300.4	1287.4	1249.4	1219.1
30°	873.5	947.9	1030.8	1116.1	1200.2	1259.3	1279.5	1259.3	1229.8	1187.3	1144.1
32.5°	844.7	921.7	1014.9	1105.1	1186.7	1238.6	1242.9	1208.2	1162.4	1114.2	1060.3
35°	801.1	884.4	985.1	1080.5	1157.8	1190.6	1171.2	1109.7	1055.5	989.6	915.9
37.5°	751.9	843.8	944.8	1044.6	1114.5	1123.1	1074.9	1010.2	933.7	856.3	769.7
40°	714.9	812.5	916.4	1017.1	1079.0	1070.0	1008.5	937.4	846.4	751.8	671.3
42.5°	682.0	779.4	885.3	984.0	1033.6	1009.2	937.4	850.0	752.3	663.1	589.5
45°	624.8	725.1	833.5	928.9	957.2	913.1	818.1	721.0	624.8	550.4	492.2
47.5°	569.3	668.4	775.8	859.7	869.7	810.4	706.5	606.7	523.9	463.3	422.2
50°	528.5	628.0	734.4	809.2	806.0	734.4	627.6	532.6	463.4	414.5	387.0
52.5°	492.0	586.0	688.1	756.1	739.0	660.9	559.0	474.7	417.8	379.5	354.7
55°	435.1	522.0	619.1	673.8	642.1	555.6	469.5	401.6	359.5	330.8	311.4
57.5°	378.7	460.2	543.3	576.9	542.1	462.2	390.3	341.0	309.4	288.2	275.5
60°	343.7	414.9	488.9	518.0	476.3	405.2	348.6	304.5	279.0	261.7	250.3
62.5°	308.8	372.6	442.4	458.2	420.1	359.9	309.7	273.1	252.2	236.7	226.1
65°	261.3	313.4	366.4	376.9	341.7	295.2	255.6	231.7	213.1	201.8	193.3
67.5°	214.3	256.1	293.7	302.1	271.3	239.1	210.5	189.6	177.1	167.6	160.5
70°	186.4	219.6	250.3	257.2	232.5	203.8	182.0	165.4	154.1	146.0	139.1
72.5°	157.0	184.7	210.2	214.8	194.6	172.8	154.8	141.8	131.7	126.6	120.0
75°	120.1	136.3	156.1	157.3	143.9	130.6	116.8	108.4	103.1	96.6	93.4
77.5°	84.8	97.4	108.8	111.0	103.1	94.0	86.3	79.6	75.1	72.2	69.2
80°	64.7	74.8	79.7	82.5	76.8	70.3	65.9	61.5	58.6	56.6	54.6
82.5°	46.3	52.5	57.0	59.2	56.2	52.3	47.8	45.3	43.1	41.4	40.7
85°	23.4	26.3	29.2	29.9	29.2	27.5	25.0	25.0	23.8	23.4	23.4
87.5°	8.5	10.1	10.3	11.6	11.2	11.3	11.6	11.4	11.2	11.1	10.9
90°	1.9	3.2	4.6	5.9	7.1	8.2	9.1	10.1	11.1	11.7	12.4
92.5°	11.1	10.9	10.9	10.7	10.9	11.4	11.9	12.4	12.8	13.2	13.5
95°	32.0	27.9	23.8	19.8	18.1	19.0	19.9	20.8	21.6	22.3	22.9
97.5°	60.0	48.6	37.2	25.7	21.0	23.0	25.0	26.9	28.9	29.5	29.9
100°	81.3	64.4	47.5	30.7	23.2	25.3	27.4	29.5	31.6	32.6	33.6
102.5°	123.9	120.3	116.7	113.1	102.6	85.1	67.6	50.0	32.5	33.7	35.1
105°	172.3	176.0	179.7	183.4	168.4	134.8	101.1	67.5	33.8	35.2	36.5
107.5°	218.5	221.5	224.4	227.4	208.7	168.4	128.1	87.7	47.4	45.9	44.6
110°	248.3	250.9	253.4	256.0	239.5	203.9	168.3	132.7	97.0	84.8	72.4



TEST NUMBER: P331531-927

CATALOG NUMBER: S122DIW-S675D710U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	276.4	278.7	280.9	283.2	280.0	271.2	262.4	253.6	244.8	199.9	154.9
115°	321.0	323.1	325.2	327.3	329.9	333.0	336.0	339.1	342.1	285.1	228.1
117.5°	361.2	363.6	365.9	368.3	370.5	372.6	374.8	376.8	379.0	365.2	351.4
120°	390.1	391.9	393.7	395.6	397.6	399.8	402.0	404.3	406.5	408.0	409.5
122.5°	415.0	416.9	418.9	420.8	423.0	425.4	427.9	430.2	432.7	433.6	434.4
125°	452.5	454.1	455.7	457.2	459.2	461.6	463.9	466.3	468.6	469.4	470.3
127.5°	486.9	488.7	490.4	492.3	494.0	495.7	497.5	499.2	501.0	502.2	503.5
130°	508.8	510.8	512.8	514.8	516.4	517.8	519.1	520.5	521.9	523.2	524.6
132.5°	530.8	532.4	534.1	535.8	537.3	538.6	540.0	541.4	542.7	543.8	545.0
135°	559.8	561.8	563.8	565.8	567.4	568.5	569.6	570.7	571.8	573.0	574.3
137.5°	588.4	589.9	591.2	592.6	593.9	595.2	596.4	597.7	599.0	600.2	601.3
140°	607.1	608.1	609.1	610.1	611.2	612.6	613.9	615.3	616.7	617.8	618.9
142.5°	623.0	623.9	624.8	625.7	626.9	628.4	630.0	631.5	633.1	634.1	635.1
145°	647.1	647.0	646.8	646.7	647.7	649.7	651.9	653.9	656.1	657.0	657.7
147.5°	668.6	668.1	667.7	667.2	668.0	670.0	672.1	674.1	676.2	676.9	677.6
150°	682.4	681.5	680.6	679.8	680.3	682.3	684.3	686.3	688.2	689.0	689.7
152.5°	694.3	693.3	692.3	691.3	691.8	693.7	695.5	697.4	699.3	700.1	700.8
155°	711.5	710.4	709.3	708.2	708.4	709.9	711.3	712.8	714.3	715.0	715.7
157.5°	725.3	724.4	723.4	722.5	722.5	723.6	724.6	725.6	726.7	727.5	728.4
160°	733.5	732.8	732.1	731.3	731.3	732.1	732.8	733.5	734.3	735.0	735.7
162.5°	740.6	739.9	739.1	738.4	738.3	738.9	739.7	740.3	740.9	741.7	742.6
165°	750.1	749.4	748.7	747.9	747.7	748.1	748.5	748.8	749.2	750.1	751.0
167.5°	757.2	756.5	755.7	755.0	754.9	755.2	755.5	755.9	756.2	757.1	758.0
170°	761.2	760.5	759.8	759.0	758.8	759.0	759.3	759.5	759.8	760.7	761.5
172.5°	763.9	763.2	762.4	761.7	761.4	761.7	761.9	762.2	762.4	763.3	764.1
175°	767.2	766.4	765.5	764.6	764.3	764.5	764.9	765.1	765.3	766.2	767.1
177.5°	767.9	767.2	766.6	765.9	765.6	765.6	765.8	765.9	766.0	766.7	767.4
180°	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4



TEST NUMBER: P331531-927

CATALOG NUMBER: S122DIW-S675D710U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3
2.5°	1091.4	1095.9	1095.9	1096.5	1101.8	1101.1	1100.7
5°	1161.4	1168.3	1169.1	1176.4	1181.2	1179.6	1175.2
7.5°	1227.5	1240.3	1250.0	1255.4	1261.8	1265.7	1264.0
10°	1279.9	1298.5	1309.9	1317.6	1326.8	1333.7	1331.3
12.5°	1327.5	1349.6	1365.2	1378.3	1379.6	1388.4	1382.4
15°	1401.6	1425.1	1427.5	1437.3	1444.9	1444.1	1444.5
17.5°	1426.2	1433.7	1435.2	1435.4	1435.5	1432.7	1426.6
20°	1417.4	1414.6	1407.7	1402.5	1393.1	1391.9	1383.9
22.5°	1376.0	1367.0	1349.8	1338.4	1323.9	1320.1	1317.9
25°	1294.5	1274.6	1247.1	1220.8	1213.6	1199.4	1203.5
27.5°	1182.6	1151.8	1122.0	1100.6	1081.2	1060.1	1066.1
30°	1104.0	1069.2	1027.1	994.8	974.2	953.9	950.3
32.5°	1010.2	959.3	912.3	883.8	852.2	839.5	825.5
35°	848.4	798.7	752.2	712.2	689.1	671.3	655.1
37.5°	702.9	645.6	608.2	575.7	559.0	548.8	551.4
40°	612.7	562.5	535.0	510.3	495.0	487.7	489.3
42.5°	539.6	502.0	479.3	462.5	451.6	447.6	446.6
45°	456.5	435.5	416.9	407.3	402.0	397.5	394.7
47.5°	400.0	382.8	372.3	366.5	361.9	357.4	357.4
50°	366.0	354.7	347.4	341.3	337.7	334.5	337.2
52.5°	340.1	329.7	322.5	317.0	315.7	312.8	312.7
55°	301.7	293.6	288.4	283.4	281.1	279.4	277.4
57.5°	266.7	259.0	254.2	251.1	246.5	244.9	244.2
60°	241.9	235.8	230.9	226.9	224.8	221.6	221.6
62.5°	218.9	212.8	208.3	205.2	201.8	200.6	200.9
65°	185.6	180.8	176.3	173.1	172.3	169.8	170.6
67.5°	155.0	151.8	147.1	145.4	143.8	142.5	141.6
70°	134.7	131.4	129.0	126.6	125.3	125.3	125.3
72.5°	117.5	113.6	112.2	109.1	109.8	108.5	107.3
75°	91.0	88.6	87.4	86.1	84.1	84.1	84.1
77.5°	66.9	66.2	64.8	63.5	63.0	62.6	62.7
80°	51.7	51.3	50.5	50.5	49.7	49.4	48.6
82.5°	39.8	38.7	38.3	37.9	37.8	37.7	37.5
85°	22.7	21.9	21.9	22.3	21.5	21.5	21.9
87.5°	11.3	11.4	11.2	11.2	11.6	11.3	11.4
90°	12.9	13.5	14.0	14.3	14.5	14.7	15.0
92.5°	13.9	14.2	14.4	14.5	14.7	14.8	15.0
95°	23.4	24.1	24.3	24.2	24.1	24.0	23.8
97.5°	30.4	30.9	31.2	31.4	31.5	31.7	31.8
100°	34.5	35.6	36.2	36.4	36.7	36.9	37.2
102.5°	36.4	37.6	38.4	38.8	39.1	39.5	39.8
105°	37.9	39.2	40.2	40.6	41.2	41.7	42.1
107.5°	43.3	41.8	41.4	41.9	42.4	42.9	43.3
110°	60.0	47.8	41.8	42.3	42.9	43.3	43.8



TEST NUMBER: P331531-927

CATALOG NUMBER: S122DIW-S675D710U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	110.0	65.0	42.7	43.1	43.5	43.9	44.3
115°	171.0	113.9	81.0	72.1	63.2	54.3	45.5
117.5°	337.5	323.8	302.3	273.1	244.0	214.8	185.7
120°	410.9	412.4	404.8	388.2	371.5	354.9	338.3
122.5°	435.3	436.3	435.1	431.8	428.6	425.4	422.2
125°	471.2	472.1	472.7	473.0	473.4	473.8	474.1
127.5°	504.8	506.0	506.7	506.8	506.8	506.9	507.0
130°	525.9	527.3	527.9	527.8	527.7	527.5	527.4
132.5°	546.2	547.3	547.9	547.7	547.6	547.5	547.4
135°	575.4	576.7	577.2	576.9	576.7	576.5	576.2
137.5°	602.5	603.8	604.2	603.7	603.3	602.9	602.5
140°	620.0	621.2	621.4	620.8	620.1	619.5	618.9
142.5°	636.1	637.2	637.3	636.8	636.1	635.5	634.9
145°	658.6	659.5	659.7	659.0	658.4	657.7	657.2
147.5°	678.2	678.8	678.9	678.3	677.9	677.3	676.8
150°	690.5	691.2	691.3	690.6	690.0	689.4	688.8
152.5°	701.6	702.3	702.3	701.4	700.6	699.8	698.9
155°	716.5	717.2	717.1	716.1	715.2	714.2	713.2
157.5°	729.2	730.1	730.0	729.0	728.1	727.1	726.1
160°	736.5	737.2	737.1	736.3	735.4	734.6	733.7
162.5°	743.4	744.3	744.2	743.1	742.0	740.9	739.9
165°	751.8	752.7	752.7	751.8	751.0	750.1	749.2
167.5°	758.8	759.6	759.5	758.4	757.3	756.2	755.1
170°	762.3	763.2	763.1	762.0	760.9	759.8	758.7
172.5°	765.0	765.9	765.7	764.6	763.5	762.4	761.3
175°	767.9	768.7	768.6	767.3	766.1	764.9	763.7
177.5°	768.0	768.7	768.7	767.8	766.8	766.0	765.1
180°	766.4	766.4	766.4	766.4	766.4	766.4	766.4

(END OF REPORT)